

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331769-927

Luminaire Tested: **S122RDIW-S290D710U927-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331769-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIW-S290D710U927-4F0-1E-UDD-A  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 710 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3142.9 lumens  
Efficiency: N/A  
Efficacy: 103.4 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 30.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331769-927

CATALOG NUMBER: S122RDIW-S290D710U927-4F0-1E-UDD-A

### Luminous Intensity Polar Plot



— 0°-180°    - - 45°-225°    ··· 90°-270°    - · - 135°-315°



TEST NUMBER: P331769-927

CATALOG NUMBER: S122RDIW-S290D710U927-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36	29
1	93	89	86	83	84	80	77	75	63	61	59	47	46	45	33	32	32	25
2	85	79	73	68	76	71	66	62	56	53	50	42	40	38	29	28	27	22
3	78	69	63	57	70	63	57	52	50	46	42	38	35	33	26	25	24	19
4	72	62	54	49	64	56	49	45	44	40	36	34	31	29	24	22	21	17
5	66	55	48	42	59	50	43	38	40	35	32	31	27	25	22	20	18	15
6	61	49	42	36	54	45	38	34	36	31	28	28	25	22	20	18	17	13
7	56	45	37	32	50	41	34	30	33	28	25	25	22	20	18	16	15	12
8	52	41	33	28	47	37	31	26	30	25	22	23	20	18	17	15	13	11
9	49	37	30	25	44	34	28	23	27	23	20	21	18	16	16	14	12	10
10	45	34	27	23	41	31	25	21	25	21	18	20	17	14	15	13	11	9

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	8360	8360	8360	8360
5°	9339	8413	7460	8413
10°	10362	8355	6466	8355
15°	10870	8232	5095	8232
20°	9424	8052	4409	8052
25°	6180	7803	3935	7803
30°	4161	7500	3563	7500
35°	3370	7121	3213	7121
40°	2995	6709	2974	6709
45°	2710	6224	2653	6224
50°	2467	5745	2459	5745
55°	2320	5210	2291	5210
60°	1941	4724	1918	4724
65°	1639	4290	1857	4290
70°	1511	3829	1751	3829
75°	1416	3337	1616	3337
80°	1302	2743	1432	2743
85°	1204	2167	1260	2167



TEST NUMBER: P331769-927

CATALOG NUMBER: S122RDIW-S290D710U927-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	49.1	1.6
10°-20°	136.8	4.4
20°-30°	176.3	5.6
30°-40°	167.5	5.3
40°-50°	143.5	4.6
50°-60°	109.3	3.5
60°-70°	69.1	2.2
70°-80°	34.5	1.1
80°-90°	10.9	0.3
90°-100°	25.6	0.8
100°-110°	93.8	3.0
110°-120°	250.6	8.0
120°-130°	413.7	13.2
130°-140°	440.0	14.0
140°-150°	408.9	13.0
150°-160°	328.8	10.5
160°-170°	211.9	6.7
170°-180°	72.9	2.3
0°-30°	362.2	11.5
0°-40°	529.7	16.9
0°-60°	782.5	24.9
0°-90°	896.9	28.5
90°-120°	369.9	11.8
90°-150°	1632.5	51.9
90°-180°	2246.0	71.5
0°-180°	3142.9	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	518	518	518	518	518	
5°	576	519	460	519	576	57
15°	650	492	305	492	650	175
25°	347	438	221	438	347	165
35°	171	361	163	361	171	109
45°	119	273	116	273	119	92
55°	82	185	81	185	82	72
65°	43	112	49	112	43	44
75°	23	54	26	54	23	24
85°	6	12	7	12	6	7
90°	15	1	15	1	15	7
95°	24	36	24	36	24	22
105°	42	169	42	169	42	44
115°	46	319	46	319	46	114
125°	474	451	474	451	474	410
135°	576	558	576	558	576	444
145°	657	647	657	647	657	411
155°	713	713	713	713	713	329
165°	749	751	749	751	749	212
175°	764	768	764	768	764	73
180°	766	766	766	766	766	



TEST NUMBER: P331769-927

CATALOG NUMBER: S122RDIW-S290D710U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8
2.5°	538.9	539.3	539.8	538.8	538.8	537.9	536.0	534.6	530.5	530.0	530.0
5°	576.2	575.8	576.6	574.2	571.0	570.2	566.8	562.3	557.6	552.5	551.4
7.5°	613.2	612.7	611.2	610.9	608.4	602.9	597.5	591.6	583.8	576.2	572.4
10°	632.0	637.9	634.3	628.0	629.2	620.8	616.3	608.6	602.1	590.7	588.3
12.5°	650.4	652.8	651.6	648.0	646.4	640.6	634.5	627.7	615.8	605.6	596.8
15°	650.3	653.7	654.7	653.6	654.4	654.1	650.9	645.3	634.9	623.7	613.9
17.5°	602.3	604.7	610.6	614.6	619.6	630.3	635.6	637.5	636.0	629.6	622.8
20°	548.5	544.5	561.1	569.5	576.7	594.7	610.2	616.2	625.7	625.5	623.7
22.5°	472.1	473.1	488.8	498.8	519.8	537.9	555.5	577.8	596.3	608.5	615.6
25°	346.9	353.8	369.4	383.1	406.5	440.0	470.4	505.6	538.9	565.2	590.3
27.5°	260.5	261.1	273.5	286.1	300.0	327.4	365.8	407.8	455.3	494.5	539.5
30°	223.2	222.0	227.3	235.0	246.9	268.2	296.9	338.3	385.6	444.7	497.2
32.5°	196.6	196.7	200.7	206.4	216.2	230.5	250.3	283.9	328.6	386.7	448.2
35°	171.0	170.8	173.6	177.8	181.9	191.1	204.6	222.2	253.0	307.1	370.1
37.5°	152.5	153.3	154.7	157.3	161.8	167.0	175.1	187.0	208.8	240.9	293.8
40°	142.1	142.5	144.5	146.6	149.3	153.3	159.9	169.5	185.5	211.0	249.8
42.5°	132.7	133.0	134.4	136.4	138.6	142.5	148.1	156.3	169.3	189.2	221.1
45°	118.7	118.7	120.0	120.9	123.3	126.8	131.3	138.2	147.2	161.9	183.2
47.5°	105.8	105.8	106.6	108.1	109.6	112.4	116.8	122.5	129.0	140.4	158.5
50°	98.2	98.5	98.9	100.2	101.2	103.6	107.1	111.9	118.7	127.6	142.7
52.5°	92.2	92.1	92.8	93.3	94.0	95.7	98.3	102.6	108.7	116.4	128.9
55°	82.4	81.7	82.8	83.7	84.2	84.9	86.3	89.0	94.3	100.8	110.1
57.5°	70.2	69.9	70.7	71.5	73.2	75.1	76.4	78.0	80.7	85.4	94.7
60°	60.1	60.1	61.7	62.3	64.2	66.8	69.3	70.7	73.4	76.4	83.3
62.5°	51.2	51.3	52.0	52.6	53.7	56.8	60.4	63.5	66.1	69.0	73.5
65°	42.9	43.2	43.2	43.6	44.3	45.0	46.4	49.0	53.5	57.6	61.0
67.5°	36.4	36.4	36.6	36.9	37.1	37.9	38.5	39.6	40.6	44.5	48.8
70°	32.0	32.6	32.4	32.7	33.0	33.3	34.0	34.5	36.2	37.1	39.6
72.5°	28.0	28.4	28.4	28.6	29.1	29.2	29.7	30.3	31.3	32.0	33.4
75°	22.7	22.5	22.7	23.1	23.2	23.4	23.4	24.1	24.6	25.3	26.3
77.5°	17.5	17.7	17.7	17.7	17.7	18.1	18.0	18.3	18.9	19.3	19.6
80°	14.0	14.2	14.0	14.2	14.4	14.6	14.4	14.6	15.1	15.4	15.4
82.5°	10.9	10.9	11.0	11.0	11.1	11.1	11.4	11.4	11.8	11.7	11.9
85°	6.5	6.3	6.3	6.3	6.5	6.7	6.5	6.5	6.7	6.7	6.7
87.5°	5.3	5.4	5.3	5.3	5.2	5.1	5.1	5.1	4.8	4.8	4.4
90°	15.0	14.7	14.5	14.3	14.0	13.5	12.9	12.4	11.7	11.1	10.1
92.5°	15.0	14.8	14.7	14.5	14.4	14.2	13.9	13.5	13.2	12.8	12.4
95°	23.8	24.0	24.1	24.2	24.3	24.1	23.4	22.9	22.3	21.6	20.8
97.5°	31.8	31.7	31.5	31.4	31.2	30.9	30.4	29.9	29.5	28.9	26.9
100°	37.2	36.9	36.7	36.4	36.2	35.6	34.5	33.6	32.6	31.6	29.5
102.5°	39.8	39.5	39.1	38.8	38.4	37.6	36.4	35.1	33.7	32.5	50.0
105°	42.1	41.7	41.2	40.6	40.2	39.2	37.9	36.5	35.2	33.8	67.5
107.5°	43.3	42.9	42.4	41.9	41.4	41.8	43.3	44.6	45.9	47.4	87.7
110°	43.8	43.3	42.9	42.3	41.8	47.8	60.0	72.4	84.8	97.0	132.7



TEST NUMBER: P331769-927

CATALOG NUMBER: S122RDIW-S290D710U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	44.3	43.9	43.5	43.1	42.7	65.0	110.0	154.9	199.9	244.8	253.6
115°	45.5	54.3	63.2	72.1	81.0	113.9	171.0	228.1	285.1	342.1	339.1
117.5°	185.7	214.8	244.0	273.1	302.3	323.8	337.5	351.4	365.2	379.0	376.8
120°	338.3	354.9	371.5	388.2	404.8	412.4	410.9	409.5	408.0	406.5	404.3
122.5°	422.2	425.4	428.6	431.8	435.1	436.3	435.3	434.4	433.6	432.7	430.2
125°	474.1	473.8	473.4	473.0	472.7	472.1	471.2	470.3	469.4	468.6	466.3
127.5°	507.0	506.9	506.8	506.8	506.7	506.0	504.8	503.5	502.2	501.0	499.2
130°	527.4	527.5	527.7	527.8	527.9	527.3	525.9	524.6	523.2	521.9	520.5
132.5°	547.4	547.5	547.6	547.7	547.9	547.3	546.2	545.0	543.8	542.7	541.4
135°	576.2	576.5	576.7	576.9	577.2	576.7	575.4	574.3	573.0	571.8	570.7
137.5°	602.5	602.9	603.3	603.7	604.2	603.8	602.5	601.3	600.2	599.0	597.7
140°	618.9	619.5	620.1	620.8	621.4	621.2	620.0	618.9	617.8	616.7	615.3
142.5°	634.9	635.5	636.1	636.8	637.3	637.2	636.1	635.1	634.1	633.1	631.5
145°	657.2	657.7	658.4	659.0	659.7	659.5	658.6	657.7	657.0	656.1	653.9
147.5°	676.8	677.3	677.9	678.3	678.9	678.8	678.2	677.6	676.9	676.2	674.1
150°	688.8	689.4	690.0	690.6	691.3	691.2	690.5	689.7	689.0	688.2	686.3
152.5°	698.9	699.8	700.6	701.4	702.3	702.3	701.6	700.8	700.1	699.3	697.4
155°	713.2	714.2	715.2	716.1	717.1	717.2	716.5	715.7	715.0	714.3	712.8
157.5°	726.1	727.1	728.1	729.0	730.0	730.1	729.2	728.4	727.5	726.7	725.6
160°	733.7	734.6	735.4	736.3	737.1	737.2	736.5	735.7	735.0	734.3	733.5
162.5°	739.9	740.9	742.0	743.1	744.2	744.3	743.4	742.6	741.7	740.9	740.3
165°	749.2	750.1	751.0	751.8	752.7	752.7	751.8	751.0	750.1	749.2	748.8
167.5°	755.1	756.2	757.3	758.4	759.5	759.6	758.8	758.0	757.1	756.2	755.9
170°	758.7	759.8	760.9	762.0	763.1	763.2	762.3	761.5	760.7	759.8	759.5
172.5°	761.3	762.4	763.5	764.6	765.7	765.9	765.0	764.1	763.3	762.4	762.2
175°	763.7	764.9	766.1	767.3	768.6	768.7	767.9	767.1	766.2	765.3	765.1
177.5°	765.1	766.0	766.8	767.8	768.7	768.7	768.0	767.4	766.7	766.0	765.9
180°	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4



TEST NUMBER: P331769-927

CATALOG NUMBER: S122RDIW-S290D710U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8
2.5°	530.3	529.1	528.1	525.5	524.2	521.3	520.9	520.8	517.1	513.4	512.4
5°	548.5	545.6	541.3	536.2	531.0	525.6	522.0	519.1	511.9	505.1	501.1
7.5°	566.8	560.6	553.2	543.7	535.7	526.8	520.1	514.2	504.0	494.2	487.6
10°	580.5	570.5	560.5	547.4	537.1	527.0	517.7	509.6	498.1	485.1	475.9
12.5°	589.0	577.9	564.3	551.4	538.1	525.3	512.8	502.4	488.9	475.5	464.6
15°	600.5	588.6	572.0	553.7	536.6	519.8	505.5	492.5	474.9	458.8	445.5
17.5°	609.9	593.5	575.8	554.5	534.7	513.5	495.0	478.4	458.8	439.4	423.7
20°	612.9	596.7	576.2	554.9	531.6	506.5	486.6	468.6	447.5	426.4	408.4
22.5°	611.0	598.4	575.6	550.2	526.2	500.1	477.5	456.6	433.2	411.8	390.9
25°	598.3	594.0	572.4	544.7	517.4	487.0	460.8	438.0	411.4	388.3	365.7
27.5°	568.7	578.1	564.7	535.1	504.7	472.1	442.8	416.8	389.1	363.2	340.6
30°	540.2	561.6	555.9	528.5	494.5	462.5	429.5	402.3	372.9	346.2	323.9
32.5°	501.2	536.5	542.2	519.3	484.1	448.9	414.4	387.4	356.6	328.5	306.7
35°	439.0	491.9	516.3	501.7	466.4	428.4	392.8	361.3	330.3	302.7	281.1
37.5°	365.0	437.0	477.5	478.6	446.2	406.7	367.9	336.6	304.9	277.7	254.4
40°	316.9	395.0	447.7	459.4	432.1	389.4	350.1	318.3	287.4	260.7	233.9
42.5°	273.7	351.5	416.3	436.7	414.9	372.6	333.2	299.9	269.8	244.6	217.2
45°	221.3	289.4	360.8	397.1	385.1	345.9	304.3	272.6	244.4	222.6	196.3
47.5°	186.7	234.6	303.8	352.9	352.8	317.0	276.0	245.7	219.5	199.1	177.8
50°	167.0	208.7	267.2	323.0	327.6	297.6	258.7	228.7	204.2	182.8	165.7
52.5°	149.2	183.7	236.2	289.8	303.1	277.0	239.3	211.6	187.8	168.1	153.5
55°	126.1	152.8	192.7	242.7	262.9	244.5	211.0	185.1	165.9	149.3	136.7
57.5°	106.7	126.7	158.8	199.0	222.4	211.0	183.3	162.2	145.8	130.8	120.9
60°	94.5	110.8	138.0	171.7	197.6	189.5	165.9	146.3	132.3	119.3	110.0
62.5°	82.9	97.0	120.3	147.7	171.3	168.0	148.8	132.3	120.0	108.2	100.3
65°	66.8	77.0	95.2	116.6	135.7	137.3	123.4	112.3	101.3	92.0	84.9
67.5°	53.2	59.9	72.6	90.7	105.0	110.1	101.6	93.1	84.4	77.2	71.1
70°	44.8	50.2	59.6	74.1	87.3	92.7	87.8	81.1	73.6	67.7	62.4
72.5°	36.3	41.6	48.5	59.2	70.4	76.3	74.5	69.8	63.7	58.7	53.8
75°	27.3	29.0	33.7	40.9	49.7	54.7	55.9	53.5	48.6	44.8	41.9
77.5°	20.2	21.2	23.4	27.2	33.0	37.5	39.3	39.0	35.6	33.5	30.7
80°	16.2	16.7	17.8	19.4	23.8	28.3	29.5	29.5	27.2	26.3	23.6
82.5°	12.3	12.7	13.4	14.3	16.2	20.2	21.6	21.9	20.4	19.3	17.1
85°	7.1	6.8	7.2	7.8	8.1	9.2	11.3	11.7	11.3	9.9	9.3
87.5°	4.3	4.2	4.0	3.6	3.5	3.4	3.8	4.3	4.0	3.8	3.8
90°	9.1	8.2	7.1	5.9	4.6	3.2	1.9	0.6	1.9	3.2	4.6
92.5°	11.9	11.4	10.9	10.7	10.9	10.9	11.1	11.2	11.1	10.9	10.9
95°	19.9	19.0	18.1	19.8	23.8	27.9	32.0	36.0	32.0	27.9	23.8
97.5°	25.0	23.0	21.0	25.7	37.2	48.6	60.0	71.5	60.0	48.6	37.2
100°	27.4	25.3	23.2	30.7	47.5	64.4	81.3	98.2	81.3	64.4	47.5
102.5°	67.6	85.1	102.6	113.1	116.7	120.3	123.9	127.5	123.9	120.3	116.7
105°	101.1	134.8	168.4	183.4	179.7	176.0	172.3	168.6	172.3	176.0	179.7
107.5°	128.1	168.4	208.7	227.4	224.4	221.5	218.5	215.5	218.5	221.5	224.4
110°	168.3	203.9	239.5	256.0	253.4	250.9	248.3	245.7	248.3	250.9	253.4





TEST NUMBER: P331769-927

CATALOG NUMBER: S122RDIW-S290D710U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	262.4	271.2	280.0	283.2	280.9	278.7	276.4	274.1	276.4	278.7	280.9
115°	336.0	333.0	329.9	327.3	325.2	323.1	321.0	318.9	321.0	323.1	325.2
117.5°	374.8	372.6	370.5	368.3	365.9	363.6	361.2	358.9	361.2	363.6	365.9
120°	402.0	399.8	397.6	395.6	393.7	391.9	390.1	388.2	390.1	391.9	393.7
122.5°	427.9	425.4	423.0	420.8	418.9	416.9	415.0	413.0	415.0	416.9	418.9
125°	463.9	461.6	459.2	457.2	455.7	454.1	452.5	450.8	452.5	454.1	455.7
127.5°	497.5	495.7	494.0	492.3	490.4	488.7	486.9	485.1	486.9	488.7	490.4
130°	519.1	517.8	516.4	514.8	512.8	510.8	508.8	506.8	508.8	510.8	512.8
132.5°	540.0	538.6	537.3	535.8	534.1	532.4	530.8	529.1	530.8	532.4	534.1
135°	569.6	568.5	567.4	565.8	563.8	561.8	559.8	557.9	559.8	561.8	563.8
137.5°	596.4	595.2	593.9	592.6	591.2	589.9	588.4	587.1	588.4	589.9	591.2
140°	613.9	612.6	611.2	610.1	609.1	608.1	607.1	606.2	607.1	608.1	609.1
142.5°	630.0	628.4	626.9	625.7	624.8	623.9	623.0	622.1	623.0	623.9	624.8
145°	651.9	649.7	647.7	646.7	646.8	647.0	647.1	647.2	647.1	647.0	646.8
147.5°	672.1	670.0	668.0	667.2	667.7	668.1	668.6	669.0	668.6	668.1	667.7
150°	684.3	682.3	680.3	679.8	680.6	681.5	682.4	683.3	682.4	681.5	680.6
152.5°	695.5	693.7	691.8	691.3	692.3	693.3	694.3	695.2	694.3	693.3	692.3
155°	711.3	709.9	708.4	708.2	709.3	710.4	711.5	712.6	711.5	710.4	709.3
157.5°	724.6	723.6	722.5	722.5	723.4	724.4	725.3	726.3	725.3	724.4	723.4
160°	732.8	732.1	731.3	731.3	732.1	732.8	733.5	734.3	733.5	732.8	732.1
162.5°	739.7	738.9	738.3	738.4	739.1	739.9	740.6	741.3	740.6	739.9	739.1
165°	748.5	748.1	747.7	747.9	748.7	749.4	750.1	750.9	750.1	749.4	748.7
167.5°	755.5	755.2	754.9	755.0	755.7	756.5	757.2	758.0	757.2	756.5	755.7
170°	759.3	759.0	758.8	759.0	759.8	760.5	761.2	762.0	761.2	760.5	759.8
172.5°	761.9	761.7	761.4	761.7	762.4	763.2	763.9	764.6	763.9	763.2	762.4
175°	764.9	764.5	764.3	764.6	765.5	766.4	767.2	768.1	767.2	766.4	765.5
177.5°	765.8	765.6	765.6	765.9	766.6	767.2	767.9	768.7	767.9	767.2	766.6
180°	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4



TEST NUMBER: P331769-927

CATALOG NUMBER: S122RDIW-S290D710U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8
2.5°	510.6	509.5	507.6	504.8	503.0	500.0	498.0	499.2	499.5	499.2	498.9
5°	496.9	493.1	487.8	482.8	478.1	473.1	470.2	469.0	466.4	465.0	464.2
7.5°	480.2	473.7	466.4	457.6	450.1	442.3	438.3	436.3	431.2	428.4	426.0
10°	467.9	457.6	450.2	438.7	431.7	421.4	414.4	414.6	407.6	403.6	400.8
12.5°	454.2	442.9	430.6	420.3	410.5	402.3	393.8	390.4	382.9	379.1	371.4
15°	431.5	418.4	405.4	391.4	381.5	368.7	356.5	341.5	329.5	319.0	316.2
17.5°	406.8	390.5	377.5	361.0	344.0	322.6	308.4	299.7	292.5	286.9	282.8
20°	389.8	373.2	359.3	334.5	311.6	297.1	286.7	280.0	272.4	266.5	263.2
22.5°	371.9	354.7	335.7	308.0	290.2	278.5	269.3	261.6	256.4	251.8	248.8
25°	346.6	327.6	296.5	277.5	263.1	250.8	244.4	239.7	234.3	228.0	225.1
27.5°	319.8	289.8	267.4	253.2	239.5	231.6	225.7	218.7	213.9	211.0	208.0
30°	299.8	269.7	252.3	236.8	227.1	218.2	211.4	207.5	202.8	198.0	196.0
32.5°	277.5	253.5	236.7	223.9	214.0	206.4	201.1	194.6	191.3	188.3	184.2
35°	249.8	231.6	216.3	205.9	196.5	190.4	184.1	180.3	174.2	171.7	170.1
37.5°	226.3	210.6	199.2	188.1	180.7	174.0	170.1	164.1	161.4	157.9	154.5
40°	213.0	197.6	186.6	177.6	169.3	164.3	159.5	154.6	150.6	149.0	144.9
42.5°	199.6	187.0	175.9	166.1	160.6	155.2	149.1	145.5	141.4	138.8	136.3
45°	180.9	169.7	160.3	152.3	146.1	140.5	136.6	130.6	128.3	123.1	120.9
47.5°	164.5	154.1	145.1	137.4	131.5	127.9	122.1	117.4	113.7	110.4	107.7
50°	152.8	144.1	135.5	128.7	123.3	118.0	112.1	109.8	104.0	102.3	100.8
52.5°	142.1	133.9	126.0	119.3	113.9	108.8	103.6	100.5	96.6	95.1	93.9
55°	127.2	119.3	111.8	105.8	100.4	95.2	92.0	88.2	86.3	85.1	83.7
57.5°	112.3	105.1	99.3	93.3	87.9	83.7	80.0	77.7	75.9	74.2	72.5
60°	102.7	95.9	90.7	85.1	79.5	76.1	73.3	70.5	68.4	65.8	65.1
62.5°	92.7	86.7	81.9	76.4	71.6	68.5	65.8	63.2	60.6	57.0	55.9
65°	78.8	74.1	69.1	64.6	60.3	57.2	53.2	50.4	49.3	49.0	48.8
67.5°	66.3	61.9	57.5	52.9	49.0	46.2	44.1	43.7	42.9	42.8	42.2
70°	57.9	53.8	49.5	45.2	41.4	40.9	40.2	39.4	38.5	38.2	37.8
72.5°	50.5	46.2	41.8	38.4	36.8	36.1	35.4	34.6	34.1	33.7	33.5
75°	38.7	34.7	31.8	30.6	29.7	29.2	28.0	27.6	27.2	26.6	26.5
77.5°	27.9	25.6	24.3	23.5	22.6	22.0	21.4	20.8	20.4	20.4	20.0
80°	21.2	20.1	19.3	18.1	17.8	17.1	17.0	16.4	16.6	16.0	16.0
82.5°	16.5	15.1	14.3	13.9	13.5	12.9	12.8	12.5	12.5	12.1	12.1
85°	8.5	8.1	7.8	7.4	7.4	6.8	7.1	6.8	6.8	6.5	6.3
87.5°	4.0	4.0	4.0	4.1	4.4	4.4	4.5	4.5	4.6	4.8	4.7
90°	5.9	7.1	8.2	9.1	10.1	11.1	11.7	12.4	12.9	13.5	14.0
92.5°	10.7	10.9	11.4	11.9	12.4	12.8	13.2	13.5	13.9	14.2	14.4
95°	19.8	18.1	19.0	19.9	20.8	21.6	22.3	22.9	23.4	24.1	24.3
97.5°	25.7	21.0	23.0	25.0	26.9	28.9	29.5	29.9	30.4	30.9	31.2
100°	30.7	23.2	25.3	27.4	29.5	31.6	32.6	33.6	34.5	35.6	36.2
102.5°	113.1	102.6	85.1	67.6	50.0	32.5	33.7	35.1	36.4	37.6	38.4
105°	183.4	168.4	134.8	101.1	67.5	33.8	35.2	36.5	37.9	39.2	40.2
107.5°	227.4	208.7	168.4	128.1	87.7	47.4	45.9	44.6	43.3	41.8	41.4
110°	256.0	239.5	203.9	168.3	132.7	97.0	84.8	72.4	60.0	47.8	41.8



TEST NUMBER: P331769-927

CATALOG NUMBER: S122RDIW-S290D710U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	283.2	280.0	271.2	262.4	253.6	244.8	199.9	154.9	110.0	65.0	42.7
115°	327.3	329.9	333.0	336.0	339.1	342.1	285.1	228.1	171.0	113.9	81.0
117.5°	368.3	370.5	372.6	374.8	376.8	379.0	365.2	351.4	337.5	323.8	302.3
120°	395.6	397.6	399.8	402.0	404.3	406.5	408.0	409.5	410.9	412.4	404.8
122.5°	420.8	423.0	425.4	427.9	430.2	432.7	433.6	434.4	435.3	436.3	435.1
125°	457.2	459.2	461.6	463.9	466.3	468.6	469.4	470.3	471.2	472.1	472.7
127.5°	492.3	494.0	495.7	497.5	499.2	501.0	502.2	503.5	504.8	506.0	506.7
130°	514.8	516.4	517.8	519.1	520.5	521.9	523.2	524.6	525.9	527.3	527.9
132.5°	535.8	537.3	538.6	540.0	541.4	542.7	543.8	545.0	546.2	547.3	547.9
135°	565.8	567.4	568.5	569.6	570.7	571.8	573.0	574.3	575.4	576.7	577.2
137.5°	592.6	593.9	595.2	596.4	597.7	599.0	600.2	601.3	602.5	603.8	604.2
140°	610.1	611.2	612.6	613.9	615.3	616.7	617.8	618.9	620.0	621.2	621.4
142.5°	625.7	626.9	628.4	630.0	631.5	633.1	634.1	635.1	636.1	637.2	637.3
145°	646.7	647.7	649.7	651.9	653.9	656.1	657.0	657.7	658.6	659.5	659.7
147.5°	667.2	668.0	670.0	672.1	674.1	676.2	676.9	677.6	678.2	678.8	678.9
150°	679.8	680.3	682.3	684.3	686.3	688.2	689.0	689.7	690.5	691.2	691.3
152.5°	691.3	691.8	693.7	695.5	697.4	699.3	700.1	700.8	701.6	702.3	702.3
155°	708.2	708.4	709.9	711.3	712.8	714.3	715.0	715.7	716.5	717.2	717.1
157.5°	722.5	722.5	723.6	724.6	725.6	726.7	727.5	728.4	729.2	730.1	730.0
160°	731.3	731.3	732.1	732.8	733.5	734.3	735.0	735.7	736.5	737.2	737.1
162.5°	738.4	738.3	738.9	739.7	740.3	740.9	741.7	742.6	743.4	744.3	744.2
165°	747.9	747.7	748.1	748.5	748.8	749.2	750.1	751.0	751.8	752.7	752.7
167.5°	755.0	754.9	755.2	755.5	755.9	756.2	757.1	758.0	758.8	759.6	759.5
170°	759.0	758.8	759.0	759.3	759.5	759.8	760.7	761.5	762.3	763.2	763.1
172.5°	761.7	761.4	761.7	761.9	762.2	762.4	763.3	764.1	765.0	765.9	765.7
175°	764.6	764.3	764.5	764.9	765.1	765.3	766.2	767.1	767.9	768.7	768.6
177.5°	765.9	765.6	765.6	765.8	765.9	766.0	766.7	767.4	768.0	768.7	768.7
180°	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4



TEST NUMBER: P331769-927

CATALOG NUMBER: S122RDIW-S290D710U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8
2.5°	497.3	497.6	497.2	497.4	497.2	497.6	497.3	498.9	499.2	499.5	499.2
5°	463.3	461.2	460.8	460.3	460.8	461.2	463.3	464.2	465.0	466.4	469.0
7.5°	422.9	422.6	421.6	420.3	421.6	422.6	422.9	426.0	428.4	431.2	436.3
10°	396.8	395.9	395.7	394.4	395.7	395.9	396.8	400.8	403.6	407.6	414.6
12.5°	366.2	360.4	359.9	356.7	359.9	360.4	366.2	371.4	379.1	382.9	390.4
15°	311.9	310.8	307.1	304.8	307.1	310.8	311.9	316.2	319.0	329.5	341.5
17.5°	280.7	277.2	276.1	275.6	276.1	277.2	280.7	282.8	286.9	292.5	299.7
20°	260.7	257.5	257.0	256.6	257.0	257.5	260.7	263.2	266.5	272.4	280.0
22.5°	246.9	243.5	242.2	241.1	242.2	243.5	246.9	248.8	251.8	256.4	261.6
25°	223.3	222.0	221.3	220.9	221.3	222.0	223.3	225.1	228.0	234.3	239.7
27.5°	204.9	202.1	201.5	200.6	201.5	202.1	204.9	208.0	211.0	213.9	218.7
30°	194.3	193.5	192.2	191.1	192.2	193.5	194.3	196.0	198.0	202.8	207.5
32.5°	182.0	181.2	180.1	179.6	180.1	181.2	182.0	184.2	188.3	191.3	194.6
35°	168.3	165.7	164.6	163.0	164.6	165.7	168.3	170.1	171.7	174.2	180.3
37.5°	153.8	152.4	150.9	151.5	150.9	152.4	153.8	154.5	157.9	161.4	164.1
40°	142.5	141.6	141.2	141.1	141.2	141.6	142.5	144.9	149.0	150.6	154.6
42.5°	133.6	131.1	130.2	130.2	130.2	131.1	133.6	136.3	138.8	141.4	145.5
45°	120.0	117.7	116.1	116.2	116.1	117.7	120.0	120.9	123.1	128.3	130.6
47.5°	106.2	106.1	105.0	105.4	105.0	106.1	106.2	107.7	110.4	113.7	117.4
50°	99.5	98.5	97.7	97.9	97.7	98.5	99.5	100.8	102.3	104.0	109.8
52.5°	93.2	92.2	91.7	92.4	91.7	92.2	93.2	93.9	95.1	96.6	100.5
55°	82.8	81.7	81.5	81.4	81.5	81.7	82.8	83.7	85.1	86.3	88.2
57.5°	71.1	70.4	69.3	68.9	69.3	70.4	71.1	72.5	74.2	75.9	77.7
60°	62.8	61.4	59.6	59.4	59.6	61.4	62.8	65.1	65.8	68.4	70.5
62.5°	55.1	54.9	54.5	54.5	54.5	54.9	55.1	55.9	57.0	60.6	63.2
65°	48.4	48.2	48.4	48.6	48.4	48.2	48.4	48.8	49.0	49.3	50.4
67.5°	42.1	41.8	41.5	41.7	41.5	41.8	42.1	42.2	42.8	42.9	43.7
70°	37.4	37.2	37.1	37.1	37.1	37.2	37.4	37.8	38.2	38.5	39.4
72.5°	32.8	32.8	32.6	32.5	32.6	32.8	32.8	33.5	33.7	34.1	34.6
75°	26.3	25.9	25.9	25.9	25.9	25.9	26.3	26.5	26.6	27.2	27.6
77.5°	20.0	19.8	19.6	19.5	19.6	19.8	20.0	20.0	20.4	20.4	20.8
80°	15.8	15.7	15.4	15.4	15.4	15.7	15.8	16.0	16.0	16.6	16.4
82.5°	12.1	11.9	11.9	11.7	11.9	11.9	12.1	12.1	12.1	12.5	12.5
85°	6.5	6.7	6.5	6.8	6.5	6.7	6.5	6.3	6.5	6.8	6.8
87.5°	4.8	4.6	4.8	4.8	4.8	4.6	4.8	4.7	4.8	4.6	4.5
90°	14.3	14.5	14.7	15.0	14.7	14.5	14.3	14.0	13.5	12.9	12.4
92.5°	14.5	14.7	14.8	15.0	14.8	14.7	14.5	14.4	14.2	13.9	13.5
95°	24.2	24.1	24.0	23.8	24.0	24.1	24.2	24.3	24.1	23.4	22.9
97.5°	31.4	31.5	31.7	31.8	31.7	31.5	31.4	31.2	30.9	30.4	29.9
100°	36.4	36.7	36.9	37.2	36.9	36.7	36.4	36.2	35.6	34.5	33.6
102.5°	38.8	39.1	39.5	39.8	39.5	39.1	38.8	38.4	37.6	36.4	35.1
105°	40.6	41.2	41.7	42.1	41.7	41.2	40.6	40.2	39.2	37.9	36.5
107.5°	41.9	42.4	42.9	43.3	42.9	42.4	41.9	41.4	41.8	43.3	44.6
110°	42.3	42.9	43.3	43.8	43.3	42.9	42.3	41.8	47.8	60.0	72.4



TEST NUMBER: P331769-927

CATALOG NUMBER: S122RDIW-S290D710U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	43.1	43.5	43.9	44.3	43.9	43.5	43.1	42.7	65.0	110.0	154.9
115°	72.1	63.2	54.3	45.5	54.3	63.2	72.1	81.0	113.9	171.0	228.1
117.5°	273.1	244.0	214.8	185.7	214.8	244.0	273.1	302.3	323.8	337.5	351.4
120°	388.2	371.5	354.9	338.3	354.9	371.5	388.2	404.8	412.4	410.9	409.5
122.5°	431.8	428.6	425.4	422.2	425.4	428.6	431.8	435.1	436.3	435.3	434.4
125°	473.0	473.4	473.8	474.1	473.8	473.4	473.0	472.7	472.1	471.2	470.3
127.5°	506.8	506.8	506.9	507.0	506.9	506.8	506.8	506.7	506.0	504.8	503.5
130°	527.8	527.7	527.5	527.4	527.5	527.7	527.8	527.9	527.3	525.9	524.6
132.5°	547.7	547.6	547.5	547.4	547.5	547.6	547.7	547.9	547.3	546.2	545.0
135°	576.9	576.7	576.5	576.2	576.5	576.7	576.9	577.2	576.7	575.4	574.3
137.5°	603.7	603.3	602.9	602.5	602.9	603.3	603.7	604.2	603.8	602.5	601.3
140°	620.8	620.1	619.5	618.9	619.5	620.1	620.8	621.4	621.2	620.0	618.9
142.5°	636.8	636.1	635.5	634.9	635.5	636.1	636.8	637.3	637.2	636.1	635.1
145°	659.0	658.4	657.7	657.2	657.7	658.4	659.0	659.7	659.5	658.6	657.7
147.5°	678.3	677.9	677.3	676.8	677.3	677.9	678.3	678.9	678.8	678.2	677.6
150°	690.6	690.0	689.4	688.8	689.4	690.0	690.6	691.3	691.2	690.5	689.7
152.5°	701.4	700.6	699.8	698.9	699.8	700.6	701.4	702.3	702.3	701.6	700.8
155°	716.1	715.2	714.2	713.2	714.2	715.2	716.1	717.1	717.2	716.5	715.7
157.5°	729.0	728.1	727.1	726.1	727.1	728.1	729.0	730.0	730.1	729.2	728.4
160°	736.3	735.4	734.6	733.7	734.6	735.4	736.3	737.1	737.2	736.5	735.7
162.5°	743.1	742.0	740.9	739.9	740.9	742.0	743.1	744.2	744.3	743.4	742.6
165°	751.8	751.0	750.1	749.2	750.1	751.0	751.8	752.7	752.7	751.8	751.0
167.5°	758.4	757.3	756.2	755.1	756.2	757.3	758.4	759.5	759.6	758.8	758.0
170°	762.0	760.9	759.8	758.7	759.8	760.9	762.0	763.1	763.2	762.3	761.5
172.5°	764.6	763.5	762.4	761.3	762.4	763.5	764.6	765.7	765.9	765.0	764.1
175°	767.3	766.1	764.9	763.7	764.9	766.1	767.3	768.6	768.7	767.9	767.1
177.5°	767.8	766.8	766.0	765.1	766.0	766.8	767.8	768.7	768.7	768.0	767.4
180°	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4



TEST NUMBER: P331769-927

CATALOG NUMBER: S122RDIW-S290D710U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8
2.5°	498.0	500.0	503.0	504.8	507.6	509.5	510.6	512.4	513.4	517.1	520.8
5°	470.2	473.1	478.1	482.8	487.8	493.1	496.9	501.1	505.1	511.9	519.1
7.5°	438.3	442.3	450.1	457.6	466.4	473.7	480.2	487.6	494.2	504.0	514.2
10°	414.4	421.4	431.7	438.7	450.2	457.6	467.9	475.9	485.1	498.1	509.6
12.5°	393.8	402.3	410.5	420.3	430.6	442.9	454.2	464.6	475.5	488.9	502.4
15°	356.5	368.7	381.5	391.4	405.4	418.4	431.5	445.5	458.8	474.9	492.5
17.5°	308.4	322.6	344.0	361.0	377.5	390.5	406.8	423.7	439.4	458.8	478.4
20°	286.7	297.1	311.6	334.5	359.3	373.2	389.8	408.4	426.4	447.5	468.6
22.5°	269.3	278.5	290.2	308.0	335.7	354.7	371.9	390.9	411.8	433.2	456.6
25°	244.4	250.8	263.1	277.5	296.5	327.6	346.6	365.7	388.3	411.4	438.0
27.5°	225.7	231.6	239.5	253.2	267.4	289.8	319.8	340.6	363.2	389.1	416.8
30°	211.4	218.2	227.1	236.8	252.3	269.7	299.8	323.9	346.2	372.9	402.3
32.5°	201.1	206.4	214.0	223.9	236.7	253.5	277.5	306.7	328.5	356.6	387.4
35°	184.1	190.4	196.5	205.9	216.3	231.6	249.8	281.1	302.7	330.3	361.3
37.5°	170.1	174.0	180.7	188.1	199.2	210.6	226.3	254.4	277.7	304.9	336.6
40°	159.5	164.3	169.3	177.6	186.6	197.6	213.0	233.9	260.7	287.4	318.3
42.5°	149.1	155.2	160.6	166.1	175.9	187.0	199.6	217.2	244.6	269.8	299.9
45°	136.6	140.5	146.1	152.3	160.3	169.7	180.9	196.3	222.6	244.4	272.6
47.5°	122.1	127.9	131.5	137.4	145.1	154.1	164.5	177.8	199.1	219.5	245.7
50°	112.1	118.0	123.3	128.7	135.5	144.1	152.8	165.7	182.8	204.2	228.7
52.5°	103.6	108.8	113.9	119.3	126.0	133.9	142.1	153.5	168.1	187.8	211.6
55°	92.0	95.2	100.4	105.8	111.8	119.3	127.2	136.7	149.3	165.9	185.1
57.5°	80.0	83.7	87.9	93.3	99.3	105.1	112.3	120.9	130.8	145.8	162.2
60°	73.3	76.1	79.5	85.1	90.7	95.9	102.7	110.0	119.3	132.3	146.3
62.5°	65.8	68.5	71.6	76.4	81.9	86.7	92.7	100.3	108.2	120.0	132.3
65°	53.2	57.2	60.3	64.6	69.1	74.1	78.8	84.9	92.0	101.3	112.3
67.5°	44.1	46.2	49.0	52.9	57.5	61.9	66.3	71.1	77.2	84.4	93.1
70°	40.2	40.9	41.4	45.2	49.5	53.8	57.9	62.4	67.7	73.6	81.1
72.5°	35.4	36.1	36.8	38.4	41.8	46.2	50.5	53.8	58.7	63.7	69.8
75°	28.0	29.2	29.7	30.6	31.8	34.7	38.7	41.9	44.8	48.6	53.5
77.5°	21.4	22.0	22.6	23.5	24.3	25.6	27.9	30.7	33.5	35.6	39.0
80°	17.0	17.1	17.8	18.1	19.3	20.1	21.2	23.6	26.3	27.2	29.5
82.5°	12.8	12.9	13.5	13.9	14.3	15.1	16.5	17.1	19.3	20.4	21.9
85°	7.1	6.8	7.4	7.4	7.8	8.1	8.5	9.3	9.9	11.3	11.7
87.5°	4.5	4.4	4.4	4.1	4.0	4.0	4.0	3.8	3.8	4.0	4.3
90°	11.7	11.1	10.1	9.1	8.2	7.1	5.9	4.6	3.2	1.9	0.6
92.5°	13.2	12.8	12.4	11.9	11.4	10.9	10.7	10.9	10.9	11.1	11.2
95°	22.3	21.6	20.8	19.9	19.0	18.1	19.8	23.8	27.9	32.0	36.0
97.5°	29.5	28.9	26.9	25.0	23.0	21.0	25.7	37.2	48.6	60.0	71.5
100°	32.6	31.6	29.5	27.4	25.3	23.2	30.7	47.5	64.4	81.3	98.2
102.5°	33.7	32.5	50.0	67.6	85.1	102.6	113.1	116.7	120.3	123.9	127.5
105°	35.2	33.8	67.5	101.1	134.8	168.4	183.4	179.7	176.0	172.3	168.6
107.5°	45.9	47.4	87.7	128.1	168.4	208.7	227.4	224.4	221.5	218.5	215.5
110°	84.8	97.0	132.7	168.3	203.9	239.5	256.0	253.4	250.9	248.3	245.7



TEST NUMBER: P331769-927

CATALOG NUMBER: S122RDIW-S290D710U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	199.9	244.8	253.6	262.4	271.2	280.0	283.2	280.9	278.7	276.4	274.1
115°	285.1	342.1	339.1	336.0	333.0	329.9	327.3	325.2	323.1	321.0	318.9
117.5°	365.2	379.0	376.8	374.8	372.6	370.5	368.3	365.9	363.6	361.2	358.9
120°	408.0	406.5	404.3	402.0	399.8	397.6	395.6	393.7	391.9	390.1	388.2
122.5°	433.6	432.7	430.2	427.9	425.4	423.0	420.8	418.9	416.9	415.0	413.0
125°	469.4	468.6	466.3	463.9	461.6	459.2	457.2	455.7	454.1	452.5	450.8
127.5°	502.2	501.0	499.2	497.5	495.7	494.0	492.3	490.4	488.7	486.9	485.1
130°	523.2	521.9	520.5	519.1	517.8	516.4	514.8	512.8	510.8	508.8	506.8
132.5°	543.8	542.7	541.4	540.0	538.6	537.3	535.8	534.1	532.4	530.8	529.1
135°	573.0	571.8	570.7	569.6	568.5	567.4	565.8	563.8	561.8	559.8	557.9
137.5°	600.2	599.0	597.7	596.4	595.2	593.9	592.6	591.2	589.9	588.4	587.1
140°	617.8	616.7	615.3	613.9	612.6	611.2	610.1	609.1	608.1	607.1	606.2
142.5°	634.1	633.1	631.5	630.0	628.4	626.9	625.7	624.8	623.9	623.0	622.1
145°	657.0	656.1	653.9	651.9	649.7	647.7	646.7	646.8	647.0	647.1	647.2
147.5°	676.9	676.2	674.1	672.1	670.0	668.0	667.2	667.7	668.1	668.6	669.0
150°	689.0	688.2	686.3	684.3	682.3	680.3	679.8	680.6	681.5	682.4	683.3
152.5°	700.1	699.3	697.4	695.5	693.7	691.8	691.3	692.3	693.3	694.3	695.2
155°	715.0	714.3	712.8	711.3	709.9	708.4	708.2	709.3	710.4	711.5	712.6
157.5°	727.5	726.7	725.6	724.6	723.6	722.5	722.5	723.4	724.4	725.3	726.3
160°	735.0	734.3	733.5	732.8	732.1	731.3	731.3	732.1	732.8	733.5	734.3
162.5°	741.7	740.9	740.3	739.7	738.9	738.3	738.4	739.1	739.9	740.6	741.3
165°	750.1	749.2	748.8	748.5	748.1	747.7	747.9	748.7	749.4	750.1	750.9
167.5°	757.1	756.2	755.9	755.5	755.2	754.9	755.0	755.7	756.5	757.2	758.0
170°	760.7	759.8	759.5	759.3	759.0	758.8	759.0	759.8	760.5	761.2	762.0
172.5°	763.3	762.4	762.2	761.9	761.7	761.4	761.7	762.4	763.2	763.9	764.6
175°	766.2	765.3	765.1	764.9	764.5	764.3	764.6	765.5	766.4	767.2	768.1
177.5°	766.7	766.0	765.9	765.8	765.6	765.6	765.9	766.6	767.2	767.9	768.7
180°	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4



TEST NUMBER: P331769-927

CATALOG NUMBER: S122RDIW-S290D710U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8
2.5°	520.9	521.3	524.2	525.5	528.1	529.1	530.3	530.0	530.0	530.5	534.6
5°	522.0	525.6	531.0	536.2	541.3	545.6	548.5	551.4	552.5	557.6	562.3
7.5°	520.1	526.8	535.7	543.7	553.2	560.6	566.8	572.4	576.2	583.8	591.6
10°	517.7	527.0	537.1	547.4	560.5	570.5	580.5	588.3	590.7	602.1	608.6
12.5°	512.8	525.3	538.1	551.4	564.3	577.9	589.0	596.8	605.6	615.8	627.7
15°	505.5	519.8	536.6	553.7	572.0	588.6	600.5	613.9	623.7	634.9	645.3
17.5°	495.0	513.5	534.7	554.5	575.8	593.5	609.9	622.8	629.6	636.0	637.5
20°	486.6	506.5	531.6	554.9	576.2	596.7	612.9	623.7	625.5	625.7	616.2
22.5°	477.5	500.1	526.2	550.2	575.6	598.4	611.0	615.6	608.5	596.3	577.8
25°	460.8	487.0	517.4	544.7	572.4	594.0	598.3	590.3	565.2	538.9	505.6
27.5°	442.8	472.1	504.7	535.1	564.7	578.1	568.7	539.5	494.5	455.3	407.8
30°	429.5	462.5	494.5	528.5	555.9	561.6	540.2	497.2	444.7	385.6	338.3
32.5°	414.4	448.9	484.1	519.3	542.2	536.5	501.2	448.2	386.7	328.6	283.9
35°	392.8	428.4	466.4	501.7	516.3	491.9	439.0	370.1	307.1	253.0	222.2
37.5°	367.9	406.7	446.2	478.6	477.5	437.0	365.0	293.8	240.9	208.8	187.0
40°	350.1	389.4	432.1	459.4	447.7	395.0	316.9	249.8	211.0	185.5	169.5
42.5°	333.2	372.6	414.9	436.7	416.3	351.5	273.7	221.1	189.2	169.3	156.3
45°	304.3	345.9	385.1	397.1	360.8	289.4	221.3	183.2	161.9	147.2	138.2
47.5°	276.0	317.0	352.8	352.9	303.8	234.6	186.7	158.5	140.4	129.0	122.5
50°	258.7	297.6	327.6	323.0	267.2	208.7	167.0	142.7	127.6	118.7	111.9
52.5°	239.3	277.0	303.1	289.8	236.2	183.7	149.2	128.9	116.4	108.7	102.6
55°	211.0	244.5	262.9	242.7	192.7	152.8	126.1	110.1	100.8	94.3	89.0
57.5°	183.3	211.0	222.4	199.0	158.8	126.7	106.7	94.7	85.4	80.7	78.0
60°	165.9	189.5	197.6	171.7	138.0	110.8	94.5	83.3	76.4	73.4	70.7
62.5°	148.8	168.0	171.3	147.7	120.3	97.0	82.9	73.5	69.0	66.1	63.5
65°	123.4	137.3	135.7	116.6	95.2	77.0	66.8	61.0	57.6	53.5	49.0
67.5°	101.6	110.1	105.0	90.7	72.6	59.9	53.2	48.8	44.5	40.6	39.6
70°	87.8	92.7	87.3	74.1	59.6	50.2	44.8	39.6	37.1	36.2	34.5
72.5°	74.5	76.3	70.4	59.2	48.5	41.6	36.3	33.4	32.0	31.3	30.3
75°	55.9	54.7	49.7	40.9	33.7	29.0	27.3	26.3	25.3	24.6	24.1
77.5°	39.3	37.5	33.0	27.2	23.4	21.2	20.2	19.6	19.3	18.9	18.3
80°	29.5	28.3	23.8	19.4	17.8	16.7	16.2	15.4	15.4	15.1	14.6
82.5°	21.6	20.2	16.2	14.3	13.4	12.7	12.3	11.9	11.7	11.8	11.4
85°	11.3	9.2	8.1	7.8	7.2	6.8	7.1	6.7	6.7	6.7	6.5
87.5°	3.8	3.4	3.5	3.6	4.0	4.2	4.3	4.4	4.8	4.8	5.1
90°	1.9	3.2	4.6	5.9	7.1	8.2	9.1	10.1	11.1	11.7	12.4
92.5°	11.1	10.9	10.9	10.7	10.9	11.4	11.9	12.4	12.8	13.2	13.5
95°	32.0	27.9	23.8	19.8	18.1	19.0	19.9	20.8	21.6	22.3	22.9
97.5°	60.0	48.6	37.2	25.7	21.0	23.0	25.0	26.9	28.9	29.5	29.9
100°	81.3	64.4	47.5	30.7	23.2	25.3	27.4	29.5	31.6	32.6	33.6
102.5°	123.9	120.3	116.7	113.1	102.6	85.1	67.6	50.0	32.5	33.7	35.1
105°	172.3	176.0	179.7	183.4	168.4	134.8	101.1	67.5	33.8	35.2	36.5
107.5°	218.5	221.5	224.4	227.4	208.7	168.4	128.1	87.7	47.4	45.9	44.6
110°	248.3	250.9	253.4	256.0	239.5	203.9	168.3	132.7	97.0	84.8	72.4





TEST NUMBER: P331769-927

CATALOG NUMBER: S122RDIW-S290D710U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	276.4	278.7	280.9	283.2	280.0	271.2	262.4	253.6	244.8	199.9	154.9
115°	321.0	323.1	325.2	327.3	329.9	333.0	336.0	339.1	342.1	285.1	228.1
117.5°	361.2	363.6	365.9	368.3	370.5	372.6	374.8	376.8	379.0	365.2	351.4
120°	390.1	391.9	393.7	395.6	397.6	399.8	402.0	404.3	406.5	408.0	409.5
122.5°	415.0	416.9	418.9	420.8	423.0	425.4	427.9	430.2	432.7	433.6	434.4
125°	452.5	454.1	455.7	457.2	459.2	461.6	463.9	466.3	468.6	469.4	470.3
127.5°	486.9	488.7	490.4	492.3	494.0	495.7	497.5	499.2	501.0	502.2	503.5
130°	508.8	510.8	512.8	514.8	516.4	517.8	519.1	520.5	521.9	523.2	524.6
132.5°	530.8	532.4	534.1	535.8	537.3	538.6	540.0	541.4	542.7	543.8	545.0
135°	559.8	561.8	563.8	565.8	567.4	568.5	569.6	570.7	571.8	573.0	574.3
137.5°	588.4	589.9	591.2	592.6	593.9	595.2	596.4	597.7	599.0	600.2	601.3
140°	607.1	608.1	609.1	610.1	611.2	612.6	613.9	615.3	616.7	617.8	618.9
142.5°	623.0	623.9	624.8	625.7	626.9	628.4	630.0	631.5	633.1	634.1	635.1
145°	647.1	647.0	646.8	646.7	647.7	649.7	651.9	653.9	656.1	657.0	657.7
147.5°	668.6	668.1	667.7	667.2	668.0	670.0	672.1	674.1	676.2	676.9	677.6
150°	682.4	681.5	680.6	679.8	680.3	682.3	684.3	686.3	688.2	689.0	689.7
152.5°	694.3	693.3	692.3	691.3	691.8	693.7	695.5	697.4	699.3	700.1	700.8
155°	711.5	710.4	709.3	708.2	708.4	709.9	711.3	712.8	714.3	715.0	715.7
157.5°	725.3	724.4	723.4	722.5	722.5	723.6	724.6	725.6	726.7	727.5	728.4
160°	733.5	732.8	732.1	731.3	731.3	732.1	732.8	733.5	734.3	735.0	735.7
162.5°	740.6	739.9	739.1	738.4	738.3	738.9	739.7	740.3	740.9	741.7	742.6
165°	750.1	749.4	748.7	747.9	747.7	748.1	748.5	748.8	749.2	750.1	751.0
167.5°	757.2	756.5	755.7	755.0	754.9	755.2	755.5	755.9	756.2	757.1	758.0
170°	761.2	760.5	759.8	759.0	758.8	759.0	759.3	759.5	759.8	760.7	761.5
172.5°	763.9	763.2	762.4	761.7	761.4	761.7	761.9	762.2	762.4	763.3	764.1
175°	767.2	766.4	765.5	764.6	764.3	764.5	764.9	765.1	765.3	766.2	767.1
177.5°	767.9	767.2	766.6	765.9	765.6	765.6	765.8	765.9	766.0	766.7	767.4
180°	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4	766.4



TEST NUMBER: P331769-927

CATALOG NUMBER: S122RDIW-S290D710U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	517.8	517.8	517.8	517.8	517.8	517.8	517.8
2.5°	536.0	537.9	538.8	538.8	539.8	539.3	538.9
5°	566.8	570.2	571.0	574.2	576.6	575.8	576.2
7.5°	597.5	602.9	608.4	610.9	611.2	612.7	613.2
10°	616.3	620.8	629.2	628.0	634.3	637.9	632.0
12.5°	634.5	640.6	646.4	648.0	651.6	652.8	650.4
15°	650.9	654.1	654.4	653.6	654.7	653.7	650.3
17.5°	635.6	630.3	619.6	614.6	610.6	604.7	602.3
20°	610.2	594.7	576.7	569.5	561.1	544.5	548.5
22.5°	555.5	537.9	519.8	498.8	488.8	473.1	472.1
25°	470.4	440.0	406.5	383.1	369.4	353.8	346.9
27.5°	365.8	327.4	300.0	286.1	273.5	261.1	260.5
30°	296.9	268.2	246.9	235.0	227.3	222.0	223.2
32.5°	250.3	230.5	216.2	206.4	200.7	196.7	196.6
35°	204.6	191.1	181.9	177.8	173.6	170.8	171.0
37.5°	175.1	167.0	161.8	157.3	154.7	153.3	152.5
40°	159.9	153.3	149.3	146.6	144.5	142.5	142.1
42.5°	148.1	142.5	138.6	136.4	134.4	133.0	132.7
45°	131.3	126.8	123.3	120.9	120.0	118.7	118.7
47.5°	116.8	112.4	109.6	108.1	106.6	105.8	105.8
50°	107.1	103.6	101.2	100.2	98.9	98.5	98.2
52.5°	98.3	95.7	94.0	93.3	92.8	92.1	92.2
55°	86.3	84.9	84.2	83.7	82.8	81.7	82.4
57.5°	76.4	75.1	73.2	71.5	70.7	69.9	70.2
60°	69.3	66.8	64.2	62.3	61.7	60.1	60.1
62.5°	60.4	56.8	53.7	52.6	52.0	51.3	51.2
65°	46.4	45.0	44.3	43.6	43.2	43.2	42.9
67.5°	38.5	37.9	37.1	36.9	36.6	36.4	36.4
70°	34.0	33.3	33.0	32.7	32.4	32.6	32.0
72.5°	29.7	29.2	29.1	28.6	28.4	28.4	28.0
75°	23.4	23.4	23.2	23.1	22.7	22.5	22.7
77.5°	18.0	18.1	17.7	17.7	17.7	17.7	17.5
80°	14.4	14.6	14.4	14.2	14.0	14.2	14.0
82.5°	11.4	11.1	11.1	11.0	11.0	10.9	10.9
85°	6.5	6.7	6.5	6.3	6.3	6.3	6.5
87.5°	5.1	5.1	5.2	5.3	5.3	5.4	5.3
90°	12.9	13.5	14.0	14.3	14.5	14.7	15.0
92.5°	13.9	14.2	14.4	14.5	14.7	14.8	15.0
95°	23.4	24.1	24.3	24.2	24.1	24.0	23.8
97.5°	30.4	30.9	31.2	31.4	31.5	31.7	31.8
100°	34.5	35.6	36.2	36.4	36.7	36.9	37.2
102.5°	36.4	37.6	38.4	38.8	39.1	39.5	39.8
105°	37.9	39.2	40.2	40.6	41.2	41.7	42.1
107.5°	43.3	41.8	41.4	41.9	42.4	42.9	43.3
110°	60.0	47.8	41.8	42.3	42.9	43.3	43.8



TEST NUMBER: P331769-927

CATALOG NUMBER: S122RDIW-S290D710U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	110.0	65.0	42.7	43.1	43.5	43.9	44.3
115°	171.0	113.9	81.0	72.1	63.2	54.3	45.5
117.5°	337.5	323.8	302.3	273.1	244.0	214.8	185.7
120°	410.9	412.4	404.8	388.2	371.5	354.9	338.3
122.5°	435.3	436.3	435.1	431.8	428.6	425.4	422.2
125°	471.2	472.1	472.7	473.0	473.4	473.8	474.1
127.5°	504.8	506.0	506.7	506.8	506.8	506.9	507.0
130°	525.9	527.3	527.9	527.8	527.7	527.5	527.4
132.5°	546.2	547.3	547.9	547.7	547.6	547.5	547.4
135°	575.4	576.7	577.2	576.9	576.7	576.5	576.2
137.5°	602.5	603.8	604.2	603.7	603.3	602.9	602.5
140°	620.0	621.2	621.4	620.8	620.1	619.5	618.9
142.5°	636.1	637.2	637.3	636.8	636.1	635.5	634.9
145°	658.6	659.5	659.7	659.0	658.4	657.7	657.2
147.5°	678.2	678.8	678.9	678.3	677.9	677.3	676.8
150°	690.5	691.2	691.3	690.6	690.0	689.4	688.8
152.5°	701.6	702.3	702.3	701.4	700.6	699.8	698.9
155°	716.5	717.2	717.1	716.1	715.2	714.2	713.2
157.5°	729.2	730.1	730.0	729.0	728.1	727.1	726.1
160°	736.5	737.2	737.1	736.3	735.4	734.6	733.7
162.5°	743.4	744.3	744.2	743.1	742.0	740.9	739.9
165°	751.8	752.7	752.7	751.8	751.0	750.1	749.2
167.5°	758.8	759.6	759.5	758.4	757.3	756.2	755.1
170°	762.3	763.2	763.1	762.0	760.9	759.8	758.7
172.5°	765.0	765.9	765.7	764.6	763.5	762.4	761.3
175°	767.9	768.7	768.6	767.3	766.1	764.9	763.7
177.5°	768.0	768.7	768.7	767.8	766.8	766.0	765.1
180°	766.4	766.4	766.4	766.4	766.4	766.4	766.4

(END OF REPORT)