

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331774-927

Luminaire Tested: **S122RDIW-S290D970U927-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331774-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIW-S290D970U927-4F0-1E-UDD-A1  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 970 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3557.4 lumens  
Efficiency: N/A  
Efficacy: 93.6 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 38  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331774-927

CATALOG NUMBER: S122RDIW-S290D970U927-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot



— 0°-180°    - - 45°-225°    - - - 90°-270°    - - - 135°-315°



TEST NUMBER: P331774-927

CATALOG NUMBER: S122RDIW-S290D970U927-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	33	33	33	25
1	93	89	85	82	82	79	76	73	61	59	58	45	44	43	30	29	29	22
2	85	78	72	67	75	70	65	61	54	51	48	40	38	36	27	26	25	19
3	77	69	62	57	69	62	56	51	48	44	41	36	33	31	24	23	22	17
4	71	61	54	48	63	55	49	44	43	39	35	32	29	27	22	20	19	15
5	65	54	47	41	58	49	42	38	39	34	31	29	26	24	20	18	17	13
6	60	49	41	36	53	44	37	33	35	30	27	26	23	21	18	16	15	12
7	56	44	37	31	49	40	33	29	32	27	24	24	21	19	17	15	14	11
8	52	40	33	28	46	36	30	26	29	24	21	22	19	17	16	14	12	10
9	48	36	29	25	43	33	27	23	26	22	19	20	17	15	14	13	11	9
10	45	33	27	22	40	30	24	20	24	20	17	19	16	14	13	12	10	8

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	8360	8360	8360	8360
5°	9339	8413	7460	8413
10°	10362	8355	6466	8355
15°	10870	8232	5095	8232
20°	9424	8052	4409	8052
25°	6180	7803	3935	7803
30°	4161	7500	3563	7500
35°	3370	7121	3213	7121
40°	2995	6709	2974	6709
45°	2710	6224	2653	6224
50°	2467	5745	2459	5745
55°	2320	5210	2291	5210
60°	1941	4724	1918	4724
65°	1639	4290	1857	4290
70°	1511	3829	1751	3829
75°	1416	3337	1616	3337
80°	1302	2743	1432	2743
85°	1204	2167	1260	2167



TEST NUMBER: P331774-927

CATALOG NUMBER: S122RDIW-S290D970U927-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	49.1	1.4
10°-20°	136.8	3.8
20°-30°	176.3	5.0
30°-40°	167.5	4.7
40°-50°	143.5	4.0
50°-60°	109.3	3.1
60°-70°	69.1	1.9
70°-80°	34.5	1.0
80°-90°	12.8	0.4
90°-100°	60.2	1.7
100°-110°	187.1	5.3
110°-120°	319.9	9.0
120°-130°	420.6	11.8
130°-140°	472.1	13.3
140°-150°	462.9	13.0
150°-160°	388.3	10.9
160°-170°	257.5	7.2
170°-180°	90.0	2.5
0°-30°	362.2	10.2
0°-40°	529.7	14.9
0°-60°	782.5	22.0
0°-90°	898.8	25.3
90°-120°	567.2	15.9
90°-150°	1922.8	54.1
90°-180°	2659.0	74.7
0°-180°	3557.4	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	518	518	518	518	518	
5°	576	519	460	519	576	57
15°	650	492	305	492	650	175
25°	347	438	221	438	347	165
35°	171	361	163	361	171	109
45°	119	273	116	273	119	92
55°	82	185	81	185	82	72
65°	43	112	49	112	43	44
75°	23	54	26	54	23	24
85°	6	12	7	12	6	8
90°	27	1	27	1	27	12
95°	50	42	50	42	50	55
105°	178	172	178	172	178	187
115°	321	321	321	321	321	317
125°	469	467	469	467	469	418
135°	611	604	611	604	611	471
145°	741	733	741	733	741	463
155°	845	838	845	838	845	389
165°	913	912	913	912	913	258
175°	946	949	946	949	946	90
180°	951	951	951	951	951	



TEST NUMBER: P331774-927

CATALOG NUMBER: S122RDIW-S290D970U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8
2.5°	538.9	539.3	539.8	538.8	538.8	537.9	536.0	534.6	530.5	530.0	530.0
5°	576.2	575.8	576.6	574.2	571.0	570.2	566.8	562.3	557.6	552.5	551.4
7.5°	613.2	612.7	611.2	610.9	608.4	602.9	597.5	591.6	583.8	576.2	572.4
10°	632.0	637.9	634.3	628.0	629.2	620.8	616.3	608.6	602.1	590.7	588.3
12.5°	650.4	652.8	651.6	648.0	646.4	640.6	634.5	627.7	615.8	605.6	596.8
15°	650.3	653.7	654.7	653.6	654.4	654.1	650.9	645.3	634.9	623.7	613.9
17.5°	602.3	604.7	610.6	614.6	619.6	630.3	635.6	637.5	636.0	629.6	622.8
20°	548.5	544.5	561.1	569.5	576.7	594.7	610.2	616.2	625.7	625.5	623.7
22.5°	472.1	473.1	488.8	498.8	519.8	537.9	555.5	577.8	596.3	608.5	615.6
25°	346.9	353.8	369.4	383.1	406.5	440.0	470.4	505.6	538.9	565.2	590.3
27.5°	260.5	261.1	273.5	286.1	300.0	327.4	365.8	407.8	455.3	494.5	539.5
30°	223.2	222.0	227.3	235.0	246.9	268.2	296.9	338.3	385.6	444.7	497.2
32.5°	196.6	196.7	200.7	206.4	216.2	230.5	250.3	283.9	328.6	386.7	448.2
35°	171.0	170.8	173.6	177.8	181.9	191.1	204.6	222.2	253.0	307.1	370.1
37.5°	152.5	153.3	154.7	157.3	161.8	167.0	175.1	187.0	208.8	240.9	293.8
40°	142.1	142.5	144.5	146.6	149.3	153.3	159.9	169.5	185.5	211.0	249.8
42.5°	132.7	133.0	134.4	136.4	138.6	142.5	148.1	156.3	169.3	189.2	221.1
45°	118.7	118.7	120.0	120.9	123.3	126.8	131.3	138.2	147.2	161.9	183.2
47.5°	105.8	105.8	106.6	108.1	109.6	112.4	116.8	122.5	129.0	140.4	158.5
50°	98.2	98.5	98.9	100.2	101.2	103.6	107.1	111.9	118.7	127.6	142.7
52.5°	92.2	92.1	92.8	93.3	94.0	95.7	98.3	102.6	108.7	116.4	128.9
55°	82.4	81.7	82.8	83.7	84.2	84.9	86.3	89.0	94.3	100.8	110.1
57.5°	70.2	69.9	70.7	71.5	73.2	75.1	76.4	78.0	80.7	85.4	94.7
60°	60.1	60.1	61.7	62.3	64.2	66.8	69.3	70.7	73.4	76.4	83.3
62.5°	51.2	51.3	52.0	52.6	53.7	56.8	60.4	63.5	66.1	69.0	73.5
65°	42.9	43.2	43.2	43.6	44.3	45.0	46.4	49.0	53.5	57.6	61.0
67.5°	36.4	36.4	36.6	36.9	37.1	37.9	38.5	39.6	40.6	44.5	48.8
70°	32.0	32.6	32.4	32.7	33.0	33.3	34.0	34.5	36.2	37.1	39.6
72.5°	28.0	28.4	28.4	28.6	29.1	29.2	29.7	30.3	31.3	32.0	33.4
75°	22.7	22.5	22.7	23.1	23.2	23.4	23.4	24.1	24.6	25.3	26.3
77.5°	17.5	17.7	17.7	17.7	17.7	18.1	18.0	18.3	18.9	19.3	19.6
80°	14.0	14.2	14.0	14.2	14.4	14.6	14.4	14.6	15.1	15.4	15.4
82.5°	10.9	10.9	11.0	11.0	11.1	11.1	11.4	11.4	11.8	11.7	11.9
85°	6.5	6.3	6.3	6.3	6.5	6.7	6.5	6.5	6.7	6.7	6.7
87.5°	7.8	7.8	7.8	7.8	7.8	7.8	7.8	8.1	8.0	8.2	7.3
90°	27.3	27.1	26.9	26.8	26.5	26.6	27.0	27.3	27.7	28.0	24.2
92.5°	26.0	26.0	25.9	25.9	25.8	25.8	25.7	25.7	25.6	25.5	24.6
95°	49.7	50.1	50.5	50.8	51.2	51.3	51.3	51.3	51.3	51.3	51.0
97.5°	86.2	86.2	86.3	86.3	86.3	86.3	86.3	86.3	86.3	86.3	85.6
100°	110.0	110.1	110.3	110.4	110.7	110.7	110.7	110.7	110.7	110.7	110.2
102.5°	136.9	137.0	137.2	137.4	137.6	137.6	137.4	137.4	137.2	137.0	136.3
105°	178.2	178.2	178.2	178.2	178.2	177.9	177.6	177.2	176.9	176.5	176.2
107.5°	217.0	217.8	218.6	219.4	220.2	220.5	220.5	220.3	220.1	220.0	220.0
110°	247.2	247.6	248.2	248.7	249.3	249.5	249.5	249.5	249.5	249.5	249.5



TEST NUMBER: P331774-927

CATALOG NUMBER: S122RDIW-S290D970U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	276.0	276.4	276.8	277.2	277.6	278.0	278.5	278.8	279.2	279.7	279.9
115°	320.9	321.5	322.0	322.6	323.1	323.4	323.6	323.8	324.0	324.2	324.5
117.5°	363.8	364.3	364.9	365.4	365.9	366.4	366.9	367.3	367.7	368.1	369.2
120°	394.0	394.5	395.1	395.5	396.1	396.4	396.4	396.4	396.4	396.4	397.8
122.5°	423.5	423.9	424.3	424.7	425.1	425.5	425.9	426.4	426.7	427.1	428.2
125°	468.6	468.7	469.0	469.1	469.3	469.7	470.2	470.7	471.3	471.8	472.3
127.5°	509.7	510.2	510.8	511.4	511.9	512.5	513.2	513.8	514.4	515.2	515.8
130°	539.2	539.9	540.6	541.3	542.0	542.6	543.0	543.3	543.7	544.0	544.4
132.5°	567.4	568.0	568.5	569.2	569.7	570.4	571.2	572.0	572.7	573.5	573.5
135°	611.4	612.0	612.4	613.0	613.5	613.9	614.1	614.3	614.4	614.6	614.3
137.5°	651.2	651.9	652.6	653.3	654.0	654.5	654.7	654.7	654.9	655.1	654.6
140°	678.8	679.5	680.2	681.0	681.7	682.0	682.0	682.0	682.0	682.0	681.1
142.5°	703.9	704.6	705.3	706.0	706.7	706.9	706.9	706.7	706.5	706.4	705.8
145°	741.4	742.1	742.8	743.5	744.3	744.5	744.3	744.2	743.9	743.8	742.8
147.5°	774.9	775.6	776.3	777.0	777.6	777.8	777.4	777.0	776.6	776.2	775.5
150°	796.8	797.3	797.8	798.4	798.9	798.9	798.4	797.8	797.3	796.8	796.1
152.5°	817.3	817.9	818.6	819.4	820.0	820.0	819.4	818.6	817.9	817.3	816.4
155°	844.9	845.4	846.0	846.5	847.0	846.8	846.0	845.1	844.1	843.3	842.7
157.5°	868.6	869.5	870.4	871.2	872.0	871.9	870.7	869.5	868.2	867.0	866.7
160°	883.4	884.2	884.9	885.6	886.3	886.1	885.0	883.9	882.9	881.8	881.6
162.5°	896.3	897.1	897.9	898.8	899.7	899.5	898.3	897.1	895.9	894.6	894.5
165°	913.1	914.0	914.9	915.8	916.6	916.5	915.2	914.0	912.8	911.5	911.5
167.5°	926.9	927.8	928.8	929.7	930.6	930.4	929.2	928.0	926.7	925.4	925.5
170°	934.0	935.0	936.1	937.2	938.3	938.2	936.9	935.6	934.4	933.2	933.3
172.5°	939.8	940.8	941.9	942.9	944.0	943.9	942.7	941.4	940.2	938.9	939.1
175°	946.0	947.1	948.2	949.2	950.3	950.1	949.0	947.7	946.4	945.2	945.5
177.5°	948.9	949.7	950.6	951.4	952.3	952.3	951.4	950.6	949.7	948.9	949.2
180°	950.8	950.8	950.8	950.8	950.8	950.8	950.8	950.8	950.8	950.8	950.8



TEST NUMBER: P331774-927

CATALOG NUMBER: S122RDIW-S290D970U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8
2.5°	530.3	529.1	528.1	525.5	524.2	521.3	520.9	520.8	517.1	513.4	512.4
5°	548.5	545.6	541.3	536.2	531.0	525.6	522.0	519.1	511.9	505.1	501.1
7.5°	566.8	560.6	553.2	543.7	535.7	526.8	520.1	514.2	504.0	494.2	487.6
10°	580.5	570.5	560.5	547.4	537.1	527.0	517.7	509.6	498.1	485.1	475.9
12.5°	589.0	577.9	564.3	551.4	538.1	525.3	512.8	502.4	488.9	475.5	464.6
15°	600.5	588.6	572.0	553.7	536.6	519.8	505.5	492.5	474.9	458.8	445.5
17.5°	609.9	593.5	575.8	554.5	534.7	513.5	495.0	478.4	458.8	439.4	423.7
20°	612.9	596.7	576.2	554.9	531.6	506.5	486.6	468.6	447.5	426.4	408.4
22.5°	611.0	598.4	575.6	550.2	526.2	500.1	477.5	456.6	433.2	411.8	390.9
25°	598.3	594.0	572.4	544.7	517.4	487.0	460.8	438.0	411.4	388.3	365.7
27.5°	568.7	578.1	564.7	535.1	504.7	472.1	442.8	416.8	389.1	363.2	340.6
30°	540.2	561.6	555.9	528.5	494.5	462.5	429.5	402.3	372.9	346.2	323.9
32.5°	501.2	536.5	542.2	519.3	484.1	448.9	414.4	387.4	356.6	328.5	306.7
35°	439.0	491.9	516.3	501.7	466.4	428.4	392.8	361.3	330.3	302.7	281.1
37.5°	365.0	437.0	477.5	478.6	446.2	406.7	367.9	336.6	304.9	277.7	254.4
40°	316.9	395.0	447.7	459.4	432.1	389.4	350.1	318.3	287.4	260.7	233.9
42.5°	273.7	351.5	416.3	436.7	414.9	372.6	333.2	299.9	269.8	244.6	217.2
45°	221.3	289.4	360.8	397.1	385.1	345.9	304.3	272.6	244.4	222.6	196.3
47.5°	186.7	234.6	303.8	352.9	352.8	317.0	276.0	245.7	219.5	199.1	177.8
50°	167.0	208.7	267.2	323.0	327.6	297.6	258.7	228.7	204.2	182.8	165.7
52.5°	149.2	183.7	236.2	289.8	303.1	277.0	239.3	211.6	187.8	168.1	153.5
55°	126.1	152.8	192.7	242.7	262.9	244.5	211.0	185.1	165.9	149.3	136.7
57.5°	106.7	126.7	158.8	199.0	222.4	211.0	183.3	162.2	145.8	130.8	120.9
60°	94.5	110.8	138.0	171.7	197.6	189.5	165.9	146.3	132.3	119.3	110.0
62.5°	82.9	97.0	120.3	147.7	171.3	168.0	148.8	132.3	120.0	108.2	100.3
65°	66.8	77.0	95.2	116.6	135.7	137.3	123.4	112.3	101.3	92.0	84.9
67.5°	53.2	59.9	72.6	90.7	105.0	110.1	101.6	93.1	84.4	77.2	71.1
70°	44.8	50.2	59.6	74.1	87.3	92.7	87.8	81.1	73.6	67.7	62.4
72.5°	36.3	41.6	48.5	59.2	70.4	76.3	74.5	69.8	63.7	58.7	53.8
75°	27.3	29.0	33.7	40.9	49.7	54.7	55.9	53.5	48.6	44.8	41.9
77.5°	20.2	21.2	23.4	27.2	33.0	37.5	39.3	39.0	35.6	33.5	30.7
80°	16.2	16.7	17.8	19.4	23.8	28.3	29.5	29.5	27.2	26.3	23.6
82.5°	12.3	12.7	13.4	14.3	16.2	20.2	21.6	21.9	20.4	19.3	17.1
85°	7.1	6.8	7.2	7.8	8.1	9.2	11.3	11.7	11.3	9.9	9.3
87.5°	6.5	5.9	5.1	4.4	4.0	3.7	4.0	4.4	4.2	4.2	4.4
90°	20.2	16.3	12.4	9.3	7.2	5.1	2.9	0.8	2.9	5.1	7.2
92.5°	23.7	22.7	21.8	20.6	19.0	17.4	15.8	14.3	15.8	17.4	19.0
95°	50.6	50.3	49.9	48.9	47.1	45.3	43.5	41.7	43.5	45.3	47.1
97.5°	85.0	84.3	83.7	82.5	81.0	79.4	77.8	76.2	77.8	79.4	81.0
100°	109.6	109.1	108.6	107.6	106.2	104.7	103.3	101.9	103.3	104.7	106.2
102.5°	135.7	135.0	134.4	133.4	132.3	131.1	130.0	128.9	130.0	131.1	132.3
105°	175.8	175.5	175.1	174.7	174.1	173.6	173.0	172.5	173.0	173.6	174.1
107.5°	220.0	220.0	220.0	219.6	218.8	218.0	217.3	216.5	217.3	218.0	218.8
110°	249.5	249.5	249.5	249.0	248.0	246.8	245.8	244.7	245.8	246.8	248.0





TEST NUMBER: P331774-927

CATALOG NUMBER: S122RDIW-S290D970U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	280.0	280.1	280.3	279.8	278.8	277.7	276.6	275.5	276.6	277.7	278.8
115°	324.9	325.2	325.6	325.2	324.2	323.1	322.0	320.9	322.0	323.1	324.2
117.5°	370.1	371.1	372.1	371.9	370.5	369.1	367.7	366.2	367.7	369.1	370.5
120°	399.3	400.7	402.1	402.1	400.7	399.3	397.8	396.4	397.8	399.3	400.7
122.5°	429.2	430.2	431.2	430.8	429.1	427.4	425.7	424.0	425.7	427.4	429.1
125°	472.9	473.4	474.0	473.4	471.8	470.2	468.6	467.0	468.6	470.2	471.8
127.5°	516.4	517.1	517.7	517.0	515.0	512.9	510.9	508.9	510.9	512.9	515.0
130°	544.7	545.1	545.4	544.5	542.2	539.8	537.5	535.2	537.5	539.8	542.2
132.5°	573.4	573.3	573.2	572.3	570.4	568.5	566.6	564.7	566.6	568.5	570.4
135°	613.9	613.5	613.1	612.0	610.1	608.1	606.2	604.2	606.2	608.1	610.1
137.5°	654.1	653.6	653.2	652.1	650.5	649.0	647.4	645.7	647.4	649.0	650.5
140°	680.2	679.4	678.4	677.2	675.6	674.0	672.4	670.7	672.4	674.0	675.6
142.5°	705.2	704.6	704.0	702.9	701.2	699.7	698.1	696.5	698.1	699.7	701.2
145°	741.6	740.6	739.5	738.4	737.1	735.9	734.6	733.3	734.6	735.9	737.1
147.5°	774.8	774.0	773.3	772.2	770.7	769.3	767.8	766.3	767.8	769.3	770.7
150°	795.4	794.6	793.9	793.0	791.9	790.8	789.8	788.7	789.8	790.8	791.9
152.5°	815.6	814.8	813.9	812.9	811.8	810.8	809.7	808.7	809.7	810.8	811.8
155°	842.2	841.7	841.1	840.6	840.1	839.6	839.0	838.4	839.0	839.6	840.1
157.5°	866.4	866.1	865.8	865.4	865.1	864.7	864.4	864.0	864.4	864.7	865.1
160°	881.5	881.3	881.1	880.8	880.4	880.1	879.7	879.4	879.7	880.1	880.4
162.5°	894.3	894.1	893.9	893.8	893.7	893.7	893.6	893.5	893.6	893.7	893.7
165°	911.5	911.5	911.5	911.6	911.7	912.0	912.1	912.3	912.1	912.0	911.7
167.5°	925.5	925.6	925.6	925.9	926.4	926.9	927.5	928.0	927.5	926.9	926.4
170°	933.5	933.7	933.9	934.2	934.8	935.3	935.8	936.4	935.8	935.3	934.8
172.5°	939.3	939.4	939.6	940.0	940.6	941.0	941.6	942.1	941.6	941.0	940.6
175°	945.9	946.3	946.6	947.1	947.6	948.2	948.6	949.2	948.6	948.2	947.6
177.5°	949.4	949.7	950.0	950.4	950.8	951.3	951.6	952.1	951.6	951.3	950.8
180°	950.8	950.8	950.8	950.8	950.8	950.8	950.8	950.8	950.8	950.8	950.8



TEST NUMBER: P331774-927

CATALOG NUMBER: S122RDIW-S290D970U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8
2.5°	510.6	509.5	507.6	504.8	503.0	500.0	498.0	499.2	499.5	499.2	498.9
5°	496.9	493.1	487.8	482.8	478.1	473.1	470.2	469.0	466.4	465.0	464.2
7.5°	480.2	473.7	466.4	457.6	450.1	442.3	438.3	436.3	431.2	428.4	426.0
10°	467.9	457.6	450.2	438.7	431.7	421.4	414.4	414.6	407.6	403.6	400.8
12.5°	454.2	442.9	430.6	420.3	410.5	402.3	393.8	390.4	382.9	379.1	371.4
15°	431.5	418.4	405.4	391.4	381.5	368.7	356.5	341.5	329.5	319.0	316.2
17.5°	406.8	390.5	377.5	361.0	344.0	322.6	308.4	299.7	292.5	286.9	282.8
20°	389.8	373.2	359.3	334.5	311.6	297.1	286.7	280.0	272.4	266.5	263.2
22.5°	371.9	354.7	335.7	308.0	290.2	278.5	269.3	261.6	256.4	251.8	248.8
25°	346.6	327.6	296.5	277.5	263.1	250.8	244.4	239.7	234.3	228.0	225.1
27.5°	319.8	289.8	267.4	253.2	239.5	231.6	225.7	218.7	213.9	211.0	208.0
30°	299.8	269.7	252.3	236.8	227.1	218.2	211.4	207.5	202.8	198.0	196.0
32.5°	277.5	253.5	236.7	223.9	214.0	206.4	201.1	194.6	191.3	188.3	184.2
35°	249.8	231.6	216.3	205.9	196.5	190.4	184.1	180.3	174.2	171.7	170.1
37.5°	226.3	210.6	199.2	188.1	180.7	174.0	170.1	164.1	161.4	157.9	154.5
40°	213.0	197.6	186.6	177.6	169.3	164.3	159.5	154.6	150.6	149.0	144.9
42.5°	199.6	187.0	175.9	166.1	160.6	155.2	149.1	145.5	141.4	138.8	136.3
45°	180.9	169.7	160.3	152.3	146.1	140.5	136.6	130.6	128.3	123.1	120.9
47.5°	164.5	154.1	145.1	137.4	131.5	127.9	122.1	117.4	113.7	110.4	107.7
50°	152.8	144.1	135.5	128.7	123.3	118.0	112.1	109.8	104.0	102.3	100.8
52.5°	142.1	133.9	126.0	119.3	113.9	108.8	103.6	100.5	96.6	95.1	93.9
55°	127.2	119.3	111.8	105.8	100.4	95.2	92.0	88.2	86.3	85.1	83.7
57.5°	112.3	105.1	99.3	93.3	87.9	83.7	80.0	77.7	75.9	74.2	72.5
60°	102.7	95.9	90.7	85.1	79.5	76.1	73.3	70.5	68.4	65.8	65.1
62.5°	92.7	86.7	81.9	76.4	71.6	68.5	65.8	63.2	60.6	57.0	55.9
65°	78.8	74.1	69.1	64.6	60.3	57.2	53.2	50.4	49.3	49.0	48.8
67.5°	66.3	61.9	57.5	52.9	49.0	46.2	44.1	43.7	42.9	42.8	42.2
70°	57.9	53.8	49.5	45.2	41.4	40.9	40.2	39.4	38.5	38.2	37.8
72.5°	50.5	46.2	41.8	38.4	36.8	36.1	35.4	34.6	34.1	33.7	33.5
75°	38.7	34.7	31.8	30.6	29.7	29.2	28.0	27.6	27.2	26.6	26.5
77.5°	27.9	25.6	24.3	23.5	22.6	22.0	21.4	20.8	20.4	20.4	20.0
80°	21.2	20.1	19.3	18.1	17.8	17.1	17.0	16.4	16.6	16.0	16.0
82.5°	16.5	15.1	14.3	13.9	13.5	12.9	12.8	12.5	12.5	12.1	12.1
85°	8.5	8.1	7.8	7.4	7.4	6.8	7.1	6.8	6.8	6.5	6.3
87.5°	4.6	5.1	5.5	6.3	7.1	7.8	7.7	7.5	7.4	7.4	7.2
90°	9.3	12.4	16.3	20.2	24.2	28.0	27.7	27.3	27.0	26.6	26.5
92.5°	20.6	21.8	22.7	23.7	24.6	25.5	25.6	25.7	25.7	25.8	25.8
95°	48.9	49.9	50.3	50.6	51.0	51.3	51.3	51.3	51.3	51.3	51.2
97.5°	82.5	83.7	84.3	85.0	85.6	86.3	86.3	86.3	86.3	86.3	86.3
100°	107.6	108.6	109.1	109.6	110.2	110.7	110.7	110.7	110.7	110.7	110.7
102.5°	133.4	134.4	135.0	135.7	136.3	137.0	137.2	137.4	137.4	137.6	137.6
105°	174.7	175.1	175.5	175.8	176.2	176.5	176.9	177.2	177.6	177.9	178.2
107.5°	219.6	220.0	220.0	220.0	220.0	220.0	220.1	220.3	220.5	220.5	220.2
110°	249.0	249.5	249.5	249.5	249.5	249.5	249.5	249.5	249.5	249.5	249.3



TEST NUMBER: P331774-927

CATALOG NUMBER: S122RDIW-S290D970U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	279.8	280.3	280.1	280.0	279.9	279.7	279.2	278.8	278.5	278.0	277.6
115°	325.2	325.6	325.2	324.9	324.5	324.2	324.0	323.8	323.6	323.4	323.1
117.5°	371.9	372.1	371.1	370.1	369.2	368.1	367.7	367.3	366.9	366.4	365.9
120°	402.1	402.1	400.7	399.3	397.8	396.4	396.4	396.4	396.4	396.4	396.1
122.5°	430.8	431.2	430.2	429.2	428.2	427.1	426.7	426.4	425.9	425.5	425.1
125°	473.4	474.0	473.4	472.9	472.3	471.8	471.3	470.7	470.2	469.7	469.3
127.5°	517.0	517.7	517.1	516.4	515.8	515.2	514.4	513.8	513.2	512.5	511.9
130°	544.5	545.4	545.1	544.7	544.4	544.0	543.7	543.3	543.0	542.6	542.0
132.5°	572.3	573.2	573.3	573.4	573.5	573.5	572.7	572.0	571.2	570.4	569.7
135°	612.0	613.1	613.5	613.9	614.3	614.6	614.4	614.3	614.1	613.9	613.5
137.5°	652.1	653.2	653.6	654.1	654.6	655.1	654.9	654.7	654.7	654.5	654.0
140°	677.2	678.4	679.4	680.2	681.1	682.0	682.0	682.0	682.0	682.0	681.7
142.5°	702.9	704.0	704.6	705.2	705.8	706.4	706.5	706.7	706.9	706.9	706.7
145°	738.4	739.5	740.6	741.6	742.8	743.8	743.9	744.2	744.3	744.5	744.3
147.5°	772.2	773.3	774.0	774.8	775.5	776.2	776.6	777.0	777.4	777.8	777.6
150°	793.0	793.9	794.6	795.4	796.1	796.8	797.3	797.8	798.4	798.9	798.9
152.5°	812.9	813.9	814.8	815.6	816.4	817.3	817.9	818.6	819.4	820.0	820.0
155°	840.6	841.1	841.7	842.2	842.7	843.3	844.1	845.1	846.0	846.8	847.0
157.5°	865.4	865.8	866.1	866.4	866.7	867.0	868.2	869.5	870.7	871.9	872.0
160°	880.8	881.1	881.3	881.5	881.6	881.8	882.9	883.9	885.0	886.1	886.3
162.5°	893.8	893.9	894.1	894.3	894.5	894.6	895.9	897.1	898.3	899.5	899.7
165°	911.6	911.5	911.5	911.5	911.5	911.5	912.8	914.0	915.2	916.5	916.6
167.5°	925.9	925.6	925.6	925.5	925.5	925.4	926.7	928.0	929.2	930.4	930.6
170°	934.2	933.9	933.7	933.5	933.3	933.2	934.4	935.6	936.9	938.2	938.3
172.5°	940.0	939.6	939.4	939.3	939.1	938.9	940.2	941.4	942.7	943.9	944.0
175°	947.1	946.6	946.3	945.9	945.5	945.2	946.4	947.7	949.0	950.1	950.3
177.5°	950.4	950.0	949.7	949.4	949.2	948.9	949.7	950.6	951.4	952.3	952.3
180°	950.8	950.8	950.8	950.8	950.8	950.8	950.8	950.8	950.8	950.8	950.8



TEST NUMBER: P331774-927

CATALOG NUMBER: S122RDIW-S290D970U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8
2.5°	497.3	497.6	497.2	497.4	497.2	497.6	497.3	498.9	499.2	499.5	499.2
5°	463.3	461.2	460.8	460.3	460.8	461.2	463.3	464.2	465.0	466.4	469.0
7.5°	422.9	422.6	421.6	420.3	421.6	422.6	422.9	426.0	428.4	431.2	436.3
10°	396.8	395.9	395.7	394.4	395.7	395.9	396.8	400.8	403.6	407.6	414.6
12.5°	366.2	360.4	359.9	356.7	359.9	360.4	366.2	371.4	379.1	382.9	390.4
15°	311.9	310.8	307.1	304.8	307.1	310.8	311.9	316.2	319.0	329.5	341.5
17.5°	280.7	277.2	276.1	275.6	276.1	277.2	280.7	282.8	286.9	292.5	299.7
20°	260.7	257.5	257.0	256.6	257.0	257.5	260.7	263.2	266.5	272.4	280.0
22.5°	246.9	243.5	242.2	241.1	242.2	243.5	246.9	248.8	251.8	256.4	261.6
25°	223.3	222.0	221.3	220.9	221.3	222.0	223.3	225.1	228.0	234.3	239.7
27.5°	204.9	202.1	201.5	200.6	201.5	202.1	204.9	208.0	211.0	213.9	218.7
30°	194.3	193.5	192.2	191.1	192.2	193.5	194.3	196.0	198.0	202.8	207.5
32.5°	182.0	181.2	180.1	179.6	180.1	181.2	182.0	184.2	188.3	191.3	194.6
35°	168.3	165.7	164.6	163.0	164.6	165.7	168.3	170.1	171.7	174.2	180.3
37.5°	153.8	152.4	150.9	151.5	150.9	152.4	153.8	154.5	157.9	161.4	164.1
40°	142.5	141.6	141.2	141.1	141.2	141.6	142.5	144.9	149.0	150.6	154.6
42.5°	133.6	131.1	130.2	130.2	130.2	131.1	133.6	136.3	138.8	141.4	145.5
45°	120.0	117.7	116.1	116.2	116.1	117.7	120.0	120.9	123.1	128.3	130.6
47.5°	106.2	106.1	105.0	105.4	105.0	106.1	106.2	107.7	110.4	113.7	117.4
50°	99.5	98.5	97.7	97.9	97.7	98.5	99.5	100.8	102.3	104.0	109.8
52.5°	93.2	92.2	91.7	92.4	91.7	92.2	93.2	93.9	95.1	96.6	100.5
55°	82.8	81.7	81.5	81.4	81.5	81.7	82.8	83.7	85.1	86.3	88.2
57.5°	71.1	70.4	69.3	68.9	69.3	70.4	71.1	72.5	74.2	75.9	77.7
60°	62.8	61.4	59.6	59.4	59.6	61.4	62.8	65.1	65.8	68.4	70.5
62.5°	55.1	54.9	54.5	54.5	54.5	54.9	55.1	55.9	57.0	60.6	63.2
65°	48.4	48.2	48.4	48.6	48.4	48.2	48.4	48.8	49.0	49.3	50.4
67.5°	42.1	41.8	41.5	41.7	41.5	41.8	42.1	42.2	42.8	42.9	43.7
70°	37.4	37.2	37.1	37.1	37.1	37.2	37.4	37.8	38.2	38.5	39.4
72.5°	32.8	32.8	32.6	32.5	32.6	32.8	32.8	33.5	33.7	34.1	34.6
75°	26.3	25.9	25.9	25.9	25.9	25.9	26.3	26.5	26.6	27.2	27.6
77.5°	20.0	19.8	19.6	19.5	19.6	19.8	20.0	20.0	20.4	20.4	20.8
80°	15.8	15.7	15.4	15.4	15.4	15.7	15.8	16.0	16.0	16.6	16.4
82.5°	12.1	11.9	11.9	11.7	11.9	11.9	12.1	12.1	12.1	12.5	12.5
85°	6.5	6.7	6.5	6.8	6.5	6.7	6.5	6.3	6.5	6.8	6.8
87.5°	7.2	7.1	7.3	7.2	7.3	7.1	7.2	7.2	7.4	7.4	7.5
90°	26.8	26.9	27.1	27.3	27.1	26.9	26.8	26.5	26.6	27.0	27.3
92.5°	25.9	25.9	26.0	26.0	26.0	25.9	25.9	25.8	25.8	25.7	25.7
95°	50.8	50.5	50.1	49.7	50.1	50.5	50.8	51.2	51.3	51.3	51.3
97.5°	86.3	86.3	86.2	86.2	86.2	86.3	86.3	86.3	86.3	86.3	86.3
100°	110.4	110.3	110.1	110.0	110.1	110.3	110.4	110.7	110.7	110.7	110.7
102.5°	137.4	137.2	137.0	136.9	137.0	137.2	137.4	137.6	137.6	137.4	137.4
105°	178.2	178.2	178.2	178.2	178.2	178.2	178.2	178.2	177.9	177.6	177.2
107.5°	219.4	218.6	217.8	217.0	217.8	218.6	219.4	220.2	220.5	220.5	220.3
110°	248.7	248.2	247.6	247.2	247.6	248.2	248.7	249.3	249.5	249.5	249.5



TEST NUMBER: P331774-927

CATALOG NUMBER: S122RDIW-S290D970U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	277.2	276.8	276.4	276.0	276.4	276.8	277.2	277.6	278.0	278.5	278.8
115°	322.6	322.0	321.5	320.9	321.5	322.0	322.6	323.1	323.4	323.6	323.8
117.5°	365.4	364.9	364.3	363.8	364.3	364.9	365.4	365.9	366.4	366.9	367.3
120°	395.5	395.1	394.5	394.0	394.5	395.1	395.5	396.1	396.4	396.4	396.4
122.5°	424.7	424.3	423.9	423.5	423.9	424.3	424.7	425.1	425.5	425.9	426.4
125°	469.1	469.0	468.7	468.6	468.7	469.0	469.1	469.3	469.7	470.2	470.7
127.5°	511.4	510.8	510.2	509.7	510.2	510.8	511.4	511.9	512.5	513.2	513.8
130°	541.3	540.6	539.9	539.2	539.9	540.6	541.3	542.0	542.6	543.0	543.3
132.5°	569.2	568.5	568.0	567.4	568.0	568.5	569.2	569.7	570.4	571.2	572.0
135°	613.0	612.4	612.0	611.4	612.0	612.4	613.0	613.5	613.9	614.1	614.3
137.5°	653.3	652.6	651.9	651.2	651.9	652.6	653.3	654.0	654.5	654.7	654.7
140°	681.0	680.2	679.5	678.8	679.5	680.2	681.0	681.7	682.0	682.0	682.0
142.5°	706.0	705.3	704.6	703.9	704.6	705.3	706.0	706.7	706.9	706.9	706.7
145°	743.5	742.8	742.1	741.4	742.1	742.8	743.5	744.3	744.5	744.3	744.2
147.5°	777.0	776.3	775.6	774.9	775.6	776.3	777.0	777.6	777.8	777.4	777.0
150°	798.4	797.8	797.3	796.8	797.3	797.8	798.4	798.9	798.9	798.4	797.8
152.5°	819.4	818.6	817.9	817.3	817.9	818.6	819.4	820.0	820.0	819.4	818.6
155°	846.5	846.0	845.4	844.9	845.4	846.0	846.5	847.0	846.8	846.0	845.1
157.5°	871.2	870.4	869.5	868.6	869.5	870.4	871.2	872.0	871.9	870.7	869.5
160°	885.6	884.9	884.2	883.4	884.2	884.9	885.6	886.3	886.1	885.0	883.9
162.5°	898.8	897.9	897.1	896.3	897.1	897.9	898.8	899.7	899.5	898.3	897.1
165°	915.8	914.9	914.0	913.1	914.0	914.9	915.8	916.6	916.5	915.2	914.0
167.5°	929.7	928.8	927.8	926.9	927.8	928.8	929.7	930.6	930.4	929.2	928.0
170°	937.2	936.1	935.0	934.0	935.0	936.1	937.2	938.3	938.2	936.9	935.6
172.5°	942.9	941.9	940.8	939.8	940.8	941.9	942.9	944.0	943.9	942.7	941.4
175°	949.2	948.2	947.1	946.0	947.1	948.2	949.2	950.3	950.1	949.0	947.7
177.5°	951.4	950.6	949.7	948.9	949.7	950.6	951.4	952.3	952.3	951.4	950.6
180°	950.8	950.8	950.8	950.8	950.8	950.8	950.8	950.8	950.8	950.8	950.8



TEST NUMBER: P331774-927

CATALOG NUMBER: S122RDIW-S290D970U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8
2.5°	498.0	500.0	503.0	504.8	507.6	509.5	510.6	512.4	513.4	517.1	520.8
5°	470.2	473.1	478.1	482.8	487.8	493.1	496.9	501.1	505.1	511.9	519.1
7.5°	438.3	442.3	450.1	457.6	466.4	473.7	480.2	487.6	494.2	504.0	514.2
10°	414.4	421.4	431.7	438.7	450.2	457.6	467.9	475.9	485.1	498.1	509.6
12.5°	393.8	402.3	410.5	420.3	430.6	442.9	454.2	464.6	475.5	488.9	502.4
15°	356.5	368.7	381.5	391.4	405.4	418.4	431.5	445.5	458.8	474.9	492.5
17.5°	308.4	322.6	344.0	361.0	377.5	390.5	406.8	423.7	439.4	458.8	478.4
20°	286.7	297.1	311.6	334.5	359.3	373.2	389.8	408.4	426.4	447.5	468.6
22.5°	269.3	278.5	290.2	308.0	335.7	354.7	371.9	390.9	411.8	433.2	456.6
25°	244.4	250.8	263.1	277.5	296.5	327.6	346.6	365.7	388.3	411.4	438.0
27.5°	225.7	231.6	239.5	253.2	267.4	289.8	319.8	340.6	363.2	389.1	416.8
30°	211.4	218.2	227.1	236.8	252.3	269.7	299.8	323.9	346.2	372.9	402.3
32.5°	201.1	206.4	214.0	223.9	236.7	253.5	277.5	306.7	328.5	356.6	387.4
35°	184.1	190.4	196.5	205.9	216.3	231.6	249.8	281.1	302.7	330.3	361.3
37.5°	170.1	174.0	180.7	188.1	199.2	210.6	226.3	254.4	277.7	304.9	336.6
40°	159.5	164.3	169.3	177.6	186.6	197.6	213.0	233.9	260.7	287.4	318.3
42.5°	149.1	155.2	160.6	166.1	175.9	187.0	199.6	217.2	244.6	269.8	299.9
45°	136.6	140.5	146.1	152.3	160.3	169.7	180.9	196.3	222.6	244.4	272.6
47.5°	122.1	127.9	131.5	137.4	145.1	154.1	164.5	177.8	199.1	219.5	245.7
50°	112.1	118.0	123.3	128.7	135.5	144.1	152.8	165.7	182.8	204.2	228.7
52.5°	103.6	108.8	113.9	119.3	126.0	133.9	142.1	153.5	168.1	187.8	211.6
55°	92.0	95.2	100.4	105.8	111.8	119.3	127.2	136.7	149.3	165.9	185.1
57.5°	80.0	83.7	87.9	93.3	99.3	105.1	112.3	120.9	130.8	145.8	162.2
60°	73.3	76.1	79.5	85.1	90.7	95.9	102.7	110.0	119.3	132.3	146.3
62.5°	65.8	68.5	71.6	76.4	81.9	86.7	92.7	100.3	108.2	120.0	132.3
65°	53.2	57.2	60.3	64.6	69.1	74.1	78.8	84.9	92.0	101.3	112.3
67.5°	44.1	46.2	49.0	52.9	57.5	61.9	66.3	71.1	77.2	84.4	93.1
70°	40.2	40.9	41.4	45.2	49.5	53.8	57.9	62.4	67.7	73.6	81.1
72.5°	35.4	36.1	36.8	38.4	41.8	46.2	50.5	53.8	58.7	63.7	69.8
75°	28.0	29.2	29.7	30.6	31.8	34.7	38.7	41.9	44.8	48.6	53.5
77.5°	21.4	22.0	22.6	23.5	24.3	25.6	27.9	30.7	33.5	35.6	39.0
80°	17.0	17.1	17.8	18.1	19.3	20.1	21.2	23.6	26.3	27.2	29.5
82.5°	12.8	12.9	13.5	13.9	14.3	15.1	16.5	17.1	19.3	20.4	21.9
85°	7.1	6.8	7.4	7.4	7.8	8.1	8.5	9.3	9.9	11.3	11.7
87.5°	7.7	7.8	7.1	6.3	5.5	5.1	4.6	4.4	4.2	4.2	4.4
90°	27.7	28.0	24.2	20.2	16.3	12.4	9.3	7.2	5.1	2.9	0.8
92.5°	25.6	25.5	24.6	23.7	22.7	21.8	20.6	19.0	17.4	15.8	14.3
95°	51.3	51.3	51.0	50.6	50.3	49.9	48.9	47.1	45.3	43.5	41.7
97.5°	86.3	86.3	85.6	85.0	84.3	83.7	82.5	81.0	79.4	77.8	76.2
100°	110.7	110.7	110.2	109.6	109.1	108.6	107.6	106.2	104.7	103.3	101.9
102.5°	137.2	137.0	136.3	135.7	135.0	134.4	133.4	132.3	131.1	130.0	128.9
105°	176.9	176.5	176.2	175.8	175.5	175.1	174.7	174.1	173.6	173.0	172.5
107.5°	220.1	220.0	220.0	220.0	220.0	220.0	219.6	218.8	218.0	217.3	216.5
110°	249.5	249.5	249.5	249.5	249.5	249.5	249.0	248.0	246.8	245.8	244.7



TEST NUMBER: P331774-927

CATALOG NUMBER: S122RDIW-S290D970U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	279.2	279.7	279.9	280.0	280.1	280.3	279.8	278.8	277.7	276.6	275.5
115°	324.0	324.2	324.5	324.9	325.2	325.6	325.2	324.2	323.1	322.0	320.9
117.5°	367.7	368.1	369.2	370.1	371.1	372.1	371.9	370.5	369.1	367.7	366.2
120°	396.4	396.4	397.8	399.3	400.7	402.1	402.1	400.7	399.3	397.8	396.4
122.5°	426.7	427.1	428.2	429.2	430.2	431.2	430.8	429.1	427.4	425.7	424.0
125°	471.3	471.8	472.3	472.9	473.4	474.0	473.4	471.8	470.2	468.6	467.0
127.5°	514.4	515.2	515.8	516.4	517.1	517.7	517.0	515.0	512.9	510.9	508.9
130°	543.7	544.0	544.4	544.7	545.1	545.4	544.5	542.2	539.8	537.5	535.2
132.5°	572.7	573.5	573.5	573.4	573.3	573.2	572.3	570.4	568.5	566.6	564.7
135°	614.4	614.6	614.3	613.9	613.5	613.1	612.0	610.1	608.1	606.2	604.2
137.5°	654.9	655.1	654.6	654.1	653.6	653.2	652.1	650.5	649.0	647.4	645.7
140°	682.0	682.0	681.1	680.2	679.4	678.4	677.2	675.6	674.0	672.4	670.7
142.5°	706.5	706.4	705.8	705.2	704.6	704.0	702.9	701.2	699.7	698.1	696.5
145°	743.9	743.8	742.8	741.6	740.6	739.5	738.4	737.1	735.9	734.6	733.3
147.5°	776.6	776.2	775.5	774.8	774.0	773.3	772.2	770.7	769.3	767.8	766.3
150°	797.3	796.8	796.1	795.4	794.6	793.9	793.0	791.9	790.8	789.8	788.7
152.5°	817.9	817.3	816.4	815.6	814.8	813.9	812.9	811.8	810.8	809.7	808.7
155°	844.1	843.3	842.7	842.2	841.7	841.1	840.6	840.1	839.6	839.0	838.4
157.5°	868.2	867.0	866.7	866.4	866.1	865.8	865.4	865.1	864.7	864.4	864.0
160°	882.9	881.8	881.6	881.5	881.3	881.1	880.8	880.4	880.1	879.7	879.4
162.5°	895.9	894.6	894.5	894.3	894.1	893.9	893.8	893.7	893.7	893.6	893.5
165°	912.8	911.5	911.5	911.5	911.5	911.5	911.6	911.7	912.0	912.1	912.3
167.5°	926.7	925.4	925.5	925.5	925.6	925.6	925.9	926.4	926.9	927.5	928.0
170°	934.4	933.2	933.3	933.5	933.7	933.9	934.2	934.8	935.3	935.8	936.4
172.5°	940.2	938.9	939.1	939.3	939.4	939.6	940.0	940.6	941.0	941.6	942.1
175°	946.4	945.2	945.5	945.9	946.3	946.6	947.1	947.6	948.2	948.6	949.2
177.5°	949.7	948.9	949.2	949.4	949.7	950.0	950.4	950.8	951.3	951.6	952.1
180°	950.8	950.8	950.8	950.8	950.8	950.8	950.8	950.8	950.8	950.8	950.8



TEST NUMBER: P331774-927

CATALOG NUMBER: S122RDIW-S290D970U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8	517.8
2.5°	520.9	521.3	524.2	525.5	528.1	529.1	530.3	530.0	530.0	530.5	534.6
5°	522.0	525.6	531.0	536.2	541.3	545.6	548.5	551.4	552.5	557.6	562.3
7.5°	520.1	526.8	535.7	543.7	553.2	560.6	566.8	572.4	576.2	583.8	591.6
10°	517.7	527.0	537.1	547.4	560.5	570.5	580.5	588.3	590.7	602.1	608.6
12.5°	512.8	525.3	538.1	551.4	564.3	577.9	589.0	596.8	605.6	615.8	627.7
15°	505.5	519.8	536.6	553.7	572.0	588.6	600.5	613.9	623.7	634.9	645.3
17.5°	495.0	513.5	534.7	554.5	575.8	593.5	609.9	622.8	629.6	636.0	637.5
20°	486.6	506.5	531.6	554.9	576.2	596.7	612.9	623.7	625.5	625.7	616.2
22.5°	477.5	500.1	526.2	550.2	575.6	598.4	611.0	615.6	608.5	596.3	577.8
25°	460.8	487.0	517.4	544.7	572.4	594.0	598.3	590.3	565.2	538.9	505.6
27.5°	442.8	472.1	504.7	535.1	564.7	578.1	568.7	539.5	494.5	455.3	407.8
30°	429.5	462.5	494.5	528.5	555.9	561.6	540.2	497.2	444.7	385.6	338.3
32.5°	414.4	448.9	484.1	519.3	542.2	536.5	501.2	448.2	386.7	328.6	283.9
35°	392.8	428.4	466.4	501.7	516.3	491.9	439.0	370.1	307.1	253.0	222.2
37.5°	367.9	406.7	446.2	478.6	477.5	437.0	365.0	293.8	240.9	208.8	187.0
40°	350.1	389.4	432.1	459.4	447.7	395.0	316.9	249.8	211.0	185.5	169.5
42.5°	333.2	372.6	414.9	436.7	416.3	351.5	273.7	221.1	189.2	169.3	156.3
45°	304.3	345.9	385.1	397.1	360.8	289.4	221.3	183.2	161.9	147.2	138.2
47.5°	276.0	317.0	352.8	352.9	303.8	234.6	186.7	158.5	140.4	129.0	122.5
50°	258.7	297.6	327.6	323.0	267.2	208.7	167.0	142.7	127.6	118.7	111.9
52.5°	239.3	277.0	303.1	289.8	236.2	183.7	149.2	128.9	116.4	108.7	102.6
55°	211.0	244.5	262.9	242.7	192.7	152.8	126.1	110.1	100.8	94.3	89.0
57.5°	183.3	211.0	222.4	199.0	158.8	126.7	106.7	94.7	85.4	80.7	78.0
60°	165.9	189.5	197.6	171.7	138.0	110.8	94.5	83.3	76.4	73.4	70.7
62.5°	148.8	168.0	171.3	147.7	120.3	97.0	82.9	73.5	69.0	66.1	63.5
65°	123.4	137.3	135.7	116.6	95.2	77.0	66.8	61.0	57.6	53.5	49.0
67.5°	101.6	110.1	105.0	90.7	72.6	59.9	53.2	48.8	44.5	40.6	39.6
70°	87.8	92.7	87.3	74.1	59.6	50.2	44.8	39.6	37.1	36.2	34.5
72.5°	74.5	76.3	70.4	59.2	48.5	41.6	36.3	33.4	32.0	31.3	30.3
75°	55.9	54.7	49.7	40.9	33.7	29.0	27.3	26.3	25.3	24.6	24.1
77.5°	39.3	37.5	33.0	27.2	23.4	21.2	20.2	19.6	19.3	18.9	18.3
80°	29.5	28.3	23.8	19.4	17.8	16.7	16.2	15.4	15.4	15.1	14.6
82.5°	21.6	20.2	16.2	14.3	13.4	12.7	12.3	11.9	11.7	11.8	11.4
85°	11.3	9.2	8.1	7.8	7.2	6.8	7.1	6.7	6.7	6.7	6.5
87.5°	4.0	3.7	4.0	4.4	5.1	5.9	6.5	7.3	8.2	8.0	8.1
90°	2.9	5.1	7.2	9.3	12.4	16.3	20.2	24.2	28.0	27.7	27.3
92.5°	15.8	17.4	19.0	20.6	21.8	22.7	23.7	24.6	25.5	25.6	25.7
95°	43.5	45.3	47.1	48.9	49.9	50.3	50.6	51.0	51.3	51.3	51.3
97.5°	77.8	79.4	81.0	82.5	83.7	84.3	85.0	85.6	86.3	86.3	86.3
100°	103.3	104.7	106.2	107.6	108.6	109.1	109.6	110.2	110.7	110.7	110.7
102.5°	130.0	131.1	132.3	133.4	134.4	135.0	135.7	136.3	137.0	137.2	137.4
105°	173.0	173.6	174.1	174.7	175.1	175.5	175.8	176.2	176.5	176.9	177.2
107.5°	217.3	218.0	218.8	219.6	220.0	220.0	220.0	220.0	220.0	220.1	220.3
110°	245.8	246.8	248.0	249.0	249.5	249.5	249.5	249.5	249.5	249.5	249.5





TEST NUMBER: P331774-927

CATALOG NUMBER: S122RDIW-S290D970U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	276.6	277.7	278.8	279.8	280.3	280.1	280.0	279.9	279.7	279.2	278.8
115°	322.0	323.1	324.2	325.2	325.6	325.2	324.9	324.5	324.2	324.0	323.8
117.5°	367.7	369.1	370.5	371.9	372.1	371.1	370.1	369.2	368.1	367.7	367.3
120°	397.8	399.3	400.7	402.1	402.1	400.7	399.3	397.8	396.4	396.4	396.4
122.5°	425.7	427.4	429.1	430.8	431.2	430.2	429.2	428.2	427.1	426.7	426.4
125°	468.6	470.2	471.8	473.4	474.0	473.4	472.9	472.3	471.8	471.3	470.7
127.5°	510.9	512.9	515.0	517.0	517.7	517.1	516.4	515.8	515.2	514.4	513.8
130°	537.5	539.8	542.2	544.5	545.4	545.1	544.7	544.4	544.0	543.7	543.3
132.5°	566.6	568.5	570.4	572.3	573.2	573.3	573.4	573.5	573.5	572.7	572.0
135°	606.2	608.1	610.1	612.0	613.1	613.5	613.9	614.3	614.6	614.4	614.3
137.5°	647.4	649.0	650.5	652.1	653.2	653.6	654.1	654.6	655.1	654.9	654.7
140°	672.4	674.0	675.6	677.2	678.4	679.4	680.2	681.1	682.0	682.0	682.0
142.5°	698.1	699.7	701.2	702.9	704.0	704.6	705.2	705.8	706.4	706.5	706.7
145°	734.6	735.9	737.1	738.4	739.5	740.6	741.6	742.8	743.8	743.9	744.2
147.5°	767.8	769.3	770.7	772.2	773.3	774.0	774.8	775.5	776.2	776.6	777.0
150°	789.8	790.8	791.9	793.0	793.9	794.6	795.4	796.1	796.8	797.3	797.8
152.5°	809.7	810.8	811.8	812.9	813.9	814.8	815.6	816.4	817.3	817.9	818.6
155°	839.0	839.6	840.1	840.6	841.1	841.7	842.2	842.7	843.3	844.1	845.1
157.5°	864.4	864.7	865.1	865.4	865.8	866.1	866.4	866.7	867.0	868.2	869.5
160°	879.7	880.1	880.4	880.8	881.1	881.3	881.5	881.6	881.8	882.9	883.9
162.5°	893.6	893.7	893.7	893.8	893.9	894.1	894.3	894.5	894.6	895.9	897.1
165°	912.1	912.0	911.7	911.6	911.5	911.5	911.5	911.5	911.5	912.8	914.0
167.5°	927.5	926.9	926.4	925.9	925.6	925.6	925.5	925.5	925.4	926.7	928.0
170°	935.8	935.3	934.8	934.2	933.9	933.7	933.5	933.3	933.2	934.4	935.6
172.5°	941.6	941.0	940.6	940.0	939.6	939.4	939.3	939.1	938.9	940.2	941.4
175°	948.6	948.2	947.6	947.1	946.6	946.3	945.9	945.5	945.2	946.4	947.7
177.5°	951.6	951.3	950.8	950.4	950.0	949.7	949.4	949.2	948.9	949.7	950.6
180°	950.8	950.8	950.8	950.8	950.8	950.8	950.8	950.8	950.8	950.8	950.8



TEST NUMBER: P331774-927

CATALOG NUMBER: S122RDIW-S290D970U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	517.8	517.8	517.8	517.8	517.8	517.8	517.8
2.5°	536.0	537.9	538.8	538.8	539.8	539.3	538.9
5°	566.8	570.2	571.0	574.2	576.6	575.8	576.2
7.5°	597.5	602.9	608.4	610.9	611.2	612.7	613.2
10°	616.3	620.8	629.2	628.0	634.3	637.9	632.0
12.5°	634.5	640.6	646.4	648.0	651.6	652.8	650.4
15°	650.9	654.1	654.4	653.6	654.7	653.7	650.3
17.5°	635.6	630.3	619.6	614.6	610.6	604.7	602.3
20°	610.2	594.7	576.7	569.5	561.1	544.5	548.5
22.5°	555.5	537.9	519.8	498.8	488.8	473.1	472.1
25°	470.4	440.0	406.5	383.1	369.4	353.8	346.9
27.5°	365.8	327.4	300.0	286.1	273.5	261.1	260.5
30°	296.9	268.2	246.9	235.0	227.3	222.0	223.2
32.5°	250.3	230.5	216.2	206.4	200.7	196.7	196.6
35°	204.6	191.1	181.9	177.8	173.6	170.8	171.0
37.5°	175.1	167.0	161.8	157.3	154.7	153.3	152.5
40°	159.9	153.3	149.3	146.6	144.5	142.5	142.1
42.5°	148.1	142.5	138.6	136.4	134.4	133.0	132.7
45°	131.3	126.8	123.3	120.9	120.0	118.7	118.7
47.5°	116.8	112.4	109.6	108.1	106.6	105.8	105.8
50°	107.1	103.6	101.2	100.2	98.9	98.5	98.2
52.5°	98.3	95.7	94.0	93.3	92.8	92.1	92.2
55°	86.3	84.9	84.2	83.7	82.8	81.7	82.4
57.5°	76.4	75.1	73.2	71.5	70.7	69.9	70.2
60°	69.3	66.8	64.2	62.3	61.7	60.1	60.1
62.5°	60.4	56.8	53.7	52.6	52.0	51.3	51.2
65°	46.4	45.0	44.3	43.6	43.2	43.2	42.9
67.5°	38.5	37.9	37.1	36.9	36.6	36.4	36.4
70°	34.0	33.3	33.0	32.7	32.4	32.6	32.0
72.5°	29.7	29.2	29.1	28.6	28.4	28.4	28.0
75°	23.4	23.4	23.2	23.1	22.7	22.5	22.7
77.5°	18.0	18.1	17.7	17.7	17.7	17.7	17.5
80°	14.4	14.6	14.4	14.2	14.0	14.2	14.0
82.5°	11.4	11.1	11.1	11.0	11.0	10.9	10.9
85°	6.5	6.7	6.5	6.3	6.3	6.3	6.5
87.5°	7.8	7.8	7.8	7.8	7.8	7.8	7.8
90°	27.0	26.6	26.5	26.8	26.9	27.1	27.3
92.5°	25.7	25.8	25.8	25.9	25.9	26.0	26.0
95°	51.3	51.3	51.2	50.8	50.5	50.1	49.7
97.5°	86.3	86.3	86.3	86.3	86.3	86.2	86.2
100°	110.7	110.7	110.7	110.4	110.3	110.1	110.0
102.5°	137.4	137.6	137.6	137.4	137.2	137.0	136.9
105°	177.6	177.9	178.2	178.2	178.2	178.2	178.2
107.5°	220.5	220.5	220.2	219.4	218.6	217.8	217.0
110°	249.5	249.5	249.3	248.7	248.2	247.6	247.2



TEST NUMBER: P331774-927

CATALOG NUMBER: S122RDIW-S290D970U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	278.5	278.0	277.6	277.2	276.8	276.4	276.0
115°	323.6	323.4	323.1	322.6	322.0	321.5	320.9
117.5°	366.9	366.4	365.9	365.4	364.9	364.3	363.8
120°	396.4	396.4	396.1	395.5	395.1	394.5	394.0
122.5°	425.9	425.5	425.1	424.7	424.3	423.9	423.5
125°	470.2	469.7	469.3	469.1	469.0	468.7	468.6
127.5°	513.2	512.5	511.9	511.4	510.8	510.2	509.7
130°	543.0	542.6	542.0	541.3	540.6	539.9	539.2
132.5°	571.2	570.4	569.7	569.2	568.5	568.0	567.4
135°	614.1	613.9	613.5	613.0	612.4	612.0	611.4
137.5°	654.7	654.5	654.0	653.3	652.6	651.9	651.2
140°	682.0	682.0	681.7	681.0	680.2	679.5	678.8
142.5°	706.9	706.9	706.7	706.0	705.3	704.6	703.9
145°	744.3	744.5	744.3	743.5	742.8	742.1	741.4
147.5°	777.4	777.8	777.6	777.0	776.3	775.6	774.9
150°	798.4	798.9	798.9	798.4	797.8	797.3	796.8
152.5°	819.4	820.0	820.0	819.4	818.6	817.9	817.3
155°	846.0	846.8	847.0	846.5	846.0	845.4	844.9
157.5°	870.7	871.9	872.0	871.2	870.4	869.5	868.6
160°	885.0	886.1	886.3	885.6	884.9	884.2	883.4
162.5°	898.3	899.5	899.7	898.8	897.9	897.1	896.3
165°	915.2	916.5	916.6	915.8	914.9	914.0	913.1
167.5°	929.2	930.4	930.6	929.7	928.8	927.8	926.9
170°	936.9	938.2	938.3	937.2	936.1	935.0	934.0
172.5°	942.7	943.9	944.0	942.9	941.9	940.8	939.8
175°	949.0	950.1	950.3	949.2	948.2	947.1	946.0
177.5°	951.4	952.3	952.3	951.4	950.6	949.7	948.9
180°	950.8	950.8	950.8	950.8	950.8	950.8	950.8

(END OF REPORT)