

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331538-830

Luminaire Tested: **S122DIW-S675D970U830-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331538-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S675D970U830-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 970 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5929.8 lumens
Efficiency: N/A
Efficacy: 112.7 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331538-830

CATALOG NUMBER: S122DIW-S675D970U830-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331538-830

CATALOG NUMBER: S122DIW-S675D970U830-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	98	98	98	98	81	81	81	67	67	67	53	53	53	47
1	97	93	90	86	89	86	83	80	72	70	68	59	58	56	48	47	46	40
2	89	82	76	71	82	76	71	66	64	60	57	53	50	48	42	41	39	34
3	82	72	65	60	75	67	61	56	57	52	48	47	44	41	38	36	34	30
4	75	64	57	51	69	60	53	48	51	45	42	42	38	35	34	32	30	26
5	69	58	50	44	63	53	46	41	45	40	36	38	34	31	31	28	26	23
6	64	52	44	38	58	48	41	36	41	36	32	34	30	27	28	25	23	20
7	59	47	39	34	54	44	37	32	37	32	28	31	27	24	26	23	21	18
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19	16
9	51	39	32	27	47	36	30	25	31	26	23	27	23	20	22	19	17	15
10	48	36	29	24	44	34	27	23	29	24	20	25	21	18	21	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	20215	20215	20215	20215
5°	22663	20345	18029	20345
10°	25968	20179	15603	20179
15°	28727	19809	13785	19809
20°	28290	19411	12565	19411
25°	25509	18884	11794	18884
30°	21080	18040	11231	18040
35°	15364	17156	10831	17156
40°	12271	16115	10608	16115
45°	10723	14908	10305	14908
50°	10078	13742	10105	13742
55°	9292	12555	9833	12555
60°	8512	11296	9416	11296
65°	7755	10166	9005	10166
70°	7039	9064	8403	9064
75°	6245	7829	7442	7829
80°	5374	6481	5997	6481
85°	4817	4817	3557	4817



TEST NUMBER: P331538-830

CATALOG NUMBER: S122DIW-S675D970U830-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	119.2	2.0
10°-20°	346.6	5.8
20°-30°	503.1	8.5
30°-40°	530.9	9.0
40°-50°	470.0	7.9
50°-60°	375.1	6.3
60°-70°	254.9	4.3
70°-80°	130.7	2.2
80°-90°	36.0	0.6
90°-100°	71.7	1.2
100°-110°	222.6	3.8
110°-120°	380.6	6.4
120°-130°	500.5	8.4
130°-140°	561.7	9.5
140°-150°	550.8	9.3
150°-160°	462.0	7.8
160°-170°	306.4	5.2
170°-180°	107.1	1.8
0°-30°	968.9	16.3
0°-40°	1499.8	25.3
0°-60°	2344.9	39.5
0°-90°	2766.6	46.7
90°-120°	674.9	11.4
90°-150°	2287.8	38.6
90°-180°	3163.0	53.3
0°-180°	5929.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1252	1252	1252	1252	1252	
5°	1398	1255	1112	1255	1398	140
15°	1719	1185	825	1185	1719	474
25°	1432	1060	662	1060	1432	647
35°	780	870	550	870	780	507
45°	470	653	451	653	470	369
55°	330	446	349	446	330	296
65°	203	266	236	266	203	202
75°	100	126	119	126	100	107
85°	26	26	19	26	26	29
90°	32	1	32	1	32	15
95°	59	50	59	50	59	66
105°	212	205	212	205	212	223
115°	382	382	382	382	382	377
125°	558	556	558	556	558	497
135°	728	719	728	719	728	560
145°	882	872	882	872	882	551
155°	1005	998	1005	998	1005	463
165°	1086	1085	1086	1085	1086	306
175°	1126	1129	1126	1129	1126	107
180°	1131	1131	1131	1131	1131	



TEST NUMBER: P331538-830

CATALOG NUMBER: S122DIW-S675D970U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0
2.5°	1309.7	1310.0	1310.9	1304.7	1303.9	1303.9	1298.5	1293.9	1288.5	1281.2	1282.0
5°	1398.3	1403.5	1405.4	1399.7	1391.0	1390.1	1381.9	1368.4	1355.8	1345.8	1338.6
7.5°	1503.9	1506.0	1501.3	1493.6	1487.2	1475.7	1460.5	1445.6	1424.7	1405.5	1391.3
10°	1583.9	1586.9	1578.7	1567.6	1558.5	1545.0	1522.9	1500.2	1472.8	1446.3	1425.1
12.5°	1644.7	1651.9	1641.4	1639.9	1624.3	1605.8	1579.4	1568.0	1529.4	1492.5	1469.8
15°	1718.6	1718.2	1719.2	1710.1	1698.5	1695.5	1667.6	1637.4	1583.0	1561.3	1523.8
17.5°	1697.3	1704.6	1708.0	1707.9	1707.6	1705.8	1696.9	1677.7	1650.5	1615.3	1572.0
20°	1646.5	1656.1	1657.6	1668.7	1674.9	1683.1	1686.4	1681.1	1664.3	1634.9	1597.4
22.5°	1568.0	1570.7	1575.2	1592.4	1606.0	1626.5	1637.2	1655.0	1648.5	1634.2	1602.8
25°	1431.9	1427.1	1444.0	1452.6	1483.8	1516.6	1540.2	1566.1	1589.2	1603.2	1594.0
27.5°	1268.5	1261.3	1286.5	1309.5	1334.9	1370.4	1407.1	1450.5	1486.6	1531.7	1547.2
30°	1130.7	1135.0	1159.1	1183.6	1222.1	1272.1	1313.5	1361.2	1412.7	1463.2	1498.3
32.5°	982.1	998.8	1014.0	1051.6	1085.4	1141.3	1201.9	1261.5	1325.7	1383.1	1437.5
35°	779.5	798.7	819.9	847.3	894.9	950.3	1009.5	1089.8	1177.4	1255.8	1320.3
37.5°	656.1	653.0	665.2	684.9	723.6	768.2	836.3	915.8	1018.8	1111.0	1201.9
40°	582.2	580.2	588.9	607.2	636.6	669.3	729.0	798.7	894.5	1007.0	1115.3
42.5°	531.4	532.5	537.3	550.3	570.3	597.3	642.0	701.3	789.0	895.0	1011.3
45°	469.6	473.0	478.2	484.6	496.1	518.2	543.2	585.6	654.9	743.4	857.9
47.5°	425.2	425.3	430.6	436.1	443.0	455.4	475.9	502.4	551.3	623.4	721.8
50°	401.2	397.9	401.8	406.0	413.3	422.0	435.5	460.4	493.1	551.4	633.7
52.5°	372.0	372.1	375.6	377.2	383.7	392.3	404.6	422.0	451.6	497.1	564.8
55°	330.1	332.4	334.4	337.2	343.1	349.3	358.9	370.5	393.6	427.7	477.8
57.5°	290.6	291.3	293.3	298.8	302.5	308.2	317.4	327.8	342.9	368.2	405.8
60°	263.6	263.6	267.5	269.9	274.8	280.5	287.8	297.8	311.3	332.0	362.3
62.5°	239.0	238.7	240.2	244.1	247.8	253.2	260.4	269.0	281.6	300.0	325.0
65°	203.0	202.1	205.0	205.9	209.8	215.1	220.8	230.0	240.1	253.5	275.7
67.5°	168.4	169.6	171.1	173.0	175.0	180.6	184.5	191.0	199.4	210.7	225.6
70°	149.1	149.1	149.1	150.6	153.4	156.4	160.2	165.5	173.7	183.3	196.8
72.5°	127.6	129.1	130.6	129.8	133.5	135.2	139.8	142.8	150.6	156.7	168.7
75°	100.1	100.1	100.1	102.5	104.0	105.4	108.3	111.1	115.0	122.7	128.9
77.5°	74.6	74.5	74.9	75.5	77.1	78.8	79.6	82.3	85.9	89.4	94.7
80°	57.8	58.7	59.2	60.1	60.1	61.1	61.5	64.9	67.4	69.7	73.1
82.5°	44.7	44.9	45.0	45.1	45.5	46.1	47.3	48.4	49.3	51.3	53.9
85°	26.0	25.5	25.5	26.5	26.0	26.0	27.0	27.9	27.9	28.4	29.8
87.5°	16.5	16.5	16.8	16.4	16.3	16.8	16.8	16.5	17.0	17.4	16.9
90°	32.4	32.2	32.0	31.9	31.6	31.7	32.1	32.5	33.0	33.4	28.7
92.5°	30.9	30.9	30.8	30.8	30.7	30.7	30.6	30.5	30.4	30.3	29.2
95°	59.2	59.6	60.0	60.4	60.9	61.1	61.1	61.1	61.1	61.1	60.7
97.5°	102.5	102.5	102.6	102.6	102.7	102.7	102.7	102.7	102.7	102.7	101.9
100°	130.8	131.0	131.2	131.4	131.7	131.8	131.8	131.8	131.8	131.8	131.1
102.5°	162.9	163.1	163.2	163.5	163.7	163.7	163.5	163.4	163.2	163.1	162.2
105°	212.0	212.0	212.0	212.0	212.0	211.7	211.3	210.8	210.5	210.0	209.6
107.5°	258.2	259.1	260.0	261.1	262.0	262.4	262.3	262.1	261.9	261.7	261.7
110°	294.1	294.6	295.3	296.0	296.6	296.9	296.9	296.9	296.9	296.9	296.9



TEST NUMBER: P331538-830

CATALOG NUMBER: S122DIW-S675D970U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	328.4	328.9	329.3	329.8	330.3	330.7	331.3	331.8	332.2	332.8	333.0
115°	381.8	382.5	383.1	383.8	384.4	384.8	385.0	385.2	385.5	385.7	386.1
117.5°	432.8	433.5	434.1	434.8	435.4	435.9	436.5	437.0	437.5	438.0	439.2
120°	468.7	469.4	470.0	470.6	471.3	471.6	471.6	471.6	471.6	471.6	473.3
122.5°	503.9	504.4	504.8	505.3	505.8	506.2	506.7	507.3	507.7	508.2	509.4
125°	557.5	557.7	558.0	558.2	558.4	558.8	559.4	560.1	560.7	561.4	561.9
127.5°	606.4	607.1	607.8	608.4	609.1	609.8	610.6	611.3	612.1	612.9	613.7
130°	641.5	642.3	643.2	644.0	644.9	645.5	646.0	646.4	646.9	647.2	647.7
132.5°	675.1	675.8	676.5	677.2	677.9	678.6	679.6	680.5	681.5	682.4	682.3
135°	727.5	728.1	728.7	729.3	730.0	730.4	730.7	730.8	731.0	731.2	730.8
137.5°	774.8	775.6	776.5	777.3	778.2	778.7	778.9	779.0	779.2	779.4	778.8
140°	807.7	808.5	809.4	810.2	811.1	811.4	811.4	811.4	811.4	811.4	810.4
142.5°	837.4	838.3	839.1	840.0	840.8	841.1	841.0	840.8	840.7	840.5	839.8
145°	882.1	883.0	883.8	884.7	885.5	885.8	885.6	885.4	885.1	885.0	883.7
147.5°	922.0	922.8	923.6	924.4	925.2	925.4	924.9	924.4	924.0	923.5	922.7
150°	948.0	948.6	949.2	949.9	950.6	950.6	949.9	949.2	948.6	948.0	947.2
152.5°	972.4	973.2	974.0	974.9	975.6	975.6	974.9	974.0	973.2	972.4	971.4
155°	1005.2	1005.9	1006.5	1007.2	1007.8	1007.6	1006.5	1005.5	1004.4	1003.3	1002.7
157.5°	1033.5	1034.5	1035.6	1036.6	1037.6	1037.4	1035.9	1034.5	1033.0	1031.6	1031.2
160°	1051.1	1052.0	1052.8	1053.7	1054.5	1054.2	1053.0	1051.7	1050.5	1049.1	1049.0
162.5°	1066.4	1067.3	1068.4	1069.4	1070.4	1070.3	1068.7	1067.3	1065.9	1064.4	1064.2
165°	1086.4	1087.5	1088.5	1089.6	1090.6	1090.4	1088.9	1087.5	1086.0	1084.5	1084.5
167.5°	1102.9	1103.9	1105.0	1106.2	1107.2	1107.0	1105.6	1104.1	1102.6	1101.1	1101.2
170°	1111.3	1112.5	1113.8	1115.0	1116.3	1116.3	1114.7	1113.2	1111.7	1110.3	1110.5
172.5°	1118.1	1119.4	1120.7	1121.9	1123.2	1123.0	1121.6	1120.1	1118.6	1117.1	1117.4
175°	1125.6	1126.8	1128.1	1129.4	1130.7	1130.5	1129.1	1127.6	1126.1	1124.5	1125.0
177.5°	1129.0	1130.0	1131.1	1132.0	1133.0	1133.0	1132.0	1131.1	1130.0	1129.0	1129.4
180°	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2



TEST NUMBER: P331538-830

CATALOG NUMBER: S122DIW-S675D970U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0
2.5°	1284.7	1281.6	1279.7	1272.7	1266.6	1260.5	1258.5	1259.2	1250.8	1242.7	1239.3
5°	1334.7	1325.1	1316.0	1303.0	1287.6	1270.7	1262.1	1255.3	1238.5	1220.2	1209.7
7.5°	1379.6	1365.8	1348.2	1323.7	1301.4	1274.9	1258.0	1243.1	1218.4	1192.7	1176.9
10°	1406.9	1388.1	1365.5	1335.7	1308.2	1276.0	1253.4	1230.8	1201.9	1171.1	1151.9
12.5°	1430.4	1405.0	1382.8	1344.5	1312.1	1271.8	1244.9	1213.1	1182.7	1146.1	1127.3
15°	1486.3	1439.6	1397.2	1354.0	1314.0	1257.7	1227.9	1185.1	1145.1	1099.9	1078.3
17.5°	1529.5	1477.1	1410.3	1355.3	1308.7	1246.4	1202.6	1151.3	1104.1	1052.3	1022.9
20°	1554.2	1493.9	1422.3	1356.9	1301.0	1229.8	1182.2	1129.7	1074.4	1016.2	984.4
22.5°	1568.8	1505.5	1434.6	1351.0	1285.6	1216.4	1156.4	1098.9	1042.8	980.1	946.7
25°	1573.4	1515.6	1440.6	1346.2	1266.4	1188.0	1115.8	1060.0	992.1	933.4	884.9
27.5°	1550.5	1509.1	1436.9	1337.2	1244.2	1152.4	1072.0	1008.8	937.2	873.5	824.6
30°	1522.4	1498.3	1428.0	1327.9	1226.4	1127.8	1039.2	967.6	896.4	831.9	781.8
32.5°	1478.8	1473.7	1411.9	1314.8	1207.6	1096.6	1005.0	932.6	853.7	790.3	742.6
35°	1393.5	1416.5	1377.5	1285.6	1172.1	1052.3	953.2	870.4	788.6	728.0	683.2
37.5°	1278.9	1336.2	1326.1	1242.8	1124.2	1004.0	894.6	808.0	730.1	668.9	625.0
40°	1200.0	1273.1	1283.7	1210.1	1090.3	966.7	850.6	764.6	688.5	632.7	588.4
42.5°	1115.3	1200.8	1229.8	1170.8	1053.3	927.4	811.4	722.2	647.0	592.7	553.5
45°	973.4	1086.5	1138.9	1105.2	991.6	862.7	743.4	652.9	584.6	533.6	503.3
47.5°	840.7	964.2	1034.7	1022.8	923.0	795.3	677.4	590.6	524.1	483.3	456.2
50°	746.8	873.7	958.9	962.8	873.7	747.2	628.9	547.1	486.0	448.0	425.8
52.5°	665.2	786.4	879.3	899.7	818.7	697.2	585.4	504.0	450.2	415.2	395.4
55°	558.6	661.1	764.0	801.6	736.6	621.1	517.7	446.0	395.5	371.5	354.1
57.5°	464.4	549.9	645.0	686.5	646.4	547.5	450.5	388.3	347.3	326.2	312.9
60°	414.7	482.1	566.8	616.3	581.7	493.7	409.0	349.8	316.1	297.4	284.8
62.5°	368.5	428.2	499.8	545.2	526.3	443.3	367.4	315.2	286.1	268.4	259.5
65°	304.1	351.3	406.6	448.5	435.9	372.9	310.9	266.1	243.0	229.0	221.8
67.5°	250.4	284.5	322.8	359.5	349.4	304.7	255.0	220.1	202.8	190.9	186.5
70°	216.5	242.5	276.6	306.0	297.8	261.3	221.8	192.0	177.1	166.9	162.6
72.5°	184.2	205.6	231.6	255.6	250.1	219.7	186.8	164.3	152.8	143.5	139.9
75°	139.0	155.4	171.3	187.2	185.7	162.1	142.9	125.5	116.4	109.2	107.7
77.5°	102.6	111.8	122.6	132.1	129.4	115.9	100.9	91.0	84.2	79.4	78.6
80°	78.4	83.7	91.4	98.1	94.8	89.0	77.0	69.7	64.9	60.1	58.2
82.5°	56.8	62.2	66.8	70.4	67.9	62.5	55.0	50.1	47.2	44.0	43.2
85°	29.8	32.7	34.7	35.6	34.7	31.3	27.9	26.0	23.6	22.1	21.7
87.5°	16.4	15.5	14.5	14.5	12.9	12.3	10.4	8.7	8.8	9.0	8.7
90°	24.0	19.4	14.7	11.1	8.6	6.0	3.5	0.9	3.5	6.0	8.6
92.5°	28.2	27.1	25.9	24.5	22.6	20.7	18.9	17.0	18.9	20.7	22.6
95°	60.2	59.9	59.4	58.2	56.0	53.9	51.7	49.7	51.7	53.9	56.0
97.5°	101.1	100.3	99.5	98.1	96.3	94.4	92.6	90.7	92.6	94.4	96.3
100°	130.4	129.8	129.2	128.0	126.3	124.6	122.9	121.2	122.9	124.6	126.3
102.5°	161.5	160.6	159.9	158.7	157.4	156.0	154.7	153.4	154.7	156.0	157.4
105°	209.2	208.8	208.3	207.8	207.2	206.5	205.9	205.3	205.9	206.5	207.2
107.5°	261.7	261.7	261.7	261.3	260.3	259.4	258.5	257.6	258.5	259.4	260.3
110°	296.9	296.9	296.9	296.2	295.0	293.7	292.5	291.2	292.5	293.7	295.0



TEST NUMBER: P331538-830

CATALOG NUMBER: S122DIW-S675D970U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	333.1	333.3	333.5	332.9	331.7	330.4	329.1	327.8	329.1	330.4	331.7
115°	386.5	386.9	387.4	386.9	385.7	384.4	383.1	381.8	383.1	384.4	385.7
117.5°	440.4	441.6	442.7	442.5	440.8	439.1	437.4	435.7	437.4	439.1	440.8
120°	475.0	476.7	478.4	478.4	476.7	475.0	473.3	471.6	473.3	475.0	476.7
122.5°	510.7	511.8	513.0	512.6	510.6	508.5	506.5	504.4	506.5	508.5	510.6
125°	562.6	563.3	563.9	563.3	561.4	559.4	557.5	555.6	557.5	559.4	561.4
127.5°	614.4	615.2	616.0	615.1	612.7	610.3	607.8	605.5	607.8	610.3	612.7
130°	648.1	648.6	648.9	647.8	645.1	642.2	639.5	636.8	639.5	642.2	645.1
132.5°	682.2	682.1	682.0	680.9	678.6	676.4	674.1	671.8	674.1	676.4	678.6
135°	730.4	730.0	729.5	728.2	725.9	723.5	721.2	718.9	721.2	723.5	725.9
137.5°	778.3	777.7	777.2	775.9	774.0	772.1	770.2	768.3	770.2	772.1	774.0
140°	809.4	808.3	807.2	805.7	803.8	801.9	800.0	798.1	800.0	801.9	803.8
142.5°	839.1	838.3	837.6	836.3	834.3	832.5	830.6	828.7	830.6	832.5	834.3
145°	882.4	881.2	879.9	878.5	877.0	875.5	874.0	872.5	874.0	875.5	877.0
147.5°	921.8	921.0	920.1	918.8	917.0	915.3	913.5	911.7	913.5	915.3	917.0
150°	946.3	945.5	944.6	943.5	942.3	940.9	939.7	938.4	939.7	940.9	942.3
152.5°	970.3	969.4	968.4	967.2	965.9	964.7	963.4	962.1	963.4	964.7	965.9
155°	1002.1	1001.5	1000.8	1000.1	999.6	998.9	998.2	997.6	998.2	998.9	999.6
157.5°	1030.9	1030.5	1030.1	1029.6	1029.3	1028.8	1028.4	1027.9	1028.4	1028.8	1029.3
160°	1048.8	1048.6	1048.3	1048.0	1047.5	1047.2	1046.7	1046.3	1046.7	1047.2	1047.5
162.5°	1064.0	1063.8	1063.6	1063.5	1063.4	1063.3	1063.2	1063.1	1063.2	1063.3	1063.4
165°	1084.5	1084.5	1084.5	1084.6	1084.8	1085.1	1085.2	1085.4	1085.2	1085.1	1084.8
167.5°	1101.2	1101.3	1101.3	1101.6	1102.2	1102.9	1103.5	1104.2	1103.5	1102.9	1102.2
170°	1110.7	1110.9	1111.2	1111.5	1112.2	1112.9	1113.4	1114.1	1113.4	1112.9	1112.2
172.5°	1117.6	1117.8	1117.9	1118.4	1119.1	1119.6	1120.3	1121.0	1120.3	1119.6	1119.1
175°	1125.4	1125.9	1126.2	1126.8	1127.5	1128.1	1128.7	1129.4	1128.7	1128.1	1127.5
177.5°	1129.6	1130.0	1130.3	1130.8	1131.2	1131.8	1132.3	1132.8	1132.3	1131.8	1131.2
180°	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2



TEST NUMBER: P331538-830

CATALOG NUMBER: S122DIW-S675D970U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0
2.5°	1235.4	1233.1	1225.0	1220.8	1213.8	1207.3	1203.1	1205.0	1206.5	1205.8	1204.6
5°	1200.0	1190.8	1176.9	1164.9	1156.2	1140.3	1133.6	1130.2	1127.4	1124.0	1120.6
7.5°	1157.8	1143.4	1123.4	1106.3	1090.1	1070.4	1059.1	1052.3	1045.5	1037.8	1031.1
10°	1127.8	1107.6	1086.5	1062.3	1043.1	1025.3	1009.5	998.9	989.3	980.1	973.4
12.5°	1096.3	1073.0	1046.8	1013.9	992.7	967.2	964.8	946.1	931.1	925.5	917.6
15°	1046.0	1013.3	980.1	941.1	924.3	901.2	886.7	872.3	859.3	850.2	847.8
17.5°	988.9	946.6	913.6	885.6	858.0	834.3	821.0	809.5	798.8	786.6	784.9
20°	945.5	908.9	872.8	848.3	819.9	795.8	779.5	767.9	758.7	751.6	745.3
22.5°	904.3	864.2	831.2	804.4	776.4	757.0	744.0	732.9	725.3	717.3	711.4
25°	838.2	806.9	770.8	740.5	717.4	704.9	694.3	684.7	679.9	674.6	667.9
27.5°	780.3	745.6	711.8	688.3	668.1	657.0	649.4	642.9	638.4	635.3	631.5
30°	739.5	704.4	678.0	654.9	638.0	627.0	622.2	618.3	613.0	611.1	609.2
32.5°	700.3	668.6	646.0	625.9	609.9	602.7	598.2	594.8	590.7	588.7	584.8
35°	644.7	618.3	596.2	585.0	572.1	565.8	562.5	557.6	553.8	551.9	551.4
37.5°	592.5	569.5	555.0	540.7	535.3	531.4	526.8	523.5	522.4	522.1	521.6
40°	558.6	539.9	526.9	515.3	512.9	507.1	503.3	500.4	500.4	500.9	500.4
42.5°	527.8	511.0	499.5	489.6	486.7	483.2	479.4	479.2	480.0	481.6	480.0
45°	481.2	469.1	460.9	456.1	450.8	447.4	447.0	448.5	448.9	449.4	450.8
47.5°	438.2	430.3	422.8	417.5	415.2	414.6	414.1	416.6	418.9	419.7	422.0
50°	412.8	403.7	397.5	394.1	392.1	391.2	391.2	395.0	396.9	399.4	400.8
52.5°	384.4	377.9	373.5	371.0	370.2	370.8	371.0	374.3	377.3	378.1	378.9
55°	345.0	340.2	339.2	334.9	336.8	336.3	338.7	340.6	343.6	346.4	346.9
57.5°	305.8	301.9	299.3	299.6	300.2	302.4	304.3	307.7	310.9	313.9	314.1
60°	279.6	277.6	276.2	276.2	277.1	280.0	282.5	285.8	287.8	289.6	291.1
62.5°	255.7	253.7	252.3	253.1	255.6	257.3	260.1	261.9	263.8	265.8	266.5
65°	217.9	217.0	218.5	219.4	219.9	222.3	225.6	227.1	229.0	230.0	233.4
67.5°	183.2	183.4	183.2	184.5	187.4	187.9	191.1	194.4	194.8	196.7	198.9
70°	159.8	160.7	161.6	162.6	165.0	166.0	168.4	169.8	171.7	173.2	174.7
72.5°	138.2	138.4	139.3	139.1	141.2	143.3	145.3	146.8	148.6	150.5	151.9
75°	106.3	106.3	107.3	107.7	110.2	112.6	112.1	113.1	115.0	116.9	117.9
77.5°	77.7	76.6	77.7	78.1	78.9	81.0	81.3	82.7	84.8	84.2	85.3
80°	59.2	57.8	59.2	59.7	59.7	62.1	62.1	63.1	64.5	63.1	64.5
82.5°	42.2	41.6	42.6	42.7	43.5	43.5	44.4	44.6	46.0	45.3	46.0
85°	21.2	20.7	21.2	20.7	21.2	21.7	21.7	21.2	21.2	22.1	20.7
87.5°	8.8	9.1	9.6	10.6	11.1	11.7	11.2	11.1	11.0	10.2	10.2
90°	11.1	14.7	19.4	24.0	28.7	33.4	33.0	32.5	32.1	31.7	31.6
92.5°	24.5	25.9	27.1	28.2	29.2	30.3	30.4	30.5	30.6	30.7	30.7
95°	58.2	59.4	59.9	60.2	60.7	61.1	61.1	61.1	61.1	61.1	60.9
97.5°	98.1	99.5	100.3	101.1	101.9	102.7	102.7	102.7	102.7	102.7	102.7
100°	128.0	129.2	129.8	130.4	131.1	131.8	131.8	131.8	131.8	131.8	131.7
102.5°	158.7	159.9	160.6	161.5	162.2	163.1	163.2	163.4	163.5	163.7	163.7
105°	207.8	208.3	208.8	209.2	209.6	210.0	210.5	210.8	211.3	211.7	212.0
107.5°	261.3	261.7	261.7	261.7	261.7	261.7	261.9	262.1	262.3	262.4	262.0
110°	296.2	296.9	296.9	296.9	296.9	296.9	296.9	296.9	296.9	296.9	296.6



TEST NUMBER: P331538-830

CATALOG NUMBER: S122DIW-S675D970U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	332.9	333.5	333.3	333.1	333.0	332.8	332.2	331.8	331.3	330.7	330.3
115°	386.9	387.4	386.9	386.5	386.1	385.7	385.5	385.2	385.0	384.8	384.4
117.5°	442.5	442.7	441.6	440.4	439.2	438.0	437.5	437.0	436.5	435.9	435.4
120°	478.4	478.4	476.7	475.0	473.3	471.6	471.6	471.6	471.6	471.6	471.3
122.5°	512.6	513.0	511.8	510.7	509.4	508.2	507.7	507.3	506.7	506.2	505.8
125°	563.3	563.9	563.3	562.6	561.9	561.4	560.7	560.1	559.4	558.8	558.4
127.5°	615.1	616.0	615.2	614.4	613.7	612.9	612.1	611.3	610.6	609.8	609.1
130°	647.8	648.9	648.6	648.1	647.7	647.2	646.9	646.4	646.0	645.5	644.9
132.5°	680.9	682.0	682.1	682.2	682.3	682.4	681.5	680.5	679.6	678.6	677.9
135°	728.2	729.5	730.0	730.4	730.8	731.2	731.0	730.8	730.7	730.4	730.0
137.5°	775.9	777.2	777.7	778.3	778.8	779.4	779.2	779.0	778.9	778.7	778.2
140°	805.7	807.2	808.3	809.4	810.4	811.4	811.4	811.4	811.4	811.4	811.1
142.5°	836.3	837.6	838.3	839.1	839.8	840.5	840.7	840.8	841.0	841.1	840.8
145°	878.5	879.9	881.2	882.4	883.7	885.0	885.1	885.4	885.6	885.8	885.5
147.5°	918.8	920.1	921.0	921.8	922.7	923.5	924.0	924.4	924.9	925.4	925.2
150°	943.5	944.6	945.5	946.3	947.2	948.0	948.6	949.2	949.9	950.6	950.6
152.5°	967.2	968.4	969.4	970.3	971.4	972.4	973.2	974.0	974.9	975.6	975.6
155°	1000.1	1000.8	1001.5	1002.1	1002.7	1003.3	1004.4	1005.5	1006.5	1007.6	1007.8
157.5°	1029.6	1030.1	1030.5	1030.9	1031.2	1031.6	1033.0	1034.5	1035.9	1037.4	1037.6
160°	1048.0	1048.3	1048.6	1048.8	1049.0	1049.1	1050.5	1051.7	1053.0	1054.2	1054.5
162.5°	1063.5	1063.6	1063.8	1064.0	1064.2	1064.4	1065.9	1067.3	1068.7	1070.3	1070.4
165°	1084.6	1084.5	1084.5	1084.5	1084.5	1084.5	1086.0	1087.5	1088.9	1090.4	1090.6
167.5°	1101.6	1101.3	1101.3	1101.2	1101.2	1101.1	1102.6	1104.1	1105.6	1107.0	1107.2
170°	1111.5	1111.2	1110.9	1110.7	1110.5	1110.3	1111.7	1113.2	1114.7	1116.3	1116.3
172.5°	1118.4	1117.9	1117.8	1117.6	1117.4	1117.1	1118.6	1120.1	1121.6	1123.0	1123.2
175°	1126.8	1126.2	1125.9	1125.4	1125.0	1124.5	1126.1	1127.6	1129.1	1130.5	1130.7
177.5°	1130.8	1130.3	1130.0	1129.6	1129.4	1129.0	1130.0	1131.1	1132.0	1133.0	1133.0
180°	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2



TEST NUMBER: P331538-830

CATALOG NUMBER: S122DIW-S675D970U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0
2.5°	1200.8	1200.0	1200.0	1196.6	1200.0	1200.0	1200.8	1204.6	1205.8	1206.5	1205.0
5°	1113.9	1112.4	1110.0	1112.4	1110.0	1112.4	1113.9	1120.6	1124.0	1127.4	1130.2
7.5°	1027.9	1022.2	1021.3	1015.6	1021.3	1022.2	1027.9	1031.1	1037.8	1045.5	1052.3
10°	965.2	961.3	960.8	951.7	960.8	961.3	965.2	973.4	980.1	989.3	998.9
12.5°	917.5	908.2	910.0	904.7	910.0	908.2	917.5	917.6	925.5	931.1	946.1
15°	834.8	834.8	832.8	824.7	832.8	834.8	834.8	847.8	850.2	859.3	872.3
17.5°	775.4	774.5	769.9	772.1	769.9	774.5	775.4	784.9	786.6	798.8	809.5
20°	740.0	737.2	731.3	731.3	731.3	737.2	740.0	745.3	751.6	758.7	767.9
22.5°	706.5	706.3	700.2	702.1	700.2	706.3	706.5	711.4	717.3	725.3	732.9
25°	667.3	663.5	660.6	662.0	660.6	663.5	667.3	667.9	674.6	679.9	684.7
27.5°	630.2	628.1	627.9	624.0	627.9	628.1	630.2	631.5	635.3	638.4	642.9
30°	608.7	603.9	604.8	602.4	604.8	603.9	608.7	609.2	611.1	613.0	618.3
32.5°	584.0	582.3	581.4	579.3	581.4	582.3	584.0	584.8	588.7	590.7	594.8
35°	550.4	550.9	548.6	549.5	548.6	550.9	550.4	551.4	551.9	553.8	557.6
37.5°	521.1	522.6	521.5	521.8	521.5	522.6	521.1	521.6	522.1	522.4	523.5
40°	501.8	501.8	501.8	503.3	501.8	501.8	501.8	500.4	500.9	500.4	500.4
42.5°	483.3	482.6	481.8	481.7	481.8	482.6	483.3	480.0	481.6	480.0	479.2
45°	451.8	453.3	453.7	451.3	453.7	453.3	451.8	450.8	449.4	448.9	448.5
47.5°	423.2	423.4	423.2	425.4	423.2	423.4	423.2	422.0	419.7	418.9	416.6
50°	403.2	402.3	403.2	402.3	403.2	402.3	403.2	400.8	399.4	396.9	395.0
52.5°	382.0	382.2	381.6	381.4	381.6	382.2	382.0	378.9	378.1	377.3	374.3
55°	348.8	349.8	349.3	349.3	349.3	349.8	348.8	346.9	346.4	343.6	340.6
57.5°	314.5	315.4	316.0	313.9	316.0	315.4	314.5	314.1	313.9	310.9	307.7
60°	290.6	293.0	292.6	291.6	292.6	293.0	290.6	291.1	289.6	287.8	285.8
62.5°	268.7	269.6	269.5	269.3	269.5	269.6	268.7	266.5	265.8	263.8	261.9
65°	234.8	235.7	234.3	235.7	234.3	235.7	234.8	233.4	230.0	229.0	227.1
67.5°	198.3	198.6	199.7	200.4	199.7	198.6	198.3	198.9	196.7	194.8	194.4
70°	175.6	175.1	176.5	178.0	176.5	175.1	175.6	174.7	173.2	171.7	169.8
72.5°	151.7	152.8	152.3	153.4	152.3	152.8	151.7	151.9	150.5	148.6	146.8
75°	116.9	118.4	117.9	119.3	117.9	118.4	116.9	117.9	116.9	115.0	113.1
77.5°	84.5	84.6	84.5	85.3	84.5	84.6	84.5	85.3	84.2	84.8	82.7
80°	64.5	63.5	62.6	64.5	62.6	63.5	64.5	64.5	63.1	64.5	63.1
82.5°	44.9	45.4	44.5	44.5	44.5	45.4	44.9	46.0	45.3	46.0	44.6
85°	20.7	20.2	19.2	19.2	19.2	20.2	20.7	20.7	22.1	21.2	21.2
87.5°	10.2	9.9	9.9	9.6	9.9	9.9	10.2	10.2	10.2	11.0	11.1
90°	31.9	32.0	32.2	32.4	32.2	32.0	31.9	31.6	31.7	32.1	32.5
92.5°	30.8	30.8	30.9	30.9	30.9	30.8	30.8	30.7	30.7	30.6	30.5
95°	60.4	60.0	59.6	59.2	59.6	60.0	60.4	60.9	61.1	61.1	61.1
97.5°	102.6	102.6	102.5	102.5	102.5	102.6	102.6	102.7	102.7	102.7	102.7
100°	131.4	131.2	131.0	130.8	131.0	131.2	131.4	131.7	131.8	131.8	131.8
102.5°	163.5	163.2	163.1	162.9	163.1	163.2	163.5	163.7	163.7	163.5	163.4
105°	212.0	212.0	212.0	212.0	212.0	212.0	212.0	212.0	211.7	211.3	210.8
107.5°	261.1	260.0	259.1	258.2	259.1	260.0	261.1	262.0	262.4	262.3	262.1
110°	296.0	295.3	294.6	294.1	294.6	295.3	296.0	296.6	296.9	296.9	296.9



TEST NUMBER: P331538-830

CATALOG NUMBER: S122DIW-S675D970U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	329.8	329.3	328.9	328.4	328.9	329.3	329.8	330.3	330.7	331.3	331.8
115°	383.8	383.1	382.5	381.8	382.5	383.1	383.8	384.4	384.8	385.0	385.2
117.5°	434.8	434.1	433.5	432.8	433.5	434.1	434.8	435.4	435.9	436.5	437.0
120°	470.6	470.0	469.4	468.7	469.4	470.0	470.6	471.3	471.6	471.6	471.6
122.5°	505.3	504.8	504.4	503.9	504.4	504.8	505.3	505.8	506.2	506.7	507.3
125°	558.2	558.0	557.7	557.5	557.7	558.0	558.2	558.4	558.8	559.4	560.1
127.5°	608.4	607.8	607.1	606.4	607.1	607.8	608.4	609.1	609.8	610.6	611.3
130°	644.0	643.2	642.3	641.5	642.3	643.2	644.0	644.9	645.5	646.0	646.4
132.5°	677.2	676.5	675.8	675.1	675.8	676.5	677.2	677.9	678.6	679.6	680.5
135°	729.3	728.7	728.1	727.5	728.1	728.7	729.3	730.0	730.4	730.7	730.8
137.5°	777.3	776.5	775.6	774.8	775.6	776.5	777.3	778.2	778.7	778.9	779.0
140°	810.2	809.4	808.5	807.7	808.5	809.4	810.2	811.1	811.4	811.4	811.4
142.5°	840.0	839.1	838.3	837.4	838.3	839.1	840.0	840.8	841.1	841.0	840.8
145°	884.7	883.8	883.0	882.1	883.0	883.8	884.7	885.5	885.8	885.6	885.4
147.5°	924.4	923.6	922.8	922.0	922.8	923.6	924.4	925.2	925.4	924.9	924.4
150°	949.9	949.2	948.6	948.0	948.6	949.2	949.9	950.6	950.6	949.9	949.2
152.5°	974.9	974.0	973.2	972.4	973.2	974.0	974.9	975.6	975.6	974.9	974.0
155°	1007.2	1006.5	1005.9	1005.2	1005.9	1006.5	1007.2	1007.8	1007.6	1006.5	1005.5
157.5°	1036.6	1035.6	1034.5	1033.5	1034.5	1035.6	1036.6	1037.6	1037.4	1035.9	1034.5
160°	1053.7	1052.8	1052.0	1051.1	1052.0	1052.8	1053.7	1054.5	1054.2	1053.0	1051.7
162.5°	1069.4	1068.4	1067.3	1066.4	1067.3	1068.4	1069.4	1070.4	1070.3	1068.7	1067.3
165°	1089.6	1088.5	1087.5	1086.4	1087.5	1088.5	1089.6	1090.6	1090.4	1088.9	1087.5
167.5°	1106.2	1105.0	1103.9	1102.9	1103.9	1105.0	1106.2	1107.2	1107.0	1105.6	1104.1
170°	1115.0	1113.8	1112.5	1111.3	1112.5	1113.8	1115.0	1116.3	1116.3	1114.7	1113.2
172.5°	1121.9	1120.7	1119.4	1118.1	1119.4	1120.7	1121.9	1123.2	1123.0	1121.6	1120.1
175°	1129.4	1128.1	1126.8	1125.6	1126.8	1128.1	1129.4	1130.7	1130.5	1129.1	1127.6
177.5°	1132.0	1131.1	1130.0	1129.0	1130.0	1131.1	1132.0	1133.0	1133.0	1132.0	1131.1
180°	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2



TEST NUMBER: P331538-830

CATALOG NUMBER: S122DIW-S675D970U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0
2.5°	1203.1	1207.3	1213.8	1220.8	1225.0	1233.1	1235.4	1239.3	1242.7	1250.8	1259.2
5°	1133.6	1140.3	1156.2	1164.9	1176.9	1190.8	1200.0	1209.7	1220.2	1238.5	1255.3
7.5°	1059.1	1070.4	1090.1	1106.3	1123.4	1143.4	1157.8	1176.9	1192.7	1218.4	1243.1
10°	1009.5	1025.3	1043.1	1062.3	1086.5	1107.6	1127.8	1151.9	1171.1	1201.9	1230.8
12.5°	964.8	967.2	992.7	1013.9	1046.8	1073.0	1096.3	1127.3	1146.1	1182.7	1213.1
15°	886.7	901.2	924.3	941.1	980.1	1013.3	1046.0	1078.3	1099.9	1145.1	1185.1
17.5°	821.0	834.3	858.0	885.6	913.6	946.6	988.9	1022.9	1052.3	1104.1	1151.3
20°	779.5	795.8	819.9	848.3	872.8	908.9	945.5	984.4	1016.2	1074.4	1129.7
22.5°	744.0	757.0	776.4	804.4	831.2	864.2	904.3	946.7	980.1	1042.8	1098.9
25°	694.3	704.9	717.4	740.5	770.8	806.9	838.2	884.9	933.4	992.1	1060.0
27.5°	649.4	657.0	668.1	688.3	711.8	745.6	780.3	824.6	873.5	937.2	1008.8
30°	622.2	627.0	638.0	654.9	678.0	704.4	739.5	781.8	831.9	896.4	967.6
32.5°	598.2	602.7	609.9	625.9	646.0	668.6	700.3	742.6	790.3	853.7	932.6
35°	562.5	565.8	572.1	585.0	596.2	618.3	644.7	683.2	728.0	788.6	870.4
37.5°	526.8	531.4	535.3	540.7	555.0	569.5	592.5	625.0	668.9	730.1	808.0
40°	503.3	507.1	512.9	515.3	526.9	539.9	558.6	588.4	632.7	688.5	764.6
42.5°	479.4	483.2	486.7	489.6	499.5	511.0	527.8	553.5	592.7	647.0	722.2
45°	447.0	447.4	450.8	456.1	460.9	469.1	481.2	503.3	533.6	584.6	652.9
47.5°	414.1	414.6	415.2	417.5	422.8	430.3	438.2	456.2	483.3	524.1	590.6
50°	392.1	391.2	392.1	394.1	397.5	403.7	412.8	425.8	448.0	486.0	547.1
52.5°	371.0	370.8	370.2	371.0	373.5	377.9	384.4	395.4	415.2	450.2	504.0
55°	338.7	336.3	336.8	334.9	339.2	340.2	345.0	354.1	371.5	395.5	446.0
57.5°	304.3	302.4	300.2	299.6	299.3	301.9	305.8	312.9	326.2	347.3	388.3
60°	282.5	280.0	277.1	276.2	276.2	277.6	279.6	284.8	297.4	316.1	349.8
62.5°	260.1	257.3	255.6	253.1	252.3	253.7	255.7	259.5	268.4	286.1	315.2
65°	225.6	222.3	219.9	219.4	218.5	217.0	217.9	221.8	229.0	243.0	266.1
67.5°	191.1	187.9	187.4	184.5	183.2	183.4	183.2	186.5	190.9	202.8	220.1
70°	168.4	166.0	165.0	162.6	161.6	160.7	159.8	162.6	166.9	177.1	192.0
72.5°	145.3	143.3	141.2	139.1	139.3	138.4	138.2	139.9	143.5	152.8	164.3
75°	112.1	112.6	110.2	107.7	107.3	106.3	106.3	107.7	109.2	116.4	125.5
77.5°	81.3	81.0	78.9	78.1	77.7	76.6	77.7	78.6	79.4	84.2	91.0
80°	62.1	62.1	59.7	59.7	59.2	57.8	59.2	58.2	60.1	64.9	69.7
82.5°	44.4	43.5	43.5	42.7	42.6	41.6	42.2	43.2	44.0	47.2	50.1
85°	21.7	21.7	21.2	20.7	21.2	20.7	21.2	21.7	22.1	23.6	26.0
87.5°	11.2	11.7	11.1	10.6	9.6	9.1	8.8	8.7	9.0	8.8	8.7
90°	33.0	33.4	28.7	24.0	19.4	14.7	11.1	8.6	6.0	3.5	0.9
92.5°	30.4	30.3	29.2	28.2	27.1	25.9	24.5	22.6	20.7	18.9	17.0
95°	61.1	61.1	60.7	60.2	59.9	59.4	58.2	56.0	53.9	51.7	49.7
97.5°	102.7	102.7	101.9	101.1	100.3	99.5	98.1	96.3	94.4	92.6	90.7
100°	131.8	131.8	131.1	130.4	129.8	129.2	128.0	126.3	124.6	122.9	121.2
102.5°	163.2	163.1	162.2	161.5	160.6	159.9	158.7	157.4	156.0	154.7	153.4
105°	210.5	210.0	209.6	209.2	208.8	208.3	207.8	207.2	206.5	205.9	205.3
107.5°	261.9	261.7	261.7	261.7	261.7	261.7	261.3	260.3	259.4	258.5	257.6
110°	296.9	296.9	296.9	296.9	296.9	296.9	296.2	295.0	293.7	292.5	291.2



TEST NUMBER: P331538-830

CATALOG NUMBER: S122DIW-S675D970U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	332.2	332.8	333.0	333.1	333.3	333.5	332.9	331.7	330.4	329.1	327.8
115°	385.5	385.7	386.1	386.5	386.9	387.4	386.9	385.7	384.4	383.1	381.8
117.5°	437.5	438.0	439.2	440.4	441.6	442.7	442.5	440.8	439.1	437.4	435.7
120°	471.6	471.6	473.3	475.0	476.7	478.4	478.4	476.7	475.0	473.3	471.6
122.5°	507.7	508.2	509.4	510.7	511.8	513.0	512.6	510.6	508.5	506.5	504.4
125°	560.7	561.4	561.9	562.6	563.3	563.9	563.3	561.4	559.4	557.5	555.6
127.5°	612.1	612.9	613.7	614.4	615.2	616.0	615.1	612.7	610.3	607.8	605.5
130°	646.9	647.2	647.7	648.1	648.6	648.9	647.8	645.1	642.2	639.5	636.8
132.5°	681.5	682.4	682.3	682.2	682.1	682.0	680.9	678.6	676.4	674.1	671.8
135°	731.0	731.2	730.8	730.4	730.0	729.5	728.2	725.9	723.5	721.2	718.9
137.5°	779.2	779.4	778.8	778.3	777.7	777.2	775.9	774.0	772.1	770.2	768.3
140°	811.4	811.4	810.4	809.4	808.3	807.2	805.7	803.8	801.9	800.0	798.1
142.5°	840.7	840.5	839.8	839.1	838.3	837.6	836.3	834.3	832.5	830.6	828.7
145°	885.1	885.0	883.7	882.4	881.2	879.9	878.5	877.0	875.5	874.0	872.5
147.5°	924.0	923.5	922.7	921.8	921.0	920.1	918.8	917.0	915.3	913.5	911.7
150°	948.6	948.0	947.2	946.3	945.5	944.6	943.5	942.3	940.9	939.7	938.4
152.5°	973.2	972.4	971.4	970.3	969.4	968.4	967.2	965.9	964.7	963.4	962.1
155°	1004.4	1003.3	1002.7	1002.1	1001.5	1000.8	1000.1	999.6	998.9	998.2	997.6
157.5°	1033.0	1031.6	1031.2	1030.9	1030.5	1030.1	1029.6	1029.3	1028.8	1028.4	1027.9
160°	1050.5	1049.1	1049.0	1048.8	1048.6	1048.3	1048.0	1047.5	1047.2	1046.7	1046.3
162.5°	1065.9	1064.4	1064.2	1064.0	1063.8	1063.6	1063.5	1063.4	1063.3	1063.2	1063.1
165°	1086.0	1084.5	1084.5	1084.5	1084.5	1084.5	1084.6	1084.8	1085.1	1085.2	1085.4
167.5°	1102.6	1101.1	1101.2	1101.2	1101.3	1101.3	1101.6	1102.2	1102.9	1103.5	1104.2
170°	1111.7	1110.3	1110.5	1110.7	1110.9	1111.2	1111.5	1112.2	1112.9	1113.4	1114.1
172.5°	1118.6	1117.1	1117.4	1117.6	1117.8	1117.9	1118.4	1119.1	1119.6	1120.3	1121.0
175°	1126.1	1124.5	1125.0	1125.4	1125.9	1126.2	1126.8	1127.5	1128.1	1128.7	1129.4
177.5°	1130.0	1129.0	1129.4	1129.6	1130.0	1130.3	1130.8	1131.2	1131.8	1132.3	1132.8
180°	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2



TEST NUMBER: P331538-830

CATALOG NUMBER: S122DIW-S675D970U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0
2.5°	1258.5	1260.5	1266.6	1272.7	1279.7	1281.6	1284.7	1282.0	1281.2	1288.5	1293.9
5°	1262.1	1270.7	1287.6	1303.0	1316.0	1325.1	1334.7	1338.6	1345.8	1355.8	1368.4
7.5°	1258.0	1274.9	1301.4	1323.7	1348.2	1365.8	1379.6	1391.3	1405.5	1424.7	1445.6
10°	1253.4	1276.0	1308.2	1335.7	1365.5	1388.1	1406.9	1425.1	1446.3	1472.8	1500.2
12.5°	1244.9	1271.8	1312.1	1344.5	1382.8	1405.0	1430.4	1469.8	1492.5	1529.4	1568.0
15°	1227.9	1257.7	1314.0	1354.0	1397.2	1439.6	1486.3	1523.8	1561.3	1583.0	1637.4
17.5°	1202.6	1246.4	1308.7	1355.3	1410.3	1477.1	1529.5	1572.0	1615.3	1650.5	1677.7
20°	1182.2	1229.8	1301.0	1356.9	1422.3	1493.9	1554.2	1597.4	1634.9	1664.3	1681.1
22.5°	1156.4	1216.4	1285.6	1351.0	1434.6	1505.5	1568.8	1602.8	1634.2	1648.5	1655.0
25°	1115.8	1188.0	1266.4	1346.2	1440.6	1515.6	1573.4	1594.0	1603.2	1589.2	1566.1
27.5°	1072.0	1152.4	1244.2	1337.2	1436.9	1509.1	1550.5	1547.2	1531.7	1486.6	1450.5
30°	1039.2	1127.8	1226.4	1327.9	1428.0	1498.3	1522.4	1498.3	1463.2	1412.7	1361.2
32.5°	1005.0	1096.6	1207.6	1314.8	1411.9	1473.7	1478.8	1437.5	1383.1	1325.7	1261.5
35°	953.2	1052.3	1172.1	1285.6	1377.5	1416.5	1393.5	1320.3	1255.8	1177.4	1089.8
37.5°	894.6	1004.0	1124.2	1242.8	1326.1	1336.2	1278.9	1201.9	1111.0	1018.8	915.8
40°	850.6	966.7	1090.3	1210.1	1283.7	1273.1	1200.0	1115.3	1007.0	894.5	798.7
42.5°	811.4	927.4	1053.3	1170.8	1229.8	1200.8	1115.3	1011.3	895.0	789.0	701.3
45°	743.4	862.7	991.6	1105.2	1138.9	1086.5	973.4	857.9	743.4	654.9	585.6
47.5°	677.4	795.3	923.0	1022.8	1034.7	964.2	840.7	721.8	623.4	551.3	502.4
50°	628.9	747.2	873.7	962.8	958.9	873.7	746.8	633.7	551.4	493.1	460.4
52.5°	585.4	697.2	818.7	899.7	879.3	786.4	665.2	564.8	497.1	451.6	422.0
55°	517.7	621.1	736.6	801.6	764.0	661.1	558.6	477.8	427.7	393.6	370.5
57.5°	450.5	547.5	646.4	686.5	645.0	549.9	464.4	405.8	368.2	342.9	327.8
60°	409.0	493.7	581.7	616.3	566.8	482.1	414.7	362.3	332.0	311.3	297.8
62.5°	367.4	443.3	526.3	545.2	499.8	428.2	368.5	325.0	300.0	281.6	269.0
65°	310.9	372.9	435.9	448.5	406.6	351.3	304.1	275.7	253.5	240.1	230.0
67.5°	255.0	304.7	349.4	359.5	322.8	284.5	250.4	225.6	210.7	199.4	191.0
70°	221.8	261.3	297.8	306.0	276.6	242.5	216.5	196.8	183.3	173.7	165.5
72.5°	186.8	219.7	250.1	255.6	231.6	205.6	184.2	168.7	156.7	150.6	142.8
75°	142.9	162.1	185.7	187.2	171.3	155.4	139.0	128.9	122.7	115.0	111.1
77.5°	100.9	115.9	129.4	132.1	122.6	111.8	102.6	94.7	89.4	85.9	82.3
80°	77.0	89.0	94.8	98.1	91.4	83.7	78.4	73.1	69.7	67.4	64.9
82.5°	55.0	62.5	67.9	70.4	66.8	62.2	56.8	53.9	51.3	49.3	48.4
85°	27.9	31.3	34.7	35.6	34.7	32.7	29.8	29.8	28.4	27.9	27.9
87.5°	10.4	12.3	12.9	14.5	14.5	15.5	16.4	16.9	17.4	17.0	16.5
90°	3.5	6.0	8.6	11.1	14.7	19.4	24.0	28.7	33.4	33.0	32.5
92.5°	18.9	20.7	22.6	24.5	25.9	27.1	28.2	29.2	30.3	30.4	30.5
95°	51.7	53.9	56.0	58.2	59.4	59.9	60.2	60.7	61.1	61.1	61.1
97.5°	92.6	94.4	96.3	98.1	99.5	100.3	101.1	101.9	102.7	102.7	102.7
100°	122.9	124.6	126.3	128.0	129.2	129.8	130.4	131.1	131.8	131.8	131.8
102.5°	154.7	156.0	157.4	158.7	159.9	160.6	161.5	162.2	163.1	163.2	163.4
105°	205.9	206.5	207.2	207.8	208.3	208.8	209.2	209.6	210.0	210.5	210.8
107.5°	258.5	259.4	260.3	261.3	261.7	261.7	261.7	261.7	261.7	261.9	262.1
110°	292.5	293.7	295.0	296.2	296.9	296.9	296.9	296.9	296.9	296.9	296.9



TEST NUMBER: P331538-830

CATALOG NUMBER: S122DIW-S675D970U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	329.1	330.4	331.7	332.9	333.5	333.3	333.1	333.0	332.8	332.2	331.8
115°	383.1	384.4	385.7	386.9	387.4	386.9	386.5	386.1	385.7	385.5	385.2
117.5°	437.4	439.1	440.8	442.5	442.7	441.6	440.4	439.2	438.0	437.5	437.0
120°	473.3	475.0	476.7	478.4	478.4	476.7	475.0	473.3	471.6	471.6	471.6
122.5°	506.5	508.5	510.6	512.6	513.0	511.8	510.7	509.4	508.2	507.7	507.3
125°	557.5	559.4	561.4	563.3	563.9	563.3	562.6	561.9	561.4	560.7	560.1
127.5°	607.8	610.3	612.7	615.1	616.0	615.2	614.4	613.7	612.9	612.1	611.3
130°	639.5	642.2	645.1	647.8	648.9	648.6	648.1	647.7	647.2	646.9	646.4
132.5°	674.1	676.4	678.6	680.9	682.0	682.1	682.2	682.3	682.4	681.5	680.5
135°	721.2	723.5	725.9	728.2	729.5	730.0	730.4	730.8	731.2	731.0	730.8
137.5°	770.2	772.1	774.0	775.9	777.2	777.7	778.3	778.8	779.4	779.2	779.0
140°	800.0	801.9	803.8	805.7	807.2	808.3	809.4	810.4	811.4	811.4	811.4
142.5°	830.6	832.5	834.3	836.3	837.6	838.3	839.1	839.8	840.5	840.7	840.8
145°	874.0	875.5	877.0	878.5	879.9	881.2	882.4	883.7	885.0	885.1	885.4
147.5°	913.5	915.3	917.0	918.8	920.1	921.0	921.8	922.7	923.5	924.0	924.4
150°	939.7	940.9	942.3	943.5	944.6	945.5	946.3	947.2	948.0	948.6	949.2
152.5°	963.4	964.7	965.9	967.2	968.4	969.4	970.3	971.4	972.4	973.2	974.0
155°	998.2	998.9	999.6	1000.1	1000.8	1001.5	1002.1	1002.7	1003.3	1004.4	1005.5
157.5°	1028.4	1028.8	1029.3	1029.6	1030.1	1030.5	1030.9	1031.2	1031.6	1033.0	1034.5
160°	1046.7	1047.2	1047.5	1048.0	1048.3	1048.6	1048.8	1049.0	1049.1	1050.5	1051.7
162.5°	1063.2	1063.3	1063.4	1063.5	1063.6	1063.8	1064.0	1064.2	1064.4	1065.9	1067.3
165°	1085.2	1085.1	1084.8	1084.6	1084.5	1084.5	1084.5	1084.5	1084.5	1086.0	1087.5
167.5°	1103.5	1102.9	1102.2	1101.6	1101.3	1101.3	1101.2	1101.2	1101.1	1102.6	1104.1
170°	1113.4	1112.9	1112.2	1111.5	1111.2	1110.9	1110.7	1110.5	1110.3	1111.7	1113.2
172.5°	1120.3	1119.6	1119.1	1118.4	1117.9	1117.8	1117.6	1117.4	1117.1	1118.6	1120.1
175°	1128.7	1128.1	1127.5	1126.8	1126.2	1125.9	1125.4	1125.0	1124.5	1126.1	1127.6
177.5°	1132.3	1131.8	1131.2	1130.8	1130.3	1130.0	1129.6	1129.4	1129.0	1130.0	1131.1
180°	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2



TEST NUMBER: P331538-830

CATALOG NUMBER: S122DIW-S675D970U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0
2.5°	1298.5	1303.9	1303.9	1304.7	1310.9	1310.0	1309.7
5°	1381.9	1390.1	1391.0	1399.7	1405.4	1403.5	1398.3
7.5°	1460.5	1475.7	1487.2	1493.6	1501.3	1506.0	1503.9
10°	1522.9	1545.0	1558.5	1567.6	1578.7	1586.9	1583.9
12.5°	1579.4	1605.8	1624.3	1639.9	1641.4	1651.9	1644.7
15°	1667.6	1695.5	1698.5	1710.1	1719.2	1718.2	1718.6
17.5°	1696.9	1705.8	1707.6	1707.9	1708.0	1704.6	1697.3
20°	1686.4	1683.1	1674.9	1668.7	1657.6	1656.1	1646.5
22.5°	1637.2	1626.5	1606.0	1592.4	1575.2	1570.7	1568.0
25°	1540.2	1516.6	1483.8	1452.6	1444.0	1427.1	1431.9
27.5°	1407.1	1370.4	1334.9	1309.5	1286.5	1261.3	1268.5
30°	1313.5	1272.1	1222.1	1183.6	1159.1	1135.0	1130.7
32.5°	1201.9	1141.3	1085.4	1051.6	1014.0	998.8	982.1
35°	1009.5	950.3	894.9	847.3	819.9	798.7	779.5
37.5°	836.3	768.2	723.6	684.9	665.2	653.0	656.1
40°	729.0	669.3	636.6	607.2	588.9	580.2	582.2
42.5°	642.0	597.3	570.3	550.3	537.3	532.5	531.4
45°	543.2	518.2	496.1	484.6	478.2	473.0	469.6
47.5°	475.9	455.4	443.0	436.1	430.6	425.3	425.2
50°	435.5	422.0	413.3	406.0	401.8	397.9	401.2
52.5°	404.6	392.3	383.7	377.2	375.6	372.1	372.0
55°	358.9	349.3	343.1	337.2	334.4	332.4	330.1
57.5°	317.4	308.2	302.5	298.8	293.3	291.3	290.6
60°	287.8	280.5	274.8	269.9	267.5	263.6	263.6
62.5°	260.4	253.2	247.8	244.1	240.2	238.7	239.0
65°	220.8	215.1	209.8	205.9	205.0	202.1	203.0
67.5°	184.5	180.6	175.0	173.0	171.1	169.6	168.4
70°	160.2	156.4	153.4	150.6	149.1	149.1	149.1
72.5°	139.8	135.2	133.5	129.8	130.6	129.1	127.6
75°	108.3	105.4	104.0	102.5	100.1	100.1	100.1
77.5°	79.6	78.8	77.1	75.5	74.9	74.5	74.6
80°	61.5	61.1	60.1	60.1	59.2	58.7	57.8
82.5°	47.3	46.1	45.5	45.1	45.0	44.9	44.7
85°	27.0	26.0	26.0	26.5	25.5	25.5	26.0
87.5°	16.8	16.8	16.3	16.4	16.8	16.5	16.5
90°	32.1	31.7	31.6	31.9	32.0	32.2	32.4
92.5°	30.6	30.7	30.7	30.8	30.8	30.9	30.9
95°	61.1	61.1	60.9	60.4	60.0	59.6	59.2
97.5°	102.7	102.7	102.7	102.6	102.6	102.5	102.5
100°	131.8	131.8	131.7	131.4	131.2	131.0	130.8
102.5°	163.5	163.7	163.7	163.5	163.2	163.1	162.9
105°	211.3	211.7	212.0	212.0	212.0	212.0	212.0
107.5°	262.3	262.4	262.0	261.1	260.0	259.1	258.2
110°	296.9	296.9	296.6	296.0	295.3	294.6	294.1



TEST NUMBER: P331538-830

CATALOG NUMBER: S122DIW-S675D970U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	331.3	330.7	330.3	329.8	329.3	328.9	328.4
115°	385.0	384.8	384.4	383.8	383.1	382.5	381.8
117.5°	436.5	435.9	435.4	434.8	434.1	433.5	432.8
120°	471.6	471.6	471.3	470.6	470.0	469.4	468.7
122.5°	506.7	506.2	505.8	505.3	504.8	504.4	503.9
125°	559.4	558.8	558.4	558.2	558.0	557.7	557.5
127.5°	610.6	609.8	609.1	608.4	607.8	607.1	606.4
130°	646.0	645.5	644.9	644.0	643.2	642.3	641.5
132.5°	679.6	678.6	677.9	677.2	676.5	675.8	675.1
135°	730.7	730.4	730.0	729.3	728.7	728.1	727.5
137.5°	778.9	778.7	778.2	777.3	776.5	775.6	774.8
140°	811.4	811.4	811.1	810.2	809.4	808.5	807.7
142.5°	841.0	841.1	840.8	840.0	839.1	838.3	837.4
145°	885.6	885.8	885.5	884.7	883.8	883.0	882.1
147.5°	924.9	925.4	925.2	924.4	923.6	922.8	922.0
150°	949.9	950.6	950.6	949.9	949.2	948.6	948.0
152.5°	974.9	975.6	975.6	974.9	974.0	973.2	972.4
155°	1006.5	1007.6	1007.8	1007.2	1006.5	1005.9	1005.2
157.5°	1035.9	1037.4	1037.6	1036.6	1035.6	1034.5	1033.5
160°	1053.0	1054.2	1054.5	1053.7	1052.8	1052.0	1051.1
162.5°	1068.7	1070.3	1070.4	1069.4	1068.4	1067.3	1066.4
165°	1088.9	1090.4	1090.6	1089.6	1088.5	1087.5	1086.4
167.5°	1105.6	1107.0	1107.2	1106.2	1105.0	1103.9	1102.9
170°	1114.7	1116.3	1116.3	1115.0	1113.8	1112.5	1111.3
172.5°	1121.6	1123.0	1123.2	1121.9	1120.7	1119.4	1118.1
175°	1129.1	1130.5	1130.7	1129.4	1128.1	1126.8	1125.6
177.5°	1132.0	1133.0	1133.0	1132.0	1131.1	1130.0	1129.0
180°	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2

(END OF REPORT)