

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331559-830

Luminaire Tested: **S122DIW-S865D435U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331559-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIW-S865D435U830-4F0-1E-UDD-F  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 435 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4942.2 lumens  
Efficiency: N/A  
Efficacy: 107.0 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 46.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331559-830

CATALOG NUMBER: S122DIW-S865D435U830-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P331559-830

CATALOG NUMBER: S122DIW-S865D435U830-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	111	111	111	111	105	105	105	105	93	93	93		82	82	82		72	72	72	67
1	102	97	93	90	96	92	88	85	81	79	76		72	70	68		63	62	61	56
2	93	85	79	73	87	80	75	70	71	67	63		63	60	57		56	53	51	47
3	84	75	67	61	79	71	64	58	63	58	53		56	52	48		49	46	43	40
4	77	66	58	52	73	63	55	50	56	50	45		50	45	41		44	41	37	34
5	71	59	51	45	67	56	48	43	50	44	39		45	40	36		40	36	33	30
6	66	53	45	39	62	50	43	37	45	39	34		41	36	32		36	32	29	26
7	61	48	40	34	57	46	38	33	41	35	30		37	32	28		33	29	26	23
8	56	44	36	30	53	42	34	29	38	32	27		34	29	25		30	26	23	21
9	53	40	32	27	50	38	31	26	35	29	24		31	26	23		28	24	21	19
10	49	37	29	24	46	35	28	24	32	26	22		29	24	21		26	22	19	17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	21001	21001	21001
5°	21081	20778	20900
10°	20956	20566	20669
15°	20697	20301	20277
20°	20330	19900	19878
25°	19963	19408	19408
30°	19494	18957	18793
35°	19056	18413	18143
40°	18506	17873	17530
45°	17961	17335	16908
50°	17372	16777	16179
55°	16757	16124	15527
60°	16075	15345	14783
65°	15339	14571	13903
70°	14408	13638	12987
75°	13107	12558	12246
80°	11632	11278	10702
85°	9503	9040	8096



TEST NUMBER: P331559-830

CATALOG NUMBER: S122DIW-S865D435U830-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	122.3	2.5
10°-20°	344.2	7.0
20°-30°	505.9	10.2
30°-40°	587.6	11.9
40°-50°	587.0	11.9
50°-60°	511.9	10.4
60°-70°	378.5	7.7
70°-80°	214.4	4.3
80°-90°	59.0	1.2
90°-100°	18.6	0.4
100°-110°	68.1	1.4
110°-120°	182.0	3.7
120°-130°	300.5	6.1
130°-140°	319.6	6.5
140°-150°	297.0	6.0
150°-160°	238.8	4.8
160°-170°	153.9	3.1
170°-180°	53.0	1.1
0°-30°	972.3	19.7
0°-40°	1559.9	31.6
0°-60°	2658.7	53.8
0°-90°	3310.6	67.0
90°-120°	268.7	5.4
90°-150°	1185.9	24.0
90°-180°	1632.0	33.0
0°-180°	4942.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1301	1301	1301	1301	1301	
5°	1301	1295	1282	1291	1290	123
15°	1238	1230	1214	1219	1213	348
25°	1121	1110	1089	1092	1089	515
35°	967	954	934	927	920	603
45°	787	777	759	746	740	607
55°	595	587	573	558	552	532
65°	402	394	381	370	364	397
75°	210	207	201	194	196	224
85°	51	50	49	45	44	59
90°	0	5	8	10	11	4
95°	26	14	16	18	17	32
105°	122	128	25	29	31	131
115°	232	239	248	71	33	228
125°	328	333	340	343	344	292
135°	405	412	415	419	419	313
145°	470	470	476	479	477	294
155°	518	514	519	521	518	238
165°	545	543	544	547	544	154
175°	558	555	556	558	555	53
180°	557	557	557	557	557	



TEST NUMBER: P331559-830

CATALOG NUMBER: S122DIW-S865D435U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1300.7	1300.7	1300.7	1300.7	1300.7	1300.7	1300.7	1300.7	1300.7	1300.7	1300.7
2.5°	1306.7	1305.6	1304.5	1303.4	1302.3	1300.5	1298.1	1295.6	1293.2	1290.7	1293.0
5°	1300.7	1299.6	1298.5	1297.4	1296.3	1294.2	1291.2	1288.1	1285.1	1282.0	1284.2
7.5°	1289.2	1287.5	1285.8	1284.0	1282.3	1279.9	1276.8	1273.7	1270.5	1267.4	1269.7
10°	1278.2	1276.3	1274.3	1272.3	1270.5	1267.8	1264.4	1261.1	1257.8	1254.4	1256.7
12.5°	1263.2	1261.5	1259.8	1258.0	1256.3	1253.8	1250.5	1247.1	1243.8	1240.5	1242.0
15°	1238.2	1236.5	1234.8	1233.2	1231.5	1228.9	1225.3	1221.6	1218.0	1214.5	1215.5
17.5°	1206.2	1204.5	1202.9	1201.2	1199.5	1196.8	1193.2	1189.5	1185.8	1182.1	1183.5
20°	1183.2	1181.5	1179.9	1178.2	1176.5	1173.7	1169.8	1165.9	1162.1	1158.2	1159.0
22.5°	1160.2	1157.8	1155.5	1153.1	1150.8	1147.8	1144.2	1140.5	1136.8	1133.1	1133.3
25°	1120.6	1118.4	1116.2	1114.0	1111.7	1108.2	1103.5	1098.8	1094.1	1089.4	1090.0
27.5°	1075.6	1073.7	1071.6	1069.6	1067.6	1064.7	1061.0	1057.2	1053.6	1049.8	1049.0
30°	1045.6	1043.4	1041.1	1039.0	1036.7	1033.5	1029.4	1025.2	1021.0	1016.8	1016.0
32.5°	1013.6	1011.8	1010.0	1008.2	1006.4	1003.3	999.0	994.6	990.2	985.8	984.3
35°	966.8	964.0	961.2	958.5	955.6	952.1	947.6	943.2	938.7	934.2	932.6
37.5°	914.0	911.5	909.1	906.6	904.3	900.8	896.4	891.9	887.4	883.0	880.9
40°	878.0	875.8	873.5	871.3	869.1	865.7	861.3	856.9	852.4	848.0	845.5
42.5°	843.0	840.7	838.5	836.3	834.1	830.8	826.3	821.9	817.4	812.9	810.2
45°	786.6	784.8	782.8	780.9	778.9	775.8	771.7	767.5	763.4	759.2	756.1
47.5°	730.7	728.9	727.0	725.2	723.3	720.2	715.9	711.5	707.2	702.9	699.6
50°	691.6	690.2	688.9	687.5	686.1	683.4	679.6	675.6	671.8	667.9	664.0
52.5°	653.7	651.8	650.0	648.1	646.3	643.6	639.9	636.2	632.5	628.9	625.7
55°	595.3	593.7	592.0	590.3	588.6	586.2	582.9	579.5	576.2	572.8	569.5
57.5°	536.8	535.5	534.1	532.8	531.5	529.0	525.3	521.6	517.9	514.3	511.0
60°	497.8	496.6	495.6	494.5	493.3	490.9	486.9	483.1	479.2	475.2	472.2
62.5°	459.8	458.0	456.2	454.4	452.6	450.3	447.2	444.2	441.2	438.3	435.5
65°	401.5	399.8	398.1	396.4	394.8	392.6	389.8	387.0	384.3	381.4	379.0
67.5°	342.2	340.8	339.5	338.2	336.9	335.0	332.4	329.9	327.4	324.9	323.0
70°	305.2	304.1	302.9	301.8	300.8	298.9	296.4	293.9	291.4	288.9	287.0
72.5°	267.1	266.1	264.9	263.8	262.7	261.4	259.8	258.2	256.5	254.9	253.0
75°	210.1	209.5	209.0	208.5	207.9	206.9	205.6	204.2	202.7	201.3	199.7
77.5°	159.1	158.2	157.2	156.3	155.3	154.6	154.0	153.4	152.9	152.3	151.5
80°	125.1	124.8	124.5	124.2	123.9	123.6	123.0	122.4	121.9	121.3	120.5
82.5°	93.0	93.0	92.9	92.8	92.8	92.7	92.3	92.0	91.6	91.3	90.2
85°	51.3	51.0	50.7	50.4	50.1	49.9	49.6	49.3	49.0	48.8	48.0
87.5°	18.1	17.8	17.6	17.3	17.1	16.9	16.5	16.2	15.9	15.6	15.1
90°	0.4	1.4	2.4	3.4	4.3	5.2	5.9	6.6	7.4	8.0	8.5
92.5°	8.1	8.0	7.9	7.8	7.8	7.9	8.3	8.7	9.0	9.3	9.6
95°	26.2	23.2	20.3	17.3	14.3	13.2	13.9	14.4	15.1	15.7	16.1
97.5°	51.9	43.6	35.3	27.0	18.7	15.3	16.7	18.1	19.6	21.0	21.4
100°	71.4	59.0	46.8	34.5	22.2	16.9	18.4	19.9	21.4	23.0	23.7
102.5°	92.6	90.0	87.4	84.8	82.2	74.6	61.8	49.1	36.4	23.6	24.5
105°	122.4	125.2	127.8	130.5	133.2	122.3	97.9	73.4	49.0	24.6	25.5
107.5°	156.6	158.7	160.9	163.1	165.2	151.7	122.3	93.0	63.7	34.4	33.4
110°	178.4	180.3	182.2	184.1	186.0	174.0	148.1	122.2	96.3	70.5	61.5



TEST NUMBER: P331559-830

CATALOG NUMBER: S122DIW-S865D435U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	199.1	200.8	202.5	204.1	205.8	203.4	197.0	190.6	184.2	177.9	145.2
115°	231.7	233.2	234.7	236.2	237.7	239.6	241.9	244.1	246.3	248.5	207.1
117.5°	260.7	262.4	264.1	265.8	267.5	269.2	270.7	272.2	273.8	275.3	265.3
120°	282.0	283.3	284.6	286.1	287.4	288.9	290.5	292.1	293.7	295.3	296.3
122.5°	300.0	301.4	302.8	304.3	305.7	307.3	309.1	310.8	312.5	314.3	315.0
125°	327.5	328.7	329.9	331.0	332.2	333.6	335.4	337.1	338.7	340.4	341.0
127.5°	352.4	353.7	355.0	356.3	357.6	358.8	360.1	361.4	362.7	363.9	364.9
130°	368.3	369.7	371.1	372.5	373.9	375.1	376.2	377.1	378.1	379.1	380.0
132.5°	384.4	385.5	386.7	388.0	389.2	390.3	391.2	392.3	393.2	394.3	395.1
135°	405.3	406.7	408.1	409.5	411.0	412.1	412.9	413.8	414.5	415.4	416.2
137.5°	426.5	427.4	428.5	429.5	430.5	431.4	432.3	433.3	434.1	435.1	435.9
140°	440.4	441.0	441.8	442.4	443.2	444.0	445.1	446.0	447.0	448.0	448.7
142.5°	451.9	452.6	453.2	453.8	454.5	455.4	456.5	457.6	458.7	459.9	460.6
145°	470.1	470.0	470.0	469.9	469.8	470.5	472.0	473.5	475.0	476.5	477.2
147.5°	486.0	485.7	485.3	485.0	484.7	485.2	486.7	488.2	489.7	491.3	491.7
150°	496.3	495.7	495.0	494.5	493.8	494.2	495.7	497.1	498.5	499.9	500.5
152.5°	505.0	504.4	503.6	502.9	502.2	502.6	503.9	505.3	506.6	508.0	508.5
155°	517.6	516.9	516.0	515.3	514.4	514.6	515.7	516.7	517.8	518.9	519.4
157.5°	527.5	526.9	526.2	525.6	524.9	524.9	525.7	526.4	527.2	527.9	528.5
160°	533.4	532.8	532.3	531.8	531.2	531.2	531.8	532.3	532.8	533.4	534.0
162.5°	538.6	538.0	537.4	537.0	536.4	536.4	536.8	537.2	537.7	538.2	538.9
165°	545.4	545.0	544.4	543.8	543.3	543.2	543.5	543.8	544.0	544.2	544.9
167.5°	550.6	550.1	549.6	549.0	548.5	548.4	548.6	548.8	549.1	549.3	550.0
170°	553.6	553.0	552.4	552.0	551.4	551.2	551.4	551.6	551.8	552.0	552.5
172.5°	555.4	555.0	554.4	553.8	553.3	553.2	553.3	553.5	553.6	553.8	554.5
175°	558.0	557.3	556.7	556.1	555.4	555.3	555.4	555.6	555.7	555.9	556.6
177.5°	558.4	557.9	557.3	556.9	556.4	556.1	556.2	556.3	556.4	556.4	556.9
180°	556.8	556.8	556.8	556.8	556.8	556.8	556.8	556.8	556.8	556.8	556.8



TEST NUMBER: P331559-830

CATALOG NUMBER: S122DIW-S865D435U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1300.7	1300.7	1300.7	1300.7	1300.7	1300.7	1300.7	1300.7
2.5°	1295.1	1297.4	1299.6	1300.5	1300.0	1299.6	1299.2	1298.7
5°	1286.4	1288.6	1290.9	1291.7	1291.2	1290.6	1290.1	1289.5
7.5°	1271.9	1274.1	1276.4	1277.1	1276.6	1275.9	1275.4	1274.7
10°	1258.9	1261.1	1263.4	1264.0	1263.2	1262.3	1261.5	1260.7
12.5°	1243.6	1245.1	1246.7	1247.2	1246.5	1245.9	1245.3	1244.7
15°	1216.6	1217.8	1218.9	1218.7	1217.4	1216.0	1214.6	1213.1
17.5°	1184.7	1186.0	1187.3	1187.2	1185.9	1184.6	1183.3	1181.9
20°	1159.8	1160.6	1161.5	1161.3	1160.3	1159.1	1158.0	1156.9
22.5°	1133.5	1133.6	1133.8	1133.6	1132.8	1132.2	1131.5	1130.9
25°	1090.5	1091.0	1091.6	1091.6	1091.0	1090.5	1090.0	1089.4
27.5°	1048.2	1047.4	1046.5	1045.5	1044.1	1042.7	1041.4	1040.1
30°	1015.1	1014.4	1013.5	1012.5	1011.4	1010.3	1009.2	1008.0
32.5°	982.8	981.3	979.8	978.5	977.4	976.3	975.2	974.0
35°	930.9	929.3	927.7	926.0	924.7	923.3	921.9	920.5
37.5°	878.9	876.8	874.8	873.1	871.8	870.4	869.1	867.7
40°	843.0	840.5	838.0	836.1	835.1	834.0	832.8	831.7
42.5°	807.5	804.7	802.1	799.9	798.3	796.8	795.2	793.7
45°	753.1	750.0	747.0	744.9	743.8	742.6	741.5	740.5
47.5°	696.4	693.2	690.0	687.6	686.0	684.4	682.8	681.2
50°	660.1	656.2	652.3	649.7	648.3	646.9	645.5	644.1
52.5°	622.4	619.2	616.0	613.4	611.6	609.7	607.9	606.1
55°	566.2	562.8	559.5	557.1	555.7	554.3	553.0	551.6
57.5°	507.7	504.4	501.1	499.0	497.9	496.9	495.9	494.7
60°	469.2	466.1	463.1	461.1	460.2	459.4	458.5	457.8
62.5°	432.5	429.7	426.9	425.0	423.9	422.8	421.8	420.8
65°	376.5	374.0	371.5	369.5	368.2	366.7	365.3	363.9
67.5°	321.0	319.1	317.2	315.7	314.5	313.4	312.3	311.1
70°	285.0	283.0	281.2	279.6	278.5	277.4	276.3	275.1
72.5°	251.0	249.0	247.1	245.7	244.8	243.9	243.0	242.1
75°	198.0	196.3	194.7	194.2	194.7	195.3	195.8	196.3
77.5°	150.7	149.9	149.0	148.2	147.4	146.7	145.9	145.1
80°	119.6	118.9	118.0	117.3	116.7	116.2	115.6	115.1
82.5°	89.2	88.1	87.1	86.5	86.3	86.2	86.1	86.1
85°	47.1	46.3	45.4	44.9	44.6	44.3	44.0	43.7
87.5°	14.4	13.9	13.3	12.9	12.7	12.5	12.3	12.2
90°	9.0	9.4	9.8	10.2	10.4	10.6	10.7	10.8
92.5°	9.8	10.1	10.3	10.5	10.6	10.7	10.7	10.8
95°	16.6	17.1	17.5	17.7	17.6	17.5	17.4	17.3
97.5°	21.8	22.1	22.4	22.7	22.8	22.9	23.0	23.1
100°	24.4	25.1	25.8	26.3	26.5	26.7	26.8	27.0
102.5°	25.4	26.4	27.3	27.9	28.2	28.5	28.7	28.9
105°	26.6	27.5	28.6	29.2	29.5	29.9	30.3	30.6
107.5°	32.4	31.4	30.3	30.1	30.4	30.8	31.1	31.5
110°	52.6	43.6	34.7	30.3	30.7	31.1	31.5	31.9





TEST NUMBER: P331559-830

CATALOG NUMBER: S122DIW-S865D435U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	112.5	79.8	47.2	31.0	31.3	31.6	31.9	32.1
115°	165.7	124.2	82.8	58.8	52.4	45.9	39.5	33.0
117.5°	255.2	245.2	235.2	219.6	198.4	177.2	156.1	134.9
120°	297.5	298.5	299.6	294.1	282.0	269.9	257.8	245.7
122.5°	315.6	316.2	316.9	316.0	313.7	311.3	309.0	306.6
125°	341.7	342.3	342.9	343.4	343.7	343.9	344.2	344.4
127.5°	365.8	366.6	367.6	368.1	368.2	368.2	368.3	368.3
130°	381.1	382.0	383.0	383.5	383.4	383.3	383.2	383.1
132.5°	396.0	396.7	397.6	397.9	397.8	397.8	397.8	397.7
135°	417.2	418.0	419.0	419.2	419.1	419.0	418.8	418.6
137.5°	436.9	437.7	438.6	438.8	438.6	438.3	438.0	437.6
140°	449.6	450.4	451.2	451.4	450.9	450.4	450.1	449.6
142.5°	461.4	462.1	462.9	463.0	462.5	462.1	461.7	461.2
145°	477.9	478.4	479.1	479.2	478.7	478.2	477.9	477.4
147.5°	492.2	492.7	493.1	493.1	492.8	492.4	492.0	491.6
150°	501.1	501.5	502.1	502.2	501.7	501.2	500.8	500.4
152.5°	509.1	509.6	510.2	510.1	509.5	509.0	508.3	507.7
155°	520.0	520.5	521.0	520.9	520.2	519.5	518.8	518.1
157.5°	529.1	529.7	530.4	530.3	529.6	528.9	528.2	527.5
160°	534.4	535.0	535.6	535.5	534.9	534.2	533.6	533.0
162.5°	539.4	540.1	540.6	540.5	539.8	539.0	538.3	537.5
165°	545.5	546.1	546.8	546.8	546.1	545.5	544.9	544.2
167.5°	550.6	551.2	551.9	551.8	550.9	550.2	549.3	548.6
170°	553.2	553.8	554.4	554.3	553.6	552.7	552.0	551.1
172.5°	555.1	555.7	556.4	556.3	555.4	554.7	553.8	553.1
175°	557.2	557.8	558.5	558.4	557.4	556.6	555.6	554.8
177.5°	557.4	557.9	558.5	558.4	557.7	557.0	556.4	555.8
180°	556.8	556.8	556.8	556.8	556.8	556.8	556.8	556.8

(END OF REPORT)