

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331572-830

Luminaire Tested: **S122DIW-S865D970U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331572-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S865D970U830-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 970 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6477.0 lumens
Efficiency: N/A
Efficacy: 105.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 61.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331572-830

CATALOG NUMBER: S122DIW-S865D970U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331572-830

CATALOG NUMBER: S122DIW-S865D970U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51
1	98	94	90	86	90	87	83	80	74	71	69	62	60	58	51	49	48	43
2	89	82	76	70	82	76	70	66	65	61	57	54	51	49	44	42	41	36
3	81	72	65	59	75	67	60	55	57	52	48	48	44	41	39	37	35	31
4	75	64	56	50	69	59	52	47	51	45	41	43	39	35	35	32	30	26
5	68	57	49	43	63	53	46	40	45	40	35	38	34	31	32	29	26	23
6	63	51	43	37	58	47	40	35	41	35	31	35	30	27	29	25	23	20
7	58	46	38	32	54	43	36	31	37	31	27	31	27	24	26	23	20	18
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18	16
9	50	38	31	26	47	36	29	24	31	25	22	27	22	19	22	19	16	14
10	47	35	28	23	44	33	26	22	29	23	19	25	20	17	21	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	21001	21001	21001
5°	21081	20778	20900
10°	20956	20566	20669
15°	20697	20301	20277
20°	20330	19900	19878
25°	19963	19408	19408
30°	19494	18957	18793
35°	19056	18413	18143
40°	18506	17873	17530
45°	17961	17335	16908
50°	17372	16777	16179
55°	16757	16124	15527
60°	16075	15345	14783
65°	15339	14571	13903
70°	14408	13638	12987
75°	13107	12558	12246
80°	11632	11278	10702
85°	9503	9040	8096



TEST NUMBER: P331572-830

CATALOG NUMBER: S122DIW-S865D970U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.3	1.9
10°-20°	344.2	5.3
20°-30°	505.9	7.8
30°-40°	587.6	9.1
40°-50°	587.0	9.1
50°-60°	511.9	7.9
60°-70°	378.5	5.8
70°-80°	214.4	3.3
80°-90°	62.2	1.0
90°-100°	71.7	1.1
100°-110°	222.6	3.4
110°-120°	380.6	5.9
120°-130°	500.5	7.7
130°-140°	561.7	8.7
140°-150°	550.8	8.5
150°-160°	462.0	7.1
160°-170°	306.4	4.7
170°-180°	107.1	1.7
0°-30°	972.3	15.0
0°-40°	1559.9	24.1
0°-60°	2658.7	41.0
0°-90°	3313.8	51.2
90°-120°	674.9	10.4
90°-150°	2287.8	35.3
90°-180°	3163.0	48.8
0°-180°	6477.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1301	1301	1301	1301	1301	
5°	1301	1295	1282	1291	1290	123
15°	1238	1230	1214	1219	1213	348
25°	1121	1110	1089	1092	1089	515
35°	967	954	934	927	920	603
45°	787	777	759	746	740	607
55°	595	587	573	558	552	532
65°	402	394	381	370	364	397
75°	210	207	201	194	196	224
85°	51	50	49	45	44	59
90°	1	13	33	32	32	5
95°	50	59	61	61	59	57
105°	205	208	210	212	212	217
115°	382	387	386	385	382	378
125°	556	564	561	559	558	496
135°	719	729	731	730	728	555
145°	872	879	885	886	882	545
155°	998	1000	1003	1008	1005	459
165°	1085	1085	1084	1090	1086	306
175°	1129	1126	1124	1131	1126	107
180°	1131	1131	1131	1131	1131	



TEST NUMBER: P331572-830

CATALOG NUMBER: S122DIW-S865D970U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1300.7	1300.7	1300.7	1300.7	1300.7	1300.7	1300.7	1300.7	1300.7	1300.7	1300.7
2.5°	1306.7	1305.6	1304.5	1303.4	1302.3	1300.5	1298.1	1295.6	1293.2	1290.7	1293.0
5°	1300.7	1299.6	1298.5	1297.4	1296.3	1294.2	1291.2	1288.1	1285.1	1282.0	1284.2
7.5°	1289.2	1287.5	1285.8	1284.0	1282.3	1279.9	1276.8	1273.7	1270.5	1267.4	1269.7
10°	1278.2	1276.3	1274.3	1272.3	1270.5	1267.8	1264.4	1261.1	1257.8	1254.4	1256.7
12.5°	1263.2	1261.5	1259.8	1258.0	1256.3	1253.8	1250.5	1247.1	1243.8	1240.5	1242.0
15°	1238.2	1236.5	1234.8	1233.2	1231.5	1228.9	1225.3	1221.6	1218.0	1214.5	1215.5
17.5°	1206.2	1204.5	1202.9	1201.2	1199.5	1196.8	1193.2	1189.5	1185.8	1182.1	1183.5
20°	1183.2	1181.5	1179.9	1178.2	1176.5	1173.7	1169.8	1165.9	1162.1	1158.2	1159.0
22.5°	1160.2	1157.8	1155.5	1153.1	1150.8	1147.8	1144.2	1140.5	1136.8	1133.1	1133.3
25°	1120.6	1118.4	1116.2	1114.0	1111.7	1108.2	1103.5	1098.8	1094.1	1089.4	1090.0
27.5°	1075.6	1073.7	1071.6	1069.6	1067.6	1064.7	1061.0	1057.2	1053.6	1049.8	1049.0
30°	1045.6	1043.4	1041.1	1039.0	1036.7	1033.5	1029.4	1025.2	1021.0	1016.8	1016.0
32.5°	1013.6	1011.8	1010.0	1008.2	1006.4	1003.3	999.0	994.6	990.2	985.8	984.3
35°	966.8	964.0	961.2	958.5	955.6	952.1	947.6	943.2	938.7	934.2	932.6
37.5°	914.0	911.5	909.1	906.6	904.3	900.8	896.4	891.9	887.4	883.0	880.9
40°	878.0	875.8	873.5	871.3	869.1	865.7	861.3	856.9	852.4	848.0	845.5
42.5°	843.0	840.7	838.5	836.3	834.1	830.8	826.3	821.9	817.4	812.9	810.2
45°	786.6	784.8	782.8	780.9	778.9	775.8	771.7	767.5	763.4	759.2	756.1
47.5°	730.7	728.9	727.0	725.2	723.3	720.2	715.9	711.5	707.2	702.9	699.6
50°	691.6	690.2	688.9	687.5	686.1	683.4	679.6	675.6	671.8	667.9	664.0
52.5°	653.7	651.8	650.0	648.1	646.3	643.6	639.9	636.2	632.5	628.9	625.7
55°	595.3	593.7	592.0	590.3	588.6	586.2	582.9	579.5	576.2	572.8	569.5
57.5°	536.8	535.5	534.1	532.8	531.5	529.0	525.3	521.6	517.9	514.3	511.0
60°	497.8	496.6	495.6	494.5	493.3	490.9	486.9	483.1	479.2	475.2	472.2
62.5°	459.8	458.0	456.2	454.4	452.6	450.3	447.2	444.2	441.2	438.3	435.5
65°	401.5	399.8	398.1	396.4	394.8	392.6	389.8	387.0	384.3	381.4	379.0
67.5°	342.2	340.8	339.5	338.2	336.9	335.0	332.4	329.9	327.4	324.9	323.0
70°	305.2	304.1	302.9	301.8	300.8	298.9	296.4	293.9	291.4	288.9	287.0
72.5°	267.1	266.1	264.9	263.8	262.7	261.4	259.8	258.2	256.5	254.9	253.0
75°	210.1	209.5	209.0	208.5	207.9	206.9	205.6	204.2	202.7	201.3	199.7
77.5°	159.1	158.2	157.2	156.3	155.3	154.6	154.0	153.4	152.9	152.3	151.5
80°	125.1	124.8	124.5	124.2	123.9	123.6	123.0	122.4	121.9	121.3	120.5
82.5°	93.0	93.0	92.9	92.8	92.8	92.7	92.3	92.0	91.6	91.3	90.2
85°	51.3	51.0	50.7	50.4	50.1	49.9	49.6	49.3	49.0	48.8	48.0
87.5°	18.2	18.3	18.3	18.4	18.5	18.8	19.2	19.7	20.2	20.7	20.0
90°	0.9	3.5	6.0	8.6	11.1	14.7	19.4	24.0	28.7	33.4	33.0
92.5°	17.0	18.9	20.7	22.6	24.5	25.9	27.1	28.2	29.2	30.3	30.4
95°	49.7	51.7	53.9	56.0	58.2	59.4	59.9	60.2	60.7	61.1	61.1
97.5°	90.7	92.6	94.4	96.3	98.1	99.5	100.3	101.1	101.9	102.7	102.7
100°	121.2	122.9	124.6	126.3	128.0	129.2	129.8	130.4	131.1	131.8	131.8
102.5°	153.4	154.7	156.0	157.4	158.7	159.9	160.6	161.5	162.2	163.1	163.2
105°	205.3	205.9	206.5	207.2	207.8	208.3	208.8	209.2	209.6	210.0	210.5
107.5°	257.6	258.5	259.4	260.3	261.3	261.7	261.7	261.7	261.7	261.7	261.9
110°	291.2	292.5	293.7	295.0	296.2	296.9	296.9	296.9	296.9	296.9	296.9



TEST NUMBER: P331572-830

CATALOG NUMBER: S122DIW-S865D970U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	327.8	329.1	330.4	331.7	332.9	333.5	333.3	333.1	333.0	332.8	332.2
115°	381.8	383.1	384.4	385.7	386.9	387.4	386.9	386.5	386.1	385.7	385.5
117.5°	435.7	437.4	439.1	440.8	442.5	442.7	441.6	440.4	439.2	438.0	437.5
120°	471.6	473.3	475.0	476.7	478.4	478.4	476.7	475.0	473.3	471.6	471.6
122.5°	504.4	506.5	508.5	510.6	512.6	513.0	511.8	510.7	509.4	508.2	507.7
125°	555.6	557.5	559.4	561.4	563.3	563.9	563.3	562.6	561.9	561.4	560.7
127.5°	605.5	607.8	610.3	612.7	615.1	616.0	615.2	614.4	613.7	612.9	612.1
130°	636.8	639.5	642.2	645.1	647.8	648.9	648.6	648.1	647.7	647.2	646.9
132.5°	671.8	674.1	676.4	678.6	680.9	682.0	682.1	682.2	682.3	682.4	681.5
135°	718.9	721.2	723.5	725.9	728.2	729.5	730.0	730.4	730.8	731.2	731.0
137.5°	768.3	770.2	772.1	774.0	775.9	777.2	777.7	778.3	778.8	779.4	779.2
140°	798.1	800.0	801.9	803.8	805.7	807.2	808.3	809.4	810.4	811.4	811.4
142.5°	828.7	830.6	832.5	834.3	836.3	837.6	838.3	839.1	839.8	840.5	840.7
145°	872.5	874.0	875.5	877.0	878.5	879.9	881.2	882.4	883.7	885.0	885.1
147.5°	911.7	913.5	915.3	917.0	918.8	920.1	921.0	921.8	922.7	923.5	924.0
150°	938.4	939.7	940.9	942.3	943.5	944.6	945.5	946.3	947.2	948.0	948.6
152.5°	962.1	963.4	964.7	965.9	967.2	968.4	969.4	970.3	971.4	972.4	973.2
155°	997.6	998.2	998.9	999.6	1000.1	1000.8	1001.5	1002.1	1002.7	1003.3	1004.4
157.5°	1027.9	1028.4	1028.8	1029.3	1029.6	1030.1	1030.5	1030.9	1031.2	1031.6	1033.0
160°	1046.3	1046.7	1047.2	1047.5	1048.0	1048.3	1048.6	1048.8	1049.0	1049.1	1050.5
162.5°	1063.1	1063.2	1063.3	1063.4	1063.5	1063.6	1063.8	1064.0	1064.2	1064.4	1065.9
165°	1085.4	1085.2	1085.1	1084.8	1084.6	1084.5	1084.5	1084.5	1084.5	1084.5	1086.0
167.5°	1104.2	1103.5	1102.9	1102.2	1101.6	1101.3	1101.3	1101.2	1101.2	1101.1	1102.6
170°	1114.1	1113.4	1112.9	1112.2	1111.5	1111.2	1110.9	1110.7	1110.5	1110.3	1111.7
172.5°	1121.0	1120.3	1119.6	1119.1	1118.4	1117.9	1117.8	1117.6	1117.4	1117.1	1118.6
175°	1129.4	1128.7	1128.1	1127.5	1126.8	1126.2	1125.9	1125.4	1125.0	1124.5	1126.1
177.5°	1132.8	1132.3	1131.8	1131.2	1130.8	1130.3	1130.0	1129.6	1129.4	1129.0	1130.0
180°	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2



TEST NUMBER: P331572-830

CATALOG NUMBER: S122DIW-S865D970U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1300.7	1300.7	1300.7	1300.7	1300.7	1300.7	1300.7	1300.7
2.5°	1295.1	1297.4	1299.6	1300.5	1300.0	1299.6	1299.2	1298.7
5°	1286.4	1288.6	1290.9	1291.7	1291.2	1290.6	1290.1	1289.5
7.5°	1271.9	1274.1	1276.4	1277.1	1276.6	1275.9	1275.4	1274.7
10°	1258.9	1261.1	1263.4	1264.0	1263.2	1262.3	1261.5	1260.7
12.5°	1243.6	1245.1	1246.7	1247.2	1246.5	1245.9	1245.3	1244.7
15°	1216.6	1217.8	1218.9	1218.7	1217.4	1216.0	1214.6	1213.1
17.5°	1184.7	1186.0	1187.3	1187.2	1185.9	1184.6	1183.3	1181.9
20°	1159.8	1160.6	1161.5	1161.3	1160.3	1159.1	1158.0	1156.9
22.5°	1133.5	1133.6	1133.8	1133.6	1132.8	1132.2	1131.5	1130.9
25°	1090.5	1091.0	1091.6	1091.6	1091.0	1090.5	1090.0	1089.4
27.5°	1048.2	1047.4	1046.5	1045.5	1044.1	1042.7	1041.4	1040.1
30°	1015.1	1014.4	1013.5	1012.5	1011.4	1010.3	1009.2	1008.0
32.5°	982.8	981.3	979.8	978.5	977.4	976.3	975.2	974.0
35°	930.9	929.3	927.7	926.0	924.7	923.3	921.9	920.5
37.5°	878.9	876.8	874.8	873.1	871.8	870.4	869.1	867.7
40°	843.0	840.5	838.0	836.1	835.1	834.0	832.8	831.7
42.5°	807.5	804.7	802.1	799.9	798.3	796.8	795.2	793.7
45°	753.1	750.0	747.0	744.9	743.8	742.6	741.5	740.5
47.5°	696.4	693.2	690.0	687.6	686.0	684.4	682.8	681.2
50°	660.1	656.2	652.3	649.7	648.3	646.9	645.5	644.1
52.5°	622.4	619.2	616.0	613.4	611.6	609.7	607.9	606.1
55°	566.2	562.8	559.5	557.1	555.7	554.3	553.0	551.6
57.5°	507.7	504.4	501.1	499.0	497.9	496.9	495.9	494.7
60°	469.2	466.1	463.1	461.1	460.2	459.4	458.5	457.8
62.5°	432.5	429.7	426.9	425.0	423.9	422.8	421.8	420.8
65°	376.5	374.0	371.5	369.5	368.2	366.7	365.3	363.9
67.5°	321.0	319.1	317.2	315.7	314.5	313.4	312.3	311.1
70°	285.0	283.0	281.2	279.6	278.5	277.4	276.3	275.1
72.5°	251.0	249.0	247.1	245.7	244.8	243.9	243.0	242.1
75°	198.0	196.3	194.7	194.2	194.7	195.3	195.8	196.3
77.5°	150.7	149.9	149.0	148.2	147.4	146.7	145.9	145.1
80°	119.6	118.9	118.0	117.3	116.7	116.2	115.6	115.1
82.5°	89.2	88.1	87.1	86.5	86.3	86.2	86.1	86.1
85°	47.1	46.3	45.4	44.9	44.6	44.3	44.0	43.7
87.5°	19.2	18.5	17.7	17.2	17.1	16.9	16.7	16.5
90°	32.5	32.1	31.7	31.6	31.9	32.0	32.2	32.4
92.5°	30.5	30.6	30.7	30.7	30.8	30.8	30.9	30.9
95°	61.1	61.1	61.1	60.9	60.4	60.0	59.6	59.2
97.5°	102.7	102.7	102.7	102.7	102.6	102.6	102.5	102.5
100°	131.8	131.8	131.8	131.7	131.4	131.2	131.0	130.8
102.5°	163.4	163.5	163.7	163.7	163.5	163.2	163.1	162.9
105°	210.8	211.3	211.7	212.0	212.0	212.0	212.0	212.0
107.5°	262.1	262.3	262.4	262.0	261.1	260.0	259.1	258.2
110°	296.9	296.9	296.9	296.6	296.0	295.3	294.6	294.1



TEST NUMBER: P331572-830

CATALOG NUMBER: S122DIW-S865D970U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	331.8	331.3	330.7	330.3	329.8	329.3	328.9	328.4
115°	385.2	385.0	384.8	384.4	383.8	383.1	382.5	381.8
117.5°	437.0	436.5	435.9	435.4	434.8	434.1	433.5	432.8
120°	471.6	471.6	471.6	471.3	470.6	470.0	469.4	468.7
122.5°	507.3	506.7	506.2	505.8	505.3	504.8	504.4	503.9
125°	560.1	559.4	558.8	558.4	558.2	558.0	557.7	557.5
127.5°	611.3	610.6	609.8	609.1	608.4	607.8	607.1	606.4
130°	646.4	646.0	645.5	644.9	644.0	643.2	642.3	641.5
132.5°	680.5	679.6	678.6	677.9	677.2	676.5	675.8	675.1
135°	730.8	730.7	730.4	730.0	729.3	728.7	728.1	727.5
137.5°	779.0	778.9	778.7	778.2	777.3	776.5	775.6	774.8
140°	811.4	811.4	811.4	811.1	810.2	809.4	808.5	807.7
142.5°	840.8	841.0	841.1	840.8	840.0	839.1	838.3	837.4
145°	885.4	885.6	885.8	885.5	884.7	883.8	883.0	882.1
147.5°	924.4	924.9	925.4	925.2	924.4	923.6	922.8	922.0
150°	949.2	949.9	950.6	950.6	949.9	949.2	948.6	948.0
152.5°	974.0	974.9	975.6	975.6	974.9	974.0	973.2	972.4
155°	1005.5	1006.5	1007.6	1007.8	1007.2	1006.5	1005.9	1005.2
157.5°	1034.5	1035.9	1037.4	1037.6	1036.6	1035.6	1034.5	1033.5
160°	1051.7	1053.0	1054.2	1054.5	1053.7	1052.8	1052.0	1051.1
162.5°	1067.3	1068.7	1070.3	1070.4	1069.4	1068.4	1067.3	1066.4
165°	1087.5	1088.9	1090.4	1090.6	1089.6	1088.5	1087.5	1086.4
167.5°	1104.1	1105.6	1107.0	1107.2	1106.2	1105.0	1103.9	1102.9
170°	1113.2	1114.7	1116.3	1116.3	1115.0	1113.8	1112.5	1111.3
172.5°	1120.1	1121.6	1123.0	1123.2	1121.9	1120.7	1119.4	1118.1
175°	1127.6	1129.1	1130.5	1130.7	1129.4	1128.1	1126.8	1125.6
177.5°	1131.1	1132.0	1133.0	1133.0	1132.0	1131.1	1130.0	1129.0
180°	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2	1131.2

(END OF REPORT)