

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: NEO-RAY

Report Number: P331782-830

Luminaire Tested: **S122RDIW-S290D1440U830-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331782-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S290D1440U830-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1440 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5779.8 lumens
Efficiency: N/A
Efficacy: 108.2 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331782-830

CATALOG NUMBER: S122RDIW-S290D1440U830-4F0-1E-UDD-A1

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - - - 90°-270° - - - 135°-315°



TEST NUMBER: P331782-830

CATALOG NUMBER: S122RDIW-S290D1440U830-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	100	100	100	100	88	88	88	88	66	66	66	46	46	46	27	27	27	19
1	91	87	83	80	80	77	74	71	58	56	54	40	39	38	24	24	23	16
2	83	76	71	66	73	67	63	59	51	48	45	36	34	32	22	21	20	14
3	76	67	60	55	67	60	54	49	45	41	38	32	30	28	20	18	17	12
4	69	60	52	47	61	53	47	42	40	36	33	29	26	24	18	16	15	11
5	64	53	45	40	56	47	41	36	36	32	28	26	23	21	16	15	14	10
6	59	47	40	35	52	42	36	31	32	28	25	23	20	18	15	13	12	9
7	54	43	35	30	48	38	32	27	29	25	22	21	18	16	13	12	11	8
8	50	39	32	27	44	35	28	24	27	22	19	19	17	14	12	11	10	7
9	47	35	28	24	41	32	26	21	24	20	17	18	15	13	12	10	9	6
10	43	32	25	21	38	29	23	19	22	18	15	16	14	12	11	9	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9947	9947	9947	9947
5°	11110	10010	8877	10010
10°	12329	9940	7694	9940
15°	12933	9795	6063	9795
20°	11213	9579	5246	9579
25°	7352	9283	4684	9283
30°	4950	8925	4238	8925
35°	4009	8474	3824	8474
40°	3564	7982	3539	7982
45°	3226	7405	3158	7405
50°	2936	6835	2926	6835
55°	2759	6201	2725	6201
60°	2309	5622	2283	5622
65°	1948	5104	2208	5104
70°	1799	4556	2082	4556
75°	1684	3968	1921	3968
80°	1553	3273	1711	3273
85°	1426	2575	1501	2575



TEST NUMBER: P331782-830

CATALOG NUMBER: S122RDIW-S290D1440U830-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.4	1.0
10°-20°	162.8	2.8
20°-30°	209.7	3.6
30°-40°	199.3	3.4
40°-50°	170.7	3.0
50°-60°	130.0	2.2
60°-70°	82.2	1.4
70°-80°	41.0	0.7
80°-90°	17.4	0.3
90°-100°	106.7	1.8
100°-110°	331.4	5.7
110°-120°	566.4	9.8
120°-130°	744.9	12.9
130°-140°	836.1	14.5
140°-150°	819.8	14.2
150°-160°	687.6	11.9
160°-170°	456.0	7.9
170°-180°	159.4	2.8
0°-30°	430.9	7.5
0°-40°	630.2	10.9
0°-60°	931.0	16.1
0°-90°	1071.6	18.5
90°-120°	1004.5	17.4
90°-150°	3405.2	58.9
90°-180°	4708.0	81.5
0°-180°	5779.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	616	616	616	616	616	
5°	686	618	548	618	686	68
15°	774	586	363	586	774	209
25°	413	521	263	521	413	196
35°	203	430	194	430	203	130
45°	141	324	138	324	141	109
55°	98	220	97	220	98	86
65°	51	134	58	134	51	52
75°	27	64	31	64	27	29
85°	8	14	8	14	8	10
90°	48	1	48	1	48	21
95°	88	74	88	74	88	98
105°	316	306	316	306	316	332
115°	568	568	568	568	568	561
125°	830	827	830	827	830	740
135°	1083	1070	1083	1070	1083	833
145°	1313	1299	1313	1299	1313	820
155°	1496	1485	1496	1485	1496	689
165°	1617	1616	1617	1616	1617	456
175°	1675	1681	1675	1681	1675	159
180°	1684	1684	1684	1684	1684	



TEST NUMBER: P331782-830

CATALOG NUMBER: S122RDIW-S290D1440U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	616.1	616.1	616.1	616.1	616.1	616.1	616.1	616.1	616.1	616.1	616.1
2.5°	641.2	641.7	642.2	641.0	641.0	640.0	637.7	636.0	631.2	630.6	630.6
5°	685.5	685.1	686.0	683.2	679.4	678.4	674.4	669.0	663.5	657.3	656.0
7.5°	729.6	729.0	727.3	726.8	723.9	717.4	710.9	703.9	694.7	685.6	681.1
10°	752.0	759.0	754.7	747.2	748.7	738.7	733.3	724.1	716.3	702.9	699.9
12.5°	773.8	776.7	775.2	771.0	769.1	762.1	754.9	746.9	732.6	720.6	710.0
15°	773.7	777.8	778.9	777.6	778.6	778.3	774.4	767.8	755.4	742.1	730.5
17.5°	716.6	719.4	726.5	731.2	737.3	749.9	756.2	758.6	756.8	749.1	741.0
20°	652.6	647.9	667.6	677.6	686.2	707.6	726.0	733.1	744.4	744.2	742.1
22.5°	561.8	562.9	581.5	593.5	618.5	640.0	660.9	687.5	709.5	724.0	732.4
25°	412.7	420.9	439.5	455.8	483.6	523.5	559.7	601.6	641.2	672.5	702.3
27.5°	310.0	310.7	325.4	340.4	356.9	389.6	435.2	485.2	541.7	588.3	641.9
30°	265.5	264.2	270.4	279.7	293.8	319.1	353.3	402.5	458.8	529.0	591.5
32.5°	233.9	234.0	238.7	245.5	257.2	274.3	297.7	337.8	391.0	460.1	533.3
35°	203.4	203.2	206.6	211.5	216.4	227.3	243.5	264.4	301.0	365.4	440.4
37.5°	181.4	182.4	184.1	187.2	192.6	198.7	208.3	222.4	248.5	286.6	349.6
40°	169.1	169.6	171.9	174.5	177.7	182.4	190.3	201.7	220.7	251.1	297.2
42.5°	157.9	158.3	159.9	162.3	164.9	169.6	176.2	186.0	201.4	225.1	263.1
45°	141.3	141.3	142.8	143.8	146.7	150.9	156.3	164.5	175.1	192.7	217.9
47.5°	125.8	125.8	126.9	128.7	130.4	133.7	139.0	145.7	153.4	167.0	188.6
50°	116.9	117.2	117.7	119.2	120.4	123.3	127.4	133.2	141.3	151.8	169.8
52.5°	109.7	109.6	110.4	111.0	111.8	113.9	117.0	122.1	129.3	138.5	153.4
55°	98.0	97.2	98.5	99.5	100.2	101.0	102.7	105.9	112.2	119.9	131.0
57.5°	83.5	83.1	84.1	85.0	87.1	89.4	90.9	92.8	96.0	101.6	112.6
60°	71.5	71.5	73.4	74.1	76.4	79.5	82.5	84.2	87.4	91.0	99.2
62.5°	60.9	61.1	61.9	62.6	63.9	67.6	71.8	75.6	78.6	82.1	87.5
65°	51.0	51.4	51.4	51.8	52.7	53.5	55.2	58.2	63.6	68.5	72.6
67.5°	43.3	43.4	43.5	43.9	44.1	45.1	45.8	47.1	48.4	53.0	58.1
70°	38.1	38.7	38.5	38.9	39.2	39.6	40.4	41.1	43.1	44.1	47.1
72.5°	33.3	33.7	33.7	34.0	34.6	34.7	35.3	36.0	37.2	38.1	39.8
75°	27.0	26.8	27.0	27.4	27.6	27.8	27.8	28.7	29.3	30.2	31.3
77.5°	20.8	21.0	21.0	21.0	21.1	21.5	21.4	21.8	22.4	22.9	23.4
80°	16.7	16.9	16.7	16.9	17.2	17.3	17.2	17.3	18.0	18.4	18.4
82.5°	12.9	13.0	13.1	13.1	13.2	13.2	13.6	13.6	14.0	13.9	14.1
85°	7.7	7.5	7.5	7.5	7.7	7.9	7.7	7.7	7.9	7.9	7.9
87.5°	12.4	12.5	12.4	12.3	12.3	12.3	12.4	12.8	12.7	13.0	11.5
90°	48.4	48.0	47.7	47.4	47.0	47.2	47.9	48.4	49.1	49.8	42.8
92.5°	46.0	46.0	45.9	45.8	45.8	45.7	45.5	45.4	45.3	45.1	43.5
95°	88.1	88.7	89.4	90.0	90.6	91.0	91.0	91.0	91.0	91.0	90.3
97.5°	152.6	152.7	152.7	152.8	152.9	152.9	152.9	152.9	152.9	152.9	151.7
100°	194.6	195.0	195.3	195.6	196.0	196.0	196.0	196.0	196.0	196.0	195.1
102.5°	242.4	242.7	243.1	243.4	243.6	243.7	243.5	243.2	243.0	242.7	241.5
105°	315.5	315.5	315.5	315.5	315.5	315.1	314.5	313.9	313.2	312.6	312.0
107.5°	384.2	385.7	387.1	388.6	390.0	390.6	390.4	390.1	389.8	389.6	389.6
110°	437.6	438.6	439.5	440.5	441.4	442.0	442.0	442.0	442.0	442.0	442.0



TEST NUMBER: P331782-830

CATALOG NUMBER: S122RDIW-S290D1440U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	488.8	489.5	490.2	490.9	491.5	492.3	493.0	493.8	494.6	495.3	495.6
115°	568.4	569.3	570.2	571.2	572.1	572.8	573.1	573.4	573.7	574.1	574.7
117.5°	644.2	645.2	646.1	647.1	648.0	648.9	649.7	650.4	651.2	652.0	653.7
120°	697.7	698.6	699.6	700.5	701.4	701.9	701.9	701.9	701.9	701.9	704.5
122.5°	750.0	750.6	751.4	752.1	752.7	753.5	754.2	755.0	755.7	756.5	758.3
125°	829.8	830.2	830.5	830.8	831.1	831.7	832.6	833.6	834.5	835.5	836.5
127.5°	902.6	903.6	904.6	905.6	906.6	907.7	908.8	909.9	911.1	912.3	913.4
130°	954.9	956.1	957.4	958.7	959.9	960.8	961.5	962.1	962.8	963.4	964.0
132.5°	1004.8	1005.9	1006.9	1008.0	1008.9	1010.1	1011.5	1013.0	1014.3	1015.7	1015.6
135°	1082.8	1083.7	1084.7	1085.6	1086.6	1087.2	1087.5	1087.8	1088.2	1088.4	1087.8
137.5°	1153.2	1154.5	1155.7	1157.1	1158.3	1159.0	1159.3	1159.5	1159.8	1160.1	1159.2
140°	1202.1	1203.3	1204.7	1205.9	1207.2	1207.8	1207.8	1207.8	1207.8	1207.8	1206.3
142.5°	1246.4	1247.7	1249.0	1250.3	1251.5	1252.0	1251.8	1251.5	1251.2	1251.0	1249.9
145°	1313.0	1314.2	1315.5	1316.7	1318.0	1318.4	1318.1	1317.9	1317.5	1317.2	1315.3
147.5°	1372.3	1373.6	1374.7	1375.9	1377.1	1377.4	1376.7	1376.0	1375.4	1374.6	1373.4
150°	1411.0	1411.9	1412.9	1413.8	1414.8	1414.8	1413.8	1412.9	1411.9	1411.0	1409.8
152.5°	1447.4	1448.6	1449.7	1451.0	1452.2	1452.2	1451.0	1449.7	1448.6	1447.4	1445.9
155°	1496.3	1497.2	1498.2	1499.1	1500.1	1499.7	1498.2	1496.6	1495.0	1493.4	1492.4
157.5°	1538.3	1539.8	1541.3	1542.8	1544.4	1544.1	1541.9	1539.7	1537.6	1535.5	1534.9
160°	1564.4	1565.8	1567.0	1568.2	1569.5	1569.1	1567.3	1565.4	1563.5	1561.6	1561.3
162.5°	1587.1	1588.7	1590.3	1591.8	1593.3	1592.9	1590.8	1588.7	1586.5	1584.3	1584.0
165°	1617.0	1618.6	1620.2	1621.7	1623.3	1623.1	1620.8	1618.6	1616.4	1614.2	1614.2
167.5°	1641.4	1643.1	1644.7	1646.4	1648.0	1647.8	1645.6	1643.3	1641.2	1638.9	1639.0
170°	1654.0	1655.9	1657.7	1659.6	1661.5	1661.4	1659.2	1657.0	1654.7	1652.6	1652.8
172.5°	1664.2	1666.1	1668.0	1669.9	1671.8	1671.6	1669.4	1667.2	1665.0	1662.7	1663.1
175°	1675.3	1677.2	1679.0	1680.9	1682.9	1682.7	1680.5	1678.3	1676.1	1673.9	1674.5
177.5°	1680.4	1681.9	1683.5	1685.0	1686.5	1686.5	1685.0	1683.5	1681.9	1680.4	1680.9
180°	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9



TEST NUMBER: P331782-830

CATALOG NUMBER: S122RDIW-S290D1440U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	616.1	616.1	616.1	616.1	616.1	616.1	616.1	616.1	616.1	616.1	616.1
2.5°	630.9	629.5	628.3	625.3	623.7	620.3	619.8	619.6	615.2	610.9	609.6
5°	652.6	649.1	644.0	638.0	631.8	625.4	621.1	617.6	609.1	601.0	596.3
7.5°	674.4	667.0	658.2	646.9	637.3	626.8	618.9	611.8	599.6	588.0	580.1
10°	690.7	678.7	666.9	651.3	639.0	627.1	616.0	606.3	592.7	577.2	566.3
12.5°	700.8	687.6	671.4	656.1	640.3	625.0	610.1	597.8	581.6	565.7	552.8
15°	714.4	700.3	680.6	658.7	638.5	618.5	601.4	586.0	565.1	545.9	530.1
17.5°	725.7	706.2	685.0	659.8	636.2	611.0	588.9	569.2	545.8	522.8	504.2
20°	729.2	709.9	685.5	660.3	632.4	602.7	578.9	557.5	532.4	507.4	486.0
22.5°	727.0	712.0	684.9	654.6	626.1	595.0	568.2	543.3	515.5	489.9	465.1
25°	711.9	706.7	681.1	648.1	615.6	579.4	548.3	521.1	489.5	462.0	435.1
27.5°	676.7	687.8	671.8	636.7	600.5	561.8	526.8	495.9	463.0	432.2	405.3
30°	642.7	668.2	661.4	628.8	588.3	550.3	511.0	478.7	443.7	411.9	385.4
32.5°	596.3	638.4	645.1	617.8	576.0	534.1	493.0	460.9	424.2	390.9	365.0
35°	522.4	585.3	614.3	596.9	555.0	509.7	467.4	429.9	393.0	360.1	334.4
37.5°	434.2	520.0	568.2	569.4	530.8	483.9	437.7	400.5	362.8	330.5	302.7
40°	377.0	470.0	532.7	546.6	514.1	463.4	416.6	378.7	342.0	310.2	278.3
42.5°	325.6	418.2	495.3	519.5	493.7	443.3	396.4	356.8	321.0	291.1	258.4
45°	263.3	344.3	429.2	472.5	458.2	411.5	362.0	324.3	290.8	264.9	233.6
47.5°	222.2	279.2	361.5	419.9	419.7	377.1	328.4	292.4	261.2	236.9	211.6
50°	198.7	248.4	317.9	384.3	389.8	354.1	307.8	272.1	243.0	217.5	197.2
52.5°	177.6	218.6	281.1	344.8	360.6	329.6	284.7	251.8	223.5	200.0	182.7
55°	150.1	181.8	229.3	288.8	312.8	291.0	251.1	220.3	197.4	177.7	162.7
57.5°	127.0	150.7	188.9	236.8	264.7	251.0	218.1	193.0	173.4	155.6	143.8
60°	112.4	131.9	164.2	204.2	235.1	225.5	197.4	174.1	157.4	141.9	130.8
62.5°	98.7	115.5	143.2	175.7	203.9	199.9	177.0	157.4	142.8	128.8	119.3
65°	79.5	91.6	113.3	138.7	161.5	163.3	146.8	133.6	120.6	109.4	101.0
67.5°	63.2	71.3	86.4	107.9	124.9	131.0	120.9	110.7	100.4	91.8	84.5
70°	53.3	59.8	70.9	88.2	103.9	110.3	104.4	96.5	87.6	80.5	74.3
72.5°	43.2	49.5	57.7	70.4	83.8	90.8	88.7	83.0	75.8	69.8	64.0
75°	32.5	34.5	40.1	48.6	59.1	65.1	66.5	63.6	57.8	53.3	49.9
77.5°	24.0	25.3	27.9	32.3	39.2	44.6	46.8	46.4	42.4	39.9	36.6
80°	19.2	19.9	21.2	23.1	28.3	33.6	35.2	35.2	32.3	31.3	28.1
82.5°	14.6	15.1	15.9	17.0	19.3	24.0	25.7	26.0	24.3	22.9	20.4
85°	8.4	8.1	8.6	9.2	9.6	10.9	13.5	13.9	13.5	11.8	11.1
87.5°	10.1	8.9	7.4	6.2	5.7	5.1	5.2	5.3	5.3	5.6	5.9
90°	35.8	28.9	22.0	16.6	12.8	9.0	5.2	1.4	5.2	9.0	12.8
92.5°	41.9	40.2	38.6	36.4	33.6	30.8	28.1	25.3	28.1	30.8	33.6
95°	89.6	89.1	88.4	86.5	83.3	80.2	77.0	73.9	77.0	80.2	83.3
97.5°	150.5	149.3	148.1	146.1	143.4	140.5	137.8	135.0	137.8	140.5	143.4
100°	194.2	193.2	192.3	190.6	188.0	185.5	182.9	180.5	182.9	185.5	188.0
102.5°	240.3	239.1	237.9	236.3	234.2	232.2	230.3	228.2	230.3	232.2	234.2
105°	311.3	310.8	310.1	309.2	308.3	307.4	306.4	305.5	306.4	307.4	308.3
107.5°	389.6	389.6	389.6	388.9	387.6	386.2	384.7	383.3	384.7	386.2	387.6
110°	442.0	442.0	442.0	440.9	439.0	437.2	435.3	433.4	435.3	437.2	439.0



TEST NUMBER: P331782-830

CATALOG NUMBER: S122RDIW-S290D1440U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	495.9	496.1	496.3	495.5	493.6	491.7	489.8	488.0	489.8	491.7	493.6
115°	575.3	576.0	576.6	576.0	574.1	572.1	570.2	568.4	570.2	572.1	574.1
117.5°	655.4	657.2	659.0	658.6	656.1	653.6	651.0	648.6	651.0	653.6	656.1
120°	707.0	709.5	712.1	712.1	709.5	707.0	704.5	701.9	704.5	707.0	709.5
122.5°	760.1	761.9	763.6	763.0	759.9	756.9	753.8	750.8	753.8	756.9	759.9
125°	837.4	838.4	839.3	838.4	835.5	832.6	829.8	827.0	829.8	832.6	835.5
127.5°	914.5	915.7	916.8	915.6	912.0	908.3	904.7	901.2	904.7	908.3	912.0
130°	964.7	965.3	965.9	964.2	960.1	956.0	951.9	947.7	951.9	956.0	960.1
132.5°	1015.4	1015.3	1015.2	1013.4	1010.1	1006.7	1003.4	1000.0	1003.4	1006.7	1010.1
135°	1087.2	1086.6	1085.9	1083.8	1080.3	1076.9	1073.5	1070.0	1073.5	1076.9	1080.3
137.5°	1158.4	1157.6	1156.8	1154.9	1152.1	1149.2	1146.4	1143.6	1146.4	1149.2	1152.1
140°	1204.7	1203.1	1201.5	1199.3	1196.5	1193.6	1190.7	1187.9	1190.7	1193.6	1196.5
142.5°	1248.9	1247.7	1246.7	1244.7	1241.9	1239.1	1236.2	1233.4	1236.2	1239.1	1241.9
145°	1313.4	1311.5	1309.7	1307.6	1305.3	1303.2	1301.0	1298.7	1301.0	1303.2	1305.3
147.5°	1372.1	1370.8	1369.6	1367.6	1365.0	1362.3	1359.6	1357.0	1359.6	1362.3	1365.0
150°	1408.4	1407.2	1405.9	1404.4	1402.5	1400.6	1398.6	1396.8	1398.6	1400.6	1402.5
152.5°	1444.4	1442.8	1441.3	1439.6	1437.7	1435.8	1433.9	1432.0	1433.9	1435.8	1437.7
155°	1491.5	1490.5	1489.6	1488.7	1487.7	1486.8	1485.8	1484.9	1485.8	1486.8	1487.7
157.5°	1534.4	1533.8	1533.2	1532.6	1532.0	1531.3	1530.7	1530.0	1530.7	1531.3	1532.0
160°	1560.9	1560.7	1560.4	1559.9	1559.2	1558.6	1558.0	1557.4	1558.0	1558.6	1559.2
162.5°	1583.8	1583.4	1583.1	1582.9	1582.7	1582.6	1582.5	1582.3	1582.5	1582.6	1582.7
165°	1614.2	1614.2	1614.2	1614.4	1614.7	1615.0	1615.3	1615.6	1615.3	1615.0	1614.7
167.5°	1639.1	1639.1	1639.2	1639.6	1640.6	1641.5	1642.5	1643.4	1642.5	1641.5	1640.6
170°	1653.2	1653.5	1653.8	1654.4	1655.4	1656.3	1657.3	1658.2	1657.3	1656.3	1655.4
172.5°	1663.4	1663.8	1664.1	1664.7	1665.7	1666.6	1667.5	1668.5	1667.5	1666.6	1665.7
175°	1675.1	1675.7	1676.4	1677.2	1678.1	1679.0	1680.0	1680.9	1680.0	1679.0	1678.1
177.5°	1681.4	1681.9	1682.4	1683.1	1683.9	1684.6	1685.4	1686.1	1685.4	1684.6	1683.9
180°	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9



TEST NUMBER: P331782-830

CATALOG NUMBER: S122RDIW-S290D1440U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	616.1	616.1	616.1	616.1	616.1	616.1	616.1	616.1	616.1	616.1	616.1
2.5°	607.5	606.2	604.0	600.6	598.5	594.9	592.6	593.9	594.3	593.9	593.6
5°	591.2	586.6	580.4	574.4	568.8	562.9	559.4	558.0	555.0	553.3	552.3
7.5°	571.4	563.6	554.9	544.4	535.6	526.2	521.5	519.2	513.0	509.7	506.8
10°	556.7	544.4	535.6	522.0	513.6	501.4	493.0	493.3	484.9	480.2	476.8
12.5°	540.4	527.0	512.4	500.0	488.4	478.6	468.5	464.5	455.6	451.1	441.9
15°	513.4	497.8	482.4	465.7	453.9	438.7	424.1	406.3	392.0	379.6	376.2
17.5°	484.0	464.6	449.1	429.5	409.3	383.8	366.9	356.6	348.0	341.4	336.5
20°	463.7	444.0	427.5	398.0	370.8	353.5	341.1	333.1	324.1	317.1	313.2
22.5°	442.5	422.0	399.4	366.5	345.3	331.4	320.4	311.2	305.1	299.6	296.1
25°	412.4	389.8	352.8	330.2	313.0	298.4	290.8	285.2	278.8	271.3	267.9
27.5°	380.5	344.8	318.1	301.2	284.9	275.5	268.5	260.2	254.5	251.1	247.5
30°	356.7	320.9	300.2	281.7	270.2	259.7	251.6	246.9	241.3	235.5	233.2
32.5°	330.2	301.6	281.6	266.4	254.6	245.6	239.2	231.6	227.6	224.0	219.1
35°	297.2	275.5	257.3	245.0	233.8	226.5	219.0	214.5	207.3	204.2	202.4
37.5°	269.3	250.5	237.0	223.9	215.0	207.0	202.4	195.2	192.1	187.8	183.8
40°	253.4	235.1	222.1	211.3	201.4	195.5	189.7	183.9	179.2	177.3	172.4
42.5°	237.4	222.4	209.3	197.7	191.1	184.6	177.4	173.1	168.2	165.1	162.1
45°	215.2	201.9	190.8	181.2	173.8	167.2	162.5	155.4	152.7	146.5	143.8
47.5°	195.7	183.3	172.7	163.5	156.5	152.1	145.2	139.7	135.3	131.4	128.1
50°	181.8	171.4	161.2	153.1	146.7	140.4	133.4	130.6	123.8	121.8	119.9
52.5°	169.1	159.3	150.0	141.9	135.5	129.5	123.3	119.6	115.0	113.1	111.7
55°	151.4	141.9	133.0	125.9	119.5	113.3	109.4	104.9	102.7	101.2	99.5
57.5°	133.6	125.1	118.2	111.0	104.5	99.6	95.2	92.5	90.3	88.3	86.2
60°	122.2	114.1	107.9	101.2	94.6	90.6	87.2	83.9	81.3	78.3	77.5
62.5°	110.3	103.1	97.5	91.0	85.2	81.5	78.2	75.2	72.1	67.8	66.5
65°	93.8	88.2	82.2	76.8	71.7	68.1	63.3	59.9	58.6	58.2	58.1
67.5°	78.9	73.6	68.4	63.0	58.3	55.0	52.5	52.0	51.1	50.9	50.2
70°	68.9	64.0	58.9	53.7	49.2	48.6	47.8	46.8	45.8	45.4	45.0
72.5°	60.0	55.0	49.8	45.7	43.7	43.0	42.1	41.2	40.5	40.1	39.9
75°	46.0	41.3	37.9	36.4	35.3	34.7	33.4	32.8	32.3	31.7	31.5
77.5°	33.2	30.4	28.9	28.0	26.9	26.2	25.4	24.8	24.3	24.2	23.8
80°	25.3	23.9	22.9	21.6	21.2	20.4	20.2	19.5	19.7	19.0	19.0
82.5°	19.6	18.0	17.1	16.5	16.0	15.4	15.2	14.9	14.9	14.4	14.4
85°	10.1	9.6	9.2	8.8	8.8	8.1	8.4	8.1	8.1	7.7	7.5
87.5°	6.6	7.4	8.5	9.9	11.3	12.5	12.3	12.1	12.0	11.9	11.6
90°	16.6	22.0	28.9	35.8	42.8	49.8	49.1	48.4	47.9	47.2	47.0
92.5°	36.4	38.6	40.2	41.9	43.5	45.1	45.3	45.4	45.5	45.7	45.8
95°	86.5	88.4	89.1	89.6	90.3	91.0	91.0	91.0	91.0	91.0	90.6
97.5°	146.1	148.1	149.3	150.5	151.7	152.9	152.9	152.9	152.9	152.9	152.9
100°	190.6	192.3	193.2	194.2	195.1	196.0	196.0	196.0	196.0	196.0	196.0
102.5°	236.3	237.9	239.1	240.3	241.5	242.7	243.0	243.2	243.5	243.7	243.6
105°	309.2	310.1	310.8	311.3	312.0	312.6	313.2	313.9	314.5	315.1	315.5
107.5°	388.9	389.6	389.6	389.6	389.6	389.6	389.8	390.1	390.4	390.6	390.0
110°	440.9	442.0	442.0	442.0	442.0	442.0	442.0	442.0	442.0	442.0	441.4



TEST NUMBER: P331782-830

CATALOG NUMBER: S122RDIW-S290D1440U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	495.5	496.3	496.1	495.9	495.6	495.3	494.6	493.8	493.0	492.3	491.5
115°	576.0	576.6	576.0	575.3	574.7	574.1	573.7	573.4	573.1	572.8	572.1
117.5°	658.6	659.0	657.2	655.4	653.7	652.0	651.2	650.4	649.7	648.9	648.0
120°	712.1	712.1	709.5	707.0	704.5	701.9	701.9	701.9	701.9	701.9	701.4
122.5°	763.0	763.6	761.9	760.1	758.3	756.5	755.7	755.0	754.2	753.5	752.7
125°	838.4	839.3	838.4	837.4	836.5	835.5	834.5	833.6	832.6	831.7	831.1
127.5°	915.6	916.8	915.7	914.5	913.4	912.3	911.1	909.9	908.8	907.7	906.6
130°	964.2	965.9	965.3	964.7	964.0	963.4	962.8	962.1	961.5	960.8	959.9
132.5°	1013.4	1015.2	1015.3	1015.4	1015.6	1015.7	1014.3	1013.0	1011.5	1010.1	1008.9
135°	1083.8	1085.9	1086.6	1087.2	1087.8	1088.4	1088.2	1087.8	1087.5	1087.2	1086.6
137.5°	1154.9	1156.8	1157.6	1158.4	1159.2	1160.1	1159.8	1159.5	1159.3	1159.0	1158.3
140°	1199.3	1201.5	1203.1	1204.7	1206.3	1207.8	1207.8	1207.8	1207.8	1207.8	1207.2
142.5°	1244.7	1246.7	1247.7	1248.9	1249.9	1251.0	1251.2	1251.5	1251.8	1252.0	1251.5
145°	1307.6	1309.7	1311.5	1313.4	1315.3	1317.2	1317.5	1317.9	1318.1	1318.4	1318.0
147.5°	1367.6	1369.6	1370.8	1372.1	1373.4	1374.6	1375.4	1376.0	1376.7	1377.4	1377.1
150°	1404.4	1405.9	1407.2	1408.4	1409.8	1411.0	1411.9	1412.9	1413.8	1414.8	1414.8
152.5°	1439.6	1441.3	1442.8	1444.4	1445.9	1447.4	1448.6	1449.7	1451.0	1452.2	1452.2
155°	1488.7	1489.6	1490.5	1491.5	1492.4	1493.4	1495.0	1496.6	1498.2	1499.7	1500.1
157.5°	1532.6	1533.2	1533.8	1534.4	1534.9	1535.5	1537.6	1539.7	1541.9	1544.1	1544.4
160°	1559.9	1560.4	1560.7	1560.9	1561.3	1561.6	1563.5	1565.4	1567.3	1569.1	1569.5
162.5°	1582.9	1583.1	1583.4	1583.8	1584.0	1584.3	1586.5	1588.7	1590.8	1592.9	1593.3
165°	1614.4	1614.2	1614.2	1614.2	1614.2	1614.2	1616.4	1618.6	1620.8	1623.1	1623.3
167.5°	1639.6	1639.2	1639.1	1639.1	1639.0	1638.9	1641.2	1643.3	1645.6	1647.8	1648.0
170°	1654.4	1653.8	1653.5	1653.2	1652.8	1652.6	1654.7	1657.0	1659.2	1661.4	1661.5
172.5°	1664.7	1664.1	1663.8	1663.4	1663.1	1662.7	1665.0	1667.2	1669.4	1671.6	1671.8
175°	1677.2	1676.4	1675.7	1675.1	1674.5	1673.9	1676.1	1678.3	1680.5	1682.7	1682.9
177.5°	1683.1	1682.4	1681.9	1681.4	1680.9	1680.4	1681.9	1683.5	1685.0	1686.5	1686.5
180°	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9



TEST NUMBER: P331782-830

CATALOG NUMBER: S122RDIW-S290D1440U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	616.1	616.1	616.1	616.1	616.1	616.1	616.1	616.1	616.1	616.1	616.1
2.5°	591.7	592.0	591.5	591.8	591.5	592.0	591.7	593.6	593.9	594.3	593.9
5°	551.3	548.7	548.3	547.7	548.3	548.7	551.3	552.3	553.3	555.0	558.0
7.5°	503.1	502.8	501.6	500.1	501.6	502.8	503.1	506.8	509.7	513.0	519.2
10°	472.1	471.0	470.8	469.3	470.8	471.0	472.1	476.8	480.2	484.9	493.3
12.5°	435.7	428.9	428.2	424.4	428.2	428.9	435.7	441.9	451.1	455.6	464.5
15°	371.1	369.8	365.4	362.7	365.4	369.8	371.1	376.2	379.6	392.0	406.3
17.5°	334.0	329.8	328.5	327.9	328.5	329.8	334.0	336.5	341.4	348.0	356.6
20°	310.2	306.4	305.8	305.3	305.8	306.4	310.2	313.2	317.1	324.1	333.1
22.5°	293.8	289.7	288.1	286.8	288.1	289.7	293.8	296.1	299.6	305.1	311.2
25°	265.7	264.2	263.3	262.9	263.3	264.2	265.7	267.9	271.3	278.8	285.2
27.5°	243.7	240.4	239.8	238.7	239.8	240.4	243.7	247.5	251.1	254.5	260.2
30°	231.2	230.2	228.7	227.3	228.7	230.2	231.2	233.2	235.5	241.3	246.9
32.5°	216.5	215.6	214.2	213.7	214.2	215.6	216.5	219.1	224.0	227.6	231.6
35°	200.2	197.2	195.9	194.0	195.9	197.2	200.2	202.4	204.2	207.3	214.5
37.5°	182.9	181.3	179.6	180.2	179.6	181.3	182.9	183.8	187.8	192.1	195.2
40°	169.6	168.5	168.1	167.9	168.1	168.5	169.6	172.4	177.3	179.2	183.9
42.5°	158.9	156.0	154.9	154.9	154.9	156.0	158.9	162.1	165.1	168.2	173.1
45°	142.8	140.1	138.1	138.3	138.1	140.1	142.8	143.8	146.5	152.7	155.4
47.5°	126.3	126.2	125.0	125.4	125.0	126.2	126.3	128.1	131.4	135.3	139.7
50°	118.4	117.2	116.2	116.5	116.2	117.2	118.4	119.9	121.8	123.8	130.6
52.5°	110.8	109.7	109.1	110.0	109.1	109.7	110.8	111.7	113.1	115.0	119.6
55°	98.5	97.2	97.0	96.8	97.0	97.2	98.5	99.5	101.2	102.7	104.9
57.5°	84.6	83.8	82.5	82.0	82.5	83.8	84.6	86.2	88.3	90.3	92.5
60°	74.7	73.0	70.9	70.7	70.9	73.0	74.7	77.5	78.3	81.3	83.9
62.5°	65.6	65.3	64.8	64.8	64.8	65.3	65.6	66.5	67.8	72.1	75.2
65°	57.6	57.4	57.6	57.8	57.6	57.4	57.6	58.1	58.2	58.6	59.9
67.5°	50.1	49.8	49.4	49.6	49.4	49.8	50.1	50.2	50.9	51.1	52.0
70°	44.5	44.3	44.1	44.1	44.1	44.3	44.5	45.0	45.4	45.8	46.8
72.5°	39.0	39.0	38.8	38.6	38.8	39.0	39.0	39.9	40.1	40.5	41.2
75°	31.3	30.8	30.8	30.8	30.8	30.8	31.3	31.5	31.7	32.3	32.8
77.5°	23.8	23.6	23.4	23.2	23.4	23.6	23.8	23.8	24.2	24.3	24.8
80°	18.9	18.7	18.4	18.4	18.4	18.7	18.9	19.0	19.0	19.7	19.5
82.5°	14.4	14.1	14.1	13.9	14.1	14.1	14.4	14.4	14.4	14.9	14.9
85°	7.7	7.9	7.7	8.1	7.7	7.9	7.7	7.5	7.7	8.1	8.1
87.5°	11.7	11.6	11.8	11.7	11.8	11.6	11.7	11.6	11.9	12.0	12.1
90°	47.4	47.7	48.0	48.4	48.0	47.7	47.4	47.0	47.2	47.9	48.4
92.5°	45.8	45.9	46.0	46.0	46.0	45.9	45.8	45.8	45.7	45.5	45.4
95°	90.0	89.4	88.7	88.1	88.7	89.4	90.0	90.6	91.0	91.0	91.0
97.5°	152.8	152.7	152.7	152.6	152.7	152.7	152.8	152.9	152.9	152.9	152.9
100°	195.6	195.3	195.0	194.6	195.0	195.3	195.6	196.0	196.0	196.0	196.0
102.5°	243.4	243.1	242.7	242.4	242.7	243.1	243.4	243.6	243.7	243.5	243.2
105°	315.5	315.5	315.5	315.5	315.5	315.5	315.5	315.5	315.1	314.5	313.9
107.5°	388.6	387.1	385.7	384.2	385.7	387.1	388.6	390.0	390.6	390.4	390.1
110°	440.5	439.5	438.6	437.6	438.6	439.5	440.5	441.4	442.0	442.0	442.0



TEST NUMBER: P331782-830

CATALOG NUMBER: S122RDIW-S290D1440U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	490.9	490.2	489.5	488.8	489.5	490.2	490.9	491.5	492.3	493.0	493.8
115°	571.2	570.2	569.3	568.4	569.3	570.2	571.2	572.1	572.8	573.1	573.4
117.5°	647.1	646.1	645.2	644.2	645.2	646.1	647.1	648.0	648.9	649.7	650.4
120°	700.5	699.6	698.6	697.7	698.6	699.6	700.5	701.4	701.9	701.9	701.9
122.5°	752.1	751.4	750.6	750.0	750.6	751.4	752.1	752.7	753.5	754.2	755.0
125°	830.8	830.5	830.2	829.8	830.2	830.5	830.8	831.1	831.7	832.6	833.6
127.5°	905.6	904.6	903.6	902.6	903.6	904.6	905.6	906.6	907.7	908.8	909.9
130°	958.7	957.4	956.1	954.9	956.1	957.4	958.7	959.9	960.8	961.5	962.1
132.5°	1008.0	1006.9	1005.9	1004.8	1005.9	1006.9	1008.0	1008.9	1010.1	1011.5	1013.0
135°	1085.6	1084.7	1083.7	1082.8	1083.7	1084.7	1085.6	1086.6	1087.2	1087.5	1087.8
137.5°	1157.1	1155.7	1154.5	1153.2	1154.5	1155.7	1157.1	1158.3	1159.0	1159.3	1159.5
140°	1205.9	1204.7	1203.3	1202.1	1203.3	1204.7	1205.9	1207.2	1207.8	1207.8	1207.8
142.5°	1250.3	1249.0	1247.7	1246.4	1247.7	1249.0	1250.3	1251.5	1252.0	1251.8	1251.5
145°	1316.7	1315.5	1314.2	1313.0	1314.2	1315.5	1316.7	1318.0	1318.4	1318.1	1317.9
147.5°	1375.9	1374.7	1373.6	1372.3	1373.6	1374.7	1375.9	1377.1	1377.4	1376.7	1376.0
150°	1413.8	1412.9	1411.9	1411.0	1411.9	1412.9	1413.8	1414.8	1414.8	1413.8	1412.9
152.5°	1451.0	1449.7	1448.6	1447.4	1448.6	1449.7	1451.0	1452.2	1452.2	1451.0	1449.7
155°	1499.1	1498.2	1497.2	1496.3	1497.2	1498.2	1499.1	1500.1	1499.7	1498.2	1496.6
157.5°	1542.8	1541.3	1539.8	1538.3	1539.8	1541.3	1542.8	1544.4	1544.1	1541.9	1539.7
160°	1568.2	1567.0	1565.8	1564.4	1565.8	1567.0	1568.2	1569.5	1569.1	1567.3	1565.4
162.5°	1591.8	1590.3	1588.7	1587.1	1588.7	1590.3	1591.8	1593.3	1592.9	1590.8	1588.7
165°	1621.7	1620.2	1618.6	1617.0	1618.6	1620.2	1621.7	1623.3	1623.1	1620.8	1618.6
167.5°	1646.4	1644.7	1643.1	1641.4	1643.1	1644.7	1646.4	1648.0	1647.8	1645.6	1643.3
170°	1659.6	1657.7	1655.9	1654.0	1655.9	1657.7	1659.6	1661.5	1661.4	1659.2	1657.0
172.5°	1669.9	1668.0	1666.1	1664.2	1666.1	1668.0	1669.9	1671.8	1671.6	1669.4	1667.2
175°	1680.9	1679.0	1677.2	1675.3	1677.2	1679.0	1680.9	1682.9	1682.7	1680.5	1678.3
177.5°	1685.0	1683.5	1681.9	1680.4	1681.9	1683.5	1685.0	1686.5	1686.5	1685.0	1683.5
180°	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9



TEST NUMBER: P331782-830

CATALOG NUMBER: S122RDIW-S290D1440U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	616.1	616.1	616.1	616.1	616.1	616.1	616.1	616.1	616.1	616.1	616.1
2.5°	592.6	594.9	598.5	600.6	604.0	606.2	607.5	609.6	610.9	615.2	619.6
5°	559.4	562.9	568.8	574.4	580.4	586.6	591.2	596.3	601.0	609.1	617.6
7.5°	521.5	526.2	535.6	544.4	554.9	563.6	571.4	580.1	588.0	599.6	611.8
10°	493.0	501.4	513.6	522.0	535.6	544.4	556.7	566.3	577.2	592.7	606.3
12.5°	468.5	478.6	488.4	500.0	512.4	527.0	540.4	552.8	565.7	581.6	597.8
15°	424.1	438.7	453.9	465.7	482.4	497.8	513.4	530.1	545.9	565.1	586.0
17.5°	366.9	383.8	409.3	429.5	449.1	464.6	484.0	504.2	522.8	545.8	569.2
20°	341.1	353.5	370.8	398.0	427.5	444.0	463.7	486.0	507.4	532.4	557.5
22.5°	320.4	331.4	345.3	366.5	399.4	422.0	442.5	465.1	489.9	515.5	543.3
25°	290.8	298.4	313.0	330.2	352.8	389.8	412.4	435.1	462.0	489.5	521.1
27.5°	268.5	275.5	284.9	301.2	318.1	344.8	380.5	405.3	432.2	463.0	495.9
30°	251.6	259.7	270.2	281.7	300.2	320.9	356.7	385.4	411.9	443.7	478.7
32.5°	239.2	245.6	254.6	266.4	281.6	301.6	330.2	365.0	390.9	424.2	460.9
35°	219.0	226.5	233.8	245.0	257.3	275.5	297.2	334.4	360.1	393.0	429.9
37.5°	202.4	207.0	215.0	223.9	237.0	250.5	269.3	302.7	330.5	362.8	400.5
40°	189.7	195.5	201.4	211.3	222.1	235.1	253.4	278.3	310.2	342.0	378.7
42.5°	177.4	184.6	191.1	197.7	209.3	222.4	237.4	258.4	291.1	321.0	356.8
45°	162.5	167.2	173.8	181.2	190.8	201.9	215.2	233.6	264.9	290.8	324.3
47.5°	145.2	152.1	156.5	163.5	172.7	183.3	195.7	211.6	236.9	261.2	292.4
50°	133.4	140.4	146.7	153.1	161.2	171.4	181.8	197.2	217.5	243.0	272.1
52.5°	123.3	129.5	135.5	141.9	150.0	159.3	169.1	182.7	200.0	223.5	251.8
55°	109.4	113.3	119.5	125.9	133.0	141.9	151.4	162.7	177.7	197.4	220.3
57.5°	95.2	99.6	104.5	111.0	118.2	125.1	133.6	143.8	155.6	173.4	193.0
60°	87.2	90.6	94.6	101.2	107.9	114.1	122.2	130.8	141.9	157.4	174.1
62.5°	78.2	81.5	85.2	91.0	97.5	103.1	110.3	119.3	128.8	142.8	157.4
65°	63.3	68.1	71.7	76.8	82.2	88.2	93.8	101.0	109.4	120.6	133.6
67.5°	52.5	55.0	58.3	63.0	68.4	73.6	78.9	84.5	91.8	100.4	110.7
70°	47.8	48.6	49.2	53.7	58.9	64.0	68.9	74.3	80.5	87.6	96.5
72.5°	42.1	43.0	43.7	45.7	49.8	55.0	60.0	64.0	69.8	75.8	83.0
75°	33.4	34.7	35.3	36.4	37.9	41.3	46.0	49.9	53.3	57.8	63.6
77.5°	25.4	26.2	26.9	28.0	28.9	30.4	33.2	36.6	39.9	42.4	46.4
80°	20.2	20.4	21.2	21.6	22.9	23.9	25.3	28.1	31.3	32.3	35.2
82.5°	15.2	15.4	16.0	16.5	17.1	18.0	19.6	20.4	22.9	24.3	26.0
85°	8.4	8.1	8.8	8.8	9.2	9.6	10.1	11.1	11.8	13.5	13.9
87.5°	12.3	12.5	11.3	9.9	8.5	7.4	6.6	5.9	5.6	5.3	5.3
90°	49.1	49.8	42.8	35.8	28.9	22.0	16.6	12.8	9.0	5.2	1.4
92.5°	45.3	45.1	43.5	41.9	40.2	38.6	36.4	33.6	30.8	28.1	25.3
95°	91.0	91.0	90.3	89.6	89.1	88.4	86.5	83.3	80.2	77.0	73.9
97.5°	152.9	152.9	151.7	150.5	149.3	148.1	146.1	143.4	140.5	137.8	135.0
100°	196.0	196.0	195.1	194.2	193.2	192.3	190.6	188.0	185.5	182.9	180.5
102.5°	243.0	242.7	241.5	240.3	239.1	237.9	236.3	234.2	232.2	230.3	228.2
105°	313.2	312.6	312.0	311.3	310.8	310.1	309.2	308.3	307.4	306.4	305.5
107.5°	389.8	389.6	389.6	389.6	389.6	389.6	388.9	387.6	386.2	384.7	383.3
110°	442.0	442.0	442.0	442.0	442.0	442.0	440.9	439.0	437.2	435.3	433.4



TEST NUMBER: P331782-830

CATALOG NUMBER: S122RDIW-S290D1440U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	494.6	495.3	495.6	495.9	496.1	496.3	495.5	493.6	491.7	489.8	488.0
115°	573.7	574.1	574.7	575.3	576.0	576.6	576.0	574.1	572.1	570.2	568.4
117.5°	651.2	652.0	653.7	655.4	657.2	659.0	658.6	656.1	653.6	651.0	648.6
120°	701.9	701.9	704.5	707.0	709.5	712.1	712.1	709.5	707.0	704.5	701.9
122.5°	755.7	756.5	758.3	760.1	761.9	763.6	763.0	759.9	756.9	753.8	750.8
125°	834.5	835.5	836.5	837.4	838.4	839.3	838.4	835.5	832.6	829.8	827.0
127.5°	911.1	912.3	913.4	914.5	915.7	916.8	915.6	912.0	908.3	904.7	901.2
130°	962.8	963.4	964.0	964.7	965.3	965.9	964.2	960.1	956.0	951.9	947.7
132.5°	1014.3	1015.7	1015.6	1015.4	1015.3	1015.2	1013.4	1010.1	1006.7	1003.4	1000.0
135°	1088.2	1088.4	1087.8	1087.2	1086.6	1085.9	1083.8	1080.3	1076.9	1073.5	1070.0
137.5°	1159.8	1160.1	1159.2	1158.4	1157.6	1156.8	1154.9	1152.1	1149.2	1146.4	1143.6
140°	1207.8	1207.8	1206.3	1204.7	1203.1	1201.5	1199.3	1196.5	1193.6	1190.7	1187.9
142.5°	1251.2	1251.0	1249.9	1248.9	1247.7	1246.7	1244.7	1241.9	1239.1	1236.2	1233.4
145°	1317.5	1317.2	1315.3	1313.4	1311.5	1309.7	1307.6	1305.3	1303.2	1301.0	1298.7
147.5°	1375.4	1374.6	1373.4	1372.1	1370.8	1369.6	1367.6	1365.0	1362.3	1359.6	1357.0
150°	1411.9	1411.0	1409.8	1408.4	1407.2	1405.9	1404.4	1402.5	1400.6	1398.6	1396.8
152.5°	1448.6	1447.4	1445.9	1444.4	1442.8	1441.3	1439.6	1437.7	1435.8	1433.9	1432.0
155°	1495.0	1493.4	1492.4	1491.5	1490.5	1489.6	1488.7	1487.7	1486.8	1485.8	1484.9
157.5°	1537.6	1535.5	1534.9	1534.4	1533.8	1533.2	1532.6	1532.0	1531.3	1530.7	1530.0
160°	1563.5	1561.6	1561.3	1560.9	1560.7	1560.4	1559.9	1559.2	1558.6	1558.0	1557.4
162.5°	1586.5	1584.3	1584.0	1583.8	1583.4	1583.1	1582.9	1582.7	1582.6	1582.5	1582.3
165°	1616.4	1614.2	1614.2	1614.2	1614.2	1614.2	1614.4	1614.7	1615.0	1615.3	1615.6
167.5°	1641.2	1638.9	1639.0	1639.1	1639.1	1639.2	1639.6	1640.6	1641.5	1642.5	1643.4
170°	1654.7	1652.6	1652.8	1653.2	1653.5	1653.8	1654.4	1655.4	1656.3	1657.3	1658.2
172.5°	1665.0	1662.7	1663.1	1663.4	1663.8	1664.1	1664.7	1665.7	1666.6	1667.5	1668.5
175°	1676.1	1673.9	1674.5	1675.1	1675.7	1676.4	1677.2	1678.1	1679.0	1680.0	1680.9
177.5°	1681.9	1680.4	1680.9	1681.4	1681.9	1682.4	1683.1	1683.9	1684.6	1685.4	1686.1
180°	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9



TEST NUMBER: P331782-830

CATALOG NUMBER: S122RDIW-S290D1440U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	616.1	616.1	616.1	616.1	616.1	616.1	616.1	616.1	616.1	616.1	616.1
2.5°	619.8	620.3	623.7	625.3	628.3	629.5	630.9	630.6	630.6	631.2	636.0
5°	621.1	625.4	631.8	638.0	644.0	649.1	652.6	656.0	657.3	663.5	669.0
7.5°	618.9	626.8	637.3	646.9	658.2	667.0	674.4	681.1	685.6	694.7	703.9
10°	616.0	627.1	639.0	651.3	666.9	678.7	690.7	699.9	702.9	716.3	724.1
12.5°	610.1	625.0	640.3	656.1	671.4	687.6	700.8	710.0	720.6	732.6	746.9
15°	601.4	618.5	638.5	658.7	680.6	700.3	714.4	730.5	742.1	755.4	767.8
17.5°	588.9	611.0	636.2	659.8	685.0	706.2	725.7	741.0	749.1	756.8	758.6
20°	578.9	602.7	632.4	660.3	685.5	709.9	729.2	742.1	744.2	744.4	733.1
22.5°	568.2	595.0	626.1	654.6	684.9	712.0	727.0	732.4	724.0	709.5	687.5
25°	548.3	579.4	615.6	648.1	681.1	706.7	711.9	702.3	672.5	641.2	601.6
27.5°	526.8	561.8	600.5	636.7	671.8	687.8	676.7	641.9	588.3	541.7	485.2
30°	511.0	550.3	588.3	628.8	661.4	668.2	642.7	591.5	529.0	458.8	402.5
32.5°	493.0	534.1	576.0	617.8	645.1	638.4	596.3	533.3	460.1	391.0	337.8
35°	467.4	509.7	555.0	596.9	614.3	585.3	522.4	440.4	365.4	301.0	264.4
37.5°	437.7	483.9	530.8	569.4	568.2	520.0	434.2	349.6	286.6	248.5	222.4
40°	416.6	463.4	514.1	546.6	532.7	470.0	377.0	297.2	251.1	220.7	201.7
42.5°	396.4	443.3	493.7	519.5	495.3	418.2	325.6	263.1	225.1	201.4	186.0
45°	362.0	411.5	458.2	472.5	429.2	344.3	263.3	217.9	192.7	175.1	164.5
47.5°	328.4	377.1	419.7	419.9	361.5	279.2	222.2	188.6	167.0	153.4	145.7
50°	307.8	354.1	389.8	384.3	317.9	248.4	198.7	169.8	151.8	141.3	133.2
52.5°	284.7	329.6	360.6	344.8	281.1	218.6	177.6	153.4	138.5	129.3	122.1
55°	251.1	291.0	312.8	288.8	229.3	181.8	150.1	131.0	119.9	112.2	105.9
57.5°	218.1	251.0	264.7	236.8	188.9	150.7	127.0	112.6	101.6	96.0	92.8
60°	197.4	225.5	235.1	204.2	164.2	131.9	112.4	99.2	91.0	87.4	84.2
62.5°	177.0	199.9	203.9	175.7	143.2	115.5	98.7	87.5	82.1	78.6	75.6
65°	146.8	163.3	161.5	138.7	113.3	91.6	79.5	72.6	68.5	63.6	58.2
67.5°	120.9	131.0	124.9	107.9	86.4	71.3	63.2	58.1	53.0	48.4	47.1
70°	104.4	110.3	103.9	88.2	70.9	59.8	53.3	47.1	44.1	43.1	41.1
72.5°	88.7	90.8	83.8	70.4	57.7	49.5	43.2	39.8	38.1	37.2	36.0
75°	66.5	65.1	59.1	48.6	40.1	34.5	32.5	31.3	30.2	29.3	28.7
77.5°	46.8	44.6	39.2	32.3	27.9	25.3	24.0	23.4	22.9	22.4	21.8
80°	35.2	33.6	28.3	23.1	21.2	19.9	19.2	18.4	18.4	18.0	17.3
82.5°	25.7	24.0	19.3	17.0	15.9	15.1	14.6	14.1	13.9	14.0	13.6
85°	13.5	10.9	9.6	9.2	8.6	8.1	8.4	7.9	7.9	7.9	7.7
87.5°	5.2	5.1	5.7	6.2	7.4	8.9	10.1	11.5	13.0	12.7	12.8
90°	5.2	9.0	12.8	16.6	22.0	28.9	35.8	42.8	49.8	49.1	48.4
92.5°	28.1	30.8	33.6	36.4	38.6	40.2	41.9	43.5	45.1	45.3	45.4
95°	77.0	80.2	83.3	86.5	88.4	89.1	89.6	90.3	91.0	91.0	91.0
97.5°	137.8	140.5	143.4	146.1	148.1	149.3	150.5	151.7	152.9	152.9	152.9
100°	182.9	185.5	188.0	190.6	192.3	193.2	194.2	195.1	196.0	196.0	196.0
102.5°	230.3	232.2	234.2	236.3	237.9	239.1	240.3	241.5	242.7	243.0	243.2
105°	306.4	307.4	308.3	309.2	310.1	310.8	311.3	312.0	312.6	313.2	313.9
107.5°	384.7	386.2	387.6	388.9	389.6	389.6	389.6	389.6	389.6	389.8	390.1
110°	435.3	437.2	439.0	440.9	442.0	442.0	442.0	442.0	442.0	442.0	442.0



TEST NUMBER: P331782-830

CATALOG NUMBER: S122RDIW-S290D1440U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	489.8	491.7	493.6	495.5	496.3	496.1	495.9	495.6	495.3	494.6	493.8
115°	570.2	572.1	574.1	576.0	576.6	576.0	575.3	574.7	574.1	573.7	573.4
117.5°	651.0	653.6	656.1	658.6	659.0	657.2	655.4	653.7	652.0	651.2	650.4
120°	704.5	707.0	709.5	712.1	712.1	709.5	707.0	704.5	701.9	701.9	701.9
122.5°	753.8	756.9	759.9	763.0	763.6	761.9	760.1	758.3	756.5	755.7	755.0
125°	829.8	832.6	835.5	838.4	839.3	838.4	837.4	836.5	835.5	834.5	833.6
127.5°	904.7	908.3	912.0	915.6	916.8	915.7	914.5	913.4	912.3	911.1	909.9
130°	951.9	956.0	960.1	964.2	965.9	965.3	964.7	964.0	963.4	962.8	962.1
132.5°	1003.4	1006.7	1010.1	1013.4	1015.2	1015.3	1015.4	1015.6	1015.7	1014.3	1013.0
135°	1073.5	1076.9	1080.3	1083.8	1085.9	1086.6	1087.2	1087.8	1088.4	1088.2	1087.8
137.5°	1146.4	1149.2	1152.1	1154.9	1156.8	1157.6	1158.4	1159.2	1160.1	1159.8	1159.5
140°	1190.7	1193.6	1196.5	1199.3	1201.5	1203.1	1204.7	1206.3	1207.8	1207.8	1207.8
142.5°	1236.2	1239.1	1241.9	1244.7	1246.7	1247.7	1248.9	1249.9	1251.0	1251.2	1251.5
145°	1301.0	1303.2	1305.3	1307.6	1309.7	1311.5	1313.4	1315.3	1317.2	1317.5	1317.9
147.5°	1359.6	1362.3	1365.0	1367.6	1369.6	1370.8	1372.1	1373.4	1374.6	1375.4	1376.0
150°	1398.6	1400.6	1402.5	1404.4	1405.9	1407.2	1408.4	1409.8	1411.0	1411.9	1412.9
152.5°	1433.9	1435.8	1437.7	1439.6	1441.3	1442.8	1444.4	1445.9	1447.4	1448.6	1449.7
155°	1485.8	1486.8	1487.7	1488.7	1489.6	1490.5	1491.5	1492.4	1493.4	1495.0	1496.6
157.5°	1530.7	1531.3	1532.0	1532.6	1533.2	1533.8	1534.4	1534.9	1535.5	1537.6	1539.7
160°	1558.0	1558.6	1559.2	1559.9	1560.4	1560.7	1560.9	1561.3	1561.6	1563.5	1565.4
162.5°	1582.5	1582.6	1582.7	1582.9	1583.1	1583.4	1583.8	1584.0	1584.3	1586.5	1588.7
165°	1615.3	1615.0	1614.7	1614.4	1614.2	1614.2	1614.2	1614.2	1614.2	1616.4	1618.6
167.5°	1642.5	1641.5	1640.6	1639.6	1639.2	1639.1	1639.1	1639.0	1638.9	1641.2	1643.3
170°	1657.3	1656.3	1655.4	1654.4	1653.8	1653.5	1653.2	1652.8	1652.6	1654.7	1657.0
172.5°	1667.5	1666.6	1665.7	1664.7	1664.1	1663.8	1663.4	1663.1	1662.7	1665.0	1667.2
175°	1680.0	1679.0	1678.1	1677.2	1676.4	1675.7	1675.1	1674.5	1673.9	1676.1	1678.3
177.5°	1685.4	1684.6	1683.9	1683.1	1682.4	1681.9	1681.4	1680.9	1680.4	1681.9	1683.5
180°	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9



TEST NUMBER: P331782-830

CATALOG NUMBER: S122RDIW-S290D1440U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	616.1	616.1	616.1	616.1	616.1	616.1	616.1
2.5°	637.7	640.0	641.0	641.0	642.2	641.7	641.2
5°	674.4	678.4	679.4	683.2	686.0	685.1	685.5
7.5°	710.9	717.4	723.9	726.8	727.3	729.0	729.6
10°	733.3	738.7	748.7	747.2	754.7	759.0	752.0
12.5°	754.9	762.1	769.1	771.0	775.2	776.7	773.8
15°	774.4	778.3	778.6	777.6	778.9	777.8	773.7
17.5°	756.2	749.9	737.3	731.2	726.5	719.4	716.6
20°	726.0	707.6	686.2	677.6	667.6	647.9	652.6
22.5°	660.9	640.0	618.5	593.5	581.5	562.9	561.8
25°	559.7	523.5	483.6	455.8	439.5	420.9	412.7
27.5°	435.2	389.6	356.9	340.4	325.4	310.7	310.0
30°	353.3	319.1	293.8	279.7	270.4	264.2	265.5
32.5°	297.7	274.3	257.2	245.5	238.7	234.0	233.9
35°	243.5	227.3	216.4	211.5	206.6	203.2	203.4
37.5°	208.3	198.7	192.6	187.2	184.1	182.4	181.4
40°	190.3	182.4	177.7	174.5	171.9	169.6	169.1
42.5°	176.2	169.6	164.9	162.3	159.9	158.3	157.9
45°	156.3	150.9	146.7	143.8	142.8	141.3	141.3
47.5°	139.0	133.7	130.4	128.7	126.9	125.8	125.8
50°	127.4	123.3	120.4	119.2	117.7	117.2	116.9
52.5°	117.0	113.9	111.8	111.0	110.4	109.6	109.7
55°	102.7	101.0	100.2	99.5	98.5	97.2	98.0
57.5°	90.9	89.4	87.1	85.0	84.1	83.1	83.5
60°	82.5	79.5	76.4	74.1	73.4	71.5	71.5
62.5°	71.8	67.6	63.9	62.6	61.9	61.1	60.9
65°	55.2	53.5	52.7	51.8	51.4	51.4	51.0
67.5°	45.8	45.1	44.1	43.9	43.5	43.4	43.3
70°	40.4	39.6	39.2	38.9	38.5	38.7	38.1
72.5°	35.3	34.7	34.6	34.0	33.7	33.7	33.3
75°	27.8	27.8	27.6	27.4	27.0	26.8	27.0
77.5°	21.4	21.5	21.1	21.0	21.0	21.0	20.8
80°	17.2	17.3	17.2	16.9	16.7	16.9	16.7
82.5°	13.6	13.2	13.2	13.1	13.1	13.0	12.9
85°	7.7	7.9	7.7	7.5	7.5	7.5	7.7
87.5°	12.4	12.3	12.3	12.3	12.4	12.5	12.4
90°	47.9	47.2	47.0	47.4	47.7	48.0	48.4
92.5°	45.5	45.7	45.8	45.8	45.9	46.0	46.0
95°	91.0	91.0	90.6	90.0	89.4	88.7	88.1
97.5°	152.9	152.9	152.9	152.8	152.7	152.7	152.6
100°	196.0	196.0	196.0	195.6	195.3	195.0	194.6
102.5°	243.5	243.7	243.6	243.4	243.1	242.7	242.4
105°	314.5	315.1	315.5	315.5	315.5	315.5	315.5
107.5°	390.4	390.6	390.0	388.6	387.1	385.7	384.2
110°	442.0	442.0	441.4	440.5	439.5	438.6	437.6



TEST NUMBER: P331782-830

CATALOG NUMBER: S122RDIW-S290D1440U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	493.0	492.3	491.5	490.9	490.2	489.5	488.8
115°	573.1	572.8	572.1	571.2	570.2	569.3	568.4
117.5°	649.7	648.9	648.0	647.1	646.1	645.2	644.2
120°	701.9	701.9	701.4	700.5	699.6	698.6	697.7
122.5°	754.2	753.5	752.7	752.1	751.4	750.6	750.0
125°	832.6	831.7	831.1	830.8	830.5	830.2	829.8
127.5°	908.8	907.7	906.6	905.6	904.6	903.6	902.6
130°	961.5	960.8	959.9	958.7	957.4	956.1	954.9
132.5°	1011.5	1010.1	1008.9	1008.0	1006.9	1005.9	1004.8
135°	1087.5	1087.2	1086.6	1085.6	1084.7	1083.7	1082.8
137.5°	1159.3	1159.0	1158.3	1157.1	1155.7	1154.5	1153.2
140°	1207.8	1207.8	1207.2	1205.9	1204.7	1203.3	1202.1
142.5°	1251.8	1252.0	1251.5	1250.3	1249.0	1247.7	1246.4
145°	1318.1	1318.4	1318.0	1316.7	1315.5	1314.2	1313.0
147.5°	1376.7	1377.4	1377.1	1375.9	1374.7	1373.6	1372.3
150°	1413.8	1414.8	1414.8	1413.8	1412.9	1411.9	1411.0
152.5°	1451.0	1452.2	1452.2	1451.0	1449.7	1448.6	1447.4
155°	1498.2	1499.7	1500.1	1499.1	1498.2	1497.2	1496.3
157.5°	1541.9	1544.1	1544.4	1542.8	1541.3	1539.8	1538.3
160°	1567.3	1569.1	1569.5	1568.2	1567.0	1565.8	1564.4
162.5°	1590.8	1592.9	1593.3	1591.8	1590.3	1588.7	1587.1
165°	1620.8	1623.1	1623.3	1621.7	1620.2	1618.6	1617.0
167.5°	1645.6	1647.8	1648.0	1646.4	1644.7	1643.1	1641.4
170°	1659.2	1661.4	1661.5	1659.6	1657.7	1655.9	1654.0
172.5°	1669.4	1671.6	1671.8	1669.9	1668.0	1666.1	1664.2
175°	1680.5	1682.7	1682.9	1680.9	1679.0	1677.2	1675.3
177.5°	1685.0	1686.5	1686.5	1685.0	1683.5	1681.9	1680.4
180°	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9

(END OF REPORT)