

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331818-830

Luminaire Tested: **S122RDIW-S675D1240U830-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331818-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S675D1240U830-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1240 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6448.3 lumens
Efficiency: N/A
Efficacy: 105.0 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 61.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331818-830

CATALOG NUMBER: S122RDIW-S675D1240U830-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331818-830

CATALOG NUMBER: S122RDIW-S675D1240U830-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	60	60	60	44	44	44	37
1	95	91	88	85	86	83	80	77	68	65	64	53	52	51	40	39	38	32
2	87	81	75	70	79	73	69	64	60	56	54	47	45	43	36	35	33	28
3	80	71	64	59	73	65	59	55	53	49	46	43	40	37	32	31	29	25
4	74	63	56	50	67	58	52	47	48	43	40	38	35	32	29	27	26	22
5	68	57	49	44	61	52	45	41	43	38	34	35	31	29	27	25	23	19
6	63	51	44	38	57	47	40	36	39	34	30	32	28	25	25	22	20	17
7	58	46	39	34	53	43	36	31	36	31	27	29	25	23	23	20	18	16
8	54	42	35	30	49	39	32	28	33	28	24	27	23	20	21	19	17	14
9	50	39	32	27	46	36	29	25	30	25	22	25	21	19	20	17	15	13
10	47	36	29	24	43	33	27	23	28	23	20	23	19	17	18	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	22357	22357	22357	22357
5°	24969	22498	19947	22498
10°	27702	22338	17290	22338
15°	29065	22011	13623	22011
20°	25197	21526	11789	21526
25°	16527	20861	10525	20861
30°	11123	20057	9527	20057
35°	9008	19042	8592	19042
40°	8011	17939	7950	17939
45°	7250	16643	7099	16643
50°	6599	15360	6574	15360
55°	6204	13937	6120	13937
60°	5189	12633	5125	12633
65°	4374	11469	4963	11469
70°	4046	10244	4683	10244
75°	3780	8914	4323	8914
80°	3487	7336	3849	7336
85°	3205	5798	3390	5798



TEST NUMBER: P331818-830

CATALOG NUMBER: S122RDIW-S675D1240U830-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	131.3	2.0
10°-20°	365.7	5.7
20°-30°	471.3	7.3
30°-40°	447.9	6.9
40°-50°	383.7	6.0
50°-60°	292.2	4.5
60°-70°	184.7	2.9
70°-80°	92.2	1.4
80°-90°	29.8	0.5
90°-100°	91.8	1.4
100°-110°	285.0	4.4
110°-120°	487.2	7.6
120°-130°	640.7	9.9
130°-140°	719.1	11.2
140°-150°	705.1	10.9
150°-160°	591.4	9.2
160°-170°	392.2	6.1
170°-180°	137.1	2.1
0°-30°	968.3	15.0
0°-40°	1416.2	22.0
0°-60°	2092.1	32.4
0°-90°	2398.8	37.2
90°-120°	864.0	13.4
90°-150°	2928.8	45.4
90°-180°	4050.0	62.8
0°-180°	6448.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1385	1385	1385	1385	1385	
5°	1541	1388	1231	1388	1541	152
15°	1739	1317	815	1317	1739	469
25°	928	1171	591	1171	928	440
35°	457	966	436	966	457	292
45°	318	729	311	729	318	246
55°	220	495	217	495	220	193
65°	114	300	130	300	114	117
75°	61	143	69	143	61	64
85°	17	31	18	31	17	20
90°	42	1	42	1	42	19
95°	76	64	76	64	76	84
105°	271	263	271	263	271	285
115°	489	489	489	489	489	483
125°	714	711	714	711	714	636
135°	931	920	931	920	931	717
145°	1129	1117	1129	1117	1129	705
155°	1287	1277	1287	1277	1287	592
165°	1391	1390	1391	1390	1391	392
175°	1441	1446	1441	1446	1441	137
180°	1448	1448	1448	1448	1448	



TEST NUMBER: P331818-830

CATALOG NUMBER: S122RDIW-S675D1240U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7
2.5°	1440.9	1442.0	1443.2	1440.5	1440.5	1438.1	1433.1	1429.4	1418.5	1417.0	1417.0
5°	1540.6	1539.5	1541.5	1535.3	1526.6	1524.7	1515.5	1503.5	1491.0	1477.1	1474.1
7.5°	1639.6	1638.2	1634.4	1633.3	1626.6	1612.1	1597.4	1581.8	1560.9	1540.7	1530.5
10°	1689.7	1705.6	1695.9	1679.1	1682.5	1659.9	1647.8	1627.2	1609.9	1579.5	1572.8
12.5°	1739.0	1745.2	1742.2	1732.6	1728.2	1712.6	1696.4	1678.4	1646.4	1619.2	1595.5
15°	1738.8	1747.9	1750.3	1747.5	1749.8	1748.9	1740.2	1725.3	1697.4	1667.5	1641.6
17.5°	1610.4	1616.7	1632.6	1643.2	1656.7	1685.2	1699.2	1704.7	1700.5	1683.6	1665.3
20°	1466.5	1455.9	1500.2	1522.8	1542.0	1590.1	1631.4	1647.4	1672.8	1672.4	1667.5
22.5°	1262.4	1265.0	1306.9	1333.8	1390.0	1438.0	1485.3	1545.0	1594.3	1626.9	1646.1
25°	927.7	945.9	987.8	1024.4	1086.8	1176.4	1257.6	1352.0	1441.0	1511.2	1578.1
27.5°	696.6	698.0	731.2	765.0	802.1	875.4	977.8	1090.4	1217.3	1322.0	1442.5
30°	596.6	593.7	607.7	628.4	660.1	716.9	793.8	904.6	1031.0	1188.8	1329.4
32.5°	525.8	525.9	536.5	551.8	578.2	616.4	669.1	759.0	878.6	1033.8	1198.4
35°	457.0	456.6	464.3	475.3	486.4	511.0	547.1	594.2	676.5	821.2	989.7
37.5°	407.8	409.9	413.7	420.6	432.8	446.5	468.2	499.8	558.4	644.0	785.6
40°	380.1	381.1	386.3	392.1	399.4	409.9	427.7	453.2	496.1	564.4	667.8
42.5°	354.7	355.6	359.4	364.8	370.4	381.1	395.8	417.8	452.5	505.9	591.2
45°	317.5	317.5	320.9	323.3	329.6	339.2	351.2	369.5	393.6	433.0	489.7
47.5°	282.7	282.8	285.0	289.2	293.1	300.6	312.5	327.3	344.9	375.4	423.9
50°	262.7	263.2	264.6	268.0	270.4	277.1	286.3	299.3	317.5	341.1	381.5
52.5°	246.6	246.2	248.1	249.5	251.2	256.0	262.8	274.3	290.6	311.1	344.6
55°	220.4	218.4	221.3	223.8	225.2	227.1	230.9	238.2	252.1	269.5	294.5
57.5°	187.7	186.9	188.9	191.1	195.7	200.9	204.1	208.7	215.9	228.4	253.2
60°	160.7	160.7	165.0	166.5	171.7	178.5	185.2	189.1	196.3	204.4	222.7
62.5°	136.9	137.2	139.2	140.7	143.6	151.9	161.4	169.8	176.6	184.5	196.6
65°	114.5	115.5	115.5	116.4	118.4	120.3	124.1	130.8	142.9	153.9	163.1
67.5°	97.2	97.5	97.7	98.7	99.2	101.3	102.8	105.8	108.7	119.1	130.4
70°	85.7	87.1	86.6	87.6	88.0	89.0	91.0	92.4	96.7	99.2	105.8
72.5°	74.8	75.9	75.8	76.4	77.7	77.9	79.4	80.9	83.6	85.7	89.3
75°	60.6	60.1	60.6	61.5	62.0	62.6	62.6	64.5	65.9	67.9	70.2
77.5°	46.8	47.2	47.1	47.2	47.3	48.2	48.1	49.0	50.4	51.4	52.5
80°	37.5	38.0	37.5	38.0	38.5	38.9	38.5	38.9	40.4	41.4	41.4
82.5°	29.0	29.1	29.4	29.5	29.6	29.7	30.4	30.5	31.6	31.4	31.8
85°	17.3	16.9	16.9	16.9	17.3	17.8	17.3	17.3	17.8	17.8	17.8
87.5°	14.5	14.8	14.7	14.7	14.6	14.7	14.8	15.3	15.0	15.5	13.9
90°	41.6	41.3	41.0	40.7	40.4	40.6	41.2	41.7	42.2	42.8	36.8
92.5°	39.6	39.6	39.5	39.4	39.4	39.3	39.2	39.1	38.9	38.8	37.4
95°	75.8	76.3	76.8	77.4	77.9	78.2	78.2	78.2	78.2	78.2	77.7
97.5°	131.3	131.3	131.4	131.4	131.5	131.5	131.5	131.5	131.5	131.5	130.4
100°	167.4	167.7	168.0	168.2	168.5	168.6	168.6	168.6	168.6	168.6	167.9
102.5°	208.5	208.8	209.1	209.3	209.6	209.6	209.4	209.2	209.0	208.8	207.7
105°	271.4	271.4	271.4	271.4	271.4	271.1	270.5	269.9	269.4	268.9	268.3
107.5°	330.5	331.7	333.0	334.2	335.5	336.0	335.7	335.5	335.4	335.1	335.1
110°	376.5	377.2	378.1	378.9	379.7	380.1	380.1	380.1	380.1	380.1	380.1



TEST NUMBER: P331818-830

CATALOG NUMBER: S122RDIW-S675D1240U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	420.4	421.0	421.6	422.2	422.8	423.4	424.0	424.7	425.4	426.0	426.2
115°	488.9	489.7	490.5	491.3	492.1	492.7	492.9	493.2	493.5	493.7	494.3
117.5°	554.1	555.0	555.7	556.6	557.4	558.1	558.7	559.4	560.1	560.7	562.2
120°	600.1	600.9	601.7	602.5	603.3	603.7	603.7	603.7	603.7	603.7	605.9
122.5°	645.1	645.6	646.2	646.9	647.4	648.1	648.8	649.4	650.0	650.6	652.1
125°	713.7	714.0	714.3	714.5	714.8	715.4	716.1	717.0	717.8	718.6	719.4
127.5°	776.3	777.2	778.1	778.9	779.8	780.7	781.7	782.7	783.6	784.6	785.6
130°	821.2	822.4	823.5	824.5	825.7	826.4	827.0	827.6	828.0	828.6	829.2
132.5°	864.3	865.2	866.0	867.0	867.8	868.8	870.0	871.2	872.4	873.5	873.5
135°	931.2	932.1	932.9	933.7	934.5	935.1	935.4	935.7	935.9	936.1	935.7
137.5°	991.9	993.0	994.1	995.1	996.3	996.9	997.1	997.3	997.6	997.8	997.0
140°	1034.0	1035.0	1036.1	1037.2	1038.3	1038.8	1038.8	1038.8	1038.8	1038.8	1037.5
142.5°	1072.0	1073.2	1074.2	1075.3	1076.4	1076.9	1076.7	1076.4	1076.2	1076.0	1075.1
145°	1129.3	1130.4	1131.4	1132.6	1133.6	1134.0	1133.8	1133.5	1133.2	1132.9	1131.3
147.5°	1180.3	1181.4	1182.4	1183.5	1184.5	1184.7	1184.1	1183.5	1182.9	1182.3	1181.2
150°	1213.6	1214.4	1215.2	1216.1	1216.8	1216.8	1216.1	1215.2	1214.4	1213.6	1212.5
152.5°	1244.9	1245.9	1247.0	1247.9	1249.0	1249.0	1247.9	1247.0	1245.9	1244.9	1243.6
155°	1286.9	1287.7	1288.5	1289.4	1290.2	1289.9	1288.5	1287.2	1285.8	1284.5	1283.6
157.5°	1323.0	1324.4	1325.7	1327.0	1328.3	1328.0	1326.2	1324.4	1322.5	1320.7	1320.1
160°	1345.6	1346.7	1347.7	1348.9	1349.9	1349.6	1348.0	1346.4	1344.7	1343.1	1342.8
162.5°	1365.2	1366.4	1367.7	1369.0	1370.4	1370.1	1368.2	1366.4	1364.5	1362.7	1362.4
165°	1390.8	1392.1	1393.5	1394.9	1396.2	1396.0	1394.0	1392.1	1390.3	1388.4	1388.4
167.5°	1411.8	1413.2	1414.7	1416.1	1417.5	1417.2	1415.3	1413.4	1411.6	1409.6	1409.7
170°	1422.6	1424.2	1425.9	1427.5	1429.1	1429.0	1427.0	1425.1	1423.2	1421.4	1421.6
172.5°	1431.3	1433.0	1434.6	1436.2	1437.8	1437.8	1435.9	1434.0	1432.1	1430.1	1430.4
175°	1440.9	1442.6	1444.2	1445.8	1447.5	1447.3	1445.4	1443.5	1441.6	1439.6	1440.2
177.5°	1445.3	1446.6	1447.9	1449.3	1450.5	1450.5	1449.3	1447.9	1446.6	1445.3	1445.8
180°	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2



TEST NUMBER: P331818-830

CATALOG NUMBER: S122RDIW-S675D1240U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7
2.5°	1417.8	1414.7	1412.0	1405.0	1401.7	1393.9	1392.8	1392.4	1382.3	1372.7	1370.1
5°	1466.5	1458.8	1447.2	1433.7	1419.8	1405.3	1395.7	1388.1	1368.8	1350.5	1339.9
7.5°	1515.5	1499.0	1479.0	1453.6	1432.3	1408.4	1390.7	1374.9	1347.6	1321.4	1303.7
10°	1552.1	1525.1	1498.7	1463.6	1436.2	1409.2	1384.2	1362.5	1331.7	1297.1	1272.5
12.5°	1574.8	1545.2	1508.7	1474.3	1438.9	1404.6	1371.1	1343.3	1307.1	1271.3	1242.2
15°	1605.5	1573.8	1529.5	1480.5	1434.7	1390.0	1351.5	1316.8	1269.7	1226.9	1191.3
17.5°	1630.6	1587.0	1539.4	1482.6	1429.7	1372.8	1323.2	1279.0	1226.5	1174.9	1132.9
20°	1638.7	1595.4	1540.6	1483.8	1421.3	1354.3	1301.0	1252.8	1196.6	1140.3	1092.1
22.5°	1633.7	1600.1	1539.0	1471.1	1407.0	1337.0	1276.7	1220.9	1158.5	1101.0	1045.2
25°	1599.8	1588.2	1530.5	1456.3	1383.3	1301.9	1232.2	1171.0	1099.9	1038.3	977.6
27.5°	1520.5	1545.5	1509.7	1430.8	1349.4	1262.3	1183.8	1114.3	1040.4	971.1	910.7
30°	1444.4	1501.6	1486.2	1413.1	1322.1	1236.5	1148.5	1075.8	996.9	925.7	866.0
32.5°	1340.0	1434.6	1449.6	1388.5	1294.4	1200.3	1108.1	1035.8	953.4	878.4	820.2
35°	1173.9	1315.4	1380.4	1341.3	1247.1	1145.6	1050.3	966.1	883.4	809.3	751.5
37.5°	975.8	1168.5	1276.7	1279.5	1192.9	1087.3	983.6	900.0	815.3	742.5	680.1
40°	847.3	1056.0	1197.0	1228.3	1155.2	1041.1	936.2	851.1	768.4	697.1	625.5
42.5°	731.8	939.8	1113.1	1167.5	1109.4	996.1	890.9	801.8	721.4	654.0	580.8
45°	591.8	773.6	964.7	1061.9	1029.6	924.7	813.6	728.9	653.4	595.1	524.9
47.5°	499.2	627.4	812.2	943.7	943.1	847.3	738.0	657.0	586.9	532.3	475.4
50°	446.5	558.1	714.4	863.7	876.1	795.8	691.8	611.5	546.1	488.8	443.1
52.5°	399.2	491.2	631.7	774.7	810.3	740.7	639.9	565.7	502.2	449.6	410.4
55°	337.2	408.5	515.3	649.0	702.9	653.8	564.4	495.1	443.6	399.4	365.6
57.5°	285.3	338.7	424.4	532.2	594.8	564.0	490.1	433.9	389.8	349.8	323.2
60°	252.6	296.3	369.0	459.0	528.3	506.6	443.6	391.2	353.6	319.0	294.0
62.5°	221.8	259.4	321.7	394.7	458.3	449.3	397.8	353.8	320.9	289.4	268.2
65°	178.5	205.9	254.5	311.8	362.8	367.1	330.1	300.2	270.9	245.8	227.1
67.5°	142.1	160.0	194.3	242.5	280.7	294.4	271.7	248.9	225.6	206.3	190.0
70°	119.8	134.2	159.3	198.2	233.4	247.8	234.8	217.0	196.8	180.9	166.9
72.5°	97.1	111.1	129.6	158.2	188.3	203.9	199.3	186.6	170.2	157.0	143.8
75°	73.1	77.5	90.0	109.2	132.8	146.3	149.7	142.9	129.9	119.8	112.1
77.5°	54.1	56.6	62.7	72.8	88.1	100.2	105.1	104.3	95.4	89.4	82.3
80°	43.3	44.8	47.6	51.9	63.5	75.5	78.9	78.9	72.7	70.2	63.1
82.5°	32.9	33.9	35.7	38.1	43.5	54.0	57.8	58.5	54.6	51.4	45.7
85°	18.8	18.3	19.2	20.6	21.7	24.5	30.3	31.3	30.3	26.5	25.0
87.5°	12.7	11.9	10.7	9.4	9.1	8.9	10.2	11.4	10.6	10.0	9.9
90°	30.8	24.9	18.9	14.2	11.0	7.7	4.5	1.2	4.5	7.7	11.0
92.5°	36.0	34.6	33.2	31.3	28.9	26.6	24.1	21.8	24.1	26.6	28.9
95°	77.1	76.6	76.1	74.5	71.7	69.0	66.3	63.5	66.3	69.0	71.7
97.5°	129.4	128.4	127.3	125.6	123.3	120.9	118.5	116.1	118.5	120.9	123.3
100°	167.0	166.2	165.4	163.9	161.7	159.6	157.4	155.2	157.4	159.6	161.7
102.5°	206.7	205.7	204.6	203.2	201.5	199.7	198.0	196.2	198.0	199.7	201.5
105°	267.8	267.2	266.7	266.0	265.2	264.4	263.5	262.8	263.5	264.4	265.2
107.5°	335.1	335.1	335.1	334.5	333.3	332.2	330.9	329.7	330.9	332.2	333.3
110°	380.1	380.1	380.1	379.3	377.7	376.0	374.4	372.8	374.4	376.0	377.7



TEST NUMBER: P331818-830

CATALOG NUMBER: S122RDIW-S675D1240U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	426.5	426.7	426.9	426.2	424.6	422.9	421.3	419.7	421.3	422.9	424.6
115°	494.8	495.4	495.9	495.4	493.7	492.1	490.5	488.9	490.5	492.1	493.7
117.5°	563.7	565.2	566.8	566.5	564.3	562.1	560.0	557.8	560.0	562.1	564.3
120°	608.1	610.3	612.5	612.5	610.3	608.1	605.9	603.7	605.9	608.1	610.3
122.5°	653.7	655.3	656.8	656.2	653.6	651.0	648.4	645.7	648.4	651.0	653.6
125°	720.3	721.0	721.9	721.0	718.6	716.1	713.7	711.2	713.7	716.1	718.6
127.5°	786.6	787.6	788.5	787.5	784.4	781.3	778.2	775.1	778.2	781.3	784.4
130°	829.7	830.3	830.8	829.2	825.8	822.3	818.7	815.2	818.7	822.3	825.8
132.5°	873.4	873.3	873.2	871.7	868.7	865.9	863.0	860.2	863.0	865.9	868.7
135°	935.1	934.5	934.0	932.3	929.3	926.2	923.2	920.3	923.2	926.2	929.3
137.5°	996.4	995.6	994.9	993.3	990.9	988.4	986.0	983.5	986.0	988.4	990.9
140°	1036.1	1034.7	1033.4	1031.5	1029.1	1026.6	1024.2	1021.7	1024.2	1026.6	1029.1
142.5°	1074.1	1073.2	1072.2	1070.6	1068.2	1065.7	1063.3	1060.8	1063.3	1065.7	1068.2
145°	1129.6	1128.0	1126.4	1124.6	1122.8	1120.9	1119.0	1117.0	1119.0	1120.9	1122.8
147.5°	1180.2	1179.0	1178.0	1176.3	1174.0	1171.7	1169.4	1167.2	1169.4	1171.7	1174.0
150°	1211.4	1210.3	1209.3	1207.9	1206.3	1204.7	1203.0	1201.4	1203.0	1204.7	1206.3
152.5°	1242.3	1241.0	1239.6	1238.2	1236.5	1234.9	1233.3	1231.7	1233.3	1234.9	1236.5
155°	1282.8	1282.0	1281.2	1280.4	1279.6	1278.7	1278.0	1277.1	1278.0	1278.7	1279.6
157.5°	1319.7	1319.2	1318.7	1318.1	1317.7	1317.1	1316.5	1316.0	1316.5	1317.1	1317.7
160°	1342.6	1342.3	1342.1	1341.6	1341.1	1340.6	1340.0	1339.4	1340.0	1340.6	1341.1
162.5°	1362.2	1361.9	1361.6	1361.4	1361.3	1361.2	1361.1	1360.9	1361.1	1361.2	1361.3
165°	1388.4	1388.4	1388.4	1388.5	1388.7	1389.0	1389.3	1389.6	1389.3	1389.0	1388.7
167.5°	1409.8	1409.8	1409.9	1410.2	1411.1	1411.9	1412.7	1413.5	1412.7	1411.9	1411.1
170°	1421.9	1422.2	1422.5	1423.0	1423.8	1424.7	1425.4	1426.3	1425.4	1424.7	1423.8
172.5°	1430.7	1431.0	1431.3	1431.8	1432.6	1433.4	1434.3	1435.0	1434.3	1433.4	1432.6
175°	1440.8	1441.3	1441.9	1442.6	1443.3	1444.2	1445.0	1445.8	1445.0	1444.2	1443.3
177.5°	1446.1	1446.6	1447.1	1447.6	1448.2	1448.9	1449.5	1450.2	1449.5	1448.9	1448.2
180°	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2



TEST NUMBER: P331818-830

CATALOG NUMBER: S122RDIW-S675D1240U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7
2.5°	1365.1	1362.4	1357.4	1349.6	1345.0	1336.9	1331.5	1334.6	1335.4	1334.6	1333.9
5°	1328.4	1318.2	1304.3	1290.8	1278.4	1264.9	1257.2	1253.8	1247.1	1243.2	1241.3
7.5°	1284.0	1266.6	1246.9	1223.4	1203.4	1182.6	1172.0	1166.6	1152.8	1145.4	1138.8
10°	1250.9	1223.5	1203.8	1173.0	1154.2	1126.8	1108.1	1108.5	1089.8	1079.1	1071.5
12.5°	1214.4	1184.2	1151.4	1123.7	1097.6	1075.6	1053.0	1043.9	1023.9	1013.7	993.0
15°	1153.8	1118.6	1084.0	1046.4	1020.0	985.8	953.1	913.1	880.9	853.0	845.4
17.5°	1087.5	1044.1	1009.3	965.3	919.9	862.4	824.5	801.3	781.9	767.2	756.2
20°	1042.1	997.9	960.8	894.4	833.3	794.4	766.5	748.7	728.4	712.6	703.9
22.5°	994.4	948.2	897.7	823.6	776.0	744.7	719.8	699.4	685.7	673.3	665.4
25°	926.6	876.1	792.9	741.9	703.4	670.7	653.4	640.8	626.4	609.5	601.9
27.5°	855.1	774.7	714.9	677.0	640.3	619.0	603.4	584.8	571.8	564.3	556.3
30°	801.5	721.2	674.6	633.2	607.2	583.6	565.3	554.8	542.2	529.2	524.0
32.5°	741.9	677.7	633.0	598.5	572.1	552.0	537.6	520.5	511.4	503.4	492.4
35°	667.8	619.3	578.3	550.4	525.4	509.1	492.2	482.1	465.7	459.0	454.7
37.5°	605.0	562.9	532.4	502.9	483.1	465.1	454.8	438.7	431.6	422.3	413.1
40°	569.7	528.3	498.9	474.9	452.7	439.2	426.3	413.3	402.7	398.4	387.3
42.5°	533.5	499.8	470.4	444.0	429.2	415.0	398.6	389.1	378.1	371.1	364.2
45°	483.5	453.7	428.7	407.0	390.7	375.8	365.1	349.3	343.1	329.0	323.3
47.5°	439.7	411.9	388.0	367.5	351.5	341.8	326.3	313.9	303.9	295.3	287.9
50°	408.5	385.4	362.3	344.0	329.6	315.7	299.7	293.5	278.1	273.7	269.5
52.5°	380.0	358.1	336.9	319.0	304.5	291.0	277.0	268.8	258.4	254.1	251.0
55°	340.2	319.0	298.8	282.9	268.4	254.5	245.8	235.7	230.9	227.5	223.8
57.5°	300.1	281.1	265.6	249.5	235.0	223.9	213.9	207.8	202.8	198.4	193.8
60°	274.8	256.5	242.5	227.5	212.6	203.5	195.9	188.6	182.9	176.1	174.2
62.5°	247.8	231.8	219.0	204.4	191.5	183.1	175.8	169.0	162.0	152.2	149.5
65°	210.8	198.2	184.7	172.8	161.2	153.0	142.4	134.7	131.9	130.8	130.4
67.5°	177.3	165.4	153.8	141.6	131.0	123.5	118.1	116.9	114.9	114.3	113.0
70°	155.0	143.8	132.3	120.7	110.7	109.2	107.3	105.4	102.9	102.0	101.0
72.5°	134.9	123.5	111.9	102.6	98.3	96.5	94.6	92.7	91.0	90.1	89.4
75°	103.4	92.8	85.2	81.8	79.4	77.9	75.0	73.6	72.7	71.2	70.7
77.5°	74.5	68.5	64.9	62.9	60.3	58.8	57.1	55.7	54.7	54.4	53.6
80°	56.7	53.9	51.5	48.6	47.6	45.7	45.2	43.8	44.3	42.8	42.8
82.5°	44.1	40.4	38.4	37.0	36.1	34.6	34.0	33.4	33.5	32.4	32.4
85°	22.6	21.7	20.6	19.7	19.7	18.3	18.8	18.3	18.3	17.3	16.9
87.5°	10.2	10.7	11.1	12.3	13.5	14.3	14.2	13.8	13.6	13.5	13.1
90°	14.2	18.9	24.9	30.8	36.8	42.8	42.2	41.7	41.2	40.6	40.4
92.5°	31.3	33.2	34.6	36.0	37.4	38.8	38.9	39.1	39.2	39.3	39.4
95°	74.5	76.1	76.6	77.1	77.7	78.2	78.2	78.2	78.2	78.2	77.9
97.5°	125.6	127.3	128.4	129.4	130.4	131.5	131.5	131.5	131.5	131.5	131.5
100°	163.9	165.4	166.2	167.0	167.9	168.6	168.6	168.6	168.6	168.6	168.5
102.5°	203.2	204.6	205.7	206.7	207.7	208.8	209.0	209.2	209.4	209.6	209.6
105°	266.0	266.7	267.2	267.8	268.3	268.9	269.4	269.9	270.5	271.1	271.4
107.5°	334.5	335.1	335.1	335.1	335.1	335.1	335.4	335.5	335.7	336.0	335.5
110°	379.3	380.1	380.1	380.1	380.1	380.1	380.1	380.1	380.1	380.1	379.7



TEST NUMBER: P331818-830

CATALOG NUMBER: S122RDIW-S675D1240U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	426.2	426.9	426.7	426.5	426.2	426.0	425.4	424.7	424.0	423.4	422.8
115°	495.4	495.9	495.4	494.8	494.3	493.7	493.5	493.2	492.9	492.7	492.1
117.5°	566.5	566.8	565.2	563.7	562.2	560.7	560.1	559.4	558.7	558.1	557.4
120°	612.5	612.5	610.3	608.1	605.9	603.7	603.7	603.7	603.7	603.7	603.3
122.5°	656.2	656.8	655.3	653.7	652.1	650.6	650.0	649.4	648.8	648.1	647.4
125°	721.0	721.9	721.0	720.3	719.4	718.6	717.8	717.0	716.1	715.4	714.8
127.5°	787.5	788.5	787.6	786.6	785.6	784.6	783.6	782.7	781.7	780.7	779.8
130°	829.2	830.8	830.3	829.7	829.2	828.6	828.0	827.6	827.0	826.4	825.7
132.5°	871.7	873.2	873.3	873.4	873.5	873.5	872.4	871.2	870.0	868.8	867.8
135°	932.3	934.0	934.5	935.1	935.7	936.1	935.9	935.7	935.4	935.1	934.5
137.5°	993.3	994.9	995.6	996.4	997.0	997.8	997.6	997.3	997.1	996.9	996.3
140°	1031.5	1033.4	1034.7	1036.1	1037.5	1038.8	1038.8	1038.8	1038.8	1038.8	1038.3
142.5°	1070.6	1072.2	1073.2	1074.1	1075.1	1076.0	1076.2	1076.4	1076.7	1076.9	1076.4
145°	1124.6	1126.4	1128.0	1129.6	1131.3	1132.9	1133.2	1133.5	1133.8	1134.0	1133.6
147.5°	1176.3	1178.0	1179.0	1180.2	1181.2	1182.3	1182.9	1183.5	1184.1	1184.7	1184.5
150°	1207.9	1209.3	1210.3	1211.4	1212.5	1213.6	1214.4	1215.2	1216.1	1216.8	1216.8
152.5°	1238.2	1239.6	1241.0	1242.3	1243.6	1244.9	1245.9	1247.0	1247.9	1249.0	1249.0
155°	1280.4	1281.2	1282.0	1282.8	1283.6	1284.5	1285.8	1287.2	1288.5	1289.9	1290.2
157.5°	1318.1	1318.7	1319.2	1319.7	1320.1	1320.7	1322.5	1324.4	1326.2	1328.0	1328.3
160°	1341.6	1342.1	1342.3	1342.6	1342.8	1343.1	1344.7	1346.4	1348.0	1349.6	1349.9
162.5°	1361.4	1361.6	1361.9	1362.2	1362.4	1362.7	1364.5	1366.4	1368.2	1370.1	1370.4
165°	1388.5	1388.4	1388.4	1388.4	1388.4	1388.4	1390.3	1392.1	1394.0	1396.0	1396.2
167.5°	1410.2	1409.9	1409.8	1409.8	1409.7	1409.6	1411.6	1413.4	1415.3	1417.2	1417.5
170°	1423.0	1422.5	1422.2	1421.9	1421.6	1421.4	1423.2	1425.1	1427.0	1429.0	1429.1
172.5°	1431.8	1431.3	1431.0	1430.7	1430.4	1430.1	1432.1	1434.0	1435.9	1437.8	1437.8
175°	1442.6	1441.9	1441.3	1440.8	1440.2	1439.6	1441.6	1443.5	1445.4	1447.3	1447.5
177.5°	1447.6	1447.1	1446.6	1446.1	1445.8	1445.3	1446.6	1447.9	1449.3	1450.5	1450.5
180°	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2



TEST NUMBER: P331818-830

CATALOG NUMBER: S122RDIW-S675D1240U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7
2.5°	1329.6	1330.4	1329.3	1330.0	1329.3	1330.4	1329.6	1333.9	1334.6	1335.4	1334.6
5°	1238.9	1233.1	1232.2	1230.7	1232.2	1233.1	1238.9	1241.3	1243.2	1247.1	1253.8
7.5°	1130.6	1129.6	1127.3	1123.9	1127.3	1129.6	1130.6	1138.8	1145.4	1152.8	1166.6
10°	1060.8	1058.5	1058.0	1054.6	1058.0	1058.5	1060.8	1071.5	1079.1	1089.8	1108.5
12.5°	979.3	963.7	962.1	953.8	962.1	963.7	979.3	993.0	1013.7	1023.9	1043.9
15°	833.8	830.9	821.2	815.0	821.2	830.9	833.8	845.4	853.0	880.9	913.1
17.5°	750.6	741.2	738.2	736.9	738.2	741.2	750.6	756.2	767.2	781.9	801.3
20°	697.1	688.5	687.0	686.1	687.0	688.5	697.1	703.9	712.6	728.4	748.7
22.5°	660.2	651.1	647.4	644.5	647.4	651.1	660.2	665.4	673.3	685.7	699.4
25°	597.1	593.7	591.8	590.8	591.8	593.7	597.1	601.9	609.5	626.4	640.8
27.5°	547.7	540.3	538.9	536.4	538.9	540.3	547.7	556.3	564.3	571.8	584.8
30°	519.6	517.2	513.9	511.0	513.9	517.2	519.6	524.0	529.2	542.2	554.8
32.5°	486.5	484.5	481.5	480.1	481.5	484.5	486.5	492.4	503.4	511.4	520.5
35°	449.9	443.1	440.3	435.9	440.3	443.1	449.9	454.7	459.0	465.7	482.1
37.5°	411.0	407.6	403.5	404.9	403.5	407.6	411.0	413.1	422.3	431.6	438.7
40°	381.1	378.6	377.7	377.2	377.7	378.6	381.1	387.3	398.4	402.7	413.3
42.5°	357.2	350.5	348.1	348.0	348.1	350.5	357.2	364.2	371.1	378.1	389.1
45°	320.9	314.6	310.3	310.9	310.3	314.6	320.9	323.3	329.0	343.1	349.3
47.5°	283.8	283.6	280.9	281.7	280.9	283.6	283.8	287.9	295.3	303.9	313.9
50°	266.1	263.2	261.3	261.7	261.3	263.2	266.1	269.5	273.7	278.1	293.5
52.5°	249.1	246.7	245.1	247.1	245.1	246.7	249.1	251.0	254.1	258.4	268.8
55°	221.3	218.4	217.9	217.4	217.9	218.4	221.3	223.8	227.5	230.9	235.7
57.5°	190.2	188.3	185.4	184.2	185.4	188.3	190.2	193.8	198.4	202.8	207.8
60°	167.9	164.1	159.3	158.7	159.3	164.1	167.9	174.2	176.1	182.9	188.6
62.5°	147.5	146.8	145.8	145.7	145.8	146.8	147.5	149.5	152.2	162.0	169.0
65°	129.4	128.9	129.4	129.9	129.4	128.9	129.4	130.4	130.8	131.9	134.7
67.5°	112.8	111.9	111.0	111.4	111.0	111.9	112.8	113.0	114.3	114.9	116.9
70°	100.1	99.6	99.2	99.2	99.2	99.6	100.1	101.0	102.0	102.9	105.4
72.5°	87.8	87.7	87.2	86.8	87.2	87.7	87.8	89.4	90.1	91.0	92.7
75°	70.2	69.3	69.3	69.3	69.3	69.3	70.2	70.7	71.2	72.7	73.6
77.5°	53.5	53.1	52.5	52.1	52.5	53.1	53.5	53.6	54.4	54.7	55.7
80°	42.3	41.8	41.4	41.4	41.4	41.8	42.3	42.8	42.8	44.3	43.8
82.5°	32.3	31.9	31.8	31.4	31.8	31.9	32.3	32.4	32.4	33.5	33.4
85°	17.3	17.8	17.3	18.3	17.3	17.8	17.3	16.9	17.3	18.3	18.3
87.5°	13.2	12.8	13.3	12.9	13.3	12.8	13.2	13.1	13.5	13.6	13.8
90°	40.7	41.0	41.3	41.6	41.3	41.0	40.7	40.4	40.6	41.2	41.7
92.5°	39.4	39.5	39.6	39.6	39.6	39.5	39.4	39.4	39.3	39.2	39.1
95°	77.4	76.8	76.3	75.8	76.3	76.8	77.4	77.9	78.2	78.2	78.2
97.5°	131.4	131.4	131.3	131.3	131.3	131.4	131.4	131.5	131.5	131.5	131.5
100°	168.2	168.0	167.7	167.4	167.7	168.0	168.2	168.5	168.6	168.6	168.6
102.5°	209.3	209.1	208.8	208.5	208.8	209.1	209.3	209.6	209.6	209.4	209.2
105°	271.4	271.4	271.4	271.4	271.4	271.4	271.4	271.4	271.1	270.5	269.9
107.5°	334.2	333.0	331.7	330.5	331.7	333.0	334.2	335.5	336.0	335.7	335.5
110°	378.9	378.1	377.2	376.5	377.2	378.1	378.9	379.7	380.1	380.1	380.1



TEST NUMBER: P331818-830

CATALOG NUMBER: S122RDIW-S675D1240U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	422.2	421.6	421.0	420.4	421.0	421.6	422.2	422.8	423.4	424.0	424.7
115°	491.3	490.5	489.7	488.9	489.7	490.5	491.3	492.1	492.7	492.9	493.2
117.5°	556.6	555.7	555.0	554.1	555.0	555.7	556.6	557.4	558.1	558.7	559.4
120°	602.5	601.7	600.9	600.1	600.9	601.7	602.5	603.3	603.7	603.7	603.7
122.5°	646.9	646.2	645.6	645.1	645.6	646.2	646.9	647.4	648.1	648.8	649.4
125°	714.5	714.3	714.0	713.7	714.0	714.3	714.5	714.8	715.4	716.1	717.0
127.5°	778.9	778.1	777.2	776.3	777.2	778.1	778.9	779.8	780.7	781.7	782.7
130°	824.5	823.5	822.4	821.2	822.4	823.5	824.5	825.7	826.4	827.0	827.6
132.5°	867.0	866.0	865.2	864.3	865.2	866.0	867.0	867.8	868.8	870.0	871.2
135°	933.7	932.9	932.1	931.2	932.1	932.9	933.7	934.5	935.1	935.4	935.7
137.5°	995.1	994.1	993.0	991.9	993.0	994.1	995.1	996.3	996.9	997.1	997.3
140°	1037.2	1036.1	1035.0	1034.0	1035.0	1036.1	1037.2	1038.3	1038.8	1038.8	1038.8
142.5°	1075.3	1074.2	1073.2	1072.0	1073.2	1074.2	1075.3	1076.4	1076.9	1076.7	1076.4
145°	1132.6	1131.4	1130.4	1129.3	1130.4	1131.4	1132.6	1133.6	1134.0	1133.8	1133.5
147.5°	1183.5	1182.4	1181.4	1180.3	1181.4	1182.4	1183.5	1184.5	1184.7	1184.1	1183.5
150°	1216.1	1215.2	1214.4	1213.6	1214.4	1215.2	1216.1	1216.8	1216.8	1216.1	1215.2
152.5°	1247.9	1247.0	1245.9	1244.9	1245.9	1247.0	1247.9	1249.0	1249.0	1247.9	1247.0
155°	1289.4	1288.5	1287.7	1286.9	1287.7	1288.5	1289.4	1290.2	1289.9	1288.5	1287.2
157.5°	1327.0	1325.7	1324.4	1323.0	1324.4	1325.7	1327.0	1328.3	1328.0	1326.2	1324.4
160°	1348.9	1347.7	1346.7	1345.6	1346.7	1347.7	1348.9	1349.9	1349.6	1348.0	1346.4
162.5°	1369.0	1367.7	1366.4	1365.2	1366.4	1367.7	1369.0	1370.4	1370.1	1368.2	1366.4
165°	1394.9	1393.5	1392.1	1390.8	1392.1	1393.5	1394.9	1396.2	1396.0	1394.0	1392.1
167.5°	1416.1	1414.7	1413.2	1411.8	1413.2	1414.7	1416.1	1417.5	1417.2	1415.3	1413.4
170°	1427.5	1425.9	1424.2	1422.6	1424.2	1425.9	1427.5	1429.1	1429.0	1427.0	1425.1
172.5°	1436.2	1434.6	1433.0	1431.3	1433.0	1434.6	1436.2	1437.8	1437.8	1435.9	1434.0
175°	1445.8	1444.2	1442.6	1440.9	1442.6	1444.2	1445.8	1447.5	1447.3	1445.4	1443.5
177.5°	1449.3	1447.9	1446.6	1445.3	1446.6	1447.9	1449.3	1450.5	1450.5	1449.3	1447.9
180°	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2



TEST NUMBER: P331818-830

CATALOG NUMBER: S122RDIW-S675D1240U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7
2.5°	1331.5	1336.9	1345.0	1349.6	1357.4	1362.4	1365.1	1370.1	1372.7	1382.3	1392.4
5°	1257.2	1264.9	1278.4	1290.8	1304.3	1318.2	1328.4	1339.9	1350.5	1368.8	1388.1
7.5°	1172.0	1182.6	1203.4	1223.4	1246.9	1266.6	1284.0	1303.7	1321.4	1347.6	1374.9
10°	1108.1	1126.8	1154.2	1173.0	1203.8	1223.5	1250.9	1272.5	1297.1	1331.7	1362.5
12.5°	1053.0	1075.6	1097.6	1123.7	1151.4	1184.2	1214.4	1242.2	1271.3	1307.1	1343.3
15°	953.1	985.8	1020.0	1046.4	1084.0	1118.6	1153.8	1191.3	1226.9	1269.7	1316.8
17.5°	824.5	862.4	919.9	965.3	1009.3	1044.1	1087.5	1132.9	1174.9	1226.5	1279.0
20°	766.5	794.4	833.3	894.4	960.8	997.9	1042.1	1092.1	1140.3	1196.6	1252.8
22.5°	719.8	744.7	776.0	823.6	897.7	948.2	994.4	1045.2	1101.0	1158.5	1220.9
25°	653.4	670.7	703.4	741.9	792.9	876.1	926.6	977.6	1038.3	1099.9	1171.0
27.5°	603.4	619.0	640.3	677.0	714.9	774.7	855.1	910.7	971.1	1040.4	1114.3
30°	565.3	583.6	607.2	633.2	674.6	721.2	801.5	866.0	925.7	996.9	1075.8
32.5°	537.6	552.0	572.1	598.5	633.0	677.7	741.9	820.2	878.4	953.4	1035.8
35°	492.2	509.1	525.4	550.4	578.3	619.3	667.8	751.5	809.3	883.4	966.1
37.5°	454.8	465.1	483.1	502.9	532.4	562.9	605.0	680.1	742.5	815.3	900.0
40°	426.3	439.2	452.7	474.9	498.9	528.3	569.7	625.5	697.1	768.4	851.1
42.5°	398.6	415.0	429.2	444.0	470.4	499.8	533.5	580.8	654.0	721.4	801.8
45°	365.1	375.8	390.7	407.0	428.7	453.7	483.5	524.9	595.1	653.4	728.9
47.5°	326.3	341.8	351.5	367.5	388.0	411.9	439.7	475.4	532.3	586.9	657.0
50°	299.7	315.7	329.6	344.0	362.3	385.4	408.5	443.1	488.8	546.1	611.5
52.5°	277.0	291.0	304.5	319.0	336.9	358.1	380.0	410.4	449.6	502.2	565.7
55°	245.8	254.5	268.4	282.9	298.8	319.0	340.2	365.6	399.4	443.6	495.1
57.5°	213.9	223.9	235.0	249.5	265.6	281.1	300.1	323.2	349.8	389.8	433.9
60°	195.9	203.5	212.6	227.5	242.5	256.5	274.8	294.0	319.0	353.6	391.2
62.5°	175.8	183.1	191.5	204.4	219.0	231.8	247.8	268.2	289.4	320.9	353.8
65°	142.4	153.0	161.2	172.8	184.7	198.2	210.8	227.1	245.8	270.9	300.2
67.5°	118.1	123.5	131.0	141.6	153.8	165.4	177.3	190.0	206.3	225.6	248.9
70°	107.3	109.2	110.7	120.7	132.3	143.8	155.0	166.9	180.9	196.8	217.0
72.5°	94.6	96.5	98.3	102.6	111.9	123.5	134.9	143.8	157.0	170.2	186.6
75°	75.0	77.9	79.4	81.8	85.2	92.8	103.4	112.1	119.8	129.9	142.9
77.5°	57.1	58.8	60.3	62.9	64.9	68.5	74.5	82.3	89.4	95.4	104.3
80°	45.2	45.7	47.6	48.6	51.5	53.9	56.7	63.1	70.2	72.7	78.9
82.5°	34.0	34.6	36.1	37.0	38.4	40.4	44.1	45.7	51.4	54.6	58.5
85°	18.8	18.3	19.7	19.7	20.6	21.7	22.6	25.0	26.5	30.3	31.3
87.5°	14.2	14.3	13.5	12.3	11.1	10.7	10.2	9.9	10.0	10.6	11.4
90°	42.2	42.8	36.8	30.8	24.9	18.9	14.2	11.0	7.7	4.5	1.2
92.5°	38.9	38.8	37.4	36.0	34.6	33.2	31.3	28.9	26.6	24.1	21.8
95°	78.2	78.2	77.7	77.1	76.6	76.1	74.5	71.7	69.0	66.3	63.5
97.5°	131.5	131.5	130.4	129.4	128.4	127.3	125.6	123.3	120.9	118.5	116.1
100°	168.6	168.6	167.9	167.0	166.2	165.4	163.9	161.7	159.6	157.4	155.2
102.5°	209.0	208.8	207.7	206.7	205.7	204.6	203.2	201.5	199.7	198.0	196.2
105°	269.4	268.9	268.3	267.8	267.2	266.7	266.0	265.2	264.4	263.5	262.8
107.5°	335.4	335.1	335.1	335.1	335.1	335.1	334.5	333.3	332.2	330.9	329.7
110°	380.1	380.1	380.1	380.1	380.1	380.1	379.3	377.7	376.0	374.4	372.8



TEST NUMBER: P331818-830

CATALOG NUMBER: S122RDIW-S675D1240U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	425.4	426.0	426.2	426.5	426.7	426.9	426.2	424.6	422.9	421.3	419.7
115°	493.5	493.7	494.3	494.8	495.4	495.9	495.4	493.7	492.1	490.5	488.9
117.5°	560.1	560.7	562.2	563.7	565.2	566.8	566.5	564.3	562.1	560.0	557.8
120°	603.7	603.7	605.9	608.1	610.3	612.5	612.5	610.3	608.1	605.9	603.7
122.5°	650.0	650.6	652.1	653.7	655.3	656.8	656.2	653.6	651.0	648.4	645.7
125°	717.8	718.6	719.4	720.3	721.0	721.9	721.0	718.6	716.1	713.7	711.2
127.5°	783.6	784.6	785.6	786.6	787.6	788.5	787.5	784.4	781.3	778.2	775.1
130°	828.0	828.6	829.2	829.7	830.3	830.8	829.2	825.8	822.3	818.7	815.2
132.5°	872.4	873.5	873.5	873.4	873.3	873.2	871.7	868.7	865.9	863.0	860.2
135°	935.9	936.1	935.7	935.1	934.5	934.0	932.3	929.3	926.2	923.2	920.3
137.5°	997.6	997.8	997.0	996.4	995.6	994.9	993.3	990.9	988.4	986.0	983.5
140°	1038.8	1038.8	1037.5	1036.1	1034.7	1033.4	1031.5	1029.1	1026.6	1024.2	1021.7
142.5°	1076.2	1076.0	1075.1	1074.1	1073.2	1072.2	1070.6	1068.2	1065.7	1063.3	1060.8
145°	1133.2	1132.9	1131.3	1129.6	1128.0	1126.4	1124.6	1122.8	1120.9	1119.0	1117.0
147.5°	1182.9	1182.3	1181.2	1180.2	1179.0	1178.0	1176.3	1174.0	1171.7	1169.4	1167.2
150°	1214.4	1213.6	1212.5	1211.4	1210.3	1209.3	1207.9	1206.3	1204.7	1203.0	1201.4
152.5°	1245.9	1244.9	1243.6	1242.3	1241.0	1239.6	1238.2	1236.5	1234.9	1233.3	1231.7
155°	1285.8	1284.5	1283.6	1282.8	1282.0	1281.2	1280.4	1279.6	1278.7	1278.0	1277.1
157.5°	1322.5	1320.7	1320.1	1319.7	1319.2	1318.7	1318.1	1317.7	1317.1	1316.5	1316.0
160°	1344.7	1343.1	1342.8	1342.6	1342.3	1342.1	1341.6	1341.1	1340.6	1340.0	1339.4
162.5°	1364.5	1362.7	1362.4	1362.2	1361.9	1361.6	1361.4	1361.3	1361.2	1361.1	1360.9
165°	1390.3	1388.4	1388.4	1388.4	1388.4	1388.4	1388.5	1388.7	1389.0	1389.3	1389.6
167.5°	1411.6	1409.6	1409.7	1409.8	1409.8	1409.9	1410.2	1411.1	1411.9	1412.7	1413.5
170°	1423.2	1421.4	1421.6	1421.9	1422.2	1422.5	1423.0	1423.8	1424.7	1425.4	1426.3
172.5°	1432.1	1430.1	1430.4	1430.7	1431.0	1431.3	1431.8	1432.6	1433.4	1434.3	1435.0
175°	1441.6	1439.6	1440.2	1440.8	1441.3	1441.9	1442.6	1443.3	1444.2	1445.0	1445.8
177.5°	1446.6	1445.3	1445.8	1446.1	1446.6	1447.1	1447.6	1448.2	1448.9	1449.5	1450.2
180°	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2



TEST NUMBER: P331818-830

CATALOG NUMBER: S122RDIW-S675D1240U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7
2.5°	1392.8	1393.9	1401.7	1405.0	1412.0	1414.7	1417.8	1417.0	1417.0	1418.5	1429.4
5°	1395.7	1405.3	1419.8	1433.7	1447.2	1458.8	1466.5	1474.1	1477.1	1491.0	1503.5
7.5°	1390.7	1408.4	1432.3	1453.6	1479.0	1499.0	1515.5	1530.5	1540.7	1560.9	1581.8
10°	1384.2	1409.2	1436.2	1463.6	1498.7	1525.1	1552.1	1572.8	1579.5	1609.9	1627.2
12.5°	1371.1	1404.6	1438.9	1474.3	1508.7	1545.2	1574.8	1595.5	1619.2	1646.4	1678.4
15°	1351.5	1390.0	1434.7	1480.5	1529.5	1573.8	1605.5	1641.6	1667.5	1697.4	1725.3
17.5°	1323.2	1372.8	1429.7	1482.6	1539.4	1587.0	1630.6	1665.3	1683.6	1700.5	1704.7
20°	1301.0	1354.3	1421.3	1483.8	1540.6	1595.4	1638.7	1667.5	1672.4	1672.8	1647.4
22.5°	1276.7	1337.0	1407.0	1471.1	1539.0	1600.1	1633.7	1646.1	1626.9	1594.3	1545.0
25°	1232.2	1301.9	1383.3	1456.3	1530.5	1588.2	1599.8	1578.1	1511.2	1441.0	1352.0
27.5°	1183.8	1262.3	1349.4	1430.8	1509.7	1545.5	1520.5	1442.5	1322.0	1217.3	1090.4
30°	1148.5	1236.5	1322.1	1413.1	1486.2	1501.6	1444.4	1329.4	1188.8	1031.0	904.6
32.5°	1108.1	1200.3	1294.4	1388.5	1449.6	1434.6	1340.0	1198.4	1033.8	878.6	759.0
35°	1050.3	1145.6	1247.1	1341.3	1380.4	1315.4	1173.9	989.7	821.2	676.5	594.2
37.5°	983.6	1087.3	1192.9	1279.5	1276.7	1168.5	975.8	785.6	644.0	558.4	499.8
40°	936.2	1041.1	1155.2	1228.3	1197.0	1056.0	847.3	667.8	564.4	496.1	453.2
42.5°	890.9	996.1	1109.4	1167.5	1113.1	939.8	731.8	591.2	505.9	452.5	417.8
45°	813.6	924.7	1029.6	1061.9	964.7	773.6	591.8	489.7	433.0	393.6	369.5
47.5°	738.0	847.3	943.1	943.7	812.2	627.4	499.2	423.9	375.4	344.9	327.3
50°	691.8	795.8	876.1	863.7	714.4	558.1	446.5	381.5	341.1	317.5	299.3
52.5°	639.9	740.7	810.3	774.7	631.7	491.2	399.2	344.6	311.1	290.6	274.3
55°	564.4	653.8	702.9	649.0	515.3	408.5	337.2	294.5	269.5	252.1	238.2
57.5°	490.1	564.0	594.8	532.2	424.4	338.7	285.3	253.2	228.4	215.9	208.7
60°	443.6	506.6	528.3	459.0	369.0	296.3	252.6	222.7	204.4	196.3	189.1
62.5°	397.8	449.3	458.3	394.7	321.7	259.4	221.8	196.6	184.5	176.6	169.8
65°	330.1	367.1	362.8	311.8	254.5	205.9	178.5	163.1	153.9	142.9	130.8
67.5°	271.7	294.4	280.7	242.5	194.3	160.0	142.1	130.4	119.1	108.7	105.8
70°	234.8	247.8	233.4	198.2	159.3	134.2	119.8	105.8	99.2	96.7	92.4
72.5°	199.3	203.9	188.3	158.2	129.6	111.1	97.1	89.3	85.7	83.6	80.9
75°	149.7	146.3	132.8	109.2	90.0	77.5	73.1	70.2	67.9	65.9	64.5
77.5°	105.1	100.2	88.1	72.8	62.7	56.6	54.1	52.5	51.4	50.4	49.0
80°	78.9	75.5	63.5	51.9	47.6	44.8	43.3	41.4	41.4	40.4	38.9
82.5°	57.8	54.0	43.5	38.1	35.7	33.9	32.9	31.8	31.4	31.6	30.5
85°	30.3	24.5	21.7	20.6	19.2	18.3	18.8	17.8	17.8	17.8	17.3
87.5°	10.2	8.9	9.1	9.4	10.7	11.9	12.7	13.9	15.5	15.0	15.3
90°	4.5	7.7	11.0	14.2	18.9	24.9	30.8	36.8	42.8	42.2	41.7
92.5°	24.1	26.6	28.9	31.3	33.2	34.6	36.0	37.4	38.8	38.9	39.1
95°	66.3	69.0	71.7	74.5	76.1	76.6	77.1	77.7	78.2	78.2	78.2
97.5°	118.5	120.9	123.3	125.6	127.3	128.4	129.4	130.4	131.5	131.5	131.5
100°	157.4	159.6	161.7	163.9	165.4	166.2	167.0	167.9	168.6	168.6	168.6
102.5°	198.0	199.7	201.5	203.2	204.6	205.7	206.7	207.7	208.8	209.0	209.2
105°	263.5	264.4	265.2	266.0	266.7	267.2	267.8	268.3	268.9	269.4	269.9
107.5°	330.9	332.2	333.3	334.5	335.1	335.1	335.1	335.1	335.1	335.4	335.5
110°	374.4	376.0	377.7	379.3	380.1	380.1	380.1	380.1	380.1	380.1	380.1



TEST NUMBER: P331818-830

CATALOG NUMBER: S122RDIW-S675D1240U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	421.3	422.9	424.6	426.2	426.9	426.7	426.5	426.2	426.0	425.4	424.7
115°	490.5	492.1	493.7	495.4	495.9	495.4	494.8	494.3	493.7	493.5	493.2
117.5°	560.0	562.1	564.3	566.5	566.8	565.2	563.7	562.2	560.7	560.1	559.4
120°	605.9	608.1	610.3	612.5	612.5	610.3	608.1	605.9	603.7	603.7	603.7
122.5°	648.4	651.0	653.6	656.2	656.8	655.3	653.7	652.1	650.6	650.0	649.4
125°	713.7	716.1	718.6	721.0	721.9	721.0	720.3	719.4	718.6	717.8	717.0
127.5°	778.2	781.3	784.4	787.5	788.5	787.6	786.6	785.6	784.6	783.6	782.7
130°	818.7	822.3	825.8	829.2	830.8	830.3	829.7	829.2	828.6	828.0	827.6
132.5°	863.0	865.9	868.7	871.7	873.2	873.3	873.4	873.5	873.5	872.4	871.2
135°	923.2	926.2	929.3	932.3	934.0	934.5	935.1	935.7	936.1	935.9	935.7
137.5°	986.0	988.4	990.9	993.3	994.9	995.6	996.4	997.0	997.8	997.6	997.3
140°	1024.2	1026.6	1029.1	1031.5	1033.4	1034.7	1036.1	1037.5	1038.8	1038.8	1038.8
142.5°	1063.3	1065.7	1068.2	1070.6	1072.2	1073.2	1074.1	1075.1	1076.0	1076.2	1076.4
145°	1119.0	1120.9	1122.8	1124.6	1126.4	1128.0	1129.6	1131.3	1132.9	1133.2	1133.5
147.5°	1169.4	1171.7	1174.0	1176.3	1178.0	1179.0	1180.2	1181.2	1182.3	1182.9	1183.5
150°	1203.0	1204.7	1206.3	1207.9	1209.3	1210.3	1211.4	1212.5	1213.6	1214.4	1215.2
152.5°	1233.3	1234.9	1236.5	1238.2	1239.6	1241.0	1242.3	1243.6	1244.9	1245.9	1247.0
155°	1278.0	1278.7	1279.6	1280.4	1281.2	1282.0	1282.8	1283.6	1284.5	1285.8	1287.2
157.5°	1316.5	1317.1	1317.7	1318.1	1318.7	1319.2	1319.7	1320.1	1320.7	1322.5	1324.4
160°	1340.0	1340.6	1341.1	1341.6	1342.1	1342.3	1342.6	1342.8	1343.1	1344.7	1346.4
162.5°	1361.1	1361.2	1361.3	1361.4	1361.6	1361.9	1362.2	1362.4	1362.7	1364.5	1366.4
165°	1389.3	1389.0	1388.7	1388.5	1388.4	1388.4	1388.4	1388.4	1388.4	1390.3	1392.1
167.5°	1412.7	1411.9	1411.1	1410.2	1409.9	1409.8	1409.8	1409.7	1409.6	1411.6	1413.4
170°	1425.4	1424.7	1423.8	1423.0	1422.5	1422.2	1421.9	1421.6	1421.4	1423.2	1425.1
172.5°	1434.3	1433.4	1432.6	1431.8	1431.3	1431.0	1430.7	1430.4	1430.1	1432.1	1434.0
175°	1445.0	1444.2	1443.3	1442.6	1441.9	1441.3	1440.8	1440.2	1439.6	1441.6	1443.5
177.5°	1449.5	1448.9	1448.2	1447.6	1447.1	1446.6	1446.1	1445.8	1445.3	1446.6	1447.9
180°	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2



TEST NUMBER: P331818-830

CATALOG NUMBER: S122RDIW-S675D1240U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7
2.5°	1433.1	1438.1	1440.5	1440.5	1443.2	1442.0	1440.9
5°	1515.5	1524.7	1526.6	1535.3	1541.5	1539.5	1540.6
7.5°	1597.4	1612.1	1626.6	1633.3	1634.4	1638.2	1639.6
10°	1647.8	1659.9	1682.5	1679.1	1695.9	1705.6	1689.7
12.5°	1696.4	1712.6	1728.2	1732.6	1742.2	1745.2	1739.0
15°	1740.2	1748.9	1749.8	1747.5	1750.3	1747.9	1738.8
17.5°	1699.2	1685.2	1656.7	1643.2	1632.6	1616.7	1610.4
20°	1631.4	1590.1	1542.0	1522.8	1500.2	1455.9	1466.5
22.5°	1485.3	1438.0	1390.0	1333.8	1306.9	1265.0	1262.4
25°	1257.6	1176.4	1086.8	1024.4	987.8	945.9	927.7
27.5°	977.8	875.4	802.1	765.0	731.2	698.0	696.6
30°	793.8	716.9	660.1	628.4	607.7	593.7	596.6
32.5°	669.1	616.4	578.2	551.8	536.5	525.9	525.8
35°	547.1	511.0	486.4	475.3	464.3	456.6	457.0
37.5°	468.2	446.5	432.8	420.6	413.7	409.9	407.8
40°	427.7	409.9	399.4	392.1	386.3	381.1	380.1
42.5°	395.8	381.1	370.4	364.8	359.4	355.6	354.7
45°	351.2	339.2	329.6	323.3	320.9	317.5	317.5
47.5°	312.5	300.6	293.1	289.2	285.0	282.8	282.7
50°	286.3	277.1	270.4	268.0	264.6	263.2	262.7
52.5°	262.8	256.0	251.2	249.5	248.1	246.2	246.6
55°	230.9	227.1	225.2	223.8	221.3	218.4	220.4
57.5°	204.1	200.9	195.7	191.1	188.9	186.9	187.7
60°	185.2	178.5	171.7	166.5	165.0	160.7	160.7
62.5°	161.4	151.9	143.6	140.7	139.2	137.2	136.9
65°	124.1	120.3	118.4	116.4	115.5	115.5	114.5
67.5°	102.8	101.3	99.2	98.7	97.7	97.5	97.2
70°	91.0	89.0	88.0	87.6	86.6	87.1	85.7
72.5°	79.4	77.9	77.7	76.4	75.8	75.9	74.8
75°	62.6	62.6	62.0	61.5	60.6	60.1	60.6
77.5°	48.1	48.2	47.3	47.2	47.1	47.2	46.8
80°	38.5	38.9	38.5	38.0	37.5	38.0	37.5
82.5°	30.4	29.7	29.6	29.5	29.4	29.1	29.0
85°	17.3	17.8	17.3	16.9	16.9	16.9	17.3
87.5°	14.8	14.7	14.6	14.7	14.7	14.8	14.5
90°	41.2	40.6	40.4	40.7	41.0	41.3	41.6
92.5°	39.2	39.3	39.4	39.4	39.5	39.6	39.6
95°	78.2	78.2	77.9	77.4	76.8	76.3	75.8
97.5°	131.5	131.5	131.5	131.4	131.4	131.3	131.3
100°	168.6	168.6	168.5	168.2	168.0	167.7	167.4
102.5°	209.4	209.6	209.6	209.3	209.1	208.8	208.5
105°	270.5	271.1	271.4	271.4	271.4	271.4	271.4
107.5°	335.7	336.0	335.5	334.2	333.0	331.7	330.5
110°	380.1	380.1	379.7	378.9	378.1	377.2	376.5



TEST NUMBER: P331818-830

CATALOG NUMBER: S122RDIW-S675D1240U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	424.0	423.4	422.8	422.2	421.6	421.0	420.4
115°	492.9	492.7	492.1	491.3	490.5	489.7	488.9
117.5°	558.7	558.1	557.4	556.6	555.7	555.0	554.1
120°	603.7	603.7	603.3	602.5	601.7	600.9	600.1
122.5°	648.8	648.1	647.4	646.9	646.2	645.6	645.1
125°	716.1	715.4	714.8	714.5	714.3	714.0	713.7
127.5°	781.7	780.7	779.8	778.9	778.1	777.2	776.3
130°	827.0	826.4	825.7	824.5	823.5	822.4	821.2
132.5°	870.0	868.8	867.8	867.0	866.0	865.2	864.3
135°	935.4	935.1	934.5	933.7	932.9	932.1	931.2
137.5°	997.1	996.9	996.3	995.1	994.1	993.0	991.9
140°	1038.8	1038.8	1038.3	1037.2	1036.1	1035.0	1034.0
142.5°	1076.7	1076.9	1076.4	1075.3	1074.2	1073.2	1072.0
145°	1133.8	1134.0	1133.6	1132.6	1131.4	1130.4	1129.3
147.5°	1184.1	1184.7	1184.5	1183.5	1182.4	1181.4	1180.3
150°	1216.1	1216.8	1216.8	1216.1	1215.2	1214.4	1213.6
152.5°	1247.9	1249.0	1249.0	1247.9	1247.0	1245.9	1244.9
155°	1288.5	1289.9	1290.2	1289.4	1288.5	1287.7	1286.9
157.5°	1326.2	1328.0	1328.3	1327.0	1325.7	1324.4	1323.0
160°	1348.0	1349.6	1349.9	1348.9	1347.7	1346.7	1345.6
162.5°	1368.2	1370.1	1370.4	1369.0	1367.7	1366.4	1365.2
165°	1394.0	1396.0	1396.2	1394.9	1393.5	1392.1	1390.8
167.5°	1415.3	1417.2	1417.5	1416.1	1414.7	1413.2	1411.8
170°	1427.0	1429.0	1429.1	1427.5	1425.9	1424.2	1422.6
172.5°	1435.9	1437.8	1437.8	1436.2	1434.6	1433.0	1431.3
175°	1445.4	1447.3	1447.5	1445.8	1444.2	1442.6	1440.9
177.5°	1449.3	1450.5	1450.5	1449.3	1447.9	1446.6	1445.3
180°	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2

(END OF REPORT)