

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331822-830

Luminaire Tested: **S122RDIW-S675D1440U830-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331822-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIW-S675D1440U830-4F0-1E-UDD-A1  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1440 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7108.0 lumens  
Efficiency: N/A  
Efficacy: 104.4 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 68.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331822-830

CATALOG NUMBER: S122RDIW-S675D1440U830-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P331822-830

CATALOG NUMBER: S122RDIW-S675D1440U830-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	34
1	95	91	87	84	85	82	79	76	66	64	62	51	50	48	37	36	36	29
2	87	80	74	69	78	72	67	63	58	55	52	45	43	41	33	32	31	26
3	79	71	64	58	71	64	58	54	52	48	44	41	38	36	30	28	27	22
4	73	63	55	50	66	57	51	46	46	42	38	36	33	31	27	25	24	20
5	67	56	49	43	60	51	45	40	42	37	33	33	30	27	25	23	21	18
6	62	51	43	37	56	46	40	35	38	33	29	30	27	24	23	21	19	16
7	57	46	38	33	52	42	35	31	34	30	26	27	24	21	21	19	17	14
8	53	42	34	29	48	38	32	27	31	27	23	25	22	19	19	17	15	13
9	50	38	31	26	45	35	29	24	29	24	21	23	20	17	18	16	14	12
10	46	35	28	24	42	32	26	22	27	22	19	22	18	16	17	15	13	11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	22357	22357	22357	22357
5°	24969	22498	19947	22498
10°	27702	22338	17290	22338
15°	29065	22011	13623	22011
20°	25197	21526	11789	21526
25°	16527	20861	10525	20861
30°	11123	20057	9527	20057
35°	9008	19042	8592	19042
40°	8011	17939	7950	17939
45°	7250	16643	7099	16643
50°	6599	15360	6574	15360
55°	6204	13937	6120	13937
60°	5189	12633	5125	12633
65°	4374	11469	4963	11469
70°	4046	10244	4683	10244
75°	3780	8914	4323	8914
80°	3487	7336	3849	7336
85°	3205	5798	3390	5798



TEST NUMBER: P331822-830

CATALOG NUMBER: S122RDIW-S675D1440U830-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	131.3	1.8
10°-20°	365.7	5.1
20°-30°	471.3	6.6
30°-40°	447.9	6.3
40°-50°	383.7	5.4
50°-60°	292.2	4.1
60°-70°	184.7	2.6
70°-80°	92.2	1.3
80°-90°	30.7	0.4
90°-100°	106.7	1.5
100°-110°	331.4	4.7
110°-120°	566.4	8.0
120°-130°	744.9	10.5
130°-140°	836.1	11.8
140°-150°	819.8	11.5
150°-160°	687.6	9.7
160°-170°	456.0	6.4
170°-180°	159.4	2.2
0°-30°	968.3	13.6
0°-40°	1416.2	19.9
0°-60°	2092.1	29.4
0°-90°	2399.7	33.8
90°-120°	1004.5	14.1
90°-150°	3405.2	47.9
90°-180°	4708.0	66.2
0°-180°	7108.0	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1385	1385	1385	1385	1385	
5°	1541	1388	1231	1388	1541	152
15°	1739	1317	815	1317	1739	469
25°	928	1171	591	1171	928	440
35°	457	966	436	966	457	292
45°	318	729	311	729	318	246
55°	220	495	217	495	220	193
65°	114	300	130	300	114	117
75°	61	143	69	143	61	64
85°	17	31	18	31	17	20
90°	48	1	48	1	48	22
95°	88	74	88	74	88	98
105°	316	306	316	306	316	332
115°	568	568	568	568	568	561
125°	830	827	830	827	830	740
135°	1083	1070	1083	1070	1083	833
145°	1313	1299	1313	1299	1313	820
155°	1496	1485	1496	1485	1496	689
165°	1617	1616	1617	1616	1617	456
175°	1675	1681	1675	1681	1675	159
180°	1684	1684	1684	1684	1684	



TEST NUMBER: P331822-830

CATALOG NUMBER: S122RDIW-S675D1440U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7
2.5°	1440.9	1442.0	1443.2	1440.5	1440.5	1438.1	1433.1	1429.4	1418.5	1417.0	1417.0
5°	1540.6	1539.5	1541.5	1535.3	1526.6	1524.7	1515.5	1503.5	1491.0	1477.1	1474.1
7.5°	1639.6	1638.2	1634.4	1633.3	1626.6	1612.1	1597.4	1581.8	1560.9	1540.7	1530.5
10°	1689.7	1705.6	1695.9	1679.1	1682.5	1659.9	1647.8	1627.2	1609.9	1579.5	1572.8
12.5°	1739.0	1745.2	1742.2	1732.6	1728.2	1712.6	1696.4	1678.4	1646.4	1619.2	1595.5
15°	1738.8	1747.9	1750.3	1747.5	1749.8	1748.9	1740.2	1725.3	1697.4	1667.5	1641.6
17.5°	1610.4	1616.7	1632.6	1643.2	1656.7	1685.2	1699.2	1704.7	1700.5	1683.6	1665.3
20°	1466.5	1455.9	1500.2	1522.8	1542.0	1590.1	1631.4	1647.4	1672.8	1672.4	1667.5
22.5°	1262.4	1265.0	1306.9	1333.8	1390.0	1438.0	1485.3	1545.0	1594.3	1626.9	1646.1
25°	927.7	945.9	987.8	1024.4	1086.8	1176.4	1257.6	1352.0	1441.0	1511.2	1578.1
27.5°	696.6	698.0	731.2	765.0	802.1	875.4	977.8	1090.4	1217.3	1322.0	1442.5
30°	596.6	593.7	607.7	628.4	660.1	716.9	793.8	904.6	1031.0	1188.8	1329.4
32.5°	525.8	525.9	536.5	551.8	578.2	616.4	669.1	759.0	878.6	1033.8	1198.4
35°	457.0	456.6	464.3	475.3	486.4	511.0	547.1	594.2	676.5	821.2	989.7
37.5°	407.8	409.9	413.7	420.6	432.8	446.5	468.2	499.8	558.4	644.0	785.6
40°	380.1	381.1	386.3	392.1	399.4	409.9	427.7	453.2	496.1	564.4	667.8
42.5°	354.7	355.6	359.4	364.8	370.4	381.1	395.8	417.8	452.5	505.9	591.2
45°	317.5	317.5	320.9	323.3	329.6	339.2	351.2	369.5	393.6	433.0	489.7
47.5°	282.7	282.8	285.0	289.2	293.1	300.6	312.5	327.3	344.9	375.4	423.9
50°	262.7	263.2	264.6	268.0	270.4	277.1	286.3	299.3	317.5	341.1	381.5
52.5°	246.6	246.2	248.1	249.5	251.2	256.0	262.8	274.3	290.6	311.1	344.6
55°	220.4	218.4	221.3	223.8	225.2	227.1	230.9	238.2	252.1	269.5	294.5
57.5°	187.7	186.9	188.9	191.1	195.7	200.9	204.1	208.7	215.9	228.4	253.2
60°	160.7	160.7	165.0	166.5	171.7	178.5	185.2	189.1	196.3	204.4	222.7
62.5°	136.9	137.2	139.2	140.7	143.6	151.9	161.4	169.8	176.6	184.5	196.6
65°	114.5	115.5	115.5	116.4	118.4	120.3	124.1	130.8	142.9	153.9	163.1
67.5°	97.2	97.5	97.7	98.7	99.2	101.3	102.8	105.8	108.7	119.1	130.4
70°	85.7	87.1	86.6	87.6	88.0	89.0	91.0	92.4	96.7	99.2	105.8
72.5°	74.8	75.9	75.8	76.4	77.7	77.9	79.4	80.9	83.6	85.7	89.3
75°	60.6	60.1	60.6	61.5	62.0	62.6	62.6	64.5	65.9	67.9	70.2
77.5°	46.8	47.2	47.1	47.2	47.3	48.2	48.1	49.0	50.4	51.4	52.5
80°	37.5	38.0	37.5	38.0	38.5	38.9	38.5	38.9	40.4	41.4	41.4
82.5°	29.0	29.1	29.4	29.5	29.6	29.7	30.4	30.5	31.6	31.4	31.8
85°	17.3	16.9	16.9	16.9	17.3	17.8	17.3	17.3	17.8	17.8	17.8
87.5°	15.8	16.1	16.1	16.0	15.9	16.0	16.1	16.6	16.4	16.9	15.1
90°	48.4	48.0	47.7	47.4	47.0	47.2	47.9	48.4	49.1	49.8	42.8
92.5°	46.0	46.0	45.9	45.8	45.8	45.7	45.5	45.4	45.3	45.1	43.5
95°	88.1	88.7	89.4	90.0	90.6	91.0	91.0	91.0	91.0	91.0	90.3
97.5°	152.6	152.7	152.7	152.8	152.9	152.9	152.9	152.9	152.9	152.9	151.7
100°	194.6	195.0	195.3	195.6	196.0	196.0	196.0	196.0	196.0	196.0	195.1
102.5°	242.4	242.7	243.1	243.4	243.6	243.7	243.5	243.2	243.0	242.7	241.5
105°	315.5	315.5	315.5	315.5	315.5	315.1	314.5	313.9	313.2	312.6	312.0
107.5°	384.2	385.7	387.1	388.6	390.0	390.6	390.4	390.1	389.8	389.6	389.6
110°	437.6	438.6	439.5	440.5	441.4	442.0	442.0	442.0	442.0	442.0	442.0



TEST NUMBER: P331822-830

CATALOG NUMBER: S122RDIW-S675D1440U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	488.8	489.5	490.2	490.9	491.5	492.3	493.0	493.8	494.6	495.3	495.6
115°	568.4	569.3	570.2	571.2	572.1	572.8	573.1	573.4	573.7	574.1	574.7
117.5°	644.2	645.2	646.1	647.1	648.0	648.9	649.7	650.4	651.2	652.0	653.7
120°	697.7	698.6	699.6	700.5	701.4	701.9	701.9	701.9	701.9	701.9	704.5
122.5°	750.0	750.6	751.4	752.1	752.7	753.5	754.2	755.0	755.7	756.5	758.3
125°	829.8	830.2	830.5	830.8	831.1	831.7	832.6	833.6	834.5	835.5	836.5
127.5°	902.6	903.6	904.6	905.6	906.6	907.7	908.8	909.9	911.1	912.3	913.4
130°	954.9	956.1	957.4	958.7	959.9	960.8	961.5	962.1	962.8	963.4	964.0
132.5°	1004.8	1005.9	1006.9	1008.0	1008.9	1010.1	1011.5	1013.0	1014.3	1015.7	1015.6
135°	1082.8	1083.7	1084.7	1085.6	1086.6	1087.2	1087.5	1087.8	1088.2	1088.4	1087.8
137.5°	1153.2	1154.5	1155.7	1157.1	1158.3	1159.0	1159.3	1159.5	1159.8	1160.1	1159.2
140°	1202.1	1203.3	1204.7	1205.9	1207.2	1207.8	1207.8	1207.8	1207.8	1207.8	1206.3
142.5°	1246.4	1247.7	1249.0	1250.3	1251.5	1252.0	1251.8	1251.5	1251.2	1251.0	1249.9
145°	1313.0	1314.2	1315.5	1316.7	1318.0	1318.4	1318.1	1317.9	1317.5	1317.2	1315.3
147.5°	1372.3	1373.6	1374.7	1375.9	1377.1	1377.4	1376.7	1376.0	1375.4	1374.6	1373.4
150°	1411.0	1411.9	1412.9	1413.8	1414.8	1414.8	1413.8	1412.9	1411.9	1411.0	1409.8
152.5°	1447.4	1448.6	1449.7	1451.0	1452.2	1452.2	1451.0	1449.7	1448.6	1447.4	1445.9
155°	1496.3	1497.2	1498.2	1499.1	1500.1	1499.7	1498.2	1496.6	1495.0	1493.4	1492.4
157.5°	1538.3	1539.8	1541.3	1542.8	1544.4	1544.1	1541.9	1539.7	1537.6	1535.5	1534.9
160°	1564.4	1565.8	1567.0	1568.2	1569.5	1569.1	1567.3	1565.4	1563.5	1561.6	1561.3
162.5°	1587.1	1588.7	1590.3	1591.8	1593.3	1592.9	1590.8	1588.7	1586.5	1584.3	1584.0
165°	1617.0	1618.6	1620.2	1621.7	1623.3	1623.1	1620.8	1618.6	1616.4	1614.2	1614.2
167.5°	1641.4	1643.1	1644.7	1646.4	1648.0	1647.8	1645.6	1643.3	1641.2	1638.9	1639.0
170°	1654.0	1655.9	1657.7	1659.6	1661.5	1661.4	1659.2	1657.0	1654.7	1652.6	1652.8
172.5°	1664.2	1666.1	1668.0	1669.9	1671.8	1671.6	1669.4	1667.2	1665.0	1662.7	1663.1
175°	1675.3	1677.2	1679.0	1680.9	1682.9	1682.7	1680.5	1678.3	1676.1	1673.9	1674.5
177.5°	1680.4	1681.9	1683.5	1685.0	1686.5	1686.5	1685.0	1683.5	1681.9	1680.4	1680.9
180°	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9



TEST NUMBER: P331822-830

CATALOG NUMBER: S122RDIW-S675D1440U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7
2.5°	1417.8	1414.7	1412.0	1405.0	1401.7	1393.9	1392.8	1392.4	1382.3	1372.7	1370.1
5°	1466.5	1458.8	1447.2	1433.7	1419.8	1405.3	1395.7	1388.1	1368.8	1350.5	1339.9
7.5°	1515.5	1499.0	1479.0	1453.6	1432.3	1408.4	1390.7	1374.9	1347.6	1321.4	1303.7
10°	1552.1	1525.1	1498.7	1463.6	1436.2	1409.2	1384.2	1362.5	1331.7	1297.1	1272.5
12.5°	1574.8	1545.2	1508.7	1474.3	1438.9	1404.6	1371.1	1343.3	1307.1	1271.3	1242.2
15°	1605.5	1573.8	1529.5	1480.5	1434.7	1390.0	1351.5	1316.8	1269.7	1226.9	1191.3
17.5°	1630.6	1587.0	1539.4	1482.6	1429.7	1372.8	1323.2	1279.0	1226.5	1174.9	1132.9
20°	1638.7	1595.4	1540.6	1483.8	1421.3	1354.3	1301.0	1252.8	1196.6	1140.3	1092.1
22.5°	1633.7	1600.1	1539.0	1471.1	1407.0	1337.0	1276.7	1220.9	1158.5	1101.0	1045.2
25°	1599.8	1588.2	1530.5	1456.3	1383.3	1301.9	1232.2	1171.0	1099.9	1038.3	977.6
27.5°	1520.5	1545.5	1509.7	1430.8	1349.4	1262.3	1183.8	1114.3	1040.4	971.1	910.7
30°	1444.4	1501.6	1486.2	1413.1	1322.1	1236.5	1148.5	1075.8	996.9	925.7	866.0
32.5°	1340.0	1434.6	1449.6	1388.5	1294.4	1200.3	1108.1	1035.8	953.4	878.4	820.2
35°	1173.9	1315.4	1380.4	1341.3	1247.1	1145.6	1050.3	966.1	883.4	809.3	751.5
37.5°	975.8	1168.5	1276.7	1279.5	1192.9	1087.3	983.6	900.0	815.3	742.5	680.1
40°	847.3	1056.0	1197.0	1228.3	1155.2	1041.1	936.2	851.1	768.4	697.1	625.5
42.5°	731.8	939.8	1113.1	1167.5	1109.4	996.1	890.9	801.8	721.4	654.0	580.8
45°	591.8	773.6	964.7	1061.9	1029.6	924.7	813.6	728.9	653.4	595.1	524.9
47.5°	499.2	627.4	812.2	943.7	943.1	847.3	738.0	657.0	586.9	532.3	475.4
50°	446.5	558.1	714.4	863.7	876.1	795.8	691.8	611.5	546.1	488.8	443.1
52.5°	399.2	491.2	631.7	774.7	810.3	740.7	639.9	565.7	502.2	449.6	410.4
55°	337.2	408.5	515.3	649.0	702.9	653.8	564.4	495.1	443.6	399.4	365.6
57.5°	285.3	338.7	424.4	532.2	594.8	564.0	490.1	433.9	389.8	349.8	323.2
60°	252.6	296.3	369.0	459.0	528.3	506.6	443.6	391.2	353.6	319.0	294.0
62.5°	221.8	259.4	321.7	394.7	458.3	449.3	397.8	353.8	320.9	289.4	268.2
65°	178.5	205.9	254.5	311.8	362.8	367.1	330.1	300.2	270.9	245.8	227.1
67.5°	142.1	160.0	194.3	242.5	280.7	294.4	271.7	248.9	225.6	206.3	190.0
70°	119.8	134.2	159.3	198.2	233.4	247.8	234.8	217.0	196.8	180.9	166.9
72.5°	97.1	111.1	129.6	158.2	188.3	203.9	199.3	186.6	170.2	157.0	143.8
75°	73.1	77.5	90.0	109.2	132.8	146.3	149.7	142.9	129.9	119.8	112.1
77.5°	54.1	56.6	62.7	72.8	88.1	100.2	105.1	104.3	95.4	89.4	82.3
80°	43.3	44.8	47.6	51.9	63.5	75.5	78.9	78.9	72.7	70.2	63.1
82.5°	32.9	33.9	35.7	38.1	43.5	54.0	57.8	58.5	54.6	51.4	45.7
85°	18.8	18.3	19.2	20.6	21.7	24.5	30.3	31.3	30.3	26.5	25.0
87.5°	13.7	12.7	11.3	9.9	9.5	9.1	10.3	11.4	10.7	10.3	10.3
90°	35.8	28.9	22.0	16.6	12.8	9.0	5.2	1.4	5.2	9.0	12.8
92.5°	41.9	40.2	38.6	36.4	33.6	30.8	28.1	25.3	28.1	30.8	33.6
95°	89.6	89.1	88.4	86.5	83.3	80.2	77.0	73.9	77.0	80.2	83.3
97.5°	150.5	149.3	148.1	146.1	143.4	140.5	137.8	135.0	137.8	140.5	143.4
100°	194.2	193.2	192.3	190.6	188.0	185.5	182.9	180.5	182.9	185.5	188.0
102.5°	240.3	239.1	237.9	236.3	234.2	232.2	230.3	228.2	230.3	232.2	234.2
105°	311.3	310.8	310.1	309.2	308.3	307.4	306.4	305.5	306.4	307.4	308.3
107.5°	389.6	389.6	389.6	388.9	387.6	386.2	384.7	383.3	384.7	386.2	387.6
110°	442.0	442.0	442.0	440.9	439.0	437.2	435.3	433.4	435.3	437.2	439.0





TEST NUMBER: P331822-830

CATALOG NUMBER: S122RDIW-S675D1440U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	495.9	496.1	496.3	495.5	493.6	491.7	489.8	488.0	489.8	491.7	493.6
115°	575.3	576.0	576.6	576.0	574.1	572.1	570.2	568.4	570.2	572.1	574.1
117.5°	655.4	657.2	659.0	658.6	656.1	653.6	651.0	648.6	651.0	653.6	656.1
120°	707.0	709.5	712.1	712.1	709.5	707.0	704.5	701.9	704.5	707.0	709.5
122.5°	760.1	761.9	763.6	763.0	759.9	756.9	753.8	750.8	753.8	756.9	759.9
125°	837.4	838.4	839.3	838.4	835.5	832.6	829.8	827.0	829.8	832.6	835.5
127.5°	914.5	915.7	916.8	915.6	912.0	908.3	904.7	901.2	904.7	908.3	912.0
130°	964.7	965.3	965.9	964.2	960.1	956.0	951.9	947.7	951.9	956.0	960.1
132.5°	1015.4	1015.3	1015.2	1013.4	1010.1	1006.7	1003.4	1000.0	1003.4	1006.7	1010.1
135°	1087.2	1086.6	1085.9	1083.8	1080.3	1076.9	1073.5	1070.0	1073.5	1076.9	1080.3
137.5°	1158.4	1157.6	1156.8	1154.9	1152.1	1149.2	1146.4	1143.6	1146.4	1149.2	1152.1
140°	1204.7	1203.1	1201.5	1199.3	1196.5	1193.6	1190.7	1187.9	1190.7	1193.6	1196.5
142.5°	1248.9	1247.7	1246.7	1244.7	1241.9	1239.1	1236.2	1233.4	1236.2	1239.1	1241.9
145°	1313.4	1311.5	1309.7	1307.6	1305.3	1303.2	1301.0	1298.7	1301.0	1303.2	1305.3
147.5°	1372.1	1370.8	1369.6	1367.6	1365.0	1362.3	1359.6	1357.0	1359.6	1362.3	1365.0
150°	1408.4	1407.2	1405.9	1404.4	1402.5	1400.6	1398.6	1396.8	1398.6	1400.6	1402.5
152.5°	1444.4	1442.8	1441.3	1439.6	1437.7	1435.8	1433.9	1432.0	1433.9	1435.8	1437.7
155°	1491.5	1490.5	1489.6	1488.7	1487.7	1486.8	1485.8	1484.9	1485.8	1486.8	1487.7
157.5°	1534.4	1533.8	1533.2	1532.6	1532.0	1531.3	1530.7	1530.0	1530.7	1531.3	1532.0
160°	1560.9	1560.7	1560.4	1559.9	1559.2	1558.6	1558.0	1557.4	1558.0	1558.6	1559.2
162.5°	1583.8	1583.4	1583.1	1582.9	1582.7	1582.6	1582.5	1582.3	1582.5	1582.6	1582.7
165°	1614.2	1614.2	1614.2	1614.4	1614.7	1615.0	1615.3	1615.6	1615.3	1615.0	1614.7
167.5°	1639.1	1639.1	1639.2	1639.6	1640.6	1641.5	1642.5	1643.4	1642.5	1641.5	1640.6
170°	1653.2	1653.5	1653.8	1654.4	1655.4	1656.3	1657.3	1658.2	1657.3	1656.3	1655.4
172.5°	1663.4	1663.8	1664.1	1664.7	1665.7	1666.6	1667.5	1668.5	1667.5	1666.6	1665.7
175°	1675.1	1675.7	1676.4	1677.2	1678.1	1679.0	1680.0	1680.9	1680.0	1679.0	1678.1
177.5°	1681.4	1681.9	1682.4	1683.1	1683.9	1684.6	1685.4	1686.1	1685.4	1684.6	1683.9
180°	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9



TEST NUMBER: P331822-830

CATALOG NUMBER: S122RDIW-S675D1440U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7
2.5°	1365.1	1362.4	1357.4	1349.6	1345.0	1336.9	1331.5	1334.6	1335.4	1334.6	1333.9
5°	1328.4	1318.2	1304.3	1290.8	1278.4	1264.9	1257.2	1253.8	1247.1	1243.2	1241.3
7.5°	1284.0	1266.6	1246.9	1223.4	1203.4	1182.6	1172.0	1166.6	1152.8	1145.4	1138.8
10°	1250.9	1223.5	1203.8	1173.0	1154.2	1126.8	1108.1	1108.5	1089.8	1079.1	1071.5
12.5°	1214.4	1184.2	1151.4	1123.7	1097.6	1075.6	1053.0	1043.9	1023.9	1013.7	993.0
15°	1153.8	1118.6	1084.0	1046.4	1020.0	985.8	953.1	913.1	880.9	853.0	845.4
17.5°	1087.5	1044.1	1009.3	965.3	919.9	862.4	824.5	801.3	781.9	767.2	756.2
20°	1042.1	997.9	960.8	894.4	833.3	794.4	766.5	748.7	728.4	712.6	703.9
22.5°	994.4	948.2	897.7	823.6	776.0	744.7	719.8	699.4	685.7	673.3	665.4
25°	926.6	876.1	792.9	741.9	703.4	670.7	653.4	640.8	626.4	609.5	601.9
27.5°	855.1	774.7	714.9	677.0	640.3	619.0	603.4	584.8	571.8	564.3	556.3
30°	801.5	721.2	674.6	633.2	607.2	583.6	565.3	554.8	542.2	529.2	524.0
32.5°	741.9	677.7	633.0	598.5	572.1	552.0	537.6	520.5	511.4	503.4	492.4
35°	667.8	619.3	578.3	550.4	525.4	509.1	492.2	482.1	465.7	459.0	454.7
37.5°	605.0	562.9	532.4	502.9	483.1	465.1	454.8	438.7	431.6	422.3	413.1
40°	569.7	528.3	498.9	474.9	452.7	439.2	426.3	413.3	402.7	398.4	387.3
42.5°	533.5	499.8	470.4	444.0	429.2	415.0	398.6	389.1	378.1	371.1	364.2
45°	483.5	453.7	428.7	407.0	390.7	375.8	365.1	349.3	343.1	329.0	323.3
47.5°	439.7	411.9	388.0	367.5	351.5	341.8	326.3	313.9	303.9	295.3	287.9
50°	408.5	385.4	362.3	344.0	329.6	315.7	299.7	293.5	278.1	273.7	269.5
52.5°	380.0	358.1	336.9	319.0	304.5	291.0	277.0	268.8	258.4	254.1	251.0
55°	340.2	319.0	298.8	282.9	268.4	254.5	245.8	235.7	230.9	227.5	223.8
57.5°	300.1	281.1	265.6	249.5	235.0	223.9	213.9	207.8	202.8	198.4	193.8
60°	274.8	256.5	242.5	227.5	212.6	203.5	195.9	188.6	182.9	176.1	174.2
62.5°	247.8	231.8	219.0	204.4	191.5	183.1	175.8	169.0	162.0	152.2	149.5
65°	210.8	198.2	184.7	172.8	161.2	153.0	142.4	134.7	131.9	130.8	130.4
67.5°	177.3	165.4	153.8	141.6	131.0	123.5	118.1	116.9	114.9	114.3	113.0
70°	155.0	143.8	132.3	120.7	110.7	109.2	107.3	105.4	102.9	102.0	101.0
72.5°	134.9	123.5	111.9	102.6	98.3	96.5	94.6	92.7	91.0	90.1	89.4
75°	103.4	92.8	85.2	81.8	79.4	77.9	75.0	73.6	72.7	71.2	70.7
77.5°	74.5	68.5	64.9	62.9	60.3	58.8	57.1	55.7	54.7	54.4	53.6
80°	56.7	53.9	51.5	48.6	47.6	45.7	45.2	43.8	44.3	42.8	42.8
82.5°	44.1	40.4	38.4	37.0	36.1	34.6	34.0	33.4	33.5	32.4	32.4
85°	22.6	21.7	20.6	19.7	19.7	18.3	18.8	18.3	18.3	17.3	16.9
87.5°	10.7	11.3	12.0	13.3	14.7	15.7	15.6	15.1	15.0	14.8	14.4
90°	16.6	22.0	28.9	35.8	42.8	49.8	49.1	48.4	47.9	47.2	47.0
92.5°	36.4	38.6	40.2	41.9	43.5	45.1	45.3	45.4	45.5	45.7	45.8
95°	86.5	88.4	89.1	89.6	90.3	91.0	91.0	91.0	91.0	91.0	90.6
97.5°	146.1	148.1	149.3	150.5	151.7	152.9	152.9	152.9	152.9	152.9	152.9
100°	190.6	192.3	193.2	194.2	195.1	196.0	196.0	196.0	196.0	196.0	196.0
102.5°	236.3	237.9	239.1	240.3	241.5	242.7	243.0	243.2	243.5	243.7	243.6
105°	309.2	310.1	310.8	311.3	312.0	312.6	313.2	313.9	314.5	315.1	315.5
107.5°	388.9	389.6	389.6	389.6	389.6	389.6	389.8	390.1	390.4	390.6	390.0
110°	440.9	442.0	442.0	442.0	442.0	442.0	442.0	442.0	442.0	442.0	441.4



TEST NUMBER: P331822-830

CATALOG NUMBER: S122RDIW-S675D1440U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	495.5	496.3	496.1	495.9	495.6	495.3	494.6	493.8	493.0	492.3	491.5
115°	576.0	576.6	576.0	575.3	574.7	574.1	573.7	573.4	573.1	572.8	572.1
117.5°	658.6	659.0	657.2	655.4	653.7	652.0	651.2	650.4	649.7	648.9	648.0
120°	712.1	712.1	709.5	707.0	704.5	701.9	701.9	701.9	701.9	701.9	701.4
122.5°	763.0	763.6	761.9	760.1	758.3	756.5	755.7	755.0	754.2	753.5	752.7
125°	838.4	839.3	838.4	837.4	836.5	835.5	834.5	833.6	832.6	831.7	831.1
127.5°	915.6	916.8	915.7	914.5	913.4	912.3	911.1	909.9	908.8	907.7	906.6
130°	964.2	965.9	965.3	964.7	964.0	963.4	962.8	962.1	961.5	960.8	959.9
132.5°	1013.4	1015.2	1015.3	1015.4	1015.6	1015.7	1014.3	1013.0	1011.5	1010.1	1008.9
135°	1083.8	1085.9	1086.6	1087.2	1087.8	1088.4	1088.2	1087.8	1087.5	1087.2	1086.6
137.5°	1154.9	1156.8	1157.6	1158.4	1159.2	1160.1	1159.8	1159.5	1159.3	1159.0	1158.3
140°	1199.3	1201.5	1203.1	1204.7	1206.3	1207.8	1207.8	1207.8	1207.8	1207.8	1207.2
142.5°	1244.7	1246.7	1247.7	1248.9	1249.9	1251.0	1251.2	1251.5	1251.8	1252.0	1251.5
145°	1307.6	1309.7	1311.5	1313.4	1315.3	1317.2	1317.5	1317.9	1318.1	1318.4	1318.0
147.5°	1367.6	1369.6	1370.8	1372.1	1373.4	1374.6	1375.4	1376.0	1376.7	1377.4	1377.1
150°	1404.4	1405.9	1407.2	1408.4	1409.8	1411.0	1411.9	1412.9	1413.8	1414.8	1414.8
152.5°	1439.6	1441.3	1442.8	1444.4	1445.9	1447.4	1448.6	1449.7	1451.0	1452.2	1452.2
155°	1488.7	1489.6	1490.5	1491.5	1492.4	1493.4	1495.0	1496.6	1498.2	1499.7	1500.1
157.5°	1532.6	1533.2	1533.8	1534.4	1534.9	1535.5	1537.6	1539.7	1541.9	1544.1	1544.4
160°	1559.9	1560.4	1560.7	1560.9	1561.3	1561.6	1563.5	1565.4	1567.3	1569.1	1569.5
162.5°	1582.9	1583.1	1583.4	1583.8	1584.0	1584.3	1586.5	1588.7	1590.8	1592.9	1593.3
165°	1614.4	1614.2	1614.2	1614.2	1614.2	1614.2	1616.4	1618.6	1620.8	1623.1	1623.3
167.5°	1639.6	1639.2	1639.1	1639.1	1639.0	1638.9	1641.2	1643.3	1645.6	1647.8	1648.0
170°	1654.4	1653.8	1653.5	1653.2	1652.8	1652.6	1654.7	1657.0	1659.2	1661.4	1661.5
172.5°	1664.7	1664.1	1663.8	1663.4	1663.1	1662.7	1665.0	1667.2	1669.4	1671.6	1671.8
175°	1677.2	1676.4	1675.7	1675.1	1674.5	1673.9	1676.1	1678.3	1680.5	1682.7	1682.9
177.5°	1683.1	1682.4	1681.9	1681.4	1680.9	1680.4	1681.9	1683.5	1685.0	1686.5	1686.5
180°	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9



TEST NUMBER: P331822-830

CATALOG NUMBER: S122RDIW-S675D1440U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7
2.5°	1329.6	1330.4	1329.3	1330.0	1329.3	1330.4	1329.6	1333.9	1334.6	1335.4	1334.6
5°	1238.9	1233.1	1232.2	1230.7	1232.2	1233.1	1238.9	1241.3	1243.2	1247.1	1253.8
7.5°	1130.6	1129.6	1127.3	1123.9	1127.3	1129.6	1130.6	1138.8	1145.4	1152.8	1166.6
10°	1060.8	1058.5	1058.0	1054.6	1058.0	1058.5	1060.8	1071.5	1079.1	1089.8	1108.5
12.5°	979.3	963.7	962.1	953.8	962.1	963.7	979.3	993.0	1013.7	1023.9	1043.9
15°	833.8	830.9	821.2	815.0	821.2	830.9	833.8	845.4	853.0	880.9	913.1
17.5°	750.6	741.2	738.2	736.9	738.2	741.2	750.6	756.2	767.2	781.9	801.3
20°	697.1	688.5	687.0	686.1	687.0	688.5	697.1	703.9	712.6	728.4	748.7
22.5°	660.2	651.1	647.4	644.5	647.4	651.1	660.2	665.4	673.3	685.7	699.4
25°	597.1	593.7	591.8	590.8	591.8	593.7	597.1	601.9	609.5	626.4	640.8
27.5°	547.7	540.3	538.9	536.4	538.9	540.3	547.7	556.3	564.3	571.8	584.8
30°	519.6	517.2	513.9	511.0	513.9	517.2	519.6	524.0	529.2	542.2	554.8
32.5°	486.5	484.5	481.5	480.1	481.5	484.5	486.5	492.4	503.4	511.4	520.5
35°	449.9	443.1	440.3	435.9	440.3	443.1	449.9	454.7	459.0	465.7	482.1
37.5°	411.0	407.6	403.5	404.9	403.5	407.6	411.0	413.1	422.3	431.6	438.7
40°	381.1	378.6	377.7	377.2	377.7	378.6	381.1	387.3	398.4	402.7	413.3
42.5°	357.2	350.5	348.1	348.0	348.1	350.5	357.2	364.2	371.1	378.1	389.1
45°	320.9	314.6	310.3	310.9	310.3	314.6	320.9	323.3	329.0	343.1	349.3
47.5°	283.8	283.6	280.9	281.7	280.9	283.6	283.8	287.9	295.3	303.9	313.9
50°	266.1	263.2	261.3	261.7	261.3	263.2	266.1	269.5	273.7	278.1	293.5
52.5°	249.1	246.7	245.1	247.1	245.1	246.7	249.1	251.0	254.1	258.4	268.8
55°	221.3	218.4	217.9	217.4	217.9	218.4	221.3	223.8	227.5	230.9	235.7
57.5°	190.2	188.3	185.4	184.2	185.4	188.3	190.2	193.8	198.4	202.8	207.8
60°	167.9	164.1	159.3	158.7	159.3	164.1	167.9	174.2	176.1	182.9	188.6
62.5°	147.5	146.8	145.8	145.7	145.8	146.8	147.5	149.5	152.2	162.0	169.0
65°	129.4	128.9	129.4	129.9	129.4	128.9	129.4	130.4	130.8	131.9	134.7
67.5°	112.8	111.9	111.0	111.4	111.0	111.9	112.8	113.0	114.3	114.9	116.9
70°	100.1	99.6	99.2	99.2	99.2	99.6	100.1	101.0	102.0	102.9	105.4
72.5°	87.8	87.7	87.2	86.8	87.2	87.7	87.8	89.4	90.1	91.0	92.7
75°	70.2	69.3	69.3	69.3	69.3	69.3	70.2	70.7	71.2	72.7	73.6
77.5°	53.5	53.1	52.5	52.1	52.5	53.1	53.5	53.6	54.4	54.7	55.7
80°	42.3	41.8	41.4	41.4	41.4	41.8	42.3	42.8	42.8	44.3	43.8
82.5°	32.3	31.9	31.8	31.4	31.8	31.9	32.3	32.4	32.4	33.5	33.4
85°	17.3	17.8	17.3	18.3	17.3	17.8	17.3	16.9	17.3	18.3	18.3
87.5°	14.5	14.1	14.6	14.3	14.6	14.1	14.5	14.4	14.8	15.0	15.1
90°	47.4	47.7	48.0	48.4	48.0	47.7	47.4	47.0	47.2	47.9	48.4
92.5°	45.8	45.9	46.0	46.0	46.0	45.9	45.8	45.8	45.7	45.5	45.4
95°	90.0	89.4	88.7	88.1	88.7	89.4	90.0	90.6	91.0	91.0	91.0
97.5°	152.8	152.7	152.7	152.6	152.7	152.7	152.8	152.9	152.9	152.9	152.9
100°	195.6	195.3	195.0	194.6	195.0	195.3	195.6	196.0	196.0	196.0	196.0
102.5°	243.4	243.1	242.7	242.4	242.7	243.1	243.4	243.6	243.7	243.5	243.2
105°	315.5	315.5	315.5	315.5	315.5	315.5	315.5	315.5	315.1	314.5	313.9
107.5°	388.6	387.1	385.7	384.2	385.7	387.1	388.6	390.0	390.6	390.4	390.1
110°	440.5	439.5	438.6	437.6	438.6	439.5	440.5	441.4	442.0	442.0	442.0



TEST NUMBER: P331822-830

CATALOG NUMBER: S122RDIW-S675D1440U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	490.9	490.2	489.5	488.8	489.5	490.2	490.9	491.5	492.3	493.0	493.8
115°	571.2	570.2	569.3	568.4	569.3	570.2	571.2	572.1	572.8	573.1	573.4
117.5°	647.1	646.1	645.2	644.2	645.2	646.1	647.1	648.0	648.9	649.7	650.4
120°	700.5	699.6	698.6	697.7	698.6	699.6	700.5	701.4	701.9	701.9	701.9
122.5°	752.1	751.4	750.6	750.0	750.6	751.4	752.1	752.7	753.5	754.2	755.0
125°	830.8	830.5	830.2	829.8	830.2	830.5	830.8	831.1	831.7	832.6	833.6
127.5°	905.6	904.6	903.6	902.6	903.6	904.6	905.6	906.6	907.7	908.8	909.9
130°	958.7	957.4	956.1	954.9	956.1	957.4	958.7	959.9	960.8	961.5	962.1
132.5°	1008.0	1006.9	1005.9	1004.8	1005.9	1006.9	1008.0	1008.9	1010.1	1011.5	1013.0
135°	1085.6	1084.7	1083.7	1082.8	1083.7	1084.7	1085.6	1086.6	1087.2	1087.5	1087.8
137.5°	1157.1	1155.7	1154.5	1153.2	1154.5	1155.7	1157.1	1158.3	1159.0	1159.3	1159.5
140°	1205.9	1204.7	1203.3	1202.1	1203.3	1204.7	1205.9	1207.2	1207.8	1207.8	1207.8
142.5°	1250.3	1249.0	1247.7	1246.4	1247.7	1249.0	1250.3	1251.5	1252.0	1251.8	1251.5
145°	1316.7	1315.5	1314.2	1313.0	1314.2	1315.5	1316.7	1318.0	1318.4	1318.1	1317.9
147.5°	1375.9	1374.7	1373.6	1372.3	1373.6	1374.7	1375.9	1377.1	1377.4	1376.7	1376.0
150°	1413.8	1412.9	1411.9	1411.0	1411.9	1412.9	1413.8	1414.8	1414.8	1413.8	1412.9
152.5°	1451.0	1449.7	1448.6	1447.4	1448.6	1449.7	1451.0	1452.2	1452.2	1451.0	1449.7
155°	1499.1	1498.2	1497.2	1496.3	1497.2	1498.2	1499.1	1500.1	1499.7	1498.2	1496.6
157.5°	1542.8	1541.3	1539.8	1538.3	1539.8	1541.3	1542.8	1544.4	1544.1	1541.9	1539.7
160°	1568.2	1567.0	1565.8	1564.4	1565.8	1567.0	1568.2	1569.5	1569.1	1567.3	1565.4
162.5°	1591.8	1590.3	1588.7	1587.1	1588.7	1590.3	1591.8	1593.3	1592.9	1590.8	1588.7
165°	1621.7	1620.2	1618.6	1617.0	1618.6	1620.2	1621.7	1623.3	1623.1	1620.8	1618.6
167.5°	1646.4	1644.7	1643.1	1641.4	1643.1	1644.7	1646.4	1648.0	1647.8	1645.6	1643.3
170°	1659.6	1657.7	1655.9	1654.0	1655.9	1657.7	1659.6	1661.5	1661.4	1659.2	1657.0
172.5°	1669.9	1668.0	1666.1	1664.2	1666.1	1668.0	1669.9	1671.8	1671.6	1669.4	1667.2
175°	1680.9	1679.0	1677.2	1675.3	1677.2	1679.0	1680.9	1682.9	1682.7	1680.5	1678.3
177.5°	1685.0	1683.5	1681.9	1680.4	1681.9	1683.5	1685.0	1686.5	1686.5	1685.0	1683.5
180°	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9



TEST NUMBER: P331822-830

CATALOG NUMBER: S122RDIW-S675D1440U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7
2.5°	1331.5	1336.9	1345.0	1349.6	1357.4	1362.4	1365.1	1370.1	1372.7	1382.3	1392.4
5°	1257.2	1264.9	1278.4	1290.8	1304.3	1318.2	1328.4	1339.9	1350.5	1368.8	1388.1
7.5°	1172.0	1182.6	1203.4	1223.4	1246.9	1266.6	1284.0	1303.7	1321.4	1347.6	1374.9
10°	1108.1	1126.8	1154.2	1173.0	1203.8	1223.5	1250.9	1272.5	1297.1	1331.7	1362.5
12.5°	1053.0	1075.6	1097.6	1123.7	1151.4	1184.2	1214.4	1242.2	1271.3	1307.1	1343.3
15°	953.1	985.8	1020.0	1046.4	1084.0	1118.6	1153.8	1191.3	1226.9	1269.7	1316.8
17.5°	824.5	862.4	919.9	965.3	1009.3	1044.1	1087.5	1132.9	1174.9	1226.5	1279.0
20°	766.5	794.4	833.3	894.4	960.8	997.9	1042.1	1092.1	1140.3	1196.6	1252.8
22.5°	719.8	744.7	776.0	823.6	897.7	948.2	994.4	1045.2	1101.0	1158.5	1220.9
25°	653.4	670.7	703.4	741.9	792.9	876.1	926.6	977.6	1038.3	1099.9	1171.0
27.5°	603.4	619.0	640.3	677.0	714.9	774.7	855.1	910.7	971.1	1040.4	1114.3
30°	565.3	583.6	607.2	633.2	674.6	721.2	801.5	866.0	925.7	996.9	1075.8
32.5°	537.6	552.0	572.1	598.5	633.0	677.7	741.9	820.2	878.4	953.4	1035.8
35°	492.2	509.1	525.4	550.4	578.3	619.3	667.8	751.5	809.3	883.4	966.1
37.5°	454.8	465.1	483.1	502.9	532.4	562.9	605.0	680.1	742.5	815.3	900.0
40°	426.3	439.2	452.7	474.9	498.9	528.3	569.7	625.5	697.1	768.4	851.1
42.5°	398.6	415.0	429.2	444.0	470.4	499.8	533.5	580.8	654.0	721.4	801.8
45°	365.1	375.8	390.7	407.0	428.7	453.7	483.5	524.9	595.1	653.4	728.9
47.5°	326.3	341.8	351.5	367.5	388.0	411.9	439.7	475.4	532.3	586.9	657.0
50°	299.7	315.7	329.6	344.0	362.3	385.4	408.5	443.1	488.8	546.1	611.5
52.5°	277.0	291.0	304.5	319.0	336.9	358.1	380.0	410.4	449.6	502.2	565.7
55°	245.8	254.5	268.4	282.9	298.8	319.0	340.2	365.6	399.4	443.6	495.1
57.5°	213.9	223.9	235.0	249.5	265.6	281.1	300.1	323.2	349.8	389.8	433.9
60°	195.9	203.5	212.6	227.5	242.5	256.5	274.8	294.0	319.0	353.6	391.2
62.5°	175.8	183.1	191.5	204.4	219.0	231.8	247.8	268.2	289.4	320.9	353.8
65°	142.4	153.0	161.2	172.8	184.7	198.2	210.8	227.1	245.8	270.9	300.2
67.5°	118.1	123.5	131.0	141.6	153.8	165.4	177.3	190.0	206.3	225.6	248.9
70°	107.3	109.2	110.7	120.7	132.3	143.8	155.0	166.9	180.9	196.8	217.0
72.5°	94.6	96.5	98.3	102.6	111.9	123.5	134.9	143.8	157.0	170.2	186.6
75°	75.0	77.9	79.4	81.8	85.2	92.8	103.4	112.1	119.8	129.9	142.9
77.5°	57.1	58.8	60.3	62.9	64.9	68.5	74.5	82.3	89.4	95.4	104.3
80°	45.2	45.7	47.6	48.6	51.5	53.9	56.7	63.1	70.2	72.7	78.9
82.5°	34.0	34.6	36.1	37.0	38.4	40.4	44.1	45.7	51.4	54.6	58.5
85°	18.8	18.3	19.7	19.7	20.6	21.7	22.6	25.0	26.5	30.3	31.3
87.5°	15.6	15.7	14.7	13.3	12.0	11.3	10.7	10.3	10.3	10.7	11.4
90°	49.1	49.8	42.8	35.8	28.9	22.0	16.6	12.8	9.0	5.2	1.4
92.5°	45.3	45.1	43.5	41.9	40.2	38.6	36.4	33.6	30.8	28.1	25.3
95°	91.0	91.0	90.3	89.6	89.1	88.4	86.5	83.3	80.2	77.0	73.9
97.5°	152.9	152.9	151.7	150.5	149.3	148.1	146.1	143.4	140.5	137.8	135.0
100°	196.0	196.0	195.1	194.2	193.2	192.3	190.6	188.0	185.5	182.9	180.5
102.5°	243.0	242.7	241.5	240.3	239.1	237.9	236.3	234.2	232.2	230.3	228.2
105°	313.2	312.6	312.0	311.3	310.8	310.1	309.2	308.3	307.4	306.4	305.5
107.5°	389.8	389.6	389.6	389.6	389.6	389.6	388.9	387.6	386.2	384.7	383.3
110°	442.0	442.0	442.0	442.0	442.0	442.0	440.9	439.0	437.2	435.3	433.4



TEST NUMBER: P331822-830

CATALOG NUMBER: S122RDIW-S675D1440U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	494.6	495.3	495.6	495.9	496.1	496.3	495.5	493.6	491.7	489.8	488.0
115°	573.7	574.1	574.7	575.3	576.0	576.6	576.0	574.1	572.1	570.2	568.4
117.5°	651.2	652.0	653.7	655.4	657.2	659.0	658.6	656.1	653.6	651.0	648.6
120°	701.9	701.9	704.5	707.0	709.5	712.1	712.1	709.5	707.0	704.5	701.9
122.5°	755.7	756.5	758.3	760.1	761.9	763.6	763.0	759.9	756.9	753.8	750.8
125°	834.5	835.5	836.5	837.4	838.4	839.3	838.4	835.5	832.6	829.8	827.0
127.5°	911.1	912.3	913.4	914.5	915.7	916.8	915.6	912.0	908.3	904.7	901.2
130°	962.8	963.4	964.0	964.7	965.3	965.9	964.2	960.1	956.0	951.9	947.7
132.5°	1014.3	1015.7	1015.6	1015.4	1015.3	1015.2	1013.4	1010.1	1006.7	1003.4	1000.0
135°	1088.2	1088.4	1087.8	1087.2	1086.6	1085.9	1083.8	1080.3	1076.9	1073.5	1070.0
137.5°	1159.8	1160.1	1159.2	1158.4	1157.6	1156.8	1154.9	1152.1	1149.2	1146.4	1143.6
140°	1207.8	1207.8	1206.3	1204.7	1203.1	1201.5	1199.3	1196.5	1193.6	1190.7	1187.9
142.5°	1251.2	1251.0	1249.9	1248.9	1247.7	1246.7	1244.7	1241.9	1239.1	1236.2	1233.4
145°	1317.5	1317.2	1315.3	1313.4	1311.5	1309.7	1307.6	1305.3	1303.2	1301.0	1298.7
147.5°	1375.4	1374.6	1373.4	1372.1	1370.8	1369.6	1367.6	1365.0	1362.3	1359.6	1357.0
150°	1411.9	1411.0	1409.8	1408.4	1407.2	1405.9	1404.4	1402.5	1400.6	1398.6	1396.8
152.5°	1448.6	1447.4	1445.9	1444.4	1442.8	1441.3	1439.6	1437.7	1435.8	1433.9	1432.0
155°	1495.0	1493.4	1492.4	1491.5	1490.5	1489.6	1488.7	1487.7	1486.8	1485.8	1484.9
157.5°	1537.6	1535.5	1534.9	1534.4	1533.8	1533.2	1532.6	1532.0	1531.3	1530.7	1530.0
160°	1563.5	1561.6	1561.3	1560.9	1560.7	1560.4	1559.9	1559.2	1558.6	1558.0	1557.4
162.5°	1586.5	1584.3	1584.0	1583.8	1583.4	1583.1	1582.9	1582.7	1582.6	1582.5	1582.3
165°	1616.4	1614.2	1614.2	1614.2	1614.2	1614.2	1614.4	1614.7	1615.0	1615.3	1615.6
167.5°	1641.2	1638.9	1639.0	1639.1	1639.1	1639.2	1639.6	1640.6	1641.5	1642.5	1643.4
170°	1654.7	1652.6	1652.8	1653.2	1653.5	1653.8	1654.4	1655.4	1656.3	1657.3	1658.2
172.5°	1665.0	1662.7	1663.1	1663.4	1663.8	1664.1	1664.7	1665.7	1666.6	1667.5	1668.5
175°	1676.1	1673.9	1674.5	1675.1	1675.7	1676.4	1677.2	1678.1	1679.0	1680.0	1680.9
177.5°	1681.9	1680.4	1680.9	1681.4	1681.9	1682.4	1683.1	1683.9	1684.6	1685.4	1686.1
180°	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9



TEST NUMBER: P331822-830

CATALOG NUMBER: S122RDIW-S675D1440U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7
2.5°	1392.8	1393.9	1401.7	1405.0	1412.0	1414.7	1417.8	1417.0	1417.0	1418.5	1429.4
5°	1395.7	1405.3	1419.8	1433.7	1447.2	1458.8	1466.5	1474.1	1477.1	1491.0	1503.5
7.5°	1390.7	1408.4	1432.3	1453.6	1479.0	1499.0	1515.5	1530.5	1540.7	1560.9	1581.8
10°	1384.2	1409.2	1436.2	1463.6	1498.7	1525.1	1552.1	1572.8	1579.5	1609.9	1627.2
12.5°	1371.1	1404.6	1438.9	1474.3	1508.7	1545.2	1574.8	1595.5	1619.2	1646.4	1678.4
15°	1351.5	1390.0	1434.7	1480.5	1529.5	1573.8	1605.5	1641.6	1667.5	1697.4	1725.3
17.5°	1323.2	1372.8	1429.7	1482.6	1539.4	1587.0	1630.6	1665.3	1683.6	1700.5	1704.7
20°	1301.0	1354.3	1421.3	1483.8	1540.6	1595.4	1638.7	1667.5	1672.4	1672.8	1647.4
22.5°	1276.7	1337.0	1407.0	1471.1	1539.0	1600.1	1633.7	1646.1	1626.9	1594.3	1545.0
25°	1232.2	1301.9	1383.3	1456.3	1530.5	1588.2	1599.8	1578.1	1511.2	1441.0	1352.0
27.5°	1183.8	1262.3	1349.4	1430.8	1509.7	1545.5	1520.5	1442.5	1322.0	1217.3	1090.4
30°	1148.5	1236.5	1322.1	1413.1	1486.2	1501.6	1444.4	1329.4	1188.8	1031.0	904.6
32.5°	1108.1	1200.3	1294.4	1388.5	1449.6	1434.6	1340.0	1198.4	1033.8	878.6	759.0
35°	1050.3	1145.6	1247.1	1341.3	1380.4	1315.4	1173.9	989.7	821.2	676.5	594.2
37.5°	983.6	1087.3	1192.9	1279.5	1276.7	1168.5	975.8	785.6	644.0	558.4	499.8
40°	936.2	1041.1	1155.2	1228.3	1197.0	1056.0	847.3	667.8	564.4	496.1	453.2
42.5°	890.9	996.1	1109.4	1167.5	1113.1	939.8	731.8	591.2	505.9	452.5	417.8
45°	813.6	924.7	1029.6	1061.9	964.7	773.6	591.8	489.7	433.0	393.6	369.5
47.5°	738.0	847.3	943.1	943.7	812.2	627.4	499.2	423.9	375.4	344.9	327.3
50°	691.8	795.8	876.1	863.7	714.4	558.1	446.5	381.5	341.1	317.5	299.3
52.5°	639.9	740.7	810.3	774.7	631.7	491.2	399.2	344.6	311.1	290.6	274.3
55°	564.4	653.8	702.9	649.0	515.3	408.5	337.2	294.5	269.5	252.1	238.2
57.5°	490.1	564.0	594.8	532.2	424.4	338.7	285.3	253.2	228.4	215.9	208.7
60°	443.6	506.6	528.3	459.0	369.0	296.3	252.6	222.7	204.4	196.3	189.1
62.5°	397.8	449.3	458.3	394.7	321.7	259.4	221.8	196.6	184.5	176.6	169.8
65°	330.1	367.1	362.8	311.8	254.5	205.9	178.5	163.1	153.9	142.9	130.8
67.5°	271.7	294.4	280.7	242.5	194.3	160.0	142.1	130.4	119.1	108.7	105.8
70°	234.8	247.8	233.4	198.2	159.3	134.2	119.8	105.8	99.2	96.7	92.4
72.5°	199.3	203.9	188.3	158.2	129.6	111.1	97.1	89.3	85.7	83.6	80.9
75°	149.7	146.3	132.8	109.2	90.0	77.5	73.1	70.2	67.9	65.9	64.5
77.5°	105.1	100.2	88.1	72.8	62.7	56.6	54.1	52.5	51.4	50.4	49.0
80°	78.9	75.5	63.5	51.9	47.6	44.8	43.3	41.4	41.4	40.4	38.9
82.5°	57.8	54.0	43.5	38.1	35.7	33.9	32.9	31.8	31.4	31.6	30.5
85°	30.3	24.5	21.7	20.6	19.2	18.3	18.8	17.8	17.8	17.8	17.3
87.5°	10.3	9.1	9.5	9.9	11.3	12.7	13.7	15.1	16.9	16.4	16.6
90°	5.2	9.0	12.8	16.6	22.0	28.9	35.8	42.8	49.8	49.1	48.4
92.5°	28.1	30.8	33.6	36.4	38.6	40.2	41.9	43.5	45.1	45.3	45.4
95°	77.0	80.2	83.3	86.5	88.4	89.1	89.6	90.3	91.0	91.0	91.0
97.5°	137.8	140.5	143.4	146.1	148.1	149.3	150.5	151.7	152.9	152.9	152.9
100°	182.9	185.5	188.0	190.6	192.3	193.2	194.2	195.1	196.0	196.0	196.0
102.5°	230.3	232.2	234.2	236.3	237.9	239.1	240.3	241.5	242.7	243.0	243.2
105°	306.4	307.4	308.3	309.2	310.1	310.8	311.3	312.0	312.6	313.2	313.9
107.5°	384.7	386.2	387.6	388.9	389.6	389.6	389.6	389.6	389.6	389.8	390.1
110°	435.3	437.2	439.0	440.9	442.0	442.0	442.0	442.0	442.0	442.0	442.0





TEST NUMBER: P331822-830

CATALOG NUMBER: S122RDIW-S675D1440U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	489.8	491.7	493.6	495.5	496.3	496.1	495.9	495.6	495.3	494.6	493.8
115°	570.2	572.1	574.1	576.0	576.6	576.0	575.3	574.7	574.1	573.7	573.4
117.5°	651.0	653.6	656.1	658.6	659.0	657.2	655.4	653.7	652.0	651.2	650.4
120°	704.5	707.0	709.5	712.1	712.1	709.5	707.0	704.5	701.9	701.9	701.9
122.5°	753.8	756.9	759.9	763.0	763.6	761.9	760.1	758.3	756.5	755.7	755.0
125°	829.8	832.6	835.5	838.4	839.3	838.4	837.4	836.5	835.5	834.5	833.6
127.5°	904.7	908.3	912.0	915.6	916.8	915.7	914.5	913.4	912.3	911.1	909.9
130°	951.9	956.0	960.1	964.2	965.9	965.3	964.7	964.0	963.4	962.8	962.1
132.5°	1003.4	1006.7	1010.1	1013.4	1015.2	1015.3	1015.4	1015.6	1015.7	1014.3	1013.0
135°	1073.5	1076.9	1080.3	1083.8	1085.9	1086.6	1087.2	1087.8	1088.4	1088.2	1087.8
137.5°	1146.4	1149.2	1152.1	1154.9	1156.8	1157.6	1158.4	1159.2	1160.1	1159.8	1159.5
140°	1190.7	1193.6	1196.5	1199.3	1201.5	1203.1	1204.7	1206.3	1207.8	1207.8	1207.8
142.5°	1236.2	1239.1	1241.9	1244.7	1246.7	1247.7	1248.9	1249.9	1251.0	1251.2	1251.5
145°	1301.0	1303.2	1305.3	1307.6	1309.7	1311.5	1313.4	1315.3	1317.2	1317.5	1317.9
147.5°	1359.6	1362.3	1365.0	1367.6	1369.6	1370.8	1372.1	1373.4	1374.6	1375.4	1376.0
150°	1398.6	1400.6	1402.5	1404.4	1405.9	1407.2	1408.4	1409.8	1411.0	1411.9	1412.9
152.5°	1433.9	1435.8	1437.7	1439.6	1441.3	1442.8	1444.4	1445.9	1447.4	1448.6	1449.7
155°	1485.8	1486.8	1487.7	1488.7	1489.6	1490.5	1491.5	1492.4	1493.4	1495.0	1496.6
157.5°	1530.7	1531.3	1532.0	1532.6	1533.2	1533.8	1534.4	1534.9	1535.5	1537.6	1539.7
160°	1558.0	1558.6	1559.2	1559.9	1560.4	1560.7	1560.9	1561.3	1561.6	1563.5	1565.4
162.5°	1582.5	1582.6	1582.7	1582.9	1583.1	1583.4	1583.8	1584.0	1584.3	1586.5	1588.7
165°	1615.3	1615.0	1614.7	1614.4	1614.2	1614.2	1614.2	1614.2	1614.2	1616.4	1618.6
167.5°	1642.5	1641.5	1640.6	1639.6	1639.2	1639.1	1639.1	1639.0	1638.9	1641.2	1643.3
170°	1657.3	1656.3	1655.4	1654.4	1653.8	1653.5	1653.2	1652.8	1652.6	1654.7	1657.0
172.5°	1667.5	1666.6	1665.7	1664.7	1664.1	1663.8	1663.4	1663.1	1662.7	1665.0	1667.2
175°	1680.0	1679.0	1678.1	1677.2	1676.4	1675.7	1675.1	1674.5	1673.9	1676.1	1678.3
177.5°	1685.4	1684.6	1683.9	1683.1	1682.4	1681.9	1681.4	1680.9	1680.4	1681.9	1683.5
180°	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9



TEST NUMBER: P331822-830

CATALOG NUMBER: S122RDIW-S675D1440U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7
2.5°	1433.1	1438.1	1440.5	1440.5	1443.2	1442.0	1440.9
5°	1515.5	1524.7	1526.6	1535.3	1541.5	1539.5	1540.6
7.5°	1597.4	1612.1	1626.6	1633.3	1634.4	1638.2	1639.6
10°	1647.8	1659.9	1682.5	1679.1	1695.9	1705.6	1689.7
12.5°	1696.4	1712.6	1728.2	1732.6	1742.2	1745.2	1739.0
15°	1740.2	1748.9	1749.8	1747.5	1750.3	1747.9	1738.8
17.5°	1699.2	1685.2	1656.7	1643.2	1632.6	1616.7	1610.4
20°	1631.4	1590.1	1542.0	1522.8	1500.2	1455.9	1466.5
22.5°	1485.3	1438.0	1390.0	1333.8	1306.9	1265.0	1262.4
25°	1257.6	1176.4	1086.8	1024.4	987.8	945.9	927.7
27.5°	977.8	875.4	802.1	765.0	731.2	698.0	696.6
30°	793.8	716.9	660.1	628.4	607.7	593.7	596.6
32.5°	669.1	616.4	578.2	551.8	536.5	525.9	525.8
35°	547.1	511.0	486.4	475.3	464.3	456.6	457.0
37.5°	468.2	446.5	432.8	420.6	413.7	409.9	407.8
40°	427.7	409.9	399.4	392.1	386.3	381.1	380.1
42.5°	395.8	381.1	370.4	364.8	359.4	355.6	354.7
45°	351.2	339.2	329.6	323.3	320.9	317.5	317.5
47.5°	312.5	300.6	293.1	289.2	285.0	282.8	282.7
50°	286.3	277.1	270.4	268.0	264.6	263.2	262.7
52.5°	262.8	256.0	251.2	249.5	248.1	246.2	246.6
55°	230.9	227.1	225.2	223.8	221.3	218.4	220.4
57.5°	204.1	200.9	195.7	191.1	188.9	186.9	187.7
60°	185.2	178.5	171.7	166.5	165.0	160.7	160.7
62.5°	161.4	151.9	143.6	140.7	139.2	137.2	136.9
65°	124.1	120.3	118.4	116.4	115.5	115.5	114.5
67.5°	102.8	101.3	99.2	98.7	97.7	97.5	97.2
70°	91.0	89.0	88.0	87.6	86.6	87.1	85.7
72.5°	79.4	77.9	77.7	76.4	75.8	75.9	74.8
75°	62.6	62.6	62.0	61.5	60.6	60.1	60.6
77.5°	48.1	48.2	47.3	47.2	47.1	47.2	46.8
80°	38.5	38.9	38.5	38.0	37.5	38.0	37.5
82.5°	30.4	29.7	29.6	29.5	29.4	29.1	29.0
85°	17.3	17.8	17.3	16.9	16.9	16.9	17.3
87.5°	16.1	16.0	15.9	16.0	16.1	16.1	15.8
90°	47.9	47.2	47.0	47.4	47.7	48.0	48.4
92.5°	45.5	45.7	45.8	45.8	45.9	46.0	46.0
95°	91.0	91.0	90.6	90.0	89.4	88.7	88.1
97.5°	152.9	152.9	152.9	152.8	152.7	152.7	152.6
100°	196.0	196.0	196.0	195.6	195.3	195.0	194.6
102.5°	243.5	243.7	243.6	243.4	243.1	242.7	242.4
105°	314.5	315.1	315.5	315.5	315.5	315.5	315.5
107.5°	390.4	390.6	390.0	388.6	387.1	385.7	384.2
110°	442.0	442.0	441.4	440.5	439.5	438.6	437.6



TEST NUMBER: P331822-830

CATALOG NUMBER: S122RDIW-S675D1440U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	493.0	492.3	491.5	490.9	490.2	489.5	488.8
115°	573.1	572.8	572.1	571.2	570.2	569.3	568.4
117.5°	649.7	648.9	648.0	647.1	646.1	645.2	644.2
120°	701.9	701.9	701.4	700.5	699.6	698.6	697.7
122.5°	754.2	753.5	752.7	752.1	751.4	750.6	750.0
125°	832.6	831.7	831.1	830.8	830.5	830.2	829.8
127.5°	908.8	907.7	906.6	905.6	904.6	903.6	902.6
130°	961.5	960.8	959.9	958.7	957.4	956.1	954.9
132.5°	1011.5	1010.1	1008.9	1008.0	1006.9	1005.9	1004.8
135°	1087.5	1087.2	1086.6	1085.6	1084.7	1083.7	1082.8
137.5°	1159.3	1159.0	1158.3	1157.1	1155.7	1154.5	1153.2
140°	1207.8	1207.8	1207.2	1205.9	1204.7	1203.3	1202.1
142.5°	1251.8	1252.0	1251.5	1250.3	1249.0	1247.7	1246.4
145°	1318.1	1318.4	1318.0	1316.7	1315.5	1314.2	1313.0
147.5°	1376.7	1377.4	1377.1	1375.9	1374.7	1373.6	1372.3
150°	1413.8	1414.8	1414.8	1413.8	1412.9	1411.9	1411.0
152.5°	1451.0	1452.2	1452.2	1451.0	1449.7	1448.6	1447.4
155°	1498.2	1499.7	1500.1	1499.1	1498.2	1497.2	1496.3
157.5°	1541.9	1544.1	1544.4	1542.8	1541.3	1539.8	1538.3
160°	1567.3	1569.1	1569.5	1568.2	1567.0	1565.8	1564.4
162.5°	1590.8	1592.9	1593.3	1591.8	1590.3	1588.7	1587.1
165°	1620.8	1623.1	1623.3	1621.7	1620.2	1618.6	1617.0
167.5°	1645.6	1647.8	1648.0	1646.4	1644.7	1643.1	1641.4
170°	1659.2	1661.4	1661.5	1659.6	1657.7	1655.9	1654.0
172.5°	1669.4	1671.6	1671.8	1669.9	1668.0	1666.1	1664.2
175°	1680.5	1682.7	1682.9	1680.9	1679.0	1677.2	1675.3
177.5°	1685.0	1686.5	1686.5	1685.0	1683.5	1681.9	1680.4
180°	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9	1683.9

(END OF REPORT)