

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331493-930

Luminaire Tested: **S122DIW-S290D1440U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331493-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S290D1440U930-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1440 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5680.1 lumens
Efficiency: N/A
Efficacy: 106.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331493-930

CATALOG NUMBER: S122DIW-S290D1440U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331493-930

CATALOG NUMBER: S122DIW-S290D1440U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	99	99	99	99	87	87	87	87	65	65	65	45	45	45	26	26	26	17																			
1	90	86	83	79	79	76	73	70	57	55	53	39	38	37	23	22	22	15																			
2	82	75	70	65	72	66	62	58	50	47	44	34	33	31	20	19	18	12																			
3	75	66	59	54	66	58	53	48	44	40	37	30	28	26	18	17	16	10																			
4	68	58	51	45	60	52	45	40	39	35	31	27	24	22	16	15	13	9																			
5	63	52	44	38	55	46	39	34	35	30	27	24	21	19	14	13	12	8																			
6	58	46	39	33	50	41	34	30	31	26	23	22	19	17	13	11	10	7																			
7	53	41	34	29	47	37	30	26	28	23	20	20	17	15	12	10	9	6																			
8	49	37	30	25	43	33	27	23	25	21	18	18	15	13	11	9	8	5																			
9	46	34	27	22	40	30	24	20	23	19	16	16	13	11	10	8	7	5																			
10	42	31	24	20	37	28	22	18	21	17	14	15	12	10	9	8	7	4																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6218	6218	6218
5°	6242	6152	6190
10°	6205	6091	6120
15°	6128	6011	6006
20°	6019	5893	5887
25°	5911	5747	5747
30°	5774	5614	5565
35°	5643	5452	5373
40°	5480	5292	5191
45°	5318	5133	5005
50°	5144	4968	4793
55°	4963	4777	4597
60°	4760	4543	4379
65°	4542	4317	4118
70°	4263	4036	3843
75°	3880	3718	3624
80°	3440	3347	3171
85°	2816	2668	2408



TEST NUMBER: P331493-930

CATALOG NUMBER: S122DIW-S290D1440U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	36.2	0.6
10°-20°	101.9	1.8
20°-30°	149.8	2.6
30°-40°	174.0	3.1
40°-50°	173.8	3.1
50°-60°	151.6	2.7
60°-70°	112.1	2.0
70°-80°	63.5	1.1
80°-90°	21.0	0.4
90°-100°	53.5	0.9
100°-110°	196.0	3.5
110°-120°	524.0	9.2
120°-130°	865.0	15.2
130°-140°	919.9	16.2
140°-150°	855.0	15.1
150°-160°	687.4	12.1
160°-170°	443.0	7.8
170°-180°	152.5	2.7
0°-30°	287.9	5.1
0°-40°	461.9	8.1
0°-60°	787.3	13.9
0°-90°	983.9	17.3
90°-120°	773.5	13.6
90°-150°	3413.3	60.1
90°-180°	4696.0	82.7
0°-180°	5680.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	385	385	385	385	385	
5°	385	384	380	382	382	37
15°	367	364	360	361	359	103
25°	332	329	323	323	323	153
35°	286	282	277	274	273	179
45°	233	230	225	221	219	180
55°	176	174	170	165	163	158
65°	119	117	113	110	108	118
75°	62	61	60	58	58	66
85°	15	15	14	13	13	17
90°	1	14	23	29	31	4
95°	75	40	45	51	50	92
105°	352	368	71	83	88	377
115°	667	687	715	204	95	656
125°	943	958	980	988	991	840
135°	1166	1185	1196	1206	1205	901
145°	1353	1353	1372	1379	1374	846
155°	1490	1481	1494	1500	1491	686
165°	1570	1564	1566	1574	1566	443
175°	1606	1598	1600	1607	1597	153
180°	1602	1602	1602	1602	1602	



TEST NUMBER: P331493-930

CATALOG NUMBER: S122DIW-S290D1440U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	385.1	385.1	385.1	385.1	385.1	385.1	385.1	385.1	385.1	385.1	385.1
2.5°	386.9	386.6	386.3	386.0	385.6	385.1	384.4	383.7	382.9	382.2	382.9
5°	385.1	384.8	384.5	384.2	383.8	383.3	382.4	381.5	380.5	379.6	380.3
7.5°	381.8	381.2	380.7	380.3	379.8	379.0	378.1	377.2	376.3	375.4	376.0
10°	378.5	378.0	377.4	376.8	376.2	375.4	374.5	373.5	372.5	371.5	372.1
12.5°	374.1	373.6	373.1	372.5	372.0	371.3	370.3	369.3	368.4	367.4	367.8
15°	366.6	366.2	365.7	365.2	364.7	363.9	362.8	361.7	360.7	359.6	360.0
17.5°	357.2	356.7	356.2	355.7	355.2	354.4	353.4	352.2	351.1	350.1	350.4
20°	350.3	349.8	349.4	348.9	348.4	347.6	346.4	345.3	344.1	343.0	343.2
22.5°	343.6	342.8	342.2	341.4	340.8	339.9	338.8	337.7	336.6	335.6	335.6
25°	331.8	331.2	330.5	329.9	329.2	328.2	326.8	325.4	324.0	322.6	322.8
27.5°	318.5	318.0	317.3	316.7	316.2	315.3	314.2	313.1	312.0	310.9	310.6
30°	309.7	309.0	308.3	307.7	307.0	306.1	304.8	303.6	302.3	301.1	300.8
32.5°	300.1	299.6	299.1	298.6	298.1	297.1	295.8	294.6	293.3	292.0	291.5
35°	286.3	285.4	284.6	283.8	283.0	281.9	280.6	279.3	278.0	276.6	276.1
37.5°	270.7	269.9	269.2	268.5	267.7	266.8	265.5	264.2	262.8	261.5	260.9
40°	260.0	259.3	258.7	258.0	257.4	256.4	255.0	253.7	252.4	251.1	250.4
42.5°	249.6	249.0	248.3	247.7	247.0	246.0	244.7	243.4	242.1	240.8	239.9
45°	232.9	232.4	231.8	231.2	230.6	229.8	228.5	227.3	226.1	224.8	223.9
47.5°	216.4	215.8	215.3	214.7	214.2	213.3	212.0	210.8	209.5	208.1	207.2
50°	204.8	204.4	204.0	203.6	203.2	202.4	201.2	200.1	198.9	197.8	196.7
52.5°	193.6	193.0	192.5	191.9	191.4	190.5	189.5	188.4	187.3	186.2	185.2
55°	176.3	175.8	175.3	174.8	174.3	173.6	172.6	171.6	170.6	169.7	168.6
57.5°	159.0	158.6	158.2	157.8	157.4	156.6	155.6	154.5	153.4	152.3	151.3
60°	147.4	147.1	146.8	146.4	146.1	145.4	144.2	143.1	141.9	140.7	139.8
62.5°	136.2	135.6	135.1	134.6	134.0	133.3	132.4	131.6	130.7	129.8	128.9
65°	118.9	118.4	117.9	117.4	116.9	116.3	115.4	114.6	113.8	113.0	112.2
67.5°	101.3	100.9	100.5	100.1	99.8	99.2	98.4	97.7	96.9	96.2	95.6
70°	90.3	90.0	89.7	89.4	89.0	88.5	87.8	87.1	86.3	85.5	85.0
72.5°	79.1	78.8	78.4	78.1	77.8	77.4	76.9	76.5	76.0	75.5	74.9
75°	62.2	62.0	61.9	61.7	61.6	61.3	60.9	60.4	60.0	59.6	59.1
77.5°	47.1	46.8	46.6	46.3	46.0	45.7	45.6	45.4	45.2	45.1	44.8
80°	37.0	36.9	36.9	36.8	36.7	36.6	36.4	36.3	36.1	36.0	35.7
82.5°	27.6	27.6	27.6	27.5	27.5	27.4	27.3	27.2	27.1	27.1	26.7
85°	15.2	15.1	15.0	14.9	14.8	14.8	14.7	14.6	14.5	14.4	14.2
87.5°	5.5	6.0	6.4	6.8	7.3	7.7	7.9	8.2	8.5	8.8	8.9
90°	1.1	4.0	6.8	9.7	12.5	14.9	17.0	19.1	21.1	23.2	24.5
92.5°	23.4	23.2	22.9	22.7	22.4	22.7	23.8	24.9	25.8	26.9	27.6
95°	75.3	66.9	58.4	49.9	41.3	38.0	39.8	41.6	43.5	45.2	46.5
97.5°	149.6	125.6	101.7	77.7	53.7	43.9	48.0	52.2	56.3	60.5	61.6
100°	205.2	169.9	134.6	99.3	64.0	48.6	52.9	57.3	61.7	66.1	68.2
102.5°	266.4	259.0	251.5	244.0	236.6	214.5	177.9	141.2	104.6	67.9	70.6
105°	352.5	360.2	367.9	375.7	383.4	352.1	281.8	211.4	141.0	70.8	73.5
107.5°	450.6	456.8	463.1	469.3	475.6	436.5	352.1	267.7	183.4	99.1	96.1
110°	513.7	519.1	524.5	529.9	535.3	500.8	426.3	351.9	277.4	202.9	177.2



TEST NUMBER: P331493-930

CATALOG NUMBER: S122DIW-S290D1440U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	573.1	577.8	582.6	587.4	592.2	585.4	567.0	548.6	530.2	511.8	417.8
115°	666.8	671.2	675.5	679.9	684.3	689.7	696.1	702.5	709.0	715.4	596.1
117.5°	750.5	755.4	760.3	765.2	770.1	774.7	779.1	783.6	788.0	792.5	763.6
120°	811.7	815.5	819.4	823.3	827.1	831.4	836.0	840.7	845.3	849.9	853.0
122.5°	863.6	867.7	871.8	875.9	880.0	884.5	889.5	894.5	899.6	904.7	906.5
125°	942.7	946.1	949.4	952.8	956.1	960.3	965.2	970.0	974.9	979.8	981.6
127.5°	1014.4	1018.1	1021.8	1025.5	1029.2	1032.9	1036.6	1040.2	1043.9	1047.6	1050.2
130°	1059.8	1064.0	1068.0	1072.2	1076.4	1079.8	1082.6	1085.5	1088.3	1091.1	1094.0
132.5°	1106.2	1109.7	1113.2	1116.7	1120.2	1123.4	1126.3	1129.0	1131.9	1134.7	1137.2
135°	1166.5	1170.6	1174.8	1178.8	1183.0	1186.2	1188.5	1190.8	1193.2	1195.5	1198.1
137.5°	1227.5	1230.4	1233.3	1236.2	1239.0	1241.8	1244.4	1247.1	1249.7	1252.3	1254.8
140°	1267.4	1269.4	1271.5	1273.6	1275.6	1278.1	1280.9	1283.8	1286.6	1289.4	1291.8
142.5°	1300.8	1302.6	1304.5	1306.4	1308.2	1310.8	1314.0	1317.3	1320.5	1323.7	1325.8
145°	1353.2	1352.9	1352.7	1352.4	1352.2	1354.2	1358.6	1363.0	1367.3	1371.7	1373.5
147.5°	1398.9	1397.9	1396.9	1396.0	1395.0	1396.6	1400.9	1405.3	1409.7	1414.0	1415.3
150°	1428.6	1426.8	1425.0	1423.2	1421.3	1422.5	1426.6	1430.8	1434.8	1439.0	1440.6
152.5°	1453.6	1451.6	1449.6	1447.6	1445.6	1446.5	1450.4	1454.3	1458.2	1462.2	1463.7
155°	1490.0	1487.7	1485.4	1483.0	1480.7	1481.2	1484.3	1487.4	1490.4	1493.5	1495.0
157.5°	1518.6	1516.6	1514.7	1512.7	1510.7	1510.8	1513.0	1515.2	1517.3	1519.5	1521.3
160°	1535.2	1533.7	1532.2	1530.6	1529.1	1529.1	1530.6	1532.2	1533.7	1535.2	1536.8
162.5°	1550.0	1548.6	1547.0	1545.5	1543.9	1543.8	1545.2	1546.5	1547.8	1549.2	1550.9
165°	1570.0	1568.5	1566.9	1565.4	1563.8	1563.5	1564.2	1565.0	1565.8	1566.5	1568.4
167.5°	1584.9	1583.3	1581.8	1580.2	1578.7	1578.3	1579.0	1579.7	1580.5	1581.2	1583.0
170°	1593.3	1591.7	1590.2	1588.6	1587.1	1586.5	1587.1	1587.6	1588.0	1588.6	1590.4
172.5°	1598.8	1597.3	1595.7	1594.2	1592.6	1592.1	1592.6	1593.1	1593.7	1594.2	1595.9
175°	1606.0	1604.2	1602.4	1600.6	1598.8	1598.1	1598.6	1599.1	1599.7	1600.2	1602.0
177.5°	1607.1	1605.7	1604.3	1602.8	1601.3	1600.8	1600.9	1601.2	1601.3	1601.6	1603.0
180°	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5



TEST NUMBER: P331493-930

CATALOG NUMBER: S122DIW-S290D1440U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	385.1	385.1	385.1	385.1	385.1	385.1	385.1	385.1
2.5°	383.5	384.2	384.8	385.1	385.0	384.8	384.7	384.6
5°	381.0	381.6	382.3	382.5	382.4	382.2	382.0	381.9
7.5°	376.7	377.3	378.0	378.2	378.1	377.8	377.6	377.5
10°	372.8	373.5	374.1	374.3	374.1	373.8	373.6	373.3
12.5°	368.3	368.7	369.2	369.3	369.2	368.9	368.8	368.6
15°	360.3	360.6	360.9	360.9	360.5	360.1	359.7	359.3
17.5°	350.8	351.2	351.6	351.6	351.1	350.8	350.4	350.0
20°	343.5	343.7	344.0	343.9	343.6	343.2	342.9	342.6
22.5°	335.7	335.7	335.7	335.7	335.5	335.3	335.1	334.9
25°	322.9	323.1	323.3	323.3	323.1	322.9	322.8	322.6
27.5°	310.4	310.1	309.9	309.6	309.2	308.8	308.4	308.0
30°	300.6	300.4	300.1	299.9	299.5	299.2	298.9	298.5
32.5°	291.1	290.6	290.2	289.8	289.4	289.1	288.8	288.5
35°	275.7	275.2	274.7	274.3	273.9	273.5	273.0	272.6
37.5°	260.2	259.7	259.0	258.5	258.1	257.7	257.4	257.0
40°	249.6	248.9	248.2	247.6	247.3	247.0	246.6	246.3
42.5°	239.1	238.3	237.5	236.8	236.4	235.9	235.5	235.1
45°	223.0	222.1	221.2	220.5	220.2	219.9	219.6	219.2
47.5°	206.3	205.3	204.3	203.6	203.2	202.7	202.2	201.7
50°	195.5	194.3	193.1	192.4	192.0	191.6	191.2	190.8
52.5°	184.3	183.4	182.4	181.6	181.1	180.6	180.0	179.4
55°	167.6	166.6	165.7	165.0	164.6	164.1	163.7	163.3
57.5°	150.3	149.4	148.4	147.7	147.5	147.2	146.8	146.5
60°	138.9	138.0	137.1	136.6	136.3	136.1	135.8	135.6
62.5°	128.1	127.3	126.5	125.9	125.6	125.2	124.9	124.6
65°	111.5	110.7	110.0	109.4	109.0	108.6	108.2	107.8
67.5°	95.1	94.5	93.9	93.4	93.1	92.8	92.5	92.1
70°	84.4	83.8	83.2	82.8	82.5	82.1	81.8	81.4
72.5°	74.4	73.8	73.2	72.7	72.5	72.2	72.0	71.7
75°	58.6	58.1	57.6	57.5	57.6	57.8	58.0	58.1
77.5°	44.6	44.4	44.1	43.9	43.6	43.5	43.2	43.0
80°	35.5	35.2	35.0	34.7	34.6	34.4	34.2	34.1
82.5°	26.4	26.1	25.8	25.6	25.6	25.5	25.5	25.5
85°	13.9	13.7	13.5	13.3	13.2	13.1	13.0	13.0
87.5°	8.9	9.0	9.0	9.0	9.1	9.1	9.2	9.2
90°	25.8	27.1	28.4	29.3	29.8	30.2	30.8	31.3
92.5°	28.2	28.9	29.6	30.1	30.4	30.7	31.0	31.3
95°	47.8	49.1	50.4	50.9	50.6	50.4	50.1	49.9
97.5°	62.6	63.6	64.7	65.3	65.6	66.0	66.3	66.5
100°	70.2	72.3	74.4	75.7	76.1	76.6	77.2	77.7
102.5°	73.3	76.0	78.7	80.4	81.1	81.8	82.5	83.2
105°	76.4	79.2	82.1	84.0	85.0	86.1	87.1	88.1
107.5°	93.3	90.3	87.5	86.6	87.6	88.6	89.7	90.7
110°	151.4	125.6	99.9	87.5	88.5	89.5	90.6	91.6



TEST NUMBER: P331493-930

CATALOG NUMBER: S122DIW-S290D1440U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	323.8	229.8	135.8	89.2	90.1	90.9	91.7	92.5
115°	476.9	357.5	238.2	169.3	150.7	132.2	113.7	95.1
117.5°	734.7	705.9	677.0	632.1	571.1	510.1	449.1	388.2
120°	856.1	859.2	862.3	846.4	811.7	776.9	742.1	707.4
122.5°	908.4	910.3	912.1	909.6	902.9	896.2	889.4	882.6
125°	983.4	985.2	987.0	988.3	989.1	989.9	990.7	991.4
127.5°	1052.8	1055.4	1058.0	1059.5	1059.6	1059.7	1059.9	1060.1
130°	1096.8	1099.7	1102.4	1103.8	1103.5	1103.3	1103.0	1102.7
132.5°	1139.5	1142.0	1144.4	1145.5	1145.3	1145.0	1144.8	1144.4
135°	1200.6	1203.2	1205.8	1206.8	1206.3	1205.8	1205.3	1204.8
137.5°	1257.4	1259.9	1262.4	1263.2	1262.3	1261.5	1260.6	1259.7
140°	1294.0	1296.4	1298.7	1299.2	1298.0	1296.7	1295.3	1294.0
142.5°	1328.0	1330.1	1332.2	1332.6	1331.3	1330.0	1328.8	1327.5
145°	1375.3	1377.1	1379.0	1379.2	1377.9	1376.6	1375.3	1374.1
147.5°	1416.7	1418.0	1419.4	1419.4	1418.4	1417.3	1416.2	1415.1
150°	1442.1	1443.7	1445.2	1445.3	1444.1	1442.8	1441.4	1440.1
152.5°	1465.3	1466.8	1468.4	1468.3	1466.6	1464.9	1463.2	1461.5
155°	1496.6	1498.1	1499.7	1499.4	1497.4	1495.3	1493.2	1491.2
157.5°	1523.0	1524.7	1526.5	1526.3	1524.4	1522.3	1520.3	1518.3
160°	1538.3	1539.9	1541.4	1541.3	1539.5	1537.7	1535.9	1534.1
162.5°	1552.7	1554.4	1556.2	1555.9	1553.7	1551.5	1549.3	1547.1
165°	1570.2	1572.0	1573.8	1573.8	1572.0	1570.2	1568.4	1566.5
167.5°	1584.8	1586.6	1588.4	1588.1	1585.8	1583.5	1581.2	1578.8
170°	1592.2	1594.0	1595.8	1595.5	1593.3	1590.9	1588.6	1586.2
172.5°	1597.7	1599.5	1601.3	1601.1	1598.8	1596.4	1594.2	1591.8
175°	1603.8	1605.6	1607.4	1607.0	1604.4	1601.8	1599.3	1596.7
177.5°	1604.4	1605.9	1607.4	1607.1	1605.2	1603.4	1601.6	1599.7
180°	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5

(END OF REPORT)