

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331577-930

Luminaire Tested: **S122DIW-S865D1240U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331577-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIW-S865D1240U930-4F0-1E-UDD-F  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1240 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6905.0 lumens  
Efficiency: N/A  
Efficacy: 98.9 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 69.8  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331577-930

CATALOG NUMBER: S122DIW-S865D1240U930-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P331577-930

CATALOG NUMBER: S122DIW-S865D1240U930-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	48	48	48	42
1	96	92	88	84	87	84	80	77	69	67	64	55	54	52	43	42	41	35
2	87	80	74	69	79	73	68	64	60	57	53	48	46	44	38	36	34	29
3	80	70	63	57	72	64	58	53	53	49	45	43	40	37	33	31	29	25
4	73	62	54	48	66	57	50	45	47	42	38	38	35	32	30	27	25	21
5	67	55	47	41	61	51	44	39	42	37	33	34	30	27	27	24	22	18
6	61	50	42	36	56	46	39	33	38	33	29	31	27	24	24	21	19	16
7	57	45	37	31	52	41	34	29	34	29	25	28	24	21	22	19	17	14
8	53	41	33	28	48	37	31	26	31	26	22	26	22	19	20	17	15	13
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	15	13	11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	18166	18166	18166
5°	18235	17973	18078
10°	18126	17790	17879
15°	17904	17560	17541
20°	17584	17213	17194
25°	17268	16787	16787
30°	16861	16397	16257
35°	16484	15928	15693
40°	16008	15460	15163
45°	15536	14995	14625
50°	15028	14511	13996
55°	14494	13948	13430
60°	13905	13275	12788
65°	13268	12607	12027
70°	12463	11797	11235
75°	11335	10861	10593
80°	10060	9754	9252
85°	8225	7818	7003



TEST NUMBER: P331577-930

CATALOG NUMBER: S122DIW-S865D1240U930-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	105.8	1.5
10°-20°	297.7	4.3
20°-30°	437.6	6.3
30°-40°	508.3	7.4
40°-50°	507.7	7.4
50°-60°	442.8	6.4
60°-70°	327.4	4.7
70°-80°	185.4	2.7
80°-90°	53.2	0.8
90°-100°	46.0	0.7
100°-110°	168.6	2.4
110°-120°	450.7	6.5
120°-130°	744.0	10.8
130°-140°	791.2	11.5
140°-150°	735.4	10.6
150°-160°	591.2	8.6
160°-170°	381.0	5.5
170°-180°	131.1	1.9
0°-30°	841.1	12.2
0°-40°	1349.3	19.5
0°-60°	2299.8	33.3
0°-90°	2865.9	41.5
90°-120°	665.3	9.6
90°-150°	2935.8	42.5
90°-180°	4039.0	58.5
0°-180°	6905.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1125	1125	1125	1125	1125	
5°	1125	1120	1109	1117	1115	107
15°	1071	1064	1050	1054	1049	301
25°	969	960	942	944	942	446
35°	836	825	808	802	796	522
45°	680	672	657	645	640	525
55°	515	508	496	483	477	460
65°	347	341	330	320	315	343
75°	182	179	174	168	170	194
85°	44	43	42	39	38	51
90°	1	12	20	25	27	5
95°	65	34	39	44	43	79
105°	303	316	61	71	76	324
115°	574	591	615	175	82	564
125°	811	824	843	850	853	723
135°	1003	1019	1028	1038	1036	775
145°	1164	1164	1180	1186	1182	728
155°	1282	1274	1285	1290	1282	590
165°	1350	1345	1347	1354	1347	381
175°	1381	1375	1376	1382	1373	131
180°	1378	1378	1378	1378	1378	



TEST NUMBER: P331577-930

CATALOG NUMBER: S122DIW-S865D1240U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1
2.5°	1130.3	1129.4	1128.4	1127.5	1126.5	1124.9	1122.8	1120.7	1118.6	1116.5	1118.4
5°	1125.1	1124.1	1123.2	1122.3	1121.3	1119.5	1116.9	1114.2	1111.6	1108.9	1110.8
7.5°	1115.2	1113.7	1112.2	1110.7	1109.2	1107.1	1104.4	1101.7	1099.0	1096.3	1098.3
10°	1105.6	1104.0	1102.3	1100.6	1098.9	1096.7	1093.7	1090.9	1088.0	1085.1	1087.0
12.5°	1092.7	1091.2	1089.7	1088.2	1086.7	1084.5	1081.7	1078.7	1075.9	1073.0	1074.3
15°	1071.1	1069.6	1068.1	1066.7	1065.3	1063.0	1059.9	1056.7	1053.6	1050.5	1051.4
17.5°	1043.3	1041.9	1040.5	1039.0	1037.5	1035.3	1032.1	1028.9	1025.7	1022.5	1023.7
20°	1023.4	1022.0	1020.6	1019.1	1017.7	1015.3	1011.9	1008.5	1005.2	1001.8	1002.5
22.5°	1003.6	1001.5	999.5	997.4	995.5	992.9	989.7	986.5	983.3	980.2	980.3
25°	969.3	967.4	965.5	963.6	961.6	958.6	954.6	950.5	946.4	942.3	942.8
27.5°	930.4	928.7	926.9	925.2	923.5	921.0	917.8	914.5	911.3	908.1	907.4
30°	904.4	902.5	900.6	898.7	896.7	894.0	890.4	886.8	883.1	879.5	878.8
32.5°	876.8	875.2	873.7	872.1	870.6	867.9	864.1	860.3	856.6	852.7	851.4
35°	836.3	833.9	831.4	829.1	826.6	823.5	819.7	815.9	812.0	808.1	806.7
37.5°	790.6	788.5	786.4	784.2	782.2	779.2	775.3	771.5	767.6	763.8	762.0
40°	759.5	757.6	755.6	753.7	751.8	748.9	745.0	741.2	737.4	733.5	731.3
42.5°	729.2	727.2	725.3	723.4	721.5	718.6	714.8	710.9	707.0	703.2	700.8
45°	680.4	678.8	677.1	675.5	673.8	671.1	667.5	663.9	660.3	656.7	654.0
47.5°	632.0	630.5	628.8	627.3	625.7	623.0	619.2	615.5	611.7	608.0	605.2
50°	598.3	597.0	595.9	594.7	593.5	591.2	587.8	584.4	581.1	577.7	574.4
52.5°	565.4	563.8	562.2	560.6	559.1	556.7	553.5	550.3	547.1	544.0	541.2
55°	514.9	513.6	512.1	510.6	509.2	507.0	504.2	501.2	498.4	495.5	492.6
57.5°	464.3	463.2	462.0	460.9	459.7	457.5	454.4	451.2	448.0	444.8	442.1
60°	430.6	429.6	428.7	427.7	426.7	424.6	421.2	417.8	414.5	411.1	408.5
62.5°	397.7	396.2	394.6	393.1	391.5	389.5	386.9	384.3	381.6	379.1	376.7
65°	347.3	345.8	344.4	342.9	341.5	339.6	337.2	334.8	332.4	330.0	327.8
67.5°	296.0	294.8	293.7	292.5	291.4	289.8	287.6	285.4	283.2	281.0	279.4
70°	264.0	263.0	262.0	261.1	260.2	258.5	256.4	254.2	252.1	249.9	248.3
72.5°	231.1	230.2	229.2	228.2	227.2	226.1	224.7	223.3	221.8	220.5	218.8
75°	181.7	181.2	180.8	180.3	179.9	179.0	177.8	176.6	175.4	174.1	172.8
77.5°	137.6	136.8	136.0	135.2	134.4	133.7	133.2	132.7	132.2	131.8	131.0
80°	108.2	107.9	107.7	107.5	107.2	106.9	106.4	105.9	105.4	104.9	104.2
82.5°	80.5	80.5	80.4	80.3	80.3	80.1	79.8	79.6	79.2	79.0	78.0
85°	44.4	44.1	43.9	43.6	43.4	43.1	42.9	42.6	42.4	42.2	41.5
87.5°	15.8	15.9	16.0	16.1	16.2	16.2	16.2	16.1	16.1	16.1	15.7
90°	1.0	3.4	5.9	8.3	10.8	12.9	14.6	16.4	18.2	20.0	21.0
92.5°	20.1	19.9	19.7	19.5	19.2	19.6	20.5	21.4	22.3	23.2	23.7
95°	64.8	57.5	50.2	42.9	35.5	32.7	34.2	35.8	37.3	38.9	40.0
97.5°	128.7	108.0	87.4	66.9	46.2	37.7	41.3	44.8	48.5	52.1	52.9
100°	176.5	146.2	115.8	85.4	55.1	41.7	45.6	49.3	53.1	56.8	58.6
102.5°	229.2	222.7	216.3	209.9	203.5	184.5	153.0	121.5	89.9	58.5	60.7
105°	303.2	309.8	316.5	323.1	329.8	302.9	242.4	181.8	121.3	60.8	63.3
107.5°	387.6	392.9	398.3	403.7	409.0	375.4	302.9	230.3	157.8	85.2	82.7
110°	441.8	446.5	451.1	455.8	460.4	430.7	366.7	302.6	238.6	174.6	152.4



TEST NUMBER: P331577-930

CATALOG NUMBER: S122DIW-S865D1240U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	492.8	497.0	501.1	505.2	509.4	503.5	487.7	471.9	456.1	440.2	359.4
115°	573.5	577.2	581.0	584.7	588.6	593.2	598.8	604.3	609.8	615.4	512.7
117.5°	645.5	649.7	653.9	658.1	662.3	666.3	670.1	673.9	677.8	681.6	656.7
120°	698.1	701.5	704.7	708.1	711.4	715.1	719.1	723.1	727.1	731.0	733.7
122.5°	742.8	746.3	749.8	753.3	756.8	760.8	765.1	769.4	773.8	778.1	779.7
125°	810.8	813.7	816.6	819.5	822.3	825.9	830.1	834.3	838.5	842.8	844.3
127.5°	872.5	875.6	878.8	882.1	885.3	888.4	891.5	894.7	897.8	901.0	903.3
130°	911.6	915.1	918.7	922.2	925.8	928.7	931.2	933.6	936.0	938.5	940.9
132.5°	951.5	954.5	957.5	960.5	963.5	966.2	968.7	971.1	973.5	976.0	978.0
135°	1003.3	1006.8	1010.4	1013.9	1017.5	1020.3	1022.2	1024.3	1026.2	1028.3	1030.5
137.5°	1055.7	1058.3	1060.7	1063.2	1065.7	1068.0	1070.3	1072.6	1074.8	1077.1	1079.3
140°	1090.1	1091.8	1093.6	1095.4	1097.1	1099.3	1101.7	1104.2	1106.6	1109.1	1111.0
142.5°	1118.8	1120.4	1122.0	1123.6	1125.2	1127.4	1130.2	1132.9	1135.7	1138.6	1140.4
145°	1163.8	1163.7	1163.4	1163.2	1163.0	1164.7	1168.6	1172.3	1176.1	1179.8	1181.4
147.5°	1203.1	1202.3	1201.5	1200.6	1199.8	1201.3	1204.9	1208.7	1212.4	1216.1	1217.3
150°	1228.7	1227.2	1225.6	1224.0	1222.5	1223.5	1227.0	1230.6	1234.1	1237.7	1239.0
152.5°	1250.3	1248.5	1246.8	1245.0	1243.3	1244.1	1247.5	1250.9	1254.3	1257.6	1259.0
155°	1281.6	1279.5	1277.6	1275.5	1273.6	1273.9	1276.6	1279.2	1281.9	1284.6	1285.9
157.5°	1306.1	1304.4	1302.7	1301.1	1299.3	1299.4	1301.3	1303.2	1305.0	1306.9	1308.4
160°	1320.5	1319.2	1317.8	1316.5	1315.2	1315.2	1316.5	1317.8	1319.2	1320.5	1321.8
162.5°	1333.3	1331.9	1330.6	1329.3	1327.9	1327.8	1328.9	1330.1	1331.3	1332.4	1333.9
165°	1350.4	1349.1	1347.7	1346.4	1345.1	1344.8	1345.4	1346.1	1346.7	1347.4	1348.9
167.5°	1363.2	1361.8	1360.5	1359.2	1357.8	1357.5	1358.1	1358.7	1359.3	1359.9	1361.5
170°	1370.4	1369.0	1367.7	1366.4	1365.0	1364.6	1365.0	1365.5	1365.9	1366.4	1367.9
172.5°	1375.1	1373.8	1372.5	1371.1	1369.8	1369.4	1369.8	1370.2	1370.7	1371.1	1372.6
175°	1381.3	1379.7	1378.2	1376.6	1375.1	1374.5	1375.0	1375.4	1375.9	1376.3	1377.9
177.5°	1382.3	1381.0	1379.8	1378.6	1377.3	1376.8	1377.0	1377.1	1377.3	1377.5	1378.8
180°	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3



TEST NUMBER: P331577-930

CATALOG NUMBER: S122DIW-S865D1240U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1
2.5°	1120.3	1122.3	1124.1	1124.9	1124.5	1124.1	1123.8	1123.4
5°	1112.7	1114.7	1116.6	1117.3	1116.9	1116.4	1115.9	1115.4
7.5°	1100.2	1102.1	1104.1	1104.7	1104.2	1103.7	1103.2	1102.6
10°	1088.9	1090.9	1092.8	1093.4	1092.7	1091.9	1091.2	1090.5
12.5°	1075.7	1077.0	1078.4	1078.8	1078.2	1077.7	1077.2	1076.7
15°	1052.4	1053.4	1054.3	1054.2	1053.0	1051.8	1050.6	1049.4
17.5°	1024.7	1025.9	1027.0	1027.0	1025.8	1024.7	1023.5	1022.4
20°	1003.2	1004.0	1004.7	1004.5	1003.6	1002.7	1001.7	1000.7
22.5°	980.5	980.6	980.7	980.6	979.9	979.3	978.8	978.2
25°	943.3	943.7	944.2	944.2	943.7	943.3	942.8	942.3
27.5°	906.7	906.0	905.2	904.3	903.1	902.0	900.8	899.7
30°	878.1	877.4	876.7	875.8	874.9	873.9	872.9	872.0
32.5°	850.1	848.8	847.5	846.4	845.5	844.5	843.5	842.5
35°	805.3	803.8	802.4	801.0	799.9	798.7	797.4	796.2
37.5°	760.3	758.5	756.7	755.2	754.1	752.9	751.8	750.6
40°	729.2	727.0	724.9	723.3	722.4	721.4	720.4	719.4
42.5°	698.5	696.1	693.8	691.9	690.6	689.3	687.9	686.6
45°	651.4	648.7	646.1	644.3	643.4	642.4	641.4	640.5
47.5°	602.4	599.7	596.9	594.8	593.4	592.0	590.6	589.2
50°	571.0	567.6	564.3	562.0	560.8	559.5	558.4	557.2
52.5°	538.3	535.6	532.8	530.6	529.0	527.4	525.9	524.2
55°	489.8	486.8	484.0	481.9	480.7	479.5	478.3	477.1
57.5°	439.2	436.3	433.5	431.6	430.7	429.8	428.9	428.0
60°	405.9	403.2	400.6	398.8	398.1	397.4	396.6	396.0
62.5°	374.1	371.7	369.2	367.6	366.6	365.7	364.8	363.9
65°	325.6	323.5	321.3	319.6	318.5	317.2	316.0	314.8
67.5°	277.7	276.0	274.3	273.0	272.1	271.1	270.1	269.1
70°	246.5	244.8	243.2	241.8	240.9	239.9	239.0	238.0
72.5°	217.1	215.4	213.8	212.5	211.7	211.0	210.2	209.5
75°	171.3	169.8	168.4	168.0	168.4	168.9	169.3	169.8
77.5°	130.4	129.6	128.9	128.2	127.5	126.9	126.2	125.5
80°	103.5	102.8	102.1	101.4	100.9	100.5	100.0	99.5
82.5°	77.1	76.2	75.3	74.8	74.7	74.6	74.5	74.4
85°	40.8	40.0	39.3	38.8	38.6	38.3	38.1	37.8
87.5°	15.4	15.0	14.7	14.4	14.3	14.3	14.1	14.0
90°	22.2	23.2	24.4	25.2	25.6	26.0	26.5	26.9
92.5°	24.3	24.9	25.4	25.8	26.1	26.4	26.7	26.9
95°	41.1	42.2	43.3	43.8	43.5	43.3	43.1	42.9
97.5°	53.8	54.7	55.6	56.2	56.4	56.7	57.0	57.2
100°	60.4	62.1	63.9	65.1	65.5	66.0	66.4	66.9
102.5°	63.0	65.4	67.7	69.1	69.7	70.4	71.0	71.6
105°	65.7	68.2	70.6	72.2	73.1	74.0	74.9	75.8
107.5°	80.2	77.7	75.3	74.4	75.3	76.2	77.1	78.0
110°	130.2	108.0	85.9	75.3	76.1	77.0	77.9	78.8





TEST NUMBER: P331577-930

CATALOG NUMBER: S122DIW-S865D1240U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	278.5	197.7	116.8	76.7	77.5	78.2	78.8	79.6
115°	410.1	307.5	204.9	145.6	129.6	113.7	97.8	81.8
117.5°	631.9	607.1	582.3	543.6	491.2	438.8	386.4	333.9
120°	736.4	739.0	741.7	728.1	698.1	668.2	638.3	608.4
122.5°	781.3	782.9	784.5	782.4	776.6	770.8	765.0	759.1
125°	845.9	847.4	849.0	850.0	850.7	851.4	852.1	852.7
127.5°	905.5	907.8	910.0	911.3	911.3	911.5	911.6	911.7
130°	943.4	945.8	948.2	949.3	949.1	948.9	948.7	948.4
132.5°	980.2	982.2	984.3	985.2	985.0	984.8	984.6	984.4
135°	1032.7	1034.9	1037.1	1038.0	1037.5	1037.1	1036.7	1036.2
137.5°	1081.4	1083.6	1085.8	1086.5	1085.7	1085.0	1084.3	1083.5
140°	1113.0	1115.0	1117.0	1117.4	1116.3	1115.2	1114.1	1113.0
142.5°	1142.2	1144.0	1145.8	1146.1	1145.1	1143.9	1142.8	1141.7
145°	1182.9	1184.5	1186.0	1186.3	1185.1	1184.1	1182.9	1181.9
147.5°	1218.5	1219.6	1220.7	1220.8	1219.9	1219.0	1218.1	1217.2
150°	1240.3	1241.7	1243.0	1243.1	1242.0	1240.9	1239.7	1238.7
152.5°	1260.3	1261.6	1263.0	1262.9	1261.4	1260.0	1258.5	1257.0
155°	1287.2	1288.6	1289.9	1289.6	1287.8	1286.1	1284.3	1282.5
157.5°	1309.9	1311.4	1313.0	1312.8	1311.1	1309.4	1307.7	1305.9
160°	1323.1	1324.5	1325.8	1325.7	1324.1	1322.6	1321.0	1319.5
162.5°	1335.5	1336.9	1338.5	1338.2	1336.4	1334.4	1332.5	1330.6
165°	1350.5	1352.0	1353.6	1353.6	1352.0	1350.5	1348.9	1347.4
167.5°	1363.0	1364.6	1366.1	1366.0	1363.9	1362.0	1359.9	1358.0
170°	1369.5	1371.0	1372.6	1372.3	1370.4	1368.3	1366.4	1364.3
172.5°	1374.2	1375.7	1377.3	1377.1	1375.1	1373.1	1371.1	1369.1
175°	1379.4	1381.0	1382.5	1382.2	1380.0	1377.8	1375.5	1373.3
177.5°	1380.0	1381.2	1382.5	1382.3	1380.7	1379.1	1377.5	1375.9
180°	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3

(END OF REPORT)