

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331578-930

Luminaire Tested: **S122DIW-S865D1240U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331578-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S865D1240U930-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1240 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6370.3 lumens
Efficiency: N/A
Efficacy: 91.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 69.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331578-930

CATALOG NUMBER: S122DIW-S865D1240U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331578-930

CATALOG NUMBER: S122DIW-S865D1240U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	81	81	81	65	65	65	52	52	52	45
1	97	92	88	85	88	85	81	78	71	68	66	58	56	54	46	44	43	38
2	88	81	75	69	80	74	69	64	62	58	55	51	48	45	40	38	37	32
3	80	71	64	58	73	65	59	54	55	50	46	45	41	38	35	33	31	27
4	73	63	55	49	67	58	51	46	48	43	39	40	36	33	32	29	27	23
5	67	56	48	42	61	51	44	39	43	38	34	36	32	29	29	26	23	20
6	62	50	42	36	57	46	39	34	39	33	29	32	28	25	26	23	21	18
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	24	21	18	16
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	16	14
9	49	37	30	25	45	35	28	23	30	24	21	25	21	18	20	17	15	13
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	19	16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18166	18166	18166
5°	18235	17973	18078
10°	18126	17790	17879
15°	17904	17560	17541
20°	17584	17213	17194
25°	17268	16787	16787
30°	16861	16397	16257
35°	16484	15928	15693
40°	16008	15460	15163
45°	15536	14995	14625
50°	15028	14511	13996
55°	14494	13948	13430
60°	13905	13275	12788
65°	13268	12607	12027
70°	12463	11797	11235
75°	11335	10861	10593
80°	10060	9754	9252
85°	8225	7818	7003



TEST NUMBER: P331578-930

CATALOG NUMBER: S122DIW-S865D1240U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	105.8	1.7
10°-20°	297.7	4.7
20°-30°	437.6	6.9
30°-40°	508.3	8.0
40°-50°	507.7	8.0
50°-60°	442.8	7.0
60°-70°	327.4	5.1
70°-80°	185.4	2.9
80°-90°	54.9	0.9
90°-100°	79.4	1.2
100°-110°	246.5	3.9
110°-120°	421.4	6.6
120°-130°	554.2	8.7
130°-140°	622.0	9.8
140°-150°	609.9	9.6
150°-160°	511.5	8.0
160°-170°	339.3	5.3
170°-180°	118.6	1.9
0°-30°	841.1	13.2
0°-40°	1349.3	21.2
0°-60°	2299.8	36.1
0°-90°	2867.5	45.0
90°-120°	747.3	11.7
90°-150°	2533.4	39.8
90°-180°	3503.0	55.0
0°-180°	6370.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1125	1125	1125	1125	1125	
5°	1125	1120	1109	1117	1115	107
15°	1071	1064	1050	1054	1049	301
25°	969	960	942	944	942	446
35°	836	825	808	802	796	522
45°	680	672	657	645	640	525
55°	515	508	496	483	477	460
65°	347	341	330	320	315	343
75°	182	179	174	168	170	194
85°	44	43	42	39	38	51
90°	1	14	37	35	36	5
95°	55	65	68	68	66	63
105°	227	230	233	235	235	240
115°	423	429	427	426	423	418
125°	615	624	622	619	617	550
135°	796	807	810	809	806	615
145°	966	974	980	981	977	603
155°	1105	1108	1111	1116	1113	508
165°	1202	1201	1201	1208	1203	339
175°	1251	1248	1245	1252	1246	119
180°	1253	1253	1253	1253	1253	



TEST NUMBER: P331578-930

CATALOG NUMBER: S122DIW-S865D1240U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1
2.5°	1130.3	1129.4	1128.4	1127.5	1126.5	1124.9	1122.8	1120.7	1118.6	1116.5	1118.4
5°	1125.1	1124.1	1123.2	1122.3	1121.3	1119.5	1116.9	1114.2	1111.6	1108.9	1110.8
7.5°	1115.2	1113.7	1112.2	1110.7	1109.2	1107.1	1104.4	1101.7	1099.0	1096.3	1098.3
10°	1105.6	1104.0	1102.3	1100.6	1098.9	1096.7	1093.7	1090.9	1088.0	1085.1	1087.0
12.5°	1092.7	1091.2	1089.7	1088.2	1086.7	1084.5	1081.7	1078.7	1075.9	1073.0	1074.3
15°	1071.1	1069.6	1068.1	1066.7	1065.3	1063.0	1059.9	1056.7	1053.6	1050.5	1051.4
17.5°	1043.3	1041.9	1040.5	1039.0	1037.5	1035.3	1032.1	1028.9	1025.7	1022.5	1023.7
20°	1023.4	1022.0	1020.6	1019.1	1017.7	1015.3	1011.9	1008.5	1005.2	1001.8	1002.5
22.5°	1003.6	1001.5	999.5	997.4	995.5	992.9	989.7	986.5	983.3	980.2	980.3
25°	969.3	967.4	965.5	963.6	961.6	958.6	954.6	950.5	946.4	942.3	942.8
27.5°	930.4	928.7	926.9	925.2	923.5	921.0	917.8	914.5	911.3	908.1	907.4
30°	904.4	902.5	900.6	898.7	896.7	894.0	890.4	886.8	883.1	879.5	878.8
32.5°	876.8	875.2	873.7	872.1	870.6	867.9	864.1	860.3	856.6	852.7	851.4
35°	836.3	833.9	831.4	829.1	826.6	823.5	819.7	815.9	812.0	808.1	806.7
37.5°	790.6	788.5	786.4	784.2	782.2	779.2	775.3	771.5	767.6	763.8	762.0
40°	759.5	757.6	755.6	753.7	751.8	748.9	745.0	741.2	737.4	733.5	731.3
42.5°	729.2	727.2	725.3	723.4	721.5	718.6	714.8	710.9	707.0	703.2	700.8
45°	680.4	678.8	677.1	675.5	673.8	671.1	667.5	663.9	660.3	656.7	654.0
47.5°	632.0	630.5	628.8	627.3	625.7	623.0	619.2	615.5	611.7	608.0	605.2
50°	598.3	597.0	595.9	594.7	593.5	591.2	587.8	584.4	581.1	577.7	574.4
52.5°	565.4	563.8	562.2	560.6	559.1	556.7	553.5	550.3	547.1	544.0	541.2
55°	514.9	513.6	512.1	510.6	509.2	507.0	504.2	501.2	498.4	495.5	492.6
57.5°	464.3	463.2	462.0	460.9	459.7	457.5	454.4	451.2	448.0	444.8	442.1
60°	430.6	429.6	428.7	427.7	426.7	424.6	421.2	417.8	414.5	411.1	408.5
62.5°	397.7	396.2	394.6	393.1	391.5	389.5	386.9	384.3	381.6	379.1	376.7
65°	347.3	345.8	344.4	342.9	341.5	339.6	337.2	334.8	332.4	330.0	327.8
67.5°	296.0	294.8	293.7	292.5	291.4	289.8	287.6	285.4	283.2	281.0	279.4
70°	264.0	263.0	262.0	261.1	260.2	258.5	256.4	254.2	252.1	249.9	248.3
72.5°	231.1	230.2	229.2	228.2	227.2	226.1	224.7	223.3	221.8	220.5	218.8
75°	181.7	181.2	180.8	180.3	179.9	179.0	177.8	176.6	175.4	174.1	172.8
77.5°	137.6	136.8	136.0	135.2	134.4	133.7	133.2	132.7	132.2	131.8	131.0
80°	108.2	107.9	107.7	107.5	107.2	106.9	106.4	105.9	105.4	104.9	104.2
82.5°	80.5	80.5	80.4	80.3	80.3	80.1	79.8	79.6	79.2	79.0	78.0
85°	44.4	44.1	43.9	43.6	43.4	43.1	42.9	42.6	42.4	42.2	41.5
87.5°	15.8	16.0	16.1	16.3	16.5	17.0	17.6	18.2	18.8	19.5	18.8
90°	1.1	3.9	6.7	9.5	12.3	16.3	21.5	26.7	31.8	37.0	36.5
92.5°	18.8	20.9	23.0	25.0	27.1	28.7	29.9	31.1	32.4	33.6	33.7
95°	55.0	57.3	59.7	62.0	64.4	65.8	66.3	66.7	67.2	67.7	67.7
97.5°	100.4	102.5	104.6	106.6	108.7	110.1	111.0	111.9	112.8	113.7	113.7
100°	134.3	136.2	138.0	139.9	141.8	143.1	143.7	144.5	145.2	145.9	145.9
102.5°	169.7	171.3	172.8	174.3	175.8	177.0	177.9	178.8	179.7	180.6	180.8
105°	227.3	228.0	228.7	229.4	230.1	230.7	231.1	231.6	232.1	232.6	233.0
107.5°	285.2	286.3	287.3	288.3	289.3	289.8	289.8	289.8	289.8	289.8	290.1
110°	322.5	323.8	325.2	326.7	328.1	328.8	328.8	328.8	328.8	328.8	328.8



TEST NUMBER: P331578-930

CATALOG NUMBER: S122DIW-S865D1240U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	363.1	364.4	365.8	367.3	368.7	369.2	369.1	368.9	368.7	368.5	367.9
115°	422.9	424.3	425.7	427.1	428.5	428.9	428.5	428.0	427.5	427.1	426.9
117.5°	482.5	484.4	486.2	488.1	490.0	490.3	488.9	487.6	486.3	485.0	484.5
120°	522.2	524.1	526.0	527.9	529.8	529.8	527.9	526.0	524.1	522.2	522.2
122.5°	558.6	560.8	563.1	565.3	567.6	568.1	566.8	565.5	564.1	562.8	562.2
125°	615.2	617.3	619.5	621.6	623.7	624.4	623.7	623.1	622.3	621.6	620.9
127.5°	670.4	673.1	675.8	678.5	681.2	682.1	681.3	680.4	679.6	678.7	677.8
130°	705.2	708.2	711.3	714.3	717.3	718.6	718.2	717.7	717.2	716.7	716.2
132.5°	744.0	746.5	749.0	751.5	754.0	755.3	755.4	755.5	755.5	755.6	754.6
135°	796.1	798.6	801.2	803.8	806.4	807.9	808.4	808.9	809.3	809.8	809.5
137.5°	850.8	852.9	855.0	857.1	859.2	860.6	861.2	861.9	862.4	863.1	862.9
140°	883.8	885.9	888.0	890.1	892.3	893.9	895.0	896.3	897.4	898.5	898.5
142.5°	917.6	919.7	921.9	924.0	926.1	927.5	928.3	929.1	929.9	930.7	930.9
145°	966.2	967.9	969.6	971.2	972.8	974.4	975.8	977.1	978.6	980.0	980.2
147.5°	1009.6	1011.5	1013.5	1015.5	1017.5	1019.0	1019.9	1020.8	1021.7	1022.7	1023.2
150°	1039.2	1040.6	1042.0	1043.4	1044.8	1046.0	1046.9	1047.9	1048.8	1049.8	1050.4
152.5°	1065.4	1066.8	1068.2	1069.6	1071.1	1072.3	1073.4	1074.6	1075.7	1076.8	1077.7
155°	1104.7	1105.5	1106.1	1106.9	1107.6	1108.2	1109.0	1109.6	1110.4	1111.1	1112.2
157.5°	1138.3	1138.8	1139.3	1139.8	1140.2	1140.7	1141.1	1141.5	1141.9	1142.4	1143.9
160°	1158.6	1159.1	1159.6	1160.1	1160.5	1160.9	1161.1	1161.3	1161.6	1161.8	1163.2
162.5°	1177.2	1177.4	1177.5	1177.5	1177.6	1177.8	1178.0	1178.3	1178.5	1178.8	1180.3
165°	1202.0	1201.8	1201.5	1201.3	1201.0	1200.9	1200.9	1200.9	1200.9	1200.9	1202.6
167.5°	1222.7	1222.0	1221.3	1220.6	1219.9	1219.5	1219.4	1219.4	1219.4	1219.3	1221.0
170°	1233.7	1233.0	1232.3	1231.6	1230.9	1230.4	1230.2	1230.0	1229.7	1229.5	1231.1
172.5°	1241.3	1240.6	1239.9	1239.2	1238.5	1238.0	1237.8	1237.5	1237.3	1237.1	1238.8
175°	1250.6	1249.9	1249.2	1248.5	1247.8	1247.2	1246.8	1246.3	1245.8	1245.3	1247.0
177.5°	1254.4	1253.8	1253.3	1252.7	1252.1	1251.7	1251.3	1250.9	1250.6	1250.2	1251.3
180°	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7



TEST NUMBER: P331578-930

CATALOG NUMBER: S122DIW-S865D1240U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1
2.5°	1120.3	1122.3	1124.1	1124.9	1124.5	1124.1	1123.8	1123.4
5°	1112.7	1114.7	1116.6	1117.3	1116.9	1116.4	1115.9	1115.4
7.5°	1100.2	1102.1	1104.1	1104.7	1104.2	1103.7	1103.2	1102.6
10°	1088.9	1090.9	1092.8	1093.4	1092.7	1091.9	1091.2	1090.5
12.5°	1075.7	1077.0	1078.4	1078.8	1078.2	1077.7	1077.2	1076.7
15°	1052.4	1053.4	1054.3	1054.2	1053.0	1051.8	1050.6	1049.4
17.5°	1024.7	1025.9	1027.0	1027.0	1025.8	1024.7	1023.5	1022.4
20°	1003.2	1004.0	1004.7	1004.5	1003.6	1002.7	1001.7	1000.7
22.5°	980.5	980.6	980.7	980.6	979.9	979.3	978.8	978.2
25°	943.3	943.7	944.2	944.2	943.7	943.3	942.8	942.3
27.5°	906.7	906.0	905.2	904.3	903.1	902.0	900.8	899.7
30°	878.1	877.4	876.7	875.8	874.9	873.9	872.9	872.0
32.5°	850.1	848.8	847.5	846.4	845.5	844.5	843.5	842.5
35°	805.3	803.8	802.4	801.0	799.9	798.7	797.4	796.2
37.5°	760.3	758.5	756.7	755.2	754.1	752.9	751.8	750.6
40°	729.2	727.0	724.9	723.3	722.4	721.4	720.4	719.4
42.5°	698.5	696.1	693.8	691.9	690.6	689.3	687.9	686.6
45°	651.4	648.7	646.1	644.3	643.4	642.4	641.4	640.5
47.5°	602.4	599.7	596.9	594.8	593.4	592.0	590.6	589.2
50°	571.0	567.6	564.3	562.0	560.8	559.5	558.4	557.2
52.5°	538.3	535.6	532.8	530.6	529.0	527.4	525.9	524.2
55°	489.8	486.8	484.0	481.9	480.7	479.5	478.3	477.1
57.5°	439.2	436.3	433.5	431.6	430.7	429.8	428.9	428.0
60°	405.9	403.2	400.6	398.8	398.1	397.4	396.6	396.0
62.5°	374.1	371.7	369.2	367.6	366.6	365.7	364.8	363.9
65°	325.6	323.5	321.3	319.6	318.5	317.2	316.0	314.8
67.5°	277.7	276.0	274.3	273.0	272.1	271.1	270.1	269.1
70°	246.5	244.8	243.2	241.8	240.9	239.9	239.0	238.0
72.5°	217.1	215.4	213.8	212.5	211.7	211.0	210.2	209.5
75°	171.3	169.8	168.4	168.0	168.4	168.9	169.3	169.8
77.5°	130.4	129.6	128.9	128.2	127.5	126.9	126.2	125.5
80°	103.5	102.8	102.1	101.4	100.9	100.5	100.0	99.5
82.5°	77.1	76.2	75.3	74.8	74.7	74.6	74.5	74.4
85°	40.8	40.0	39.3	38.8	38.6	38.3	38.1	37.8
87.5°	18.2	17.5	16.8	16.4	16.3	16.1	16.0	15.8
90°	36.0	35.6	35.1	35.0	35.2	35.5	35.7	36.0
92.5°	33.8	33.9	34.0	34.1	34.1	34.2	34.2	34.2
95°	67.7	67.7	67.7	67.4	66.9	66.4	66.0	65.6
97.5°	113.7	113.7	113.7	113.7	113.7	113.7	113.6	113.6
100°	145.9	145.9	145.9	145.8	145.5	145.3	145.0	144.8
102.5°	180.9	181.2	181.3	181.3	181.1	180.8	180.6	180.3
105°	233.5	234.0	234.5	234.7	234.7	234.7	234.7	234.7
107.5°	290.2	290.4	290.7	290.2	289.1	288.0	286.9	285.8
110°	328.8	328.8	328.8	328.4	327.8	327.0	326.3	325.6



TEST NUMBER: P331578-930

CATALOG NUMBER: S122DIW-S865D1240U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	367.4	366.8	366.2	365.7	365.2	364.7	364.2	363.6
115°	426.6	426.4	426.2	425.7	425.0	424.3	423.5	422.9
117.5°	483.9	483.3	482.7	482.2	481.4	480.7	480.0	479.3
120°	522.2	522.2	522.2	521.9	521.1	520.5	519.8	519.1
122.5°	561.7	561.2	560.6	560.0	559.5	559.0	558.5	558.0
125°	620.2	619.5	618.8	618.3	618.1	617.8	617.6	617.3
127.5°	677.0	676.1	675.3	674.5	673.8	673.0	672.3	671.5
130°	715.8	715.3	714.9	714.2	713.2	712.3	711.3	710.4
132.5°	753.6	752.5	751.5	750.6	749.9	749.1	748.4	747.6
135°	809.3	809.1	808.9	808.4	807.6	807.0	806.2	805.5
137.5°	862.7	862.5	862.3	861.8	860.8	859.9	858.9	858.0
140°	898.5	898.5	898.5	898.1	897.2	896.3	895.3	894.4
142.5°	931.1	931.3	931.5	931.1	930.2	929.2	928.3	927.3
145°	980.5	980.7	980.9	980.6	979.7	978.7	977.8	976.8
147.5°	1023.7	1024.3	1024.7	1024.6	1023.7	1022.8	1021.9	1021.0
150°	1051.2	1051.9	1052.6	1052.6	1051.9	1051.2	1050.4	1049.8
152.5°	1078.6	1079.5	1080.4	1080.4	1079.5	1078.6	1077.7	1076.8
155°	1113.5	1114.6	1115.7	1116.0	1115.3	1114.6	1113.9	1113.2
157.5°	1145.6	1147.1	1148.8	1149.0	1147.9	1146.7	1145.6	1144.4
160°	1164.7	1166.0	1167.4	1167.7	1166.8	1165.8	1164.9	1163.9
162.5°	1181.9	1183.5	1185.1	1185.4	1184.2	1183.1	1181.9	1180.9
165°	1204.2	1205.8	1207.5	1207.7	1206.6	1205.4	1204.2	1203.1
167.5°	1222.6	1224.3	1225.9	1226.1	1224.9	1223.7	1222.5	1221.2
170°	1232.7	1234.4	1236.1	1236.2	1234.8	1233.4	1231.9	1230.5
172.5°	1240.4	1242.0	1243.7	1243.7	1242.4	1241.0	1239.6	1238.1
175°	1248.6	1250.3	1251.9	1252.1	1250.6	1249.2	1247.8	1246.3
177.5°	1252.5	1253.6	1254.7	1254.7	1253.6	1252.5	1251.3	1250.2
180°	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7	1252.7

(END OF REPORT)