

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331556-930

Luminaire Tested: **S122DIW-S865D435U930-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331556-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S865D435U930-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 435 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4331.2 lumens
Efficiency: N/A
Efficacy: 93.7 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 46.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331556-930

CATALOG NUMBER: S122DIW-S865D435U930-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331556-930

CATALOG NUMBER: S122DIW-S865D435U930-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR																																														
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	76	76	76	72																												
1	103	99	95	92	98	94	91	88	85	82	80	76	74	73	68	67	66	62																												
2	95	87	81	76	90	83	78	73	75	71	67	68	65	62	61	59	56	53																												
3	87	78	70	64	82	74	67	62	67	62	58	61	57	53	55	52	49	46																												
4	80	69	61	55	76	66	59	53	60	54	50	55	50	46	49	46	43	40																												
5	74	62	54	48	70	59	52	47	54	48	44	49	44	41	45	41	38	35																												
6	68	56	48	42	65	54	46	41	49	43	38	45	40	36	41	37	34	31																												
7	63	51	43	38	60	49	42	36	45	39	34	41	36	32	38	33	30	28																												
8	59	47	39	34	56	45	38	33	41	35	31	38	33	29	35	30	27	25																												
9	55	43	35	30	52	41	34	29	38	32	28	35	30	26	32	28	25	23																												
10	52	40	32	27	49	38	31	27	35	29	25	33	28	24	30	26	23	21																												

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	22727	22727	22727	22727
5°	25480	22875	20272	22875
10°	29198	22689	17544	22689
15°	32301	22272	15499	22272
20°	31809	21825	14129	21825
25°	28682	21232	13261	21232
30°	23702	20282	12629	20282
35°	17274	19291	12177	19291
40°	13797	18120	11927	18120
45°	12056	16762	11586	16762
50°	11333	15450	11359	15450
55°	10446	14117	11054	14117
60°	9571	12700	10585	12700
65°	8722	11427	10128	11427
70°	7917	10192	9451	10192
75°	7018	8808	8372	8808
80°	6034	7290	6741	7290
85°	5409	5409	4001	5409



TEST NUMBER: P331556-930

CATALOG NUMBER: S122DIW-S865D435U930-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	134.1	3.1
10°-20°	389.7	9.0
20°-30°	565.6	13.1
30°-40°	596.9	13.8
40°-50°	528.5	12.2
50°-60°	421.7	9.7
60°-70°	286.7	6.6
70°-80°	147.0	3.4
80°-90°	37.2	0.9
90°-100°	27.7	0.6
100°-110°	86.1	2.0
110°-120°	147.2	3.4
120°-130°	193.6	4.5
130°-140°	217.3	5.0
140°-150°	213.1	4.9
150°-160°	178.7	4.1
160°-170°	118.6	2.7
170°-180°	41.4	1.0
0°-30°	1089.4	25.2
0°-40°	1686.3	38.9
0°-60°	2636.5	60.9
0°-90°	3107.3	71.7
90°-120°	261.1	6.0
90°-150°	885.2	20.4
90°-180°	1224.0	28.3
0°-180°	4331.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1408	1408	1408	1408	1408	
5°	1572	1411	1251	1411	1572	157
15°	1932	1332	927	1332	1932	533
25°	1610	1192	744	1192	1610	728
35°	876	979	618	979	876	570
45°	528	734	507	734	528	415
55°	371	502	393	502	371	333
65°	228	299	265	299	228	227
75°	112	141	134	141	112	120
85°	29	29	22	29	29	32
90°	13	0	13	0	13	7
95°	23	19	23	19	23	26
105°	82	79	82	79	82	86
115°	148	148	148	148	148	146
125°	216	215	216	215	216	192
135°	281	278	281	278	281	217
145°	341	338	341	338	341	213
155°	389	386	389	386	389	179
165°	420	420	420	420	420	119
175°	436	437	436	437	436	41
180°	438	438	438	438	438	



TEST NUMBER: P331556-930

CATALOG NUMBER: S122DIW-S865D435U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6
2.5°	1472.6	1473.0	1473.9	1467.0	1466.1	1466.1	1460.0	1454.8	1448.8	1440.6	1441.4
5°	1572.1	1578.1	1580.2	1573.8	1564.0	1562.9	1553.7	1538.6	1524.5	1513.1	1505.0
7.5°	1690.9	1693.3	1688.0	1679.4	1672.2	1659.2	1642.1	1625.4	1601.9	1580.4	1564.3
10°	1780.9	1784.2	1775.0	1762.5	1752.2	1737.1	1712.2	1686.8	1656.0	1626.2	1602.4
12.5°	1849.3	1857.3	1845.5	1843.9	1826.3	1805.5	1775.9	1763.0	1719.6	1678.1	1652.6
15°	1932.4	1931.9	1933.0	1922.6	1909.7	1906.4	1875.1	1841.0	1779.9	1755.5	1713.4
17.5°	1908.4	1916.6	1920.4	1920.3	1919.9	1917.9	1907.9	1886.4	1855.7	1816.2	1767.5
20°	1851.3	1862.1	1863.7	1876.2	1883.2	1892.4	1896.1	1890.2	1871.3	1838.3	1796.1
22.5°	1763.0	1766.0	1771.1	1790.5	1805.7	1828.8	1840.8	1860.8	1853.5	1837.4	1802.1
25°	1610.0	1604.6	1623.5	1633.2	1668.4	1705.2	1731.7	1760.9	1786.9	1802.5	1792.3
27.5°	1426.3	1418.1	1446.5	1472.3	1500.9	1540.8	1582.1	1630.8	1671.4	1722.2	1739.6
30°	1271.3	1276.2	1303.3	1330.8	1374.1	1430.4	1476.9	1530.5	1588.4	1645.1	1684.7
32.5°	1104.2	1123.0	1140.1	1182.3	1220.5	1283.2	1351.4	1418.4	1490.5	1555.1	1616.2
35°	876.4	898.1	921.9	952.7	1006.2	1068.4	1135.0	1225.3	1323.8	1412.0	1484.5
37.5°	737.7	734.3	747.9	770.1	813.5	863.7	940.4	1029.6	1145.5	1249.1	1351.4
40°	654.6	652.4	662.2	682.7	715.8	752.5	819.6	898.1	1005.7	1132.3	1254.0
42.5°	597.5	598.8	604.1	618.6	641.3	671.6	721.8	788.6	887.1	1006.3	1137.2
45°	528.0	531.8	537.8	544.8	557.7	582.6	610.7	658.4	736.3	835.8	964.6
47.5°	478.0	478.1	484.2	490.3	498.1	512.1	535.0	564.9	619.9	700.9	811.6
50°	451.2	447.4	451.8	456.6	464.7	474.4	489.6	517.7	554.5	620.0	712.5
52.5°	418.3	418.4	422.3	424.1	431.4	441.2	454.9	474.4	507.8	559.0	635.0
55°	371.1	373.8	376.0	379.2	385.7	392.7	403.6	416.5	442.5	480.9	537.2
57.5°	326.8	327.6	329.8	336.0	340.1	346.6	356.9	368.6	385.5	413.9	456.2
60°	296.4	296.4	300.8	303.5	308.9	315.4	323.5	334.8	350.0	373.2	407.4
62.5°	268.8	268.3	270.0	274.5	278.6	284.7	292.8	302.4	316.7	337.4	365.4
65°	228.3	227.2	230.5	231.5	235.9	241.8	248.3	258.6	269.9	285.1	310.0
67.5°	189.3	190.6	192.4	194.4	196.8	203.1	207.4	214.7	224.3	236.8	253.7
70°	167.7	167.7	167.7	169.3	172.6	175.9	180.2	186.1	195.3	206.1	221.3
72.5°	143.5	145.2	146.9	145.9	150.1	152.1	157.2	160.5	169.3	176.3	189.6
75°	112.5	112.5	112.5	115.2	116.8	118.5	121.7	125.0	129.3	137.9	145.0
77.5°	84.0	83.7	84.3	85.0	86.7	88.6	89.6	92.5	96.5	100.5	106.5
80°	64.9	66.0	66.5	67.6	67.6	68.7	69.2	73.1	75.7	78.4	82.3
82.5°	50.2	50.4	50.5	50.7	51.2	51.9	53.2	54.5	55.4	57.6	60.6
85°	29.2	28.7	28.7	29.8	29.2	29.2	30.3	31.4	31.4	31.9	33.5
87.5°	13.8	13.8	14.2	13.7	13.7	14.1	14.2	13.8	14.3	14.7	14.8
90°	12.6	12.5	12.4	12.3	12.2	12.3	12.5	12.6	12.8	13.0	11.1
92.5°	12.0	12.0	11.9	11.9	11.9	11.9	11.8	11.8	11.7	11.7	11.3
95°	22.9	23.1	23.2	23.4	23.6	23.6	23.6	23.6	23.6	23.6	23.5
97.5°	39.7	39.7	39.7	39.7	39.7	39.7	39.7	39.7	39.7	39.7	39.5
100°	50.6	50.7	50.8	50.9	51.0	51.0	51.0	51.0	51.0	51.0	50.7
102.5°	63.0	63.1	63.2	63.3	63.3	63.3	63.3	63.2	63.2	63.1	62.8
105°	82.0	82.0	82.0	82.0	82.0	81.9	81.8	81.6	81.4	81.3	81.1
107.5°	99.9	100.3	100.6	101.0	101.4	101.6	101.5	101.4	101.3	101.3	101.3
110°	113.7	114.0	114.2	114.5	114.7	114.9	114.9	114.9	114.9	114.9	114.9



TEST NUMBER: P331556-930

CATALOG NUMBER: S122DIW-S865D435U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	127.1	127.3	127.4	127.6	127.8	128.0	128.2	128.4	128.6	128.7	128.8
115°	147.7	148.0	148.2	148.5	148.7	148.9	149.0	149.0	149.1	149.2	149.4
117.5°	167.5	167.7	168.0	168.2	168.4	168.7	168.8	169.1	169.3	169.5	169.9
120°	181.4	181.6	181.9	182.1	182.4	182.5	182.5	182.5	182.5	182.5	183.1
122.5°	194.9	195.1	195.3	195.5	195.7	195.8	196.1	196.2	196.5	196.7	197.1
125°	215.7	215.8	215.9	216.0	216.1	216.2	216.5	216.7	217.0	217.2	217.4
127.5°	234.6	234.9	235.1	235.4	235.7	235.9	236.3	236.5	236.8	237.2	237.4
130°	248.3	248.6	248.9	249.2	249.6	249.8	250.0	250.1	250.3	250.5	250.6
132.5°	261.2	261.5	261.7	262.0	262.3	262.6	262.9	263.3	263.7	264.0	264.0
135°	281.4	281.7	281.9	282.2	282.4	282.6	282.7	282.7	282.8	282.9	282.7
137.5°	299.8	300.1	300.4	300.8	301.1	301.3	301.3	301.4	301.5	301.6	301.3
140°	312.5	312.8	313.2	313.5	313.8	314.0	314.0	314.0	314.0	314.0	313.6
142.5°	324.0	324.3	324.7	325.0	325.3	325.5	325.4	325.3	325.3	325.2	324.9
145°	341.3	341.6	341.9	342.3	342.6	342.8	342.7	342.6	342.5	342.4	341.9
147.5°	356.8	357.0	357.3	357.7	358.0	358.1	357.9	357.7	357.5	357.3	357.0
150°	366.8	367.0	367.3	367.5	367.8	367.8	367.5	367.3	367.0	366.8	366.5
152.5°	376.3	376.6	376.8	377.2	377.5	377.5	377.2	376.8	376.6	376.3	375.9
155°	389.0	389.2	389.5	389.7	390.0	389.9	389.5	389.1	388.7	388.2	388.0
157.5°	399.9	400.3	400.6	401.0	401.5	401.4	400.8	400.2	399.7	399.2	399.0
160°	406.7	407.0	407.3	407.6	408.0	407.9	407.4	406.9	406.4	405.9	405.9
162.5°	412.6	412.9	413.4	413.8	414.2	414.1	413.5	412.9	412.4	411.9	411.8
165°	420.4	420.8	421.2	421.6	422.0	421.9	421.3	420.8	420.2	419.6	419.6
167.5°	426.7	427.1	427.5	428.0	428.4	428.4	427.8	427.2	426.6	426.1	426.1
170°	430.0	430.5	431.0	431.5	431.9	431.9	431.3	430.7	430.2	429.6	429.7
172.5°	432.6	433.1	433.6	434.1	434.6	434.6	434.0	433.4	432.8	432.3	432.4
175°	435.5	436.0	436.5	437.0	437.5	437.4	436.8	436.3	435.7	435.1	435.3
177.5°	436.8	437.2	437.7	438.0	438.4	438.4	438.0	437.7	437.2	436.8	436.9
180°	437.7	437.7	437.7	437.7	437.7	437.7	437.7	437.7	437.7	437.7	437.7



TEST NUMBER: P331556-930

CATALOG NUMBER: S122DIW-S865D435U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6
2.5°	1444.5	1441.0	1438.8	1431.0	1424.1	1417.2	1415.0	1415.8	1406.4	1397.3	1393.3
5°	1500.7	1489.9	1479.6	1465.0	1447.7	1428.7	1419.0	1411.4	1392.5	1372.0	1360.1
7.5°	1551.1	1535.6	1515.9	1488.4	1463.1	1433.4	1414.5	1397.7	1370.0	1341.0	1323.2
10°	1581.8	1560.7	1535.3	1501.8	1471.0	1434.7	1409.2	1383.9	1351.4	1316.8	1295.1
12.5°	1608.3	1579.8	1554.8	1511.7	1475.3	1430.0	1399.8	1363.9	1329.8	1288.7	1267.5
15°	1671.1	1618.6	1571.0	1522.3	1477.4	1414.1	1380.6	1332.4	1287.5	1236.7	1212.4
17.5°	1719.7	1660.8	1585.8	1523.9	1471.5	1401.4	1352.2	1294.5	1241.4	1183.2	1150.1
20°	1747.4	1679.8	1599.1	1525.6	1462.8	1382.7	1329.2	1270.2	1208.0	1142.6	1106.9
22.5°	1763.8	1692.7	1613.0	1519.1	1445.5	1367.6	1300.2	1235.6	1172.6	1101.9	1064.5
25°	1769.0	1704.1	1619.8	1513.7	1423.9	1335.7	1254.6	1191.8	1115.5	1049.5	994.9
27.5°	1743.3	1696.7	1615.6	1503.5	1398.9	1295.8	1205.3	1134.2	1053.8	982.1	927.2
30°	1711.7	1684.7	1605.7	1493.1	1379.0	1268.1	1168.6	1087.9	1007.9	935.4	879.1
32.5°	1662.8	1656.9	1587.5	1478.4	1357.8	1233.1	1130.0	1048.6	959.9	888.6	834.9
35°	1566.7	1592.7	1548.8	1445.5	1317.8	1183.2	1071.7	978.7	886.7	818.5	768.2
37.5°	1437.9	1502.4	1490.9	1397.3	1264.0	1128.9	1005.8	908.6	820.9	752.1	702.7
40°	1349.2	1431.4	1443.3	1360.6	1225.9	1086.9	956.5	859.7	774.1	711.4	661.6
42.5°	1254.0	1350.1	1382.7	1316.5	1184.3	1042.7	912.3	812.0	727.4	666.4	622.2
45°	1094.5	1221.6	1280.5	1242.7	1115.0	970.0	835.8	734.1	657.3	600.0	565.9
47.5°	945.2	1084.1	1163.4	1150.1	1037.8	894.2	761.6	664.0	589.2	543.5	513.0
50°	839.6	982.4	1078.2	1082.6	982.4	840.2	707.1	615.1	546.4	503.7	478.7
52.5°	747.9	884.2	988.6	1011.5	920.6	783.9	658.2	566.6	506.1	466.8	444.6
55°	628.1	743.3	859.1	901.3	828.3	698.4	582.1	501.5	444.7	417.7	398.2
57.5°	522.2	618.2	725.1	771.8	726.8	615.6	506.5	436.6	390.4	366.8	351.9
60°	466.4	542.1	637.3	693.0	654.0	555.1	459.8	393.3	355.5	334.4	320.2
62.5°	414.4	481.5	562.0	612.9	591.7	498.4	413.1	354.3	321.6	301.9	291.7
65°	341.9	394.9	457.1	504.2	490.2	419.2	349.5	299.1	273.2	257.5	249.4
67.5°	281.5	319.8	363.0	404.2	392.9	342.7	286.6	247.4	228.1	214.6	209.7
70°	243.4	272.6	311.0	344.1	334.8	293.8	249.4	215.9	199.1	187.8	182.9
72.5°	207.1	231.1	260.4	287.4	281.2	247.0	210.0	184.7	171.8	161.3	157.4
75°	156.4	174.7	192.6	210.4	208.8	182.3	160.7	141.2	130.9	122.8	121.2
77.5°	115.4	125.7	137.9	148.5	145.5	130.4	113.4	102.2	94.7	89.3	88.4
80°	88.2	94.2	102.8	110.4	106.6	100.1	86.6	78.4	73.1	67.6	65.5
82.5°	63.9	69.9	75.1	79.2	76.3	70.2	61.9	56.3	53.2	49.4	48.6
85°	33.5	36.8	39.0	40.0	39.0	35.1	31.4	29.2	26.5	24.9	24.4
87.5°	14.8	14.5	14.1	14.7	13.2	13.0	11.1	9.6	9.4	9.1	8.5
90°	9.3	7.5	5.7	4.3	3.3	2.4	1.4	0.4	1.4	2.4	3.3
92.5°	10.9	10.4	10.0	9.5	8.7	8.0	7.3	6.6	7.3	8.0	8.7
95°	23.3	23.2	23.0	22.5	21.7	20.9	20.1	19.2	20.1	20.9	21.7
97.5°	39.1	38.8	38.5	38.0	37.3	36.5	35.8	35.1	35.8	36.5	37.3
100°	50.5	50.2	50.0	49.6	48.9	48.2	47.5	46.9	47.5	48.2	48.9
102.5°	62.5	62.1	61.9	61.4	60.9	60.3	59.8	59.4	59.8	60.3	60.9
105°	81.0	80.8	80.6	80.4	80.1	79.9	79.7	79.4	79.7	79.9	80.1
107.5°	101.3	101.3	101.3	101.1	100.8	100.4	100.0	99.6	100.0	100.4	100.8
110°	114.9	114.9	114.9	114.6	114.1	113.7	113.2	112.7	113.2	113.7	114.1



TEST NUMBER: P331556-930

CATALOG NUMBER: S122DIW-S865D435U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	128.9	129.0	129.1	128.8	128.3	127.8	127.3	126.9	127.3	127.8	128.3
115°	149.5	149.7	149.9	149.7	149.2	148.7	148.2	147.7	148.2	148.7	149.2
117.5°	170.4	170.9	171.3	171.2	170.6	169.9	169.3	168.6	169.3	169.9	170.6
120°	183.8	184.4	185.1	185.1	184.4	183.8	183.1	182.5	183.1	183.8	184.4
122.5°	197.5	198.0	198.5	198.4	197.5	196.7	196.0	195.2	196.0	196.7	197.5
125°	217.7	217.9	218.2	217.9	217.2	216.5	215.7	215.0	215.7	216.5	217.2
127.5°	237.7	238.1	238.3	238.0	237.1	236.1	235.2	234.2	235.2	236.1	237.1
130°	250.8	250.9	251.1	250.6	249.6	248.5	247.4	246.4	247.4	248.5	249.6
132.5°	264.0	263.9	263.9	263.4	262.6	261.7	260.8	260.0	260.8	261.7	262.6
135°	282.6	282.4	282.3	281.8	280.9	280.0	279.1	278.2	279.1	280.0	280.9
137.5°	301.2	300.9	300.7	300.2	299.5	298.7	298.0	297.3	298.0	298.7	299.5
140°	313.2	312.7	312.3	311.8	311.0	310.3	309.6	308.8	309.6	310.3	311.0
142.5°	324.7	324.3	324.1	323.6	322.9	322.1	321.4	320.7	321.4	322.1	322.9
145°	341.4	341.0	340.5	339.9	339.3	338.8	338.2	337.6	338.2	338.8	339.3
147.5°	356.7	356.4	356.0	355.6	354.8	354.2	353.4	352.8	353.4	354.2	354.8
150°	366.2	365.8	365.5	365.1	364.6	364.1	363.6	363.1	363.6	364.1	364.6
152.5°	375.4	375.0	374.7	374.2	373.7	373.2	372.8	372.3	372.8	373.2	373.7
155°	387.8	387.5	387.3	387.0	386.8	386.5	386.2	386.0	386.2	386.5	386.8
157.5°	398.8	398.7	398.5	398.4	398.3	398.1	397.9	397.8	397.9	398.1	398.3
160°	405.8	405.7	405.6	405.5	405.4	405.2	405.0	404.9	405.0	405.2	405.4
162.5°	411.7	411.6	411.6	411.5	411.4	411.4	411.4	411.3	411.4	411.4	411.4
165°	419.6	419.6	419.6	419.6	419.7	419.8	419.9	420.0	419.9	419.8	419.7
167.5°	426.1	426.1	426.1	426.2	426.5	426.7	427.0	427.2	427.0	426.7	426.5
170°	429.7	429.8	429.9	430.1	430.3	430.6	430.8	431.0	430.8	430.6	430.3
172.5°	432.4	432.5	432.6	432.8	433.0	433.3	433.5	433.7	433.5	433.3	433.0
175°	435.5	435.6	435.8	436.0	436.3	436.5	436.8	437.0	436.8	436.5	436.3
177.5°	437.1	437.2	437.3	437.5	437.7	437.9	438.1	438.3	438.1	437.9	437.7
180°	437.7	437.7	437.7	437.7	437.7	437.7	437.7	437.7	437.7	437.7	437.7



TEST NUMBER: P331556-930

CATALOG NUMBER: S122DIW-S865D435U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6
2.5°	1389.0	1386.4	1377.4	1372.6	1364.8	1357.5	1352.7	1354.9	1356.6	1355.7	1354.5
5°	1349.2	1339.0	1323.2	1309.7	1300.0	1282.1	1274.6	1270.8	1267.5	1263.7	1260.0
7.5°	1301.9	1285.6	1263.1	1243.8	1225.6	1203.5	1190.8	1183.2	1175.5	1166.9	1159.4
10°	1268.1	1245.4	1221.6	1194.5	1172.9	1152.8	1135.0	1123.1	1112.3	1102.0	1094.5
12.5°	1232.6	1206.4	1177.0	1140.0	1116.1	1087.5	1084.8	1063.8	1046.9	1040.6	1031.7
15°	1176.2	1139.3	1102.0	1058.2	1039.3	1013.3	997.0	980.8	966.2	955.9	953.2
17.5°	1112.0	1064.4	1027.2	995.7	964.7	938.1	923.2	910.2	898.1	884.4	882.6
20°	1063.1	1021.9	981.4	953.7	921.9	894.8	876.4	863.4	853.1	845.1	838.0
22.5°	1016.8	971.8	934.6	904.4	872.9	851.1	836.6	824.0	815.5	806.5	799.9
25°	942.4	907.3	866.7	832.6	806.6	792.6	780.6	769.8	764.4	758.5	750.9
27.5°	877.3	838.3	800.4	774.0	751.1	738.7	730.3	722.8	717.8	714.3	710.0
30°	831.5	792.0	762.2	736.3	717.4	704.9	699.5	695.2	689.3	687.1	684.9
32.5°	787.3	751.8	726.4	703.8	685.7	677.7	672.7	668.8	664.1	661.9	657.6
35°	725.0	695.2	670.3	657.9	643.3	636.2	632.4	627.0	622.6	620.5	620.0
37.5°	666.2	640.3	623.9	608.0	601.8	597.5	592.3	588.6	587.3	586.9	586.4
40°	628.1	607.0	592.4	579.4	576.7	570.2	565.9	562.6	562.6	563.2	562.6
42.5°	593.5	574.5	561.7	550.4	547.2	543.4	539.1	538.8	539.7	541.5	539.7
45°	541.0	527.5	518.3	512.8	506.9	503.1	502.6	504.2	504.8	505.3	506.9
47.5°	492.8	483.7	475.4	469.4	466.8	466.2	465.5	468.4	471.0	472.0	474.4
50°	464.1	453.9	446.9	443.0	440.9	439.9	440.9	444.2	446.3	449.0	450.6
52.5°	432.1	424.9	420.0	417.1	416.2	416.9	417.1	420.8	424.3	425.2	426.0
55°	387.9	382.5	381.4	376.5	378.7	378.1	380.8	383.0	386.3	389.6	390.0
57.5°	343.7	339.4	336.5	337.0	337.6	340.0	342.3	346.0	349.5	352.9	353.3
60°	314.3	312.2	310.5	310.5	311.6	314.9	317.6	321.3	323.5	325.7	327.3
62.5°	287.5	285.4	283.7	284.5	287.4	289.3	292.4	294.5	296.7	298.8	299.6
65°	245.1	244.0	245.6	246.7	247.2	250.0	253.7	255.4	257.5	258.6	262.4
67.5°	206.0	206.2	206.0	207.5	210.7	211.3	214.9	218.7	219.1	221.2	223.6
70°	179.6	180.7	181.8	182.9	185.6	186.6	189.3	190.9	193.1	194.8	196.4
72.5°	155.4	155.6	156.7	156.5	158.7	161.1	163.4	165.0	167.1	169.3	170.8
75°	119.5	119.5	120.7	121.2	123.9	126.6	126.0	127.1	129.3	131.4	132.6
77.5°	87.3	86.1	87.3	87.9	88.7	91.0	91.4	92.9	95.4	94.7	95.9
80°	66.5	64.9	66.5	67.1	67.1	69.8	69.8	70.8	72.5	70.8	72.5
82.5°	47.5	46.7	47.9	48.0	48.9	49.0	49.9	50.1	51.7	51.0	51.7
85°	23.8	23.2	23.8	23.2	23.8	24.4	24.4	23.8	23.8	24.9	23.2
87.5°	8.2	8.1	8.0	8.3	8.3	8.2	7.7	7.7	7.7	6.8	6.8
90°	4.3	5.7	7.5	9.3	11.1	13.0	12.8	12.6	12.5	12.3	12.2
92.5°	9.5	10.0	10.4	10.9	11.3	11.7	11.7	11.8	11.8	11.9	11.9
95°	22.5	23.0	23.2	23.3	23.5	23.6	23.6	23.6	23.6	23.6	23.6
97.5°	38.0	38.5	38.8	39.1	39.5	39.7	39.7	39.7	39.7	39.7	39.7
100°	49.6	50.0	50.2	50.5	50.7	51.0	51.0	51.0	51.0	51.0	51.0
102.5°	61.4	61.9	62.1	62.5	62.8	63.1	63.2	63.2	63.3	63.3	63.3
105°	80.4	80.6	80.8	81.0	81.1	81.3	81.4	81.6	81.8	81.9	82.0
107.5°	101.1	101.3	101.3	101.3	101.3	101.3	101.3	101.4	101.5	101.6	101.4
110°	114.6	114.9	114.9	114.9	114.9	114.9	114.9	114.9	114.9	114.9	114.7



TEST NUMBER: P331556-930

CATALOG NUMBER: S122DIW-S865D435U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	128.8	129.1	129.0	128.9	128.8	128.7	128.6	128.4	128.2	128.0	127.8
115°	149.7	149.9	149.7	149.5	149.4	149.2	149.1	149.0	149.0	148.9	148.7
117.5°	171.2	171.3	170.9	170.4	169.9	169.5	169.3	169.1	168.8	168.7	168.4
120°	185.1	185.1	184.4	183.8	183.1	182.5	182.5	182.5	182.5	182.5	182.4
122.5°	198.4	198.5	198.0	197.5	197.1	196.7	196.5	196.2	196.1	195.8	195.7
125°	217.9	218.2	217.9	217.7	217.4	217.2	217.0	216.7	216.5	216.2	216.1
127.5°	238.0	238.3	238.1	237.7	237.4	237.2	236.8	236.5	236.3	235.9	235.7
130°	250.6	251.1	250.9	250.8	250.6	250.5	250.3	250.1	250.0	249.8	249.6
132.5°	263.4	263.9	263.9	264.0	264.0	264.0	263.7	263.3	262.9	262.6	262.3
135°	281.8	282.3	282.4	282.6	282.7	282.9	282.8	282.7	282.7	282.6	282.4
137.5°	300.2	300.7	300.9	301.2	301.3	301.6	301.5	301.4	301.3	301.3	301.1
140°	311.8	312.3	312.7	313.2	313.6	314.0	314.0	314.0	314.0	314.0	313.8
142.5°	323.6	324.1	324.3	324.7	324.9	325.2	325.3	325.3	325.4	325.5	325.3
145°	339.9	340.5	341.0	341.4	341.9	342.4	342.5	342.6	342.7	342.8	342.6
147.5°	355.6	356.0	356.4	356.7	357.0	357.3	357.5	357.7	357.9	358.1	358.0
150°	365.1	365.5	365.8	366.2	366.5	366.8	367.0	367.3	367.5	367.8	367.8
152.5°	374.2	374.7	375.0	375.4	375.9	376.3	376.6	376.8	377.2	377.5	377.5
155°	387.0	387.3	387.5	387.8	388.0	388.2	388.7	389.1	389.5	389.9	390.0
157.5°	398.4	398.5	398.7	398.8	399.0	399.2	399.7	400.2	400.8	401.4	401.5
160°	405.5	405.6	405.7	405.8	405.9	405.9	406.4	406.9	407.4	407.9	408.0
162.5°	411.5	411.6	411.6	411.7	411.8	411.9	412.4	412.9	413.5	414.1	414.2
165°	419.6	419.6	419.6	419.6	419.6	419.6	420.2	420.8	421.3	421.9	422.0
167.5°	426.2	426.1	426.1	426.1	426.1	426.1	426.6	427.2	427.8	428.4	428.4
170°	430.1	429.9	429.8	429.7	429.7	429.6	430.2	430.7	431.3	431.9	431.9
172.5°	432.8	432.6	432.5	432.4	432.4	432.3	432.8	433.4	434.0	434.6	434.6
175°	436.0	435.8	435.6	435.5	435.3	435.1	435.7	436.3	436.8	437.4	437.5
177.5°	437.5	437.3	437.2	437.1	436.9	436.8	437.2	437.7	438.0	438.4	438.4
180°	437.7	437.7	437.7	437.7	437.7	437.7	437.7	437.7	437.7	437.7	437.7



TEST NUMBER: P331556-930

CATALOG NUMBER: S122DIW-S865D435U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6
2.5°	1350.1	1349.2	1349.2	1345.3	1349.2	1349.2	1350.1	1354.5	1355.7	1356.6	1354.9
5°	1252.4	1250.8	1248.1	1250.8	1248.1	1250.8	1252.4	1260.0	1263.7	1267.5	1270.8
7.5°	1155.8	1149.2	1148.3	1141.9	1148.3	1149.2	1155.8	1159.4	1166.9	1175.5	1183.2
10°	1085.2	1080.9	1080.4	1070.1	1080.4	1080.9	1085.2	1094.5	1102.0	1112.3	1123.1
12.5°	1031.6	1021.2	1023.2	1017.2	1023.2	1021.2	1031.6	1031.7	1040.6	1046.9	1063.8
15°	938.7	938.7	936.5	927.2	936.5	938.7	938.7	953.2	955.9	966.2	980.8
17.5°	871.9	870.7	865.6	868.2	865.6	870.7	871.9	882.6	884.4	898.1	910.2
20°	832.0	828.8	822.3	822.3	822.3	828.8	832.0	838.0	845.1	853.1	863.4
22.5°	794.4	794.2	787.3	789.4	787.3	794.2	794.4	799.9	806.5	815.5	824.0
25°	750.3	746.0	742.8	744.4	742.8	746.0	750.3	750.9	758.5	764.4	769.8
27.5°	708.6	706.2	706.0	701.6	706.0	706.2	708.6	710.0	714.3	717.8	722.8
30°	684.4	679.0	680.0	677.4	680.0	679.0	684.4	684.9	687.1	689.3	695.2
32.5°	656.6	654.7	653.6	651.3	653.6	654.7	656.6	657.6	661.9	664.1	668.8
35°	618.9	619.5	616.7	617.8	616.7	619.5	618.9	620.0	620.5	622.6	627.0
37.5°	585.9	587.6	586.4	586.7	586.4	587.6	585.9	586.4	586.9	587.3	588.6
40°	564.3	564.3	564.3	565.9	564.3	564.3	564.3	562.6	563.2	562.6	562.6
42.5°	543.5	542.6	541.8	541.6	541.8	542.6	543.5	539.7	541.5	539.7	538.8
45°	508.0	509.6	510.1	507.4	510.1	509.6	508.0	506.9	505.3	504.8	504.2
47.5°	475.9	476.1	475.9	478.3	475.9	476.1	475.9	474.4	472.0	471.0	468.4
50°	453.4	452.2	453.4	452.2	453.4	452.2	453.4	450.6	449.0	446.3	444.2
52.5°	429.6	429.7	429.1	428.9	429.1	429.7	429.6	426.0	425.2	424.3	420.8
55°	392.2	393.3	392.7	392.7	392.7	393.3	392.2	390.0	389.6	386.3	383.0
57.5°	353.6	354.6	355.3	352.9	355.3	354.6	353.6	353.3	352.9	349.5	346.0
60°	326.8	329.5	328.9	327.8	328.9	329.5	326.8	327.3	325.7	323.5	321.3
62.5°	302.1	303.0	303.0	302.7	303.0	303.0	302.1	299.6	298.8	296.7	294.5
65°	264.0	265.1	263.4	265.1	263.4	265.1	264.0	262.4	258.6	257.5	255.4
67.5°	223.0	223.3	224.5	225.3	224.5	223.3	223.0	223.6	221.2	219.1	218.7
70°	197.5	196.9	198.5	200.2	198.5	196.9	197.5	196.4	194.8	193.1	190.9
72.5°	170.6	171.8	171.3	172.4	171.3	171.8	170.6	170.8	169.3	167.1	165.0
75°	131.4	133.1	132.6	134.2	132.6	133.1	131.4	132.6	131.4	129.3	127.1
77.5°	95.0	95.2	95.0	95.9	95.0	95.2	95.0	95.9	94.7	95.4	92.9
80°	72.5	71.4	70.4	72.5	70.4	71.4	72.5	72.5	70.8	72.5	70.8
82.5°	50.4	51.0	50.0	50.0	50.0	51.0	50.4	51.7	51.0	51.7	50.1
85°	23.2	22.7	21.6	21.6	21.6	22.7	23.2	23.2	24.9	23.8	23.8
87.5°	6.8	6.4	6.4	6.0	6.4	6.4	6.8	6.8	6.8	7.7	7.7
90°	12.3	12.4	12.5	12.6	12.5	12.4	12.3	12.2	12.3	12.5	12.6
92.5°	11.9	11.9	12.0	12.0	12.0	11.9	11.9	11.9	11.9	11.8	11.8
95°	23.4	23.2	23.1	22.9	23.1	23.2	23.4	23.6	23.6	23.6	23.6
97.5°	39.7	39.7	39.7	39.7	39.7	39.7	39.7	39.7	39.7	39.7	39.7
100°	50.9	50.8	50.7	50.6	50.7	50.8	50.9	51.0	51.0	51.0	51.0
102.5°	63.3	63.2	63.1	63.0	63.1	63.2	63.3	63.3	63.3	63.3	63.2
105°	82.0	82.0	82.0	82.0	82.0	82.0	82.0	82.0	81.9	81.8	81.6
107.5°	101.0	100.6	100.3	99.9	100.3	100.6	101.0	101.4	101.6	101.5	101.4
110°	114.5	114.2	114.0	113.7	114.0	114.2	114.5	114.7	114.9	114.9	114.9



TEST NUMBER: P331556-930

CATALOG NUMBER: S122DIW-S865D435U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	127.6	127.4	127.3	127.1	127.3	127.4	127.6	127.8	128.0	128.2	128.4
115°	148.5	148.2	148.0	147.7	148.0	148.2	148.5	148.7	148.9	149.0	149.0
117.5°	168.2	168.0	167.7	167.5	167.7	168.0	168.2	168.4	168.7	168.8	169.1
120°	182.1	181.9	181.6	181.4	181.6	181.9	182.1	182.4	182.5	182.5	182.5
122.5°	195.5	195.3	195.1	194.9	195.1	195.3	195.5	195.7	195.8	196.1	196.2
125°	216.0	215.9	215.8	215.7	215.8	215.9	216.0	216.1	216.2	216.5	216.7
127.5°	235.4	235.1	234.9	234.6	234.9	235.1	235.4	235.7	235.9	236.3	236.5
130°	249.2	248.9	248.6	248.3	248.6	248.9	249.2	249.6	249.8	250.0	250.1
132.5°	262.0	261.7	261.5	261.2	261.5	261.7	262.0	262.3	262.6	262.9	263.3
135°	282.2	281.9	281.7	281.4	281.7	281.9	282.2	282.4	282.6	282.7	282.7
137.5°	300.8	300.4	300.1	299.8	300.1	300.4	300.8	301.1	301.3	301.3	301.4
140°	313.5	313.2	312.8	312.5	312.8	313.2	313.5	313.8	314.0	314.0	314.0
142.5°	325.0	324.7	324.3	324.0	324.3	324.7	325.0	325.3	325.5	325.4	325.3
145°	342.3	341.9	341.6	341.3	341.6	341.9	342.3	342.6	342.8	342.7	342.6
147.5°	357.7	357.3	357.0	356.8	357.0	357.3	357.7	358.0	358.1	357.9	357.7
150°	367.5	367.3	367.0	366.8	367.0	367.3	367.5	367.8	367.8	367.5	367.3
152.5°	377.2	376.8	376.6	376.3	376.6	376.8	377.2	377.5	377.5	377.2	376.8
155°	389.7	389.5	389.2	389.0	389.2	389.5	389.7	390.0	389.9	389.5	389.1
157.5°	401.0	400.6	400.3	399.9	400.3	400.6	401.0	401.5	401.4	400.8	400.2
160°	407.6	407.3	407.0	406.7	407.0	407.3	407.6	408.0	407.9	407.4	406.9
162.5°	413.8	413.4	412.9	412.6	412.9	413.4	413.8	414.2	414.1	413.5	412.9
165°	421.6	421.2	420.8	420.4	420.8	421.2	421.6	422.0	421.9	421.3	420.8
167.5°	428.0	427.5	427.1	426.7	427.1	427.5	428.0	428.4	428.4	427.8	427.2
170°	431.5	431.0	430.5	430.0	430.5	431.0	431.5	431.9	431.9	431.3	430.7
172.5°	434.1	433.6	433.1	432.6	433.1	433.6	434.1	434.6	434.6	434.0	433.4
175°	437.0	436.5	436.0	435.5	436.0	436.5	437.0	437.5	437.4	436.8	436.3
177.5°	438.0	437.7	437.2	436.8	437.2	437.7	438.0	438.4	438.4	438.0	437.7
180°	437.7	437.7	437.7	437.7	437.7	437.7	437.7	437.7	437.7	437.7	437.7



TEST NUMBER: P331556-930

CATALOG NUMBER: S122DIW-S865D435U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6
2.5°	1352.7	1357.5	1364.8	1372.6	1377.4	1386.4	1389.0	1393.3	1397.3	1406.4	1415.8
5°	1274.6	1282.1	1300.0	1309.7	1323.2	1339.0	1349.2	1360.1	1372.0	1392.5	1411.4
7.5°	1190.8	1203.5	1225.6	1243.8	1263.1	1285.6	1301.9	1323.2	1341.0	1370.0	1397.7
10°	1135.0	1152.8	1172.9	1194.5	1221.6	1245.4	1268.1	1295.1	1316.8	1351.4	1383.9
12.5°	1084.8	1087.5	1116.1	1140.0	1177.0	1206.4	1232.6	1267.5	1288.7	1329.8	1363.9
15°	997.0	1013.3	1039.3	1058.2	1102.0	1139.3	1176.2	1212.4	1236.7	1287.5	1332.4
17.5°	923.2	938.1	964.7	995.7	1027.2	1064.4	1112.0	1150.1	1183.2	1241.4	1294.5
20°	876.4	894.8	921.9	953.7	981.4	1021.9	1063.1	1106.9	1142.6	1208.0	1270.2
22.5°	836.6	851.1	872.9	904.4	934.6	971.8	1016.8	1064.5	1101.9	1172.6	1235.6
25°	780.6	792.6	806.6	832.6	866.7	907.3	942.4	994.9	1049.5	1115.5	1191.8
27.5°	730.3	738.7	751.1	774.0	800.4	838.3	877.3	927.2	982.1	1053.8	1134.2
30°	699.5	704.9	717.4	736.3	762.2	792.0	831.5	879.1	935.4	1007.9	1087.9
32.5°	672.7	677.7	685.7	703.8	726.4	751.8	787.3	834.9	888.6	959.9	1048.6
35°	632.4	636.2	643.3	657.9	670.3	695.2	725.0	768.2	818.5	886.7	978.7
37.5°	592.3	597.5	601.8	608.0	623.9	640.3	666.2	702.7	752.1	820.9	908.6
40°	565.9	570.2	576.7	579.4	592.4	607.0	628.1	661.6	711.4	774.1	859.7
42.5°	539.1	543.4	547.2	550.4	561.7	574.5	593.5	622.2	666.4	727.4	812.0
45°	502.6	503.1	506.9	512.8	518.3	527.5	541.0	565.9	600.0	657.3	734.1
47.5°	465.5	466.2	466.8	469.4	475.4	483.7	492.8	513.0	543.5	589.2	664.0
50°	440.9	439.9	440.9	443.0	446.9	453.9	464.1	478.7	503.7	546.4	615.1
52.5°	417.1	416.9	416.2	417.1	420.0	424.9	432.1	444.6	466.8	506.1	566.6
55°	380.8	378.1	378.7	376.5	381.4	382.5	387.9	398.2	417.7	444.7	501.5
57.5°	342.3	340.0	337.6	337.0	336.5	339.4	343.7	351.9	366.8	390.4	436.6
60°	317.6	314.9	311.6	310.5	310.5	312.2	314.3	320.2	334.4	355.5	393.3
62.5°	292.4	289.3	287.4	284.5	283.7	285.4	287.5	291.7	301.9	321.6	354.3
65°	253.7	250.0	247.2	246.7	245.6	244.0	245.1	249.4	257.5	273.2	299.1
67.5°	214.9	211.3	210.7	207.5	206.0	206.2	206.0	209.7	214.6	228.1	247.4
70°	189.3	186.6	185.6	182.9	181.8	180.7	179.6	182.9	187.8	199.1	215.9
72.5°	163.4	161.1	158.7	156.5	156.7	155.6	155.4	157.4	161.3	171.8	184.7
75°	126.0	126.6	123.9	121.2	120.7	119.5	119.5	121.2	122.8	130.9	141.2
77.5°	91.4	91.0	88.7	87.9	87.3	86.1	87.3	88.4	89.3	94.7	102.2
80°	69.8	69.8	67.1	67.1	66.5	64.9	66.5	65.5	67.6	73.1	78.4
82.5°	49.9	49.0	48.9	48.0	47.9	46.7	47.5	48.6	49.4	53.2	56.3
85°	24.4	24.4	23.8	23.2	23.8	23.2	23.8	24.4	24.9	26.5	29.2
87.5°	7.7	8.2	8.3	8.3	8.0	8.1	8.2	8.5	9.1	9.4	9.6
90°	12.8	13.0	11.1	9.3	7.5	5.7	4.3	3.3	2.4	1.4	0.4
92.5°	11.7	11.7	11.3	10.9	10.4	10.0	9.5	8.7	8.0	7.3	6.6
95°	23.6	23.6	23.5	23.3	23.2	23.0	22.5	21.7	20.9	20.1	19.2
97.5°	39.7	39.7	39.5	39.1	38.8	38.5	38.0	37.3	36.5	35.8	35.1
100°	51.0	51.0	50.7	50.5	50.2	50.0	49.6	48.9	48.2	47.5	46.9
102.5°	63.2	63.1	62.8	62.5	62.1	61.9	61.4	60.9	60.3	59.8	59.4
105°	81.4	81.3	81.1	81.0	80.8	80.6	80.4	80.1	79.9	79.7	79.4
107.5°	101.3	101.3	101.3	101.3	101.3	101.3	101.1	100.8	100.4	100.0	99.6
110°	114.9	114.9	114.9	114.9	114.9	114.9	114.6	114.1	113.7	113.2	112.7



TEST NUMBER: P331556-930

CATALOG NUMBER: S122DIW-S865D435U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	128.6	128.7	128.8	128.9	129.0	129.1	128.8	128.3	127.8	127.3	126.9
115°	149.1	149.2	149.4	149.5	149.7	149.9	149.7	149.2	148.7	148.2	147.7
117.5°	169.3	169.5	169.9	170.4	170.9	171.3	171.2	170.6	169.9	169.3	168.6
120°	182.5	182.5	183.1	183.8	184.4	185.1	185.1	184.4	183.8	183.1	182.5
122.5°	196.5	196.7	197.1	197.5	198.0	198.5	198.4	197.5	196.7	196.0	195.2
125°	217.0	217.2	217.4	217.7	217.9	218.2	217.9	217.2	216.5	215.7	215.0
127.5°	236.8	237.2	237.4	237.7	238.1	238.3	238.0	237.1	236.1	235.2	234.2
130°	250.3	250.5	250.6	250.8	250.9	251.1	250.6	249.6	248.5	247.4	246.4
132.5°	263.7	264.0	264.0	264.0	263.9	263.9	263.4	262.6	261.7	260.8	260.0
135°	282.8	282.9	282.7	282.6	282.4	282.3	281.8	280.9	280.0	279.1	278.2
137.5°	301.5	301.6	301.3	301.2	300.9	300.7	300.2	299.5	298.7	298.0	297.3
140°	314.0	314.0	313.6	313.2	312.7	312.3	311.8	311.0	310.3	309.6	308.8
142.5°	325.3	325.2	324.9	324.7	324.3	324.1	323.6	322.9	322.1	321.4	320.7
145°	342.5	342.4	341.9	341.4	341.0	340.5	339.9	339.3	338.8	338.2	337.6
147.5°	357.5	357.3	357.0	356.7	356.4	356.0	355.6	354.8	354.2	353.4	352.8
150°	367.0	366.8	366.5	366.2	365.8	365.5	365.1	364.6	364.1	363.6	363.1
152.5°	376.6	376.3	375.9	375.4	375.0	374.7	374.2	373.7	373.2	372.8	372.3
155°	388.7	388.2	388.0	387.8	387.5	387.3	387.0	386.8	386.5	386.2	386.0
157.5°	399.7	399.2	399.0	398.8	398.7	398.5	398.4	398.3	398.1	397.9	397.8
160°	406.4	405.9	405.9	405.8	405.7	405.6	405.5	405.4	405.2	405.0	404.9
162.5°	412.4	411.9	411.8	411.7	411.6	411.6	411.5	411.4	411.4	411.4	411.3
165°	420.2	419.6	419.6	419.6	419.6	419.6	419.6	419.7	419.8	419.9	420.0
167.5°	426.6	426.1	426.1	426.1	426.1	426.1	426.2	426.5	426.7	427.0	427.2
170°	430.2	429.6	429.7	429.7	429.8	429.9	430.1	430.3	430.6	430.8	431.0
172.5°	432.8	432.3	432.4	432.4	432.5	432.6	432.8	433.0	433.3	433.5	433.7
175°	435.7	435.1	435.3	435.5	435.6	435.8	436.0	436.3	436.5	436.8	437.0
177.5°	437.2	436.8	436.9	437.1	437.2	437.3	437.5	437.7	437.9	438.1	438.3
180°	437.7	437.7	437.7	437.7	437.7	437.7	437.7	437.7	437.7	437.7	437.7



TEST NUMBER: P331556-930

CATALOG NUMBER: S122DIW-S865D435U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6
2.5°	1415.0	1417.2	1424.1	1431.0	1438.8	1441.0	1444.5	1441.4	1440.6	1448.8	1454.8
5°	1419.0	1428.7	1447.7	1465.0	1479.6	1489.9	1500.7	1505.0	1513.1	1524.5	1538.6
7.5°	1414.5	1433.4	1463.1	1488.4	1515.9	1535.6	1551.1	1564.3	1580.4	1601.9	1625.4
10°	1409.2	1434.7	1471.0	1501.8	1535.3	1560.7	1581.8	1602.4	1626.2	1656.0	1686.8
12.5°	1399.8	1430.0	1475.3	1511.7	1554.8	1579.8	1608.3	1652.6	1678.1	1719.6	1763.0
15°	1380.6	1414.1	1477.4	1522.3	1571.0	1618.6	1671.1	1713.4	1755.5	1779.9	1841.0
17.5°	1352.2	1401.4	1471.5	1523.9	1585.8	1660.8	1719.7	1767.5	1816.2	1855.7	1886.4
20°	1329.2	1382.7	1462.8	1525.6	1599.1	1679.8	1747.4	1796.1	1838.3	1871.3	1890.2
22.5°	1300.2	1367.6	1445.5	1519.1	1613.0	1692.7	1763.8	1802.1	1837.4	1853.5	1860.8
25°	1254.6	1335.7	1423.9	1513.7	1619.8	1704.1	1769.0	1792.3	1802.5	1786.9	1760.9
27.5°	1205.3	1295.8	1398.9	1503.5	1615.6	1696.7	1743.3	1739.6	1722.2	1671.4	1630.8
30°	1168.6	1268.1	1379.0	1493.1	1605.7	1684.7	1711.7	1684.7	1645.1	1588.4	1530.5
32.5°	1130.0	1233.1	1357.8	1478.4	1587.5	1656.9	1662.8	1616.2	1555.1	1490.5	1418.4
35°	1071.7	1183.2	1317.8	1445.5	1548.8	1592.7	1566.7	1484.5	1412.0	1323.8	1225.3
37.5°	1005.8	1128.9	1264.0	1397.3	1490.9	1502.4	1437.9	1351.4	1249.1	1145.5	1029.6
40°	956.5	1086.9	1225.9	1360.6	1443.3	1431.4	1349.2	1254.0	1132.3	1005.7	898.1
42.5°	912.3	1042.7	1184.3	1316.5	1382.7	1350.1	1254.0	1137.2	1006.3	887.1	788.6
45°	835.8	970.0	1115.0	1242.7	1280.5	1221.6	1094.5	964.6	835.8	736.3	658.4
47.5°	761.6	894.2	1037.8	1150.1	1163.4	1084.1	945.2	811.6	700.9	619.9	564.9
50°	707.1	840.2	982.4	1082.6	1078.2	982.4	839.6	712.5	620.0	554.5	517.7
52.5°	658.2	783.9	920.6	1011.5	988.6	884.2	747.9	635.0	559.0	507.8	474.4
55°	582.1	698.4	828.3	901.3	859.1	743.3	628.1	537.2	480.9	442.5	416.5
57.5°	506.5	615.6	726.8	771.8	725.1	618.2	522.2	456.2	413.9	385.5	368.6
60°	459.8	555.1	654.0	693.0	637.3	542.1	466.4	407.4	373.2	350.0	334.8
62.5°	413.1	498.4	591.7	612.9	562.0	481.5	414.4	365.4	337.4	316.7	302.4
65°	349.5	419.2	490.2	504.2	457.1	394.9	341.9	310.0	285.1	269.9	258.6
67.5°	286.6	342.7	392.9	404.2	363.0	319.8	281.5	253.7	236.8	224.3	214.7
70°	249.4	293.8	334.8	344.1	311.0	272.6	243.4	221.3	206.1	195.3	186.1
72.5°	210.0	247.0	281.2	287.4	260.4	231.1	207.1	189.6	176.3	169.3	160.5
75°	160.7	182.3	208.8	210.4	192.6	174.7	156.4	145.0	137.9	129.3	125.0
77.5°	113.4	130.4	145.5	148.5	137.9	125.7	115.4	106.5	100.5	96.5	92.5
80°	86.6	100.1	106.6	110.4	102.8	94.2	88.2	82.3	78.4	75.7	73.1
82.5°	61.9	70.2	76.3	79.2	75.1	69.9	63.9	60.6	57.6	55.4	54.5
85°	31.4	35.1	39.0	40.0	39.0	36.8	33.5	33.5	31.9	31.4	31.4
87.5°	11.1	13.0	13.2	14.7	14.1	14.5	14.8	14.8	14.7	14.3	13.8
90°	1.4	2.4	3.3	4.3	5.7	7.5	9.3	11.1	13.0	12.8	12.6
92.5°	7.3	8.0	8.7	9.5	10.0	10.4	10.9	11.3	11.7	11.7	11.8
95°	20.1	20.9	21.7	22.5	23.0	23.2	23.3	23.5	23.6	23.6	23.6
97.5°	35.8	36.5	37.3	38.0	38.5	38.8	39.1	39.5	39.7	39.7	39.7
100°	47.5	48.2	48.9	49.6	50.0	50.2	50.5	50.7	51.0	51.0	51.0
102.5°	59.8	60.3	60.9	61.4	61.9	62.1	62.5	62.8	63.1	63.2	63.2
105°	79.7	79.9	80.1	80.4	80.6	80.8	81.0	81.1	81.3	81.4	81.6
107.5°	100.0	100.4	100.8	101.1	101.3	101.3	101.3	101.3	101.3	101.3	101.4
110°	113.2	113.7	114.1	114.6	114.9	114.9	114.9	114.9	114.9	114.9	114.9



TEST NUMBER: P331556-930

CATALOG NUMBER: S122DIW-S865D435U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	127.3	127.8	128.3	128.8	129.1	129.0	128.9	128.8	128.7	128.6	128.4
115°	148.2	148.7	149.2	149.7	149.9	149.7	149.5	149.4	149.2	149.1	149.0
117.5°	169.3	169.9	170.6	171.2	171.3	170.9	170.4	169.9	169.5	169.3	169.1
120°	183.1	183.8	184.4	185.1	185.1	184.4	183.8	183.1	182.5	182.5	182.5
122.5°	196.0	196.7	197.5	198.4	198.5	198.0	197.5	197.1	196.7	196.5	196.2
125°	215.7	216.5	217.2	217.9	218.2	217.9	217.7	217.4	217.2	217.0	216.7
127.5°	235.2	236.1	237.1	238.0	238.3	238.1	237.7	237.4	237.2	236.8	236.5
130°	247.4	248.5	249.6	250.6	251.1	250.9	250.8	250.6	250.5	250.3	250.1
132.5°	260.8	261.7	262.6	263.4	263.9	263.9	264.0	264.0	264.0	263.7	263.3
135°	279.1	280.0	280.9	281.8	282.3	282.4	282.6	282.7	282.9	282.8	282.7
137.5°	298.0	298.7	299.5	300.2	300.7	300.9	301.2	301.3	301.6	301.5	301.4
140°	309.6	310.3	311.0	311.8	312.3	312.7	313.2	313.6	314.0	314.0	314.0
142.5°	321.4	322.1	322.9	323.6	324.1	324.3	324.7	324.9	325.2	325.3	325.3
145°	338.2	338.8	339.3	339.9	340.5	341.0	341.4	341.9	342.4	342.5	342.6
147.5°	353.4	354.2	354.8	355.6	356.0	356.4	356.7	357.0	357.3	357.5	357.7
150°	363.6	364.1	364.6	365.1	365.5	365.8	366.2	366.5	366.8	367.0	367.3
152.5°	372.8	373.2	373.7	374.2	374.7	375.0	375.4	375.9	376.3	376.6	376.8
155°	386.2	386.5	386.8	387.0	387.3	387.5	387.8	388.0	388.2	388.7	389.1
157.5°	397.9	398.1	398.3	398.4	398.5	398.7	398.8	399.0	399.2	399.7	400.2
160°	405.0	405.2	405.4	405.5	405.6	405.7	405.8	405.9	405.9	406.4	406.9
162.5°	411.4	411.4	411.4	411.5	411.6	411.6	411.7	411.8	411.9	412.4	412.9
165°	419.9	419.8	419.7	419.6	419.6	419.6	419.6	419.6	419.6	420.2	420.8
167.5°	427.0	426.7	426.5	426.2	426.1	426.1	426.1	426.1	426.1	426.6	427.2
170°	430.8	430.6	430.3	430.1	429.9	429.8	429.7	429.7	429.6	430.2	430.7
172.5°	433.5	433.3	433.0	432.8	432.6	432.5	432.4	432.4	432.3	432.8	433.4
175°	436.8	436.5	436.3	436.0	435.8	435.6	435.5	435.3	435.1	435.7	436.3
177.5°	438.1	437.9	437.7	437.5	437.3	437.2	437.1	436.9	436.8	437.2	437.7
180°	437.7	437.7	437.7	437.7	437.7	437.7	437.7	437.7	437.7	437.7	437.7



TEST NUMBER: P331556-930

CATALOG NUMBER: S122DIW-S865D435U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6
2.5°	1460.0	1466.1	1466.1	1467.0	1473.9	1473.0	1472.6
5°	1553.7	1562.9	1564.0	1573.8	1580.2	1578.1	1572.1
7.5°	1642.1	1659.2	1672.2	1679.4	1688.0	1693.3	1690.9
10°	1712.2	1737.1	1752.2	1762.5	1775.0	1784.2	1780.9
12.5°	1775.9	1805.5	1826.3	1843.9	1845.5	1857.3	1849.3
15°	1875.1	1906.4	1909.7	1922.6	1933.0	1931.9	1932.4
17.5°	1907.9	1917.9	1919.9	1920.3	1920.4	1916.6	1908.4
20°	1896.1	1892.4	1883.2	1876.2	1863.7	1862.1	1851.3
22.5°	1840.8	1828.8	1805.7	1790.5	1771.1	1766.0	1763.0
25°	1731.7	1705.2	1668.4	1633.2	1623.5	1604.6	1610.0
27.5°	1582.1	1540.8	1500.9	1472.3	1446.5	1418.1	1426.3
30°	1476.9	1430.4	1374.1	1330.8	1303.3	1276.2	1271.3
32.5°	1351.4	1283.2	1220.5	1182.3	1140.1	1123.0	1104.2
35°	1135.0	1068.4	1006.2	952.7	921.9	898.1	876.4
37.5°	940.4	863.7	813.5	770.1	747.9	734.3	737.7
40°	819.6	752.5	715.8	682.7	662.2	652.4	654.6
42.5°	721.8	671.6	641.3	618.6	604.1	598.8	597.5
45°	610.7	582.6	557.7	544.8	537.8	531.8	528.0
47.5°	535.0	512.1	498.1	490.3	484.2	478.1	478.0
50°	489.6	474.4	464.7	456.6	451.8	447.4	451.2
52.5°	454.9	441.2	431.4	424.1	422.3	418.4	418.3
55°	403.6	392.7	385.7	379.2	376.0	373.8	371.1
57.5°	356.9	346.6	340.1	336.0	329.8	327.6	326.8
60°	323.5	315.4	308.9	303.5	300.8	296.4	296.4
62.5°	292.8	284.7	278.6	274.5	270.0	268.3	268.8
65°	248.3	241.8	235.9	231.5	230.5	227.2	228.3
67.5°	207.4	203.1	196.8	194.4	192.4	190.6	189.3
70°	180.2	175.9	172.6	169.3	167.7	167.7	167.7
72.5°	157.2	152.1	150.1	145.9	146.9	145.2	143.5
75°	121.7	118.5	116.8	115.2	112.5	112.5	112.5
77.5°	89.6	88.6	86.7	85.0	84.3	83.7	84.0
80°	69.2	68.7	67.6	67.6	66.5	66.0	64.9
82.5°	53.2	51.9	51.2	50.7	50.5	50.4	50.2
85°	30.3	29.2	29.2	29.8	28.7	28.7	29.2
87.5°	14.2	14.1	13.7	13.7	14.2	13.8	13.8
90°	12.5	12.3	12.2	12.3	12.4	12.5	12.6
92.5°	11.8	11.9	11.9	11.9	11.9	12.0	12.0
95°	23.6	23.6	23.6	23.4	23.2	23.1	22.9
97.5°	39.7	39.7	39.7	39.7	39.7	39.7	39.7
100°	51.0	51.0	51.0	50.9	50.8	50.7	50.6
102.5°	63.3	63.3	63.3	63.3	63.2	63.1	63.0
105°	81.8	81.9	82.0	82.0	82.0	82.0	82.0
107.5°	101.5	101.6	101.4	101.0	100.6	100.3	99.9
110°	114.9	114.9	114.7	114.5	114.2	114.0	113.7



TEST NUMBER: P331556-930

CATALOG NUMBER: S122DIW-S865D435U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	128.2	128.0	127.8	127.6	127.4	127.3	127.1
115°	149.0	148.9	148.7	148.5	148.2	148.0	147.7
117.5°	168.8	168.7	168.4	168.2	168.0	167.7	167.5
120°	182.5	182.5	182.4	182.1	181.9	181.6	181.4
122.5°	196.1	195.8	195.7	195.5	195.3	195.1	194.9
125°	216.5	216.2	216.1	216.0	215.9	215.8	215.7
127.5°	236.3	235.9	235.7	235.4	235.1	234.9	234.6
130°	250.0	249.8	249.6	249.2	248.9	248.6	248.3
132.5°	262.9	262.6	262.3	262.0	261.7	261.5	261.2
135°	282.7	282.6	282.4	282.2	281.9	281.7	281.4
137.5°	301.3	301.3	301.1	300.8	300.4	300.1	299.8
140°	314.0	314.0	313.8	313.5	313.2	312.8	312.5
142.5°	325.4	325.5	325.3	325.0	324.7	324.3	324.0
145°	342.7	342.8	342.6	342.3	341.9	341.6	341.3
147.5°	357.9	358.1	358.0	357.7	357.3	357.0	356.8
150°	367.5	367.8	367.8	367.5	367.3	367.0	366.8
152.5°	377.2	377.5	377.5	377.2	376.8	376.6	376.3
155°	389.5	389.9	390.0	389.7	389.5	389.2	389.0
157.5°	400.8	401.4	401.5	401.0	400.6	400.3	399.9
160°	407.4	407.9	408.0	407.6	407.3	407.0	406.7
162.5°	413.5	414.1	414.2	413.8	413.4	412.9	412.6
165°	421.3	421.9	422.0	421.6	421.2	420.8	420.4
167.5°	427.8	428.4	428.4	428.0	427.5	427.1	426.7
170°	431.3	431.9	431.9	431.5	431.0	430.5	430.0
172.5°	434.0	434.6	434.6	434.1	433.6	433.1	432.6
175°	436.8	437.4	437.5	437.0	436.5	436.0	435.5
177.5°	438.0	438.4	438.4	438.0	437.7	437.2	436.8
180°	437.7	437.7	437.7	437.7	437.7	437.7	437.7

(END OF REPORT)