

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331572-930

Luminaire Tested: **S122DIW-S865D970U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331572-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S865D970U930-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 970 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5602.6 lumens
Efficiency: N/A
Efficacy: 91.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 61.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331572-930

CATALOG NUMBER: S122DIW-S865D970U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331572-930

CATALOG NUMBER: S122DIW-S865D970U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51	51	51	51	51	51	51		
1	98	94	90	86	90	87	83	80	74	71	69	62	60	58	51	49	48	43	43	43	43	43	43	43		
2	89	82	76	70	82	76	70	66	65	61	57	54	51	49	44	42	41	36	36	36	36	36	36	36		
3	81	72	65	59	75	67	60	55	57	52	48	48	44	41	39	37	35	31	31	31	31	31	31	31		
4	75	64	56	50	69	59	52	47	51	45	41	43	39	35	35	32	30	26	26	26	26	26	26	26		
5	68	57	49	43	63	53	46	40	45	40	35	38	34	31	32	29	26	23	23	23	23	23	23	23		
6	63	51	43	37	58	47	40	35	41	35	31	35	30	27	29	25	23	20	20	20	20	20	20	20		
7	58	46	38	32	54	43	36	31	37	31	27	31	27	24	26	23	20	18	18	18	18	18	18	18		
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18	16	16	16	16	16	16	16		
9	50	38	31	26	47	36	29	24	31	25	22	27	22	19	22	19	16	14	14	14	14	14	14	14		
10	47	35	28	23	44	33	26	22	29	23	19	24	20	17	21	17	15	13	13	13	13	13	13	13		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18166	18166	18166
5°	18235	17973	18078
10°	18126	17790	17879
15°	17904	17560	17541
20°	17584	17213	17194
25°	17268	16787	16787
30°	16861	16397	16257
35°	16484	15928	15693
40°	16008	15460	15163
45°	15536	14995	14625
50°	15028	14511	13996
55°	14494	13948	13430
60°	13905	13275	12788
65°	13268	12607	12027
70°	12463	11797	11235
75°	11335	10861	10593
80°	10060	9754	9252
85°	8225	7818	7003



TEST NUMBER: P331572-930

CATALOG NUMBER: S122DIW-S865D970U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	105.8	1.9
10°-20°	297.7	5.3
20°-30°	437.6	7.8
30°-40°	508.3	9.1
40°-50°	507.7	9.1
50°-60°	442.8	7.9
60°-70°	327.4	5.8
70°-80°	185.4	3.3
80°-90°	53.8	1.0
90°-100°	62.0	1.1
100°-110°	192.6	3.4
110°-120°	329.2	5.9
120°-130°	432.9	7.7
130°-140°	485.9	8.7
140°-150°	476.4	8.5
150°-160°	399.6	7.1
160°-170°	265.0	4.7
170°-180°	92.6	1.7
0°-30°	841.1	15.0
0°-40°	1349.3	24.1
0°-60°	2299.8	41.0
0°-90°	2866.4	51.2
90°-120°	583.8	10.4
90°-150°	1979.0	35.3
90°-180°	2736.0	48.8
0°-180°	5602.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1125	1125	1125	1125	1125	
5°	1125	1120	1109	1117	1115	107
15°	1071	1064	1050	1054	1049	301
25°	969	960	942	944	942	446
35°	836	825	808	802	796	522
45°	680	672	657	645	640	525
55°	515	508	496	483	477	460
65°	347	341	330	320	315	343
75°	182	179	174	168	170	194
85°	44	43	42	39	38	51
90°	1	11	29	27	28	4
95°	43	51	53	53	51	49
105°	178	180	182	183	183	188
115°	330	335	334	333	330	327
125°	481	488	486	483	482	429
135°	622	630	632	632	629	480
145°	755	760	766	766	763	471
155°	863	865	868	872	870	397
165°	939	938	938	943	940	265
175°	977	974	973	978	974	93
180°	978	978	978	978	978	



TEST NUMBER: P331572-930

CATALOG NUMBER: S122DIW-S865D970U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1
2.5°	1130.3	1129.4	1128.4	1127.5	1126.5	1124.9	1122.8	1120.7	1118.6	1116.5	1118.4
5°	1125.1	1124.1	1123.2	1122.3	1121.3	1119.5	1116.9	1114.2	1111.6	1108.9	1110.8
7.5°	1115.2	1113.7	1112.2	1110.7	1109.2	1107.1	1104.4	1101.7	1099.0	1096.3	1098.3
10°	1105.6	1104.0	1102.3	1100.6	1098.9	1096.7	1093.7	1090.9	1088.0	1085.1	1087.0
12.5°	1092.7	1091.2	1089.7	1088.2	1086.7	1084.5	1081.7	1078.7	1075.9	1073.0	1074.3
15°	1071.1	1069.6	1068.1	1066.7	1065.3	1063.0	1059.9	1056.7	1053.6	1050.5	1051.4
17.5°	1043.3	1041.9	1040.5	1039.0	1037.5	1035.3	1032.1	1028.9	1025.7	1022.5	1023.7
20°	1023.4	1022.0	1020.6	1019.1	1017.7	1015.3	1011.9	1008.5	1005.2	1001.8	1002.5
22.5°	1003.6	1001.5	999.5	997.4	995.5	992.9	989.7	986.5	983.3	980.2	980.3
25°	969.3	967.4	965.5	963.6	961.6	958.6	954.6	950.5	946.4	942.3	942.8
27.5°	930.4	928.7	926.9	925.2	923.5	921.0	917.8	914.5	911.3	908.1	907.4
30°	904.4	902.5	900.6	898.7	896.7	894.0	890.4	886.8	883.1	879.5	878.8
32.5°	876.8	875.2	873.7	872.1	870.6	867.9	864.1	860.3	856.6	852.7	851.4
35°	836.3	833.9	831.4	829.1	826.6	823.5	819.7	815.9	812.0	808.1	806.7
37.5°	790.6	788.5	786.4	784.2	782.2	779.2	775.3	771.5	767.6	763.8	762.0
40°	759.5	757.6	755.6	753.7	751.8	748.9	745.0	741.2	737.4	733.5	731.3
42.5°	729.2	727.2	725.3	723.4	721.5	718.6	714.8	710.9	707.0	703.2	700.8
45°	680.4	678.8	677.1	675.5	673.8	671.1	667.5	663.9	660.3	656.7	654.0
47.5°	632.0	630.5	628.8	627.3	625.7	623.0	619.2	615.5	611.7	608.0	605.2
50°	598.3	597.0	595.9	594.7	593.5	591.2	587.8	584.4	581.1	577.7	574.4
52.5°	565.4	563.8	562.2	560.6	559.1	556.7	553.5	550.3	547.1	544.0	541.2
55°	514.9	513.6	512.1	510.6	509.2	507.0	504.2	501.2	498.4	495.5	492.6
57.5°	464.3	463.2	462.0	460.9	459.7	457.5	454.4	451.2	448.0	444.8	442.1
60°	430.6	429.6	428.7	427.7	426.7	424.6	421.2	417.8	414.5	411.1	408.5
62.5°	397.7	396.2	394.6	393.1	391.5	389.5	386.9	384.3	381.6	379.1	376.7
65°	347.3	345.8	344.4	342.9	341.5	339.6	337.2	334.8	332.4	330.0	327.8
67.5°	296.0	294.8	293.7	292.5	291.4	289.8	287.6	285.4	283.2	281.0	279.4
70°	264.0	263.0	262.0	261.1	260.2	258.5	256.4	254.2	252.1	249.9	248.3
72.5°	231.1	230.2	229.2	228.2	227.2	226.1	224.7	223.3	221.8	220.5	218.8
75°	181.7	181.2	180.8	180.3	179.9	179.0	177.8	176.6	175.4	174.1	172.8
77.5°	137.6	136.8	136.0	135.2	134.4	133.7	133.2	132.7	132.2	131.8	131.0
80°	108.2	107.9	107.7	107.5	107.2	106.9	106.4	105.9	105.4	104.9	104.2
82.5°	80.5	80.5	80.4	80.3	80.3	80.1	79.8	79.6	79.2	79.0	78.0
85°	44.4	44.1	43.9	43.6	43.4	43.1	42.9	42.6	42.4	42.2	41.5
87.5°	15.7	15.8	15.8	15.9	16.0	16.2	16.6	17.0	17.4	17.9	17.3
90°	0.8	3.0	5.2	7.4	9.6	12.7	16.8	20.8	24.9	28.9	28.5
92.5°	14.7	16.3	17.9	19.6	21.2	22.4	23.4	24.4	25.3	26.3	26.3
95°	43.0	44.8	46.6	48.4	50.3	51.4	51.8	52.1	52.5	52.8	52.8
97.5°	78.4	80.1	81.7	83.3	84.9	86.1	86.7	87.5	88.1	88.9	88.9
100°	104.8	106.3	107.8	109.3	110.7	111.8	112.3	112.8	113.4	114.0	114.0
102.5°	132.6	133.8	134.9	136.2	137.3	138.3	138.9	139.7	140.3	141.0	141.2
105°	177.6	178.1	178.6	179.2	179.8	180.2	180.6	180.9	181.3	181.6	182.1
107.5°	222.8	223.6	224.4	225.2	226.0	226.4	226.4	226.4	226.4	226.4	226.6
110°	251.8	253.0	254.0	255.2	256.2	256.8	256.8	256.8	256.8	256.8	256.8



TEST NUMBER: P331572-930

CATALOG NUMBER: S122DIW-S865D970U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	283.6	284.7	285.8	286.9	288.0	288.5	288.3	288.1	288.0	287.9	287.4
115°	330.3	331.4	332.5	333.6	334.7	335.1	334.7	334.4	333.9	333.6	333.5
117.5°	376.9	378.4	379.8	381.3	382.8	382.9	382.0	380.9	379.9	378.9	378.5
120°	408.0	409.4	410.9	412.4	413.8	413.8	412.4	410.9	409.4	408.0	408.0
122.5°	436.3	438.1	439.9	441.6	443.4	443.8	442.7	441.7	440.7	439.6	439.2
125°	480.6	482.2	483.9	485.6	487.2	487.8	487.2	486.7	486.1	485.6	485.0
127.5°	523.7	525.8	527.9	530.0	532.1	532.8	532.1	531.5	530.8	530.2	529.5
130°	550.8	553.2	555.5	558.0	560.4	561.3	561.0	560.6	560.3	559.9	559.5
132.5°	581.1	583.1	585.1	587.0	589.0	590.0	590.0	590.1	590.2	590.3	589.5
135°	621.8	623.9	625.8	627.9	629.9	631.0	631.4	631.8	632.2	632.5	632.3
137.5°	664.6	666.3	667.9	669.5	671.2	672.3	672.7	673.2	673.7	674.2	674.0
140°	690.3	692.0	693.7	695.3	696.9	698.2	699.2	700.1	701.0	701.9	701.9
142.5°	716.8	718.4	720.1	721.7	723.4	724.6	725.1	725.8	726.4	727.0	727.2
145°	754.7	756.0	757.3	758.6	759.9	761.1	762.2	763.3	764.4	765.5	765.6
147.5°	788.6	790.2	791.7	793.2	794.8	795.9	796.6	797.4	798.1	798.8	799.2
150°	811.7	812.9	813.9	815.1	816.1	817.1	817.8	818.6	819.3	820.0	820.5
152.5°	832.3	833.3	834.5	835.5	836.7	837.6	838.5	839.4	840.2	841.1	841.8
155°	862.9	863.5	864.1	864.6	865.1	865.7	866.3	866.8	867.3	867.9	868.8
157.5°	889.2	889.6	889.9	890.3	890.6	891.0	891.4	891.7	892.0	892.3	893.6
160°	905.1	905.4	905.8	906.1	906.5	906.8	907.0	907.2	907.3	907.5	908.7
162.5°	919.6	919.7	919.7	919.8	919.9	920.0	920.2	920.4	920.6	920.7	922.0
165°	938.9	938.7	938.6	938.3	938.2	938.1	938.1	938.1	938.1	938.1	939.4
167.5°	955.1	954.6	954.0	953.4	952.9	952.6	952.6	952.5	952.5	952.4	953.7
170°	963.7	963.1	962.6	962.1	961.5	961.2	960.9	960.7	960.6	960.4	961.6
172.5°	969.6	969.1	968.5	968.0	967.4	967.0	966.9	966.7	966.5	966.3	967.6
175°	976.9	976.3	975.8	975.3	974.7	974.2	973.9	973.5	973.1	972.7	974.0
177.5°	979.9	979.4	979.0	978.5	978.1	977.7	977.5	977.1	976.9	976.6	977.5
180°	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5



TEST NUMBER: P331572-930

CATALOG NUMBER: S122DIW-S865D970U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1
2.5°	1120.3	1122.3	1124.1	1124.9	1124.5	1124.1	1123.8	1123.4
5°	1112.7	1114.7	1116.6	1117.3	1116.9	1116.4	1115.9	1115.4
7.5°	1100.2	1102.1	1104.1	1104.7	1104.2	1103.7	1103.2	1102.6
10°	1088.9	1090.9	1092.8	1093.4	1092.7	1091.9	1091.2	1090.5
12.5°	1075.7	1077.0	1078.4	1078.8	1078.2	1077.7	1077.2	1076.7
15°	1052.4	1053.4	1054.3	1054.2	1053.0	1051.8	1050.6	1049.4
17.5°	1024.7	1025.9	1027.0	1027.0	1025.8	1024.7	1023.5	1022.4
20°	1003.2	1004.0	1004.7	1004.5	1003.6	1002.7	1001.7	1000.7
22.5°	980.5	980.6	980.7	980.6	979.9	979.3	978.8	978.2
25°	943.3	943.7	944.2	944.2	943.7	943.3	942.8	942.3
27.5°	906.7	906.0	905.2	904.3	903.1	902.0	900.8	899.7
30°	878.1	877.4	876.7	875.8	874.9	873.9	872.9	872.0
32.5°	850.1	848.8	847.5	846.4	845.5	844.5	843.5	842.5
35°	805.3	803.8	802.4	801.0	799.9	798.7	797.4	796.2
37.5°	760.3	758.5	756.7	755.2	754.1	752.9	751.8	750.6
40°	729.2	727.0	724.9	723.3	722.4	721.4	720.4	719.4
42.5°	698.5	696.1	693.8	691.9	690.6	689.3	687.9	686.6
45°	651.4	648.7	646.1	644.3	643.4	642.4	641.4	640.5
47.5°	602.4	599.7	596.9	594.8	593.4	592.0	590.6	589.2
50°	571.0	567.6	564.3	562.0	560.8	559.5	558.4	557.2
52.5°	538.3	535.6	532.8	530.6	529.0	527.4	525.9	524.2
55°	489.8	486.8	484.0	481.9	480.7	479.5	478.3	477.1
57.5°	439.2	436.3	433.5	431.6	430.7	429.8	428.9	428.0
60°	405.9	403.2	400.6	398.8	398.1	397.4	396.6	396.0
62.5°	374.1	371.7	369.2	367.6	366.6	365.7	364.8	363.9
65°	325.6	323.5	321.3	319.6	318.5	317.2	316.0	314.8
67.5°	277.7	276.0	274.3	273.0	272.1	271.1	270.1	269.1
70°	246.5	244.8	243.2	241.8	240.9	239.9	239.0	238.0
72.5°	217.1	215.4	213.8	212.5	211.7	211.0	210.2	209.5
75°	171.3	169.8	168.4	168.0	168.4	168.9	169.3	169.8
77.5°	130.4	129.6	128.9	128.2	127.5	126.9	126.2	125.5
80°	103.5	102.8	102.1	101.4	100.9	100.5	100.0	99.5
82.5°	77.1	76.2	75.3	74.8	74.7	74.6	74.5	74.4
85°	40.8	40.0	39.3	38.8	38.6	38.3	38.1	37.8
87.5°	16.6	16.0	15.3	14.9	14.8	14.6	14.4	14.3
90°	28.1	27.8	27.4	27.3	27.6	27.7	27.9	28.0
92.5°	26.4	26.5	26.6	26.6	26.7	26.7	26.7	26.7
95°	52.8	52.8	52.8	52.7	52.3	51.9	51.5	51.2
97.5°	88.9	88.9	88.9	88.9	88.8	88.8	88.7	88.7
100°	114.0	114.0	114.0	113.9	113.7	113.5	113.3	113.2
102.5°	141.4	141.5	141.6	141.6	141.5	141.2	141.0	140.9
105°	182.4	182.8	183.1	183.4	183.4	183.4	183.4	183.4
107.5°	226.7	226.9	227.0	226.7	225.8	224.9	224.1	223.3
110°	256.8	256.8	256.8	256.6	256.0	255.4	254.9	254.4



TEST NUMBER: P331572-930

CATALOG NUMBER: S122DIW-S865D970U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	287.0	286.6	286.1	285.7	285.3	284.9	284.5	284.1
115°	333.2	333.0	332.9	332.5	332.0	331.4	330.8	330.3
117.5°	378.0	377.6	377.1	376.6	376.1	375.5	375.0	374.4
120°	408.0	408.0	408.0	407.6	407.1	406.6	406.0	405.4
122.5°	438.8	438.3	437.9	437.5	437.1	436.7	436.3	435.9
125°	484.5	483.9	483.4	483.0	482.8	482.7	482.4	482.2
127.5°	528.8	528.2	527.5	526.8	526.3	525.7	525.1	524.6
130°	559.1	558.8	558.4	557.8	557.1	556.4	555.6	554.9
132.5°	588.6	587.8	587.0	586.4	585.8	585.1	584.6	584.0
135°	632.2	632.0	631.8	631.4	630.9	630.3	629.8	629.2
137.5°	673.8	673.8	673.6	673.1	672.4	671.6	670.9	670.2
140°	701.9	701.9	701.9	701.6	700.8	700.1	699.4	698.6
142.5°	727.3	727.5	727.6	727.3	726.6	725.9	725.1	724.4
145°	765.9	766.1	766.2	766.0	765.2	764.5	763.8	763.0
147.5°	799.6	800.1	800.5	800.3	799.6	798.9	798.3	797.5
150°	821.1	821.7	822.2	822.2	821.7	821.1	820.5	820.0
152.5°	842.5	843.3	843.9	843.9	843.3	842.5	841.8	841.1
155°	869.8	870.7	871.6	871.7	871.2	870.7	870.1	869.5
157.5°	894.9	896.1	897.3	897.5	896.7	895.8	894.9	894.0
160°	909.7	910.9	911.9	912.2	911.4	910.7	910.0	909.2
162.5°	923.2	924.5	925.8	925.9	925.0	924.1	923.2	922.4
165°	940.7	941.9	943.2	943.4	942.5	941.6	940.7	939.7
167.5°	955.0	956.3	957.6	957.7	956.8	955.9	954.9	954.0
170°	963.0	964.3	965.6	965.6	964.5	963.4	962.3	961.2
172.5°	968.9	970.2	971.4	971.6	970.5	969.4	968.2	967.2
175°	975.3	976.6	977.9	978.0	976.9	975.8	974.7	973.6
177.5°	978.4	979.2	980.1	980.1	979.2	978.4	977.5	976.6
180°	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5

(END OF REPORT)