

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331774-930

Luminaire Tested: **S122RDIW-S290D970U930-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331774-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S290D970U930-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 970 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3661.2 lumens
Efficiency: N/A
Efficacy: 96.3 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 38
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331774-930

CATALOG NUMBER: S122RDIW-S290D970U930-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331774-930

CATALOG NUMBER: S122RDIW-S290D970U930-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	33	33	33	25
1	93	89	85	82	82	79	76	73	61	59	58	45	44	43	30	29	29	22
2	85	78	72	67	75	70	65	61	54	51	48	40	38	36	27	26	25	19
3	77	69	62	57	69	62	56	51	48	44	41	36	33	31	24	23	22	17
4	71	61	54	48	63	55	49	44	43	39	35	32	29	27	22	20	19	15
5	65	54	47	41	58	49	42	38	39	34	31	29	26	24	20	18	17	13
6	60	49	41	36	53	44	37	33	35	30	27	26	23	21	18	16	15	12
7	56	44	37	31	49	40	33	29	32	27	24	24	21	19	17	15	14	11
8	52	40	33	28	46	36	30	26	29	24	21	22	19	17	16	14	12	10
9	48	36	29	25	43	33	27	23	26	22	19	20	17	15	14	13	11	9
10	45	33	27	22	40	30	24	20	24	20	17	19	16	14	13	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8606	8606	8606	8606
5°	9611	8660	7679	8660
10°	10663	8599	6655	8599
15°	11188	8473	5244	8473
20°	9699	8285	4538	8285
25°	6360	8031	4051	8031
30°	4282	7720	3667	7720
35°	3467	7330	3307	7330
40°	3084	6905	3060	6905
45°	2790	6405	2731	6405
50°	2539	5913	2532	5913
55°	2387	5362	2356	5362
60°	1999	4863	1973	4863
65°	1685	4413	1910	4413
70°	1553	3942	1803	3942
75°	1454	3431	1666	3431
80°	1339	2827	1478	2827
85°	1241	2242	1297	2242



TEST NUMBER: P331774-930

CATALOG NUMBER: S122RDIW-S290D970U930-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.5	1.4
10°-20°	140.8	3.8
20°-30°	181.4	5.0
30°-40°	172.4	4.7
40°-50°	147.7	4.0
50°-60°	112.5	3.1
60°-70°	71.1	1.9
70°-80°	35.5	1.0
80°-90°	13.1	0.4
90°-100°	62.0	1.7
100°-110°	192.6	5.3
110°-120°	329.2	9.0
120°-130°	432.9	11.8
130°-140°	485.9	13.3
140°-150°	476.4	13.0
150°-160°	399.6	10.9
160°-170°	265.0	7.2
170°-180°	92.6	2.5
0°-30°	372.7	10.2
0°-40°	545.1	14.9
0°-60°	805.3	22.0
0°-90°	925.0	25.3
90°-120°	583.8	15.9
90°-150°	1979.0	54.1
90°-180°	2736.0	74.7
0°-180°	3661.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	533	533	533	533	533	
5°	593	534	474	534	593	59
15°	669	507	314	507	669	181
25°	357	451	227	451	357	169
35°	176	372	168	372	176	113
45°	122	280	120	280	122	95
55°	85	190	84	190	85	74
65°	44	116	50	116	44	45
75°	23	55	27	55	23	25
85°	7	12	7	12	7	8
90°	28	1	28	1	28	12
95°	51	43	51	43	51	57
105°	183	178	183	178	183	193
115°	330	330	330	330	330	326
125°	482	481	482	481	482	430
135°	629	622	629	622	629	484
145°	763	755	763	755	763	476
155°	870	863	870	863	870	400
165°	940	939	940	939	940	265
175°	974	977	974	977	974	92
180°	978	978	978	978	978	



TEST NUMBER: P331774-930

CATALOG NUMBER: S122RDIW-S290D970U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0
2.5°	554.6	555.1	555.5	554.5	554.5	553.6	551.6	550.2	546.0	545.4	545.4
5°	593.0	592.6	593.4	590.9	587.7	586.9	583.3	578.7	573.9	568.6	567.4
7.5°	631.1	630.6	629.1	628.7	626.1	620.5	614.9	608.9	600.9	593.0	589.1
10°	650.4	656.6	652.8	646.4	647.6	639.0	634.3	626.3	619.6	608.0	605.4
12.5°	669.4	671.8	670.6	666.9	665.3	659.3	653.0	646.0	633.7	623.3	614.2
15°	669.3	672.8	673.8	672.6	673.5	673.2	669.8	664.1	653.4	641.9	631.9
17.5°	619.9	622.3	628.4	632.5	637.7	648.7	654.1	656.2	654.6	648.0	641.0
20°	564.5	560.4	577.5	586.1	593.5	612.0	628.0	634.1	643.9	643.8	641.9
22.5°	485.9	486.9	503.0	513.4	535.0	553.6	571.7	594.7	613.7	626.2	633.6
25°	357.0	364.1	380.2	394.3	418.3	452.8	484.1	520.4	554.6	581.7	607.5
27.5°	268.2	268.7	281.4	294.5	308.8	337.0	376.4	419.7	468.6	508.9	555.2
30°	229.7	228.5	233.9	241.9	254.1	276.0	305.6	348.1	396.9	457.6	511.7
32.5°	202.4	202.4	206.5	212.4	222.5	237.3	257.6	292.2	338.2	397.9	461.3
35°	175.9	175.8	178.7	183.0	187.2	196.7	210.6	228.7	260.4	316.1	380.9
37.5°	156.9	157.8	159.2	161.9	166.6	171.9	180.2	192.4	214.9	247.9	302.4
40°	146.3	146.7	148.7	150.9	153.7	157.8	164.6	174.5	190.9	217.2	257.1
42.5°	136.6	136.9	138.4	140.4	142.6	146.7	152.4	160.9	174.2	194.7	227.6
45°	122.2	122.2	123.5	124.4	126.9	130.5	135.2	142.3	151.5	166.6	188.5
47.5°	108.8	108.8	109.7	111.3	112.8	115.7	120.3	126.0	132.7	144.5	163.1
50°	101.1	101.3	101.8	103.1	104.1	106.6	110.2	115.2	122.2	131.3	146.8
52.5°	94.9	94.8	95.5	96.0	96.7	98.5	101.2	105.6	111.9	119.8	132.6
55°	84.8	84.1	85.2	86.1	86.7	87.4	88.9	91.6	97.0	103.7	113.3
57.5°	72.2	71.9	72.7	73.5	75.3	77.3	78.6	80.3	83.1	87.9	97.4
60°	61.9	61.9	63.5	64.1	66.1	68.7	71.3	72.8	75.6	78.7	85.8
62.5°	52.7	52.8	53.6	54.1	55.3	58.5	62.1	65.4	68.0	71.0	75.7
65°	44.1	44.4	44.4	44.8	45.6	46.3	47.8	50.4	55.0	59.3	62.8
67.5°	37.4	37.5	37.7	38.0	38.2	39.0	39.6	40.8	41.8	45.8	50.2
70°	32.9	33.5	33.3	33.7	33.9	34.2	35.0	35.5	37.3	38.2	40.8
72.5°	28.8	29.2	29.2	29.4	29.9	30.0	30.6	31.1	32.2	32.9	34.4
75°	23.3	23.2	23.3	23.7	23.9	24.1	24.1	24.8	25.4	26.1	27.1
77.5°	18.0	18.2	18.2	18.2	18.3	18.6	18.5	18.8	19.4	19.8	20.2
80°	14.4	14.6	14.4	14.6	14.8	15.0	14.8	15.0	15.6	15.9	15.9
82.5°	11.2	11.3	11.3	11.3	11.4	11.4	11.7	11.7	12.1	12.1	12.2
85°	6.7	6.5	6.5	6.5	6.7	6.8	6.7	6.7	6.8	6.8	6.8
87.5°	8.0	8.1	8.1	8.0	8.0	8.0	8.1	8.3	8.2	8.5	7.5
90°	28.0	27.9	27.7	27.6	27.3	27.4	27.8	28.1	28.5	28.9	24.9
92.5°	26.7	26.7	26.7	26.7	26.6	26.6	26.5	26.4	26.3	26.3	25.3
95°	51.2	51.5	51.9	52.3	52.7	52.8	52.8	52.8	52.8	52.8	52.5
97.5°	88.7	88.7	88.8	88.8	88.9	88.9	88.9	88.9	88.9	88.9	88.1
100°	113.2	113.3	113.5	113.7	113.9	114.0	114.0	114.0	114.0	114.0	113.4
102.5°	140.9	141.0	141.2	141.5	141.6	141.6	141.5	141.4	141.2	141.0	140.3
105°	183.4	183.4	183.4	183.4	183.4	183.1	182.8	182.4	182.1	181.6	181.3
107.5°	223.3	224.1	224.9	225.8	226.7	227.0	226.9	226.7	226.6	226.4	226.4
110°	254.4	254.9	255.4	256.0	256.6	256.8	256.8	256.8	256.8	256.8	256.8



TEST NUMBER: P331774-930

CATALOG NUMBER: S122RDIW-S290D970U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	284.1	284.5	284.9	285.3	285.7	286.1	286.6	287.0	287.4	287.9	288.0
115°	330.3	330.8	331.4	332.0	332.5	332.9	333.0	333.2	333.5	333.6	333.9
117.5°	374.4	375.0	375.5	376.1	376.6	377.1	377.6	378.0	378.5	378.9	379.9
120°	405.4	406.0	406.6	407.1	407.6	408.0	408.0	408.0	408.0	408.0	409.4
122.5°	435.9	436.3	436.7	437.1	437.5	437.9	438.3	438.8	439.2	439.6	440.7
125°	482.2	482.4	482.7	482.8	483.0	483.4	483.9	484.5	485.0	485.6	486.1
127.5°	524.6	525.1	525.7	526.3	526.8	527.5	528.2	528.8	529.5	530.2	530.8
130°	554.9	555.6	556.4	557.1	557.8	558.4	558.8	559.1	559.5	559.9	560.3
132.5°	584.0	584.6	585.1	585.8	586.4	587.0	587.8	588.6	589.5	590.3	590.2
135°	629.2	629.8	630.3	630.9	631.4	631.8	632.0	632.2	632.3	632.5	632.2
137.5°	670.2	670.9	671.6	672.4	673.1	673.6	673.8	673.8	674.0	674.2	673.7
140°	698.6	699.4	700.1	700.8	701.6	701.9	701.9	701.9	701.9	701.9	701.0
142.5°	724.4	725.1	725.9	726.6	727.3	727.6	727.5	727.3	727.2	727.0	726.4
145°	763.0	763.8	764.5	765.2	766.0	766.2	766.1	765.9	765.6	765.5	764.4
147.5°	797.5	798.3	798.9	799.6	800.3	800.5	800.1	799.6	799.2	798.8	798.1
150°	820.0	820.5	821.1	821.7	822.2	822.2	821.7	821.1	820.5	820.0	819.3
152.5°	841.1	841.8	842.5	843.3	843.9	843.9	843.3	842.5	841.8	841.1	840.2
155°	869.5	870.1	870.7	871.2	871.7	871.6	870.7	869.8	868.8	867.9	867.3
157.5°	894.0	894.9	895.8	896.7	897.5	897.3	896.1	894.9	893.6	892.3	892.0
160°	909.2	910.0	910.7	911.4	912.2	911.9	910.9	909.7	908.7	907.5	907.3
162.5°	922.4	923.2	924.1	925.0	925.9	925.8	924.5	923.2	922.0	920.7	920.6
165°	939.7	940.7	941.6	942.5	943.4	943.2	941.9	940.7	939.4	938.1	938.1
167.5°	954.0	954.9	955.9	956.8	957.7	957.6	956.3	955.0	953.7	952.4	952.5
170°	961.2	962.3	963.4	964.5	965.6	965.6	964.3	963.0	961.6	960.4	960.6
172.5°	967.2	968.2	969.4	970.5	971.6	971.4	970.2	968.9	967.6	966.3	966.5
175°	973.6	974.7	975.8	976.9	978.0	977.9	976.6	975.3	974.0	972.7	973.1
177.5°	976.6	977.5	978.4	979.2	980.1	980.1	979.2	978.4	977.5	976.6	976.9
180°	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5



TEST NUMBER: P331774-930

CATALOG NUMBER: S122RDIW-S290D970U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0
2.5°	545.8	544.5	543.5	540.9	539.5	536.5	536.1	536.0	532.1	528.4	527.3
5°	564.5	561.5	557.1	551.9	546.5	541.0	537.3	534.3	526.8	519.8	515.8
7.5°	583.3	577.0	569.3	559.5	551.3	542.2	535.3	529.2	518.7	508.6	501.8
10°	597.5	587.1	576.9	563.4	552.8	542.4	532.8	524.5	512.7	499.3	489.8
12.5°	606.2	594.8	580.7	567.5	553.8	540.6	527.7	517.1	503.1	489.3	478.2
15°	618.0	605.8	588.7	569.8	552.3	535.0	520.2	506.9	488.8	472.2	458.5
17.5°	627.7	610.8	592.6	570.7	550.3	528.5	509.4	492.4	472.1	452.2	436.1
20°	630.8	614.1	593.0	571.1	547.1	521.3	500.8	482.2	460.6	438.9	420.4
22.5°	628.8	615.9	592.4	566.2	541.6	514.7	491.5	469.9	445.9	423.8	402.4
25°	615.8	611.3	589.1	560.6	532.5	501.2	474.3	450.8	423.4	399.7	376.3
27.5°	585.3	594.9	581.1	550.7	519.4	485.9	455.7	428.9	400.5	373.8	350.6
30°	556.0	578.0	572.1	543.9	508.9	476.0	442.1	414.1	383.8	356.3	333.4
32.5°	515.8	552.2	558.0	534.4	498.2	462.0	426.5	398.7	367.0	338.1	315.7
35°	451.8	506.3	531.3	516.3	480.0	440.9	404.3	371.9	340.0	311.5	289.3
37.5°	375.6	449.8	491.5	492.5	459.2	418.6	378.6	346.4	313.8	285.8	261.8
40°	326.1	406.5	460.8	472.8	444.7	400.8	360.4	327.6	295.8	268.3	240.8
42.5°	281.7	361.7	428.4	449.4	427.1	383.4	342.9	308.7	277.7	251.8	223.6
45°	227.8	297.8	371.3	408.7	396.3	356.0	313.2	280.5	251.5	229.1	202.0
47.5°	192.2	241.5	312.7	363.2	363.1	326.2	284.1	252.9	225.9	204.9	183.0
50°	171.9	214.8	275.0	332.4	337.2	306.3	266.3	235.4	210.2	188.2	170.6
52.5°	153.6	189.1	243.1	298.2	311.9	285.1	246.3	217.8	193.3	173.0	158.0
55°	129.8	157.3	198.4	249.8	270.6	251.7	217.2	190.5	170.7	153.7	140.7
57.5°	109.8	130.4	163.4	204.8	228.9	217.1	188.7	167.0	150.0	134.6	124.4
60°	97.3	114.1	142.0	176.7	203.3	195.0	170.7	150.6	136.2	122.8	113.2
62.5°	85.4	99.9	123.8	152.0	176.3	172.9	153.1	136.2	123.5	111.4	103.2
65°	68.7	79.2	98.0	120.0	139.7	141.3	127.0	115.5	104.3	94.7	87.4
67.5°	54.7	61.6	74.8	93.4	108.0	113.3	104.6	95.8	86.8	79.4	73.1
70°	46.1	51.7	61.3	76.3	89.8	95.4	90.3	83.5	75.7	69.6	64.2
72.5°	37.3	42.8	49.9	60.9	72.5	78.5	76.7	71.8	65.6	60.4	55.4
75°	28.1	29.8	34.7	42.1	51.1	56.3	57.6	55.0	50.0	46.1	43.1
77.5°	20.8	21.9	24.1	28.0	33.9	38.6	40.4	40.1	36.7	34.5	31.6
80°	16.6	17.2	18.3	20.0	24.5	29.1	30.4	30.4	28.0	27.1	24.3
82.5°	12.6	13.0	13.8	14.7	16.7	20.8	22.3	22.5	21.0	19.8	17.6
85°	7.3	7.0	7.4	8.0	8.3	9.5	11.7	12.1	11.7	10.2	9.6
87.5°	6.7	6.0	5.2	4.5	4.2	3.8	4.2	4.5	4.3	4.3	4.5
90°	20.8	16.8	12.7	9.6	7.4	5.2	3.0	0.8	3.0	5.2	7.4
92.5°	24.4	23.4	22.4	21.2	19.6	17.9	16.3	14.7	16.3	17.9	19.6
95°	52.1	51.8	51.4	50.3	48.4	46.6	44.8	43.0	44.8	46.6	48.4
97.5°	87.5	86.7	86.1	84.9	83.3	81.7	80.1	78.4	80.1	81.7	83.3
100°	112.8	112.3	111.8	110.7	109.3	107.8	106.3	104.8	106.3	107.8	109.3
102.5°	139.7	138.9	138.3	137.3	136.2	134.9	133.8	132.6	133.8	134.9	136.2
105°	180.9	180.6	180.2	179.8	179.2	178.6	178.1	177.6	178.1	178.6	179.2
107.5°	226.4	226.4	226.4	226.0	225.2	224.4	223.6	222.8	223.6	224.4	225.2
110°	256.8	256.8	256.8	256.2	255.2	254.0	253.0	251.8	253.0	254.0	255.2



TEST NUMBER: P331774-930

CATALOG NUMBER: S122RDIW-S290D970U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	288.1	288.3	288.5	288.0	286.9	285.8	284.7	283.6	284.7	285.8	286.9
115°	334.4	334.7	335.1	334.7	333.6	332.5	331.4	330.3	331.4	332.5	333.6
117.5°	380.9	382.0	382.9	382.8	381.3	379.8	378.4	376.9	378.4	379.8	381.3
120°	410.9	412.4	413.8	413.8	412.4	410.9	409.4	408.0	409.4	410.9	412.4
122.5°	441.7	442.7	443.8	443.4	441.6	439.9	438.1	436.3	438.1	439.9	441.6
125°	486.7	487.2	487.8	487.2	485.6	483.9	482.2	480.6	482.2	483.9	485.6
127.5°	531.5	532.1	532.8	532.1	530.0	527.9	525.8	523.7	525.8	527.9	530.0
130°	560.6	561.0	561.3	560.4	558.0	555.5	553.2	550.8	553.2	555.5	558.0
132.5°	590.1	590.0	590.0	589.0	587.0	585.1	583.1	581.1	583.1	585.1	587.0
135°	631.8	631.4	631.0	629.9	627.9	625.8	623.9	621.8	623.9	625.8	627.9
137.5°	673.2	672.7	672.3	671.2	669.5	667.9	666.3	664.6	666.3	667.9	669.5
140°	700.1	699.2	698.2	696.9	695.3	693.7	692.0	690.3	692.0	693.7	695.3
142.5°	725.8	725.1	724.6	723.4	721.7	720.1	718.4	716.8	718.4	720.1	721.7
145°	763.3	762.2	761.1	759.9	758.6	757.3	756.0	754.7	756.0	757.3	758.6
147.5°	797.4	796.6	795.9	794.8	793.2	791.7	790.2	788.6	790.2	791.7	793.2
150°	818.6	817.8	817.1	816.1	815.1	813.9	812.9	811.7	812.9	813.9	815.1
152.5°	839.4	838.5	837.6	836.7	835.5	834.5	833.3	832.3	833.3	834.5	835.5
155°	866.8	866.3	865.7	865.1	864.6	864.1	863.5	862.9	863.5	864.1	864.6
157.5°	891.7	891.4	891.0	890.6	890.3	889.9	889.6	889.2	889.6	889.9	890.3
160°	907.2	907.0	906.8	906.5	906.1	905.8	905.4	905.1	905.4	905.8	906.1
162.5°	920.4	920.2	920.0	919.9	919.8	919.7	919.7	919.6	919.7	919.7	919.8
165°	938.1	938.1	938.1	938.2	938.3	938.6	938.7	938.9	938.7	938.6	938.3
167.5°	952.5	952.6	952.6	952.9	953.4	954.0	954.6	955.1	954.6	954.0	953.4
170°	960.7	960.9	961.2	961.5	962.1	962.6	963.1	963.7	963.1	962.6	962.1
172.5°	966.7	966.9	967.0	967.4	968.0	968.5	969.1	969.6	969.1	968.5	968.0
175°	973.5	973.9	974.2	974.7	975.3	975.8	976.3	976.9	976.3	975.8	975.3
177.5°	977.1	977.5	977.7	978.1	978.5	979.0	979.4	979.9	979.4	979.0	978.5
180°	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5



TEST NUMBER: P331774-930

CATALOG NUMBER: S122RDIW-S290D970U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0
2.5°	525.5	524.4	522.4	519.5	517.7	514.6	512.6	513.7	514.0	513.7	513.5
5°	511.4	507.4	502.1	496.8	492.0	486.9	483.9	482.7	480.0	478.6	477.8
7.5°	494.2	487.5	480.0	470.9	463.3	455.2	451.1	449.1	443.8	440.9	438.4
10°	481.5	470.9	463.3	451.5	444.3	433.7	426.5	426.7	419.5	415.4	412.5
12.5°	467.4	455.8	443.2	432.5	422.5	414.0	405.3	401.8	394.1	390.2	382.2
15°	444.1	430.6	417.3	402.8	392.6	379.4	366.9	351.5	339.1	328.3	325.4
17.5°	418.7	401.9	388.5	371.5	354.1	332.0	317.4	308.4	301.0	295.3	291.1
20°	401.1	384.1	369.8	344.3	320.7	305.7	295.1	288.1	280.4	274.3	270.9
22.5°	382.8	365.0	345.5	317.0	298.6	286.7	277.1	269.2	263.9	259.2	256.1
25°	356.7	337.2	305.2	285.6	270.8	258.1	251.5	246.7	241.2	234.6	231.7
27.5°	329.1	298.2	275.2	260.6	246.5	238.3	232.3	225.1	220.1	217.2	214.1
30°	308.5	277.6	259.7	243.7	233.7	224.6	217.6	213.5	208.7	203.7	201.7
32.5°	285.6	260.9	243.6	230.4	220.2	212.5	206.9	200.3	196.9	193.8	189.6
35°	257.1	238.3	222.6	211.9	202.2	195.9	189.5	185.6	179.3	176.7	175.0
37.5°	232.9	216.7	205.0	193.6	186.0	179.0	175.0	168.8	166.2	162.5	159.0
40°	219.2	203.3	192.1	182.8	174.2	169.1	164.1	159.1	155.0	153.4	149.1
42.5°	205.4	192.4	181.1	171.0	165.3	159.7	153.4	149.8	145.5	142.8	140.2
45°	186.1	174.6	165.0	156.7	150.3	144.6	140.6	134.4	132.1	126.7	124.4
47.5°	169.3	158.6	149.4	141.5	135.3	131.6	125.6	120.8	117.0	113.7	110.8
50°	157.3	148.3	139.4	132.4	126.9	121.5	115.4	113.0	107.0	105.3	103.7
52.5°	146.3	137.8	129.7	122.8	117.2	112.0	106.6	103.5	99.5	97.8	96.6
55°	130.9	122.8	115.0	108.9	103.4	98.0	94.7	90.7	88.9	87.6	86.1
57.5°	115.5	108.2	102.2	96.0	90.4	86.2	82.3	80.0	78.1	76.4	74.6
60°	105.7	98.7	93.4	87.6	81.9	78.4	75.4	72.6	70.4	67.8	67.0
62.5°	95.4	89.2	84.3	78.7	73.7	70.5	67.7	65.1	62.4	58.6	57.6
65°	81.1	76.3	71.1	66.4	62.0	58.9	54.8	51.9	50.7	50.4	50.2
67.5°	68.2	63.7	59.2	54.5	50.5	47.5	45.4	45.0	44.2	44.0	43.5
70°	59.6	55.4	51.0	46.5	42.6	42.1	41.3	40.5	39.6	39.3	38.9
72.5°	51.9	47.5	43.0	39.5	37.8	37.2	36.4	35.6	35.1	34.7	34.5
75°	39.8	35.7	32.8	31.5	30.6	30.0	28.9	28.4	28.0	27.4	27.2
77.5°	28.7	26.3	25.0	24.2	23.2	22.7	22.0	21.4	21.0	21.0	20.6
80°	21.9	20.7	19.8	18.7	18.3	17.6	17.4	16.9	17.0	16.5	16.5
82.5°	17.0	15.6	14.8	14.3	13.9	13.3	13.1	12.9	12.9	12.5	12.5
85°	8.7	8.3	8.0	7.6	7.6	7.0	7.3	7.0	7.0	6.7	6.5
87.5°	4.7	5.2	5.7	6.5	7.3	8.0	7.9	7.7	7.7	7.6	7.4
90°	9.6	12.7	16.8	20.8	24.9	28.9	28.5	28.1	27.8	27.4	27.3
92.5°	21.2	22.4	23.4	24.4	25.3	26.3	26.3	26.4	26.5	26.6	26.6
95°	50.3	51.4	51.8	52.1	52.5	52.8	52.8	52.8	52.8	52.8	52.7
97.5°	84.9	86.1	86.7	87.5	88.1	88.9	88.9	88.9	88.9	88.9	88.9
100°	110.7	111.8	112.3	112.8	113.4	114.0	114.0	114.0	114.0	114.0	113.9
102.5°	137.3	138.3	138.9	139.7	140.3	141.0	141.2	141.4	141.5	141.6	141.6
105°	179.8	180.2	180.6	180.9	181.3	181.6	182.1	182.4	182.8	183.1	183.4
107.5°	226.0	226.4	226.4	226.4	226.4	226.4	226.6	226.7	226.9	227.0	226.7
110°	256.2	256.8	256.8	256.8	256.8	256.8	256.8	256.8	256.8	256.8	256.6



TEST NUMBER: P331774-930

CATALOG NUMBER: S122RDIW-S290D970U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	288.0	288.5	288.3	288.1	288.0	287.9	287.4	287.0	286.6	286.1	285.7
115°	334.7	335.1	334.7	334.4	333.9	333.6	333.5	333.2	333.0	332.9	332.5
117.5°	382.8	382.9	382.0	380.9	379.9	378.9	378.5	378.0	377.6	377.1	376.6
120°	413.8	413.8	412.4	410.9	409.4	408.0	408.0	408.0	408.0	408.0	407.6
122.5°	443.4	443.8	442.7	441.7	440.7	439.6	439.2	438.8	438.3	437.9	437.5
125°	487.2	487.8	487.2	486.7	486.1	485.6	485.0	484.5	483.9	483.4	483.0
127.5°	532.1	532.8	532.1	531.5	530.8	530.2	529.5	528.8	528.2	527.5	526.8
130°	560.4	561.3	561.0	560.6	560.3	559.9	559.5	559.1	558.8	558.4	557.8
132.5°	589.0	590.0	590.0	590.1	590.2	590.3	589.5	588.6	587.8	587.0	586.4
135°	629.9	631.0	631.4	631.8	632.2	632.5	632.3	632.2	632.0	631.8	631.4
137.5°	671.2	672.3	672.7	673.2	673.7	674.2	674.0	673.8	673.8	673.6	673.1
140°	696.9	698.2	699.2	700.1	701.0	701.9	701.9	701.9	701.9	701.9	701.6
142.5°	723.4	724.6	725.1	725.8	726.4	727.0	727.2	727.3	727.5	727.6	727.3
145°	759.9	761.1	762.2	763.3	764.4	765.5	765.6	765.9	766.1	766.2	766.0
147.5°	794.8	795.9	796.6	797.4	798.1	798.8	799.2	799.6	800.1	800.5	800.3
150°	816.1	817.1	817.8	818.6	819.3	820.0	820.5	821.1	821.7	822.2	822.2
152.5°	836.7	837.6	838.5	839.4	840.2	841.1	841.8	842.5	843.3	843.9	843.9
155°	865.1	865.7	866.3	866.8	867.3	867.9	868.8	869.8	870.7	871.6	871.7
157.5°	890.6	891.0	891.4	891.7	892.0	892.3	893.6	894.9	896.1	897.3	897.5
160°	906.5	906.8	907.0	907.2	907.3	907.5	908.7	909.7	910.9	911.9	912.2
162.5°	919.9	920.0	920.2	920.4	920.6	920.7	922.0	923.2	924.5	925.8	925.9
165°	938.2	938.1	938.1	938.1	938.1	938.1	939.4	940.7	941.9	943.2	943.4
167.5°	952.9	952.6	952.6	952.5	952.5	952.4	953.7	955.0	956.3	957.6	957.7
170°	961.5	961.2	960.9	960.7	960.6	960.4	961.6	963.0	964.3	965.6	965.6
172.5°	967.4	967.0	966.9	966.7	966.5	966.3	967.6	968.9	970.2	971.4	971.6
175°	974.7	974.2	973.9	973.5	973.1	972.7	974.0	975.3	976.6	977.9	978.0
177.5°	978.1	977.7	977.5	977.1	976.9	976.6	977.5	978.4	979.2	980.1	980.1
180°	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5



TEST NUMBER: P331774-930

CATALOG NUMBER: S122RDIW-S290D970U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0
2.5°	511.8	512.1	511.7	511.9	511.7	512.1	511.8	513.5	513.7	514.0	513.7
5°	476.9	474.7	474.3	473.8	474.3	474.7	476.9	477.8	478.6	480.0	482.7
7.5°	435.2	434.9	433.9	432.6	433.9	434.9	435.2	438.4	440.9	443.8	449.1
10°	408.4	407.4	407.2	405.9	407.2	407.4	408.4	412.5	415.4	419.5	426.7
12.5°	376.9	371.0	370.4	367.1	370.4	371.0	376.9	382.2	390.2	394.1	401.8
15°	321.0	319.8	316.1	313.7	316.1	319.8	321.0	325.4	328.3	339.1	351.5
17.5°	288.9	285.3	284.1	283.6	284.1	285.3	288.9	291.1	295.3	301.0	308.4
20°	268.3	265.1	264.5	264.1	264.5	265.1	268.3	270.9	274.3	280.4	288.1
22.5°	254.1	250.6	249.2	248.1	249.2	250.6	254.1	256.1	259.2	263.9	269.2
25°	229.8	228.5	227.8	227.4	227.8	228.5	229.8	231.7	234.6	241.2	246.7
27.5°	210.8	208.0	207.4	206.4	207.4	208.0	210.8	214.1	217.2	220.1	225.1
30°	200.0	199.1	197.8	196.7	197.8	199.1	200.0	201.7	203.7	208.7	213.5
32.5°	187.3	186.5	185.3	184.8	185.3	186.5	187.3	189.6	193.8	196.9	200.3
35°	173.2	170.6	169.4	167.8	169.4	170.6	173.2	175.0	176.7	179.3	185.6
37.5°	158.2	156.9	155.3	155.9	155.3	156.9	158.2	159.0	162.5	166.2	168.8
40°	146.7	145.8	145.4	145.2	145.4	145.8	146.7	149.1	153.4	155.0	159.1
42.5°	137.5	134.9	134.0	134.0	134.0	134.9	137.5	140.2	142.8	145.5	149.8
45°	123.5	121.2	119.4	119.6	119.4	121.2	123.5	124.4	126.7	132.1	134.4
47.5°	109.3	109.2	108.1	108.4	108.1	109.2	109.3	110.8	113.7	117.0	120.8
50°	102.4	101.3	100.5	100.8	100.5	101.3	102.4	103.7	105.3	107.0	113.0
52.5°	95.9	94.9	94.3	95.1	94.3	94.9	95.9	96.6	97.8	99.5	103.5
55°	85.2	84.1	83.9	83.7	83.9	84.1	85.2	86.1	87.6	88.9	90.7
57.5°	73.2	72.5	71.3	70.9	71.3	72.5	73.2	74.6	76.4	78.1	80.0
60°	64.7	63.2	61.3	61.1	61.3	63.2	64.7	67.0	67.8	70.4	72.6
62.5°	56.7	56.5	56.1	56.1	56.1	56.5	56.7	57.6	58.6	62.4	65.1
65°	49.8	49.7	49.8	50.0	49.8	49.7	49.8	50.2	50.4	50.7	51.9
67.5°	43.4	43.0	42.7	42.9	42.7	43.0	43.4	43.5	44.0	44.2	45.0
70°	38.5	38.3	38.2	38.2	38.2	38.3	38.5	38.9	39.3	39.6	40.5
72.5°	33.8	33.8	33.6	33.4	33.6	33.8	33.8	34.5	34.7	35.1	35.6
75°	27.1	26.7	26.7	26.7	26.7	26.7	27.1	27.2	27.4	28.0	28.4
77.5°	20.6	20.4	20.2	20.1	20.2	20.4	20.6	20.6	21.0	21.0	21.4
80°	16.3	16.1	15.9	15.9	15.9	16.1	16.3	16.5	16.5	17.0	16.9
82.5°	12.5	12.2	12.2	12.1	12.2	12.2	12.5	12.5	12.5	12.9	12.9
85°	6.7	6.8	6.7	7.0	6.7	6.8	6.7	6.5	6.7	7.0	7.0
87.5°	7.4	7.3	7.5	7.4	7.5	7.3	7.4	7.4	7.6	7.7	7.7
90°	27.6	27.7	27.9	28.0	27.9	27.7	27.6	27.3	27.4	27.8	28.1
92.5°	26.7	26.7	26.7	26.7	26.7	26.7	26.7	26.6	26.6	26.5	26.4
95°	52.3	51.9	51.5	51.2	51.5	51.9	52.3	52.7	52.8	52.8	52.8
97.5°	88.8	88.8	88.7	88.7	88.7	88.8	88.8	88.9	88.9	88.9	88.9
100°	113.7	113.5	113.3	113.2	113.3	113.5	113.7	113.9	114.0	114.0	114.0
102.5°	141.5	141.2	141.0	140.9	141.0	141.2	141.5	141.6	141.6	141.5	141.4
105°	183.4	183.4	183.4	183.4	183.4	183.4	183.4	183.4	183.1	182.8	182.4
107.5°	225.8	224.9	224.1	223.3	224.1	224.9	225.8	226.7	227.0	226.9	226.7
110°	256.0	255.4	254.9	254.4	254.9	255.4	256.0	256.6	256.8	256.8	256.8



TEST NUMBER: P331774-930

CATALOG NUMBER: S122RDIW-S290D970U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	285.3	284.9	284.5	284.1	284.5	284.9	285.3	285.7	286.1	286.6	287.0
115°	332.0	331.4	330.8	330.3	330.8	331.4	332.0	332.5	332.9	333.0	333.2
117.5°	376.1	375.5	375.0	374.4	375.0	375.5	376.1	376.6	377.1	377.6	378.0
120°	407.1	406.6	406.0	405.4	406.0	406.6	407.1	407.6	408.0	408.0	408.0
122.5°	437.1	436.7	436.3	435.9	436.3	436.7	437.1	437.5	437.9	438.3	438.8
125°	482.8	482.7	482.4	482.2	482.4	482.7	482.8	483.0	483.4	483.9	484.5
127.5°	526.3	525.7	525.1	524.6	525.1	525.7	526.3	526.8	527.5	528.2	528.8
130°	557.1	556.4	555.6	554.9	555.6	556.4	557.1	557.8	558.4	558.8	559.1
132.5°	585.8	585.1	584.6	584.0	584.6	585.1	585.8	586.4	587.0	587.8	588.6
135°	630.9	630.3	629.8	629.2	629.8	630.3	630.9	631.4	631.8	632.0	632.2
137.5°	672.4	671.6	670.9	670.2	670.9	671.6	672.4	673.1	673.6	673.8	673.8
140°	700.8	700.1	699.4	698.6	699.4	700.1	700.8	701.6	701.9	701.9	701.9
142.5°	726.6	725.9	725.1	724.4	725.1	725.9	726.6	727.3	727.6	727.5	727.3
145°	765.2	764.5	763.8	763.0	763.8	764.5	765.2	766.0	766.2	766.1	765.9
147.5°	799.6	798.9	798.3	797.5	798.3	798.9	799.6	800.3	800.5	800.1	799.6
150°	821.7	821.1	820.5	820.0	820.5	821.1	821.7	822.2	822.2	821.7	821.1
152.5°	843.3	842.5	841.8	841.1	841.8	842.5	843.3	843.9	843.9	843.3	842.5
155°	871.2	870.7	870.1	869.5	870.1	870.7	871.2	871.7	871.6	870.7	869.8
157.5°	896.7	895.8	894.9	894.0	894.9	895.8	896.7	897.5	897.3	896.1	894.9
160°	911.4	910.7	910.0	909.2	910.0	910.7	911.4	912.2	911.9	910.9	909.7
162.5°	925.0	924.1	923.2	922.4	923.2	924.1	925.0	925.9	925.8	924.5	923.2
165°	942.5	941.6	940.7	939.7	940.7	941.6	942.5	943.4	943.2	941.9	940.7
167.5°	956.8	955.9	954.9	954.0	954.9	955.9	956.8	957.7	957.6	956.3	955.0
170°	964.5	963.4	962.3	961.2	962.3	963.4	964.5	965.6	965.6	964.3	963.0
172.5°	970.5	969.4	968.2	967.2	968.2	969.4	970.5	971.6	971.4	970.2	968.9
175°	976.9	975.8	974.7	973.6	974.7	975.8	976.9	978.0	977.9	976.6	975.3
177.5°	979.2	978.4	977.5	976.6	977.5	978.4	979.2	980.1	980.1	979.2	978.4
180°	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5



TEST NUMBER: P331774-930

CATALOG NUMBER: S122RDIW-S290D970U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0
2.5°	512.6	514.6	517.7	519.5	522.4	524.4	525.5	527.3	528.4	532.1	536.0
5°	483.9	486.9	492.0	496.8	502.1	507.4	511.4	515.8	519.8	526.8	534.3
7.5°	451.1	455.2	463.3	470.9	480.0	487.5	494.2	501.8	508.6	518.7	529.2
10°	426.5	433.7	444.3	451.5	463.3	470.9	481.5	489.8	499.3	512.7	524.5
12.5°	405.3	414.0	422.5	432.5	443.2	455.8	467.4	478.2	489.3	503.1	517.1
15°	366.9	379.4	392.6	402.8	417.3	430.6	444.1	458.5	472.2	488.8	506.9
17.5°	317.4	332.0	354.1	371.5	388.5	401.9	418.7	436.1	452.2	472.1	492.4
20°	295.1	305.7	320.7	344.3	369.8	384.1	401.1	420.4	438.9	460.6	482.2
22.5°	277.1	286.7	298.6	317.0	345.5	365.0	382.8	402.4	423.8	445.9	469.9
25°	251.5	258.1	270.8	285.6	305.2	337.2	356.7	376.3	399.7	423.4	450.8
27.5°	232.3	238.3	246.5	260.6	275.2	298.2	329.1	350.6	373.8	400.5	428.9
30°	217.6	224.6	233.7	243.7	259.7	277.6	308.5	333.4	356.3	383.8	414.1
32.5°	206.9	212.5	220.2	230.4	243.6	260.9	285.6	315.7	338.1	367.0	398.7
35°	189.5	195.9	202.2	211.9	222.6	238.3	257.1	289.3	311.5	340.0	371.9
37.5°	175.0	179.0	186.0	193.6	205.0	216.7	232.9	261.8	285.8	313.8	346.4
40°	164.1	169.1	174.2	182.8	192.1	203.3	219.2	240.8	268.3	295.8	327.6
42.5°	153.4	159.7	165.3	171.0	181.1	192.4	205.4	223.6	251.8	277.7	308.7
45°	140.6	144.6	150.3	156.7	165.0	174.6	186.1	202.0	229.1	251.5	280.5
47.5°	125.6	131.6	135.3	141.5	149.4	158.6	169.3	183.0	204.9	225.9	252.9
50°	115.4	121.5	126.9	132.4	139.4	148.3	157.3	170.6	188.2	210.2	235.4
52.5°	106.6	112.0	117.2	122.8	129.7	137.8	146.3	158.0	173.0	193.3	217.8
55°	94.7	98.0	103.4	108.9	115.0	122.8	130.9	140.7	153.7	170.7	190.5
57.5°	82.3	86.2	90.4	96.0	102.2	108.2	115.5	124.4	134.6	150.0	167.0
60°	75.4	78.4	81.9	87.6	93.4	98.7	105.7	113.2	122.8	136.2	150.6
62.5°	67.7	70.5	73.7	78.7	84.3	89.2	95.4	103.2	111.4	123.5	136.2
65°	54.8	58.9	62.0	66.4	71.1	76.3	81.1	87.4	94.7	104.3	115.5
67.5°	45.4	47.5	50.5	54.5	59.2	63.7	68.2	73.1	79.4	86.8	95.8
70°	41.3	42.1	42.6	46.5	51.0	55.4	59.6	64.2	69.6	75.7	83.5
72.5°	36.4	37.2	37.8	39.5	43.0	47.5	51.9	55.4	60.4	65.6	71.8
75°	28.9	30.0	30.6	31.5	32.8	35.7	39.8	43.1	46.1	50.0	55.0
77.5°	22.0	22.7	23.2	24.2	25.0	26.3	28.7	31.6	34.5	36.7	40.1
80°	17.4	17.6	18.3	18.7	19.8	20.7	21.9	24.3	27.1	28.0	30.4
82.5°	13.1	13.3	13.9	14.3	14.8	15.6	17.0	17.6	19.8	21.0	22.5
85°	7.3	7.0	7.6	7.6	8.0	8.3	8.7	9.6	10.2	11.7	12.1
87.5°	7.9	8.0	7.3	6.5	5.7	5.2	4.7	4.5	4.3	4.3	4.5
90°	28.5	28.9	24.9	20.8	16.8	12.7	9.6	7.4	5.2	3.0	0.8
92.5°	26.3	26.3	25.3	24.4	23.4	22.4	21.2	19.6	17.9	16.3	14.7
95°	52.8	52.8	52.5	52.1	51.8	51.4	50.3	48.4	46.6	44.8	43.0
97.5°	88.9	88.9	88.1	87.5	86.7	86.1	84.9	83.3	81.7	80.1	78.4
100°	114.0	114.0	113.4	112.8	112.3	111.8	110.7	109.3	107.8	106.3	104.8
102.5°	141.2	141.0	140.3	139.7	138.9	138.3	137.3	136.2	134.9	133.8	132.6
105°	182.1	181.6	181.3	180.9	180.6	180.2	179.8	179.2	178.6	178.1	177.6
107.5°	226.6	226.4	226.4	226.4	226.4	226.4	226.0	225.2	224.4	223.6	222.8
110°	256.8	256.8	256.8	256.8	256.8	256.8	256.2	255.2	254.0	253.0	251.8



TEST NUMBER: P331774-930

CATALOG NUMBER: S122RDIW-S290D970U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	287.4	287.9	288.0	288.1	288.3	288.5	288.0	286.9	285.8	284.7	283.6
115°	333.5	333.6	333.9	334.4	334.7	335.1	334.7	333.6	332.5	331.4	330.3
117.5°	378.5	378.9	379.9	380.9	382.0	382.9	382.8	381.3	379.8	378.4	376.9
120°	408.0	408.0	409.4	410.9	412.4	413.8	413.8	412.4	410.9	409.4	408.0
122.5°	439.2	439.6	440.7	441.7	442.7	443.8	443.4	441.6	439.9	438.1	436.3
125°	485.0	485.6	486.1	486.7	487.2	487.8	487.2	485.6	483.9	482.2	480.6
127.5°	529.5	530.2	530.8	531.5	532.1	532.8	532.1	530.0	527.9	525.8	523.7
130°	559.5	559.9	560.3	560.6	561.0	561.3	560.4	558.0	555.5	553.2	550.8
132.5°	589.5	590.3	590.2	590.1	590.0	590.0	589.0	587.0	585.1	583.1	581.1
135°	632.3	632.5	632.2	631.8	631.4	631.0	629.9	627.9	625.8	623.9	621.8
137.5°	674.0	674.2	673.7	673.2	672.7	672.3	671.2	669.5	667.9	666.3	664.6
140°	701.9	701.9	701.0	700.1	699.2	698.2	696.9	695.3	693.7	692.0	690.3
142.5°	727.2	727.0	726.4	725.8	725.1	724.6	723.4	721.7	720.1	718.4	716.8
145°	765.6	765.5	764.4	763.3	762.2	761.1	759.9	758.6	757.3	756.0	754.7
147.5°	799.2	798.8	798.1	797.4	796.6	795.9	794.8	793.2	791.7	790.2	788.6
150°	820.5	820.0	819.3	818.6	817.8	817.1	816.1	815.1	813.9	812.9	811.7
152.5°	841.8	841.1	840.2	839.4	838.5	837.6	836.7	835.5	834.5	833.3	832.3
155°	868.8	867.9	867.3	866.8	866.3	865.7	865.1	864.6	864.1	863.5	862.9
157.5°	893.6	892.3	892.0	891.7	891.4	891.0	890.6	890.3	889.9	889.6	889.2
160°	908.7	907.5	907.3	907.2	907.0	906.8	906.5	906.1	905.8	905.4	905.1
162.5°	922.0	920.7	920.6	920.4	920.2	920.0	919.9	919.8	919.7	919.7	919.6
165°	939.4	938.1	938.1	938.1	938.1	938.1	938.2	938.3	938.6	938.7	938.9
167.5°	953.7	952.4	952.5	952.5	952.6	952.6	952.9	953.4	954.0	954.6	955.1
170°	961.6	960.4	960.6	960.7	960.9	961.2	961.5	962.1	962.6	963.1	963.7
172.5°	967.6	966.3	966.5	966.7	966.9	967.0	967.4	968.0	968.5	969.1	969.6
175°	974.0	972.7	973.1	973.5	973.9	974.2	974.7	975.3	975.8	976.3	976.9
177.5°	977.5	976.6	976.9	977.1	977.5	977.7	978.1	978.5	979.0	979.4	979.9
180°	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5



TEST NUMBER: P331774-930

CATALOG NUMBER: S122RDIW-S290D970U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0
2.5°	536.1	536.5	539.5	540.9	543.5	544.5	545.8	545.4	545.4	546.0	550.2
5°	537.3	541.0	546.5	551.9	557.1	561.5	564.5	567.4	568.6	573.9	578.7
7.5°	535.3	542.2	551.3	559.5	569.3	577.0	583.3	589.1	593.0	600.9	608.9
10°	532.8	542.4	552.8	563.4	576.9	587.1	597.5	605.4	608.0	619.6	626.3
12.5°	527.7	540.6	553.8	567.5	580.7	594.8	606.2	614.2	623.3	633.7	646.0
15°	520.2	535.0	552.3	569.8	588.7	605.8	618.0	631.9	641.9	653.4	664.1
17.5°	509.4	528.5	550.3	570.7	592.6	610.8	627.7	641.0	648.0	654.6	656.2
20°	500.8	521.3	547.1	571.1	593.0	614.1	630.8	641.9	643.8	643.9	634.1
22.5°	491.5	514.7	541.6	566.2	592.4	615.9	628.8	633.6	626.2	613.7	594.7
25°	474.3	501.2	532.5	560.6	589.1	611.3	615.8	607.5	581.7	554.6	520.4
27.5°	455.7	485.9	519.4	550.7	581.1	594.9	585.3	555.2	508.9	468.6	419.7
30°	442.1	476.0	508.9	543.9	572.1	578.0	556.0	511.7	457.6	396.9	348.1
32.5°	426.5	462.0	498.2	534.4	558.0	552.2	515.8	461.3	397.9	338.2	292.2
35°	404.3	440.9	480.0	516.3	531.3	506.3	451.8	380.9	316.1	260.4	228.7
37.5°	378.6	418.6	459.2	492.5	491.5	449.8	375.6	302.4	247.9	214.9	192.4
40°	360.4	400.8	444.7	472.8	460.8	406.5	326.1	257.1	217.2	190.9	174.5
42.5°	342.9	383.4	427.1	449.4	428.4	361.7	281.7	227.6	194.7	174.2	160.9
45°	313.2	356.0	396.3	408.7	371.3	297.8	227.8	188.5	166.6	151.5	142.3
47.5°	284.1	326.2	363.1	363.2	312.7	241.5	192.2	163.1	144.5	132.7	126.0
50°	266.3	306.3	337.2	332.4	275.0	214.8	171.9	146.8	131.3	122.2	115.2
52.5°	246.3	285.1	311.9	298.2	243.1	189.1	153.6	132.6	119.8	111.9	105.6
55°	217.2	251.7	270.6	249.8	198.4	157.3	129.8	113.3	103.7	97.0	91.6
57.5°	188.7	217.1	228.9	204.8	163.4	130.4	109.8	97.4	87.9	83.1	80.3
60°	170.7	195.0	203.3	176.7	142.0	114.1	97.3	85.8	78.7	75.6	72.8
62.5°	153.1	172.9	176.3	152.0	123.8	99.9	85.4	75.7	71.0	68.0	65.4
65°	127.0	141.3	139.7	120.0	98.0	79.2	68.7	62.8	59.3	55.0	50.4
67.5°	104.6	113.3	108.0	93.4	74.8	61.6	54.7	50.2	45.8	41.8	40.8
70°	90.3	95.4	89.8	76.3	61.3	51.7	46.1	40.8	38.2	37.3	35.5
72.5°	76.7	78.5	72.5	60.9	49.9	42.8	37.3	34.4	32.9	32.2	31.1
75°	57.6	56.3	51.1	42.1	34.7	29.8	28.1	27.1	26.1	25.4	24.8
77.5°	40.4	38.6	33.9	28.0	24.1	21.9	20.8	20.2	19.8	19.4	18.8
80°	30.4	29.1	24.5	20.0	18.3	17.2	16.6	15.9	15.9	15.6	15.0
82.5°	22.3	20.8	16.7	14.7	13.8	13.0	12.6	12.2	12.1	12.1	11.7
85°	11.7	9.5	8.3	8.0	7.4	7.0	7.3	6.8	6.8	6.8	6.7
87.5°	4.2	3.8	4.2	4.5	5.2	6.0	6.7	7.5	8.5	8.2	8.3
90°	3.0	5.2	7.4	9.6	12.7	16.8	20.8	24.9	28.9	28.5	28.1
92.5°	16.3	17.9	19.6	21.2	22.4	23.4	24.4	25.3	26.3	26.3	26.4
95°	44.8	46.6	48.4	50.3	51.4	51.8	52.1	52.5	52.8	52.8	52.8
97.5°	80.1	81.7	83.3	84.9	86.1	86.7	87.5	88.1	88.9	88.9	88.9
100°	106.3	107.8	109.3	110.7	111.8	112.3	112.8	113.4	114.0	114.0	114.0
102.5°	133.8	134.9	136.2	137.3	138.3	138.9	139.7	140.3	141.0	141.2	141.4
105°	178.1	178.6	179.2	179.8	180.2	180.6	180.9	181.3	181.6	182.1	182.4
107.5°	223.6	224.4	225.2	226.0	226.4	226.4	226.4	226.4	226.4	226.6	226.7
110°	253.0	254.0	255.2	256.2	256.8	256.8	256.8	256.8	256.8	256.8	256.8



TEST NUMBER: P331774-930

CATALOG NUMBER: S122RDIW-S290D970U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	284.7	285.8	286.9	288.0	288.5	288.3	288.1	288.0	287.9	287.4	287.0
115°	331.4	332.5	333.6	334.7	335.1	334.7	334.4	333.9	333.6	333.5	333.2
117.5°	378.4	379.8	381.3	382.8	382.9	382.0	380.9	379.9	378.9	378.5	378.0
120°	409.4	410.9	412.4	413.8	413.8	412.4	410.9	409.4	408.0	408.0	408.0
122.5°	438.1	439.9	441.6	443.4	443.8	442.7	441.7	440.7	439.6	439.2	438.8
125°	482.2	483.9	485.6	487.2	487.8	487.2	486.7	486.1	485.6	485.0	484.5
127.5°	525.8	527.9	530.0	532.1	532.8	532.1	531.5	530.8	530.2	529.5	528.8
130°	553.2	555.5	558.0	560.4	561.3	561.0	560.6	560.3	559.9	559.5	559.1
132.5°	583.1	585.1	587.0	589.0	590.0	590.0	590.1	590.2	590.3	589.5	588.6
135°	623.9	625.8	627.9	629.9	631.0	631.4	631.8	632.2	632.5	632.3	632.2
137.5°	666.3	667.9	669.5	671.2	672.3	672.7	673.2	673.7	674.2	674.0	673.8
140°	692.0	693.7	695.3	696.9	698.2	699.2	700.1	701.0	701.9	701.9	701.9
142.5°	718.4	720.1	721.7	723.4	724.6	725.1	725.8	726.4	727.0	727.2	727.3
145°	756.0	757.3	758.6	759.9	761.1	762.2	763.3	764.4	765.5	765.6	765.9
147.5°	790.2	791.7	793.2	794.8	795.9	796.6	797.4	798.1	798.8	799.2	799.6
150°	812.9	813.9	815.1	816.1	817.1	817.8	818.6	819.3	820.0	820.5	821.1
152.5°	833.3	834.5	835.5	836.7	837.6	838.5	839.4	840.2	841.1	841.8	842.5
155°	863.5	864.1	864.6	865.1	865.7	866.3	866.8	867.3	867.9	868.8	869.8
157.5°	889.6	889.9	890.3	890.6	891.0	891.4	891.7	892.0	892.3	893.6	894.9
160°	905.4	905.8	906.1	906.5	906.8	907.0	907.2	907.3	907.5	908.7	909.7
162.5°	919.7	919.7	919.8	919.9	920.0	920.2	920.4	920.6	920.7	922.0	923.2
165°	938.7	938.6	938.3	938.2	938.1	938.1	938.1	938.1	938.1	939.4	940.7
167.5°	954.6	954.0	953.4	952.9	952.6	952.6	952.5	952.5	952.4	953.7	955.0
170°	963.1	962.6	962.1	961.5	961.2	960.9	960.7	960.6	960.4	961.6	963.0
172.5°	969.1	968.5	968.0	967.4	967.0	966.9	966.7	966.5	966.3	967.6	968.9
175°	976.3	975.8	975.3	974.7	974.2	973.9	973.5	973.1	972.7	974.0	975.3
177.5°	979.4	979.0	978.5	978.1	977.7	977.5	977.1	976.9	976.6	977.5	978.4
180°	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5



TEST NUMBER: P331774-930

CATALOG NUMBER: S122RDIW-S290D970U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	533.0	533.0	533.0	533.0	533.0	533.0	533.0
2.5°	551.6	553.6	554.5	554.5	555.5	555.1	554.6
5°	583.3	586.9	587.7	590.9	593.4	592.6	593.0
7.5°	614.9	620.5	626.1	628.7	629.1	630.6	631.1
10°	634.3	639.0	647.6	646.4	652.8	656.6	650.4
12.5°	653.0	659.3	665.3	666.9	670.6	671.8	669.4
15°	669.8	673.2	673.5	672.6	673.8	672.8	669.3
17.5°	654.1	648.7	637.7	632.5	628.4	622.3	619.9
20°	628.0	612.0	593.5	586.1	577.5	560.4	564.5
22.5°	571.7	553.6	535.0	513.4	503.0	486.9	485.9
25°	484.1	452.8	418.3	394.3	380.2	364.1	357.0
27.5°	376.4	337.0	308.8	294.5	281.4	268.7	268.2
30°	305.6	276.0	254.1	241.9	233.9	228.5	229.7
32.5°	257.6	237.3	222.5	212.4	206.5	202.4	202.4
35°	210.6	196.7	187.2	183.0	178.7	175.8	175.9
37.5°	180.2	171.9	166.6	161.9	159.2	157.8	156.9
40°	164.6	157.8	153.7	150.9	148.7	146.7	146.3
42.5°	152.4	146.7	142.6	140.4	138.4	136.9	136.6
45°	135.2	130.5	126.9	124.4	123.5	122.2	122.2
47.5°	120.3	115.7	112.8	111.3	109.7	108.8	108.8
50°	110.2	106.6	104.1	103.1	101.8	101.3	101.1
52.5°	101.2	98.5	96.7	96.0	95.5	94.8	94.9
55°	88.9	87.4	86.7	86.1	85.2	84.1	84.8
57.5°	78.6	77.3	75.3	73.5	72.7	71.9	72.2
60°	71.3	68.7	66.1	64.1	63.5	61.9	61.9
62.5°	62.1	58.5	55.3	54.1	53.6	52.8	52.7
65°	47.8	46.3	45.6	44.8	44.4	44.4	44.1
67.5°	39.6	39.0	38.2	38.0	37.7	37.5	37.4
70°	35.0	34.2	33.9	33.7	33.3	33.5	32.9
72.5°	30.6	30.0	29.9	29.4	29.2	29.2	28.8
75°	24.1	24.1	23.9	23.7	23.3	23.2	23.3
77.5°	18.5	18.6	18.3	18.2	18.2	18.2	18.0
80°	14.8	15.0	14.8	14.6	14.4	14.6	14.4
82.5°	11.7	11.4	11.4	11.3	11.3	11.3	11.2
85°	6.7	6.8	6.7	6.5	6.5	6.5	6.7
87.5°	8.1	8.0	8.0	8.0	8.1	8.1	8.0
90°	27.8	27.4	27.3	27.6	27.7	27.9	28.0
92.5°	26.5	26.6	26.6	26.7	26.7	26.7	26.7
95°	52.8	52.8	52.7	52.3	51.9	51.5	51.2
97.5°	88.9	88.9	88.9	88.8	88.8	88.7	88.7
100°	114.0	114.0	113.9	113.7	113.5	113.3	113.2
102.5°	141.5	141.6	141.6	141.5	141.2	141.0	140.9
105°	182.8	183.1	183.4	183.4	183.4	183.4	183.4
107.5°	226.9	227.0	226.7	225.8	224.9	224.1	223.3
110°	256.8	256.8	256.6	256.0	255.4	254.9	254.4



TEST NUMBER: P331774-930

CATALOG NUMBER: S122RDIW-S290D970U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	286.6	286.1	285.7	285.3	284.9	284.5	284.1
115°	333.0	332.9	332.5	332.0	331.4	330.8	330.3
117.5°	377.6	377.1	376.6	376.1	375.5	375.0	374.4
120°	408.0	408.0	407.6	407.1	406.6	406.0	405.4
122.5°	438.3	437.9	437.5	437.1	436.7	436.3	435.9
125°	483.9	483.4	483.0	482.8	482.7	482.4	482.2
127.5°	528.2	527.5	526.8	526.3	525.7	525.1	524.6
130°	558.8	558.4	557.8	557.1	556.4	555.6	554.9
132.5°	587.8	587.0	586.4	585.8	585.1	584.6	584.0
135°	632.0	631.8	631.4	630.9	630.3	629.8	629.2
137.5°	673.8	673.6	673.1	672.4	671.6	670.9	670.2
140°	701.9	701.9	701.6	700.8	700.1	699.4	698.6
142.5°	727.5	727.6	727.3	726.6	725.9	725.1	724.4
145°	766.1	766.2	766.0	765.2	764.5	763.8	763.0
147.5°	800.1	800.5	800.3	799.6	798.9	798.3	797.5
150°	821.7	822.2	822.2	821.7	821.1	820.5	820.0
152.5°	843.3	843.9	843.9	843.3	842.5	841.8	841.1
155°	870.7	871.6	871.7	871.2	870.7	870.1	869.5
157.5°	896.1	897.3	897.5	896.7	895.8	894.9	894.0
160°	910.9	911.9	912.2	911.4	910.7	910.0	909.2
162.5°	924.5	925.8	925.9	925.0	924.1	923.2	922.4
165°	941.9	943.2	943.4	942.5	941.6	940.7	939.7
167.5°	956.3	957.6	957.7	956.8	955.9	954.9	954.0
170°	964.3	965.6	965.6	964.5	963.4	962.3	961.2
172.5°	970.2	971.4	971.6	970.5	969.4	968.2	967.2
175°	976.6	977.9	978.0	976.9	975.8	974.7	973.6
177.5°	979.2	980.1	980.1	979.2	978.4	977.5	976.6
180°	978.5	978.5	978.5	978.5	978.5	978.5	978.5

(END OF REPORT)