

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331789-930

Luminaire Tested: **S122RDIW-S485D710U930-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331789-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S485D710U930-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 710 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3827.8 lumens
Efficiency: N/A
Efficacy: 101.8 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 37.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331789-930

CATALOG NUMBER: S122RDIW-S485D710U930-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331789-930

CATALOG NUMBER: S122RDIW-S485D710U930-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	78	78	78	61	61	61	47	47	47	40
1	96	92	88	85	87	84	81	78	69	67	65	55	54	52	42	41	40	35
2	88	81	75	71	80	74	69	65	61	58	55	49	47	45	38	36	35	30
3	81	72	65	60	73	66	60	55	54	50	47	44	41	39	34	32	31	26
4	74	64	57	51	67	59	52	47	49	44	40	40	36	34	31	29	27	23
5	68	57	50	44	62	53	46	41	44	39	35	36	32	30	28	26	24	21
6	63	52	44	39	57	48	41	36	40	35	31	33	29	26	26	23	22	18
7	58	47	39	34	53	43	37	32	36	31	28	30	26	24	24	21	19	17
8	54	43	35	30	50	39	33	28	33	28	25	28	24	21	22	20	18	15
9	51	39	32	27	46	36	30	26	31	26	22	25	22	19	21	18	16	14
10	47	36	29	25	43	33	27	23	28	24	20	24	20	18	19	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	14149	14149	14149	14149
5°	15801	14237	12624	14237
10°	17531	14137	10942	14137
15°	18392	13929	8622	13929
20°	15945	13622	7459	13622
25°	10457	13201	6661	13201
30°	7040	12693	6027	12693
35°	5702	12051	5436	12051
40°	5069	11352	5031	11352
45°	4590	10533	4491	10533
50°	4175	9718	4160	9718
55°	3924	8819	3873	8819
60°	3284	7992	3242	7992
65°	2770	7259	3140	7259
70°	2559	6482	2960	6482
75°	2395	5639	2739	5639
80°	2204	4640	2436	4640
85°	2019	3668	2149	3668



TEST NUMBER: P331789-930

CATALOG NUMBER: S122RDIW-S485D710U930-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.1	2.2
10°-20°	231.5	6.0
20°-30°	298.2	7.8
30°-40°	283.4	7.4
40°-50°	242.8	6.3
50°-60°	184.9	4.8
60°-70°	116.9	3.1
70°-80°	58.4	1.5
80°-90°	17.1	0.4
90°-100°	26.3	0.7
100°-110°	96.5	2.5
110°-120°	257.9	6.7
120°-130°	425.7	11.1
130°-140°	452.8	11.8
140°-150°	420.8	11.0
150°-160°	338.4	8.8
160°-170°	218.0	5.7
170°-180°	75.1	2.0
0°-30°	612.8	16.0
0°-40°	896.2	23.4
0°-60°	1323.9	34.6
0°-90°	1516.3	39.6
90°-120°	380.7	9.9
90°-150°	1680.1	43.9
90°-180°	2312.0	60.4
0°-180°	3827.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	876	876	876	876	876	
5°	975	878	779	878	975	96
15°	1100	833	516	833	1100	297
25°	587	741	374	741	587	279
35°	289	611	276	611	289	185
45°	201	461	197	461	201	156
55°	139	313	138	313	139	122
65°	72	190	82	190	72	74
75°	38	90	44	90	38	41
85°	11	20	12	20	11	12
90°	15	1	15	1	15	7
95°	24	37	24	37	24	23
105°	43	174	43	174	43	45
115°	47	328	47	328	47	117
125°	488	464	488	464	488	422
135°	593	574	593	574	593	457
145°	676	666	676	666	676	423
155°	734	733	734	733	734	339
165°	771	773	771	773	771	218
175°	786	790	786	790	786	75
180°	789	789	789	789	789	



TEST NUMBER: P331789-930

CATALOG NUMBER: S122RDIW-S485D710U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3
2.5°	911.8	912.6	913.3	911.6	911.6	910.1	906.9	904.5	897.6	896.7	896.7
5°	974.9	974.3	975.5	971.5	966.0	964.8	959.0	951.5	943.5	934.7	932.9
7.5°	1037.6	1036.7	1034.3	1033.6	1029.4	1020.2	1010.9	1000.9	987.8	974.9	968.5
10°	1069.3	1079.3	1073.3	1062.6	1064.7	1050.4	1042.8	1029.7	1018.7	999.6	995.3
12.5°	1100.4	1104.4	1102.4	1096.4	1093.7	1083.8	1073.5	1062.1	1041.9	1024.7	1009.7
15°	1100.3	1106.1	1107.7	1105.8	1107.3	1106.7	1101.2	1091.8	1074.2	1055.2	1038.9
17.5°	1019.1	1023.1	1033.1	1039.8	1048.4	1066.4	1075.3	1078.8	1076.1	1065.4	1053.8
20°	928.0	921.3	949.3	963.6	975.8	1006.2	1032.4	1042.4	1058.6	1058.3	1055.2
22.5°	798.9	800.5	827.0	844.0	879.6	910.0	939.9	977.7	1008.9	1029.6	1041.6
25°	587.0	598.6	625.1	648.2	687.8	744.4	795.9	855.6	911.8	956.3	998.7
27.5°	440.8	441.7	462.7	484.1	507.6	554.0	618.8	690.1	770.4	836.6	912.8
30°	377.6	375.7	384.6	397.6	417.8	453.6	502.4	572.4	652.5	752.4	841.2
32.5°	332.7	332.8	339.5	349.2	365.8	390.0	423.5	480.3	556.0	654.2	758.4
35°	289.3	288.9	293.8	300.8	307.8	323.3	346.2	376.0	428.1	519.8	626.3
37.5°	258.0	259.4	261.8	266.2	273.9	282.5	296.3	316.3	353.4	407.6	497.1
40°	240.5	241.2	244.5	248.2	252.7	259.4	270.7	286.8	313.9	357.1	422.6
42.5°	224.5	225.0	227.5	230.8	234.4	241.2	250.5	264.4	286.4	320.1	374.1
45°	201.0	201.0	203.1	204.6	208.6	214.7	222.3	233.8	249.1	274.0	310.0
47.5°	178.9	179.0	180.3	183.0	185.5	190.2	197.7	207.2	218.3	237.6	268.2
50°	166.2	166.6	167.5	169.6	171.1	175.4	181.2	189.4	201.0	215.9	241.4
52.5°	156.0	155.8	156.9	157.9	158.9	162.0	166.3	173.6	183.9	196.9	218.1
55°	139.4	138.2	140.1	141.5	142.5	143.7	146.1	150.7	159.6	170.5	186.3
57.5°	118.7	118.2	119.5	120.9	123.8	127.1	129.1	132.1	136.6	144.5	160.2
60°	101.7	101.7	104.4	105.3	108.7	112.9	117.2	119.7	124.3	129.4	141.0
62.5°	86.6	86.8	88.1	89.0	90.9	96.1	102.2	107.5	111.8	116.8	124.4
65°	72.5	73.1	73.1	73.7	74.9	76.1	78.5	82.8	90.4	97.4	103.2
67.5°	61.5	61.7	61.9	62.5	62.8	64.1	65.1	67.0	68.7	75.4	82.6
70°	54.2	55.1	54.8	55.4	55.7	56.3	57.6	58.5	61.2	62.7	67.0
72.5°	47.4	48.0	48.0	48.3	49.2	49.2	50.2	51.1	52.9	54.2	56.5
75°	38.4	38.1	38.4	39.0	39.3	39.5	39.5	40.8	41.7	43.0	44.4
77.5°	29.6	29.9	29.8	29.9	29.9	30.5	30.4	31.0	31.9	32.5	33.3
80°	23.7	24.1	23.7	24.1	24.4	24.6	24.4	24.6	25.6	26.2	26.2
82.5°	18.4	18.4	18.7	18.7	18.8	18.8	19.2	19.3	20.0	19.8	20.1
85°	10.9	10.7	10.7	10.7	10.9	11.3	10.9	10.9	11.3	11.3	11.3
87.5°	7.0	7.2	7.1	7.1	7.0	6.9	6.8	6.9	6.5	6.7	6.2
90°	15.4	15.2	14.9	14.7	14.4	13.9	13.3	12.7	12.1	11.4	10.4
92.5°	15.4	15.2	15.1	14.9	14.8	14.6	14.3	13.9	13.5	13.2	12.7
95°	24.5	24.7	24.8	24.9	25.0	24.8	24.1	23.6	22.9	22.3	21.4
97.5°	32.8	32.6	32.4	32.3	32.1	31.8	31.3	30.8	30.3	29.8	27.7
100°	38.2	38.0	37.7	37.5	37.3	36.6	35.5	34.6	33.5	32.5	30.4
102.5°	41.0	40.6	40.3	39.9	39.5	38.7	37.4	36.1	34.7	33.4	31.4
105°	43.4	42.9	42.4	41.8	41.3	40.4	39.0	37.6	36.2	34.8	32.5
107.5°	44.6	44.1	43.6	43.1	42.6	43.0	44.5	45.9	47.3	48.8	50.3
110°	45.1	44.6	44.1	43.5	43.0	49.2	61.8	74.5	87.2	99.9	136.6



TEST NUMBER: P331789-930

CATALOG NUMBER: S122RDIW-S485D710U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	45.6	45.2	44.8	44.4	43.9	66.9	113.2	159.4	205.7	251.9	261.0
115°	46.8	55.9	65.1	74.2	83.3	117.2	175.9	234.7	293.4	352.1	348.9
117.5°	191.1	221.1	251.1	281.1	311.1	333.2	347.4	361.7	375.9	390.0	387.8
120°	348.1	365.3	382.4	399.5	416.6	424.4	422.9	421.4	419.9	418.3	416.0
122.5°	434.5	437.8	441.1	444.4	447.8	449.0	448.0	447.1	446.2	445.3	442.8
125°	488.0	487.6	487.2	486.8	486.5	485.8	484.9	484.0	483.1	482.2	479.9
127.5°	521.8	521.7	521.6	521.5	521.5	520.8	519.5	518.2	516.9	515.6	513.8
130°	542.8	542.9	543.1	543.2	543.3	542.7	541.3	539.9	538.5	537.1	535.7
132.5°	563.4	563.5	563.6	563.7	563.9	563.3	562.1	560.9	559.7	558.6	557.2
135°	593.0	593.3	593.5	593.8	594.0	593.5	592.2	591.0	589.7	588.5	587.3
137.5°	620.0	620.5	620.9	621.3	621.8	621.4	620.1	618.9	617.7	616.4	615.1
140°	637.0	637.6	638.2	638.9	639.5	639.3	638.1	637.0	635.9	634.7	633.2
142.5°	653.4	654.0	654.7	655.3	655.9	655.7	654.7	653.6	652.6	651.6	650.0
145°	676.4	676.9	677.6	678.2	678.9	678.7	677.8	676.9	676.1	675.2	673.0
147.5°	696.5	697.1	697.7	698.1	698.7	698.6	698.0	697.3	696.7	695.9	693.8
150°	708.9	709.5	710.1	710.8	711.4	711.3	710.6	709.8	709.1	708.3	706.3
152.5°	719.3	720.2	721.1	721.9	722.8	722.8	722.0	721.2	720.5	719.7	717.8
155°	734.0	735.0	736.1	737.0	738.0	738.2	737.4	736.6	735.9	735.2	733.6
157.5°	747.3	748.4	749.3	750.3	751.3	751.4	750.5	749.7	748.8	747.9	746.8
160°	755.1	756.0	756.8	757.7	758.6	758.7	758.0	757.2	756.4	755.7	754.9
162.5°	761.5	762.5	763.7	764.8	765.9	766.0	765.1	764.3	763.4	762.5	761.9
165°	771.1	772.0	772.9	773.7	774.6	774.6	773.7	772.9	772.0	771.1	770.7
167.5°	777.1	778.3	779.4	780.6	781.7	781.8	781.0	780.1	779.2	778.3	778.0
170°	780.8	782.0	783.1	784.2	785.4	785.5	784.6	783.7	782.9	782.0	781.7
172.5°	783.5	784.6	785.8	786.9	788.1	788.2	787.3	786.4	785.5	784.6	784.4
175°	785.9	787.2	788.5	789.7	791.0	791.2	790.3	789.5	788.6	787.7	787.4
177.5°	787.4	788.3	789.2	790.2	791.1	791.2	790.4	789.8	789.0	788.3	788.2
180°	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8



TEST NUMBER: P331789-930

CATALOG NUMBER: S122RDIW-S485D710U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3
2.5°	897.2	895.3	893.6	889.2	887.0	882.1	881.3	881.1	874.8	868.7	867.0
5°	928.0	923.2	915.8	907.3	898.5	889.3	883.2	878.4	866.2	854.6	847.9
7.5°	959.0	948.6	936.0	919.8	906.4	891.3	880.1	870.0	852.7	836.2	825.0
10°	982.2	965.2	948.4	926.2	908.8	891.8	876.0	862.3	842.8	820.8	805.3
12.5°	996.5	977.8	954.7	933.0	910.5	888.8	867.6	850.0	827.2	804.5	786.0
15°	1016.0	995.9	967.9	936.9	907.9	879.6	855.2	833.3	803.5	776.4	753.8
17.5°	1031.9	1004.2	974.1	938.2	904.7	868.8	837.4	809.3	776.2	743.5	717.0
20°	1037.0	1009.6	974.9	939.0	899.4	857.0	823.3	792.8	757.2	721.5	691.1
22.5°	1033.8	1012.5	973.9	930.9	890.4	846.1	808.0	772.6	733.1	696.8	661.5
25°	1012.4	1005.0	968.5	921.6	875.3	823.9	779.8	741.0	696.0	657.0	618.6
27.5°	962.2	978.0	955.4	905.4	853.9	798.7	749.2	705.2	658.4	614.5	576.3
30°	914.0	950.2	940.4	894.2	836.7	782.4	726.8	680.8	630.9	585.8	548.0
32.5°	848.0	907.8	917.4	878.6	819.1	759.5	701.2	655.4	603.3	555.8	519.0
35°	742.9	832.4	873.5	848.8	789.1	725.0	664.6	611.4	559.0	512.1	475.6
37.5°	617.5	739.4	808.0	809.7	754.9	688.1	622.5	569.6	515.9	469.9	430.4
40°	536.1	668.3	757.5	777.3	731.0	658.8	592.5	538.6	486.2	441.2	395.8
42.5°	463.1	594.8	704.4	738.8	702.1	630.4	563.8	507.4	456.5	413.8	367.5
45°	374.5	489.6	610.4	672.0	651.6	585.1	514.9	461.3	413.4	376.6	332.2
47.5°	315.9	397.1	514.0	597.2	596.8	536.2	467.1	415.7	371.4	336.9	300.8
50°	282.5	353.2	452.2	546.5	554.4	503.6	437.8	386.9	345.6	309.3	280.4
52.5°	252.6	310.8	399.7	490.2	512.7	468.7	405.0	358.0	317.8	284.5	259.7
55°	213.4	258.4	326.1	410.7	444.8	413.8	357.1	313.3	280.7	252.7	231.4
57.5°	180.5	214.3	268.6	336.7	376.4	356.9	310.2	274.6	246.7	221.4	204.6
60°	159.9	187.5	233.5	290.5	334.3	320.6	280.7	247.5	223.8	201.9	186.1
62.5°	140.4	164.2	203.6	249.8	290.0	284.3	251.8	223.9	203.1	183.1	169.7
65°	112.9	130.3	161.0	197.3	229.6	232.3	208.9	190.0	171.4	155.6	143.7
67.5°	89.9	101.3	122.9	153.4	177.7	186.3	171.9	157.5	142.8	130.5	120.3
70°	75.8	85.0	100.8	125.5	147.7	156.8	148.5	137.3	124.5	114.5	105.7
72.5°	61.5	70.4	82.0	100.1	119.2	129.1	126.2	118.1	107.7	99.4	91.1
75°	46.3	49.0	56.9	69.1	84.1	92.5	94.7	90.4	82.2	75.8	70.9
77.5°	34.2	35.9	39.6	46.1	55.8	63.3	66.5	66.0	60.3	56.7	52.1
80°	27.4	28.3	30.2	32.9	40.2	47.8	49.9	49.9	46.0	44.4	39.9
82.5°	20.8	21.5	22.6	24.1	27.6	34.2	36.5	37.0	34.5	32.5	28.9
85°	11.9	11.6	12.1	13.1	13.7	15.5	19.2	19.8	19.2	16.7	15.8
87.5°	6.0	6.0	5.9	5.4	5.3	5.3	6.3	7.2	6.5	6.0	5.8
90°	9.4	8.4	7.3	6.1	4.7	3.3	2.0	0.6	2.0	3.3	4.7
92.5°	12.2	11.7	11.3	11.0	11.2	11.3	11.4	11.5	11.4	11.3	11.2
95°	20.5	19.6	18.7	20.4	24.5	28.7	32.9	37.1	32.9	28.7	24.5
97.5°	25.7	23.6	21.6	26.4	38.2	50.1	61.8	73.6	61.8	50.1	38.2
100°	28.2	26.1	23.9	31.6	48.9	66.3	83.6	101.0	83.6	66.3	48.9
102.5°	69.5	87.6	105.6	116.4	120.1	123.8	127.5	131.2	127.5	123.8	120.1
105°	104.0	138.7	173.3	188.7	184.9	181.2	177.3	173.5	177.3	181.2	184.9
107.5°	131.8	173.3	214.8	234.1	231.0	228.0	224.9	221.8	224.9	228.0	231.0
110°	173.2	209.9	246.5	263.5	260.8	258.2	255.5	252.8	255.5	258.2	260.8



TEST NUMBER: P331789-930

CATALOG NUMBER: S122RDIW-S485D710U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	270.0	279.1	288.1	291.5	289.1	286.8	284.5	282.1	284.5	286.8	289.1
115°	345.8	342.7	339.5	336.8	334.7	332.5	330.4	328.2	330.4	332.5	334.7
117.5°	385.7	383.5	381.3	379.0	376.6	374.2	371.8	369.4	371.8	374.2	376.6
120°	413.8	411.5	409.2	407.2	405.2	403.3	401.5	399.5	401.5	403.3	405.2
122.5°	440.3	437.8	435.4	433.1	431.1	429.1	427.1	425.1	427.1	429.1	431.1
125°	477.4	475.1	472.6	470.6	469.0	467.3	465.7	464.0	465.7	467.3	469.0
127.5°	512.0	510.2	508.4	506.6	504.8	503.0	501.1	499.3	501.1	503.0	504.8
130°	534.3	532.9	531.5	529.8	527.7	525.7	523.7	521.6	523.7	525.7	527.7
132.5°	555.7	554.3	552.9	551.4	549.7	548.0	546.3	544.5	546.3	548.0	549.7
135°	586.2	585.1	583.9	582.3	580.2	578.2	576.2	574.2	576.2	578.2	580.2
137.5°	613.8	612.5	611.2	609.8	608.5	607.1	605.6	604.2	605.6	607.1	608.5
140°	631.9	630.5	629.1	627.9	626.9	625.8	624.8	623.9	624.8	625.8	626.9
142.5°	648.4	646.8	645.1	643.9	643.0	642.1	641.2	640.3	641.2	642.1	643.0
145°	670.9	668.7	666.6	665.5	665.7	665.9	665.9	666.1	665.9	665.9	665.7
147.5°	691.7	689.6	687.5	686.6	687.1	687.6	688.1	688.5	688.1	687.6	687.1
150°	704.3	702.2	700.2	699.6	700.5	701.4	702.3	703.2	702.3	701.4	700.5
152.5°	715.8	714.0	712.0	711.5	712.5	713.5	714.5	715.5	714.5	713.5	712.5
155°	732.1	730.6	729.0	728.9	730.0	731.2	732.3	733.4	732.3	731.2	730.0
157.5°	745.8	744.7	743.6	743.6	744.5	745.5	746.5	747.5	746.5	745.5	744.5
160°	754.2	753.4	752.6	752.6	753.4	754.2	754.9	755.7	754.9	754.2	753.4
162.5°	761.2	760.5	759.9	759.9	760.7	761.5	762.2	763.0	762.2	761.5	760.7
165°	770.3	770.0	769.6	769.7	770.5	771.3	772.0	772.8	772.0	771.3	770.5
167.5°	777.6	777.2	776.9	777.1	777.8	778.6	779.3	780.1	779.3	778.6	777.8
170°	781.5	781.1	780.9	781.1	782.0	782.7	783.4	784.2	783.4	782.7	782.0
172.5°	784.2	783.9	783.7	783.9	784.6	785.5	786.2	786.9	786.2	785.5	784.6
175°	787.2	786.8	786.6	786.9	787.8	788.7	789.6	790.5	789.6	788.7	787.8
177.5°	788.1	788.0	787.9	788.2	789.0	789.6	790.4	791.1	790.4	789.6	789.0
180°	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8



TEST NUMBER: P331789-930

CATALOG NUMBER: S122RDIW-S485D710U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3
2.5°	863.8	862.1	858.9	854.1	851.2	846.0	842.6	844.6	845.1	844.6	844.1
5°	840.7	834.2	825.4	816.8	808.9	800.5	795.6	793.4	789.1	786.8	785.5
7.5°	812.5	801.5	789.0	774.2	761.6	748.4	741.6	738.3	729.5	724.8	720.6
10°	791.6	774.2	761.7	742.2	730.4	713.1	701.2	701.5	689.6	682.9	678.0
12.5°	768.5	749.4	728.6	711.1	694.6	680.7	666.3	660.6	647.9	641.5	628.4
15°	730.1	707.8	686.0	662.2	645.5	623.9	603.2	577.9	557.5	539.8	534.9
17.5°	688.2	660.7	638.7	610.8	582.1	545.8	521.8	507.1	494.8	485.5	478.6
20°	659.5	631.4	608.1	566.0	527.3	502.6	485.0	473.8	461.0	450.9	445.4
22.5°	629.2	600.1	568.1	521.1	491.1	471.2	455.5	442.5	433.9	426.1	421.1
25°	586.4	554.4	501.7	469.4	445.2	424.4	413.4	405.5	396.4	385.7	380.9
27.5°	541.1	490.2	452.4	428.4	405.2	391.8	381.9	370.1	361.9	357.1	352.0
30°	507.2	456.4	426.9	400.6	384.3	369.3	357.8	351.1	343.2	334.9	331.6
32.5°	469.4	428.8	400.6	378.8	362.1	349.4	340.2	329.4	323.7	318.6	311.6
35°	422.6	391.8	366.0	348.3	332.5	322.1	311.4	305.1	294.7	290.5	287.7
37.5°	382.9	356.2	336.9	318.3	305.7	294.3	287.8	277.6	273.1	267.2	261.4
40°	360.4	334.3	315.8	300.5	286.5	277.9	269.8	261.5	254.9	252.1	245.1
42.5°	337.6	316.3	297.7	281.0	271.7	262.6	252.3	246.2	239.2	234.8	230.5
45°	306.0	287.1	271.3	257.6	247.2	237.8	231.1	221.0	217.1	208.2	204.6
47.5°	278.2	260.7	245.6	232.5	222.4	216.3	206.5	198.6	192.3	186.9	182.2
50°	258.4	243.9	229.3	217.7	208.6	199.7	189.7	185.7	175.9	173.3	170.5
52.5°	240.4	226.6	213.2	201.9	192.7	184.2	175.3	170.2	163.5	160.8	158.8
55°	215.2	201.9	189.1	179.0	169.9	161.0	155.6	149.2	146.1	144.0	141.5
57.5°	189.9	177.9	168.0	157.9	148.7	141.7	135.3	131.5	128.3	125.6	122.6
60°	173.8	162.2	153.4	144.0	134.6	128.8	123.9	119.4	115.7	111.5	110.2
62.5°	156.8	146.7	138.6	129.4	121.2	115.9	111.3	107.0	102.6	96.4	94.7
65°	133.4	125.5	116.9	109.3	102.0	96.9	90.1	85.3	83.4	82.8	82.5
67.5°	112.2	104.7	97.3	89.6	82.9	78.1	74.7	73.9	72.7	72.3	71.5
70°	98.0	91.1	83.7	76.4	70.0	69.1	67.9	66.7	65.1	64.6	63.9
72.5°	85.4	78.1	70.8	65.0	62.2	61.1	59.8	58.6	57.6	57.0	56.7
75°	65.5	58.8	53.9	51.8	50.2	49.3	47.5	46.6	46.0	45.1	44.8
77.5°	47.1	43.4	41.1	39.8	38.2	37.2	36.2	35.2	34.6	34.4	33.9
80°	36.0	34.1	32.6	30.7	30.2	28.9	28.6	27.7	28.0	27.1	27.1
82.5°	27.9	25.6	24.3	23.5	22.8	21.9	21.5	21.1	21.2	20.5	20.5
85°	14.3	13.7	13.1	12.5	12.5	11.6	11.9	11.6	11.6	10.9	10.7
87.5°	5.9	5.9	5.5	5.8	6.0	6.0	6.0	6.0	6.0	6.2	6.0
90°	6.1	7.3	8.4	9.4	10.4	11.4	12.1	12.7	13.3	13.9	14.4
92.5°	11.0	11.3	11.7	12.2	12.7	13.2	13.5	13.9	14.3	14.6	14.8
95°	20.4	18.7	19.6	20.5	21.4	22.3	22.9	23.6	24.1	24.8	25.0
97.5°	26.4	21.6	23.6	25.7	27.7	29.8	30.3	30.8	31.3	31.8	32.1
100°	31.6	23.9	26.1	28.2	30.4	32.5	33.5	34.6	35.5	36.6	37.3
102.5°	116.4	105.6	87.6	69.5	51.4	33.4	34.7	36.1	37.4	38.7	39.5
105°	188.7	173.3	138.7	104.0	69.5	34.8	36.2	37.6	39.0	40.4	41.3
107.5°	234.1	214.8	173.3	131.8	90.3	48.8	47.3	45.9	44.5	43.0	42.6
110°	263.5	246.5	209.9	173.2	136.6	99.9	87.2	74.5	61.8	49.2	43.0



TEST NUMBER: P331789-930

CATALOG NUMBER: S122RDIW-S485D710U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	291.5	288.1	279.1	270.0	261.0	251.9	205.7	159.4	113.2	66.9	43.9
115°	336.8	339.5	342.7	345.8	348.9	352.1	293.4	234.7	175.9	117.2	83.3
117.5°	379.0	381.3	383.5	385.7	387.8	390.0	375.9	361.7	347.4	333.2	311.1
120°	407.2	409.2	411.5	413.8	416.0	418.3	419.9	421.4	422.9	424.4	416.6
122.5°	433.1	435.4	437.8	440.3	442.8	445.3	446.2	447.1	448.0	449.0	447.8
125°	470.6	472.6	475.1	477.4	479.9	482.2	483.1	484.0	484.9	485.8	486.5
127.5°	506.6	508.4	510.2	512.0	513.8	515.6	516.9	518.2	519.5	520.8	521.5
130°	529.8	531.5	532.9	534.3	535.7	537.1	538.5	539.9	541.3	542.7	543.3
132.5°	551.4	552.9	554.3	555.7	557.2	558.6	559.7	560.9	562.1	563.3	563.9
135°	582.3	583.9	585.1	586.2	587.3	588.5	589.7	591.0	592.2	593.5	594.0
137.5°	609.8	611.2	612.5	613.8	615.1	616.4	617.7	618.9	620.1	621.4	621.8
140°	627.9	629.1	630.5	631.9	633.2	634.7	635.9	637.0	638.1	639.3	639.5
142.5°	643.9	645.1	646.8	648.4	650.0	651.6	652.6	653.6	654.7	655.7	655.9
145°	665.5	666.6	668.7	670.9	673.0	675.2	676.1	676.9	677.8	678.7	678.9
147.5°	686.6	687.5	689.6	691.7	693.8	695.9	696.7	697.3	698.0	698.6	698.7
150°	699.6	700.2	702.2	704.3	706.3	708.3	709.1	709.8	710.6	711.3	711.4
152.5°	711.5	712.0	714.0	715.8	717.8	719.7	720.5	721.2	722.0	722.8	722.8
155°	728.9	729.0	730.6	732.1	733.6	735.2	735.9	736.6	737.4	738.2	738.0
157.5°	743.6	743.6	744.7	745.8	746.8	747.9	748.8	749.7	750.5	751.4	751.3
160°	752.6	752.6	753.4	754.2	754.9	755.7	756.4	757.2	758.0	758.7	758.6
162.5°	759.9	759.9	760.5	761.2	761.9	762.5	763.4	764.3	765.1	766.0	765.9
165°	769.7	769.6	770.0	770.3	770.7	771.1	772.0	772.9	773.7	774.6	774.6
167.5°	777.1	776.9	777.2	777.6	778.0	778.3	779.2	780.1	781.0	781.8	781.7
170°	781.1	780.9	781.1	781.5	781.7	782.0	782.9	783.7	784.6	785.5	785.4
172.5°	783.9	783.7	783.9	784.2	784.4	784.6	785.5	786.4	787.3	788.2	788.1
175°	786.9	786.6	786.8	787.2	787.4	787.7	788.6	789.5	790.3	791.2	791.0
177.5°	788.2	787.9	788.0	788.1	788.2	788.3	789.0	789.8	790.4	791.2	791.1
180°	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8



TEST NUMBER: P331789-930

CATALOG NUMBER: S122RDIW-S485D710U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3
2.5°	841.4	841.9	841.1	841.6	841.1	841.9	841.4	844.1	844.6	845.1	844.6
5°	784.0	780.3	779.8	778.9	779.8	780.3	784.0	785.5	786.8	789.1	793.4
7.5°	715.4	714.9	713.4	711.2	713.4	714.9	715.4	720.6	724.8	729.5	738.3
10°	671.3	669.8	669.5	667.4	669.5	669.8	671.3	678.0	682.9	689.6	701.5
12.5°	619.7	609.9	608.9	603.6	608.9	609.9	619.7	628.4	641.5	647.9	660.6
15°	527.7	525.8	519.8	515.8	519.8	525.8	527.7	534.9	539.8	557.5	577.9
17.5°	475.0	469.0	467.2	466.4	467.2	469.0	475.0	478.6	485.5	494.8	507.1
20°	441.2	435.7	434.8	434.1	434.8	435.7	441.2	445.4	450.9	461.0	473.8
22.5°	417.8	412.1	409.7	407.9	409.7	412.1	417.8	421.1	426.1	433.9	442.5
25°	377.8	375.7	374.5	373.9	374.5	375.7	377.8	380.9	385.7	396.4	405.5
27.5°	346.6	341.9	341.0	339.4	341.0	341.9	346.6	352.0	357.1	361.9	370.1
30°	328.8	327.3	325.1	323.3	325.1	327.3	328.8	331.6	334.9	343.2	351.1
32.5°	307.9	306.6	304.7	303.9	304.7	306.6	307.9	311.6	318.6	323.7	329.4
35°	284.7	280.4	278.6	275.8	278.6	280.4	284.7	287.7	290.5	294.7	305.1
37.5°	260.2	257.9	255.4	256.2	255.4	257.9	260.2	261.4	267.2	273.1	277.6
40°	241.2	239.6	239.0	238.7	239.0	239.6	241.2	245.1	252.1	254.9	261.5
42.5°	226.0	221.8	220.2	220.2	220.2	221.8	226.0	230.5	234.8	239.2	246.2
45°	203.1	199.1	196.4	196.7	196.4	199.1	203.1	204.6	208.2	217.1	221.0
47.5°	179.6	179.4	177.7	178.3	177.7	179.4	179.6	182.2	186.9	192.3	198.6
50°	168.4	166.6	165.3	165.6	165.3	166.6	168.4	170.5	173.3	175.9	185.7
52.5°	157.7	156.0	155.1	156.4	155.1	156.0	157.7	158.8	160.8	163.5	170.2
55°	140.1	138.2	137.9	137.6	137.9	138.2	140.1	141.5	144.0	146.1	149.2
57.5°	120.4	119.2	117.3	116.6	117.3	119.2	120.4	122.6	125.6	128.3	131.5
60°	106.2	103.8	100.8	100.4	100.8	103.8	106.2	110.2	111.5	115.7	119.4
62.5°	93.4	92.9	92.3	92.2	92.3	92.9	93.4	94.7	96.4	102.6	107.0
65°	81.9	81.6	81.9	82.2	81.9	81.6	81.9	82.5	82.8	83.4	85.3
67.5°	71.3	70.8	70.3	70.5	70.3	70.8	71.3	71.5	72.3	72.7	73.9
70°	63.3	63.0	62.7	62.7	62.7	63.0	63.3	63.9	64.6	65.1	66.7
72.5°	55.5	55.4	55.2	55.0	55.2	55.4	55.5	56.7	57.0	57.6	58.6
75°	44.4	43.9	43.9	43.9	43.9	43.9	44.4	44.8	45.1	46.0	46.6
77.5°	33.8	33.6	33.3	33.0	33.3	33.6	33.8	33.9	34.4	34.6	35.2
80°	26.8	26.5	26.2	26.2	26.2	26.5	26.8	27.1	27.1	28.0	27.7
82.5°	20.5	20.1	20.1	19.8	20.1	20.1	20.5	20.5	20.5	21.2	21.1
85°	10.9	11.3	10.9	11.6	10.9	11.3	10.9	10.7	10.9	11.6	11.6
87.5°	6.1	5.9	6.2	6.0	6.2	5.9	6.1	6.0	6.2	6.0	6.0
90°	14.7	14.9	15.2	15.4	15.2	14.9	14.7	14.4	13.9	13.3	12.7
92.5°	14.9	15.1	15.2	15.4	15.2	15.1	14.9	14.8	14.6	14.3	13.9
95°	24.9	24.8	24.7	24.5	24.7	24.8	24.9	25.0	24.8	24.1	23.6
97.5°	32.3	32.4	32.6	32.8	32.6	32.4	32.3	32.1	31.8	31.3	30.8
100°	37.5	37.7	38.0	38.2	38.0	37.7	37.5	37.3	36.6	35.5	34.6
102.5°	39.9	40.3	40.6	41.0	40.6	40.3	39.9	39.5	38.7	37.4	36.1
105°	41.8	42.4	42.9	43.4	42.9	42.4	41.8	41.3	40.4	39.0	37.6
107.5°	43.1	43.6	44.1	44.6	44.1	43.6	43.1	42.6	43.0	44.5	45.9
110°	43.5	44.1	44.6	45.1	44.6	44.1	43.5	43.0	49.2	61.8	74.5



TEST NUMBER: P331789-930

CATALOG NUMBER: S122RDIW-S485D710U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	44.4	44.8	45.2	45.6	45.2	44.8	44.4	43.9	66.9	113.2	159.4
115°	74.2	65.1	55.9	46.8	55.9	65.1	74.2	83.3	117.2	175.9	234.7
117.5°	281.1	251.1	221.1	191.1	221.1	251.1	281.1	311.1	333.2	347.4	361.7
120°	399.5	382.4	365.3	348.1	365.3	382.4	399.5	416.6	424.4	422.9	421.4
122.5°	444.4	441.1	437.8	434.5	437.8	441.1	444.4	447.8	449.0	448.0	447.1
125°	486.8	487.2	487.6	488.0	487.6	487.2	486.8	486.5	485.8	484.9	484.0
127.5°	521.5	521.6	521.7	521.8	521.7	521.6	521.5	521.5	520.8	519.5	518.2
130°	543.2	543.1	542.9	542.8	542.9	543.1	543.2	543.3	542.7	541.3	539.9
132.5°	563.7	563.6	563.5	563.4	563.5	563.6	563.7	563.9	563.3	562.1	560.9
135°	593.8	593.5	593.3	593.0	593.3	593.5	593.8	594.0	593.5	592.2	591.0
137.5°	621.3	620.9	620.5	620.0	620.5	620.9	621.3	621.8	621.4	620.1	618.9
140°	638.9	638.2	637.6	637.0	637.6	638.2	638.9	639.5	639.3	638.1	637.0
142.5°	655.3	654.7	654.0	653.4	654.0	654.7	655.3	655.9	655.7	654.7	653.6
145°	678.2	677.6	676.9	676.4	676.9	677.6	678.2	678.9	678.7	677.8	676.9
147.5°	698.1	697.7	697.1	696.5	697.1	697.7	698.1	698.7	698.6	698.0	697.3
150°	710.8	710.1	709.5	708.9	709.5	710.1	710.8	711.4	711.3	710.6	709.8
152.5°	721.9	721.1	720.2	719.3	720.2	721.1	721.9	722.8	722.8	722.0	721.2
155°	737.0	736.1	735.0	734.0	735.0	736.1	737.0	738.0	738.2	737.4	736.6
157.5°	750.3	749.3	748.4	747.3	748.4	749.3	750.3	751.3	751.4	750.5	749.7
160°	757.7	756.8	756.0	755.1	756.0	756.8	757.7	758.6	758.7	758.0	757.2
162.5°	764.8	763.7	762.5	761.5	762.5	763.7	764.8	765.9	766.0	765.1	764.3
165°	773.7	772.9	772.0	771.1	772.0	772.9	773.7	774.6	774.6	773.7	772.9
167.5°	780.6	779.4	778.3	777.1	778.3	779.4	780.6	781.7	781.8	781.0	780.1
170°	784.2	783.1	782.0	780.8	782.0	783.1	784.2	785.4	785.5	784.6	783.7
172.5°	786.9	785.8	784.6	783.5	784.6	785.8	786.9	788.1	788.2	787.3	786.4
175°	789.7	788.5	787.2	785.9	787.2	788.5	789.7	791.0	791.2	790.3	789.5
177.5°	790.2	789.2	788.3	787.4	788.3	789.2	790.2	791.1	791.2	790.4	789.8
180°	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8



TEST NUMBER: P331789-930

CATALOG NUMBER: S122RDIW-S485D710U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3
2.5°	842.6	846.0	851.2	854.1	858.9	862.1	863.8	867.0	868.7	874.8	881.1
5°	795.6	800.5	808.9	816.8	825.4	834.2	840.7	847.9	854.6	866.2	878.4
7.5°	741.6	748.4	761.6	774.2	789.0	801.5	812.5	825.0	836.2	852.7	870.0
10°	701.2	713.1	730.4	742.2	761.7	774.2	791.6	805.3	820.8	842.8	862.3
12.5°	666.3	680.7	694.6	711.1	728.6	749.4	768.5	786.0	804.5	827.2	850.0
15°	603.2	623.9	645.5	662.2	686.0	707.8	730.1	753.8	776.4	803.5	833.3
17.5°	521.8	545.8	582.1	610.8	638.7	660.7	688.2	717.0	743.5	776.2	809.3
20°	485.0	502.6	527.3	566.0	608.1	631.4	659.5	691.1	721.5	757.2	792.8
22.5°	455.5	471.2	491.1	521.1	568.1	600.1	629.2	661.5	696.8	733.1	772.6
25°	413.4	424.4	445.2	469.4	501.7	554.4	586.4	618.6	657.0	696.0	741.0
27.5°	381.9	391.8	405.2	428.4	452.4	490.2	541.1	576.3	614.5	658.4	705.2
30°	357.8	369.3	384.3	400.6	426.9	456.4	507.2	548.0	585.8	630.9	680.8
32.5°	340.2	349.4	362.1	378.8	400.6	428.8	469.4	519.0	555.8	603.3	655.4
35°	311.4	322.1	332.5	348.3	366.0	391.8	422.6	475.6	512.1	559.0	611.4
37.5°	287.8	294.3	305.7	318.3	336.9	356.2	382.9	430.4	469.9	515.9	569.6
40°	269.8	277.9	286.5	300.5	315.8	334.3	360.4	395.8	441.2	486.2	538.6
42.5°	252.3	262.6	271.7	281.0	297.7	316.3	337.6	367.5	413.8	456.5	507.4
45°	231.1	237.8	247.2	257.6	271.3	287.1	306.0	332.2	376.6	413.4	461.3
47.5°	206.5	216.3	222.4	232.5	245.6	260.7	278.2	300.8	336.9	371.4	415.7
50°	189.7	199.7	208.6	217.7	229.3	243.9	258.4	280.4	309.3	345.6	386.9
52.5°	175.3	184.2	192.7	201.9	213.2	226.6	240.4	259.7	284.5	317.8	358.0
55°	155.6	161.0	169.9	179.0	189.1	201.9	215.2	231.4	252.7	280.7	313.3
57.5°	135.3	141.7	148.7	157.9	168.0	177.9	189.9	204.6	221.4	246.7	274.6
60°	123.9	128.8	134.6	144.0	153.4	162.2	173.8	186.1	201.9	223.8	247.5
62.5°	111.3	115.9	121.2	129.4	138.6	146.7	156.8	169.7	183.1	203.1	223.9
65°	90.1	96.9	102.0	109.3	116.9	125.5	133.4	143.7	155.6	171.4	190.0
67.5°	74.7	78.1	82.9	89.6	97.3	104.7	112.2	120.3	130.5	142.8	157.5
70°	67.9	69.1	70.0	76.4	83.7	91.1	98.0	105.7	114.5	124.5	137.3
72.5°	59.8	61.1	62.2	65.0	70.8	78.1	85.4	91.1	99.4	107.7	118.1
75°	47.5	49.3	50.2	51.8	53.9	58.8	65.5	70.9	75.8	82.2	90.4
77.5°	36.2	37.2	38.2	39.8	41.1	43.4	47.1	52.1	56.7	60.3	66.0
80°	28.6	28.9	30.2	30.7	32.6	34.1	36.0	39.9	44.4	46.0	49.9
82.5°	21.5	21.9	22.8	23.5	24.3	25.6	27.9	28.9	32.5	34.5	37.0
85°	11.9	11.6	12.5	12.5	13.1	13.7	14.3	15.8	16.7	19.2	19.8
87.5°	6.0	6.0	6.0	5.8	5.5	5.9	5.9	5.8	6.0	6.5	7.2
90°	12.1	11.4	10.4	9.4	8.4	7.3	6.1	4.7	3.3	2.0	0.6
92.5°	13.5	13.2	12.7	12.2	11.7	11.3	11.0	11.2	11.3	11.4	11.5
95°	22.9	22.3	21.4	20.5	19.6	18.7	20.4	24.5	28.7	32.9	37.1
97.5°	30.3	29.8	27.7	25.7	23.6	21.6	26.4	38.2	50.1	61.8	73.6
100°	33.5	32.5	30.4	28.2	26.1	23.9	31.6	48.9	66.3	83.6	101.0
102.5°	34.7	33.4	51.4	69.5	87.6	105.6	116.4	120.1	123.8	127.5	131.2
105°	36.2	34.8	69.5	104.0	138.7	173.3	188.7	184.9	181.2	177.3	173.5
107.5°	47.3	48.8	90.3	131.8	173.3	214.8	234.1	231.0	228.0	224.9	221.8
110°	87.2	99.9	136.6	173.2	209.9	246.5	263.5	260.8	258.2	255.5	252.8



TEST NUMBER: P331789-930

CATALOG NUMBER: S122RDIW-S485D710U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	205.7	251.9	261.0	270.0	279.1	288.1	291.5	289.1	286.8	284.5	282.1
115°	293.4	352.1	348.9	345.8	342.7	339.5	336.8	334.7	332.5	330.4	328.2
117.5°	375.9	390.0	387.8	385.7	383.5	381.3	379.0	376.6	374.2	371.8	369.4
120°	419.9	418.3	416.0	413.8	411.5	409.2	407.2	405.2	403.3	401.5	399.5
122.5°	446.2	445.3	442.8	440.3	437.8	435.4	433.1	431.1	429.1	427.1	425.1
125°	483.1	482.2	479.9	477.4	475.1	472.6	470.6	469.0	467.3	465.7	464.0
127.5°	516.9	515.6	513.8	512.0	510.2	508.4	506.6	504.8	503.0	501.1	499.3
130°	538.5	537.1	535.7	534.3	532.9	531.5	529.8	527.7	525.7	523.7	521.6
132.5°	559.7	558.6	557.2	555.7	554.3	552.9	551.4	549.7	548.0	546.3	544.5
135°	589.7	588.5	587.3	586.2	585.1	583.9	582.3	580.2	578.2	576.2	574.2
137.5°	617.7	616.4	615.1	613.8	612.5	611.2	609.8	608.5	607.1	605.6	604.2
140°	635.9	634.7	633.2	631.9	630.5	629.1	627.9	626.9	625.8	624.8	623.9
142.5°	652.6	651.6	650.0	648.4	646.8	645.1	643.9	643.0	642.1	641.2	640.3
145°	676.1	675.2	673.0	670.9	668.7	666.6	665.5	665.7	665.9	665.9	666.1
147.5°	696.7	695.9	693.8	691.7	689.6	687.5	686.6	687.1	687.6	688.1	688.5
150°	709.1	708.3	706.3	704.3	702.2	700.2	699.6	700.5	701.4	702.3	703.2
152.5°	720.5	719.7	717.8	715.8	714.0	712.0	711.5	712.5	713.5	714.5	715.5
155°	735.9	735.2	733.6	732.1	730.6	729.0	728.9	730.0	731.2	732.3	733.4
157.5°	748.8	747.9	746.8	745.8	744.7	743.6	743.6	744.5	745.5	746.5	747.5
160°	756.4	755.7	754.9	754.2	753.4	752.6	752.6	753.4	754.2	754.9	755.7
162.5°	763.4	762.5	761.9	761.2	760.5	759.9	759.9	760.7	761.5	762.2	763.0
165°	772.0	771.1	770.7	770.3	770.0	769.6	769.7	770.5	771.3	772.0	772.8
167.5°	779.2	778.3	778.0	777.6	777.2	776.9	777.1	777.8	778.6	779.3	780.1
170°	782.9	782.0	781.7	781.5	781.1	780.9	781.1	782.0	782.7	783.4	784.2
172.5°	785.5	784.6	784.4	784.2	783.9	783.7	783.9	784.6	785.5	786.2	786.9
175°	788.6	787.7	787.4	787.2	786.8	786.6	786.9	787.8	788.7	789.6	790.5
177.5°	789.0	788.3	788.2	788.1	788.0	787.9	788.2	789.0	789.6	790.4	791.1
180°	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8



TEST NUMBER: P331789-930

CATALOG NUMBER: S122RDIW-S485D710U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3	876.3
2.5°	881.3	882.1	887.0	889.2	893.6	895.3	897.2	896.7	896.7	897.6	904.5
5°	883.2	889.3	898.5	907.3	915.8	923.2	928.0	932.9	934.7	943.5	951.5
7.5°	880.1	891.3	906.4	919.8	936.0	948.6	959.0	968.5	974.9	987.8	1000.9
10°	876.0	891.8	908.8	926.2	948.4	965.2	982.2	995.3	999.6	1018.7	1029.7
12.5°	867.6	888.8	910.5	933.0	954.7	977.8	996.5	1009.7	1024.7	1041.9	1062.1
15°	855.2	879.6	907.9	936.9	967.9	995.9	1016.0	1038.9	1055.2	1074.2	1091.8
17.5°	837.4	868.8	904.7	938.2	974.1	1004.2	1031.9	1053.8	1065.4	1076.1	1078.8
20°	823.3	857.0	899.4	939.0	974.9	1009.6	1037.0	1055.2	1058.3	1058.6	1042.4
22.5°	808.0	846.1	890.4	930.9	973.9	1012.5	1033.8	1041.6	1029.6	1008.9	977.7
25°	779.8	823.9	875.3	921.6	968.5	1005.0	1012.4	998.7	956.3	911.8	855.6
27.5°	749.2	798.7	853.9	905.4	955.4	978.0	962.2	912.8	836.6	770.4	690.1
30°	726.8	782.4	836.7	894.2	940.4	950.2	914.0	841.2	752.4	652.5	572.4
32.5°	701.2	759.5	819.1	878.6	917.4	907.8	848.0	758.4	654.2	556.0	480.3
35°	664.6	725.0	789.1	848.8	873.5	832.4	742.9	626.3	519.8	428.1	376.0
37.5°	622.5	688.1	754.9	809.7	808.0	739.4	617.5	497.1	407.6	353.4	316.3
40°	592.5	658.8	731.0	777.3	757.5	668.3	536.1	422.6	357.1	313.9	286.8
42.5°	563.8	630.4	702.1	738.8	704.4	594.8	463.1	374.1	320.1	286.4	264.4
45°	514.9	585.1	651.6	672.0	610.4	489.6	374.5	310.0	274.0	249.1	233.8
47.5°	467.1	536.2	596.8	597.2	514.0	397.1	315.9	268.2	237.6	218.3	207.2
50°	437.8	503.6	554.4	546.5	452.2	353.2	282.5	241.4	215.9	201.0	189.4
52.5°	405.0	468.7	512.7	490.2	399.7	310.8	252.6	218.1	196.9	183.9	173.6
55°	357.1	413.8	444.8	410.7	326.1	258.4	213.4	186.3	170.5	159.6	150.7
57.5°	310.2	356.9	376.4	336.7	268.6	214.3	180.5	160.2	144.5	136.6	132.1
60°	280.7	320.6	334.3	290.5	233.5	187.5	159.9	141.0	129.4	124.3	119.7
62.5°	251.8	284.3	290.0	249.8	203.6	164.2	140.4	124.4	116.8	111.8	107.5
65°	208.9	232.3	229.6	197.3	161.0	130.3	112.9	103.2	97.4	90.4	82.8
67.5°	171.9	186.3	177.7	153.4	122.9	101.3	89.9	82.6	75.4	68.7	67.0
70°	148.5	156.8	147.7	125.5	100.8	85.0	75.8	67.0	62.7	61.2	58.5
72.5°	126.2	129.1	119.2	100.1	82.0	70.4	61.5	56.5	54.2	52.9	51.1
75°	94.7	92.5	84.1	69.1	56.9	49.0	46.3	44.4	43.0	41.7	40.8
77.5°	66.5	63.3	55.8	46.1	39.6	35.9	34.2	33.3	32.5	31.9	31.0
80°	49.9	47.8	40.2	32.9	30.2	28.3	27.4	26.2	26.2	25.6	24.6
82.5°	36.5	34.2	27.6	24.1	22.6	21.5	20.8	20.1	19.8	20.0	19.3
85°	19.2	15.5	13.7	13.1	12.1	11.6	11.9	11.3	11.3	11.3	10.9
87.5°	6.3	5.3	5.3	5.4	5.9	6.0	6.0	6.2	6.7	6.5	6.9
90°	2.0	3.3	4.7	6.1	7.3	8.4	9.4	10.4	11.4	12.1	12.7
92.5°	11.4	11.3	11.2	11.0	11.3	11.7	12.2	12.7	13.2	13.5	13.9
95°	32.9	28.7	24.5	20.4	18.7	19.6	20.5	21.4	22.3	22.9	23.6
97.5°	61.8	50.1	38.2	26.4	21.6	23.6	25.7	27.7	29.8	30.3	30.8
100°	83.6	66.3	48.9	31.6	23.9	26.1	28.2	30.4	32.5	33.5	34.6
102.5°	127.5	123.8	120.1	116.4	105.6	87.6	69.5	51.4	33.4	34.7	36.1
105°	177.3	181.2	184.9	188.7	173.3	138.7	104.0	69.5	34.8	36.2	37.6
107.5°	224.9	228.0	231.0	234.1	214.8	173.3	131.8	90.3	48.8	47.3	45.9
110°	255.5	258.2	260.8	263.5	246.5	209.9	173.2	136.6	99.9	87.2	74.5



TEST NUMBER: P331789-930

CATALOG NUMBER: S122RDIW-S485D710U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	284.5	286.8	289.1	291.5	288.1	279.1	270.0	261.0	251.9	205.7	159.4
115°	330.4	332.5	334.7	336.8	339.5	342.7	345.8	348.9	352.1	293.4	234.7
117.5°	371.8	374.2	376.6	379.0	381.3	383.5	385.7	387.8	390.0	375.9	361.7
120°	401.5	403.3	405.2	407.2	409.2	411.5	413.8	416.0	418.3	419.9	421.4
122.5°	427.1	429.1	431.1	433.1	435.4	437.8	440.3	442.8	445.3	446.2	447.1
125°	465.7	467.3	469.0	470.6	472.6	475.1	477.4	479.9	482.2	483.1	484.0
127.5°	501.1	503.0	504.8	506.6	508.4	510.2	512.0	513.8	515.6	516.9	518.2
130°	523.7	525.7	527.7	529.8	531.5	532.9	534.3	535.7	537.1	538.5	539.9
132.5°	546.3	548.0	549.7	551.4	552.9	554.3	555.7	557.2	558.6	559.7	560.9
135°	576.2	578.2	580.2	582.3	583.9	585.1	586.2	587.3	588.5	589.7	591.0
137.5°	605.6	607.1	608.5	609.8	611.2	612.5	613.8	615.1	616.4	617.7	618.9
140°	624.8	625.8	626.9	627.9	629.1	630.5	631.9	633.2	634.7	635.9	637.0
142.5°	641.2	642.1	643.0	643.9	645.1	646.8	648.4	650.0	651.6	652.6	653.6
145°	665.9	665.9	665.7	665.5	666.6	668.7	670.9	673.0	675.2	676.1	676.9
147.5°	688.1	687.6	687.1	686.6	687.5	689.6	691.7	693.8	695.9	696.7	697.3
150°	702.3	701.4	700.5	699.6	700.2	702.2	704.3	706.3	708.3	709.1	709.8
152.5°	714.5	713.5	712.5	711.5	712.0	714.0	715.8	717.8	719.7	720.5	721.2
155°	732.3	731.2	730.0	728.9	729.0	730.6	732.1	733.6	735.2	735.9	736.6
157.5°	746.5	745.5	744.5	743.6	743.6	744.7	745.8	746.8	747.9	748.8	749.7
160°	754.9	754.2	753.4	752.6	752.6	753.4	754.2	754.9	755.7	756.4	757.2
162.5°	762.2	761.5	760.7	759.9	759.9	760.5	761.2	761.9	762.5	763.4	764.3
165°	772.0	771.3	770.5	769.7	769.6	770.0	770.3	770.7	771.1	772.0	772.9
167.5°	779.3	778.6	777.8	777.1	776.9	777.2	777.6	778.0	778.3	779.2	780.1
170°	783.4	782.7	782.0	781.1	780.9	781.1	781.5	781.7	782.0	782.9	783.7
172.5°	786.2	785.5	784.6	783.9	783.7	783.9	784.2	784.4	784.6	785.5	786.4
175°	789.6	788.7	787.8	786.9	786.6	786.8	787.2	787.4	787.7	788.6	789.5
177.5°	790.4	789.6	789.0	788.2	787.9	788.0	788.1	788.2	788.3	789.0	789.8
180°	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8



TEST NUMBER: P331789-930

CATALOG NUMBER: S122RDIW-S485D710U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	876.3	876.3	876.3	876.3	876.3	876.3	876.3
2.5°	906.9	910.1	911.6	911.6	913.3	912.6	911.8
5°	959.0	964.8	966.0	971.5	975.5	974.3	974.9
7.5°	1010.9	1020.2	1029.4	1033.6	1034.3	1036.7	1037.6
10°	1042.8	1050.4	1064.7	1062.6	1073.3	1079.3	1069.3
12.5°	1073.5	1083.8	1093.7	1096.4	1102.4	1104.4	1100.4
15°	1101.2	1106.7	1107.3	1105.8	1107.7	1106.1	1100.3
17.5°	1075.3	1066.4	1048.4	1039.8	1033.1	1023.1	1019.1
20°	1032.4	1006.2	975.8	963.6	949.3	921.3	928.0
22.5°	939.9	910.0	879.6	844.0	827.0	800.5	798.9
25°	795.9	744.4	687.8	648.2	625.1	598.6	587.0
27.5°	618.8	554.0	507.6	484.1	462.7	441.7	440.8
30°	502.4	453.6	417.8	397.6	384.6	375.7	377.6
32.5°	423.5	390.0	365.8	349.2	339.5	332.8	332.7
35°	346.2	323.3	307.8	300.8	293.8	288.9	289.3
37.5°	296.3	282.5	273.9	266.2	261.8	259.4	258.0
40°	270.7	259.4	252.7	248.2	244.5	241.2	240.5
42.5°	250.5	241.2	234.4	230.8	227.5	225.0	224.5
45°	222.3	214.7	208.6	204.6	203.1	201.0	201.0
47.5°	197.7	190.2	185.5	183.0	180.3	179.0	178.9
50°	181.2	175.4	171.1	169.6	167.5	166.6	166.2
52.5°	166.3	162.0	158.9	157.9	156.9	155.8	156.0
55°	146.1	143.7	142.5	141.5	140.1	138.2	139.4
57.5°	129.1	127.1	123.8	120.9	119.5	118.2	118.7
60°	117.2	112.9	108.7	105.3	104.4	101.7	101.7
62.5°	102.2	96.1	90.9	89.0	88.1	86.8	86.6
65°	78.5	76.1	74.9	73.7	73.1	73.1	72.5
67.5°	65.1	64.1	62.8	62.5	61.9	61.7	61.5
70°	57.6	56.3	55.7	55.4	54.8	55.1	54.2
72.5°	50.2	49.2	49.2	48.3	48.0	48.0	47.4
75°	39.5	39.5	39.3	39.0	38.4	38.1	38.4
77.5°	30.4	30.5	29.9	29.9	29.8	29.9	29.6
80°	24.4	24.6	24.4	24.1	23.7	24.1	23.7
82.5°	19.2	18.8	18.8	18.7	18.7	18.4	18.4
85°	10.9	11.3	10.9	10.7	10.7	10.7	10.9
87.5°	6.8	6.9	7.0	7.1	7.1	7.2	7.0
90°	13.3	13.9	14.4	14.7	14.9	15.2	15.4
92.5°	14.3	14.6	14.8	14.9	15.1	15.2	15.4
95°	24.1	24.8	25.0	24.9	24.8	24.7	24.5
97.5°	31.3	31.8	32.1	32.3	32.4	32.6	32.8
100°	35.5	36.6	37.3	37.5	37.7	38.0	38.2
102.5°	37.4	38.7	39.5	39.9	40.3	40.6	41.0
105°	39.0	40.4	41.3	41.8	42.4	42.9	43.4
107.5°	44.5	43.0	42.6	43.1	43.6	44.1	44.6
110°	61.8	49.2	43.0	43.5	44.1	44.6	45.1



TEST NUMBER: P331789-930

CATALOG NUMBER: S122RDIW-S485D710U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	113.2	66.9	43.9	44.4	44.8	45.2	45.6
115°	175.9	117.2	83.3	74.2	65.1	55.9	46.8
117.5°	347.4	333.2	311.1	281.1	251.1	221.1	191.1
120°	422.9	424.4	416.6	399.5	382.4	365.3	348.1
122.5°	448.0	449.0	447.8	444.4	441.1	437.8	434.5
125°	484.9	485.8	486.5	486.8	487.2	487.6	488.0
127.5°	519.5	520.8	521.5	521.5	521.6	521.7	521.8
130°	541.3	542.7	543.3	543.2	543.1	542.9	542.8
132.5°	562.1	563.3	563.9	563.7	563.6	563.5	563.4
135°	592.2	593.5	594.0	593.8	593.5	593.3	593.0
137.5°	620.1	621.4	621.8	621.3	620.9	620.5	620.0
140°	638.1	639.3	639.5	638.9	638.2	637.6	637.0
142.5°	654.7	655.7	655.9	655.3	654.7	654.0	653.4
145°	677.8	678.7	678.9	678.2	677.6	676.9	676.4
147.5°	698.0	698.6	698.7	698.1	697.7	697.1	696.5
150°	710.6	711.3	711.4	710.8	710.1	709.5	708.9
152.5°	722.0	722.8	722.8	721.9	721.1	720.2	719.3
155°	737.4	738.2	738.0	737.0	736.1	735.0	734.0
157.5°	750.5	751.4	751.3	750.3	749.3	748.4	747.3
160°	758.0	758.7	758.6	757.7	756.8	756.0	755.1
162.5°	765.1	766.0	765.9	764.8	763.7	762.5	761.5
165°	773.7	774.6	774.6	773.7	772.9	772.0	771.1
167.5°	781.0	781.8	781.7	780.6	779.4	778.3	777.1
170°	784.6	785.5	785.4	784.2	783.1	782.0	780.8
172.5°	787.3	788.2	788.1	786.9	785.8	784.6	783.5
175°	790.3	791.2	791.0	789.7	788.5	787.2	785.9
177.5°	790.4	791.2	791.1	790.2	789.2	788.3	787.4
180°	788.8	788.8	788.8	788.8	788.8	788.8	788.8

(END OF REPORT)