

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331842-930

Luminaire Tested: **S122RDIW-S865D1440U930-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331842-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S865D1440U930-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1440 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6769.1 lumens
Efficiency: N/A
Efficacy: 88.4 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 76.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331842-930

CATALOG NUMBER: S122RDIW-S865D1440U930-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331842-930

CATALOG NUMBER: S122RDIW-S865D1440U930-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	40
1	96	92	88	85	87	84	81	78	69	67	65	55	54	52	42	41	41	35
2	88	81	75	71	80	74	69	65	61	58	55	49	47	45	38	37	35	30
3	81	72	65	60	73	66	60	55	55	50	47	44	41	39	34	32	31	26
4	74	64	57	51	67	59	52	47	49	44	40	40	36	34	31	29	27	23
5	68	57	50	44	62	53	46	41	44	39	35	36	32	30	28	26	24	21
6	63	52	44	39	57	48	41	36	40	35	31	33	29	26	26	24	22	19
7	59	47	39	34	53	43	37	32	36	31	28	30	26	24	24	21	19	17
8	54	43	35	30	50	40	33	29	33	28	25	28	24	21	22	20	18	15
9	51	39	32	27	46	36	30	26	31	26	22	26	22	19	21	18	16	14
10	47	36	29	25	43	33	27	23	28	24	20	24	20	18	19	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	25137	25137	25137	25137
5°	28075	25293	22428	25293
10°	31147	25117	19441	25117
15°	32679	24749	15318	24749
20°	28331	24204	13254	24204
25°	18579	23457	11834	23457
30°	12506	22551	10711	22551
35°	10129	21409	9660	21409
40°	9008	20168	8939	20168
45°	8152	18712	7978	18712
50°	7420	17269	7390	17269
55°	6975	15671	6883	15671
60°	5835	14202	5767	14202
65°	4917	12894	5578	12894
70°	4546	11514	5264	11514
75°	4255	10025	4860	10025
80°	3924	8247	4333	8247
85°	3612	6502	3798	6502



TEST NUMBER: P331842-930

CATALOG NUMBER: S122RDIW-S865D1440U930-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	147.6	2.2
10°-20°	411.2	6.1
20°-30°	529.9	7.8
30°-40°	503.6	7.4
40°-50°	431.4	6.4
50°-60°	328.5	4.9
60°-70°	207.7	3.1
70°-80°	103.7	1.5
80°-90°	32.8	0.5
90°-100°	92.3	1.4
100°-110°	286.6	4.2
110°-120°	490.0	7.2
120°-130°	644.3	9.5
130°-140°	723.2	10.7
140°-150°	709.1	10.5
150°-160°	594.8	8.8
160°-170°	394.5	5.8
170°-180°	137.9	2.0
0°-30°	1088.7	16.1
0°-40°	1592.3	23.5
0°-60°	2352.3	34.8
0°-90°	2696.4	39.8
90°-120°	868.9	12.8
90°-150°	2945.5	43.5
90°-180°	4073.0	60.2
0°-180°	6769.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1557	1557	1557	1557	1557	
5°	1732	1561	1384	1561	1732	171
15°	1955	1481	916	1481	1955	527
25°	1043	1317	664	1317	1043	495
35°	514	1086	490	1086	514	329
45°	357	820	349	820	357	276
55°	248	557	244	557	248	217
65°	129	338	146	338	129	131
75°	68	161	78	161	68	72
85°	20	35	20	35	20	22
90°	42	1	42	1	42	19
95°	76	64	76	64	76	85
105°	273	264	273	264	273	287
115°	492	492	492	492	492	486
125°	718	715	718	715	718	640
135°	937	926	937	926	937	721
145°	1136	1123	1136	1123	1136	709
155°	1294	1284	1294	1284	1294	596
165°	1399	1398	1399	1398	1399	394
175°	1449	1454	1449	1454	1449	138
180°	1456	1456	1456	1456	1456	



TEST NUMBER: P331842-930

CATALOG NUMBER: S122RDIW-S865D1440U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9
2.5°	1620.1	1621.4	1622.7	1619.6	1619.6	1617.1	1611.4	1607.1	1595.0	1593.3	1593.3
5°	1732.2	1731.0	1733.2	1726.2	1716.4	1714.3	1704.1	1690.5	1676.4	1660.8	1657.5
7.5°	1843.6	1841.9	1837.6	1836.5	1829.0	1812.7	1796.1	1778.5	1755.1	1732.3	1720.8
10°	1899.8	1917.7	1906.9	1887.9	1891.7	1866.3	1852.8	1829.5	1810.0	1776.0	1768.4
12.5°	1955.3	1962.3	1958.8	1948.1	1943.3	1925.6	1907.3	1887.1	1851.1	1820.6	1793.9
15°	1955.0	1965.3	1968.0	1964.8	1967.5	1966.4	1956.6	1939.8	1908.5	1874.9	1845.8
17.5°	1810.7	1817.9	1835.6	1847.5	1862.7	1894.8	1910.6	1916.7	1912.0	1892.9	1872.3
20°	1648.9	1637.0	1686.7	1712.1	1733.7	1787.9	1834.4	1852.3	1880.9	1880.4	1874.9
22.5°	1419.4	1422.3	1469.5	1499.7	1562.8	1616.9	1670.0	1737.2	1792.6	1829.3	1850.7
25°	1042.9	1063.6	1110.6	1151.7	1222.1	1322.7	1414.1	1520.1	1620.2	1699.2	1774.3
27.5°	783.3	784.8	822.1	860.1	901.9	984.3	1099.4	1226.0	1368.7	1486.5	1621.9
30°	670.8	667.6	683.2	706.5	742.2	806.0	892.6	1017.0	1159.3	1336.7	1494.7
32.5°	591.2	591.3	603.2	620.4	650.0	693.1	752.4	853.5	987.9	1162.3	1347.5
35°	513.9	513.4	522.0	534.4	546.9	574.5	615.1	668.1	760.6	923.4	1112.7
37.5°	458.5	460.9	465.1	472.9	486.7	502.0	526.4	562.0	627.9	724.1	883.3
40°	427.4	428.4	434.4	440.9	449.0	460.9	480.9	509.6	557.7	634.5	750.8
42.5°	398.8	399.9	404.1	410.2	416.5	428.4	445.0	469.8	508.8	568.8	664.7
45°	357.0	357.0	360.9	363.5	370.6	381.4	394.9	415.5	442.5	486.9	550.7
47.5°	317.9	318.0	320.5	325.1	329.5	338.0	351.3	368.1	387.8	422.1	476.6
50°	295.4	295.9	297.5	301.3	304.0	311.6	321.9	336.5	357.0	383.5	429.0
52.5°	277.2	276.9	278.9	280.5	282.4	287.8	295.5	308.3	326.8	349.8	387.4
55°	247.8	245.6	248.8	251.5	253.2	255.4	259.7	267.7	283.5	303.0	331.1
57.5°	211.0	210.1	212.4	214.8	220.0	225.8	229.5	234.6	242.8	256.7	284.6
60°	180.7	180.7	185.6	187.2	193.1	200.7	208.3	212.6	220.7	229.9	250.5
62.5°	153.8	154.3	156.5	158.2	161.5	170.8	181.4	190.9	198.6	207.4	221.0
65°	128.7	129.8	129.8	130.9	133.1	135.3	139.6	147.2	160.7	173.1	183.4
67.5°	109.3	109.6	109.9	111.0	111.5	113.9	115.7	119.0	122.1	134.0	146.7
70°	96.3	97.9	97.3	98.5	99.0	100.0	102.2	103.9	108.8	111.5	119.0
72.5°	84.1	85.4	85.3	85.9	87.3	87.6	89.3	90.9	94.0	96.3	100.4
75°	68.2	67.6	68.2	69.2	69.8	70.4	70.4	72.5	74.1	76.3	79.0
77.5°	52.6	53.2	53.0	53.2	53.2	54.2	54.1	55.0	56.7	57.8	59.1
80°	42.2	42.7	42.2	42.7	43.3	43.8	43.3	43.8	45.4	46.6	46.6
82.5°	32.7	32.8	33.1	33.2	33.3	33.4	34.2	34.3	35.5	35.3	35.7
85°	19.5	18.9	18.9	18.9	19.5	20.0	19.5	19.5	20.0	20.0	20.0
87.5°	15.2	15.7	15.6	15.6	15.5	15.5	15.7	16.1	15.8	16.4	14.8
90°	41.8	41.5	41.3	41.0	40.7	40.8	41.4	41.9	42.5	43.0	37.0
92.5°	39.8	39.8	39.7	39.6	39.6	39.5	39.4	39.3	39.2	39.1	37.7
95°	76.2	76.7	77.3	77.9	78.4	78.7	78.7	78.7	78.7	78.7	78.1
97.5°	132.0	132.1	132.1	132.2	132.2	132.2	132.2	132.2	132.2	132.2	131.2
100°	168.4	168.7	168.9	169.2	169.5	169.6	169.6	169.6	169.6	169.6	168.8
102.5°	209.7	209.9	210.3	210.5	210.8	210.8	210.6	210.3	210.2	209.9	208.9
105°	272.9	272.9	272.9	272.9	272.9	272.6	272.1	271.5	270.9	270.4	269.9
107.5°	332.3	333.6	334.8	336.1	337.4	337.9	337.7	337.5	337.2	337.0	337.0
110°	378.5	379.4	380.2	381.0	381.8	382.3	382.3	382.3	382.3	382.3	382.3



TEST NUMBER: P331842-930

CATALOG NUMBER: S122RDIW-S865D1440U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	422.8	423.4	424.0	424.6	425.2	425.8	426.5	427.1	427.8	428.4	428.7
115°	491.6	492.4	493.3	494.1	494.9	495.5	495.7	496.0	496.3	496.6	497.1
117.5°	557.3	558.1	558.9	559.7	560.5	561.3	562.0	562.6	563.3	563.9	565.4
120°	603.5	604.3	605.1	605.9	606.7	607.2	607.2	607.2	607.2	607.2	609.4
122.5°	648.7	649.3	650.0	650.5	651.1	651.8	652.4	653.1	653.7	654.4	655.9
125°	717.8	718.1	718.4	718.6	718.9	719.4	720.2	721.1	721.9	722.7	723.6
127.5°	780.7	781.6	782.4	783.3	784.2	785.1	786.1	787.1	788.1	789.1	790.1
130°	826.0	827.0	828.2	829.2	830.3	831.1	831.7	832.3	832.8	833.3	833.9
132.5°	869.2	870.1	871.0	871.9	872.7	873.8	875.0	876.2	877.3	878.6	878.5
135°	936.6	937.4	938.2	939.1	939.9	940.4	940.7	940.9	941.3	941.5	940.9
137.5°	997.5	998.7	999.7	1000.9	1001.9	1002.6	1002.8	1003.0	1003.2	1003.5	1002.7
140°	1039.8	1040.9	1042.0	1043.1	1044.2	1044.7	1044.7	1044.7	1044.7	1044.7	1043.4
142.5°	1078.2	1079.3	1080.4	1081.5	1082.6	1083.0	1082.8	1082.6	1082.3	1082.1	1081.2
145°	1135.7	1136.8	1137.9	1139.0	1140.0	1140.4	1140.2	1140.0	1139.6	1139.4	1137.8
147.5°	1187.1	1188.1	1189.1	1190.2	1191.2	1191.5	1190.8	1190.3	1189.7	1189.0	1188.0
150°	1220.5	1221.3	1222.1	1222.9	1223.8	1223.8	1222.9	1222.1	1221.3	1220.5	1219.4
152.5°	1252.0	1253.0	1254.0	1255.1	1256.1	1256.1	1255.1	1254.0	1253.0	1252.0	1250.7
155°	1294.3	1295.1	1295.9	1296.7	1297.5	1297.2	1295.9	1294.5	1293.1	1291.8	1290.9
157.5°	1330.6	1332.0	1333.3	1334.6	1335.9	1335.6	1333.7	1331.9	1330.0	1328.2	1327.7
160°	1353.2	1354.4	1355.4	1356.5	1357.6	1357.3	1355.7	1354.0	1352.4	1350.8	1350.5
162.5°	1372.9	1374.3	1375.6	1376.9	1378.2	1377.9	1376.1	1374.2	1372.3	1370.4	1370.2
165°	1398.7	1400.1	1401.5	1402.8	1404.2	1403.9	1402.0	1400.1	1398.2	1396.3	1396.3
167.5°	1419.8	1421.3	1422.7	1424.2	1425.6	1425.3	1423.4	1421.5	1419.6	1417.6	1417.7
170°	1430.7	1432.3	1433.9	1435.6	1437.2	1437.1	1435.2	1433.3	1431.3	1429.5	1429.7
172.5°	1439.6	1441.2	1442.8	1444.5	1446.1	1445.9	1444.1	1442.1	1440.2	1438.3	1438.6
175°	1449.1	1450.7	1452.4	1454.0	1455.7	1455.6	1453.6	1451.7	1449.8	1447.9	1448.5
177.5°	1453.5	1454.8	1456.2	1457.5	1458.8	1458.8	1457.5	1456.2	1454.8	1453.5	1454.0
180°	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5



TEST NUMBER: P331842-930

CATALOG NUMBER: S122RDIW-S865D1440U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9
2.5°	1594.1	1590.6	1587.6	1579.8	1575.9	1567.2	1565.9	1565.5	1554.3	1543.4	1540.4
5°	1648.9	1640.2	1627.2	1612.1	1596.4	1580.1	1569.3	1560.6	1539.0	1518.5	1506.6
7.5°	1704.1	1685.4	1663.0	1634.3	1610.5	1583.6	1563.7	1545.8	1515.2	1485.7	1465.9
10°	1745.1	1714.8	1685.1	1645.6	1614.8	1584.5	1556.3	1532.0	1497.4	1458.4	1430.9
12.5°	1770.7	1737.3	1696.3	1657.7	1617.8	1579.2	1541.6	1510.3	1469.7	1429.5	1396.6
15°	1805.2	1769.4	1719.7	1664.5	1613.2	1562.8	1519.6	1480.6	1427.6	1379.4	1339.4
17.5°	1833.4	1784.3	1730.9	1667.0	1607.5	1543.6	1487.8	1438.1	1379.1	1321.0	1273.8
20°	1842.5	1793.8	1732.2	1668.3	1598.0	1522.8	1462.7	1408.7	1345.3	1282.1	1228.0
22.5°	1836.9	1799.0	1730.4	1654.0	1582.0	1503.3	1435.5	1372.7	1302.5	1238.0	1175.2
25°	1798.7	1785.7	1720.8	1637.4	1555.3	1463.9	1385.4	1316.7	1236.6	1167.4	1099.2
27.5°	1709.7	1737.6	1697.5	1608.7	1517.3	1419.3	1331.1	1252.9	1169.8	1091.8	1023.9
30°	1624.0	1688.3	1671.0	1588.8	1486.5	1390.2	1291.3	1209.6	1120.9	1040.8	973.7
32.5°	1506.7	1613.0	1629.9	1561.1	1455.4	1349.6	1245.9	1164.6	1072.0	987.6	922.2
35°	1320.0	1479.0	1552.0	1508.2	1402.2	1288.0	1180.9	1086.2	993.2	909.9	845.0
37.5°	1097.1	1313.8	1435.5	1438.6	1341.2	1222.5	1106.0	1011.9	916.7	834.9	764.7
40°	952.6	1187.4	1345.9	1381.0	1298.9	1170.6	1052.7	956.9	863.9	783.8	703.3
42.5°	822.8	1056.7	1251.6	1312.7	1247.3	1120.0	1001.7	901.6	811.1	735.4	653.1
45°	665.4	869.8	1084.6	1193.9	1157.6	1039.8	914.8	819.5	734.6	669.2	590.2
47.5°	561.3	705.4	913.2	1061.0	1060.4	952.8	829.8	738.7	659.8	598.5	534.6
50°	502.0	627.5	803.3	971.0	985.0	894.7	777.9	687.5	614.0	549.6	498.2
52.5°	448.7	552.2	710.3	871.1	911.1	832.8	719.5	636.1	564.7	505.5	461.5
55°	379.2	459.3	579.4	729.8	790.4	735.2	634.5	556.7	498.8	449.0	411.2
57.5°	320.8	380.8	477.2	598.3	668.9	634.1	551.1	487.9	438.3	393.3	363.4
60°	284.0	333.2	414.9	516.1	593.9	569.6	498.8	439.8	397.6	358.7	330.5
62.5°	249.4	291.7	361.7	443.8	515.2	505.2	447.3	397.8	360.9	325.3	301.5
65°	200.7	231.5	286.2	350.6	407.9	412.8	371.1	337.5	304.6	276.5	255.4
67.5°	159.8	179.9	218.4	272.6	315.6	330.9	305.5	279.9	253.7	232.0	213.7
70°	134.7	150.9	179.0	222.9	262.4	278.6	264.0	243.9	221.3	203.4	187.7
72.5°	109.2	125.0	145.7	177.9	211.7	229.3	224.2	209.8	191.4	176.6	161.8
75°	82.3	87.1	101.2	122.8	149.3	164.4	168.3	160.7	146.0	134.7	126.0
77.5°	60.8	63.8	70.4	81.8	99.1	112.6	118.1	117.2	107.2	100.6	92.5
80°	48.7	50.3	53.6	58.5	71.4	85.0	88.7	88.7	81.7	79.0	70.8
82.5°	37.0	38.2	40.1	42.8	48.9	60.7	64.9	65.8	61.3	57.8	51.4
85°	21.1	20.5	21.6	23.2	24.4	27.6	34.1	35.1	34.1	29.8	28.1
87.5°	13.5	12.8	11.6	10.2	10.0	9.8	11.3	12.8	11.7	11.1	10.8
90°	31.0	25.0	19.0	14.3	11.1	7.7	4.5	1.2	4.5	7.7	11.1
92.5°	36.3	34.8	33.4	31.5	29.1	26.7	24.3	21.9	24.3	26.7	29.1
95°	77.5	77.0	76.5	74.8	72.1	69.4	66.6	63.9	66.6	69.4	72.1
97.5°	130.2	129.1	128.1	126.4	124.0	121.6	119.2	116.8	119.2	121.6	124.0
100°	168.0	167.1	166.3	164.9	162.7	160.5	158.2	156.1	158.2	160.5	162.7
102.5°	207.8	206.8	205.8	204.4	202.6	200.9	199.2	197.4	199.2	200.9	202.6
105°	269.3	268.8	268.2	267.5	266.7	265.9	265.1	264.2	265.1	265.9	266.7
107.5°	337.0	337.0	337.0	336.4	335.3	334.0	332.8	331.6	332.8	334.0	335.3
110°	382.3	382.3	382.3	381.4	379.8	378.1	376.5	374.9	376.5	378.1	379.8



TEST NUMBER: P331842-930

CATALOG NUMBER: S122RDIW-S865D1440U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	428.9	429.1	429.3	428.6	427.0	425.3	423.7	422.1	423.7	425.3	427.0
115°	497.7	498.2	498.7	498.2	496.6	494.9	493.3	491.6	493.3	494.9	496.6
117.5°	567.0	568.5	570.1	569.7	567.5	565.3	563.1	561.0	563.1	565.3	567.5
120°	611.6	613.8	616.0	616.0	613.8	611.6	609.4	607.2	609.4	611.6	613.8
122.5°	657.5	659.0	660.5	660.0	657.3	654.7	652.1	649.5	652.1	654.7	657.3
125°	724.4	725.2	726.0	725.2	722.7	720.2	717.8	715.3	717.8	720.2	722.7
127.5°	791.1	792.1	793.0	792.0	788.9	785.7	782.6	779.5	782.6	785.7	788.9
130°	834.5	834.9	835.5	834.1	830.5	827.0	823.4	819.8	823.4	827.0	830.5
132.5°	878.3	878.2	878.2	876.6	873.8	870.8	868.0	865.0	868.0	870.8	873.8
135°	940.4	939.9	939.3	937.5	934.5	931.6	928.5	925.5	928.5	931.6	934.5
137.5°	1002.0	1001.4	1000.6	999.0	996.5	994.1	991.6	989.2	991.6	994.1	996.5
140°	1042.0	1040.6	1039.3	1037.4	1034.9	1032.5	1030.0	1027.5	1030.0	1032.5	1034.9
142.5°	1080.3	1079.3	1078.4	1076.7	1074.2	1071.8	1069.3	1066.9	1069.3	1071.8	1074.2
145°	1136.1	1134.5	1132.9	1131.1	1129.1	1127.2	1125.4	1123.4	1125.4	1127.2	1129.1
147.5°	1186.8	1185.8	1184.7	1183.0	1180.7	1178.4	1176.1	1173.8	1176.1	1178.4	1180.7
150°	1218.3	1217.2	1216.1	1214.8	1213.2	1211.5	1209.8	1208.2	1209.8	1211.5	1213.2
152.5°	1249.4	1248.1	1246.8	1245.3	1243.6	1241.9	1240.3	1238.7	1240.3	1241.9	1243.6
155°	1290.1	1289.3	1288.5	1287.7	1286.9	1286.1	1285.2	1284.4	1285.2	1286.1	1286.9
157.5°	1327.2	1326.7	1326.2	1325.7	1325.2	1324.6	1324.0	1323.5	1324.0	1324.6	1325.2
160°	1350.2	1350.0	1349.7	1349.3	1348.7	1348.2	1347.7	1347.1	1347.7	1348.2	1348.7
162.5°	1369.9	1369.6	1369.4	1369.2	1369.1	1369.0	1368.9	1368.7	1368.9	1369.0	1369.1
165°	1396.3	1396.3	1396.3	1396.4	1396.7	1396.9	1397.3	1397.5	1397.3	1396.9	1396.7
167.5°	1417.8	1417.8	1417.9	1418.3	1419.1	1419.9	1420.7	1421.6	1420.7	1419.9	1419.1
170°	1430.0	1430.3	1430.5	1431.1	1431.9	1432.7	1433.5	1434.4	1433.5	1432.7	1431.9
172.5°	1438.8	1439.2	1439.4	1440.0	1440.8	1441.6	1442.4	1443.2	1442.4	1441.6	1440.8
175°	1448.9	1449.5	1450.1	1450.7	1451.6	1452.4	1453.2	1454.0	1453.2	1452.4	1451.6
177.5°	1454.4	1454.8	1455.3	1455.9	1456.5	1457.2	1457.8	1458.5	1457.8	1457.2	1456.5
180°	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5



TEST NUMBER: P331842-930

CATALOG NUMBER: S122RDIW-S865D1440U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9
2.5°	1534.8	1531.8	1526.2	1517.5	1512.3	1503.2	1497.1	1500.6	1501.5	1500.6	1499.7
5°	1493.5	1482.2	1466.6	1451.4	1437.3	1422.2	1413.5	1409.7	1402.2	1397.8	1395.7
7.5°	1443.7	1424.2	1401.9	1375.6	1353.2	1329.7	1317.7	1311.7	1296.2	1287.8	1280.4
10°	1406.5	1375.7	1353.5	1318.8	1297.8	1266.9	1245.9	1246.3	1225.2	1213.3	1204.7
12.5°	1365.4	1331.5	1294.6	1263.5	1234.1	1209.3	1184.0	1173.6	1151.3	1139.8	1116.4
15°	1297.2	1257.8	1218.8	1176.6	1146.8	1108.4	1071.6	1026.7	990.5	959.1	950.5
17.5°	1222.8	1173.9	1134.8	1085.2	1034.3	969.7	927.1	901.0	879.1	862.6	850.3
20°	1171.7	1121.9	1080.3	1005.7	936.9	893.2	861.8	841.7	819.0	801.2	791.4
22.5°	1118.0	1066.1	1009.3	926.0	872.5	837.3	809.3	786.4	770.9	757.0	748.1
25°	1041.9	985.0	891.5	834.1	790.8	754.1	734.6	720.6	704.3	685.4	676.7
27.5°	961.4	871.1	803.9	761.2	719.9	696.0	678.5	657.5	642.9	634.5	625.4
30°	901.2	810.9	758.4	711.9	682.7	656.2	635.6	623.7	609.7	595.1	589.1
32.5°	834.1	762.0	711.7	672.9	643.3	620.7	604.5	585.2	575.0	566.1	553.6
35°	750.8	696.2	650.2	618.9	590.8	572.3	553.4	542.0	523.7	516.1	511.2
37.5°	680.3	632.9	598.6	565.5	543.2	522.9	511.3	493.3	485.3	474.7	464.5
40°	640.5	593.9	561.0	533.9	509.1	493.9	479.3	464.7	452.8	447.9	435.5
42.5°	599.8	562.0	529.0	499.3	482.7	466.6	448.2	437.4	425.1	417.2	409.5
45°	543.6	510.1	482.0	457.6	439.3	422.5	410.6	392.7	385.7	370.0	363.5
47.5°	494.3	463.2	436.3	413.2	395.3	384.3	366.9	352.9	341.7	332.1	323.7
50°	459.3	433.3	407.3	386.8	370.6	354.9	337.0	330.0	312.7	307.8	303.0
52.5°	427.2	402.6	378.8	358.7	342.4	327.2	311.4	302.3	290.6	285.8	282.2
55°	382.5	358.7	335.9	318.0	301.8	286.2	276.5	265.1	259.7	255.8	251.5
57.5°	337.5	316.0	298.6	280.5	264.2	251.8	240.5	233.7	228.0	223.1	217.9
60°	308.9	288.3	272.6	255.8	239.1	228.9	220.1	212.1	205.5	198.0	195.8
62.5°	278.6	260.7	246.2	229.9	215.3	205.9	197.6	190.0	182.2	171.1	168.1
65°	236.9	222.9	207.7	194.2	181.2	172.0	160.1	151.5	148.2	147.2	146.6
67.5°	199.3	186.0	173.0	159.1	147.3	138.8	132.7	131.4	129.1	128.5	127.0
70°	174.1	161.8	148.8	135.7	124.4	122.8	120.7	118.5	115.8	114.7	113.6
72.5°	151.6	138.8	125.8	115.4	110.6	108.5	106.3	104.2	102.3	101.3	100.6
75°	116.3	104.4	95.7	92.0	89.3	87.6	84.4	82.8	81.7	80.1	79.5
77.5°	83.7	77.0	73.1	70.7	67.8	66.1	64.2	62.6	61.5	61.1	60.3
80°	63.8	60.6	57.9	54.6	53.6	51.4	50.9	49.2	49.7	48.2	48.2
82.5°	49.6	45.4	43.1	41.7	40.6	38.8	38.3	37.5	37.7	36.4	36.4
85°	25.4	24.4	23.2	22.2	22.2	20.5	21.1	20.5	20.5	19.5	18.9
87.5°	11.1	11.6	11.9	13.1	14.3	15.1	15.0	14.4	14.3	14.2	13.8
90°	14.3	19.0	25.0	31.0	37.0	43.0	42.5	41.9	41.4	40.8	40.7
92.5°	31.5	33.4	34.8	36.3	37.7	39.1	39.2	39.3	39.4	39.5	39.6
95°	74.8	76.5	77.0	77.5	78.1	78.7	78.7	78.7	78.7	78.7	78.4
97.5°	126.4	128.1	129.1	130.2	131.2	132.2	132.2	132.2	132.2	132.2	132.2
100°	164.9	166.3	167.1	168.0	168.8	169.6	169.6	169.6	169.6	169.6	169.5
102.5°	204.4	205.8	206.8	207.8	208.9	209.9	210.2	210.3	210.6	210.8	210.8
105°	267.5	268.2	268.8	269.3	269.9	270.4	270.9	271.5	272.1	272.6	272.9
107.5°	336.4	337.0	337.0	337.0	337.0	337.0	337.2	337.5	337.7	337.9	337.4
110°	381.4	382.3	382.3	382.3	382.3	382.3	382.3	382.3	382.3	382.3	381.8



TEST NUMBER: P331842-930

CATALOG NUMBER: S122RDIW-S865D1440U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	428.6	429.3	429.1	428.9	428.7	428.4	427.8	427.1	426.5	425.8	425.2
115°	498.2	498.7	498.2	497.7	497.1	496.6	496.3	496.0	495.7	495.5	494.9
117.5°	569.7	570.1	568.5	567.0	565.4	563.9	563.3	562.6	562.0	561.3	560.5
120°	616.0	616.0	613.8	611.6	609.4	607.2	607.2	607.2	607.2	607.2	606.7
122.5°	660.0	660.5	659.0	657.5	655.9	654.4	653.7	653.1	652.4	651.8	651.1
125°	725.2	726.0	725.2	724.4	723.6	722.7	721.9	721.1	720.2	719.4	718.9
127.5°	792.0	793.0	792.1	791.1	790.1	789.1	788.1	787.1	786.1	785.1	784.2
130°	834.1	835.5	834.9	834.5	833.9	833.3	832.8	832.3	831.7	831.1	830.3
132.5°	876.6	878.2	878.2	878.3	878.5	878.6	877.3	876.2	875.0	873.8	872.7
135°	937.5	939.3	939.9	940.4	940.9	941.5	941.3	940.9	940.7	940.4	939.9
137.5°	999.0	1000.6	1001.4	1002.0	1002.7	1003.5	1003.2	1003.0	1002.8	1002.6	1001.9
140°	1037.4	1039.3	1040.6	1042.0	1043.4	1044.7	1044.7	1044.7	1044.7	1044.7	1044.2
142.5°	1076.7	1078.4	1079.3	1080.3	1081.2	1082.1	1082.3	1082.6	1082.8	1083.0	1082.6
145°	1131.1	1132.9	1134.5	1136.1	1137.8	1139.4	1139.6	1140.0	1140.2	1140.4	1140.0
147.5°	1183.0	1184.7	1185.8	1186.8	1188.0	1189.0	1189.7	1190.3	1190.8	1191.5	1191.2
150°	1214.8	1216.1	1217.2	1218.3	1219.4	1220.5	1221.3	1222.1	1222.9	1223.8	1223.8
152.5°	1245.3	1246.8	1248.1	1249.4	1250.7	1252.0	1253.0	1254.0	1255.1	1256.1	1256.1
155°	1287.7	1288.5	1289.3	1290.1	1290.9	1291.8	1293.1	1294.5	1295.9	1297.2	1297.5
157.5°	1325.7	1326.2	1326.7	1327.2	1327.7	1328.2	1330.0	1331.9	1333.7	1335.6	1335.9
160°	1349.3	1349.7	1350.0	1350.2	1350.5	1350.8	1352.4	1354.0	1355.7	1357.3	1357.6
162.5°	1369.2	1369.4	1369.6	1369.9	1370.2	1370.4	1372.3	1374.2	1376.1	1377.9	1378.2
165°	1396.4	1396.3	1396.3	1396.3	1396.3	1396.3	1398.2	1400.1	1402.0	1403.9	1404.2
167.5°	1418.3	1417.9	1417.8	1417.8	1417.7	1417.6	1419.6	1421.5	1423.4	1425.3	1425.6
170°	1431.1	1430.5	1430.3	1430.0	1429.7	1429.5	1431.3	1433.3	1435.2	1437.1	1437.2
172.5°	1440.0	1439.4	1439.2	1438.8	1438.6	1438.3	1440.2	1442.1	1444.1	1445.9	1446.1
175°	1450.7	1450.1	1449.5	1448.9	1448.5	1447.9	1449.8	1451.7	1453.6	1455.6	1455.7
177.5°	1455.9	1455.3	1454.8	1454.4	1454.0	1453.5	1454.8	1456.2	1457.5	1458.8	1458.8
180°	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5



TEST NUMBER: P331842-930

CATALOG NUMBER: S122RDIW-S865D1440U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9
2.5°	1495.0	1495.8	1494.5	1495.4	1494.5	1495.8	1495.0	1499.7	1500.6	1501.5	1500.6
5°	1392.9	1386.5	1385.4	1383.8	1385.4	1386.5	1392.9	1395.7	1397.8	1402.2	1409.7
7.5°	1271.1	1270.2	1267.5	1263.7	1267.5	1270.2	1271.1	1280.4	1287.8	1296.2	1311.7
10°	1192.8	1190.1	1189.6	1185.8	1189.6	1190.1	1192.8	1204.7	1213.3	1225.2	1246.3
12.5°	1101.1	1083.6	1081.8	1072.4	1081.8	1083.6	1101.1	1116.4	1139.8	1151.3	1173.6
15°	937.5	934.3	923.4	916.4	923.4	934.3	937.5	950.5	959.1	990.5	1026.7
17.5°	844.0	833.4	830.1	828.5	830.1	833.4	844.0	850.3	862.6	879.1	901.0
20°	783.8	774.1	772.5	771.4	772.5	774.1	783.8	791.4	801.2	819.0	841.7
22.5°	742.3	732.1	727.9	724.6	727.9	732.1	742.3	748.1	757.0	770.9	786.4
25°	671.3	667.6	665.4	664.3	665.4	667.6	671.3	676.7	685.4	704.3	720.6
27.5°	615.8	607.5	605.8	603.1	605.8	607.5	615.8	625.4	634.5	642.9	657.5
30°	584.2	581.6	577.7	574.5	577.7	581.6	584.2	589.1	595.1	609.7	623.7
32.5°	547.0	544.8	541.4	539.9	541.4	544.8	547.0	553.6	566.1	575.0	585.2
35°	505.8	498.2	495.0	490.1	495.0	498.2	505.8	511.2	516.1	523.7	542.0
37.5°	462.2	458.2	453.6	455.3	453.6	458.2	462.2	464.5	474.7	485.3	493.3
40°	428.4	425.7	424.7	424.1	424.7	425.7	428.4	435.5	447.9	452.8	464.7
42.5°	401.6	394.1	391.3	391.2	391.3	394.1	401.6	409.5	417.2	425.1	437.4
45°	360.9	353.8	348.9	349.4	348.9	353.8	360.9	363.5	370.0	385.7	392.7
47.5°	319.0	318.9	315.8	316.8	315.8	318.9	319.0	323.7	332.1	341.7	352.9
50°	299.1	295.9	293.8	294.2	293.8	295.9	299.1	303.0	307.8	312.7	330.0
52.5°	280.1	277.3	275.6	277.9	275.6	277.3	280.1	282.2	285.8	290.6	302.3
55°	248.8	245.6	245.1	244.5	245.1	245.6	248.8	251.5	255.8	259.7	265.1
57.5°	213.9	211.7	208.5	207.1	208.5	211.7	213.9	217.9	223.1	228.0	233.7
60°	188.8	184.5	179.0	178.6	179.0	184.5	188.8	195.8	198.0	205.5	212.1
62.5°	165.8	165.0	163.9	163.8	163.9	165.0	165.8	168.1	171.1	182.2	190.0
65°	145.5	145.0	145.5	146.0	145.5	145.0	145.5	146.6	147.2	148.2	151.5
67.5°	126.8	125.8	124.8	125.3	124.8	125.8	126.8	127.0	128.5	129.1	131.4
70°	112.5	111.9	111.5	111.5	111.5	111.9	112.5	113.6	114.7	115.8	118.5
72.5°	98.7	98.6	98.0	97.6	98.0	98.6	98.7	100.6	101.3	102.3	104.2
75°	79.0	77.9	77.9	77.9	77.9	77.9	79.0	79.5	80.1	81.7	82.8
77.5°	60.2	59.6	59.1	58.6	59.1	59.6	60.2	60.3	61.1	61.5	62.6
80°	47.6	47.0	46.6	46.6	46.6	47.0	47.6	48.2	48.2	49.7	49.2
82.5°	36.4	35.8	35.7	35.3	35.7	35.8	36.4	36.4	36.4	37.7	37.5
85°	19.5	20.0	19.5	20.5	19.5	20.0	19.5	18.9	19.5	20.5	20.5
87.5°	13.9	13.5	13.9	13.5	13.9	13.5	13.9	13.8	14.2	14.3	14.4
90°	41.0	41.3	41.5	41.8	41.5	41.3	41.0	40.7	40.8	41.4	41.9
92.5°	39.6	39.7	39.8	39.8	39.8	39.7	39.6	39.6	39.5	39.4	39.3
95°	77.9	77.3	76.7	76.2	76.7	77.3	77.9	78.4	78.7	78.7	78.7
97.5°	132.2	132.1	132.1	132.0	132.1	132.1	132.2	132.2	132.2	132.2	132.2
100°	169.2	168.9	168.7	168.4	168.7	168.9	169.2	169.5	169.6	169.6	169.6
102.5°	210.5	210.3	209.9	209.7	209.9	210.3	210.5	210.8	210.8	210.6	210.3
105°	272.9	272.9	272.9	272.9	272.9	272.9	272.9	272.9	272.6	272.1	271.5
107.5°	336.1	334.8	333.6	332.3	333.6	334.8	336.1	337.4	337.9	337.7	337.5
110°	381.0	380.2	379.4	378.5	379.4	380.2	381.0	381.8	382.3	382.3	382.3



TEST NUMBER: P331842-930

CATALOG NUMBER: S122RDIW-S865D1440U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	424.6	424.0	423.4	422.8	423.4	424.0	424.6	425.2	425.8	426.5	427.1
115°	494.1	493.3	492.4	491.6	492.4	493.3	494.1	494.9	495.5	495.7	496.0
117.5°	559.7	558.9	558.1	557.3	558.1	558.9	559.7	560.5	561.3	562.0	562.6
120°	605.9	605.1	604.3	603.5	604.3	605.1	605.9	606.7	607.2	607.2	607.2
122.5°	650.5	650.0	649.3	648.7	649.3	650.0	650.5	651.1	651.8	652.4	653.1
125°	718.6	718.4	718.1	717.8	718.1	718.4	718.6	718.9	719.4	720.2	721.1
127.5°	783.3	782.4	781.6	780.7	781.6	782.4	783.3	784.2	785.1	786.1	787.1
130°	829.2	828.2	827.0	826.0	827.0	828.2	829.2	830.3	831.1	831.7	832.3
132.5°	871.9	871.0	870.1	869.2	870.1	871.0	871.9	872.7	873.8	875.0	876.2
135°	939.1	938.2	937.4	936.6	937.4	938.2	939.1	939.9	940.4	940.7	940.9
137.5°	1000.9	999.7	998.7	997.5	998.7	999.7	1000.9	1001.9	1002.6	1002.8	1003.0
140°	1043.1	1042.0	1040.9	1039.8	1040.9	1042.0	1043.1	1044.2	1044.7	1044.7	1044.7
142.5°	1081.5	1080.4	1079.3	1078.2	1079.3	1080.4	1081.5	1082.6	1083.0	1082.8	1082.6
145°	1139.0	1137.9	1136.8	1135.7	1136.8	1137.9	1139.0	1140.0	1140.4	1140.2	1140.0
147.5°	1190.2	1189.1	1188.1	1187.1	1188.1	1189.1	1190.2	1191.2	1191.5	1190.8	1190.3
150°	1222.9	1222.1	1221.3	1220.5	1221.3	1222.1	1222.9	1223.8	1223.8	1222.9	1222.1
152.5°	1255.1	1254.0	1253.0	1252.0	1253.0	1254.0	1255.1	1256.1	1256.1	1255.1	1254.0
155°	1296.7	1295.9	1295.1	1294.3	1295.1	1295.9	1296.7	1297.5	1297.2	1295.9	1294.5
157.5°	1334.6	1333.3	1332.0	1330.6	1332.0	1333.3	1334.6	1335.9	1335.6	1333.7	1331.9
160°	1356.5	1355.4	1354.4	1353.2	1354.4	1355.4	1356.5	1357.6	1357.3	1355.7	1354.0
162.5°	1376.9	1375.6	1374.3	1372.9	1374.3	1375.6	1376.9	1378.2	1377.9	1376.1	1374.2
165°	1402.8	1401.5	1400.1	1398.7	1400.1	1401.5	1402.8	1404.2	1403.9	1402.0	1400.1
167.5°	1424.2	1422.7	1421.3	1419.8	1421.3	1422.7	1424.2	1425.6	1425.3	1423.4	1421.5
170°	1435.6	1433.9	1432.3	1430.7	1432.3	1433.9	1435.6	1437.2	1437.1	1435.2	1433.3
172.5°	1444.5	1442.8	1441.2	1439.6	1441.2	1442.8	1444.5	1446.1	1445.9	1444.1	1442.1
175°	1454.0	1452.4	1450.7	1449.1	1450.7	1452.4	1454.0	1455.7	1455.6	1453.6	1451.7
177.5°	1457.5	1456.2	1454.8	1453.5	1454.8	1456.2	1457.5	1458.8	1458.8	1457.5	1456.2
180°	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5



TEST NUMBER: P331842-930

CATALOG NUMBER: S122RDIW-S865D1440U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9
2.5°	1497.1	1503.2	1512.3	1517.5	1526.2	1531.8	1534.8	1540.4	1543.4	1554.3	1565.5
5°	1413.5	1422.2	1437.3	1451.4	1466.6	1482.2	1493.5	1506.6	1518.5	1539.0	1560.6
7.5°	1317.7	1329.7	1353.2	1375.6	1401.9	1424.2	1443.7	1465.9	1485.7	1515.2	1545.8
10°	1245.9	1266.9	1297.8	1318.8	1353.5	1375.7	1406.5	1430.9	1458.4	1497.4	1532.0
12.5°	1184.0	1209.3	1234.1	1263.5	1294.6	1331.5	1365.4	1396.6	1429.5	1469.7	1510.3
15°	1071.6	1108.4	1146.8	1176.6	1218.8	1257.8	1297.2	1339.4	1379.4	1427.6	1480.6
17.5°	927.1	969.7	1034.3	1085.2	1134.8	1173.9	1222.8	1273.8	1321.0	1379.1	1438.1
20°	861.8	893.2	936.9	1005.7	1080.3	1121.9	1171.7	1228.0	1282.1	1345.3	1408.7
22.5°	809.3	837.3	872.5	926.0	1009.3	1066.1	1118.0	1175.2	1238.0	1302.5	1372.7
25°	734.6	754.1	790.8	834.1	891.5	985.0	1041.9	1099.2	1167.4	1236.6	1316.7
27.5°	678.5	696.0	719.9	761.2	803.9	871.1	961.4	1023.9	1091.8	1169.8	1252.9
30°	635.6	656.2	682.7	711.9	758.4	810.9	901.2	973.7	1040.8	1120.9	1209.6
32.5°	604.5	620.7	643.3	672.9	711.7	762.0	834.1	922.2	987.6	1072.0	1164.6
35°	553.4	572.3	590.8	618.9	650.2	696.2	750.8	845.0	909.9	993.2	1086.2
37.5°	511.3	522.9	543.2	565.5	598.6	632.9	680.3	764.7	834.9	916.7	1011.9
40°	479.3	493.9	509.1	533.9	561.0	593.9	640.5	703.3	783.8	863.9	956.9
42.5°	448.2	466.6	482.7	499.3	529.0	562.0	599.8	653.1	735.4	811.1	901.6
45°	410.6	422.5	439.3	457.6	482.0	510.1	543.6	590.2	669.2	734.6	819.5
47.5°	366.9	384.3	395.3	413.2	436.3	463.2	494.3	534.6	598.5	659.8	738.7
50°	337.0	354.9	370.6	386.8	407.3	433.3	459.3	498.2	549.6	614.0	687.5
52.5°	311.4	327.2	342.4	358.7	378.8	402.6	427.2	461.5	505.5	564.7	636.1
55°	276.5	286.2	301.8	318.0	335.9	358.7	382.5	411.2	449.0	498.8	556.7
57.5°	240.5	251.8	264.2	280.5	298.6	316.0	337.5	363.4	393.3	438.3	487.9
60°	220.1	228.9	239.1	255.8	272.6	288.3	308.9	330.5	358.7	397.6	439.8
62.5°	197.6	205.9	215.3	229.9	246.2	260.7	278.6	301.5	325.3	360.9	397.8
65°	160.1	172.0	181.2	194.2	207.7	222.9	236.9	255.4	276.5	304.6	337.5
67.5°	132.7	138.8	147.3	159.1	173.0	186.0	199.3	213.7	232.0	253.7	279.9
70°	120.7	122.8	124.4	135.7	148.8	161.8	174.1	187.7	203.4	221.3	243.9
72.5°	106.3	108.5	110.6	115.4	125.8	138.8	151.6	161.8	176.6	191.4	209.8
75°	84.4	87.6	89.3	92.0	95.7	104.4	116.3	126.0	134.7	146.0	160.7
77.5°	64.2	66.1	67.8	70.7	73.1	77.0	83.7	92.5	100.6	107.2	117.2
80°	50.9	51.4	53.6	54.6	57.9	60.6	63.8	70.8	79.0	81.7	88.7
82.5°	38.3	38.8	40.6	41.7	43.1	45.4	49.6	51.4	57.8	61.3	65.8
85°	21.1	20.5	22.2	22.2	23.2	24.4	25.4	28.1	29.8	34.1	35.1
87.5°	15.0	15.1	14.3	13.1	11.9	11.6	11.1	10.8	11.1	11.7	12.8
90°	42.5	43.0	37.0	31.0	25.0	19.0	14.3	11.1	7.7	4.5	1.2
92.5°	39.2	39.1	37.7	36.3	34.8	33.4	31.5	29.1	26.7	24.3	21.9
95°	78.7	78.7	78.1	77.5	77.0	76.5	74.8	72.1	69.4	66.6	63.9
97.5°	132.2	132.2	131.2	130.2	129.1	128.1	126.4	124.0	121.6	119.2	116.8
100°	169.6	169.6	168.8	168.0	167.1	166.3	164.9	162.7	160.5	158.2	156.1
102.5°	210.2	209.9	208.9	207.8	206.8	205.8	204.4	202.6	200.9	199.2	197.4
105°	270.9	270.4	269.9	269.3	268.8	268.2	267.5	266.7	265.9	265.1	264.2
107.5°	337.2	337.0	337.0	337.0	337.0	337.0	336.4	335.3	334.0	332.8	331.6
110°	382.3	382.3	382.3	382.3	382.3	382.3	381.4	379.8	378.1	376.5	374.9



TEST NUMBER: P331842-930

CATALOG NUMBER: S122RDIW-S865D1440U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	427.8	428.4	428.7	428.9	429.1	429.3	428.6	427.0	425.3	423.7	422.1
115°	496.3	496.6	497.1	497.7	498.2	498.7	498.2	496.6	494.9	493.3	491.6
117.5°	563.3	563.9	565.4	567.0	568.5	570.1	569.7	567.5	565.3	563.1	561.0
120°	607.2	607.2	609.4	611.6	613.8	616.0	616.0	613.8	611.6	609.4	607.2
122.5°	653.7	654.4	655.9	657.5	659.0	660.5	660.0	657.3	654.7	652.1	649.5
125°	721.9	722.7	723.6	724.4	725.2	726.0	725.2	722.7	720.2	717.8	715.3
127.5°	788.1	789.1	790.1	791.1	792.1	793.0	792.0	788.9	785.7	782.6	779.5
130°	832.8	833.3	833.9	834.5	834.9	835.5	834.1	830.5	827.0	823.4	819.8
132.5°	877.3	878.6	878.5	878.3	878.2	878.2	876.6	873.8	870.8	868.0	865.0
135°	941.3	941.5	940.9	940.4	939.9	939.3	937.5	934.5	931.6	928.5	925.5
137.5°	1003.2	1003.5	1002.7	1002.0	1001.4	1000.6	999.0	996.5	994.1	991.6	989.2
140°	1044.7	1044.7	1043.4	1042.0	1040.6	1039.3	1037.4	1034.9	1032.5	1030.0	1027.5
142.5°	1082.3	1082.1	1081.2	1080.3	1079.3	1078.4	1076.7	1074.2	1071.8	1069.3	1066.9
145°	1139.6	1139.4	1137.8	1136.1	1134.5	1132.9	1131.1	1129.1	1127.2	1125.4	1123.4
147.5°	1189.7	1189.0	1188.0	1186.8	1185.8	1184.7	1183.0	1180.7	1178.4	1176.1	1173.8
150°	1221.3	1220.5	1219.4	1218.3	1217.2	1216.1	1214.8	1213.2	1211.5	1209.8	1208.2
152.5°	1253.0	1252.0	1250.7	1249.4	1248.1	1246.8	1245.3	1243.6	1241.9	1240.3	1238.7
155°	1293.1	1291.8	1290.9	1290.1	1289.3	1288.5	1287.7	1286.9	1286.1	1285.2	1284.4
157.5°	1330.0	1328.2	1327.7	1327.2	1326.7	1326.2	1325.7	1325.2	1324.6	1324.0	1323.5
160°	1352.4	1350.8	1350.5	1350.2	1350.0	1349.7	1349.3	1348.7	1348.2	1347.7	1347.1
162.5°	1372.3	1370.4	1370.2	1369.9	1369.6	1369.4	1369.2	1369.1	1369.0	1368.9	1368.7
165°	1398.2	1396.3	1396.3	1396.3	1396.3	1396.3	1396.4	1396.7	1396.9	1397.3	1397.5
167.5°	1419.6	1417.6	1417.7	1417.8	1417.8	1417.9	1418.3	1419.1	1419.9	1420.7	1421.6
170°	1431.3	1429.5	1429.7	1430.0	1430.3	1430.5	1431.1	1431.9	1432.7	1433.5	1434.4
172.5°	1440.2	1438.3	1438.6	1438.8	1439.2	1439.4	1440.0	1440.8	1441.6	1442.4	1443.2
175°	1449.8	1447.9	1448.5	1448.9	1449.5	1450.1	1450.7	1451.6	1452.4	1453.2	1454.0
177.5°	1454.8	1453.5	1454.0	1454.4	1454.8	1455.3	1455.9	1456.5	1457.2	1457.8	1458.5
180°	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5



TEST NUMBER: P331842-930

CATALOG NUMBER: S122RDIW-S865D1440U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9
2.5°	1565.9	1567.2	1575.9	1579.8	1587.6	1590.6	1594.1	1593.3	1593.3	1595.0	1607.1
5°	1569.3	1580.1	1596.4	1612.1	1627.2	1640.2	1648.9	1657.5	1660.8	1676.4	1690.5
7.5°	1563.7	1583.6	1610.5	1634.3	1663.0	1685.4	1704.1	1720.8	1732.3	1755.1	1778.5
10°	1556.3	1584.5	1614.8	1645.6	1685.1	1714.8	1745.1	1768.4	1776.0	1810.0	1829.5
12.5°	1541.6	1579.2	1617.8	1657.7	1696.3	1737.3	1770.7	1793.9	1820.6	1851.1	1887.1
15°	1519.6	1562.8	1613.2	1664.5	1719.7	1769.4	1805.2	1845.8	1874.9	1908.5	1939.8
17.5°	1487.8	1543.6	1607.5	1667.0	1730.9	1784.3	1833.4	1872.3	1892.9	1912.0	1916.7
20°	1462.7	1522.8	1598.0	1668.3	1732.2	1793.8	1842.5	1874.9	1880.4	1880.9	1852.3
22.5°	1435.5	1503.3	1582.0	1654.0	1730.4	1799.0	1836.9	1850.7	1829.3	1792.6	1737.2
25°	1385.4	1463.9	1555.3	1637.4	1720.8	1785.7	1798.7	1774.3	1699.2	1620.2	1520.1
27.5°	1331.1	1419.3	1517.3	1608.7	1697.5	1737.6	1709.7	1621.9	1486.5	1368.7	1226.0
30°	1291.3	1390.2	1486.5	1588.8	1671.0	1688.3	1624.0	1494.7	1336.7	1159.3	1017.0
32.5°	1245.9	1349.6	1455.4	1561.1	1629.9	1613.0	1506.7	1347.5	1162.3	987.9	853.5
35°	1180.9	1288.0	1402.2	1508.2	1552.0	1479.0	1320.0	1112.7	923.4	760.6	668.1
37.5°	1106.0	1222.5	1341.2	1438.6	1435.5	1313.8	1097.1	883.3	724.1	627.9	562.0
40°	1052.7	1170.6	1298.9	1381.0	1345.9	1187.4	952.6	750.8	634.5	557.7	509.6
42.5°	1001.7	1120.0	1247.3	1312.7	1251.6	1056.7	822.8	664.7	568.8	508.8	469.8
45°	914.8	1039.8	1157.6	1193.9	1084.6	869.8	665.4	550.7	486.9	442.5	415.5
47.5°	829.8	952.8	1060.4	1061.0	913.2	705.4	561.3	476.6	422.1	387.8	368.1
50°	777.9	894.7	985.0	971.0	803.3	627.5	502.0	429.0	383.5	357.0	336.5
52.5°	719.5	832.8	911.1	871.1	710.3	552.2	448.7	387.4	349.8	326.8	308.3
55°	634.5	735.2	790.4	729.8	579.4	459.3	379.2	331.1	303.0	283.5	267.7
57.5°	551.1	634.1	668.9	598.3	477.2	380.8	320.8	284.6	256.7	242.8	234.6
60°	498.8	569.6	593.9	516.1	414.9	333.2	284.0	250.5	229.9	220.7	212.6
62.5°	447.3	505.2	515.2	443.8	361.7	291.7	249.4	221.0	207.4	198.6	190.9
65°	371.1	412.8	407.9	350.6	286.2	231.5	200.7	183.4	173.1	160.7	147.2
67.5°	305.5	330.9	315.6	272.6	218.4	179.9	159.8	146.7	134.0	122.1	119.0
70°	264.0	278.6	262.4	222.9	179.0	150.9	134.7	119.0	111.5	108.8	103.9
72.5°	224.2	229.3	211.7	177.9	145.7	125.0	109.2	100.4	96.3	94.0	90.9
75°	168.3	164.4	149.3	122.8	101.2	87.1	82.3	79.0	76.3	74.1	72.5
77.5°	118.1	112.6	99.1	81.8	70.4	63.8	60.8	59.1	57.8	56.7	55.0
80°	88.7	85.0	71.4	58.5	53.6	50.3	48.7	46.6	46.6	45.4	43.8
82.5°	64.9	60.7	48.9	42.8	40.1	38.2	37.0	35.7	35.3	35.5	34.3
85°	34.1	27.6	24.4	23.2	21.6	20.5	21.1	20.0	20.0	20.0	19.5
87.5°	11.3	9.8	10.0	10.2	11.6	12.8	13.5	14.8	16.4	15.8	16.1
90°	4.5	7.7	11.1	14.3	19.0	25.0	31.0	37.0	43.0	42.5	41.9
92.5°	24.3	26.7	29.1	31.5	33.4	34.8	36.3	37.7	39.1	39.2	39.3
95°	66.6	69.4	72.1	74.8	76.5	77.0	77.5	78.1	78.7	78.7	78.7
97.5°	119.2	121.6	124.0	126.4	128.1	129.1	130.2	131.2	132.2	132.2	132.2
100°	158.2	160.5	162.7	164.9	166.3	167.1	168.0	168.8	169.6	169.6	169.6
102.5°	199.2	200.9	202.6	204.4	205.8	206.8	207.8	208.9	209.9	210.2	210.3
105°	265.1	265.9	266.7	267.5	268.2	268.8	269.3	269.9	270.4	270.9	271.5
107.5°	332.8	334.0	335.3	336.4	337.0	337.0	337.0	337.0	337.0	337.2	337.5
110°	376.5	378.1	379.8	381.4	382.3	382.3	382.3	382.3	382.3	382.3	382.3



TEST NUMBER: P331842-930

CATALOG NUMBER: S122RDIW-S865D1440U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	423.7	425.3	427.0	428.6	429.3	429.1	428.9	428.7	428.4	427.8	427.1
115°	493.3	494.9	496.6	498.2	498.7	498.2	497.7	497.1	496.6	496.3	496.0
117.5°	563.1	565.3	567.5	569.7	570.1	568.5	567.0	565.4	563.9	563.3	562.6
120°	609.4	611.6	613.8	616.0	616.0	613.8	611.6	609.4	607.2	607.2	607.2
122.5°	652.1	654.7	657.3	660.0	660.5	659.0	657.5	655.9	654.4	653.7	653.1
125°	717.8	720.2	722.7	725.2	726.0	725.2	724.4	723.6	722.7	721.9	721.1
127.5°	782.6	785.7	788.9	792.0	793.0	792.1	791.1	790.1	789.1	788.1	787.1
130°	823.4	827.0	830.5	834.1	835.5	834.9	834.5	833.9	833.3	832.8	832.3
132.5°	868.0	870.8	873.8	876.6	878.2	878.2	878.3	878.5	878.6	877.3	876.2
135°	928.5	931.6	934.5	937.5	939.3	939.9	940.4	940.9	941.5	941.3	940.9
137.5°	991.6	994.1	996.5	999.0	1000.6	1001.4	1002.0	1002.7	1003.5	1003.2	1003.0
140°	1030.0	1032.5	1034.9	1037.4	1039.3	1040.6	1042.0	1043.4	1044.7	1044.7	1044.7
142.5°	1069.3	1071.8	1074.2	1076.7	1078.4	1079.3	1080.3	1081.2	1082.1	1082.3	1082.6
145°	1125.4	1127.2	1129.1	1131.1	1132.9	1134.5	1136.1	1137.8	1139.4	1139.6	1140.0
147.5°	1176.1	1178.4	1180.7	1183.0	1184.7	1185.8	1186.8	1188.0	1189.0	1189.7	1190.3
150°	1209.8	1211.5	1213.2	1214.8	1216.1	1217.2	1218.3	1219.4	1220.5	1221.3	1222.1
152.5°	1240.3	1241.9	1243.6	1245.3	1246.8	1248.1	1249.4	1250.7	1252.0	1253.0	1254.0
155°	1285.2	1286.1	1286.9	1287.7	1288.5	1289.3	1290.1	1290.9	1291.8	1293.1	1294.5
157.5°	1324.0	1324.6	1325.2	1325.7	1326.2	1326.7	1327.2	1327.7	1328.2	1330.0	1331.9
160°	1347.7	1348.2	1348.7	1349.3	1349.7	1350.0	1350.2	1350.5	1350.8	1352.4	1354.0
162.5°	1368.9	1369.0	1369.1	1369.2	1369.4	1369.6	1369.9	1370.2	1370.4	1372.3	1374.2
165°	1397.3	1396.9	1396.7	1396.4	1396.3	1396.3	1396.3	1396.3	1396.3	1398.2	1400.1
167.5°	1420.7	1419.9	1419.1	1418.3	1417.9	1417.8	1417.8	1417.7	1417.6	1419.6	1421.5
170°	1433.5	1432.7	1431.9	1431.1	1430.5	1430.3	1430.0	1429.7	1429.5	1431.3	1433.3
172.5°	1442.4	1441.6	1440.8	1440.0	1439.4	1439.2	1438.8	1438.6	1438.3	1440.2	1442.1
175°	1453.2	1452.4	1451.6	1450.7	1450.1	1449.5	1448.9	1448.5	1447.9	1449.8	1451.7
177.5°	1457.8	1457.2	1456.5	1455.9	1455.3	1454.8	1454.4	1454.0	1453.5	1454.8	1456.2
180°	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5



TEST NUMBER: P331842-930

CATALOG NUMBER: S122RDIW-S865D1440U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9	1556.9
2.5°	1611.4	1617.1	1619.6	1619.6	1622.7	1621.4	1620.1
5°	1704.1	1714.3	1716.4	1726.2	1733.2	1731.0	1732.2
7.5°	1796.1	1812.7	1829.0	1836.5	1837.6	1841.9	1843.6
10°	1852.8	1866.3	1891.7	1887.9	1906.9	1917.7	1899.8
12.5°	1907.3	1925.6	1943.3	1948.1	1958.8	1962.3	1955.3
15°	1956.6	1966.4	1967.5	1964.8	1968.0	1965.3	1955.0
17.5°	1910.6	1894.8	1862.7	1847.5	1835.6	1817.9	1810.7
20°	1834.4	1787.9	1733.7	1712.1	1686.7	1637.0	1648.9
22.5°	1670.0	1616.9	1562.8	1499.7	1469.5	1422.3	1419.4
25°	1414.1	1322.7	1222.1	1151.7	1110.6	1063.6	1042.9
27.5°	1099.4	984.3	901.9	860.1	822.1	784.8	783.3
30°	892.6	806.0	742.2	706.5	683.2	667.6	670.8
32.5°	752.4	693.1	650.0	620.4	603.2	591.3	591.2
35°	615.1	574.5	546.9	534.4	522.0	513.4	513.9
37.5°	526.4	502.0	486.7	472.9	465.1	460.9	458.5
40°	480.9	460.9	449.0	440.9	434.4	428.4	427.4
42.5°	445.0	428.4	416.5	410.2	404.1	399.9	398.8
45°	394.9	381.4	370.6	363.5	360.9	357.0	357.0
47.5°	351.3	338.0	329.5	325.1	320.5	318.0	317.9
50°	321.9	311.6	304.0	301.3	297.5	295.9	295.4
52.5°	295.5	287.8	282.4	280.5	278.9	276.9	277.2
55°	259.7	255.4	253.2	251.5	248.8	245.6	247.8
57.5°	229.5	225.8	220.0	214.8	212.4	210.1	211.0
60°	208.3	200.7	193.1	187.2	185.6	180.7	180.7
62.5°	181.4	170.8	161.5	158.2	156.5	154.3	153.8
65°	139.6	135.3	133.1	130.9	129.8	129.8	128.7
67.5°	115.7	113.9	111.5	111.0	109.9	109.6	109.3
70°	102.2	100.0	99.0	98.5	97.3	97.9	96.3
72.5°	89.3	87.6	87.3	85.9	85.3	85.4	84.1
75°	70.4	70.4	69.8	69.2	68.2	67.6	68.2
77.5°	54.1	54.2	53.2	53.2	53.0	53.2	52.6
80°	43.3	43.8	43.3	42.7	42.2	42.7	42.2
82.5°	34.2	33.4	33.3	33.2	33.1	32.8	32.7
85°	19.5	20.0	19.5	18.9	18.9	18.9	19.5
87.5°	15.7	15.5	15.5	15.6	15.6	15.7	15.2
90°	41.4	40.8	40.7	41.0	41.3	41.5	41.8
92.5°	39.4	39.5	39.6	39.6	39.7	39.8	39.8
95°	78.7	78.7	78.4	77.9	77.3	76.7	76.2
97.5°	132.2	132.2	132.2	132.2	132.1	132.1	132.0
100°	169.6	169.6	169.5	169.2	168.9	168.7	168.4
102.5°	210.6	210.8	210.8	210.5	210.3	209.9	209.7
105°	272.1	272.6	272.9	272.9	272.9	272.9	272.9
107.5°	337.7	337.9	337.4	336.1	334.8	333.6	332.3
110°	382.3	382.3	381.8	381.0	380.2	379.4	378.5



TEST NUMBER: P331842-930

CATALOG NUMBER: S122RDIW-S865D1440U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	426.5	425.8	425.2	424.6	424.0	423.4	422.8
115°	495.7	495.5	494.9	494.1	493.3	492.4	491.6
117.5°	562.0	561.3	560.5	559.7	558.9	558.1	557.3
120°	607.2	607.2	606.7	605.9	605.1	604.3	603.5
122.5°	652.4	651.8	651.1	650.5	650.0	649.3	648.7
125°	720.2	719.4	718.9	718.6	718.4	718.1	717.8
127.5°	786.1	785.1	784.2	783.3	782.4	781.6	780.7
130°	831.7	831.1	830.3	829.2	828.2	827.0	826.0
132.5°	875.0	873.8	872.7	871.9	871.0	870.1	869.2
135°	940.7	940.4	939.9	939.1	938.2	937.4	936.6
137.5°	1002.8	1002.6	1001.9	1000.9	999.7	998.7	997.5
140°	1044.7	1044.7	1044.2	1043.1	1042.0	1040.9	1039.8
142.5°	1082.8	1083.0	1082.6	1081.5	1080.4	1079.3	1078.2
145°	1140.2	1140.4	1140.0	1139.0	1137.9	1136.8	1135.7
147.5°	1190.8	1191.5	1191.2	1190.2	1189.1	1188.1	1187.1
150°	1222.9	1223.8	1223.8	1222.9	1222.1	1221.3	1220.5
152.5°	1255.1	1256.1	1256.1	1255.1	1254.0	1253.0	1252.0
155°	1295.9	1297.2	1297.5	1296.7	1295.9	1295.1	1294.3
157.5°	1333.7	1335.6	1335.9	1334.6	1333.3	1332.0	1330.6
160°	1355.7	1357.3	1357.6	1356.5	1355.4	1354.4	1353.2
162.5°	1376.1	1377.9	1378.2	1376.9	1375.6	1374.3	1372.9
165°	1402.0	1403.9	1404.2	1402.8	1401.5	1400.1	1398.7
167.5°	1423.4	1425.3	1425.6	1424.2	1422.7	1421.3	1419.8
170°	1435.2	1437.1	1437.2	1435.6	1433.9	1432.3	1430.7
172.5°	1444.1	1445.9	1446.1	1444.5	1442.8	1441.2	1439.6
175°	1453.6	1455.6	1455.7	1454.0	1452.4	1450.7	1449.1
177.5°	1457.5	1458.8	1458.8	1457.5	1456.2	1454.8	1453.5
180°	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5

(END OF REPORT)