

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331490

Luminaire Tested: **S122DIW-S290D1440U835-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331490  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIW-S290D1440U835-4F0-1E-UDD-A1  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1440 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6306.4 lumens  
Efficiency: N/A  
Efficacy: 118.1 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 53.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331490

CATALOG NUMBER: S122DIW-S290D1440U835-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot



— 0°-180°    - - 45°-225°    - - - 90°-270°    - - - 135°-315°



TEST NUMBER: P331490

CATALOG NUMBER: S122DIW-S290D1440U835-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	100	100	100	100	89	89	89	89	67	67	67	47	47	47	29	29	29	21
1	91	87	84	80	81	77	74	72	59	57	55	42	41	40	26	26	25	18
2	83	76	71	66	74	68	63	59	52	49	46	37	35	33	23	22	21	15
3	76	67	60	55	67	60	54	49	46	42	39	33	30	28	21	19	18	13
4	70	60	52	46	61	53	47	42	41	36	33	29	27	24	19	17	16	11
5	64	53	45	40	56	47	41	36	36	32	28	26	23	21	17	15	14	10
6	59	47	40	34	52	42	36	31	33	28	25	24	21	18	15	14	12	9
7	54	43	35	30	48	38	32	27	30	25	22	22	19	16	14	12	11	8
8	50	39	31	26	44	35	28	24	27	22	19	20	17	14	13	11	10	7
9	47	35	28	23	41	31	25	21	25	20	17	18	15	13	12	10	9	7
10	43	32	25	21	38	29	23	19	22	18	15	17	14	12	11	9	8	6

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	9544	9544	9544	9544
5°	10699	9606	8512	9606
10°	12260	9527	7366	9527
15°	13563	9352	6509	9352
20°	13357	9165	5933	9165
25°	12043	8915	5569	8915
30°	9952	8516	5302	8516
35°	7253	8099	5113	8099
40°	5794	7609	5008	7609
45°	5062	7040	4866	7040
50°	4760	6488	4770	6488
55°	4386	5928	4642	5928
60°	4020	5331	4447	5331
65°	3664	4798	4252	4798
70°	3323	4277	3970	4277
75°	2951	3699	3512	3699
80°	2538	3059	2827	3059
85°	2279	2279	1686	2279



TEST NUMBER: P331490

CATALOG NUMBER: S122DIW-S290D1440U835-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	56.3	0.9
10°-20°	163.7	2.6
20°-30°	237.5	3.8
30°-40°	250.6	4.0
40°-50°	221.9	3.5
50°-60°	177.1	2.8
60°-70°	120.4	1.9
70°-80°	61.7	1.0
80°-90°	22.0	0.3
90°-100°	113.2	1.8
100°-110°	351.6	5.6
110°-120°	601.0	9.5
120°-130°	790.3	12.5
130°-140°	887.0	14.1
140°-150°	869.7	13.8
150°-160°	729.5	11.6
160°-170°	483.8	7.7
170°-180°	169.1	2.7
0°-30°	457.5	7.3
0°-40°	708.1	11.2
0°-60°	1107.1	17.6
0°-90°	1311.2	20.8
90°-120°	1065.7	16.9
90°-150°	3612.8	57.3
90°-180°	4995.0	79.2
0°-180°	6306.4	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	591	591	591	591	591	
5°	660	593	525	593	660	66
15°	811	560	389	560	811	224
25°	676	500	313	500	676	306
35°	368	411	259	411	368	239
45°	222	308	213	308	222	174
55°	156	211	165	211	156	140
65°	96	126	111	126	96	95
75°	47	59	56	59	47	51
85°	12	12	9	12	12	15
90°	51	2	51	2	51	23
95°	94	78	94	78	94	104
105°	335	324	335	324	335	352
115°	603	603	603	603	603	596
125°	880	877	880	877	880	785
135°	1149	1135	1149	1135	1149	884
145°	1393	1378	1393	1378	1393	870
155°	1588	1575	1588	1575	1588	731
165°	1716	1714	1716	1714	1716	484
175°	1777	1783	1777	1783	1777	169
180°	1786	1786	1786	1786	1786	



TEST NUMBER: P331490

CATALOG NUMBER: S122DIW-S290D1440U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1
2.5°	618.3	618.5	618.9	616.0	615.6	615.6	613.1	610.9	608.3	604.9	605.3
5°	660.1	662.6	663.5	660.8	656.7	656.3	652.4	646.1	640.1	635.4	632.0
7.5°	710.0	711.0	708.8	705.2	702.2	696.7	689.5	682.5	672.6	663.6	656.9
10°	747.8	749.2	745.3	740.1	735.8	729.4	719.0	708.3	695.4	682.9	672.9
12.5°	776.5	779.9	774.9	774.3	766.9	758.1	745.7	740.3	722.1	704.7	693.9
15°	811.4	811.2	811.7	807.3	801.9	800.5	787.4	773.0	747.4	737.1	719.4
17.5°	801.3	804.8	806.4	806.3	806.2	805.3	801.1	792.1	779.2	762.6	742.2
20°	777.4	781.9	782.6	787.8	790.8	794.6	796.2	793.7	785.8	771.9	754.2
22.5°	740.3	741.6	743.7	751.8	758.2	767.9	772.9	781.4	778.3	771.5	756.7
25°	676.0	673.8	681.7	685.8	700.6	716.0	727.2	739.4	750.3	756.9	752.6
27.5°	598.9	595.5	607.4	618.3	630.2	647.0	664.3	684.8	701.8	723.2	730.5
30°	533.8	535.9	547.2	558.8	577.0	600.6	620.2	642.6	667.0	690.8	707.4
32.5°	463.7	471.5	478.7	496.5	512.5	538.8	567.5	595.6	625.9	653.0	678.7
35°	368.0	377.1	387.1	400.0	422.5	448.6	476.6	514.5	555.9	592.9	623.3
37.5°	309.8	308.3	314.0	323.4	341.6	362.7	394.9	432.3	481.0	524.5	567.5
40°	274.9	274.0	278.0	286.7	300.5	316.0	344.2	377.1	422.3	475.5	526.6
42.5°	250.9	251.4	253.7	259.8	269.3	282.0	303.1	331.1	372.5	422.6	477.5
45°	221.7	223.3	225.8	228.8	234.2	244.7	256.5	276.5	309.2	351.0	405.0
47.5°	200.7	200.8	203.3	205.9	209.1	215.0	224.7	237.2	260.3	294.3	340.8
50°	189.5	187.9	189.7	191.7	195.1	199.2	205.6	217.4	232.8	260.3	299.2
52.5°	175.6	175.7	177.3	178.1	181.1	185.2	191.0	199.2	213.2	234.7	266.6
55°	155.8	157.0	157.9	159.2	162.0	164.9	169.5	174.9	185.8	201.9	225.6
57.5°	137.2	137.6	138.5	141.1	142.8	145.5	149.8	154.8	161.9	173.8	191.6
60°	124.5	124.5	126.3	127.4	129.7	132.4	135.8	140.6	147.0	156.7	171.1
62.5°	112.9	112.7	113.4	115.3	117.0	119.5	122.9	127.0	133.0	141.7	153.4
65°	95.9	95.4	96.8	97.2	99.0	101.5	104.3	108.6	113.4	119.7	130.2
67.5°	79.5	80.1	80.8	81.6	82.6	85.3	87.1	90.1	94.2	99.5	106.5
70°	70.4	70.4	70.4	71.1	72.5	73.8	75.6	78.1	82.0	86.5	92.9
72.5°	60.2	61.0	61.7	61.3	63.0	63.8	66.0	67.4	71.1	74.0	79.6
75°	47.3	47.3	47.3	48.4	49.1	49.7	51.1	52.5	54.3	57.9	60.9
77.5°	35.3	35.2	35.4	35.7	36.4	37.2	37.6	38.8	40.5	42.2	44.7
80°	27.3	27.7	27.9	28.4	28.4	28.8	29.1	30.7	31.8	32.9	34.5
82.5°	21.1	21.2	21.2	21.3	21.5	21.8	22.4	22.9	23.3	24.2	25.4
85°	12.3	12.0	12.0	12.5	12.3	12.3	12.7	13.2	13.2	13.4	14.1
87.5°	15.0	14.9	15.0	14.8	14.7	14.9	15.1	15.0	15.3	15.6	14.3
90°	51.3	50.9	50.6	50.3	49.9	50.1	50.8	51.4	52.1	52.8	45.4
92.5°	48.8	48.8	48.7	48.6	48.6	48.5	48.3	48.2	48.1	47.9	46.2
95°	93.5	94.1	94.8	95.5	96.1	96.5	96.5	96.5	96.5	96.5	95.8
97.5°	161.9	162.0	162.0	162.1	162.2	162.2	162.2	162.2	162.2	162.2	160.9
100°	206.5	206.9	207.2	207.5	207.9	208.0	208.0	208.0	208.0	208.0	207.0
102.5°	257.2	257.5	257.9	258.2	258.5	258.6	258.3	258.0	257.8	257.5	256.2
105°	334.7	334.7	334.7	334.7	334.7	334.3	333.7	333.0	332.3	331.7	331.0
107.5°	407.6	409.2	410.7	412.3	413.8	414.4	414.2	413.9	413.6	413.4	413.4
110°	464.3	465.3	466.3	467.3	468.3	468.9	468.9	468.9	468.9	468.9	468.9



TEST NUMBER: P331490

CATALOG NUMBER: S122DIW-S290D1440U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	518.6	519.3	520.1	520.8	521.5	522.3	523.1	523.9	524.7	525.5	525.8
115°	603.0	604.0	605.0	606.0	607.0	607.7	608.0	608.4	608.7	609.1	609.7
117.5°	683.5	684.5	685.5	686.5	687.5	688.5	689.3	690.1	690.9	691.7	693.5
120°	740.2	741.2	742.2	743.2	744.2	744.7	744.7	744.7	744.7	744.7	747.4
122.5°	795.7	796.4	797.2	797.9	798.6	799.4	800.2	801.0	801.8	802.6	804.5
125°	880.4	880.8	881.1	881.4	881.8	882.4	883.4	884.4	885.4	886.4	887.5
127.5°	957.6	958.7	959.7	960.8	961.9	963.0	964.2	965.4	966.6	967.9	969.1
130°	1013.1	1014.4	1015.8	1017.1	1018.4	1019.4	1020.1	1020.8	1021.5	1022.1	1022.8
132.5°	1066.1	1067.2	1068.3	1069.4	1070.4	1071.7	1073.2	1074.7	1076.1	1077.6	1077.5
135°	1148.8	1149.8	1150.8	1151.8	1152.8	1153.5	1153.8	1154.1	1154.5	1154.8	1154.1
137.5°	1223.5	1224.9	1226.2	1227.6	1228.9	1229.7	1230.0	1230.2	1230.5	1230.8	1229.9
140°	1275.4	1276.7	1278.1	1279.4	1280.8	1281.4	1281.4	1281.4	1281.4	1281.4	1279.8
142.5°	1322.4	1323.8	1325.1	1326.5	1327.8	1328.3	1328.1	1327.8	1327.5	1327.3	1326.1
145°	1393.0	1394.3	1395.7	1397.0	1398.3	1398.8	1398.5	1398.2	1397.8	1397.5	1395.5
147.5°	1456.0	1457.3	1458.5	1459.8	1461.1	1461.4	1460.6	1459.9	1459.2	1458.4	1457.1
150°	1497.0	1498.0	1499.0	1500.0	1501.0	1501.0	1500.0	1499.0	1498.0	1497.0	1495.7
152.5°	1535.6	1536.9	1538.1	1539.4	1540.7	1540.7	1539.4	1538.1	1536.9	1535.6	1534.0
155°	1587.5	1588.5	1589.5	1590.5	1591.5	1591.1	1589.5	1587.8	1586.1	1584.4	1583.4
157.5°	1632.1	1633.7	1635.3	1636.9	1638.5	1638.2	1635.9	1633.6	1631.3	1629.1	1628.5
160°	1659.8	1661.2	1662.5	1663.8	1665.2	1664.8	1662.8	1660.8	1658.8	1656.8	1656.5
162.5°	1683.9	1685.6	1687.2	1688.8	1690.4	1690.0	1687.8	1685.5	1683.2	1680.9	1680.6
165°	1715.6	1717.3	1719.0	1720.6	1722.3	1722.0	1719.6	1717.3	1714.9	1712.6	1712.6
167.5°	1741.5	1743.3	1745.0	1746.8	1748.5	1748.2	1745.9	1743.5	1741.2	1738.8	1738.9
170°	1754.8	1756.8	1758.8	1760.8	1762.8	1762.7	1760.3	1758.0	1755.6	1753.3	1753.6
172.5°	1765.7	1767.7	1769.7	1771.7	1773.7	1773.5	1771.2	1768.8	1766.5	1764.1	1764.5
175°	1777.4	1779.4	1781.4	1783.4	1785.5	1785.3	1782.9	1780.6	1778.3	1775.9	1776.6
177.5°	1782.8	1784.4	1786.1	1787.7	1789.3	1789.3	1787.7	1786.1	1784.4	1782.8	1783.4
180°	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5



TEST NUMBER: P331490

CATALOG NUMBER: S122DIW-S290D1440U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1
2.5°	606.5	605.1	604.2	600.9	598.0	595.1	594.2	594.5	590.5	586.7	585.1
5°	630.2	625.6	621.3	615.2	607.9	599.9	595.9	592.7	584.7	576.1	571.1
7.5°	651.3	644.8	636.5	625.0	614.4	601.9	593.9	586.9	575.3	563.1	555.6
10°	664.2	655.4	644.7	630.6	617.7	602.4	591.8	581.1	567.5	552.9	543.8
12.5°	675.3	663.4	652.9	634.8	619.5	600.4	587.8	572.7	558.4	541.1	532.2
15°	701.7	679.7	659.7	639.2	620.4	593.8	579.7	559.5	540.7	519.3	509.1
17.5°	722.1	697.3	665.9	639.9	617.9	588.4	567.8	543.6	521.3	496.9	483.0
20°	733.7	705.3	671.5	640.6	614.3	580.6	558.1	533.4	507.3	479.8	464.8
22.5°	740.6	710.8	677.3	637.9	607.0	574.3	546.0	518.8	492.4	462.7	447.0
25°	742.8	715.6	680.1	635.6	597.9	560.9	526.8	500.4	468.4	440.7	417.8
27.5°	732.0	712.5	678.4	631.3	587.4	544.1	506.1	476.3	442.5	412.4	389.3
30°	718.7	707.4	674.2	627.0	579.0	532.5	490.7	456.8	423.2	392.8	369.1
32.5°	698.2	695.8	666.6	620.8	570.1	517.8	474.5	440.3	403.0	373.1	350.6
35°	657.9	668.8	650.4	607.0	553.4	496.8	450.0	410.9	372.3	343.7	322.6
37.5°	603.8	630.9	626.1	586.8	530.7	474.0	422.3	381.5	344.7	315.8	295.1
40°	566.5	601.1	606.1	571.3	514.8	456.4	401.6	361.0	325.1	298.7	277.8
42.5°	526.6	566.9	580.6	552.8	497.3	437.8	383.1	341.0	305.4	279.8	261.3
45°	459.6	512.9	537.7	521.8	468.2	407.3	351.0	308.3	276.0	251.9	237.6
47.5°	396.9	455.2	488.5	482.9	435.8	375.5	319.8	278.8	247.4	228.2	215.4
50°	352.6	412.5	452.7	454.6	412.5	352.8	296.9	258.3	229.4	211.5	201.0
52.5°	314.0	371.3	415.1	424.8	386.5	329.2	276.4	237.9	212.5	196.0	186.7
55°	263.7	312.1	360.7	378.5	347.8	293.3	244.4	210.6	186.7	175.4	167.2
57.5°	219.3	259.6	304.5	324.1	305.2	258.5	212.7	183.3	164.0	154.0	147.7
60°	195.8	227.6	267.6	291.0	274.6	233.1	193.1	165.1	149.2	140.4	134.5
62.5°	174.0	202.2	236.0	257.4	248.5	209.3	173.5	148.8	135.1	126.8	122.5
65°	143.6	165.8	192.0	211.7	205.8	176.1	146.7	125.6	114.7	108.1	104.7
67.5°	118.2	134.3	152.4	169.7	165.0	143.9	120.4	103.9	95.8	90.1	88.0
70°	102.2	114.5	130.6	144.5	140.6	123.4	104.7	90.6	83.6	78.8	76.8
72.5°	87.0	97.0	109.4	120.7	118.1	103.7	88.2	77.6	72.1	67.7	66.1
75°	65.7	73.4	80.9	88.4	87.7	76.6	67.5	59.3	55.0	51.6	50.9
77.5°	48.5	52.8	57.9	62.3	61.1	54.7	47.6	42.9	39.8	37.5	37.1
80°	37.0	39.5	43.2	46.3	44.8	42.0	36.3	32.9	30.7	28.4	27.5
82.5°	26.9	29.3	31.5	33.3	32.0	29.5	26.0	23.7	22.3	20.8	20.4
85°	14.1	15.4	16.4	16.8	16.4	14.8	13.2	12.3	11.1	10.4	10.2
87.5°	13.1	11.6	10.1	9.3	8.0	7.2	5.6	4.3	4.9	5.5	6.0
90°	38.0	30.7	23.3	17.6	13.6	9.5	5.5	1.5	5.5	9.5	13.6
92.5°	44.5	42.7	41.0	38.6	35.7	32.7	29.8	26.8	29.8	32.7	35.7
95°	95.1	94.5	93.8	91.8	88.4	85.1	81.7	78.4	81.7	85.1	88.4
97.5°	159.7	158.4	157.1	155.0	152.1	149.1	146.2	143.2	146.2	149.1	152.1
100°	206.0	205.0	204.0	202.2	199.5	196.8	194.1	191.5	194.1	196.8	199.5
102.5°	254.9	253.7	252.4	250.7	248.5	246.4	244.3	242.1	244.3	246.4	248.5
105°	330.3	329.7	329.0	328.1	327.1	326.1	325.1	324.1	325.1	326.1	327.1
107.5°	413.4	413.4	413.4	412.6	411.2	409.7	408.2	406.7	408.2	409.7	411.2
110°	468.9	468.9	468.9	467.8	465.8	463.8	461.8	459.8	461.8	463.8	465.8





TEST NUMBER: P331490

CATALOG NUMBER: S122DIW-S290D1440U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	526.1	526.3	526.6	525.7	523.7	521.7	519.7	517.7	519.7	521.7	523.7
115°	610.4	611.1	611.7	611.1	609.1	607.0	605.0	603.0	605.0	607.0	609.1
117.5°	695.4	697.3	699.2	698.8	696.1	693.4	690.7	688.1	690.7	693.4	696.1
120°	750.1	752.8	755.5	755.5	752.8	750.1	747.4	744.7	747.4	750.1	752.8
122.5°	806.4	808.3	810.1	809.5	806.2	803.0	799.8	796.6	799.8	803.0	806.2
125°	888.5	889.5	890.5	889.5	886.4	883.4	880.4	877.4	880.4	883.4	886.4
127.5°	970.3	971.5	972.7	971.4	967.6	963.7	959.9	956.1	959.9	963.7	967.6
130°	1023.5	1024.1	1024.8	1023.0	1018.6	1014.3	1009.9	1005.5	1009.9	1014.3	1018.6
132.5°	1077.3	1077.2	1077.1	1075.2	1071.7	1068.1	1064.6	1061.0	1064.6	1068.1	1071.7
135°	1153.5	1152.8	1152.1	1149.9	1146.2	1142.6	1138.9	1135.2	1138.9	1142.6	1146.2
137.5°	1229.0	1228.2	1227.3	1225.3	1222.3	1219.3	1216.3	1213.3	1216.3	1219.3	1222.3
140°	1278.1	1276.4	1274.7	1272.4	1269.4	1266.4	1263.3	1260.3	1263.3	1266.4	1269.4
142.5°	1325.0	1323.8	1322.7	1320.6	1317.6	1314.6	1311.6	1308.6	1311.6	1314.6	1317.6
145°	1393.5	1391.5	1389.5	1387.3	1384.9	1382.6	1380.3	1377.9	1380.3	1382.6	1384.9
147.5°	1455.7	1454.4	1453.1	1451.0	1448.2	1445.3	1442.5	1439.7	1442.5	1445.3	1448.2
150°	1494.3	1493.0	1491.6	1490.0	1488.0	1486.0	1483.9	1481.9	1483.9	1486.0	1488.0
152.5°	1532.4	1530.8	1529.2	1527.4	1525.3	1523.3	1521.3	1519.3	1521.3	1523.3	1525.3
155°	1582.4	1581.4	1580.4	1579.4	1578.4	1577.4	1576.4	1575.4	1576.4	1577.4	1578.4
157.5°	1627.9	1627.3	1626.7	1626.0	1625.4	1624.7	1624.0	1623.3	1624.0	1624.7	1625.4
160°	1656.1	1655.8	1655.5	1655.0	1654.3	1653.6	1653.0	1652.3	1653.0	1653.6	1654.3
162.5°	1680.3	1679.9	1679.6	1679.4	1679.2	1679.1	1679.0	1678.8	1679.0	1679.1	1679.2
165°	1712.6	1712.6	1712.6	1712.8	1713.1	1713.4	1713.8	1714.1	1713.8	1713.4	1713.1
167.5°	1739.0	1739.0	1739.1	1739.6	1740.6	1741.6	1742.6	1743.6	1742.6	1741.6	1740.6
170°	1754.0	1754.3	1754.6	1755.3	1756.3	1757.3	1758.3	1759.3	1758.3	1757.3	1756.3
172.5°	1764.8	1765.2	1765.5	1766.2	1767.2	1768.2	1769.2	1770.2	1769.2	1768.2	1767.2
175°	1777.2	1777.9	1778.6	1779.4	1780.4	1781.4	1782.4	1783.4	1782.4	1781.4	1780.4
177.5°	1783.9	1784.4	1785.0	1785.7	1786.5	1787.3	1788.1	1788.9	1788.1	1787.3	1786.5
180°	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5



TEST NUMBER: P331490

CATALOG NUMBER: S122DIW-S290D1440U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1
2.5°	583.3	582.2	578.4	576.4	573.1	570.0	568.0	568.9	569.6	569.3	568.7
5°	566.5	562.2	555.6	550.0	545.9	538.4	535.2	533.6	532.2	530.7	529.1
7.5°	546.6	539.8	530.4	522.3	514.7	505.3	500.0	496.9	493.6	490.0	486.8
10°	532.5	522.9	512.9	501.6	492.5	484.1	476.6	471.6	467.0	462.7	459.6
12.5°	517.6	506.6	494.2	478.7	468.7	456.6	455.5	446.7	439.6	436.9	433.2
15°	493.9	478.4	462.7	444.3	436.4	425.5	418.7	411.8	405.7	401.4	400.3
17.5°	466.9	446.9	431.3	418.1	405.1	393.9	387.6	382.2	377.1	371.4	370.6
20°	446.4	429.1	412.1	400.5	387.1	375.7	368.0	362.6	358.2	354.8	351.9
22.5°	426.9	408.0	392.4	379.8	366.6	357.4	351.3	346.0	342.4	338.7	335.9
25°	395.7	381.0	363.9	349.6	338.7	332.8	327.8	323.3	321.0	318.5	315.3
27.5°	368.4	352.0	336.1	325.0	315.4	310.2	306.6	303.5	301.4	299.9	298.1
30°	349.2	332.6	320.1	309.2	301.2	296.0	293.7	291.9	289.4	288.5	287.6
32.5°	330.6	315.7	305.0	295.5	288.0	284.5	282.5	280.8	278.9	278.0	276.1
35°	304.4	291.9	281.5	276.2	270.1	267.1	265.6	263.3	261.5	260.6	260.3
37.5°	279.7	268.9	262.0	255.3	252.7	250.9	248.7	247.2	246.6	246.5	246.2
40°	263.7	254.9	248.7	243.3	242.2	239.4	237.6	236.3	236.3	236.5	236.3
42.5°	249.2	241.2	235.8	231.1	229.8	228.2	226.3	226.3	226.6	227.4	226.6
45°	227.2	221.5	217.6	215.4	212.9	211.3	211.0	211.7	211.9	212.2	212.9
47.5°	206.9	203.1	199.6	197.1	196.0	195.8	195.5	196.7	197.8	198.2	199.2
50°	194.9	190.6	187.6	186.0	185.1	184.7	185.1	186.5	187.4	188.5	189.2
52.5°	181.5	178.4	176.4	175.1	174.8	175.1	175.1	176.7	178.1	178.6	178.9
55°	162.9	160.6	160.2	158.1	159.0	158.8	159.9	160.8	162.2	163.6	163.8
57.5°	144.3	142.5	141.3	141.5	141.8	142.8	143.7	145.3	146.7	148.2	148.3
60°	132.0	131.1	130.4	130.4	130.8	132.2	133.3	134.9	135.8	136.8	137.4
62.5°	120.7	119.8	119.1	119.5	120.7	121.5	122.8	123.7	124.6	125.5	125.8
65°	102.9	102.5	103.1	103.6	103.8	104.9	106.5	107.2	108.1	108.6	110.2
67.5°	86.5	86.6	86.5	87.1	88.5	88.7	90.2	91.8	92.0	92.9	93.9
70°	75.4	75.9	76.3	76.8	77.9	78.4	79.5	80.2	81.1	81.8	82.5
72.5°	65.2	65.3	65.8	65.7	66.7	67.6	68.6	69.3	70.2	71.1	71.7
75°	50.2	50.2	50.7	50.9	52.0	53.2	52.9	53.4	54.3	55.2	55.7
77.5°	36.7	36.2	36.7	36.9	37.3	38.2	38.4	39.0	40.1	39.8	40.3
80°	27.9	27.3	27.9	28.2	28.2	29.3	29.3	29.8	30.4	29.8	30.4
82.5°	19.9	19.6	20.1	20.2	20.5	20.6	20.9	21.0	21.7	21.4	21.7
85°	10.0	9.8	10.0	9.8	10.0	10.2	10.2	10.0	10.0	10.4	9.8
87.5°	6.6	7.6	8.9	10.3	11.6	12.9	12.6	12.5	12.3	11.8	11.8
90°	17.6	23.3	30.7	38.0	45.4	52.8	52.1	51.4	50.8	50.1	49.9
92.5°	38.6	41.0	42.7	44.5	46.2	47.9	48.1	48.2	48.3	48.5	48.6
95°	91.8	93.8	94.5	95.1	95.8	96.5	96.5	96.5	96.5	96.5	96.1
97.5°	155.0	157.1	158.4	159.7	160.9	162.2	162.2	162.2	162.2	162.2	162.2
100°	202.2	204.0	205.0	206.0	207.0	208.0	208.0	208.0	208.0	208.0	207.9
102.5°	250.7	252.4	253.7	254.9	256.2	257.5	257.8	258.0	258.3	258.6	258.5
105°	328.1	329.0	329.7	330.3	331.0	331.7	332.3	333.0	333.7	334.3	334.7
107.5°	412.6	413.4	413.4	413.4	413.4	413.4	413.6	413.9	414.2	414.4	413.8
110°	467.8	468.9	468.9	468.9	468.9	468.9	468.9	468.9	468.9	468.9	468.3



TEST NUMBER: P331490

CATALOG NUMBER: S122DIW-S290D1440U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	525.7	526.6	526.3	526.1	525.8	525.5	524.7	523.9	523.1	522.3	521.5
115°	611.1	611.7	611.1	610.4	609.7	609.1	608.7	608.4	608.0	607.7	607.0
117.5°	698.8	699.2	697.3	695.4	693.5	691.7	690.9	690.1	689.3	688.5	687.5
120°	755.5	755.5	752.8	750.1	747.4	744.7	744.7	744.7	744.7	744.7	744.2
122.5°	809.5	810.1	808.3	806.4	804.5	802.6	801.8	801.0	800.2	799.4	798.6
125°	889.5	890.5	889.5	888.5	887.5	886.4	885.4	884.4	883.4	882.4	881.8
127.5°	971.4	972.7	971.5	970.3	969.1	967.9	966.6	965.4	964.2	963.0	961.9
130°	1023.0	1024.8	1024.1	1023.5	1022.8	1022.1	1021.5	1020.8	1020.1	1019.4	1018.4
132.5°	1075.2	1077.1	1077.2	1077.3	1077.5	1077.6	1076.1	1074.7	1073.2	1071.7	1070.4
135°	1149.9	1152.1	1152.8	1153.5	1154.1	1154.8	1154.5	1154.1	1153.8	1153.5	1152.8
137.5°	1225.3	1227.3	1228.2	1229.0	1229.9	1230.8	1230.5	1230.2	1230.0	1229.7	1228.9
140°	1272.4	1274.7	1276.4	1278.1	1279.8	1281.4	1281.4	1281.4	1281.4	1281.4	1280.8
142.5°	1320.6	1322.7	1323.8	1325.0	1326.1	1327.3	1327.5	1327.8	1328.1	1328.3	1327.8
145°	1387.3	1389.5	1391.5	1393.5	1395.5	1397.5	1397.8	1398.2	1398.5	1398.8	1398.3
147.5°	1451.0	1453.1	1454.4	1455.7	1457.1	1458.4	1459.2	1459.9	1460.6	1461.4	1461.1
150°	1490.0	1491.6	1493.0	1494.3	1495.7	1497.0	1498.0	1499.0	1500.0	1501.0	1501.0
152.5°	1527.4	1529.2	1530.8	1532.4	1534.0	1535.6	1536.9	1538.1	1539.4	1540.7	1540.7
155°	1579.4	1580.4	1581.4	1582.4	1583.4	1584.4	1586.1	1587.8	1589.5	1591.1	1591.5
157.5°	1626.0	1626.7	1627.3	1627.9	1628.5	1629.1	1631.3	1633.6	1635.9	1638.2	1638.5
160°	1655.0	1655.5	1655.8	1656.1	1656.5	1656.8	1658.8	1660.8	1662.8	1664.8	1665.2
162.5°	1679.4	1679.6	1679.9	1680.3	1680.6	1680.9	1683.2	1685.5	1687.8	1690.0	1690.4
165°	1712.8	1712.6	1712.6	1712.6	1712.6	1712.6	1714.9	1717.3	1719.6	1722.0	1722.3
167.5°	1739.6	1739.1	1739.0	1739.0	1738.9	1738.8	1741.2	1743.5	1745.9	1748.2	1748.5
170°	1755.3	1754.6	1754.3	1754.0	1753.6	1753.3	1755.6	1758.0	1760.3	1762.7	1762.8
172.5°	1766.2	1765.5	1765.2	1764.8	1764.5	1764.1	1766.5	1768.8	1771.2	1773.5	1773.7
175°	1779.4	1778.6	1777.9	1777.2	1776.6	1775.9	1778.3	1780.6	1782.9	1785.3	1785.5
177.5°	1785.7	1785.0	1784.4	1783.9	1783.4	1782.8	1784.4	1786.1	1787.7	1789.3	1789.3
180°	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5



TEST NUMBER: P331490

CATALOG NUMBER: S122DIW-S290D1440U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1
2.5°	566.9	566.5	566.5	564.9	566.5	566.5	566.9	568.7	569.3	569.6	568.9
5°	525.9	525.2	524.1	525.2	524.1	525.2	525.9	529.1	530.7	532.2	533.6
7.5°	485.3	482.6	482.2	479.5	482.2	482.6	485.3	486.8	490.0	493.6	496.9
10°	455.7	453.9	453.6	449.3	453.6	453.9	455.7	459.6	462.7	467.0	471.6
12.5°	433.2	428.8	429.7	427.2	429.7	428.8	433.2	433.2	436.9	439.6	446.7
15°	394.1	394.1	393.2	389.4	393.2	394.1	394.1	400.3	401.4	405.7	411.8
17.5°	366.1	365.6	363.5	364.6	363.5	365.6	366.1	370.6	371.4	377.1	382.2
20°	349.4	348.0	345.3	345.3	345.3	348.0	349.4	351.9	354.8	358.2	362.6
22.5°	333.6	333.5	330.6	331.5	330.6	333.5	333.6	335.9	338.7	342.4	346.0
25°	315.1	313.3	311.9	312.6	311.9	313.3	315.1	315.3	318.5	321.0	323.3
27.5°	297.5	296.5	296.4	294.6	296.4	296.5	297.5	298.1	299.9	301.4	303.5
30°	287.4	285.1	285.5	284.4	285.5	285.1	287.4	287.6	288.5	289.4	291.9
32.5°	275.7	274.9	274.5	273.5	274.5	274.9	275.7	276.1	278.0	278.9	280.8
35°	259.9	260.1	259.0	259.4	259.0	260.1	259.9	260.3	260.6	261.5	263.3
37.5°	246.0	246.7	246.2	246.3	246.2	246.7	246.0	246.2	246.5	246.6	247.2
40°	236.9	236.9	236.9	237.6	236.9	236.9	236.9	236.3	236.5	236.3	236.3
42.5°	228.2	227.8	227.5	227.4	227.5	227.8	228.2	226.6	227.4	226.6	226.3
45°	213.3	214.0	214.2	213.1	214.2	214.0	213.3	212.9	212.2	211.9	211.7
47.5°	199.8	199.9	199.8	200.8	199.8	199.9	199.8	199.2	198.2	197.8	196.7
50°	190.4	189.9	190.4	189.9	190.4	189.9	190.4	189.2	188.5	187.4	186.5
52.5°	180.4	180.5	180.2	180.1	180.2	180.5	180.4	178.9	178.6	178.1	176.7
55°	164.7	165.1	164.9	164.9	164.9	165.1	164.7	163.8	163.6	162.2	160.8
57.5°	148.5	148.9	149.2	148.2	149.2	148.9	148.5	148.3	148.2	146.7	145.3
60°	137.2	138.3	138.1	137.7	138.1	138.3	137.2	137.4	136.8	135.8	134.9
62.5°	126.8	127.3	127.2	127.1	127.2	127.3	126.8	125.8	125.5	124.6	123.7
65°	110.9	111.3	110.6	111.3	110.6	111.3	110.9	110.2	108.6	108.1	107.2
67.5°	93.6	93.8	94.3	94.6	94.3	93.8	93.6	93.9	92.9	92.0	91.8
70°	82.9	82.7	83.4	84.1	83.4	82.7	82.9	82.5	81.8	81.1	80.2
72.5°	71.6	72.1	71.9	72.4	71.9	72.1	71.6	71.7	71.1	70.2	69.3
75°	55.2	55.9	55.7	56.3	55.7	55.9	55.2	55.7	55.2	54.3	53.4
77.5°	39.9	40.0	39.9	40.3	39.9	40.0	39.9	40.3	39.8	40.1	39.0
80°	30.4	30.0	29.5	30.4	29.5	30.0	30.4	30.4	29.8	30.4	29.8
82.5°	21.2	21.4	21.0	21.0	21.0	21.4	21.2	21.7	21.4	21.7	21.0
85°	9.8	9.5	9.1	9.1	9.1	9.5	9.8	9.8	10.4	10.0	10.0
87.5°	11.9	11.8	11.8	11.7	11.8	11.8	11.9	11.8	11.8	12.3	12.5
90°	50.3	50.6	50.9	51.3	50.9	50.6	50.3	49.9	50.1	50.8	51.4
92.5°	48.6	48.7	48.8	48.8	48.8	48.7	48.6	48.6	48.5	48.3	48.2
95°	95.5	94.8	94.1	93.5	94.1	94.8	95.5	96.1	96.5	96.5	96.5
97.5°	162.1	162.0	162.0	161.9	162.0	162.0	162.1	162.2	162.2	162.2	162.2
100°	207.5	207.2	206.9	206.5	206.9	207.2	207.5	207.9	208.0	208.0	208.0
102.5°	258.2	257.9	257.5	257.2	257.5	257.9	258.2	258.5	258.6	258.3	258.0
105°	334.7	334.7	334.7	334.7	334.7	334.7	334.7	334.7	334.3	333.7	333.0
107.5°	412.3	410.7	409.2	407.6	409.2	410.7	412.3	413.8	414.4	414.2	413.9
110°	467.3	466.3	465.3	464.3	465.3	466.3	467.3	468.3	468.9	468.9	468.9



TEST NUMBER: P331490

CATALOG NUMBER: S122DIW-S290D1440U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	520.8	520.1	519.3	518.6	519.3	520.1	520.8	521.5	522.3	523.1	523.9
115°	606.0	605.0	604.0	603.0	604.0	605.0	606.0	607.0	607.7	608.0	608.4
117.5°	686.5	685.5	684.5	683.5	684.5	685.5	686.5	687.5	688.5	689.3	690.1
120°	743.2	742.2	741.2	740.2	741.2	742.2	743.2	744.2	744.7	744.7	744.7
122.5°	797.9	797.2	796.4	795.7	796.4	797.2	797.9	798.6	799.4	800.2	801.0
125°	881.4	881.1	880.8	880.4	880.8	881.1	881.4	881.8	882.4	883.4	884.4
127.5°	960.8	959.7	958.7	957.6	958.7	959.7	960.8	961.9	963.0	964.2	965.4
130°	1017.1	1015.8	1014.4	1013.1	1014.4	1015.8	1017.1	1018.4	1019.4	1020.1	1020.8
132.5°	1069.4	1068.3	1067.2	1066.1	1067.2	1068.3	1069.4	1070.4	1071.7	1073.2	1074.7
135°	1151.8	1150.8	1149.8	1148.8	1149.8	1150.8	1151.8	1152.8	1153.5	1153.8	1154.1
137.5°	1227.6	1226.2	1224.9	1223.5	1224.9	1226.2	1227.6	1228.9	1229.7	1230.0	1230.2
140°	1279.4	1278.1	1276.7	1275.4	1276.7	1278.1	1279.4	1280.8	1281.4	1281.4	1281.4
142.5°	1326.5	1325.1	1323.8	1322.4	1323.8	1325.1	1326.5	1327.8	1328.3	1328.1	1327.8
145°	1397.0	1395.7	1394.3	1393.0	1394.3	1395.7	1397.0	1398.3	1398.8	1398.5	1398.2
147.5°	1459.8	1458.5	1457.3	1456.0	1457.3	1458.5	1459.8	1461.1	1461.4	1460.6	1459.9
150°	1500.0	1499.0	1498.0	1497.0	1498.0	1499.0	1500.0	1501.0	1501.0	1500.0	1499.0
152.5°	1539.4	1538.1	1536.9	1535.6	1536.9	1538.1	1539.4	1540.7	1540.7	1539.4	1538.1
155°	1590.5	1589.5	1588.5	1587.5	1588.5	1589.5	1590.5	1591.5	1591.1	1589.5	1587.8
157.5°	1636.9	1635.3	1633.7	1632.1	1633.7	1635.3	1636.9	1638.5	1638.2	1635.9	1633.6
160°	1663.8	1662.5	1661.2	1659.8	1661.2	1662.5	1663.8	1665.2	1664.8	1662.8	1660.8
162.5°	1688.8	1687.2	1685.6	1683.9	1685.6	1687.2	1688.8	1690.4	1690.0	1687.8	1685.5
165°	1720.6	1719.0	1717.3	1715.6	1717.3	1719.0	1720.6	1722.3	1722.0	1719.6	1717.3
167.5°	1746.8	1745.0	1743.3	1741.5	1743.3	1745.0	1746.8	1748.5	1748.2	1745.9	1743.5
170°	1760.8	1758.8	1756.8	1754.8	1756.8	1758.8	1760.8	1762.8	1762.7	1760.3	1758.0
172.5°	1771.7	1769.7	1767.7	1765.7	1767.7	1769.7	1771.7	1773.7	1773.5	1771.2	1768.8
175°	1783.4	1781.4	1779.4	1777.4	1779.4	1781.4	1783.4	1785.5	1785.3	1782.9	1780.6
177.5°	1787.7	1786.1	1784.4	1782.8	1784.4	1786.1	1787.7	1789.3	1789.3	1787.7	1786.1
180°	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5



TEST NUMBER: P331490

CATALOG NUMBER: S122DIW-S290D1440U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1
2.5°	568.0	570.0	573.1	576.4	578.4	582.2	583.3	585.1	586.7	590.5	594.5
5°	535.2	538.4	545.9	550.0	555.6	562.2	566.5	571.1	576.1	584.7	592.7
7.5°	500.0	505.3	514.7	522.3	530.4	539.8	546.6	555.6	563.1	575.3	586.9
10°	476.6	484.1	492.5	501.6	512.9	522.9	532.5	543.8	552.9	567.5	581.1
12.5°	455.5	456.6	468.7	478.7	494.2	506.6	517.6	532.2	541.1	558.4	572.7
15°	418.7	425.5	436.4	444.3	462.7	478.4	493.9	509.1	519.3	540.7	559.5
17.5°	387.6	393.9	405.1	418.1	431.3	446.9	466.9	483.0	496.9	521.3	543.6
20°	368.0	375.7	387.1	400.5	412.1	429.1	446.4	464.8	479.8	507.3	533.4
22.5°	351.3	357.4	366.6	379.8	392.4	408.0	426.9	447.0	462.7	492.4	518.8
25°	327.8	332.8	338.7	349.6	363.9	381.0	395.7	417.8	440.7	468.4	500.4
27.5°	306.6	310.2	315.4	325.0	336.1	352.0	368.4	389.3	412.4	442.5	476.3
30°	293.7	296.0	301.2	309.2	320.1	332.6	349.2	369.1	392.8	423.2	456.8
32.5°	282.5	284.5	288.0	295.5	305.0	315.7	330.6	350.6	373.1	403.0	440.3
35°	265.6	267.1	270.1	276.2	281.5	291.9	304.4	322.6	343.7	372.3	410.9
37.5°	248.7	250.9	252.7	255.3	262.0	268.9	279.7	295.1	315.8	344.7	381.5
40°	237.6	239.4	242.2	243.3	248.7	254.9	263.7	277.8	298.7	325.1	361.0
42.5°	226.3	228.2	229.8	231.1	235.8	241.2	249.2	261.3	279.8	305.4	341.0
45°	211.0	211.3	212.9	215.4	217.6	221.5	227.2	237.6	251.9	276.0	308.3
47.5°	195.5	195.8	196.0	197.1	199.6	203.1	206.9	215.4	228.2	247.4	278.8
50°	185.1	184.7	185.1	186.0	187.6	190.6	194.9	201.0	211.5	229.4	258.3
52.5°	175.1	175.1	174.8	175.1	176.4	178.4	181.5	186.7	196.0	212.5	237.9
55°	159.9	158.8	159.0	158.1	160.2	160.6	162.9	167.2	175.4	186.7	210.6
57.5°	143.7	142.8	141.8	141.5	141.3	142.5	144.3	147.7	154.0	164.0	183.3
60°	133.3	132.2	130.8	130.4	130.4	131.1	132.0	134.5	140.4	149.2	165.1
62.5°	122.8	121.5	120.7	119.5	119.1	119.8	120.7	122.5	126.8	135.1	148.8
65°	106.5	104.9	103.8	103.6	103.1	102.5	102.9	104.7	108.1	114.7	125.6
67.5°	90.2	88.7	88.5	87.1	86.5	86.6	86.5	88.0	90.1	95.8	103.9
70°	79.5	78.4	77.9	76.8	76.3	75.9	75.4	76.8	78.8	83.6	90.6
72.5°	68.6	67.6	66.7	65.7	65.8	65.3	65.2	66.1	67.7	72.1	77.6
75°	52.9	53.2	52.0	50.9	50.7	50.2	50.2	50.9	51.6	55.0	59.3
77.5°	38.4	38.2	37.3	36.9	36.7	36.2	36.7	37.1	37.5	39.8	42.9
80°	29.3	29.3	28.2	28.2	27.9	27.3	27.9	27.5	28.4	30.7	32.9
82.5°	20.9	20.6	20.5	20.2	20.1	19.6	19.9	20.4	20.8	22.3	23.7
85°	10.2	10.2	10.0	9.8	10.0	9.8	10.0	10.2	10.4	11.1	12.3
87.5°	12.6	12.9	11.6	10.3	8.9	7.6	6.6	6.0	5.5	4.9	4.3
90°	52.1	52.8	45.4	38.0	30.7	23.3	17.6	13.6	9.5	5.5	1.5
92.5°	48.1	47.9	46.2	44.5	42.7	41.0	38.6	35.7	32.7	29.8	26.8
95°	96.5	96.5	95.8	95.1	94.5	93.8	91.8	88.4	85.1	81.7	78.4
97.5°	162.2	162.2	160.9	159.7	158.4	157.1	155.0	152.1	149.1	146.2	143.2
100°	208.0	208.0	207.0	206.0	205.0	204.0	202.2	199.5	196.8	194.1	191.5
102.5°	257.8	257.5	256.2	254.9	253.7	252.4	250.7	248.5	246.4	244.3	242.1
105°	332.3	331.7	331.0	330.3	329.7	329.0	328.1	327.1	326.1	325.1	324.1
107.5°	413.6	413.4	413.4	413.4	413.4	413.4	412.6	411.2	409.7	408.2	406.7
110°	468.9	468.9	468.9	468.9	468.9	468.9	467.8	465.8	463.8	461.8	459.8



TEST NUMBER: P331490

CATALOG NUMBER: S122DIW-S290D1440U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	524.7	525.5	525.8	526.1	526.3	526.6	525.7	523.7	521.7	519.7	517.7
115°	608.7	609.1	609.7	610.4	611.1	611.7	611.1	609.1	607.0	605.0	603.0
117.5°	690.9	691.7	693.5	695.4	697.3	699.2	698.8	696.1	693.4	690.7	688.1
120°	744.7	744.7	747.4	750.1	752.8	755.5	755.5	752.8	750.1	747.4	744.7
122.5°	801.8	802.6	804.5	806.4	808.3	810.1	809.5	806.2	803.0	799.8	796.6
125°	885.4	886.4	887.5	888.5	889.5	890.5	889.5	886.4	883.4	880.4	877.4
127.5°	966.6	967.9	969.1	970.3	971.5	972.7	971.4	967.6	963.7	959.9	956.1
130°	1021.5	1022.1	1022.8	1023.5	1024.1	1024.8	1023.0	1018.6	1014.3	1009.9	1005.5
132.5°	1076.1	1077.6	1077.5	1077.3	1077.2	1077.1	1075.2	1071.7	1068.1	1064.6	1061.0
135°	1154.5	1154.8	1154.1	1153.5	1152.8	1152.1	1149.9	1146.2	1142.6	1138.9	1135.2
137.5°	1230.5	1230.8	1229.9	1229.0	1228.2	1227.3	1225.3	1222.3	1219.3	1216.3	1213.3
140°	1281.4	1281.4	1279.8	1278.1	1276.4	1274.7	1272.4	1269.4	1266.4	1263.3	1260.3
142.5°	1327.5	1327.3	1326.1	1325.0	1323.8	1322.7	1320.6	1317.6	1314.6	1311.6	1308.6
145°	1397.8	1397.5	1395.5	1393.5	1391.5	1389.5	1387.3	1384.9	1382.6	1380.3	1377.9
147.5°	1459.2	1458.4	1457.1	1455.7	1454.4	1453.1	1451.0	1448.2	1445.3	1442.5	1439.7
150°	1498.0	1497.0	1495.7	1494.3	1493.0	1491.6	1490.0	1488.0	1486.0	1483.9	1481.9
152.5°	1536.9	1535.6	1534.0	1532.4	1530.8	1529.2	1527.4	1525.3	1523.3	1521.3	1519.3
155°	1586.1	1584.4	1583.4	1582.4	1581.4	1580.4	1579.4	1578.4	1577.4	1576.4	1575.4
157.5°	1631.3	1629.1	1628.5	1627.9	1627.3	1626.7	1626.0	1625.4	1624.7	1624.0	1623.3
160°	1658.8	1656.8	1656.5	1656.1	1655.8	1655.5	1655.0	1654.3	1653.6	1653.0	1652.3
162.5°	1683.2	1680.9	1680.6	1680.3	1679.9	1679.6	1679.4	1679.2	1679.1	1679.0	1678.8
165°	1714.9	1712.6	1712.6	1712.6	1712.6	1712.6	1712.8	1713.1	1713.4	1713.8	1714.1
167.5°	1741.2	1738.8	1738.9	1739.0	1739.0	1739.1	1739.6	1740.6	1741.6	1742.6	1743.6
170°	1755.6	1753.3	1753.6	1754.0	1754.3	1754.6	1755.3	1756.3	1757.3	1758.3	1759.3
172.5°	1766.5	1764.1	1764.5	1764.8	1765.2	1765.5	1766.2	1767.2	1768.2	1769.2	1770.2
175°	1778.3	1775.9	1776.6	1777.2	1777.9	1778.6	1779.4	1780.4	1781.4	1782.4	1783.4
177.5°	1784.4	1782.8	1783.4	1783.9	1784.4	1785.0	1785.7	1786.5	1787.3	1788.1	1788.9
180°	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5



TEST NUMBER: P331490

CATALOG NUMBER: S122DIW-S290D1440U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1
2.5°	594.2	595.1	598.0	600.9	604.2	605.1	606.5	605.3	604.9	608.3	610.9
5°	595.9	599.9	607.9	615.2	621.3	625.6	630.2	632.0	635.4	640.1	646.1
7.5°	593.9	601.9	614.4	625.0	636.5	644.8	651.3	656.9	663.6	672.6	682.5
10°	591.8	602.4	617.7	630.6	644.7	655.4	664.2	672.9	682.9	695.4	708.3
12.5°	587.8	600.4	619.5	634.8	652.9	663.4	675.3	693.9	704.7	722.1	740.3
15°	579.7	593.8	620.4	639.2	659.7	679.7	701.7	719.4	737.1	747.4	773.0
17.5°	567.8	588.4	617.9	639.9	665.9	697.3	722.1	742.2	762.6	779.2	792.1
20°	558.1	580.6	614.3	640.6	671.5	705.3	733.7	754.2	771.9	785.8	793.7
22.5°	546.0	574.3	607.0	637.9	677.3	710.8	740.6	756.7	771.5	778.3	781.4
25°	526.8	560.9	597.9	635.6	680.1	715.6	742.8	752.6	756.9	750.3	739.4
27.5°	506.1	544.1	587.4	631.3	678.4	712.5	732.0	730.5	723.2	701.8	684.8
30°	490.7	532.5	579.0	627.0	674.2	707.4	718.7	707.4	690.8	667.0	642.6
32.5°	474.5	517.8	570.1	620.8	666.6	695.8	698.2	678.7	653.0	625.9	595.6
35°	450.0	496.8	553.4	607.0	650.4	668.8	657.9	623.3	592.9	555.9	514.5
37.5°	422.3	474.0	530.7	586.8	626.1	630.9	603.8	567.5	524.5	481.0	432.3
40°	401.6	456.4	514.8	571.3	606.1	601.1	566.5	526.6	475.5	422.3	377.1
42.5°	383.1	437.8	497.3	552.8	580.6	566.9	526.6	477.5	422.6	372.5	331.1
45°	351.0	407.3	468.2	521.8	537.7	512.9	459.6	405.0	351.0	309.2	276.5
47.5°	319.8	375.5	435.8	482.9	488.5	455.2	396.9	340.8	294.3	260.3	237.2
50°	296.9	352.8	412.5	454.6	452.7	412.5	352.6	299.2	260.3	232.8	217.4
52.5°	276.4	329.2	386.5	424.8	415.1	371.3	314.0	266.6	234.7	213.2	199.2
55°	244.4	293.3	347.8	378.5	360.7	312.1	263.7	225.6	201.9	185.8	174.9
57.5°	212.7	258.5	305.2	324.1	304.5	259.6	219.3	191.6	173.8	161.9	154.8
60°	193.1	233.1	274.6	291.0	267.6	227.6	195.8	171.1	156.7	147.0	140.6
62.5°	173.5	209.3	248.5	257.4	236.0	202.2	174.0	153.4	141.7	133.0	127.0
65°	146.7	176.1	205.8	211.7	192.0	165.8	143.6	130.2	119.7	113.4	108.6
67.5°	120.4	143.9	165.0	169.7	152.4	134.3	118.2	106.5	99.5	94.2	90.1
70°	104.7	123.4	140.6	144.5	130.6	114.5	102.2	92.9	86.5	82.0	78.1
72.5°	88.2	103.7	118.1	120.7	109.4	97.0	87.0	79.6	74.0	71.1	67.4
75°	67.5	76.6	87.7	88.4	80.9	73.4	65.7	60.9	57.9	54.3	52.5
77.5°	47.6	54.7	61.1	62.3	57.9	52.8	48.5	44.7	42.2	40.5	38.8
80°	36.3	42.0	44.8	46.3	43.2	39.5	37.0	34.5	32.9	31.8	30.7
82.5°	26.0	29.5	32.0	33.3	31.5	29.3	26.9	25.4	24.2	23.3	22.9
85°	13.2	14.8	16.4	16.8	16.4	15.4	14.1	14.1	13.4	13.2	13.2
87.5°	5.6	7.2	8.0	9.3	10.1	11.6	13.1	14.3	15.6	15.3	15.0
90°	5.5	9.5	13.6	17.6	23.3	30.7	38.0	45.4	52.8	52.1	51.4
92.5°	29.8	32.7	35.7	38.6	41.0	42.7	44.5	46.2	47.9	48.1	48.2
95°	81.7	85.1	88.4	91.8	93.8	94.5	95.1	95.8	96.5	96.5	96.5
97.5°	146.2	149.1	152.1	155.0	157.1	158.4	159.7	160.9	162.2	162.2	162.2
100°	194.1	196.8	199.5	202.2	204.0	205.0	206.0	207.0	208.0	208.0	208.0
102.5°	244.3	246.4	248.5	250.7	252.4	253.7	254.9	256.2	257.5	257.8	258.0
105°	325.1	326.1	327.1	328.1	329.0	329.7	330.3	331.0	331.7	332.3	333.0
107.5°	408.2	409.7	411.2	412.6	413.4	413.4	413.4	413.4	413.4	413.6	413.9
110°	461.8	463.8	465.8	467.8	468.9	468.9	468.9	468.9	468.9	468.9	468.9





TEST NUMBER: P331490

CATALOG NUMBER: S122DIW-S290D1440U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	519.7	521.7	523.7	525.7	526.6	526.3	526.1	525.8	525.5	524.7	523.9
115°	605.0	607.0	609.1	611.1	611.7	611.1	610.4	609.7	609.1	608.7	608.4
117.5°	690.7	693.4	696.1	698.8	699.2	697.3	695.4	693.5	691.7	690.9	690.1
120°	747.4	750.1	752.8	755.5	755.5	752.8	750.1	747.4	744.7	744.7	744.7
122.5°	799.8	803.0	806.2	809.5	810.1	808.3	806.4	804.5	802.6	801.8	801.0
125°	880.4	883.4	886.4	889.5	890.5	889.5	888.5	887.5	886.4	885.4	884.4
127.5°	959.9	963.7	967.6	971.4	972.7	971.5	970.3	969.1	967.9	966.6	965.4
130°	1009.9	1014.3	1018.6	1023.0	1024.8	1024.1	1023.5	1022.8	1022.1	1021.5	1020.8
132.5°	1064.6	1068.1	1071.7	1075.2	1077.1	1077.2	1077.3	1077.5	1077.6	1076.1	1074.7
135°	1138.9	1142.6	1146.2	1149.9	1152.1	1152.8	1153.5	1154.1	1154.8	1154.5	1154.1
137.5°	1216.3	1219.3	1222.3	1225.3	1227.3	1228.2	1229.0	1229.9	1230.8	1230.5	1230.2
140°	1263.3	1266.4	1269.4	1272.4	1274.7	1276.4	1278.1	1279.8	1281.4	1281.4	1281.4
142.5°	1311.6	1314.6	1317.6	1320.6	1322.7	1323.8	1325.0	1326.1	1327.3	1327.5	1327.8
145°	1380.3	1382.6	1384.9	1387.3	1389.5	1391.5	1393.5	1395.5	1397.5	1397.8	1398.2
147.5°	1442.5	1445.3	1448.2	1451.0	1453.1	1454.4	1455.7	1457.1	1458.4	1459.2	1459.9
150°	1483.9	1486.0	1488.0	1490.0	1491.6	1493.0	1494.3	1495.7	1497.0	1498.0	1499.0
152.5°	1521.3	1523.3	1525.3	1527.4	1529.2	1530.8	1532.4	1534.0	1535.6	1536.9	1538.1
155°	1576.4	1577.4	1578.4	1579.4	1580.4	1581.4	1582.4	1583.4	1584.4	1586.1	1587.8
157.5°	1624.0	1624.7	1625.4	1626.0	1626.7	1627.3	1627.9	1628.5	1629.1	1631.3	1633.6
160°	1653.0	1653.6	1654.3	1655.0	1655.5	1655.8	1656.1	1656.5	1656.8	1658.8	1660.8
162.5°	1679.0	1679.1	1679.2	1679.4	1679.6	1679.9	1680.3	1680.6	1680.9	1683.2	1685.5
165°	1713.8	1713.4	1713.1	1712.8	1712.6	1712.6	1712.6	1712.6	1712.6	1714.9	1717.3
167.5°	1742.6	1741.6	1740.6	1739.6	1739.1	1739.0	1739.0	1738.9	1738.8	1741.2	1743.5
170°	1758.3	1757.3	1756.3	1755.3	1754.6	1754.3	1754.0	1753.6	1753.3	1755.6	1758.0
172.5°	1769.2	1768.2	1767.2	1766.2	1765.5	1765.2	1764.8	1764.5	1764.1	1766.5	1768.8
175°	1782.4	1781.4	1780.4	1779.4	1778.6	1777.9	1777.2	1776.6	1775.9	1778.3	1780.6
177.5°	1788.1	1787.3	1786.5	1785.7	1785.0	1784.4	1783.9	1783.4	1782.8	1784.4	1786.1
180°	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5



TEST NUMBER: P331490

CATALOG NUMBER: S122DIW-S290D1440U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	591.1	591.1	591.1	591.1	591.1	591.1	591.1
2.5°	613.1	615.6	615.6	616.0	618.9	618.5	618.3
5°	652.4	656.3	656.7	660.8	663.5	662.6	660.1
7.5°	689.5	696.7	702.2	705.2	708.8	711.0	710.0
10°	719.0	729.4	735.8	740.1	745.3	749.2	747.8
12.5°	745.7	758.1	766.9	774.3	774.9	779.9	776.5
15°	787.4	800.5	801.9	807.3	811.7	811.2	811.4
17.5°	801.1	805.3	806.2	806.3	806.4	804.8	801.3
20°	796.2	794.6	790.8	787.8	782.6	781.9	777.4
22.5°	772.9	767.9	758.2	751.8	743.7	741.6	740.3
25°	727.2	716.0	700.6	685.8	681.7	673.8	676.0
27.5°	664.3	647.0	630.2	618.3	607.4	595.5	598.9
30°	620.2	600.6	577.0	558.8	547.2	535.9	533.8
32.5°	567.5	538.8	512.5	496.5	478.7	471.5	463.7
35°	476.6	448.6	422.5	400.0	387.1	377.1	368.0
37.5°	394.9	362.7	341.6	323.4	314.0	308.3	309.8
40°	344.2	316.0	300.5	286.7	278.0	274.0	274.9
42.5°	303.1	282.0	269.3	259.8	253.7	251.4	250.9
45°	256.5	244.7	234.2	228.8	225.8	223.3	221.7
47.5°	224.7	215.0	209.1	205.9	203.3	200.8	200.7
50°	205.6	199.2	195.1	191.7	189.7	187.9	189.5
52.5°	191.0	185.2	181.1	178.1	177.3	175.7	175.6
55°	169.5	164.9	162.0	159.2	157.9	157.0	155.8
57.5°	149.8	145.5	142.8	141.1	138.5	137.6	137.2
60°	135.8	132.4	129.7	127.4	126.3	124.5	124.5
62.5°	122.9	119.5	117.0	115.3	113.4	112.7	112.9
65°	104.3	101.5	99.0	97.2	96.8	95.4	95.9
67.5°	87.1	85.3	82.6	81.6	80.8	80.1	79.5
70°	75.6	73.8	72.5	71.1	70.4	70.4	70.4
72.5°	66.0	63.8	63.0	61.3	61.7	61.0	60.2
75°	51.1	49.7	49.1	48.4	47.3	47.3	47.3
77.5°	37.6	37.2	36.4	35.7	35.4	35.2	35.3
80°	29.1	28.8	28.4	28.4	27.9	27.7	27.3
82.5°	22.4	21.8	21.5	21.3	21.2	21.2	21.1
85°	12.7	12.3	12.3	12.5	12.0	12.0	12.3
87.5°	15.1	14.9	14.7	14.8	15.0	14.9	15.0
90°	50.8	50.1	49.9	50.3	50.6	50.9	51.3
92.5°	48.3	48.5	48.6	48.6	48.7	48.8	48.8
95°	96.5	96.5	96.1	95.5	94.8	94.1	93.5
97.5°	162.2	162.2	162.2	162.1	162.0	162.0	161.9
100°	208.0	208.0	207.9	207.5	207.2	206.9	206.5
102.5°	258.3	258.6	258.5	258.2	257.9	257.5	257.2
105°	333.7	334.3	334.7	334.7	334.7	334.7	334.7
107.5°	414.2	414.4	413.8	412.3	410.7	409.2	407.6
110°	468.9	468.9	468.3	467.3	466.3	465.3	464.3



TEST NUMBER: P331490

CATALOG NUMBER: S122DIW-S290D1440U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	523.1	522.3	521.5	520.8	520.1	519.3	518.6
115°	608.0	607.7	607.0	606.0	605.0	604.0	603.0
117.5°	689.3	688.5	687.5	686.5	685.5	684.5	683.5
120°	744.7	744.7	744.2	743.2	742.2	741.2	740.2
122.5°	800.2	799.4	798.6	797.9	797.2	796.4	795.7
125°	883.4	882.4	881.8	881.4	881.1	880.8	880.4
127.5°	964.2	963.0	961.9	960.8	959.7	958.7	957.6
130°	1020.1	1019.4	1018.4	1017.1	1015.8	1014.4	1013.1
132.5°	1073.2	1071.7	1070.4	1069.4	1068.3	1067.2	1066.1
135°	1153.8	1153.5	1152.8	1151.8	1150.8	1149.8	1148.8
137.5°	1230.0	1229.7	1228.9	1227.6	1226.2	1224.9	1223.5
140°	1281.4	1281.4	1280.8	1279.4	1278.1	1276.7	1275.4
142.5°	1328.1	1328.3	1327.8	1326.5	1325.1	1323.8	1322.4
145°	1398.5	1398.8	1398.3	1397.0	1395.7	1394.3	1393.0
147.5°	1460.6	1461.4	1461.1	1459.8	1458.5	1457.3	1456.0
150°	1500.0	1501.0	1501.0	1500.0	1499.0	1498.0	1497.0
152.5°	1539.4	1540.7	1540.7	1539.4	1538.1	1536.9	1535.6
155°	1589.5	1591.1	1591.5	1590.5	1589.5	1588.5	1587.5
157.5°	1635.9	1638.2	1638.5	1636.9	1635.3	1633.7	1632.1
160°	1662.8	1664.8	1665.2	1663.8	1662.5	1661.2	1659.8
162.5°	1687.8	1690.0	1690.4	1688.8	1687.2	1685.6	1683.9
165°	1719.6	1722.0	1722.3	1720.6	1719.0	1717.3	1715.6
167.5°	1745.9	1748.2	1748.5	1746.8	1745.0	1743.3	1741.5
170°	1760.3	1762.7	1762.8	1760.8	1758.8	1756.8	1754.8
172.5°	1771.2	1773.5	1773.7	1771.7	1769.7	1767.7	1765.7
175°	1782.9	1785.3	1785.5	1783.4	1781.4	1779.4	1777.4
177.5°	1787.7	1789.3	1789.3	1787.7	1786.1	1784.4	1782.8
180°	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5	1786.5

(END OF REPORT)