

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331478

Luminaire Tested: **S122DIW-S290D970U835-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331478
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S290D970U835-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 970 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4664.9 lumens
Efficiency: N/A
Efficacy: 122.8 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 38
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331478

CATALOG NUMBER: S122DIW-S290D970U835-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331478

CATALOG NUMBER: S122DIW-S290D970U835-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36	28
1	93	89	85	82	83	80	77	74	63	61	59	47	45	44	32	31	31	24
2	85	78	72	67	76	70	65	61	55	52	49	41	39	37	29	27	26	21
3	78	69	62	56	69	62	56	51	49	45	41	37	34	32	26	24	23	18
4	71	61	53	48	63	55	48	44	43	39	35	33	30	27	23	21	20	15
5	65	54	47	41	58	49	42	37	39	34	31	30	26	24	21	19	17	14
6	60	49	41	35	54	44	37	32	35	30	27	27	23	21	19	17	15	12
7	55	44	36	31	50	40	33	28	32	27	23	24	21	19	17	15	14	11
8	51	40	32	27	46	36	30	25	29	24	21	22	19	17	16	14	12	10
9	48	36	29	24	43	33	27	22	26	22	19	20	17	15	15	13	11	9
10	45	33	26	22	40	30	24	20	24	20	17	19	16	13	14	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9544	9544	9544	9544
5°	10699	9606	8512	9606
10°	12260	9527	7366	9527
15°	13563	9352	6509	9352
20°	13357	9165	5933	9165
25°	12043	8915	5569	8915
30°	9952	8516	5302	8516
35°	7253	8099	5113	8099
40°	5794	7609	5008	7609
45°	5062	7040	4866	7040
50°	4760	6488	4770	6488
55°	4386	5928	4642	5928
60°	4020	5331	4447	5331
65°	3664	4798	4252	4798
70°	3323	4277	3970	4277
75°	2951	3699	3512	3699
80°	2538	3059	2827	3059
85°	2279	2279	1686	2279



TEST NUMBER: P331478

CATALOG NUMBER: S122DIW-S290D970U835-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.3	1.2
10°-20°	163.7	3.5
20°-30°	237.5	5.1
30°-40°	250.6	5.4
40°-50°	221.9	4.8
50°-60°	177.1	3.8
60°-70°	120.4	2.6
70°-80°	61.7	1.3
80°-90°	19.7	0.4
90°-100°	76.0	1.6
100°-110°	236.2	5.1
110°-120°	403.8	8.7
120°-130°	531.0	11.4
130°-140°	595.9	12.8
140°-150°	584.3	12.5
150°-160°	490.1	10.5
160°-170°	325.1	7.0
170°-180°	113.6	2.4
0°-30°	457.5	9.8
0°-40°	708.1	15.2
0°-60°	1107.1	23.7
0°-90°	1308.8	28.1
90°-120°	716.0	15.3
90°-150°	2427.3	52.0
90°-180°	3356.0	71.9
0°-180°	4664.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	591	591	591	591	591	
5°	660	593	525	593	660	66
15°	811	560	389	560	811	224
25°	676	500	313	500	676	306
35°	368	411	259	411	368	239
45°	222	308	213	308	222	174
55°	156	211	165	211	156	140
65°	96	126	111	126	96	95
75°	47	59	56	59	47	51
85°	12	12	9	12	12	14
90°	34	1	34	1	34	16
95°	63	53	63	53	63	70
105°	225	218	225	218	225	237
115°	405	405	405	405	405	400
125°	592	590	592	590	592	527
135°	772	763	772	763	772	594
145°	936	926	936	926	936	584
155°	1066	1058	1066	1058	1066	491
165°	1153	1152	1153	1152	1153	325
175°	1194	1198	1194	1198	1194	113
180°	1200	1200	1200	1200	1200	



TEST NUMBER: P331478

CATALOG NUMBER: S122DIW-S290D970U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1
2.5°	618.3	618.5	618.9	616.0	615.6	615.6	613.1	610.9	608.3	604.9	605.3
5°	660.1	662.6	663.5	660.8	656.7	656.3	652.4	646.1	640.1	635.4	632.0
7.5°	710.0	711.0	708.8	705.2	702.2	696.7	689.5	682.5	672.6	663.6	656.9
10°	747.8	749.2	745.3	740.1	735.8	729.4	719.0	708.3	695.4	682.9	672.9
12.5°	776.5	779.9	774.9	774.3	766.9	758.1	745.7	740.3	722.1	704.7	693.9
15°	811.4	811.2	811.7	807.3	801.9	800.5	787.4	773.0	747.4	737.1	719.4
17.5°	801.3	804.8	806.4	806.3	806.2	805.3	801.1	792.1	779.2	762.6	742.2
20°	777.4	781.9	782.6	787.8	790.8	794.6	796.2	793.7	785.8	771.9	754.2
22.5°	740.3	741.6	743.7	751.8	758.2	767.9	772.9	781.4	778.3	771.5	756.7
25°	676.0	673.8	681.7	685.8	700.6	716.0	727.2	739.4	750.3	756.9	752.6
27.5°	598.9	595.5	607.4	618.3	630.2	647.0	664.3	684.8	701.8	723.2	730.5
30°	533.8	535.9	547.2	558.8	577.0	600.6	620.2	642.6	667.0	690.8	707.4
32.5°	463.7	471.5	478.7	496.5	512.5	538.8	567.5	595.6	625.9	653.0	678.7
35°	368.0	377.1	387.1	400.0	422.5	448.6	476.6	514.5	555.9	592.9	623.3
37.5°	309.8	308.3	314.0	323.4	341.6	362.7	394.9	432.3	481.0	524.5	567.5
40°	274.9	274.0	278.0	286.7	300.5	316.0	344.2	377.1	422.3	475.5	526.6
42.5°	250.9	251.4	253.7	259.8	269.3	282.0	303.1	331.1	372.5	422.6	477.5
45°	221.7	223.3	225.8	228.8	234.2	244.7	256.5	276.5	309.2	351.0	405.0
47.5°	200.7	200.8	203.3	205.9	209.1	215.0	224.7	237.2	260.3	294.3	340.8
50°	189.5	187.9	189.7	191.7	195.1	199.2	205.6	217.4	232.8	260.3	299.2
52.5°	175.6	175.7	177.3	178.1	181.1	185.2	191.0	199.2	213.2	234.7	266.6
55°	155.8	157.0	157.9	159.2	162.0	164.9	169.5	174.9	185.8	201.9	225.6
57.5°	137.2	137.6	138.5	141.1	142.8	145.5	149.8	154.8	161.9	173.8	191.6
60°	124.5	124.5	126.3	127.4	129.7	132.4	135.8	140.6	147.0	156.7	171.1
62.5°	112.9	112.7	113.4	115.3	117.0	119.5	122.9	127.0	133.0	141.7	153.4
65°	95.9	95.4	96.8	97.2	99.0	101.5	104.3	108.6	113.4	119.7	130.2
67.5°	79.5	80.1	80.8	81.6	82.6	85.3	87.1	90.1	94.2	99.5	106.5
70°	70.4	70.4	70.4	71.1	72.5	73.8	75.6	78.1	82.0	86.5	92.9
72.5°	60.2	61.0	61.7	61.3	63.0	63.8	66.0	67.4	71.1	74.0	79.6
75°	47.3	47.3	47.3	48.4	49.1	49.7	51.1	52.5	54.3	57.9	60.9
77.5°	35.3	35.2	35.4	35.7	36.4	37.2	37.6	38.8	40.5	42.2	44.7
80°	27.3	27.7	27.9	28.4	28.4	28.8	29.1	30.7	31.8	32.9	34.5
82.5°	21.1	21.2	21.2	21.3	21.5	21.8	22.4	22.9	23.3	24.2	25.4
85°	12.3	12.0	12.0	12.5	12.3	12.3	12.7	13.2	13.2	13.4	14.1
87.5°	11.6	11.6	11.7	11.5	11.4	11.6	11.7	11.6	11.9	12.2	11.4
90°	34.4	34.2	34.0	33.8	33.5	33.6	34.1	34.5	35.0	35.4	30.5
92.5°	32.8	32.8	32.7	32.7	32.6	32.6	32.5	32.4	32.3	32.2	31.0
95°	62.8	63.2	63.7	64.1	64.6	64.8	64.8	64.8	64.8	64.8	64.4
97.5°	108.8	108.8	108.9	108.9	109.0	109.0	109.0	109.0	109.0	109.0	108.1
100°	138.8	139.0	139.2	139.4	139.7	139.8	139.8	139.8	139.8	139.8	139.1
102.5°	172.8	173.0	173.2	173.5	173.7	173.7	173.5	173.4	173.2	173.0	172.1
105°	224.9	224.9	224.9	224.9	224.9	224.6	224.2	223.7	223.3	222.8	222.4
107.5°	273.9	274.9	275.9	277.0	278.0	278.4	278.3	278.1	277.9	277.7	277.7
110°	312.0	312.6	313.3	314.0	314.7	315.0	315.0	315.0	315.0	315.0	315.0



TEST NUMBER: P331478

CATALOG NUMBER: S122DIW-S290D970U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	348.4	348.9	349.4	349.9	350.4	350.9	351.5	352.0	352.5	353.1	353.3
115°	405.1	405.8	406.5	407.2	407.8	408.3	408.5	408.7	409.0	409.2	409.6
117.5°	459.2	459.9	460.6	461.3	461.9	462.5	463.1	463.6	464.2	464.7	466.0
120°	497.3	498.0	498.7	499.3	500.0	500.4	500.4	500.4	500.4	500.4	502.2
122.5°	534.6	535.1	535.6	536.1	536.6	537.1	537.6	538.2	538.7	539.2	540.5
125°	591.5	591.7	592.0	592.2	592.4	592.9	593.5	594.2	594.9	595.6	596.2
127.5°	643.4	644.1	644.8	645.5	646.2	647.0	647.8	648.6	649.4	650.3	651.1
130°	680.6	681.5	682.4	683.3	684.2	684.9	685.4	685.8	686.3	686.7	687.2
132.5°	716.3	717.0	717.7	718.5	719.2	720.0	721.0	722.0	723.0	724.0	723.9
135°	771.8	772.5	773.1	773.8	774.5	774.9	775.2	775.4	775.6	775.8	775.4
137.5°	822.0	822.9	823.8	824.7	825.6	826.2	826.4	826.5	826.7	826.9	826.3
140°	856.9	857.8	858.7	859.6	860.5	860.9	860.9	860.9	860.9	860.9	859.8
142.5°	888.5	889.4	890.3	891.2	892.1	892.4	892.3	892.1	891.9	891.7	891.0
145°	935.9	936.8	937.7	938.6	939.5	939.8	939.6	939.4	939.1	938.9	937.6
147.5°	978.2	979.1	979.9	980.8	981.6	981.8	981.3	980.8	980.3	979.8	978.9
150°	1005.8	1006.4	1007.1	1007.8	1008.5	1008.5	1007.8	1007.1	1006.4	1005.8	1004.9
152.5°	1031.7	1032.5	1033.4	1034.3	1035.1	1035.1	1034.3	1033.4	1032.5	1031.7	1030.6
155°	1066.5	1067.2	1067.9	1068.6	1069.2	1069.0	1067.9	1066.8	1065.6	1064.5	1063.8
157.5°	1096.5	1097.6	1098.7	1099.8	1100.8	1100.6	1099.1	1097.6	1096.0	1094.5	1094.1
160°	1115.2	1116.1	1117.0	1117.9	1118.8	1118.5	1117.2	1115.8	1114.5	1113.1	1112.9
162.5°	1131.4	1132.4	1133.5	1134.6	1135.7	1135.5	1133.9	1132.4	1130.9	1129.3	1129.1
165°	1152.6	1153.8	1154.9	1156.0	1157.1	1156.9	1155.3	1153.8	1152.2	1150.6	1150.6
167.5°	1170.1	1171.2	1172.4	1173.6	1174.7	1174.5	1173.0	1171.4	1169.8	1168.2	1168.3
170°	1179.0	1180.3	1181.7	1183.0	1184.4	1184.3	1182.7	1181.1	1179.5	1178.0	1178.2
172.5°	1186.3	1187.6	1189.0	1190.3	1191.7	1191.5	1190.0	1188.4	1186.8	1185.2	1185.5
175°	1194.2	1195.5	1196.9	1198.2	1199.6	1199.4	1197.9	1196.3	1194.7	1193.1	1193.6
177.5°	1197.8	1198.9	1200.0	1201.0	1202.1	1202.1	1201.0	1200.0	1198.9	1197.8	1198.2
180°	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2



TEST NUMBER: P331478

CATALOG NUMBER: S122DIW-S290D970U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1
2.5°	606.5	605.1	604.2	600.9	598.0	595.1	594.2	594.5	590.5	586.7	585.1
5°	630.2	625.6	621.3	615.2	607.9	599.9	595.9	592.7	584.7	576.1	571.1
7.5°	651.3	644.8	636.5	625.0	614.4	601.9	593.9	586.9	575.3	563.1	555.6
10°	664.2	655.4	644.7	630.6	617.7	602.4	591.8	581.1	567.5	552.9	543.8
12.5°	675.3	663.4	652.9	634.8	619.5	600.4	587.8	572.7	558.4	541.1	532.2
15°	701.7	679.7	659.7	639.2	620.4	593.8	579.7	559.5	540.7	519.3	509.1
17.5°	722.1	697.3	665.9	639.9	617.9	588.4	567.8	543.6	521.3	496.9	483.0
20°	733.7	705.3	671.5	640.6	614.3	580.6	558.1	533.4	507.3	479.8	464.8
22.5°	740.6	710.8	677.3	637.9	607.0	574.3	546.0	518.8	492.4	462.7	447.0
25°	742.8	715.6	680.1	635.6	597.9	560.9	526.8	500.4	468.4	440.7	417.8
27.5°	732.0	712.5	678.4	631.3	587.4	544.1	506.1	476.3	442.5	412.4	389.3
30°	718.7	707.4	674.2	627.0	579.0	532.5	490.7	456.8	423.2	392.8	369.1
32.5°	698.2	695.8	666.6	620.8	570.1	517.8	474.5	440.3	403.0	373.1	350.6
35°	657.9	668.8	650.4	607.0	553.4	496.8	450.0	410.9	372.3	343.7	322.6
37.5°	603.8	630.9	626.1	586.8	530.7	474.0	422.3	381.5	344.7	315.8	295.1
40°	566.5	601.1	606.1	571.3	514.8	456.4	401.6	361.0	325.1	298.7	277.8
42.5°	526.6	566.9	580.6	552.8	497.3	437.8	383.1	341.0	305.4	279.8	261.3
45°	459.6	512.9	537.7	521.8	468.2	407.3	351.0	308.3	276.0	251.9	237.6
47.5°	396.9	455.2	488.5	482.9	435.8	375.5	319.8	278.8	247.4	228.2	215.4
50°	352.6	412.5	452.7	454.6	412.5	352.8	296.9	258.3	229.4	211.5	201.0
52.5°	314.0	371.3	415.1	424.8	386.5	329.2	276.4	237.9	212.5	196.0	186.7
55°	263.7	312.1	360.7	378.5	347.8	293.3	244.4	210.6	186.7	175.4	167.2
57.5°	219.3	259.6	304.5	324.1	305.2	258.5	212.7	183.3	164.0	154.0	147.7
60°	195.8	227.6	267.6	291.0	274.6	233.1	193.1	165.1	149.2	140.4	134.5
62.5°	174.0	202.2	236.0	257.4	248.5	209.3	173.5	148.8	135.1	126.8	122.5
65°	143.6	165.8	192.0	211.7	205.8	176.1	146.7	125.6	114.7	108.1	104.7
67.5°	118.2	134.3	152.4	169.7	165.0	143.9	120.4	103.9	95.8	90.1	88.0
70°	102.2	114.5	130.6	144.5	140.6	123.4	104.7	90.6	83.6	78.8	76.8
72.5°	87.0	97.0	109.4	120.7	118.1	103.7	88.2	77.6	72.1	67.7	66.1
75°	65.7	73.4	80.9	88.4	87.7	76.6	67.5	59.3	55.0	51.6	50.9
77.5°	48.5	52.8	57.9	62.3	61.1	54.7	47.6	42.9	39.8	37.5	37.1
80°	37.0	39.5	43.2	46.3	44.8	42.0	36.3	32.9	30.7	28.4	27.5
82.5°	26.9	29.3	31.5	33.3	32.0	29.5	26.0	23.7	22.3	20.8	20.4
85°	14.1	15.4	16.4	16.8	16.4	14.8	13.2	12.3	11.1	10.4	10.2
87.5°	10.6	9.6	8.6	8.2	7.1	6.6	5.3	4.2	4.6	4.9	5.1
90°	25.5	20.6	15.6	11.8	9.1	6.4	3.7	1.0	3.7	6.4	9.1
92.5°	29.9	28.7	27.5	26.0	24.0	22.0	20.0	18.0	20.0	22.0	24.0
95°	63.9	63.5	63.0	61.7	59.4	57.2	54.9	52.7	54.9	57.2	59.4
97.5°	107.3	106.4	105.6	104.1	102.2	100.2	98.2	96.2	98.2	100.2	102.2
100°	138.4	137.7	137.1	135.8	134.0	132.2	130.4	128.6	130.4	132.2	134.0
102.5°	171.3	170.4	169.6	168.4	167.0	165.5	164.1	162.7	164.1	165.5	167.0
105°	221.9	221.5	221.0	220.5	219.8	219.1	218.4	217.8	218.4	219.1	219.8
107.5°	277.7	277.7	277.7	277.2	276.2	275.2	274.3	273.3	274.3	275.2	276.2
110°	315.0	315.0	315.0	314.3	313.0	311.6	310.3	308.9	310.3	311.6	313.0



TEST NUMBER: P331478

CATALOG NUMBER: S122DIW-S290D970U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	353.4	353.6	353.8	353.2	351.9	350.5	349.2	347.8	349.2	350.5	351.9
115°	410.1	410.5	411.0	410.5	409.2	407.8	406.5	405.1	406.5	407.8	409.2
117.5°	467.2	468.5	469.7	469.5	467.7	465.9	464.1	462.3	464.1	465.9	467.7
120°	504.0	505.8	507.6	507.6	505.8	504.0	502.2	500.4	502.2	504.0	505.8
122.5°	541.8	543.0	544.3	543.8	541.7	539.5	537.4	535.2	537.4	539.5	541.7
125°	596.9	597.6	598.3	597.6	595.6	593.5	591.5	589.5	591.5	593.5	595.6
127.5°	651.9	652.7	653.5	652.6	650.1	647.5	644.9	642.4	644.9	647.5	650.1
130°	687.6	688.1	688.5	687.3	684.4	681.4	678.5	675.6	678.5	681.4	684.4
132.5°	723.8	723.7	723.6	722.4	720.0	717.6	715.2	712.8	715.2	717.6	720.0
135°	774.9	774.5	774.0	772.6	770.1	767.6	765.2	762.7	765.2	767.6	770.1
137.5°	825.7	825.1	824.6	823.2	821.2	819.2	817.2	815.1	817.2	819.2	821.2
140°	858.7	857.6	856.4	854.8	852.8	850.8	848.8	846.7	848.8	850.8	852.8
142.5°	890.2	889.4	888.7	887.3	885.2	883.2	881.2	879.2	881.2	883.2	885.2
145°	936.2	934.9	933.5	932.1	930.5	928.9	927.3	925.7	927.3	928.9	930.5
147.5°	978.0	977.1	976.2	974.8	972.9	971.1	969.2	967.3	969.2	971.1	972.9
150°	1004.0	1003.1	1002.2	1001.0	999.7	998.3	997.0	995.6	997.0	998.3	999.7
152.5°	1029.5	1028.5	1027.4	1026.2	1024.8	1023.5	1022.1	1020.8	1022.1	1023.5	1024.8
155°	1063.2	1062.5	1061.8	1061.1	1060.5	1059.8	1059.1	1058.4	1059.1	1059.8	1060.5
157.5°	1093.7	1093.3	1092.9	1092.4	1092.0	1091.5	1091.1	1090.6	1091.1	1091.5	1092.0
160°	1112.7	1112.5	1112.2	1111.9	1111.4	1111.0	1110.5	1110.1	1110.5	1111.0	1111.4
162.5°	1128.9	1128.7	1128.4	1128.3	1128.2	1128.1	1128.0	1127.9	1128.0	1128.1	1128.2
165°	1150.6	1150.6	1150.6	1150.7	1150.9	1151.2	1151.4	1151.6	1151.4	1151.2	1150.9
167.5°	1168.3	1168.4	1168.4	1168.8	1169.4	1170.1	1170.8	1171.5	1170.8	1170.1	1169.4
170°	1178.4	1178.6	1178.9	1179.3	1180.0	1180.7	1181.3	1182.0	1181.3	1180.7	1180.0
172.5°	1185.7	1185.9	1186.1	1186.6	1187.3	1187.9	1188.6	1189.3	1188.6	1187.9	1187.3
175°	1194.0	1194.5	1194.9	1195.5	1196.2	1196.9	1197.5	1198.2	1197.5	1196.9	1196.2
177.5°	1198.5	1198.9	1199.2	1199.7	1200.2	1200.8	1201.3	1201.9	1201.3	1200.8	1200.2
180°	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2



TEST NUMBER: P331478

CATALOG NUMBER: S122DIW-S290D970U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1
2.5°	583.3	582.2	578.4	576.4	573.1	570.0	568.0	568.9	569.6	569.3	568.7
5°	566.5	562.2	555.6	550.0	545.9	538.4	535.2	533.6	532.2	530.7	529.1
7.5°	546.6	539.8	530.4	522.3	514.7	505.3	500.0	496.9	493.6	490.0	486.8
10°	532.5	522.9	512.9	501.6	492.5	484.1	476.6	471.6	467.0	462.7	459.6
12.5°	517.6	506.6	494.2	478.7	468.7	456.6	455.5	446.7	439.6	436.9	433.2
15°	493.9	478.4	462.7	444.3	436.4	425.5	418.7	411.8	405.7	401.4	400.3
17.5°	466.9	446.9	431.3	418.1	405.1	393.9	387.6	382.2	377.1	371.4	370.6
20°	446.4	429.1	412.1	400.5	387.1	375.7	368.0	362.6	358.2	354.8	351.9
22.5°	426.9	408.0	392.4	379.8	366.6	357.4	351.3	346.0	342.4	338.7	335.9
25°	395.7	381.0	363.9	349.6	338.7	332.8	327.8	323.3	321.0	318.5	315.3
27.5°	368.4	352.0	336.1	325.0	315.4	310.2	306.6	303.5	301.4	299.9	298.1
30°	349.2	332.6	320.1	309.2	301.2	296.0	293.7	291.9	289.4	288.5	287.6
32.5°	330.6	315.7	305.0	295.5	288.0	284.5	282.5	280.8	278.9	278.0	276.1
35°	304.4	291.9	281.5	276.2	270.1	267.1	265.6	263.3	261.5	260.6	260.3
37.5°	279.7	268.9	262.0	255.3	252.7	250.9	248.7	247.2	246.6	246.5	246.2
40°	263.7	254.9	248.7	243.3	242.2	239.4	237.6	236.3	236.3	236.5	236.3
42.5°	249.2	241.2	235.8	231.1	229.8	228.2	226.3	226.3	226.6	227.4	226.6
45°	227.2	221.5	217.6	215.4	212.9	211.3	211.0	211.7	211.9	212.2	212.9
47.5°	206.9	203.1	199.6	197.1	196.0	195.8	195.5	196.7	197.8	198.2	199.2
50°	194.9	190.6	187.6	186.0	185.1	184.7	185.1	186.5	187.4	188.5	189.2
52.5°	181.5	178.4	176.4	175.1	174.8	175.1	175.1	176.7	178.1	178.6	178.9
55°	162.9	160.6	160.2	158.1	159.0	158.8	159.9	160.8	162.2	163.6	163.8
57.5°	144.3	142.5	141.3	141.5	141.8	142.8	143.7	145.3	146.7	148.2	148.3
60°	132.0	131.1	130.4	130.4	130.8	132.2	133.3	134.9	135.8	136.8	137.4
62.5°	120.7	119.8	119.1	119.5	120.7	121.5	122.8	123.7	124.6	125.5	125.8
65°	102.9	102.5	103.1	103.6	103.8	104.9	106.5	107.2	108.1	108.6	110.2
67.5°	86.5	86.6	86.5	87.1	88.5	88.7	90.2	91.8	92.0	92.9	93.9
70°	75.4	75.9	76.3	76.8	77.9	78.4	79.5	80.2	81.1	81.8	82.5
72.5°	65.2	65.3	65.8	65.7	66.7	67.6	68.6	69.3	70.2	71.1	71.7
75°	50.2	50.2	50.7	50.9	52.0	53.2	52.9	53.4	54.3	55.2	55.7
77.5°	36.7	36.2	36.7	36.9	37.3	38.2	38.4	39.0	40.1	39.8	40.3
80°	27.9	27.3	27.9	28.2	28.2	29.3	29.3	29.8	30.4	29.8	30.4
82.5°	19.9	19.6	20.1	20.2	20.5	20.6	20.9	21.0	21.7	21.4	21.7
85°	10.0	9.8	10.0	9.8	10.0	10.2	10.2	10.0	10.0	10.4	9.8
87.5°	5.5	6.0	6.8	7.8	8.6	9.5	9.2	9.1	9.0	8.5	8.5
90°	11.8	15.6	20.6	25.5	30.5	35.4	35.0	34.5	34.1	33.6	33.5
92.5°	26.0	27.5	28.7	29.9	31.0	32.2	32.3	32.4	32.5	32.6	32.6
95°	61.7	63.0	63.5	63.9	64.4	64.8	64.8	64.8	64.8	64.8	64.6
97.5°	104.1	105.6	106.4	107.3	108.1	109.0	109.0	109.0	109.0	109.0	109.0
100°	135.8	137.1	137.7	138.4	139.1	139.8	139.8	139.8	139.8	139.8	139.7
102.5°	168.4	169.6	170.4	171.3	172.1	173.0	173.2	173.4	173.5	173.7	173.7
105°	220.5	221.0	221.5	221.9	222.4	222.8	223.3	223.7	224.2	224.6	224.9
107.5°	277.2	277.7	277.7	277.7	277.7	277.7	277.9	278.1	278.3	278.4	278.0
110°	314.3	315.0	315.0	315.0	315.0	315.0	315.0	315.0	315.0	315.0	314.7



TEST NUMBER: P331478

CATALOG NUMBER: S122DIW-S290D970U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	353.2	353.8	353.6	353.4	353.3	353.1	352.5	352.0	351.5	350.9	350.4
115°	410.5	411.0	410.5	410.1	409.6	409.2	409.0	408.7	408.5	408.3	407.8
117.5°	469.5	469.7	468.5	467.2	466.0	464.7	464.2	463.6	463.1	462.5	461.9
120°	507.6	507.6	505.8	504.0	502.2	500.4	500.4	500.4	500.4	500.4	500.0
122.5°	543.8	544.3	543.0	541.8	540.5	539.2	538.7	538.2	537.6	537.1	536.6
125°	597.6	598.3	597.6	596.9	596.2	595.6	594.9	594.2	593.5	592.9	592.4
127.5°	652.6	653.5	652.7	651.9	651.1	650.3	649.4	648.6	647.8	647.0	646.2
130°	687.3	688.5	688.1	687.6	687.2	686.7	686.3	685.8	685.4	684.9	684.2
132.5°	722.4	723.6	723.7	723.8	723.9	724.0	723.0	722.0	721.0	720.0	719.2
135°	772.6	774.0	774.5	774.9	775.4	775.8	775.6	775.4	775.2	774.9	774.5
137.5°	823.2	824.6	825.1	825.7	826.3	826.9	826.7	826.5	826.4	826.2	825.6
140°	854.8	856.4	857.6	858.7	859.8	860.9	860.9	860.9	860.9	860.9	860.5
142.5°	887.3	888.7	889.4	890.2	891.0	891.7	891.9	892.1	892.3	892.4	892.1
145°	932.1	933.5	934.9	936.2	937.6	938.9	939.1	939.4	939.6	939.8	939.5
147.5°	974.8	976.2	977.1	978.0	978.9	979.8	980.3	980.8	981.3	981.8	981.6
150°	1001.0	1002.2	1003.1	1004.0	1004.9	1005.8	1006.4	1007.1	1007.8	1008.5	1008.5
152.5°	1026.2	1027.4	1028.5	1029.5	1030.6	1031.7	1032.5	1033.4	1034.3	1035.1	1035.1
155°	1061.1	1061.8	1062.5	1063.2	1063.8	1064.5	1065.6	1066.8	1067.9	1069.0	1069.2
157.5°	1092.4	1092.9	1093.3	1093.7	1094.1	1094.5	1096.0	1097.6	1099.1	1100.6	1100.8
160°	1111.9	1112.2	1112.5	1112.7	1112.9	1113.1	1114.5	1115.8	1117.2	1118.5	1118.8
162.5°	1128.3	1128.4	1128.7	1128.9	1129.1	1129.3	1130.9	1132.4	1133.9	1135.5	1135.7
165°	1150.7	1150.6	1150.6	1150.6	1150.6	1150.6	1152.2	1153.8	1155.3	1156.9	1157.1
167.5°	1168.8	1168.4	1168.4	1168.3	1168.3	1168.2	1169.8	1171.4	1173.0	1174.5	1174.7
170°	1179.3	1178.9	1178.6	1178.4	1178.2	1178.0	1179.5	1181.1	1182.7	1184.3	1184.4
172.5°	1186.6	1186.1	1185.9	1185.7	1185.5	1185.2	1186.8	1188.4	1190.0	1191.5	1191.7
175°	1195.5	1194.9	1194.5	1194.0	1193.6	1193.1	1194.7	1196.3	1197.9	1199.4	1199.6
177.5°	1199.7	1199.2	1198.9	1198.5	1198.2	1197.8	1198.9	1200.0	1201.0	1202.1	1202.1
180°	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2



TEST NUMBER: P331478

CATALOG NUMBER: S122DIW-S290D970U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1
2.5°	566.9	566.5	566.5	564.9	566.5	566.5	566.9	568.7	569.3	569.6	568.9
5°	525.9	525.2	524.1	525.2	524.1	525.2	525.9	529.1	530.7	532.2	533.6
7.5°	485.3	482.6	482.2	479.5	482.2	482.6	485.3	486.8	490.0	493.6	496.9
10°	455.7	453.9	453.6	449.3	453.6	453.9	455.7	459.6	462.7	467.0	471.6
12.5°	433.2	428.8	429.7	427.2	429.7	428.8	433.2	433.2	436.9	439.6	446.7
15°	394.1	394.1	393.2	389.4	393.2	394.1	394.1	400.3	401.4	405.7	411.8
17.5°	366.1	365.6	363.5	364.6	363.5	365.6	366.1	370.6	371.4	377.1	382.2
20°	349.4	348.0	345.3	345.3	345.3	348.0	349.4	351.9	354.8	358.2	362.6
22.5°	333.6	333.5	330.6	331.5	330.6	333.5	333.6	335.9	338.7	342.4	346.0
25°	315.1	313.3	311.9	312.6	311.9	313.3	315.1	315.3	318.5	321.0	323.3
27.5°	297.5	296.5	296.4	294.6	296.4	296.5	297.5	298.1	299.9	301.4	303.5
30°	287.4	285.1	285.5	284.4	285.5	285.1	287.4	287.6	288.5	289.4	291.9
32.5°	275.7	274.9	274.5	273.5	274.5	274.9	275.7	276.1	278.0	278.9	280.8
35°	259.9	260.1	259.0	259.4	259.0	260.1	259.9	260.3	260.6	261.5	263.3
37.5°	246.0	246.7	246.2	246.3	246.2	246.7	246.0	246.2	246.5	246.6	247.2
40°	236.9	236.9	236.9	237.6	236.9	236.9	236.9	236.3	236.5	236.3	236.3
42.5°	228.2	227.8	227.5	227.4	227.5	227.8	228.2	226.6	227.4	226.6	226.3
45°	213.3	214.0	214.2	213.1	214.2	214.0	213.3	212.9	212.2	211.9	211.7
47.5°	199.8	199.9	199.8	200.8	199.8	199.9	199.8	199.2	198.2	197.8	196.7
50°	190.4	189.9	190.4	189.9	190.4	189.9	190.4	189.2	188.5	187.4	186.5
52.5°	180.4	180.5	180.2	180.1	180.2	180.5	180.4	178.9	178.6	178.1	176.7
55°	164.7	165.1	164.9	164.9	164.9	165.1	164.7	163.8	163.6	162.2	160.8
57.5°	148.5	148.9	149.2	148.2	149.2	148.9	148.5	148.3	148.2	146.7	145.3
60°	137.2	138.3	138.1	137.7	138.1	138.3	137.2	137.4	136.8	135.8	134.9
62.5°	126.8	127.3	127.2	127.1	127.2	127.3	126.8	125.8	125.5	124.6	123.7
65°	110.9	111.3	110.6	111.3	110.6	111.3	110.9	110.2	108.6	108.1	107.2
67.5°	93.6	93.8	94.3	94.6	94.3	93.8	93.6	93.9	92.9	92.0	91.8
70°	82.9	82.7	83.4	84.1	83.4	82.7	82.9	82.5	81.8	81.1	80.2
72.5°	71.6	72.1	71.9	72.4	71.9	72.1	71.6	71.7	71.1	70.2	69.3
75°	55.2	55.9	55.7	56.3	55.7	55.9	55.2	55.7	55.2	54.3	53.4
77.5°	39.9	40.0	39.9	40.3	39.9	40.0	39.9	40.3	39.8	40.1	39.0
80°	30.4	30.0	29.5	30.4	29.5	30.0	30.4	30.4	29.8	30.4	29.8
82.5°	21.2	21.4	21.0	21.0	21.0	21.4	21.2	21.7	21.4	21.7	21.0
85°	9.8	9.5	9.1	9.1	9.1	9.5	9.8	9.8	10.4	10.0	10.0
87.5°	8.6	8.4	8.5	8.3	8.5	8.4	8.6	8.5	8.5	9.0	9.1
90°	33.8	34.0	34.2	34.4	34.2	34.0	33.8	33.5	33.6	34.1	34.5
92.5°	32.7	32.7	32.8	32.8	32.8	32.7	32.7	32.6	32.6	32.5	32.4
95°	64.1	63.7	63.2	62.8	63.2	63.7	64.1	64.6	64.8	64.8	64.8
97.5°	108.9	108.9	108.8	108.8	108.8	108.9	108.9	109.0	109.0	109.0	109.0
100°	139.4	139.2	139.0	138.8	139.0	139.2	139.4	139.7	139.8	139.8	139.8
102.5°	173.5	173.2	173.0	172.8	173.0	173.2	173.5	173.7	173.7	173.5	173.4
105°	224.9	224.9	224.9	224.9	224.9	224.9	224.9	224.9	224.6	224.2	223.7
107.5°	277.0	275.9	274.9	273.9	274.9	275.9	277.0	278.0	278.4	278.3	278.1
110°	314.0	313.3	312.6	312.0	312.6	313.3	314.0	314.7	315.0	315.0	315.0



TEST NUMBER: P331478

CATALOG NUMBER: S122DIW-S290D970U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	349.9	349.4	348.9	348.4	348.9	349.4	349.9	350.4	350.9	351.5	352.0
115°	407.2	406.5	405.8	405.1	405.8	406.5	407.2	407.8	408.3	408.5	408.7
117.5°	461.3	460.6	459.9	459.2	459.9	460.6	461.3	461.9	462.5	463.1	463.6
120°	499.3	498.7	498.0	497.3	498.0	498.7	499.3	500.0	500.4	500.4	500.4
122.5°	536.1	535.6	535.1	534.6	535.1	535.6	536.1	536.6	537.1	537.6	538.2
125°	592.2	592.0	591.7	591.5	591.7	592.0	592.2	592.4	592.9	593.5	594.2
127.5°	645.5	644.8	644.1	643.4	644.1	644.8	645.5	646.2	647.0	647.8	648.6
130°	683.3	682.4	681.5	680.6	681.5	682.4	683.3	684.2	684.9	685.4	685.8
132.5°	718.5	717.7	717.0	716.3	717.0	717.7	718.5	719.2	720.0	721.0	722.0
135°	773.8	773.1	772.5	771.8	772.5	773.1	773.8	774.5	774.9	775.2	775.4
137.5°	824.7	823.8	822.9	822.0	822.9	823.8	824.7	825.6	826.2	826.4	826.5
140°	859.6	858.7	857.8	856.9	857.8	858.7	859.6	860.5	860.9	860.9	860.9
142.5°	891.2	890.3	889.4	888.5	889.4	890.3	891.2	892.1	892.4	892.3	892.1
145°	938.6	937.7	936.8	935.9	936.8	937.7	938.6	939.5	939.8	939.6	939.4
147.5°	980.8	979.9	979.1	978.2	979.1	979.9	980.8	981.6	981.8	981.3	980.8
150°	1007.8	1007.1	1006.4	1005.8	1006.4	1007.1	1007.8	1008.5	1008.5	1007.8	1007.1
152.5°	1034.3	1033.4	1032.5	1031.7	1032.5	1033.4	1034.3	1035.1	1035.1	1034.3	1033.4
155°	1068.6	1067.9	1067.2	1066.5	1067.2	1067.9	1068.6	1069.2	1069.0	1067.9	1066.8
157.5°	1099.8	1098.7	1097.6	1096.5	1097.6	1098.7	1099.8	1100.8	1100.6	1099.1	1097.6
160°	1117.9	1117.0	1116.1	1115.2	1116.1	1117.0	1117.9	1118.8	1118.5	1117.2	1115.8
162.5°	1134.6	1133.5	1132.4	1131.4	1132.4	1133.5	1134.6	1135.7	1135.5	1133.9	1132.4
165°	1156.0	1154.9	1153.8	1152.6	1153.8	1154.9	1156.0	1157.1	1156.9	1155.3	1153.8
167.5°	1173.6	1172.4	1171.2	1170.1	1171.2	1172.4	1173.6	1174.7	1174.5	1173.0	1171.4
170°	1183.0	1181.7	1180.3	1179.0	1180.3	1181.7	1183.0	1184.4	1184.3	1182.7	1181.1
172.5°	1190.3	1189.0	1187.6	1186.3	1187.6	1189.0	1190.3	1191.7	1191.5	1190.0	1188.4
175°	1198.2	1196.9	1195.5	1194.2	1195.5	1196.9	1198.2	1199.6	1199.4	1197.9	1196.3
177.5°	1201.0	1200.0	1198.9	1197.8	1198.9	1200.0	1201.0	1202.1	1202.1	1201.0	1200.0
180°	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2



TEST NUMBER: P331478

CATALOG NUMBER: S122DIW-S290D970U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1
2.5°	568.0	570.0	573.1	576.4	578.4	582.2	583.3	585.1	586.7	590.5	594.5
5°	535.2	538.4	545.9	550.0	555.6	562.2	566.5	571.1	576.1	584.7	592.7
7.5°	500.0	505.3	514.7	522.3	530.4	539.8	546.6	555.6	563.1	575.3	586.9
10°	476.6	484.1	492.5	501.6	512.9	522.9	532.5	543.8	552.9	567.5	581.1
12.5°	455.5	456.6	468.7	478.7	494.2	506.6	517.6	532.2	541.1	558.4	572.7
15°	418.7	425.5	436.4	444.3	462.7	478.4	493.9	509.1	519.3	540.7	559.5
17.5°	387.6	393.9	405.1	418.1	431.3	446.9	466.9	483.0	496.9	521.3	543.6
20°	368.0	375.7	387.1	400.5	412.1	429.1	446.4	464.8	479.8	507.3	533.4
22.5°	351.3	357.4	366.6	379.8	392.4	408.0	426.9	447.0	462.7	492.4	518.8
25°	327.8	332.8	338.7	349.6	363.9	381.0	395.7	417.8	440.7	468.4	500.4
27.5°	306.6	310.2	315.4	325.0	336.1	352.0	368.4	389.3	412.4	442.5	476.3
30°	293.7	296.0	301.2	309.2	320.1	332.6	349.2	369.1	392.8	423.2	456.8
32.5°	282.5	284.5	288.0	295.5	305.0	315.7	330.6	350.6	373.1	403.0	440.3
35°	265.6	267.1	270.1	276.2	281.5	291.9	304.4	322.6	343.7	372.3	410.9
37.5°	248.7	250.9	252.7	255.3	262.0	268.9	279.7	295.1	315.8	344.7	381.5
40°	237.6	239.4	242.2	243.3	248.7	254.9	263.7	277.8	298.7	325.1	361.0
42.5°	226.3	228.2	229.8	231.1	235.8	241.2	249.2	261.3	279.8	305.4	341.0
45°	211.0	211.3	212.9	215.4	217.6	221.5	227.2	237.6	251.9	276.0	308.3
47.5°	195.5	195.8	196.0	197.1	199.6	203.1	206.9	215.4	228.2	247.4	278.8
50°	185.1	184.7	185.1	186.0	187.6	190.6	194.9	201.0	211.5	229.4	258.3
52.5°	175.1	175.1	174.8	175.1	176.4	178.4	181.5	186.7	196.0	212.5	237.9
55°	159.9	158.8	159.0	158.1	160.2	160.6	162.9	167.2	175.4	186.7	210.6
57.5°	143.7	142.8	141.8	141.5	141.3	142.5	144.3	147.7	154.0	164.0	183.3
60°	133.3	132.2	130.8	130.4	130.4	131.1	132.0	134.5	140.4	149.2	165.1
62.5°	122.8	121.5	120.7	119.5	119.1	119.8	120.7	122.5	126.8	135.1	148.8
65°	106.5	104.9	103.8	103.6	103.1	102.5	102.9	104.7	108.1	114.7	125.6
67.5°	90.2	88.7	88.5	87.1	86.5	86.6	86.5	88.0	90.1	95.8	103.9
70°	79.5	78.4	77.9	76.8	76.3	75.9	75.4	76.8	78.8	83.6	90.6
72.5°	68.6	67.6	66.7	65.7	65.8	65.3	65.2	66.1	67.7	72.1	77.6
75°	52.9	53.2	52.0	50.9	50.7	50.2	50.2	50.9	51.6	55.0	59.3
77.5°	38.4	38.2	37.3	36.9	36.7	36.2	36.7	37.1	37.5	39.8	42.9
80°	29.3	29.3	28.2	28.2	27.9	27.3	27.9	27.5	28.4	30.7	32.9
82.5°	20.9	20.6	20.5	20.2	20.1	19.6	19.9	20.4	20.8	22.3	23.7
85°	10.2	10.2	10.0	9.8	10.0	9.8	10.0	10.2	10.4	11.1	12.3
87.5°	9.2	9.5	8.6	7.8	6.8	6.0	5.5	5.1	4.9	4.6	4.2
90°	35.0	35.4	30.5	25.5	20.6	15.6	11.8	9.1	6.4	3.7	1.0
92.5°	32.3	32.2	31.0	29.9	28.7	27.5	26.0	24.0	22.0	20.0	18.0
95°	64.8	64.8	64.4	63.9	63.5	63.0	61.7	59.4	57.2	54.9	52.7
97.5°	109.0	109.0	108.1	107.3	106.4	105.6	104.1	102.2	100.2	98.2	96.2
100°	139.8	139.8	139.1	138.4	137.7	137.1	135.8	134.0	132.2	130.4	128.6
102.5°	173.2	173.0	172.1	171.3	170.4	169.6	168.4	167.0	165.5	164.1	162.7
105°	223.3	222.8	222.4	221.9	221.5	221.0	220.5	219.8	219.1	218.4	217.8
107.5°	277.9	277.7	277.7	277.7	277.7	277.7	277.2	276.2	275.2	274.3	273.3
110°	315.0	315.0	315.0	315.0	315.0	315.0	314.3	313.0	311.6	310.3	308.9



TEST NUMBER: P331478

CATALOG NUMBER: S122DIW-S290D970U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	352.5	353.1	353.3	353.4	353.6	353.8	353.2	351.9	350.5	349.2	347.8
115°	409.0	409.2	409.6	410.1	410.5	411.0	410.5	409.2	407.8	406.5	405.1
117.5°	464.2	464.7	466.0	467.2	468.5	469.7	469.5	467.7	465.9	464.1	462.3
120°	500.4	500.4	502.2	504.0	505.8	507.6	507.6	505.8	504.0	502.2	500.4
122.5°	538.7	539.2	540.5	541.8	543.0	544.3	543.8	541.7	539.5	537.4	535.2
125°	594.9	595.6	596.2	596.9	597.6	598.3	597.6	595.6	593.5	591.5	589.5
127.5°	649.4	650.3	651.1	651.9	652.7	653.5	652.6	650.1	647.5	644.9	642.4
130°	686.3	686.7	687.2	687.6	688.1	688.5	687.3	684.4	681.4	678.5	675.6
132.5°	723.0	724.0	723.9	723.8	723.7	723.6	722.4	720.0	717.6	715.2	712.8
135°	775.6	775.8	775.4	774.9	774.5	774.0	772.6	770.1	767.6	765.2	762.7
137.5°	826.7	826.9	826.3	825.7	825.1	824.6	823.2	821.2	819.2	817.2	815.1
140°	860.9	860.9	859.8	858.7	857.6	856.4	854.8	852.8	850.8	848.8	846.7
142.5°	891.9	891.7	891.0	890.2	889.4	888.7	887.3	885.2	883.2	881.2	879.2
145°	939.1	938.9	937.6	936.2	934.9	933.5	932.1	930.5	928.9	927.3	925.7
147.5°	980.3	979.8	978.9	978.0	977.1	976.2	974.8	972.9	971.1	969.2	967.3
150°	1006.4	1005.8	1004.9	1004.0	1003.1	1002.2	1001.0	999.7	998.3	997.0	995.6
152.5°	1032.5	1031.7	1030.6	1029.5	1028.5	1027.4	1026.2	1024.8	1023.5	1022.1	1020.8
155°	1065.6	1064.5	1063.8	1063.2	1062.5	1061.8	1061.1	1060.5	1059.8	1059.1	1058.4
157.5°	1096.0	1094.5	1094.1	1093.7	1093.3	1092.9	1092.4	1092.0	1091.5	1091.1	1090.6
160°	1114.5	1113.1	1112.9	1112.7	1112.5	1112.2	1111.9	1111.4	1111.0	1110.5	1110.1
162.5°	1130.9	1129.3	1129.1	1128.9	1128.7	1128.4	1128.3	1128.2	1128.1	1128.0	1127.9
165°	1152.2	1150.6	1150.6	1150.6	1150.6	1150.6	1150.7	1150.9	1151.2	1151.4	1151.6
167.5°	1169.8	1168.2	1168.3	1168.3	1168.4	1168.4	1168.8	1169.4	1170.1	1170.8	1171.5
170°	1179.5	1178.0	1178.2	1178.4	1178.6	1178.9	1179.3	1180.0	1180.7	1181.3	1182.0
172.5°	1186.8	1185.2	1185.5	1185.7	1185.9	1186.1	1186.6	1187.3	1187.9	1188.6	1189.3
175°	1194.7	1193.1	1193.6	1194.0	1194.5	1194.9	1195.5	1196.2	1196.9	1197.5	1198.2
177.5°	1198.9	1197.8	1198.2	1198.5	1198.9	1199.2	1199.7	1200.2	1200.8	1201.3	1201.9
180°	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2



TEST NUMBER: P331478

CATALOG NUMBER: S122DIW-S290D970U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1	591.1
2.5°	594.2	595.1	598.0	600.9	604.2	605.1	606.5	605.3	604.9	608.3	610.9
5°	595.9	599.9	607.9	615.2	621.3	625.6	630.2	632.0	635.4	640.1	646.1
7.5°	593.9	601.9	614.4	625.0	636.5	644.8	651.3	656.9	663.6	672.6	682.5
10°	591.8	602.4	617.7	630.6	644.7	655.4	664.2	672.9	682.9	695.4	708.3
12.5°	587.8	600.4	619.5	634.8	652.9	663.4	675.3	693.9	704.7	722.1	740.3
15°	579.7	593.8	620.4	639.2	659.7	679.7	701.7	719.4	737.1	747.4	773.0
17.5°	567.8	588.4	617.9	639.9	665.9	697.3	722.1	742.2	762.6	779.2	792.1
20°	558.1	580.6	614.3	640.6	671.5	705.3	733.7	754.2	771.9	785.8	793.7
22.5°	546.0	574.3	607.0	637.9	677.3	710.8	740.6	756.7	771.5	778.3	781.4
25°	526.8	560.9	597.9	635.6	680.1	715.6	742.8	752.6	756.9	750.3	739.4
27.5°	506.1	544.1	587.4	631.3	678.4	712.5	732.0	730.5	723.2	701.8	684.8
30°	490.7	532.5	579.0	627.0	674.2	707.4	718.7	707.4	690.8	667.0	642.6
32.5°	474.5	517.8	570.1	620.8	666.6	695.8	698.2	678.7	653.0	625.9	595.6
35°	450.0	496.8	553.4	607.0	650.4	668.8	657.9	623.3	592.9	555.9	514.5
37.5°	422.3	474.0	530.7	586.8	626.1	630.9	603.8	567.5	524.5	481.0	432.3
40°	401.6	456.4	514.8	571.3	606.1	601.1	566.5	526.6	475.5	422.3	377.1
42.5°	383.1	437.8	497.3	552.8	580.6	566.9	526.6	477.5	422.6	372.5	331.1
45°	351.0	407.3	468.2	521.8	537.7	512.9	459.6	405.0	351.0	309.2	276.5
47.5°	319.8	375.5	435.8	482.9	488.5	455.2	396.9	340.8	294.3	260.3	237.2
50°	296.9	352.8	412.5	454.6	452.7	412.5	352.6	299.2	260.3	232.8	217.4
52.5°	276.4	329.2	386.5	424.8	415.1	371.3	314.0	266.6	234.7	213.2	199.2
55°	244.4	293.3	347.8	378.5	360.7	312.1	263.7	225.6	201.9	185.8	174.9
57.5°	212.7	258.5	305.2	324.1	304.5	259.6	219.3	191.6	173.8	161.9	154.8
60°	193.1	233.1	274.6	291.0	267.6	227.6	195.8	171.1	156.7	147.0	140.6
62.5°	173.5	209.3	248.5	257.4	236.0	202.2	174.0	153.4	141.7	133.0	127.0
65°	146.7	176.1	205.8	211.7	192.0	165.8	143.6	130.2	119.7	113.4	108.6
67.5°	120.4	143.9	165.0	169.7	152.4	134.3	118.2	106.5	99.5	94.2	90.1
70°	104.7	123.4	140.6	144.5	130.6	114.5	102.2	92.9	86.5	82.0	78.1
72.5°	88.2	103.7	118.1	120.7	109.4	97.0	87.0	79.6	74.0	71.1	67.4
75°	67.5	76.6	87.7	88.4	80.9	73.4	65.7	60.9	57.9	54.3	52.5
77.5°	47.6	54.7	61.1	62.3	57.9	52.8	48.5	44.7	42.2	40.5	38.8
80°	36.3	42.0	44.8	46.3	43.2	39.5	37.0	34.5	32.9	31.8	30.7
82.5°	26.0	29.5	32.0	33.3	31.5	29.3	26.9	25.4	24.2	23.3	22.9
85°	13.2	14.8	16.4	16.8	16.4	15.4	14.1	14.1	13.4	13.2	13.2
87.5°	5.3	6.6	7.1	8.2	8.6	9.6	10.6	11.4	12.2	11.9	11.6
90°	3.7	6.4	9.1	11.8	15.6	20.6	25.5	30.5	35.4	35.0	34.5
92.5°	20.0	22.0	24.0	26.0	27.5	28.7	29.9	31.0	32.2	32.3	32.4
95°	54.9	57.2	59.4	61.7	63.0	63.5	63.9	64.4	64.8	64.8	64.8
97.5°	98.2	100.2	102.2	104.1	105.6	106.4	107.3	108.1	109.0	109.0	109.0
100°	130.4	132.2	134.0	135.8	137.1	137.7	138.4	139.1	139.8	139.8	139.8
102.5°	164.1	165.5	167.0	168.4	169.6	170.4	171.3	172.1	173.0	173.2	173.4
105°	218.4	219.1	219.8	220.5	221.0	221.5	221.9	222.4	222.8	223.3	223.7
107.5°	274.3	275.2	276.2	277.2	277.7	277.7	277.7	277.7	277.7	277.9	278.1
110°	310.3	311.6	313.0	314.3	315.0	315.0	315.0	315.0	315.0	315.0	315.0



TEST NUMBER: P331478

CATALOG NUMBER: S122DIW-S290D970U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	349.2	350.5	351.9	353.2	353.8	353.6	353.4	353.3	353.1	352.5	352.0
115°	406.5	407.8	409.2	410.5	411.0	410.5	410.1	409.6	409.2	409.0	408.7
117.5°	464.1	465.9	467.7	469.5	469.7	468.5	467.2	466.0	464.7	464.2	463.6
120°	502.2	504.0	505.8	507.6	507.6	505.8	504.0	502.2	500.4	500.4	500.4
122.5°	537.4	539.5	541.7	543.8	544.3	543.0	541.8	540.5	539.2	538.7	538.2
125°	591.5	593.5	595.6	597.6	598.3	597.6	596.9	596.2	595.6	594.9	594.2
127.5°	644.9	647.5	650.1	652.6	653.5	652.7	651.9	651.1	650.3	649.4	648.6
130°	678.5	681.4	684.4	687.3	688.5	688.1	687.6	687.2	686.7	686.3	685.8
132.5°	715.2	717.6	720.0	722.4	723.6	723.7	723.8	723.9	724.0	723.0	722.0
135°	765.2	767.6	770.1	772.6	774.0	774.5	774.9	775.4	775.8	775.6	775.4
137.5°	817.2	819.2	821.2	823.2	824.6	825.1	825.7	826.3	826.9	826.7	826.5
140°	848.8	850.8	852.8	854.8	856.4	857.6	858.7	859.8	860.9	860.9	860.9
142.5°	881.2	883.2	885.2	887.3	888.7	889.4	890.2	891.0	891.7	891.9	892.1
145°	927.3	928.9	930.5	932.1	933.5	934.9	936.2	937.6	938.9	939.1	939.4
147.5°	969.2	971.1	972.9	974.8	976.2	977.1	978.0	978.9	979.8	980.3	980.8
150°	997.0	998.3	999.7	1001.0	1002.2	1003.1	1004.0	1004.9	1005.8	1006.4	1007.1
152.5°	1022.1	1023.5	1024.8	1026.2	1027.4	1028.5	1029.5	1030.6	1031.7	1032.5	1033.4
155°	1059.1	1059.8	1060.5	1061.1	1061.8	1062.5	1063.2	1063.8	1064.5	1065.6	1066.8
157.5°	1091.1	1091.5	1092.0	1092.4	1092.9	1093.3	1093.7	1094.1	1094.5	1096.0	1097.6
160°	1110.5	1111.0	1111.4	1111.9	1112.2	1112.5	1112.7	1112.9	1113.1	1114.5	1115.8
162.5°	1128.0	1128.1	1128.2	1128.3	1128.4	1128.7	1128.9	1129.1	1129.3	1130.9	1132.4
165°	1151.4	1151.2	1150.9	1150.7	1150.6	1150.6	1150.6	1150.6	1150.6	1152.2	1153.8
167.5°	1170.8	1170.1	1169.4	1168.8	1168.4	1168.4	1168.3	1168.3	1168.2	1169.8	1171.4
170°	1181.3	1180.7	1180.0	1179.3	1178.9	1178.6	1178.4	1178.2	1178.0	1179.5	1181.1
172.5°	1188.6	1187.9	1187.3	1186.6	1186.1	1185.9	1185.7	1185.5	1185.2	1186.8	1188.4
175°	1197.5	1196.9	1196.2	1195.5	1194.9	1194.5	1194.0	1193.6	1193.1	1194.7	1196.3
177.5°	1201.3	1200.8	1200.2	1199.7	1199.2	1198.9	1198.5	1198.2	1197.8	1198.9	1200.0
180°	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2



TEST NUMBER: P331478

CATALOG NUMBER: S122DIW-S290D970U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	591.1	591.1	591.1	591.1	591.1	591.1	591.1
2.5°	613.1	615.6	615.6	616.0	618.9	618.5	618.3
5°	652.4	656.3	656.7	660.8	663.5	662.6	660.1
7.5°	689.5	696.7	702.2	705.2	708.8	711.0	710.0
10°	719.0	729.4	735.8	740.1	745.3	749.2	747.8
12.5°	745.7	758.1	766.9	774.3	774.9	779.9	776.5
15°	787.4	800.5	801.9	807.3	811.7	811.2	811.4
17.5°	801.1	805.3	806.2	806.3	806.4	804.8	801.3
20°	796.2	794.6	790.8	787.8	782.6	781.9	777.4
22.5°	772.9	767.9	758.2	751.8	743.7	741.6	740.3
25°	727.2	716.0	700.6	685.8	681.7	673.8	676.0
27.5°	664.3	647.0	630.2	618.3	607.4	595.5	598.9
30°	620.2	600.6	577.0	558.8	547.2	535.9	533.8
32.5°	567.5	538.8	512.5	496.5	478.7	471.5	463.7
35°	476.6	448.6	422.5	400.0	387.1	377.1	368.0
37.5°	394.9	362.7	341.6	323.4	314.0	308.3	309.8
40°	344.2	316.0	300.5	286.7	278.0	274.0	274.9
42.5°	303.1	282.0	269.3	259.8	253.7	251.4	250.9
45°	256.5	244.7	234.2	228.8	225.8	223.3	221.7
47.5°	224.7	215.0	209.1	205.9	203.3	200.8	200.7
50°	205.6	199.2	195.1	191.7	189.7	187.9	189.5
52.5°	191.0	185.2	181.1	178.1	177.3	175.7	175.6
55°	169.5	164.9	162.0	159.2	157.9	157.0	155.8
57.5°	149.8	145.5	142.8	141.1	138.5	137.6	137.2
60°	135.8	132.4	129.7	127.4	126.3	124.5	124.5
62.5°	122.9	119.5	117.0	115.3	113.4	112.7	112.9
65°	104.3	101.5	99.0	97.2	96.8	95.4	95.9
67.5°	87.1	85.3	82.6	81.6	80.8	80.1	79.5
70°	75.6	73.8	72.5	71.1	70.4	70.4	70.4
72.5°	66.0	63.8	63.0	61.3	61.7	61.0	60.2
75°	51.1	49.7	49.1	48.4	47.3	47.3	47.3
77.5°	37.6	37.2	36.4	35.7	35.4	35.2	35.3
80°	29.1	28.8	28.4	28.4	27.9	27.7	27.3
82.5°	22.4	21.8	21.5	21.3	21.2	21.2	21.1
85°	12.7	12.3	12.3	12.5	12.0	12.0	12.3
87.5°	11.7	11.6	11.4	11.5	11.7	11.6	11.6
90°	34.1	33.6	33.5	33.8	34.0	34.2	34.4
92.5°	32.5	32.6	32.6	32.7	32.7	32.8	32.8
95°	64.8	64.8	64.6	64.1	63.7	63.2	62.8
97.5°	109.0	109.0	109.0	108.9	108.9	108.8	108.8
100°	139.8	139.8	139.7	139.4	139.2	139.0	138.8
102.5°	173.5	173.7	173.7	173.5	173.2	173.0	172.8
105°	224.2	224.6	224.9	224.9	224.9	224.9	224.9
107.5°	278.3	278.4	278.0	277.0	275.9	274.9	273.9
110°	315.0	315.0	314.7	314.0	313.3	312.6	312.0



TEST NUMBER: P331478

CATALOG NUMBER: S122DIW-S290D970U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	351.5	350.9	350.4	349.9	349.4	348.9	348.4
115°	408.5	408.3	407.8	407.2	406.5	405.8	405.1
117.5°	463.1	462.5	461.9	461.3	460.6	459.9	459.2
120°	500.4	500.4	500.0	499.3	498.7	498.0	497.3
122.5°	537.6	537.1	536.6	536.1	535.6	535.1	534.6
125°	593.5	592.9	592.4	592.2	592.0	591.7	591.5
127.5°	647.8	647.0	646.2	645.5	644.8	644.1	643.4
130°	685.4	684.9	684.2	683.3	682.4	681.5	680.6
132.5°	721.0	720.0	719.2	718.5	717.7	717.0	716.3
135°	775.2	774.9	774.5	773.8	773.1	772.5	771.8
137.5°	826.4	826.2	825.6	824.7	823.8	822.9	822.0
140°	860.9	860.9	860.5	859.6	858.7	857.8	856.9
142.5°	892.3	892.4	892.1	891.2	890.3	889.4	888.5
145°	939.6	939.8	939.5	938.6	937.7	936.8	935.9
147.5°	981.3	981.8	981.6	980.8	979.9	979.1	978.2
150°	1007.8	1008.5	1008.5	1007.8	1007.1	1006.4	1005.8
152.5°	1034.3	1035.1	1035.1	1034.3	1033.4	1032.5	1031.7
155°	1067.9	1069.0	1069.2	1068.6	1067.9	1067.2	1066.5
157.5°	1099.1	1100.6	1100.8	1099.8	1098.7	1097.6	1096.5
160°	1117.2	1118.5	1118.8	1117.9	1117.0	1116.1	1115.2
162.5°	1133.9	1135.5	1135.7	1134.6	1133.5	1132.4	1131.4
165°	1155.3	1156.9	1157.1	1156.0	1154.9	1153.8	1152.6
167.5°	1173.0	1174.5	1174.7	1173.6	1172.4	1171.2	1170.1
170°	1182.7	1184.3	1184.4	1183.0	1181.7	1180.3	1179.0
172.5°	1190.0	1191.5	1191.7	1190.3	1189.0	1187.6	1186.3
175°	1197.9	1199.4	1199.6	1198.2	1196.9	1195.5	1194.2
177.5°	1201.0	1202.1	1202.1	1201.0	1200.0	1198.9	1197.8
180°	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2

(END OF REPORT)