

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331769

Luminaire Tested: **S122RDIW-S290D710U835-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331769
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S290D710U835-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 710 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3967.4 lumens
Efficiency: N/A
Efficacy: 130.5 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 30.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331769

CATALOG NUMBER: S122RDIW-S290D710U835-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331769

CATALOG NUMBER: S122RDIW-S290D710U835-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36	29								
1	93	89	86	83	84	80	77	75	63	61	59	47	46	45	33	32	32	25								
2	85	79	73	68	76	71	66	62	56	53	50	42	40	38	29	28	27	22								
3	78	69	63	57	70	63	57	52	50	46	42	38	35	33	26	25	24	19								
4	72	62	54	49	64	56	49	45	44	40	36	34	31	29	24	22	21	17								
5	66	55	48	42	59	50	43	38	40	35	32	31	27	25	22	20	18	15								
6	61	49	42	36	54	45	38	34	36	31	28	28	25	22	20	18	17	13								
7	56	45	37	32	50	41	34	30	33	28	25	25	22	20	18	16	15	12								
8	52	41	33	28	47	37	31	26	30	25	22	23	20	18	17	15	13	11								
9	49	37	30	25	44	34	28	23	27	23	20	21	18	16	16	14	12	10								
10	45	34	27	23	41	31	25	21	25	21	18	20	17	14	15	13	11	9								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10555	10555	10555	10555
5°	11788	10621	9418	10621
10°	13080	10547	8163	10547
15°	13722	10392	6432	10392
20°	11897	10163	5565	10163
25°	7801	9850	4969	9850
30°	5252	9469	4497	9469
35°	4254	8990	4056	8990
40°	3781	8469	3754	8469
45°	3423	7857	3350	7857
50°	3115	7252	3105	7252
55°	2928	6579	2891	6579
60°	2451	5964	2422	5964
65°	2067	5414	2342	5414
70°	1907	4834	2209	4834
75°	1784	4211	2040	4211
80°	1646	3468	1813	3468
85°	1519	2742	1593	2742



TEST NUMBER: P331769

CATALOG NUMBER: S122RDIW-S290D710U835-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	62.0	1.6
10°-20°	172.7	4.4
20°-30°	222.5	5.6
30°-40°	211.5	5.3
40°-50°	181.1	4.6
50°-60°	137.9	3.5
60°-70°	87.2	2.2
70°-80°	43.5	1.1
80°-90°	13.7	0.3
90°-100°	32.3	0.8
100°-110°	118.3	3.0
110°-120°	316.3	8.0
120°-130°	522.2	13.2
130°-140°	555.4	14.0
140°-150°	516.2	13.0
150°-160°	415.0	10.5
160°-170°	267.4	6.7
170°-180°	92.1	2.3
0°-30°	457.2	11.5
0°-40°	668.6	16.9
0°-60°	987.7	24.9
0°-90°	1132.2	28.5
90°-120°	467.0	11.8
90°-150°	2060.7	51.9
90°-180°	2835.0	71.5
0°-180°	3967.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	654	654	654	654	654	
5°	727	655	581	655	727	72
15°	821	622	385	622	821	221
25°	438	553	279	553	438	208
35°	216	456	206	456	216	138
45°	150	344	147	344	150	116
55°	104	234	103	234	104	91
65°	54	142	61	142	54	55
75°	29	68	33	68	29	30
85°	8	15	9	15	8	9
90°	19	1	19	1	19	9
95°	30	46	30	46	30	28
105°	53	213	53	213	53	55
115°	57	402	57	402	57	144
125°	598	569	598	569	598	518
135°	727	704	727	704	727	561
145°	830	817	830	817	830	519
155°	900	900	900	900	900	415
165°	946	948	946	948	946	267
175°	964	970	964	970	964	92
180°	968	968	968	968	968	



TEST NUMBER: P331769

CATALOG NUMBER: S122RDIW-S290D710U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7
2.5°	680.3	680.8	681.4	680.1	680.1	679.0	676.6	674.8	669.7	669.0	669.0
5°	727.3	726.9	727.8	724.8	720.8	719.8	715.5	709.8	703.9	697.4	696.0
7.5°	774.1	773.4	771.6	771.1	768.0	761.1	754.2	746.8	737.0	727.4	722.6
10°	797.8	805.3	800.7	792.8	794.3	783.7	778.0	768.2	760.0	745.7	742.6
12.5°	821.0	824.0	822.5	818.0	816.0	808.6	800.9	792.4	777.3	764.5	753.3
15°	820.9	825.2	826.4	825.0	826.1	825.7	821.6	814.6	801.4	787.3	775.0
17.5°	760.3	763.3	770.8	775.8	782.2	795.6	802.3	804.8	802.9	794.8	786.2
20°	692.4	687.4	708.3	718.9	728.0	750.7	770.3	777.8	789.8	789.6	787.3
22.5°	596.0	597.2	617.0	629.7	656.2	679.0	701.2	729.4	752.7	768.1	777.1
25°	437.9	446.6	466.3	483.6	513.1	555.4	593.8	638.3	680.3	713.5	745.1
27.5°	328.9	329.6	345.2	361.2	378.7	413.3	461.7	514.8	574.7	624.2	681.0
30°	281.7	280.3	286.9	296.7	311.7	338.5	374.8	427.0	486.8	561.3	627.6
32.5°	248.2	248.3	253.3	260.5	272.9	291.0	315.9	358.4	414.8	488.1	565.8
35°	215.8	215.6	219.2	224.4	229.6	241.2	258.3	280.5	319.4	387.7	467.2
37.5°	192.5	193.5	195.3	198.6	204.3	210.8	221.0	236.0	263.6	304.1	370.9
40°	179.4	179.9	182.4	185.1	188.5	193.5	201.9	214.0	234.2	266.4	315.3
42.5°	167.5	167.9	169.7	172.2	174.9	179.9	186.9	197.3	213.7	238.8	279.1
45°	149.9	149.9	151.5	152.6	155.6	160.1	165.8	174.5	185.8	204.4	231.2
47.5°	133.5	133.5	134.6	136.5	138.4	141.9	147.5	154.6	162.8	177.2	200.1
50°	124.0	124.3	124.9	126.5	127.7	130.8	135.2	141.3	149.9	161.1	180.1
52.5°	116.4	116.3	117.1	117.8	118.6	120.8	124.1	129.5	137.2	146.9	162.7
55°	104.0	103.1	104.5	105.6	106.3	107.2	109.0	112.4	119.0	127.2	139.0
57.5°	88.6	88.2	89.2	90.2	92.4	94.8	96.4	98.5	101.9	107.8	119.5
60°	75.9	75.9	77.9	78.6	81.1	84.3	87.5	89.3	92.7	96.5	105.2
62.5°	64.6	64.8	65.7	66.4	67.8	71.7	76.2	80.2	83.4	87.1	92.8
65°	54.1	54.5	54.5	55.0	55.9	56.8	58.6	61.8	67.5	72.7	77.0
67.5°	45.9	46.0	46.2	46.6	46.8	47.8	48.6	50.0	51.3	56.2	61.6
70°	40.4	41.1	40.9	41.3	41.6	42.0	42.9	43.6	45.7	46.8	50.0
72.5°	35.3	35.8	35.8	36.1	36.7	36.8	37.5	38.2	39.5	40.4	42.2
75°	28.6	28.4	28.6	29.1	29.3	29.5	29.5	30.4	31.1	32.0	33.2
77.5°	22.1	22.3	22.3	22.3	22.4	22.8	22.7	23.1	23.8	24.3	24.8
80°	17.7	17.9	17.7	17.9	18.2	18.4	18.2	18.4	19.1	19.5	19.5
82.5°	13.7	13.8	13.9	13.9	14.0	14.0	14.4	14.4	14.9	14.8	15.0
85°	8.2	8.0	8.0	8.0	8.2	8.4	8.2	8.2	8.4	8.4	8.4
87.5°	6.7	6.8	6.7	6.7	6.6	6.5	6.4	6.4	6.0	6.1	5.6
90°	18.9	18.6	18.3	18.0	17.7	17.1	16.3	15.6	14.8	14.0	12.8
92.5°	18.9	18.7	18.5	18.3	18.2	17.9	17.5	17.1	16.6	16.2	15.6
95°	30.1	30.3	30.4	30.6	30.7	30.4	29.6	28.9	28.1	27.3	26.2
97.5°	40.2	40.0	39.8	39.6	39.4	39.0	38.4	37.8	37.2	36.5	34.0
100°	46.9	46.6	46.3	46.0	45.7	44.9	43.6	42.4	41.1	39.9	37.3
102.5°	50.3	49.8	49.4	49.0	48.5	47.5	45.9	44.3	42.6	41.0	38.1
105°	53.2	52.6	52.0	51.3	50.7	49.5	47.8	46.1	44.4	42.7	40.2
107.5°	54.7	54.1	53.5	52.9	52.3	52.8	54.6	56.3	58.0	59.8	61.7
110°	55.3	54.7	54.1	53.4	52.8	60.3	75.8	91.4	107.0	122.5	167.5



TEST NUMBER: P331769

CATALOG NUMBER: S122RDIW-S290D710U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	55.9	55.4	54.9	54.4	53.9	82.0	138.8	195.5	252.3	309.0	320.1
115°	57.4	68.6	79.8	91.0	102.2	143.8	215.8	287.9	359.9	431.9	428.0
117.5°	234.4	271.2	308.0	344.8	381.6	408.7	426.1	443.6	461.0	478.4	475.7
120°	427.0	448.0	469.0	490.0	511.0	520.6	518.7	516.9	515.0	513.1	510.3
122.5°	532.9	537.0	541.0	545.1	549.2	550.7	549.5	548.4	547.3	546.2	543.1
125°	598.5	598.1	597.6	597.1	596.7	595.9	594.8	593.7	592.6	591.5	588.6
127.5°	640.0	639.9	639.8	639.7	639.6	638.8	637.2	635.6	634.0	632.4	630.2
130°	665.8	665.9	666.1	666.2	666.4	665.6	663.9	662.2	660.5	658.8	657.0
132.5°	691.0	691.1	691.3	691.4	691.6	690.9	689.5	688.0	686.5	685.1	683.4
135°	727.4	727.7	728.0	728.3	728.6	728.0	726.4	724.9	723.3	721.8	720.4
137.5°	760.5	761.1	761.6	762.1	762.7	762.2	760.6	759.1	757.6	756.1	754.5
140°	781.3	782.0	782.8	783.6	784.4	784.1	782.7	781.3	779.9	778.5	776.7
142.5°	801.4	802.2	803.0	803.8	804.5	804.3	803.0	801.7	800.5	799.2	797.2
145°	829.6	830.3	831.1	831.9	832.7	832.5	831.4	830.3	829.3	828.2	825.5
147.5°	854.3	855.0	855.7	856.3	857.0	856.9	856.1	855.3	854.5	853.6	851.0
150°	869.5	870.2	871.0	871.8	872.6	872.5	871.6	870.6	869.7	868.8	866.3
152.5°	882.3	883.4	884.4	885.4	886.5	886.5	885.6	884.6	883.7	882.8	880.4
155°	900.3	901.5	902.8	904.0	905.2	905.4	904.5	903.5	902.6	901.7	899.8
157.5°	916.6	917.9	919.1	920.3	921.5	921.6	920.5	919.5	918.4	917.3	916.0
160°	926.2	927.3	928.3	929.4	930.5	930.6	929.7	928.7	927.8	926.9	925.9
162.5°	934.0	935.3	936.7	938.0	939.4	939.5	938.4	937.4	936.3	935.3	934.5
165°	945.8	946.9	948.0	949.0	950.1	950.1	949.0	948.0	946.9	945.8	945.3
167.5°	953.2	954.6	956.0	957.4	958.8	958.9	957.9	956.8	955.7	954.6	954.2
170°	957.7	959.1	960.5	961.9	963.3	963.4	962.3	961.3	960.2	959.1	958.8
172.5°	961.0	962.4	963.8	965.2	966.6	966.8	965.7	964.6	963.5	962.4	962.1
175°	964.0	965.5	967.1	968.6	970.2	970.4	969.3	968.3	967.2	966.1	965.8
177.5°	965.8	966.9	968.0	969.2	970.3	970.4	969.5	968.7	967.8	966.9	966.8
180°	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5



TEST NUMBER: P331769

CATALOG NUMBER: S122RDIW-S290D710U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7
2.5°	669.4	667.9	666.6	663.4	661.7	658.1	657.6	657.4	652.7	648.1	646.8
5°	692.4	688.7	683.3	676.9	670.3	663.5	659.0	655.3	646.2	637.6	632.6
7.5°	715.5	707.7	698.3	686.3	676.2	665.0	656.6	649.1	636.2	623.8	615.5
10°	732.8	720.1	707.6	691.0	678.0	665.3	653.5	643.3	628.8	612.4	600.8
12.5°	743.5	729.5	712.3	696.1	679.3	663.1	647.3	634.2	617.1	600.2	586.5
15°	758.0	743.0	722.1	698.9	677.4	656.2	638.1	621.7	599.5	579.2	562.4
17.5°	769.9	749.2	726.8	700.0	675.0	648.2	624.8	603.9	579.1	554.7	534.9
20°	773.7	753.2	727.3	700.5	671.0	639.4	614.2	591.5	564.9	538.3	515.6
22.5°	771.3	755.4	726.6	694.5	664.3	631.3	602.8	576.4	546.9	519.8	493.5
25°	755.3	749.8	722.6	687.6	653.1	614.7	581.7	552.9	519.3	490.2	461.6
27.5°	717.9	729.7	712.8	675.5	637.1	596.0	558.9	526.1	491.2	458.5	430.0
30°	681.9	708.9	701.7	667.1	624.2	583.8	542.2	507.9	470.7	437.0	408.9
32.5°	632.7	677.3	684.4	655.5	611.1	566.7	523.1	489.0	450.1	414.7	387.2
35°	554.2	621.0	651.7	633.3	588.8	540.8	495.9	456.1	417.0	382.1	354.8
37.5°	460.7	551.7	602.8	604.1	563.2	513.4	464.4	424.9	384.9	350.6	321.1
40°	400.0	498.6	565.2	579.9	545.4	491.6	442.0	401.8	362.8	329.1	295.3
42.5°	345.5	443.7	525.5	551.2	523.8	470.3	420.6	378.6	340.6	308.8	274.2
45°	279.4	365.3	455.4	501.3	486.1	436.6	384.1	344.1	308.5	281.0	247.8
47.5°	235.7	296.2	383.5	445.5	445.3	400.1	348.4	310.2	277.1	251.3	224.5
50°	210.8	263.5	337.3	407.7	413.6	375.7	326.6	288.7	257.8	230.8	209.2
52.5°	188.4	231.9	298.2	365.8	382.6	349.7	302.1	267.1	237.1	212.2	193.8
55°	159.2	192.9	243.3	306.4	331.9	308.7	266.4	233.7	209.4	188.5	172.6
57.5°	134.7	159.9	200.4	251.2	280.8	266.3	231.4	204.8	184.0	165.1	152.6
60°	119.3	139.9	174.2	216.7	249.4	239.2	209.4	184.7	167.0	150.6	138.8
62.5°	104.7	122.5	151.9	186.4	216.3	212.1	187.8	167.0	151.5	136.6	126.6
65°	84.3	97.2	120.2	147.2	171.3	173.3	155.8	141.7	127.9	116.1	107.2
67.5°	67.1	75.6	91.7	114.5	132.5	139.0	128.3	117.5	106.5	97.4	89.7
70°	56.6	63.4	75.2	93.6	110.2	117.0	110.8	102.4	92.9	85.4	78.8
72.5°	45.8	52.5	61.2	74.7	88.9	96.3	94.1	88.1	80.4	74.1	67.9
75°	34.5	36.6	42.5	51.6	62.7	69.1	70.6	67.5	61.3	56.6	52.9
77.5°	25.5	26.8	29.6	34.3	41.6	47.3	49.6	49.2	45.0	42.3	38.8
80°	20.4	21.1	22.5	24.5	30.0	35.7	37.3	37.3	34.3	33.2	29.8
82.5°	15.5	16.0	16.9	18.0	20.5	25.5	27.3	27.6	25.8	24.3	21.6
85°	8.9	8.6	9.1	9.8	10.2	11.6	14.3	14.8	14.3	12.5	11.8
87.5°	5.4	5.3	5.1	4.6	4.4	4.3	4.8	5.4	5.0	4.8	4.8
90°	11.5	10.3	9.0	7.5	5.8	4.1	2.4	0.7	2.4	4.1	5.8
92.5°	15.0	14.4	13.8	13.5	13.7	13.8	14.0	14.1	14.0	13.8	13.7
95°	25.1	24.0	22.9	25.0	30.1	35.2	40.4	45.5	40.4	35.2	30.1
97.5°	31.5	29.0	26.5	32.4	46.9	61.4	75.8	90.3	75.8	61.4	46.9
100°	34.6	32.0	29.3	38.7	60.0	81.3	102.6	123.9	102.6	81.3	60.0
102.5°	85.3	107.4	129.5	142.8	147.3	151.8	156.4	160.9	156.4	151.8	147.3
105°	127.6	170.1	212.6	231.5	226.8	222.2	217.5	212.8	217.5	222.2	226.8
107.5°	161.7	212.6	263.5	287.1	283.3	279.6	275.8	272.0	275.8	279.6	283.3
110°	212.4	257.4	302.3	323.2	319.9	316.7	313.4	310.1	313.4	316.7	319.9



TEST NUMBER: P331769

CATALOG NUMBER: S122RDIW-S290D710U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	331.2	342.3	353.4	357.5	354.6	351.8	348.9	346.0	348.9	351.8	354.6
115°	424.2	420.3	416.4	413.1	410.5	407.8	405.2	402.5	405.2	407.8	410.5
117.5°	473.1	470.4	467.7	464.9	461.9	459.0	456.0	453.1	456.0	459.0	461.9
120°	507.5	504.7	501.9	499.4	497.0	494.7	492.4	490.0	492.4	494.7	497.0
122.5°	540.1	537.0	534.0	531.2	528.8	526.3	523.9	521.4	523.9	526.3	528.8
125°	585.6	582.7	579.7	577.2	575.2	573.2	571.2	569.1	571.2	573.2	575.2
127.5°	628.0	625.8	623.6	621.4	619.1	616.9	614.6	612.4	614.6	616.9	619.1
130°	655.3	653.6	651.9	649.8	647.3	644.8	642.3	639.8	642.3	644.8	647.3
132.5°	681.6	679.9	678.2	676.3	674.2	672.1	670.0	667.9	670.0	672.1	674.2
135°	719.0	717.6	716.2	714.2	711.7	709.2	706.7	704.3	706.7	709.2	711.7
137.5°	752.9	751.3	749.7	748.0	746.3	744.6	742.8	741.1	742.8	744.6	746.3
140°	775.0	773.3	771.6	770.1	768.9	767.6	766.4	765.2	766.4	767.6	768.9
142.5°	795.3	793.3	791.3	789.8	788.7	787.6	786.4	785.3	786.4	787.6	788.7
145°	822.9	820.2	817.6	816.3	816.5	816.7	816.8	817.0	816.8	816.7	816.5
147.5°	848.4	845.8	843.2	842.2	842.8	843.4	844.0	844.5	844.0	843.4	842.8
150°	863.8	861.3	858.8	858.1	859.2	860.3	861.4	862.5	861.4	860.3	859.2
152.5°	878.0	875.7	873.3	872.7	873.9	875.2	876.4	877.6	876.4	875.2	873.9
155°	897.9	896.1	894.2	894.0	895.4	896.8	898.2	899.6	898.2	896.8	895.4
157.5°	914.7	913.4	912.1	912.1	913.2	914.4	915.6	916.8	915.6	914.4	913.2
160°	925.0	924.1	923.1	923.1	924.1	925.0	925.9	926.9	925.9	925.0	924.1
162.5°	933.7	932.8	932.0	932.1	933.0	934.0	934.9	935.8	934.9	934.0	933.0
165°	944.8	944.4	943.9	944.1	945.1	946.0	946.9	947.9	946.9	946.0	945.1
167.5°	953.7	953.3	952.9	953.1	954.0	955.0	955.9	956.8	955.9	955.0	954.0
170°	958.5	958.1	957.8	958.1	959.1	960.0	960.9	961.9	960.9	960.0	959.1
172.5°	961.8	961.5	961.2	961.5	962.4	963.4	964.3	965.2	964.3	963.4	962.4
175°	965.5	965.1	964.8	965.2	966.3	967.4	968.5	969.6	968.5	967.4	966.3
177.5°	966.7	966.5	966.4	966.8	967.7	968.5	969.4	970.3	969.4	968.5	967.7
180°	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5



TEST NUMBER: P331769

CATALOG NUMBER: S122RDIW-S290D710U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7
2.5°	644.5	643.2	640.8	637.2	635.0	631.2	628.7	630.1	630.5	630.1	629.8
5°	627.2	622.4	615.8	609.4	603.5	597.2	593.5	592.0	588.8	587.0	586.0
7.5°	606.2	598.0	588.7	577.6	568.2	558.3	553.3	550.8	544.3	540.8	537.7
10°	590.6	577.6	568.3	553.8	544.9	532.0	523.1	523.4	514.5	509.5	505.9
12.5°	573.3	559.1	543.6	530.5	518.2	507.8	497.1	492.8	483.4	478.6	468.8
15°	544.7	528.1	511.8	494.1	481.6	465.4	450.0	431.1	415.9	402.7	399.1
17.5°	513.5	492.9	476.5	455.7	434.3	407.2	389.3	378.3	369.2	362.2	357.0
20°	492.0	471.1	453.6	422.3	393.4	375.0	361.9	353.4	343.9	336.4	332.3
22.5°	469.5	447.7	423.8	388.8	366.3	351.6	339.9	330.2	323.7	317.9	314.1
25°	437.5	413.6	374.3	350.3	332.1	316.6	308.5	302.6	295.8	287.8	284.2
27.5°	403.7	365.8	337.5	319.6	302.3	292.3	284.9	276.1	270.0	266.4	262.6
30°	378.4	340.5	318.5	298.9	286.7	275.5	266.9	261.9	256.0	249.9	247.4
32.5°	350.3	320.0	298.8	282.6	270.1	260.6	253.8	245.7	241.5	237.7	232.5
35°	315.3	292.3	273.0	259.9	248.0	240.3	232.4	227.6	219.9	216.7	214.7
37.5°	285.7	265.8	251.4	237.5	228.1	219.6	214.7	207.1	203.8	199.3	195.0
40°	268.9	249.4	235.6	224.2	213.7	207.4	201.3	195.1	190.1	188.1	182.9
42.5°	251.9	236.0	222.1	209.7	202.7	195.9	188.2	183.7	178.5	175.2	172.0
45°	228.3	214.2	202.4	192.2	184.4	177.4	172.4	164.9	162.0	155.4	152.6
47.5°	207.6	194.5	183.2	173.5	166.0	161.4	154.1	148.2	143.5	139.4	135.9
50°	192.9	181.9	171.0	162.4	155.6	149.0	141.5	138.6	131.3	129.2	127.2
52.5°	179.4	169.0	159.1	150.6	143.8	137.4	130.8	126.9	122.0	120.0	118.5
55°	160.6	150.6	141.1	133.6	126.8	120.2	116.1	111.3	109.0	107.4	105.6
57.5°	141.7	132.7	125.4	117.8	110.9	105.7	101.0	98.1	95.8	93.7	91.5
60°	129.7	121.1	114.5	107.4	100.4	96.1	92.5	89.0	86.3	83.1	82.2
62.5°	117.0	109.4	103.4	96.5	90.4	86.5	83.0	79.8	76.5	71.9	70.6
65°	99.5	93.6	87.2	81.5	76.1	72.2	67.2	63.6	62.2	61.8	61.6
67.5°	83.7	78.1	72.6	66.8	61.9	58.3	55.7	55.2	54.2	54.0	53.3
70°	73.1	67.9	62.5	57.0	52.2	51.6	50.7	49.7	48.6	48.2	47.7
72.5°	63.7	58.3	52.8	48.5	46.4	45.6	44.7	43.7	43.0	42.5	42.3
75°	48.8	43.8	40.2	38.6	37.5	36.8	35.4	34.8	34.3	33.6	33.4
77.5°	35.2	32.3	30.7	29.7	28.5	27.8	27.0	26.3	25.8	25.7	25.3
80°	26.8	25.4	24.3	22.9	22.5	21.6	21.4	20.7	20.9	20.2	20.2
82.5°	20.8	19.1	18.1	17.5	17.0	16.3	16.1	15.8	15.8	15.3	15.3
85°	10.7	10.2	9.8	9.3	9.3	8.6	8.9	8.6	8.6	8.2	8.0
87.5°	5.0	5.1	5.0	5.2	5.5	5.5	5.7	5.7	5.8	6.0	5.9
90°	7.5	9.0	10.3	11.5	12.8	14.0	14.8	15.6	16.3	17.1	17.7
92.5°	13.5	13.8	14.4	15.0	15.6	16.2	16.6	17.1	17.5	17.9	18.2
95°	25.0	22.9	24.0	25.1	26.2	27.3	28.1	28.9	29.6	30.4	30.7
97.5°	32.4	26.5	29.0	31.5	34.0	36.5	37.2	37.8	38.4	39.0	39.4
100°	38.7	29.3	32.0	34.6	37.3	39.9	41.1	42.4	43.6	44.9	45.7
102.5°	142.8	129.5	107.4	85.3	63.1	41.0	42.6	44.3	45.9	47.5	48.5
105°	231.5	212.6	170.1	127.6	85.2	42.7	44.4	46.1	47.8	49.5	50.7
107.5°	287.1	263.5	212.6	161.7	110.7	59.8	58.0	56.3	54.6	52.8	52.3
110°	323.2	302.3	257.4	212.4	167.5	122.5	107.0	91.4	75.8	60.3	52.8



TEST NUMBER: P331769

CATALOG NUMBER: S122RDIW-S290D710U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	357.5	353.4	342.3	331.2	320.1	309.0	252.3	195.5	138.8	82.0	53.9
115°	413.1	416.4	420.3	424.2	428.0	431.9	359.9	287.9	215.8	143.8	102.2
117.5°	464.9	467.7	470.4	473.1	475.7	478.4	461.0	443.6	426.1	408.7	381.6
120°	499.4	501.9	504.7	507.5	510.3	513.1	515.0	516.9	518.7	520.6	511.0
122.5°	531.2	534.0	537.0	540.1	543.1	546.2	547.3	548.4	549.5	550.7	549.2
125°	577.2	579.7	582.7	585.6	588.6	591.5	592.6	593.7	594.8	595.9	596.7
127.5°	621.4	623.6	625.8	628.0	630.2	632.4	634.0	635.6	637.2	638.8	639.6
130°	649.8	651.9	653.6	655.3	657.0	658.8	660.5	662.2	663.9	665.6	666.4
132.5°	676.3	678.2	679.9	681.6	683.4	685.1	686.5	688.0	689.5	690.9	691.6
135°	714.2	716.2	717.6	719.0	720.4	721.8	723.3	724.9	726.4	728.0	728.6
137.5°	748.0	749.7	751.3	752.9	754.5	756.1	757.6	759.1	760.6	762.2	762.7
140°	770.1	771.6	773.3	775.0	776.7	778.5	779.9	781.3	782.7	784.1	784.4
142.5°	789.8	791.3	793.3	795.3	797.2	799.2	800.5	801.7	803.0	804.3	804.5
145°	816.3	817.6	820.2	822.9	825.5	828.2	829.3	830.3	831.4	832.5	832.7
147.5°	842.2	843.2	845.8	848.4	851.0	853.6	854.5	855.3	856.1	856.9	857.0
150°	858.1	858.8	861.3	863.8	866.3	868.8	869.7	870.6	871.6	872.5	872.6
152.5°	872.7	873.3	875.7	878.0	880.4	882.8	883.7	884.6	885.6	886.5	886.5
155°	894.0	894.2	896.1	897.9	899.8	901.7	902.6	903.5	904.5	905.4	905.2
157.5°	912.1	912.1	913.4	914.7	916.0	917.3	918.4	919.5	920.5	921.6	921.5
160°	923.1	923.1	924.1	925.0	925.9	926.9	927.8	928.7	929.7	930.6	930.5
162.5°	932.1	932.0	932.8	933.7	934.5	935.3	936.3	937.4	938.4	939.5	939.4
165°	944.1	943.9	944.4	944.8	945.3	945.8	946.9	948.0	949.0	950.1	950.1
167.5°	953.1	952.9	953.3	953.7	954.2	954.6	955.7	956.8	957.9	958.9	958.8
170°	958.1	957.8	958.1	958.5	958.8	959.1	960.2	961.3	962.3	963.4	963.3
172.5°	961.5	961.2	961.5	961.8	962.1	962.4	963.5	964.6	965.7	966.8	966.6
175°	965.2	964.8	965.1	965.5	965.8	966.1	967.2	968.3	969.3	970.4	970.2
177.5°	966.8	966.4	966.5	966.7	966.8	966.9	967.8	968.7	969.5	970.4	970.3
180°	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5



TEST NUMBER: P331769

CATALOG NUMBER: S122RDIW-S290D710U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7
2.5°	627.8	628.1	627.6	627.9	627.6	628.1	627.8	629.8	630.1	630.5	630.1
5°	584.9	582.2	581.7	581.1	581.7	582.2	584.9	586.0	587.0	588.8	592.0
7.5°	533.8	533.4	532.2	530.6	532.2	533.4	533.8	537.7	540.8	544.3	550.8
10°	500.9	499.7	499.5	497.9	499.5	499.7	500.9	505.9	509.5	514.5	523.4
12.5°	462.3	455.0	454.3	450.3	454.3	455.0	462.3	468.8	478.6	483.4	492.8
15°	393.7	392.3	387.7	384.8	387.7	392.3	393.7	399.1	402.7	415.9	431.1
17.5°	354.4	349.9	348.5	347.9	348.5	349.9	354.4	357.0	362.2	369.2	378.3
20°	329.1	325.1	324.4	323.9	324.4	325.1	329.1	332.3	336.4	343.9	353.4
22.5°	311.7	307.4	305.7	304.3	305.7	307.4	311.7	314.1	317.9	323.7	330.2
25°	281.9	280.3	279.4	278.9	279.4	280.3	281.9	284.2	287.8	295.8	302.6
27.5°	258.6	255.1	254.4	253.2	254.4	255.1	258.6	262.6	266.4	270.0	276.1
30°	245.3	244.2	242.6	241.2	242.6	244.2	245.3	247.4	249.9	256.0	261.9
32.5°	229.7	228.7	227.3	226.7	227.3	228.7	229.7	232.5	237.7	241.5	245.7
35°	212.4	209.2	207.8	205.8	207.8	209.2	212.4	214.7	216.7	219.9	227.6
37.5°	194.1	192.4	190.5	191.2	190.5	192.4	194.1	195.0	199.3	203.8	207.1
40°	179.9	178.8	178.3	178.1	178.3	178.8	179.9	182.9	188.1	190.1	195.1
42.5°	168.6	165.5	164.3	164.3	164.3	165.5	168.6	172.0	175.2	178.5	183.7
45°	151.5	148.6	146.5	146.7	146.5	148.6	151.5	152.6	155.4	162.0	164.9
47.5°	134.0	133.9	132.6	133.0	132.6	133.9	134.0	135.9	139.4	143.5	148.2
50°	125.6	124.3	123.3	123.6	123.3	124.3	125.6	127.2	129.2	131.3	138.6
52.5°	117.6	116.4	115.7	116.7	115.7	116.4	117.6	118.5	120.0	122.0	126.9
55°	104.5	103.1	102.9	102.7	102.9	103.1	104.5	105.6	107.4	109.0	111.3
57.5°	89.8	88.9	87.5	87.0	87.5	88.9	89.8	91.5	93.7	95.8	98.1
60°	79.3	77.5	75.2	75.0	75.2	77.5	79.3	82.2	83.1	86.3	89.0
62.5°	69.6	69.3	68.8	68.8	68.8	69.3	69.6	70.6	71.9	76.5	79.8
65°	61.1	60.9	61.1	61.3	61.1	60.9	61.1	61.6	61.8	62.2	63.6
67.5°	53.2	52.8	52.4	52.6	52.4	52.8	53.2	53.3	54.0	54.2	55.2
70°	47.2	47.0	46.8	46.8	46.8	47.0	47.2	47.7	48.2	48.6	49.7
72.5°	41.4	41.4	41.2	41.0	41.2	41.4	41.4	42.3	42.5	43.0	43.7
75°	33.2	32.7	32.7	32.7	32.7	32.7	33.2	33.4	33.6	34.3	34.8
77.5°	25.3	25.0	24.8	24.6	24.8	25.0	25.3	25.3	25.7	25.8	26.3
80°	20.0	19.8	19.5	19.5	19.5	19.8	20.0	20.2	20.2	20.9	20.7
82.5°	15.3	15.0	15.0	14.8	15.0	15.0	15.3	15.3	15.3	15.8	15.8
85°	8.2	8.4	8.2	8.6	8.2	8.4	8.2	8.0	8.2	8.6	8.6
87.5°	6.0	5.8	6.1	6.0	6.1	5.8	6.0	5.9	6.0	5.8	5.7
90°	18.0	18.3	18.6	18.9	18.6	18.3	18.0	17.7	17.1	16.3	15.6
92.5°	18.3	18.5	18.7	18.9	18.7	18.5	18.3	18.2	17.9	17.5	17.1
95°	30.6	30.4	30.3	30.1	30.3	30.4	30.6	30.7	30.4	29.6	28.9
97.5°	39.6	39.8	40.0	40.2	40.0	39.8	39.6	39.4	39.0	38.4	37.8
100°	46.0	46.3	46.6	46.9	46.6	46.3	46.0	45.7	44.9	43.6	42.4
102.5°	49.0	49.4	49.8	50.3	49.8	49.4	49.0	48.5	47.5	45.9	44.3
105°	51.3	52.0	52.6	53.2	52.6	52.0	51.3	50.7	49.5	47.8	46.1
107.5°	52.9	53.5	54.1	54.7	54.1	53.5	52.9	52.3	52.8	54.6	56.3
110°	53.4	54.1	54.7	55.3	54.7	54.1	53.4	52.8	60.3	75.8	91.4



TEST NUMBER: P331769

CATALOG NUMBER: S122RDIW-S290D710U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	54.4	54.9	55.4	55.9	55.4	54.9	54.4	53.9	82.0	138.8	195.5
115°	91.0	79.8	68.6	57.4	68.6	79.8	91.0	102.2	143.8	215.8	287.9
117.5°	344.8	308.0	271.2	234.4	271.2	308.0	344.8	381.6	408.7	426.1	443.6
120°	490.0	469.0	448.0	427.0	448.0	469.0	490.0	511.0	520.6	518.7	516.9
122.5°	545.1	541.0	537.0	532.9	537.0	541.0	545.1	549.2	550.7	549.5	548.4
125°	597.1	597.6	598.1	598.5	598.1	597.6	597.1	596.7	595.9	594.8	593.7
127.5°	639.7	639.8	639.9	640.0	639.9	639.8	639.7	639.6	638.8	637.2	635.6
130°	666.2	666.1	665.9	665.8	665.9	666.1	666.2	666.4	665.6	663.9	662.2
132.5°	691.4	691.3	691.1	691.0	691.1	691.3	691.4	691.6	690.9	689.5	688.0
135°	728.3	728.0	727.7	727.4	727.7	728.0	728.3	728.6	728.0	726.4	724.9
137.5°	762.1	761.6	761.1	760.5	761.1	761.6	762.1	762.7	762.2	760.6	759.1
140°	783.6	782.8	782.0	781.3	782.0	782.8	783.6	784.4	784.1	782.7	781.3
142.5°	803.8	803.0	802.2	801.4	802.2	803.0	803.8	804.5	804.3	803.0	801.7
145°	831.9	831.1	830.3	829.6	830.3	831.1	831.9	832.7	832.5	831.4	830.3
147.5°	856.3	855.7	855.0	854.3	855.0	855.7	856.3	857.0	856.9	856.1	855.3
150°	871.8	871.0	870.2	869.5	870.2	871.0	871.8	872.6	872.5	871.6	870.6
152.5°	885.4	884.4	883.4	882.3	883.4	884.4	885.4	886.5	886.5	885.6	884.6
155°	904.0	902.8	901.5	900.3	901.5	902.8	904.0	905.2	905.4	904.5	903.5
157.5°	920.3	919.1	917.9	916.6	917.9	919.1	920.3	921.5	921.6	920.5	919.5
160°	929.4	928.3	927.3	926.2	927.3	928.3	929.4	930.5	930.6	929.7	928.7
162.5°	938.0	936.7	935.3	934.0	935.3	936.7	938.0	939.4	939.5	938.4	937.4
165°	949.0	948.0	946.9	945.8	946.9	948.0	949.0	950.1	950.1	949.0	948.0
167.5°	957.4	956.0	954.6	953.2	954.6	956.0	957.4	958.8	958.9	957.9	956.8
170°	961.9	960.5	959.1	957.7	959.1	960.5	961.9	963.3	963.4	962.3	961.3
172.5°	965.2	963.8	962.4	961.0	962.4	963.8	965.2	966.6	966.8	965.7	964.6
175°	968.6	967.1	965.5	964.0	965.5	967.1	968.6	970.2	970.4	969.3	968.3
177.5°	969.2	968.0	966.9	965.8	966.9	968.0	969.2	970.3	970.4	969.5	968.7
180°	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5



TEST NUMBER: P331769

CATALOG NUMBER: S122RDIW-S290D710U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7
2.5°	628.7	631.2	635.0	637.2	640.8	643.2	644.5	646.8	648.1	652.7	657.4
5°	593.5	597.2	603.5	609.4	615.8	622.4	627.2	632.6	637.6	646.2	655.3
7.5°	553.3	558.3	568.2	577.6	588.7	598.0	606.2	615.5	623.8	636.2	649.1
10°	523.1	532.0	544.9	553.8	568.3	577.6	590.6	600.8	612.4	628.8	643.3
12.5°	497.1	507.8	518.2	530.5	543.6	559.1	573.3	586.5	600.2	617.1	634.2
15°	450.0	465.4	481.6	494.1	511.8	528.1	544.7	562.4	579.2	599.5	621.7
17.5°	389.3	407.2	434.3	455.7	476.5	492.9	513.5	534.9	554.7	579.1	603.9
20°	361.9	375.0	393.4	422.3	453.6	471.1	492.0	515.6	538.3	564.9	591.5
22.5°	339.9	351.6	366.3	388.8	423.8	447.7	469.5	493.5	519.8	546.9	576.4
25°	308.5	316.6	332.1	350.3	374.3	413.6	437.5	461.6	490.2	519.3	552.9
27.5°	284.9	292.3	302.3	319.6	337.5	365.8	403.7	430.0	458.5	491.2	526.1
30°	266.9	275.5	286.7	298.9	318.5	340.5	378.4	408.9	437.0	470.7	507.9
32.5°	253.8	260.6	270.1	282.6	298.8	320.0	350.3	387.2	414.7	450.1	489.0
35°	232.4	240.3	248.0	259.9	273.0	292.3	315.3	354.8	382.1	417.0	456.1
37.5°	214.7	219.6	228.1	237.5	251.4	265.8	285.7	321.1	350.6	384.9	424.9
40°	201.3	207.4	213.7	224.2	235.6	249.4	268.9	295.3	329.1	362.8	401.8
42.5°	188.2	195.9	202.7	209.7	222.1	236.0	251.9	274.2	308.8	340.6	378.6
45°	172.4	177.4	184.4	192.2	202.4	214.2	228.3	247.8	281.0	308.5	344.1
47.5°	154.1	161.4	166.0	173.5	183.2	194.5	207.6	224.5	251.3	277.1	310.2
50°	141.5	149.0	155.6	162.4	171.0	181.9	192.9	209.2	230.8	257.8	288.7
52.5°	130.8	137.4	143.8	150.6	159.1	169.0	179.4	193.8	212.2	237.1	267.1
55°	116.1	120.2	126.8	133.6	141.1	150.6	160.6	172.6	188.5	209.4	233.7
57.5°	101.0	105.7	110.9	117.8	125.4	132.7	141.7	152.6	165.1	184.0	204.8
60°	92.5	96.1	100.4	107.4	114.5	121.1	129.7	138.8	150.6	167.0	184.7
62.5°	83.0	86.5	90.4	96.5	103.4	109.4	117.0	126.6	136.6	151.5	167.0
65°	67.2	72.2	76.1	81.5	87.2	93.6	99.5	107.2	116.1	127.9	141.7
67.5°	55.7	58.3	61.9	66.8	72.6	78.1	83.7	89.7	97.4	106.5	117.5
70°	50.7	51.6	52.2	57.0	62.5	67.9	73.1	78.8	85.4	92.9	102.4
72.5°	44.7	45.6	46.4	48.5	52.8	58.3	63.7	67.9	74.1	80.4	88.1
75°	35.4	36.8	37.5	38.6	40.2	43.8	48.8	52.9	56.6	61.3	67.5
77.5°	27.0	27.8	28.5	29.7	30.7	32.3	35.2	38.8	42.3	45.0	49.2
80°	21.4	21.6	22.5	22.9	24.3	25.4	26.8	29.8	33.2	34.3	37.3
82.5°	16.1	16.3	17.0	17.5	18.1	19.1	20.8	21.6	24.3	25.8	27.6
85°	8.9	8.6	9.3	9.3	9.8	10.2	10.7	11.8	12.5	14.3	14.8
87.5°	5.7	5.5	5.5	5.2	5.0	5.1	5.0	4.8	4.8	5.0	5.4
90°	14.8	14.0	12.8	11.5	10.3	9.0	7.5	5.8	4.1	2.4	0.7
92.5°	16.6	16.2	15.6	15.0	14.4	13.8	13.5	13.7	13.8	14.0	14.1
95°	28.1	27.3	26.2	25.1	24.0	22.9	25.0	30.1	35.2	40.4	45.5
97.5°	37.2	36.5	34.0	31.5	29.0	26.5	32.4	46.9	61.4	75.8	90.3
100°	41.1	39.9	37.3	34.6	32.0	29.3	38.7	60.0	81.3	102.6	123.9
102.5°	42.6	41.0	63.1	85.3	107.4	129.5	142.8	147.3	151.8	156.4	160.9
105°	44.4	42.7	85.2	127.6	170.1	212.6	231.5	226.8	222.2	217.5	212.8
107.5°	58.0	59.8	110.7	161.7	212.6	263.5	287.1	283.3	279.6	275.8	272.0
110°	107.0	122.5	167.5	212.4	257.4	302.3	323.2	319.9	316.7	313.4	310.1



TEST NUMBER: P331769

CATALOG NUMBER: S122RDIW-S290D710U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	252.3	309.0	320.1	331.2	342.3	353.4	357.5	354.6	351.8	348.9	346.0
115°	359.9	431.9	428.0	424.2	420.3	416.4	413.1	410.5	407.8	405.2	402.5
117.5°	461.0	478.4	475.7	473.1	470.4	467.7	464.9	461.9	459.0	456.0	453.1
120°	515.0	513.1	510.3	507.5	504.7	501.9	499.4	497.0	494.7	492.4	490.0
122.5°	547.3	546.2	543.1	540.1	537.0	534.0	531.2	528.8	526.3	523.9	521.4
125°	592.6	591.5	588.6	585.6	582.7	579.7	577.2	575.2	573.2	571.2	569.1
127.5°	634.0	632.4	630.2	628.0	625.8	623.6	621.4	619.1	616.9	614.6	612.4
130°	660.5	658.8	657.0	655.3	653.6	651.9	649.8	647.3	644.8	642.3	639.8
132.5°	686.5	685.1	683.4	681.6	679.9	678.2	676.3	674.2	672.1	670.0	667.9
135°	723.3	721.8	720.4	719.0	717.6	716.2	714.2	711.7	709.2	706.7	704.3
137.5°	757.6	756.1	754.5	752.9	751.3	749.7	748.0	746.3	744.6	742.8	741.1
140°	779.9	778.5	776.7	775.0	773.3	771.6	770.1	768.9	767.6	766.4	765.2
142.5°	800.5	799.2	797.2	795.3	793.3	791.3	789.8	788.7	787.6	786.4	785.3
145°	829.3	828.2	825.5	822.9	820.2	817.6	816.3	816.5	816.7	816.8	817.0
147.5°	854.5	853.6	851.0	848.4	845.8	843.2	842.2	842.8	843.4	844.0	844.5
150°	869.7	868.8	866.3	863.8	861.3	858.8	858.1	859.2	860.3	861.4	862.5
152.5°	883.7	882.8	880.4	878.0	875.7	873.3	872.7	873.9	875.2	876.4	877.6
155°	902.6	901.7	899.8	897.9	896.1	894.2	894.0	895.4	896.8	898.2	899.6
157.5°	918.4	917.3	916.0	914.7	913.4	912.1	912.1	913.2	914.4	915.6	916.8
160°	927.8	926.9	925.9	925.0	924.1	923.1	923.1	924.1	925.0	925.9	926.9
162.5°	936.3	935.3	934.5	933.7	932.8	932.0	932.1	933.0	934.0	934.9	935.8
165°	946.9	945.8	945.3	944.8	944.4	943.9	944.1	945.1	946.0	946.9	947.9
167.5°	955.7	954.6	954.2	953.7	953.3	952.9	953.1	954.0	955.0	955.9	956.8
170°	960.2	959.1	958.8	958.5	958.1	957.8	958.1	959.1	960.0	960.9	961.9
172.5°	963.5	962.4	962.1	961.8	961.5	961.2	961.5	962.4	963.4	964.3	965.2
175°	967.2	966.1	965.8	965.5	965.1	964.8	965.2	966.3	967.4	968.5	969.6
177.5°	967.8	966.9	966.8	966.7	966.5	966.4	966.8	967.7	968.5	969.4	970.3
180°	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5



TEST NUMBER: P331769

CATALOG NUMBER: S122RDIW-S290D710U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7
2.5°	657.6	658.1	661.7	663.4	666.6	667.9	669.4	669.0	669.0	669.7	674.8
5°	659.0	663.5	670.3	676.9	683.3	688.7	692.4	696.0	697.4	703.9	709.8
7.5°	656.6	665.0	676.2	686.3	698.3	707.7	715.5	722.6	727.4	737.0	746.8
10°	653.5	665.3	678.0	691.0	707.6	720.1	732.8	742.6	745.7	760.0	768.2
12.5°	647.3	663.1	679.3	696.1	712.3	729.5	743.5	753.3	764.5	777.3	792.4
15°	638.1	656.2	677.4	698.9	722.1	743.0	758.0	775.0	787.3	801.4	814.6
17.5°	624.8	648.2	675.0	700.0	726.8	749.2	769.9	786.2	794.8	802.9	804.8
20°	614.2	639.4	671.0	700.5	727.3	753.2	773.7	787.3	789.6	789.8	777.8
22.5°	602.8	631.3	664.3	694.5	726.6	755.4	771.3	777.1	768.1	752.7	729.4
25°	581.7	614.7	653.1	687.6	722.6	749.8	755.3	745.1	713.5	680.3	638.3
27.5°	558.9	596.0	637.1	675.5	712.8	729.7	717.9	681.0	624.2	574.7	514.8
30°	542.2	583.8	624.2	667.1	701.7	708.9	681.9	627.6	561.3	486.8	427.0
32.5°	523.1	566.7	611.1	655.5	684.4	677.3	632.7	565.8	488.1	414.8	358.4
35°	495.9	540.8	588.8	633.3	651.7	621.0	554.2	467.2	387.7	319.4	280.5
37.5°	464.4	513.4	563.2	604.1	602.8	551.7	460.7	370.9	304.1	263.6	236.0
40°	442.0	491.6	545.4	579.9	565.2	498.6	400.0	315.3	266.4	234.2	214.0
42.5°	420.6	470.3	523.8	551.2	525.5	443.7	345.5	279.1	238.8	213.7	197.3
45°	384.1	436.6	486.1	501.3	455.4	365.3	279.4	231.2	204.4	185.8	174.5
47.5°	348.4	400.1	445.3	445.5	383.5	296.2	235.7	200.1	177.2	162.8	154.6
50°	326.6	375.7	413.6	407.7	337.3	263.5	210.8	180.1	161.1	149.9	141.3
52.5°	302.1	349.7	382.6	365.8	298.2	231.9	188.4	162.7	146.9	137.2	129.5
55°	266.4	308.7	331.9	306.4	243.3	192.9	159.2	139.0	127.2	119.0	112.4
57.5°	231.4	266.3	280.8	251.2	200.4	159.9	134.7	119.5	107.8	101.9	98.5
60°	209.4	239.2	249.4	216.7	174.2	139.9	119.3	105.2	96.5	92.7	89.3
62.5°	187.8	212.1	216.3	186.4	151.9	122.5	104.7	92.8	87.1	83.4	80.2
65°	155.8	173.3	171.3	147.2	120.2	97.2	84.3	77.0	72.7	67.5	61.8
67.5°	128.3	139.0	132.5	114.5	91.7	75.6	67.1	61.6	56.2	51.3	50.0
70°	110.8	117.0	110.2	93.6	75.2	63.4	56.6	50.0	46.8	45.7	43.6
72.5°	94.1	96.3	88.9	74.7	61.2	52.5	45.8	42.2	40.4	39.5	38.2
75°	70.6	69.1	62.7	51.6	42.5	36.6	34.5	33.2	32.0	31.1	30.4
77.5°	49.6	47.3	41.6	34.3	29.6	26.8	25.5	24.8	24.3	23.8	23.1
80°	37.3	35.7	30.0	24.5	22.5	21.1	20.4	19.5	19.5	19.1	18.4
82.5°	27.3	25.5	20.5	18.0	16.9	16.0	15.5	15.0	14.8	14.9	14.4
85°	14.3	11.6	10.2	9.8	9.1	8.6	8.9	8.4	8.4	8.4	8.2
87.5°	4.8	4.3	4.4	4.6	5.1	5.3	5.4	5.6	6.1	6.0	6.4
90°	2.4	4.1	5.8	7.5	9.0	10.3	11.5	12.8	14.0	14.8	15.6
92.5°	14.0	13.8	13.7	13.5	13.8	14.4	15.0	15.6	16.2	16.6	17.1
95°	40.4	35.2	30.1	25.0	22.9	24.0	25.1	26.2	27.3	28.1	28.9
97.5°	75.8	61.4	46.9	32.4	26.5	29.0	31.5	34.0	36.5	37.2	37.8
100°	102.6	81.3	60.0	38.7	29.3	32.0	34.6	37.3	39.9	41.1	42.4
102.5°	156.4	151.8	147.3	142.8	129.5	107.4	85.3	63.1	41.0	42.6	44.3
105°	217.5	222.2	226.8	231.5	212.6	170.1	127.6	85.2	42.7	44.4	46.1
107.5°	275.8	279.6	283.3	287.1	263.5	212.6	161.7	110.7	59.8	58.0	56.3
110°	313.4	316.7	319.9	323.2	302.3	257.4	212.4	167.5	122.5	107.0	91.4



TEST NUMBER: P331769

CATALOG NUMBER: S122RDIW-S290D710U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	348.9	351.8	354.6	357.5	353.4	342.3	331.2	320.1	309.0	252.3	195.5
115°	405.2	407.8	410.5	413.1	416.4	420.3	424.2	428.0	431.9	359.9	287.9
117.5°	456.0	459.0	461.9	464.9	467.7	470.4	473.1	475.7	478.4	461.0	443.6
120°	492.4	494.7	497.0	499.4	501.9	504.7	507.5	510.3	513.1	515.0	516.9
122.5°	523.9	526.3	528.8	531.2	534.0	537.0	540.1	543.1	546.2	547.3	548.4
125°	571.2	573.2	575.2	577.2	579.7	582.7	585.6	588.6	591.5	592.6	593.7
127.5°	614.6	616.9	619.1	621.4	623.6	625.8	628.0	630.2	632.4	634.0	635.6
130°	642.3	644.8	647.3	649.8	651.9	653.6	655.3	657.0	658.8	660.5	662.2
132.5°	670.0	672.1	674.2	676.3	678.2	679.9	681.6	683.4	685.1	686.5	688.0
135°	706.7	709.2	711.7	714.2	716.2	717.6	719.0	720.4	721.8	723.3	724.9
137.5°	742.8	744.6	746.3	748.0	749.7	751.3	752.9	754.5	756.1	757.6	759.1
140°	766.4	767.6	768.9	770.1	771.6	773.3	775.0	776.7	778.5	779.9	781.3
142.5°	786.4	787.6	788.7	789.8	791.3	793.3	795.3	797.2	799.2	800.5	801.7
145°	816.8	816.7	816.5	816.3	817.6	820.2	822.9	825.5	828.2	829.3	830.3
147.5°	844.0	843.4	842.8	842.2	843.2	845.8	848.4	851.0	853.6	854.5	855.3
150°	861.4	860.3	859.2	858.1	858.8	861.3	863.8	866.3	868.8	869.7	870.6
152.5°	876.4	875.2	873.9	872.7	873.3	875.7	878.0	880.4	882.8	883.7	884.6
155°	898.2	896.8	895.4	894.0	894.2	896.1	897.9	899.8	901.7	902.6	903.5
157.5°	915.6	914.4	913.2	912.1	912.1	913.4	914.7	916.0	917.3	918.4	919.5
160°	925.9	925.0	924.1	923.1	923.1	924.1	925.0	925.9	926.9	927.8	928.7
162.5°	934.9	934.0	933.0	932.1	932.0	932.8	933.7	934.5	935.3	936.3	937.4
165°	946.9	946.0	945.1	944.1	943.9	944.4	944.8	945.3	945.8	946.9	948.0
167.5°	955.9	955.0	954.0	953.1	952.9	953.3	953.7	954.2	954.6	955.7	956.8
170°	960.9	960.0	959.1	958.1	957.8	958.1	958.5	958.8	959.1	960.2	961.3
172.5°	964.3	963.4	962.4	961.5	961.2	961.5	961.8	962.1	962.4	963.5	964.6
175°	968.5	967.4	966.3	965.2	964.8	965.1	965.5	965.8	966.1	967.2	968.3
177.5°	969.4	968.5	967.7	966.8	966.4	966.5	966.7	966.8	966.9	967.8	968.7
180°	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5	967.5



TEST NUMBER: P331769

CATALOG NUMBER: S122RDIW-S290D710U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	653.7	653.7	653.7	653.7	653.7	653.7	653.7
2.5°	676.6	679.0	680.1	680.1	681.4	680.8	680.3
5°	715.5	719.8	720.8	724.8	727.8	726.9	727.3
7.5°	754.2	761.1	768.0	771.1	771.6	773.4	774.1
10°	778.0	783.7	794.3	792.8	800.7	805.3	797.8
12.5°	800.9	808.6	816.0	818.0	822.5	824.0	821.0
15°	821.6	825.7	826.1	825.0	826.4	825.2	820.9
17.5°	802.3	795.6	782.2	775.8	770.8	763.3	760.3
20°	770.3	750.7	728.0	718.9	708.3	687.4	692.4
22.5°	701.2	679.0	656.2	629.7	617.0	597.2	596.0
25°	593.8	555.4	513.1	483.6	466.3	446.6	437.9
27.5°	461.7	413.3	378.7	361.2	345.2	329.6	328.9
30°	374.8	338.5	311.7	296.7	286.9	280.3	281.7
32.5°	315.9	291.0	272.9	260.5	253.3	248.3	248.2
35°	258.3	241.2	229.6	224.4	219.2	215.6	215.8
37.5°	221.0	210.8	204.3	198.6	195.3	193.5	192.5
40°	201.9	193.5	188.5	185.1	182.4	179.9	179.4
42.5°	186.9	179.9	174.9	172.2	169.7	167.9	167.5
45°	165.8	160.1	155.6	152.6	151.5	149.9	149.9
47.5°	147.5	141.9	138.4	136.5	134.6	133.5	133.5
50°	135.2	130.8	127.7	126.5	124.9	124.3	124.0
52.5°	124.1	120.8	118.6	117.8	117.1	116.3	116.4
55°	109.0	107.2	106.3	105.6	104.5	103.1	104.0
57.5°	96.4	94.8	92.4	90.2	89.2	88.2	88.6
60°	87.5	84.3	81.1	78.6	77.9	75.9	75.9
62.5°	76.2	71.7	67.8	66.4	65.7	64.8	64.6
65°	58.6	56.8	55.9	55.0	54.5	54.5	54.1
67.5°	48.6	47.8	46.8	46.6	46.2	46.0	45.9
70°	42.9	42.0	41.6	41.3	40.9	41.1	40.4
72.5°	37.5	36.8	36.7	36.1	35.8	35.8	35.3
75°	29.5	29.5	29.3	29.1	28.6	28.4	28.6
77.5°	22.7	22.8	22.4	22.3	22.3	22.3	22.1
80°	18.2	18.4	18.2	17.9	17.7	17.9	17.7
82.5°	14.4	14.0	14.0	13.9	13.9	13.8	13.7
85°	8.2	8.4	8.2	8.0	8.0	8.0	8.2
87.5°	6.4	6.5	6.6	6.7	6.7	6.8	6.7
90°	16.3	17.1	17.7	18.0	18.3	18.6	18.9
92.5°	17.5	17.9	18.2	18.3	18.5	18.7	18.9
95°	29.6	30.4	30.7	30.6	30.4	30.3	30.1
97.5°	38.4	39.0	39.4	39.6	39.8	40.0	40.2
100°	43.6	44.9	45.7	46.0	46.3	46.6	46.9
102.5°	45.9	47.5	48.5	49.0	49.4	49.8	50.3
105°	47.8	49.5	50.7	51.3	52.0	52.6	53.2
107.5°	54.6	52.8	52.3	52.9	53.5	54.1	54.7
110°	75.8	60.3	52.8	53.4	54.1	54.7	55.3



TEST NUMBER: P331769

CATALOG NUMBER: S122RDIW-S290D710U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	138.8	82.0	53.9	54.4	54.9	55.4	55.9
115°	215.8	143.8	102.2	91.0	79.8	68.6	57.4
117.5°	426.1	408.7	381.6	344.8	308.0	271.2	234.4
120°	518.7	520.6	511.0	490.0	469.0	448.0	427.0
122.5°	549.5	550.7	549.2	545.1	541.0	537.0	532.9
125°	594.8	595.9	596.7	597.1	597.6	598.1	598.5
127.5°	637.2	638.8	639.6	639.7	639.8	639.9	640.0
130°	663.9	665.6	666.4	666.2	666.1	665.9	665.8
132.5°	689.5	690.9	691.6	691.4	691.3	691.1	691.0
135°	726.4	728.0	728.6	728.3	728.0	727.7	727.4
137.5°	760.6	762.2	762.7	762.1	761.6	761.1	760.5
140°	782.7	784.1	784.4	783.6	782.8	782.0	781.3
142.5°	803.0	804.3	804.5	803.8	803.0	802.2	801.4
145°	831.4	832.5	832.7	831.9	831.1	830.3	829.6
147.5°	856.1	856.9	857.0	856.3	855.7	855.0	854.3
150°	871.6	872.5	872.6	871.8	871.0	870.2	869.5
152.5°	885.6	886.5	886.5	885.4	884.4	883.4	882.3
155°	904.5	905.4	905.2	904.0	902.8	901.5	900.3
157.5°	920.5	921.6	921.5	920.3	919.1	917.9	916.6
160°	929.7	930.6	930.5	929.4	928.3	927.3	926.2
162.5°	938.4	939.5	939.4	938.0	936.7	935.3	934.0
165°	949.0	950.1	950.1	949.0	948.0	946.9	945.8
167.5°	957.9	958.9	958.8	957.4	956.0	954.6	953.2
170°	962.3	963.4	963.3	961.9	960.5	959.1	957.7
172.5°	965.7	966.8	966.6	965.2	963.8	962.4	961.0
175°	969.3	970.4	970.2	968.6	967.1	965.5	964.0
177.5°	969.5	970.4	970.3	969.2	968.0	966.9	965.8
180°	967.5	967.5	967.5	967.5	967.5	967.5	967.5

(END OF REPORT)