

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331774

Luminaire Tested: **S122RDIW-S290D970U835-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331774
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S290D970U835-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 970 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4490.7 lumens
Efficiency: N/A
Efficacy: 118.2 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 38
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331774

CATALOG NUMBER: S122RDIW-S290D970U835-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331774

CATALOG NUMBER: S122RDIW-S290D970U835-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	33	33	33	25				
1	93	89	85	82	82	79	76	73	61	59	58	45	44	43	30	29	29	22				
2	85	78	72	67	75	70	65	61	54	51	48	40	38	36	27	26	25	19				
3	77	69	62	57	69	62	56	51	48	44	41	36	33	31	24	23	22	17				
4	71	61	54	48	63	55	49	44	43	39	35	32	29	27	22	20	19	15				
5	65	54	47	41	58	49	42	38	39	34	31	29	26	24	20	18	17	13				
6	60	49	41	36	53	44	37	33	35	30	27	26	23	21	18	16	15	12				
7	56	44	37	31	49	40	33	29	32	27	24	24	21	19	17	15	14	11				
8	52	40	33	28	46	36	30	26	29	24	21	22	19	17	16	14	12	10				
9	48	36	29	25	43	33	27	23	26	22	19	20	17	15	14	13	11	9				
10	45	33	27	22	40	30	24	20	24	20	17	19	16	14	13	12	10	8				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10555	10555	10555	10555
5°	11788	10621	9418	10621
10°	13080	10547	8163	10547
15°	13722	10392	6432	10392
20°	11897	10163	5565	10163
25°	7801	9850	4969	9850
30°	5252	9469	4497	9469
35°	4254	8990	4056	8990
40°	3781	8469	3754	8469
45°	3423	7857	3350	7857
50°	3115	7252	3105	7252
55°	2928	6579	2891	6579
60°	2451	5964	2422	5964
65°	2067	5414	2342	5414
70°	1907	4834	2209	4834
75°	1784	4211	2040	4211
80°	1646	3468	1813	3468
85°	1519	2742	1593	2742



TEST NUMBER: P331774

CATALOG NUMBER: S122RDIW-S290D970U835-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	62.0	1.4
10°-20°	172.7	3.8
20°-30°	222.5	5.0
30°-40°	211.5	4.7
40°-50°	181.1	4.0
50°-60°	137.9	3.1
60°-70°	87.2	1.9
70°-80°	43.5	1.0
80°-90°	16.1	0.4
90°-100°	76.0	1.7
100°-110°	236.2	5.3
110°-120°	403.8	9.0
120°-130°	531.0	11.8
130°-140°	595.9	13.3
140°-150°	584.3	13.0
150°-160°	490.1	10.9
160°-170°	325.1	7.2
170°-180°	113.6	2.5
0°-30°	457.2	10.2
0°-40°	668.6	14.9
0°-60°	987.7	22.0
0°-90°	1134.6	25.3
90°-120°	716.0	15.9
90°-150°	2427.3	54.1
90°-180°	3356.0	74.7
0°-180°	4490.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	654	654	654	654	654	
5°	727	655	581	655	727	72
15°	821	622	385	622	821	221
25°	438	553	279	553	438	208
35°	216	456	206	456	216	138
45°	150	344	147	344	150	116
55°	104	234	103	234	104	91
65°	54	142	61	142	54	55
75°	29	68	33	68	29	30
85°	8	15	9	15	8	10
90°	34	1	34	1	34	15
95°	63	53	63	53	63	70
105°	225	218	225	218	225	237
115°	405	405	405	405	405	400
125°	592	590	592	590	592	527
135°	772	763	772	763	772	594
145°	936	926	936	926	936	584
155°	1066	1058	1066	1058	1066	491
165°	1153	1152	1153	1152	1153	325
175°	1194	1198	1194	1198	1194	113
180°	1200	1200	1200	1200	1200	



TEST NUMBER: P331774

CATALOG NUMBER: S122RDIW-S290D970U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7
2.5°	680.3	680.8	681.4	680.1	680.1	679.0	676.6	674.8	669.7	669.0	669.0
5°	727.3	726.9	727.8	724.8	720.8	719.8	715.5	709.8	703.9	697.4	696.0
7.5°	774.1	773.4	771.6	771.1	768.0	761.1	754.2	746.8	737.0	727.4	722.6
10°	797.8	805.3	800.7	792.8	794.3	783.7	778.0	768.2	760.0	745.7	742.6
12.5°	821.0	824.0	822.5	818.0	816.0	808.6	800.9	792.4	777.3	764.5	753.3
15°	820.9	825.2	826.4	825.0	826.1	825.7	821.6	814.6	801.4	787.3	775.0
17.5°	760.3	763.3	770.8	775.8	782.2	795.6	802.3	804.8	802.9	794.8	786.2
20°	692.4	687.4	708.3	718.9	728.0	750.7	770.3	777.8	789.8	789.6	787.3
22.5°	596.0	597.2	617.0	629.7	656.2	679.0	701.2	729.4	752.7	768.1	777.1
25°	437.9	446.6	466.3	483.6	513.1	555.4	593.8	638.3	680.3	713.5	745.1
27.5°	328.9	329.6	345.2	361.2	378.7	413.3	461.7	514.8	574.7	624.2	681.0
30°	281.7	280.3	286.9	296.7	311.7	338.5	374.8	427.0	486.8	561.3	627.6
32.5°	248.2	248.3	253.3	260.5	272.9	291.0	315.9	358.4	414.8	488.1	565.8
35°	215.8	215.6	219.2	224.4	229.6	241.2	258.3	280.5	319.4	387.7	467.2
37.5°	192.5	193.5	195.3	198.6	204.3	210.8	221.0	236.0	263.6	304.1	370.9
40°	179.4	179.9	182.4	185.1	188.5	193.5	201.9	214.0	234.2	266.4	315.3
42.5°	167.5	167.9	169.7	172.2	174.9	179.9	186.9	197.3	213.7	238.8	279.1
45°	149.9	149.9	151.5	152.6	155.6	160.1	165.8	174.5	185.8	204.4	231.2
47.5°	133.5	133.5	134.6	136.5	138.4	141.9	147.5	154.6	162.8	177.2	200.1
50°	124.0	124.3	124.9	126.5	127.7	130.8	135.2	141.3	149.9	161.1	180.1
52.5°	116.4	116.3	117.1	117.8	118.6	120.8	124.1	129.5	137.2	146.9	162.7
55°	104.0	103.1	104.5	105.6	106.3	107.2	109.0	112.4	119.0	127.2	139.0
57.5°	88.6	88.2	89.2	90.2	92.4	94.8	96.4	98.5	101.9	107.8	119.5
60°	75.9	75.9	77.9	78.6	81.1	84.3	87.5	89.3	92.7	96.5	105.2
62.5°	64.6	64.8	65.7	66.4	67.8	71.7	76.2	80.2	83.4	87.1	92.8
65°	54.1	54.5	54.5	55.0	55.9	56.8	58.6	61.8	67.5	72.7	77.0
67.5°	45.9	46.0	46.2	46.6	46.8	47.8	48.6	50.0	51.3	56.2	61.6
70°	40.4	41.1	40.9	41.3	41.6	42.0	42.9	43.6	45.7	46.8	50.0
72.5°	35.3	35.8	35.8	36.1	36.7	36.8	37.5	38.2	39.5	40.4	42.2
75°	28.6	28.4	28.6	29.1	29.3	29.5	29.5	30.4	31.1	32.0	33.2
77.5°	22.1	22.3	22.3	22.3	22.4	22.8	22.7	23.1	23.8	24.3	24.8
80°	17.7	17.9	17.7	17.9	18.2	18.4	18.2	18.4	19.1	19.5	19.5
82.5°	13.7	13.8	13.9	13.9	14.0	14.0	14.4	14.4	14.9	14.8	15.0
85°	8.2	8.0	8.0	8.0	8.2	8.4	8.2	8.2	8.4	8.4	8.4
87.5°	9.8	9.9	9.9	9.8	9.8	9.8	9.9	10.2	10.1	10.4	9.2
90°	34.4	34.2	34.0	33.8	33.5	33.6	34.1	34.5	35.0	35.4	30.5
92.5°	32.8	32.8	32.7	32.7	32.6	32.6	32.5	32.4	32.3	32.2	31.0
95°	62.8	63.2	63.7	64.1	64.6	64.8	64.8	64.8	64.8	64.8	64.4
97.5°	108.8	108.8	108.9	108.9	109.0	109.0	109.0	109.0	109.0	109.0	108.1
100°	138.8	139.0	139.2	139.4	139.7	139.8	139.8	139.8	139.8	139.8	139.1
102.5°	172.8	173.0	173.2	173.5	173.7	173.7	173.5	173.4	173.2	173.0	172.1
105°	224.9	224.9	224.9	224.9	224.9	224.6	224.2	223.7	223.3	222.8	222.4
107.5°	273.9	274.9	275.9	277.0	278.0	278.4	278.3	278.1	277.9	277.7	277.7
110°	312.0	312.6	313.3	314.0	314.7	315.0	315.0	315.0	315.0	315.0	315.0



TEST NUMBER: P331774

CATALOG NUMBER: S122RDIW-S290D970U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	348.4	348.9	349.4	349.9	350.4	350.9	351.5	352.0	352.5	353.1	353.3
115°	405.1	405.8	406.5	407.2	407.8	408.3	408.5	408.7	409.0	409.2	409.6
117.5°	459.2	459.9	460.6	461.3	461.9	462.5	463.1	463.6	464.2	464.7	466.0
120°	497.3	498.0	498.7	499.3	500.0	500.4	500.4	500.4	500.4	500.4	502.2
122.5°	534.6	535.1	535.6	536.1	536.6	537.1	537.6	538.2	538.7	539.2	540.5
125°	591.5	591.7	592.0	592.2	592.4	592.9	593.5	594.2	594.9	595.6	596.2
127.5°	643.4	644.1	644.8	645.5	646.2	647.0	647.8	648.6	649.4	650.3	651.1
130°	680.6	681.5	682.4	683.3	684.2	684.9	685.4	685.8	686.3	686.7	687.2
132.5°	716.3	717.0	717.7	718.5	719.2	720.0	721.0	722.0	723.0	724.0	723.9
135°	771.8	772.5	773.1	773.8	774.5	774.9	775.2	775.4	775.6	775.8	775.4
137.5°	822.0	822.9	823.8	824.7	825.6	826.2	826.4	826.5	826.7	826.9	826.3
140°	856.9	857.8	858.7	859.6	860.5	860.9	860.9	860.9	860.9	860.9	859.8
142.5°	888.5	889.4	890.3	891.2	892.1	892.4	892.3	892.1	891.9	891.7	891.0
145°	935.9	936.8	937.7	938.6	939.5	939.8	939.6	939.4	939.1	938.9	937.6
147.5°	978.2	979.1	979.9	980.8	981.6	981.8	981.3	980.8	980.3	979.8	978.9
150°	1005.8	1006.4	1007.1	1007.8	1008.5	1008.5	1007.8	1007.1	1006.4	1005.8	1004.9
152.5°	1031.7	1032.5	1033.4	1034.3	1035.1	1035.1	1034.3	1033.4	1032.5	1031.7	1030.6
155°	1066.5	1067.2	1067.9	1068.6	1069.2	1069.0	1067.9	1066.8	1065.6	1064.5	1063.8
157.5°	1096.5	1097.6	1098.7	1099.8	1100.8	1100.6	1099.1	1097.6	1096.0	1094.5	1094.1
160°	1115.2	1116.1	1117.0	1117.9	1118.8	1118.5	1117.2	1115.8	1114.5	1113.1	1112.9
162.5°	1131.4	1132.4	1133.5	1134.6	1135.7	1135.5	1133.9	1132.4	1130.9	1129.3	1129.1
165°	1152.6	1153.8	1154.9	1156.0	1157.1	1156.9	1155.3	1153.8	1152.2	1150.6	1150.6
167.5°	1170.1	1171.2	1172.4	1173.6	1174.7	1174.5	1173.0	1171.4	1169.8	1168.2	1168.3
170°	1179.0	1180.3	1181.7	1183.0	1184.4	1184.3	1182.7	1181.1	1179.5	1178.0	1178.2
172.5°	1186.3	1187.6	1189.0	1190.3	1191.7	1191.5	1190.0	1188.4	1186.8	1185.2	1185.5
175°	1194.2	1195.5	1196.9	1198.2	1199.6	1199.4	1197.9	1196.3	1194.7	1193.1	1193.6
177.5°	1197.8	1198.9	1200.0	1201.0	1202.1	1202.1	1201.0	1200.0	1198.9	1197.8	1198.2
180°	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2



TEST NUMBER: P331774

CATALOG NUMBER: S122RDIW-S290D970U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7
2.5°	669.4	667.9	666.6	663.4	661.7	658.1	657.6	657.4	652.7	648.1	646.8
5°	692.4	688.7	683.3	676.9	670.3	663.5	659.0	655.3	646.2	637.6	632.6
7.5°	715.5	707.7	698.3	686.3	676.2	665.0	656.6	649.1	636.2	623.8	615.5
10°	732.8	720.1	707.6	691.0	678.0	665.3	653.5	643.3	628.8	612.4	600.8
12.5°	743.5	729.5	712.3	696.1	679.3	663.1	647.3	634.2	617.1	600.2	586.5
15°	758.0	743.0	722.1	698.9	677.4	656.2	638.1	621.7	599.5	579.2	562.4
17.5°	769.9	749.2	726.8	700.0	675.0	648.2	624.8	603.9	579.1	554.7	534.9
20°	773.7	753.2	727.3	700.5	671.0	639.4	614.2	591.5	564.9	538.3	515.6
22.5°	771.3	755.4	726.6	694.5	664.3	631.3	602.8	576.4	546.9	519.8	493.5
25°	755.3	749.8	722.6	687.6	653.1	614.7	581.7	552.9	519.3	490.2	461.6
27.5°	717.9	729.7	712.8	675.5	637.1	596.0	558.9	526.1	491.2	458.5	430.0
30°	681.9	708.9	701.7	667.1	624.2	583.8	542.2	507.9	470.7	437.0	408.9
32.5°	632.7	677.3	684.4	655.5	611.1	566.7	523.1	489.0	450.1	414.7	387.2
35°	554.2	621.0	651.7	633.3	588.8	540.8	495.9	456.1	417.0	382.1	354.8
37.5°	460.7	551.7	602.8	604.1	563.2	513.4	464.4	424.9	384.9	350.6	321.1
40°	400.0	498.6	565.2	579.9	545.4	491.6	442.0	401.8	362.8	329.1	295.3
42.5°	345.5	443.7	525.5	551.2	523.8	470.3	420.6	378.6	340.6	308.8	274.2
45°	279.4	365.3	455.4	501.3	486.1	436.6	384.1	344.1	308.5	281.0	247.8
47.5°	235.7	296.2	383.5	445.5	445.3	400.1	348.4	310.2	277.1	251.3	224.5
50°	210.8	263.5	337.3	407.7	413.6	375.7	326.6	288.7	257.8	230.8	209.2
52.5°	188.4	231.9	298.2	365.8	382.6	349.7	302.1	267.1	237.1	212.2	193.8
55°	159.2	192.9	243.3	306.4	331.9	308.7	266.4	233.7	209.4	188.5	172.6
57.5°	134.7	159.9	200.4	251.2	280.8	266.3	231.4	204.8	184.0	165.1	152.6
60°	119.3	139.9	174.2	216.7	249.4	239.2	209.4	184.7	167.0	150.6	138.8
62.5°	104.7	122.5	151.9	186.4	216.3	212.1	187.8	167.0	151.5	136.6	126.6
65°	84.3	97.2	120.2	147.2	171.3	173.3	155.8	141.7	127.9	116.1	107.2
67.5°	67.1	75.6	91.7	114.5	132.5	139.0	128.3	117.5	106.5	97.4	89.7
70°	56.6	63.4	75.2	93.6	110.2	117.0	110.8	102.4	92.9	85.4	78.8
72.5°	45.8	52.5	61.2	74.7	88.9	96.3	94.1	88.1	80.4	74.1	67.9
75°	34.5	36.6	42.5	51.6	62.7	69.1	70.6	67.5	61.3	56.6	52.9
77.5°	25.5	26.8	29.6	34.3	41.6	47.3	49.6	49.2	45.0	42.3	38.8
80°	20.4	21.1	22.5	24.5	30.0	35.7	37.3	37.3	34.3	33.2	29.8
82.5°	15.5	16.0	16.9	18.0	20.5	25.5	27.3	27.6	25.8	24.3	21.6
85°	8.9	8.6	9.1	9.8	10.2	11.6	14.3	14.8	14.3	12.5	11.8
87.5°	8.2	7.4	6.4	5.5	5.1	4.7	5.1	5.5	5.3	5.3	5.5
90°	25.5	20.6	15.6	11.8	9.1	6.4	3.7	1.0	3.7	6.4	9.1
92.5°	29.9	28.7	27.5	26.0	24.0	22.0	20.0	18.0	20.0	22.0	24.0
95°	63.9	63.5	63.0	61.7	59.4	57.2	54.9	52.7	54.9	57.2	59.4
97.5°	107.3	106.4	105.6	104.1	102.2	100.2	98.2	96.2	98.2	100.2	102.2
100°	138.4	137.7	137.1	135.8	134.0	132.2	130.4	128.6	130.4	132.2	134.0
102.5°	171.3	170.4	169.6	168.4	167.0	165.5	164.1	162.7	164.1	165.5	167.0
105°	221.9	221.5	221.0	220.5	219.8	219.1	218.4	217.8	218.4	219.1	219.8
107.5°	277.7	277.7	277.7	277.2	276.2	275.2	274.3	273.3	274.3	275.2	276.2
110°	315.0	315.0	315.0	314.3	313.0	311.6	310.3	308.9	310.3	311.6	313.0



TEST NUMBER: P331774

CATALOG NUMBER: S122RDIW-S290D970U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	353.4	353.6	353.8	353.2	351.9	350.5	349.2	347.8	349.2	350.5	351.9
115°	410.1	410.5	411.0	410.5	409.2	407.8	406.5	405.1	406.5	407.8	409.2
117.5°	467.2	468.5	469.7	469.5	467.7	465.9	464.1	462.3	464.1	465.9	467.7
120°	504.0	505.8	507.6	507.6	505.8	504.0	502.2	500.4	502.2	504.0	505.8
122.5°	541.8	543.0	544.3	543.8	541.7	539.5	537.4	535.2	537.4	539.5	541.7
125°	596.9	597.6	598.3	597.6	595.6	593.5	591.5	589.5	591.5	593.5	595.6
127.5°	651.9	652.7	653.5	652.6	650.1	647.5	644.9	642.4	644.9	647.5	650.1
130°	687.6	688.1	688.5	687.3	684.4	681.4	678.5	675.6	678.5	681.4	684.4
132.5°	723.8	723.7	723.6	722.4	720.0	717.6	715.2	712.8	715.2	717.6	720.0
135°	774.9	774.5	774.0	772.6	770.1	767.6	765.2	762.7	765.2	767.6	770.1
137.5°	825.7	825.1	824.6	823.2	821.2	819.2	817.2	815.1	817.2	819.2	821.2
140°	858.7	857.6	856.4	854.8	852.8	850.8	848.8	846.7	848.8	850.8	852.8
142.5°	890.2	889.4	888.7	887.3	885.2	883.2	881.2	879.2	881.2	883.2	885.2
145°	936.2	934.9	933.5	932.1	930.5	928.9	927.3	925.7	927.3	928.9	930.5
147.5°	978.0	977.1	976.2	974.8	972.9	971.1	969.2	967.3	969.2	971.1	972.9
150°	1004.0	1003.1	1002.2	1001.0	999.7	998.3	997.0	995.6	997.0	998.3	999.7
152.5°	1029.5	1028.5	1027.4	1026.2	1024.8	1023.5	1022.1	1020.8	1022.1	1023.5	1024.8
155°	1063.2	1062.5	1061.8	1061.1	1060.5	1059.8	1059.1	1058.4	1059.1	1059.8	1060.5
157.5°	1093.7	1093.3	1092.9	1092.4	1092.0	1091.5	1091.1	1090.6	1091.1	1091.5	1092.0
160°	1112.7	1112.5	1112.2	1111.9	1111.4	1111.0	1110.5	1110.1	1110.5	1111.0	1111.4
162.5°	1128.9	1128.7	1128.4	1128.3	1128.2	1128.1	1128.0	1127.9	1128.0	1128.1	1128.2
165°	1150.6	1150.6	1150.6	1150.7	1150.9	1151.2	1151.4	1151.6	1151.4	1151.2	1150.9
167.5°	1168.3	1168.4	1168.4	1168.8	1169.4	1170.1	1170.8	1171.5	1170.8	1170.1	1169.4
170°	1178.4	1178.6	1178.9	1179.3	1180.0	1180.7	1181.3	1182.0	1181.3	1180.7	1180.0
172.5°	1185.7	1185.9	1186.1	1186.6	1187.3	1187.9	1188.6	1189.3	1188.6	1187.9	1187.3
175°	1194.0	1194.5	1194.9	1195.5	1196.2	1196.9	1197.5	1198.2	1197.5	1196.9	1196.2
177.5°	1198.5	1198.9	1199.2	1199.7	1200.2	1200.8	1201.3	1201.9	1201.3	1200.8	1200.2
180°	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2



TEST NUMBER: P331774

CATALOG NUMBER: S122RDIW-S290D970U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7
2.5°	644.5	643.2	640.8	637.2	635.0	631.2	628.7	630.1	630.5	630.1	629.8
5°	627.2	622.4	615.8	609.4	603.5	597.2	593.5	592.0	588.8	587.0	586.0
7.5°	606.2	598.0	588.7	577.6	568.2	558.3	553.3	550.8	544.3	540.8	537.7
10°	590.6	577.6	568.3	553.8	544.9	532.0	523.1	523.4	514.5	509.5	505.9
12.5°	573.3	559.1	543.6	530.5	518.2	507.8	497.1	492.8	483.4	478.6	468.8
15°	544.7	528.1	511.8	494.1	481.6	465.4	450.0	431.1	415.9	402.7	399.1
17.5°	513.5	492.9	476.5	455.7	434.3	407.2	389.3	378.3	369.2	362.2	357.0
20°	492.0	471.1	453.6	422.3	393.4	375.0	361.9	353.4	343.9	336.4	332.3
22.5°	469.5	447.7	423.8	388.8	366.3	351.6	339.9	330.2	323.7	317.9	314.1
25°	437.5	413.6	374.3	350.3	332.1	316.6	308.5	302.6	295.8	287.8	284.2
27.5°	403.7	365.8	337.5	319.6	302.3	292.3	284.9	276.1	270.0	266.4	262.6
30°	378.4	340.5	318.5	298.9	286.7	275.5	266.9	261.9	256.0	249.9	247.4
32.5°	350.3	320.0	298.8	282.6	270.1	260.6	253.8	245.7	241.5	237.7	232.5
35°	315.3	292.3	273.0	259.9	248.0	240.3	232.4	227.6	219.9	216.7	214.7
37.5°	285.7	265.8	251.4	237.5	228.1	219.6	214.7	207.1	203.8	199.3	195.0
40°	268.9	249.4	235.6	224.2	213.7	207.4	201.3	195.1	190.1	188.1	182.9
42.5°	251.9	236.0	222.1	209.7	202.7	195.9	188.2	183.7	178.5	175.2	172.0
45°	228.3	214.2	202.4	192.2	184.4	177.4	172.4	164.9	162.0	155.4	152.6
47.5°	207.6	194.5	183.2	173.5	166.0	161.4	154.1	148.2	143.5	139.4	135.9
50°	192.9	181.9	171.0	162.4	155.6	149.0	141.5	138.6	131.3	129.2	127.2
52.5°	179.4	169.0	159.1	150.6	143.8	137.4	130.8	126.9	122.0	120.0	118.5
55°	160.6	150.6	141.1	133.6	126.8	120.2	116.1	111.3	109.0	107.4	105.6
57.5°	141.7	132.7	125.4	117.8	110.9	105.7	101.0	98.1	95.8	93.7	91.5
60°	129.7	121.1	114.5	107.4	100.4	96.1	92.5	89.0	86.3	83.1	82.2
62.5°	117.0	109.4	103.4	96.5	90.4	86.5	83.0	79.8	76.5	71.9	70.6
65°	99.5	93.6	87.2	81.5	76.1	72.2	67.2	63.6	62.2	61.8	61.6
67.5°	83.7	78.1	72.6	66.8	61.9	58.3	55.7	55.2	54.2	54.0	53.3
70°	73.1	67.9	62.5	57.0	52.2	51.6	50.7	49.7	48.6	48.2	47.7
72.5°	63.7	58.3	52.8	48.5	46.4	45.6	44.7	43.7	43.0	42.5	42.3
75°	48.8	43.8	40.2	38.6	37.5	36.8	35.4	34.8	34.3	33.6	33.4
77.5°	35.2	32.3	30.7	29.7	28.5	27.8	27.0	26.3	25.8	25.7	25.3
80°	26.8	25.4	24.3	22.9	22.5	21.6	21.4	20.7	20.9	20.2	20.2
82.5°	20.8	19.1	18.1	17.5	17.0	16.3	16.1	15.8	15.8	15.3	15.3
85°	10.7	10.2	9.8	9.3	9.3	8.6	8.9	8.6	8.6	8.2	8.0
87.5°	5.8	6.4	7.0	8.0	9.0	9.8	9.7	9.5	9.4	9.3	9.1
90°	11.8	15.6	20.6	25.5	30.5	35.4	35.0	34.5	34.1	33.6	33.5
92.5°	26.0	27.5	28.7	29.9	31.0	32.2	32.3	32.4	32.5	32.6	32.6
95°	61.7	63.0	63.5	63.9	64.4	64.8	64.8	64.8	64.8	64.8	64.6
97.5°	104.1	105.6	106.4	107.3	108.1	109.0	109.0	109.0	109.0	109.0	109.0
100°	135.8	137.1	137.7	138.4	139.1	139.8	139.8	139.8	139.8	139.8	139.7
102.5°	168.4	169.6	170.4	171.3	172.1	173.0	173.2	173.4	173.5	173.7	173.7
105°	220.5	221.0	221.5	221.9	222.4	222.8	223.3	223.7	224.2	224.6	224.9
107.5°	277.2	277.7	277.7	277.7	277.7	277.7	277.9	278.1	278.3	278.4	278.0
110°	314.3	315.0	315.0	315.0	315.0	315.0	315.0	315.0	315.0	315.0	314.7



TEST NUMBER: P331774

CATALOG NUMBER: S122RDIW-S290D970U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	353.2	353.8	353.6	353.4	353.3	353.1	352.5	352.0	351.5	350.9	350.4
115°	410.5	411.0	410.5	410.1	409.6	409.2	409.0	408.7	408.5	408.3	407.8
117.5°	469.5	469.7	468.5	467.2	466.0	464.7	464.2	463.6	463.1	462.5	461.9
120°	507.6	507.6	505.8	504.0	502.2	500.4	500.4	500.4	500.4	500.4	500.0
122.5°	543.8	544.3	543.0	541.8	540.5	539.2	538.7	538.2	537.6	537.1	536.6
125°	597.6	598.3	597.6	596.9	596.2	595.6	594.9	594.2	593.5	592.9	592.4
127.5°	652.6	653.5	652.7	651.9	651.1	650.3	649.4	648.6	647.8	647.0	646.2
130°	687.3	688.5	688.1	687.6	687.2	686.7	686.3	685.8	685.4	684.9	684.2
132.5°	722.4	723.6	723.7	723.8	723.9	724.0	723.0	722.0	721.0	720.0	719.2
135°	772.6	774.0	774.5	774.9	775.4	775.8	775.6	775.4	775.2	774.9	774.5
137.5°	823.2	824.6	825.1	825.7	826.3	826.9	826.7	826.5	826.4	826.2	825.6
140°	854.8	856.4	857.6	858.7	859.8	860.9	860.9	860.9	860.9	860.9	860.5
142.5°	887.3	888.7	889.4	890.2	891.0	891.7	891.9	892.1	892.3	892.4	892.1
145°	932.1	933.5	934.9	936.2	937.6	938.9	939.1	939.4	939.6	939.8	939.5
147.5°	974.8	976.2	977.1	978.0	978.9	979.8	980.3	980.8	981.3	981.8	981.6
150°	1001.0	1002.2	1003.1	1004.0	1004.9	1005.8	1006.4	1007.1	1007.8	1008.5	1008.5
152.5°	1026.2	1027.4	1028.5	1029.5	1030.6	1031.7	1032.5	1033.4	1034.3	1035.1	1035.1
155°	1061.1	1061.8	1062.5	1063.2	1063.8	1064.5	1065.6	1066.8	1067.9	1069.0	1069.2
157.5°	1092.4	1092.9	1093.3	1093.7	1094.1	1094.5	1096.0	1097.6	1099.1	1100.6	1100.8
160°	1111.9	1112.2	1112.5	1112.7	1112.9	1113.1	1114.5	1115.8	1117.2	1118.5	1118.8
162.5°	1128.3	1128.4	1128.7	1128.9	1129.1	1129.3	1130.9	1132.4	1133.9	1135.5	1135.7
165°	1150.7	1150.6	1150.6	1150.6	1150.6	1150.6	1152.2	1153.8	1155.3	1156.9	1157.1
167.5°	1168.8	1168.4	1168.4	1168.3	1168.3	1168.2	1169.8	1171.4	1173.0	1174.5	1174.7
170°	1179.3	1178.9	1178.6	1178.4	1178.2	1178.0	1179.5	1181.1	1182.7	1184.3	1184.4
172.5°	1186.6	1186.1	1185.9	1185.7	1185.5	1185.2	1186.8	1188.4	1190.0	1191.5	1191.7
175°	1195.5	1194.9	1194.5	1194.0	1193.6	1193.1	1194.7	1196.3	1197.9	1199.4	1199.6
177.5°	1199.7	1199.2	1198.9	1198.5	1198.2	1197.8	1198.9	1200.0	1201.0	1202.1	1202.1
180°	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2



TEST NUMBER: P331774

CATALOG NUMBER: S122RDIW-S290D970U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7
2.5°	627.8	628.1	627.6	627.9	627.6	628.1	627.8	629.8	630.1	630.5	630.1
5°	584.9	582.2	581.7	581.1	581.7	582.2	584.9	586.0	587.0	588.8	592.0
7.5°	533.8	533.4	532.2	530.6	532.2	533.4	533.8	537.7	540.8	544.3	550.8
10°	500.9	499.7	499.5	497.9	499.5	499.7	500.9	505.9	509.5	514.5	523.4
12.5°	462.3	455.0	454.3	450.3	454.3	455.0	462.3	468.8	478.6	483.4	492.8
15°	393.7	392.3	387.7	384.8	387.7	392.3	393.7	399.1	402.7	415.9	431.1
17.5°	354.4	349.9	348.5	347.9	348.5	349.9	354.4	357.0	362.2	369.2	378.3
20°	329.1	325.1	324.4	323.9	324.4	325.1	329.1	332.3	336.4	343.9	353.4
22.5°	311.7	307.4	305.7	304.3	305.7	307.4	311.7	314.1	317.9	323.7	330.2
25°	281.9	280.3	279.4	278.9	279.4	280.3	281.9	284.2	287.8	295.8	302.6
27.5°	258.6	255.1	254.4	253.2	254.4	255.1	258.6	262.6	266.4	270.0	276.1
30°	245.3	244.2	242.6	241.2	242.6	244.2	245.3	247.4	249.9	256.0	261.9
32.5°	229.7	228.7	227.3	226.7	227.3	228.7	229.7	232.5	237.7	241.5	245.7
35°	212.4	209.2	207.8	205.8	207.8	209.2	212.4	214.7	216.7	219.9	227.6
37.5°	194.1	192.4	190.5	191.2	190.5	192.4	194.1	195.0	199.3	203.8	207.1
40°	179.9	178.8	178.3	178.1	178.3	178.8	179.9	182.9	188.1	190.1	195.1
42.5°	168.6	165.5	164.3	164.3	164.3	165.5	168.6	172.0	175.2	178.5	183.7
45°	151.5	148.6	146.5	146.7	146.5	148.6	151.5	152.6	155.4	162.0	164.9
47.5°	134.0	133.9	132.6	133.0	132.6	133.9	134.0	135.9	139.4	143.5	148.2
50°	125.6	124.3	123.3	123.6	123.3	124.3	125.6	127.2	129.2	131.3	138.6
52.5°	117.6	116.4	115.7	116.7	115.7	116.4	117.6	118.5	120.0	122.0	126.9
55°	104.5	103.1	102.9	102.7	102.9	103.1	104.5	105.6	107.4	109.0	111.3
57.5°	89.8	88.9	87.5	87.0	87.5	88.9	89.8	91.5	93.7	95.8	98.1
60°	79.3	77.5	75.2	75.0	75.2	77.5	79.3	82.2	83.1	86.3	89.0
62.5°	69.6	69.3	68.8	68.8	68.8	69.3	69.6	70.6	71.9	76.5	79.8
65°	61.1	60.9	61.1	61.3	61.1	60.9	61.1	61.6	61.8	62.2	63.6
67.5°	53.2	52.8	52.4	52.6	52.4	52.8	53.2	53.3	54.0	54.2	55.2
70°	47.2	47.0	46.8	46.8	46.8	47.0	47.2	47.7	48.2	48.6	49.7
72.5°	41.4	41.4	41.2	41.0	41.2	41.4	41.4	42.3	42.5	43.0	43.7
75°	33.2	32.7	32.7	32.7	32.7	32.7	33.2	33.4	33.6	34.3	34.8
77.5°	25.3	25.0	24.8	24.6	24.8	25.0	25.3	25.3	25.7	25.8	26.3
80°	20.0	19.8	19.5	19.5	19.5	19.8	20.0	20.2	20.2	20.9	20.7
82.5°	15.3	15.0	15.0	14.8	15.0	15.0	15.3	15.3	15.3	15.8	15.8
85°	8.2	8.4	8.2	8.6	8.2	8.4	8.2	8.0	8.2	8.6	8.6
87.5°	9.1	9.0	9.2	9.1	9.2	9.0	9.1	9.1	9.3	9.4	9.5
90°	33.8	34.0	34.2	34.4	34.2	34.0	33.8	33.5	33.6	34.1	34.5
92.5°	32.7	32.7	32.8	32.8	32.8	32.7	32.7	32.6	32.6	32.5	32.4
95°	64.1	63.7	63.2	62.8	63.2	63.7	64.1	64.6	64.8	64.8	64.8
97.5°	108.9	108.9	108.8	108.8	108.8	108.9	108.9	109.0	109.0	109.0	109.0
100°	139.4	139.2	139.0	138.8	139.0	139.2	139.4	139.7	139.8	139.8	139.8
102.5°	173.5	173.2	173.0	172.8	173.0	173.2	173.5	173.7	173.7	173.5	173.4
105°	224.9	224.9	224.9	224.9	224.9	224.9	224.9	224.9	224.6	224.2	223.7
107.5°	277.0	275.9	274.9	273.9	274.9	275.9	277.0	278.0	278.4	278.3	278.1
110°	314.0	313.3	312.6	312.0	312.6	313.3	314.0	314.7	315.0	315.0	315.0



TEST NUMBER: P331774

CATALOG NUMBER: S122RDIW-S290D970U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	349.9	349.4	348.9	348.4	348.9	349.4	349.9	350.4	350.9	351.5	352.0
115°	407.2	406.5	405.8	405.1	405.8	406.5	407.2	407.8	408.3	408.5	408.7
117.5°	461.3	460.6	459.9	459.2	459.9	460.6	461.3	461.9	462.5	463.1	463.6
120°	499.3	498.7	498.0	497.3	498.0	498.7	499.3	500.0	500.4	500.4	500.4
122.5°	536.1	535.6	535.1	534.6	535.1	535.6	536.1	536.6	537.1	537.6	538.2
125°	592.2	592.0	591.7	591.5	591.7	592.0	592.2	592.4	592.9	593.5	594.2
127.5°	645.5	644.8	644.1	643.4	644.1	644.8	645.5	646.2	647.0	647.8	648.6
130°	683.3	682.4	681.5	680.6	681.5	682.4	683.3	684.2	684.9	685.4	685.8
132.5°	718.5	717.7	717.0	716.3	717.0	717.7	718.5	719.2	720.0	721.0	722.0
135°	773.8	773.1	772.5	771.8	772.5	773.1	773.8	774.5	774.9	775.2	775.4
137.5°	824.7	823.8	822.9	822.0	822.9	823.8	824.7	825.6	826.2	826.4	826.5
140°	859.6	858.7	857.8	856.9	857.8	858.7	859.6	860.5	860.9	860.9	860.9
142.5°	891.2	890.3	889.4	888.5	889.4	890.3	891.2	892.1	892.4	892.3	892.1
145°	938.6	937.7	936.8	935.9	936.8	937.7	938.6	939.5	939.8	939.6	939.4
147.5°	980.8	979.9	979.1	978.2	979.1	979.9	980.8	981.6	981.8	981.3	980.8
150°	1007.8	1007.1	1006.4	1005.8	1006.4	1007.1	1007.8	1008.5	1008.5	1007.8	1007.1
152.5°	1034.3	1033.4	1032.5	1031.7	1032.5	1033.4	1034.3	1035.1	1035.1	1034.3	1033.4
155°	1068.6	1067.9	1067.2	1066.5	1067.2	1067.9	1068.6	1069.2	1069.0	1067.9	1066.8
157.5°	1099.8	1098.7	1097.6	1096.5	1097.6	1098.7	1099.8	1100.8	1100.6	1099.1	1097.6
160°	1117.9	1117.0	1116.1	1115.2	1116.1	1117.0	1117.9	1118.8	1118.5	1117.2	1115.8
162.5°	1134.6	1133.5	1132.4	1131.4	1132.4	1133.5	1134.6	1135.7	1135.5	1133.9	1132.4
165°	1156.0	1154.9	1153.8	1152.6	1153.8	1154.9	1156.0	1157.1	1156.9	1155.3	1153.8
167.5°	1173.6	1172.4	1171.2	1170.1	1171.2	1172.4	1173.6	1174.7	1174.5	1173.0	1171.4
170°	1183.0	1181.7	1180.3	1179.0	1180.3	1181.7	1183.0	1184.4	1184.3	1182.7	1181.1
172.5°	1190.3	1189.0	1187.6	1186.3	1187.6	1189.0	1190.3	1191.7	1191.5	1190.0	1188.4
175°	1198.2	1196.9	1195.5	1194.2	1195.5	1196.9	1198.2	1199.6	1199.4	1197.9	1196.3
177.5°	1201.0	1200.0	1198.9	1197.8	1198.9	1200.0	1201.0	1202.1	1202.1	1201.0	1200.0
180°	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2



TEST NUMBER: P331774

CATALOG NUMBER: S122RDIW-S290D970U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7
2.5°	628.7	631.2	635.0	637.2	640.8	643.2	644.5	646.8	648.1	652.7	657.4
5°	593.5	597.2	603.5	609.4	615.8	622.4	627.2	632.6	637.6	646.2	655.3
7.5°	553.3	558.3	568.2	577.6	588.7	598.0	606.2	615.5	623.8	636.2	649.1
10°	523.1	532.0	544.9	553.8	568.3	577.6	590.6	600.8	612.4	628.8	643.3
12.5°	497.1	507.8	518.2	530.5	543.6	559.1	573.3	586.5	600.2	617.1	634.2
15°	450.0	465.4	481.6	494.1	511.8	528.1	544.7	562.4	579.2	599.5	621.7
17.5°	389.3	407.2	434.3	455.7	476.5	492.9	513.5	534.9	554.7	579.1	603.9
20°	361.9	375.0	393.4	422.3	453.6	471.1	492.0	515.6	538.3	564.9	591.5
22.5°	339.9	351.6	366.3	388.8	423.8	447.7	469.5	493.5	519.8	546.9	576.4
25°	308.5	316.6	332.1	350.3	374.3	413.6	437.5	461.6	490.2	519.3	552.9
27.5°	284.9	292.3	302.3	319.6	337.5	365.8	403.7	430.0	458.5	491.2	526.1
30°	266.9	275.5	286.7	298.9	318.5	340.5	378.4	408.9	437.0	470.7	507.9
32.5°	253.8	260.6	270.1	282.6	298.8	320.0	350.3	387.2	414.7	450.1	489.0
35°	232.4	240.3	248.0	259.9	273.0	292.3	315.3	354.8	382.1	417.0	456.1
37.5°	214.7	219.6	228.1	237.5	251.4	265.8	285.7	321.1	350.6	384.9	424.9
40°	201.3	207.4	213.7	224.2	235.6	249.4	268.9	295.3	329.1	362.8	401.8
42.5°	188.2	195.9	202.7	209.7	222.1	236.0	251.9	274.2	308.8	340.6	378.6
45°	172.4	177.4	184.4	192.2	202.4	214.2	228.3	247.8	281.0	308.5	344.1
47.5°	154.1	161.4	166.0	173.5	183.2	194.5	207.6	224.5	251.3	277.1	310.2
50°	141.5	149.0	155.6	162.4	171.0	181.9	192.9	209.2	230.8	257.8	288.7
52.5°	130.8	137.4	143.8	150.6	159.1	169.0	179.4	193.8	212.2	237.1	267.1
55°	116.1	120.2	126.8	133.6	141.1	150.6	160.6	172.6	188.5	209.4	233.7
57.5°	101.0	105.7	110.9	117.8	125.4	132.7	141.7	152.6	165.1	184.0	204.8
60°	92.5	96.1	100.4	107.4	114.5	121.1	129.7	138.8	150.6	167.0	184.7
62.5°	83.0	86.5	90.4	96.5	103.4	109.4	117.0	126.6	136.6	151.5	167.0
65°	67.2	72.2	76.1	81.5	87.2	93.6	99.5	107.2	116.1	127.9	141.7
67.5°	55.7	58.3	61.9	66.8	72.6	78.1	83.7	89.7	97.4	106.5	117.5
70°	50.7	51.6	52.2	57.0	62.5	67.9	73.1	78.8	85.4	92.9	102.4
72.5°	44.7	45.6	46.4	48.5	52.8	58.3	63.7	67.9	74.1	80.4	88.1
75°	35.4	36.8	37.5	38.6	40.2	43.8	48.8	52.9	56.6	61.3	67.5
77.5°	27.0	27.8	28.5	29.7	30.7	32.3	35.2	38.8	42.3	45.0	49.2
80°	21.4	21.6	22.5	22.9	24.3	25.4	26.8	29.8	33.2	34.3	37.3
82.5°	16.1	16.3	17.0	17.5	18.1	19.1	20.8	21.6	24.3	25.8	27.6
85°	8.9	8.6	9.3	9.3	9.8	10.2	10.7	11.8	12.5	14.3	14.8
87.5°	9.7	9.8	9.0	8.0	7.0	6.4	5.8	5.5	5.3	5.3	5.5
90°	35.0	35.4	30.5	25.5	20.6	15.6	11.8	9.1	6.4	3.7	1.0
92.5°	32.3	32.2	31.0	29.9	28.7	27.5	26.0	24.0	22.0	20.0	18.0
95°	64.8	64.8	64.4	63.9	63.5	63.0	61.7	59.4	57.2	54.9	52.7
97.5°	109.0	109.0	108.1	107.3	106.4	105.6	104.1	102.2	100.2	98.2	96.2
100°	139.8	139.8	139.1	138.4	137.7	137.1	135.8	134.0	132.2	130.4	128.6
102.5°	173.2	173.0	172.1	171.3	170.4	169.6	168.4	167.0	165.5	164.1	162.7
105°	223.3	222.8	222.4	221.9	221.5	221.0	220.5	219.8	219.1	218.4	217.8
107.5°	277.9	277.7	277.7	277.7	277.7	277.7	277.2	276.2	275.2	274.3	273.3
110°	315.0	315.0	315.0	315.0	315.0	315.0	314.3	313.0	311.6	310.3	308.9



TEST NUMBER: P331774

CATALOG NUMBER: S122RDIW-S290D970U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	352.5	353.1	353.3	353.4	353.6	353.8	353.2	351.9	350.5	349.2	347.8
115°	409.0	409.2	409.6	410.1	410.5	411.0	410.5	409.2	407.8	406.5	405.1
117.5°	464.2	464.7	466.0	467.2	468.5	469.7	469.5	467.7	465.9	464.1	462.3
120°	500.4	500.4	502.2	504.0	505.8	507.6	507.6	505.8	504.0	502.2	500.4
122.5°	538.7	539.2	540.5	541.8	543.0	544.3	543.8	541.7	539.5	537.4	535.2
125°	594.9	595.6	596.2	596.9	597.6	598.3	597.6	595.6	593.5	591.5	589.5
127.5°	649.4	650.3	651.1	651.9	652.7	653.5	652.6	650.1	647.5	644.9	642.4
130°	686.3	686.7	687.2	687.6	688.1	688.5	687.3	684.4	681.4	678.5	675.6
132.5°	723.0	724.0	723.9	723.8	723.7	723.6	722.4	720.0	717.6	715.2	712.8
135°	775.6	775.8	775.4	774.9	774.5	774.0	772.6	770.1	767.6	765.2	762.7
137.5°	826.7	826.9	826.3	825.7	825.1	824.6	823.2	821.2	819.2	817.2	815.1
140°	860.9	860.9	859.8	858.7	857.6	856.4	854.8	852.8	850.8	848.8	846.7
142.5°	891.9	891.7	891.0	890.2	889.4	888.7	887.3	885.2	883.2	881.2	879.2
145°	939.1	938.9	937.6	936.2	934.9	933.5	932.1	930.5	928.9	927.3	925.7
147.5°	980.3	979.8	978.9	978.0	977.1	976.2	974.8	972.9	971.1	969.2	967.3
150°	1006.4	1005.8	1004.9	1004.0	1003.1	1002.2	1001.0	999.7	998.3	997.0	995.6
152.5°	1032.5	1031.7	1030.6	1029.5	1028.5	1027.4	1026.2	1024.8	1023.5	1022.1	1020.8
155°	1065.6	1064.5	1063.8	1063.2	1062.5	1061.8	1061.1	1060.5	1059.8	1059.1	1058.4
157.5°	1096.0	1094.5	1094.1	1093.7	1093.3	1092.9	1092.4	1092.0	1091.5	1091.1	1090.6
160°	1114.5	1113.1	1112.9	1112.7	1112.5	1112.2	1111.9	1111.4	1111.0	1110.5	1110.1
162.5°	1130.9	1129.3	1129.1	1128.9	1128.7	1128.4	1128.3	1128.2	1128.1	1128.0	1127.9
165°	1152.2	1150.6	1150.6	1150.6	1150.6	1150.6	1150.7	1150.9	1151.2	1151.4	1151.6
167.5°	1169.8	1168.2	1168.3	1168.3	1168.4	1168.4	1168.8	1169.4	1170.1	1170.8	1171.5
170°	1179.5	1178.0	1178.2	1178.4	1178.6	1178.9	1179.3	1180.0	1180.7	1181.3	1182.0
172.5°	1186.8	1185.2	1185.5	1185.7	1185.9	1186.1	1186.6	1187.3	1187.9	1188.6	1189.3
175°	1194.7	1193.1	1193.6	1194.0	1194.5	1194.9	1195.5	1196.2	1196.9	1197.5	1198.2
177.5°	1198.9	1197.8	1198.2	1198.5	1198.9	1199.2	1199.7	1200.2	1200.8	1201.3	1201.9
180°	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2



TEST NUMBER: P331774

CATALOG NUMBER: S122RDIW-S290D970U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7
2.5°	657.6	658.1	661.7	663.4	666.6	667.9	669.4	669.0	669.0	669.7	674.8
5°	659.0	663.5	670.3	676.9	683.3	688.7	692.4	696.0	697.4	703.9	709.8
7.5°	656.6	665.0	676.2	686.3	698.3	707.7	715.5	722.6	727.4	737.0	746.8
10°	653.5	665.3	678.0	691.0	707.6	720.1	732.8	742.6	745.7	760.0	768.2
12.5°	647.3	663.1	679.3	696.1	712.3	729.5	743.5	753.3	764.5	777.3	792.4
15°	638.1	656.2	677.4	698.9	722.1	743.0	758.0	775.0	787.3	801.4	814.6
17.5°	624.8	648.2	675.0	700.0	726.8	749.2	769.9	786.2	794.8	802.9	804.8
20°	614.2	639.4	671.0	700.5	727.3	753.2	773.7	787.3	789.6	789.8	777.8
22.5°	602.8	631.3	664.3	694.5	726.6	755.4	771.3	777.1	768.1	752.7	729.4
25°	581.7	614.7	653.1	687.6	722.6	749.8	755.3	745.1	713.5	680.3	638.3
27.5°	558.9	596.0	637.1	675.5	712.8	729.7	717.9	681.0	624.2	574.7	514.8
30°	542.2	583.8	624.2	667.1	701.7	708.9	681.9	627.6	561.3	486.8	427.0
32.5°	523.1	566.7	611.1	655.5	684.4	677.3	632.7	565.8	488.1	414.8	358.4
35°	495.9	540.8	588.8	633.3	651.7	621.0	554.2	467.2	387.7	319.4	280.5
37.5°	464.4	513.4	563.2	604.1	602.8	551.7	460.7	370.9	304.1	263.6	236.0
40°	442.0	491.6	545.4	579.9	565.2	498.6	400.0	315.3	266.4	234.2	214.0
42.5°	420.6	470.3	523.8	551.2	525.5	443.7	345.5	279.1	238.8	213.7	197.3
45°	384.1	436.6	486.1	501.3	455.4	365.3	279.4	231.2	204.4	185.8	174.5
47.5°	348.4	400.1	445.3	445.5	383.5	296.2	235.7	200.1	177.2	162.8	154.6
50°	326.6	375.7	413.6	407.7	337.3	263.5	210.8	180.1	161.1	149.9	141.3
52.5°	302.1	349.7	382.6	365.8	298.2	231.9	188.4	162.7	146.9	137.2	129.5
55°	266.4	308.7	331.9	306.4	243.3	192.9	159.2	139.0	127.2	119.0	112.4
57.5°	231.4	266.3	280.8	251.2	200.4	159.9	134.7	119.5	107.8	101.9	98.5
60°	209.4	239.2	249.4	216.7	174.2	139.9	119.3	105.2	96.5	92.7	89.3
62.5°	187.8	212.1	216.3	186.4	151.9	122.5	104.7	92.8	87.1	83.4	80.2
65°	155.8	173.3	171.3	147.2	120.2	97.2	84.3	77.0	72.7	67.5	61.8
67.5°	128.3	139.0	132.5	114.5	91.7	75.6	67.1	61.6	56.2	51.3	50.0
70°	110.8	117.0	110.2	93.6	75.2	63.4	56.6	50.0	46.8	45.7	43.6
72.5°	94.1	96.3	88.9	74.7	61.2	52.5	45.8	42.2	40.4	39.5	38.2
75°	70.6	69.1	62.7	51.6	42.5	36.6	34.5	33.2	32.0	31.1	30.4
77.5°	49.6	47.3	41.6	34.3	29.6	26.8	25.5	24.8	24.3	23.8	23.1
80°	37.3	35.7	30.0	24.5	22.5	21.1	20.4	19.5	19.5	19.1	18.4
82.5°	27.3	25.5	20.5	18.0	16.9	16.0	15.5	15.0	14.8	14.9	14.4
85°	14.3	11.6	10.2	9.8	9.1	8.6	8.9	8.4	8.4	8.4	8.2
87.5°	5.1	4.7	5.1	5.5	6.4	7.4	8.2	9.2	10.4	10.1	10.2
90°	3.7	6.4	9.1	11.8	15.6	20.6	25.5	30.5	35.4	35.0	34.5
92.5°	20.0	22.0	24.0	26.0	27.5	28.7	29.9	31.0	32.2	32.3	32.4
95°	54.9	57.2	59.4	61.7	63.0	63.5	63.9	64.4	64.8	64.8	64.8
97.5°	98.2	100.2	102.2	104.1	105.6	106.4	107.3	108.1	109.0	109.0	109.0
100°	130.4	132.2	134.0	135.8	137.1	137.7	138.4	139.1	139.8	139.8	139.8
102.5°	164.1	165.5	167.0	168.4	169.6	170.4	171.3	172.1	173.0	173.2	173.4
105°	218.4	219.1	219.8	220.5	221.0	221.5	221.9	222.4	222.8	223.3	223.7
107.5°	274.3	275.2	276.2	277.2	277.7	277.7	277.7	277.7	277.7	277.9	278.1
110°	310.3	311.6	313.0	314.3	315.0	315.0	315.0	315.0	315.0	315.0	315.0



TEST NUMBER: P331774

CATALOG NUMBER: S122RDIW-S290D970U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	349.2	350.5	351.9	353.2	353.8	353.6	353.4	353.3	353.1	352.5	352.0
115°	406.5	407.8	409.2	410.5	411.0	410.5	410.1	409.6	409.2	409.0	408.7
117.5°	464.1	465.9	467.7	469.5	469.7	468.5	467.2	466.0	464.7	464.2	463.6
120°	502.2	504.0	505.8	507.6	507.6	505.8	504.0	502.2	500.4	500.4	500.4
122.5°	537.4	539.5	541.7	543.8	544.3	543.0	541.8	540.5	539.2	538.7	538.2
125°	591.5	593.5	595.6	597.6	598.3	597.6	596.9	596.2	595.6	594.9	594.2
127.5°	644.9	647.5	650.1	652.6	653.5	652.7	651.9	651.1	650.3	649.4	648.6
130°	678.5	681.4	684.4	687.3	688.5	688.1	687.6	687.2	686.7	686.3	685.8
132.5°	715.2	717.6	720.0	722.4	723.6	723.7	723.8	723.9	724.0	723.0	722.0
135°	765.2	767.6	770.1	772.6	774.0	774.5	774.9	775.4	775.8	775.6	775.4
137.5°	817.2	819.2	821.2	823.2	824.6	825.1	825.7	826.3	826.9	826.7	826.5
140°	848.8	850.8	852.8	854.8	856.4	857.6	858.7	859.8	860.9	860.9	860.9
142.5°	881.2	883.2	885.2	887.3	888.7	889.4	890.2	891.0	891.7	891.9	892.1
145°	927.3	928.9	930.5	932.1	933.5	934.9	936.2	937.6	938.9	939.1	939.4
147.5°	969.2	971.1	972.9	974.8	976.2	977.1	978.0	978.9	979.8	980.3	980.8
150°	997.0	998.3	999.7	1001.0	1002.2	1003.1	1004.0	1004.9	1005.8	1006.4	1007.1
152.5°	1022.1	1023.5	1024.8	1026.2	1027.4	1028.5	1029.5	1030.6	1031.7	1032.5	1033.4
155°	1059.1	1059.8	1060.5	1061.1	1061.8	1062.5	1063.2	1063.8	1064.5	1065.6	1066.8
157.5°	1091.1	1091.5	1092.0	1092.4	1092.9	1093.3	1093.7	1094.1	1094.5	1096.0	1097.6
160°	1110.5	1111.0	1111.4	1111.9	1112.2	1112.5	1112.7	1112.9	1113.1	1114.5	1115.8
162.5°	1128.0	1128.1	1128.2	1128.3	1128.4	1128.7	1128.9	1129.1	1129.3	1130.9	1132.4
165°	1151.4	1151.2	1150.9	1150.7	1150.6	1150.6	1150.6	1150.6	1150.6	1152.2	1153.8
167.5°	1170.8	1170.1	1169.4	1168.8	1168.4	1168.4	1168.3	1168.3	1168.2	1169.8	1171.4
170°	1181.3	1180.7	1180.0	1179.3	1178.9	1178.6	1178.4	1178.2	1178.0	1179.5	1181.1
172.5°	1188.6	1187.9	1187.3	1186.6	1186.1	1185.9	1185.7	1185.5	1185.2	1186.8	1188.4
175°	1197.5	1196.9	1196.2	1195.5	1194.9	1194.5	1194.0	1193.6	1193.1	1194.7	1196.3
177.5°	1201.3	1200.8	1200.2	1199.7	1199.2	1198.9	1198.5	1198.2	1197.8	1198.9	1200.0
180°	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2



TEST NUMBER: P331774

CATALOG NUMBER: S122RDIW-S290D970U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	653.7	653.7	653.7	653.7	653.7	653.7	653.7
2.5°	676.6	679.0	680.1	680.1	681.4	680.8	680.3
5°	715.5	719.8	720.8	724.8	727.8	726.9	727.3
7.5°	754.2	761.1	768.0	771.1	771.6	773.4	774.1
10°	778.0	783.7	794.3	792.8	800.7	805.3	797.8
12.5°	800.9	808.6	816.0	818.0	822.5	824.0	821.0
15°	821.6	825.7	826.1	825.0	826.4	825.2	820.9
17.5°	802.3	795.6	782.2	775.8	770.8	763.3	760.3
20°	770.3	750.7	728.0	718.9	708.3	687.4	692.4
22.5°	701.2	679.0	656.2	629.7	617.0	597.2	596.0
25°	593.8	555.4	513.1	483.6	466.3	446.6	437.9
27.5°	461.7	413.3	378.7	361.2	345.2	329.6	328.9
30°	374.8	338.5	311.7	296.7	286.9	280.3	281.7
32.5°	315.9	291.0	272.9	260.5	253.3	248.3	248.2
35°	258.3	241.2	229.6	224.4	219.2	215.6	215.8
37.5°	221.0	210.8	204.3	198.6	195.3	193.5	192.5
40°	201.9	193.5	188.5	185.1	182.4	179.9	179.4
42.5°	186.9	179.9	174.9	172.2	169.7	167.9	167.5
45°	165.8	160.1	155.6	152.6	151.5	149.9	149.9
47.5°	147.5	141.9	138.4	136.5	134.6	133.5	133.5
50°	135.2	130.8	127.7	126.5	124.9	124.3	124.0
52.5°	124.1	120.8	118.6	117.8	117.1	116.3	116.4
55°	109.0	107.2	106.3	105.6	104.5	103.1	104.0
57.5°	96.4	94.8	92.4	90.2	89.2	88.2	88.6
60°	87.5	84.3	81.1	78.6	77.9	75.9	75.9
62.5°	76.2	71.7	67.8	66.4	65.7	64.8	64.6
65°	58.6	56.8	55.9	55.0	54.5	54.5	54.1
67.5°	48.6	47.8	46.8	46.6	46.2	46.0	45.9
70°	42.9	42.0	41.6	41.3	40.9	41.1	40.4
72.5°	37.5	36.8	36.7	36.1	35.8	35.8	35.3
75°	29.5	29.5	29.3	29.1	28.6	28.4	28.6
77.5°	22.7	22.8	22.4	22.3	22.3	22.3	22.1
80°	18.2	18.4	18.2	17.9	17.7	17.9	17.7
82.5°	14.4	14.0	14.0	13.9	13.9	13.8	13.7
85°	8.2	8.4	8.2	8.0	8.0	8.0	8.2
87.5°	9.9	9.8	9.8	9.8	9.9	9.9	9.8
90°	34.1	33.6	33.5	33.8	34.0	34.2	34.4
92.5°	32.5	32.6	32.6	32.7	32.7	32.8	32.8
95°	64.8	64.8	64.6	64.1	63.7	63.2	62.8
97.5°	109.0	109.0	109.0	108.9	108.9	108.8	108.8
100°	139.8	139.8	139.7	139.4	139.2	139.0	138.8
102.5°	173.5	173.7	173.7	173.5	173.2	173.0	172.8
105°	224.2	224.6	224.9	224.9	224.9	224.9	224.9
107.5°	278.3	278.4	278.0	277.0	275.9	274.9	273.9
110°	315.0	315.0	314.7	314.0	313.3	312.6	312.0



TEST NUMBER: P331774

CATALOG NUMBER: S122RDIW-S290D970U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	351.5	350.9	350.4	349.9	349.4	348.9	348.4
115°	408.5	408.3	407.8	407.2	406.5	405.8	405.1
117.5°	463.1	462.5	461.9	461.3	460.6	459.9	459.2
120°	500.4	500.4	500.0	499.3	498.7	498.0	497.3
122.5°	537.6	537.1	536.6	536.1	535.6	535.1	534.6
125°	593.5	592.9	592.4	592.2	592.0	591.7	591.5
127.5°	647.8	647.0	646.2	645.5	644.8	644.1	643.4
130°	685.4	684.9	684.2	683.3	682.4	681.5	680.6
132.5°	721.0	720.0	719.2	718.5	717.7	717.0	716.3
135°	775.2	774.9	774.5	773.8	773.1	772.5	771.8
137.5°	826.4	826.2	825.6	824.7	823.8	822.9	822.0
140°	860.9	860.9	860.5	859.6	858.7	857.8	856.9
142.5°	892.3	892.4	892.1	891.2	890.3	889.4	888.5
145°	939.6	939.8	939.5	938.6	937.7	936.8	935.9
147.5°	981.3	981.8	981.6	980.8	979.9	979.1	978.2
150°	1007.8	1008.5	1008.5	1007.8	1007.1	1006.4	1005.8
152.5°	1034.3	1035.1	1035.1	1034.3	1033.4	1032.5	1031.7
155°	1067.9	1069.0	1069.2	1068.6	1067.9	1067.2	1066.5
157.5°	1099.1	1100.6	1100.8	1099.8	1098.7	1097.6	1096.5
160°	1117.2	1118.5	1118.8	1117.9	1117.0	1116.1	1115.2
162.5°	1133.9	1135.5	1135.7	1134.6	1133.5	1132.4	1131.4
165°	1155.3	1156.9	1157.1	1156.0	1154.9	1153.8	1152.6
167.5°	1173.0	1174.5	1174.7	1173.6	1172.4	1171.2	1170.1
170°	1182.7	1184.3	1184.4	1183.0	1181.7	1180.3	1179.0
172.5°	1190.0	1191.5	1191.7	1190.3	1189.0	1187.6	1186.3
175°	1197.9	1199.4	1199.6	1198.2	1196.9	1195.5	1194.2
177.5°	1201.0	1202.1	1202.1	1201.0	1200.0	1198.9	1197.8
180°	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2	1200.2

(END OF REPORT)