

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331490-935

Luminaire Tested: **S122DIW-S290D1440U935-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331490-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S290D1440U935-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1440 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5429.8 lumens
Efficiency: N/A
Efficacy: 101.7 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331490-935

CATALOG NUMBER: S122DIW-S290D1440U935-4F0-1E-UDD-A1

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - - - 90°-270° - - - 135°-315°



TEST NUMBER: P331490-935

CATALOG NUMBER: S122DIW-S290D1440U935-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	100	100	100	100	89	89	89	89	67	67	67	47	47	47	29	29	29	21				
1	91	87	84	80	81	77	74	72	59	57	55	42	41	40	26	26	25	18				
2	83	76	71	66	74	68	63	59	52	49	46	37	35	33	23	22	21	15				
3	76	67	60	55	67	60	54	49	46	42	39	33	30	28	21	19	18	13				
4	70	60	52	46	61	53	47	42	41	36	33	29	27	24	19	17	16	11				
5	64	53	45	40	56	47	41	36	36	32	28	26	23	21	17	15	14	10				
6	59	47	40	34	52	42	36	31	33	28	25	24	21	18	15	14	12	9				
7	54	43	35	30	48	38	32	27	30	25	22	22	19	16	14	12	11	8				
8	50	39	31	26	44	35	28	24	27	22	19	20	17	14	13	11	10	7				
9	47	35	28	23	41	31	25	21	25	20	17	18	15	13	12	10	9	7				
10	43	32	25	21	38	29	23	19	22	18	15	17	14	12	11	9	8	6				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8217	8217	8217	8217
5°	9211	8271	7329	8271
10°	10557	8202	6342	8202
15°	11677	8052	5605	8052
20°	11500	7892	5108	7892
25°	10368	7675	4794	7675
30°	8569	7333	4566	7333
35°	6244	6974	4401	6974
40°	4989	6551	4312	6551
45°	4359	6060	4190	6060
50°	4099	5586	4107	5586
55°	3775	5103	3997	5103
60°	3462	4592	3830	4592
65°	3156	4130	3660	4130
70°	2861	3682	3418	3682
75°	2539	3188	3026	3188
80°	2185	2631	2436	2631
85°	1964	1964	1445	1964



TEST NUMBER: P331490-935

CATALOG NUMBER: S122DIW-S290D1440U935-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.5	0.9
10°-20°	140.9	2.6
20°-30°	204.5	3.8
30°-40°	215.8	4.0
40°-50°	191.1	3.5
50°-60°	152.5	2.8
60°-70°	103.6	1.9
70°-80°	53.1	1.0
80°-90°	19.0	0.3
90°-100°	97.5	1.8
100°-110°	302.7	5.6
110°-120°	517.4	9.5
120°-130°	680.4	12.5
130°-140°	763.7	14.1
140°-150°	748.8	13.8
150°-160°	628.1	11.6
160°-170°	416.6	7.7
170°-180°	145.6	2.7
0°-30°	393.9	7.3
0°-40°	609.7	11.2
0°-60°	953.2	17.6
0°-90°	1128.9	20.8
90°-120°	917.6	16.9
90°-150°	3110.6	57.3
90°-180°	4301.0	79.2
0°-180°	5429.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	509	509	509	509	509	
5°	568	510	452	510	568	57
15°	699	482	335	482	699	193
25°	582	431	269	431	582	263
35°	317	354	223	354	317	206
45°	191	265	184	265	191	150
55°	134	181	142	181	134	120
65°	83	108	96	108	83	82
75°	41	51	48	51	41	43
85°	11	11	8	11	11	13
90°	44	1	44	1	44	20
95°	80	68	80	68	80	90
105°	288	279	288	279	288	303
115°	519	519	519	519	519	513
125°	758	755	758	755	758	676
135°	989	977	989	977	989	761
145°	1199	1186	1199	1186	1199	749
155°	1367	1356	1367	1356	1367	629
165°	1477	1476	1477	1476	1477	417
175°	1530	1536	1530	1536	1530	145
180°	1538	1538	1538	1538	1538	



TEST NUMBER: P331490-935

CATALOG NUMBER: S122DIW-S290D1440U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	532.4	532.5	532.9	530.4	530.0	530.0	527.9	526.0	523.7	520.8	521.2
5°	568.3	570.5	571.3	568.9	565.4	565.1	561.7	556.3	551.1	547.1	544.2
7.5°	611.3	612.2	610.3	607.2	604.6	599.9	593.7	587.6	579.1	571.4	565.6
10°	643.9	645.1	641.7	637.2	633.5	628.0	619.1	609.8	598.7	588.0	579.4
12.5°	668.6	671.5	667.2	666.7	660.3	652.7	642.0	637.4	621.7	606.7	597.4
15°	698.6	698.4	698.9	695.1	690.4	689.2	678.0	665.6	643.5	634.6	619.4
17.5°	689.9	692.9	694.3	694.2	694.1	693.4	689.7	682.0	670.9	656.6	639.0
20°	669.3	673.2	673.8	678.3	680.9	684.2	685.5	683.4	676.6	664.6	649.4
22.5°	637.4	638.5	640.3	647.3	652.8	661.2	665.5	672.8	670.1	664.3	651.5
25°	582.0	580.1	586.9	590.5	603.2	616.5	626.1	636.6	646.0	651.7	648.0
27.5°	515.7	512.7	523.0	532.4	542.6	557.1	572.0	589.6	604.2	622.7	629.0
30°	459.6	461.4	471.1	481.1	496.8	517.1	534.0	553.3	574.3	594.8	609.1
32.5°	399.2	406.0	412.2	427.5	441.3	463.9	488.6	512.8	538.9	562.2	584.4
35°	316.8	324.7	333.3	344.4	363.8	386.2	410.4	443.0	478.6	510.5	536.7
37.5°	266.7	265.4	270.4	278.4	294.1	312.3	340.0	372.2	414.1	451.6	488.6
40°	236.7	235.9	239.4	246.8	258.7	272.1	296.4	324.7	363.6	409.4	453.4
42.5°	216.0	216.5	218.4	223.7	231.9	242.8	261.0	285.1	320.7	363.9	411.1
45°	190.9	192.3	194.4	197.0	201.6	210.7	220.8	238.1	266.2	302.2	348.7
47.5°	172.8	172.9	175.0	177.3	180.0	185.1	193.5	204.2	224.1	253.4	293.4
50°	163.2	161.8	163.3	165.1	168.0	171.5	177.0	187.2	200.4	224.1	257.6
52.5°	151.2	151.3	152.7	153.3	155.9	159.5	164.5	171.5	183.6	202.1	229.5
55°	134.1	135.2	136.0	137.1	139.5	142.0	145.9	150.6	160.0	173.8	194.2
57.5°	118.1	118.5	119.2	121.5	123.0	125.3	129.0	133.3	139.4	149.6	165.0
60°	107.2	107.2	108.7	109.7	111.7	114.0	116.9	121.1	126.6	134.9	147.3
62.5°	97.2	97.0	97.6	99.3	100.7	102.9	105.8	109.3	114.5	122.0	132.1
65°	82.6	82.1	83.3	83.7	85.2	87.4	89.8	93.5	97.6	103.1	112.1
67.5°	68.4	69.0	69.6	70.3	71.1	73.4	75.0	77.6	81.1	85.7	91.7
70°	60.6	60.6	60.6	61.2	62.4	63.5	65.1	67.2	70.6	74.5	80.0
72.5°	51.8	52.5	53.1	52.8	54.2	54.9	56.8	58.0	61.2	63.7	68.5
75°	40.7	40.7	40.7	41.7	42.3	42.8	44.0	45.2	46.8	49.9	52.4
77.5°	30.4	30.3	30.5	30.7	31.3	32.0	32.4	33.4	34.9	36.3	38.5
80°	23.5	23.8	24.0	24.5	24.5	24.8	25.1	26.4	27.4	28.3	29.7
82.5°	18.2	18.3	18.3	18.3	18.5	18.8	19.3	19.7	20.1	20.8	21.9
85°	10.6	10.3	10.3	10.8	10.6	10.6	10.9	11.4	11.4	11.5	12.1
87.5°	12.9	12.8	12.9	12.7	12.7	12.8	13.0	12.9	13.2	13.4	12.3
90°	44.2	43.8	43.6	43.3	43.0	43.1	43.7	44.3	44.9	45.5	39.1
92.5°	42.0	42.0	41.9	41.8	41.8	41.8	41.6	41.5	41.4	41.2	39.8
95°	80.5	81.0	81.6	82.2	82.7	83.1	83.1	83.1	83.1	83.1	82.5
97.5°	139.4	139.5	139.5	139.6	139.7	139.7	139.7	139.7	139.7	139.7	138.5
100°	177.8	178.1	178.4	178.7	179.0	179.1	179.1	179.1	179.1	179.1	178.2
102.5°	221.4	221.7	222.1	222.3	222.6	222.7	222.4	222.1	222.0	221.7	220.6
105°	288.2	288.2	288.2	288.2	288.2	287.8	287.3	286.7	286.1	285.6	285.0
107.5°	350.9	352.3	353.6	355.0	356.3	356.8	356.6	356.4	356.1	355.9	355.9
110°	399.8	400.6	401.5	402.3	403.2	403.7	403.7	403.7	403.7	403.7	403.7



TEST NUMBER: P331490-935

CATALOG NUMBER: S122DIW-S290D1440U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	446.5	447.1	447.8	448.4	449.0	449.7	450.4	451.1	451.8	452.5	452.7
115°	519.2	520.0	520.9	521.8	522.6	523.2	523.5	523.8	524.1	524.4	525.0
117.5°	588.5	589.4	590.2	591.1	591.9	592.8	593.5	594.2	594.9	595.6	597.1
120°	637.3	638.2	639.0	639.9	640.8	641.2	641.2	641.2	641.2	641.2	643.5
122.5°	685.1	685.7	686.4	687.0	687.6	688.3	689.0	689.7	690.3	691.0	692.7
125°	758.0	758.4	758.6	758.9	759.2	759.7	760.6	761.5	762.3	763.2	764.1
127.5°	824.5	825.4	826.3	827.2	828.2	829.1	830.2	831.2	832.2	833.4	834.4
130°	872.3	873.4	874.6	875.7	876.8	877.7	878.3	878.9	879.5	880.0	880.6
132.5°	917.9	918.9	919.8	920.8	921.6	922.7	924.0	925.3	926.5	927.8	927.7
135°	989.1	990.0	990.8	991.7	992.6	993.2	993.4	993.7	994.0	994.3	993.7
137.5°	1053.4	1054.6	1055.8	1057.0	1058.1	1058.8	1059.0	1059.2	1059.5	1059.7	1058.9
140°	1098.1	1099.2	1100.4	1101.6	1102.8	1103.3	1103.3	1103.3	1103.3	1103.3	1101.9
142.5°	1138.6	1139.8	1140.9	1142.1	1143.2	1143.7	1143.5	1143.2	1143.0	1142.8	1141.8
145°	1199.4	1200.5	1201.7	1202.8	1203.9	1204.4	1204.1	1203.9	1203.5	1203.2	1201.5
147.5°	1253.6	1254.7	1255.8	1256.9	1258.0	1258.3	1257.6	1257.0	1256.4	1255.7	1254.6
150°	1288.9	1289.8	1290.6	1291.5	1292.4	1292.4	1291.5	1290.6	1289.8	1288.9	1287.8
152.5°	1322.2	1323.3	1324.3	1325.4	1326.5	1326.5	1325.4	1324.3	1323.3	1322.2	1320.8
155°	1366.8	1367.7	1368.6	1369.4	1370.3	1369.9	1368.6	1367.1	1365.6	1364.2	1363.3
157.5°	1405.2	1406.6	1408.0	1409.4	1410.7	1410.5	1408.5	1406.5	1404.5	1402.7	1402.1
160°	1429.1	1430.3	1431.4	1432.5	1433.7	1433.4	1431.7	1429.9	1428.2	1426.5	1426.2
162.5°	1449.8	1451.3	1452.7	1454.1	1455.4	1455.1	1453.2	1451.2	1449.2	1447.3	1447.0
165°	1477.1	1478.6	1480.1	1481.4	1482.9	1482.6	1480.6	1478.6	1476.5	1474.5	1474.5
167.5°	1499.4	1501.0	1502.4	1504.0	1505.5	1505.2	1503.2	1501.2	1499.2	1497.1	1497.2
170°	1510.9	1512.6	1514.3	1516.0	1517.8	1517.7	1515.6	1513.6	1511.6	1509.6	1509.8
172.5°	1520.3	1522.0	1523.7	1525.4	1527.2	1527.0	1525.0	1522.9	1521.0	1518.9	1519.2
175°	1530.3	1532.1	1533.8	1535.5	1537.3	1537.1	1535.1	1533.1	1531.1	1529.0	1529.7
177.5°	1535.0	1536.4	1537.8	1539.2	1540.6	1540.6	1539.2	1537.8	1536.4	1535.0	1535.5
180°	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2



TEST NUMBER: P331490-935

CATALOG NUMBER: S122DIW-S290D1440U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	522.2	521.0	520.2	517.4	514.9	512.4	511.6	511.9	508.4	505.1	503.8
5°	542.6	538.6	534.9	529.7	523.4	516.5	513.1	510.3	503.4	496.0	491.7
7.5°	560.8	555.2	548.0	538.1	529.0	518.2	511.3	505.3	495.3	484.8	478.4
10°	571.9	564.3	555.1	542.9	531.8	518.7	509.5	500.3	488.6	476.0	468.2
12.5°	581.4	571.2	562.1	546.6	533.4	516.9	506.1	493.1	480.8	465.9	458.2
15°	604.2	585.2	568.0	550.4	534.2	511.3	499.1	481.7	465.5	447.1	438.3
17.5°	621.7	600.4	573.3	551.0	532.0	506.6	488.9	468.0	448.8	427.8	415.9
20°	631.7	607.3	578.2	551.6	528.9	499.9	480.5	459.3	436.8	413.1	400.2
22.5°	637.7	612.0	583.2	549.2	522.6	494.5	470.1	446.7	424.0	398.4	384.9
25°	639.6	616.1	585.6	547.3	514.8	482.9	453.6	430.8	403.3	379.4	359.7
27.5°	630.3	613.5	584.1	543.5	505.8	468.5	435.8	410.1	381.0	355.1	335.2
30°	618.8	609.1	580.5	539.8	498.5	458.5	422.5	393.3	364.4	338.2	317.8
32.5°	601.2	599.1	573.9	534.5	490.9	445.8	408.5	379.1	347.0	321.2	301.9
35°	566.5	575.8	560.0	522.6	476.5	427.7	387.4	353.8	320.6	295.9	277.8
37.5°	519.9	543.2	539.1	505.2	456.9	408.1	363.6	328.5	296.8	271.9	254.1
40°	487.8	517.5	521.9	491.9	443.2	393.0	345.8	310.8	279.9	257.2	239.2
42.5°	453.4	488.1	499.9	476.0	428.2	376.9	329.8	293.6	262.9	240.9	225.0
45°	395.7	441.6	463.0	449.3	403.1	350.7	302.2	265.4	237.6	216.9	204.6
47.5°	341.7	391.9	420.6	415.8	375.2	323.3	275.3	240.0	213.0	196.5	185.5
50°	303.6	355.2	389.8	391.4	355.2	303.8	255.6	222.4	197.5	182.1	173.1
52.5°	270.4	319.7	357.4	365.8	332.8	283.4	238.0	204.8	183.0	168.8	160.7
55°	227.0	268.7	310.6	325.9	299.5	252.5	210.4	181.3	160.7	151.0	144.0
57.5°	188.8	223.5	262.2	279.1	262.8	222.6	183.1	157.8	141.2	132.6	127.2
60°	168.6	196.0	230.4	250.6	236.4	200.7	166.3	142.2	128.5	120.9	115.8
62.5°	149.8	174.1	203.2	221.6	214.0	180.2	149.4	128.1	116.3	109.2	105.5
65°	123.6	142.8	165.3	182.3	177.2	151.6	126.3	108.1	98.8	93.1	90.1
67.5°	101.8	115.6	131.2	146.1	142.1	123.9	103.7	89.5	82.5	77.6	75.8
70°	88.0	98.6	112.4	124.4	121.1	106.2	90.1	78.0	72.0	67.8	66.1
72.5°	74.9	83.5	94.2	103.9	101.7	89.3	75.9	66.8	62.1	58.3	56.9
75°	56.6	63.2	69.7	76.1	75.5	66.0	58.1	51.1	47.4	44.4	43.8
77.5°	41.8	45.5	49.9	53.6	52.6	47.1	41.0	36.9	34.3	32.3	31.9
80°	31.9	34.0	37.2	39.9	38.6	36.2	31.3	28.3	26.4	24.5	23.7
82.5°	23.2	25.2	27.1	28.7	27.6	25.4	22.4	20.4	19.2	17.9	17.6
85°	12.1	13.3	14.1	14.5	14.1	12.7	11.4	10.6	9.6	9.0	8.8
87.5°	11.3	10.0	8.7	8.0	6.9	6.2	4.8	3.7	4.2	4.7	5.2
90°	32.7	26.4	20.1	15.2	11.7	8.2	4.7	1.3	4.7	8.2	11.7
92.5°	38.3	36.8	35.3	33.2	30.7	28.2	25.7	23.1	25.7	28.2	30.7
95°	81.9	81.4	80.8	79.0	76.1	73.3	70.3	67.5	70.3	73.3	76.1
97.5°	137.5	136.4	135.3	133.5	131.0	128.4	125.9	123.3	125.9	128.4	131.0
100°	177.4	176.5	175.6	174.1	171.8	169.4	167.1	164.9	167.1	169.4	171.8
102.5°	219.5	218.4	217.3	215.9	214.0	212.2	210.3	208.4	210.3	212.2	214.0
105°	284.4	283.9	283.3	282.5	281.6	280.8	279.9	279.1	279.9	280.8	281.6
107.5°	355.9	355.9	355.9	355.2	354.0	352.8	351.5	350.2	351.5	352.8	354.0
110°	403.7	403.7	403.7	402.8	401.1	399.3	397.6	395.9	397.6	399.3	401.1



TEST NUMBER: P331490-935

CATALOG NUMBER: S122DIW-S290D1440U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	453.0	453.1	453.4	452.6	450.9	449.2	447.5	445.7	447.5	449.2	450.9
115°	525.6	526.2	526.7	526.2	524.4	522.6	520.9	519.2	520.9	522.6	524.4
117.5°	598.7	600.4	602.0	601.7	599.3	597.0	594.7	592.5	594.7	597.0	599.3
120°	645.8	648.2	650.5	650.5	648.2	645.8	643.5	641.2	643.5	645.8	648.2
122.5°	694.3	695.9	697.5	697.0	694.1	691.4	688.6	685.9	688.6	691.4	694.1
125°	765.0	765.9	766.7	765.9	763.2	760.6	758.0	755.4	758.0	760.6	763.2
127.5°	835.4	836.5	837.5	836.4	833.1	829.7	826.5	823.2	826.5	829.7	833.1
130°	881.2	881.8	882.4	880.8	877.0	873.3	869.5	865.7	869.5	873.3	877.0
132.5°	927.6	927.5	927.4	925.7	922.7	919.6	916.6	913.5	916.6	919.6	922.7
135°	993.2	992.6	992.0	990.1	986.9	983.8	980.6	977.4	980.6	983.8	986.9
137.5°	1058.2	1057.5	1056.7	1055.0	1052.4	1049.8	1047.2	1044.7	1047.2	1049.8	1052.4
140°	1100.4	1099.0	1097.5	1095.5	1093.0	1090.4	1087.7	1085.1	1087.7	1090.4	1093.0
142.5°	1140.8	1139.8	1138.8	1137.0	1134.5	1131.9	1129.3	1126.7	1129.3	1131.9	1134.5
145°	1199.8	1198.1	1196.4	1194.5	1192.4	1190.4	1188.4	1186.4	1188.4	1190.4	1192.4
147.5°	1253.4	1252.2	1251.1	1249.3	1246.9	1244.4	1242.0	1239.6	1242.0	1244.4	1246.9
150°	1286.6	1285.5	1284.3	1282.9	1281.2	1279.4	1277.6	1275.9	1277.6	1279.4	1281.2
152.5°	1319.4	1318.0	1316.6	1315.1	1313.3	1311.6	1309.8	1308.1	1309.8	1311.6	1313.3
155°	1362.4	1361.6	1360.7	1359.9	1359.0	1358.1	1357.3	1356.4	1357.3	1358.1	1359.0
157.5°	1401.6	1401.1	1400.6	1400.0	1399.5	1398.9	1398.3	1397.7	1398.3	1398.9	1399.5
160°	1425.9	1425.6	1425.4	1425.0	1424.4	1423.7	1423.2	1422.6	1423.2	1423.7	1424.4
162.5°	1446.7	1446.4	1446.1	1446.0	1445.8	1445.7	1445.6	1445.4	1445.6	1445.7	1445.8
165°	1474.5	1474.5	1474.5	1474.7	1475.0	1475.2	1475.6	1475.8	1475.6	1475.2	1475.0
167.5°	1497.3	1497.3	1497.4	1497.8	1498.7	1499.5	1500.4	1501.2	1500.4	1499.5	1498.7
170°	1510.2	1510.5	1510.7	1511.3	1512.2	1513.0	1513.9	1514.8	1513.9	1513.0	1512.2
172.5°	1519.5	1519.8	1520.1	1520.7	1521.6	1522.4	1523.3	1524.1	1523.3	1522.4	1521.6
175°	1530.2	1530.8	1531.4	1532.1	1532.9	1533.8	1534.6	1535.5	1534.6	1533.8	1532.9
177.5°	1535.9	1536.4	1536.9	1537.5	1538.2	1538.9	1539.6	1540.2	1539.6	1538.9	1538.2
180°	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2



TEST NUMBER: P331490-935

CATALOG NUMBER: S122DIW-S290D1440U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	502.2	501.3	498.0	496.3	493.4	490.8	489.0	489.8	490.4	490.2	489.7
5°	487.8	484.1	478.4	473.6	470.0	463.6	460.8	459.4	458.2	456.9	455.6
7.5°	470.6	464.8	456.7	449.7	443.2	435.1	430.5	427.8	425.0	421.9	419.1
10°	458.5	450.2	441.6	431.9	424.0	416.8	410.4	406.0	402.1	398.4	395.7
12.5°	445.7	436.2	425.5	412.2	403.6	393.1	392.2	384.6	378.5	376.2	373.0
15°	425.2	411.9	398.4	382.5	375.7	366.4	360.5	354.6	349.3	345.6	344.7
17.5°	402.0	384.8	371.3	360.0	348.8	339.1	333.7	329.1	324.7	319.8	319.1
20°	384.4	369.5	354.8	344.8	333.3	323.5	316.8	312.2	308.4	305.5	303.0
22.5°	367.6	351.3	337.9	327.0	315.6	307.7	302.5	297.9	294.8	291.6	289.2
25°	340.7	328.0	313.3	301.0	291.6	286.5	282.2	278.4	276.4	274.2	271.5
27.5°	317.2	303.1	289.4	279.8	271.6	267.1	264.0	261.3	259.5	258.2	256.7
30°	300.7	286.4	275.6	266.2	259.3	254.9	252.9	251.3	249.2	248.4	247.6
32.5°	284.6	271.8	262.6	254.4	248.0	245.0	243.2	241.8	240.1	239.4	237.7
35°	262.1	251.3	242.4	237.8	232.6	230.0	228.7	226.7	225.2	224.4	224.1
37.5°	240.8	231.5	225.6	219.8	217.6	216.0	214.1	212.8	212.3	212.2	212.0
40°	227.0	219.5	214.1	209.5	208.5	206.1	204.6	203.5	203.5	203.6	203.5
42.5°	214.6	207.7	203.0	199.0	197.9	196.5	194.8	194.8	195.1	195.8	195.1
45°	195.6	190.7	187.4	185.5	183.3	181.9	181.7	182.3	182.4	182.7	183.3
47.5°	178.1	174.9	171.9	169.7	168.8	168.6	168.3	169.4	170.3	170.7	171.5
50°	167.8	164.1	161.5	160.1	159.4	159.0	159.4	160.6	161.4	162.3	162.9
52.5°	156.3	153.6	151.9	150.8	150.5	150.8	150.8	152.1	153.3	153.8	154.0
55°	140.3	138.3	137.9	136.1	136.9	136.7	137.7	138.4	139.7	140.9	141.0
57.5°	124.2	122.7	121.7	121.8	122.1	123.0	123.7	125.1	126.3	127.6	127.7
60°	113.7	112.9	112.3	112.3	112.6	113.8	114.8	116.1	116.9	117.8	118.3
62.5°	103.9	103.1	102.5	102.9	103.9	104.6	105.7	106.5	107.3	108.1	108.3
65°	88.6	88.3	88.8	89.2	89.4	90.3	91.7	92.3	93.1	93.5	94.9
67.5°	74.5	74.6	74.5	75.0	76.2	76.4	77.7	79.0	79.2	80.0	80.8
70°	64.9	65.3	65.7	66.1	67.1	67.5	68.4	69.1	69.8	70.4	71.0
72.5°	56.1	56.2	56.7	56.6	57.4	58.2	59.1	59.7	60.4	61.2	61.7
75°	43.2	43.2	43.7	43.8	44.8	45.8	45.5	46.0	46.8	47.5	48.0
77.5°	31.6	31.2	31.6	31.8	32.1	32.9	33.1	33.6	34.5	34.3	34.7
80°	24.0	23.5	24.0	24.3	24.3	25.2	25.2	25.7	26.2	25.7	26.2
82.5°	17.1	16.9	17.3	17.4	17.7	17.7	18.0	18.1	18.7	18.4	18.7
85°	8.6	8.4	8.6	8.4	8.6	8.8	8.8	8.6	8.6	9.0	8.4
87.5°	5.7	6.5	7.7	8.9	10.0	11.1	10.8	10.8	10.6	10.2	10.2
90°	15.2	20.1	26.4	32.7	39.1	45.5	44.9	44.3	43.7	43.1	43.0
92.5°	33.2	35.3	36.8	38.3	39.8	41.2	41.4	41.5	41.6	41.8	41.8
95°	79.0	80.8	81.4	81.9	82.5	83.1	83.1	83.1	83.1	83.1	82.7
97.5°	133.5	135.3	136.4	137.5	138.5	139.7	139.7	139.7	139.7	139.7	139.7
100°	174.1	175.6	176.5	177.4	178.2	179.1	179.1	179.1	179.1	179.1	179.0
102.5°	215.9	217.3	218.4	219.5	220.6	221.7	222.0	222.1	222.4	222.7	222.6
105°	282.5	283.3	283.9	284.4	285.0	285.6	286.1	286.7	287.3	287.8	288.2
107.5°	355.2	355.9	355.9	355.9	355.9	355.9	356.1	356.4	356.6	356.8	356.3
110°	402.8	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.2



TEST NUMBER: P331490-935

CATALOG NUMBER: S122DIW-S290D1440U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	452.6	453.4	453.1	453.0	452.7	452.5	451.8	451.1	450.4	449.7	449.0
115°	526.2	526.7	526.2	525.6	525.0	524.4	524.1	523.8	523.5	523.2	522.6
117.5°	601.7	602.0	600.4	598.7	597.1	595.6	594.9	594.2	593.5	592.8	591.9
120°	650.5	650.5	648.2	645.8	643.5	641.2	641.2	641.2	641.2	641.2	640.8
122.5°	697.0	697.5	695.9	694.3	692.7	691.0	690.3	689.7	689.0	688.3	687.6
125°	765.9	766.7	765.9	765.0	764.1	763.2	762.3	761.5	760.6	759.7	759.2
127.5°	836.4	837.5	836.5	835.4	834.4	833.4	832.2	831.2	830.2	829.1	828.2
130°	880.8	882.4	881.8	881.2	880.6	880.0	879.5	878.9	878.3	877.7	876.8
132.5°	925.7	927.4	927.5	927.6	927.7	927.8	926.5	925.3	924.0	922.7	921.6
135°	990.1	992.0	992.6	993.2	993.7	994.3	994.0	993.7	993.4	993.2	992.6
137.5°	1055.0	1056.7	1057.5	1058.2	1058.9	1059.7	1059.5	1059.2	1059.0	1058.8	1058.1
140°	1095.5	1097.5	1099.0	1100.4	1101.9	1103.3	1103.3	1103.3	1103.3	1103.3	1102.8
142.5°	1137.0	1138.8	1139.8	1140.8	1141.8	1142.8	1143.0	1143.2	1143.5	1143.7	1143.2
145°	1194.5	1196.4	1198.1	1199.8	1201.5	1203.2	1203.5	1203.9	1204.1	1204.4	1203.9
147.5°	1249.3	1251.1	1252.2	1253.4	1254.6	1255.7	1256.4	1257.0	1257.6	1258.3	1258.0
150°	1282.9	1284.3	1285.5	1286.6	1287.8	1288.9	1289.8	1290.6	1291.5	1292.4	1292.4
152.5°	1315.1	1316.6	1318.0	1319.4	1320.8	1322.2	1323.3	1324.3	1325.4	1326.5	1326.5
155°	1359.9	1360.7	1361.6	1362.4	1363.3	1364.2	1365.6	1367.1	1368.6	1369.9	1370.3
157.5°	1400.0	1400.6	1401.1	1401.6	1402.1	1402.7	1404.5	1406.5	1408.5	1410.5	1410.7
160°	1425.0	1425.4	1425.6	1425.9	1426.2	1426.5	1428.2	1429.9	1431.7	1433.4	1433.7
162.5°	1446.0	1446.1	1446.4	1446.7	1447.0	1447.3	1449.2	1451.2	1453.2	1455.1	1455.4
165°	1474.7	1474.5	1474.5	1474.5	1474.5	1474.5	1476.5	1478.6	1480.6	1482.6	1482.9
167.5°	1497.8	1497.4	1497.3	1497.3	1497.2	1497.1	1499.2	1501.2	1503.2	1505.2	1505.5
170°	1511.3	1510.7	1510.5	1510.2	1509.8	1509.6	1511.6	1513.6	1515.6	1517.7	1517.8
172.5°	1520.7	1520.1	1519.8	1519.5	1519.2	1518.9	1521.0	1522.9	1525.0	1527.0	1527.2
175°	1532.1	1531.4	1530.8	1530.2	1529.7	1529.0	1531.1	1533.1	1535.1	1537.1	1537.3
177.5°	1537.5	1536.9	1536.4	1535.9	1535.5	1535.0	1536.4	1537.8	1539.2	1540.6	1540.6
180°	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2



TEST NUMBER: P331490-935

CATALOG NUMBER: S122DIW-S290D1440U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	488.1	487.8	487.8	486.4	487.8	487.8	488.1	489.7	490.2	490.4	489.8
5°	452.8	452.2	451.3	452.2	451.3	452.2	452.8	455.6	456.9	458.2	459.4
7.5°	417.8	415.5	415.2	412.8	415.2	415.5	417.8	419.1	421.9	425.0	427.8
10°	392.4	390.8	390.5	386.8	390.5	390.8	392.4	395.7	398.4	402.1	406.0
12.5°	373.0	369.2	370.0	367.8	370.0	369.2	373.0	373.0	376.2	378.5	384.6
15°	339.3	339.3	338.5	335.3	338.5	339.3	339.3	344.7	345.6	349.3	354.6
17.5°	315.2	314.8	313.0	313.9	313.0	314.8	315.2	319.1	319.8	324.7	329.1
20°	300.8	299.6	297.3	297.3	297.3	299.6	300.8	303.0	305.5	308.4	312.2
22.5°	287.2	287.1	284.6	285.4	284.6	287.1	287.2	289.2	291.6	294.8	297.9
25°	271.3	269.8	268.5	269.1	268.5	269.8	271.3	271.5	274.2	276.4	278.4
27.5°	256.1	255.3	255.2	253.7	255.2	255.3	256.1	256.7	258.2	259.5	261.3
30°	247.5	245.5	245.8	244.9	245.8	245.5	247.5	247.6	248.4	249.2	251.3
32.5°	237.4	236.7	236.3	235.5	236.3	236.7	237.4	237.7	239.4	240.1	241.8
35°	223.8	223.9	223.0	223.3	223.0	223.9	223.8	224.1	224.4	225.2	226.7
37.5°	211.8	212.4	212.0	212.1	212.0	212.4	211.8	212.0	212.2	212.3	212.8
40°	204.0	204.0	204.0	204.6	204.0	204.0	204.0	203.5	203.6	203.5	203.5
42.5°	196.5	196.1	195.9	195.8	195.9	196.1	196.5	195.1	195.8	195.1	194.8
45°	183.7	184.3	184.4	183.5	184.4	184.3	183.7	183.3	182.7	182.4	182.3
47.5°	172.0	172.1	172.0	172.9	172.0	172.1	172.0	171.5	170.7	170.3	169.4
50°	163.9	163.5	163.9	163.5	163.9	163.5	163.9	162.9	162.3	161.4	160.6
52.5°	155.3	155.4	155.2	155.1	155.2	155.4	155.3	154.0	153.8	153.3	152.1
55°	141.8	142.2	142.0	142.0	142.0	142.2	141.8	141.0	140.9	139.7	138.4
57.5°	127.9	128.2	128.5	127.6	128.5	128.2	127.9	127.7	127.6	126.3	125.1
60°	118.1	119.1	118.9	118.6	118.9	119.1	118.1	118.3	117.8	116.9	116.1
62.5°	109.2	109.6	109.5	109.4	109.5	109.6	109.2	108.3	108.1	107.3	106.5
65°	95.5	95.8	95.2	95.8	95.2	95.8	95.5	94.9	93.5	93.1	92.3
67.5°	80.6	80.8	81.2	81.5	81.2	80.8	80.6	80.8	80.0	79.2	79.0
70°	71.4	71.2	71.8	72.4	71.8	71.2	71.4	71.0	70.4	69.8	69.1
72.5°	61.6	62.1	61.9	62.3	61.9	62.1	61.6	61.7	61.2	60.4	59.7
75°	47.5	48.1	48.0	48.5	48.0	48.1	47.5	48.0	47.5	46.8	46.0
77.5°	34.4	34.4	34.4	34.7	34.4	34.4	34.4	34.7	34.3	34.5	33.6
80°	26.2	25.8	25.4	26.2	25.4	25.8	26.2	26.2	25.7	26.2	25.7
82.5°	18.3	18.4	18.1	18.1	18.1	18.4	18.3	18.7	18.4	18.7	18.1
85°	8.4	8.2	7.8	7.8	7.8	8.2	8.4	8.4	9.0	8.6	8.6
87.5°	10.2	10.2	10.2	10.1	10.2	10.2	10.2	10.2	10.2	10.6	10.8
90°	43.3	43.6	43.8	44.2	43.8	43.6	43.3	43.0	43.1	43.7	44.3
92.5°	41.8	41.9	42.0	42.0	42.0	41.9	41.8	41.8	41.8	41.6	41.5
95°	82.2	81.6	81.0	80.5	81.0	81.6	82.2	82.7	83.1	83.1	83.1
97.5°	139.6	139.5	139.5	139.4	139.5	139.5	139.6	139.7	139.7	139.7	139.7
100°	178.7	178.4	178.1	177.8	178.1	178.4	178.7	179.0	179.1	179.1	179.1
102.5°	222.3	222.1	221.7	221.4	221.7	222.1	222.3	222.6	222.7	222.4	222.1
105°	288.2	288.2	288.2	288.2	288.2	288.2	288.2	288.2	287.8	287.3	286.7
107.5°	355.0	353.6	352.3	350.9	352.3	353.6	355.0	356.3	356.8	356.6	356.4
110°	402.3	401.5	400.6	399.8	400.6	401.5	402.3	403.2	403.7	403.7	403.7



TEST NUMBER: P331490-935

CATALOG NUMBER: S122DIW-S290D1440U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	448.4	447.8	447.1	446.5	447.1	447.8	448.4	449.0	449.7	450.4	451.1
115°	521.8	520.9	520.0	519.2	520.0	520.9	521.8	522.6	523.2	523.5	523.8
117.5°	591.1	590.2	589.4	588.5	589.4	590.2	591.1	591.9	592.8	593.5	594.2
120°	639.9	639.0	638.2	637.3	638.2	639.0	639.9	640.8	641.2	641.2	641.2
122.5°	687.0	686.4	685.7	685.1	685.7	686.4	687.0	687.6	688.3	689.0	689.7
125°	758.9	758.6	758.4	758.0	758.4	758.6	758.9	759.2	759.7	760.6	761.5
127.5°	827.2	826.3	825.4	824.5	825.4	826.3	827.2	828.2	829.1	830.2	831.2
130°	875.7	874.6	873.4	872.3	873.4	874.6	875.7	876.8	877.7	878.3	878.9
132.5°	920.8	919.8	918.9	917.9	918.9	919.8	920.8	921.6	922.7	924.0	925.3
135°	991.7	990.8	990.0	989.1	990.0	990.8	991.7	992.6	993.2	993.4	993.7
137.5°	1057.0	1055.8	1054.6	1053.4	1054.6	1055.8	1057.0	1058.1	1058.8	1059.0	1059.2
140°	1101.6	1100.4	1099.2	1098.1	1099.2	1100.4	1101.6	1102.8	1103.3	1103.3	1103.3
142.5°	1142.1	1140.9	1139.8	1138.6	1139.8	1140.9	1142.1	1143.2	1143.7	1143.5	1143.2
145°	1202.8	1201.7	1200.5	1199.4	1200.5	1201.7	1202.8	1203.9	1204.4	1204.1	1203.9
147.5°	1256.9	1255.8	1254.7	1253.6	1254.7	1255.8	1256.9	1258.0	1258.3	1257.6	1257.0
150°	1291.5	1290.6	1289.8	1288.9	1289.8	1290.6	1291.5	1292.4	1292.4	1291.5	1290.6
152.5°	1325.4	1324.3	1323.3	1322.2	1323.3	1324.3	1325.4	1326.5	1326.5	1325.4	1324.3
155°	1369.4	1368.6	1367.7	1366.8	1367.7	1368.6	1369.4	1370.3	1369.9	1368.6	1367.1
157.5°	1409.4	1408.0	1406.6	1405.2	1406.6	1408.0	1409.4	1410.7	1410.5	1408.5	1406.5
160°	1432.5	1431.4	1430.3	1429.1	1430.3	1431.4	1432.5	1433.7	1433.4	1431.7	1429.9
162.5°	1454.1	1452.7	1451.3	1449.8	1451.3	1452.7	1454.1	1455.4	1455.1	1453.2	1451.2
165°	1481.4	1480.1	1478.6	1477.1	1478.6	1480.1	1481.4	1482.9	1482.6	1480.6	1478.6
167.5°	1504.0	1502.4	1501.0	1499.4	1501.0	1502.4	1504.0	1505.5	1505.2	1503.2	1501.2
170°	1516.0	1514.3	1512.6	1510.9	1512.6	1514.3	1516.0	1517.8	1517.7	1515.6	1513.6
172.5°	1525.4	1523.7	1522.0	1520.3	1522.0	1523.7	1525.4	1527.2	1527.0	1525.0	1522.9
175°	1535.5	1533.8	1532.1	1530.3	1532.1	1533.8	1535.5	1537.3	1537.1	1535.1	1533.1
177.5°	1539.2	1537.8	1536.4	1535.0	1536.4	1537.8	1539.2	1540.6	1540.6	1539.2	1537.8
180°	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2



TEST NUMBER: P331490-935

CATALOG NUMBER: S122DIW-S290D1440U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	489.0	490.8	493.4	496.3	498.0	501.3	502.2	503.8	505.1	508.4	511.9
5°	460.8	463.6	470.0	473.6	478.4	484.1	487.8	491.7	496.0	503.4	510.3
7.5°	430.5	435.1	443.2	449.7	456.7	464.8	470.6	478.4	484.8	495.3	505.3
10°	410.4	416.8	424.0	431.9	441.6	450.2	458.5	468.2	476.0	488.6	500.3
12.5°	392.2	393.1	403.6	412.2	425.5	436.2	445.7	458.2	465.9	480.8	493.1
15°	360.5	366.4	375.7	382.5	398.4	411.9	425.2	438.3	447.1	465.5	481.7
17.5°	333.7	339.1	348.8	360.0	371.3	384.8	402.0	415.9	427.8	448.8	468.0
20°	316.8	323.5	333.3	344.8	354.8	369.5	384.4	400.2	413.1	436.8	459.3
22.5°	302.5	307.7	315.6	327.0	337.9	351.3	367.6	384.9	398.4	424.0	446.7
25°	282.2	286.5	291.6	301.0	313.3	328.0	340.7	359.7	379.4	403.3	430.8
27.5°	264.0	267.1	271.6	279.8	289.4	303.1	317.2	335.2	355.1	381.0	410.1
30°	252.9	254.9	259.3	266.2	275.6	286.4	300.7	317.8	338.2	364.4	393.3
32.5°	243.2	245.0	248.0	254.4	262.6	271.8	284.6	301.9	321.2	347.0	379.1
35°	228.7	230.0	232.6	237.8	242.4	251.3	262.1	277.8	295.9	320.6	353.8
37.5°	214.1	216.0	217.6	219.8	225.6	231.5	240.8	254.1	271.9	296.8	328.5
40°	204.6	206.1	208.5	209.5	214.1	219.5	227.0	239.2	257.2	279.9	310.8
42.5°	194.8	196.5	197.9	199.0	203.0	207.7	214.6	225.0	240.9	262.9	293.6
45°	181.7	181.9	183.3	185.5	187.4	190.7	195.6	204.6	216.9	237.6	265.4
47.5°	168.3	168.6	168.8	169.7	171.9	174.9	178.1	185.5	196.5	213.0	240.0
50°	159.4	159.0	159.4	160.1	161.5	164.1	167.8	173.1	182.1	197.5	222.4
52.5°	150.8	150.8	150.5	150.8	151.9	153.6	156.3	160.7	168.8	183.0	204.8
55°	137.7	136.7	136.9	136.1	137.9	138.3	140.3	144.0	151.0	160.7	181.3
57.5°	123.7	123.0	122.1	121.8	121.7	122.7	124.2	127.2	132.6	141.2	157.8
60°	114.8	113.8	112.6	112.3	112.3	112.9	113.7	115.8	120.9	128.5	142.2
62.5°	105.7	104.6	103.9	102.9	102.5	103.1	103.9	105.5	109.2	116.3	128.1
65°	91.7	90.3	89.4	89.2	88.8	88.3	88.6	90.1	93.1	98.8	108.1
67.5°	77.7	76.4	76.2	75.0	74.5	74.6	74.5	75.8	77.6	82.5	89.5
70°	68.4	67.5	67.1	66.1	65.7	65.3	64.9	66.1	67.8	72.0	78.0
72.5°	59.1	58.2	57.4	56.6	56.7	56.2	56.1	56.9	58.3	62.1	66.8
75°	45.5	45.8	44.8	43.8	43.7	43.2	43.2	43.8	44.4	47.4	51.1
77.5°	33.1	32.9	32.1	31.8	31.6	31.2	31.6	31.9	32.3	34.3	36.9
80°	25.2	25.2	24.3	24.3	24.0	23.5	24.0	23.7	24.5	26.4	28.3
82.5°	18.0	17.7	17.7	17.4	17.3	16.9	17.1	17.6	17.9	19.2	20.4
85°	8.8	8.8	8.6	8.4	8.6	8.4	8.6	8.8	9.0	9.6	10.6
87.5°	10.8	11.1	10.0	8.9	7.7	6.5	5.7	5.2	4.7	4.2	3.7
90°	44.9	45.5	39.1	32.7	26.4	20.1	15.2	11.7	8.2	4.7	1.3
92.5°	41.4	41.2	39.8	38.3	36.8	35.3	33.2	30.7	28.2	25.7	23.1
95°	83.1	83.1	82.5	81.9	81.4	80.8	79.0	76.1	73.3	70.3	67.5
97.5°	139.7	139.7	138.5	137.5	136.4	135.3	133.5	131.0	128.4	125.9	123.3
100°	179.1	179.1	178.2	177.4	176.5	175.6	174.1	171.8	169.4	167.1	164.9
102.5°	222.0	221.7	220.6	219.5	218.4	217.3	215.9	214.0	212.2	210.3	208.4
105°	286.1	285.6	285.0	284.4	283.9	283.3	282.5	281.6	280.8	279.9	279.1
107.5°	356.1	355.9	355.9	355.9	355.9	355.9	355.2	354.0	352.8	351.5	350.2
110°	403.7	403.7	403.7	403.7	403.7	403.7	402.8	401.1	399.3	397.6	395.9



TEST NUMBER: P331490-935

CATALOG NUMBER: S122DIW-S290D1440U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	451.8	452.5	452.7	453.0	453.1	453.4	452.6	450.9	449.2	447.5	445.7
115°	524.1	524.4	525.0	525.6	526.2	526.7	526.2	524.4	522.6	520.9	519.2
117.5°	594.9	595.6	597.1	598.7	600.4	602.0	601.7	599.3	597.0	594.7	592.5
120°	641.2	641.2	643.5	645.8	648.2	650.5	650.5	648.2	645.8	643.5	641.2
122.5°	690.3	691.0	692.7	694.3	695.9	697.5	697.0	694.1	691.4	688.6	685.9
125°	762.3	763.2	764.1	765.0	765.9	766.7	765.9	763.2	760.6	758.0	755.4
127.5°	832.2	833.4	834.4	835.4	836.5	837.5	836.4	833.1	829.7	826.5	823.2
130°	879.5	880.0	880.6	881.2	881.8	882.4	880.8	877.0	873.3	869.5	865.7
132.5°	926.5	927.8	927.7	927.6	927.5	927.4	925.7	922.7	919.6	916.6	913.5
135°	994.0	994.3	993.7	993.2	992.6	992.0	990.1	986.9	983.8	980.6	977.4
137.5°	1059.5	1059.7	1058.9	1058.2	1057.5	1056.7	1055.0	1052.4	1049.8	1047.2	1044.7
140°	1103.3	1103.3	1101.9	1100.4	1099.0	1097.5	1095.5	1093.0	1090.4	1087.7	1085.1
142.5°	1143.0	1142.8	1141.8	1140.8	1139.8	1138.8	1137.0	1134.5	1131.9	1129.3	1126.7
145°	1203.5	1203.2	1201.5	1199.8	1198.1	1196.4	1194.5	1192.4	1190.4	1188.4	1186.4
147.5°	1256.4	1255.7	1254.6	1253.4	1252.2	1251.1	1249.3	1246.9	1244.4	1242.0	1239.6
150°	1289.8	1288.9	1287.8	1286.6	1285.5	1284.3	1282.9	1281.2	1279.4	1277.6	1275.9
152.5°	1323.3	1322.2	1320.8	1319.4	1318.0	1316.6	1315.1	1313.3	1311.6	1309.8	1308.1
155°	1365.6	1364.2	1363.3	1362.4	1361.6	1360.7	1359.9	1359.0	1358.1	1357.3	1356.4
157.5°	1404.5	1402.7	1402.1	1401.6	1401.1	1400.6	1400.0	1399.5	1398.9	1398.3	1397.7
160°	1428.2	1426.5	1426.2	1425.9	1425.6	1425.4	1425.0	1424.4	1423.7	1423.2	1422.6
162.5°	1449.2	1447.3	1447.0	1446.7	1446.4	1446.1	1446.0	1445.8	1445.7	1445.6	1445.4
165°	1476.5	1474.5	1474.5	1474.5	1474.5	1474.5	1474.7	1475.0	1475.2	1475.6	1475.8
167.5°	1499.2	1497.1	1497.2	1497.3	1497.3	1497.4	1497.8	1498.7	1499.5	1500.4	1501.2
170°	1511.6	1509.6	1509.8	1510.2	1510.5	1510.7	1511.3	1512.2	1513.0	1513.9	1514.8
172.5°	1521.0	1518.9	1519.2	1519.5	1519.8	1520.1	1520.7	1521.6	1522.4	1523.3	1524.1
175°	1531.1	1529.0	1529.7	1530.2	1530.8	1531.4	1532.1	1532.9	1533.8	1534.6	1535.5
177.5°	1536.4	1535.0	1535.5	1535.9	1536.4	1536.9	1537.5	1538.2	1538.9	1539.6	1540.2
180°	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2



TEST NUMBER: P331490-935

CATALOG NUMBER: S122DIW-S290D1440U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	511.6	512.4	514.9	517.4	520.2	521.0	522.2	521.2	520.8	523.7	526.0
5°	513.1	516.5	523.4	529.7	534.9	538.6	542.6	544.2	547.1	551.1	556.3
7.5°	511.3	518.2	529.0	538.1	548.0	555.2	560.8	565.6	571.4	579.1	587.6
10°	509.5	518.7	531.8	542.9	555.1	564.3	571.9	579.4	588.0	598.7	609.8
12.5°	506.1	516.9	533.4	546.6	562.1	571.2	581.4	597.4	606.7	621.7	637.4
15°	499.1	511.3	534.2	550.4	568.0	585.2	604.2	619.4	634.6	643.5	665.6
17.5°	488.9	506.6	532.0	551.0	573.3	600.4	621.7	639.0	656.6	670.9	682.0
20°	480.5	499.9	528.9	551.6	578.2	607.3	631.7	649.4	664.6	676.6	683.4
22.5°	470.1	494.5	522.6	549.2	583.2	612.0	637.7	651.5	664.3	670.1	672.8
25°	453.6	482.9	514.8	547.3	585.6	616.1	639.6	648.0	651.7	646.0	636.6
27.5°	435.8	468.5	505.8	543.5	584.1	613.5	630.3	629.0	622.7	604.2	589.6
30°	422.5	458.5	498.5	539.8	580.5	609.1	618.8	609.1	594.8	574.3	553.3
32.5°	408.5	445.8	490.9	534.5	573.9	599.1	601.2	584.4	562.2	538.9	512.8
35°	387.4	427.7	476.5	522.6	560.0	575.8	566.5	536.7	510.5	478.6	443.0
37.5°	363.6	408.1	456.9	505.2	539.1	543.2	519.9	488.6	451.6	414.1	372.2
40°	345.8	393.0	443.2	491.9	521.9	517.5	487.8	453.4	409.4	363.6	324.7
42.5°	329.8	376.9	428.2	476.0	499.9	488.1	453.4	411.1	363.9	320.7	285.1
45°	302.2	350.7	403.1	449.3	463.0	441.6	395.7	348.7	302.2	266.2	238.1
47.5°	275.3	323.3	375.2	415.8	420.6	391.9	341.7	293.4	253.4	224.1	204.2
50°	255.6	303.8	355.2	391.4	389.8	355.2	303.6	257.6	224.1	200.4	187.2
52.5°	238.0	283.4	332.8	365.8	357.4	319.7	270.4	229.5	202.1	183.6	171.5
55°	210.4	252.5	299.5	325.9	310.6	268.7	227.0	194.2	173.8	160.0	150.6
57.5°	183.1	222.6	262.8	279.1	262.2	223.5	188.8	165.0	149.6	139.4	133.3
60°	166.3	200.7	236.4	250.6	230.4	196.0	168.6	147.3	134.9	126.6	121.1
62.5°	149.4	180.2	214.0	221.6	203.2	174.1	149.8	132.1	122.0	114.5	109.3
65°	126.3	151.6	177.2	182.3	165.3	142.8	123.6	112.1	103.1	97.6	93.5
67.5°	103.7	123.9	142.1	146.1	131.2	115.6	101.8	91.7	85.7	81.1	77.6
70°	90.1	106.2	121.1	124.4	112.4	98.6	88.0	80.0	74.5	70.6	67.2
72.5°	75.9	89.3	101.7	103.9	94.2	83.5	74.9	68.5	63.7	61.2	58.0
75°	58.1	66.0	75.5	76.1	69.7	63.2	56.6	52.4	49.9	46.8	45.2
77.5°	41.0	47.1	52.6	53.6	49.9	45.5	41.8	38.5	36.3	34.9	33.4
80°	31.3	36.2	38.6	39.9	37.2	34.0	31.9	29.7	28.3	27.4	26.4
82.5°	22.4	25.4	27.6	28.7	27.1	25.2	23.2	21.9	20.8	20.1	19.7
85°	11.4	12.7	14.1	14.5	14.1	13.3	12.1	12.1	11.5	11.4	11.4
87.5°	4.8	6.2	6.9	8.0	8.7	10.0	11.3	12.3	13.4	13.2	12.9
90°	4.7	8.2	11.7	15.2	20.1	26.4	32.7	39.1	45.5	44.9	44.3
92.5°	25.7	28.2	30.7	33.2	35.3	36.8	38.3	39.8	41.2	41.4	41.5
95°	70.3	73.3	76.1	79.0	80.8	81.4	81.9	82.5	83.1	83.1	83.1
97.5°	125.9	128.4	131.0	133.5	135.3	136.4	137.5	138.5	139.7	139.7	139.7
100°	167.1	169.4	171.8	174.1	175.6	176.5	177.4	178.2	179.1	179.1	179.1
102.5°	210.3	212.2	214.0	215.9	217.3	218.4	219.5	220.6	221.7	222.0	222.1
105°	279.9	280.8	281.6	282.5	283.3	283.9	284.4	285.0	285.6	286.1	286.7
107.5°	351.5	352.8	354.0	355.2	355.9	355.9	355.9	355.9	355.9	356.1	356.4
110°	397.6	399.3	401.1	402.8	403.7	403.7	403.7	403.7	403.7	403.7	403.7



TEST NUMBER: P331490-935

CATALOG NUMBER: S122DIW-S290D1440U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	447.5	449.2	450.9	452.6	453.4	453.1	453.0	452.7	452.5	451.8	451.1
115°	520.9	522.6	524.4	526.2	526.7	526.2	525.6	525.0	524.4	524.1	523.8
117.5°	594.7	597.0	599.3	601.7	602.0	600.4	598.7	597.1	595.6	594.9	594.2
120°	643.5	645.8	648.2	650.5	650.5	648.2	645.8	643.5	641.2	641.2	641.2
122.5°	688.6	691.4	694.1	697.0	697.5	695.9	694.3	692.7	691.0	690.3	689.7
125°	758.0	760.6	763.2	765.9	766.7	765.9	765.0	764.1	763.2	762.3	761.5
127.5°	826.5	829.7	833.1	836.4	837.5	836.5	835.4	834.4	833.4	832.2	831.2
130°	869.5	873.3	877.0	880.8	882.4	881.8	881.2	880.6	880.0	879.5	878.9
132.5°	916.6	919.6	922.7	925.7	927.4	927.5	927.6	927.7	927.8	926.5	925.3
135°	980.6	983.8	986.9	990.1	992.0	992.6	993.2	993.7	994.3	994.0	993.7
137.5°	1047.2	1049.8	1052.4	1055.0	1056.7	1057.5	1058.2	1058.9	1059.7	1059.5	1059.2
140°	1087.7	1090.4	1093.0	1095.5	1097.5	1099.0	1100.4	1101.9	1103.3	1103.3	1103.3
142.5°	1129.3	1131.9	1134.5	1137.0	1138.8	1139.8	1140.8	1141.8	1142.8	1143.0	1143.2
145°	1188.4	1190.4	1192.4	1194.5	1196.4	1198.1	1199.8	1201.5	1203.2	1203.5	1203.9
147.5°	1242.0	1244.4	1246.9	1249.3	1251.1	1252.2	1253.4	1254.6	1255.7	1256.4	1257.0
150°	1277.6	1279.4	1281.2	1282.9	1284.3	1285.5	1286.6	1287.8	1288.9	1289.8	1290.6
152.5°	1309.8	1311.6	1313.3	1315.1	1316.6	1318.0	1319.4	1320.8	1322.2	1323.3	1324.3
155°	1357.3	1358.1	1359.0	1359.9	1360.7	1361.6	1362.4	1363.3	1364.2	1365.6	1367.1
157.5°	1398.3	1398.9	1399.5	1400.0	1400.6	1401.1	1401.6	1402.1	1402.7	1404.5	1406.5
160°	1423.2	1423.7	1424.4	1425.0	1425.4	1425.6	1425.9	1426.2	1426.5	1428.2	1429.9
162.5°	1445.6	1445.7	1445.8	1446.0	1446.1	1446.4	1446.7	1447.0	1447.3	1449.2	1451.2
165°	1475.6	1475.2	1475.0	1474.7	1474.5	1474.5	1474.5	1474.5	1474.5	1476.5	1478.6
167.5°	1500.4	1499.5	1498.7	1497.8	1497.4	1497.3	1497.3	1497.2	1497.1	1499.2	1501.2
170°	1513.9	1513.0	1512.2	1511.3	1510.7	1510.5	1510.2	1509.8	1509.6	1511.6	1513.6
172.5°	1523.3	1522.4	1521.6	1520.7	1520.1	1519.8	1519.5	1519.2	1518.9	1521.0	1522.9
175°	1534.6	1533.8	1532.9	1532.1	1531.4	1530.8	1530.2	1529.7	1529.0	1531.1	1533.1
177.5°	1539.6	1538.9	1538.2	1537.5	1536.9	1536.4	1535.9	1535.5	1535.0	1536.4	1537.8
180°	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2



TEST NUMBER: P331490-935

CATALOG NUMBER: S122DIW-S290D1440U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	527.9	530.0	530.0	530.4	532.9	532.5	532.4
5°	561.7	565.1	565.4	568.9	571.3	570.5	568.3
7.5°	593.7	599.9	604.6	607.2	610.3	612.2	611.3
10°	619.1	628.0	633.5	637.2	641.7	645.1	643.9
12.5°	642.0	652.7	660.3	666.7	667.2	671.5	668.6
15°	678.0	689.2	690.4	695.1	698.9	698.4	698.6
17.5°	689.7	693.4	694.1	694.2	694.3	692.9	689.9
20°	685.5	684.2	680.9	678.3	673.8	673.2	669.3
22.5°	665.5	661.2	652.8	647.3	640.3	638.5	637.4
25°	626.1	616.5	603.2	590.5	586.9	580.1	582.0
27.5°	572.0	557.1	542.6	532.4	523.0	512.7	515.7
30°	534.0	517.1	496.8	481.1	471.1	461.4	459.6
32.5°	488.6	463.9	441.3	427.5	412.2	406.0	399.2
35°	410.4	386.2	363.8	344.4	333.3	324.7	316.8
37.5°	340.0	312.3	294.1	278.4	270.4	265.4	266.7
40°	296.4	272.1	258.7	246.8	239.4	235.9	236.7
42.5°	261.0	242.8	231.9	223.7	218.4	216.5	216.0
45°	220.8	210.7	201.6	197.0	194.4	192.3	190.9
47.5°	193.5	185.1	180.0	177.3	175.0	172.9	172.8
50°	177.0	171.5	168.0	165.1	163.3	161.8	163.2
52.5°	164.5	159.5	155.9	153.3	152.7	151.3	151.2
55°	145.9	142.0	139.5	137.1	136.0	135.2	134.1
57.5°	129.0	125.3	123.0	121.5	119.2	118.5	118.1
60°	116.9	114.0	111.7	109.7	108.7	107.2	107.2
62.5°	105.8	102.9	100.7	99.3	97.6	97.0	97.2
65°	89.8	87.4	85.2	83.7	83.3	82.1	82.6
67.5°	75.0	73.4	71.1	70.3	69.6	69.0	68.4
70°	65.1	63.5	62.4	61.2	60.6	60.6	60.6
72.5°	56.8	54.9	54.2	52.8	53.1	52.5	51.8
75°	44.0	42.8	42.3	41.7	40.7	40.7	40.7
77.5°	32.4	32.0	31.3	30.7	30.5	30.3	30.4
80°	25.1	24.8	24.5	24.5	24.0	23.8	23.5
82.5°	19.3	18.8	18.5	18.3	18.3	18.3	18.2
85°	10.9	10.6	10.6	10.8	10.3	10.3	10.6
87.5°	13.0	12.8	12.7	12.7	12.9	12.8	12.9
90°	43.7	43.1	43.0	43.3	43.6	43.8	44.2
92.5°	41.6	41.8	41.8	41.8	41.9	42.0	42.0
95°	83.1	83.1	82.7	82.2	81.6	81.0	80.5
97.5°	139.7	139.7	139.7	139.6	139.5	139.5	139.4
100°	179.1	179.1	179.0	178.7	178.4	178.1	177.8
102.5°	222.4	222.7	222.6	222.3	222.1	221.7	221.4
105°	287.3	287.8	288.2	288.2	288.2	288.2	288.2
107.5°	356.6	356.8	356.3	355.0	353.6	352.3	350.9
110°	403.7	403.7	403.2	402.3	401.5	400.6	399.8



TEST NUMBER: P331490-935

CATALOG NUMBER: S122DIW-S290D1440U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	450.4	449.7	449.0	448.4	447.8	447.1	446.5
115°	523.5	523.2	522.6	521.8	520.9	520.0	519.2
117.5°	593.5	592.8	591.9	591.1	590.2	589.4	588.5
120°	641.2	641.2	640.8	639.9	639.0	638.2	637.3
122.5°	689.0	688.3	687.6	687.0	686.4	685.7	685.1
125°	760.6	759.7	759.2	758.9	758.6	758.4	758.0
127.5°	830.2	829.1	828.2	827.2	826.3	825.4	824.5
130°	878.3	877.7	876.8	875.7	874.6	873.4	872.3
132.5°	924.0	922.7	921.6	920.8	919.8	918.9	917.9
135°	993.4	993.2	992.6	991.7	990.8	990.0	989.1
137.5°	1059.0	1058.8	1058.1	1057.0	1055.8	1054.6	1053.4
140°	1103.3	1103.3	1102.8	1101.6	1100.4	1099.2	1098.1
142.5°	1143.5	1143.7	1143.2	1142.1	1140.9	1139.8	1138.6
145°	1204.1	1204.4	1203.9	1202.8	1201.7	1200.5	1199.4
147.5°	1257.6	1258.3	1258.0	1256.9	1255.8	1254.7	1253.6
150°	1291.5	1292.4	1292.4	1291.5	1290.6	1289.8	1288.9
152.5°	1325.4	1326.5	1326.5	1325.4	1324.3	1323.3	1322.2
155°	1368.6	1369.9	1370.3	1369.4	1368.6	1367.7	1366.8
157.5°	1408.5	1410.5	1410.7	1409.4	1408.0	1406.6	1405.2
160°	1431.7	1433.4	1433.7	1432.5	1431.4	1430.3	1429.1
162.5°	1453.2	1455.1	1455.4	1454.1	1452.7	1451.3	1449.8
165°	1480.6	1482.6	1482.9	1481.4	1480.1	1478.6	1477.1
167.5°	1503.2	1505.2	1505.5	1504.0	1502.4	1501.0	1499.4
170°	1515.6	1517.7	1517.8	1516.0	1514.3	1512.6	1510.9
172.5°	1525.0	1527.0	1527.2	1525.4	1523.7	1522.0	1520.3
175°	1535.1	1537.1	1537.3	1535.5	1533.8	1532.1	1530.3
177.5°	1539.2	1540.6	1540.6	1539.2	1537.8	1536.4	1535.0
180°	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2

(END OF REPORT)