

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331471-935

Luminaire Tested: **S122DIW-S290D710U935-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331471-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S290D710U935-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 710 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3566.0 lumens
Efficiency: N/A
Efficacy: 117.3 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 30.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331471-935

CATALOG NUMBER: S122DIW-S290D710U935-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331471-935

CATALOG NUMBER: S122DIW-S290D710U935-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39	32																				
1	94	90	86	83	84	81	78	75	64	62	60	49	48	47	35	34	34	27																				
2	86	79	73	68	77	71	66	62	57	53	50	43	41	39	31	30	29	23																				
3	78	69	63	57	70	63	57	52	50	46	43	39	36	34	28	26	25	20																				
4	72	62	54	48	64	56	49	44	45	40	37	35	31	29	25	23	22	17																				
5	66	55	47	41	59	50	43	38	40	35	32	31	28	25	23	21	19	15																				
6	61	49	42	36	54	45	38	33	36	31	28	28	25	22	21	19	17	14																				
7	56	44	37	32	50	40	34	29	33	28	24	26	22	20	19	17	15	12																				
8	52	40	33	28	47	37	30	26	30	25	22	24	20	18	17	15	14	11																				
9	48	37	30	25	44	34	27	23	27	23	19	22	18	16	16	14	12	10																				
10	45	34	27	22	41	31	25	21	25	21	17	20	17	14	15	13	11	9																				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8217	8217	8217	8217
5°	9211	8271	7329	8271
10°	10557	8202	6342	8202
15°	11677	8052	5605	8052
20°	11500	7892	5108	7892
25°	10368	7675	4794	7675
30°	8569	7333	4566	7333
35°	6244	6974	4401	6974
40°	4989	6551	4312	6551
45°	4359	6060	4190	6060
50°	4099	5586	4107	5586
55°	3775	5103	3997	5103
60°	3462	4592	3830	4592
65°	3156	4130	3660	4130
70°	2861	3682	3418	3682
75°	2539	3188	3026	3188
80°	2185	2631	2436	2631
85°	1964	1964	1445	1964



TEST NUMBER: P331471-935

CATALOG NUMBER: S122DIW-S290D710U935-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.5	1.4
10°-20°	140.9	4.0
20°-30°	204.5	5.7
30°-40°	215.8	6.1
40°-50°	191.1	5.4
50°-60°	152.5	4.3
60°-70°	103.6	2.9
70°-80°	53.1	1.5
80°-90°	14.9	0.4
90°-100°	27.8	0.8
100°-110°	101.9	2.9
110°-120°	272.4	7.6
120°-130°	449.6	12.6
130°-140°	478.2	13.4
140°-150°	444.4	12.5
150°-160°	357.3	10.0
160°-170°	230.3	6.5
170°-180°	79.3	2.2
0°-30°	393.9	11.0
0°-40°	609.7	17.1
0°-60°	953.2	26.7
0°-90°	1124.8	31.5
90°-120°	402.1	11.3
90°-150°	1774.3	49.8
90°-180°	2441.0	68.5
0°-180°	3566.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	509	509	509	509	509	
5°	568	510	452	510	568	57
15°	699	482	335	482	699	193
25°	582	431	269	431	582	263
35°	317	354	223	354	317	206
45°	191	265	184	265	191	150
55°	134	181	142	181	134	120
65°	83	108	96	108	83	82
75°	41	51	48	51	41	43
85°	11	11	8	11	11	12
90°	16	1	16	1	16	8
95°	26	39	26	39	26	24
105°	46	183	46	183	46	48
115°	49	347	49	347	49	124
125°	515	490	515	490	515	446
135°	626	606	626	606	626	483
145°	714	703	714	703	714	447
155°	775	775	775	775	775	358
165°	814	816	814	816	814	230
175°	830	835	830	835	830	79
180°	833	833	833	833	833	



TEST NUMBER: P331471-935

CATALOG NUMBER: S122DIW-S290D710U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	532.4	532.5	532.9	530.4	530.0	530.0	527.9	526.0	523.7	520.8	521.2
5°	568.3	570.5	571.3	568.9	565.4	565.1	561.7	556.3	551.1	547.1	544.2
7.5°	611.3	612.2	610.3	607.2	604.6	599.9	593.7	587.6	579.1	571.4	565.6
10°	643.9	645.1	641.7	637.2	633.5	628.0	619.1	609.8	598.7	588.0	579.4
12.5°	668.6	671.5	667.2	666.7	660.3	652.7	642.0	637.4	621.7	606.7	597.4
15°	698.6	698.4	698.9	695.1	690.4	689.2	678.0	665.6	643.5	634.6	619.4
17.5°	689.9	692.9	694.3	694.2	694.1	693.4	689.7	682.0	670.9	656.6	639.0
20°	669.3	673.2	673.8	678.3	680.9	684.2	685.5	683.4	676.6	664.6	649.4
22.5°	637.4	638.5	640.3	647.3	652.8	661.2	665.5	672.8	670.1	664.3	651.5
25°	582.0	580.1	586.9	590.5	603.2	616.5	626.1	636.6	646.0	651.7	648.0
27.5°	515.7	512.7	523.0	532.4	542.6	557.1	572.0	589.6	604.2	622.7	629.0
30°	459.6	461.4	471.1	481.1	496.8	517.1	534.0	553.3	574.3	594.8	609.1
32.5°	399.2	406.0	412.2	427.5	441.3	463.9	488.6	512.8	538.9	562.2	584.4
35°	316.8	324.7	333.3	344.4	363.8	386.2	410.4	443.0	478.6	510.5	536.7
37.5°	266.7	265.4	270.4	278.4	294.1	312.3	340.0	372.2	414.1	451.6	488.6
40°	236.7	235.9	239.4	246.8	258.7	272.1	296.4	324.7	363.6	409.4	453.4
42.5°	216.0	216.5	218.4	223.7	231.9	242.8	261.0	285.1	320.7	363.9	411.1
45°	190.9	192.3	194.4	197.0	201.6	210.7	220.8	238.1	266.2	302.2	348.7
47.5°	172.8	172.9	175.0	177.3	180.0	185.1	193.5	204.2	224.1	253.4	293.4
50°	163.2	161.8	163.3	165.1	168.0	171.5	177.0	187.2	200.4	224.1	257.6
52.5°	151.2	151.3	152.7	153.3	155.9	159.5	164.5	171.5	183.6	202.1	229.5
55°	134.1	135.2	136.0	137.1	139.5	142.0	145.9	150.6	160.0	173.8	194.2
57.5°	118.1	118.5	119.2	121.5	123.0	125.3	129.0	133.3	139.4	149.6	165.0
60°	107.2	107.2	108.7	109.7	111.7	114.0	116.9	121.1	126.6	134.9	147.3
62.5°	97.2	97.0	97.6	99.3	100.7	102.9	105.8	109.3	114.5	122.0	132.1
65°	82.6	82.1	83.3	83.7	85.2	87.4	89.8	93.5	97.6	103.1	112.1
67.5°	68.4	69.0	69.6	70.3	71.1	73.4	75.0	77.6	81.1	85.7	91.7
70°	60.6	60.6	60.6	61.2	62.4	63.5	65.1	67.2	70.6	74.5	80.0
72.5°	51.8	52.5	53.1	52.8	54.2	54.9	56.8	58.0	61.2	63.7	68.5
75°	40.7	40.7	40.7	41.7	42.3	42.8	44.0	45.2	46.8	49.9	52.4
77.5°	30.4	30.3	30.5	30.7	31.3	32.0	32.4	33.4	34.9	36.3	38.5
80°	23.5	23.8	24.0	24.5	24.5	24.8	25.1	26.4	27.4	28.3	29.7
82.5°	18.2	18.3	18.3	18.3	18.5	18.8	19.3	19.7	20.1	20.8	21.9
85°	10.6	10.3	10.3	10.8	10.6	10.6	10.9	11.4	11.4	11.5	12.1
87.5°	7.3	7.2	7.4	7.1	7.1	7.1	7.1	6.7	6.8	6.8	6.7
90°	16.3	16.0	15.8	15.5	15.2	14.7	14.0	13.4	12.7	12.1	11.0
92.5°	16.3	16.1	15.9	15.8	15.7	15.4	15.1	14.7	14.3	13.9	13.4
95°	25.9	26.1	26.2	26.3	26.4	26.2	25.5	24.9	24.2	23.5	22.6
97.5°	34.6	34.4	34.3	34.1	33.9	33.6	33.1	32.5	32.0	31.4	29.3
100°	40.4	40.1	39.9	39.6	39.3	38.7	37.5	36.5	35.4	34.4	32.1
102.5°	43.3	42.9	42.5	42.2	41.8	40.9	39.5	38.1	36.7	35.3	34.3
105°	45.8	45.3	44.8	44.2	43.7	42.6	41.2	39.7	38.2	36.8	35.4
107.5°	47.1	46.6	46.1	45.5	45.0	45.5	47.0	48.5	49.9	51.5	53.3
110°	47.6	47.1	46.6	46.0	45.5	51.9	65.3	78.7	92.1	105.5	144.2



TEST NUMBER: P331471-935

CATALOG NUMBER: S122DIW-S290D710U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	48.1	47.7	47.3	46.8	46.4	70.6	119.5	168.3	217.2	266.0	275.6
115°	49.4	59.1	68.7	78.4	88.0	123.8	185.8	247.9	309.9	371.9	368.5
117.5°	201.8	233.5	265.2	296.9	328.6	351.9	366.9	381.9	396.9	411.9	409.6
120°	367.6	385.7	403.8	421.9	440.0	448.2	446.6	445.1	443.4	441.8	439.4
122.5°	458.8	462.4	465.8	469.3	472.9	474.2	473.1	472.2	471.2	470.3	467.6
125°	515.3	515.0	514.5	514.1	513.8	513.1	512.1	511.2	510.2	509.3	506.8
127.5°	551.0	551.0	550.9	550.8	550.7	550.0	548.6	547.3	545.9	544.5	542.6
130°	573.3	573.3	573.5	573.6	573.8	573.1	571.6	570.2	568.7	567.2	565.7
132.5°	595.0	595.0	595.2	595.3	595.5	594.9	593.7	592.4	591.1	589.9	588.4
135°	626.3	626.5	626.8	627.1	627.3	626.8	625.4	624.1	622.8	621.5	620.3
137.5°	654.8	655.3	655.7	656.2	656.7	656.3	654.9	653.6	652.3	651.0	649.6
140°	672.7	673.3	674.0	674.7	675.4	675.1	673.9	672.7	671.5	670.3	668.7
142.5°	690.0	690.7	691.4	692.1	692.7	692.5	691.4	690.3	689.2	688.1	686.4
145°	714.3	714.9	715.6	716.3	717.0	716.8	715.8	714.9	714.0	713.1	710.8
147.5°	735.6	736.2	736.8	737.3	737.9	737.8	737.1	736.4	735.7	734.9	732.7
150°	748.6	749.2	749.9	750.6	751.3	751.2	750.4	749.6	748.8	748.0	745.9
152.5°	759.7	760.6	761.5	762.3	763.3	763.3	762.5	761.6	760.9	760.1	758.0
155°	775.2	776.2	777.3	778.3	779.4	779.5	778.8	777.9	777.1	776.4	774.7
157.5°	789.2	790.3	791.3	792.4	793.4	793.5	792.6	791.7	790.7	789.8	788.7
160°	797.5	798.4	799.3	800.2	801.2	801.2	800.5	799.6	798.8	798.1	797.2
162.5°	804.2	805.3	806.5	807.6	808.8	808.9	808.0	807.1	806.2	805.3	804.6
165°	814.3	815.3	816.2	817.1	818.0	818.0	817.1	816.2	815.3	814.3	813.9
167.5°	820.7	821.9	823.1	824.3	825.5	825.6	824.8	823.8	822.9	821.9	821.6
170°	824.6	825.8	827.0	828.2	829.4	829.5	828.5	827.7	826.7	825.8	825.5
172.5°	827.4	828.6	829.8	831.0	832.2	832.4	831.5	830.5	829.6	828.6	828.4
175°	830.0	831.3	832.7	834.0	835.3	835.5	834.6	833.7	832.8	831.8	831.6
177.5°	831.6	832.5	833.4	834.5	835.4	835.5	834.7	834.1	833.3	832.5	832.4
180°	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0



TEST NUMBER: P331471-935

CATALOG NUMBER: S122DIW-S290D710U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	522.2	521.0	520.2	517.4	514.9	512.4	511.6	511.9	508.4	505.1	503.8
5°	542.6	538.6	534.9	529.7	523.4	516.5	513.1	510.3	503.4	496.0	491.7
7.5°	560.8	555.2	548.0	538.1	529.0	518.2	511.3	505.3	495.3	484.8	478.4
10°	571.9	564.3	555.1	542.9	531.8	518.7	509.5	500.3	488.6	476.0	468.2
12.5°	581.4	571.2	562.1	546.6	533.4	516.9	506.1	493.1	480.8	465.9	458.2
15°	604.2	585.2	568.0	550.4	534.2	511.3	499.1	481.7	465.5	447.1	438.3
17.5°	621.7	600.4	573.3	551.0	532.0	506.6	488.9	468.0	448.8	427.8	415.9
20°	631.7	607.3	578.2	551.6	528.9	499.9	480.5	459.3	436.8	413.1	400.2
22.5°	637.7	612.0	583.2	549.2	522.6	494.5	470.1	446.7	424.0	398.4	384.9
25°	639.6	616.1	585.6	547.3	514.8	482.9	453.6	430.8	403.3	379.4	359.7
27.5°	630.3	613.5	584.1	543.5	505.8	468.5	435.8	410.1	381.0	355.1	335.2
30°	618.8	609.1	580.5	539.8	498.5	458.5	422.5	393.3	364.4	338.2	317.8
32.5°	601.2	599.1	573.9	534.5	490.9	445.8	408.5	379.1	347.0	321.2	301.9
35°	566.5	575.8	560.0	522.6	476.5	427.7	387.4	353.8	320.6	295.9	277.8
37.5°	519.9	543.2	539.1	505.2	456.9	408.1	363.6	328.5	296.8	271.9	254.1
40°	487.8	517.5	521.9	491.9	443.2	393.0	345.8	310.8	279.9	257.2	239.2
42.5°	453.4	488.1	499.9	476.0	428.2	376.9	329.8	293.6	262.9	240.9	225.0
45°	395.7	441.6	463.0	449.3	403.1	350.7	302.2	265.4	237.6	216.9	204.6
47.5°	341.7	391.9	420.6	415.8	375.2	323.3	275.3	240.0	213.0	196.5	185.5
50°	303.6	355.2	389.8	391.4	355.2	303.8	255.6	222.4	197.5	182.1	173.1
52.5°	270.4	319.7	357.4	365.8	332.8	283.4	238.0	204.8	183.0	168.8	160.7
55°	227.0	268.7	310.6	325.9	299.5	252.5	210.4	181.3	160.7	151.0	144.0
57.5°	188.8	223.5	262.2	279.1	262.8	222.6	183.1	157.8	141.2	132.6	127.2
60°	168.6	196.0	230.4	250.6	236.4	200.7	166.3	142.2	128.5	120.9	115.8
62.5°	149.8	174.1	203.2	221.6	214.0	180.2	149.4	128.1	116.3	109.2	105.5
65°	123.6	142.8	165.3	182.3	177.2	151.6	126.3	108.1	98.8	93.1	90.1
67.5°	101.8	115.6	131.2	146.1	142.1	123.9	103.7	89.5	82.5	77.6	75.8
70°	88.0	98.6	112.4	124.4	121.1	106.2	90.1	78.0	72.0	67.8	66.1
72.5°	74.9	83.5	94.2	103.9	101.7	89.3	75.9	66.8	62.1	58.3	56.9
75°	56.6	63.2	69.7	76.1	75.5	66.0	58.1	51.1	47.4	44.4	43.8
77.5°	41.8	45.5	49.9	53.6	52.6	47.1	41.0	36.9	34.3	32.3	31.9
80°	31.9	34.0	37.2	39.9	38.6	36.2	31.3	28.3	26.4	24.5	23.7
82.5°	23.2	25.2	27.1	28.7	27.6	25.4	22.4	20.4	19.2	17.9	17.6
85°	12.1	13.3	14.1	14.5	14.1	12.7	11.4	10.6	9.6	9.0	8.8
87.5°	6.7	6.5	6.3	6.3	5.5	5.3	4.3	3.5	3.7	3.9	3.8
90°	9.9	8.9	7.7	6.5	5.0	3.5	2.1	0.6	2.1	3.5	5.0
92.5°	12.9	12.4	11.9	11.6	11.8	11.9	12.1	12.1	12.1	11.9	11.8
95°	21.6	20.7	19.7	21.5	25.9	30.3	34.8	39.2	34.8	30.3	25.9
97.5°	27.1	25.0	22.8	27.9	40.4	52.9	65.3	77.7	65.3	52.9	40.4
100°	29.8	27.6	25.2	33.3	51.7	70.0	88.3	106.7	88.3	70.0	51.7
102.5°	73.4	92.5	111.5	123.0	126.8	130.7	134.7	138.5	134.7	130.7	126.8
105°	109.9	146.5	183.0	199.3	195.3	191.3	187.3	183.2	187.3	191.3	195.3
107.5°	139.2	183.0	226.9	247.2	243.9	240.7	237.5	234.2	237.5	240.7	243.9
110°	182.9	221.6	260.3	278.3	275.4	272.7	269.8	267.0	269.8	272.7	275.4



TEST NUMBER: P331471-935

CATALOG NUMBER: S122DIW-S290D710U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	285.2	294.7	304.3	307.8	305.3	302.9	300.4	297.9	300.4	302.9	305.3
115°	365.2	361.9	358.5	355.7	353.4	351.1	348.9	346.6	348.9	351.1	353.4
117.5°	407.3	405.0	402.7	400.3	397.7	395.2	392.6	390.1	392.6	395.2	397.7
120°	437.0	434.5	432.1	430.0	427.9	425.9	424.0	421.9	424.0	425.9	427.9
122.5°	465.0	462.4	459.8	457.4	455.3	453.1	451.1	448.9	451.1	453.1	455.3
125°	504.2	501.7	499.1	497.0	495.2	493.5	491.8	490.0	491.8	493.5	495.2
127.5°	540.7	538.8	536.9	535.0	533.0	531.2	529.2	527.3	529.2	531.2	533.0
130°	564.2	562.7	561.3	559.5	557.3	555.2	553.0	550.9	553.0	555.2	557.3
132.5°	586.9	585.4	583.9	582.3	580.5	578.7	576.9	575.1	576.9	578.7	580.5
135°	619.1	617.9	616.6	614.9	612.8	610.6	608.5	606.4	608.5	610.6	612.8
137.5°	648.2	646.9	645.5	644.0	642.6	641.1	639.6	638.1	639.6	641.1	642.6
140°	667.3	665.8	664.3	663.1	662.0	660.9	659.9	658.8	659.9	660.9	662.0
142.5°	684.8	683.0	681.3	680.0	679.1	678.1	677.1	676.1	677.1	678.1	679.1
145°	708.5	706.2	704.0	702.8	703.0	703.2	703.3	703.4	703.3	703.2	703.0
147.5°	730.5	728.2	726.0	725.1	725.7	726.2	726.7	727.1	726.7	726.2	725.7
150°	743.7	741.6	739.4	738.8	739.8	740.7	741.7	742.6	741.7	740.7	739.8
152.5°	756.0	754.0	751.9	751.4	752.4	753.5	754.6	755.6	754.6	753.5	752.4
155°	773.1	771.5	769.9	769.7	770.9	772.1	773.4	774.6	773.4	772.1	770.9
157.5°	787.6	786.4	785.3	785.3	786.3	787.3	788.3	789.4	788.3	787.3	786.3
160°	796.4	795.7	794.8	794.8	795.7	796.4	797.2	798.1	797.2	796.4	795.7
162.5°	803.9	803.1	802.5	802.5	803.3	804.2	804.9	805.7	804.9	804.2	803.3
165°	813.5	813.1	812.7	812.9	813.7	814.5	815.3	816.1	815.3	814.5	813.7
167.5°	821.1	820.8	820.4	820.6	821.4	822.3	823.0	823.8	823.0	822.3	821.4
170°	825.3	824.9	824.7	824.9	825.8	826.6	827.3	828.2	827.3	826.6	825.8
172.5°	828.1	827.9	827.6	827.9	828.6	829.5	830.3	831.0	830.3	829.5	828.6
175°	831.3	831.0	830.7	831.0	832.0	832.9	833.9	834.8	833.9	832.9	832.0
177.5°	832.3	832.2	832.1	832.4	833.2	833.9	834.7	835.4	834.7	833.9	833.2
180°	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0



TEST NUMBER: P331471-935

CATALOG NUMBER: S122DIW-S290D710U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	502.2	501.3	498.0	496.3	493.4	490.8	489.0	489.8	490.4	490.2	489.7
5°	487.8	484.1	478.4	473.6	470.0	463.6	460.8	459.4	458.2	456.9	455.6
7.5°	470.6	464.8	456.7	449.7	443.2	435.1	430.5	427.8	425.0	421.9	419.1
10°	458.5	450.2	441.6	431.9	424.0	416.8	410.4	406.0	402.1	398.4	395.7
12.5°	445.7	436.2	425.5	412.2	403.6	393.1	392.2	384.6	378.5	376.2	373.0
15°	425.2	411.9	398.4	382.5	375.7	366.4	360.5	354.6	349.3	345.6	344.7
17.5°	402.0	384.8	371.3	360.0	348.8	339.1	333.7	329.1	324.7	319.8	319.1
20°	384.4	369.5	354.8	344.8	333.3	323.5	316.8	312.2	308.4	305.5	303.0
22.5°	367.6	351.3	337.9	327.0	315.6	307.7	302.5	297.9	294.8	291.6	289.2
25°	340.7	328.0	313.3	301.0	291.6	286.5	282.2	278.4	276.4	274.2	271.5
27.5°	317.2	303.1	289.4	279.8	271.6	267.1	264.0	261.3	259.5	258.2	256.7
30°	300.7	286.4	275.6	266.2	259.3	254.9	252.9	251.3	249.2	248.4	247.6
32.5°	284.6	271.8	262.6	254.4	248.0	245.0	243.2	241.8	240.1	239.4	237.7
35°	262.1	251.3	242.4	237.8	232.6	230.0	228.7	226.7	225.2	224.4	224.1
37.5°	240.8	231.5	225.6	219.8	217.6	216.0	214.1	212.8	212.3	212.2	212.0
40°	227.0	219.5	214.1	209.5	208.5	206.1	204.6	203.5	203.5	203.6	203.5
42.5°	214.6	207.7	203.0	199.0	197.9	196.5	194.8	194.8	195.1	195.8	195.1
45°	195.6	190.7	187.4	185.5	183.3	181.9	181.7	182.3	182.4	182.7	183.3
47.5°	178.1	174.9	171.9	169.7	168.8	168.6	168.3	169.4	170.3	170.7	171.5
50°	167.8	164.1	161.5	160.1	159.4	159.0	159.4	160.6	161.4	162.3	162.9
52.5°	156.3	153.6	151.9	150.8	150.5	150.8	150.8	152.1	153.3	153.8	154.0
55°	140.3	138.3	137.9	136.1	136.9	136.7	137.7	138.4	139.7	140.9	141.0
57.5°	124.2	122.7	121.7	121.8	122.1	123.0	123.7	125.1	126.3	127.6	127.7
60°	113.7	112.9	112.3	112.3	112.6	113.8	114.8	116.1	116.9	117.8	118.3
62.5°	103.9	103.1	102.5	102.9	103.9	104.6	105.7	106.5	107.3	108.1	108.3
65°	88.6	88.3	88.8	89.2	89.4	90.3	91.7	92.3	93.1	93.5	94.9
67.5°	74.5	74.6	74.5	75.0	76.2	76.4	77.7	79.0	79.2	80.0	80.8
70°	64.9	65.3	65.7	66.1	67.1	67.5	68.4	69.1	69.8	70.4	71.0
72.5°	56.1	56.2	56.7	56.6	57.4	58.2	59.1	59.7	60.4	61.2	61.7
75°	43.2	43.2	43.7	43.8	44.8	45.8	45.5	46.0	46.8	47.5	48.0
77.5°	31.6	31.2	31.6	31.8	32.1	32.9	33.1	33.6	34.5	34.3	34.7
80°	24.0	23.5	24.0	24.3	24.3	25.2	25.2	25.7	26.2	25.7	26.2
82.5°	17.1	16.9	17.3	17.4	17.7	17.7	18.0	18.1	18.7	18.4	18.7
85°	8.6	8.4	8.6	8.4	8.6	8.8	8.8	8.6	8.6	9.0	8.4
87.5°	4.0	4.0	4.1	4.3	4.4	4.5	4.4	4.6	4.6	4.5	4.6
90°	6.5	7.7	8.9	9.9	11.0	12.1	12.7	13.4	14.0	14.7	15.2
92.5°	11.6	11.9	12.4	12.9	13.4	13.9	14.3	14.7	15.1	15.4	15.7
95°	21.5	19.7	20.7	21.6	22.6	23.5	24.2	24.9	25.5	26.2	26.4
97.5°	27.9	22.8	25.0	27.1	29.3	31.4	32.0	32.5	33.1	33.6	33.9
100°	33.3	25.2	27.6	29.8	32.1	34.4	35.4	36.5	37.5	38.7	39.3
102.5°	123.0	111.5	92.5	73.4	54.3	35.3	36.7	38.1	39.5	40.9	41.8
105°	199.3	183.0	146.5	109.9	73.4	36.8	38.2	39.7	41.2	42.6	43.7
107.5°	247.2	226.9	183.0	139.2	95.3	51.5	49.9	48.5	47.0	45.5	45.0
110°	278.3	260.3	221.6	182.9	144.2	105.5	92.1	78.7	65.3	51.9	45.5



TEST NUMBER: P331471-935

CATALOG NUMBER: S122DIW-S290D710U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	307.8	304.3	294.7	285.2	275.6	266.0	217.2	168.3	119.5	70.6	46.4
115°	355.7	358.5	361.9	365.2	368.5	371.9	309.9	247.9	185.8	123.8	88.0
117.5°	400.3	402.7	405.0	407.3	409.6	411.9	396.9	381.9	366.9	351.9	328.6
120°	430.0	432.1	434.5	437.0	439.4	441.8	443.4	445.1	446.6	448.2	440.0
122.5°	457.4	459.8	462.4	465.0	467.6	470.3	471.2	472.2	473.1	474.2	472.9
125°	497.0	499.1	501.7	504.2	506.8	509.3	510.2	511.2	512.1	513.1	513.8
127.5°	535.0	536.9	538.8	540.7	542.6	544.5	545.9	547.3	548.6	550.0	550.7
130°	559.5	561.3	562.7	564.2	565.7	567.2	568.7	570.2	571.6	573.1	573.8
132.5°	582.3	583.9	585.4	586.9	588.4	589.9	591.1	592.4	593.7	594.9	595.5
135°	614.9	616.6	617.9	619.1	620.3	621.5	622.8	624.1	625.4	626.8	627.3
137.5°	644.0	645.5	646.9	648.2	649.6	651.0	652.3	653.6	654.9	656.3	656.7
140°	663.1	664.3	665.8	667.3	668.7	670.3	671.5	672.7	673.9	675.1	675.4
142.5°	680.0	681.3	683.0	684.8	686.4	688.1	689.2	690.3	691.4	692.5	692.7
145°	702.8	704.0	706.2	708.5	710.8	713.1	714.0	714.9	715.8	716.8	717.0
147.5°	725.1	726.0	728.2	730.5	732.7	734.9	735.7	736.4	737.1	737.8	737.9
150°	738.8	739.4	741.6	743.7	745.9	748.0	748.8	749.6	750.4	751.2	751.3
152.5°	751.4	751.9	754.0	756.0	758.0	760.1	760.9	761.6	762.5	763.3	763.3
155°	769.7	769.9	771.5	773.1	774.7	776.4	777.1	777.9	778.8	779.5	779.4
157.5°	785.3	785.3	786.4	787.6	788.7	789.8	790.7	791.7	792.6	793.5	793.4
160°	794.8	794.8	795.7	796.4	797.2	798.1	798.8	799.6	800.5	801.2	801.2
162.5°	802.5	802.5	803.1	803.9	804.6	805.3	806.2	807.1	808.0	808.9	808.8
165°	812.9	812.7	813.1	813.5	813.9	814.3	815.3	816.2	817.1	818.0	818.0
167.5°	820.6	820.4	820.8	821.1	821.6	821.9	822.9	823.8	824.8	825.6	825.5
170°	824.9	824.7	824.9	825.3	825.5	825.8	826.7	827.7	828.5	829.5	829.4
172.5°	827.9	827.6	827.9	828.1	828.4	828.6	829.6	830.5	831.5	832.4	832.2
175°	831.0	830.7	831.0	831.3	831.6	831.8	832.8	833.7	834.6	835.5	835.3
177.5°	832.4	832.1	832.2	832.3	832.4	832.5	833.3	834.1	834.7	835.5	835.4
180°	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0



TEST NUMBER: P331471-935

CATALOG NUMBER: S122DIW-S290D710U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	488.1	487.8	487.8	486.4	487.8	487.8	488.1	489.7	490.2	490.4	489.8
5°	452.8	452.2	451.3	452.2	451.3	452.2	452.8	455.6	456.9	458.2	459.4
7.5°	417.8	415.5	415.2	412.8	415.2	415.5	417.8	419.1	421.9	425.0	427.8
10°	392.4	390.8	390.5	386.8	390.5	390.8	392.4	395.7	398.4	402.1	406.0
12.5°	373.0	369.2	370.0	367.8	370.0	369.2	373.0	373.0	376.2	378.5	384.6
15°	339.3	339.3	338.5	335.3	338.5	339.3	339.3	344.7	345.6	349.3	354.6
17.5°	315.2	314.8	313.0	313.9	313.0	314.8	315.2	319.1	319.8	324.7	329.1
20°	300.8	299.6	297.3	297.3	297.3	299.6	300.8	303.0	305.5	308.4	312.2
22.5°	287.2	287.1	284.6	285.4	284.6	287.1	287.2	289.2	291.6	294.8	297.9
25°	271.3	269.8	268.5	269.1	268.5	269.8	271.3	271.5	274.2	276.4	278.4
27.5°	256.1	255.3	255.2	253.7	255.2	255.3	256.1	256.7	258.2	259.5	261.3
30°	247.5	245.5	245.8	244.9	245.8	245.5	247.5	247.6	248.4	249.2	251.3
32.5°	237.4	236.7	236.3	235.5	236.3	236.7	237.4	237.7	239.4	240.1	241.8
35°	223.8	223.9	223.0	223.3	223.0	223.9	223.8	224.1	224.4	225.2	226.7
37.5°	211.8	212.4	212.0	212.1	212.0	212.4	211.8	212.0	212.2	212.3	212.8
40°	204.0	204.0	204.0	204.6	204.0	204.0	204.0	203.5	203.6	203.5	203.5
42.5°	196.5	196.1	195.9	195.8	195.9	196.1	196.5	195.1	195.8	195.1	194.8
45°	183.7	184.3	184.4	183.5	184.4	184.3	183.7	183.3	182.7	182.4	182.3
47.5°	172.0	172.1	172.0	172.9	172.0	172.1	172.0	171.5	170.7	170.3	169.4
50°	163.9	163.5	163.9	163.5	163.9	163.5	163.9	162.9	162.3	161.4	160.6
52.5°	155.3	155.4	155.2	155.1	155.2	155.4	155.3	154.0	153.8	153.3	152.1
55°	141.8	142.2	142.0	142.0	142.0	142.2	141.8	141.0	140.9	139.7	138.4
57.5°	127.9	128.2	128.5	127.6	128.5	128.2	127.9	127.7	127.6	126.3	125.1
60°	118.1	119.1	118.9	118.6	118.9	119.1	118.1	118.3	117.8	116.9	116.1
62.5°	109.2	109.6	109.5	109.4	109.5	109.6	109.2	108.3	108.1	107.3	106.5
65°	95.5	95.8	95.2	95.8	95.2	95.8	95.5	94.9	93.5	93.1	92.3
67.5°	80.6	80.8	81.2	81.5	81.2	80.8	80.6	80.8	80.0	79.2	79.0
70°	71.4	71.2	71.8	72.4	71.8	71.2	71.4	71.0	70.4	69.8	69.1
72.5°	61.6	62.1	61.9	62.3	61.9	62.1	61.6	61.7	61.2	60.4	59.7
75°	47.5	48.1	48.0	48.5	48.0	48.1	47.5	48.0	47.5	46.8	46.0
77.5°	34.4	34.4	34.4	34.7	34.4	34.4	34.4	34.7	34.3	34.5	33.6
80°	26.2	25.8	25.4	26.2	25.4	25.8	26.2	26.2	25.7	26.2	25.7
82.5°	18.3	18.4	18.1	18.1	18.1	18.4	18.3	18.7	18.4	18.7	18.1
85°	8.4	8.2	7.8	7.8	7.8	8.2	8.4	8.4	9.0	8.6	8.6
87.5°	4.6	4.6	4.6	4.5	4.6	4.6	4.6	4.6	4.5	4.6	4.6
90°	15.5	15.8	16.0	16.3	16.0	15.8	15.5	15.2	14.7	14.0	13.4
92.5°	15.8	15.9	16.1	16.3	16.1	15.9	15.8	15.7	15.4	15.1	14.7
95°	26.3	26.2	26.1	25.9	26.1	26.2	26.3	26.4	26.2	25.5	24.9
97.5°	34.1	34.3	34.4	34.6	34.4	34.3	34.1	33.9	33.6	33.1	32.5
100°	39.6	39.9	40.1	40.4	40.1	39.9	39.6	39.3	38.7	37.5	36.5
102.5°	42.2	42.5	42.9	43.3	42.9	42.5	42.2	41.8	40.9	39.5	38.1
105°	44.2	44.8	45.3	45.8	45.3	44.8	44.2	43.7	42.6	41.2	39.7
107.5°	45.5	46.1	46.6	47.1	46.6	46.1	45.5	45.0	45.5	47.0	48.5
110°	46.0	46.6	47.1	47.6	47.1	46.6	46.0	45.5	51.9	65.3	78.7



TEST NUMBER: P331471-935

CATALOG NUMBER: S122DIW-S290D710U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	46.8	47.3	47.7	48.1	47.7	47.3	46.8	46.4	70.6	119.5	168.3
115°	78.4	68.7	59.1	49.4	59.1	68.7	78.4	88.0	123.8	185.8	247.9
117.5°	296.9	265.2	233.5	201.8	233.5	265.2	296.9	328.6	351.9	366.9	381.9
120°	421.9	403.8	385.7	367.6	385.7	403.8	421.9	440.0	448.2	446.6	445.1
122.5°	469.3	465.8	462.4	458.8	462.4	465.8	469.3	472.9	474.2	473.1	472.2
125°	514.1	514.5	515.0	515.3	515.0	514.5	514.1	513.8	513.1	512.1	511.2
127.5°	550.8	550.9	551.0	551.0	551.0	550.9	550.8	550.7	550.0	548.6	547.3
130°	573.6	573.5	573.3	573.3	573.3	573.5	573.6	573.8	573.1	571.6	570.2
132.5°	595.3	595.2	595.0	595.0	595.0	595.2	595.3	595.5	594.9	593.7	592.4
135°	627.1	626.8	626.5	626.3	626.5	626.8	627.1	627.3	626.8	625.4	624.1
137.5°	656.2	655.7	655.3	654.8	655.3	655.7	656.2	656.7	656.3	654.9	653.6
140°	674.7	674.0	673.3	672.7	673.3	674.0	674.7	675.4	675.1	673.9	672.7
142.5°	692.1	691.4	690.7	690.0	690.7	691.4	692.1	692.7	692.5	691.4	690.3
145°	716.3	715.6	714.9	714.3	714.9	715.6	716.3	717.0	716.8	715.8	714.9
147.5°	737.3	736.8	736.2	735.6	736.2	736.8	737.3	737.9	737.8	737.1	736.4
150°	750.6	749.9	749.2	748.6	749.2	749.9	750.6	751.3	751.2	750.4	749.6
152.5°	762.3	761.5	760.6	759.7	760.6	761.5	762.3	763.3	763.3	762.5	761.6
155°	778.3	777.3	776.2	775.2	776.2	777.3	778.3	779.4	779.5	778.8	777.9
157.5°	792.4	791.3	790.3	789.2	790.3	791.3	792.4	793.4	793.5	792.6	791.7
160°	800.2	799.3	798.4	797.5	798.4	799.3	800.2	801.2	801.2	800.5	799.6
162.5°	807.6	806.5	805.3	804.2	805.3	806.5	807.6	808.8	808.9	808.0	807.1
165°	817.1	816.2	815.3	814.3	815.3	816.2	817.1	818.0	818.0	817.1	816.2
167.5°	824.3	823.1	821.9	820.7	821.9	823.1	824.3	825.5	825.6	824.8	823.8
170°	828.2	827.0	825.8	824.6	825.8	827.0	828.2	829.4	829.5	828.5	827.7
172.5°	831.0	829.8	828.6	827.4	828.6	829.8	831.0	832.2	832.4	831.5	830.5
175°	834.0	832.7	831.3	830.0	831.3	832.7	834.0	835.3	835.5	834.6	833.7
177.5°	834.5	833.4	832.5	831.6	832.5	833.4	834.5	835.4	835.5	834.7	834.1
180°	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0



TEST NUMBER: P331471-935

CATALOG NUMBER: S122DIW-S290D710U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	489.0	490.8	493.4	496.3	498.0	501.3	502.2	503.8	505.1	508.4	511.9
5°	460.8	463.6	470.0	473.6	478.4	484.1	487.8	491.7	496.0	503.4	510.3
7.5°	430.5	435.1	443.2	449.7	456.7	464.8	470.6	478.4	484.8	495.3	505.3
10°	410.4	416.8	424.0	431.9	441.6	450.2	458.5	468.2	476.0	488.6	500.3
12.5°	392.2	393.1	403.6	412.2	425.5	436.2	445.7	458.2	465.9	480.8	493.1
15°	360.5	366.4	375.7	382.5	398.4	411.9	425.2	438.3	447.1	465.5	481.7
17.5°	333.7	339.1	348.8	360.0	371.3	384.8	402.0	415.9	427.8	448.8	468.0
20°	316.8	323.5	333.3	344.8	354.8	369.5	384.4	400.2	413.1	436.8	459.3
22.5°	302.5	307.7	315.6	327.0	337.9	351.3	367.6	384.9	398.4	424.0	446.7
25°	282.2	286.5	291.6	301.0	313.3	328.0	340.7	359.7	379.4	403.3	430.8
27.5°	264.0	267.1	271.6	279.8	289.4	303.1	317.2	335.2	355.1	381.0	410.1
30°	252.9	254.9	259.3	266.2	275.6	286.4	300.7	317.8	338.2	364.4	393.3
32.5°	243.2	245.0	248.0	254.4	262.6	271.8	284.6	301.9	321.2	347.0	379.1
35°	228.7	230.0	232.6	237.8	242.4	251.3	262.1	277.8	295.9	320.6	353.8
37.5°	214.1	216.0	217.6	219.8	225.6	231.5	240.8	254.1	271.9	296.8	328.5
40°	204.6	206.1	208.5	209.5	214.1	219.5	227.0	239.2	257.2	279.9	310.8
42.5°	194.8	196.5	197.9	199.0	203.0	207.7	214.6	225.0	240.9	262.9	293.6
45°	181.7	181.9	183.3	185.5	187.4	190.7	195.6	204.6	216.9	237.6	265.4
47.5°	168.3	168.6	168.8	169.7	171.9	174.9	178.1	185.5	196.5	213.0	240.0
50°	159.4	159.0	159.4	160.1	161.5	164.1	167.8	173.1	182.1	197.5	222.4
52.5°	150.8	150.8	150.5	150.8	151.9	153.6	156.3	160.7	168.8	183.0	204.8
55°	137.7	136.7	136.9	136.1	137.9	138.3	140.3	144.0	151.0	160.7	181.3
57.5°	123.7	123.0	122.1	121.8	121.7	122.7	124.2	127.2	132.6	141.2	157.8
60°	114.8	113.8	112.6	112.3	112.3	112.9	113.7	115.8	120.9	128.5	142.2
62.5°	105.7	104.6	103.9	102.9	102.5	103.1	103.9	105.5	109.2	116.3	128.1
65°	91.7	90.3	89.4	89.2	88.8	88.3	88.6	90.1	93.1	98.8	108.1
67.5°	77.7	76.4	76.2	75.0	74.5	74.6	74.5	75.8	77.6	82.5	89.5
70°	68.4	67.5	67.1	66.1	65.7	65.3	64.9	66.1	67.8	72.0	78.0
72.5°	59.1	58.2	57.4	56.6	56.7	56.2	56.1	56.9	58.3	62.1	66.8
75°	45.5	45.8	44.8	43.8	43.7	43.2	43.2	43.8	44.4	47.4	51.1
77.5°	33.1	32.9	32.1	31.8	31.6	31.2	31.6	31.9	32.3	34.3	36.9
80°	25.2	25.2	24.3	24.3	24.0	23.5	24.0	23.7	24.5	26.4	28.3
82.5°	18.0	17.7	17.7	17.4	17.3	16.9	17.1	17.6	17.9	19.2	20.4
85°	8.8	8.8	8.6	8.4	8.6	8.4	8.6	8.8	9.0	9.6	10.6
87.5°	4.4	4.5	4.4	4.3	4.1	4.0	4.0	3.8	3.9	3.7	3.5
90°	12.7	12.1	11.0	9.9	8.9	7.7	6.5	5.0	3.5	2.1	0.6
92.5°	14.3	13.9	13.4	12.9	12.4	11.9	11.6	11.8	11.9	12.1	12.1
95°	24.2	23.5	22.6	21.6	20.7	19.7	21.5	25.9	30.3	34.8	39.2
97.5°	32.0	31.4	29.3	27.1	25.0	22.8	27.9	40.4	52.9	65.3	77.7
100°	35.4	34.4	32.1	29.8	27.6	25.2	33.3	51.7	70.0	88.3	106.7
102.5°	36.7	35.3	54.3	73.4	92.5	111.5	123.0	126.8	130.7	134.7	138.5
105°	38.2	36.8	73.4	109.9	146.5	183.0	199.3	195.3	191.3	187.3	183.2
107.5°	49.9	51.5	95.3	139.2	183.0	226.9	247.2	243.9	240.7	237.5	234.2
110°	92.1	105.5	144.2	182.9	221.6	260.3	278.3	275.4	272.7	269.8	267.0



TEST NUMBER: P331471-935

CATALOG NUMBER: S122DIW-S290D710U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	217.2	266.0	275.6	285.2	294.7	304.3	307.8	305.3	302.9	300.4	297.9
115°	309.9	371.9	368.5	365.2	361.9	358.5	355.7	353.4	351.1	348.9	346.6
117.5°	396.9	411.9	409.6	407.3	405.0	402.7	400.3	397.7	395.2	392.6	390.1
120°	443.4	441.8	439.4	437.0	434.5	432.1	430.0	427.9	425.9	424.0	421.9
122.5°	471.2	470.3	467.6	465.0	462.4	459.8	457.4	455.3	453.1	451.1	448.9
125°	510.2	509.3	506.8	504.2	501.7	499.1	497.0	495.2	493.5	491.8	490.0
127.5°	545.9	544.5	542.6	540.7	538.8	536.9	535.0	533.0	531.2	529.2	527.3
130°	568.7	567.2	565.7	564.2	562.7	561.3	559.5	557.3	555.2	553.0	550.9
132.5°	591.1	589.9	588.4	586.9	585.4	583.9	582.3	580.5	578.7	576.9	575.1
135°	622.8	621.5	620.3	619.1	617.9	616.6	614.9	612.8	610.6	608.5	606.4
137.5°	652.3	651.0	649.6	648.2	646.9	645.5	644.0	642.6	641.1	639.6	638.1
140°	671.5	670.3	668.7	667.3	665.8	664.3	663.1	662.0	660.9	659.9	658.8
142.5°	689.2	688.1	686.4	684.8	683.0	681.3	680.0	679.1	678.1	677.1	676.1
145°	714.0	713.1	710.8	708.5	706.2	704.0	702.8	703.0	703.2	703.3	703.4
147.5°	735.7	734.9	732.7	730.5	728.2	726.0	725.1	725.7	726.2	726.7	727.1
150°	748.8	748.0	745.9	743.7	741.6	739.4	738.8	739.8	740.7	741.7	742.6
152.5°	760.9	760.1	758.0	756.0	754.0	751.9	751.4	752.4	753.5	754.6	755.6
155°	777.1	776.4	774.7	773.1	771.5	769.9	769.7	770.9	772.1	773.4	774.6
157.5°	790.7	789.8	788.7	787.6	786.4	785.3	785.3	786.3	787.3	788.3	789.4
160°	798.8	798.1	797.2	796.4	795.7	794.8	794.8	795.7	796.4	797.2	798.1
162.5°	806.2	805.3	804.6	803.9	803.1	802.5	802.5	803.3	804.2	804.9	805.7
165°	815.3	814.3	813.9	813.5	813.1	812.7	812.9	813.7	814.5	815.3	816.1
167.5°	822.9	821.9	821.6	821.1	820.8	820.4	820.6	821.4	822.3	823.0	823.8
170°	826.7	825.8	825.5	825.3	824.9	824.7	824.9	825.8	826.6	827.3	828.2
172.5°	829.6	828.6	828.4	828.1	827.9	827.6	827.9	828.6	829.5	830.3	831.0
175°	832.8	831.8	831.6	831.3	831.0	830.7	831.0	832.0	832.9	833.9	834.8
177.5°	833.3	832.5	832.4	832.3	832.2	832.1	832.4	833.2	833.9	834.7	835.4
180°	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0



TEST NUMBER: P331471-935

CATALOG NUMBER: S122DIW-S290D710U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	511.6	512.4	514.9	517.4	520.2	521.0	522.2	521.2	520.8	523.7	526.0
5°	513.1	516.5	523.4	529.7	534.9	538.6	542.6	544.2	547.1	551.1	556.3
7.5°	511.3	518.2	529.0	538.1	548.0	555.2	560.8	565.6	571.4	579.1	587.6
10°	509.5	518.7	531.8	542.9	555.1	564.3	571.9	579.4	588.0	598.7	609.8
12.5°	506.1	516.9	533.4	546.6	562.1	571.2	581.4	597.4	606.7	621.7	637.4
15°	499.1	511.3	534.2	550.4	568.0	585.2	604.2	619.4	634.6	643.5	665.6
17.5°	488.9	506.6	532.0	551.0	573.3	600.4	621.7	639.0	656.6	670.9	682.0
20°	480.5	499.9	528.9	551.6	578.2	607.3	631.7	649.4	664.6	676.6	683.4
22.5°	470.1	494.5	522.6	549.2	583.2	612.0	637.7	651.5	664.3	670.1	672.8
25°	453.6	482.9	514.8	547.3	585.6	616.1	639.6	648.0	651.7	646.0	636.6
27.5°	435.8	468.5	505.8	543.5	584.1	613.5	630.3	629.0	622.7	604.2	589.6
30°	422.5	458.5	498.5	539.8	580.5	609.1	618.8	609.1	594.8	574.3	553.3
32.5°	408.5	445.8	490.9	534.5	573.9	599.1	601.2	584.4	562.2	538.9	512.8
35°	387.4	427.7	476.5	522.6	560.0	575.8	566.5	536.7	510.5	478.6	443.0
37.5°	363.6	408.1	456.9	505.2	539.1	543.2	519.9	488.6	451.6	414.1	372.2
40°	345.8	393.0	443.2	491.9	521.9	517.5	487.8	453.4	409.4	363.6	324.7
42.5°	329.8	376.9	428.2	476.0	499.9	488.1	453.4	411.1	363.9	320.7	285.1
45°	302.2	350.7	403.1	449.3	463.0	441.6	395.7	348.7	302.2	266.2	238.1
47.5°	275.3	323.3	375.2	415.8	420.6	391.9	341.7	293.4	253.4	224.1	204.2
50°	255.6	303.8	355.2	391.4	389.8	355.2	303.6	257.6	224.1	200.4	187.2
52.5°	238.0	283.4	332.8	365.8	357.4	319.7	270.4	229.5	202.1	183.6	171.5
55°	210.4	252.5	299.5	325.9	310.6	268.7	227.0	194.2	173.8	160.0	150.6
57.5°	183.1	222.6	262.8	279.1	262.2	223.5	188.8	165.0	149.6	139.4	133.3
60°	166.3	200.7	236.4	250.6	230.4	196.0	168.6	147.3	134.9	126.6	121.1
62.5°	149.4	180.2	214.0	221.6	203.2	174.1	149.8	132.1	122.0	114.5	109.3
65°	126.3	151.6	177.2	182.3	165.3	142.8	123.6	112.1	103.1	97.6	93.5
67.5°	103.7	123.9	142.1	146.1	131.2	115.6	101.8	91.7	85.7	81.1	77.6
70°	90.1	106.2	121.1	124.4	112.4	98.6	88.0	80.0	74.5	70.6	67.2
72.5°	75.9	89.3	101.7	103.9	94.2	83.5	74.9	68.5	63.7	61.2	58.0
75°	58.1	66.0	75.5	76.1	69.7	63.2	56.6	52.4	49.9	46.8	45.2
77.5°	41.0	47.1	52.6	53.6	49.9	45.5	41.8	38.5	36.3	34.9	33.4
80°	31.3	36.2	38.6	39.9	37.2	34.0	31.9	29.7	28.3	27.4	26.4
82.5°	22.4	25.4	27.6	28.7	27.1	25.2	23.2	21.9	20.8	20.1	19.7
85°	11.4	12.7	14.1	14.5	14.1	13.3	12.1	12.1	11.5	11.4	11.4
87.5°	4.3	5.3	5.5	6.3	6.3	6.5	6.7	6.7	6.8	6.8	6.7
90°	2.1	3.5	5.0	6.5	7.7	8.9	9.9	11.0	12.1	12.7	13.4
92.5°	12.1	11.9	11.8	11.6	11.9	12.4	12.9	13.4	13.9	14.3	14.7
95°	34.8	30.3	25.9	21.5	19.7	20.7	21.6	22.6	23.5	24.2	24.9
97.5°	65.3	52.9	40.4	27.9	22.8	25.0	27.1	29.3	31.4	32.0	32.5
100°	88.3	70.0	51.7	33.3	25.2	27.6	29.8	32.1	34.4	35.4	36.5
102.5°	134.7	130.7	126.8	123.0	111.5	92.5	73.4	54.3	35.3	36.7	38.1
105°	187.3	191.3	195.3	199.3	183.0	146.5	109.9	73.4	36.8	38.2	39.7
107.5°	237.5	240.7	243.9	247.2	226.9	183.0	139.2	95.3	51.5	49.9	48.5
110°	269.8	272.7	275.4	278.3	260.3	221.6	182.9	144.2	105.5	92.1	78.7



TEST NUMBER: P331471-935

CATALOG NUMBER: S122DIW-S290D710U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	300.4	302.9	305.3	307.8	304.3	294.7	285.2	275.6	266.0	217.2	168.3
115°	348.9	351.1	353.4	355.7	358.5	361.9	365.2	368.5	371.9	309.9	247.9
117.5°	392.6	395.2	397.7	400.3	402.7	405.0	407.3	409.6	411.9	396.9	381.9
120°	424.0	425.9	427.9	430.0	432.1	434.5	437.0	439.4	441.8	443.4	445.1
122.5°	451.1	453.1	455.3	457.4	459.8	462.4	465.0	467.6	470.3	471.2	472.2
125°	491.8	493.5	495.2	497.0	499.1	501.7	504.2	506.8	509.3	510.2	511.2
127.5°	529.2	531.2	533.0	535.0	536.9	538.8	540.7	542.6	544.5	545.9	547.3
130°	553.0	555.2	557.3	559.5	561.3	562.7	564.2	565.7	567.2	568.7	570.2
132.5°	576.9	578.7	580.5	582.3	583.9	585.4	586.9	588.4	589.9	591.1	592.4
135°	608.5	610.6	612.8	614.9	616.6	617.9	619.1	620.3	621.5	622.8	624.1
137.5°	639.6	641.1	642.6	644.0	645.5	646.9	648.2	649.6	651.0	652.3	653.6
140°	659.9	660.9	662.0	663.1	664.3	665.8	667.3	668.7	670.3	671.5	672.7
142.5°	677.1	678.1	679.1	680.0	681.3	683.0	684.8	686.4	688.1	689.2	690.3
145°	703.3	703.2	703.0	702.8	704.0	706.2	708.5	710.8	713.1	714.0	714.9
147.5°	726.7	726.2	725.7	725.1	726.0	728.2	730.5	732.7	734.9	735.7	736.4
150°	741.7	740.7	739.8	738.8	739.4	741.6	743.7	745.9	748.0	748.8	749.6
152.5°	754.6	753.5	752.4	751.4	751.9	754.0	756.0	758.0	760.1	760.9	761.6
155°	773.4	772.1	770.9	769.7	769.9	771.5	773.1	774.7	776.4	777.1	777.9
157.5°	788.3	787.3	786.3	785.3	785.3	786.4	787.6	788.7	789.8	790.7	791.7
160°	797.2	796.4	795.7	794.8	794.8	795.7	796.4	797.2	798.1	798.8	799.6
162.5°	804.9	804.2	803.3	802.5	802.5	803.1	803.9	804.6	805.3	806.2	807.1
165°	815.3	814.5	813.7	812.9	812.7	813.1	813.5	813.9	814.3	815.3	816.2
167.5°	823.0	822.3	821.4	820.6	820.4	820.8	821.1	821.6	821.9	822.9	823.8
170°	827.3	826.6	825.8	824.9	824.7	824.9	825.3	825.5	825.8	826.7	827.7
172.5°	830.3	829.5	828.6	827.9	827.6	827.9	828.1	828.4	828.6	829.6	830.5
175°	833.9	832.9	832.0	831.0	830.7	831.0	831.3	831.6	831.8	832.8	833.7
177.5°	834.7	833.9	833.2	832.4	832.1	832.2	832.3	832.4	832.5	833.3	834.1
180°	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0



TEST NUMBER: P331471-935

CATALOG NUMBER: S122DIW-S290D710U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	527.9	530.0	530.0	530.4	532.9	532.5	532.4
5°	561.7	565.1	565.4	568.9	571.3	570.5	568.3
7.5°	593.7	599.9	604.6	607.2	610.3	612.2	611.3
10°	619.1	628.0	633.5	637.2	641.7	645.1	643.9
12.5°	642.0	652.7	660.3	666.7	667.2	671.5	668.6
15°	678.0	689.2	690.4	695.1	698.9	698.4	698.6
17.5°	689.7	693.4	694.1	694.2	694.3	692.9	689.9
20°	685.5	684.2	680.9	678.3	673.8	673.2	669.3
22.5°	665.5	661.2	652.8	647.3	640.3	638.5	637.4
25°	626.1	616.5	603.2	590.5	586.9	580.1	582.0
27.5°	572.0	557.1	542.6	532.4	523.0	512.7	515.7
30°	534.0	517.1	496.8	481.1	471.1	461.4	459.6
32.5°	488.6	463.9	441.3	427.5	412.2	406.0	399.2
35°	410.4	386.2	363.8	344.4	333.3	324.7	316.8
37.5°	340.0	312.3	294.1	278.4	270.4	265.4	266.7
40°	296.4	272.1	258.7	246.8	239.4	235.9	236.7
42.5°	261.0	242.8	231.9	223.7	218.4	216.5	216.0
45°	220.8	210.7	201.6	197.0	194.4	192.3	190.9
47.5°	193.5	185.1	180.0	177.3	175.0	172.9	172.8
50°	177.0	171.5	168.0	165.1	163.3	161.8	163.2
52.5°	164.5	159.5	155.9	153.3	152.7	151.3	151.2
55°	145.9	142.0	139.5	137.1	136.0	135.2	134.1
57.5°	129.0	125.3	123.0	121.5	119.2	118.5	118.1
60°	116.9	114.0	111.7	109.7	108.7	107.2	107.2
62.5°	105.8	102.9	100.7	99.3	97.6	97.0	97.2
65°	89.8	87.4	85.2	83.7	83.3	82.1	82.6
67.5°	75.0	73.4	71.1	70.3	69.6	69.0	68.4
70°	65.1	63.5	62.4	61.2	60.6	60.6	60.6
72.5°	56.8	54.9	54.2	52.8	53.1	52.5	51.8
75°	44.0	42.8	42.3	41.7	40.7	40.7	40.7
77.5°	32.4	32.0	31.3	30.7	30.5	30.3	30.4
80°	25.1	24.8	24.5	24.5	24.0	23.8	23.5
82.5°	19.3	18.8	18.5	18.3	18.3	18.3	18.2
85°	10.9	10.6	10.6	10.8	10.3	10.3	10.6
87.5°	7.1	7.1	7.1	7.1	7.4	7.2	7.3
90°	14.0	14.7	15.2	15.5	15.8	16.0	16.3
92.5°	15.1	15.4	15.7	15.8	15.9	16.1	16.3
95°	25.5	26.2	26.4	26.3	26.2	26.1	25.9
97.5°	33.1	33.6	33.9	34.1	34.3	34.4	34.6
100°	37.5	38.7	39.3	39.6	39.9	40.1	40.4
102.5°	39.5	40.9	41.8	42.2	42.5	42.9	43.3
105°	41.2	42.6	43.7	44.2	44.8	45.3	45.8
107.5°	47.0	45.5	45.0	45.5	46.1	46.6	47.1
110°	65.3	51.9	45.5	46.0	46.6	47.1	47.6



TEST NUMBER: P331471-935

CATALOG NUMBER: S122DIW-S290D710U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	119.5	70.6	46.4	46.8	47.3	47.7	48.1
115°	185.8	123.8	88.0	78.4	68.7	59.1	49.4
117.5°	366.9	351.9	328.6	296.9	265.2	233.5	201.8
120°	446.6	448.2	440.0	421.9	403.8	385.7	367.6
122.5°	473.1	474.2	472.9	469.3	465.8	462.4	458.8
125°	512.1	513.1	513.8	514.1	514.5	515.0	515.3
127.5°	548.6	550.0	550.7	550.8	550.9	551.0	551.0
130°	571.6	573.1	573.8	573.6	573.5	573.3	573.3
132.5°	593.7	594.9	595.5	595.3	595.2	595.0	595.0
135°	625.4	626.8	627.3	627.1	626.8	626.5	626.3
137.5°	654.9	656.3	656.7	656.2	655.7	655.3	654.8
140°	673.9	675.1	675.4	674.7	674.0	673.3	672.7
142.5°	691.4	692.5	692.7	692.1	691.4	690.7	690.0
145°	715.8	716.8	717.0	716.3	715.6	714.9	714.3
147.5°	737.1	737.8	737.9	737.3	736.8	736.2	735.6
150°	750.4	751.2	751.3	750.6	749.9	749.2	748.6
152.5°	762.5	763.3	763.3	762.3	761.5	760.6	759.7
155°	778.8	779.5	779.4	778.3	777.3	776.2	775.2
157.5°	792.6	793.5	793.4	792.4	791.3	790.3	789.2
160°	800.5	801.2	801.2	800.2	799.3	798.4	797.5
162.5°	808.0	808.9	808.8	807.6	806.5	805.3	804.2
165°	817.1	818.0	818.0	817.1	816.2	815.3	814.3
167.5°	824.8	825.6	825.5	824.3	823.1	821.9	820.7
170°	828.5	829.5	829.4	828.2	827.0	825.8	824.6
172.5°	831.5	832.4	832.2	831.0	829.8	828.6	827.4
175°	834.6	835.5	835.3	834.0	832.7	831.3	830.0
177.5°	834.7	835.5	835.4	834.5	833.4	832.5	831.6
180°	833.0	833.0	833.0	833.0	833.0	833.0	833.0

(END OF REPORT)