

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331472-935

Luminaire Tested: **S122DIW-S290D710U935-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331472-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIW-S290D710U935-4F0-1E-UDD-A1  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 710 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3242.8 lumens  
Efficiency: N/A  
Efficacy: 106.7 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 30.4  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331472-935

CATALOG NUMBER: S122DIW-S290D710U935-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P331472-935

CATALOG NUMBER: S122DIW-S290D710U935-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	42	42	42	35			35
1	95	91	87	84	85	82	79	76	66	64	62	51	50	49	38	37	36	30			30
2	86	79	74	69	78	72	67	63	58	55	52	45	43	41	34	32	31	26			26
3	79	70	63	58	71	64	58	53	52	47	44	40	38	35	30	28	27	22			22
4	72	62	55	49	65	57	50	45	46	41	38	36	33	30	27	25	23	19			19
5	67	55	48	42	60	51	44	39	41	36	33	33	29	26	24	22	20	17			17
6	61	50	42	36	55	45	39	34	37	32	28	30	26	23	22	20	18	15			15
7	57	45	37	32	51	41	34	30	34	29	25	27	23	21	20	18	16	13			13
8	53	41	33	28	48	37	31	26	31	26	22	25	21	18	19	16	15	12			12
9	49	37	30	25	44	34	28	23	28	23	20	23	19	17	17	15	13	11			11
10	46	34	27	23	41	31	25	21	26	21	18	21	17	15	16	14	12	10			10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	8217	8217	8217	8217
5°	9211	8271	7329	8271
10°	10557	8202	6342	8202
15°	11677	8052	5605	8052
20°	11500	7892	5108	7892
25°	10368	7675	4794	7675
30°	8569	7333	4566	7333
35°	6244	6974	4401	6974
40°	4989	6551	4312	6551
45°	4359	6060	4190	6060
50°	4099	5586	4107	5586
55°	3775	5103	3997	5103
60°	3462	4592	3830	4592
65°	3156	4130	3660	4130
70°	2861	3682	3418	3682
75°	2539	3188	3026	3188
80°	2185	2631	2436	2631
85°	1964	1964	1445	1964



TEST NUMBER: P331472-935

CATALOG NUMBER: S122DIW-S290D710U935-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	48.5	1.5
10°-20°	140.9	4.3
20°-30°	204.5	6.3
30°-40°	215.8	6.7
40°-50°	191.1	5.9
50°-60°	152.5	4.7
60°-70°	103.6	3.2
70°-80°	53.1	1.6
80°-90°	15.8	0.5
90°-100°	48.0	1.5
100°-110°	149.0	4.6
110°-120°	254.7	7.9
120°-130°	334.9	10.3
130°-140°	375.9	11.6
140°-150°	368.6	11.4
150°-160°	309.2	9.5
160°-170°	205.1	6.3
170°-180°	71.7	2.2
0°-30°	393.9	12.1
0°-40°	609.7	18.8
0°-60°	953.2	29.4
0°-90°	1125.8	34.7
90°-120°	451.7	13.9
90°-150°	1531.1	47.2
90°-180°	2117.0	65.3
0°-180°	3242.8	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	509	509	509	509	509	
5°	568	510	452	510	568	57
15°	699	482	335	482	699	193
25°	582	431	269	431	582	263
35°	317	354	223	354	317	206
45°	191	265	184	265	191	150
55°	134	181	142	181	134	120
65°	83	108	96	108	83	82
75°	41	51	48	51	41	43
85°	11	11	8	11	11	12
90°	22	1	22	1	22	10
95°	40	33	40	33	40	44
105°	142	137	142	137	142	149
115°	256	256	256	256	256	252
125°	373	372	373	372	373	333
135°	487	481	487	481	487	375
145°	590	584	590	584	590	369
155°	673	668	673	668	673	310
165°	727	726	727	726	727	205
175°	753	756	753	756	753	72
180°	757	757	757	757	757	



TEST NUMBER: P331472-935

CATALOG NUMBER: S122DIW-S290D710U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	532.4	532.5	532.9	530.4	530.0	530.0	527.9	526.0	523.7	520.8	521.2
5°	568.3	570.5	571.3	568.9	565.4	565.1	561.7	556.3	551.1	547.1	544.2
7.5°	611.3	612.2	610.3	607.2	604.6	599.9	593.7	587.6	579.1	571.4	565.6
10°	643.9	645.1	641.7	637.2	633.5	628.0	619.1	609.8	598.7	588.0	579.4
12.5°	668.6	671.5	667.2	666.7	660.3	652.7	642.0	637.4	621.7	606.7	597.4
15°	698.6	698.4	698.9	695.1	690.4	689.2	678.0	665.6	643.5	634.6	619.4
17.5°	689.9	692.9	694.3	694.2	694.1	693.4	689.7	682.0	670.9	656.6	639.0
20°	669.3	673.2	673.8	678.3	680.9	684.2	685.5	683.4	676.6	664.6	649.4
22.5°	637.4	638.5	640.3	647.3	652.8	661.2	665.5	672.8	670.1	664.3	651.5
25°	582.0	580.1	586.9	590.5	603.2	616.5	626.1	636.6	646.0	651.7	648.0
27.5°	515.7	512.7	523.0	532.4	542.6	557.1	572.0	589.6	604.2	622.7	629.0
30°	459.6	461.4	471.1	481.1	496.8	517.1	534.0	553.3	574.3	594.8	609.1
32.5°	399.2	406.0	412.2	427.5	441.3	463.9	488.6	512.8	538.9	562.2	584.4
35°	316.8	324.7	333.3	344.4	363.8	386.2	410.4	443.0	478.6	510.5	536.7
37.5°	266.7	265.4	270.4	278.4	294.1	312.3	340.0	372.2	414.1	451.6	488.6
40°	236.7	235.9	239.4	246.8	258.7	272.1	296.4	324.7	363.6	409.4	453.4
42.5°	216.0	216.5	218.4	223.7	231.9	242.8	261.0	285.1	320.7	363.9	411.1
45°	190.9	192.3	194.4	197.0	201.6	210.7	220.8	238.1	266.2	302.2	348.7
47.5°	172.8	172.9	175.0	177.3	180.0	185.1	193.5	204.2	224.1	253.4	293.4
50°	163.2	161.8	163.3	165.1	168.0	171.5	177.0	187.2	200.4	224.1	257.6
52.5°	151.2	151.3	152.7	153.3	155.9	159.5	164.5	171.5	183.6	202.1	229.5
55°	134.1	135.2	136.0	137.1	139.5	142.0	145.9	150.6	160.0	173.8	194.2
57.5°	118.1	118.5	119.2	121.5	123.0	125.3	129.0	133.3	139.4	149.6	165.0
60°	107.2	107.2	108.7	109.7	111.7	114.0	116.9	121.1	126.6	134.9	147.3
62.5°	97.2	97.0	97.6	99.3	100.7	102.9	105.8	109.3	114.5	122.0	132.1
65°	82.6	82.1	83.3	83.7	85.2	87.4	89.8	93.5	97.6	103.1	112.1
67.5°	68.4	69.0	69.6	70.3	71.1	73.4	75.0	77.6	81.1	85.7	91.7
70°	60.6	60.6	60.6	61.2	62.4	63.5	65.1	67.2	70.6	74.5	80.0
72.5°	51.8	52.5	53.1	52.8	54.2	54.9	56.8	58.0	61.2	63.7	68.5
75°	40.7	40.7	40.7	41.7	42.3	42.8	44.0	45.2	46.8	49.9	52.4
77.5°	30.4	30.3	30.5	30.7	31.3	32.0	32.4	33.4	34.9	36.3	38.5
80°	23.5	23.8	24.0	24.5	24.5	24.8	25.1	26.4	27.4	28.3	29.7
82.5°	18.2	18.3	18.3	18.3	18.5	18.8	19.3	19.7	20.1	20.8	21.9
85°	10.6	10.3	10.3	10.8	10.6	10.6	10.9	11.4	11.4	11.5	12.1
87.5°	8.4	8.4	8.5	8.4	8.3	8.4	8.5	8.4	8.6	8.9	8.4
90°	21.7	21.6	21.4	21.3	21.2	21.3	21.5	21.8	22.0	22.4	19.2
92.5°	20.7	20.7	20.7	20.6	20.6	20.6	20.5	20.4	20.4	20.3	19.5
95°	39.6	39.9	40.2	40.5	40.7	40.9	40.9	40.9	40.9	40.9	40.6
97.5°	68.6	68.6	68.7	68.7	68.7	68.7	68.7	68.7	68.7	68.7	68.2
100°	87.6	87.6	87.8	88.0	88.1	88.2	88.2	88.2	88.2	88.2	87.7
102.5°	109.0	109.2	109.3	109.4	109.6	109.6	109.4	109.3	109.3	109.1	108.6
105°	141.8	141.8	141.8	141.8	141.8	141.7	141.4	141.1	140.9	140.6	140.3
107.5°	172.8	173.4	174.1	174.7	175.4	175.6	175.6	175.4	175.3	175.2	175.2
110°	196.8	197.2	197.6	198.0	198.5	198.7	198.7	198.7	198.7	198.7	198.7



TEST NUMBER: P331472-935

CATALOG NUMBER: S122DIW-S290D710U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	219.8	220.1	220.4	220.8	221.0	221.4	221.7	222.1	222.4	222.7	222.8
115°	255.5	256.0	256.4	256.8	257.3	257.5	257.7	257.9	258.0	258.1	258.4
117.5°	289.6	290.1	290.5	290.9	291.4	291.8	292.1	292.5	292.8	293.2	293.9
120°	313.7	314.1	314.5	315.0	315.4	315.6	315.6	315.6	315.6	315.6	316.8
122.5°	337.3	337.5	337.9	338.1	338.5	338.8	339.1	339.5	339.8	340.2	341.0
125°	373.2	373.2	373.4	373.6	373.7	373.9	374.4	374.8	375.2	375.7	376.1
127.5°	405.9	406.3	406.7	407.2	407.7	408.1	408.6	409.1	409.7	410.2	410.7
130°	429.4	429.9	430.5	431.0	431.6	432.0	432.3	432.7	432.9	433.2	433.4
132.5°	451.9	452.3	452.7	453.2	453.7	454.2	454.8	455.5	456.1	456.7	456.7
135°	486.8	487.2	487.7	488.1	488.5	488.9	489.0	489.1	489.2	489.4	489.1
137.5°	518.5	519.1	519.7	520.2	520.8	521.2	521.2	521.3	521.5	521.6	521.2
140°	540.5	541.1	541.7	542.3	542.8	543.0	543.0	543.0	543.0	543.0	542.3
142.5°	560.4	561.0	561.5	562.1	562.7	562.9	562.8	562.7	562.6	562.5	562.0
145°	590.4	590.9	591.5	592.0	592.6	592.8	592.7	592.5	592.4	592.3	591.4
147.5°	617.1	617.6	618.1	618.7	619.2	619.3	619.0	618.7	618.4	618.1	617.5
150°	634.5	634.9	635.2	635.7	636.1	636.1	635.7	635.2	634.9	634.5	633.9
152.5°	650.8	651.3	651.9	652.4	653.0	653.0	652.4	651.9	651.3	650.8	650.1
155°	672.8	673.2	673.6	674.1	674.5	674.3	673.6	672.9	672.2	671.5	671.1
157.5°	691.6	692.3	693.0	693.7	694.4	694.2	693.3	692.3	691.4	690.4	690.2
160°	703.4	704.0	704.6	705.2	705.7	705.6	704.7	703.9	703.0	702.1	702.0
162.5°	713.7	714.4	715.1	715.7	716.4	716.3	715.3	714.3	713.3	712.4	712.2
165°	727.1	727.8	728.5	729.2	730.0	729.8	728.8	727.8	726.8	725.8	725.8
167.5°	738.0	738.8	739.5	740.3	741.0	740.9	739.9	738.9	737.9	736.9	736.9
170°	743.6	744.5	745.4	746.2	747.1	747.0	746.1	745.0	744.1	743.0	743.2
172.5°	748.3	749.2	750.0	750.9	751.7	751.7	750.6	749.7	748.6	747.6	747.8
175°	753.3	754.1	755.0	755.8	756.6	756.6	755.6	754.6	753.6	752.6	752.9
177.5°	755.5	756.2	756.9	757.6	758.3	758.3	757.6	756.9	756.2	755.5	755.8
180°	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1



TEST NUMBER: P331472-935

CATALOG NUMBER: S122DIW-S290D710U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	522.2	521.0	520.2	517.4	514.9	512.4	511.6	511.9	508.4	505.1	503.8
5°	542.6	538.6	534.9	529.7	523.4	516.5	513.1	510.3	503.4	496.0	491.7
7.5°	560.8	555.2	548.0	538.1	529.0	518.2	511.3	505.3	495.3	484.8	478.4
10°	571.9	564.3	555.1	542.9	531.8	518.7	509.5	500.3	488.6	476.0	468.2
12.5°	581.4	571.2	562.1	546.6	533.4	516.9	506.1	493.1	480.8	465.9	458.2
15°	604.2	585.2	568.0	550.4	534.2	511.3	499.1	481.7	465.5	447.1	438.3
17.5°	621.7	600.4	573.3	551.0	532.0	506.6	488.9	468.0	448.8	427.8	415.9
20°	631.7	607.3	578.2	551.6	528.9	499.9	480.5	459.3	436.8	413.1	400.2
22.5°	637.7	612.0	583.2	549.2	522.6	494.5	470.1	446.7	424.0	398.4	384.9
25°	639.6	616.1	585.6	547.3	514.8	482.9	453.6	430.8	403.3	379.4	359.7
27.5°	630.3	613.5	584.1	543.5	505.8	468.5	435.8	410.1	381.0	355.1	335.2
30°	618.8	609.1	580.5	539.8	498.5	458.5	422.5	393.3	364.4	338.2	317.8
32.5°	601.2	599.1	573.9	534.5	490.9	445.8	408.5	379.1	347.0	321.2	301.9
35°	566.5	575.8	560.0	522.6	476.5	427.7	387.4	353.8	320.6	295.9	277.8
37.5°	519.9	543.2	539.1	505.2	456.9	408.1	363.6	328.5	296.8	271.9	254.1
40°	487.8	517.5	521.9	491.9	443.2	393.0	345.8	310.8	279.9	257.2	239.2
42.5°	453.4	488.1	499.9	476.0	428.2	376.9	329.8	293.6	262.9	240.9	225.0
45°	395.7	441.6	463.0	449.3	403.1	350.7	302.2	265.4	237.6	216.9	204.6
47.5°	341.7	391.9	420.6	415.8	375.2	323.3	275.3	240.0	213.0	196.5	185.5
50°	303.6	355.2	389.8	391.4	355.2	303.8	255.6	222.4	197.5	182.1	173.1
52.5°	270.4	319.7	357.4	365.8	332.8	283.4	238.0	204.8	183.0	168.8	160.7
55°	227.0	268.7	310.6	325.9	299.5	252.5	210.4	181.3	160.7	151.0	144.0
57.5°	188.8	223.5	262.2	279.1	262.8	222.6	183.1	157.8	141.2	132.6	127.2
60°	168.6	196.0	230.4	250.6	236.4	200.7	166.3	142.2	128.5	120.9	115.8
62.5°	149.8	174.1	203.2	221.6	214.0	180.2	149.4	128.1	116.3	109.2	105.5
65°	123.6	142.8	165.3	182.3	177.2	151.6	126.3	108.1	98.8	93.1	90.1
67.5°	101.8	115.6	131.2	146.1	142.1	123.9	103.7	89.5	82.5	77.6	75.8
70°	88.0	98.6	112.4	124.4	121.1	106.2	90.1	78.0	72.0	67.8	66.1
72.5°	74.9	83.5	94.2	103.9	101.7	89.3	75.9	66.8	62.1	58.3	56.9
75°	56.6	63.2	69.7	76.1	75.5	66.0	58.1	51.1	47.4	44.4	43.8
77.5°	41.8	45.5	49.9	53.6	52.6	47.1	41.0	36.9	34.3	32.3	31.9
80°	31.9	34.0	37.2	39.9	38.6	36.2	31.3	28.3	26.4	24.5	23.7
82.5°	23.2	25.2	27.1	28.7	27.6	25.4	22.4	20.4	19.2	17.9	17.6
85°	12.1	13.3	14.1	14.5	14.1	12.7	11.4	10.6	9.6	9.0	8.8
87.5°	7.9	7.3	6.6	6.5	5.7	5.3	4.4	3.5	3.8	4.0	4.0
90°	16.1	13.0	9.9	7.5	5.8	4.0	2.3	0.6	2.3	4.0	5.8
92.5°	18.9	18.1	17.4	16.4	15.2	13.9	12.7	11.4	12.7	13.9	15.2
95°	40.3	40.0	39.8	38.9	37.5	36.1	34.6	33.2	34.6	36.1	37.5
97.5°	67.7	67.2	66.6	65.7	64.4	63.2	61.9	60.7	61.9	63.2	64.4
100°	87.3	86.9	86.4	85.7	84.6	83.4	82.3	81.1	82.3	83.4	84.6
102.5°	108.1	107.5	106.9	106.2	105.3	104.4	103.5	102.6	103.5	104.4	105.3
105°	140.0	139.7	139.4	139.1	138.6	138.2	137.8	137.3	137.8	138.2	138.6
107.5°	175.2	175.2	175.2	174.9	174.3	173.7	173.0	172.4	173.0	173.7	174.3
110°	198.7	198.7	198.7	198.3	197.4	196.6	195.7	194.8	195.7	196.6	197.4





TEST NUMBER: P331472-935

CATALOG NUMBER: S122DIW-S290D710U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	222.9	223.1	223.2	222.8	222.0	221.1	220.2	219.4	220.2	221.1	222.0
115°	258.6	259.0	259.2	259.0	258.1	257.3	256.4	255.5	256.4	257.3	258.1
117.5°	294.7	295.5	296.3	296.1	295.0	293.9	292.7	291.6	292.7	293.9	295.0
120°	317.9	319.0	320.1	320.1	319.0	317.9	316.8	315.6	316.8	317.9	319.0
122.5°	341.7	342.5	343.4	343.0	341.6	340.4	339.0	337.6	339.0	340.4	341.6
125°	376.5	376.9	377.4	376.9	375.7	374.4	373.2	371.9	373.2	374.4	375.7
127.5°	411.2	411.7	412.2	411.6	410.0	408.5	406.8	405.2	406.8	408.5	410.0
130°	433.8	434.0	434.3	433.5	431.7	429.8	428.0	426.1	428.0	429.8	431.7
132.5°	456.6	456.5	456.5	455.6	454.2	452.7	451.2	449.7	451.2	452.7	454.2
135°	488.9	488.5	488.3	487.3	485.8	484.2	482.7	481.1	482.7	484.2	485.8
137.5°	520.9	520.5	520.1	519.3	518.1	516.8	515.5	514.2	515.5	516.8	518.1
140°	541.7	541.0	540.2	539.2	538.0	536.7	535.4	534.2	535.4	536.7	538.0
142.5°	561.5	561.0	560.6	559.6	558.4	557.2	555.9	554.6	555.9	557.2	558.4
145°	590.6	589.7	588.8	588.0	586.9	585.9	585.0	583.9	585.0	585.9	586.9
147.5°	616.9	616.4	615.8	614.9	613.7	612.5	611.3	610.2	611.3	612.5	613.7
150°	633.3	632.7	632.1	631.5	630.6	629.7	628.9	628.0	628.9	629.7	630.6
152.5°	649.5	648.8	648.1	647.3	646.4	645.6	644.7	643.9	644.7	645.6	646.4
155°	670.6	670.2	669.8	669.3	668.9	668.5	668.0	667.6	668.0	668.5	668.9
157.5°	689.9	689.7	689.4	689.1	688.8	688.5	688.3	687.9	688.3	688.5	688.8
160°	701.9	701.7	701.6	701.4	701.1	700.8	700.5	700.3	700.5	700.8	701.1
162.5°	712.1	712.0	711.8	711.7	711.6	711.6	711.5	711.4	711.5	711.6	711.6
165°	725.8	725.8	725.8	725.9	726.0	726.2	726.3	726.4	726.3	726.2	726.0
167.5°	736.9	737.0	737.0	737.3	737.7	738.1	738.6	739.0	738.6	738.1	737.7
170°	743.3	743.5	743.6	743.9	744.3	744.8	745.2	745.6	745.2	744.8	744.3
172.5°	748.0	748.0	748.2	748.5	748.9	749.3	749.8	750.2	749.8	749.3	748.9
175°	753.2	753.5	753.8	754.1	754.6	755.0	755.4	755.8	755.4	755.0	754.6
177.5°	756.0	756.2	756.5	756.7	757.1	757.4	757.8	758.1	757.8	757.4	757.1
180°	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1



TEST NUMBER: P331472-935

CATALOG NUMBER: S122DIW-S290D710U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	502.2	501.3	498.0	496.3	493.4	490.8	489.0	489.8	490.4	490.2	489.7
5°	487.8	484.1	478.4	473.6	470.0	463.6	460.8	459.4	458.2	456.9	455.6
7.5°	470.6	464.8	456.7	449.7	443.2	435.1	430.5	427.8	425.0	421.9	419.1
10°	458.5	450.2	441.6	431.9	424.0	416.8	410.4	406.0	402.1	398.4	395.7
12.5°	445.7	436.2	425.5	412.2	403.6	393.1	392.2	384.6	378.5	376.2	373.0
15°	425.2	411.9	398.4	382.5	375.7	366.4	360.5	354.6	349.3	345.6	344.7
17.5°	402.0	384.8	371.3	360.0	348.8	339.1	333.7	329.1	324.7	319.8	319.1
20°	384.4	369.5	354.8	344.8	333.3	323.5	316.8	312.2	308.4	305.5	303.0
22.5°	367.6	351.3	337.9	327.0	315.6	307.7	302.5	297.9	294.8	291.6	289.2
25°	340.7	328.0	313.3	301.0	291.6	286.5	282.2	278.4	276.4	274.2	271.5
27.5°	317.2	303.1	289.4	279.8	271.6	267.1	264.0	261.3	259.5	258.2	256.7
30°	300.7	286.4	275.6	266.2	259.3	254.9	252.9	251.3	249.2	248.4	247.6
32.5°	284.6	271.8	262.6	254.4	248.0	245.0	243.2	241.8	240.1	239.4	237.7
35°	262.1	251.3	242.4	237.8	232.6	230.0	228.7	226.7	225.2	224.4	224.1
37.5°	240.8	231.5	225.6	219.8	217.6	216.0	214.1	212.8	212.3	212.2	212.0
40°	227.0	219.5	214.1	209.5	208.5	206.1	204.6	203.5	203.5	203.6	203.5
42.5°	214.6	207.7	203.0	199.0	197.9	196.5	194.8	194.8	195.1	195.8	195.1
45°	195.6	190.7	187.4	185.5	183.3	181.9	181.7	182.3	182.4	182.7	183.3
47.5°	178.1	174.9	171.9	169.7	168.8	168.6	168.3	169.4	170.3	170.7	171.5
50°	167.8	164.1	161.5	160.1	159.4	159.0	159.4	160.6	161.4	162.3	162.9
52.5°	156.3	153.6	151.9	150.8	150.5	150.8	150.8	152.1	153.3	153.8	154.0
55°	140.3	138.3	137.9	136.1	136.9	136.7	137.7	138.4	139.7	140.9	141.0
57.5°	124.2	122.7	121.7	121.8	122.1	123.0	123.7	125.1	126.3	127.6	127.7
60°	113.7	112.9	112.3	112.3	112.6	113.8	114.8	116.1	116.9	117.8	118.3
62.5°	103.9	103.1	102.5	102.9	103.9	104.6	105.7	106.5	107.3	108.1	108.3
65°	88.6	88.3	88.8	89.2	89.4	90.3	91.7	92.3	93.1	93.5	94.9
67.5°	74.5	74.6	74.5	75.0	76.2	76.4	77.7	79.0	79.2	80.0	80.8
70°	64.9	65.3	65.7	66.1	67.1	67.5	68.4	69.1	69.8	70.4	71.0
72.5°	56.1	56.2	56.7	56.6	57.4	58.2	59.1	59.7	60.4	61.2	61.7
75°	43.2	43.2	43.7	43.8	44.8	45.8	45.5	46.0	46.8	47.5	48.0
77.5°	31.6	31.2	31.6	31.8	32.1	32.9	33.1	33.6	34.5	34.3	34.7
80°	24.0	23.5	24.0	24.3	24.3	25.2	25.2	25.7	26.2	25.7	26.2
82.5°	17.1	16.9	17.3	17.4	17.7	17.7	18.0	18.1	18.7	18.4	18.7
85°	8.6	8.4	8.6	8.4	8.6	8.8	8.8	8.6	8.6	9.0	8.4
87.5°	4.1	4.5	4.9	5.6	6.0	6.5	6.3	6.2	6.2	5.8	5.8
90°	7.5	9.9	13.0	16.1	19.2	22.4	22.0	21.8	21.5	21.3	21.2
92.5°	16.4	17.4	18.1	18.9	19.5	20.3	20.4	20.4	20.5	20.6	20.6
95°	38.9	39.8	40.0	40.3	40.6	40.9	40.9	40.9	40.9	40.9	40.7
97.5°	65.7	66.6	67.2	67.7	68.2	68.7	68.7	68.7	68.7	68.7	68.7
100°	85.7	86.4	86.9	87.3	87.7	88.2	88.2	88.2	88.2	88.2	88.1
102.5°	106.2	106.9	107.5	108.1	108.6	109.1	109.3	109.3	109.4	109.6	109.6
105°	139.1	139.4	139.7	140.0	140.3	140.6	140.9	141.1	141.4	141.7	141.8
107.5°	174.9	175.2	175.2	175.2	175.2	175.2	175.3	175.4	175.6	175.6	175.4
110°	198.3	198.7	198.7	198.7	198.7	198.7	198.7	198.7	198.7	198.7	198.5



TEST NUMBER: P331472-935

CATALOG NUMBER: S122DIW-S290D710U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	222.8	223.2	223.1	222.9	222.8	222.7	222.4	222.1	221.7	221.4	221.0
115°	259.0	259.2	259.0	258.6	258.4	258.1	258.0	257.9	257.7	257.5	257.3
117.5°	296.1	296.3	295.5	294.7	293.9	293.2	292.8	292.5	292.1	291.8	291.4
120°	320.1	320.1	319.0	317.9	316.8	315.6	315.6	315.6	315.6	315.6	315.4
122.5°	343.0	343.4	342.5	341.7	341.0	340.2	339.8	339.5	339.1	338.8	338.5
125°	376.9	377.4	376.9	376.5	376.1	375.7	375.2	374.8	374.4	373.9	373.7
127.5°	411.6	412.2	411.7	411.2	410.7	410.2	409.7	409.1	408.6	408.1	407.7
130°	433.5	434.3	434.0	433.8	433.4	433.2	432.9	432.7	432.3	432.0	431.6
132.5°	455.6	456.5	456.5	456.6	456.7	456.7	456.1	455.5	454.8	454.2	453.7
135°	487.3	488.3	488.5	488.9	489.1	489.4	489.2	489.1	489.0	488.9	488.5
137.5°	519.3	520.1	520.5	520.9	521.2	521.6	521.5	521.3	521.2	521.2	520.8
140°	539.2	540.2	541.0	541.7	542.3	543.0	543.0	543.0	543.0	543.0	542.8
142.5°	559.6	560.6	561.0	561.5	562.0	562.5	562.6	562.7	562.8	562.9	562.7
145°	588.0	588.8	589.7	590.6	591.4	592.3	592.4	592.5	592.7	592.8	592.6
147.5°	614.9	615.8	616.4	616.9	617.5	618.1	618.4	618.7	619.0	619.3	619.2
150°	631.5	632.1	632.7	633.3	633.9	634.5	634.9	635.2	635.7	636.1	636.1
152.5°	647.3	648.1	648.8	649.5	650.1	650.8	651.3	651.9	652.4	653.0	653.0
155°	669.3	669.8	670.2	670.6	671.1	671.5	672.2	672.9	673.6	674.3	674.5
157.5°	689.1	689.4	689.7	689.9	690.2	690.4	691.4	692.3	693.3	694.2	694.4
160°	701.4	701.6	701.7	701.9	702.0	702.1	703.0	703.9	704.7	705.6	705.7
162.5°	711.7	711.8	712.0	712.1	712.2	712.4	713.3	714.3	715.3	716.3	716.4
165°	725.9	725.8	725.8	725.8	725.8	725.8	726.8	727.8	728.8	729.8	730.0
167.5°	737.3	737.0	737.0	736.9	736.9	736.9	737.9	738.9	739.9	740.9	741.0
170°	743.9	743.6	743.5	743.3	743.2	743.0	744.1	745.0	746.1	747.0	747.1
172.5°	748.5	748.2	748.0	748.0	747.8	747.6	748.6	749.7	750.6	751.7	751.7
175°	754.1	753.8	753.5	753.2	752.9	752.6	753.6	754.6	755.6	756.6	756.6
177.5°	756.7	756.5	756.2	756.0	755.8	755.5	756.2	756.9	757.6	758.3	758.3
180°	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1



TEST NUMBER: P331472-935

CATALOG NUMBER: S122DIW-S290D710U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	488.1	487.8	487.8	486.4	487.8	487.8	488.1	489.7	490.2	490.4	489.8
5°	452.8	452.2	451.3	452.2	451.3	452.2	452.8	455.6	456.9	458.2	459.4
7.5°	417.8	415.5	415.2	412.8	415.2	415.5	417.8	419.1	421.9	425.0	427.8
10°	392.4	390.8	390.5	386.8	390.5	390.8	392.4	395.7	398.4	402.1	406.0
12.5°	373.0	369.2	370.0	367.8	370.0	369.2	373.0	373.0	376.2	378.5	384.6
15°	339.3	339.3	338.5	335.3	338.5	339.3	339.3	344.7	345.6	349.3	354.6
17.5°	315.2	314.8	313.0	313.9	313.0	314.8	315.2	319.1	319.8	324.7	329.1
20°	300.8	299.6	297.3	297.3	297.3	299.6	300.8	303.0	305.5	308.4	312.2
22.5°	287.2	287.1	284.6	285.4	284.6	287.1	287.2	289.2	291.6	294.8	297.9
25°	271.3	269.8	268.5	269.1	268.5	269.8	271.3	271.5	274.2	276.4	278.4
27.5°	256.1	255.3	255.2	253.7	255.2	255.3	256.1	256.7	258.2	259.5	261.3
30°	247.5	245.5	245.8	244.9	245.8	245.5	247.5	247.6	248.4	249.2	251.3
32.5°	237.4	236.7	236.3	235.5	236.3	236.7	237.4	237.7	239.4	240.1	241.8
35°	223.8	223.9	223.0	223.3	223.0	223.9	223.8	224.1	224.4	225.2	226.7
37.5°	211.8	212.4	212.0	212.1	212.0	212.4	211.8	212.0	212.2	212.3	212.8
40°	204.0	204.0	204.0	204.6	204.0	204.0	204.0	203.5	203.6	203.5	203.5
42.5°	196.5	196.1	195.9	195.8	195.9	196.1	196.5	195.1	195.8	195.1	194.8
45°	183.7	184.3	184.4	183.5	184.4	184.3	183.7	183.3	182.7	182.4	182.3
47.5°	172.0	172.1	172.0	172.9	172.0	172.1	172.0	171.5	170.7	170.3	169.4
50°	163.9	163.5	163.9	163.5	163.9	163.5	163.9	162.9	162.3	161.4	160.6
52.5°	155.3	155.4	155.2	155.1	155.2	155.4	155.3	154.0	153.8	153.3	152.1
55°	141.8	142.2	142.0	142.0	142.0	142.2	141.8	141.0	140.9	139.7	138.4
57.5°	127.9	128.2	128.5	127.6	128.5	128.2	127.9	127.7	127.6	126.3	125.1
60°	118.1	119.1	118.9	118.6	118.9	119.1	118.1	118.3	117.8	116.9	116.1
62.5°	109.2	109.6	109.5	109.4	109.5	109.6	109.2	108.3	108.1	107.3	106.5
65°	95.5	95.8	95.2	95.8	95.2	95.8	95.5	94.9	93.5	93.1	92.3
67.5°	80.6	80.8	81.2	81.5	81.2	80.8	80.6	80.8	80.0	79.2	79.0
70°	71.4	71.2	71.8	72.4	71.8	71.2	71.4	71.0	70.4	69.8	69.1
72.5°	61.6	62.1	61.9	62.3	61.9	62.1	61.6	61.7	61.2	60.4	59.7
75°	47.5	48.1	48.0	48.5	48.0	48.1	47.5	48.0	47.5	46.8	46.0
77.5°	34.4	34.4	34.4	34.7	34.4	34.4	34.4	34.7	34.3	34.5	33.6
80°	26.2	25.8	25.4	26.2	25.4	25.8	26.2	26.2	25.7	26.2	25.7
82.5°	18.3	18.4	18.1	18.1	18.1	18.4	18.3	18.7	18.4	18.7	18.1
85°	8.4	8.2	7.8	7.8	7.8	8.2	8.4	8.4	9.0	8.6	8.6
87.5°	5.9	5.7	5.7	5.6	5.7	5.7	5.9	5.8	5.8	6.2	6.2
90°	21.3	21.4	21.6	21.7	21.6	21.4	21.3	21.2	21.3	21.5	21.8
92.5°	20.6	20.7	20.7	20.7	20.7	20.7	20.6	20.6	20.6	20.5	20.4
95°	40.5	40.2	39.9	39.6	39.9	40.2	40.5	40.7	40.9	40.9	40.9
97.5°	68.7	68.7	68.6	68.6	68.6	68.7	68.7	68.7	68.7	68.7	68.7
100°	88.0	87.8	87.6	87.6	87.6	87.8	88.0	88.1	88.2	88.2	88.2
102.5°	109.4	109.3	109.2	109.0	109.2	109.3	109.4	109.6	109.6	109.4	109.3
105°	141.8	141.8	141.8	141.8	141.8	141.8	141.8	141.8	141.7	141.4	141.1
107.5°	174.7	174.1	173.4	172.8	173.4	174.1	174.7	175.4	175.6	175.6	175.4
110°	198.0	197.6	197.2	196.8	197.2	197.6	198.0	198.5	198.7	198.7	198.7



TEST NUMBER: P331472-935

CATALOG NUMBER: S122DIW-S290D710U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	220.8	220.4	220.1	219.8	220.1	220.4	220.8	221.0	221.4	221.7	222.1
115°	256.8	256.4	256.0	255.5	256.0	256.4	256.8	257.3	257.5	257.7	257.9
117.5°	290.9	290.5	290.1	289.6	290.1	290.5	290.9	291.4	291.8	292.1	292.5
120°	315.0	314.5	314.1	313.7	314.1	314.5	315.0	315.4	315.6	315.6	315.6
122.5°	338.1	337.9	337.5	337.3	337.5	337.9	338.1	338.5	338.8	339.1	339.5
125°	373.6	373.4	373.2	373.2	373.2	373.4	373.6	373.7	373.9	374.4	374.8
127.5°	407.2	406.7	406.3	405.9	406.3	406.7	407.2	407.7	408.1	408.6	409.1
130°	431.0	430.5	429.9	429.4	429.9	430.5	431.0	431.6	432.0	432.3	432.7
132.5°	453.2	452.7	452.3	451.9	452.3	452.7	453.2	453.7	454.2	454.8	455.5
135°	488.1	487.7	487.2	486.8	487.2	487.7	488.1	488.5	488.9	489.0	489.1
137.5°	520.2	519.7	519.1	518.5	519.1	519.7	520.2	520.8	521.2	521.2	521.3
140°	542.3	541.7	541.1	540.5	541.1	541.7	542.3	542.8	543.0	543.0	543.0
142.5°	562.1	561.5	561.0	560.4	561.0	561.5	562.1	562.7	562.9	562.8	562.7
145°	592.0	591.5	590.9	590.4	590.9	591.5	592.0	592.6	592.8	592.7	592.5
147.5°	618.7	618.1	617.6	617.1	617.6	618.1	618.7	619.2	619.3	619.0	618.7
150°	635.7	635.2	634.9	634.5	634.9	635.2	635.7	636.1	636.1	635.7	635.2
152.5°	652.4	651.9	651.3	650.8	651.3	651.9	652.4	653.0	653.0	652.4	651.9
155°	674.1	673.6	673.2	672.8	673.2	673.6	674.1	674.5	674.3	673.6	672.9
157.5°	693.7	693.0	692.3	691.6	692.3	693.0	693.7	694.4	694.2	693.3	692.3
160°	705.2	704.6	704.0	703.4	704.0	704.6	705.2	705.7	705.6	704.7	703.9
162.5°	715.7	715.1	714.4	713.7	714.4	715.1	715.7	716.4	716.3	715.3	714.3
165°	729.2	728.5	727.8	727.1	727.8	728.5	729.2	730.0	729.8	728.8	727.8
167.5°	740.3	739.5	738.8	738.0	738.8	739.5	740.3	741.0	740.9	739.9	738.9
170°	746.2	745.4	744.5	743.6	744.5	745.4	746.2	747.1	747.0	746.1	745.0
172.5°	750.9	750.0	749.2	748.3	749.2	750.0	750.9	751.7	751.7	750.6	749.7
175°	755.8	755.0	754.1	753.3	754.1	755.0	755.8	756.6	756.6	755.6	754.6
177.5°	757.6	756.9	756.2	755.5	756.2	756.9	757.6	758.3	758.3	757.6	756.9
180°	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1



TEST NUMBER: P331472-935

CATALOG NUMBER: S122DIW-S290D710U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	489.0	490.8	493.4	496.3	498.0	501.3	502.2	503.8	505.1	508.4	511.9
5°	460.8	463.6	470.0	473.6	478.4	484.1	487.8	491.7	496.0	503.4	510.3
7.5°	430.5	435.1	443.2	449.7	456.7	464.8	470.6	478.4	484.8	495.3	505.3
10°	410.4	416.8	424.0	431.9	441.6	450.2	458.5	468.2	476.0	488.6	500.3
12.5°	392.2	393.1	403.6	412.2	425.5	436.2	445.7	458.2	465.9	480.8	493.1
15°	360.5	366.4	375.7	382.5	398.4	411.9	425.2	438.3	447.1	465.5	481.7
17.5°	333.7	339.1	348.8	360.0	371.3	384.8	402.0	415.9	427.8	448.8	468.0
20°	316.8	323.5	333.3	344.8	354.8	369.5	384.4	400.2	413.1	436.8	459.3
22.5°	302.5	307.7	315.6	327.0	337.9	351.3	367.6	384.9	398.4	424.0	446.7
25°	282.2	286.5	291.6	301.0	313.3	328.0	340.7	359.7	379.4	403.3	430.8
27.5°	264.0	267.1	271.6	279.8	289.4	303.1	317.2	335.2	355.1	381.0	410.1
30°	252.9	254.9	259.3	266.2	275.6	286.4	300.7	317.8	338.2	364.4	393.3
32.5°	243.2	245.0	248.0	254.4	262.6	271.8	284.6	301.9	321.2	347.0	379.1
35°	228.7	230.0	232.6	237.8	242.4	251.3	262.1	277.8	295.9	320.6	353.8
37.5°	214.1	216.0	217.6	219.8	225.6	231.5	240.8	254.1	271.9	296.8	328.5
40°	204.6	206.1	208.5	209.5	214.1	219.5	227.0	239.2	257.2	279.9	310.8
42.5°	194.8	196.5	197.9	199.0	203.0	207.7	214.6	225.0	240.9	262.9	293.6
45°	181.7	181.9	183.3	185.5	187.4	190.7	195.6	204.6	216.9	237.6	265.4
47.5°	168.3	168.6	168.8	169.7	171.9	174.9	178.1	185.5	196.5	213.0	240.0
50°	159.4	159.0	159.4	160.1	161.5	164.1	167.8	173.1	182.1	197.5	222.4
52.5°	150.8	150.8	150.5	150.8	151.9	153.6	156.3	160.7	168.8	183.0	204.8
55°	137.7	136.7	136.9	136.1	137.9	138.3	140.3	144.0	151.0	160.7	181.3
57.5°	123.7	123.0	122.1	121.8	121.7	122.7	124.2	127.2	132.6	141.2	157.8
60°	114.8	113.8	112.6	112.3	112.3	112.9	113.7	115.8	120.9	128.5	142.2
62.5°	105.7	104.6	103.9	102.9	102.5	103.1	103.9	105.5	109.2	116.3	128.1
65°	91.7	90.3	89.4	89.2	88.8	88.3	88.6	90.1	93.1	98.8	108.1
67.5°	77.7	76.4	76.2	75.0	74.5	74.6	74.5	75.8	77.6	82.5	89.5
70°	68.4	67.5	67.1	66.1	65.7	65.3	64.9	66.1	67.8	72.0	78.0
72.5°	59.1	58.2	57.4	56.6	56.7	56.2	56.1	56.9	58.3	62.1	66.8
75°	45.5	45.8	44.8	43.8	43.7	43.2	43.2	43.8	44.4	47.4	51.1
77.5°	33.1	32.9	32.1	31.8	31.6	31.2	31.6	31.9	32.3	34.3	36.9
80°	25.2	25.2	24.3	24.3	24.0	23.5	24.0	23.7	24.5	26.4	28.3
82.5°	18.0	17.7	17.7	17.4	17.3	16.9	17.1	17.6	17.9	19.2	20.4
85°	8.8	8.8	8.6	8.4	8.6	8.4	8.6	8.8	9.0	9.6	10.6
87.5°	6.3	6.5	6.0	5.6	4.9	4.5	4.1	4.0	4.0	3.8	3.5
90°	22.0	22.4	19.2	16.1	13.0	9.9	7.5	5.8	4.0	2.3	0.6
92.5°	20.4	20.3	19.5	18.9	18.1	17.4	16.4	15.2	13.9	12.7	11.4
95°	40.9	40.9	40.6	40.3	40.0	39.8	38.9	37.5	36.1	34.6	33.2
97.5°	68.7	68.7	68.2	67.7	67.2	66.6	65.7	64.4	63.2	61.9	60.7
100°	88.2	88.2	87.7	87.3	86.9	86.4	85.7	84.6	83.4	82.3	81.1
102.5°	109.3	109.1	108.6	108.1	107.5	106.9	106.2	105.3	104.4	103.5	102.6
105°	140.9	140.6	140.3	140.0	139.7	139.4	139.1	138.6	138.2	137.8	137.3
107.5°	175.3	175.2	175.2	175.2	175.2	175.2	174.9	174.3	173.7	173.0	172.4
110°	198.7	198.7	198.7	198.7	198.7	198.7	198.3	197.4	196.6	195.7	194.8



TEST NUMBER: P331472-935

CATALOG NUMBER: S122DIW-S290D710U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	222.4	222.7	222.8	222.9	223.1	223.2	222.8	222.0	221.1	220.2	219.4
115°	258.0	258.1	258.4	258.6	259.0	259.2	259.0	258.1	257.3	256.4	255.5
117.5°	292.8	293.2	293.9	294.7	295.5	296.3	296.1	295.0	293.9	292.7	291.6
120°	315.6	315.6	316.8	317.9	319.0	320.1	320.1	319.0	317.9	316.8	315.6
122.5°	339.8	340.2	341.0	341.7	342.5	343.4	343.0	341.6	340.4	339.0	337.6
125°	375.2	375.7	376.1	376.5	376.9	377.4	376.9	375.7	374.4	373.2	371.9
127.5°	409.7	410.2	410.7	411.2	411.7	412.2	411.6	410.0	408.5	406.8	405.2
130°	432.9	433.2	433.4	433.8	434.0	434.3	433.5	431.7	429.8	428.0	426.1
132.5°	456.1	456.7	456.7	456.6	456.5	456.5	455.6	454.2	452.7	451.2	449.7
135°	489.2	489.4	489.1	488.9	488.5	488.3	487.3	485.8	484.2	482.7	481.1
137.5°	521.5	521.6	521.2	520.9	520.5	520.1	519.3	518.1	516.8	515.5	514.2
140°	543.0	543.0	542.3	541.7	541.0	540.2	539.2	538.0	536.7	535.4	534.2
142.5°	562.6	562.5	562.0	561.5	561.0	560.6	559.6	558.4	557.2	555.9	554.6
145°	592.4	592.3	591.4	590.6	589.7	588.8	588.0	586.9	585.9	585.0	583.9
147.5°	618.4	618.1	617.5	616.9	616.4	615.8	614.9	613.7	612.5	611.3	610.2
150°	634.9	634.5	633.9	633.3	632.7	632.1	631.5	630.6	629.7	628.9	628.0
152.5°	651.3	650.8	650.1	649.5	648.8	648.1	647.3	646.4	645.6	644.7	643.9
155°	672.2	671.5	671.1	670.6	670.2	669.8	669.3	668.9	668.5	668.0	667.6
157.5°	691.4	690.4	690.2	689.9	689.7	689.4	689.1	688.8	688.5	688.3	687.9
160°	703.0	702.1	702.0	701.9	701.7	701.6	701.4	701.1	700.8	700.5	700.3
162.5°	713.3	712.4	712.2	712.1	712.0	711.8	711.7	711.6	711.6	711.5	711.4
165°	726.8	725.8	725.8	725.8	725.8	725.8	725.9	726.0	726.2	726.3	726.4
167.5°	737.9	736.9	736.9	736.9	737.0	737.0	737.3	737.7	738.1	738.6	739.0
170°	744.1	743.0	743.2	743.3	743.5	743.6	743.9	744.3	744.8	745.2	745.6
172.5°	748.6	747.6	747.8	748.0	748.0	748.2	748.5	748.9	749.3	749.8	750.2
175°	753.6	752.6	752.9	753.2	753.5	753.8	754.1	754.6	755.0	755.4	755.8
177.5°	756.2	755.5	755.8	756.0	756.2	756.5	756.7	757.1	757.4	757.8	758.1
180°	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1



TEST NUMBER: P331472-935

CATALOG NUMBER: S122DIW-S290D710U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	511.6	512.4	514.9	517.4	520.2	521.0	522.2	521.2	520.8	523.7	526.0
5°	513.1	516.5	523.4	529.7	534.9	538.6	542.6	544.2	547.1	551.1	556.3
7.5°	511.3	518.2	529.0	538.1	548.0	555.2	560.8	565.6	571.4	579.1	587.6
10°	509.5	518.7	531.8	542.9	555.1	564.3	571.9	579.4	588.0	598.7	609.8
12.5°	506.1	516.9	533.4	546.6	562.1	571.2	581.4	597.4	606.7	621.7	637.4
15°	499.1	511.3	534.2	550.4	568.0	585.2	604.2	619.4	634.6	643.5	665.6
17.5°	488.9	506.6	532.0	551.0	573.3	600.4	621.7	639.0	656.6	670.9	682.0
20°	480.5	499.9	528.9	551.6	578.2	607.3	631.7	649.4	664.6	676.6	683.4
22.5°	470.1	494.5	522.6	549.2	583.2	612.0	637.7	651.5	664.3	670.1	672.8
25°	453.6	482.9	514.8	547.3	585.6	616.1	639.6	648.0	651.7	646.0	636.6
27.5°	435.8	468.5	505.8	543.5	584.1	613.5	630.3	629.0	622.7	604.2	589.6
30°	422.5	458.5	498.5	539.8	580.5	609.1	618.8	609.1	594.8	574.3	553.3
32.5°	408.5	445.8	490.9	534.5	573.9	599.1	601.2	584.4	562.2	538.9	512.8
35°	387.4	427.7	476.5	522.6	560.0	575.8	566.5	536.7	510.5	478.6	443.0
37.5°	363.6	408.1	456.9	505.2	539.1	543.2	519.9	488.6	451.6	414.1	372.2
40°	345.8	393.0	443.2	491.9	521.9	517.5	487.8	453.4	409.4	363.6	324.7
42.5°	329.8	376.9	428.2	476.0	499.9	488.1	453.4	411.1	363.9	320.7	285.1
45°	302.2	350.7	403.1	449.3	463.0	441.6	395.7	348.7	302.2	266.2	238.1
47.5°	275.3	323.3	375.2	415.8	420.6	391.9	341.7	293.4	253.4	224.1	204.2
50°	255.6	303.8	355.2	391.4	389.8	355.2	303.6	257.6	224.1	200.4	187.2
52.5°	238.0	283.4	332.8	365.8	357.4	319.7	270.4	229.5	202.1	183.6	171.5
55°	210.4	252.5	299.5	325.9	310.6	268.7	227.0	194.2	173.8	160.0	150.6
57.5°	183.1	222.6	262.8	279.1	262.2	223.5	188.8	165.0	149.6	139.4	133.3
60°	166.3	200.7	236.4	250.6	230.4	196.0	168.6	147.3	134.9	126.6	121.1
62.5°	149.4	180.2	214.0	221.6	203.2	174.1	149.8	132.1	122.0	114.5	109.3
65°	126.3	151.6	177.2	182.3	165.3	142.8	123.6	112.1	103.1	97.6	93.5
67.5°	103.7	123.9	142.1	146.1	131.2	115.6	101.8	91.7	85.7	81.1	77.6
70°	90.1	106.2	121.1	124.4	112.4	98.6	88.0	80.0	74.5	70.6	67.2
72.5°	75.9	89.3	101.7	103.9	94.2	83.5	74.9	68.5	63.7	61.2	58.0
75°	58.1	66.0	75.5	76.1	69.7	63.2	56.6	52.4	49.9	46.8	45.2
77.5°	41.0	47.1	52.6	53.6	49.9	45.5	41.8	38.5	36.3	34.9	33.4
80°	31.3	36.2	38.6	39.9	37.2	34.0	31.9	29.7	28.3	27.4	26.4
82.5°	22.4	25.4	27.6	28.7	27.1	25.2	23.2	21.9	20.8	20.1	19.7
85°	11.4	12.7	14.1	14.5	14.1	13.3	12.1	12.1	11.5	11.4	11.4
87.5°	4.4	5.3	5.7	6.5	6.6	7.3	7.9	8.4	8.9	8.6	8.4
90°	2.3	4.0	5.8	7.5	9.9	13.0	16.1	19.2	22.4	22.0	21.8
92.5°	12.7	13.9	15.2	16.4	17.4	18.1	18.9	19.5	20.3	20.4	20.4
95°	34.6	36.1	37.5	38.9	39.8	40.0	40.3	40.6	40.9	40.9	40.9
97.5°	61.9	63.2	64.4	65.7	66.6	67.2	67.7	68.2	68.7	68.7	68.7
100°	82.3	83.4	84.6	85.7	86.4	86.9	87.3	87.7	88.2	88.2	88.2
102.5°	103.5	104.4	105.3	106.2	106.9	107.5	108.1	108.6	109.1	109.3	109.3
105°	137.8	138.2	138.6	139.1	139.4	139.7	140.0	140.3	140.6	140.9	141.1
107.5°	173.0	173.7	174.3	174.9	175.2	175.2	175.2	175.2	175.2	175.3	175.4
110°	195.7	196.6	197.4	198.3	198.7	198.7	198.7	198.7	198.7	198.7	198.7





TEST NUMBER: P331472-935

CATALOG NUMBER: S122DIW-S290D710U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	220.2	221.1	222.0	222.8	223.2	223.1	222.9	222.8	222.7	222.4	222.1
115°	256.4	257.3	258.1	259.0	259.2	259.0	258.6	258.4	258.1	258.0	257.9
117.5°	292.7	293.9	295.0	296.1	296.3	295.5	294.7	293.9	293.2	292.8	292.5
120°	316.8	317.9	319.0	320.1	320.1	319.0	317.9	316.8	315.6	315.6	315.6
122.5°	339.0	340.4	341.6	343.0	343.4	342.5	341.7	341.0	340.2	339.8	339.5
125°	373.2	374.4	375.7	376.9	377.4	376.9	376.5	376.1	375.7	375.2	374.8
127.5°	406.8	408.5	410.0	411.6	412.2	411.7	411.2	410.7	410.2	409.7	409.1
130°	428.0	429.8	431.7	433.5	434.3	434.0	433.8	433.4	433.2	432.9	432.7
132.5°	451.2	452.7	454.2	455.6	456.5	456.5	456.6	456.7	456.7	456.1	455.5
135°	482.7	484.2	485.8	487.3	488.3	488.5	488.9	489.1	489.4	489.2	489.1
137.5°	515.5	516.8	518.1	519.3	520.1	520.5	520.9	521.2	521.6	521.5	521.3
140°	535.4	536.7	538.0	539.2	540.2	541.0	541.7	542.3	543.0	543.0	543.0
142.5°	555.9	557.2	558.4	559.6	560.6	561.0	561.5	562.0	562.5	562.6	562.7
145°	585.0	585.9	586.9	588.0	588.8	589.7	590.6	591.4	592.3	592.4	592.5
147.5°	611.3	612.5	613.7	614.9	615.8	616.4	616.9	617.5	618.1	618.4	618.7
150°	628.9	629.7	630.6	631.5	632.1	632.7	633.3	633.9	634.5	634.9	635.2
152.5°	644.7	645.6	646.4	647.3	648.1	648.8	649.5	650.1	650.8	651.3	651.9
155°	668.0	668.5	668.9	669.3	669.8	670.2	670.6	671.1	671.5	672.2	672.9
157.5°	688.3	688.5	688.8	689.1	689.4	689.7	689.9	690.2	690.4	691.4	692.3
160°	700.5	700.8	701.1	701.4	701.6	701.7	701.9	702.0	702.1	703.0	703.9
162.5°	711.5	711.6	711.6	711.7	711.8	712.0	712.1	712.2	712.4	713.3	714.3
165°	726.3	726.2	726.0	725.9	725.8	725.8	725.8	725.8	725.8	726.8	727.8
167.5°	738.6	738.1	737.7	737.3	737.0	737.0	736.9	736.9	736.9	737.9	738.9
170°	745.2	744.8	744.3	743.9	743.6	743.5	743.3	743.2	743.0	744.1	745.0
172.5°	749.8	749.3	748.9	748.5	748.2	748.0	748.0	747.8	747.6	748.6	749.7
175°	755.4	755.0	754.6	754.1	753.8	753.5	753.2	752.9	752.6	753.6	754.6
177.5°	757.8	757.4	757.1	756.7	756.5	756.2	756.0	755.8	755.5	756.2	756.9
180°	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1



TEST NUMBER: P331472-935

CATALOG NUMBER: S122DIW-S290D710U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	527.9	530.0	530.0	530.4	532.9	532.5	532.4
5°	561.7	565.1	565.4	568.9	571.3	570.5	568.3
7.5°	593.7	599.9	604.6	607.2	610.3	612.2	611.3
10°	619.1	628.0	633.5	637.2	641.7	645.1	643.9
12.5°	642.0	652.7	660.3	666.7	667.2	671.5	668.6
15°	678.0	689.2	690.4	695.1	698.9	698.4	698.6
17.5°	689.7	693.4	694.1	694.2	694.3	692.9	689.9
20°	685.5	684.2	680.9	678.3	673.8	673.2	669.3
22.5°	665.5	661.2	652.8	647.3	640.3	638.5	637.4
25°	626.1	616.5	603.2	590.5	586.9	580.1	582.0
27.5°	572.0	557.1	542.6	532.4	523.0	512.7	515.7
30°	534.0	517.1	496.8	481.1	471.1	461.4	459.6
32.5°	488.6	463.9	441.3	427.5	412.2	406.0	399.2
35°	410.4	386.2	363.8	344.4	333.3	324.7	316.8
37.5°	340.0	312.3	294.1	278.4	270.4	265.4	266.7
40°	296.4	272.1	258.7	246.8	239.4	235.9	236.7
42.5°	261.0	242.8	231.9	223.7	218.4	216.5	216.0
45°	220.8	210.7	201.6	197.0	194.4	192.3	190.9
47.5°	193.5	185.1	180.0	177.3	175.0	172.9	172.8
50°	177.0	171.5	168.0	165.1	163.3	161.8	163.2
52.5°	164.5	159.5	155.9	153.3	152.7	151.3	151.2
55°	145.9	142.0	139.5	137.1	136.0	135.2	134.1
57.5°	129.0	125.3	123.0	121.5	119.2	118.5	118.1
60°	116.9	114.0	111.7	109.7	108.7	107.2	107.2
62.5°	105.8	102.9	100.7	99.3	97.6	97.0	97.2
65°	89.8	87.4	85.2	83.7	83.3	82.1	82.6
67.5°	75.0	73.4	71.1	70.3	69.6	69.0	68.4
70°	65.1	63.5	62.4	61.2	60.6	60.6	60.6
72.5°	56.8	54.9	54.2	52.8	53.1	52.5	51.8
75°	44.0	42.8	42.3	41.7	40.7	40.7	40.7
77.5°	32.4	32.0	31.3	30.7	30.5	30.3	30.4
80°	25.1	24.8	24.5	24.5	24.0	23.8	23.5
82.5°	19.3	18.8	18.5	18.3	18.3	18.3	18.2
85°	10.9	10.6	10.6	10.8	10.3	10.3	10.6
87.5°	8.5	8.4	8.3	8.4	8.5	8.4	8.4
90°	21.5	21.3	21.2	21.3	21.4	21.6	21.7
92.5°	20.5	20.6	20.6	20.6	20.7	20.7	20.7
95°	40.9	40.9	40.7	40.5	40.2	39.9	39.6
97.5°	68.7	68.7	68.7	68.7	68.7	68.6	68.6
100°	88.2	88.2	88.1	88.0	87.8	87.6	87.6
102.5°	109.4	109.6	109.6	109.4	109.3	109.2	109.0
105°	141.4	141.7	141.8	141.8	141.8	141.8	141.8
107.5°	175.6	175.6	175.4	174.7	174.1	173.4	172.8
110°	198.7	198.7	198.5	198.0	197.6	197.2	196.8



TEST NUMBER: P331472-935

CATALOG NUMBER: S122DIW-S290D710U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	221.7	221.4	221.0	220.8	220.4	220.1	219.8
115°	257.7	257.5	257.3	256.8	256.4	256.0	255.5
117.5°	292.1	291.8	291.4	290.9	290.5	290.1	289.6
120°	315.6	315.6	315.4	315.0	314.5	314.1	313.7
122.5°	339.1	338.8	338.5	338.1	337.9	337.5	337.3
125°	374.4	373.9	373.7	373.6	373.4	373.2	373.2
127.5°	408.6	408.1	407.7	407.2	406.7	406.3	405.9
130°	432.3	432.0	431.6	431.0	430.5	429.9	429.4
132.5°	454.8	454.2	453.7	453.2	452.7	452.3	451.9
135°	489.0	488.9	488.5	488.1	487.7	487.2	486.8
137.5°	521.2	521.2	520.8	520.2	519.7	519.1	518.5
140°	543.0	543.0	542.8	542.3	541.7	541.1	540.5
142.5°	562.8	562.9	562.7	562.1	561.5	561.0	560.4
145°	592.7	592.8	592.6	592.0	591.5	590.9	590.4
147.5°	619.0	619.3	619.2	618.7	618.1	617.6	617.1
150°	635.7	636.1	636.1	635.7	635.2	634.9	634.5
152.5°	652.4	653.0	653.0	652.4	651.9	651.3	650.8
155°	673.6	674.3	674.5	674.1	673.6	673.2	672.8
157.5°	693.3	694.2	694.4	693.7	693.0	692.3	691.6
160°	704.7	705.6	705.7	705.2	704.6	704.0	703.4
162.5°	715.3	716.3	716.4	715.7	715.1	714.4	713.7
165°	728.8	729.8	730.0	729.2	728.5	727.8	727.1
167.5°	739.9	740.9	741.0	740.3	739.5	738.8	738.0
170°	746.1	747.0	747.1	746.2	745.4	744.5	743.6
172.5°	750.6	751.7	751.7	750.9	750.0	749.2	748.3
175°	755.6	756.6	756.6	755.8	755.0	754.1	753.3
177.5°	757.6	758.3	758.3	757.6	756.9	756.2	755.5
180°	757.1	757.1	757.1	757.1	757.1	757.1	757.1

(END OF REPORT)