

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331578-935

Luminaire Tested: **S122DIW-S865D1240U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331578-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S865D1240U935-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1240 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6727.4 lumens
Efficiency: N/A
Efficacy: 96.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 69.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331578-935

CATALOG NUMBER: S122DIW-S865D1240U935-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331578-935

CATALOG NUMBER: S122DIW-S865D1240U935-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	106	106	106	106	97	97	97	97	81	81	81	65	65	65	52	52	52	45			45
1	97	92	88	85	88	85	81	78	71	68	66	58	56	54	46	44	43	38			38
2	88	81	75	69	80	74	69	64	62	58	55	51	48	45	40	38	37	32			32
3	80	71	64	58	73	65	59	54	55	50	46	45	41	38	35	33	31	27			27
4	73	63	55	49	67	58	51	46	48	43	39	40	36	33	32	29	27	23			23
5	67	56	48	42	61	51	44	39	43	38	34	36	32	29	29	26	23	20			20
6	62	50	42	36	57	46	39	34	39	33	29	32	28	25	26	23	21	18			18
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	24	21	18	16			16
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	16	14			14
9	49	37	30	25	45	35	28	23	30	24	21	25	21	18	20	17	15	13			13
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	19	16	13	11			11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	19184	19184	19184
5°	19258	18979	19091
10°	19143	18787	18882
15°	18907	18544	18524
20°	18570	18179	18158
25°	18235	17728	17728
30°	17807	17316	17167
35°	17406	16821	16575
40°	16904	16326	16012
45°	16408	15835	15445
50°	15870	15325	14780
55°	15308	14728	14184
60°	14683	14018	13504
65°	14013	13310	12699
70°	13161	12458	11863
75°	11971	11472	11185
80°	10628	10302	9772
85°	8670	8262	7410



TEST NUMBER: P331578-935

CATALOG NUMBER: S122DIW-S865D1240U935-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	111.7	1.7
10°-20°	314.4	4.7
20°-30°	462.1	6.9
30°-40°	536.8	8.0
40°-50°	536.2	8.0
50°-60°	467.6	7.0
60°-70°	345.7	5.1
70°-80°	195.8	2.9
80°-90°	57.9	0.9
90°-100°	83.8	1.2
100°-110°	260.4	3.9
110°-120°	445.0	6.6
120°-130°	585.3	8.7
130°-140°	656.9	9.8
140°-150°	644.1	9.6
150°-160°	540.2	8.0
160°-170°	358.3	5.3
170°-180°	125.2	1.9
0°-30°	888.2	13.2
0°-40°	1425.0	21.2
0°-60°	2428.7	36.1
0°-90°	3028.2	45.0
90°-120°	789.2	11.7
90°-150°	2675.4	39.8
90°-180°	3699.0	55.0
0°-180°	6727.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1188	1188	1188	1188	1188	
5°	1188	1183	1171	1180	1178	113
15°	1131	1124	1109	1113	1108	318
25°	1024	1014	995	997	995	471
35°	883	871	853	847	841	551
45°	719	710	694	681	676	554
55°	544	537	523	510	504	486
65°	367	360	348	338	332	363
75°	192	189	184	178	179	205
85°	47	46	45	41	40	54
90°	1	15	39	37	38	5
95°	58	69	72	71	69	67
105°	240	243	246	248	248	253
115°	447	453	451	450	447	442
125°	650	659	656	653	652	580
135°	841	852	855	854	851	649
145°	1020	1028	1035	1036	1032	637
155°	1167	1170	1173	1178	1176	537
165°	1269	1268	1268	1275	1270	358
175°	1321	1318	1315	1322	1316	125
180°	1323	1323	1323	1323	1323	



TEST NUMBER: P331578-935

CATALOG NUMBER: S122DIW-S865D1240U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1188.2	1188.2	1188.2	1188.2	1188.2	1188.2	1188.2	1188.2	1188.2	1188.2	1188.2
2.5°	1193.7	1192.7	1191.6	1190.7	1189.6	1188.0	1185.8	1183.5	1181.3	1179.1	1181.1
5°	1188.2	1187.1	1186.2	1185.2	1184.1	1182.2	1179.5	1176.6	1173.9	1171.0	1173.1
7.5°	1177.7	1176.1	1174.6	1172.9	1171.4	1169.2	1166.3	1163.5	1160.6	1157.8	1159.9
10°	1167.6	1165.9	1164.1	1162.3	1160.5	1158.1	1155.0	1152.0	1149.0	1145.9	1148.0
12.5°	1153.9	1152.4	1150.8	1149.2	1147.6	1145.3	1142.3	1139.2	1136.2	1133.2	1134.5
15°	1131.1	1129.5	1128.0	1126.5	1125.0	1122.6	1119.3	1115.9	1112.7	1109.4	1110.3
17.5°	1101.8	1100.3	1098.8	1097.3	1095.7	1093.3	1089.9	1086.6	1083.2	1079.9	1081.1
20°	1080.8	1079.3	1077.8	1076.2	1074.7	1072.2	1068.6	1065.1	1061.5	1058.0	1058.7
22.5°	1059.8	1057.7	1055.5	1053.3	1051.3	1048.5	1045.2	1041.8	1038.5	1035.1	1035.3
25°	1023.6	1021.7	1019.6	1017.6	1015.5	1012.4	1008.1	1003.8	999.4	995.1	995.7
27.5°	982.6	980.8	978.9	977.1	975.3	972.6	969.2	965.8	962.4	959.0	958.3
30°	955.1	953.1	951.1	949.1	947.0	944.1	940.3	936.5	932.6	928.8	928.1
32.5°	925.9	924.3	922.6	921.0	919.4	916.5	912.6	908.5	904.6	900.5	899.1
35°	883.1	880.6	878.0	875.6	873.0	869.7	865.6	861.6	857.5	853.4	852.0
37.5°	834.9	832.7	830.4	828.2	826.0	822.9	818.8	814.8	810.6	806.6	804.7
40°	802.0	800.0	798.0	795.9	793.9	790.8	786.8	782.7	778.7	774.6	772.3
42.5°	770.1	768.0	765.9	764.0	761.9	758.9	754.8	750.8	746.7	742.6	740.1
45°	718.6	716.9	715.1	713.3	711.5	708.7	704.9	701.1	697.3	693.5	690.7
47.5°	667.4	665.8	664.1	662.5	660.7	657.9	653.9	650.0	646.0	642.0	639.1
50°	631.8	630.5	629.3	628.0	626.7	624.3	620.8	617.2	613.6	610.1	606.6
52.5°	597.1	595.4	593.7	592.0	590.4	587.9	584.5	581.2	577.8	574.5	571.5
55°	543.8	542.3	540.8	539.2	537.7	535.5	532.4	529.3	526.3	523.2	520.2
57.5°	490.3	489.1	487.9	486.7	485.5	483.2	479.8	476.5	473.1	469.8	466.8
60°	454.7	453.7	452.7	451.7	450.6	448.4	444.8	441.3	437.7	434.1	431.4
62.5°	420.0	418.4	416.7	415.1	413.5	411.3	408.5	405.8	403.0	400.4	397.8
65°	366.8	365.2	363.7	362.1	360.7	358.6	356.1	353.5	351.0	348.4	346.2
67.5°	312.6	311.3	310.1	308.9	307.7	306.0	303.7	301.4	299.1	296.8	295.1
70°	278.8	277.8	276.7	275.7	274.7	273.0	270.8	268.5	266.2	263.9	262.2
72.5°	244.0	243.1	242.0	241.0	240.0	238.8	237.3	235.8	234.3	232.8	231.1
75°	191.9	191.4	190.9	190.5	189.9	189.0	187.8	186.5	185.2	183.9	182.4
77.5°	145.3	144.5	143.6	142.8	141.9	141.2	140.7	140.2	139.7	139.1	138.4
80°	114.3	114.0	113.7	113.5	113.2	112.9	112.4	111.8	111.3	110.8	110.0
82.5°	85.0	85.0	84.9	84.8	84.8	84.6	84.3	84.0	83.7	83.4	82.4
85°	46.8	46.6	46.3	46.1	45.8	45.5	45.3	45.0	44.8	44.6	43.8
87.5°	16.7	16.9	17.0	17.2	17.4	17.9	18.6	19.2	19.9	20.6	19.9
90°	1.1	4.1	7.1	10.1	13.0	17.2	22.7	28.2	33.6	39.1	38.6
92.5°	19.9	22.0	24.3	26.4	28.6	30.3	31.6	32.9	34.2	35.5	35.6
95°	58.0	60.5	63.0	65.5	68.0	69.5	70.0	70.4	70.9	71.5	71.5
97.5°	106.1	108.2	110.5	112.6	114.8	116.3	117.3	118.2	119.2	120.1	120.1
100°	141.8	143.8	145.8	147.7	149.7	151.1	151.8	152.6	153.3	154.0	154.0
102.5°	179.3	180.9	182.4	184.1	185.6	186.9	187.9	188.8	189.8	190.7	190.9
105°	240.0	240.7	241.5	242.3	243.0	243.7	244.1	244.6	245.1	245.6	246.1
107.5°	301.2	302.3	303.4	304.4	305.6	306.1	306.1	306.1	306.1	306.1	306.3
110°	340.5	342.0	343.5	345.0	346.5	347.2	347.2	347.2	347.2	347.2	347.2



TEST NUMBER: P331578-935

CATALOG NUMBER: S122DIW-S865D1240U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	383.4	384.9	386.3	387.9	389.3	389.9	389.8	389.6	389.3	389.2	388.6
115°	446.6	448.1	449.5	451.0	452.5	453.0	452.5	452.0	451.5	451.0	450.8
117.5°	509.5	511.5	513.5	515.5	517.5	517.8	516.3	515.0	513.6	512.2	511.6
120°	551.5	553.5	555.5	557.5	559.5	559.5	557.5	555.5	553.5	551.5	551.5
122.5°	589.9	592.3	594.7	597.0	599.4	599.9	598.6	597.2	595.7	594.3	593.7
125°	649.7	651.9	654.2	656.4	658.7	659.4	658.7	658.0	657.2	656.4	655.7
127.5°	708.0	710.8	713.7	716.5	719.4	720.3	719.5	718.5	717.6	716.7	715.8
130°	744.7	747.9	751.1	754.3	757.5	758.9	758.5	757.9	757.4	756.9	756.4
132.5°	785.7	788.3	791.0	793.6	796.3	797.6	797.7	797.8	797.9	798.0	796.9
135°	840.7	843.3	846.1	848.9	851.6	853.2	853.7	854.2	854.7	855.1	854.9
137.5°	898.5	900.7	902.9	905.2	907.4	908.9	909.5	910.2	910.8	911.5	911.3
140°	933.3	935.6	937.8	940.0	942.3	944.0	945.2	946.5	947.7	948.9	948.9
142.5°	969.1	971.3	973.5	975.8	978.0	979.5	980.3	981.2	982.1	982.9	983.1
145°	1020.4	1022.2	1023.9	1025.6	1027.3	1029.0	1030.4	1031.9	1033.5	1034.9	1035.2
147.5°	1066.2	1068.2	1070.3	1072.5	1074.5	1076.1	1077.0	1078.1	1079.0	1080.0	1080.6
150°	1097.4	1098.9	1100.4	1101.9	1103.4	1104.7	1105.6	1106.6	1107.6	1108.6	1109.3
152.5°	1125.2	1126.6	1128.1	1129.5	1131.1	1132.4	1133.6	1134.8	1136.0	1137.2	1138.2
155°	1166.7	1167.4	1168.1	1168.9	1169.7	1170.4	1171.1	1171.8	1172.6	1173.4	1174.6
157.5°	1202.1	1202.6	1203.2	1203.7	1204.1	1204.6	1205.1	1205.5	1205.9	1206.4	1208.1
160°	1223.6	1224.1	1224.6	1225.1	1225.5	1226.0	1226.2	1226.4	1226.7	1226.9	1228.4
162.5°	1243.2	1243.4	1243.5	1243.5	1243.6	1243.8	1244.1	1244.3	1244.6	1244.8	1246.5
165°	1269.4	1269.1	1268.9	1268.6	1268.3	1268.3	1268.3	1268.3	1268.3	1268.3	1270.0
167.5°	1291.2	1290.5	1289.8	1289.0	1288.2	1287.9	1287.8	1287.8	1287.7	1287.6	1289.4
170°	1302.9	1302.1	1301.4	1300.6	1299.9	1299.4	1299.2	1298.9	1298.6	1298.4	1300.1
172.5°	1310.9	1310.2	1309.4	1308.6	1307.9	1307.4	1307.2	1306.9	1306.7	1306.4	1308.2
175°	1320.7	1320.0	1319.2	1318.4	1317.8	1317.2	1316.6	1316.1	1315.6	1315.1	1316.9
177.5°	1324.7	1324.1	1323.5	1322.9	1322.3	1321.9	1321.5	1321.0	1320.7	1320.3	1321.5
180°	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9



TEST NUMBER: P331578-935

CATALOG NUMBER: S122DIW-S865D1240U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1188.2	1188.2	1188.2	1188.2	1188.2	1188.2	1188.2	1188.2
2.5°	1183.1	1185.2	1187.1	1188.0	1187.6	1187.1	1186.8	1186.4
5°	1175.1	1177.2	1179.2	1179.9	1179.5	1179.0	1178.5	1177.9
7.5°	1161.8	1163.9	1166.0	1166.7	1166.1	1165.5	1165.0	1164.4
10°	1150.0	1152.0	1154.1	1154.7	1153.9	1153.1	1152.4	1151.7
12.5°	1136.0	1137.4	1138.8	1139.3	1138.7	1138.2	1137.6	1137.0
15°	1111.4	1112.4	1113.4	1113.3	1112.1	1110.8	1109.5	1108.2
17.5°	1082.2	1083.4	1084.6	1084.5	1083.3	1082.1	1080.9	1079.7
20°	1059.5	1060.2	1061.0	1060.8	1059.9	1058.9	1057.8	1056.8
22.5°	1035.4	1035.5	1035.7	1035.5	1034.8	1034.2	1033.6	1033.0
25°	996.2	996.6	997.1	997.1	996.6	996.2	995.7	995.1
27.5°	957.5	956.7	956.0	955.0	953.7	952.5	951.3	950.1
30°	927.3	926.6	925.8	924.9	923.9	922.9	921.9	920.8
32.5°	897.8	896.4	895.0	893.8	892.9	891.8	890.8	889.8
35°	850.4	848.9	847.4	845.9	844.7	843.4	842.1	840.9
37.5°	802.9	801.0	799.1	797.5	796.3	795.1	793.9	792.6
40°	770.1	767.8	765.5	763.8	762.8	761.8	760.8	759.7
42.5°	737.6	735.1	732.7	730.7	729.3	727.9	726.4	725.0
45°	687.9	685.1	682.3	680.4	679.4	678.4	677.3	676.4
47.5°	636.2	633.3	630.3	628.1	626.6	625.2	623.7	622.2
50°	603.0	599.4	595.9	593.5	592.2	590.9	589.7	588.4
52.5°	568.5	565.6	562.7	560.3	558.7	557.0	555.3	553.6
55°	517.2	514.1	511.1	508.9	507.6	506.4	505.1	503.9
57.5°	463.8	460.8	457.8	455.8	454.9	453.9	453.0	451.9
60°	428.6	425.8	423.0	421.2	420.4	419.7	418.9	418.2
62.5°	395.1	392.5	389.9	388.2	387.2	386.2	385.3	384.4
65°	343.9	341.6	339.3	337.5	336.3	335.0	333.7	332.4
67.5°	293.3	291.4	289.7	288.3	287.3	286.3	285.2	284.2
70°	260.4	258.6	256.8	255.4	254.4	253.4	252.4	251.3
72.5°	229.3	227.5	225.8	224.5	223.6	222.8	222.0	221.2
75°	180.9	179.3	177.9	177.4	177.9	178.4	178.8	179.3
77.5°	137.7	136.9	136.1	135.3	134.7	134.0	133.3	132.5
80°	109.3	108.6	107.8	107.1	106.6	106.2	105.6	105.1
82.5°	81.5	80.5	79.6	79.0	78.9	78.8	78.7	78.6
85°	43.0	42.3	41.5	41.0	40.7	40.5	40.2	40.0
87.5°	19.2	18.5	17.7	17.3	17.2	17.0	16.9	16.7
90°	38.1	37.6	37.1	36.9	37.2	37.5	37.7	38.0
92.5°	35.7	35.8	35.9	36.0	36.0	36.1	36.2	36.2
95°	71.5	71.5	71.5	71.2	70.7	70.2	69.7	69.2
97.5°	120.1	120.1	120.1	120.1	120.0	120.0	119.9	119.9
100°	154.0	154.0	154.0	153.9	153.7	153.4	153.2	152.9
102.5°	191.1	191.3	191.5	191.5	191.2	191.0	190.7	190.5
105°	246.6	247.1	247.6	247.9	247.9	247.9	247.9	247.9
107.5°	306.5	306.7	306.9	306.4	305.3	304.2	303.0	301.9
110°	347.2	347.2	347.2	346.8	346.1	345.3	344.6	343.9



TEST NUMBER: P331578-935

CATALOG NUMBER: S122DIW-S865D1240U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	388.0	387.4	386.8	386.2	385.6	385.1	384.6	384.0
115°	450.6	450.3	450.0	449.5	448.8	448.1	447.3	446.6
117.5°	511.0	510.4	509.8	509.2	508.4	507.6	507.0	506.2
120°	551.5	551.5	551.5	551.1	550.4	549.7	548.9	548.2
122.5°	593.2	592.6	592.0	591.4	590.9	590.3	589.8	589.3
125°	655.0	654.2	653.5	653.0	652.7	652.5	652.2	651.9
127.5°	715.0	714.0	713.2	712.3	711.5	710.8	710.0	709.1
130°	756.0	755.4	754.9	754.2	753.2	752.3	751.2	750.2
132.5°	795.8	794.7	793.7	792.7	791.9	791.1	790.3	789.5
135°	854.7	854.5	854.2	853.7	852.9	852.2	851.4	850.7
137.5°	911.0	910.9	910.7	910.1	909.0	908.1	907.1	906.1
140°	948.9	948.9	948.9	948.5	947.4	946.5	945.5	944.5
142.5°	983.3	983.5	983.7	983.3	982.3	981.3	980.3	979.3
145°	1035.4	1035.7	1035.9	1035.5	1034.6	1033.5	1032.6	1031.6
147.5°	1081.1	1081.7	1082.2	1082.0	1081.1	1080.1	1079.2	1078.2
150°	1110.1	1110.9	1111.6	1111.6	1110.9	1110.1	1109.3	1108.6
152.5°	1139.1	1140.0	1140.9	1140.9	1140.0	1139.1	1138.2	1137.2
155°	1175.9	1177.1	1178.3	1178.5	1177.8	1177.1	1176.3	1175.6
157.5°	1209.8	1211.4	1213.1	1213.4	1212.2	1211.0	1209.8	1208.6
160°	1229.9	1231.4	1232.9	1233.1	1232.2	1231.1	1230.2	1229.2
162.5°	1248.2	1249.8	1251.5	1251.8	1250.6	1249.4	1248.2	1247.1
165°	1271.7	1273.4	1275.2	1275.4	1274.2	1273.0	1271.7	1270.5
167.5°	1291.2	1292.9	1294.6	1294.9	1293.6	1292.3	1291.0	1289.7
170°	1301.8	1303.6	1305.4	1305.4	1304.0	1302.5	1301.0	1299.5
172.5°	1309.9	1311.6	1313.4	1313.5	1312.0	1310.5	1309.1	1307.5
175°	1318.6	1320.3	1322.1	1322.2	1320.7	1319.2	1317.8	1316.2
177.5°	1322.7	1323.9	1325.0	1325.0	1323.9	1322.7	1321.5	1320.3
180°	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9

(END OF REPORT)