

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331770-935

Luminaire Tested: **S122RDIW-S290D710U935-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331770-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIW-S290D710U935-4F0-1E-UDD-A1  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 710 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3092.8 lumens  
Efficiency: N/A  
Efficacy: 101.7 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 30.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331770-935

CATALOG NUMBER: S122RDIW-S290D710U935-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P331770-935

CATALOG NUMBER: S122RDIW-S290D710U935-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39	32
1	94	90	86	83	85	81	78	75	65	63	61	49	48	47	35	35	34	27
2	86	79	74	69	77	72	67	63	57	54	51	44	42	40	32	30	29	24
3	79	70	63	58	71	63	58	53	51	47	44	39	37	34	29	27	26	21
4	72	62	55	49	65	56	50	45	46	41	37	35	32	30	26	24	23	18
5	67	56	48	42	60	51	44	39	41	36	33	32	29	26	24	22	20	16
6	61	50	42	37	55	46	39	34	37	32	29	29	26	23	22	20	18	15
7	57	45	38	33	51	41	35	30	34	29	25	27	23	21	20	18	16	13
8	53	41	34	29	48	38	31	27	31	26	23	24	21	19	18	16	15	12
9	49	38	31	26	44	34	28	24	28	24	20	23	19	17	17	15	13	11
10	46	35	28	23	41	32	26	22	26	22	18	21	18	15	16	14	12	10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	9087	9087	9087	9087
5°	10149	9144	8109	9144
10°	11262	9081	7029	9081
15°	11814	8948	5538	8948
20°	10244	8751	4792	8751
25°	6716	8480	4277	8480
30°	4521	8153	3872	8153
35°	3662	7740	3493	7740
40°	3256	7290	3231	7290
45°	2948	6766	2884	6766
50°	2683	6244	2673	6244
55°	2519	5664	2488	5664
60°	2109	5134	2086	5134
65°	1780	4661	2017	4661
70°	1643	4164	1902	4164
75°	1535	3624	1759	3624
80°	1413	2985	1562	2985
85°	1315	2353	1371	2353



TEST NUMBER: P331770-935

CATALOG NUMBER: S122RDIW-S290D710U935-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	53.4	1.7
10°-20°	148.7	4.8
20°-30°	191.6	6.2
30°-40°	182.1	5.9
40°-50°	156.0	5.0
50°-60°	118.8	3.8
60°-70°	75.1	2.4
70°-80°	37.5	1.2
80°-90°	12.8	0.4
90°-100°	48.0	1.6
100°-110°	149.0	4.8
110°-120°	254.7	8.2
120°-130°	334.9	10.8
130°-140°	375.9	12.2
140°-150°	368.6	11.9
150°-160°	309.2	10.0
160°-170°	205.1	6.6
170°-180°	71.7	2.3
0°-30°	393.6	12.7
0°-40°	575.7	18.6
0°-60°	850.4	27.5
0°-90°	975.8	31.6
90°-120°	451.7	14.6
90°-150°	1531.1	49.5
90°-180°	2117.0	68.4
0°-180°	3092.8	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	563	563	563	563	563	
5°	626	564	500	564	626	62
15°	707	535	331	535	707	191
25°	377	476	240	476	377	179
35°	186	393	177	393	186	119
45°	129	296	126	296	129	100
55°	90	201	88	201	90	79
65°	47	122	53	122	47	47
75°	25	58	28	58	25	26
85°	7	13	7	13	7	8
90°	22	1	22	1	22	10
95°	40	33	40	33	40	44
105°	142	137	142	137	142	149
115°	256	256	256	256	256	252
125°	373	372	373	372	373	333
135°	487	481	487	481	487	375
145°	590	584	590	584	590	369
155°	673	668	673	668	673	310
165°	727	726	727	726	727	205
175°	753	756	753	756	753	72
180°	757	757	757	757	757	



TEST NUMBER: P331770-935

CATALOG NUMBER: S122RDIW-S290D710U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8
2.5°	585.7	586.2	586.7	585.6	585.6	584.6	582.6	581.0	576.6	576.0	576.0
5°	626.2	625.9	626.6	624.1	620.6	619.7	616.0	611.1	606.1	600.5	599.3
7.5°	666.5	665.9	664.3	663.9	661.2	655.3	649.4	643.0	634.6	626.3	622.2
10°	686.9	693.4	689.4	682.6	683.9	674.8	669.9	661.4	654.4	642.0	639.4
12.5°	706.9	709.5	708.2	704.3	702.6	696.2	689.6	682.3	669.3	658.2	648.6
15°	706.8	710.5	711.5	710.3	711.3	710.9	707.4	701.4	690.0	677.9	667.3
17.5°	654.6	657.2	663.7	668.0	673.5	685.0	690.8	692.9	691.3	684.3	676.9
20°	596.2	591.9	609.8	619.0	626.8	646.4	663.2	669.7	680.0	679.8	677.9
22.5°	513.2	514.2	531.2	542.2	565.0	584.6	603.7	628.0	648.1	661.3	669.1
25°	377.0	384.5	401.5	416.4	441.8	478.2	511.3	549.6	585.7	614.3	641.5
27.5°	283.2	283.8	297.2	311.0	326.1	355.9	397.5	443.2	494.8	537.4	586.3
30°	242.5	241.3	247.0	255.5	268.4	291.4	322.7	367.6	419.1	483.3	540.4
32.5°	213.7	213.8	218.1	224.3	235.0	250.6	272.0	308.6	357.1	420.3	487.2
35°	185.8	185.6	188.7	193.2	197.7	207.7	222.4	241.5	275.0	333.8	402.3
37.5°	165.7	166.6	168.2	171.0	175.9	181.5	190.3	203.2	227.0	261.8	319.3
40°	154.5	154.9	157.0	159.4	162.3	166.6	173.8	184.3	201.6	229.4	271.5
42.5°	144.2	144.6	146.1	148.3	150.6	154.9	160.9	169.9	184.0	205.6	240.3
45°	129.1	129.1	130.4	131.4	134.0	137.8	142.8	150.2	160.0	176.0	199.1
47.5°	114.9	114.9	115.9	117.5	119.2	122.2	127.0	133.1	140.2	152.6	172.3
50°	106.8	107.0	107.5	108.9	109.9	112.6	116.4	121.7	129.1	138.7	155.1
52.5°	100.2	100.1	100.8	101.4	102.1	104.0	106.9	111.5	118.1	126.5	140.1
55°	89.5	88.8	90.0	90.9	91.5	92.3	93.8	96.8	102.5	109.5	119.7
57.5°	76.3	75.9	76.8	77.7	79.6	81.6	83.0	84.8	87.7	92.8	102.9
60°	65.3	65.3	67.1	67.7	69.8	72.6	75.3	76.9	79.8	83.1	90.6
62.5°	55.6	55.8	56.6	57.2	58.4	61.7	65.6	69.1	71.8	75.0	79.9
65°	46.6	46.9	46.9	47.4	48.1	48.9	50.5	53.2	58.1	62.6	66.3
67.5°	39.5	39.6	39.8	40.1	40.3	41.2	41.8	43.0	44.2	48.4	53.0
70°	34.8	35.4	35.2	35.6	35.8	36.2	36.9	37.5	39.3	40.3	43.0
72.5°	30.4	30.8	30.8	31.1	31.6	31.7	32.3	32.9	34.0	34.8	36.3
75°	24.6	24.5	24.6	25.1	25.2	25.4	25.4	26.2	26.8	27.6	28.6
77.5°	19.0	19.2	19.2	19.2	19.3	19.6	19.5	19.9	20.5	20.9	21.4
80°	15.2	15.4	15.2	15.4	15.7	15.8	15.7	15.8	16.4	16.8	16.8
82.5°	11.8	11.9	12.0	12.0	12.1	12.1	12.4	12.4	12.8	12.7	12.9
85°	7.1	6.9	6.9	6.9	7.1	7.2	7.1	7.1	7.2	7.2	7.2
87.5°	6.9	7.0	7.0	6.9	6.9	6.9	7.0	7.1	7.1	7.3	6.5
90°	21.7	21.6	21.4	21.3	21.2	21.3	21.5	21.8	22.0	22.4	19.2
92.5°	20.7	20.7	20.7	20.6	20.6	20.6	20.5	20.4	20.4	20.3	19.5
95°	39.6	39.9	40.2	40.5	40.7	40.9	40.9	40.9	40.9	40.9	40.6
97.5°	68.6	68.6	68.7	68.7	68.7	68.7	68.7	68.7	68.7	68.7	68.2
100°	87.6	87.6	87.8	88.0	88.1	88.2	88.2	88.2	88.2	88.2	87.7
102.5°	109.0	109.2	109.3	109.4	109.6	109.6	109.4	109.3	109.3	109.1	108.6
105°	141.8	141.8	141.8	141.8	141.8	141.7	141.4	141.1	140.9	140.6	140.3
107.5°	172.8	173.4	174.1	174.7	175.4	175.6	175.6	175.4	175.3	175.2	175.2
110°	196.8	197.2	197.6	198.0	198.5	198.7	198.7	198.7	198.7	198.7	198.7



TEST NUMBER: P331770-935

CATALOG NUMBER: S122RDIW-S290D710U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	219.8	220.1	220.4	220.8	221.0	221.4	221.7	222.1	222.4	222.7	222.8
115°	255.5	256.0	256.4	256.8	257.3	257.5	257.7	257.9	258.0	258.1	258.4
117.5°	289.6	290.1	290.5	290.9	291.4	291.8	292.1	292.5	292.8	293.2	293.9
120°	313.7	314.1	314.5	315.0	315.4	315.6	315.6	315.6	315.6	315.6	316.8
122.5°	337.3	337.5	337.9	338.1	338.5	338.8	339.1	339.5	339.8	340.2	341.0
125°	373.2	373.2	373.4	373.6	373.7	373.9	374.4	374.8	375.2	375.7	376.1
127.5°	405.9	406.3	406.7	407.2	407.7	408.1	408.6	409.1	409.7	410.2	410.7
130°	429.4	429.9	430.5	431.0	431.6	432.0	432.3	432.7	432.9	433.2	433.4
132.5°	451.9	452.3	452.7	453.2	453.7	454.2	454.8	455.5	456.1	456.7	456.7
135°	486.8	487.2	487.7	488.1	488.5	488.9	489.0	489.1	489.2	489.4	489.1
137.5°	518.5	519.1	519.7	520.2	520.8	521.2	521.2	521.3	521.5	521.6	521.2
140°	540.5	541.1	541.7	542.3	542.8	543.0	543.0	543.0	543.0	543.0	542.3
142.5°	560.4	561.0	561.5	562.1	562.7	562.9	562.8	562.7	562.6	562.5	562.0
145°	590.4	590.9	591.5	592.0	592.6	592.8	592.7	592.5	592.4	592.3	591.4
147.5°	617.1	617.6	618.1	618.7	619.2	619.3	619.0	618.7	618.4	618.1	617.5
150°	634.5	634.9	635.2	635.7	636.1	636.1	635.7	635.2	634.9	634.5	633.9
152.5°	650.8	651.3	651.9	652.4	653.0	653.0	652.4	651.9	651.3	650.8	650.1
155°	672.8	673.2	673.6	674.1	674.5	674.3	673.6	672.9	672.2	671.5	671.1
157.5°	691.6	692.3	693.0	693.7	694.4	694.2	693.3	692.3	691.4	690.4	690.2
160°	703.4	704.0	704.6	705.2	705.7	705.6	704.7	703.9	703.0	702.1	702.0
162.5°	713.7	714.4	715.1	715.7	716.4	716.3	715.3	714.3	713.3	712.4	712.2
165°	727.1	727.8	728.5	729.2	730.0	729.8	728.8	727.8	726.8	725.8	725.8
167.5°	738.0	738.8	739.5	740.3	741.0	740.9	739.9	738.9	737.9	736.9	736.9
170°	743.6	744.5	745.4	746.2	747.1	747.0	746.1	745.0	744.1	743.0	743.2
172.5°	748.3	749.2	750.0	750.9	751.7	751.7	750.6	749.7	748.6	747.6	747.8
175°	753.3	754.1	755.0	755.8	756.6	756.6	755.6	754.6	753.6	752.6	752.9
177.5°	755.5	756.2	756.9	757.6	758.3	758.3	757.6	756.9	756.2	755.5	755.8
180°	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1



TEST NUMBER: P331770-935

CATALOG NUMBER: S122RDIW-S290D710U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8
2.5°	576.4	575.1	573.9	571.2	569.7	566.6	566.2	566.0	562.0	558.0	556.9
5°	596.2	593.0	588.3	582.8	577.1	571.3	567.4	564.2	556.4	549.0	544.7
7.5°	616.0	609.3	601.2	590.9	582.2	572.6	565.3	558.9	547.8	537.1	529.9
10°	630.9	620.0	609.2	595.0	583.8	572.8	562.7	553.9	541.4	527.3	517.3
12.5°	640.2	628.1	613.3	599.3	584.9	570.9	557.3	546.0	531.3	516.8	505.0
15°	652.6	639.7	621.7	601.8	583.2	565.0	549.4	535.3	516.2	498.7	484.2
17.5°	662.9	645.1	625.8	602.7	581.2	558.1	538.0	520.0	498.6	477.6	460.5
20°	666.2	648.5	626.2	603.1	577.7	550.5	528.8	509.3	486.4	463.5	443.9
22.5°	664.1	650.4	625.6	598.0	572.0	543.5	519.0	496.3	470.9	447.5	424.9
25°	650.3	645.6	622.2	592.0	562.3	529.3	500.8	476.0	447.1	422.1	397.4
27.5°	618.1	628.3	613.7	581.6	548.5	513.2	481.2	453.0	422.9	394.8	370.2
30°	587.1	610.4	604.2	574.4	537.4	502.7	466.8	437.3	405.3	376.3	352.1
32.5°	544.8	583.2	589.3	564.4	526.2	487.9	450.4	421.0	387.5	357.1	333.4
35°	477.2	534.7	561.1	545.3	507.0	465.6	427.0	392.7	359.0	329.0	305.5
37.5°	396.7	475.0	519.0	520.1	484.9	442.0	399.8	365.8	331.4	301.9	276.5
40°	344.4	429.3	486.6	499.3	469.6	423.3	380.6	345.9	312.4	283.4	254.3
42.5°	297.5	382.0	452.5	474.6	451.0	404.9	362.1	326.0	293.3	265.9	236.1
45°	240.6	314.5	392.1	431.6	418.5	375.9	330.7	296.3	265.6	241.9	213.4
47.5°	202.9	255.0	330.2	383.6	383.4	344.5	300.0	267.1	238.6	216.4	193.3
50°	181.5	226.9	290.4	351.0	356.1	323.5	281.2	248.6	222.0	198.7	180.1
52.5°	162.2	199.7	256.8	315.0	329.4	301.1	260.1	230.0	204.1	182.7	166.9
55°	137.1	166.1	209.5	263.8	285.8	265.8	229.4	201.2	180.3	162.3	148.6
57.5°	116.0	137.7	172.5	216.3	241.8	229.3	199.2	176.3	158.4	142.2	131.4
60°	102.7	120.5	150.0	186.6	214.7	206.0	180.3	159.0	143.8	129.7	119.5
62.5°	90.1	105.5	130.8	160.5	186.2	182.6	161.7	143.8	130.4	117.6	109.0
65°	72.6	83.7	103.5	126.7	147.5	149.2	134.1	122.0	110.1	100.0	92.3
67.5°	57.8	65.1	79.0	98.6	114.1	119.7	110.5	101.2	91.7	83.9	77.2
70°	48.7	54.6	64.7	80.6	94.9	100.7	95.4	88.2	80.0	73.5	67.8
72.5°	39.4	45.2	52.7	64.3	76.5	82.9	81.0	75.9	69.2	63.8	58.5
75°	29.7	31.5	36.6	44.4	54.0	59.5	60.8	58.1	52.8	48.7	45.5
77.5°	22.0	23.1	25.5	29.5	35.8	40.7	42.7	42.4	38.7	36.4	33.4
80°	17.6	18.2	19.4	21.1	25.8	30.7	32.1	32.1	29.5	28.6	25.7
82.5°	13.3	13.8	14.6	15.5	17.7	22.0	23.5	23.8	22.2	20.9	18.6
85°	7.7	7.4	7.8	8.4	8.8	10.0	12.3	12.7	12.3	10.8	10.2
87.5°	5.9	5.4	4.8	4.1	4.0	3.8	4.2	4.6	4.4	4.2	4.3
90°	16.1	13.0	9.9	7.5	5.8	4.0	2.3	0.6	2.3	4.0	5.8
92.5°	18.9	18.1	17.4	16.4	15.2	13.9	12.7	11.4	12.7	13.9	15.2
95°	40.3	40.0	39.8	38.9	37.5	36.1	34.6	33.2	34.6	36.1	37.5
97.5°	67.7	67.2	66.6	65.7	64.4	63.2	61.9	60.7	61.9	63.2	64.4
100°	87.3	86.9	86.4	85.7	84.6	83.4	82.3	81.1	82.3	83.4	84.6
102.5°	108.1	107.5	106.9	106.2	105.3	104.4	103.5	102.6	103.5	104.4	105.3
105°	140.0	139.7	139.4	139.1	138.6	138.2	137.8	137.3	137.8	138.2	138.6
107.5°	175.2	175.2	175.2	174.9	174.3	173.7	173.0	172.4	173.0	173.7	174.3
110°	198.7	198.7	198.7	198.3	197.4	196.6	195.7	194.8	195.7	196.6	197.4





TEST NUMBER: P331770-935

CATALOG NUMBER: S122RDIW-S290D710U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	222.9	223.1	223.2	222.8	222.0	221.1	220.2	219.4	220.2	221.1	222.0
115°	258.6	259.0	259.2	259.0	258.1	257.3	256.4	255.5	256.4	257.3	258.1
117.5°	294.7	295.5	296.3	296.1	295.0	293.9	292.7	291.6	292.7	293.9	295.0
120°	317.9	319.0	320.1	320.1	319.0	317.9	316.8	315.6	316.8	317.9	319.0
122.5°	341.7	342.5	343.4	343.0	341.6	340.4	339.0	337.6	339.0	340.4	341.6
125°	376.5	376.9	377.4	376.9	375.7	374.4	373.2	371.9	373.2	374.4	375.7
127.5°	411.2	411.7	412.2	411.6	410.0	408.5	406.8	405.2	406.8	408.5	410.0
130°	433.8	434.0	434.3	433.5	431.7	429.8	428.0	426.1	428.0	429.8	431.7
132.5°	456.6	456.5	456.5	455.6	454.2	452.7	451.2	449.7	451.2	452.7	454.2
135°	488.9	488.5	488.3	487.3	485.8	484.2	482.7	481.1	482.7	484.2	485.8
137.5°	520.9	520.5	520.1	519.3	518.1	516.8	515.5	514.2	515.5	516.8	518.1
140°	541.7	541.0	540.2	539.2	538.0	536.7	535.4	534.2	535.4	536.7	538.0
142.5°	561.5	561.0	560.6	559.6	558.4	557.2	555.9	554.6	555.9	557.2	558.4
145°	590.6	589.7	588.8	588.0	586.9	585.9	585.0	583.9	585.0	585.9	586.9
147.5°	616.9	616.4	615.8	614.9	613.7	612.5	611.3	610.2	611.3	612.5	613.7
150°	633.3	632.7	632.1	631.5	630.6	629.7	628.9	628.0	628.9	629.7	630.6
152.5°	649.5	648.8	648.1	647.3	646.4	645.6	644.7	643.9	644.7	645.6	646.4
155°	670.6	670.2	669.8	669.3	668.9	668.5	668.0	667.6	668.0	668.5	668.9
157.5°	689.9	689.7	689.4	689.1	688.8	688.5	688.3	687.9	688.3	688.5	688.8
160°	701.9	701.7	701.6	701.4	701.1	700.8	700.5	700.3	700.5	700.8	701.1
162.5°	712.1	712.0	711.8	711.7	711.6	711.6	711.5	711.4	711.5	711.6	711.6
165°	725.8	725.8	725.8	725.9	726.0	726.2	726.3	726.4	726.3	726.2	726.0
167.5°	736.9	737.0	737.0	737.3	737.7	738.1	738.6	739.0	738.6	738.1	737.7
170°	743.3	743.5	743.6	743.9	744.3	744.8	745.2	745.6	745.2	744.8	744.3
172.5°	748.0	748.0	748.2	748.5	748.9	749.3	749.8	750.2	749.8	749.3	748.9
175°	753.2	753.5	753.8	754.1	754.6	755.0	755.4	755.8	755.4	755.0	754.6
177.5°	756.0	756.2	756.5	756.7	757.1	757.4	757.8	758.1	757.8	757.4	757.1
180°	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1



TEST NUMBER: P331770-935

CATALOG NUMBER: S122RDIW-S290D710U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8
2.5°	554.9	553.8	551.7	548.6	546.7	543.5	541.3	542.5	542.9	542.5	542.3
5°	540.0	535.9	530.2	524.7	519.6	514.2	511.0	509.7	507.0	505.4	504.5
7.5°	521.9	514.9	506.9	497.3	489.2	480.7	476.4	474.2	468.6	465.6	463.0
10°	508.5	497.3	489.3	476.8	469.2	458.1	450.4	450.6	443.0	438.7	435.6
12.5°	493.6	481.4	468.0	456.8	446.2	437.2	428.0	424.3	416.2	412.1	403.6
15°	469.0	454.7	440.7	425.4	414.7	400.7	387.4	371.2	358.1	346.7	343.6
17.5°	442.1	424.4	410.3	392.4	373.9	350.6	335.2	325.7	317.9	311.9	307.4
20°	423.6	405.6	390.5	363.6	338.7	322.9	311.6	304.3	296.1	289.6	286.1
22.5°	404.2	385.5	364.9	334.8	315.4	302.7	292.7	284.3	278.7	273.7	270.4
25°	376.7	356.1	322.3	301.6	285.9	272.6	265.6	260.5	254.7	247.8	244.7
27.5°	347.6	315.0	290.6	275.2	260.3	251.7	245.3	237.7	232.5	229.4	226.1
30°	325.8	293.2	274.2	257.4	246.8	237.2	229.8	225.5	220.4	215.2	213.0
32.5°	301.6	275.5	257.3	243.3	232.6	224.4	218.5	211.5	207.9	204.7	200.2
35°	271.5	251.7	235.1	223.8	213.5	206.9	200.1	196.0	189.3	186.6	184.9
37.5°	246.0	228.9	216.5	204.5	196.4	189.1	184.9	178.3	175.5	171.6	167.9
40°	231.5	214.7	202.9	193.0	184.0	178.6	173.3	168.0	163.7	162.0	157.5
42.5°	216.9	203.2	191.2	180.6	174.5	168.7	162.0	158.2	153.7	150.8	148.1
45°	196.6	184.4	174.3	165.5	158.8	152.7	148.4	142.0	139.5	133.8	131.4
47.5°	178.7	167.5	157.7	149.4	142.9	139.0	132.7	127.6	123.6	120.0	117.0
50°	166.1	156.6	147.2	139.8	134.0	128.3	121.8	119.3	113.0	111.2	109.5
52.5°	154.5	145.5	137.0	129.7	123.8	118.3	112.6	109.3	105.0	103.3	102.0
55°	138.3	129.7	121.5	115.0	109.2	103.5	100.0	95.8	93.8	92.5	90.9
57.5°	122.0	114.3	108.0	101.4	95.5	91.0	87.0	84.5	82.5	80.7	78.8
60°	111.7	104.3	98.6	92.5	86.4	82.7	79.6	76.6	74.3	71.5	70.8
62.5°	100.7	94.2	89.0	83.1	77.8	74.5	71.5	68.7	65.9	61.9	60.8
65°	85.7	80.6	75.1	70.2	65.5	62.2	57.9	54.8	53.6	53.2	53.0
67.5°	72.1	67.2	62.5	57.5	53.3	50.2	48.0	47.5	46.7	46.5	45.9
70°	62.9	58.5	53.8	49.1	44.9	44.4	43.7	42.8	41.8	41.5	41.1
72.5°	54.8	50.2	45.5	41.8	40.0	39.3	38.5	37.6	37.0	36.6	36.4
75°	42.0	37.7	34.6	33.2	32.3	31.7	30.5	30.0	29.5	28.9	28.8
77.5°	30.3	27.8	26.4	25.6	24.5	23.9	23.2	22.6	22.2	22.1	21.8
80°	23.1	21.9	20.9	19.7	19.4	18.6	18.4	17.8	18.0	17.4	17.4
82.5°	17.9	16.4	15.6	15.1	14.6	14.0	13.9	13.6	13.6	13.2	13.2
85°	9.2	8.8	8.4	8.0	8.0	7.4	7.7	7.4	7.4	7.1	6.9
87.5°	4.5	4.8	5.1	5.8	6.4	6.8	6.8	6.5	6.5	6.5	6.3
90°	7.5	9.9	13.0	16.1	19.2	22.4	22.0	21.8	21.5	21.3	21.2
92.5°	16.4	17.4	18.1	18.9	19.5	20.3	20.4	20.4	20.5	20.6	20.6
95°	38.9	39.8	40.0	40.3	40.6	40.9	40.9	40.9	40.9	40.9	40.7
97.5°	65.7	66.6	67.2	67.7	68.2	68.7	68.7	68.7	68.7	68.7	68.7
100°	85.7	86.4	86.9	87.3	87.7	88.2	88.2	88.2	88.2	88.2	88.1
102.5°	106.2	106.9	107.5	108.1	108.6	109.1	109.3	109.3	109.4	109.6	109.6
105°	139.1	139.4	139.7	140.0	140.3	140.6	140.9	141.1	141.4	141.7	141.8
107.5°	174.9	175.2	175.2	175.2	175.2	175.2	175.3	175.4	175.6	175.6	175.4
110°	198.3	198.7	198.7	198.7	198.7	198.7	198.7	198.7	198.7	198.7	198.5



TEST NUMBER: P331770-935

CATALOG NUMBER: S122RDIW-S290D710U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	222.8	223.2	223.1	222.9	222.8	222.7	222.4	222.1	221.7	221.4	221.0
115°	259.0	259.2	259.0	258.6	258.4	258.1	258.0	257.9	257.7	257.5	257.3
117.5°	296.1	296.3	295.5	294.7	293.9	293.2	292.8	292.5	292.1	291.8	291.4
120°	320.1	320.1	319.0	317.9	316.8	315.6	315.6	315.6	315.6	315.6	315.4
122.5°	343.0	343.4	342.5	341.7	341.0	340.2	339.8	339.5	339.1	338.8	338.5
125°	376.9	377.4	376.9	376.5	376.1	375.7	375.2	374.8	374.4	373.9	373.7
127.5°	411.6	412.2	411.7	411.2	410.7	410.2	409.7	409.1	408.6	408.1	407.7
130°	433.5	434.3	434.0	433.8	433.4	433.2	432.9	432.7	432.3	432.0	431.6
132.5°	455.6	456.5	456.5	456.6	456.7	456.7	456.1	455.5	454.8	454.2	453.7
135°	487.3	488.3	488.5	488.9	489.1	489.4	489.2	489.1	489.0	488.9	488.5
137.5°	519.3	520.1	520.5	520.9	521.2	521.6	521.5	521.3	521.2	521.2	520.8
140°	539.2	540.2	541.0	541.7	542.3	543.0	543.0	543.0	543.0	543.0	542.8
142.5°	559.6	560.6	561.0	561.5	562.0	562.5	562.6	562.7	562.8	562.9	562.7
145°	588.0	588.8	589.7	590.6	591.4	592.3	592.4	592.5	592.7	592.8	592.6
147.5°	614.9	615.8	616.4	616.9	617.5	618.1	618.4	618.7	619.0	619.3	619.2
150°	631.5	632.1	632.7	633.3	633.9	634.5	634.9	635.2	635.7	636.1	636.1
152.5°	647.3	648.1	648.8	649.5	650.1	650.8	651.3	651.9	652.4	653.0	653.0
155°	669.3	669.8	670.2	670.6	671.1	671.5	672.2	672.9	673.6	674.3	674.5
157.5°	689.1	689.4	689.7	689.9	690.2	690.4	691.4	692.3	693.3	694.2	694.4
160°	701.4	701.6	701.7	701.9	702.0	702.1	703.0	703.9	704.7	705.6	705.7
162.5°	711.7	711.8	712.0	712.1	712.2	712.4	713.3	714.3	715.3	716.3	716.4
165°	725.9	725.8	725.8	725.8	725.8	725.8	726.8	727.8	728.8	729.8	730.0
167.5°	737.3	737.0	737.0	736.9	736.9	736.9	737.9	738.9	739.9	740.9	741.0
170°	743.9	743.6	743.5	743.3	743.2	743.0	744.1	745.0	746.1	747.0	747.1
172.5°	748.5	748.2	748.0	748.0	747.8	747.6	748.6	749.7	750.6	751.7	751.7
175°	754.1	753.8	753.5	753.2	752.9	752.6	753.6	754.6	755.6	756.6	756.6
177.5°	756.7	756.5	756.2	756.0	755.8	755.5	756.2	756.9	757.6	758.3	758.3
180°	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1



TEST NUMBER: P331770-935

CATALOG NUMBER: S122RDIW-S290D710U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8
2.5°	540.5	540.8	540.4	540.6	540.4	540.8	540.5	542.3	542.5	542.9	542.5
5°	503.6	501.3	500.8	500.3	500.8	501.3	503.6	504.5	505.4	507.0	509.7
7.5°	459.6	459.3	458.2	456.8	458.2	459.3	459.6	463.0	465.6	468.6	474.2
10°	431.3	430.2	430.1	428.7	430.1	430.2	431.3	435.6	438.7	443.0	450.6
12.5°	398.0	391.8	391.2	387.7	391.2	391.8	398.0	403.6	412.1	416.2	424.3
15°	339.0	337.8	333.8	331.3	333.8	337.8	339.0	343.6	346.7	358.1	371.2
17.5°	305.1	301.3	300.1	299.5	300.1	301.3	305.1	307.4	311.9	317.9	325.7
20°	283.4	279.9	279.3	278.9	279.3	279.9	283.4	286.1	289.6	296.1	304.3
22.5°	268.4	264.7	263.2	262.0	263.2	264.7	268.4	270.4	273.7	278.7	284.3
25°	242.7	241.3	240.6	240.1	240.6	241.3	242.7	244.7	247.8	254.7	260.5
27.5°	222.7	219.6	219.0	218.0	219.0	219.6	222.7	226.1	229.4	232.5	237.7
30°	211.2	210.3	208.9	207.7	208.9	210.3	211.2	213.0	215.2	220.4	225.5
32.5°	197.8	196.9	195.7	195.2	195.7	196.9	197.8	200.2	204.7	207.9	211.5
35°	182.9	180.1	178.9	177.2	178.9	180.1	182.9	184.9	186.6	189.3	196.0
37.5°	167.1	165.7	164.0	164.6	164.0	165.7	167.1	167.9	171.6	175.5	178.3
40°	154.9	153.9	153.5	153.3	153.5	153.9	154.9	157.5	162.0	163.7	168.0
42.5°	145.2	142.5	141.5	141.5	141.5	142.5	145.2	148.1	150.8	153.7	158.2
45°	130.4	127.9	126.1	126.3	126.1	127.9	130.4	131.4	133.8	139.5	142.0
47.5°	115.4	115.3	114.2	114.5	114.2	115.3	115.4	117.0	120.0	123.6	127.6
50°	108.1	107.0	106.2	106.4	106.2	107.0	108.1	109.5	111.2	113.0	119.3
52.5°	101.3	100.2	99.6	100.5	99.6	100.2	101.3	102.0	103.3	105.0	109.3
55°	90.0	88.8	88.6	88.4	88.6	88.8	90.0	90.9	92.5	93.8	95.8
57.5°	77.3	76.5	75.3	74.9	75.3	76.5	77.3	78.8	80.7	82.5	84.5
60°	68.3	66.7	64.7	64.6	64.7	66.7	68.3	70.8	71.5	74.3	76.6
62.5°	59.9	59.7	59.2	59.2	59.2	59.7	59.9	60.8	61.9	65.9	68.7
65°	52.6	52.4	52.6	52.8	52.6	52.4	52.6	53.0	53.2	53.6	54.8
67.5°	45.8	45.5	45.1	45.3	45.1	45.5	45.8	45.9	46.5	46.7	47.5
70°	40.6	40.5	40.3	40.3	40.3	40.5	40.6	41.1	41.5	41.8	42.8
72.5°	35.6	35.6	35.5	35.3	35.5	35.6	35.6	36.4	36.6	37.0	37.6
75°	28.6	28.2	28.2	28.2	28.2	28.2	28.6	28.8	28.9	29.5	30.0
77.5°	21.8	21.5	21.4	21.2	21.4	21.5	21.8	21.8	22.1	22.2	22.6
80°	17.2	17.0	16.8	16.8	16.8	17.0	17.2	17.4	17.4	18.0	17.8
82.5°	13.2	12.9	12.9	12.7	12.9	12.9	13.2	13.2	13.2	13.6	13.6
85°	7.1	7.2	7.1	7.4	7.1	7.2	7.1	6.9	7.1	7.4	7.4
87.5°	6.3	6.2	6.4	6.2	6.4	6.2	6.3	6.3	6.5	6.5	6.5
90°	21.3	21.4	21.6	21.7	21.6	21.4	21.3	21.2	21.3	21.5	21.8
92.5°	20.6	20.7	20.7	20.7	20.7	20.7	20.6	20.6	20.6	20.5	20.4
95°	40.5	40.2	39.9	39.6	39.9	40.2	40.5	40.7	40.9	40.9	40.9
97.5°	68.7	68.7	68.6	68.6	68.6	68.7	68.7	68.7	68.7	68.7	68.7
100°	88.0	87.8	87.6	87.6	87.6	87.8	88.0	88.1	88.2	88.2	88.2
102.5°	109.4	109.3	109.2	109.0	109.2	109.3	109.4	109.6	109.6	109.4	109.3
105°	141.8	141.8	141.8	141.8	141.8	141.8	141.8	141.8	141.7	141.4	141.1
107.5°	174.7	174.1	173.4	172.8	173.4	174.1	174.7	175.4	175.6	175.6	175.4
110°	198.0	197.6	197.2	196.8	197.2	197.6	198.0	198.5	198.7	198.7	198.7



TEST NUMBER: P331770-935

CATALOG NUMBER: S122RDIW-S290D710U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	220.8	220.4	220.1	219.8	220.1	220.4	220.8	221.0	221.4	221.7	222.1
115°	256.8	256.4	256.0	255.5	256.0	256.4	256.8	257.3	257.5	257.7	257.9
117.5°	290.9	290.5	290.1	289.6	290.1	290.5	290.9	291.4	291.8	292.1	292.5
120°	315.0	314.5	314.1	313.7	314.1	314.5	315.0	315.4	315.6	315.6	315.6
122.5°	338.1	337.9	337.5	337.3	337.5	337.9	338.1	338.5	338.8	339.1	339.5
125°	373.6	373.4	373.2	373.2	373.2	373.4	373.6	373.7	373.9	374.4	374.8
127.5°	407.2	406.7	406.3	405.9	406.3	406.7	407.2	407.7	408.1	408.6	409.1
130°	431.0	430.5	429.9	429.4	429.9	430.5	431.0	431.6	432.0	432.3	432.7
132.5°	453.2	452.7	452.3	451.9	452.3	452.7	453.2	453.7	454.2	454.8	455.5
135°	488.1	487.7	487.2	486.8	487.2	487.7	488.1	488.5	488.9	489.0	489.1
137.5°	520.2	519.7	519.1	518.5	519.1	519.7	520.2	520.8	521.2	521.2	521.3
140°	542.3	541.7	541.1	540.5	541.1	541.7	542.3	542.8	543.0	543.0	543.0
142.5°	562.1	561.5	561.0	560.4	561.0	561.5	562.1	562.7	562.9	562.8	562.7
145°	592.0	591.5	590.9	590.4	590.9	591.5	592.0	592.6	592.8	592.7	592.5
147.5°	618.7	618.1	617.6	617.1	617.6	618.1	618.7	619.2	619.3	619.0	618.7
150°	635.7	635.2	634.9	634.5	634.9	635.2	635.7	636.1	636.1	635.7	635.2
152.5°	652.4	651.9	651.3	650.8	651.3	651.9	652.4	653.0	653.0	652.4	651.9
155°	674.1	673.6	673.2	672.8	673.2	673.6	674.1	674.5	674.3	673.6	672.9
157.5°	693.7	693.0	692.3	691.6	692.3	693.0	693.7	694.4	694.2	693.3	692.3
160°	705.2	704.6	704.0	703.4	704.0	704.6	705.2	705.7	705.6	704.7	703.9
162.5°	715.7	715.1	714.4	713.7	714.4	715.1	715.7	716.4	716.3	715.3	714.3
165°	729.2	728.5	727.8	727.1	727.8	728.5	729.2	730.0	729.8	728.8	727.8
167.5°	740.3	739.5	738.8	738.0	738.8	739.5	740.3	741.0	740.9	739.9	738.9
170°	746.2	745.4	744.5	743.6	744.5	745.4	746.2	747.1	747.0	746.1	745.0
172.5°	750.9	750.0	749.2	748.3	749.2	750.0	750.9	751.7	751.7	750.6	749.7
175°	755.8	755.0	754.1	753.3	754.1	755.0	755.8	756.6	756.6	755.6	754.6
177.5°	757.6	756.9	756.2	755.5	756.2	756.9	757.6	758.3	758.3	757.6	756.9
180°	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1



TEST NUMBER: P331770-935

CATALOG NUMBER: S122RDIW-S290D710U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8
2.5°	541.3	543.5	546.7	548.6	551.7	553.8	554.9	556.9	558.0	562.0	566.0
5°	511.0	514.2	519.6	524.7	530.2	535.9	540.0	544.7	549.0	556.4	564.2
7.5°	476.4	480.7	489.2	497.3	506.9	514.9	521.9	529.9	537.1	547.8	558.9
10°	450.4	458.1	469.2	476.8	489.3	497.3	508.5	517.3	527.3	541.4	553.9
12.5°	428.0	437.2	446.2	456.8	468.0	481.4	493.6	505.0	516.8	531.3	546.0
15°	387.4	400.7	414.7	425.4	440.7	454.7	469.0	484.2	498.7	516.2	535.3
17.5°	335.2	350.6	373.9	392.4	410.3	424.4	442.1	460.5	477.6	498.6	520.0
20°	311.6	322.9	338.7	363.6	390.5	405.6	423.6	443.9	463.5	486.4	509.3
22.5°	292.7	302.7	315.4	334.8	364.9	385.5	404.2	424.9	447.5	470.9	496.3
25°	265.6	272.6	285.9	301.6	322.3	356.1	376.7	397.4	422.1	447.1	476.0
27.5°	245.3	251.7	260.3	275.2	290.6	315.0	347.6	370.2	394.8	422.9	453.0
30°	229.8	237.2	246.8	257.4	274.2	293.2	325.8	352.1	376.3	405.3	437.3
32.5°	218.5	224.4	232.6	243.3	257.3	275.5	301.6	333.4	357.1	387.5	421.0
35°	200.1	206.9	213.5	223.8	235.1	251.7	271.5	305.5	329.0	359.0	392.7
37.5°	184.9	189.1	196.4	204.5	216.5	228.9	246.0	276.5	301.9	331.4	365.8
40°	173.3	178.6	184.0	193.0	202.9	214.7	231.5	254.3	283.4	312.4	345.9
42.5°	162.0	168.7	174.5	180.6	191.2	203.2	216.9	236.1	265.9	293.3	326.0
45°	148.4	152.7	158.8	165.5	174.3	184.4	196.6	213.4	241.9	265.6	296.3
47.5°	132.7	139.0	142.9	149.4	157.7	167.5	178.7	193.3	216.4	238.6	267.1
50°	121.8	128.3	134.0	139.8	147.2	156.6	166.1	180.1	198.7	222.0	248.6
52.5°	112.6	118.3	123.8	129.7	137.0	145.5	154.5	166.9	182.7	204.1	230.0
55°	100.0	103.5	109.2	115.0	121.5	129.7	138.3	148.6	162.3	180.3	201.2
57.5°	87.0	91.0	95.5	101.4	108.0	114.3	122.0	131.4	142.2	158.4	176.3
60°	79.6	82.7	86.4	92.5	98.6	104.3	111.7	119.5	129.7	143.8	159.0
62.5°	71.5	74.5	77.8	83.1	89.0	94.2	100.7	109.0	117.6	130.4	143.8
65°	57.9	62.2	65.5	70.2	75.1	80.6	85.7	92.3	100.0	110.1	122.0
67.5°	48.0	50.2	53.3	57.5	62.5	67.2	72.1	77.2	83.9	91.7	101.2
70°	43.7	44.4	44.9	49.1	53.8	58.5	62.9	67.8	73.5	80.0	88.2
72.5°	38.5	39.3	40.0	41.8	45.5	50.2	54.8	58.5	63.8	69.2	75.9
75°	30.5	31.7	32.3	33.2	34.6	37.7	42.0	45.5	48.7	52.8	58.1
77.5°	23.2	23.9	24.5	25.6	26.4	27.8	30.3	33.4	36.4	38.7	42.4
80°	18.4	18.6	19.4	19.7	20.9	21.9	23.1	25.7	28.6	29.5	32.1
82.5°	13.9	14.0	14.6	15.1	15.6	16.4	17.9	18.6	20.9	22.2	23.8
85°	7.7	7.4	8.0	8.0	8.4	8.8	9.2	10.2	10.8	12.3	12.7
87.5°	6.8	6.8	6.4	5.8	5.1	4.8	4.5	4.3	4.2	4.4	4.6
90°	22.0	22.4	19.2	16.1	13.0	9.9	7.5	5.8	4.0	2.3	0.6
92.5°	20.4	20.3	19.5	18.9	18.1	17.4	16.4	15.2	13.9	12.7	11.4
95°	40.9	40.9	40.6	40.3	40.0	39.8	38.9	37.5	36.1	34.6	33.2
97.5°	68.7	68.7	68.2	67.7	67.2	66.6	65.7	64.4	63.2	61.9	60.7
100°	88.2	88.2	87.7	87.3	86.9	86.4	85.7	84.6	83.4	82.3	81.1
102.5°	109.3	109.1	108.6	108.1	107.5	106.9	106.2	105.3	104.4	103.5	102.6
105°	140.9	140.6	140.3	140.0	139.7	139.4	139.1	138.6	138.2	137.8	137.3
107.5°	175.3	175.2	175.2	175.2	175.2	175.2	174.9	174.3	173.7	173.0	172.4
110°	198.7	198.7	198.7	198.7	198.7	198.7	198.3	197.4	196.6	195.7	194.8



TEST NUMBER: P331770-935

CATALOG NUMBER: S122RDIW-S290D710U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	222.4	222.7	222.8	222.9	223.1	223.2	222.8	222.0	221.1	220.2	219.4
115°	258.0	258.1	258.4	258.6	259.0	259.2	259.0	258.1	257.3	256.4	255.5
117.5°	292.8	293.2	293.9	294.7	295.5	296.3	296.1	295.0	293.9	292.7	291.6
120°	315.6	315.6	316.8	317.9	319.0	320.1	320.1	319.0	317.9	316.8	315.6
122.5°	339.8	340.2	341.0	341.7	342.5	343.4	343.0	341.6	340.4	339.0	337.6
125°	375.2	375.7	376.1	376.5	376.9	377.4	376.9	375.7	374.4	373.2	371.9
127.5°	409.7	410.2	410.7	411.2	411.7	412.2	411.6	410.0	408.5	406.8	405.2
130°	432.9	433.2	433.4	433.8	434.0	434.3	433.5	431.7	429.8	428.0	426.1
132.5°	456.1	456.7	456.7	456.6	456.5	456.5	455.6	454.2	452.7	451.2	449.7
135°	489.2	489.4	489.1	488.9	488.5	488.3	487.3	485.8	484.2	482.7	481.1
137.5°	521.5	521.6	521.2	520.9	520.5	520.1	519.3	518.1	516.8	515.5	514.2
140°	543.0	543.0	542.3	541.7	541.0	540.2	539.2	538.0	536.7	535.4	534.2
142.5°	562.6	562.5	562.0	561.5	561.0	560.6	559.6	558.4	557.2	555.9	554.6
145°	592.4	592.3	591.4	590.6	589.7	588.8	588.0	586.9	585.9	585.0	583.9
147.5°	618.4	618.1	617.5	616.9	616.4	615.8	614.9	613.7	612.5	611.3	610.2
150°	634.9	634.5	633.9	633.3	632.7	632.1	631.5	630.6	629.7	628.9	628.0
152.5°	651.3	650.8	650.1	649.5	648.8	648.1	647.3	646.4	645.6	644.7	643.9
155°	672.2	671.5	671.1	670.6	670.2	669.8	669.3	668.9	668.5	668.0	667.6
157.5°	691.4	690.4	690.2	689.9	689.7	689.4	689.1	688.8	688.5	688.3	687.9
160°	703.0	702.1	702.0	701.9	701.7	701.6	701.4	701.1	700.8	700.5	700.3
162.5°	713.3	712.4	712.2	712.1	712.0	711.8	711.7	711.6	711.6	711.5	711.4
165°	726.8	725.8	725.8	725.8	725.8	725.8	725.9	726.0	726.2	726.3	726.4
167.5°	737.9	736.9	736.9	736.9	737.0	737.0	737.3	737.7	738.1	738.6	739.0
170°	744.1	743.0	743.2	743.3	743.5	743.6	743.9	744.3	744.8	745.2	745.6
172.5°	748.6	747.6	747.8	748.0	748.0	748.2	748.5	748.9	749.3	749.8	750.2
175°	753.6	752.6	752.9	753.2	753.5	753.8	754.1	754.6	755.0	755.4	755.8
177.5°	756.2	755.5	755.8	756.0	756.2	756.5	756.7	757.1	757.4	757.8	758.1
180°	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1



TEST NUMBER: P331770-935

CATALOG NUMBER: S122RDIW-S290D710U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8	562.8
2.5°	566.2	566.6	569.7	571.2	573.9	575.1	576.4	576.0	576.0	576.6	581.0
5°	567.4	571.3	577.1	582.8	588.3	593.0	596.2	599.3	600.5	606.1	611.1
7.5°	565.3	572.6	582.2	590.9	601.2	609.3	616.0	622.2	626.3	634.6	643.0
10°	562.7	572.8	583.8	595.0	609.2	620.0	630.9	639.4	642.0	654.4	661.4
12.5°	557.3	570.9	584.9	599.3	613.3	628.1	640.2	648.6	658.2	669.3	682.3
15°	549.4	565.0	583.2	601.8	621.7	639.7	652.6	667.3	677.9	690.0	701.4
17.5°	538.0	558.1	581.2	602.7	625.8	645.1	662.9	676.9	684.3	691.3	692.9
20°	528.8	550.5	577.7	603.1	626.2	648.5	666.2	677.9	679.8	680.0	669.7
22.5°	519.0	543.5	572.0	598.0	625.6	650.4	664.1	669.1	661.3	648.1	628.0
25°	500.8	529.3	562.3	592.0	622.2	645.6	650.3	641.5	614.3	585.7	549.6
27.5°	481.2	513.2	548.5	581.6	613.7	628.3	618.1	586.3	537.4	494.8	443.2
30°	466.8	502.7	537.4	574.4	604.2	610.4	587.1	540.4	483.3	419.1	367.6
32.5°	450.4	487.9	526.2	564.4	589.3	583.2	544.8	487.2	420.3	357.1	308.6
35°	427.0	465.6	507.0	545.3	561.1	534.7	477.2	402.3	333.8	275.0	241.5
37.5°	399.8	442.0	484.9	520.1	519.0	475.0	396.7	319.3	261.8	227.0	203.2
40°	380.6	423.3	469.6	499.3	486.6	429.3	344.4	271.5	229.4	201.6	184.3
42.5°	362.1	404.9	451.0	474.6	452.5	382.0	297.5	240.3	205.6	184.0	169.9
45°	330.7	375.9	418.5	431.6	392.1	314.5	240.6	199.1	176.0	160.0	150.2
47.5°	300.0	344.5	383.4	383.6	330.2	255.0	202.9	172.3	152.6	140.2	133.1
50°	281.2	323.5	356.1	351.0	290.4	226.9	181.5	155.1	138.7	129.1	121.7
52.5°	260.1	301.1	329.4	315.0	256.8	199.7	162.2	140.1	126.5	118.1	111.5
55°	229.4	265.8	285.8	263.8	209.5	166.1	137.1	119.7	109.5	102.5	96.8
57.5°	199.2	229.3	241.8	216.3	172.5	137.7	116.0	102.9	92.8	87.7	84.8
60°	180.3	206.0	214.7	186.6	150.0	120.5	102.7	90.6	83.1	79.8	76.9
62.5°	161.7	182.6	186.2	160.5	130.8	105.5	90.1	79.9	75.0	71.8	69.1
65°	134.1	149.2	147.5	126.7	103.5	83.7	72.6	66.3	62.6	58.1	53.2
67.5°	110.5	119.7	114.1	98.6	79.0	65.1	57.8	53.0	48.4	44.2	43.0
70°	95.4	100.7	94.9	80.6	64.7	54.6	48.7	43.0	40.3	39.3	37.5
72.5°	81.0	82.9	76.5	64.3	52.7	45.2	39.4	36.3	34.8	34.0	32.9
75°	60.8	59.5	54.0	44.4	36.6	31.5	29.7	28.6	27.6	26.8	26.2
77.5°	42.7	40.7	35.8	29.5	25.5	23.1	22.0	21.4	20.9	20.5	19.9
80°	32.1	30.7	25.8	21.1	19.4	18.2	17.6	16.8	16.8	16.4	15.8
82.5°	23.5	22.0	17.7	15.5	14.6	13.8	13.3	12.9	12.7	12.8	12.4
85°	12.3	10.0	8.8	8.4	7.8	7.4	7.7	7.2	7.2	7.2	7.1
87.5°	4.2	3.8	4.0	4.1	4.8	5.4	5.9	6.5	7.3	7.1	7.1
90°	2.3	4.0	5.8	7.5	9.9	13.0	16.1	19.2	22.4	22.0	21.8
92.5°	12.7	13.9	15.2	16.4	17.4	18.1	18.9	19.5	20.3	20.4	20.4
95°	34.6	36.1	37.5	38.9	39.8	40.0	40.3	40.6	40.9	40.9	40.9
97.5°	61.9	63.2	64.4	65.7	66.6	67.2	67.7	68.2	68.7	68.7	68.7
100°	82.3	83.4	84.6	85.7	86.4	86.9	87.3	87.7	88.2	88.2	88.2
102.5°	103.5	104.4	105.3	106.2	106.9	107.5	108.1	108.6	109.1	109.3	109.3
105°	137.8	138.2	138.6	139.1	139.4	139.7	140.0	140.3	140.6	140.9	141.1
107.5°	173.0	173.7	174.3	174.9	175.2	175.2	175.2	175.2	175.2	175.3	175.4
110°	195.7	196.6	197.4	198.3	198.7	198.7	198.7	198.7	198.7	198.7	198.7





TEST NUMBER: P331770-935

CATALOG NUMBER: S122RDIW-S290D710U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	220.2	221.1	222.0	222.8	223.2	223.1	222.9	222.8	222.7	222.4	222.1
115°	256.4	257.3	258.1	259.0	259.2	259.0	258.6	258.4	258.1	258.0	257.9
117.5°	292.7	293.9	295.0	296.1	296.3	295.5	294.7	293.9	293.2	292.8	292.5
120°	316.8	317.9	319.0	320.1	320.1	319.0	317.9	316.8	315.6	315.6	315.6
122.5°	339.0	340.4	341.6	343.0	343.4	342.5	341.7	341.0	340.2	339.8	339.5
125°	373.2	374.4	375.7	376.9	377.4	376.9	376.5	376.1	375.7	375.2	374.8
127.5°	406.8	408.5	410.0	411.6	412.2	411.7	411.2	410.7	410.2	409.7	409.1
130°	428.0	429.8	431.7	433.5	434.3	434.0	433.8	433.4	433.2	432.9	432.7
132.5°	451.2	452.7	454.2	455.6	456.5	456.5	456.6	456.7	456.7	456.1	455.5
135°	482.7	484.2	485.8	487.3	488.3	488.5	488.9	489.1	489.4	489.2	489.1
137.5°	515.5	516.8	518.1	519.3	520.1	520.5	520.9	521.2	521.6	521.5	521.3
140°	535.4	536.7	538.0	539.2	540.2	541.0	541.7	542.3	543.0	543.0	543.0
142.5°	555.9	557.2	558.4	559.6	560.6	561.0	561.5	562.0	562.5	562.6	562.7
145°	585.0	585.9	586.9	588.0	588.8	589.7	590.6	591.4	592.3	592.4	592.5
147.5°	611.3	612.5	613.7	614.9	615.8	616.4	616.9	617.5	618.1	618.4	618.7
150°	628.9	629.7	630.6	631.5	632.1	632.7	633.3	633.9	634.5	634.9	635.2
152.5°	644.7	645.6	646.4	647.3	648.1	648.8	649.5	650.1	650.8	651.3	651.9
155°	668.0	668.5	668.9	669.3	669.8	670.2	670.6	671.1	671.5	672.2	672.9
157.5°	688.3	688.5	688.8	689.1	689.4	689.7	689.9	690.2	690.4	691.4	692.3
160°	700.5	700.8	701.1	701.4	701.6	701.7	701.9	702.0	702.1	703.0	703.9
162.5°	711.5	711.6	711.6	711.7	711.8	712.0	712.1	712.2	712.4	713.3	714.3
165°	726.3	726.2	726.0	725.9	725.8	725.8	725.8	725.8	725.8	726.8	727.8
167.5°	738.6	738.1	737.7	737.3	737.0	737.0	736.9	736.9	736.9	737.9	738.9
170°	745.2	744.8	744.3	743.9	743.6	743.5	743.3	743.2	743.0	744.1	745.0
172.5°	749.8	749.3	748.9	748.5	748.2	748.0	748.0	747.8	747.6	748.6	749.7
175°	755.4	755.0	754.6	754.1	753.8	753.5	753.2	752.9	752.6	753.6	754.6
177.5°	757.8	757.4	757.1	756.7	756.5	756.2	756.0	755.8	755.5	756.2	756.9
180°	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1



TEST NUMBER: P331770-935

CATALOG NUMBER: S122RDIW-S290D710U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	562.8	562.8	562.8	562.8	562.8	562.8	562.8
2.5°	582.6	584.6	585.6	585.6	586.7	586.2	585.7
5°	616.0	619.7	620.6	624.1	626.6	625.9	626.2
7.5°	649.4	655.3	661.2	663.9	664.3	665.9	666.5
10°	669.9	674.8	683.9	682.6	689.4	693.4	686.9
12.5°	689.6	696.2	702.6	704.3	708.2	709.5	706.9
15°	707.4	710.9	711.3	710.3	711.5	710.5	706.8
17.5°	690.8	685.0	673.5	668.0	663.7	657.2	654.6
20°	663.2	646.4	626.8	619.0	609.8	591.9	596.2
22.5°	603.7	584.6	565.0	542.2	531.2	514.2	513.2
25°	511.3	478.2	441.8	416.4	401.5	384.5	377.0
27.5°	397.5	355.9	326.1	311.0	297.2	283.8	283.2
30°	322.7	291.4	268.4	255.5	247.0	241.3	242.5
32.5°	272.0	250.6	235.0	224.3	218.1	213.8	213.7
35°	222.4	207.7	197.7	193.2	188.7	185.6	185.8
37.5°	190.3	181.5	175.9	171.0	168.2	166.6	165.7
40°	173.8	166.6	162.3	159.4	157.0	154.9	154.5
42.5°	160.9	154.9	150.6	148.3	146.1	144.6	144.2
45°	142.8	137.8	134.0	131.4	130.4	129.1	129.1
47.5°	127.0	122.2	119.2	117.5	115.9	114.9	114.9
50°	116.4	112.6	109.9	108.9	107.5	107.0	106.8
52.5°	106.9	104.0	102.1	101.4	100.8	100.1	100.2
55°	93.8	92.3	91.5	90.9	90.0	88.8	89.5
57.5°	83.0	81.6	79.6	77.7	76.8	75.9	76.3
60°	75.3	72.6	69.8	67.7	67.1	65.3	65.3
62.5°	65.6	61.7	58.4	57.2	56.6	55.8	55.6
65°	50.5	48.9	48.1	47.4	46.9	46.9	46.6
67.5°	41.8	41.2	40.3	40.1	39.8	39.6	39.5
70°	36.9	36.2	35.8	35.6	35.2	35.4	34.8
72.5°	32.3	31.7	31.6	31.1	30.8	30.8	30.4
75°	25.4	25.4	25.2	25.1	24.6	24.5	24.6
77.5°	19.5	19.6	19.3	19.2	19.2	19.2	19.0
80°	15.7	15.8	15.7	15.4	15.2	15.4	15.2
82.5°	12.4	12.1	12.1	12.0	12.0	11.9	11.8
85°	7.1	7.2	7.1	6.9	6.9	6.9	7.1
87.5°	7.0	6.9	6.9	6.9	7.0	7.0	6.9
90°	21.5	21.3	21.2	21.3	21.4	21.6	21.7
92.5°	20.5	20.6	20.6	20.6	20.7	20.7	20.7
95°	40.9	40.9	40.7	40.5	40.2	39.9	39.6
97.5°	68.7	68.7	68.7	68.7	68.7	68.6	68.6
100°	88.2	88.2	88.1	88.0	87.8	87.6	87.6
102.5°	109.4	109.6	109.6	109.4	109.3	109.2	109.0
105°	141.4	141.7	141.8	141.8	141.8	141.8	141.8
107.5°	175.6	175.6	175.4	174.7	174.1	173.4	172.8
110°	198.7	198.7	198.5	198.0	197.6	197.2	196.8



TEST NUMBER: P331770-935

CATALOG NUMBER: S122RDIW-S290D710U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	221.7	221.4	221.0	220.8	220.4	220.1	219.8
115°	257.7	257.5	257.3	256.8	256.4	256.0	255.5
117.5°	292.1	291.8	291.4	290.9	290.5	290.1	289.6
120°	315.6	315.6	315.4	315.0	314.5	314.1	313.7
122.5°	339.1	338.8	338.5	338.1	337.9	337.5	337.3
125°	374.4	373.9	373.7	373.6	373.4	373.2	373.2
127.5°	408.6	408.1	407.7	407.2	406.7	406.3	405.9
130°	432.3	432.0	431.6	431.0	430.5	429.9	429.4
132.5°	454.8	454.2	453.7	453.2	452.7	452.3	451.9
135°	489.0	488.9	488.5	488.1	487.7	487.2	486.8
137.5°	521.2	521.2	520.8	520.2	519.7	519.1	518.5
140°	543.0	543.0	542.8	542.3	541.7	541.1	540.5
142.5°	562.8	562.9	562.7	562.1	561.5	561.0	560.4
145°	592.7	592.8	592.6	592.0	591.5	590.9	590.4
147.5°	619.0	619.3	619.2	618.7	618.1	617.6	617.1
150°	635.7	636.1	636.1	635.7	635.2	634.9	634.5
152.5°	652.4	653.0	653.0	652.4	651.9	651.3	650.8
155°	673.6	674.3	674.5	674.1	673.6	673.2	672.8
157.5°	693.3	694.2	694.4	693.7	693.0	692.3	691.6
160°	704.7	705.6	705.7	705.2	704.6	704.0	703.4
162.5°	715.3	716.3	716.4	715.7	715.1	714.4	713.7
165°	728.8	729.8	730.0	729.2	728.5	727.8	727.1
167.5°	739.9	740.9	741.0	740.3	739.5	738.8	738.0
170°	746.1	747.0	747.1	746.2	745.4	744.5	743.6
172.5°	750.6	751.7	751.7	750.9	750.0	749.2	748.3
175°	755.6	756.6	756.6	755.8	755.0	754.1	753.3
177.5°	757.6	758.3	758.3	757.6	756.9	756.2	755.5
180°	757.1	757.1	757.1	757.1	757.1	757.1	757.1

(END OF REPORT)