

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331484-840

Luminaire Tested: **S122DIW-S290D1240U840-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331484-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S290D1240U840-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1240 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5661.9 lumens
Efficiency: N/A
Efficacy: 121.5 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 46.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331484-840

CATALOG NUMBER: S122DIW-S290D1240U840-4F0-1E-UDD-A1

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - - - 90°-270° - - - 135°-315°



TEST NUMBER: P331484-840

CATALOG NUMBER: S122DIW-S290D1240U840-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	69	69	69	49	49	49	32	32	32	23
1	92	88	84	81	82	78	75	73	60	58	56	44	42	41	28	28	27	20
2	84	77	71	66	74	69	64	60	53	50	47	38	36	35	25	24	23	17
3	77	68	61	55	68	61	55	50	47	43	40	34	32	30	22	21	20	15
4	70	60	53	47	62	54	47	43	42	37	34	31	28	25	20	19	17	13
5	64	53	46	40	57	48	41	36	37	33	29	27	24	22	18	17	15	11
6	59	48	40	35	52	43	36	32	34	29	25	25	22	19	17	15	13	10
7	55	43	36	30	48	39	32	28	30	26	22	23	19	17	15	13	12	9
8	51	39	32	27	45	35	29	24	28	23	20	21	17	15	14	12	11	8
9	47	35	28	24	42	32	26	22	25	21	18	19	16	14	13	11	10	7
10	44	32	26	21	39	29	23	19	23	19	16	17	14	12	12	10	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9637	9637	9637	9637
5°	10804	9700	8596	9700
10°	12381	9621	7438	9621
15°	13697	9444	6572	9444
20°	13490	9256	5991	9256
25°	12162	9002	5624	9002
30°	10051	8600	5354	8600
35°	7324	8180	5164	8180
40°	5851	7685	5056	7685
45°	5112	7108	4914	7108
50°	4808	6551	4818	6551
55°	4428	5987	4687	5987
60°	4059	5383	4492	5383
65°	3698	4844	4294	4844
70°	3356	4319	4008	4319
75°	2982	3737	3550	3737
80°	2566	3087	2854	3087
85°	2297	2297	1704	2297



TEST NUMBER: P331484-840

CATALOG NUMBER: S122DIW-S290D1240U840-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.8	1.0
10°-20°	165.3	2.9
20°-30°	239.9	4.2
30°-40°	253.1	4.5
40°-50°	224.1	4.0
50°-60°	178.8	3.2
60°-70°	121.6	2.1
70°-80°	62.3	1.1
80°-90°	21.2	0.4
90°-100°	98.3	1.7
100°-110°	305.4	5.4
110°-120°	522.0	9.2
120°-130°	686.4	12.1
130°-140°	770.4	13.6
140°-150°	755.4	13.3
150°-160°	633.6	11.2
160°-170°	420.3	7.4
170°-180°	146.9	2.6
0°-30°	462.0	8.2
0°-40°	715.1	12.6
0°-60°	1118.0	19.7
0°-90°	1323.1	23.4
90°-120°	925.7	16.3
90°-150°	3138.0	55.4
90°-180°	4339.0	76.6
0°-180°	5661.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	597	597	597	597	597	
5°	667	598	530	598	667	67
15°	819	565	393	565	819	226
25°	683	505	316	505	683	309
35°	372	415	262	415	372	242
45°	224	311	215	311	224	176
55°	157	213	166	213	157	141
65°	97	127	112	127	97	96
75°	48	60	57	60	48	51
85°	12	12	9	12	12	15
90°	44	1	44	1	44	20
95°	81	68	81	68	81	91
105°	291	282	291	282	291	306
115°	524	524	524	524	524	517
125°	765	762	765	762	765	682
135°	998	986	998	986	998	768
145°	1210	1197	1210	1197	1210	756
155°	1379	1368	1379	1368	1379	635
165°	1490	1489	1490	1489	1490	420
175°	1544	1549	1544	1549	1544	147
180°	1552	1552	1552	1552	1552	



TEST NUMBER: P331484-840

CATALOG NUMBER: S122DIW-S290D1240U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9
2.5°	624.4	624.6	625.0	622.1	621.7	621.7	619.1	616.9	614.3	610.9	611.3
5°	666.6	669.1	670.0	667.3	663.2	662.8	658.8	652.5	646.4	641.7	638.2
7.5°	717.0	718.0	715.8	712.2	709.1	703.6	696.3	689.2	679.2	670.1	663.4
10°	755.2	756.6	752.7	747.4	743.1	736.6	726.1	715.3	702.3	689.6	679.5
12.5°	784.2	787.6	782.5	781.9	774.5	765.6	753.1	747.6	729.2	711.7	700.7
15°	819.4	819.2	819.7	815.3	809.8	808.4	795.2	780.6	754.8	744.4	726.5
17.5°	809.2	812.7	814.4	814.3	814.2	813.2	809.0	799.9	786.9	770.1	749.5
20°	785.1	789.6	790.3	795.6	798.6	802.4	804.1	801.5	793.6	779.5	761.6
22.5°	747.6	748.9	751.0	759.2	765.7	775.5	780.5	789.1	786.0	779.1	764.2
25°	682.7	680.4	688.4	692.6	707.5	723.1	734.4	746.7	757.7	764.4	760.0
27.5°	604.8	601.4	613.4	624.4	636.4	653.4	670.9	691.6	708.7	730.3	737.7
30°	539.1	541.2	552.6	564.3	582.7	606.5	626.3	648.9	673.6	697.6	714.4
32.5°	468.3	476.2	483.4	501.4	517.6	544.1	573.1	601.5	632.1	659.4	685.4
35°	371.6	380.8	390.9	403.9	426.7	453.0	481.3	519.6	561.4	598.7	629.4
37.5°	312.9	311.3	317.1	326.6	345.0	366.3	398.8	436.6	485.7	529.7	573.1
40°	277.6	276.7	280.7	289.5	303.5	319.1	347.6	380.8	426.5	480.2	531.8
42.5°	253.4	253.9	256.2	262.4	272.0	284.8	306.1	334.4	376.2	426.8	482.2
45°	223.9	225.5	228.0	231.1	236.5	247.1	259.0	279.2	312.3	354.5	409.0
47.5°	202.7	202.8	205.3	207.9	211.2	217.1	226.9	239.5	262.9	297.2	344.2
50°	191.4	189.8	191.6	193.6	197.0	201.2	207.6	219.5	235.1	262.9	302.2
52.5°	177.3	177.4	179.0	179.9	182.9	187.0	192.9	201.2	215.3	237.0	269.2
55°	157.3	158.5	159.5	160.8	163.6	166.5	171.2	176.6	187.6	203.9	227.8
57.5°	138.6	139.0	139.9	142.5	144.2	146.9	151.3	156.3	163.5	175.5	193.5
60°	125.7	125.7	127.5	128.7	131.0	133.7	137.1	142.0	148.5	158.2	172.8
62.5°	114.0	113.8	114.5	116.4	118.2	120.7	124.1	128.3	134.3	143.1	154.9
65°	96.8	96.3	97.8	98.2	100.0	102.5	105.3	109.7	114.5	120.9	131.5
67.5°	80.3	80.9	81.6	82.4	83.4	86.1	88.0	91.0	95.1	100.5	107.6
70°	71.1	71.1	71.1	71.8	73.2	74.5	76.3	78.9	82.8	87.4	93.8
72.5°	60.8	61.6	62.3	61.9	63.6	64.4	66.7	68.1	71.8	74.7	80.4
75°	47.8	47.8	47.8	48.9	49.6	50.2	51.6	53.0	54.8	58.5	61.5
77.5°	35.6	35.5	35.7	36.1	36.8	37.6	38.0	39.2	40.9	42.6	45.1
80°	27.6	28.0	28.2	28.7	28.7	29.1	29.4	31.0	32.1	33.2	34.8
82.5°	21.3	21.4	21.4	21.5	21.7	22.0	22.6	23.1	23.5	24.4	25.7
85°	12.4	12.1	12.1	12.6	12.4	12.4	12.8	13.3	13.3	13.5	14.2
87.5°	13.6	13.6	13.7	13.5	13.4	13.6	13.7	13.7	14.0	14.3	13.2
90°	44.5	44.2	43.9	43.6	43.3	43.5	44.1	44.6	45.2	45.8	39.4
92.5°	42.4	42.4	42.3	42.2	42.2	42.1	42.0	41.9	41.7	41.6	40.1
95°	81.2	81.8	82.3	82.9	83.5	83.8	83.8	83.8	83.8	83.8	83.2
97.5°	140.7	140.7	140.8	140.8	140.9	140.9	140.9	140.9	140.9	140.9	139.8
100°	179.4	179.7	180.0	180.3	180.6	180.7	180.7	180.7	180.7	180.7	179.9
102.5°	223.4	223.7	224.0	224.3	224.6	224.6	224.4	224.1	223.9	223.7	222.6
105°	290.7	290.7	290.7	290.7	290.7	290.4	289.8	289.2	288.6	288.1	287.5
107.5°	354.1	355.4	356.8	358.1	359.4	360.0	359.7	359.5	359.3	359.0	359.0
110°	403.3	404.1	405.1	406.0	406.8	407.3	407.3	407.3	407.3	407.3	407.3



TEST NUMBER: P331484-840

CATALOG NUMBER: S122DIW-S290D1240U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	450.4	451.1	451.7	452.3	453.0	453.6	454.3	455.0	455.8	456.5	456.7
115°	523.8	524.6	525.5	526.4	527.3	527.9	528.2	528.5	528.8	529.0	529.6
117.5°	593.7	594.6	595.4	596.3	597.2	597.9	598.6	599.4	600.1	600.8	602.4
120°	643.0	643.8	644.7	645.5	646.4	646.8	646.8	646.8	646.8	646.8	649.1
122.5°	691.2	691.8	692.4	693.1	693.7	694.4	695.1	695.8	696.4	697.1	698.7
125°	764.7	765.0	765.3	765.6	765.9	766.5	767.3	768.2	769.1	769.9	770.8
127.5°	831.7	832.7	833.6	834.6	835.5	836.5	837.5	838.6	839.6	840.6	841.7
130°	879.9	881.1	882.3	883.4	884.6	885.4	886.1	886.7	887.2	887.8	888.4
132.5°	926.0	927.0	927.9	928.9	929.8	930.9	932.1	933.4	934.7	935.9	935.8
135°	997.7	998.7	999.6	1000.4	1001.3	1001.9	1002.2	1002.5	1002.7	1003.0	1002.5
137.5°	1062.8	1063.9	1065.1	1066.2	1067.4	1068.1	1068.3	1068.5	1068.8	1069.0	1068.2
140°	1107.8	1108.9	1110.1	1111.3	1112.5	1113.0	1113.0	1113.0	1113.0	1113.0	1111.6
142.5°	1148.6	1149.8	1150.9	1152.2	1153.3	1153.8	1153.6	1153.3	1153.1	1152.9	1151.9
145°	1209.9	1211.1	1212.2	1213.5	1214.6	1215.0	1214.8	1214.5	1214.2	1213.9	1212.1
147.5°	1264.7	1265.8	1266.9	1268.0	1269.1	1269.3	1268.7	1268.0	1267.4	1266.8	1265.6
150°	1300.3	1301.1	1302.0	1302.9	1303.7	1303.7	1302.9	1302.0	1301.1	1300.3	1299.1
152.5°	1333.8	1334.9	1336.1	1337.1	1338.2	1338.2	1337.1	1336.1	1334.9	1333.8	1332.4
155°	1378.9	1379.7	1380.6	1381.5	1382.3	1382.0	1380.6	1379.2	1377.7	1376.2	1375.3
157.5°	1417.5	1419.0	1420.4	1421.8	1423.2	1422.9	1420.9	1419.0	1416.9	1415.0	1414.4
160°	1441.7	1442.9	1444.0	1445.2	1446.3	1446.0	1444.3	1442.6	1440.8	1439.1	1438.8
162.5°	1462.7	1464.0	1465.4	1466.8	1468.2	1467.9	1465.9	1464.0	1462.0	1460.1	1459.8
165°	1490.2	1491.6	1493.1	1494.5	1495.9	1495.7	1493.6	1491.6	1489.6	1487.5	1487.5
167.5°	1512.7	1514.2	1515.7	1517.2	1518.7	1518.4	1516.4	1514.4	1512.4	1510.3	1510.4
170°	1524.2	1525.9	1527.7	1529.4	1531.2	1531.1	1528.9	1526.9	1524.9	1522.9	1523.2
172.5°	1533.6	1535.4	1537.1	1538.8	1540.5	1540.4	1538.4	1536.4	1534.4	1532.3	1532.6
175°	1543.8	1545.6	1547.3	1549.0	1550.8	1550.6	1548.6	1546.6	1544.6	1542.5	1543.1
177.5°	1548.5	1549.9	1551.4	1552.8	1554.1	1554.1	1552.8	1551.4	1549.9	1548.5	1549.0
180°	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7



TEST NUMBER: P331484-840

CATALOG NUMBER: S122DIW-S290D1240U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9
2.5°	612.5	611.1	610.2	606.8	603.9	601.0	600.1	600.4	596.3	592.5	590.9
5°	636.4	631.8	627.4	621.3	613.9	605.8	601.8	598.5	590.5	581.8	576.7
7.5°	657.7	651.2	642.8	631.2	620.5	607.8	599.8	592.7	581.0	568.7	561.1
10°	670.8	661.9	651.1	636.8	623.8	608.3	597.6	586.8	573.1	558.4	549.2
12.5°	682.0	669.9	659.3	641.1	625.6	606.3	593.6	578.3	563.9	546.4	537.5
15°	708.6	686.4	666.2	645.5	626.5	599.7	585.4	565.0	546.0	524.4	514.1
17.5°	729.2	704.2	672.5	646.2	624.0	594.2	573.4	549.0	526.4	501.8	487.8
20°	740.9	712.3	678.1	646.9	620.4	586.3	563.6	538.7	512.3	484.5	469.4
22.5°	747.9	717.8	684.0	644.2	613.0	580.0	551.4	523.9	497.3	467.3	451.4
25°	750.1	722.7	686.8	641.9	603.8	566.4	532.0	505.3	473.0	445.0	421.9
27.5°	739.2	719.5	685.1	637.5	593.2	549.5	511.1	481.0	446.9	416.5	393.1
30°	725.8	714.4	680.9	633.2	584.7	537.8	495.5	461.3	427.4	396.7	372.7
32.5°	705.1	702.7	673.2	626.9	575.7	522.9	479.2	444.6	407.0	376.8	354.1
35°	664.4	675.4	656.8	613.0	558.9	501.7	454.4	415.0	376.0	347.1	325.8
37.5°	609.8	637.1	632.3	592.6	535.9	478.7	426.5	385.3	348.1	318.9	298.0
40°	572.1	607.0	612.1	576.9	519.9	460.9	405.6	364.6	328.3	301.6	280.5
42.5°	531.8	572.5	586.3	558.3	502.2	442.1	386.9	344.4	308.4	282.6	263.9
45°	464.1	518.0	543.0	526.9	472.8	411.3	354.5	311.3	278.7	254.4	239.9
47.5°	400.8	459.7	493.3	487.7	440.1	379.2	323.0	281.6	249.8	230.5	217.5
50°	356.1	416.6	457.2	459.1	416.6	356.3	299.8	260.8	231.7	213.6	203.0
52.5°	317.1	375.0	419.2	429.0	390.3	332.4	279.1	240.2	214.6	197.9	188.5
55°	266.3	315.2	364.3	382.2	351.2	296.2	246.8	212.7	188.5	177.1	168.8
57.5°	221.5	262.2	307.5	327.3	308.2	261.1	214.8	185.1	165.6	155.5	149.2
60°	197.7	229.8	270.2	293.9	277.3	235.4	195.0	166.7	150.7	141.8	135.8
62.5°	175.7	204.2	238.3	259.9	251.0	211.4	175.2	150.3	136.4	128.1	123.7
65°	145.0	167.4	193.9	213.8	207.8	177.8	148.1	126.8	115.8	109.2	105.7
67.5°	119.4	135.6	153.9	171.4	166.6	145.3	121.6	104.9	96.7	91.0	88.9
70°	103.2	115.6	131.9	145.9	142.0	124.6	105.7	91.5	84.4	79.6	77.6
72.5°	87.9	98.0	110.5	121.9	119.3	104.7	89.1	78.4	72.8	68.4	66.8
75°	66.3	74.1	81.7	89.3	88.6	77.4	68.2	59.9	55.5	52.1	51.4
77.5°	49.0	53.3	58.5	62.9	61.7	55.2	48.1	43.3	40.2	37.9	37.5
80°	37.4	39.9	43.6	46.8	45.2	42.4	36.7	33.2	31.0	28.7	27.8
82.5°	27.2	29.6	31.8	33.6	32.3	29.8	26.3	23.9	22.5	21.0	20.6
85°	14.2	15.6	16.6	17.0	16.6	14.9	13.3	12.4	11.2	10.5	10.3
87.5°	12.1	10.8	9.6	8.9	7.7	7.0	5.6	4.3	4.8	5.4	5.7
90°	33.0	26.7	20.2	15.2	11.8	8.3	4.8	1.3	4.8	8.3	11.8
92.5°	38.6	37.1	35.5	33.5	31.0	28.5	25.9	23.3	25.9	28.5	31.0
95°	82.6	82.1	81.5	79.8	76.9	73.9	71.0	68.1	71.0	73.9	76.9
97.5°	138.7	137.5	136.4	134.6	132.1	129.6	126.9	124.4	126.9	129.6	132.1
100°	178.9	178.0	177.2	175.6	173.3	171.0	168.6	166.3	168.6	171.0	173.3
102.5°	221.5	220.4	219.2	217.7	215.9	214.0	212.2	210.3	212.2	214.0	215.9
105°	286.9	286.3	285.8	285.0	284.2	283.3	282.4	281.6	282.4	283.3	284.2
107.5°	359.0	359.0	359.0	358.4	357.1	355.9	354.6	353.3	354.6	355.9	357.1
110°	407.3	407.3	407.3	406.4	404.7	402.8	401.1	399.4	401.1	402.8	404.7



TEST NUMBER: P331484-840

CATALOG NUMBER: S122DIW-S290D1240U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	457.0	457.2	457.4	456.7	454.9	453.1	451.4	449.7	451.4	453.1	454.9
115°	530.2	530.8	531.3	530.8	529.0	527.3	525.5	523.8	525.5	527.3	529.0
117.5°	604.0	605.6	607.3	606.9	604.6	602.3	600.0	597.6	600.0	602.3	604.6
120°	651.6	653.9	656.2	656.2	653.9	651.6	649.1	646.8	649.1	651.6	653.9
122.5°	700.4	702.1	703.7	703.1	700.2	697.5	694.7	691.9	694.7	697.5	700.2
125°	771.7	772.5	773.5	772.5	769.9	767.3	764.7	762.0	764.7	767.3	769.9
127.5°	842.7	843.8	844.9	843.7	840.4	837.1	833.7	830.4	833.7	837.1	840.4
130°	889.0	889.6	890.1	888.5	884.7	881.0	877.2	873.4	877.2	881.0	884.7
132.5°	935.7	935.6	935.5	933.9	930.8	927.8	924.6	921.6	924.6	927.8	930.8
135°	1001.9	1001.3	1000.7	998.9	995.6	992.4	989.2	986.0	989.2	992.4	995.6
137.5°	1067.5	1066.7	1066.0	1064.3	1061.7	1059.0	1056.4	1053.8	1056.4	1059.0	1061.7
140°	1110.1	1108.6	1107.2	1105.2	1102.6	1099.9	1097.3	1094.7	1097.3	1099.9	1102.6
142.5°	1150.8	1149.8	1148.8	1147.1	1144.5	1141.9	1139.2	1136.6	1139.2	1141.9	1144.5
145°	1210.3	1208.6	1206.9	1205.0	1203.0	1200.9	1198.9	1196.8	1198.9	1200.9	1203.0
147.5°	1264.5	1263.2	1262.1	1260.3	1257.9	1255.4	1252.9	1250.5	1252.9	1255.4	1257.9
150°	1298.0	1296.8	1295.7	1294.1	1292.4	1290.7	1288.9	1287.2	1288.9	1290.7	1292.4
152.5°	1331.0	1329.6	1328.2	1326.7	1324.8	1323.1	1321.4	1319.7	1321.4	1323.1	1324.8
155°	1374.4	1373.6	1372.7	1371.9	1371.0	1370.1	1369.3	1368.4	1369.3	1370.1	1371.0
157.5°	1413.9	1413.4	1412.9	1412.3	1411.8	1411.2	1410.6	1410.0	1410.6	1411.2	1411.8
160°	1438.5	1438.1	1437.9	1437.4	1436.9	1436.3	1435.7	1435.1	1435.7	1436.3	1436.9
162.5°	1459.5	1459.2	1458.9	1458.6	1458.5	1458.4	1458.3	1458.1	1458.3	1458.4	1458.5
165°	1487.5	1487.5	1487.5	1487.6	1487.9	1488.2	1488.5	1488.8	1488.5	1488.2	1487.9
167.5°	1510.5	1510.5	1510.6	1511.0	1511.9	1512.8	1513.6	1514.5	1513.6	1512.8	1511.9
170°	1523.5	1523.8	1524.1	1524.6	1525.5	1526.4	1527.2	1528.1	1527.2	1526.4	1525.5
172.5°	1532.9	1533.2	1533.5	1534.1	1534.9	1535.8	1536.7	1537.5	1536.7	1535.8	1534.9
175°	1543.7	1544.3	1544.9	1545.6	1546.4	1547.3	1548.2	1549.0	1548.2	1547.3	1546.4
177.5°	1549.4	1549.9	1550.4	1551.0	1551.7	1552.4	1553.1	1553.8	1553.1	1552.4	1551.7
180°	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7



TEST NUMBER: P331484-840

CATALOG NUMBER: S122DIW-S290D1240U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9
2.5°	589.1	587.9	584.1	582.1	578.8	575.6	573.6	574.5	575.2	574.9	574.3
5°	572.1	567.7	561.1	555.4	551.3	543.7	540.5	538.9	537.5	535.9	534.3
7.5°	552.0	545.1	535.6	527.5	519.8	510.3	504.9	501.8	498.5	494.8	491.6
10°	537.8	528.1	518.0	506.5	497.4	488.9	481.3	476.3	471.6	467.3	464.1
12.5°	522.7	511.6	499.1	483.4	473.3	461.1	460.0	451.1	443.9	441.2	437.5
15°	498.8	483.1	467.3	448.7	440.7	429.7	422.8	415.9	409.7	405.4	404.2
17.5°	471.5	451.3	435.6	422.2	409.1	397.8	391.4	386.0	380.8	375.1	374.3
20°	450.8	433.3	416.2	404.5	390.9	379.4	371.6	366.2	361.7	358.3	355.4
22.5°	431.1	412.0	396.3	383.5	370.2	360.9	354.8	349.4	345.8	342.0	339.2
25°	399.6	384.8	367.5	353.0	342.0	336.1	331.0	326.5	324.2	321.6	318.4
27.5°	372.0	355.5	339.4	328.2	318.5	313.3	309.6	306.5	304.4	302.9	301.0
30°	352.6	335.9	323.3	312.3	304.2	298.9	296.6	294.8	292.3	291.3	290.4
32.5°	333.9	318.8	308.0	298.4	290.8	287.3	285.3	283.6	281.7	280.7	278.8
35°	307.4	294.8	284.3	278.9	272.8	269.7	268.2	265.9	264.1	263.2	262.9
37.5°	282.5	271.6	264.6	257.8	255.2	253.4	251.2	249.6	249.0	248.9	248.6
40°	266.3	257.4	251.2	245.7	244.6	241.8	239.9	238.6	238.6	238.8	238.6
42.5°	251.7	243.6	238.1	233.4	232.1	230.5	228.5	228.5	228.8	229.6	228.8
45°	229.4	223.7	219.7	217.5	215.0	213.4	213.1	213.8	214.0	214.3	215.0
47.5°	208.9	205.1	201.6	199.0	197.9	197.7	197.4	198.6	199.8	200.2	201.2
50°	196.8	192.5	189.5	187.8	186.9	186.5	186.9	188.3	189.2	190.4	191.1
52.5°	183.3	180.2	178.1	176.8	176.5	176.8	176.8	178.4	179.9	180.4	180.7
55°	164.5	162.2	161.8	159.7	160.6	160.4	161.5	162.4	163.8	165.2	165.4
57.5°	145.7	143.9	142.7	142.9	143.2	144.2	145.1	146.7	148.1	149.7	149.8
60°	133.3	132.4	131.7	131.7	132.1	133.5	134.6	136.2	137.1	138.1	138.8
62.5°	121.9	121.0	120.3	120.7	121.9	122.7	124.0	124.9	125.8	126.7	127.0
65°	103.9	103.5	104.1	104.6	104.8	105.9	107.6	108.3	109.2	109.7	111.3
67.5°	87.4	87.5	87.4	88.0	89.4	89.6	91.1	92.7	92.9	93.8	94.8
70°	76.1	76.6	77.1	77.6	78.7	79.2	80.3	81.0	81.9	82.6	83.3
72.5°	65.8	65.9	66.4	66.3	67.4	68.3	69.3	70.0	70.9	71.8	72.4
75°	50.7	50.7	51.2	51.4	52.5	53.7	53.4	53.9	54.8	55.7	56.2
77.5°	37.1	36.6	37.1	37.3	37.7	38.6	38.8	39.4	40.5	40.2	40.7
80°	28.2	27.6	28.2	28.5	28.5	29.6	29.6	30.1	30.7	30.1	30.7
82.5°	20.1	19.8	20.3	20.4	20.7	20.8	21.1	21.2	21.9	21.6	21.9
85°	10.1	9.9	10.1	9.9	10.1	10.3	10.3	10.1	10.1	10.5	9.9
87.5°	6.2	7.0	8.1	9.4	10.5	11.5	11.2	11.1	11.0	10.5	10.5
90°	15.2	20.2	26.7	33.0	39.4	45.8	45.2	44.6	44.1	43.5	43.3
92.5°	33.5	35.5	37.1	38.6	40.1	41.6	41.7	41.9	42.0	42.1	42.2
95°	79.8	81.5	82.1	82.6	83.2	83.8	83.8	83.8	83.8	83.8	83.5
97.5°	134.6	136.4	137.5	138.7	139.8	140.9	140.9	140.9	140.9	140.9	140.9
100°	175.6	177.2	178.0	178.9	179.9	180.7	180.7	180.7	180.7	180.7	180.6
102.5°	217.7	219.2	220.4	221.5	222.6	223.7	223.9	224.1	224.4	224.6	224.6
105°	285.0	285.8	286.3	286.9	287.5	288.1	288.6	289.2	289.8	290.4	290.7
107.5°	358.4	359.0	359.0	359.0	359.0	359.0	359.3	359.5	359.7	360.0	359.4
110°	406.4	407.3	407.3	407.3	407.3	407.3	407.3	407.3	407.3	407.3	406.8



TEST NUMBER: P331484-840

CATALOG NUMBER: S122DIW-S290D1240U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	456.7	457.4	457.2	457.0	456.7	456.5	455.8	455.0	454.3	453.6	453.0
115°	530.8	531.3	530.8	530.2	529.6	529.0	528.8	528.5	528.2	527.9	527.3
117.5°	606.9	607.3	605.6	604.0	602.4	600.8	600.1	599.4	598.6	597.9	597.2
120°	656.2	656.2	653.9	651.6	649.1	646.8	646.8	646.8	646.8	646.8	646.4
122.5°	703.1	703.7	702.1	700.4	698.7	697.1	696.4	695.8	695.1	694.4	693.7
125°	772.5	773.5	772.5	771.7	770.8	769.9	769.1	768.2	767.3	766.5	765.9
127.5°	843.7	844.9	843.8	842.7	841.7	840.6	839.6	838.6	837.5	836.5	835.5
130°	888.5	890.1	889.6	889.0	888.4	887.8	887.2	886.7	886.1	885.4	884.6
132.5°	933.9	935.5	935.6	935.7	935.8	935.9	934.7	933.4	932.1	930.9	929.8
135°	998.9	1000.7	1001.3	1001.9	1002.5	1003.0	1002.7	1002.5	1002.2	1001.9	1001.3
137.5°	1064.3	1066.0	1066.7	1067.5	1068.2	1069.0	1068.8	1068.5	1068.3	1068.1	1067.4
140°	1105.2	1107.2	1108.6	1110.1	1111.6	1113.0	1113.0	1113.0	1113.0	1113.0	1112.5
142.5°	1147.1	1148.8	1149.8	1150.8	1151.9	1152.9	1153.1	1153.3	1153.6	1153.8	1153.3
145°	1205.0	1206.9	1208.6	1210.3	1212.1	1213.9	1214.2	1214.5	1214.8	1215.0	1214.6
147.5°	1260.3	1262.1	1263.2	1264.5	1265.6	1266.8	1267.4	1268.0	1268.7	1269.3	1269.1
150°	1294.1	1295.7	1296.8	1298.0	1299.1	1300.3	1301.1	1302.0	1302.9	1303.7	1303.7
152.5°	1326.7	1328.2	1329.6	1331.0	1332.4	1333.8	1334.9	1336.1	1337.1	1338.2	1338.2
155°	1371.9	1372.7	1373.6	1374.4	1375.3	1376.2	1377.7	1379.2	1380.6	1382.0	1382.3
157.5°	1412.3	1412.9	1413.4	1413.9	1414.4	1415.0	1416.9	1419.0	1420.9	1422.9	1423.2
160°	1437.4	1437.9	1438.1	1438.5	1438.8	1439.1	1440.8	1442.6	1444.3	1446.0	1446.3
162.5°	1458.6	1458.9	1459.2	1459.5	1459.8	1460.1	1462.0	1464.0	1465.9	1467.9	1468.2
165°	1487.6	1487.5	1487.5	1487.5	1487.5	1487.5	1489.6	1491.6	1493.6	1495.7	1495.9
167.5°	1511.0	1510.6	1510.5	1510.5	1510.4	1510.3	1512.4	1514.4	1516.4	1518.4	1518.7
170°	1524.6	1524.1	1523.8	1523.5	1523.2	1522.9	1524.9	1526.9	1528.9	1531.1	1531.2
172.5°	1534.1	1533.5	1533.2	1532.9	1532.6	1532.3	1534.4	1536.4	1538.4	1540.4	1540.5
175°	1545.6	1544.9	1544.3	1543.7	1543.1	1542.5	1544.6	1546.6	1548.6	1550.6	1550.8
177.5°	1551.0	1550.4	1549.9	1549.4	1549.0	1548.5	1549.9	1551.4	1552.8	1554.1	1554.1
180°	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7



TEST NUMBER: P331484-840

CATALOG NUMBER: S122DIW-S290D1240U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9
2.5°	572.5	572.1	572.1	570.5	572.1	572.1	572.5	574.3	574.9	575.2	574.5
5°	531.1	530.4	529.3	530.4	529.3	530.4	531.1	534.3	535.9	537.5	538.9
7.5°	490.1	487.4	487.0	484.2	487.0	487.4	490.1	491.6	494.8	498.5	501.8
10°	460.2	458.4	458.1	453.7	458.1	458.4	460.2	464.1	467.3	471.6	476.3
12.5°	437.5	433.0	433.9	431.4	433.9	433.0	437.5	437.5	441.2	443.9	451.1
15°	398.0	398.0	397.1	393.2	397.1	398.0	398.0	404.2	405.4	409.7	415.9
17.5°	369.7	369.2	367.1	368.2	367.1	369.2	369.7	374.3	375.1	380.8	386.0
20°	352.8	351.4	348.7	348.7	348.7	351.4	352.8	355.4	358.3	361.7	366.2
22.5°	336.9	336.8	333.9	334.8	333.9	336.8	336.9	339.2	342.0	345.8	349.4
25°	318.2	316.4	315.0	315.7	315.0	316.4	318.2	318.4	321.6	324.2	326.5
27.5°	300.4	299.4	299.3	297.5	299.3	299.4	300.4	301.0	302.9	304.4	306.5
30°	290.2	287.9	288.3	287.2	288.3	287.9	290.2	290.4	291.3	292.3	294.8
32.5°	278.4	277.6	277.2	276.2	277.2	277.6	278.4	278.8	280.7	281.7	283.6
35°	262.5	262.7	261.6	262.0	261.6	262.7	262.5	262.9	263.2	264.1	265.9
37.5°	248.4	249.1	248.6	248.7	248.6	249.1	248.4	248.6	248.9	249.0	249.6
40°	239.2	239.2	239.2	239.9	239.2	239.2	239.2	238.6	238.8	238.6	238.6
42.5°	230.5	230.0	229.7	229.6	229.7	230.0	230.5	228.8	229.6	228.8	228.5
45°	215.4	216.1	216.3	215.2	216.3	216.1	215.4	215.0	214.3	214.0	213.8
47.5°	201.8	201.9	201.8	202.8	201.8	201.9	201.8	201.2	200.2	199.8	198.6
50°	192.3	191.8	192.3	191.8	192.3	191.8	192.3	191.1	190.4	189.2	188.3
52.5°	182.2	182.3	182.0	181.9	182.0	182.3	182.2	180.7	180.4	179.9	178.4
55°	166.3	166.7	166.5	166.5	166.5	166.7	166.3	165.4	165.2	163.8	162.4
57.5°	150.0	150.4	150.7	149.7	150.7	150.4	150.0	149.8	149.7	148.1	146.7
60°	138.6	139.7	139.5	139.1	139.5	139.7	138.6	138.8	138.1	137.1	136.2
62.5°	128.1	128.6	128.5	128.4	128.5	128.6	128.1	127.0	126.7	125.8	124.9
65°	112.0	112.4	111.7	112.4	111.7	112.4	112.0	111.3	109.7	109.2	108.3
67.5°	94.5	94.7	95.2	95.5	95.2	94.7	94.5	94.8	93.8	92.9	92.7
70°	83.7	83.5	84.2	84.9	84.2	83.5	83.7	83.3	82.6	81.9	81.0
72.5°	72.3	72.8	72.6	73.1	72.6	72.8	72.3	72.4	71.8	70.9	70.0
75°	55.7	56.5	56.2	56.9	56.2	56.5	55.7	56.2	55.7	54.8	53.9
77.5°	40.3	40.4	40.3	40.7	40.3	40.4	40.3	40.7	40.2	40.5	39.4
80°	30.7	30.3	29.8	30.7	29.8	30.3	30.7	30.7	30.1	30.7	30.1
82.5°	21.4	21.6	21.2	21.2	21.2	21.6	21.4	21.9	21.6	21.9	21.2
85°	9.9	9.6	9.2	9.2	9.2	9.6	9.9	9.9	10.5	10.1	10.1
87.5°	10.6	10.4	10.5	10.4	10.5	10.4	10.6	10.5	10.5	11.0	11.1
90°	43.6	43.9	44.2	44.5	44.2	43.9	43.6	43.3	43.5	44.1	44.6
92.5°	42.2	42.3	42.4	42.4	42.4	42.3	42.2	42.2	42.1	42.0	41.9
95°	82.9	82.3	81.8	81.2	81.8	82.3	82.9	83.5	83.8	83.8	83.8
97.5°	140.8	140.8	140.7	140.7	140.7	140.8	140.8	140.9	140.9	140.9	140.9
100°	180.3	180.0	179.7	179.4	179.7	180.0	180.3	180.6	180.7	180.7	180.7
102.5°	224.3	224.0	223.7	223.4	223.7	224.0	224.3	224.6	224.6	224.4	224.1
105°	290.7	290.7	290.7	290.7	290.7	290.7	290.7	290.7	290.4	289.8	289.2
107.5°	358.1	356.8	355.4	354.1	355.4	356.8	358.1	359.4	360.0	359.7	359.5
110°	406.0	405.1	404.1	403.3	404.1	405.1	406.0	406.8	407.3	407.3	407.3



TEST NUMBER: P331484-840

CATALOG NUMBER: S122DIW-S290D1240U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	452.3	451.7	451.1	450.4	451.1	451.7	452.3	453.0	453.6	454.3	455.0
115°	526.4	525.5	524.6	523.8	524.6	525.5	526.4	527.3	527.9	528.2	528.5
117.5°	596.3	595.4	594.6	593.7	594.6	595.4	596.3	597.2	597.9	598.6	599.4
120°	645.5	644.7	643.8	643.0	643.8	644.7	645.5	646.4	646.8	646.8	646.8
122.5°	693.1	692.4	691.8	691.2	691.8	692.4	693.1	693.7	694.4	695.1	695.8
125°	765.6	765.3	765.0	764.7	765.0	765.3	765.6	765.9	766.5	767.3	768.2
127.5°	834.6	833.6	832.7	831.7	832.7	833.6	834.6	835.5	836.5	837.5	838.6
130°	883.4	882.3	881.1	879.9	881.1	882.3	883.4	884.6	885.4	886.1	886.7
132.5°	928.9	927.9	927.0	926.0	927.0	927.9	928.9	929.8	930.9	932.1	933.4
135°	1000.4	999.6	998.7	997.7	998.7	999.6	1000.4	1001.3	1001.9	1002.2	1002.5
137.5°	1066.2	1065.1	1063.9	1062.8	1063.9	1065.1	1066.2	1067.4	1068.1	1068.3	1068.5
140°	1111.3	1110.1	1108.9	1107.8	1108.9	1110.1	1111.3	1112.5	1113.0	1113.0	1113.0
142.5°	1152.2	1150.9	1149.8	1148.6	1149.8	1150.9	1152.2	1153.3	1153.8	1153.6	1153.3
145°	1213.5	1212.2	1211.1	1209.9	1211.1	1212.2	1213.5	1214.6	1215.0	1214.8	1214.5
147.5°	1268.0	1266.9	1265.8	1264.7	1265.8	1266.9	1268.0	1269.1	1269.3	1268.7	1268.0
150°	1302.9	1302.0	1301.1	1300.3	1301.1	1302.0	1302.9	1303.7	1303.7	1302.9	1302.0
152.5°	1337.1	1336.1	1334.9	1333.8	1334.9	1336.1	1337.1	1338.2	1338.2	1337.1	1336.1
155°	1381.5	1380.6	1379.7	1378.9	1379.7	1380.6	1381.5	1382.3	1382.0	1380.6	1379.2
157.5°	1421.8	1420.4	1419.0	1417.5	1419.0	1420.4	1421.8	1423.2	1422.9	1420.9	1419.0
160°	1445.2	1444.0	1442.9	1441.7	1442.9	1444.0	1445.2	1446.3	1446.0	1444.3	1442.6
162.5°	1466.8	1465.4	1464.0	1462.7	1464.0	1465.4	1466.8	1468.2	1467.9	1465.9	1464.0
165°	1494.5	1493.1	1491.6	1490.2	1491.6	1493.1	1494.5	1495.9	1495.7	1493.6	1491.6
167.5°	1517.2	1515.7	1514.2	1512.7	1514.2	1515.7	1517.2	1518.7	1518.4	1516.4	1514.4
170°	1529.4	1527.7	1525.9	1524.2	1525.9	1527.7	1529.4	1531.2	1531.1	1528.9	1526.9
172.5°	1538.8	1537.1	1535.4	1533.6	1535.4	1537.1	1538.8	1540.5	1540.4	1538.4	1536.4
175°	1549.0	1547.3	1545.6	1543.8	1545.6	1547.3	1549.0	1550.8	1550.6	1548.6	1546.6
177.5°	1552.8	1551.4	1549.9	1548.5	1549.9	1551.4	1552.8	1554.1	1554.1	1552.8	1551.4
180°	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7



TEST NUMBER: P331484-840

CATALOG NUMBER: S122DIW-S290D1240U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9
2.5°	573.6	575.6	578.8	582.1	584.1	587.9	589.1	590.9	592.5	596.3	600.4
5°	540.5	543.7	551.3	555.4	561.1	567.7	572.1	576.7	581.8	590.5	598.5
7.5°	504.9	510.3	519.8	527.5	535.6	545.1	552.0	561.1	568.7	581.0	592.7
10°	481.3	488.9	497.4	506.5	518.0	528.1	537.8	549.2	558.4	573.1	586.8
12.5°	460.0	461.1	473.3	483.4	499.1	511.6	522.7	537.5	546.4	563.9	578.3
15°	422.8	429.7	440.7	448.7	467.3	483.1	498.8	514.1	524.4	546.0	565.0
17.5°	391.4	397.8	409.1	422.2	435.6	451.3	471.5	487.8	501.8	526.4	549.0
20°	371.6	379.4	390.9	404.5	416.2	433.3	450.8	469.4	484.5	512.3	538.7
22.5°	354.8	360.9	370.2	383.5	396.3	412.0	431.1	451.4	467.3	497.3	523.9
25°	331.0	336.1	342.0	353.0	367.5	384.8	399.6	421.9	445.0	473.0	505.3
27.5°	309.6	313.3	318.5	328.2	339.4	355.5	372.0	393.1	416.5	446.9	481.0
30°	296.6	298.9	304.2	312.3	323.3	335.9	352.6	372.7	396.7	427.4	461.3
32.5°	285.3	287.3	290.8	298.4	308.0	318.8	333.9	354.1	376.8	407.0	444.6
35°	268.2	269.7	272.8	278.9	284.3	294.8	307.4	325.8	347.1	376.0	415.0
37.5°	251.2	253.4	255.2	257.8	264.6	271.6	282.5	298.0	318.9	348.1	385.3
40°	239.9	241.8	244.6	245.7	251.2	257.4	266.3	280.5	301.6	328.3	364.6
42.5°	228.5	230.5	232.1	233.4	238.1	243.6	251.7	263.9	282.6	308.4	344.4
45°	213.1	213.4	215.0	217.5	219.7	223.7	229.4	239.9	254.4	278.7	311.3
47.5°	197.4	197.7	197.9	199.0	201.6	205.1	208.9	217.5	230.5	249.8	281.6
50°	186.9	186.5	186.9	187.8	189.5	192.5	196.8	203.0	213.6	231.7	260.8
52.5°	176.8	176.8	176.5	176.8	178.1	180.2	183.3	188.5	197.9	214.6	240.2
55°	161.5	160.4	160.6	159.7	161.8	162.2	164.5	168.8	177.1	188.5	212.7
57.5°	145.1	144.2	143.2	142.9	142.7	143.9	145.7	149.2	155.5	165.6	185.1
60°	134.6	133.5	132.1	131.7	131.7	132.4	133.3	135.8	141.8	150.7	166.7
62.5°	124.0	122.7	121.9	120.7	120.3	121.0	121.9	123.7	128.1	136.4	150.3
65°	107.6	105.9	104.8	104.6	104.1	103.5	103.9	105.7	109.2	115.8	126.8
67.5°	91.1	89.6	89.4	88.0	87.4	87.5	87.4	88.9	91.0	96.7	104.9
70°	80.3	79.2	78.7	77.6	77.1	76.6	76.1	77.6	79.6	84.4	91.5
72.5°	69.3	68.3	67.4	66.3	66.4	65.9	65.8	66.8	68.4	72.8	78.4
75°	53.4	53.7	52.5	51.4	51.2	50.7	50.7	51.4	52.1	55.5	59.9
77.5°	38.8	38.6	37.7	37.3	37.1	36.6	37.1	37.5	37.9	40.2	43.3
80°	29.6	29.6	28.5	28.5	28.2	27.6	28.2	27.8	28.7	31.0	33.2
82.5°	21.1	20.8	20.7	20.4	20.3	19.8	20.1	20.6	21.0	22.5	23.9
85°	10.3	10.3	10.1	9.9	10.1	9.9	10.1	10.3	10.5	11.2	12.4
87.5°	11.2	11.5	10.5	9.4	8.1	7.0	6.2	5.7	5.4	4.8	4.3
90°	45.2	45.8	39.4	33.0	26.7	20.2	15.2	11.8	8.3	4.8	1.3
92.5°	41.7	41.6	40.1	38.6	37.1	35.5	33.5	31.0	28.5	25.9	23.3
95°	83.8	83.8	83.2	82.6	82.1	81.5	79.8	76.9	73.9	71.0	68.1
97.5°	140.9	140.9	139.8	138.7	137.5	136.4	134.6	132.1	129.6	126.9	124.4
100°	180.7	180.7	179.9	178.9	178.0	177.2	175.6	173.3	171.0	168.6	166.3
102.5°	223.9	223.7	222.6	221.5	220.4	219.2	217.7	215.9	214.0	212.2	210.3
105°	288.6	288.1	287.5	286.9	286.3	285.8	285.0	284.2	283.3	282.4	281.6
107.5°	359.3	359.0	359.0	359.0	359.0	359.0	358.4	357.1	355.9	354.6	353.3
110°	407.3	407.3	407.3	407.3	407.3	407.3	406.4	404.7	402.8	401.1	399.4



TEST NUMBER: P331484-840

CATALOG NUMBER: S122DIW-S290D1240U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	455.8	456.5	456.7	457.0	457.2	457.4	456.7	454.9	453.1	451.4	449.7
115°	528.8	529.0	529.6	530.2	530.8	531.3	530.8	529.0	527.3	525.5	523.8
117.5°	600.1	600.8	602.4	604.0	605.6	607.3	606.9	604.6	602.3	600.0	597.6
120°	646.8	646.8	649.1	651.6	653.9	656.2	656.2	653.9	651.6	649.1	646.8
122.5°	696.4	697.1	698.7	700.4	702.1	703.7	703.1	700.2	697.5	694.7	691.9
125°	769.1	769.9	770.8	771.7	772.5	773.5	772.5	769.9	767.3	764.7	762.0
127.5°	839.6	840.6	841.7	842.7	843.8	844.9	843.7	840.4	837.1	833.7	830.4
130°	887.2	887.8	888.4	889.0	889.6	890.1	888.5	884.7	881.0	877.2	873.4
132.5°	934.7	935.9	935.8	935.7	935.6	935.5	933.9	930.8	927.8	924.6	921.6
135°	1002.7	1003.0	1002.5	1001.9	1001.3	1000.7	998.9	995.6	992.4	989.2	986.0
137.5°	1068.8	1069.0	1068.2	1067.5	1066.7	1066.0	1064.3	1061.7	1059.0	1056.4	1053.8
140°	1113.0	1113.0	1111.6	1110.1	1108.6	1107.2	1105.2	1102.6	1099.9	1097.3	1094.7
142.5°	1153.1	1152.9	1151.9	1150.8	1149.8	1148.8	1147.1	1144.5	1141.9	1139.2	1136.6
145°	1214.2	1213.9	1212.1	1210.3	1208.6	1206.9	1205.0	1203.0	1200.9	1198.9	1196.8
147.5°	1267.4	1266.8	1265.6	1264.5	1263.2	1262.1	1260.3	1257.9	1255.4	1252.9	1250.5
150°	1301.1	1300.3	1299.1	1298.0	1296.8	1295.7	1294.1	1292.4	1290.7	1288.9	1287.2
152.5°	1334.9	1333.8	1332.4	1331.0	1329.6	1328.2	1326.7	1324.8	1323.1	1321.4	1319.7
155°	1377.7	1376.2	1375.3	1374.4	1373.6	1372.7	1371.9	1371.0	1370.1	1369.3	1368.4
157.5°	1416.9	1415.0	1414.4	1413.9	1413.4	1412.9	1412.3	1411.8	1411.2	1410.6	1410.0
160°	1440.8	1439.1	1438.8	1438.5	1438.1	1437.9	1437.4	1436.9	1436.3	1435.7	1435.1
162.5°	1462.0	1460.1	1459.8	1459.5	1459.2	1458.9	1458.6	1458.5	1458.4	1458.3	1458.1
165°	1489.6	1487.5	1487.5	1487.5	1487.5	1487.5	1487.6	1487.9	1488.2	1488.5	1488.8
167.5°	1512.4	1510.3	1510.4	1510.5	1510.5	1510.6	1511.0	1511.9	1512.8	1513.6	1514.5
170°	1524.9	1522.9	1523.2	1523.5	1523.8	1524.1	1524.6	1525.5	1526.4	1527.2	1528.1
172.5°	1534.4	1532.3	1532.6	1532.9	1533.2	1533.5	1534.1	1534.9	1535.8	1536.7	1537.5
175°	1544.6	1542.5	1543.1	1543.7	1544.3	1544.9	1545.6	1546.4	1547.3	1548.2	1549.0
177.5°	1549.9	1548.5	1549.0	1549.4	1549.9	1550.4	1551.0	1551.7	1552.4	1553.1	1553.8
180°	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7



TEST NUMBER: P331484-840

CATALOG NUMBER: S122DIW-S290D1240U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9
2.5°	600.1	601.0	603.9	606.8	610.2	611.1	612.5	611.3	610.9	614.3	616.9
5°	601.8	605.8	613.9	621.3	627.4	631.8	636.4	638.2	641.7	646.4	652.5
7.5°	599.8	607.8	620.5	631.2	642.8	651.2	657.7	663.4	670.1	679.2	689.2
10°	597.6	608.3	623.8	636.8	651.1	661.9	670.8	679.5	689.6	702.3	715.3
12.5°	593.6	606.3	625.6	641.1	659.3	669.9	682.0	700.7	711.7	729.2	747.6
15°	585.4	599.7	626.5	645.5	666.2	686.4	708.6	726.5	744.4	754.8	780.6
17.5°	573.4	594.2	624.0	646.2	672.5	704.2	729.2	749.5	770.1	786.9	799.9
20°	563.6	586.3	620.4	646.9	678.1	712.3	740.9	761.6	779.5	793.6	801.5
22.5°	551.4	580.0	613.0	644.2	684.0	717.8	747.9	764.2	779.1	786.0	789.1
25°	532.0	566.4	603.8	641.9	686.8	722.7	750.1	760.0	764.4	757.7	746.7
27.5°	511.1	549.5	593.2	637.5	685.1	719.5	739.2	737.7	730.3	708.7	691.6
30°	495.5	537.8	584.7	633.2	680.9	714.4	725.8	714.4	697.6	673.6	648.9
32.5°	479.2	522.9	575.7	626.9	673.2	702.7	705.1	685.4	659.4	632.1	601.5
35°	454.4	501.7	558.9	613.0	656.8	675.4	664.4	629.4	598.7	561.4	519.6
37.5°	426.5	478.7	535.9	592.6	632.3	637.1	609.8	573.1	529.7	485.7	436.6
40°	405.6	460.9	519.9	576.9	612.1	607.0	572.1	531.8	480.2	426.5	380.8
42.5°	386.9	442.1	502.2	558.3	586.3	572.5	531.8	482.2	426.8	376.2	334.4
45°	354.5	411.3	472.8	526.9	543.0	518.0	464.1	409.0	354.5	312.3	279.2
47.5°	323.0	379.2	440.1	487.7	493.3	459.7	400.8	344.2	297.2	262.9	239.5
50°	299.8	356.3	416.6	459.1	457.2	416.6	356.1	302.2	262.9	235.1	219.5
52.5°	279.1	332.4	390.3	429.0	419.2	375.0	317.1	269.2	237.0	215.3	201.2
55°	246.8	296.2	351.2	382.2	364.3	315.2	266.3	227.8	203.9	187.6	176.6
57.5°	214.8	261.1	308.2	327.3	307.5	262.2	221.5	193.5	175.5	163.5	156.3
60°	195.0	235.4	277.3	293.9	270.2	229.8	197.7	172.8	158.2	148.5	142.0
62.5°	175.2	211.4	251.0	259.9	238.3	204.2	175.7	154.9	143.1	134.3	128.3
65°	148.1	177.8	207.8	213.8	193.9	167.4	145.0	131.5	120.9	114.5	109.7
67.5°	121.6	145.3	166.6	171.4	153.9	135.6	119.4	107.6	100.5	95.1	91.0
70°	105.7	124.6	142.0	145.9	131.9	115.6	103.2	93.8	87.4	82.8	78.9
72.5°	89.1	104.7	119.3	121.9	110.5	98.0	87.9	80.4	74.7	71.8	68.1
75°	68.2	77.4	88.6	89.3	81.7	74.1	66.3	61.5	58.5	54.8	53.0
77.5°	48.1	55.2	61.7	62.9	58.5	53.3	49.0	45.1	42.6	40.9	39.2
80°	36.7	42.4	45.2	46.8	43.6	39.9	37.4	34.8	33.2	32.1	31.0
82.5°	26.3	29.8	32.3	33.6	31.8	29.6	27.2	25.7	24.4	23.5	23.1
85°	13.3	14.9	16.6	17.0	16.6	15.6	14.2	14.2	13.5	13.3	13.3
87.5°	5.6	7.0	7.7	8.9	9.6	10.8	12.1	13.2	14.3	14.0	13.7
90°	4.8	8.3	11.8	15.2	20.2	26.7	33.0	39.4	45.8	45.2	44.6
92.5°	25.9	28.5	31.0	33.5	35.5	37.1	38.6	40.1	41.6	41.7	41.9
95°	71.0	73.9	76.9	79.8	81.5	82.1	82.6	83.2	83.8	83.8	83.8
97.5°	126.9	129.6	132.1	134.6	136.4	137.5	138.7	139.8	140.9	140.9	140.9
100°	168.6	171.0	173.3	175.6	177.2	178.0	178.9	179.9	180.7	180.7	180.7
102.5°	212.2	214.0	215.9	217.7	219.2	220.4	221.5	222.6	223.7	223.9	224.1
105°	282.4	283.3	284.2	285.0	285.8	286.3	286.9	287.5	288.1	288.6	289.2
107.5°	354.6	355.9	357.1	358.4	359.0	359.0	359.0	359.0	359.0	359.3	359.5
110°	401.1	402.8	404.7	406.4	407.3	407.3	407.3	407.3	407.3	407.3	407.3



TEST NUMBER: P331484-840

CATALOG NUMBER: S122DIW-S290D1240U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	451.4	453.1	454.9	456.7	457.4	457.2	457.0	456.7	456.5	455.8	455.0
115°	525.5	527.3	529.0	530.8	531.3	530.8	530.2	529.6	529.0	528.8	528.5
117.5°	600.0	602.3	604.6	606.9	607.3	605.6	604.0	602.4	600.8	600.1	599.4
120°	649.1	651.6	653.9	656.2	656.2	653.9	651.6	649.1	646.8	646.8	646.8
122.5°	694.7	697.5	700.2	703.1	703.7	702.1	700.4	698.7	697.1	696.4	695.8
125°	764.7	767.3	769.9	772.5	773.5	772.5	771.7	770.8	769.9	769.1	768.2
127.5°	833.7	837.1	840.4	843.7	844.9	843.8	842.7	841.7	840.6	839.6	838.6
130°	877.2	881.0	884.7	888.5	890.1	889.6	889.0	888.4	887.8	887.2	886.7
132.5°	924.6	927.8	930.8	933.9	935.5	935.6	935.7	935.8	935.9	934.7	933.4
135°	989.2	992.4	995.6	998.9	1000.7	1001.3	1001.9	1002.5	1003.0	1002.7	1002.5
137.5°	1056.4	1059.0	1061.7	1064.3	1066.0	1066.7	1067.5	1068.2	1069.0	1068.8	1068.5
140°	1097.3	1099.9	1102.6	1105.2	1107.2	1108.6	1110.1	1111.6	1113.0	1113.0	1113.0
142.5°	1139.2	1141.9	1144.5	1147.1	1148.8	1149.8	1150.8	1151.9	1152.9	1153.1	1153.3
145°	1198.9	1200.9	1203.0	1205.0	1206.9	1208.6	1210.3	1212.1	1213.9	1214.2	1214.5
147.5°	1252.9	1255.4	1257.9	1260.3	1262.1	1263.2	1264.5	1265.6	1266.8	1267.4	1268.0
150°	1288.9	1290.7	1292.4	1294.1	1295.7	1296.8	1298.0	1299.1	1300.3	1301.1	1302.0
152.5°	1321.4	1323.1	1324.8	1326.7	1328.2	1329.6	1331.0	1332.4	1333.8	1334.9	1336.1
155°	1369.3	1370.1	1371.0	1371.9	1372.7	1373.6	1374.4	1375.3	1376.2	1377.7	1379.2
157.5°	1410.6	1411.2	1411.8	1412.3	1412.9	1413.4	1413.9	1414.4	1415.0	1416.9	1419.0
160°	1435.7	1436.3	1436.9	1437.4	1437.9	1438.1	1438.5	1438.8	1439.1	1440.8	1442.6
162.5°	1458.3	1458.4	1458.5	1458.6	1458.9	1459.2	1459.5	1459.8	1460.1	1462.0	1464.0
165°	1488.5	1488.2	1487.9	1487.6	1487.5	1487.5	1487.5	1487.5	1487.5	1489.6	1491.6
167.5°	1513.6	1512.8	1511.9	1511.0	1510.6	1510.5	1510.5	1510.4	1510.3	1512.4	1514.4
170°	1527.2	1526.4	1525.5	1524.6	1524.1	1523.8	1523.5	1523.2	1522.9	1524.9	1526.9
172.5°	1536.7	1535.8	1534.9	1534.1	1533.5	1533.2	1532.9	1532.6	1532.3	1534.4	1536.4
175°	1548.2	1547.3	1546.4	1545.6	1544.9	1544.3	1543.7	1543.1	1542.5	1544.6	1546.6
177.5°	1553.1	1552.4	1551.7	1551.0	1550.4	1549.9	1549.4	1549.0	1548.5	1549.9	1551.4
180°	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7



TEST NUMBER: P331484-840

CATALOG NUMBER: S122DIW-S290D1240U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	596.9	596.9	596.9	596.9	596.9	596.9	596.9
2.5°	619.1	621.7	621.7	622.1	625.0	624.6	624.4
5°	658.8	662.8	663.2	667.3	670.0	669.1	666.6
7.5°	696.3	703.6	709.1	712.2	715.8	718.0	717.0
10°	726.1	736.6	743.1	747.4	752.7	756.6	755.2
12.5°	753.1	765.6	774.5	781.9	782.5	787.6	784.2
15°	795.2	808.4	809.8	815.3	819.7	819.2	819.4
17.5°	809.0	813.2	814.2	814.3	814.4	812.7	809.2
20°	804.1	802.4	798.6	795.6	790.3	789.6	785.1
22.5°	780.5	775.5	765.7	759.2	751.0	748.9	747.6
25°	734.4	723.1	707.5	692.6	688.4	680.4	682.7
27.5°	670.9	653.4	636.4	624.4	613.4	601.4	604.8
30°	626.3	606.5	582.7	564.3	552.6	541.2	539.1
32.5°	573.1	544.1	517.6	501.4	483.4	476.2	468.3
35°	481.3	453.0	426.7	403.9	390.9	380.8	371.6
37.5°	398.8	366.3	345.0	326.6	317.1	311.3	312.9
40°	347.6	319.1	303.5	289.5	280.7	276.7	277.6
42.5°	306.1	284.8	272.0	262.4	256.2	253.9	253.4
45°	259.0	247.1	236.5	231.1	228.0	225.5	223.9
47.5°	226.9	217.1	211.2	207.9	205.3	202.8	202.7
50°	207.6	201.2	197.0	193.6	191.6	189.8	191.4
52.5°	192.9	187.0	182.9	179.9	179.0	177.4	177.3
55°	171.2	166.5	163.6	160.8	159.5	158.5	157.3
57.5°	151.3	146.9	144.2	142.5	139.9	139.0	138.6
60°	137.1	133.7	131.0	128.7	127.5	125.7	125.7
62.5°	124.1	120.7	118.2	116.4	114.5	113.8	114.0
65°	105.3	102.5	100.0	98.2	97.8	96.3	96.8
67.5°	88.0	86.1	83.4	82.4	81.6	80.9	80.3
70°	76.3	74.5	73.2	71.8	71.1	71.1	71.1
72.5°	66.7	64.4	63.6	61.9	62.3	61.6	60.8
75°	51.6	50.2	49.6	48.9	47.8	47.8	47.8
77.5°	38.0	37.6	36.8	36.1	35.7	35.5	35.6
80°	29.4	29.1	28.7	28.7	28.2	28.0	27.6
82.5°	22.6	22.0	21.7	21.5	21.4	21.4	21.3
85°	12.8	12.4	12.4	12.6	12.1	12.1	12.4
87.5°	13.7	13.6	13.4	13.5	13.7	13.6	13.6
90°	44.1	43.5	43.3	43.6	43.9	44.2	44.5
92.5°	42.0	42.1	42.2	42.2	42.3	42.4	42.4
95°	83.8	83.8	83.5	82.9	82.3	81.8	81.2
97.5°	140.9	140.9	140.9	140.8	140.8	140.7	140.7
100°	180.7	180.7	180.6	180.3	180.0	179.7	179.4
102.5°	224.4	224.6	224.6	224.3	224.0	223.7	223.4
105°	289.8	290.4	290.7	290.7	290.7	290.7	290.7
107.5°	359.7	360.0	359.4	358.1	356.8	355.4	354.1
110°	407.3	407.3	406.8	406.0	405.1	404.1	403.3



TEST NUMBER: P331484-840

CATALOG NUMBER: S122DIW-S290D1240U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	454.3	453.6	453.0	452.3	451.7	451.1	450.4
115°	528.2	527.9	527.3	526.4	525.5	524.6	523.8
117.5°	598.6	597.9	597.2	596.3	595.4	594.6	593.7
120°	646.8	646.8	646.4	645.5	644.7	643.8	643.0
122.5°	695.1	694.4	693.7	693.1	692.4	691.8	691.2
125°	767.3	766.5	765.9	765.6	765.3	765.0	764.7
127.5°	837.5	836.5	835.5	834.6	833.6	832.7	831.7
130°	886.1	885.4	884.6	883.4	882.3	881.1	879.9
132.5°	932.1	930.9	929.8	928.9	927.9	927.0	926.0
135°	1002.2	1001.9	1001.3	1000.4	999.6	998.7	997.7
137.5°	1068.3	1068.1	1067.4	1066.2	1065.1	1063.9	1062.8
140°	1113.0	1113.0	1112.5	1111.3	1110.1	1108.9	1107.8
142.5°	1153.6	1153.8	1153.3	1152.2	1150.9	1149.8	1148.6
145°	1214.8	1215.0	1214.6	1213.5	1212.2	1211.1	1209.9
147.5°	1268.7	1269.3	1269.1	1268.0	1266.9	1265.8	1264.7
150°	1302.9	1303.7	1303.7	1302.9	1302.0	1301.1	1300.3
152.5°	1337.1	1338.2	1338.2	1337.1	1336.1	1334.9	1333.8
155°	1380.6	1382.0	1382.3	1381.5	1380.6	1379.7	1378.9
157.5°	1420.9	1422.9	1423.2	1421.8	1420.4	1419.0	1417.5
160°	1444.3	1446.0	1446.3	1445.2	1444.0	1442.9	1441.7
162.5°	1465.9	1467.9	1468.2	1466.8	1465.4	1464.0	1462.7
165°	1493.6	1495.7	1495.9	1494.5	1493.1	1491.6	1490.2
167.5°	1516.4	1518.4	1518.7	1517.2	1515.7	1514.2	1512.7
170°	1528.9	1531.1	1531.2	1529.4	1527.7	1525.9	1524.2
172.5°	1538.4	1540.4	1540.5	1538.8	1537.1	1535.4	1533.6
175°	1548.6	1550.6	1550.8	1549.0	1547.3	1545.6	1543.8
177.5°	1552.8	1554.1	1554.1	1552.8	1551.4	1549.9	1548.5
180°	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7

(END OF REPORT)