

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331472-840

Luminaire Tested: **S122DIW-S290D710U840-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331472-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIW-S290D710U840-4F0-1E-UDD-A1  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 710 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3803.5 lumens  
Efficiency: N/A  
Efficacy: 125.1 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 30.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331472-840

CATALOG NUMBER: S122DIW-S290D710U840-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P331472-840

CATALOG NUMBER: S122DIW-S290D710U840-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	42	42	42	35
1	95	91	87	84	85	82	79	76	66	64	62	51	50	49	38	37	36	30
2	86	79	74	69	78	72	67	63	58	55	52	45	43	41	34	32	31	26
3	79	70	63	58	71	64	58	53	52	47	44	40	38	35	30	28	27	22
4	72	62	55	49	65	57	50	45	46	41	38	36	33	30	27	25	23	19
5	67	55	48	42	60	51	44	39	41	36	33	33	29	26	24	22	20	17
6	61	50	42	36	55	45	39	34	37	32	28	30	26	23	22	20	18	15
7	57	45	37	32	51	41	34	30	34	29	25	27	23	21	20	18	16	13
8	53	41	33	28	48	37	31	26	31	26	22	25	21	18	19	16	15	12
9	49	37	30	25	44	34	28	23	28	23	20	23	19	17	17	15	13	11
10	46	34	27	23	41	31	25	21	26	21	18	21	17	15	16	14	12	10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	9637	9637	9637	9637
5°	10804	9700	8596	9700
10°	12381	9621	7438	9621
15°	13697	9444	6572	9444
20°	13490	9256	5991	9256
25°	12162	9002	5624	9002
30°	10051	8600	5354	8600
35°	7324	8180	5164	8180
40°	5851	7685	5056	7685
45°	5112	7108	4914	7108
50°	4808	6551	4818	6551
55°	4428	5987	4687	5987
60°	4059	5383	4492	5383
65°	3698	4844	4294	4844
70°	3356	4319	4008	4319
75°	2982	3737	3550	3737
80°	2566	3087	2854	3087
85°	2297	2297	1704	2297



TEST NUMBER: P331472-840

CATALOG NUMBER: S122DIW-S290D710U840-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	56.8	1.5
10°-20°	165.3	4.3
20°-30°	239.9	6.3
30°-40°	253.1	6.7
40°-50°	224.1	5.9
50°-60°	178.8	4.7
60°-70°	121.6	3.2
70°-80°	62.3	1.6
80°-90°	18.6	0.5
90°-100°	56.3	1.5
100°-110°	174.8	4.6
110°-120°	298.7	7.9
120°-130°	392.8	10.3
130°-140°	440.9	11.6
140°-150°	432.3	11.4
150°-160°	362.6	9.5
160°-170°	240.5	6.3
170°-180°	84.1	2.2
0°-30°	462.0	12.1
0°-40°	715.1	18.8
0°-60°	1118.0	29.4
0°-90°	1320.5	34.7
90°-120°	529.8	13.9
90°-150°	1795.8	47.2
90°-180°	2483.0	65.3
0°-180°	3803.5	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	597	597	597	597	597	
5°	667	598	530	598	667	67
15°	819	565	393	565	819	226
25°	683	505	316	505	683	309
35°	372	415	262	415	372	242
45°	224	311	215	311	224	176
55°	157	213	166	213	157	141
65°	97	127	112	127	97	96
75°	48	60	57	60	48	51
85°	12	12	9	12	12	14
90°	25	1	25	1	25	12
95°	46	39	46	39	46	52
105°	166	161	166	161	166	175
115°	300	300	300	300	300	296
125°	438	436	438	436	438	390
135°	571	564	571	564	571	440
145°	692	685	692	685	692	432
155°	789	783	789	783	789	363
165°	853	852	853	852	853	241
175°	884	886	884	886	884	84
180°	888	888	888	888	888	



TEST NUMBER: P331472-840

CATALOG NUMBER: S122DIW-S290D710U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9
2.5°	624.4	624.6	625.0	622.1	621.7	621.7	619.1	616.9	614.3	610.9	611.3
5°	666.6	669.1	670.0	667.3	663.2	662.8	658.8	652.5	646.4	641.7	638.2
7.5°	717.0	718.0	715.8	712.2	709.1	703.6	696.3	689.2	679.2	670.1	663.4
10°	755.2	756.6	752.7	747.4	743.1	736.6	726.1	715.3	702.3	689.6	679.5
12.5°	784.2	787.6	782.5	781.9	774.5	765.6	753.1	747.6	729.2	711.7	700.7
15°	819.4	819.2	819.7	815.3	809.8	808.4	795.2	780.6	754.8	744.4	726.5
17.5°	809.2	812.7	814.4	814.3	814.2	813.2	809.0	799.9	786.9	770.1	749.5
20°	785.1	789.6	790.3	795.6	798.6	802.4	804.1	801.5	793.6	779.5	761.6
22.5°	747.6	748.9	751.0	759.2	765.7	775.5	780.5	789.1	786.0	779.1	764.2
25°	682.7	680.4	688.4	692.6	707.5	723.1	734.4	746.7	757.7	764.4	760.0
27.5°	604.8	601.4	613.4	624.4	636.4	653.4	670.9	691.6	708.7	730.3	737.7
30°	539.1	541.2	552.6	564.3	582.7	606.5	626.3	648.9	673.6	697.6	714.4
32.5°	468.3	476.2	483.4	501.4	517.6	544.1	573.1	601.5	632.1	659.4	685.4
35°	371.6	380.8	390.9	403.9	426.7	453.0	481.3	519.6	561.4	598.7	629.4
37.5°	312.9	311.3	317.1	326.6	345.0	366.3	398.8	436.6	485.7	529.7	573.1
40°	277.6	276.7	280.7	289.5	303.5	319.1	347.6	380.8	426.5	480.2	531.8
42.5°	253.4	253.9	256.2	262.4	272.0	284.8	306.1	334.4	376.2	426.8	482.2
45°	223.9	225.5	228.0	231.1	236.5	247.1	259.0	279.2	312.3	354.5	409.0
47.5°	202.7	202.8	205.3	207.9	211.2	217.1	226.9	239.5	262.9	297.2	344.2
50°	191.4	189.8	191.6	193.6	197.0	201.2	207.6	219.5	235.1	262.9	302.2
52.5°	177.3	177.4	179.0	179.9	182.9	187.0	192.9	201.2	215.3	237.0	269.2
55°	157.3	158.5	159.5	160.8	163.6	166.5	171.2	176.6	187.6	203.9	227.8
57.5°	138.6	139.0	139.9	142.5	144.2	146.9	151.3	156.3	163.5	175.5	193.5
60°	125.7	125.7	127.5	128.7	131.0	133.7	137.1	142.0	148.5	158.2	172.8
62.5°	114.0	113.8	114.5	116.4	118.2	120.7	124.1	128.3	134.3	143.1	154.9
65°	96.8	96.3	97.8	98.2	100.0	102.5	105.3	109.7	114.5	120.9	131.5
67.5°	80.3	80.9	81.6	82.4	83.4	86.1	88.0	91.0	95.1	100.5	107.6
70°	71.1	71.1	71.1	71.8	73.2	74.5	76.3	78.9	82.8	87.4	93.8
72.5°	60.8	61.6	62.3	61.9	63.6	64.4	66.7	68.1	71.8	74.7	80.4
75°	47.8	47.8	47.8	48.9	49.6	50.2	51.6	53.0	54.8	58.5	61.5
77.5°	35.6	35.5	35.7	36.1	36.8	37.6	38.0	39.2	40.9	42.6	45.1
80°	27.6	28.0	28.2	28.7	28.7	29.1	29.4	31.0	32.1	33.2	34.8
82.5°	21.3	21.4	21.4	21.5	21.7	22.0	22.6	23.1	23.5	24.4	25.7
85°	12.4	12.1	12.1	12.6	12.4	12.4	12.8	13.3	13.3	13.5	14.2
87.5°	9.9	9.8	10.0	9.8	9.7	9.9	10.0	9.9	10.1	10.4	9.8
90°	25.4	25.3	25.1	24.9	24.8	24.9	25.2	25.5	25.9	26.3	22.5
92.5°	24.2	24.2	24.2	24.1	24.1	24.1	24.0	23.9	23.9	23.8	22.9
95°	46.5	46.8	47.2	47.5	47.8	48.0	48.0	48.0	48.0	48.0	47.7
97.5°	80.5	80.5	80.6	80.6	80.6	80.6	80.6	80.6	80.6	80.6	80.0
100°	102.7	102.8	103.0	103.2	103.3	103.4	103.4	103.4	103.4	103.4	102.9
102.5°	127.8	128.1	128.2	128.4	128.6	128.6	128.4	128.3	128.2	127.9	127.3
105°	166.3	166.3	166.3	166.3	166.3	166.2	165.8	165.5	165.2	164.9	164.5
107.5°	202.7	203.4	204.2	204.9	205.7	206.0	205.9	205.7	205.6	205.5	205.5
110°	230.9	231.3	231.8	232.3	232.8	233.1	233.1	233.1	233.1	233.1	233.1



TEST NUMBER: P331472-840

CATALOG NUMBER: S122DIW-S290D710U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	257.8	258.1	258.5	258.9	259.2	259.6	260.0	260.4	260.8	261.3	261.4
115°	299.7	300.2	300.7	301.2	301.7	302.1	302.3	302.5	302.6	302.8	303.1
117.5°	339.7	340.2	340.7	341.2	341.7	342.2	342.6	343.1	343.5	343.9	344.8
120°	367.9	368.4	368.9	369.4	369.9	370.2	370.2	370.2	370.2	370.2	371.5
122.5°	395.6	395.9	396.3	396.6	397.0	397.4	397.8	398.2	398.6	399.0	399.9
125°	437.7	437.8	438.0	438.2	438.3	438.6	439.1	439.6	440.1	440.6	441.1
127.5°	476.1	476.6	477.1	477.6	478.2	478.7	479.3	479.9	480.5	481.1	481.7
130°	503.6	504.2	504.9	505.5	506.2	506.8	507.1	507.5	507.8	508.1	508.4
132.5°	530.0	530.5	531.0	531.6	532.1	532.7	533.4	534.2	534.9	535.6	535.6
135°	571.0	571.5	572.0	572.5	573.0	573.4	573.5	573.7	573.8	574.0	573.7
137.5°	608.1	608.8	609.6	610.2	610.9	611.3	611.4	611.5	611.7	611.8	611.4
140°	634.0	634.6	635.3	636.0	636.6	636.9	636.9	636.9	636.9	636.9	636.1
142.5°	657.3	658.0	658.6	659.3	660.0	660.2	660.1	660.0	659.8	659.7	659.1
145°	692.5	693.1	693.8	694.4	695.1	695.3	695.2	695.0	694.8	694.7	693.7
147.5°	723.8	724.4	725.0	725.7	726.3	726.4	726.0	725.7	725.3	725.0	724.3
150°	744.2	744.7	745.1	745.6	746.1	746.1	745.6	745.1	744.7	744.2	743.5
152.5°	763.4	764.0	764.6	765.2	765.9	765.9	765.2	764.6	764.0	763.4	762.5
155°	789.1	789.6	790.1	790.6	791.1	790.9	790.1	789.2	788.4	787.6	787.1
157.5°	811.2	812.0	812.8	813.6	814.5	814.3	813.1	812.0	810.9	809.8	809.5
160°	825.1	825.8	826.4	827.1	827.7	827.6	826.6	825.6	824.6	823.5	823.3
162.5°	837.1	837.9	838.7	839.4	840.2	840.1	839.0	837.8	836.7	835.6	835.4
165°	852.8	853.6	854.4	855.3	856.2	856.0	854.7	853.6	852.4	851.3	851.3
167.5°	865.7	866.6	867.4	868.3	869.1	869.0	867.8	866.7	865.5	864.3	864.3
170°	872.2	873.2	874.2	875.3	876.3	876.2	875.0	873.8	872.7	871.5	871.7
172.5°	877.7	878.7	879.7	880.7	881.6	881.6	880.4	879.3	878.1	876.9	877.1
175°	883.5	884.5	885.6	886.5	887.5	887.5	886.3	885.0	883.9	882.7	883.1
177.5°	886.2	887.0	887.8	888.6	889.4	889.4	888.6	887.8	887.0	886.2	886.5
180°	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0



TEST NUMBER: P331472-840

CATALOG NUMBER: S122DIW-S290D710U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9
2.5°	612.5	611.1	610.2	606.8	603.9	601.0	600.1	600.4	596.3	592.5	590.9
5°	636.4	631.8	627.4	621.3	613.9	605.8	601.8	598.5	590.5	581.8	576.7
7.5°	657.7	651.2	642.8	631.2	620.5	607.8	599.8	592.7	581.0	568.7	561.1
10°	670.8	661.9	651.1	636.8	623.8	608.3	597.6	586.8	573.1	558.4	549.2
12.5°	682.0	669.9	659.3	641.1	625.6	606.3	593.6	578.3	563.9	546.4	537.5
15°	708.6	686.4	666.2	645.5	626.5	599.7	585.4	565.0	546.0	524.4	514.1
17.5°	729.2	704.2	672.5	646.2	624.0	594.2	573.4	549.0	526.4	501.8	487.8
20°	740.9	712.3	678.1	646.9	620.4	586.3	563.6	538.7	512.3	484.5	469.4
22.5°	747.9	717.8	684.0	644.2	613.0	580.0	551.4	523.9	497.3	467.3	451.4
25°	750.1	722.7	686.8	641.9	603.8	566.4	532.0	505.3	473.0	445.0	421.9
27.5°	739.2	719.5	685.1	637.5	593.2	549.5	511.1	481.0	446.9	416.5	393.1
30°	725.8	714.4	680.9	633.2	584.7	537.8	495.5	461.3	427.4	396.7	372.7
32.5°	705.1	702.7	673.2	626.9	575.7	522.9	479.2	444.6	407.0	376.8	354.1
35°	664.4	675.4	656.8	613.0	558.9	501.7	454.4	415.0	376.0	347.1	325.8
37.5°	609.8	637.1	632.3	592.6	535.9	478.7	426.5	385.3	348.1	318.9	298.0
40°	572.1	607.0	612.1	576.9	519.9	460.9	405.6	364.6	328.3	301.6	280.5
42.5°	531.8	572.5	586.3	558.3	502.2	442.1	386.9	344.4	308.4	282.6	263.9
45°	464.1	518.0	543.0	526.9	472.8	411.3	354.5	311.3	278.7	254.4	239.9
47.5°	400.8	459.7	493.3	487.7	440.1	379.2	323.0	281.6	249.8	230.5	217.5
50°	356.1	416.6	457.2	459.1	416.6	356.3	299.8	260.8	231.7	213.6	203.0
52.5°	317.1	375.0	419.2	429.0	390.3	332.4	279.1	240.2	214.6	197.9	188.5
55°	266.3	315.2	364.3	382.2	351.2	296.2	246.8	212.7	188.5	177.1	168.8
57.5°	221.5	262.2	307.5	327.3	308.2	261.1	214.8	185.1	165.6	155.5	149.2
60°	197.7	229.8	270.2	293.9	277.3	235.4	195.0	166.7	150.7	141.8	135.8
62.5°	175.7	204.2	238.3	259.9	251.0	211.4	175.2	150.3	136.4	128.1	123.7
65°	145.0	167.4	193.9	213.8	207.8	177.8	148.1	126.8	115.8	109.2	105.7
67.5°	119.4	135.6	153.9	171.4	166.6	145.3	121.6	104.9	96.7	91.0	88.9
70°	103.2	115.6	131.9	145.9	142.0	124.6	105.7	91.5	84.4	79.6	77.6
72.5°	87.9	98.0	110.5	121.9	119.3	104.7	89.1	78.4	72.8	68.4	66.8
75°	66.3	74.1	81.7	89.3	88.6	77.4	68.2	59.9	55.5	52.1	51.4
77.5°	49.0	53.3	58.5	62.9	61.7	55.2	48.1	43.3	40.2	37.9	37.5
80°	37.4	39.9	43.6	46.8	45.2	42.4	36.7	33.2	31.0	28.7	27.8
82.5°	27.2	29.6	31.8	33.6	32.3	29.8	26.3	23.9	22.5	21.0	20.6
85°	14.2	15.6	16.6	17.0	16.6	14.9	13.3	12.4	11.2	10.5	10.3
87.5°	9.3	8.6	7.8	7.6	6.7	6.3	5.2	4.1	4.4	4.6	4.6
90°	18.9	15.2	11.6	8.8	6.8	4.7	2.7	0.7	2.7	4.7	6.8
92.5°	22.1	21.2	20.4	19.2	17.8	16.3	14.8	13.3	14.8	16.3	17.8
95°	47.3	47.0	46.7	45.6	43.9	42.3	40.6	39.0	40.6	42.3	43.9
97.5°	79.4	78.8	78.1	77.1	75.5	74.1	72.6	71.2	72.6	74.1	75.5
100°	102.4	101.9	101.4	100.5	99.2	97.9	96.5	95.1	96.5	97.9	99.2
102.5°	126.7	126.1	125.4	124.6	123.5	122.5	121.4	120.4	121.4	122.5	123.5
105°	164.2	163.9	163.5	163.1	162.6	162.1	161.6	161.1	161.6	162.1	162.6
107.5°	205.5	205.5	205.5	205.1	204.4	203.7	202.9	202.2	202.9	203.7	204.4
110°	233.1	233.1	233.1	232.6	231.6	230.6	229.5	228.5	229.5	230.6	231.6





TEST NUMBER: P331472-840

CATALOG NUMBER: S122DIW-S290D710U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	261.5	261.7	261.8	261.4	260.3	259.3	258.3	257.3	258.3	259.3	260.3
115°	303.4	303.8	304.1	303.8	302.8	301.7	300.7	299.7	300.7	301.7	302.8
117.5°	345.7	346.6	347.5	347.3	346.0	344.7	343.4	342.0	343.4	344.7	346.0
120°	372.8	374.2	375.5	375.5	374.2	372.8	371.5	370.2	371.5	372.8	374.2
122.5°	400.8	401.7	402.7	402.3	400.7	399.2	397.6	396.0	397.6	399.2	400.7
125°	441.6	442.1	442.6	442.1	440.6	439.1	437.7	436.2	437.7	439.1	440.6
127.5°	482.3	482.9	483.5	482.8	480.9	479.1	477.2	475.2	477.2	479.1	480.9
130°	508.8	509.1	509.4	508.5	506.3	504.1	502.0	499.8	502.0	504.1	506.3
132.5°	535.5	535.4	535.4	534.4	532.7	531.0	529.2	527.5	529.2	531.0	532.7
135°	573.4	573.0	572.7	571.6	569.8	567.9	566.1	564.3	566.1	567.9	569.8
137.5°	611.0	610.5	610.1	609.0	607.6	606.1	604.6	603.1	604.6	606.1	607.6
140°	635.3	634.5	633.6	632.5	631.0	629.4	627.9	626.5	627.9	629.4	631.0
142.5°	658.6	658.0	657.5	656.4	655.0	653.5	652.0	650.5	652.0	653.5	655.0
145°	692.7	691.7	690.6	689.6	688.4	687.2	686.1	684.9	686.1	687.2	688.4
147.5°	723.6	723.0	722.3	721.2	719.8	718.4	717.0	715.7	717.0	718.4	719.8
150°	742.8	742.1	741.4	740.6	739.6	738.6	737.6	736.6	737.6	738.6	739.6
152.5°	761.7	760.9	760.1	759.2	758.2	757.2	756.2	755.2	756.2	757.2	758.2
155°	786.6	786.1	785.6	785.1	784.6	784.1	783.6	783.0	783.6	784.1	784.6
157.5°	809.2	808.9	808.6	808.3	807.9	807.6	807.3	806.9	807.3	807.6	807.9
160°	823.2	823.0	822.9	822.6	822.3	821.9	821.6	821.3	821.6	821.9	822.3
162.5°	835.3	835.1	834.9	834.8	834.7	834.7	834.6	834.5	834.6	834.7	834.7
165°	851.3	851.3	851.3	851.4	851.5	851.7	851.8	852.0	851.8	851.7	851.5
167.5°	864.3	864.4	864.4	864.7	865.3	865.8	866.3	866.8	866.3	865.8	865.3
170°	871.8	872.0	872.2	872.5	873.0	873.5	874.0	874.5	874.0	873.5	873.0
172.5°	877.3	877.4	877.6	877.9	878.4	878.9	879.4	879.9	879.4	878.9	878.4
175°	883.4	883.7	884.1	884.5	885.0	885.6	886.1	886.5	886.1	885.6	885.0
177.5°	886.8	887.0	887.3	887.6	888.0	888.4	888.8	889.2	888.8	888.4	888.0
180°	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0



TEST NUMBER: P331472-840

CATALOG NUMBER: S122DIW-S290D710U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9
2.5°	589.1	587.9	584.1	582.1	578.8	575.6	573.6	574.5	575.2	574.9	574.3
5°	572.1	567.7	561.1	555.4	551.3	543.7	540.5	538.9	537.5	535.9	534.3
7.5°	552.0	545.1	535.6	527.5	519.8	510.3	504.9	501.8	498.5	494.8	491.6
10°	537.8	528.1	518.0	506.5	497.4	488.9	481.3	476.3	471.6	467.3	464.1
12.5°	522.7	511.6	499.1	483.4	473.3	461.1	460.0	451.1	443.9	441.2	437.5
15°	498.8	483.1	467.3	448.7	440.7	429.7	422.8	415.9	409.7	405.4	404.2
17.5°	471.5	451.3	435.6	422.2	409.1	397.8	391.4	386.0	380.8	375.1	374.3
20°	450.8	433.3	416.2	404.5	390.9	379.4	371.6	366.2	361.7	358.3	355.4
22.5°	431.1	412.0	396.3	383.5	370.2	360.9	354.8	349.4	345.8	342.0	339.2
25°	399.6	384.8	367.5	353.0	342.0	336.1	331.0	326.5	324.2	321.6	318.4
27.5°	372.0	355.5	339.4	328.2	318.5	313.3	309.6	306.5	304.4	302.9	301.0
30°	352.6	335.9	323.3	312.3	304.2	298.9	296.6	294.8	292.3	291.3	290.4
32.5°	333.9	318.8	308.0	298.4	290.8	287.3	285.3	283.6	281.7	280.7	278.8
35°	307.4	294.8	284.3	278.9	272.8	269.7	268.2	265.9	264.1	263.2	262.9
37.5°	282.5	271.6	264.6	257.8	255.2	253.4	251.2	249.6	249.0	248.9	248.6
40°	266.3	257.4	251.2	245.7	244.6	241.8	239.9	238.6	238.6	238.8	238.6
42.5°	251.7	243.6	238.1	233.4	232.1	230.5	228.5	228.5	228.8	229.6	228.8
45°	229.4	223.7	219.7	217.5	215.0	213.4	213.1	213.8	214.0	214.3	215.0
47.5°	208.9	205.1	201.6	199.0	197.9	197.7	197.4	198.6	199.8	200.2	201.2
50°	196.8	192.5	189.5	187.8	186.9	186.5	186.9	188.3	189.2	190.4	191.1
52.5°	183.3	180.2	178.1	176.8	176.5	176.8	176.8	178.4	179.9	180.4	180.7
55°	164.5	162.2	161.8	159.7	160.6	160.4	161.5	162.4	163.8	165.2	165.4
57.5°	145.7	143.9	142.7	142.9	143.2	144.2	145.1	146.7	148.1	149.7	149.8
60°	133.3	132.4	131.7	131.7	132.1	133.5	134.6	136.2	137.1	138.1	138.8
62.5°	121.9	121.0	120.3	120.7	121.9	122.7	124.0	124.9	125.8	126.7	127.0
65°	103.9	103.5	104.1	104.6	104.8	105.9	107.6	108.3	109.2	109.7	111.3
67.5°	87.4	87.5	87.4	88.0	89.4	89.6	91.1	92.7	92.9	93.8	94.8
70°	76.1	76.6	77.1	77.6	78.7	79.2	80.3	81.0	81.9	82.6	83.3
72.5°	65.8	65.9	66.4	66.3	67.4	68.3	69.3	70.0	70.9	71.8	72.4
75°	50.7	50.7	51.2	51.4	52.5	53.7	53.4	53.9	54.8	55.7	56.2
77.5°	37.1	36.6	37.1	37.3	37.7	38.6	38.8	39.4	40.5	40.2	40.7
80°	28.2	27.6	28.2	28.5	28.5	29.6	29.6	30.1	30.7	30.1	30.7
82.5°	20.1	19.8	20.3	20.4	20.7	20.8	21.1	21.2	21.9	21.6	21.9
85°	10.1	9.9	10.1	9.9	10.1	10.3	10.3	10.1	10.1	10.5	9.9
87.5°	4.8	5.3	5.8	6.6	7.1	7.7	7.4	7.3	7.3	6.8	6.8
90°	8.8	11.6	15.2	18.9	22.5	26.3	25.9	25.5	25.2	24.9	24.8
92.5°	19.2	20.4	21.2	22.1	22.9	23.8	23.9	23.9	24.0	24.1	24.1
95°	45.6	46.7	47.0	47.3	47.7	48.0	48.0	48.0	48.0	48.0	47.8
97.5°	77.1	78.1	78.8	79.4	80.0	80.6	80.6	80.6	80.6	80.6	80.6
100°	100.5	101.4	101.9	102.4	102.9	103.4	103.4	103.4	103.4	103.4	103.3
102.5°	124.6	125.4	126.1	126.7	127.3	127.9	128.2	128.3	128.4	128.6	128.6
105°	163.1	163.5	163.9	164.2	164.5	164.9	165.2	165.5	165.8	166.2	166.3
107.5°	205.1	205.5	205.5	205.5	205.5	205.5	205.6	205.7	205.9	206.0	205.7
110°	232.6	233.1	233.1	233.1	233.1	233.1	233.1	233.1	233.1	233.1	232.8



TEST NUMBER: P331472-840

CATALOG NUMBER: S122DIW-S290D710U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	261.4	261.8	261.7	261.5	261.4	261.3	260.8	260.4	260.0	259.6	259.2
115°	303.8	304.1	303.8	303.4	303.1	302.8	302.6	302.5	302.3	302.1	301.7
117.5°	347.3	347.5	346.6	345.7	344.8	343.9	343.5	343.1	342.6	342.2	341.7
120°	375.5	375.5	374.2	372.8	371.5	370.2	370.2	370.2	370.2	370.2	369.9
122.5°	402.3	402.7	401.7	400.8	399.9	399.0	398.6	398.2	397.8	397.4	397.0
125°	442.1	442.6	442.1	441.6	441.1	440.6	440.1	439.6	439.1	438.6	438.3
127.5°	482.8	483.5	482.9	482.3	481.7	481.1	480.5	479.9	479.3	478.7	478.2
130°	508.5	509.4	509.1	508.8	508.4	508.1	507.8	507.5	507.1	506.8	506.2
132.5°	534.4	535.4	535.4	535.5	535.6	535.6	534.9	534.2	533.4	532.7	532.1
135°	571.6	572.7	573.0	573.4	573.7	574.0	573.8	573.7	573.5	573.4	573.0
137.5°	609.0	610.1	610.5	611.0	611.4	611.8	611.7	611.5	611.4	611.3	610.9
140°	632.5	633.6	634.5	635.3	636.1	636.9	636.9	636.9	636.9	636.9	636.6
142.5°	656.4	657.5	658.0	658.6	659.1	659.7	659.8	660.0	660.1	660.2	660.0
145°	689.6	690.6	691.7	692.7	693.7	694.7	694.8	695.0	695.2	695.3	695.1
147.5°	721.2	722.3	723.0	723.6	724.3	725.0	725.3	725.7	726.0	726.4	726.3
150°	740.6	741.4	742.1	742.8	743.5	744.2	744.7	745.1	745.6	746.1	746.1
152.5°	759.2	760.1	760.9	761.7	762.5	763.4	764.0	764.6	765.2	765.9	765.9
155°	785.1	785.6	786.1	786.6	787.1	787.6	788.4	789.2	790.1	790.9	791.1
157.5°	808.3	808.6	808.9	809.2	809.5	809.8	810.9	812.0	813.1	814.3	814.5
160°	822.6	822.9	823.0	823.2	823.3	823.5	824.6	825.6	826.6	827.6	827.7
162.5°	834.8	834.9	835.1	835.3	835.4	835.6	836.7	837.8	839.0	840.1	840.2
165°	851.4	851.3	851.3	851.3	851.3	851.3	852.4	853.6	854.7	856.0	856.2
167.5°	864.7	864.4	864.4	864.3	864.3	864.3	865.5	866.7	867.8	869.0	869.1
170°	872.5	872.2	872.0	871.8	871.7	871.5	872.7	873.8	875.0	876.2	876.3
172.5°	877.9	877.6	877.4	877.3	877.1	876.9	878.1	879.3	880.4	881.6	881.6
175°	884.5	884.1	883.7	883.4	883.1	882.7	883.9	885.0	886.3	887.5	887.5
177.5°	887.6	887.3	887.0	886.8	886.5	886.2	887.0	887.8	888.6	889.4	889.4
180°	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0



TEST NUMBER: P331472-840

CATALOG NUMBER: S122DIW-S290D710U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9
2.5°	572.5	572.1	572.1	570.5	572.1	572.1	572.5	574.3	574.9	575.2	574.5
5°	531.1	530.4	529.3	530.4	529.3	530.4	531.1	534.3	535.9	537.5	538.9
7.5°	490.1	487.4	487.0	484.2	487.0	487.4	490.1	491.6	494.8	498.5	501.8
10°	460.2	458.4	458.1	453.7	458.1	458.4	460.2	464.1	467.3	471.6	476.3
12.5°	437.5	433.0	433.9	431.4	433.9	433.0	437.5	437.5	441.2	443.9	451.1
15°	398.0	398.0	397.1	393.2	397.1	398.0	398.0	404.2	405.4	409.7	415.9
17.5°	369.7	369.2	367.1	368.2	367.1	369.2	369.7	374.3	375.1	380.8	386.0
20°	352.8	351.4	348.7	348.7	348.7	351.4	352.8	355.4	358.3	361.7	366.2
22.5°	336.9	336.8	333.9	334.8	333.9	336.8	336.9	339.2	342.0	345.8	349.4
25°	318.2	316.4	315.0	315.7	315.0	316.4	318.2	318.4	321.6	324.2	326.5
27.5°	300.4	299.4	299.3	297.5	299.3	299.4	300.4	301.0	302.9	304.4	306.5
30°	290.2	287.9	288.3	287.2	288.3	287.9	290.2	290.4	291.3	292.3	294.8
32.5°	278.4	277.6	277.2	276.2	277.2	277.6	278.4	278.8	280.7	281.7	283.6
35°	262.5	262.7	261.6	262.0	261.6	262.7	262.5	262.9	263.2	264.1	265.9
37.5°	248.4	249.1	248.6	248.7	248.6	249.1	248.4	248.6	248.9	249.0	249.6
40°	239.2	239.2	239.2	239.9	239.2	239.2	239.2	238.6	238.8	238.6	238.6
42.5°	230.5	230.0	229.7	229.6	229.7	230.0	230.5	228.8	229.6	228.8	228.5
45°	215.4	216.1	216.3	215.2	216.3	216.1	215.4	215.0	214.3	214.0	213.8
47.5°	201.8	201.9	201.8	202.8	201.8	201.9	201.8	201.2	200.2	199.8	198.6
50°	192.3	191.8	192.3	191.8	192.3	191.8	192.3	191.1	190.4	189.2	188.3
52.5°	182.2	182.3	182.0	181.9	182.0	182.3	182.2	180.7	180.4	179.9	178.4
55°	166.3	166.7	166.5	166.5	166.5	166.7	166.3	165.4	165.2	163.8	162.4
57.5°	150.0	150.4	150.7	149.7	150.7	150.4	150.0	149.8	149.7	148.1	146.7
60°	138.6	139.7	139.5	139.1	139.5	139.7	138.6	138.8	138.1	137.1	136.2
62.5°	128.1	128.6	128.5	128.4	128.5	128.6	128.1	127.0	126.7	125.8	124.9
65°	112.0	112.4	111.7	112.4	111.7	112.4	112.0	111.3	109.7	109.2	108.3
67.5°	94.5	94.7	95.2	95.5	95.2	94.7	94.5	94.8	93.8	92.9	92.7
70°	83.7	83.5	84.2	84.9	84.2	83.5	83.7	83.3	82.6	81.9	81.0
72.5°	72.3	72.8	72.6	73.1	72.6	72.8	72.3	72.4	71.8	70.9	70.0
75°	55.7	56.5	56.2	56.9	56.2	56.5	55.7	56.2	55.7	54.8	53.9
77.5°	40.3	40.4	40.3	40.7	40.3	40.4	40.3	40.7	40.2	40.5	39.4
80°	30.7	30.3	29.8	30.7	29.8	30.3	30.7	30.7	30.1	30.7	30.1
82.5°	21.4	21.6	21.2	21.2	21.2	21.6	21.4	21.9	21.6	21.9	21.2
85°	9.9	9.6	9.2	9.2	9.2	9.6	9.9	9.9	10.5	10.1	10.1
87.5°	6.9	6.7	6.7	6.6	6.7	6.7	6.9	6.8	6.8	7.3	7.3
90°	24.9	25.1	25.3	25.4	25.3	25.1	24.9	24.8	24.9	25.2	25.5
92.5°	24.1	24.2	24.2	24.2	24.2	24.2	24.1	24.1	24.1	24.0	23.9
95°	47.5	47.2	46.8	46.5	46.8	47.2	47.5	47.8	48.0	48.0	48.0
97.5°	80.6	80.6	80.5	80.5	80.5	80.6	80.6	80.6	80.6	80.6	80.6
100°	103.2	103.0	102.8	102.7	102.8	103.0	103.2	103.3	103.4	103.4	103.4
102.5°	128.4	128.2	128.1	127.8	128.1	128.2	128.4	128.6	128.6	128.4	128.3
105°	166.3	166.3	166.3	166.3	166.3	166.3	166.3	166.3	166.2	165.8	165.5
107.5°	204.9	204.2	203.4	202.7	203.4	204.2	204.9	205.7	206.0	205.9	205.7
110°	232.3	231.8	231.3	230.9	231.3	231.8	232.3	232.8	233.1	233.1	233.1



TEST NUMBER: P331472-840

CATALOG NUMBER: S122DIW-S290D710U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	258.9	258.5	258.1	257.8	258.1	258.5	258.9	259.2	259.6	260.0	260.4
115°	301.2	300.7	300.2	299.7	300.2	300.7	301.2	301.7	302.1	302.3	302.5
117.5°	341.2	340.7	340.2	339.7	340.2	340.7	341.2	341.7	342.2	342.6	343.1
120°	369.4	368.9	368.4	367.9	368.4	368.9	369.4	369.9	370.2	370.2	370.2
122.5°	396.6	396.3	395.9	395.6	395.9	396.3	396.6	397.0	397.4	397.8	398.2
125°	438.2	438.0	437.8	437.7	437.8	438.0	438.2	438.3	438.6	439.1	439.6
127.5°	477.6	477.1	476.6	476.1	476.6	477.1	477.6	478.2	478.7	479.3	479.9
130°	505.5	504.9	504.2	503.6	504.2	504.9	505.5	506.2	506.8	507.1	507.5
132.5°	531.6	531.0	530.5	530.0	530.5	531.0	531.6	532.1	532.7	533.4	534.2
135°	572.5	572.0	571.5	571.0	571.5	572.0	572.5	573.0	573.4	573.5	573.7
137.5°	610.2	609.6	608.8	608.1	608.8	609.6	610.2	610.9	611.3	611.4	611.5
140°	636.0	635.3	634.6	634.0	634.6	635.3	636.0	636.6	636.9	636.9	636.9
142.5°	659.3	658.6	658.0	657.3	658.0	658.6	659.3	660.0	660.2	660.1	660.0
145°	694.4	693.8	693.1	692.5	693.1	693.8	694.4	695.1	695.3	695.2	695.0
147.5°	725.7	725.0	724.4	723.8	724.4	725.0	725.7	726.3	726.4	726.0	725.7
150°	745.6	745.1	744.7	744.2	744.7	745.1	745.6	746.1	746.1	745.6	745.1
152.5°	765.2	764.6	764.0	763.4	764.0	764.6	765.2	765.9	765.9	765.2	764.6
155°	790.6	790.1	789.6	789.1	789.6	790.1	790.6	791.1	790.9	790.1	789.2
157.5°	813.6	812.8	812.0	811.2	812.0	812.8	813.6	814.5	814.3	813.1	812.0
160°	827.1	826.4	825.8	825.1	825.8	826.4	827.1	827.7	827.6	826.6	825.6
162.5°	839.4	838.7	837.9	837.1	837.9	838.7	839.4	840.2	840.1	839.0	837.8
165°	855.3	854.4	853.6	852.8	853.6	854.4	855.3	856.2	856.0	854.7	853.6
167.5°	868.3	867.4	866.6	865.7	866.6	867.4	868.3	869.1	869.0	867.8	866.7
170°	875.3	874.2	873.2	872.2	873.2	874.2	875.3	876.3	876.2	875.0	873.8
172.5°	880.7	879.7	878.7	877.7	878.7	879.7	880.7	881.6	881.6	880.4	879.3
175°	886.5	885.6	884.5	883.5	884.5	885.6	886.5	887.5	887.5	886.3	885.0
177.5°	888.6	887.8	887.0	886.2	887.0	887.8	888.6	889.4	889.4	888.6	887.8
180°	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0



TEST NUMBER: P331472-840

CATALOG NUMBER: S122DIW-S290D710U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9
2.5°	573.6	575.6	578.8	582.1	584.1	587.9	589.1	590.9	592.5	596.3	600.4
5°	540.5	543.7	551.3	555.4	561.1	567.7	572.1	576.7	581.8	590.5	598.5
7.5°	504.9	510.3	519.8	527.5	535.6	545.1	552.0	561.1	568.7	581.0	592.7
10°	481.3	488.9	497.4	506.5	518.0	528.1	537.8	549.2	558.4	573.1	586.8
12.5°	460.0	461.1	473.3	483.4	499.1	511.6	522.7	537.5	546.4	563.9	578.3
15°	422.8	429.7	440.7	448.7	467.3	483.1	498.8	514.1	524.4	546.0	565.0
17.5°	391.4	397.8	409.1	422.2	435.6	451.3	471.5	487.8	501.8	526.4	549.0
20°	371.6	379.4	390.9	404.5	416.2	433.3	450.8	469.4	484.5	512.3	538.7
22.5°	354.8	360.9	370.2	383.5	396.3	412.0	431.1	451.4	467.3	497.3	523.9
25°	331.0	336.1	342.0	353.0	367.5	384.8	399.6	421.9	445.0	473.0	505.3
27.5°	309.6	313.3	318.5	328.2	339.4	355.5	372.0	393.1	416.5	446.9	481.0
30°	296.6	298.9	304.2	312.3	323.3	335.9	352.6	372.7	396.7	427.4	461.3
32.5°	285.3	287.3	290.8	298.4	308.0	318.8	333.9	354.1	376.8	407.0	444.6
35°	268.2	269.7	272.8	278.9	284.3	294.8	307.4	325.8	347.1	376.0	415.0
37.5°	251.2	253.4	255.2	257.8	264.6	271.6	282.5	298.0	318.9	348.1	385.3
40°	239.9	241.8	244.6	245.7	251.2	257.4	266.3	280.5	301.6	328.3	364.6
42.5°	228.5	230.5	232.1	233.4	238.1	243.6	251.7	263.9	282.6	308.4	344.4
45°	213.1	213.4	215.0	217.5	219.7	223.7	229.4	239.9	254.4	278.7	311.3
47.5°	197.4	197.7	197.9	199.0	201.6	205.1	208.9	217.5	230.5	249.8	281.6
50°	186.9	186.5	186.9	187.8	189.5	192.5	196.8	203.0	213.6	231.7	260.8
52.5°	176.8	176.8	176.5	176.8	178.1	180.2	183.3	188.5	197.9	214.6	240.2
55°	161.5	160.4	160.6	159.7	161.8	162.2	164.5	168.8	177.1	188.5	212.7
57.5°	145.1	144.2	143.2	142.9	142.7	143.9	145.7	149.2	155.5	165.6	185.1
60°	134.6	133.5	132.1	131.7	131.7	132.4	133.3	135.8	141.8	150.7	166.7
62.5°	124.0	122.7	121.9	120.7	120.3	121.0	121.9	123.7	128.1	136.4	150.3
65°	107.6	105.9	104.8	104.6	104.1	103.5	103.9	105.7	109.2	115.8	126.8
67.5°	91.1	89.6	89.4	88.0	87.4	87.5	87.4	88.9	91.0	96.7	104.9
70°	80.3	79.2	78.7	77.6	77.1	76.6	76.1	77.6	79.6	84.4	91.5
72.5°	69.3	68.3	67.4	66.3	66.4	65.9	65.8	66.8	68.4	72.8	78.4
75°	53.4	53.7	52.5	51.4	51.2	50.7	50.7	51.4	52.1	55.5	59.9
77.5°	38.8	38.6	37.7	37.3	37.1	36.6	37.1	37.5	37.9	40.2	43.3
80°	29.6	29.6	28.5	28.5	28.2	27.6	28.2	27.8	28.7	31.0	33.2
82.5°	21.1	20.8	20.7	20.4	20.3	19.8	20.1	20.6	21.0	22.5	23.9
85°	10.3	10.3	10.1	9.9	10.1	9.9	10.1	10.3	10.5	11.2	12.4
87.5°	7.4	7.7	7.1	6.6	5.8	5.3	4.8	4.6	4.6	4.4	4.1
90°	25.9	26.3	22.5	18.9	15.2	11.6	8.8	6.8	4.7	2.7	0.7
92.5°	23.9	23.8	22.9	22.1	21.2	20.4	19.2	17.8	16.3	14.8	13.3
95°	48.0	48.0	47.7	47.3	47.0	46.7	45.6	43.9	42.3	40.6	39.0
97.5°	80.6	80.6	80.0	79.4	78.8	78.1	77.1	75.5	74.1	72.6	71.2
100°	103.4	103.4	102.9	102.4	101.9	101.4	100.5	99.2	97.9	96.5	95.1
102.5°	128.2	127.9	127.3	126.7	126.1	125.4	124.6	123.5	122.5	121.4	120.4
105°	165.2	164.9	164.5	164.2	163.9	163.5	163.1	162.6	162.1	161.6	161.1
107.5°	205.6	205.5	205.5	205.5	205.5	205.5	205.1	204.4	203.7	202.9	202.2
110°	233.1	233.1	233.1	233.1	233.1	233.1	232.6	231.6	230.6	229.5	228.5



TEST NUMBER: P331472-840

CATALOG NUMBER: S122DIW-S290D710U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	260.8	261.3	261.4	261.5	261.7	261.8	261.4	260.3	259.3	258.3	257.3
115°	302.6	302.8	303.1	303.4	303.8	304.1	303.8	302.8	301.7	300.7	299.7
117.5°	343.5	343.9	344.8	345.7	346.6	347.5	347.3	346.0	344.7	343.4	342.0
120°	370.2	370.2	371.5	372.8	374.2	375.5	375.5	374.2	372.8	371.5	370.2
122.5°	398.6	399.0	399.9	400.8	401.7	402.7	402.3	400.7	399.2	397.6	396.0
125°	440.1	440.6	441.1	441.6	442.1	442.6	442.1	440.6	439.1	437.7	436.2
127.5°	480.5	481.1	481.7	482.3	482.9	483.5	482.8	480.9	479.1	477.2	475.2
130°	507.8	508.1	508.4	508.8	509.1	509.4	508.5	506.3	504.1	502.0	499.8
132.5°	534.9	535.6	535.6	535.5	535.4	535.4	534.4	532.7	531.0	529.2	527.5
135°	573.8	574.0	573.7	573.4	573.0	572.7	571.6	569.8	567.9	566.1	564.3
137.5°	611.7	611.8	611.4	611.0	610.5	610.1	609.0	607.6	606.1	604.6	603.1
140°	636.9	636.9	636.1	635.3	634.5	633.6	632.5	631.0	629.4	627.9	626.5
142.5°	659.8	659.7	659.1	658.6	658.0	657.5	656.4	655.0	653.5	652.0	650.5
145°	694.8	694.7	693.7	692.7	691.7	690.6	689.6	688.4	687.2	686.1	684.9
147.5°	725.3	725.0	724.3	723.6	723.0	722.3	721.2	719.8	718.4	717.0	715.7
150°	744.7	744.2	743.5	742.8	742.1	741.4	740.6	739.6	738.6	737.6	736.6
152.5°	764.0	763.4	762.5	761.7	760.9	760.1	759.2	758.2	757.2	756.2	755.2
155°	788.4	787.6	787.1	786.6	786.1	785.6	785.1	784.6	784.1	783.6	783.0
157.5°	810.9	809.8	809.5	809.2	808.9	808.6	808.3	807.9	807.6	807.3	806.9
160°	824.6	823.5	823.3	823.2	823.0	822.9	822.6	822.3	821.9	821.6	821.3
162.5°	836.7	835.6	835.4	835.3	835.1	834.9	834.8	834.7	834.7	834.6	834.5
165°	852.4	851.3	851.3	851.3	851.3	851.3	851.4	851.5	851.7	851.8	852.0
167.5°	865.5	864.3	864.3	864.3	864.4	864.4	864.7	865.3	865.8	866.3	866.8
170°	872.7	871.5	871.7	871.8	872.0	872.2	872.5	873.0	873.5	874.0	874.5
172.5°	878.1	876.9	877.1	877.3	877.4	877.6	877.9	878.4	878.9	879.4	879.9
175°	883.9	882.7	883.1	883.4	883.7	884.1	884.5	885.0	885.6	886.1	886.5
177.5°	887.0	886.2	886.5	886.8	887.0	887.3	887.6	888.0	888.4	888.8	889.2
180°	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0



TEST NUMBER: P331472-840

CATALOG NUMBER: S122DIW-S290D710U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9	596.9
2.5°	600.1	601.0	603.9	606.8	610.2	611.1	612.5	611.3	610.9	614.3	616.9
5°	601.8	605.8	613.9	621.3	627.4	631.8	636.4	638.2	641.7	646.4	652.5
7.5°	599.8	607.8	620.5	631.2	642.8	651.2	657.7	663.4	670.1	679.2	689.2
10°	597.6	608.3	623.8	636.8	651.1	661.9	670.8	679.5	689.6	702.3	715.3
12.5°	593.6	606.3	625.6	641.1	659.3	669.9	682.0	700.7	711.7	729.2	747.6
15°	585.4	599.7	626.5	645.5	666.2	686.4	708.6	726.5	744.4	754.8	780.6
17.5°	573.4	594.2	624.0	646.2	672.5	704.2	729.2	749.5	770.1	786.9	799.9
20°	563.6	586.3	620.4	646.9	678.1	712.3	740.9	761.6	779.5	793.6	801.5
22.5°	551.4	580.0	613.0	644.2	684.0	717.8	747.9	764.2	779.1	786.0	789.1
25°	532.0	566.4	603.8	641.9	686.8	722.7	750.1	760.0	764.4	757.7	746.7
27.5°	511.1	549.5	593.2	637.5	685.1	719.5	739.2	737.7	730.3	708.7	691.6
30°	495.5	537.8	584.7	633.2	680.9	714.4	725.8	714.4	697.6	673.6	648.9
32.5°	479.2	522.9	575.7	626.9	673.2	702.7	705.1	685.4	659.4	632.1	601.5
35°	454.4	501.7	558.9	613.0	656.8	675.4	664.4	629.4	598.7	561.4	519.6
37.5°	426.5	478.7	535.9	592.6	632.3	637.1	609.8	573.1	529.7	485.7	436.6
40°	405.6	460.9	519.9	576.9	612.1	607.0	572.1	531.8	480.2	426.5	380.8
42.5°	386.9	442.1	502.2	558.3	586.3	572.5	531.8	482.2	426.8	376.2	334.4
45°	354.5	411.3	472.8	526.9	543.0	518.0	464.1	409.0	354.5	312.3	279.2
47.5°	323.0	379.2	440.1	487.7	493.3	459.7	400.8	344.2	297.2	262.9	239.5
50°	299.8	356.3	416.6	459.1	457.2	416.6	356.1	302.2	262.9	235.1	219.5
52.5°	279.1	332.4	390.3	429.0	419.2	375.0	317.1	269.2	237.0	215.3	201.2
55°	246.8	296.2	351.2	382.2	364.3	315.2	266.3	227.8	203.9	187.6	176.6
57.5°	214.8	261.1	308.2	327.3	307.5	262.2	221.5	193.5	175.5	163.5	156.3
60°	195.0	235.4	277.3	293.9	270.2	229.8	197.7	172.8	158.2	148.5	142.0
62.5°	175.2	211.4	251.0	259.9	238.3	204.2	175.7	154.9	143.1	134.3	128.3
65°	148.1	177.8	207.8	213.8	193.9	167.4	145.0	131.5	120.9	114.5	109.7
67.5°	121.6	145.3	166.6	171.4	153.9	135.6	119.4	107.6	100.5	95.1	91.0
70°	105.7	124.6	142.0	145.9	131.9	115.6	103.2	93.8	87.4	82.8	78.9
72.5°	89.1	104.7	119.3	121.9	110.5	98.0	87.9	80.4	74.7	71.8	68.1
75°	68.2	77.4	88.6	89.3	81.7	74.1	66.3	61.5	58.5	54.8	53.0
77.5°	48.1	55.2	61.7	62.9	58.5	53.3	49.0	45.1	42.6	40.9	39.2
80°	36.7	42.4	45.2	46.8	43.6	39.9	37.4	34.8	33.2	32.1	31.0
82.5°	26.3	29.8	32.3	33.6	31.8	29.6	27.2	25.7	24.4	23.5	23.1
85°	13.3	14.9	16.6	17.0	16.6	15.6	14.2	14.2	13.5	13.3	13.3
87.5°	5.2	6.3	6.7	7.6	7.8	8.6	9.3	9.8	10.4	10.1	9.9
90°	2.7	4.7	6.8	8.8	11.6	15.2	18.9	22.5	26.3	25.9	25.5
92.5°	14.8	16.3	17.8	19.2	20.4	21.2	22.1	22.9	23.8	23.9	23.9
95°	40.6	42.3	43.9	45.6	46.7	47.0	47.3	47.7	48.0	48.0	48.0
97.5°	72.6	74.1	75.5	77.1	78.1	78.8	79.4	80.0	80.6	80.6	80.6
100°	96.5	97.9	99.2	100.5	101.4	101.9	102.4	102.9	103.4	103.4	103.4
102.5°	121.4	122.5	123.5	124.6	125.4	126.1	126.7	127.3	127.9	128.2	128.3
105°	161.6	162.1	162.6	163.1	163.5	163.9	164.2	164.5	164.9	165.2	165.5
107.5°	202.9	203.7	204.4	205.1	205.5	205.5	205.5	205.5	205.5	205.6	205.7
110°	229.5	230.6	231.6	232.6	233.1	233.1	233.1	233.1	233.1	233.1	233.1





TEST NUMBER: P331472-840

CATALOG NUMBER: S122DIW-S290D710U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	258.3	259.3	260.3	261.4	261.8	261.7	261.5	261.4	261.3	260.8	260.4
115°	300.7	301.7	302.8	303.8	304.1	303.8	303.4	303.1	302.8	302.6	302.5
117.5°	343.4	344.7	346.0	347.3	347.5	346.6	345.7	344.8	343.9	343.5	343.1
120°	371.5	372.8	374.2	375.5	375.5	374.2	372.8	371.5	370.2	370.2	370.2
122.5°	397.6	399.2	400.7	402.3	402.7	401.7	400.8	399.9	399.0	398.6	398.2
125°	437.7	439.1	440.6	442.1	442.6	442.1	441.6	441.1	440.6	440.1	439.6
127.5°	477.2	479.1	480.9	482.8	483.5	482.9	482.3	481.7	481.1	480.5	479.9
130°	502.0	504.1	506.3	508.5	509.4	509.1	508.8	508.4	508.1	507.8	507.5
132.5°	529.2	531.0	532.7	534.4	535.4	535.4	535.5	535.6	535.6	534.9	534.2
135°	566.1	567.9	569.8	571.6	572.7	573.0	573.4	573.7	574.0	573.8	573.7
137.5°	604.6	606.1	607.6	609.0	610.1	610.5	611.0	611.4	611.8	611.7	611.5
140°	627.9	629.4	631.0	632.5	633.6	634.5	635.3	636.1	636.9	636.9	636.9
142.5°	652.0	653.5	655.0	656.4	657.5	658.0	658.6	659.1	659.7	659.8	660.0
145°	686.1	687.2	688.4	689.6	690.6	691.7	692.7	693.7	694.7	694.8	695.0
147.5°	717.0	718.4	719.8	721.2	722.3	723.0	723.6	724.3	725.0	725.3	725.7
150°	737.6	738.6	739.6	740.6	741.4	742.1	742.8	743.5	744.2	744.7	745.1
152.5°	756.2	757.2	758.2	759.2	760.1	760.9	761.7	762.5	763.4	764.0	764.6
155°	783.6	784.1	784.6	785.1	785.6	786.1	786.6	787.1	787.6	788.4	789.2
157.5°	807.3	807.6	807.9	808.3	808.6	808.9	809.2	809.5	809.8	810.9	812.0
160°	821.6	821.9	822.3	822.6	822.9	823.0	823.2	823.3	823.5	824.6	825.6
162.5°	834.6	834.7	834.7	834.8	834.9	835.1	835.3	835.4	835.6	836.7	837.8
165°	851.8	851.7	851.5	851.4	851.3	851.3	851.3	851.3	851.3	852.4	853.6
167.5°	866.3	865.8	865.3	864.7	864.4	864.4	864.3	864.3	864.3	865.5	866.7
170°	874.0	873.5	873.0	872.5	872.2	872.0	871.8	871.7	871.5	872.7	873.8
172.5°	879.4	878.9	878.4	877.9	877.6	877.4	877.3	877.1	876.9	878.1	879.3
175°	886.1	885.6	885.0	884.5	884.1	883.7	883.4	883.1	882.7	883.9	885.0
177.5°	888.8	888.4	888.0	887.6	887.3	887.0	886.8	886.5	886.2	887.0	887.8
180°	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0



TEST NUMBER: P331472-840

CATALOG NUMBER: S122DIW-S290D710U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	596.9	596.9	596.9	596.9	596.9	596.9	596.9
2.5°	619.1	621.7	621.7	622.1	625.0	624.6	624.4
5°	658.8	662.8	663.2	667.3	670.0	669.1	666.6
7.5°	696.3	703.6	709.1	712.2	715.8	718.0	717.0
10°	726.1	736.6	743.1	747.4	752.7	756.6	755.2
12.5°	753.1	765.6	774.5	781.9	782.5	787.6	784.2
15°	795.2	808.4	809.8	815.3	819.7	819.2	819.4
17.5°	809.0	813.2	814.2	814.3	814.4	812.7	809.2
20°	804.1	802.4	798.6	795.6	790.3	789.6	785.1
22.5°	780.5	775.5	765.7	759.2	751.0	748.9	747.6
25°	734.4	723.1	707.5	692.6	688.4	680.4	682.7
27.5°	670.9	653.4	636.4	624.4	613.4	601.4	604.8
30°	626.3	606.5	582.7	564.3	552.6	541.2	539.1
32.5°	573.1	544.1	517.6	501.4	483.4	476.2	468.3
35°	481.3	453.0	426.7	403.9	390.9	380.8	371.6
37.5°	398.8	366.3	345.0	326.6	317.1	311.3	312.9
40°	347.6	319.1	303.5	289.5	280.7	276.7	277.6
42.5°	306.1	284.8	272.0	262.4	256.2	253.9	253.4
45°	259.0	247.1	236.5	231.1	228.0	225.5	223.9
47.5°	226.9	217.1	211.2	207.9	205.3	202.8	202.7
50°	207.6	201.2	197.0	193.6	191.6	189.8	191.4
52.5°	192.9	187.0	182.9	179.9	179.0	177.4	177.3
55°	171.2	166.5	163.6	160.8	159.5	158.5	157.3
57.5°	151.3	146.9	144.2	142.5	139.9	139.0	138.6
60°	137.1	133.7	131.0	128.7	127.5	125.7	125.7
62.5°	124.1	120.7	118.2	116.4	114.5	113.8	114.0
65°	105.3	102.5	100.0	98.2	97.8	96.3	96.8
67.5°	88.0	86.1	83.4	82.4	81.6	80.9	80.3
70°	76.3	74.5	73.2	71.8	71.1	71.1	71.1
72.5°	66.7	64.4	63.6	61.9	62.3	61.6	60.8
75°	51.6	50.2	49.6	48.9	47.8	47.8	47.8
77.5°	38.0	37.6	36.8	36.1	35.7	35.5	35.6
80°	29.4	29.1	28.7	28.7	28.2	28.0	27.6
82.5°	22.6	22.0	21.7	21.5	21.4	21.4	21.3
85°	12.8	12.4	12.4	12.6	12.1	12.1	12.4
87.5°	10.0	9.9	9.7	9.8	10.0	9.8	9.9
90°	25.2	24.9	24.8	24.9	25.1	25.3	25.4
92.5°	24.0	24.1	24.1	24.1	24.2	24.2	24.2
95°	48.0	48.0	47.8	47.5	47.2	46.8	46.5
97.5°	80.6	80.6	80.6	80.6	80.6	80.5	80.5
100°	103.4	103.4	103.3	103.2	103.0	102.8	102.7
102.5°	128.4	128.6	128.6	128.4	128.2	128.1	127.8
105°	165.8	166.2	166.3	166.3	166.3	166.3	166.3
107.5°	205.9	206.0	205.7	204.9	204.2	203.4	202.7
110°	233.1	233.1	232.8	232.3	231.8	231.3	230.9



TEST NUMBER: P331472-840

CATALOG NUMBER: S122DIW-S290D710U840-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	260.0	259.6	259.2	258.9	258.5	258.1	257.8
115°	302.3	302.1	301.7	301.2	300.7	300.2	299.7
117.5°	342.6	342.2	341.7	341.2	340.7	340.2	339.7
120°	370.2	370.2	369.9	369.4	368.9	368.4	367.9
122.5°	397.8	397.4	397.0	396.6	396.3	395.9	395.6
125°	439.1	438.6	438.3	438.2	438.0	437.8	437.7
127.5°	479.3	478.7	478.2	477.6	477.1	476.6	476.1
130°	507.1	506.8	506.2	505.5	504.9	504.2	503.6
132.5°	533.4	532.7	532.1	531.6	531.0	530.5	530.0
135°	573.5	573.4	573.0	572.5	572.0	571.5	571.0
137.5°	611.4	611.3	610.9	610.2	609.6	608.8	608.1
140°	636.9	636.9	636.6	636.0	635.3	634.6	634.0
142.5°	660.1	660.2	660.0	659.3	658.6	658.0	657.3
145°	695.2	695.3	695.1	694.4	693.8	693.1	692.5
147.5°	726.0	726.4	726.3	725.7	725.0	724.4	723.8
150°	745.6	746.1	746.1	745.6	745.1	744.7	744.2
152.5°	765.2	765.9	765.9	765.2	764.6	764.0	763.4
155°	790.1	790.9	791.1	790.6	790.1	789.6	789.1
157.5°	813.1	814.3	814.5	813.6	812.8	812.0	811.2
160°	826.6	827.6	827.7	827.1	826.4	825.8	825.1
162.5°	839.0	840.1	840.2	839.4	838.7	837.9	837.1
165°	854.7	856.0	856.2	855.3	854.4	853.6	852.8
167.5°	867.8	869.0	869.1	868.3	867.4	866.6	865.7
170°	875.0	876.2	876.3	875.3	874.2	873.2	872.2
172.5°	880.4	881.6	881.6	880.7	879.7	878.7	877.7
175°	886.3	887.5	887.5	886.5	885.6	884.5	883.5
177.5°	888.6	889.4	889.4	888.6	887.8	887.0	886.2
180°	888.0	888.0	888.0	888.0	888.0	888.0	888.0

(END OF REPORT)