

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331778-840

Luminaire Tested: **S122RDIW-S290D1240U840-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331778-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S290D1240U840-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1240 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5485.9 lumens
Efficiency: N/A
Efficacy: 117.7 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 46.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331778-840

CATALOG NUMBER: S122RDIW-S290D1240U840-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331778-840

CATALOG NUMBER: S122RDIW-S290D1240U840-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	100	100	100	100	89	89	89	89	67	67	67	47	47	47	29	29	29	21
1	92	88	84	81	81	78	75	72	59	57	55	42	41	40	26	26	25	18
2	84	77	71	66	74	68	64	60	52	49	46	37	35	34	24	23	22	16
3	76	68	61	56	67	60	55	50	46	42	39	33	31	29	21	20	19	14
4	70	60	53	47	62	54	47	43	41	37	34	30	27	25	19	18	17	12
5	64	53	46	40	57	48	41	37	37	33	29	27	24	22	17	16	15	11
6	59	48	40	35	52	43	36	32	33	29	25	24	21	19	16	14	13	10
7	55	43	36	31	48	39	32	28	30	26	22	22	19	17	15	13	12	9
8	51	39	32	27	45	35	29	25	27	23	20	20	17	15	14	12	11	8
9	47	36	29	24	42	32	26	22	25	21	18	19	16	14	13	11	10	7
10	44	33	26	21	39	29	24	20	23	19	16	17	14	12	12	10	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10658	10658	10658	10658
5°	11904	10726	9511	10726
10°	13209	10650	8243	10650
15°	13857	10494	6496	10494
20°	12014	10263	5620	10263
25°	7878	9948	5018	9948
30°	5304	9562	4542	9562
35°	4295	9079	4096	9079
40°	3819	8553	3792	8553
45°	3457	7935	3382	7935
50°	3145	7322	3135	7322
55°	2956	6643	2919	6643
60°	2474	6022	2444	6022
65°	2086	5467	2365	5467
70°	1926	4881	2233	4881
75°	1803	4255	2059	4255
80°	1664	3505	1832	3505
85°	1538	2760	1612	2760



TEST NUMBER: P331778-840

CATALOG NUMBER: S122RDIW-S290D1240U840-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	62.6	1.1
10°-20°	174.4	3.2
20°-30°	224.7	4.1
30°-40°	213.5	3.9
40°-50°	182.9	3.3
50°-60°	139.3	2.5
60°-70°	88.1	1.6
70°-80°	44.0	0.8
80°-90°	17.6	0.3
90°-100°	98.3	1.8
100°-110°	305.4	5.6
110°-120°	522.0	9.5
120°-130°	686.4	12.5
130°-140°	770.4	14.0
140°-150°	755.4	13.8
150°-160°	633.6	11.5
160°-170°	420.3	7.7
170°-180°	146.9	2.7
0°-30°	461.7	8.4
0°-40°	675.2	12.3
0°-60°	997.5	18.2
0°-90°	1147.1	20.9
90°-120°	925.7	16.9
90°-150°	3138.0	57.2
90°-180°	4339.0	79.1
0°-180°	5485.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	660	660	660	660	660	
5°	734	662	587	662	734	72
15°	829	628	389	628	829	224
25°	442	558	282	558	442	210
35°	218	461	208	461	218	139
45°	151	348	148	348	151	117
55°	105	236	104	236	105	92
65°	55	143	62	143	55	56
75°	29	68	33	68	29	31
85°	8	15	9	15	8	10
90°	44	1	44	1	44	20
95°	81	68	81	68	81	91
105°	291	282	291	282	291	306
115°	524	524	524	524	524	517
125°	765	762	765	762	765	682
135°	998	986	998	986	998	768
145°	1210	1197	1210	1197	1210	756
155°	1379	1368	1379	1368	1379	635
165°	1490	1489	1490	1489	1490	420
175°	1544	1549	1544	1549	1544	147
180°	1552	1552	1552	1552	1552	



TEST NUMBER: P331778-840

CATALOG NUMBER: S122RDIW-S290D1240U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1
2.5°	687.0	687.5	688.1	686.8	686.8	685.7	683.3	681.5	676.3	675.6	675.6
5°	734.5	734.1	735.0	732.0	727.9	726.9	722.6	716.8	710.8	704.3	702.9
7.5°	781.7	781.0	779.2	778.7	775.6	768.6	761.6	754.2	744.3	734.6	729.7
10°	805.7	813.2	808.6	800.6	802.1	791.4	785.7	775.8	767.5	753.1	749.9
12.5°	829.1	832.1	830.6	826.1	824.0	816.6	808.8	800.2	785.0	772.0	760.7
15°	829.0	833.3	834.6	833.1	834.2	833.8	829.7	822.6	809.3	795.1	782.6
17.5°	767.8	770.8	778.4	783.5	789.9	803.4	810.2	812.7	810.8	802.6	794.0
20°	699.2	694.2	715.3	726.0	735.2	758.1	777.9	785.5	797.6	797.4	795.1
22.5°	601.9	603.1	623.1	635.9	662.7	685.7	708.1	736.6	760.1	775.7	784.8
25°	442.2	451.0	470.9	488.4	518.2	560.9	599.7	644.6	687.0	720.5	752.5
27.5°	332.1	332.9	348.6	364.8	382.4	417.4	466.3	519.9	580.4	630.4	687.7
30°	284.5	283.1	289.7	299.6	314.8	341.8	378.5	431.2	491.6	566.8	633.8
32.5°	250.6	250.7	255.8	263.1	275.6	293.9	319.0	361.9	418.9	492.9	571.4
35°	217.9	217.7	221.4	226.6	231.9	243.6	260.8	283.3	322.6	391.5	471.8
37.5°	194.4	195.4	197.2	200.6	206.3	212.9	223.2	238.3	266.2	307.1	374.6
40°	181.2	181.7	184.2	186.9	190.4	195.4	203.9	216.1	236.5	269.0	318.4
42.5°	169.2	169.6	171.4	173.9	176.6	181.7	188.7	199.2	215.8	241.2	281.9
45°	151.4	151.4	153.0	154.1	157.1	161.7	167.4	176.2	187.6	206.4	233.5
47.5°	134.8	134.8	135.9	137.8	139.8	143.3	149.0	156.1	164.4	178.9	202.1
50°	125.2	125.5	126.1	127.7	129.0	132.1	136.5	142.7	151.4	162.7	181.9
52.5°	117.5	117.4	118.3	119.0	119.8	122.0	125.3	130.8	138.6	148.3	164.3
55°	105.0	104.1	105.5	106.6	107.3	108.3	110.1	113.5	120.2	128.5	140.4
57.5°	89.5	89.1	90.1	91.1	93.3	95.7	97.4	99.5	102.9	108.9	120.7
60°	76.6	76.6	78.7	79.4	81.9	85.1	88.4	90.2	93.6	97.5	106.2
62.5°	65.2	65.4	66.3	67.1	68.5	72.4	77.0	81.0	84.2	88.0	93.7
65°	54.6	55.0	55.0	55.5	56.5	57.4	59.2	62.4	68.2	73.4	77.8
67.5°	46.4	46.5	46.7	47.1	47.3	48.3	49.1	50.5	51.8	56.8	62.2
70°	40.8	41.5	41.3	41.7	42.0	42.4	43.3	44.0	46.2	47.3	50.5
72.5°	35.6	36.2	36.2	36.5	37.1	37.2	37.9	38.6	39.9	40.8	42.6
75°	28.9	28.7	28.9	29.4	29.6	29.8	29.8	30.7	31.4	32.3	33.5
77.5°	22.3	22.5	22.5	22.5	22.6	23.0	22.9	23.3	24.0	24.5	25.0
80°	17.9	18.1	17.9	18.1	18.4	18.6	18.4	18.6	19.3	19.7	19.7
82.5°	13.8	13.9	14.0	14.0	14.1	14.1	14.5	14.5	15.0	14.9	15.1
85°	8.3	8.1	8.1	8.1	8.3	8.5	8.3	8.3	8.5	8.5	8.5
87.5°	11.8	11.9	11.9	11.8	11.8	11.8	11.9	12.2	12.2	12.4	11.0
90°	44.5	44.2	43.9	43.6	43.3	43.5	44.1	44.6	45.2	45.8	39.4
92.5°	42.4	42.4	42.3	42.2	42.2	42.1	42.0	41.9	41.7	41.6	40.1
95°	81.2	81.8	82.3	82.9	83.5	83.8	83.8	83.8	83.8	83.8	83.2
97.5°	140.7	140.7	140.8	140.8	140.9	140.9	140.9	140.9	140.9	140.9	139.8
100°	179.4	179.7	180.0	180.3	180.6	180.7	180.7	180.7	180.7	180.7	179.9
102.5°	223.4	223.7	224.0	224.3	224.6	224.6	224.4	224.1	223.9	223.7	222.6
105°	290.7	290.7	290.7	290.7	290.7	290.4	289.8	289.2	288.6	288.1	287.5
107.5°	354.1	355.4	356.8	358.1	359.4	360.0	359.7	359.5	359.3	359.0	359.0
110°	403.3	404.1	405.1	406.0	406.8	407.3	407.3	407.3	407.3	407.3	407.3



TEST NUMBER: P331778-840

CATALOG NUMBER: S122RDIW-S290D1240U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	450.4	451.1	451.7	452.3	453.0	453.6	454.3	455.0	455.8	456.5	456.7
115°	523.8	524.6	525.5	526.4	527.3	527.9	528.2	528.5	528.8	529.0	529.6
117.5°	593.7	594.6	595.4	596.3	597.2	597.9	598.6	599.4	600.1	600.8	602.4
120°	643.0	643.8	644.7	645.5	646.4	646.8	646.8	646.8	646.8	646.8	649.1
122.5°	691.2	691.8	692.4	693.1	693.7	694.4	695.1	695.8	696.4	697.1	698.7
125°	764.7	765.0	765.3	765.6	765.9	766.5	767.3	768.2	769.1	769.9	770.8
127.5°	831.7	832.7	833.6	834.6	835.5	836.5	837.5	838.6	839.6	840.6	841.7
130°	879.9	881.1	882.3	883.4	884.6	885.4	886.1	886.7	887.2	887.8	888.4
132.5°	926.0	927.0	927.9	928.9	929.8	930.9	932.1	933.4	934.7	935.9	935.8
135°	997.7	998.7	999.6	1000.4	1001.3	1001.9	1002.2	1002.5	1002.7	1003.0	1002.5
137.5°	1062.8	1063.9	1065.1	1066.2	1067.4	1068.1	1068.3	1068.5	1068.8	1069.0	1068.2
140°	1107.8	1108.9	1110.1	1111.3	1112.5	1113.0	1113.0	1113.0	1113.0	1113.0	1111.6
142.5°	1148.6	1149.8	1150.9	1152.2	1153.3	1153.8	1153.6	1153.3	1153.1	1152.9	1151.9
145°	1209.9	1211.1	1212.2	1213.5	1214.6	1215.0	1214.8	1214.5	1214.2	1213.9	1212.1
147.5°	1264.7	1265.8	1266.9	1268.0	1269.1	1269.3	1268.7	1268.0	1267.4	1266.8	1265.6
150°	1300.3	1301.1	1302.0	1302.9	1303.7	1303.7	1302.9	1302.0	1301.1	1300.3	1299.1
152.5°	1333.8	1334.9	1336.1	1337.1	1338.2	1338.2	1337.1	1336.1	1334.9	1333.8	1332.4
155°	1378.9	1379.7	1380.6	1381.5	1382.3	1382.0	1380.6	1379.2	1377.7	1376.2	1375.3
157.5°	1417.5	1419.0	1420.4	1421.8	1423.2	1422.9	1420.9	1419.0	1416.9	1415.0	1414.4
160°	1441.7	1442.9	1444.0	1445.2	1446.3	1446.0	1444.3	1442.6	1440.8	1439.1	1438.8
162.5°	1462.7	1464.0	1465.4	1466.8	1468.2	1467.9	1465.9	1464.0	1462.0	1460.1	1459.8
165°	1490.2	1491.6	1493.1	1494.5	1495.9	1495.7	1493.6	1491.6	1489.6	1487.5	1487.5
167.5°	1512.7	1514.2	1515.7	1517.2	1518.7	1518.4	1516.4	1514.4	1512.4	1510.3	1510.4
170°	1524.2	1525.9	1527.7	1529.4	1531.2	1531.1	1528.9	1526.9	1524.9	1522.9	1523.2
172.5°	1533.6	1535.4	1537.1	1538.8	1540.5	1540.4	1538.4	1536.4	1534.4	1532.3	1532.6
175°	1543.8	1545.6	1547.3	1549.0	1550.8	1550.6	1548.6	1546.6	1544.6	1542.5	1543.1
177.5°	1548.5	1549.9	1551.4	1552.8	1554.1	1554.1	1552.8	1551.4	1549.9	1548.5	1549.0
180°	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7



TEST NUMBER: P331778-840

CATALOG NUMBER: S122RDIW-S290D1240U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1
2.5°	676.0	674.5	673.2	669.9	668.2	664.6	664.1	663.9	659.1	654.5	653.2
5°	699.2	695.5	690.0	683.6	676.9	670.0	665.5	661.8	652.6	643.9	638.8
7.5°	722.6	714.7	705.2	693.1	682.9	671.6	663.1	655.5	642.5	630.0	621.6
10°	740.0	727.2	714.6	697.8	684.7	671.9	659.9	649.6	635.0	618.4	606.7
12.5°	750.8	736.7	719.3	703.0	686.0	669.6	653.7	640.5	623.2	606.1	592.3
15°	765.5	750.3	729.2	705.8	684.1	662.7	644.4	627.8	605.4	584.9	567.9
17.5°	777.5	756.6	734.0	706.9	681.7	654.6	631.0	609.9	584.8	560.2	540.2
20°	781.3	760.6	734.5	707.4	677.6	645.7	620.3	597.3	570.5	543.6	520.7
22.5°	778.9	762.9	733.8	701.4	670.9	637.5	608.7	582.1	552.3	524.9	498.4
25°	762.8	757.2	729.7	694.4	659.5	620.8	587.4	558.4	524.4	495.0	466.2
27.5°	725.0	736.9	719.8	682.2	643.4	601.9	564.4	531.3	496.0	463.0	434.2
30°	688.6	715.9	708.6	673.7	630.4	589.6	547.5	512.9	475.3	441.3	412.9
32.5°	638.9	684.0	691.2	662.0	617.1	572.3	528.3	493.8	454.5	418.8	391.0
35°	559.7	627.1	658.1	639.5	594.6	546.1	500.8	460.6	421.1	385.9	358.3
37.5°	465.2	557.1	608.7	610.1	568.8	518.5	469.0	429.1	388.7	354.1	324.3
40°	403.9	503.5	570.8	585.6	550.8	496.4	446.4	405.8	366.4	332.3	298.2
42.5°	348.9	448.1	530.7	556.6	529.0	474.9	424.7	382.3	344.0	311.8	276.9
45°	282.2	368.9	459.9	506.2	490.9	440.9	387.9	347.5	311.5	283.8	250.2
47.5°	238.0	299.1	387.3	449.9	449.7	404.0	351.8	313.3	279.8	253.8	226.7
50°	212.9	266.1	340.6	411.7	417.7	379.4	329.8	291.5	260.3	233.1	211.3
52.5°	190.3	234.2	301.1	369.4	386.4	353.1	305.1	269.7	239.4	214.3	195.7
55°	160.8	194.8	245.7	309.4	335.2	311.7	269.0	236.0	211.5	190.4	174.3
57.5°	136.0	161.5	202.4	253.7	283.6	268.9	233.7	206.8	185.8	166.7	154.1
60°	120.5	141.3	175.9	218.8	251.9	241.6	211.5	186.5	168.6	152.1	140.2
62.5°	105.7	123.7	153.4	188.2	218.4	214.2	189.7	168.6	153.0	137.9	127.8
65°	85.1	98.2	121.4	148.7	173.0	175.0	157.3	143.1	129.2	117.2	108.3
67.5°	67.8	76.3	92.6	115.6	133.8	140.4	129.6	118.7	107.6	98.4	90.6
70°	57.2	64.0	75.9	94.5	111.3	118.2	111.9	103.4	93.8	86.2	79.6
72.5°	46.3	53.0	61.8	75.4	89.8	97.3	95.0	89.0	81.2	74.8	68.6
75°	34.8	37.0	42.9	52.1	63.3	69.8	71.3	68.2	61.9	57.2	53.4
77.5°	25.8	27.1	29.9	34.6	42.0	47.8	50.1	49.7	45.4	42.7	39.2
80°	20.6	21.3	22.7	24.7	30.3	36.1	37.7	37.7	34.6	33.5	30.1
82.5°	15.7	16.2	17.1	18.2	20.7	25.8	27.6	27.9	26.1	24.5	21.8
85°	9.0	8.7	9.2	9.9	10.3	11.7	14.4	14.9	14.4	12.6	11.9
87.5°	9.7	8.6	7.4	6.2	5.7	5.2	5.4	5.6	5.6	5.7	6.1
90°	33.0	26.7	20.2	15.2	11.8	8.3	4.8	1.3	4.8	8.3	11.8
92.5°	38.6	37.1	35.5	33.5	31.0	28.5	25.9	23.3	25.9	28.5	31.0
95°	82.6	82.1	81.5	79.8	76.9	73.9	71.0	68.1	71.0	73.9	76.9
97.5°	138.7	137.5	136.4	134.6	132.1	129.6	126.9	124.4	126.9	129.6	132.1
100°	178.9	178.0	177.2	175.6	173.3	171.0	168.6	166.3	168.6	171.0	173.3
102.5°	221.5	220.4	219.2	217.7	215.9	214.0	212.2	210.3	212.2	214.0	215.9
105°	286.9	286.3	285.8	285.0	284.2	283.3	282.4	281.6	282.4	283.3	284.2
107.5°	359.0	359.0	359.0	358.4	357.1	355.9	354.6	353.3	354.6	355.9	357.1
110°	407.3	407.3	407.3	406.4	404.7	402.8	401.1	399.4	401.1	402.8	404.7



TEST NUMBER: P331778-840

CATALOG NUMBER: S122RDIW-S290D1240U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	457.0	457.2	457.4	456.7	454.9	453.1	451.4	449.7	451.4	453.1	454.9
115°	530.2	530.8	531.3	530.8	529.0	527.3	525.5	523.8	525.5	527.3	529.0
117.5°	604.0	605.6	607.3	606.9	604.6	602.3	600.0	597.6	600.0	602.3	604.6
120°	651.6	653.9	656.2	656.2	653.9	651.6	649.1	646.8	649.1	651.6	653.9
122.5°	700.4	702.1	703.7	703.1	700.2	697.5	694.7	691.9	694.7	697.5	700.2
125°	771.7	772.5	773.5	772.5	769.9	767.3	764.7	762.0	764.7	767.3	769.9
127.5°	842.7	843.8	844.9	843.7	840.4	837.1	833.7	830.4	833.7	837.1	840.4
130°	889.0	889.6	890.1	888.5	884.7	881.0	877.2	873.4	877.2	881.0	884.7
132.5°	935.7	935.6	935.5	933.9	930.8	927.8	924.6	921.6	924.6	927.8	930.8
135°	1001.9	1001.3	1000.7	998.9	995.6	992.4	989.2	986.0	989.2	992.4	995.6
137.5°	1067.5	1066.7	1066.0	1064.3	1061.7	1059.0	1056.4	1053.8	1056.4	1059.0	1061.7
140°	1110.1	1108.6	1107.2	1105.2	1102.6	1099.9	1097.3	1094.7	1097.3	1099.9	1102.6
142.5°	1150.8	1149.8	1148.8	1147.1	1144.5	1141.9	1139.2	1136.6	1139.2	1141.9	1144.5
145°	1210.3	1208.6	1206.9	1205.0	1203.0	1200.9	1198.9	1196.8	1198.9	1200.9	1203.0
147.5°	1264.5	1263.2	1262.1	1260.3	1257.9	1255.4	1252.9	1250.5	1252.9	1255.4	1257.9
150°	1298.0	1296.8	1295.7	1294.1	1292.4	1290.7	1288.9	1287.2	1288.9	1290.7	1292.4
152.5°	1331.0	1329.6	1328.2	1326.7	1324.8	1323.1	1321.4	1319.7	1321.4	1323.1	1324.8
155°	1374.4	1373.6	1372.7	1371.9	1371.0	1370.1	1369.3	1368.4	1369.3	1370.1	1371.0
157.5°	1413.9	1413.4	1412.9	1412.3	1411.8	1411.2	1410.6	1410.0	1410.6	1411.2	1411.8
160°	1438.5	1438.1	1437.9	1437.4	1436.9	1436.3	1435.7	1435.1	1435.7	1436.3	1436.9
162.5°	1459.5	1459.2	1458.9	1458.6	1458.5	1458.4	1458.3	1458.1	1458.3	1458.4	1458.5
165°	1487.5	1487.5	1487.5	1487.6	1487.9	1488.2	1488.5	1488.8	1488.5	1488.2	1487.9
167.5°	1510.5	1510.5	1510.6	1511.0	1511.9	1512.8	1513.6	1514.5	1513.6	1512.8	1511.9
170°	1523.5	1523.8	1524.1	1524.6	1525.5	1526.4	1527.2	1528.1	1527.2	1526.4	1525.5
172.5°	1532.9	1533.2	1533.5	1534.1	1534.9	1535.8	1536.7	1537.5	1536.7	1535.8	1534.9
175°	1543.7	1544.3	1544.9	1545.6	1546.4	1547.3	1548.2	1549.0	1548.2	1547.3	1546.4
177.5°	1549.4	1549.9	1550.4	1551.0	1551.7	1552.4	1553.1	1553.8	1553.1	1552.4	1551.7
180°	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7



TEST NUMBER: P331778-840

CATALOG NUMBER: S122RDIW-S290D1240U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1
2.5°	650.9	649.5	647.1	643.5	641.3	637.4	634.9	636.3	636.7	636.3	636.0
5°	633.4	628.5	621.9	615.4	609.5	603.1	599.4	597.8	594.6	592.8	591.8
7.5°	612.2	603.9	594.5	583.3	573.8	563.8	558.8	556.2	549.7	546.1	543.0
10°	596.4	583.3	573.9	559.3	550.3	537.2	528.3	528.6	519.6	514.5	510.9
12.5°	579.0	564.6	549.0	535.7	523.3	512.8	502.0	497.7	488.2	483.3	473.4
15°	550.1	533.3	516.8	499.0	486.4	470.0	454.4	435.4	420.0	406.7	403.0
17.5°	518.6	497.8	481.2	460.2	438.6	411.2	393.1	382.0	372.8	365.8	360.5
20°	496.9	475.7	458.1	426.5	397.3	378.7	365.5	356.9	347.3	339.7	335.6
22.5°	474.1	452.1	428.0	392.6	369.9	355.1	343.3	333.5	326.9	321.0	317.2
25°	441.8	417.7	378.0	353.8	335.4	319.7	311.5	305.6	298.7	290.6	287.0
27.5°	407.7	369.4	340.8	322.8	305.3	295.2	287.7	278.8	272.7	269.0	265.2
30°	382.1	343.9	321.6	301.8	289.5	278.2	269.5	264.5	258.5	252.4	249.8
32.5°	353.8	323.2	301.7	285.4	272.8	263.2	256.3	248.1	243.9	240.0	234.8
35°	318.4	295.2	275.7	262.5	250.4	242.7	234.7	229.8	222.1	218.8	216.8
37.5°	288.5	268.4	253.9	239.8	230.4	221.8	216.8	209.1	205.8	201.3	196.9
40°	271.6	251.9	237.9	226.4	215.8	209.4	203.3	197.0	192.0	190.0	184.7
42.5°	254.4	238.3	224.3	211.8	204.7	197.8	190.1	185.5	180.3	176.9	173.7
45°	230.6	216.3	204.4	194.1	186.2	179.2	174.1	166.5	163.6	156.9	154.1
47.5°	209.6	196.4	185.0	175.2	167.6	163.0	155.6	149.7	144.9	140.8	137.2
50°	194.8	183.7	172.7	164.0	157.1	150.5	142.9	140.0	132.6	130.5	128.5
52.5°	181.2	170.7	160.7	152.1	145.2	138.8	132.1	128.2	123.2	121.2	119.7
55°	162.2	152.1	142.5	134.9	128.1	121.4	117.2	112.4	110.1	108.5	106.6
57.5°	143.1	134.0	126.6	119.0	112.0	106.7	102.0	99.1	96.7	94.6	92.4
60°	131.0	122.3	115.6	108.5	101.4	97.0	93.4	89.9	87.2	83.9	83.0
62.5°	118.2	110.5	104.4	97.5	91.3	87.4	83.8	80.6	77.3	72.6	71.3
65°	100.5	94.5	88.1	82.3	76.9	72.9	67.9	64.2	62.8	62.4	62.2
67.5°	84.5	78.9	73.3	67.5	62.5	58.9	56.2	55.7	54.7	54.5	53.8
70°	73.8	68.6	63.1	57.6	52.7	52.1	51.2	50.2	49.1	48.7	48.2
72.5°	64.3	58.9	53.3	49.0	46.9	46.0	45.1	44.1	43.4	42.9	42.7
75°	49.3	44.2	40.6	39.0	37.9	37.2	35.7	35.1	34.6	33.9	33.7
77.5°	35.5	32.6	31.0	30.0	28.8	28.1	27.3	26.6	26.1	26.0	25.5
80°	27.1	25.7	24.5	23.1	22.7	21.8	21.6	20.9	21.1	20.4	20.4
82.5°	21.0	19.3	18.3	17.7	17.2	16.5	16.3	16.0	16.0	15.5	15.5
85°	10.8	10.3	9.9	9.4	9.4	8.7	9.0	8.7	8.7	8.3	8.1
87.5°	6.6	7.4	8.3	9.5	10.8	11.9	11.8	11.5	11.4	11.3	11.0
90°	15.2	20.2	26.7	33.0	39.4	45.8	45.2	44.6	44.1	43.5	43.3
92.5°	33.5	35.5	37.1	38.6	40.1	41.6	41.7	41.9	42.0	42.1	42.2
95°	79.8	81.5	82.1	82.6	83.2	83.8	83.8	83.8	83.8	83.8	83.5
97.5°	134.6	136.4	137.5	138.7	139.8	140.9	140.9	140.9	140.9	140.9	140.9
100°	175.6	177.2	178.0	178.9	179.9	180.7	180.7	180.7	180.7	180.7	180.6
102.5°	217.7	219.2	220.4	221.5	222.6	223.7	223.9	224.1	224.4	224.6	224.6
105°	285.0	285.8	286.3	286.9	287.5	288.1	288.6	289.2	289.8	290.4	290.7
107.5°	358.4	359.0	359.0	359.0	359.0	359.0	359.3	359.5	359.7	360.0	359.4
110°	406.4	407.3	407.3	407.3	407.3	407.3	407.3	407.3	407.3	407.3	406.8



TEST NUMBER: P331778-840

CATALOG NUMBER: S122RDIW-S290D1240U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	456.7	457.4	457.2	457.0	456.7	456.5	455.8	455.0	454.3	453.6	453.0
115°	530.8	531.3	530.8	530.2	529.6	529.0	528.8	528.5	528.2	527.9	527.3
117.5°	606.9	607.3	605.6	604.0	602.4	600.8	600.1	599.4	598.6	597.9	597.2
120°	656.2	656.2	653.9	651.6	649.1	646.8	646.8	646.8	646.8	646.8	646.4
122.5°	703.1	703.7	702.1	700.4	698.7	697.1	696.4	695.8	695.1	694.4	693.7
125°	772.5	773.5	772.5	771.7	770.8	769.9	769.1	768.2	767.3	766.5	765.9
127.5°	843.7	844.9	843.8	842.7	841.7	840.6	839.6	838.6	837.5	836.5	835.5
130°	888.5	890.1	889.6	889.0	888.4	887.8	887.2	886.7	886.1	885.4	884.6
132.5°	933.9	935.5	935.6	935.7	935.8	935.9	934.7	933.4	932.1	930.9	929.8
135°	998.9	1000.7	1001.3	1001.9	1002.5	1003.0	1002.7	1002.5	1002.2	1001.9	1001.3
137.5°	1064.3	1066.0	1066.7	1067.5	1068.2	1069.0	1068.8	1068.5	1068.3	1068.1	1067.4
140°	1105.2	1107.2	1108.6	1110.1	1111.6	1113.0	1113.0	1113.0	1113.0	1113.0	1112.5
142.5°	1147.1	1148.8	1149.8	1150.8	1151.9	1152.9	1153.1	1153.3	1153.6	1153.8	1153.3
145°	1205.0	1206.9	1208.6	1210.3	1212.1	1213.9	1214.2	1214.5	1214.8	1215.0	1214.6
147.5°	1260.3	1262.1	1263.2	1264.5	1265.6	1266.8	1267.4	1268.0	1268.7	1269.3	1269.1
150°	1294.1	1295.7	1296.8	1298.0	1299.1	1300.3	1301.1	1302.0	1302.9	1303.7	1303.7
152.5°	1326.7	1328.2	1329.6	1331.0	1332.4	1333.8	1334.9	1336.1	1337.1	1338.2	1338.2
155°	1371.9	1372.7	1373.6	1374.4	1375.3	1376.2	1377.7	1379.2	1380.6	1382.0	1382.3
157.5°	1412.3	1412.9	1413.4	1413.9	1414.4	1415.0	1416.9	1419.0	1420.9	1422.9	1423.2
160°	1437.4	1437.9	1438.1	1438.5	1438.8	1439.1	1440.8	1442.6	1444.3	1446.0	1446.3
162.5°	1458.6	1458.9	1459.2	1459.5	1459.8	1460.1	1462.0	1464.0	1465.9	1467.9	1468.2
165°	1487.6	1487.5	1487.5	1487.5	1487.5	1487.5	1489.6	1491.6	1493.6	1495.7	1495.9
167.5°	1511.0	1510.6	1510.5	1510.5	1510.4	1510.3	1512.4	1514.4	1516.4	1518.4	1518.7
170°	1524.6	1524.1	1523.8	1523.5	1523.2	1522.9	1524.9	1526.9	1528.9	1531.1	1531.2
172.5°	1534.1	1533.5	1533.2	1532.9	1532.6	1532.3	1534.4	1536.4	1538.4	1540.4	1540.5
175°	1545.6	1544.9	1544.3	1543.7	1543.1	1542.5	1544.6	1546.6	1548.6	1550.6	1550.8
177.5°	1551.0	1550.4	1549.9	1549.4	1549.0	1548.5	1549.9	1551.4	1552.8	1554.1	1554.1
180°	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7



TEST NUMBER: P331778-840

CATALOG NUMBER: S122RDIW-S290D1240U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1
2.5°	634.0	634.3	633.8	634.1	633.8	634.3	634.0	636.0	636.3	636.7	636.3
5°	590.7	587.9	587.4	586.8	587.4	587.9	590.7	591.8	592.8	594.6	597.8
7.5°	539.1	538.7	537.5	535.8	537.5	538.7	539.1	543.0	546.1	549.7	556.2
10°	505.8	504.6	504.4	502.8	504.4	504.6	505.8	510.9	514.5	519.6	528.6
12.5°	466.9	459.5	458.8	454.7	458.8	459.5	466.9	473.4	483.3	488.2	497.7
15°	397.6	396.2	391.5	388.6	391.5	396.2	397.6	403.0	406.7	420.0	435.4
17.5°	357.9	353.4	351.9	351.3	351.9	353.4	357.9	360.5	365.8	372.8	382.0
20°	332.3	328.3	327.6	327.1	327.6	328.3	332.3	335.6	339.7	347.3	356.9
22.5°	314.8	310.4	308.7	307.3	308.7	310.4	314.8	317.2	321.0	326.9	333.5
25°	284.7	283.1	282.2	281.7	282.2	283.1	284.7	287.0	290.6	298.7	305.6
27.5°	261.2	257.6	256.9	255.7	256.9	257.6	261.2	265.2	269.0	272.7	278.8
30°	247.7	246.6	245.0	243.6	245.0	246.6	247.7	249.8	252.4	258.5	264.5
32.5°	232.0	231.0	229.5	228.9	229.5	231.0	232.0	234.8	240.0	243.9	248.1
35°	214.5	211.3	209.8	207.8	209.8	211.3	214.5	216.8	218.8	222.1	229.8
37.5°	196.0	194.3	192.4	193.1	192.4	194.3	196.0	196.9	201.3	205.8	209.1
40°	181.7	180.6	180.1	179.9	180.1	180.6	181.7	184.7	190.0	192.0	197.0
42.5°	170.3	167.1	165.9	165.9	165.9	167.1	170.3	173.7	176.9	180.3	185.5
45°	153.0	150.1	147.9	148.1	147.9	150.1	153.0	154.1	156.9	163.6	166.5
47.5°	135.3	135.2	133.9	134.3	133.9	135.2	135.3	137.2	140.8	144.9	149.7
50°	126.8	125.5	124.5	124.8	124.5	125.5	126.8	128.5	130.5	132.6	140.0
52.5°	118.8	117.5	116.8	117.9	116.8	117.5	118.8	119.7	121.2	123.2	128.2
55°	105.5	104.1	103.9	103.7	103.9	104.1	105.5	106.6	108.5	110.1	112.4
57.5°	90.7	89.8	88.4	87.9	88.4	89.8	90.7	92.4	94.6	96.7	99.1
60°	80.1	78.3	75.9	75.7	75.9	78.3	80.1	83.0	83.9	87.2	89.9
62.5°	70.3	70.0	69.5	69.5	69.5	70.0	70.3	71.3	72.6	77.3	80.6
65°	61.7	61.5	61.7	61.9	61.7	61.5	61.7	62.2	62.4	62.8	64.2
67.5°	53.7	53.3	52.9	53.1	52.9	53.3	53.7	53.8	54.5	54.7	55.7
70°	47.7	47.5	47.3	47.3	47.3	47.5	47.7	48.2	48.7	49.1	50.2
72.5°	41.8	41.8	41.6	41.4	41.6	41.8	41.8	42.7	42.9	43.4	44.1
75°	33.5	33.0	33.0	33.0	33.0	33.0	33.5	33.7	33.9	34.6	35.1
77.5°	25.5	25.2	25.0	24.8	25.0	25.2	25.5	25.5	26.0	26.1	26.6
80°	20.2	20.0	19.7	19.7	19.7	20.0	20.2	20.4	20.4	21.1	20.9
82.5°	15.5	15.1	15.1	14.9	15.1	15.1	15.5	15.5	15.5	16.0	16.0
85°	8.3	8.5	8.3	8.7	8.3	8.5	8.3	8.1	8.3	8.7	8.7
87.5°	11.1	11.0	11.2	11.1	11.2	11.0	11.1	11.0	11.3	11.4	11.5
90°	43.6	43.9	44.2	44.5	44.2	43.9	43.6	43.3	43.5	44.1	44.6
92.5°	42.2	42.3	42.4	42.4	42.4	42.3	42.2	42.2	42.1	42.0	41.9
95°	82.9	82.3	81.8	81.2	81.8	82.3	82.9	83.5	83.8	83.8	83.8
97.5°	140.8	140.8	140.7	140.7	140.7	140.8	140.8	140.9	140.9	140.9	140.9
100°	180.3	180.0	179.7	179.4	179.7	180.0	180.3	180.6	180.7	180.7	180.7
102.5°	224.3	224.0	223.7	223.4	223.7	224.0	224.3	224.6	224.6	224.4	224.1
105°	290.7	290.7	290.7	290.7	290.7	290.7	290.7	290.7	290.4	289.8	289.2
107.5°	358.1	356.8	355.4	354.1	355.4	356.8	358.1	359.4	360.0	359.7	359.5
110°	406.0	405.1	404.1	403.3	404.1	405.1	406.0	406.8	407.3	407.3	407.3



TEST NUMBER: P331778-840

CATALOG NUMBER: S122RDIW-S290D1240U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	452.3	451.7	451.1	450.4	451.1	451.7	452.3	453.0	453.6	454.3	455.0
115°	526.4	525.5	524.6	523.8	524.6	525.5	526.4	527.3	527.9	528.2	528.5
117.5°	596.3	595.4	594.6	593.7	594.6	595.4	596.3	597.2	597.9	598.6	599.4
120°	645.5	644.7	643.8	643.0	643.8	644.7	645.5	646.4	646.8	646.8	646.8
122.5°	693.1	692.4	691.8	691.2	691.8	692.4	693.1	693.7	694.4	695.1	695.8
125°	765.6	765.3	765.0	764.7	765.0	765.3	765.6	765.9	766.5	767.3	768.2
127.5°	834.6	833.6	832.7	831.7	832.7	833.6	834.6	835.5	836.5	837.5	838.6
130°	883.4	882.3	881.1	879.9	881.1	882.3	883.4	884.6	885.4	886.1	886.7
132.5°	928.9	927.9	927.0	926.0	927.0	927.9	928.9	929.8	930.9	932.1	933.4
135°	1000.4	999.6	998.7	997.7	998.7	999.6	1000.4	1001.3	1001.9	1002.2	1002.5
137.5°	1066.2	1065.1	1063.9	1062.8	1063.9	1065.1	1066.2	1067.4	1068.1	1068.3	1068.5
140°	1111.3	1110.1	1108.9	1107.8	1108.9	1110.1	1111.3	1112.5	1113.0	1113.0	1113.0
142.5°	1152.2	1150.9	1149.8	1148.6	1149.8	1150.9	1152.2	1153.3	1153.8	1153.6	1153.3
145°	1213.5	1212.2	1211.1	1209.9	1211.1	1212.2	1213.5	1214.6	1215.0	1214.8	1214.5
147.5°	1268.0	1266.9	1265.8	1264.7	1265.8	1266.9	1268.0	1269.1	1269.3	1268.7	1268.0
150°	1302.9	1302.0	1301.1	1300.3	1301.1	1302.0	1302.9	1303.7	1303.7	1302.9	1302.0
152.5°	1337.1	1336.1	1334.9	1333.8	1334.9	1336.1	1337.1	1338.2	1338.2	1337.1	1336.1
155°	1381.5	1380.6	1379.7	1378.9	1379.7	1380.6	1381.5	1382.3	1382.0	1380.6	1379.2
157.5°	1421.8	1420.4	1419.0	1417.5	1419.0	1420.4	1421.8	1423.2	1422.9	1420.9	1419.0
160°	1445.2	1444.0	1442.9	1441.7	1442.9	1444.0	1445.2	1446.3	1446.0	1444.3	1442.6
162.5°	1466.8	1465.4	1464.0	1462.7	1464.0	1465.4	1466.8	1468.2	1467.9	1465.9	1464.0
165°	1494.5	1493.1	1491.6	1490.2	1491.6	1493.1	1494.5	1495.9	1495.7	1493.6	1491.6
167.5°	1517.2	1515.7	1514.2	1512.7	1514.2	1515.7	1517.2	1518.7	1518.4	1516.4	1514.4
170°	1529.4	1527.7	1525.9	1524.2	1525.9	1527.7	1529.4	1531.2	1531.1	1528.9	1526.9
172.5°	1538.8	1537.1	1535.4	1533.6	1535.4	1537.1	1538.8	1540.5	1540.4	1538.4	1536.4
175°	1549.0	1547.3	1545.6	1543.8	1545.6	1547.3	1549.0	1550.8	1550.6	1548.6	1546.6
177.5°	1552.8	1551.4	1549.9	1548.5	1549.9	1551.4	1552.8	1554.1	1554.1	1552.8	1551.4
180°	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7



TEST NUMBER: P331778-840

CATALOG NUMBER: S122RDIW-S290D1240U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1
2.5°	634.9	637.4	641.3	643.5	647.1	649.5	650.9	653.2	654.5	659.1	663.9
5°	599.4	603.1	609.5	615.4	621.9	628.5	633.4	638.8	643.9	652.6	661.8
7.5°	558.8	563.8	573.8	583.3	594.5	603.9	612.2	621.6	630.0	642.5	655.5
10°	528.3	537.2	550.3	559.3	573.9	583.3	596.4	606.7	618.4	635.0	649.6
12.5°	502.0	512.8	523.3	535.7	549.0	564.6	579.0	592.3	606.1	623.2	640.5
15°	454.4	470.0	486.4	499.0	516.8	533.3	550.1	567.9	584.9	605.4	627.8
17.5°	393.1	411.2	438.6	460.2	481.2	497.8	518.6	540.2	560.2	584.8	609.9
20°	365.5	378.7	397.3	426.5	458.1	475.7	496.9	520.7	543.6	570.5	597.3
22.5°	343.3	355.1	369.9	392.6	428.0	452.1	474.1	498.4	524.9	552.3	582.1
25°	311.5	319.7	335.4	353.8	378.0	417.7	441.8	466.2	495.0	524.4	558.4
27.5°	287.7	295.2	305.3	322.8	340.8	369.4	407.7	434.2	463.0	496.0	531.3
30°	269.5	278.2	289.5	301.8	321.6	343.9	382.1	412.9	441.3	475.3	512.9
32.5°	256.3	263.2	272.8	285.4	301.7	323.2	353.8	391.0	418.8	454.5	493.8
35°	234.7	242.7	250.4	262.5	275.7	295.2	318.4	358.3	385.9	421.1	460.6
37.5°	216.8	221.8	230.4	239.8	253.9	268.4	288.5	324.3	354.1	388.7	429.1
40°	203.3	209.4	215.8	226.4	237.9	251.9	271.6	298.2	332.3	366.4	405.8
42.5°	190.1	197.8	204.7	211.8	224.3	238.3	254.4	276.9	311.8	344.0	382.3
45°	174.1	179.2	186.2	194.1	204.4	216.3	230.6	250.2	283.8	311.5	347.5
47.5°	155.6	163.0	167.6	175.2	185.0	196.4	209.6	226.7	253.8	279.8	313.3
50°	142.9	150.5	157.1	164.0	172.7	183.7	194.8	211.3	233.1	260.3	291.5
52.5°	132.1	138.8	145.2	152.1	160.7	170.7	181.2	195.7	214.3	239.4	269.7
55°	117.2	121.4	128.1	134.9	142.5	152.1	162.2	174.3	190.4	211.5	236.0
57.5°	102.0	106.7	112.0	119.0	126.6	134.0	143.1	154.1	166.7	185.8	206.8
60°	93.4	97.0	101.4	108.5	115.6	122.3	131.0	140.2	152.1	168.6	186.5
62.5°	83.8	87.4	91.3	97.5	104.4	110.5	118.2	127.8	137.9	153.0	168.6
65°	67.9	72.9	76.9	82.3	88.1	94.5	100.5	108.3	117.2	129.2	143.1
67.5°	56.2	58.9	62.5	67.5	73.3	78.9	84.5	90.6	98.4	107.6	118.7
70°	51.2	52.1	52.7	57.6	63.1	68.6	73.8	79.6	86.2	93.8	103.4
72.5°	45.1	46.0	46.9	49.0	53.3	58.9	64.3	68.6	74.8	81.2	89.0
75°	35.7	37.2	37.9	39.0	40.6	44.2	49.3	53.4	57.2	61.9	68.2
77.5°	27.3	28.1	28.8	30.0	31.0	32.6	35.5	39.2	42.7	45.4	49.7
80°	21.6	21.8	22.7	23.1	24.5	25.7	27.1	30.1	33.5	34.6	37.7
82.5°	16.3	16.5	17.2	17.7	18.3	19.3	21.0	21.8	24.5	26.1	27.9
85°	9.0	8.7	9.4	9.4	9.9	10.3	10.8	11.9	12.6	14.4	14.9
87.5°	11.8	11.9	10.8	9.5	8.3	7.4	6.6	6.1	5.7	5.6	5.6
90°	45.2	45.8	39.4	33.0	26.7	20.2	15.2	11.8	8.3	4.8	1.3
92.5°	41.7	41.6	40.1	38.6	37.1	35.5	33.5	31.0	28.5	25.9	23.3
95°	83.8	83.8	83.2	82.6	82.1	81.5	79.8	76.9	73.9	71.0	68.1
97.5°	140.9	140.9	139.8	138.7	137.5	136.4	134.6	132.1	129.6	126.9	124.4
100°	180.7	180.7	179.9	178.9	178.0	177.2	175.6	173.3	171.0	168.6	166.3
102.5°	223.9	223.7	222.6	221.5	220.4	219.2	217.7	215.9	214.0	212.2	210.3
105°	288.6	288.1	287.5	286.9	286.3	285.8	285.0	284.2	283.3	282.4	281.6
107.5°	359.3	359.0	359.0	359.0	359.0	359.0	358.4	357.1	355.9	354.6	353.3
110°	407.3	407.3	407.3	407.3	407.3	407.3	406.4	404.7	402.8	401.1	399.4



TEST NUMBER: P331778-840

CATALOG NUMBER: S122RDIW-S290D1240U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	455.8	456.5	456.7	457.0	457.2	457.4	456.7	454.9	453.1	451.4	449.7
115°	528.8	529.0	529.6	530.2	530.8	531.3	530.8	529.0	527.3	525.5	523.8
117.5°	600.1	600.8	602.4	604.0	605.6	607.3	606.9	604.6	602.3	600.0	597.6
120°	646.8	646.8	649.1	651.6	653.9	656.2	656.2	653.9	651.6	649.1	646.8
122.5°	696.4	697.1	698.7	700.4	702.1	703.7	703.1	700.2	697.5	694.7	691.9
125°	769.1	769.9	770.8	771.7	772.5	773.5	772.5	769.9	767.3	764.7	762.0
127.5°	839.6	840.6	841.7	842.7	843.8	844.9	843.7	840.4	837.1	833.7	830.4
130°	887.2	887.8	888.4	889.0	889.6	890.1	888.5	884.7	881.0	877.2	873.4
132.5°	934.7	935.9	935.8	935.7	935.6	935.5	933.9	930.8	927.8	924.6	921.6
135°	1002.7	1003.0	1002.5	1001.9	1001.3	1000.7	998.9	995.6	992.4	989.2	986.0
137.5°	1068.8	1069.0	1068.2	1067.5	1066.7	1066.0	1064.3	1061.7	1059.0	1056.4	1053.8
140°	1113.0	1113.0	1111.6	1110.1	1108.6	1107.2	1105.2	1102.6	1099.9	1097.3	1094.7
142.5°	1153.1	1152.9	1151.9	1150.8	1149.8	1148.8	1147.1	1144.5	1141.9	1139.2	1136.6
145°	1214.2	1213.9	1212.1	1210.3	1208.6	1206.9	1205.0	1203.0	1200.9	1198.9	1196.8
147.5°	1267.4	1266.8	1265.6	1264.5	1263.2	1262.1	1260.3	1257.9	1255.4	1252.9	1250.5
150°	1301.1	1300.3	1299.1	1298.0	1296.8	1295.7	1294.1	1292.4	1290.7	1288.9	1287.2
152.5°	1334.9	1333.8	1332.4	1331.0	1329.6	1328.2	1326.7	1324.8	1323.1	1321.4	1319.7
155°	1377.7	1376.2	1375.3	1374.4	1373.6	1372.7	1371.9	1371.0	1370.1	1369.3	1368.4
157.5°	1416.9	1415.0	1414.4	1413.9	1413.4	1412.9	1412.3	1411.8	1411.2	1410.6	1410.0
160°	1440.8	1439.1	1438.8	1438.5	1438.1	1437.9	1437.4	1436.9	1436.3	1435.7	1435.1
162.5°	1462.0	1460.1	1459.8	1459.5	1459.2	1458.9	1458.6	1458.5	1458.4	1458.3	1458.1
165°	1489.6	1487.5	1487.5	1487.5	1487.5	1487.5	1487.6	1487.9	1488.2	1488.5	1488.8
167.5°	1512.4	1510.3	1510.4	1510.5	1510.5	1510.6	1511.0	1511.9	1512.8	1513.6	1514.5
170°	1524.9	1522.9	1523.2	1523.5	1523.8	1524.1	1524.6	1525.5	1526.4	1527.2	1528.1
172.5°	1534.4	1532.3	1532.6	1532.9	1533.2	1533.5	1534.1	1534.9	1535.8	1536.7	1537.5
175°	1544.6	1542.5	1543.1	1543.7	1544.3	1544.9	1545.6	1546.4	1547.3	1548.2	1549.0
177.5°	1549.9	1548.5	1549.0	1549.4	1549.9	1550.4	1551.0	1551.7	1552.4	1553.1	1553.8
180°	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7



TEST NUMBER: P331778-840

CATALOG NUMBER: S122RDIW-S290D1240U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1
2.5°	664.1	664.6	668.2	669.9	673.2	674.5	676.0	675.6	675.6	676.3	681.5
5°	665.5	670.0	676.9	683.6	690.0	695.5	699.2	702.9	704.3	710.8	716.8
7.5°	663.1	671.6	682.9	693.1	705.2	714.7	722.6	729.7	734.6	744.3	754.2
10°	659.9	671.9	684.7	697.8	714.6	727.2	740.0	749.9	753.1	767.5	775.8
12.5°	653.7	669.6	686.0	703.0	719.3	736.7	750.8	760.7	772.0	785.0	800.2
15°	644.4	662.7	684.1	705.8	729.2	750.3	765.5	782.6	795.1	809.3	822.6
17.5°	631.0	654.6	681.7	706.9	734.0	756.6	777.5	794.0	802.6	810.8	812.7
20°	620.3	645.7	677.6	707.4	734.5	760.6	781.3	795.1	797.4	797.6	785.5
22.5°	608.7	637.5	670.9	701.4	733.8	762.9	778.9	784.8	775.7	760.1	736.6
25°	587.4	620.8	659.5	694.4	729.7	757.2	762.8	752.5	720.5	687.0	644.6
27.5°	564.4	601.9	643.4	682.2	719.8	736.9	725.0	687.7	630.4	580.4	519.9
30°	547.5	589.6	630.4	673.7	708.6	715.9	688.6	633.8	566.8	491.6	431.2
32.5°	528.3	572.3	617.1	662.0	691.2	684.0	638.9	571.4	492.9	418.9	361.9
35°	500.8	546.1	594.6	639.5	658.1	627.1	559.7	471.8	391.5	322.6	283.3
37.5°	469.0	518.5	568.8	610.1	608.7	557.1	465.2	374.6	307.1	266.2	238.3
40°	446.4	496.4	550.8	585.6	570.8	503.5	403.9	318.4	269.0	236.5	216.1
42.5°	424.7	474.9	529.0	556.6	530.7	448.1	348.9	281.9	241.2	215.8	199.2
45°	387.9	440.9	490.9	506.2	459.9	368.9	282.2	233.5	206.4	187.6	176.2
47.5°	351.8	404.0	449.7	449.9	387.3	299.1	238.0	202.1	178.9	164.4	156.1
50°	329.8	379.4	417.7	411.7	340.6	266.1	212.9	181.9	162.7	151.4	142.7
52.5°	305.1	353.1	386.4	369.4	301.1	234.2	190.3	164.3	148.3	138.6	130.8
55°	269.0	311.7	335.2	309.4	245.7	194.8	160.8	140.4	128.5	120.2	113.5
57.5°	233.7	268.9	283.6	253.7	202.4	161.5	136.0	120.7	108.9	102.9	99.5
60°	211.5	241.6	251.9	218.8	175.9	141.3	120.5	106.2	97.5	93.6	90.2
62.5°	189.7	214.2	218.4	188.2	153.4	123.7	105.7	93.7	88.0	84.2	81.0
65°	157.3	175.0	173.0	148.7	121.4	98.2	85.1	77.8	73.4	68.2	62.4
67.5°	129.6	140.4	133.8	115.6	92.6	76.3	67.8	62.2	56.8	51.8	50.5
70°	111.9	118.2	111.3	94.5	75.9	64.0	57.2	50.5	47.3	46.2	44.0
72.5°	95.0	97.3	89.8	75.4	61.8	53.0	46.3	42.6	40.8	39.9	38.6
75°	71.3	69.8	63.3	52.1	42.9	37.0	34.8	33.5	32.3	31.4	30.7
77.5°	50.1	47.8	42.0	34.6	29.9	27.1	25.8	25.0	24.5	24.0	23.3
80°	37.7	36.1	30.3	24.7	22.7	21.3	20.6	19.7	19.7	19.3	18.6
82.5°	27.6	25.8	20.7	18.2	17.1	16.2	15.7	15.1	14.9	15.0	14.5
85°	14.4	11.7	10.3	9.9	9.2	8.7	9.0	8.5	8.5	8.5	8.3
87.5°	5.4	5.2	5.7	6.2	7.4	8.6	9.7	11.0	12.4	12.2	12.2
90°	4.8	8.3	11.8	15.2	20.2	26.7	33.0	39.4	45.8	45.2	44.6
92.5°	25.9	28.5	31.0	33.5	35.5	37.1	38.6	40.1	41.6	41.7	41.9
95°	71.0	73.9	76.9	79.8	81.5	82.1	82.6	83.2	83.8	83.8	83.8
97.5°	126.9	129.6	132.1	134.6	136.4	137.5	138.7	139.8	140.9	140.9	140.9
100°	168.6	171.0	173.3	175.6	177.2	178.0	178.9	179.9	180.7	180.7	180.7
102.5°	212.2	214.0	215.9	217.7	219.2	220.4	221.5	222.6	223.7	223.9	224.1
105°	282.4	283.3	284.2	285.0	285.8	286.3	286.9	287.5	288.1	288.6	289.2
107.5°	354.6	355.9	357.1	358.4	359.0	359.0	359.0	359.0	359.0	359.3	359.5
110°	401.1	402.8	404.7	406.4	407.3	407.3	407.3	407.3	407.3	407.3	407.3



TEST NUMBER: P331778-840

CATALOG NUMBER: S122RDIW-S290D1240U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	451.4	453.1	454.9	456.7	457.4	457.2	457.0	456.7	456.5	455.8	455.0
115°	525.5	527.3	529.0	530.8	531.3	530.8	530.2	529.6	529.0	528.8	528.5
117.5°	600.0	602.3	604.6	606.9	607.3	605.6	604.0	602.4	600.8	600.1	599.4
120°	649.1	651.6	653.9	656.2	656.2	653.9	651.6	649.1	646.8	646.8	646.8
122.5°	694.7	697.5	700.2	703.1	703.7	702.1	700.4	698.7	697.1	696.4	695.8
125°	764.7	767.3	769.9	772.5	773.5	772.5	771.7	770.8	769.9	769.1	768.2
127.5°	833.7	837.1	840.4	843.7	844.9	843.8	842.7	841.7	840.6	839.6	838.6
130°	877.2	881.0	884.7	888.5	890.1	889.6	889.0	888.4	887.8	887.2	886.7
132.5°	924.6	927.8	930.8	933.9	935.5	935.6	935.7	935.8	935.9	934.7	933.4
135°	989.2	992.4	995.6	998.9	1000.7	1001.3	1001.9	1002.5	1003.0	1002.7	1002.5
137.5°	1056.4	1059.0	1061.7	1064.3	1066.0	1066.7	1067.5	1068.2	1069.0	1068.8	1068.5
140°	1097.3	1099.9	1102.6	1105.2	1107.2	1108.6	1110.1	1111.6	1113.0	1113.0	1113.0
142.5°	1139.2	1141.9	1144.5	1147.1	1148.8	1149.8	1150.8	1151.9	1152.9	1153.1	1153.3
145°	1198.9	1200.9	1203.0	1205.0	1206.9	1208.6	1210.3	1212.1	1213.9	1214.2	1214.5
147.5°	1252.9	1255.4	1257.9	1260.3	1262.1	1263.2	1264.5	1265.6	1266.8	1267.4	1268.0
150°	1288.9	1290.7	1292.4	1294.1	1295.7	1296.8	1298.0	1299.1	1300.3	1301.1	1302.0
152.5°	1321.4	1323.1	1324.8	1326.7	1328.2	1329.6	1331.0	1332.4	1333.8	1334.9	1336.1
155°	1369.3	1370.1	1371.0	1371.9	1372.7	1373.6	1374.4	1375.3	1376.2	1377.7	1379.2
157.5°	1410.6	1411.2	1411.8	1412.3	1412.9	1413.4	1413.9	1414.4	1415.0	1416.9	1419.0
160°	1435.7	1436.3	1436.9	1437.4	1437.9	1438.1	1438.5	1438.8	1439.1	1440.8	1442.6
162.5°	1458.3	1458.4	1458.5	1458.6	1458.9	1459.2	1459.5	1459.8	1460.1	1462.0	1464.0
165°	1488.5	1488.2	1487.9	1487.6	1487.5	1487.5	1487.5	1487.5	1487.5	1489.6	1491.6
167.5°	1513.6	1512.8	1511.9	1511.0	1510.6	1510.5	1510.5	1510.4	1510.3	1512.4	1514.4
170°	1527.2	1526.4	1525.5	1524.6	1524.1	1523.8	1523.5	1523.2	1522.9	1524.9	1526.9
172.5°	1536.7	1535.8	1534.9	1534.1	1533.5	1533.2	1532.9	1532.6	1532.3	1534.4	1536.4
175°	1548.2	1547.3	1546.4	1545.6	1544.9	1544.3	1543.7	1543.1	1542.5	1544.6	1546.6
177.5°	1553.1	1552.4	1551.7	1551.0	1550.4	1549.9	1549.4	1549.0	1548.5	1549.9	1551.4
180°	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7



TEST NUMBER: P331778-840

CATALOG NUMBER: S122RDIW-S290D1240U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	660.1	660.1	660.1	660.1	660.1	660.1	660.1
2.5°	683.3	685.7	686.8	686.8	688.1	687.5	687.0
5°	722.6	726.9	727.9	732.0	735.0	734.1	734.5
7.5°	761.6	768.6	775.6	778.7	779.2	781.0	781.7
10°	785.7	791.4	802.1	800.6	808.6	813.2	805.7
12.5°	808.8	816.6	824.0	826.1	830.6	832.1	829.1
15°	829.7	833.8	834.2	833.1	834.6	833.3	829.0
17.5°	810.2	803.4	789.9	783.5	778.4	770.8	767.8
20°	777.9	758.1	735.2	726.0	715.3	694.2	699.2
22.5°	708.1	685.7	662.7	635.9	623.1	603.1	601.9
25°	599.7	560.9	518.2	488.4	470.9	451.0	442.2
27.5°	466.3	417.4	382.4	364.8	348.6	332.9	332.1
30°	378.5	341.8	314.8	299.6	289.7	283.1	284.5
32.5°	319.0	293.9	275.6	263.1	255.8	250.7	250.6
35°	260.8	243.6	231.9	226.6	221.4	217.7	217.9
37.5°	223.2	212.9	206.3	200.6	197.2	195.4	194.4
40°	203.9	195.4	190.4	186.9	184.2	181.7	181.2
42.5°	188.7	181.7	176.6	173.9	171.4	169.6	169.2
45°	167.4	161.7	157.1	154.1	153.0	151.4	151.4
47.5°	149.0	143.3	139.8	137.8	135.9	134.8	134.8
50°	136.5	132.1	129.0	127.7	126.1	125.5	125.2
52.5°	125.3	122.0	119.8	119.0	118.3	117.4	117.5
55°	110.1	108.3	107.3	106.6	105.5	104.1	105.0
57.5°	97.4	95.7	93.3	91.1	90.1	89.1	89.5
60°	88.4	85.1	81.9	79.4	78.7	76.6	76.6
62.5°	77.0	72.4	68.5	67.1	66.3	65.4	65.2
65°	59.2	57.4	56.5	55.5	55.0	55.0	54.6
67.5°	49.1	48.3	47.3	47.1	46.7	46.5	46.4
70°	43.3	42.4	42.0	41.7	41.3	41.5	40.8
72.5°	37.9	37.2	37.1	36.5	36.2	36.2	35.6
75°	29.8	29.8	29.6	29.4	28.9	28.7	28.9
77.5°	22.9	23.0	22.6	22.5	22.5	22.5	22.3
80°	18.4	18.6	18.4	18.1	17.9	18.1	17.9
82.5°	14.5	14.1	14.1	14.0	14.0	13.9	13.8
85°	8.3	8.5	8.3	8.1	8.1	8.1	8.3
87.5°	11.9	11.8	11.8	11.8	11.9	11.9	11.8
90°	44.1	43.5	43.3	43.6	43.9	44.2	44.5
92.5°	42.0	42.1	42.2	42.2	42.3	42.4	42.4
95°	83.8	83.8	83.5	82.9	82.3	81.8	81.2
97.5°	140.9	140.9	140.9	140.8	140.8	140.7	140.7
100°	180.7	180.7	180.6	180.3	180.0	179.7	179.4
102.5°	224.4	224.6	224.6	224.3	224.0	223.7	223.4
105°	289.8	290.4	290.7	290.7	290.7	290.7	290.7
107.5°	359.7	360.0	359.4	358.1	356.8	355.4	354.1
110°	407.3	407.3	406.8	406.0	405.1	404.1	403.3



TEST NUMBER: P331778-840

CATALOG NUMBER: S122RDIW-S290D1240U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	454.3	453.6	453.0	452.3	451.7	451.1	450.4
115°	528.2	527.9	527.3	526.4	525.5	524.6	523.8
117.5°	598.6	597.9	597.2	596.3	595.4	594.6	593.7
120°	646.8	646.8	646.4	645.5	644.7	643.8	643.0
122.5°	695.1	694.4	693.7	693.1	692.4	691.8	691.2
125°	767.3	766.5	765.9	765.6	765.3	765.0	764.7
127.5°	837.5	836.5	835.5	834.6	833.6	832.7	831.7
130°	886.1	885.4	884.6	883.4	882.3	881.1	879.9
132.5°	932.1	930.9	929.8	928.9	927.9	927.0	926.0
135°	1002.2	1001.9	1001.3	1000.4	999.6	998.7	997.7
137.5°	1068.3	1068.1	1067.4	1066.2	1065.1	1063.9	1062.8
140°	1113.0	1113.0	1112.5	1111.3	1110.1	1108.9	1107.8
142.5°	1153.6	1153.8	1153.3	1152.2	1150.9	1149.8	1148.6
145°	1214.8	1215.0	1214.6	1213.5	1212.2	1211.1	1209.9
147.5°	1268.7	1269.3	1269.1	1268.0	1266.9	1265.8	1264.7
150°	1302.9	1303.7	1303.7	1302.9	1302.0	1301.1	1300.3
152.5°	1337.1	1338.2	1338.2	1337.1	1336.1	1334.9	1333.8
155°	1380.6	1382.0	1382.3	1381.5	1380.6	1379.7	1378.9
157.5°	1420.9	1422.9	1423.2	1421.8	1420.4	1419.0	1417.5
160°	1444.3	1446.0	1446.3	1445.2	1444.0	1442.9	1441.7
162.5°	1465.9	1467.9	1468.2	1466.8	1465.4	1464.0	1462.7
165°	1493.6	1495.7	1495.9	1494.5	1493.1	1491.6	1490.2
167.5°	1516.4	1518.4	1518.7	1517.2	1515.7	1514.2	1512.7
170°	1528.9	1531.1	1531.2	1529.4	1527.7	1525.9	1524.2
172.5°	1538.4	1540.4	1540.5	1538.8	1537.1	1535.4	1533.6
175°	1548.6	1550.6	1550.8	1549.0	1547.3	1545.6	1543.8
177.5°	1552.8	1554.1	1554.1	1552.8	1551.4	1549.9	1548.5
180°	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7	1551.7

(END OF REPORT)