

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331782-840

Luminaire Tested: **S122RDIW-S290D1440U840-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331782-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S290D1440U840-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1440 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6192.7 lumens
Efficiency: N/A
Efficacy: 116.0 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331782-840

CATALOG NUMBER: S122RDIW-S290D1440U840-4F0-1E-UDD-A1

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - - - 90°-270° - - - 135°-315°



TEST NUMBER: P331782-840

CATALOG NUMBER: S122RDIW-S290D1440U840-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	100	100	100	100	88	88	88	88	66	66	66	46	46	46	27	27	27	19
1	91	87	83	80	80	77	74	71	58	56	54	40	39	38	24	24	23	16
2	83	76	71	66	73	67	63	59	51	48	45	36	34	32	22	21	20	14
3	76	67	60	55	67	60	54	49	45	41	38	32	30	28	20	18	17	12
4	69	60	52	47	61	53	47	42	40	36	33	29	26	24	18	16	15	11
5	64	53	45	40	56	47	41	36	36	32	28	26	23	21	16	15	14	10
6	59	47	40	35	52	42	36	31	32	28	25	23	20	18	15	13	12	9
7	54	43	35	30	48	38	32	27	29	25	22	21	18	16	13	12	11	8
8	50	39	32	27	44	35	28	24	27	22	19	19	17	14	12	11	10	7
9	47	35	28	24	41	32	26	21	24	20	17	18	15	13	12	10	9	6
10	43	32	25	21	38	29	23	19	22	18	15	16	14	12	11	9	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10658	10658	10658	10658
5°	11904	10726	9511	10726
10°	13209	10650	8243	10650
15°	13857	10494	6496	10494
20°	12014	10263	5620	10263
25°	7878	9948	5018	9948
30°	5304	9562	4542	9562
35°	4295	9079	4096	9079
40°	3819	8553	3792	8553
45°	3457	7935	3382	7935
50°	3145	7322	3135	7322
55°	2956	6643	2919	6643
60°	2474	6022	2444	6022
65°	2086	5467	2365	5467
70°	1926	4881	2233	4881
75°	1803	4255	2059	4255
80°	1664	3505	1832	3505
85°	1538	2760	1612	2760



TEST NUMBER: P331782-840

CATALOG NUMBER: S122RDIW-S290D1440U840-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	62.6	1.0
10°-20°	174.4	2.8
20°-30°	224.7	3.6
30°-40°	213.5	3.4
40°-50°	182.9	3.0
50°-60°	139.3	2.2
60°-70°	88.1	1.4
70°-80°	44.0	0.7
80°-90°	18.6	0.3
90°-100°	114.3	1.8
100°-110°	355.0	5.7
110°-120°	606.9	9.8
120°-130°	798.1	12.9
130°-140°	895.8	14.5
140°-150°	878.3	14.2
150°-160°	736.7	11.9
160°-170°	488.6	7.9
170°-180°	170.8	2.8
0°-30°	461.7	7.5
0°-40°	675.2	10.9
0°-60°	997.5	16.1
0°-90°	1148.2	18.5
90°-120°	1076.2	17.4
90°-150°	3648.4	58.9
90°-180°	5045.0	81.5
0°-180°	6192.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	660	660	660	660	660	
5°	734	662	587	662	734	72
15°	829	628	389	628	829	224
25°	442	558	282	558	442	210
35°	218	461	208	461	218	139
45°	151	348	148	348	151	117
55°	105	236	104	236	105	92
65°	55	143	62	143	55	56
75°	29	68	33	68	29	31
85°	8	15	9	15	8	10
90°	52	2	52	2	52	23
95°	94	79	94	79	94	105
105°	338	327	338	327	338	355
115°	609	609	609	609	609	601
125°	889	886	889	886	889	793
135°	1160	1146	1160	1146	1160	893
145°	1407	1392	1407	1392	1407	878
155°	1603	1591	1603	1591	1603	738
165°	1732	1731	1732	1731	1732	489
175°	1795	1801	1795	1801	1795	171
180°	1804	1804	1804	1804	1804	



TEST NUMBER: P331782-840

CATALOG NUMBER: S122RDIW-S290D1440U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1
2.5°	687.0	687.5	688.1	686.8	686.8	685.7	683.3	681.5	676.3	675.6	675.6
5°	734.5	734.1	735.0	732.0	727.9	726.9	722.6	716.8	710.8	704.3	702.9
7.5°	781.7	781.0	779.2	778.7	775.6	768.6	761.6	754.2	744.3	734.6	729.7
10°	805.7	813.2	808.6	800.6	802.1	791.4	785.7	775.8	767.5	753.1	749.9
12.5°	829.1	832.1	830.6	826.1	824.0	816.6	808.8	800.2	785.0	772.0	760.7
15°	829.0	833.3	834.6	833.1	834.2	833.8	829.7	822.6	809.3	795.1	782.6
17.5°	767.8	770.8	778.4	783.5	789.9	803.4	810.2	812.7	810.8	802.6	794.0
20°	699.2	694.2	715.3	726.0	735.2	758.1	777.9	785.5	797.6	797.4	795.1
22.5°	601.9	603.1	623.1	635.9	662.7	685.7	708.1	736.6	760.1	775.7	784.8
25°	442.2	451.0	470.9	488.4	518.2	560.9	599.7	644.6	687.0	720.5	752.5
27.5°	332.1	332.9	348.6	364.8	382.4	417.4	466.3	519.9	580.4	630.4	687.7
30°	284.5	283.1	289.7	299.6	314.8	341.8	378.5	431.2	491.6	566.8	633.8
32.5°	250.6	250.7	255.8	263.1	275.6	293.9	319.0	361.9	418.9	492.9	571.4
35°	217.9	217.7	221.4	226.6	231.9	243.6	260.8	283.3	322.6	391.5	471.8
37.5°	194.4	195.4	197.2	200.6	206.3	212.9	223.2	238.3	266.2	307.1	374.6
40°	181.2	181.7	184.2	186.9	190.4	195.4	203.9	216.1	236.5	269.0	318.4
42.5°	169.2	169.6	171.4	173.9	176.6	181.7	188.7	199.2	215.8	241.2	281.9
45°	151.4	151.4	153.0	154.1	157.1	161.7	167.4	176.2	187.6	206.4	233.5
47.5°	134.8	134.8	135.9	137.8	139.8	143.3	149.0	156.1	164.4	178.9	202.1
50°	125.2	125.5	126.1	127.7	129.0	132.1	136.5	142.7	151.4	162.7	181.9
52.5°	117.5	117.4	118.3	119.0	119.8	122.0	125.3	130.8	138.6	148.3	164.3
55°	105.0	104.1	105.5	106.6	107.3	108.3	110.1	113.5	120.2	128.5	140.4
57.5°	89.5	89.1	90.1	91.1	93.3	95.7	97.4	99.5	102.9	108.9	120.7
60°	76.6	76.6	78.7	79.4	81.9	85.1	88.4	90.2	93.6	97.5	106.2
62.5°	65.2	65.4	66.3	67.1	68.5	72.4	77.0	81.0	84.2	88.0	93.7
65°	54.6	55.0	55.0	55.5	56.5	57.4	59.2	62.4	68.2	73.4	77.8
67.5°	46.4	46.5	46.7	47.1	47.3	48.3	49.1	50.5	51.8	56.8	62.2
70°	40.8	41.5	41.3	41.7	42.0	42.4	43.3	44.0	46.2	47.3	50.5
72.5°	35.6	36.2	36.2	36.5	37.1	37.2	37.9	38.6	39.9	40.8	42.6
75°	28.9	28.7	28.9	29.4	29.6	29.8	29.8	30.7	31.4	32.3	33.5
77.5°	22.3	22.5	22.5	22.5	22.6	23.0	22.9	23.3	24.0	24.5	25.0
80°	17.9	18.1	17.9	18.1	18.4	18.6	18.4	18.6	19.3	19.7	19.7
82.5°	13.8	13.9	14.0	14.0	14.1	14.1	14.5	14.5	15.0	14.9	15.1
85°	8.3	8.1	8.1	8.1	8.3	8.5	8.3	8.3	8.5	8.5	8.5
87.5°	13.3	13.4	13.3	13.2	13.2	13.2	13.3	13.7	13.6	13.9	12.3
90°	51.8	51.4	51.1	50.8	50.4	50.6	51.3	51.9	52.6	53.3	45.8
92.5°	49.3	49.3	49.2	49.1	49.1	49.0	48.8	48.7	48.6	48.4	46.7
95°	94.4	95.0	95.7	96.4	97.0	97.5	97.5	97.5	97.5	97.5	96.7
97.5°	163.5	163.6	163.6	163.7	163.8	163.8	163.8	163.8	163.8	163.8	162.5
100°	208.5	208.9	209.2	209.5	210.0	210.1	210.1	210.1	210.1	210.1	209.0
102.5°	259.7	260.0	260.4	260.7	261.1	261.2	260.8	260.5	260.3	260.0	258.7
105°	338.0	338.0	338.0	338.0	338.0	337.6	337.0	336.3	335.6	335.0	334.3
107.5°	411.6	413.2	414.8	416.4	417.9	418.5	418.3	418.0	417.7	417.5	417.5
110°	468.9	469.9	470.9	471.9	472.9	473.5	473.5	473.5	473.5	473.5	473.5



TEST NUMBER: P331782-840

CATALOG NUMBER: S122RDIW-S290D1440U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	523.7	524.4	525.2	525.9	526.6	527.5	528.3	529.1	529.9	530.7	531.0
115°	608.9	610.0	611.0	612.0	613.0	613.7	614.0	614.4	614.7	615.1	615.7
117.5°	690.2	691.3	692.3	693.3	694.3	695.3	696.1	696.9	697.7	698.5	700.3
120°	747.5	748.5	749.5	750.5	751.5	752.0	752.0	752.0	752.0	752.0	754.8
122.5°	803.5	804.3	805.1	805.8	806.5	807.3	808.1	808.9	809.7	810.5	812.4
125°	889.1	889.5	889.8	890.1	890.5	891.1	892.1	893.1	894.1	895.1	896.3
127.5°	967.0	968.2	969.2	970.3	971.4	972.5	973.7	974.9	976.1	977.4	978.7
130°	1023.1	1024.4	1025.8	1027.1	1028.4	1029.5	1030.2	1030.9	1031.6	1032.2	1032.9
132.5°	1076.6	1077.7	1078.8	1079.9	1081.0	1082.3	1083.8	1085.3	1086.7	1088.2	1088.1
135°	1160.1	1161.1	1162.2	1163.2	1164.2	1164.9	1165.2	1165.5	1165.9	1166.2	1165.5
137.5°	1235.6	1237.0	1238.3	1239.7	1241.0	1241.8	1242.1	1242.3	1242.6	1242.9	1242.0
140°	1288.0	1289.3	1290.7	1292.0	1293.4	1294.0	1294.0	1294.0	1294.0	1294.0	1292.4
142.5°	1335.4	1336.9	1338.2	1339.6	1340.9	1341.4	1341.2	1340.9	1340.6	1340.4	1339.2
145°	1406.7	1408.1	1409.5	1410.8	1412.1	1412.6	1412.3	1412.0	1411.6	1411.3	1409.3
147.5°	1470.4	1471.7	1472.9	1474.2	1475.5	1475.8	1475.0	1474.3	1473.6	1472.8	1471.5
150°	1511.8	1512.8	1513.8	1514.8	1515.8	1515.8	1514.8	1513.8	1512.8	1511.8	1510.5
152.5°	1550.7	1552.1	1553.3	1554.6	1555.9	1555.9	1554.6	1553.3	1552.1	1550.7	1549.1
155°	1603.2	1604.2	1605.2	1606.2	1607.2	1606.8	1605.2	1603.5	1601.7	1600.0	1599.0
157.5°	1648.2	1649.8	1651.4	1653.0	1654.7	1654.4	1652.0	1649.7	1647.4	1645.2	1644.6
160°	1676.2	1677.6	1678.9	1680.2	1681.6	1681.2	1679.2	1677.2	1675.2	1673.1	1672.8
162.5°	1700.5	1702.2	1703.8	1705.5	1707.1	1706.7	1704.5	1702.1	1699.8	1697.5	1697.2
165°	1732.5	1734.2	1736.0	1737.6	1739.3	1739.0	1736.6	1734.2	1731.8	1729.5	1729.5
167.5°	1758.7	1760.5	1762.2	1764.0	1765.7	1765.4	1763.1	1760.7	1758.4	1756.0	1756.1
170°	1772.1	1774.1	1776.2	1778.2	1780.2	1780.1	1777.7	1775.3	1772.9	1770.6	1770.9
172.5°	1783.1	1785.1	1787.2	1789.2	1791.2	1791.0	1788.7	1786.2	1783.9	1781.5	1781.9
175°	1794.9	1797.0	1799.0	1801.0	1803.1	1802.9	1800.5	1798.2	1795.8	1793.4	1794.1
177.5°	1800.4	1802.0	1803.7	1805.3	1807.0	1807.0	1805.3	1803.7	1802.0	1800.4	1801.0
180°	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1



TEST NUMBER: P331782-840

CATALOG NUMBER: S122RDIW-S290D1440U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1
2.5°	676.0	674.5	673.2	669.9	668.2	664.6	664.1	663.9	659.1	654.5	653.2
5°	699.2	695.5	690.0	683.6	676.9	670.0	665.5	661.8	652.6	643.9	638.8
7.5°	722.6	714.7	705.2	693.1	682.9	671.6	663.1	655.5	642.5	630.0	621.6
10°	740.0	727.2	714.6	697.8	684.7	671.9	659.9	649.6	635.0	618.4	606.7
12.5°	750.8	736.7	719.3	703.0	686.0	669.6	653.7	640.5	623.2	606.1	592.3
15°	765.5	750.3	729.2	705.8	684.1	662.7	644.4	627.8	605.4	584.9	567.9
17.5°	777.5	756.6	734.0	706.9	681.7	654.6	631.0	609.9	584.8	560.2	540.2
20°	781.3	760.6	734.5	707.4	677.6	645.7	620.3	597.3	570.5	543.6	520.7
22.5°	778.9	762.9	733.8	701.4	670.9	637.5	608.7	582.1	552.3	524.9	498.4
25°	762.8	757.2	729.7	694.4	659.5	620.8	587.4	558.4	524.4	495.0	466.2
27.5°	725.0	736.9	719.8	682.2	643.4	601.9	564.4	531.3	496.0	463.0	434.2
30°	688.6	715.9	708.6	673.7	630.4	589.6	547.5	512.9	475.3	441.3	412.9
32.5°	638.9	684.0	691.2	662.0	617.1	572.3	528.3	493.8	454.5	418.8	391.0
35°	559.7	627.1	658.1	639.5	594.6	546.1	500.8	460.6	421.1	385.9	358.3
37.5°	465.2	557.1	608.7	610.1	568.8	518.5	469.0	429.1	388.7	354.1	324.3
40°	403.9	503.5	570.8	585.6	550.8	496.4	446.4	405.8	366.4	332.3	298.2
42.5°	348.9	448.1	530.7	556.6	529.0	474.9	424.7	382.3	344.0	311.8	276.9
45°	282.2	368.9	459.9	506.2	490.9	440.9	387.9	347.5	311.5	283.8	250.2
47.5°	238.0	299.1	387.3	449.9	449.7	404.0	351.8	313.3	279.8	253.8	226.7
50°	212.9	266.1	340.6	411.7	417.7	379.4	329.8	291.5	260.3	233.1	211.3
52.5°	190.3	234.2	301.1	369.4	386.4	353.1	305.1	269.7	239.4	214.3	195.7
55°	160.8	194.8	245.7	309.4	335.2	311.7	269.0	236.0	211.5	190.4	174.3
57.5°	136.0	161.5	202.4	253.7	283.6	268.9	233.7	206.8	185.8	166.7	154.1
60°	120.5	141.3	175.9	218.8	251.9	241.6	211.5	186.5	168.6	152.1	140.2
62.5°	105.7	123.7	153.4	188.2	218.4	214.2	189.7	168.6	153.0	137.9	127.8
65°	85.1	98.2	121.4	148.7	173.0	175.0	157.3	143.1	129.2	117.2	108.3
67.5°	67.8	76.3	92.6	115.6	133.8	140.4	129.6	118.7	107.6	98.4	90.6
70°	57.2	64.0	75.9	94.5	111.3	118.2	111.9	103.4	93.8	86.2	79.6
72.5°	46.3	53.0	61.8	75.4	89.8	97.3	95.0	89.0	81.2	74.8	68.6
75°	34.8	37.0	42.9	52.1	63.3	69.8	71.3	68.2	61.9	57.2	53.4
77.5°	25.8	27.1	29.9	34.6	42.0	47.8	50.1	49.7	45.4	42.7	39.2
80°	20.6	21.3	22.7	24.7	30.3	36.1	37.7	37.7	34.6	33.5	30.1
82.5°	15.7	16.2	17.1	18.2	20.7	25.8	27.6	27.9	26.1	24.5	21.8
85°	9.0	8.7	9.2	9.9	10.3	11.7	14.4	14.9	14.4	12.6	11.9
87.5°	10.8	9.5	8.0	6.7	6.1	5.5	5.6	5.7	5.7	6.0	6.4
90°	38.4	31.0	23.5	17.8	13.7	9.6	5.6	1.5	5.6	9.6	13.7
92.5°	44.9	43.1	41.4	39.0	36.1	33.0	30.1	27.1	30.1	33.0	36.1
95°	96.0	95.4	94.7	92.7	89.3	85.9	82.5	79.2	82.5	85.9	89.3
97.5°	161.3	160.0	158.6	156.5	153.6	150.6	147.6	144.6	147.6	150.6	153.6
100°	208.0	207.0	206.0	204.2	201.5	198.7	196.0	193.4	196.0	198.7	201.5
102.5°	257.4	256.2	254.9	253.2	251.0	248.8	246.7	244.5	246.7	248.8	251.0
105°	333.6	333.0	332.2	331.3	330.3	329.3	328.3	327.3	328.3	329.3	330.3
107.5°	417.5	417.5	417.5	416.7	415.3	413.7	412.2	410.7	412.2	413.7	415.3
110°	473.5	473.5	473.5	472.4	470.4	468.4	466.4	464.3	466.4	468.4	470.4



TEST NUMBER: P331782-840

CATALOG NUMBER: S122RDIW-S290D1440U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	531.3	531.5	531.8	530.9	528.9	526.8	524.8	522.8	524.8	526.8	528.9
115°	616.4	617.1	617.7	617.1	615.1	613.0	611.0	608.9	611.0	613.0	615.1
117.5°	702.3	704.2	706.1	705.7	703.0	700.2	697.5	694.9	697.5	700.2	703.0
120°	757.5	760.2	763.0	763.0	760.2	757.5	754.8	752.0	754.8	757.5	760.2
122.5°	814.4	816.3	818.1	817.5	814.2	810.9	807.7	804.5	807.7	810.9	814.2
125°	897.3	898.3	899.3	898.3	895.1	892.1	889.1	886.1	889.1	892.1	895.1
127.5°	979.9	981.1	982.3	981.0	977.1	973.2	969.4	965.5	969.4	973.2	977.1
130°	1033.6	1034.2	1034.9	1033.1	1028.6	1024.3	1019.9	1015.4	1019.9	1024.3	1028.6
132.5°	1087.9	1087.8	1087.7	1085.8	1082.3	1078.6	1075.1	1071.5	1075.1	1078.6	1082.3
135°	1164.9	1164.2	1163.5	1161.2	1157.5	1153.9	1150.1	1146.4	1150.1	1153.9	1157.5
137.5°	1241.1	1240.3	1239.4	1237.4	1234.4	1231.3	1228.3	1225.3	1228.3	1231.3	1234.4
140°	1290.7	1289.0	1287.3	1285.0	1281.9	1278.9	1275.8	1272.7	1275.8	1278.9	1281.9
142.5°	1338.1	1336.9	1335.7	1333.6	1330.6	1327.6	1324.5	1321.5	1324.5	1327.6	1330.6
145°	1407.2	1405.2	1403.2	1401.0	1398.6	1396.2	1393.9	1391.5	1393.9	1396.2	1398.6
147.5°	1470.1	1468.7	1467.4	1465.3	1462.5	1459.6	1456.7	1453.9	1456.7	1459.6	1462.5
150°	1509.0	1507.7	1506.3	1504.7	1502.7	1500.7	1498.5	1496.5	1498.5	1500.7	1502.7
152.5°	1547.5	1545.9	1544.3	1542.5	1540.3	1538.3	1536.3	1534.3	1536.3	1538.3	1540.3
155°	1598.0	1597.0	1596.0	1595.0	1594.0	1593.0	1592.0	1590.9	1592.0	1593.0	1594.0
157.5°	1644.0	1643.4	1642.7	1642.0	1641.4	1640.7	1640.0	1639.3	1640.0	1640.7	1641.4
160°	1672.4	1672.1	1671.8	1671.3	1670.6	1669.9	1669.3	1668.6	1669.3	1669.9	1670.6
162.5°	1696.9	1696.5	1696.2	1696.0	1695.8	1695.7	1695.6	1695.4	1695.6	1695.7	1695.8
165°	1729.5	1729.5	1729.5	1729.7	1730.0	1730.3	1730.7	1731.0	1730.7	1730.3	1730.0
167.5°	1756.2	1756.2	1756.3	1756.8	1757.8	1758.8	1759.8	1760.8	1759.8	1758.8	1757.8
170°	1771.3	1771.6	1771.9	1772.6	1773.6	1774.6	1775.6	1776.7	1775.6	1774.6	1773.6
172.5°	1782.2	1782.6	1782.9	1783.6	1784.6	1785.6	1786.7	1787.7	1786.7	1785.6	1784.6
175°	1794.7	1795.4	1796.1	1797.0	1798.0	1799.0	1800.0	1801.0	1800.0	1799.0	1798.0
177.5°	1801.5	1802.0	1802.6	1803.3	1804.1	1804.9	1805.7	1806.5	1805.7	1804.9	1804.1
180°	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1



TEST NUMBER: P331782-840

CATALOG NUMBER: S122RDIW-S290D1440U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1
2.5°	650.9	649.5	647.1	643.5	641.3	637.4	634.9	636.3	636.7	636.3	636.0
5°	633.4	628.5	621.9	615.4	609.5	603.1	599.4	597.8	594.6	592.8	591.8
7.5°	612.2	603.9	594.5	583.3	573.8	563.8	558.8	556.2	549.7	546.1	543.0
10°	596.4	583.3	573.9	559.3	550.3	537.2	528.3	528.6	519.6	514.5	510.9
12.5°	579.0	564.6	549.0	535.7	523.3	512.8	502.0	497.7	488.2	483.3	473.4
15°	550.1	533.3	516.8	499.0	486.4	470.0	454.4	435.4	420.0	406.7	403.0
17.5°	518.6	497.8	481.2	460.2	438.6	411.2	393.1	382.0	372.8	365.8	360.5
20°	496.9	475.7	458.1	426.5	397.3	378.7	365.5	356.9	347.3	339.7	335.6
22.5°	474.1	452.1	428.0	392.6	369.9	355.1	343.3	333.5	326.9	321.0	317.2
25°	441.8	417.7	378.0	353.8	335.4	319.7	311.5	305.6	298.7	290.6	287.0
27.5°	407.7	369.4	340.8	322.8	305.3	295.2	287.7	278.8	272.7	269.0	265.2
30°	382.1	343.9	321.6	301.8	289.5	278.2	269.5	264.5	258.5	252.4	249.8
32.5°	353.8	323.2	301.7	285.4	272.8	263.2	256.3	248.1	243.9	240.0	234.8
35°	318.4	295.2	275.7	262.5	250.4	242.7	234.7	229.8	222.1	218.8	216.8
37.5°	288.5	268.4	253.9	239.8	230.4	221.8	216.8	209.1	205.8	201.3	196.9
40°	271.6	251.9	237.9	226.4	215.8	209.4	203.3	197.0	192.0	190.0	184.7
42.5°	254.4	238.3	224.3	211.8	204.7	197.8	190.1	185.5	180.3	176.9	173.7
45°	230.6	216.3	204.4	194.1	186.2	179.2	174.1	166.5	163.6	156.9	154.1
47.5°	209.6	196.4	185.0	175.2	167.6	163.0	155.6	149.7	144.9	140.8	137.2
50°	194.8	183.7	172.7	164.0	157.1	150.5	142.9	140.0	132.6	130.5	128.5
52.5°	181.2	170.7	160.7	152.1	145.2	138.8	132.1	128.2	123.2	121.2	119.7
55°	162.2	152.1	142.5	134.9	128.1	121.4	117.2	112.4	110.1	108.5	106.6
57.5°	143.1	134.0	126.6	119.0	112.0	106.7	102.0	99.1	96.7	94.6	92.4
60°	131.0	122.3	115.6	108.5	101.4	97.0	93.4	89.9	87.2	83.9	83.0
62.5°	118.2	110.5	104.4	97.5	91.3	87.4	83.8	80.6	77.3	72.6	71.3
65°	100.5	94.5	88.1	82.3	76.9	72.9	67.9	64.2	62.8	62.4	62.2
67.5°	84.5	78.9	73.3	67.5	62.5	58.9	56.2	55.7	54.7	54.5	53.8
70°	73.8	68.6	63.1	57.6	52.7	52.1	51.2	50.2	49.1	48.7	48.2
72.5°	64.3	58.9	53.3	49.0	46.9	46.0	45.1	44.1	43.4	42.9	42.7
75°	49.3	44.2	40.6	39.0	37.9	37.2	35.7	35.1	34.6	33.9	33.7
77.5°	35.5	32.6	31.0	30.0	28.8	28.1	27.3	26.6	26.1	26.0	25.5
80°	27.1	25.7	24.5	23.1	22.7	21.8	21.6	20.9	21.1	20.4	20.4
82.5°	21.0	19.3	18.3	17.7	17.2	16.5	16.3	16.0	16.0	15.5	15.5
85°	10.8	10.3	9.9	9.4	9.4	8.7	9.0	8.7	8.7	8.3	8.1
87.5°	7.1	8.0	9.1	10.6	12.1	13.4	13.2	12.9	12.8	12.7	12.4
90°	17.8	23.5	31.0	38.4	45.8	53.3	52.6	51.9	51.3	50.6	50.4
92.5°	39.0	41.4	43.1	44.9	46.7	48.4	48.6	48.7	48.8	49.0	49.1
95°	92.7	94.7	95.4	96.0	96.7	97.5	97.5	97.5	97.5	97.5	97.0
97.5°	156.5	158.6	160.0	161.3	162.5	163.8	163.8	163.8	163.8	163.8	163.8
100°	204.2	206.0	207.0	208.0	209.0	210.1	210.1	210.1	210.1	210.1	210.0
102.5°	253.2	254.9	256.2	257.4	258.7	260.0	260.3	260.5	260.8	261.2	261.1
105°	331.3	332.2	333.0	333.6	334.3	335.0	335.6	336.3	337.0	337.6	338.0
107.5°	416.7	417.5	417.5	417.5	417.5	417.5	417.7	418.0	418.3	418.5	417.9
110°	472.4	473.5	473.5	473.5	473.5	473.5	473.5	473.5	473.5	473.5	472.9



TEST NUMBER: P331782-840

CATALOG NUMBER: S122RDIW-S290D1440U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	530.9	531.8	531.5	531.3	531.0	530.7	529.9	529.1	528.3	527.5	526.6
115°	617.1	617.7	617.1	616.4	615.7	615.1	614.7	614.4	614.0	613.7	613.0
117.5°	705.7	706.1	704.2	702.3	700.3	698.5	697.7	696.9	696.1	695.3	694.3
120°	763.0	763.0	760.2	757.5	754.8	752.0	752.0	752.0	752.0	752.0	751.5
122.5°	817.5	818.1	816.3	814.4	812.4	810.5	809.7	808.9	808.1	807.3	806.5
125°	898.3	899.3	898.3	897.3	896.3	895.1	894.1	893.1	892.1	891.1	890.5
127.5°	981.0	982.3	981.1	979.9	978.7	977.4	976.1	974.9	973.7	972.5	971.4
130°	1033.1	1034.9	1034.2	1033.6	1032.9	1032.2	1031.6	1030.9	1030.2	1029.5	1028.4
132.5°	1085.8	1087.7	1087.8	1087.9	1088.1	1088.2	1086.7	1085.3	1083.8	1082.3	1081.0
135°	1161.2	1163.5	1164.2	1164.9	1165.5	1166.2	1165.9	1165.5	1165.2	1164.9	1164.2
137.5°	1237.4	1239.4	1240.3	1241.1	1242.0	1242.9	1242.6	1242.3	1242.1	1241.8	1241.0
140°	1285.0	1287.3	1289.0	1290.7	1292.4	1294.0	1294.0	1294.0	1294.0	1294.0	1293.4
142.5°	1333.6	1335.7	1336.9	1338.1	1339.2	1340.4	1340.6	1340.9	1341.2	1341.4	1340.9
145°	1401.0	1403.2	1405.2	1407.2	1409.3	1411.3	1411.6	1412.0	1412.3	1412.6	1412.1
147.5°	1465.3	1467.4	1468.7	1470.1	1471.5	1472.8	1473.6	1474.3	1475.0	1475.8	1475.5
150°	1504.7	1506.3	1507.7	1509.0	1510.5	1511.8	1512.8	1513.8	1514.8	1515.8	1515.8
152.5°	1542.5	1544.3	1545.9	1547.5	1549.1	1550.7	1552.1	1553.3	1554.6	1555.9	1555.9
155°	1595.0	1596.0	1597.0	1598.0	1599.0	1600.0	1601.7	1603.5	1605.2	1606.8	1607.2
157.5°	1642.0	1642.7	1643.4	1644.0	1644.6	1645.2	1647.4	1649.7	1652.0	1654.4	1654.7
160°	1671.3	1671.8	1672.1	1672.4	1672.8	1673.1	1675.2	1677.2	1679.2	1681.2	1681.6
162.5°	1696.0	1696.2	1696.5	1696.9	1697.2	1697.5	1699.8	1702.1	1704.5	1706.7	1707.1
165°	1729.7	1729.5	1729.5	1729.5	1729.5	1729.5	1731.8	1734.2	1736.6	1739.0	1739.3
167.5°	1756.8	1756.3	1756.2	1756.2	1756.1	1756.0	1758.4	1760.7	1763.1	1765.4	1765.7
170°	1772.6	1771.9	1771.6	1771.3	1770.9	1770.6	1772.9	1775.3	1777.7	1780.1	1780.2
172.5°	1783.6	1782.9	1782.6	1782.2	1781.9	1781.5	1783.9	1786.2	1788.7	1791.0	1791.2
175°	1797.0	1796.1	1795.4	1794.7	1794.1	1793.4	1795.8	1798.2	1800.5	1802.9	1803.1
177.5°	1803.3	1802.6	1802.0	1801.5	1801.0	1800.4	1802.0	1803.7	1805.3	1807.0	1807.0
180°	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1



TEST NUMBER: P331782-840

CATALOG NUMBER: S122RDIW-S290D1440U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1
2.5°	634.0	634.3	633.8	634.1	633.8	634.3	634.0	636.0	636.3	636.7	636.3
5°	590.7	587.9	587.4	586.8	587.4	587.9	590.7	591.8	592.8	594.6	597.8
7.5°	539.1	538.7	537.5	535.8	537.5	538.7	539.1	543.0	546.1	549.7	556.2
10°	505.8	504.6	504.4	502.8	504.4	504.6	505.8	510.9	514.5	519.6	528.6
12.5°	466.9	459.5	458.8	454.7	458.8	459.5	466.9	473.4	483.3	488.2	497.7
15°	397.6	396.2	391.5	388.6	391.5	396.2	397.6	403.0	406.7	420.0	435.4
17.5°	357.9	353.4	351.9	351.3	351.9	353.4	357.9	360.5	365.8	372.8	382.0
20°	332.3	328.3	327.6	327.1	327.6	328.3	332.3	335.6	339.7	347.3	356.9
22.5°	314.8	310.4	308.7	307.3	308.7	310.4	314.8	317.2	321.0	326.9	333.5
25°	284.7	283.1	282.2	281.7	282.2	283.1	284.7	287.0	290.6	298.7	305.6
27.5°	261.2	257.6	256.9	255.7	256.9	257.6	261.2	265.2	269.0	272.7	278.8
30°	247.7	246.6	245.0	243.6	245.0	246.6	247.7	249.8	252.4	258.5	264.5
32.5°	232.0	231.0	229.5	228.9	229.5	231.0	232.0	234.8	240.0	243.9	248.1
35°	214.5	211.3	209.8	207.8	209.8	211.3	214.5	216.8	218.8	222.1	229.8
37.5°	196.0	194.3	192.4	193.1	192.4	194.3	196.0	196.9	201.3	205.8	209.1
40°	181.7	180.6	180.1	179.9	180.1	180.6	181.7	184.7	190.0	192.0	197.0
42.5°	170.3	167.1	165.9	165.9	165.9	167.1	170.3	173.7	176.9	180.3	185.5
45°	153.0	150.1	147.9	148.1	147.9	150.1	153.0	154.1	156.9	163.6	166.5
47.5°	135.3	135.2	133.9	134.3	133.9	135.2	135.3	137.2	140.8	144.9	149.7
50°	126.8	125.5	124.5	124.8	124.5	125.5	126.8	128.5	130.5	132.6	140.0
52.5°	118.8	117.5	116.8	117.9	116.8	117.5	118.8	119.7	121.2	123.2	128.2
55°	105.5	104.1	103.9	103.7	103.9	104.1	105.5	106.6	108.5	110.1	112.4
57.5°	90.7	89.8	88.4	87.9	88.4	89.8	90.7	92.4	94.6	96.7	99.1
60°	80.1	78.3	75.9	75.7	75.9	78.3	80.1	83.0	83.9	87.2	89.9
62.5°	70.3	70.0	69.5	69.5	69.5	70.0	70.3	71.3	72.6	77.3	80.6
65°	61.7	61.5	61.7	61.9	61.7	61.5	61.7	62.2	62.4	62.8	64.2
67.5°	53.7	53.3	52.9	53.1	52.9	53.3	53.7	53.8	54.5	54.7	55.7
70°	47.7	47.5	47.3	47.3	47.3	47.5	47.7	48.2	48.7	49.1	50.2
72.5°	41.8	41.8	41.6	41.4	41.6	41.8	41.8	42.7	42.9	43.4	44.1
75°	33.5	33.0	33.0	33.0	33.0	33.0	33.5	33.7	33.9	34.6	35.1
77.5°	25.5	25.2	25.0	24.8	25.0	25.2	25.5	25.5	26.0	26.1	26.6
80°	20.2	20.0	19.7	19.7	19.7	20.0	20.2	20.4	20.4	21.1	20.9
82.5°	15.5	15.1	15.1	14.9	15.1	15.1	15.5	15.5	15.5	16.0	16.0
85°	8.3	8.5	8.3	8.7	8.3	8.5	8.3	8.1	8.3	8.7	8.7
87.5°	12.5	12.4	12.6	12.5	12.6	12.4	12.5	12.4	12.7	12.8	12.9
90°	50.8	51.1	51.4	51.8	51.4	51.1	50.8	50.4	50.6	51.3	51.9
92.5°	49.1	49.2	49.3	49.3	49.3	49.2	49.1	49.1	49.0	48.8	48.7
95°	96.4	95.7	95.0	94.4	95.0	95.7	96.4	97.0	97.5	97.5	97.5
97.5°	163.7	163.6	163.6	163.5	163.6	163.6	163.7	163.8	163.8	163.8	163.8
100°	209.5	209.2	208.9	208.5	208.9	209.2	209.5	210.0	210.1	210.1	210.1
102.5°	260.7	260.4	260.0	259.7	260.0	260.4	260.7	261.1	261.2	260.8	260.5
105°	338.0	338.0	338.0	338.0	338.0	338.0	338.0	338.0	337.6	337.0	336.3
107.5°	416.4	414.8	413.2	411.6	413.2	414.8	416.4	417.9	418.5	418.3	418.0
110°	471.9	470.9	469.9	468.9	469.9	470.9	471.9	472.9	473.5	473.5	473.5



TEST NUMBER: P331782-840

CATALOG NUMBER: S122RDIW-S290D1440U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	525.9	525.2	524.4	523.7	524.4	525.2	525.9	526.6	527.5	528.3	529.1
115°	612.0	611.0	610.0	608.9	610.0	611.0	612.0	613.0	613.7	614.0	614.4
117.5°	693.3	692.3	691.3	690.2	691.3	692.3	693.3	694.3	695.3	696.1	696.9
120°	750.5	749.5	748.5	747.5	748.5	749.5	750.5	751.5	752.0	752.0	752.0
122.5°	805.8	805.1	804.3	803.5	804.3	805.1	805.8	806.5	807.3	808.1	808.9
125°	890.1	889.8	889.5	889.1	889.5	889.8	890.1	890.5	891.1	892.1	893.1
127.5°	970.3	969.2	968.2	967.0	968.2	969.2	970.3	971.4	972.5	973.7	974.9
130°	1027.1	1025.8	1024.4	1023.1	1024.4	1025.8	1027.1	1028.4	1029.5	1030.2	1030.9
132.5°	1079.9	1078.8	1077.7	1076.6	1077.7	1078.8	1079.9	1081.0	1082.3	1083.8	1085.3
135°	1163.2	1162.2	1161.1	1160.1	1161.1	1162.2	1163.2	1164.2	1164.9	1165.2	1165.5
137.5°	1239.7	1238.3	1237.0	1235.6	1237.0	1238.3	1239.7	1241.0	1241.8	1242.1	1242.3
140°	1292.0	1290.7	1289.3	1288.0	1289.3	1290.7	1292.0	1293.4	1294.0	1294.0	1294.0
142.5°	1339.6	1338.2	1336.9	1335.4	1336.9	1338.2	1339.6	1340.9	1341.4	1341.2	1340.9
145°	1410.8	1409.5	1408.1	1406.7	1408.1	1409.5	1410.8	1412.1	1412.6	1412.3	1412.0
147.5°	1474.2	1472.9	1471.7	1470.4	1471.7	1472.9	1474.2	1475.5	1475.8	1475.0	1474.3
150°	1514.8	1513.8	1512.8	1511.8	1512.8	1513.8	1514.8	1515.8	1515.8	1514.8	1513.8
152.5°	1554.6	1553.3	1552.1	1550.7	1552.1	1553.3	1554.6	1555.9	1555.9	1554.6	1553.3
155°	1606.2	1605.2	1604.2	1603.2	1604.2	1605.2	1606.2	1607.2	1606.8	1605.2	1603.5
157.5°	1653.0	1651.4	1649.8	1648.2	1649.8	1651.4	1653.0	1654.7	1654.4	1652.0	1649.7
160°	1680.2	1678.9	1677.6	1676.2	1677.6	1678.9	1680.2	1681.6	1681.2	1679.2	1677.2
162.5°	1705.5	1703.8	1702.2	1700.5	1702.2	1703.8	1705.5	1707.1	1706.7	1704.5	1702.1
165°	1737.6	1736.0	1734.2	1732.5	1734.2	1736.0	1737.6	1739.3	1739.0	1736.6	1734.2
167.5°	1764.0	1762.2	1760.5	1758.7	1760.5	1762.2	1764.0	1765.7	1765.4	1763.1	1760.7
170°	1778.2	1776.2	1774.1	1772.1	1774.1	1776.2	1778.2	1780.2	1780.1	1777.7	1775.3
172.5°	1789.2	1787.2	1785.1	1783.1	1785.1	1787.2	1789.2	1791.2	1791.0	1788.7	1786.2
175°	1801.0	1799.0	1797.0	1794.9	1797.0	1799.0	1801.0	1803.1	1802.9	1800.5	1798.2
177.5°	1805.3	1803.7	1802.0	1800.4	1802.0	1803.7	1805.3	1807.0	1807.0	1805.3	1803.7
180°	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1



TEST NUMBER: P331782-840

CATALOG NUMBER: S122RDIW-S290D1440U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1
2.5°	634.9	637.4	641.3	643.5	647.1	649.5	650.9	653.2	654.5	659.1	663.9
5°	599.4	603.1	609.5	615.4	621.9	628.5	633.4	638.8	643.9	652.6	661.8
7.5°	558.8	563.8	573.8	583.3	594.5	603.9	612.2	621.6	630.0	642.5	655.5
10°	528.3	537.2	550.3	559.3	573.9	583.3	596.4	606.7	618.4	635.0	649.6
12.5°	502.0	512.8	523.3	535.7	549.0	564.6	579.0	592.3	606.1	623.2	640.5
15°	454.4	470.0	486.4	499.0	516.8	533.3	550.1	567.9	584.9	605.4	627.8
17.5°	393.1	411.2	438.6	460.2	481.2	497.8	518.6	540.2	560.2	584.8	609.9
20°	365.5	378.7	397.3	426.5	458.1	475.7	496.9	520.7	543.6	570.5	597.3
22.5°	343.3	355.1	369.9	392.6	428.0	452.1	474.1	498.4	524.9	552.3	582.1
25°	311.5	319.7	335.4	353.8	378.0	417.7	441.8	466.2	495.0	524.4	558.4
27.5°	287.7	295.2	305.3	322.8	340.8	369.4	407.7	434.2	463.0	496.0	531.3
30°	269.5	278.2	289.5	301.8	321.6	343.9	382.1	412.9	441.3	475.3	512.9
32.5°	256.3	263.2	272.8	285.4	301.7	323.2	353.8	391.0	418.8	454.5	493.8
35°	234.7	242.7	250.4	262.5	275.7	295.2	318.4	358.3	385.9	421.1	460.6
37.5°	216.8	221.8	230.4	239.8	253.9	268.4	288.5	324.3	354.1	388.7	429.1
40°	203.3	209.4	215.8	226.4	237.9	251.9	271.6	298.2	332.3	366.4	405.8
42.5°	190.1	197.8	204.7	211.8	224.3	238.3	254.4	276.9	311.8	344.0	382.3
45°	174.1	179.2	186.2	194.1	204.4	216.3	230.6	250.2	283.8	311.5	347.5
47.5°	155.6	163.0	167.6	175.2	185.0	196.4	209.6	226.7	253.8	279.8	313.3
50°	142.9	150.5	157.1	164.0	172.7	183.7	194.8	211.3	233.1	260.3	291.5
52.5°	132.1	138.8	145.2	152.1	160.7	170.7	181.2	195.7	214.3	239.4	269.7
55°	117.2	121.4	128.1	134.9	142.5	152.1	162.2	174.3	190.4	211.5	236.0
57.5°	102.0	106.7	112.0	119.0	126.6	134.0	143.1	154.1	166.7	185.8	206.8
60°	93.4	97.0	101.4	108.5	115.6	122.3	131.0	140.2	152.1	168.6	186.5
62.5°	83.8	87.4	91.3	97.5	104.4	110.5	118.2	127.8	137.9	153.0	168.6
65°	67.9	72.9	76.9	82.3	88.1	94.5	100.5	108.3	117.2	129.2	143.1
67.5°	56.2	58.9	62.5	67.5	73.3	78.9	84.5	90.6	98.4	107.6	118.7
70°	51.2	52.1	52.7	57.6	63.1	68.6	73.8	79.6	86.2	93.8	103.4
72.5°	45.1	46.0	46.9	49.0	53.3	58.9	64.3	68.6	74.8	81.2	89.0
75°	35.7	37.2	37.9	39.0	40.6	44.2	49.3	53.4	57.2	61.9	68.2
77.5°	27.3	28.1	28.8	30.0	31.0	32.6	35.5	39.2	42.7	45.4	49.7
80°	21.6	21.8	22.7	23.1	24.5	25.7	27.1	30.1	33.5	34.6	37.7
82.5°	16.3	16.5	17.2	17.7	18.3	19.3	21.0	21.8	24.5	26.1	27.9
85°	9.0	8.7	9.4	9.4	9.9	10.3	10.8	11.9	12.6	14.4	14.9
87.5°	13.2	13.4	12.1	10.6	9.1	8.0	7.1	6.4	6.0	5.7	5.7
90°	52.6	53.3	45.8	38.4	31.0	23.5	17.8	13.7	9.6	5.6	1.5
92.5°	48.6	48.4	46.7	44.9	43.1	41.4	39.0	36.1	33.0	30.1	27.1
95°	97.5	97.5	96.7	96.0	95.4	94.7	92.7	89.3	85.9	82.5	79.2
97.5°	163.8	163.8	162.5	161.3	160.0	158.6	156.5	153.6	150.6	147.6	144.6
100°	210.1	210.1	209.0	208.0	207.0	206.0	204.2	201.5	198.7	196.0	193.4
102.5°	260.3	260.0	258.7	257.4	256.2	254.9	253.2	251.0	248.8	246.7	244.5
105°	335.6	335.0	334.3	333.6	333.0	332.2	331.3	330.3	329.3	328.3	327.3
107.5°	417.7	417.5	417.5	417.5	417.5	417.5	416.7	415.3	413.7	412.2	410.7
110°	473.5	473.5	473.5	473.5	473.5	473.5	472.4	470.4	468.4	466.4	464.3



TEST NUMBER: P331782-840

CATALOG NUMBER: S122RDIW-S290D1440U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	529.9	530.7	531.0	531.3	531.5	531.8	530.9	528.9	526.8	524.8	522.8
115°	614.7	615.1	615.7	616.4	617.1	617.7	617.1	615.1	613.0	611.0	608.9
117.5°	697.7	698.5	700.3	702.3	704.2	706.1	705.7	703.0	700.2	697.5	694.9
120°	752.0	752.0	754.8	757.5	760.2	763.0	763.0	760.2	757.5	754.8	752.0
122.5°	809.7	810.5	812.4	814.4	816.3	818.1	817.5	814.2	810.9	807.7	804.5
125°	894.1	895.1	896.3	897.3	898.3	899.3	898.3	895.1	892.1	889.1	886.1
127.5°	976.1	977.4	978.7	979.9	981.1	982.3	981.0	977.1	973.2	969.4	965.5
130°	1031.6	1032.2	1032.9	1033.6	1034.2	1034.9	1033.1	1028.6	1024.3	1019.9	1015.4
132.5°	1086.7	1088.2	1088.1	1087.9	1087.8	1087.7	1085.8	1082.3	1078.6	1075.1	1071.5
135°	1165.9	1166.2	1165.5	1164.9	1164.2	1163.5	1161.2	1157.5	1153.9	1150.1	1146.4
137.5°	1242.6	1242.9	1242.0	1241.1	1240.3	1239.4	1237.4	1234.4	1231.3	1228.3	1225.3
140°	1294.0	1294.0	1292.4	1290.7	1289.0	1287.3	1285.0	1281.9	1278.9	1275.8	1272.7
142.5°	1340.6	1340.4	1339.2	1338.1	1336.9	1335.7	1333.6	1330.6	1327.6	1324.5	1321.5
145°	1411.6	1411.3	1409.3	1407.2	1405.2	1403.2	1401.0	1398.6	1396.2	1393.9	1391.5
147.5°	1473.6	1472.8	1471.5	1470.1	1468.7	1467.4	1465.3	1462.5	1459.6	1456.7	1453.9
150°	1512.8	1511.8	1510.5	1509.0	1507.7	1506.3	1504.7	1502.7	1500.7	1498.5	1496.5
152.5°	1552.1	1550.7	1549.1	1547.5	1545.9	1544.3	1542.5	1540.3	1538.3	1536.3	1534.3
155°	1601.7	1600.0	1599.0	1598.0	1597.0	1596.0	1595.0	1594.0	1593.0	1592.0	1590.9
157.5°	1647.4	1645.2	1644.6	1644.0	1643.4	1642.7	1642.0	1641.4	1640.7	1640.0	1639.3
160°	1675.2	1673.1	1672.8	1672.4	1672.1	1671.8	1671.3	1670.6	1669.9	1669.3	1668.6
162.5°	1699.8	1697.5	1697.2	1696.9	1696.5	1696.2	1696.0	1695.8	1695.7	1695.6	1695.4
165°	1731.8	1729.5	1729.5	1729.5	1729.5	1729.5	1729.7	1730.0	1730.3	1730.7	1731.0
167.5°	1758.4	1756.0	1756.1	1756.2	1756.2	1756.3	1756.8	1757.8	1758.8	1759.8	1760.8
170°	1772.9	1770.6	1770.9	1771.3	1771.6	1771.9	1772.6	1773.6	1774.6	1775.6	1776.7
172.5°	1783.9	1781.5	1781.9	1782.2	1782.6	1782.9	1783.6	1784.6	1785.6	1786.7	1787.7
175°	1795.8	1793.4	1794.1	1794.7	1795.4	1796.1	1797.0	1798.0	1799.0	1800.0	1801.0
177.5°	1802.0	1800.4	1801.0	1801.5	1802.0	1802.6	1803.3	1804.1	1804.9	1805.7	1806.5
180°	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1



TEST NUMBER: P331782-840

CATALOG NUMBER: S122RDIW-S290D1440U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1
2.5°	664.1	664.6	668.2	669.9	673.2	674.5	676.0	675.6	675.6	676.3	681.5
5°	665.5	670.0	676.9	683.6	690.0	695.5	699.2	702.9	704.3	710.8	716.8
7.5°	663.1	671.6	682.9	693.1	705.2	714.7	722.6	729.7	734.6	744.3	754.2
10°	659.9	671.9	684.7	697.8	714.6	727.2	740.0	749.9	753.1	767.5	775.8
12.5°	653.7	669.6	686.0	703.0	719.3	736.7	750.8	760.7	772.0	785.0	800.2
15°	644.4	662.7	684.1	705.8	729.2	750.3	765.5	782.6	795.1	809.3	822.6
17.5°	631.0	654.6	681.7	706.9	734.0	756.6	777.5	794.0	802.6	810.8	812.7
20°	620.3	645.7	677.6	707.4	734.5	760.6	781.3	795.1	797.4	797.6	785.5
22.5°	608.7	637.5	670.9	701.4	733.8	762.9	778.9	784.8	775.7	760.1	736.6
25°	587.4	620.8	659.5	694.4	729.7	757.2	762.8	752.5	720.5	687.0	644.6
27.5°	564.4	601.9	643.4	682.2	719.8	736.9	725.0	687.7	630.4	580.4	519.9
30°	547.5	589.6	630.4	673.7	708.6	715.9	688.6	633.8	566.8	491.6	431.2
32.5°	528.3	572.3	617.1	662.0	691.2	684.0	638.9	571.4	492.9	418.9	361.9
35°	500.8	546.1	594.6	639.5	658.1	627.1	559.7	471.8	391.5	322.6	283.3
37.5°	469.0	518.5	568.8	610.1	608.7	557.1	465.2	374.6	307.1	266.2	238.3
40°	446.4	496.4	550.8	585.6	570.8	503.5	403.9	318.4	269.0	236.5	216.1
42.5°	424.7	474.9	529.0	556.6	530.7	448.1	348.9	281.9	241.2	215.8	199.2
45°	387.9	440.9	490.9	506.2	459.9	368.9	282.2	233.5	206.4	187.6	176.2
47.5°	351.8	404.0	449.7	449.9	387.3	299.1	238.0	202.1	178.9	164.4	156.1
50°	329.8	379.4	417.7	411.7	340.6	266.1	212.9	181.9	162.7	151.4	142.7
52.5°	305.1	353.1	386.4	369.4	301.1	234.2	190.3	164.3	148.3	138.6	130.8
55°	269.0	311.7	335.2	309.4	245.7	194.8	160.8	140.4	128.5	120.2	113.5
57.5°	233.7	268.9	283.6	253.7	202.4	161.5	136.0	120.7	108.9	102.9	99.5
60°	211.5	241.6	251.9	218.8	175.9	141.3	120.5	106.2	97.5	93.6	90.2
62.5°	189.7	214.2	218.4	188.2	153.4	123.7	105.7	93.7	88.0	84.2	81.0
65°	157.3	175.0	173.0	148.7	121.4	98.2	85.1	77.8	73.4	68.2	62.4
67.5°	129.6	140.4	133.8	115.6	92.6	76.3	67.8	62.2	56.8	51.8	50.5
70°	111.9	118.2	111.3	94.5	75.9	64.0	57.2	50.5	47.3	46.2	44.0
72.5°	95.0	97.3	89.8	75.4	61.8	53.0	46.3	42.6	40.8	39.9	38.6
75°	71.3	69.8	63.3	52.1	42.9	37.0	34.8	33.5	32.3	31.4	30.7
77.5°	50.1	47.8	42.0	34.6	29.9	27.1	25.8	25.0	24.5	24.0	23.3
80°	37.7	36.1	30.3	24.7	22.7	21.3	20.6	19.7	19.7	19.3	18.6
82.5°	27.6	25.8	20.7	18.2	17.1	16.2	15.7	15.1	14.9	15.0	14.5
85°	14.4	11.7	10.3	9.9	9.2	8.7	9.0	8.5	8.5	8.5	8.3
87.5°	5.6	5.5	6.1	6.7	8.0	9.5	10.8	12.3	13.9	13.6	13.7
90°	5.6	9.6	13.7	17.8	23.5	31.0	38.4	45.8	53.3	52.6	51.9
92.5°	30.1	33.0	36.1	39.0	41.4	43.1	44.9	46.7	48.4	48.6	48.7
95°	82.5	85.9	89.3	92.7	94.7	95.4	96.0	96.7	97.5	97.5	97.5
97.5°	147.6	150.6	153.6	156.5	158.6	160.0	161.3	162.5	163.8	163.8	163.8
100°	196.0	198.7	201.5	204.2	206.0	207.0	208.0	209.0	210.1	210.1	210.1
102.5°	246.7	248.8	251.0	253.2	254.9	256.2	257.4	258.7	260.0	260.3	260.5
105°	328.3	329.3	330.3	331.3	332.2	333.0	333.6	334.3	335.0	335.6	336.3
107.5°	412.2	413.7	415.3	416.7	417.5	417.5	417.5	417.5	417.5	417.7	418.0
110°	466.4	468.4	470.4	472.4	473.5	473.5	473.5	473.5	473.5	473.5	473.5



TEST NUMBER: P331782-840

CATALOG NUMBER: S122RDIW-S290D1440U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	524.8	526.8	528.9	530.9	531.8	531.5	531.3	531.0	530.7	529.9	529.1
115°	611.0	613.0	615.1	617.1	617.7	617.1	616.4	615.7	615.1	614.7	614.4
117.5°	697.5	700.2	703.0	705.7	706.1	704.2	702.3	700.3	698.5	697.7	696.9
120°	754.8	757.5	760.2	763.0	763.0	760.2	757.5	754.8	752.0	752.0	752.0
122.5°	807.7	810.9	814.2	817.5	818.1	816.3	814.4	812.4	810.5	809.7	808.9
125°	889.1	892.1	895.1	898.3	899.3	898.3	897.3	896.3	895.1	894.1	893.1
127.5°	969.4	973.2	977.1	981.0	982.3	981.1	979.9	978.7	977.4	976.1	974.9
130°	1019.9	1024.3	1028.6	1033.1	1034.9	1034.2	1033.6	1032.9	1032.2	1031.6	1030.9
132.5°	1075.1	1078.6	1082.3	1085.8	1087.7	1087.8	1087.9	1088.1	1088.2	1086.7	1085.3
135°	1150.1	1153.9	1157.5	1161.2	1163.5	1164.2	1164.9	1165.5	1166.2	1165.9	1165.5
137.5°	1228.3	1231.3	1234.4	1237.4	1239.4	1240.3	1241.1	1242.0	1242.9	1242.6	1242.3
140°	1275.8	1278.9	1281.9	1285.0	1287.3	1289.0	1290.7	1292.4	1294.0	1294.0	1294.0
142.5°	1324.5	1327.6	1330.6	1333.6	1335.7	1336.9	1338.1	1339.2	1340.4	1340.6	1340.9
145°	1393.9	1396.2	1398.6	1401.0	1403.2	1405.2	1407.2	1409.3	1411.3	1411.6	1412.0
147.5°	1456.7	1459.6	1462.5	1465.3	1467.4	1468.7	1470.1	1471.5	1472.8	1473.6	1474.3
150°	1498.5	1500.7	1502.7	1504.7	1506.3	1507.7	1509.0	1510.5	1511.8	1512.8	1513.8
152.5°	1536.3	1538.3	1540.3	1542.5	1544.3	1545.9	1547.5	1549.1	1550.7	1552.1	1553.3
155°	1592.0	1593.0	1594.0	1595.0	1596.0	1597.0	1598.0	1599.0	1600.0	1601.7	1603.5
157.5°	1640.0	1640.7	1641.4	1642.0	1642.7	1643.4	1644.0	1644.6	1645.2	1647.4	1649.7
160°	1669.3	1669.9	1670.6	1671.3	1671.8	1672.1	1672.4	1672.8	1673.1	1675.2	1677.2
162.5°	1695.6	1695.7	1695.8	1696.0	1696.2	1696.5	1696.9	1697.2	1697.5	1699.8	1702.1
165°	1730.7	1730.3	1730.0	1729.7	1729.5	1729.5	1729.5	1729.5	1729.5	1731.8	1734.2
167.5°	1759.8	1758.8	1757.8	1756.8	1756.3	1756.2	1756.2	1756.1	1756.0	1758.4	1760.7
170°	1775.6	1774.6	1773.6	1772.6	1771.9	1771.6	1771.3	1770.9	1770.6	1772.9	1775.3
172.5°	1786.7	1785.6	1784.6	1783.6	1782.9	1782.6	1782.2	1781.9	1781.5	1783.9	1786.2
175°	1800.0	1799.0	1798.0	1797.0	1796.1	1795.4	1794.7	1794.1	1793.4	1795.8	1798.2
177.5°	1805.7	1804.9	1804.1	1803.3	1802.6	1802.0	1801.5	1801.0	1800.4	1802.0	1803.7
180°	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1



TEST NUMBER: P331782-840

CATALOG NUMBER: S122RDIW-S290D1440U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	660.1	660.1	660.1	660.1	660.1	660.1	660.1
2.5°	683.3	685.7	686.8	686.8	688.1	687.5	687.0
5°	722.6	726.9	727.9	732.0	735.0	734.1	734.5
7.5°	761.6	768.6	775.6	778.7	779.2	781.0	781.7
10°	785.7	791.4	802.1	800.6	808.6	813.2	805.7
12.5°	808.8	816.6	824.0	826.1	830.6	832.1	829.1
15°	829.7	833.8	834.2	833.1	834.6	833.3	829.0
17.5°	810.2	803.4	789.9	783.5	778.4	770.8	767.8
20°	777.9	758.1	735.2	726.0	715.3	694.2	699.2
22.5°	708.1	685.7	662.7	635.9	623.1	603.1	601.9
25°	599.7	560.9	518.2	488.4	470.9	451.0	442.2
27.5°	466.3	417.4	382.4	364.8	348.6	332.9	332.1
30°	378.5	341.8	314.8	299.6	289.7	283.1	284.5
32.5°	319.0	293.9	275.6	263.1	255.8	250.7	250.6
35°	260.8	243.6	231.9	226.6	221.4	217.7	217.9
37.5°	223.2	212.9	206.3	200.6	197.2	195.4	194.4
40°	203.9	195.4	190.4	186.9	184.2	181.7	181.2
42.5°	188.7	181.7	176.6	173.9	171.4	169.6	169.2
45°	167.4	161.7	157.1	154.1	153.0	151.4	151.4
47.5°	149.0	143.3	139.8	137.8	135.9	134.8	134.8
50°	136.5	132.1	129.0	127.7	126.1	125.5	125.2
52.5°	125.3	122.0	119.8	119.0	118.3	117.4	117.5
55°	110.1	108.3	107.3	106.6	105.5	104.1	105.0
57.5°	97.4	95.7	93.3	91.1	90.1	89.1	89.5
60°	88.4	85.1	81.9	79.4	78.7	76.6	76.6
62.5°	77.0	72.4	68.5	67.1	66.3	65.4	65.2
65°	59.2	57.4	56.5	55.5	55.0	55.0	54.6
67.5°	49.1	48.3	47.3	47.1	46.7	46.5	46.4
70°	43.3	42.4	42.0	41.7	41.3	41.5	40.8
72.5°	37.9	37.2	37.1	36.5	36.2	36.2	35.6
75°	29.8	29.8	29.6	29.4	28.9	28.7	28.9
77.5°	22.9	23.0	22.6	22.5	22.5	22.5	22.3
80°	18.4	18.6	18.4	18.1	17.9	18.1	17.9
82.5°	14.5	14.1	14.1	14.0	14.0	13.9	13.8
85°	8.3	8.5	8.3	8.1	8.1	8.1	8.3
87.5°	13.3	13.2	13.2	13.2	13.3	13.4	13.3
90°	51.3	50.6	50.4	50.8	51.1	51.4	51.8
92.5°	48.8	49.0	49.1	49.1	49.2	49.3	49.3
95°	97.5	97.5	97.0	96.4	95.7	95.0	94.4
97.5°	163.8	163.8	163.8	163.7	163.6	163.6	163.5
100°	210.1	210.1	210.0	209.5	209.2	208.9	208.5
102.5°	260.8	261.2	261.1	260.7	260.4	260.0	259.7
105°	337.0	337.6	338.0	338.0	338.0	338.0	338.0
107.5°	418.3	418.5	417.9	416.4	414.8	413.2	411.6
110°	473.5	473.5	472.9	471.9	470.9	469.9	468.9



TEST NUMBER: P331782-840

CATALOG NUMBER: S122RDIW-S290D1440U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	528.3	527.5	526.6	525.9	525.2	524.4	523.7
115°	614.0	613.7	613.0	612.0	611.0	610.0	608.9
117.5°	696.1	695.3	694.3	693.3	692.3	691.3	690.2
120°	752.0	752.0	751.5	750.5	749.5	748.5	747.5
122.5°	808.1	807.3	806.5	805.8	805.1	804.3	803.5
125°	892.1	891.1	890.5	890.1	889.8	889.5	889.1
127.5°	973.7	972.5	971.4	970.3	969.2	968.2	967.0
130°	1030.2	1029.5	1028.4	1027.1	1025.8	1024.4	1023.1
132.5°	1083.8	1082.3	1081.0	1079.9	1078.8	1077.7	1076.6
135°	1165.2	1164.9	1164.2	1163.2	1162.2	1161.1	1160.1
137.5°	1242.1	1241.8	1241.0	1239.7	1238.3	1237.0	1235.6
140°	1294.0	1294.0	1293.4	1292.0	1290.7	1289.3	1288.0
142.5°	1341.2	1341.4	1340.9	1339.6	1338.2	1336.9	1335.4
145°	1412.3	1412.6	1412.1	1410.8	1409.5	1408.1	1406.7
147.5°	1475.0	1475.8	1475.5	1474.2	1472.9	1471.7	1470.4
150°	1514.8	1515.8	1515.8	1514.8	1513.8	1512.8	1511.8
152.5°	1554.6	1555.9	1555.9	1554.6	1553.3	1552.1	1550.7
155°	1605.2	1606.8	1607.2	1606.2	1605.2	1604.2	1603.2
157.5°	1652.0	1654.4	1654.7	1653.0	1651.4	1649.8	1648.2
160°	1679.2	1681.2	1681.6	1680.2	1678.9	1677.6	1676.2
162.5°	1704.5	1706.7	1707.1	1705.5	1703.8	1702.2	1700.5
165°	1736.6	1739.0	1739.3	1737.6	1736.0	1734.2	1732.5
167.5°	1763.1	1765.4	1765.7	1764.0	1762.2	1760.5	1758.7
170°	1777.7	1780.1	1780.2	1778.2	1776.2	1774.1	1772.1
172.5°	1788.7	1791.0	1791.2	1789.2	1787.2	1785.1	1783.1
175°	1800.5	1802.9	1803.1	1801.0	1799.0	1797.0	1794.9
177.5°	1805.3	1807.0	1807.0	1805.3	1803.7	1802.0	1800.4
180°	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1	1804.1

(END OF REPORT)