

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331769-840

Luminaire Tested: **S122RDIW-S290D710U840-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331769-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S290D710U840-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 710 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4006.5 lumens
Efficiency: N/A
Efficacy: 131.8 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 30.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331769-840

CATALOG NUMBER: S122RDIW-S290D710U840-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331769-840

CATALOG NUMBER: S122RDIW-S290D710U840-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36	29
1	93	89	86	83	84	80	77	75	63	61	59	47	46	45	33	32	32	25
2	85	79	73	68	76	71	66	62	56	53	50	42	40	38	29	28	27	22
3	78	69	63	57	70	63	57	52	50	46	42	38	35	33	26	25	24	19
4	72	62	54	49	64	56	49	45	44	40	36	34	31	29	24	22	21	17
5	66	55	48	42	59	50	43	38	40	35	32	31	27	25	22	20	18	15
6	61	49	42	36	54	45	38	34	36	31	28	28	25	22	20	18	17	13
7	56	45	37	32	50	41	34	30	33	28	25	25	22	20	18	16	15	12
8	52	41	33	28	47	37	31	26	30	25	22	23	20	18	17	15	13	11
9	49	37	30	25	44	34	28	23	27	23	20	21	18	16	16	14	12	10
10	45	34	27	23	41	31	25	21	25	21	18	20	17	14	15	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10658	10658	10658	10658
5°	11904	10726	9511	10726
10°	13209	10650	8243	10650
15°	13857	10494	6496	10494
20°	12014	10263	5620	10263
25°	7878	9948	5018	9948
30°	5304	9562	4542	9562
35°	4295	9079	4096	9079
40°	3819	8553	3792	8553
45°	3457	7935	3382	7935
50°	3145	7322	3135	7322
55°	2956	6643	2919	6643
60°	2474	6022	2444	6022
65°	2086	5467	2365	5467
70°	1926	4881	2233	4881
75°	1803	4255	2059	4255
80°	1664	3505	1832	3505
85°	1538	2760	1612	2760



TEST NUMBER: P331769-840

CATALOG NUMBER: S122RDIW-S290D710U840-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	62.6	1.6
10°-20°	174.4	4.4
20°-30°	224.7	5.6
30°-40°	213.5	5.3
40°-50°	182.9	4.6
50°-60°	139.3	3.5
60°-70°	88.1	2.2
70°-80°	44.0	1.1
80°-90°	13.9	0.3
90°-100°	32.6	0.8
100°-110°	119.5	3.0
110°-120°	319.5	8.0
120°-130°	527.3	13.2
130°-140°	560.8	14.0
140°-150°	521.3	13.0
150°-160°	419.1	10.5
160°-170°	270.1	6.7
170°-180°	93.0	2.3
0°-30°	461.7	11.5
0°-40°	675.2	16.9
0°-60°	997.5	24.9
0°-90°	1143.4	28.5
90°-120°	471.6	11.8
90°-150°	2081.0	51.9
90°-180°	2863.0	71.5
0°-180°	4006.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	660	660	660	660	660	
5°	734	662	587	662	734	72
15°	829	628	389	628	829	224
25°	442	558	282	558	442	210
35°	218	461	208	461	218	139
45°	151	348	148	348	151	117
55°	105	236	104	236	105	92
65°	55	143	62	143	55	56
75°	29	68	33	68	29	31
85°	8	15	9	15	8	9
90°	19	1	19	1	19	9
95°	30	46	30	46	30	28
105°	54	215	54	215	54	56
115°	58	406	58	406	58	145
125°	604	575	604	575	604	523
135°	735	711	735	711	735	566
145°	838	825	838	825	838	524
155°	909	908	909	908	909	419
165°	955	957	955	957	955	270
175°	974	979	974	979	974	93
180°	977	977	977	977	977	



TEST NUMBER: P331769-840

CATALOG NUMBER: S122RDIW-S290D710U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1
2.5°	687.0	687.5	688.1	686.8	686.8	685.7	683.3	681.5	676.3	675.6	675.6
5°	734.5	734.1	735.0	732.0	727.9	726.9	722.6	716.8	710.8	704.3	702.9
7.5°	781.7	781.0	779.2	778.7	775.6	768.6	761.6	754.2	744.3	734.6	729.7
10°	805.7	813.2	808.6	800.6	802.1	791.4	785.7	775.8	767.5	753.1	749.9
12.5°	829.1	832.1	830.6	826.1	824.0	816.6	808.8	800.2	785.0	772.0	760.7
15°	829.0	833.3	834.6	833.1	834.2	833.8	829.7	822.6	809.3	795.1	782.6
17.5°	767.8	770.8	778.4	783.5	789.9	803.4	810.2	812.7	810.8	802.6	794.0
20°	699.2	694.2	715.3	726.0	735.2	758.1	777.9	785.5	797.6	797.4	795.1
22.5°	601.9	603.1	623.1	635.9	662.7	685.7	708.1	736.6	760.1	775.7	784.8
25°	442.2	451.0	470.9	488.4	518.2	560.9	599.7	644.6	687.0	720.5	752.5
27.5°	332.1	332.9	348.6	364.8	382.4	417.4	466.3	519.9	580.4	630.4	687.7
30°	284.5	283.1	289.7	299.6	314.8	341.8	378.5	431.2	491.6	566.8	633.8
32.5°	250.6	250.7	255.8	263.1	275.6	293.9	319.0	361.9	418.9	492.9	571.4
35°	217.9	217.7	221.4	226.6	231.9	243.6	260.8	283.3	322.6	391.5	471.8
37.5°	194.4	195.4	197.2	200.6	206.3	212.9	223.2	238.3	266.2	307.1	374.6
40°	181.2	181.7	184.2	186.9	190.4	195.4	203.9	216.1	236.5	269.0	318.4
42.5°	169.2	169.6	171.4	173.9	176.6	181.7	188.7	199.2	215.8	241.2	281.9
45°	151.4	151.4	153.0	154.1	157.1	161.7	167.4	176.2	187.6	206.4	233.5
47.5°	134.8	134.8	135.9	137.8	139.8	143.3	149.0	156.1	164.4	178.9	202.1
50°	125.2	125.5	126.1	127.7	129.0	132.1	136.5	142.7	151.4	162.7	181.9
52.5°	117.5	117.4	118.3	119.0	119.8	122.0	125.3	130.8	138.6	148.3	164.3
55°	105.0	104.1	105.5	106.6	107.3	108.3	110.1	113.5	120.2	128.5	140.4
57.5°	89.5	89.1	90.1	91.1	93.3	95.7	97.4	99.5	102.9	108.9	120.7
60°	76.6	76.6	78.7	79.4	81.9	85.1	88.4	90.2	93.6	97.5	106.2
62.5°	65.2	65.4	66.3	67.1	68.5	72.4	77.0	81.0	84.2	88.0	93.7
65°	54.6	55.0	55.0	55.5	56.5	57.4	59.2	62.4	68.2	73.4	77.8
67.5°	46.4	46.5	46.7	47.1	47.3	48.3	49.1	50.5	51.8	56.8	62.2
70°	40.8	41.5	41.3	41.7	42.0	42.4	43.3	44.0	46.2	47.3	50.5
72.5°	35.6	36.2	36.2	36.5	37.1	37.2	37.9	38.6	39.9	40.8	42.6
75°	28.9	28.7	28.9	29.4	29.6	29.8	29.8	30.7	31.4	32.3	33.5
77.5°	22.3	22.5	22.5	22.5	22.6	23.0	22.9	23.3	24.0	24.5	25.0
80°	17.9	18.1	17.9	18.1	18.4	18.6	18.4	18.6	19.3	19.7	19.7
82.5°	13.8	13.9	14.0	14.0	14.1	14.1	14.5	14.5	15.0	14.9	15.1
85°	8.3	8.1	8.1	8.1	8.3	8.5	8.3	8.3	8.5	8.5	8.5
87.5°	6.8	6.9	6.8	6.8	6.7	6.6	6.5	6.5	6.1	6.2	5.7
90°	19.1	18.8	18.5	18.2	17.9	17.3	16.5	15.8	14.9	14.1	12.9
92.5°	19.1	18.9	18.7	18.5	18.4	18.1	17.7	17.3	16.8	16.4	15.8
95°	30.4	30.6	30.7	30.9	31.0	30.7	29.9	29.2	28.4	27.6	26.5
97.5°	40.6	40.4	40.2	40.0	39.8	39.4	38.8	38.2	37.6	36.9	34.3
100°	47.4	47.1	46.8	46.5	46.2	45.3	44.0	42.8	41.5	40.3	37.7
102.5°	50.8	50.3	49.9	49.5	49.0	48.0	46.4	44.7	43.0	41.4	37.7
105°	53.7	53.1	52.5	51.8	51.2	50.0	48.3	46.6	44.8	43.1	37.7
107.5°	55.2	54.6	54.0	53.4	52.8	53.3	55.1	56.9	58.6	60.4	111.8
110°	55.8	55.2	54.6	53.9	53.3	60.9	76.5	92.3	108.1	123.7	169.2



TEST NUMBER: P331769-840

CATALOG NUMBER: S122RDIW-S290D710U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	56.5	55.9	55.4	54.9	54.4	82.8	140.2	197.4	254.8	312.0	323.3
115°	58.0	69.3	80.6	91.9	103.2	145.2	217.9	290.7	363.5	436.2	432.2
117.5°	236.7	273.9	311.0	348.2	385.4	412.7	430.3	448.0	465.5	483.1	480.4
120°	431.2	452.4	473.6	494.8	516.0	525.7	523.8	522.0	520.1	518.2	515.3
122.5°	538.2	542.3	546.3	550.5	554.6	556.1	554.9	553.8	552.7	551.6	548.5
125°	604.4	604.0	603.5	603.0	602.6	601.8	600.7	599.6	598.4	597.3	594.4
127.5°	646.3	646.2	646.1	646.0	645.9	645.1	643.5	641.9	640.3	638.6	636.4
130°	672.4	672.5	672.7	672.8	673.0	672.2	670.4	668.7	667.0	665.3	663.5
132.5°	697.8	697.9	698.1	698.2	698.4	697.7	696.3	694.8	693.3	691.9	690.1
135°	734.6	734.9	735.2	735.5	735.8	735.2	733.6	732.1	730.4	728.9	727.5
137.5°	768.0	768.6	769.1	769.6	770.2	769.7	768.1	766.6	765.1	763.6	761.9
140°	789.0	789.7	790.5	791.3	792.1	791.8	790.4	789.0	787.6	786.2	784.4
142.5°	809.3	810.1	810.9	811.7	812.4	812.2	810.9	809.6	808.4	807.1	805.1
145°	837.8	838.5	839.3	840.1	840.9	840.7	839.6	838.5	837.5	836.4	833.6
147.5°	862.7	863.4	864.1	864.7	865.5	865.4	864.5	863.7	862.9	862.0	859.4
150°	878.1	878.8	879.6	880.4	881.2	881.1	880.2	879.2	878.3	877.4	874.8
152.5°	891.0	892.1	893.1	894.1	895.2	895.2	894.3	893.3	892.4	891.5	889.1
155°	909.2	910.4	911.7	912.9	914.1	914.3	913.4	912.4	911.5	910.6	908.7
157.5°	925.6	927.0	928.2	929.4	930.6	930.7	929.6	928.6	927.5	926.3	925.0
160°	935.3	936.4	937.5	938.6	939.7	939.8	938.9	937.9	937.0	936.0	935.0
162.5°	943.2	944.5	945.9	947.3	948.7	948.8	947.7	946.6	945.5	944.5	943.7
165°	955.1	956.2	957.4	958.4	959.5	959.5	958.4	957.4	956.2	955.1	954.6
167.5°	962.6	964.0	965.4	966.8	968.3	968.4	967.3	966.2	965.1	964.0	963.6
170°	967.1	968.6	970.0	971.4	972.8	972.9	971.8	970.8	969.7	968.6	968.3
172.5°	970.5	971.9	973.3	974.7	976.1	976.3	975.2	974.1	973.0	971.9	971.6
175°	973.5	975.0	976.6	978.2	979.8	980.0	978.9	977.9	976.7	975.6	975.3
177.5°	975.3	976.4	977.5	978.8	979.9	980.0	979.1	978.3	977.3	976.4	976.3
180°	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0



TEST NUMBER: P331769-840

CATALOG NUMBER: S122RDIW-S290D710U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1
2.5°	676.0	674.5	673.2	669.9	668.2	664.6	664.1	663.9	659.1	654.5	653.2
5°	699.2	695.5	690.0	683.6	676.9	670.0	665.5	661.8	652.6	643.9	638.8
7.5°	722.6	714.7	705.2	693.1	682.9	671.6	663.1	655.5	642.5	630.0	621.6
10°	740.0	727.2	714.6	697.8	684.7	671.9	659.9	649.6	635.0	618.4	606.7
12.5°	750.8	736.7	719.3	703.0	686.0	669.6	653.7	640.5	623.2	606.1	592.3
15°	765.5	750.3	729.2	705.8	684.1	662.7	644.4	627.8	605.4	584.9	567.9
17.5°	777.5	756.6	734.0	706.9	681.7	654.6	631.0	609.9	584.8	560.2	540.2
20°	781.3	760.6	734.5	707.4	677.6	645.7	620.3	597.3	570.5	543.6	520.7
22.5°	778.9	762.9	733.8	701.4	670.9	637.5	608.7	582.1	552.3	524.9	498.4
25°	762.8	757.2	729.7	694.4	659.5	620.8	587.4	558.4	524.4	495.0	466.2
27.5°	725.0	736.9	719.8	682.2	643.4	601.9	564.4	531.3	496.0	463.0	434.2
30°	688.6	715.9	708.6	673.7	630.4	589.6	547.5	512.9	475.3	441.3	412.9
32.5°	638.9	684.0	691.2	662.0	617.1	572.3	528.3	493.8	454.5	418.8	391.0
35°	559.7	627.1	658.1	639.5	594.6	546.1	500.8	460.6	421.1	385.9	358.3
37.5°	465.2	557.1	608.7	610.1	568.8	518.5	469.0	429.1	388.7	354.1	324.3
40°	403.9	503.5	570.8	585.6	550.8	496.4	446.4	405.8	366.4	332.3	298.2
42.5°	348.9	448.1	530.7	556.6	529.0	474.9	424.7	382.3	344.0	311.8	276.9
45°	282.2	368.9	459.9	506.2	490.9	440.9	387.9	347.5	311.5	283.8	250.2
47.5°	238.0	299.1	387.3	449.9	449.7	404.0	351.8	313.3	279.8	253.8	226.7
50°	212.9	266.1	340.6	411.7	417.7	379.4	329.8	291.5	260.3	233.1	211.3
52.5°	190.3	234.2	301.1	369.4	386.4	353.1	305.1	269.7	239.4	214.3	195.7
55°	160.8	194.8	245.7	309.4	335.2	311.7	269.0	236.0	211.5	190.4	174.3
57.5°	136.0	161.5	202.4	253.7	283.6	268.9	233.7	206.8	185.8	166.7	154.1
60°	120.5	141.3	175.9	218.8	251.9	241.6	211.5	186.5	168.6	152.1	140.2
62.5°	105.7	123.7	153.4	188.2	218.4	214.2	189.7	168.6	153.0	137.9	127.8
65°	85.1	98.2	121.4	148.7	173.0	175.0	157.3	143.1	129.2	117.2	108.3
67.5°	67.8	76.3	92.6	115.6	133.8	140.4	129.6	118.7	107.6	98.4	90.6
70°	57.2	64.0	75.9	94.5	111.3	118.2	111.9	103.4	93.8	86.2	79.6
72.5°	46.3	53.0	61.8	75.4	89.8	97.3	95.0	89.0	81.2	74.8	68.6
75°	34.8	37.0	42.9	52.1	63.3	69.8	71.3	68.2	61.9	57.2	53.4
77.5°	25.8	27.1	29.9	34.6	42.0	47.8	50.1	49.7	45.4	42.7	39.2
80°	20.6	21.3	22.7	24.7	30.3	36.1	37.7	37.7	34.6	33.5	30.1
82.5°	15.7	16.2	17.1	18.2	20.7	25.8	27.6	27.9	26.1	24.5	21.8
85°	9.0	8.7	9.2	9.9	10.3	11.7	14.4	14.9	14.4	12.6	11.9
87.5°	5.5	5.4	5.2	4.6	4.4	4.3	4.8	5.5	5.0	4.8	4.8
90°	11.6	10.4	9.1	7.6	5.9	4.1	2.4	0.7	2.4	4.1	5.9
92.5°	15.1	14.5	13.9	13.6	13.8	13.9	14.1	14.2	14.1	13.9	13.8
95°	25.3	24.2	23.1	25.2	30.4	35.5	40.8	45.9	40.8	35.5	30.4
97.5°	31.8	29.3	26.8	32.7	47.4	62.0	76.5	91.2	76.5	62.0	47.4
100°	34.9	32.3	29.6	39.1	60.6	82.1	103.6	125.1	103.6	82.1	60.6
102.5°	86.1	108.5	130.8	144.2	148.8	153.3	157.9	162.5	157.9	153.3	148.8
105°	128.9	171.8	214.7	233.8	229.0	224.4	219.6	214.9	219.6	224.4	229.0
107.5°	163.3	214.7	266.1	289.9	286.1	282.4	278.5	274.7	278.5	282.4	286.1
110°	214.5	259.9	305.3	326.4	323.1	319.8	316.5	313.2	316.5	319.8	323.1



TEST NUMBER: P331769-840

CATALOG NUMBER: S122RDIW-S290D710U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	334.5	345.7	356.9	361.0	358.1	355.3	352.3	349.4	352.3	355.3	358.1
115°	428.4	424.4	420.5	417.2	414.5	411.8	409.2	406.5	409.2	411.8	414.5
117.5°	477.8	475.0	472.3	469.5	466.5	463.5	460.5	457.6	460.5	463.5	466.5
120°	512.5	509.7	506.9	504.3	501.9	499.6	497.3	494.8	497.3	499.6	501.9
122.5°	545.4	542.3	539.3	536.4	534.0	531.5	529.1	526.5	529.1	531.5	534.0
125°	591.4	588.4	585.4	582.9	580.9	578.9	576.8	574.7	576.8	578.9	580.9
127.5°	634.2	632.0	629.8	627.5	625.2	623.0	620.7	618.4	620.7	623.0	625.2
130°	661.8	660.0	658.3	656.2	653.7	651.2	648.6	646.1	648.6	651.2	653.7
132.5°	688.3	686.6	684.9	683.0	680.9	678.7	676.6	674.5	676.6	678.7	680.9
135°	726.1	724.7	723.3	721.2	718.7	716.2	713.7	711.2	713.7	716.2	718.7
137.5°	760.3	758.7	757.1	755.4	753.7	751.9	750.1	748.4	750.1	751.9	753.7
140°	782.6	780.9	779.2	777.7	776.5	775.2	774.0	772.7	774.0	775.2	776.5
142.5°	803.1	801.1	799.1	797.6	796.5	795.4	794.2	793.0	794.2	795.4	796.5
145°	831.0	828.3	825.7	824.4	824.6	824.8	824.9	825.1	824.9	824.8	824.6
147.5°	856.8	854.1	851.5	850.5	851.1	851.7	852.3	852.8	852.3	851.7	851.1
150°	872.3	869.8	867.3	866.6	867.7	868.8	869.9	871.0	869.9	868.8	867.7
152.5°	886.7	884.3	881.9	881.3	882.5	883.8	885.0	886.3	885.0	883.8	882.5
155°	906.8	904.9	903.0	902.8	904.2	905.6	907.1	908.5	907.1	905.6	904.2
157.5°	923.7	922.4	921.1	921.1	922.2	923.4	924.6	925.8	924.6	923.4	922.2
160°	934.1	933.2	932.2	932.2	933.2	934.1	935.0	936.0	935.0	934.1	933.2
162.5°	942.9	942.0	941.2	941.3	942.2	943.2	944.1	945.0	944.1	943.2	942.2
165°	954.1	953.7	953.2	953.4	954.4	955.3	956.2	957.3	956.2	955.3	954.4
167.5°	963.1	962.7	962.3	962.5	963.4	964.4	965.3	966.2	965.3	964.4	963.4
170°	968.0	967.6	967.2	967.6	968.6	969.5	970.4	971.4	970.4	969.5	968.6
172.5°	971.3	971.0	970.7	971.0	971.9	972.9	973.8	974.7	973.8	972.9	971.9
175°	975.0	974.6	974.3	974.7	975.8	976.9	978.1	979.2	978.1	976.9	975.8
177.5°	976.2	976.0	975.9	976.3	977.2	978.1	979.0	979.9	979.0	978.1	977.2
180°	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0



TEST NUMBER: P331769-840

CATALOG NUMBER: S122RDIW-S290D710U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1
2.5°	650.9	649.5	647.1	643.5	641.3	637.4	634.9	636.3	636.7	636.3	636.0
5°	633.4	628.5	621.9	615.4	609.5	603.1	599.4	597.8	594.6	592.8	591.8
7.5°	612.2	603.9	594.5	583.3	573.8	563.8	558.8	556.2	549.7	546.1	543.0
10°	596.4	583.3	573.9	559.3	550.3	537.2	528.3	528.6	519.6	514.5	510.9
12.5°	579.0	564.6	549.0	535.7	523.3	512.8	502.0	497.7	488.2	483.3	473.4
15°	550.1	533.3	516.8	499.0	486.4	470.0	454.4	435.4	420.0	406.7	403.0
17.5°	518.6	497.8	481.2	460.2	438.6	411.2	393.1	382.0	372.8	365.8	360.5
20°	496.9	475.7	458.1	426.5	397.3	378.7	365.5	356.9	347.3	339.7	335.6
22.5°	474.1	452.1	428.0	392.6	369.9	355.1	343.3	333.5	326.9	321.0	317.2
25°	441.8	417.7	378.0	353.8	335.4	319.7	311.5	305.6	298.7	290.6	287.0
27.5°	407.7	369.4	340.8	322.8	305.3	295.2	287.7	278.8	272.7	269.0	265.2
30°	382.1	343.9	321.6	301.8	289.5	278.2	269.5	264.5	258.5	252.4	249.8
32.5°	353.8	323.2	301.7	285.4	272.8	263.2	256.3	248.1	243.9	240.0	234.8
35°	318.4	295.2	275.7	262.5	250.4	242.7	234.7	229.8	222.1	218.8	216.8
37.5°	288.5	268.4	253.9	239.8	230.4	221.8	216.8	209.1	205.8	201.3	196.9
40°	271.6	251.9	237.9	226.4	215.8	209.4	203.3	197.0	192.0	190.0	184.7
42.5°	254.4	238.3	224.3	211.8	204.7	197.8	190.1	185.5	180.3	176.9	173.7
45°	230.6	216.3	204.4	194.1	186.2	179.2	174.1	166.5	163.6	156.9	154.1
47.5°	209.6	196.4	185.0	175.2	167.6	163.0	155.6	149.7	144.9	140.8	137.2
50°	194.8	183.7	172.7	164.0	157.1	150.5	142.9	140.0	132.6	130.5	128.5
52.5°	181.2	170.7	160.7	152.1	145.2	138.8	132.1	128.2	123.2	121.2	119.7
55°	162.2	152.1	142.5	134.9	128.1	121.4	117.2	112.4	110.1	108.5	106.6
57.5°	143.1	134.0	126.6	119.0	112.0	106.7	102.0	99.1	96.7	94.6	92.4
60°	131.0	122.3	115.6	108.5	101.4	97.0	93.4	89.9	87.2	83.9	83.0
62.5°	118.2	110.5	104.4	97.5	91.3	87.4	83.8	80.6	77.3	72.6	71.3
65°	100.5	94.5	88.1	82.3	76.9	72.9	67.9	64.2	62.8	62.4	62.2
67.5°	84.5	78.9	73.3	67.5	62.5	58.9	56.2	55.7	54.7	54.5	53.8
70°	73.8	68.6	63.1	57.6	52.7	52.1	51.2	50.2	49.1	48.7	48.2
72.5°	64.3	58.9	53.3	49.0	46.9	46.0	45.1	44.1	43.4	42.9	42.7
75°	49.3	44.2	40.6	39.0	37.9	37.2	35.7	35.1	34.6	33.9	33.7
77.5°	35.5	32.6	31.0	30.0	28.8	28.1	27.3	26.6	26.1	26.0	25.5
80°	27.1	25.7	24.5	23.1	22.7	21.8	21.6	20.9	21.1	20.4	20.4
82.5°	21.0	19.3	18.3	17.7	17.2	16.5	16.3	16.0	16.0	15.5	15.5
85°	10.8	10.3	9.9	9.4	9.4	8.7	9.0	8.7	8.7	8.3	8.1
87.5°	5.0	5.2	5.0	5.3	5.6	5.6	5.8	5.8	5.9	6.1	6.0
90°	7.6	9.1	10.4	11.6	12.9	14.1	14.9	15.8	16.5	17.3	17.9
92.5°	13.6	13.9	14.5	15.1	15.8	16.4	16.8	17.3	17.7	18.1	18.4
95°	25.2	23.1	24.2	25.3	26.5	27.6	28.4	29.2	29.9	30.7	31.0
97.5°	32.7	26.8	29.3	31.8	34.3	36.9	37.6	38.2	38.8	39.4	39.8
100°	39.1	29.6	32.3	34.9	37.7	40.3	41.5	42.8	44.0	45.3	46.2
102.5°	144.2	130.8	108.5	86.1	63.7	41.4	43.0	44.7	46.4	48.0	49.0
105°	233.8	214.7	171.8	128.9	86.0	43.1	44.8	46.6	48.3	50.0	51.2
107.5°	289.9	266.1	214.7	163.3	111.8	60.4	58.6	56.9	55.1	53.3	52.8
110°	326.4	305.3	259.9	214.5	169.2	123.7	108.1	92.3	76.5	60.9	53.3



TEST NUMBER: P331769-840

CATALOG NUMBER: S122RDIW-S290D710U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	361.0	356.9	345.7	334.5	323.3	312.0	254.8	197.4	140.2	82.8	54.4
115°	417.2	420.5	424.4	428.4	432.2	436.2	363.5	290.7	217.9	145.2	103.2
117.5°	469.5	472.3	475.0	477.8	480.4	483.1	465.5	448.0	430.3	412.7	385.4
120°	504.3	506.9	509.7	512.5	515.3	518.2	520.1	522.0	523.8	525.7	516.0
122.5°	536.4	539.3	542.3	545.4	548.5	551.6	552.7	553.8	554.9	556.1	554.6
125°	582.9	585.4	588.4	591.4	594.4	597.3	598.4	599.6	600.7	601.8	602.6
127.5°	627.5	629.8	632.0	634.2	636.4	638.6	640.3	641.9	643.5	645.1	645.9
130°	656.2	658.3	660.0	661.8	663.5	665.3	667.0	668.7	670.4	672.2	673.0
132.5°	683.0	684.9	686.6	688.3	690.1	691.9	693.3	694.8	696.3	697.7	698.4
135°	721.2	723.3	724.7	726.1	727.5	728.9	730.4	732.1	733.6	735.2	735.8
137.5°	755.4	757.1	758.7	760.3	761.9	763.6	765.1	766.6	768.1	769.7	770.2
140°	777.7	779.2	780.9	782.6	784.4	786.2	787.6	789.0	790.4	791.8	792.1
142.5°	797.6	799.1	801.1	803.1	805.1	807.1	808.4	809.6	810.9	812.2	812.4
145°	824.4	825.7	828.3	831.0	833.6	836.4	837.5	838.5	839.6	840.7	840.9
147.5°	850.5	851.5	854.1	856.8	859.4	862.0	862.9	863.7	864.5	865.4	865.5
150°	866.6	867.3	869.8	872.3	874.8	877.4	878.3	879.2	880.2	881.1	881.2
152.5°	881.3	881.9	884.3	886.7	889.1	891.5	892.4	893.3	894.3	895.2	895.2
155°	902.8	903.0	904.9	906.8	908.7	910.6	911.5	912.4	913.4	914.3	914.1
157.5°	921.1	921.1	922.4	923.7	925.0	926.3	927.5	928.6	929.6	930.7	930.6
160°	932.2	932.2	933.2	934.1	935.0	936.0	937.0	937.9	938.9	939.8	939.7
162.5°	941.3	941.2	942.0	942.9	943.7	944.5	945.5	946.6	947.7	948.8	948.7
165°	953.4	953.2	953.7	954.1	954.6	955.1	956.2	957.4	958.4	959.5	959.5
167.5°	962.5	962.3	962.7	963.1	963.6	964.0	965.1	966.2	967.3	968.4	968.3
170°	967.6	967.2	967.6	968.0	968.3	968.6	969.7	970.8	971.8	972.9	972.8
172.5°	971.0	970.7	971.0	971.3	971.6	971.9	973.0	974.1	975.2	976.3	976.1
175°	974.7	974.3	974.6	975.0	975.3	975.6	976.7	977.9	978.9	980.0	979.8
177.5°	976.3	975.9	976.0	976.2	976.3	976.4	977.3	978.3	979.1	980.0	979.9
180°	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0



TEST NUMBER: P331769-840

CATALOG NUMBER: S122RDIW-S290D710U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1
2.5°	634.0	634.3	633.8	634.1	633.8	634.3	634.0	636.0	636.3	636.7	636.3
5°	590.7	587.9	587.4	586.8	587.4	587.9	590.7	591.8	592.8	594.6	597.8
7.5°	539.1	538.7	537.5	535.8	537.5	538.7	539.1	543.0	546.1	549.7	556.2
10°	505.8	504.6	504.4	502.8	504.4	504.6	505.8	510.9	514.5	519.6	528.6
12.5°	466.9	459.5	458.8	454.7	458.8	459.5	466.9	473.4	483.3	488.2	497.7
15°	397.6	396.2	391.5	388.6	391.5	396.2	397.6	403.0	406.7	420.0	435.4
17.5°	357.9	353.4	351.9	351.3	351.9	353.4	357.9	360.5	365.8	372.8	382.0
20°	332.3	328.3	327.6	327.1	327.6	328.3	332.3	335.6	339.7	347.3	356.9
22.5°	314.8	310.4	308.7	307.3	308.7	310.4	314.8	317.2	321.0	326.9	333.5
25°	284.7	283.1	282.2	281.7	282.2	283.1	284.7	287.0	290.6	298.7	305.6
27.5°	261.2	257.6	256.9	255.7	256.9	257.6	261.2	265.2	269.0	272.7	278.8
30°	247.7	246.6	245.0	243.6	245.0	246.6	247.7	249.8	252.4	258.5	264.5
32.5°	232.0	231.0	229.5	228.9	229.5	231.0	232.0	234.8	240.0	243.9	248.1
35°	214.5	211.3	209.8	207.8	209.8	211.3	214.5	216.8	218.8	222.1	229.8
37.5°	196.0	194.3	192.4	193.1	192.4	194.3	196.0	196.9	201.3	205.8	209.1
40°	181.7	180.6	180.1	179.9	180.1	180.6	181.7	184.7	190.0	192.0	197.0
42.5°	170.3	167.1	165.9	165.9	165.9	167.1	170.3	173.7	176.9	180.3	185.5
45°	153.0	150.1	147.9	148.1	147.9	150.1	153.0	154.1	156.9	163.6	166.5
47.5°	135.3	135.2	133.9	134.3	133.9	135.2	135.3	137.2	140.8	144.9	149.7
50°	126.8	125.5	124.5	124.8	124.5	125.5	126.8	128.5	130.5	132.6	140.0
52.5°	118.8	117.5	116.8	117.9	116.8	117.5	118.8	119.7	121.2	123.2	128.2
55°	105.5	104.1	103.9	103.7	103.9	104.1	105.5	106.6	108.5	110.1	112.4
57.5°	90.7	89.8	88.4	87.9	88.4	89.8	90.7	92.4	94.6	96.7	99.1
60°	80.1	78.3	75.9	75.7	75.9	78.3	80.1	83.0	83.9	87.2	89.9
62.5°	70.3	70.0	69.5	69.5	69.5	70.0	70.3	71.3	72.6	77.3	80.6
65°	61.7	61.5	61.7	61.9	61.7	61.5	61.7	62.2	62.4	62.8	64.2
67.5°	53.7	53.3	52.9	53.1	52.9	53.3	53.7	53.8	54.5	54.7	55.7
70°	47.7	47.5	47.3	47.3	47.3	47.5	47.7	48.2	48.7	49.1	50.2
72.5°	41.8	41.8	41.6	41.4	41.6	41.8	41.8	42.7	42.9	43.4	44.1
75°	33.5	33.0	33.0	33.0	33.0	33.0	33.5	33.7	33.9	34.6	35.1
77.5°	25.5	25.2	25.0	24.8	25.0	25.2	25.5	25.5	26.0	26.1	26.6
80°	20.2	20.0	19.7	19.7	19.7	20.0	20.2	20.4	20.4	21.1	20.9
82.5°	15.5	15.1	15.1	14.9	15.1	15.1	15.5	15.5	15.5	16.0	16.0
85°	8.3	8.5	8.3	8.7	8.3	8.5	8.3	8.1	8.3	8.7	8.7
87.5°	6.1	5.9	6.2	6.1	6.2	5.9	6.1	6.0	6.1	5.9	5.8
90°	18.2	18.5	18.8	19.1	18.8	18.5	18.2	17.9	17.3	16.5	15.8
92.5°	18.5	18.7	18.9	19.1	18.9	18.7	18.5	18.4	18.1	17.7	17.3
95°	30.9	30.7	30.6	30.4	30.6	30.7	30.9	31.0	30.7	29.9	29.2
97.5°	40.0	40.2	40.4	40.6	40.4	40.2	40.0	39.8	39.4	38.8	38.2
100°	46.5	46.8	47.1	47.4	47.1	46.8	46.5	46.2	45.3	44.0	42.8
102.5°	49.5	49.9	50.3	50.8	50.3	49.9	49.5	49.0	48.0	46.4	44.7
105°	51.8	52.5	53.1	53.7	53.1	52.5	51.8	51.2	50.0	48.3	46.6
107.5°	53.4	54.0	54.6	55.2	54.6	54.0	53.4	52.8	53.3	55.1	56.9
110°	53.9	54.6	55.2	55.8	55.2	54.6	53.9	53.3	60.9	76.5	92.3



TEST NUMBER: P331769-840

CATALOG NUMBER: S122RDIW-S290D710U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	54.9	55.4	55.9	56.5	55.9	55.4	54.9	54.4	82.8	140.2	197.4
115°	91.9	80.6	69.3	58.0	69.3	80.6	91.9	103.2	145.2	217.9	290.7
117.5°	348.2	311.0	273.9	236.7	273.9	311.0	348.2	385.4	412.7	430.3	448.0
120°	494.8	473.6	452.4	431.2	452.4	473.6	494.8	516.0	525.7	523.8	522.0
122.5°	550.5	546.3	542.3	538.2	542.3	546.3	550.5	554.6	556.1	554.9	553.8
125°	603.0	603.5	604.0	604.4	604.0	603.5	603.0	602.6	601.8	600.7	599.6
127.5°	646.0	646.1	646.2	646.3	646.2	646.1	646.0	645.9	645.1	643.5	641.9
130°	672.8	672.7	672.5	672.4	672.5	672.7	672.8	673.0	672.2	670.4	668.7
132.5°	698.2	698.1	697.9	697.8	697.9	698.1	698.2	698.4	697.7	696.3	694.8
135°	735.5	735.2	734.9	734.6	734.9	735.2	735.5	735.8	735.2	733.6	732.1
137.5°	769.6	769.1	768.6	768.0	768.6	769.1	769.6	770.2	769.7	768.1	766.6
140°	791.3	790.5	789.7	789.0	789.7	790.5	791.3	792.1	791.8	790.4	789.0
142.5°	811.7	810.9	810.1	809.3	810.1	810.9	811.7	812.4	812.2	810.9	809.6
145°	840.1	839.3	838.5	837.8	838.5	839.3	840.1	840.9	840.7	839.6	838.5
147.5°	864.7	864.1	863.4	862.7	863.4	864.1	864.7	865.5	865.4	864.5	863.7
150°	880.4	879.6	878.8	878.1	878.8	879.6	880.4	881.2	881.1	880.2	879.2
152.5°	894.1	893.1	892.1	891.0	892.1	893.1	894.1	895.2	895.2	894.3	893.3
155°	912.9	911.7	910.4	909.2	910.4	911.7	912.9	914.1	914.3	913.4	912.4
157.5°	929.4	928.2	927.0	925.6	927.0	928.2	929.4	930.6	930.7	929.6	928.6
160°	938.6	937.5	936.4	935.3	936.4	937.5	938.6	939.7	939.8	938.9	937.9
162.5°	947.3	945.9	944.5	943.2	944.5	945.9	947.3	948.7	948.8	947.7	946.6
165°	958.4	957.4	956.2	955.1	956.2	957.4	958.4	959.5	959.5	958.4	957.4
167.5°	966.8	965.4	964.0	962.6	964.0	965.4	966.8	968.3	968.4	967.3	966.2
170°	971.4	970.0	968.6	967.1	968.6	970.0	971.4	972.8	972.9	971.8	970.8
172.5°	974.7	973.3	971.9	970.5	971.9	973.3	974.7	976.1	976.3	975.2	974.1
175°	978.2	976.6	975.0	973.5	975.0	976.6	978.2	979.8	980.0	978.9	977.9
177.5°	978.8	977.5	976.4	975.3	976.4	977.5	978.8	979.9	980.0	979.1	978.3
180°	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0



TEST NUMBER: P331769-840

CATALOG NUMBER: S122RDIW-S290D710U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1
2.5°	634.9	637.4	641.3	643.5	647.1	649.5	650.9	653.2	654.5	659.1	663.9
5°	599.4	603.1	609.5	615.4	621.9	628.5	633.4	638.8	643.9	652.6	661.8
7.5°	558.8	563.8	573.8	583.3	594.5	603.9	612.2	621.6	630.0	642.5	655.5
10°	528.3	537.2	550.3	559.3	573.9	583.3	596.4	606.7	618.4	635.0	649.6
12.5°	502.0	512.8	523.3	535.7	549.0	564.6	579.0	592.3	606.1	623.2	640.5
15°	454.4	470.0	486.4	499.0	516.8	533.3	550.1	567.9	584.9	605.4	627.8
17.5°	393.1	411.2	438.6	460.2	481.2	497.8	518.6	540.2	560.2	584.8	609.9
20°	365.5	378.7	397.3	426.5	458.1	475.7	496.9	520.7	543.6	570.5	597.3
22.5°	343.3	355.1	369.9	392.6	428.0	452.1	474.1	498.4	524.9	552.3	582.1
25°	311.5	319.7	335.4	353.8	378.0	417.7	441.8	466.2	495.0	524.4	558.4
27.5°	287.7	295.2	305.3	322.8	340.8	369.4	407.7	434.2	463.0	496.0	531.3
30°	269.5	278.2	289.5	301.8	321.6	343.9	382.1	412.9	441.3	475.3	512.9
32.5°	256.3	263.2	272.8	285.4	301.7	323.2	353.8	391.0	418.8	454.5	493.8
35°	234.7	242.7	250.4	262.5	275.7	295.2	318.4	358.3	385.9	421.1	460.6
37.5°	216.8	221.8	230.4	239.8	253.9	268.4	288.5	324.3	354.1	388.7	429.1
40°	203.3	209.4	215.8	226.4	237.9	251.9	271.6	298.2	332.3	366.4	405.8
42.5°	190.1	197.8	204.7	211.8	224.3	238.3	254.4	276.9	311.8	344.0	382.3
45°	174.1	179.2	186.2	194.1	204.4	216.3	230.6	250.2	283.8	311.5	347.5
47.5°	155.6	163.0	167.6	175.2	185.0	196.4	209.6	226.7	253.8	279.8	313.3
50°	142.9	150.5	157.1	164.0	172.7	183.7	194.8	211.3	233.1	260.3	291.5
52.5°	132.1	138.8	145.2	152.1	160.7	170.7	181.2	195.7	214.3	239.4	269.7
55°	117.2	121.4	128.1	134.9	142.5	152.1	162.2	174.3	190.4	211.5	236.0
57.5°	102.0	106.7	112.0	119.0	126.6	134.0	143.1	154.1	166.7	185.8	206.8
60°	93.4	97.0	101.4	108.5	115.6	122.3	131.0	140.2	152.1	168.6	186.5
62.5°	83.8	87.4	91.3	97.5	104.4	110.5	118.2	127.8	137.9	153.0	168.6
65°	67.9	72.9	76.9	82.3	88.1	94.5	100.5	108.3	117.2	129.2	143.1
67.5°	56.2	58.9	62.5	67.5	73.3	78.9	84.5	90.6	98.4	107.6	118.7
70°	51.2	52.1	52.7	57.6	63.1	68.6	73.8	79.6	86.2	93.8	103.4
72.5°	45.1	46.0	46.9	49.0	53.3	58.9	64.3	68.6	74.8	81.2	89.0
75°	35.7	37.2	37.9	39.0	40.6	44.2	49.3	53.4	57.2	61.9	68.2
77.5°	27.3	28.1	28.8	30.0	31.0	32.6	35.5	39.2	42.7	45.4	49.7
80°	21.6	21.8	22.7	23.1	24.5	25.7	27.1	30.1	33.5	34.6	37.7
82.5°	16.3	16.5	17.2	17.7	18.3	19.3	21.0	21.8	24.5	26.1	27.9
85°	9.0	8.7	9.4	9.4	9.9	10.3	10.8	11.9	12.6	14.4	14.9
87.5°	5.8	5.6	5.6	5.3	5.0	5.2	5.0	4.8	4.8	5.0	5.5
90°	14.9	14.1	12.9	11.6	10.4	9.1	7.6	5.9	4.1	2.4	0.7
92.5°	16.8	16.4	15.8	15.1	14.5	13.9	13.6	13.8	13.9	14.1	14.2
95°	28.4	27.6	26.5	25.3	24.2	23.1	25.2	30.4	35.5	40.8	45.9
97.5°	37.6	36.9	34.3	31.8	29.3	26.8	32.7	47.4	62.0	76.5	91.2
100°	41.5	40.3	37.7	34.9	32.3	29.6	39.1	60.6	82.1	103.6	125.1
102.5°	43.0	41.4	63.7	86.1	108.5	130.8	144.2	148.8	153.3	157.9	162.5
105°	44.8	43.1	86.0	128.9	171.8	214.7	233.8	229.0	224.4	219.6	214.9
107.5°	58.6	60.4	111.8	163.3	214.7	266.1	289.9	286.1	282.4	278.5	274.7
110°	108.1	123.7	169.2	214.5	259.9	305.3	326.4	323.1	319.8	316.5	313.2



TEST NUMBER: P331769-840

CATALOG NUMBER: S122RDIW-S290D710U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	254.8	312.0	323.3	334.5	345.7	356.9	361.0	358.1	355.3	352.3	349.4
115°	363.5	436.2	432.2	428.4	424.4	420.5	417.2	414.5	411.8	409.2	406.5
117.5°	465.5	483.1	480.4	477.8	475.0	472.3	469.5	466.5	463.5	460.5	457.6
120°	520.1	518.2	515.3	512.5	509.7	506.9	504.3	501.9	499.6	497.3	494.8
122.5°	552.7	551.6	548.5	545.4	542.3	539.3	536.4	534.0	531.5	529.1	526.5
125°	598.4	597.3	594.4	591.4	588.4	585.4	582.9	580.9	578.9	576.8	574.7
127.5°	640.3	638.6	636.4	634.2	632.0	629.8	627.5	625.2	623.0	620.7	618.4
130°	667.0	665.3	663.5	661.8	660.0	658.3	656.2	653.7	651.2	648.6	646.1
132.5°	693.3	691.9	690.1	688.3	686.6	684.9	683.0	680.9	678.7	676.6	674.5
135°	730.4	728.9	727.5	726.1	724.7	723.3	721.2	718.7	716.2	713.7	711.2
137.5°	765.1	763.6	761.9	760.3	758.7	757.1	755.4	753.7	751.9	750.1	748.4
140°	787.6	786.2	784.4	782.6	780.9	779.2	777.7	776.5	775.2	774.0	772.7
142.5°	808.4	807.1	805.1	803.1	801.1	799.1	797.6	796.5	795.4	794.2	793.0
145°	837.5	836.4	833.6	831.0	828.3	825.7	824.4	824.6	824.8	824.9	825.1
147.5°	862.9	862.0	859.4	856.8	854.1	851.5	850.5	851.1	851.7	852.3	852.8
150°	878.3	877.4	874.8	872.3	869.8	867.3	866.6	867.7	868.8	869.9	871.0
152.5°	892.4	891.5	889.1	886.7	884.3	881.9	881.3	882.5	883.8	885.0	886.3
155°	911.5	910.6	908.7	906.8	904.9	903.0	902.8	904.2	905.6	907.1	908.5
157.5°	927.5	926.3	925.0	923.7	922.4	921.1	921.1	922.2	923.4	924.6	925.8
160°	937.0	936.0	935.0	934.1	933.2	932.2	932.2	933.2	934.1	935.0	936.0
162.5°	945.5	944.5	943.7	942.9	942.0	941.2	941.3	942.2	943.2	944.1	945.0
165°	956.2	955.1	954.6	954.1	953.7	953.2	953.4	954.4	955.3	956.2	957.3
167.5°	965.1	964.0	963.6	963.1	962.7	962.3	962.5	963.4	964.4	965.3	966.2
170°	969.7	968.6	968.3	968.0	967.6	967.2	967.6	968.6	969.5	970.4	971.4
172.5°	973.0	971.9	971.6	971.3	971.0	970.7	971.0	971.9	972.9	973.8	974.7
175°	976.7	975.6	975.3	975.0	974.6	974.3	974.7	975.8	976.9	978.1	979.2
177.5°	977.3	976.4	976.3	976.2	976.0	975.9	976.3	977.2	978.1	979.0	979.9
180°	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0



TEST NUMBER: P331769-840

CATALOG NUMBER: S122RDIW-S290D710U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1
2.5°	664.1	664.6	668.2	669.9	673.2	674.5	676.0	675.6	675.6	676.3	681.5
5°	665.5	670.0	676.9	683.6	690.0	695.5	699.2	702.9	704.3	710.8	716.8
7.5°	663.1	671.6	682.9	693.1	705.2	714.7	722.6	729.7	734.6	744.3	754.2
10°	659.9	671.9	684.7	697.8	714.6	727.2	740.0	749.9	753.1	767.5	775.8
12.5°	653.7	669.6	686.0	703.0	719.3	736.7	750.8	760.7	772.0	785.0	800.2
15°	644.4	662.7	684.1	705.8	729.2	750.3	765.5	782.6	795.1	809.3	822.6
17.5°	631.0	654.6	681.7	706.9	734.0	756.6	777.5	794.0	802.6	810.8	812.7
20°	620.3	645.7	677.6	707.4	734.5	760.6	781.3	795.1	797.4	797.6	785.5
22.5°	608.7	637.5	670.9	701.4	733.8	762.9	778.9	784.8	775.7	760.1	736.6
25°	587.4	620.8	659.5	694.4	729.7	757.2	762.8	752.5	720.5	687.0	644.6
27.5°	564.4	601.9	643.4	682.2	719.8	736.9	725.0	687.7	630.4	580.4	519.9
30°	547.5	589.6	630.4	673.7	708.6	715.9	688.6	633.8	566.8	491.6	431.2
32.5°	528.3	572.3	617.1	662.0	691.2	684.0	638.9	571.4	492.9	418.9	361.9
35°	500.8	546.1	594.6	639.5	658.1	627.1	559.7	471.8	391.5	322.6	283.3
37.5°	469.0	518.5	568.8	610.1	608.7	557.1	465.2	374.6	307.1	266.2	238.3
40°	446.4	496.4	550.8	585.6	570.8	503.5	403.9	318.4	269.0	236.5	216.1
42.5°	424.7	474.9	529.0	556.6	530.7	448.1	348.9	281.9	241.2	215.8	199.2
45°	387.9	440.9	490.9	506.2	459.9	368.9	282.2	233.5	206.4	187.6	176.2
47.5°	351.8	404.0	449.7	449.9	387.3	299.1	238.0	202.1	178.9	164.4	156.1
50°	329.8	379.4	417.7	411.7	340.6	266.1	212.9	181.9	162.7	151.4	142.7
52.5°	305.1	353.1	386.4	369.4	301.1	234.2	190.3	164.3	148.3	138.6	130.8
55°	269.0	311.7	335.2	309.4	245.7	194.8	160.8	140.4	128.5	120.2	113.5
57.5°	233.7	268.9	283.6	253.7	202.4	161.5	136.0	120.7	108.9	102.9	99.5
60°	211.5	241.6	251.9	218.8	175.9	141.3	120.5	106.2	97.5	93.6	90.2
62.5°	189.7	214.2	218.4	188.2	153.4	123.7	105.7	93.7	88.0	84.2	81.0
65°	157.3	175.0	173.0	148.7	121.4	98.2	85.1	77.8	73.4	68.2	62.4
67.5°	129.6	140.4	133.8	115.6	92.6	76.3	67.8	62.2	56.8	51.8	50.5
70°	111.9	118.2	111.3	94.5	75.9	64.0	57.2	50.5	47.3	46.2	44.0
72.5°	95.0	97.3	89.8	75.4	61.8	53.0	46.3	42.6	40.8	39.9	38.6
75°	71.3	69.8	63.3	52.1	42.9	37.0	34.8	33.5	32.3	31.4	30.7
77.5°	50.1	47.8	42.0	34.6	29.9	27.1	25.8	25.0	24.5	24.0	23.3
80°	37.7	36.1	30.3	24.7	22.7	21.3	20.6	19.7	19.7	19.3	18.6
82.5°	27.6	25.8	20.7	18.2	17.1	16.2	15.7	15.1	14.9	15.0	14.5
85°	14.4	11.7	10.3	9.9	9.2	8.7	9.0	8.5	8.5	8.5	8.3
87.5°	4.8	4.3	4.4	4.6	5.2	5.4	5.5	5.7	6.2	6.1	6.5
90°	2.4	4.1	5.9	7.6	9.1	10.4	11.6	12.9	14.1	14.9	15.8
92.5°	14.1	13.9	13.8	13.6	13.9	14.5	15.1	15.8	16.4	16.8	17.3
95°	40.8	35.5	30.4	25.2	23.1	24.2	25.3	26.5	27.6	28.4	29.2
97.5°	76.5	62.0	47.4	32.7	26.8	29.3	31.8	34.3	36.9	37.6	38.2
100°	103.6	82.1	60.6	39.1	29.6	32.3	34.9	37.7	40.3	41.5	42.8
102.5°	157.9	153.3	148.8	144.2	130.8	108.5	86.1	63.7	41.4	43.0	44.7
105°	219.6	224.4	229.0	233.8	214.7	171.8	128.9	86.0	43.1	44.8	46.6
107.5°	278.5	282.4	286.1	289.9	266.1	214.7	163.3	111.8	60.4	58.6	56.9
110°	316.5	319.8	323.1	326.4	305.3	259.9	214.5	169.2	123.7	108.1	92.3



TEST NUMBER: P331769-840

CATALOG NUMBER: S122RDIW-S290D710U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	352.3	355.3	358.1	361.0	356.9	345.7	334.5	323.3	312.0	254.8	197.4
115°	409.2	411.8	414.5	417.2	420.5	424.4	428.4	432.2	436.2	363.5	290.7
117.5°	460.5	463.5	466.5	469.5	472.3	475.0	477.8	480.4	483.1	465.5	448.0
120°	497.3	499.6	501.9	504.3	506.9	509.7	512.5	515.3	518.2	520.1	522.0
122.5°	529.1	531.5	534.0	536.4	539.3	542.3	545.4	548.5	551.6	552.7	553.8
125°	576.8	578.9	580.9	582.9	585.4	588.4	591.4	594.4	597.3	598.4	599.6
127.5°	620.7	623.0	625.2	627.5	629.8	632.0	634.2	636.4	638.6	640.3	641.9
130°	648.6	651.2	653.7	656.2	658.3	660.0	661.8	663.5	665.3	667.0	668.7
132.5°	676.6	678.7	680.9	683.0	684.9	686.6	688.3	690.1	691.9	693.3	694.8
135°	713.7	716.2	718.7	721.2	723.3	724.7	726.1	727.5	728.9	730.4	732.1
137.5°	750.1	751.9	753.7	755.4	757.1	758.7	760.3	761.9	763.6	765.1	766.6
140°	774.0	775.2	776.5	777.7	779.2	780.9	782.6	784.4	786.2	787.6	789.0
142.5°	794.2	795.4	796.5	797.6	799.1	801.1	803.1	805.1	807.1	808.4	809.6
145°	824.9	824.8	824.6	824.4	825.7	828.3	831.0	833.6	836.4	837.5	838.5
147.5°	852.3	851.7	851.1	850.5	851.5	854.1	856.8	859.4	862.0	862.9	863.7
150°	869.9	868.8	867.7	866.6	867.3	869.8	872.3	874.8	877.4	878.3	879.2
152.5°	885.0	883.8	882.5	881.3	881.9	884.3	886.7	889.1	891.5	892.4	893.3
155°	907.1	905.6	904.2	902.8	903.0	904.9	906.8	908.7	910.6	911.5	912.4
157.5°	924.6	923.4	922.2	921.1	921.1	922.4	923.7	925.0	926.3	927.5	928.6
160°	935.0	934.1	933.2	932.2	932.2	933.2	934.1	935.0	936.0	937.0	937.9
162.5°	944.1	943.2	942.2	941.3	941.2	942.0	942.9	943.7	944.5	945.5	946.6
165°	956.2	955.3	954.4	953.4	953.2	953.7	954.1	954.6	955.1	956.2	957.4
167.5°	965.3	964.4	963.4	962.5	962.3	962.7	963.1	963.6	964.0	965.1	966.2
170°	970.4	969.5	968.6	967.6	967.2	967.6	968.0	968.3	968.6	969.7	970.8
172.5°	973.8	972.9	971.9	971.0	970.7	971.0	971.3	971.6	971.9	973.0	974.1
175°	978.1	976.9	975.8	974.7	974.3	974.6	975.0	975.3	975.6	976.7	977.9
177.5°	979.0	978.1	977.2	976.3	975.9	976.0	976.2	976.3	976.4	977.3	978.3
180°	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0	977.0



TEST NUMBER: P331769-840

CATALOG NUMBER: S122RDIW-S290D710U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	660.1	660.1	660.1	660.1	660.1	660.1	660.1
2.5°	683.3	685.7	686.8	686.8	688.1	687.5	687.0
5°	722.6	726.9	727.9	732.0	735.0	734.1	734.5
7.5°	761.6	768.6	775.6	778.7	779.2	781.0	781.7
10°	785.7	791.4	802.1	800.6	808.6	813.2	805.7
12.5°	808.8	816.6	824.0	826.1	830.6	832.1	829.1
15°	829.7	833.8	834.2	833.1	834.6	833.3	829.0
17.5°	810.2	803.4	789.9	783.5	778.4	770.8	767.8
20°	777.9	758.1	735.2	726.0	715.3	694.2	699.2
22.5°	708.1	685.7	662.7	635.9	623.1	603.1	601.9
25°	599.7	560.9	518.2	488.4	470.9	451.0	442.2
27.5°	466.3	417.4	382.4	364.8	348.6	332.9	332.1
30°	378.5	341.8	314.8	299.6	289.7	283.1	284.5
32.5°	319.0	293.9	275.6	263.1	255.8	250.7	250.6
35°	260.8	243.6	231.9	226.6	221.4	217.7	217.9
37.5°	223.2	212.9	206.3	200.6	197.2	195.4	194.4
40°	203.9	195.4	190.4	186.9	184.2	181.7	181.2
42.5°	188.7	181.7	176.6	173.9	171.4	169.6	169.2
45°	167.4	161.7	157.1	154.1	153.0	151.4	151.4
47.5°	149.0	143.3	139.8	137.8	135.9	134.8	134.8
50°	136.5	132.1	129.0	127.7	126.1	125.5	125.2
52.5°	125.3	122.0	119.8	119.0	118.3	117.4	117.5
55°	110.1	108.3	107.3	106.6	105.5	104.1	105.0
57.5°	97.4	95.7	93.3	91.1	90.1	89.1	89.5
60°	88.4	85.1	81.9	79.4	78.7	76.6	76.6
62.5°	77.0	72.4	68.5	67.1	66.3	65.4	65.2
65°	59.2	57.4	56.5	55.5	55.0	55.0	54.6
67.5°	49.1	48.3	47.3	47.1	46.7	46.5	46.4
70°	43.3	42.4	42.0	41.7	41.3	41.5	40.8
72.5°	37.9	37.2	37.1	36.5	36.2	36.2	35.6
75°	29.8	29.8	29.6	29.4	28.9	28.7	28.9
77.5°	22.9	23.0	22.6	22.5	22.5	22.5	22.3
80°	18.4	18.6	18.4	18.1	17.9	18.1	17.9
82.5°	14.5	14.1	14.1	14.0	14.0	13.9	13.8
85°	8.3	8.5	8.3	8.1	8.1	8.1	8.3
87.5°	6.5	6.6	6.7	6.8	6.8	6.9	6.8
90°	16.5	17.3	17.9	18.2	18.5	18.8	19.1
92.5°	17.7	18.1	18.4	18.5	18.7	18.9	19.1
95°	29.9	30.7	31.0	30.9	30.7	30.6	30.4
97.5°	38.8	39.4	39.8	40.0	40.2	40.4	40.6
100°	44.0	45.3	46.2	46.5	46.8	47.1	47.4
102.5°	46.4	48.0	49.0	49.5	49.9	50.3	50.8
105°	48.3	50.0	51.2	51.8	52.5	53.1	53.7
107.5°	55.1	53.3	52.8	53.4	54.0	54.6	55.2
110°	76.5	60.9	53.3	53.9	54.6	55.2	55.8



TEST NUMBER: P331769-840

CATALOG NUMBER: S122RDIW-S290D710U840-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	140.2	82.8	54.4	54.9	55.4	55.9	56.5
115°	217.9	145.2	103.2	91.9	80.6	69.3	58.0
117.5°	430.3	412.7	385.4	348.2	311.0	273.9	236.7
120°	523.8	525.7	516.0	494.8	473.6	452.4	431.2
122.5°	554.9	556.1	554.6	550.5	546.3	542.3	538.2
125°	600.7	601.8	602.6	603.0	603.5	604.0	604.4
127.5°	643.5	645.1	645.9	646.0	646.1	646.2	646.3
130°	670.4	672.2	673.0	672.8	672.7	672.5	672.4
132.5°	696.3	697.7	698.4	698.2	698.1	697.9	697.8
135°	733.6	735.2	735.8	735.5	735.2	734.9	734.6
137.5°	768.1	769.7	770.2	769.6	769.1	768.6	768.0
140°	790.4	791.8	792.1	791.3	790.5	789.7	789.0
142.5°	810.9	812.2	812.4	811.7	810.9	810.1	809.3
145°	839.6	840.7	840.9	840.1	839.3	838.5	837.8
147.5°	864.5	865.4	865.5	864.7	864.1	863.4	862.7
150°	880.2	881.1	881.2	880.4	879.6	878.8	878.1
152.5°	894.3	895.2	895.2	894.1	893.1	892.1	891.0
155°	913.4	914.3	914.1	912.9	911.7	910.4	909.2
157.5°	929.6	930.7	930.6	929.4	928.2	927.0	925.6
160°	938.9	939.8	939.7	938.6	937.5	936.4	935.3
162.5°	947.7	948.8	948.7	947.3	945.9	944.5	943.2
165°	958.4	959.5	959.5	958.4	957.4	956.2	955.1
167.5°	967.3	968.4	968.3	966.8	965.4	964.0	962.6
170°	971.8	972.9	972.8	971.4	970.0	968.6	967.1
172.5°	975.2	976.3	976.1	974.7	973.3	971.9	970.5
175°	978.9	980.0	979.8	978.2	976.6	975.0	973.5
177.5°	979.1	980.0	979.9	978.8	977.5	976.4	975.3
180°	977.0	977.0	977.0	977.0	977.0	977.0	977.0

(END OF REPORT)