

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331770-840

Luminaire Tested: **S122RDIW-S290D710U840-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331770-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S290D710U840-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 710 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3627.5 lumens
Efficiency: N/A
Efficacy: 119.3 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 30.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331770-840

CATALOG NUMBER: S122RDIW-S290D710U840-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331770-840

CATALOG NUMBER: S122RDIW-S290D710U840-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39	32
1	94	90	86	83	85	81	78	75	65	63	61	49	48	47	35	35	34	27
2	86	79	74	69	77	72	67	63	57	54	51	44	42	40	32	30	29	24
3	79	70	63	58	71	63	58	53	51	47	44	39	37	34	29	27	26	21
4	72	62	55	49	65	56	50	45	46	41	37	35	32	30	26	24	23	18
5	67	56	48	42	60	51	44	39	41	36	33	32	29	26	24	22	20	16
6	61	50	42	37	55	46	39	34	37	32	29	29	26	23	22	20	18	15
7	57	45	38	33	51	41	35	30	34	29	25	27	23	21	20	18	16	13
8	53	41	34	29	48	38	31	27	31	26	23	24	21	19	18	16	15	12
9	49	38	31	26	44	34	28	24	28	24	20	23	19	17	17	15	13	11
10	46	35	28	23	41	32	26	22	26	22	18	21	18	15	16	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10658	10658	10658	10658
5°	11904	10726	9511	10726
10°	13209	10650	8243	10650
15°	13857	10494	6496	10494
20°	12014	10263	5620	10263
25°	7878	9948	5018	9948
30°	5304	9562	4542	9562
35°	4295	9079	4096	9079
40°	3819	8553	3792	8553
45°	3457	7935	3382	7935
50°	3145	7322	3135	7322
55°	2956	6643	2919	6643
60°	2474	6022	2444	6022
65°	2086	5467	2365	5467
70°	1926	4881	2233	4881
75°	1803	4255	2059	4255
80°	1664	3505	1832	3505
85°	1538	2760	1612	2760



TEST NUMBER: P331770-840

CATALOG NUMBER: S122RDIW-S290D710U840-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	62.6	1.7
10°-20°	174.4	4.8
20°-30°	224.7	6.2
30°-40°	213.5	5.9
40°-50°	182.9	5.0
50°-60°	139.3	3.8
60°-70°	88.1	2.4
70°-80°	44.0	1.2
80°-90°	15.0	0.4
90°-100°	56.3	1.6
100°-110°	174.8	4.8
110°-120°	298.7	8.2
120°-130°	392.8	10.8
130°-140°	440.9	12.2
140°-150°	432.3	11.9
150°-160°	362.6	10.0
160°-170°	240.5	6.6
170°-180°	84.1	2.3
0°-30°	461.7	12.7
0°-40°	675.2	18.6
0°-60°	997.5	27.5
0°-90°	1144.5	31.6
90°-120°	529.8	14.6
90°-150°	1795.8	49.5
90°-180°	2483.0	68.4
0°-180°	3627.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	660	660	660	660	660	
5°	734	662	587	662	734	72
15°	829	628	389	628	829	224
25°	442	558	282	558	442	210
35°	218	461	208	461	218	139
45°	151	348	148	348	151	117
55°	105	236	104	236	105	92
65°	55	143	62	143	55	56
75°	29	68	33	68	29	31
85°	8	15	9	15	8	10
90°	25	1	25	1	25	11
95°	46	39	46	39	46	52
105°	166	161	166	161	166	175
115°	300	300	300	300	300	296
125°	438	436	438	436	438	390
135°	571	564	571	564	571	440
145°	692	685	692	685	692	432
155°	789	783	789	783	789	363
165°	853	852	853	852	853	241
175°	884	886	884	886	884	84
180°	888	888	888	888	888	



TEST NUMBER: P331770-840

CATALOG NUMBER: S122RDIW-S290D710U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1
2.5°	687.0	687.5	688.1	686.8	686.8	685.7	683.3	681.5	676.3	675.6	675.6
5°	734.5	734.1	735.0	732.0	727.9	726.9	722.6	716.8	710.8	704.3	702.9
7.5°	781.7	781.0	779.2	778.7	775.6	768.6	761.6	754.2	744.3	734.6	729.7
10°	805.7	813.2	808.6	800.6	802.1	791.4	785.7	775.8	767.5	753.1	749.9
12.5°	829.1	832.1	830.6	826.1	824.0	816.6	808.8	800.2	785.0	772.0	760.7
15°	829.0	833.3	834.6	833.1	834.2	833.8	829.7	822.6	809.3	795.1	782.6
17.5°	767.8	770.8	778.4	783.5	789.9	803.4	810.2	812.7	810.8	802.6	794.0
20°	699.2	694.2	715.3	726.0	735.2	758.1	777.9	785.5	797.6	797.4	795.1
22.5°	601.9	603.1	623.1	635.9	662.7	685.7	708.1	736.6	760.1	775.7	784.8
25°	442.2	451.0	470.9	488.4	518.2	560.9	599.7	644.6	687.0	720.5	752.5
27.5°	332.1	332.9	348.6	364.8	382.4	417.4	466.3	519.9	580.4	630.4	687.7
30°	284.5	283.1	289.7	299.6	314.8	341.8	378.5	431.2	491.6	566.8	633.8
32.5°	250.6	250.7	255.8	263.1	275.6	293.9	319.0	361.9	418.9	492.9	571.4
35°	217.9	217.7	221.4	226.6	231.9	243.6	260.8	283.3	322.6	391.5	471.8
37.5°	194.4	195.4	197.2	200.6	206.3	212.9	223.2	238.3	266.2	307.1	374.6
40°	181.2	181.7	184.2	186.9	190.4	195.4	203.9	216.1	236.5	269.0	318.4
42.5°	169.2	169.6	171.4	173.9	176.6	181.7	188.7	199.2	215.8	241.2	281.9
45°	151.4	151.4	153.0	154.1	157.1	161.7	167.4	176.2	187.6	206.4	233.5
47.5°	134.8	134.8	135.9	137.8	139.8	143.3	149.0	156.1	164.4	178.9	202.1
50°	125.2	125.5	126.1	127.7	129.0	132.1	136.5	142.7	151.4	162.7	181.9
52.5°	117.5	117.4	118.3	119.0	119.8	122.0	125.3	130.8	138.6	148.3	164.3
55°	105.0	104.1	105.5	106.6	107.3	108.3	110.1	113.5	120.2	128.5	140.4
57.5°	89.5	89.1	90.1	91.1	93.3	95.7	97.4	99.5	102.9	108.9	120.7
60°	76.6	76.6	78.7	79.4	81.9	85.1	88.4	90.2	93.6	97.5	106.2
62.5°	65.2	65.4	66.3	67.1	68.5	72.4	77.0	81.0	84.2	88.0	93.7
65°	54.6	55.0	55.0	55.5	56.5	57.4	59.2	62.4	68.2	73.4	77.8
67.5°	46.4	46.5	46.7	47.1	47.3	48.3	49.1	50.5	51.8	56.8	62.2
70°	40.8	41.5	41.3	41.7	42.0	42.4	43.3	44.0	46.2	47.3	50.5
72.5°	35.6	36.2	36.2	36.5	37.1	37.2	37.9	38.6	39.9	40.8	42.6
75°	28.9	28.7	28.9	29.4	29.6	29.8	29.8	30.7	31.4	32.3	33.5
77.5°	22.3	22.5	22.5	22.5	22.6	23.0	22.9	23.3	24.0	24.5	25.0
80°	17.9	18.1	17.9	18.1	18.4	18.6	18.4	18.6	19.3	19.7	19.7
82.5°	13.8	13.9	14.0	14.0	14.1	14.1	14.5	14.5	15.0	14.9	15.1
85°	8.3	8.1	8.1	8.1	8.3	8.5	8.3	8.3	8.5	8.5	8.5
87.5°	8.1	8.2	8.2	8.1	8.1	8.1	8.2	8.4	8.3	8.6	7.7
90°	25.4	25.3	25.1	24.9	24.8	24.9	25.2	25.5	25.9	26.3	22.5
92.5°	24.2	24.2	24.2	24.1	24.1	24.1	24.0	23.9	23.9	23.8	22.9
95°	46.5	46.8	47.2	47.5	47.8	48.0	48.0	48.0	48.0	48.0	47.7
97.5°	80.5	80.5	80.6	80.6	80.6	80.6	80.6	80.6	80.6	80.6	80.0
100°	102.7	102.8	103.0	103.2	103.3	103.4	103.4	103.4	103.4	103.4	102.9
102.5°	127.8	128.1	128.2	128.4	128.6	128.6	128.4	128.3	128.2	127.9	127.3
105°	166.3	166.3	166.3	166.3	166.3	166.2	165.8	165.5	165.2	164.9	164.5
107.5°	202.7	203.4	204.2	204.9	205.7	206.0	205.9	205.7	205.6	205.5	205.5
110°	230.9	231.3	231.8	232.3	232.8	233.1	233.1	233.1	233.1	233.1	233.1



TEST NUMBER: P331770-840

CATALOG NUMBER: S122RDIW-S290D710U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	257.8	258.1	258.5	258.9	259.2	259.6	260.0	260.4	260.8	261.3	261.4
115°	299.7	300.2	300.7	301.2	301.7	302.1	302.3	302.5	302.6	302.8	303.1
117.5°	339.7	340.2	340.7	341.2	341.7	342.2	342.6	343.1	343.5	343.9	344.8
120°	367.9	368.4	368.9	369.4	369.9	370.2	370.2	370.2	370.2	370.2	371.5
122.5°	395.6	395.9	396.3	396.6	397.0	397.4	397.8	398.2	398.6	399.0	399.9
125°	437.7	437.8	438.0	438.2	438.3	438.6	439.1	439.6	440.1	440.6	441.1
127.5°	476.1	476.6	477.1	477.6	478.2	478.7	479.3	479.9	480.5	481.1	481.7
130°	503.6	504.2	504.9	505.5	506.2	506.8	507.1	507.5	507.8	508.1	508.4
132.5°	530.0	530.5	531.0	531.6	532.1	532.7	533.4	534.2	534.9	535.6	535.6
135°	571.0	571.5	572.0	572.5	573.0	573.4	573.5	573.7	573.8	574.0	573.7
137.5°	608.1	608.8	609.6	610.2	610.9	611.3	611.4	611.5	611.7	611.8	611.4
140°	634.0	634.6	635.3	636.0	636.6	636.9	636.9	636.9	636.9	636.9	636.1
142.5°	657.3	658.0	658.6	659.3	660.0	660.2	660.1	660.0	659.8	659.7	659.1
145°	692.5	693.1	693.8	694.4	695.1	695.3	695.2	695.0	694.8	694.7	693.7
147.5°	723.8	724.4	725.0	725.7	726.3	726.4	726.0	725.7	725.3	725.0	724.3
150°	744.2	744.7	745.1	745.6	746.1	746.1	745.6	745.1	744.7	744.2	743.5
152.5°	763.4	764.0	764.6	765.2	765.9	765.9	765.2	764.6	764.0	763.4	762.5
155°	789.1	789.6	790.1	790.6	791.1	790.9	790.1	789.2	788.4	787.6	787.1
157.5°	811.2	812.0	812.8	813.6	814.5	814.3	813.1	812.0	810.9	809.8	809.5
160°	825.1	825.8	826.4	827.1	827.7	827.6	826.6	825.6	824.6	823.5	823.3
162.5°	837.1	837.9	838.7	839.4	840.2	840.1	839.0	837.8	836.7	835.6	835.4
165°	852.8	853.6	854.4	855.3	856.2	856.0	854.7	853.6	852.4	851.3	851.3
167.5°	865.7	866.6	867.4	868.3	869.1	869.0	867.8	866.7	865.5	864.3	864.3
170°	872.2	873.2	874.2	875.3	876.3	876.2	875.0	873.8	872.7	871.5	871.7
172.5°	877.7	878.7	879.7	880.7	881.6	881.6	880.4	879.3	878.1	876.9	877.1
175°	883.5	884.5	885.6	886.5	887.5	887.5	886.3	885.0	883.9	882.7	883.1
177.5°	886.2	887.0	887.8	888.6	889.4	889.4	888.6	887.8	887.0	886.2	886.5
180°	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0



TEST NUMBER: P331770-840

CATALOG NUMBER: S122RDIW-S290D710U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1
2.5°	676.0	674.5	673.2	669.9	668.2	664.6	664.1	663.9	659.1	654.5	653.2
5°	699.2	695.5	690.0	683.6	676.9	670.0	665.5	661.8	652.6	643.9	638.8
7.5°	722.6	714.7	705.2	693.1	682.9	671.6	663.1	655.5	642.5	630.0	621.6
10°	740.0	727.2	714.6	697.8	684.7	671.9	659.9	649.6	635.0	618.4	606.7
12.5°	750.8	736.7	719.3	703.0	686.0	669.6	653.7	640.5	623.2	606.1	592.3
15°	765.5	750.3	729.2	705.8	684.1	662.7	644.4	627.8	605.4	584.9	567.9
17.5°	777.5	756.6	734.0	706.9	681.7	654.6	631.0	609.9	584.8	560.2	540.2
20°	781.3	760.6	734.5	707.4	677.6	645.7	620.3	597.3	570.5	543.6	520.7
22.5°	778.9	762.9	733.8	701.4	670.9	637.5	608.7	582.1	552.3	524.9	498.4
25°	762.8	757.2	729.7	694.4	659.5	620.8	587.4	558.4	524.4	495.0	466.2
27.5°	725.0	736.9	719.8	682.2	643.4	601.9	564.4	531.3	496.0	463.0	434.2
30°	688.6	715.9	708.6	673.7	630.4	589.6	547.5	512.9	475.3	441.3	412.9
32.5°	638.9	684.0	691.2	662.0	617.1	572.3	528.3	493.8	454.5	418.8	391.0
35°	559.7	627.1	658.1	639.5	594.6	546.1	500.8	460.6	421.1	385.9	358.3
37.5°	465.2	557.1	608.7	610.1	568.8	518.5	469.0	429.1	388.7	354.1	324.3
40°	403.9	503.5	570.8	585.6	550.8	496.4	446.4	405.8	366.4	332.3	298.2
42.5°	348.9	448.1	530.7	556.6	529.0	474.9	424.7	382.3	344.0	311.8	276.9
45°	282.2	368.9	459.9	506.2	490.9	440.9	387.9	347.5	311.5	283.8	250.2
47.5°	238.0	299.1	387.3	449.9	449.7	404.0	351.8	313.3	279.8	253.8	226.7
50°	212.9	266.1	340.6	411.7	417.7	379.4	329.8	291.5	260.3	233.1	211.3
52.5°	190.3	234.2	301.1	369.4	386.4	353.1	305.1	269.7	239.4	214.3	195.7
55°	160.8	194.8	245.7	309.4	335.2	311.7	269.0	236.0	211.5	190.4	174.3
57.5°	136.0	161.5	202.4	253.7	283.6	268.9	233.7	206.8	185.8	166.7	154.1
60°	120.5	141.3	175.9	218.8	251.9	241.6	211.5	186.5	168.6	152.1	140.2
62.5°	105.7	123.7	153.4	188.2	218.4	214.2	189.7	168.6	153.0	137.9	127.8
65°	85.1	98.2	121.4	148.7	173.0	175.0	157.3	143.1	129.2	117.2	108.3
67.5°	67.8	76.3	92.6	115.6	133.8	140.4	129.6	118.7	107.6	98.4	90.6
70°	57.2	64.0	75.9	94.5	111.3	118.2	111.9	103.4	93.8	86.2	79.6
72.5°	46.3	53.0	61.8	75.4	89.8	97.3	95.0	89.0	81.2	74.8	68.6
75°	34.8	37.0	42.9	52.1	63.3	69.8	71.3	68.2	61.9	57.2	53.4
77.5°	25.8	27.1	29.9	34.6	42.0	47.8	50.1	49.7	45.4	42.7	39.2
80°	20.6	21.3	22.7	24.7	30.3	36.1	37.7	37.7	34.6	33.5	30.1
82.5°	15.7	16.2	17.1	18.2	20.7	25.8	27.6	27.9	26.1	24.5	21.8
85°	9.0	8.7	9.2	9.9	10.3	11.7	14.4	14.9	14.4	12.6	11.9
87.5°	6.9	6.4	5.7	4.8	4.6	4.4	4.9	5.5	5.2	4.9	5.0
90°	18.9	15.2	11.6	8.8	6.8	4.7	2.7	0.7	2.7	4.7	6.8
92.5°	22.1	21.2	20.4	19.2	17.8	16.3	14.8	13.3	14.8	16.3	17.8
95°	47.3	47.0	46.7	45.6	43.9	42.3	40.6	39.0	40.6	42.3	43.9
97.5°	79.4	78.8	78.1	77.1	75.5	74.1	72.6	71.2	72.6	74.1	75.5
100°	102.4	101.9	101.4	100.5	99.2	97.9	96.5	95.1	96.5	97.9	99.2
102.5°	126.7	126.1	125.4	124.6	123.5	122.5	121.4	120.4	121.4	122.5	123.5
105°	164.2	163.9	163.5	163.1	162.6	162.1	161.6	161.1	161.6	162.1	162.6
107.5°	205.5	205.5	205.5	205.1	204.4	203.7	202.9	202.2	202.9	203.7	204.4
110°	233.1	233.1	233.1	232.6	231.6	230.6	229.5	228.5	229.5	230.6	231.6



TEST NUMBER: P331770-840

CATALOG NUMBER: S122RDIW-S290D710U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	261.5	261.7	261.8	261.4	260.3	259.3	258.3	257.3	258.3	259.3	260.3
115°	303.4	303.8	304.1	303.8	302.8	301.7	300.7	299.7	300.7	301.7	302.8
117.5°	345.7	346.6	347.5	347.3	346.0	344.7	343.4	342.0	343.4	344.7	346.0
120°	372.8	374.2	375.5	375.5	374.2	372.8	371.5	370.2	371.5	372.8	374.2
122.5°	400.8	401.7	402.7	402.3	400.7	399.2	397.6	396.0	397.6	399.2	400.7
125°	441.6	442.1	442.6	442.1	440.6	439.1	437.7	436.2	437.7	439.1	440.6
127.5°	482.3	482.9	483.5	482.8	480.9	479.1	477.2	475.2	477.2	479.1	480.9
130°	508.8	509.1	509.4	508.5	506.3	504.1	502.0	499.8	502.0	504.1	506.3
132.5°	535.5	535.4	535.4	534.4	532.7	531.0	529.2	527.5	529.2	531.0	532.7
135°	573.4	573.0	572.7	571.6	569.8	567.9	566.1	564.3	566.1	567.9	569.8
137.5°	611.0	610.5	610.1	609.0	607.6	606.1	604.6	603.1	604.6	606.1	607.6
140°	635.3	634.5	633.6	632.5	631.0	629.4	627.9	626.5	627.9	629.4	631.0
142.5°	658.6	658.0	657.5	656.4	655.0	653.5	652.0	650.5	652.0	653.5	655.0
145°	692.7	691.7	690.6	689.6	688.4	687.2	686.1	684.9	686.1	687.2	688.4
147.5°	723.6	723.0	722.3	721.2	719.8	718.4	717.0	715.7	717.0	718.4	719.8
150°	742.8	742.1	741.4	740.6	739.6	738.6	737.6	736.6	737.6	738.6	739.6
152.5°	761.7	760.9	760.1	759.2	758.2	757.2	756.2	755.2	756.2	757.2	758.2
155°	786.6	786.1	785.6	785.1	784.6	784.1	783.6	783.0	783.6	784.1	784.6
157.5°	809.2	808.9	808.6	808.3	807.9	807.6	807.3	806.9	807.3	807.6	807.9
160°	823.2	823.0	822.9	822.6	822.3	821.9	821.6	821.3	821.6	821.9	822.3
162.5°	835.3	835.1	834.9	834.8	834.7	834.7	834.6	834.5	834.6	834.7	834.7
165°	851.3	851.3	851.3	851.4	851.5	851.7	851.8	852.0	851.8	851.7	851.5
167.5°	864.3	864.4	864.4	864.7	865.3	865.8	866.3	866.8	866.3	865.8	865.3
170°	871.8	872.0	872.2	872.5	873.0	873.5	874.0	874.5	874.0	873.5	873.0
172.5°	877.3	877.4	877.6	877.9	878.4	878.9	879.4	879.9	879.4	878.9	878.4
175°	883.4	883.7	884.1	884.5	885.0	885.6	886.1	886.5	886.1	885.6	885.0
177.5°	886.8	887.0	887.3	887.6	888.0	888.4	888.8	889.2	888.8	888.4	888.0
180°	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0



TEST NUMBER: P331770-840

CATALOG NUMBER: S122RDIW-S290D710U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1
2.5°	650.9	649.5	647.1	643.5	641.3	637.4	634.9	636.3	636.7	636.3	636.0
5°	633.4	628.5	621.9	615.4	609.5	603.1	599.4	597.8	594.6	592.8	591.8
7.5°	612.2	603.9	594.5	583.3	573.8	563.8	558.8	556.2	549.7	546.1	543.0
10°	596.4	583.3	573.9	559.3	550.3	537.2	528.3	528.6	519.6	514.5	510.9
12.5°	579.0	564.6	549.0	535.7	523.3	512.8	502.0	497.7	488.2	483.3	473.4
15°	550.1	533.3	516.8	499.0	486.4	470.0	454.4	435.4	420.0	406.7	403.0
17.5°	518.6	497.8	481.2	460.2	438.6	411.2	393.1	382.0	372.8	365.8	360.5
20°	496.9	475.7	458.1	426.5	397.3	378.7	365.5	356.9	347.3	339.7	335.6
22.5°	474.1	452.1	428.0	392.6	369.9	355.1	343.3	333.5	326.9	321.0	317.2
25°	441.8	417.7	378.0	353.8	335.4	319.7	311.5	305.6	298.7	290.6	287.0
27.5°	407.7	369.4	340.8	322.8	305.3	295.2	287.7	278.8	272.7	269.0	265.2
30°	382.1	343.9	321.6	301.8	289.5	278.2	269.5	264.5	258.5	252.4	249.8
32.5°	353.8	323.2	301.7	285.4	272.8	263.2	256.3	248.1	243.9	240.0	234.8
35°	318.4	295.2	275.7	262.5	250.4	242.7	234.7	229.8	222.1	218.8	216.8
37.5°	288.5	268.4	253.9	239.8	230.4	221.8	216.8	209.1	205.8	201.3	196.9
40°	271.6	251.9	237.9	226.4	215.8	209.4	203.3	197.0	192.0	190.0	184.7
42.5°	254.4	238.3	224.3	211.8	204.7	197.8	190.1	185.5	180.3	176.9	173.7
45°	230.6	216.3	204.4	194.1	186.2	179.2	174.1	166.5	163.6	156.9	154.1
47.5°	209.6	196.4	185.0	175.2	167.6	163.0	155.6	149.7	144.9	140.8	137.2
50°	194.8	183.7	172.7	164.0	157.1	150.5	142.9	140.0	132.6	130.5	128.5
52.5°	181.2	170.7	160.7	152.1	145.2	138.8	132.1	128.2	123.2	121.2	119.7
55°	162.2	152.1	142.5	134.9	128.1	121.4	117.2	112.4	110.1	108.5	106.6
57.5°	143.1	134.0	126.6	119.0	112.0	106.7	102.0	99.1	96.7	94.6	92.4
60°	131.0	122.3	115.6	108.5	101.4	97.0	93.4	89.9	87.2	83.9	83.0
62.5°	118.2	110.5	104.4	97.5	91.3	87.4	83.8	80.6	77.3	72.6	71.3
65°	100.5	94.5	88.1	82.3	76.9	72.9	67.9	64.2	62.8	62.4	62.2
67.5°	84.5	78.9	73.3	67.5	62.5	58.9	56.2	55.7	54.7	54.5	53.8
70°	73.8	68.6	63.1	57.6	52.7	52.1	51.2	50.2	49.1	48.7	48.2
72.5°	64.3	58.9	53.3	49.0	46.9	46.0	45.1	44.1	43.4	42.9	42.7
75°	49.3	44.2	40.6	39.0	37.9	37.2	35.7	35.1	34.6	33.9	33.7
77.5°	35.5	32.6	31.0	30.0	28.8	28.1	27.3	26.6	26.1	26.0	25.5
80°	27.1	25.7	24.5	23.1	22.7	21.8	21.6	20.9	21.1	20.4	20.4
82.5°	21.0	19.3	18.3	17.7	17.2	16.5	16.3	16.0	16.0	15.5	15.5
85°	10.8	10.3	9.9	9.4	9.4	8.7	9.0	8.7	8.7	8.3	8.1
87.5°	5.3	5.7	6.0	6.8	7.5	8.0	8.0	7.7	7.6	7.6	7.4
90°	8.8	11.6	15.2	18.9	22.5	26.3	25.9	25.5	25.2	24.9	24.8
92.5°	19.2	20.4	21.2	22.1	22.9	23.8	23.9	23.9	24.0	24.1	24.1
95°	45.6	46.7	47.0	47.3	47.7	48.0	48.0	48.0	48.0	48.0	47.8
97.5°	77.1	78.1	78.8	79.4	80.0	80.6	80.6	80.6	80.6	80.6	80.6
100°	100.5	101.4	101.9	102.4	102.9	103.4	103.4	103.4	103.4	103.4	103.3
102.5°	124.6	125.4	126.1	126.7	127.3	127.9	128.2	128.3	128.4	128.6	128.6
105°	163.1	163.5	163.9	164.2	164.5	164.9	165.2	165.5	165.8	166.2	166.3
107.5°	205.1	205.5	205.5	205.5	205.5	205.5	205.6	205.7	205.9	206.0	205.7
110°	232.6	233.1	233.1	233.1	233.1	233.1	233.1	233.1	233.1	233.1	232.8



TEST NUMBER: P331770-840

CATALOG NUMBER: S122RDIW-S290D710U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	261.4	261.8	261.7	261.5	261.4	261.3	260.8	260.4	260.0	259.6	259.2
115°	303.8	304.1	303.8	303.4	303.1	302.8	302.6	302.5	302.3	302.1	301.7
117.5°	347.3	347.5	346.6	345.7	344.8	343.9	343.5	343.1	342.6	342.2	341.7
120°	375.5	375.5	374.2	372.8	371.5	370.2	370.2	370.2	370.2	370.2	369.9
122.5°	402.3	402.7	401.7	400.8	399.9	399.0	398.6	398.2	397.8	397.4	397.0
125°	442.1	442.6	442.1	441.6	441.1	440.6	440.1	439.6	439.1	438.6	438.3
127.5°	482.8	483.5	482.9	482.3	481.7	481.1	480.5	479.9	479.3	478.7	478.2
130°	508.5	509.4	509.1	508.8	508.4	508.1	507.8	507.5	507.1	506.8	506.2
132.5°	534.4	535.4	535.4	535.5	535.6	535.6	534.9	534.2	533.4	532.7	532.1
135°	571.6	572.7	573.0	573.4	573.7	574.0	573.8	573.7	573.5	573.4	573.0
137.5°	609.0	610.1	610.5	611.0	611.4	611.8	611.7	611.5	611.4	611.3	610.9
140°	632.5	633.6	634.5	635.3	636.1	636.9	636.9	636.9	636.9	636.9	636.6
142.5°	656.4	657.5	658.0	658.6	659.1	659.7	659.8	660.0	660.1	660.2	660.0
145°	689.6	690.6	691.7	692.7	693.7	694.7	694.8	695.0	695.2	695.3	695.1
147.5°	721.2	722.3	723.0	723.6	724.3	725.0	725.3	725.7	726.0	726.4	726.3
150°	740.6	741.4	742.1	742.8	743.5	744.2	744.7	745.1	745.6	746.1	746.1
152.5°	759.2	760.1	760.9	761.7	762.5	763.4	764.0	764.6	765.2	765.9	765.9
155°	785.1	785.6	786.1	786.6	787.1	787.6	788.4	789.2	790.1	790.9	791.1
157.5°	808.3	808.6	808.9	809.2	809.5	809.8	810.9	812.0	813.1	814.3	814.5
160°	822.6	822.9	823.0	823.2	823.3	823.5	824.6	825.6	826.6	827.6	827.7
162.5°	834.8	834.9	835.1	835.3	835.4	835.6	836.7	837.8	839.0	840.1	840.2
165°	851.4	851.3	851.3	851.3	851.3	851.3	852.4	853.6	854.7	856.0	856.2
167.5°	864.7	864.4	864.4	864.3	864.3	864.3	865.5	866.7	867.8	869.0	869.1
170°	872.5	872.2	872.0	871.8	871.7	871.5	872.7	873.8	875.0	876.2	876.3
172.5°	877.9	877.6	877.4	877.3	877.1	876.9	878.1	879.3	880.4	881.6	881.6
175°	884.5	884.1	883.7	883.4	883.1	882.7	883.9	885.0	886.3	887.5	887.5
177.5°	887.6	887.3	887.0	886.8	886.5	886.2	887.0	887.8	888.6	889.4	889.4
180°	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0



TEST NUMBER: P331770-840

CATALOG NUMBER: S122RDIW-S290D710U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1
2.5°	634.0	634.3	633.8	634.1	633.8	634.3	634.0	636.0	636.3	636.7	636.3
5°	590.7	587.9	587.4	586.8	587.4	587.9	590.7	591.8	592.8	594.6	597.8
7.5°	539.1	538.7	537.5	535.8	537.5	538.7	539.1	543.0	546.1	549.7	556.2
10°	505.8	504.6	504.4	502.8	504.4	504.6	505.8	510.9	514.5	519.6	528.6
12.5°	466.9	459.5	458.8	454.7	458.8	459.5	466.9	473.4	483.3	488.2	497.7
15°	397.6	396.2	391.5	388.6	391.5	396.2	397.6	403.0	406.7	420.0	435.4
17.5°	357.9	353.4	351.9	351.3	351.9	353.4	357.9	360.5	365.8	372.8	382.0
20°	332.3	328.3	327.6	327.1	327.6	328.3	332.3	335.6	339.7	347.3	356.9
22.5°	314.8	310.4	308.7	307.3	308.7	310.4	314.8	317.2	321.0	326.9	333.5
25°	284.7	283.1	282.2	281.7	282.2	283.1	284.7	287.0	290.6	298.7	305.6
27.5°	261.2	257.6	256.9	255.7	256.9	257.6	261.2	265.2	269.0	272.7	278.8
30°	247.7	246.6	245.0	243.6	245.0	246.6	247.7	249.8	252.4	258.5	264.5
32.5°	232.0	231.0	229.5	228.9	229.5	231.0	232.0	234.8	240.0	243.9	248.1
35°	214.5	211.3	209.8	207.8	209.8	211.3	214.5	216.8	218.8	222.1	229.8
37.5°	196.0	194.3	192.4	193.1	192.4	194.3	196.0	196.9	201.3	205.8	209.1
40°	181.7	180.6	180.1	179.9	180.1	180.6	181.7	184.7	190.0	192.0	197.0
42.5°	170.3	167.1	165.9	165.9	165.9	167.1	170.3	173.7	176.9	180.3	185.5
45°	153.0	150.1	147.9	148.1	147.9	150.1	153.0	154.1	156.9	163.6	166.5
47.5°	135.3	135.2	133.9	134.3	133.9	135.2	135.3	137.2	140.8	144.9	149.7
50°	126.8	125.5	124.5	124.8	124.5	125.5	126.8	128.5	130.5	132.6	140.0
52.5°	118.8	117.5	116.8	117.9	116.8	117.5	118.8	119.7	121.2	123.2	128.2
55°	105.5	104.1	103.9	103.7	103.9	104.1	105.5	106.6	108.5	110.1	112.4
57.5°	90.7	89.8	88.4	87.9	88.4	89.8	90.7	92.4	94.6	96.7	99.1
60°	80.1	78.3	75.9	75.7	75.9	78.3	80.1	83.0	83.9	87.2	89.9
62.5°	70.3	70.0	69.5	69.5	69.5	70.0	70.3	71.3	72.6	77.3	80.6
65°	61.7	61.5	61.7	61.9	61.7	61.5	61.7	62.2	62.4	62.8	64.2
67.5°	53.7	53.3	52.9	53.1	52.9	53.3	53.7	53.8	54.5	54.7	55.7
70°	47.7	47.5	47.3	47.3	47.3	47.5	47.7	48.2	48.7	49.1	50.2
72.5°	41.8	41.8	41.6	41.4	41.6	41.8	41.8	42.7	42.9	43.4	44.1
75°	33.5	33.0	33.0	33.0	33.0	33.0	33.5	33.7	33.9	34.6	35.1
77.5°	25.5	25.2	25.0	24.8	25.0	25.2	25.5	25.5	26.0	26.1	26.6
80°	20.2	20.0	19.7	19.7	19.7	20.0	20.2	20.4	20.4	21.1	20.9
82.5°	15.5	15.1	15.1	14.9	15.1	15.1	15.5	15.5	15.5	16.0	16.0
85°	8.3	8.5	8.3	8.7	8.3	8.5	8.3	8.1	8.3	8.7	8.7
87.5°	7.4	7.3	7.5	7.3	7.5	7.3	7.4	7.4	7.6	7.6	7.7
90°	24.9	25.1	25.3	25.4	25.3	25.1	24.9	24.8	24.9	25.2	25.5
92.5°	24.1	24.2	24.2	24.2	24.2	24.2	24.1	24.1	24.1	24.0	23.9
95°	47.5	47.2	46.8	46.5	46.8	47.2	47.5	47.8	48.0	48.0	48.0
97.5°	80.6	80.6	80.5	80.5	80.5	80.6	80.6	80.6	80.6	80.6	80.6
100°	103.2	103.0	102.8	102.7	102.8	103.0	103.2	103.3	103.4	103.4	103.4
102.5°	128.4	128.2	128.1	127.8	128.1	128.2	128.4	128.6	128.6	128.4	128.3
105°	166.3	166.3	166.3	166.3	166.3	166.3	166.3	166.3	166.2	165.8	165.5
107.5°	204.9	204.2	203.4	202.7	203.4	204.2	204.9	205.7	206.0	205.9	205.7
110°	232.3	231.8	231.3	230.9	231.3	231.8	232.3	232.8	233.1	233.1	233.1



TEST NUMBER: P331770-840

CATALOG NUMBER: S122RDIW-S290D710U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	258.9	258.5	258.1	257.8	258.1	258.5	258.9	259.2	259.6	260.0	260.4
115°	301.2	300.7	300.2	299.7	300.2	300.7	301.2	301.7	302.1	302.3	302.5
117.5°	341.2	340.7	340.2	339.7	340.2	340.7	341.2	341.7	342.2	342.6	343.1
120°	369.4	368.9	368.4	367.9	368.4	368.9	369.4	369.9	370.2	370.2	370.2
122.5°	396.6	396.3	395.9	395.6	395.9	396.3	396.6	397.0	397.4	397.8	398.2
125°	438.2	438.0	437.8	437.7	437.8	438.0	438.2	438.3	438.6	439.1	439.6
127.5°	477.6	477.1	476.6	476.1	476.6	477.1	477.6	478.2	478.7	479.3	479.9
130°	505.5	504.9	504.2	503.6	504.2	504.9	505.5	506.2	506.8	507.1	507.5
132.5°	531.6	531.0	530.5	530.0	530.5	531.0	531.6	532.1	532.7	533.4	534.2
135°	572.5	572.0	571.5	571.0	571.5	572.0	572.5	573.0	573.4	573.5	573.7
137.5°	610.2	609.6	608.8	608.1	608.8	609.6	610.2	610.9	611.3	611.4	611.5
140°	636.0	635.3	634.6	634.0	634.6	635.3	636.0	636.6	636.9	636.9	636.9
142.5°	659.3	658.6	658.0	657.3	658.0	658.6	659.3	660.0	660.2	660.1	660.0
145°	694.4	693.8	693.1	692.5	693.1	693.8	694.4	695.1	695.3	695.2	695.0
147.5°	725.7	725.0	724.4	723.8	724.4	725.0	725.7	726.3	726.4	726.0	725.7
150°	745.6	745.1	744.7	744.2	744.7	745.1	745.6	746.1	746.1	745.6	745.1
152.5°	765.2	764.6	764.0	763.4	764.0	764.6	765.2	765.9	765.9	765.2	764.6
155°	790.6	790.1	789.6	789.1	789.6	790.1	790.6	791.1	790.9	790.1	789.2
157.5°	813.6	812.8	812.0	811.2	812.0	812.8	813.6	814.5	814.3	813.1	812.0
160°	827.1	826.4	825.8	825.1	825.8	826.4	827.1	827.7	827.6	826.6	825.6
162.5°	839.4	838.7	837.9	837.1	837.9	838.7	839.4	840.2	840.1	839.0	837.8
165°	855.3	854.4	853.6	852.8	853.6	854.4	855.3	856.2	856.0	854.7	853.6
167.5°	868.3	867.4	866.6	865.7	866.6	867.4	868.3	869.1	869.0	867.8	866.7
170°	875.3	874.2	873.2	872.2	873.2	874.2	875.3	876.3	876.2	875.0	873.8
172.5°	880.7	879.7	878.7	877.7	878.7	879.7	880.7	881.6	881.6	880.4	879.3
175°	886.5	885.6	884.5	883.5	884.5	885.6	886.5	887.5	887.5	886.3	885.0
177.5°	888.6	887.8	887.0	886.2	887.0	887.8	888.6	889.4	889.4	888.6	887.8
180°	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0



TEST NUMBER: P331770-840

CATALOG NUMBER: S122RDIW-S290D710U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1
2.5°	634.9	637.4	641.3	643.5	647.1	649.5	650.9	653.2	654.5	659.1	663.9
5°	599.4	603.1	609.5	615.4	621.9	628.5	633.4	638.8	643.9	652.6	661.8
7.5°	558.8	563.8	573.8	583.3	594.5	603.9	612.2	621.6	630.0	642.5	655.5
10°	528.3	537.2	550.3	559.3	573.9	583.3	596.4	606.7	618.4	635.0	649.6
12.5°	502.0	512.8	523.3	535.7	549.0	564.6	579.0	592.3	606.1	623.2	640.5
15°	454.4	470.0	486.4	499.0	516.8	533.3	550.1	567.9	584.9	605.4	627.8
17.5°	393.1	411.2	438.6	460.2	481.2	497.8	518.6	540.2	560.2	584.8	609.9
20°	365.5	378.7	397.3	426.5	458.1	475.7	496.9	520.7	543.6	570.5	597.3
22.5°	343.3	355.1	369.9	392.6	428.0	452.1	474.1	498.4	524.9	552.3	582.1
25°	311.5	319.7	335.4	353.8	378.0	417.7	441.8	466.2	495.0	524.4	558.4
27.5°	287.7	295.2	305.3	322.8	340.8	369.4	407.7	434.2	463.0	496.0	531.3
30°	269.5	278.2	289.5	301.8	321.6	343.9	382.1	412.9	441.3	475.3	512.9
32.5°	256.3	263.2	272.8	285.4	301.7	323.2	353.8	391.0	418.8	454.5	493.8
35°	234.7	242.7	250.4	262.5	275.7	295.2	318.4	358.3	385.9	421.1	460.6
37.5°	216.8	221.8	230.4	239.8	253.9	268.4	288.5	324.3	354.1	388.7	429.1
40°	203.3	209.4	215.8	226.4	237.9	251.9	271.6	298.2	332.3	366.4	405.8
42.5°	190.1	197.8	204.7	211.8	224.3	238.3	254.4	276.9	311.8	344.0	382.3
45°	174.1	179.2	186.2	194.1	204.4	216.3	230.6	250.2	283.8	311.5	347.5
47.5°	155.6	163.0	167.6	175.2	185.0	196.4	209.6	226.7	253.8	279.8	313.3
50°	142.9	150.5	157.1	164.0	172.7	183.7	194.8	211.3	233.1	260.3	291.5
52.5°	132.1	138.8	145.2	152.1	160.7	170.7	181.2	195.7	214.3	239.4	269.7
55°	117.2	121.4	128.1	134.9	142.5	152.1	162.2	174.3	190.4	211.5	236.0
57.5°	102.0	106.7	112.0	119.0	126.6	134.0	143.1	154.1	166.7	185.8	206.8
60°	93.4	97.0	101.4	108.5	115.6	122.3	131.0	140.2	152.1	168.6	186.5
62.5°	83.8	87.4	91.3	97.5	104.4	110.5	118.2	127.8	137.9	153.0	168.6
65°	67.9	72.9	76.9	82.3	88.1	94.5	100.5	108.3	117.2	129.2	143.1
67.5°	56.2	58.9	62.5	67.5	73.3	78.9	84.5	90.6	98.4	107.6	118.7
70°	51.2	52.1	52.7	57.6	63.1	68.6	73.8	79.6	86.2	93.8	103.4
72.5°	45.1	46.0	46.9	49.0	53.3	58.9	64.3	68.6	74.8	81.2	89.0
75°	35.7	37.2	37.9	39.0	40.6	44.2	49.3	53.4	57.2	61.9	68.2
77.5°	27.3	28.1	28.8	30.0	31.0	32.6	35.5	39.2	42.7	45.4	49.7
80°	21.6	21.8	22.7	23.1	24.5	25.7	27.1	30.1	33.5	34.6	37.7
82.5°	16.3	16.5	17.2	17.7	18.3	19.3	21.0	21.8	24.5	26.1	27.9
85°	9.0	8.7	9.4	9.4	9.9	10.3	10.8	11.9	12.6	14.4	14.9
87.5°	8.0	8.0	7.5	6.8	6.0	5.7	5.3	5.0	4.9	5.2	5.5
90°	25.9	26.3	22.5	18.9	15.2	11.6	8.8	6.8	4.7	2.7	0.7
92.5°	23.9	23.8	22.9	22.1	21.2	20.4	19.2	17.8	16.3	14.8	13.3
95°	48.0	48.0	47.7	47.3	47.0	46.7	45.6	43.9	42.3	40.6	39.0
97.5°	80.6	80.6	80.0	79.4	78.8	78.1	77.1	75.5	74.1	72.6	71.2
100°	103.4	103.4	102.9	102.4	101.9	101.4	100.5	99.2	97.9	96.5	95.1
102.5°	128.2	127.9	127.3	126.7	126.1	125.4	124.6	123.5	122.5	121.4	120.4
105°	165.2	164.9	164.5	164.2	163.9	163.5	163.1	162.6	162.1	161.6	161.1
107.5°	205.6	205.5	205.5	205.5	205.5	205.5	205.1	204.4	203.7	202.9	202.2
110°	233.1	233.1	233.1	233.1	233.1	233.1	232.6	231.6	230.6	229.5	228.5



TEST NUMBER: P331770-840

CATALOG NUMBER: S122RDIW-S290D710U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	260.8	261.3	261.4	261.5	261.7	261.8	261.4	260.3	259.3	258.3	257.3
115°	302.6	302.8	303.1	303.4	303.8	304.1	303.8	302.8	301.7	300.7	299.7
117.5°	343.5	343.9	344.8	345.7	346.6	347.5	347.3	346.0	344.7	343.4	342.0
120°	370.2	370.2	371.5	372.8	374.2	375.5	375.5	374.2	372.8	371.5	370.2
122.5°	398.6	399.0	399.9	400.8	401.7	402.7	402.3	400.7	399.2	397.6	396.0
125°	440.1	440.6	441.1	441.6	442.1	442.6	442.1	440.6	439.1	437.7	436.2
127.5°	480.5	481.1	481.7	482.3	482.9	483.5	482.8	480.9	479.1	477.2	475.2
130°	507.8	508.1	508.4	508.8	509.1	509.4	508.5	506.3	504.1	502.0	499.8
132.5°	534.9	535.6	535.6	535.5	535.4	535.4	534.4	532.7	531.0	529.2	527.5
135°	573.8	574.0	573.7	573.4	573.0	572.7	571.6	569.8	567.9	566.1	564.3
137.5°	611.7	611.8	611.4	611.0	610.5	610.1	609.0	607.6	606.1	604.6	603.1
140°	636.9	636.9	636.1	635.3	634.5	633.6	632.5	631.0	629.4	627.9	626.5
142.5°	659.8	659.7	659.1	658.6	658.0	657.5	656.4	655.0	653.5	652.0	650.5
145°	694.8	694.7	693.7	692.7	691.7	690.6	689.6	688.4	687.2	686.1	684.9
147.5°	725.3	725.0	724.3	723.6	723.0	722.3	721.2	719.8	718.4	717.0	715.7
150°	744.7	744.2	743.5	742.8	742.1	741.4	740.6	739.6	738.6	737.6	736.6
152.5°	764.0	763.4	762.5	761.7	760.9	760.1	759.2	758.2	757.2	756.2	755.2
155°	788.4	787.6	787.1	786.6	786.1	785.6	785.1	784.6	784.1	783.6	783.0
157.5°	810.9	809.8	809.5	809.2	808.9	808.6	808.3	807.9	807.6	807.3	806.9
160°	824.6	823.5	823.3	823.2	823.0	822.9	822.6	822.3	821.9	821.6	821.3
162.5°	836.7	835.6	835.4	835.3	835.1	834.9	834.8	834.7	834.7	834.6	834.5
165°	852.4	851.3	851.3	851.3	851.3	851.3	851.4	851.5	851.7	851.8	852.0
167.5°	865.5	864.3	864.3	864.3	864.4	864.4	864.7	865.3	865.8	866.3	866.8
170°	872.7	871.5	871.7	871.8	872.0	872.2	872.5	873.0	873.5	874.0	874.5
172.5°	878.1	876.9	877.1	877.3	877.4	877.6	877.9	878.4	878.9	879.4	879.9
175°	883.9	882.7	883.1	883.4	883.7	884.1	884.5	885.0	885.6	886.1	886.5
177.5°	887.0	886.2	886.5	886.8	887.0	887.3	887.6	888.0	888.4	888.8	889.2
180°	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0



TEST NUMBER: P331770-840

CATALOG NUMBER: S122RDIW-S290D710U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1	660.1
2.5°	664.1	664.6	668.2	669.9	673.2	674.5	676.0	675.6	675.6	676.3	681.5
5°	665.5	670.0	676.9	683.6	690.0	695.5	699.2	702.9	704.3	710.8	716.8
7.5°	663.1	671.6	682.9	693.1	705.2	714.7	722.6	729.7	734.6	744.3	754.2
10°	659.9	671.9	684.7	697.8	714.6	727.2	740.0	749.9	753.1	767.5	775.8
12.5°	653.7	669.6	686.0	703.0	719.3	736.7	750.8	760.7	772.0	785.0	800.2
15°	644.4	662.7	684.1	705.8	729.2	750.3	765.5	782.6	795.1	809.3	822.6
17.5°	631.0	654.6	681.7	706.9	734.0	756.6	777.5	794.0	802.6	810.8	812.7
20°	620.3	645.7	677.6	707.4	734.5	760.6	781.3	795.1	797.4	797.6	785.5
22.5°	608.7	637.5	670.9	701.4	733.8	762.9	778.9	784.8	775.7	760.1	736.6
25°	587.4	620.8	659.5	694.4	729.7	757.2	762.8	752.5	720.5	687.0	644.6
27.5°	564.4	601.9	643.4	682.2	719.8	736.9	725.0	687.7	630.4	580.4	519.9
30°	547.5	589.6	630.4	673.7	708.6	715.9	688.6	633.8	566.8	491.6	431.2
32.5°	528.3	572.3	617.1	662.0	691.2	684.0	638.9	571.4	492.9	418.9	361.9
35°	500.8	546.1	594.6	639.5	658.1	627.1	559.7	471.8	391.5	322.6	283.3
37.5°	469.0	518.5	568.8	610.1	608.7	557.1	465.2	374.6	307.1	266.2	238.3
40°	446.4	496.4	550.8	585.6	570.8	503.5	403.9	318.4	269.0	236.5	216.1
42.5°	424.7	474.9	529.0	556.6	530.7	448.1	348.9	281.9	241.2	215.8	199.2
45°	387.9	440.9	490.9	506.2	459.9	368.9	282.2	233.5	206.4	187.6	176.2
47.5°	351.8	404.0	449.7	449.9	387.3	299.1	238.0	202.1	178.9	164.4	156.1
50°	329.8	379.4	417.7	411.7	340.6	266.1	212.9	181.9	162.7	151.4	142.7
52.5°	305.1	353.1	386.4	369.4	301.1	234.2	190.3	164.3	148.3	138.6	130.8
55°	269.0	311.7	335.2	309.4	245.7	194.8	160.8	140.4	128.5	120.2	113.5
57.5°	233.7	268.9	283.6	253.7	202.4	161.5	136.0	120.7	108.9	102.9	99.5
60°	211.5	241.6	251.9	218.8	175.9	141.3	120.5	106.2	97.5	93.6	90.2
62.5°	189.7	214.2	218.4	188.2	153.4	123.7	105.7	93.7	88.0	84.2	81.0
65°	157.3	175.0	173.0	148.7	121.4	98.2	85.1	77.8	73.4	68.2	62.4
67.5°	129.6	140.4	133.8	115.6	92.6	76.3	67.8	62.2	56.8	51.8	50.5
70°	111.9	118.2	111.3	94.5	75.9	64.0	57.2	50.5	47.3	46.2	44.0
72.5°	95.0	97.3	89.8	75.4	61.8	53.0	46.3	42.6	40.8	39.9	38.6
75°	71.3	69.8	63.3	52.1	42.9	37.0	34.8	33.5	32.3	31.4	30.7
77.5°	50.1	47.8	42.0	34.6	29.9	27.1	25.8	25.0	24.5	24.0	23.3
80°	37.7	36.1	30.3	24.7	22.7	21.3	20.6	19.7	19.7	19.3	18.6
82.5°	27.6	25.8	20.7	18.2	17.1	16.2	15.7	15.1	14.9	15.0	14.5
85°	14.4	11.7	10.3	9.9	9.2	8.7	9.0	8.5	8.5	8.5	8.3
87.5°	4.9	4.4	4.6	4.8	5.7	6.4	6.9	7.7	8.6	8.3	8.4
90°	2.7	4.7	6.8	8.8	11.6	15.2	18.9	22.5	26.3	25.9	25.5
92.5°	14.8	16.3	17.8	19.2	20.4	21.2	22.1	22.9	23.8	23.9	23.9
95°	40.6	42.3	43.9	45.6	46.7	47.0	47.3	47.7	48.0	48.0	48.0
97.5°	72.6	74.1	75.5	77.1	78.1	78.8	79.4	80.0	80.6	80.6	80.6
100°	96.5	97.9	99.2	100.5	101.4	101.9	102.4	102.9	103.4	103.4	103.4
102.5°	121.4	122.5	123.5	124.6	125.4	126.1	126.7	127.3	127.9	128.2	128.3
105°	161.6	162.1	162.6	163.1	163.5	163.9	164.2	164.5	164.9	165.2	165.5
107.5°	202.9	203.7	204.4	205.1	205.5	205.5	205.5	205.5	205.5	205.6	205.7
110°	229.5	230.6	231.6	232.6	233.1	233.1	233.1	233.1	233.1	233.1	233.1



TEST NUMBER: P331770-840

CATALOG NUMBER: S122RDIW-S290D710U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	258.3	259.3	260.3	261.4	261.8	261.7	261.5	261.4	261.3	260.8	260.4
115°	300.7	301.7	302.8	303.8	304.1	303.8	303.4	303.1	302.8	302.6	302.5
117.5°	343.4	344.7	346.0	347.3	347.5	346.6	345.7	344.8	343.9	343.5	343.1
120°	371.5	372.8	374.2	375.5	375.5	374.2	372.8	371.5	370.2	370.2	370.2
122.5°	397.6	399.2	400.7	402.3	402.7	401.7	400.8	399.9	399.0	398.6	398.2
125°	437.7	439.1	440.6	442.1	442.6	442.1	441.6	441.1	440.6	440.1	439.6
127.5°	477.2	479.1	480.9	482.8	483.5	482.9	482.3	481.7	481.1	480.5	479.9
130°	502.0	504.1	506.3	508.5	509.4	509.1	508.8	508.4	508.1	507.8	507.5
132.5°	529.2	531.0	532.7	534.4	535.4	535.4	535.5	535.6	535.6	534.9	534.2
135°	566.1	567.9	569.8	571.6	572.7	573.0	573.4	573.7	574.0	573.8	573.7
137.5°	604.6	606.1	607.6	609.0	610.1	610.5	611.0	611.4	611.8	611.7	611.5
140°	627.9	629.4	631.0	632.5	633.6	634.5	635.3	636.1	636.9	636.9	636.9
142.5°	652.0	653.5	655.0	656.4	657.5	658.0	658.6	659.1	659.7	659.8	660.0
145°	686.1	687.2	688.4	689.6	690.6	691.7	692.7	693.7	694.7	694.8	695.0
147.5°	717.0	718.4	719.8	721.2	722.3	723.0	723.6	724.3	725.0	725.3	725.7
150°	737.6	738.6	739.6	740.6	741.4	742.1	742.8	743.5	744.2	744.7	745.1
152.5°	756.2	757.2	758.2	759.2	760.1	760.9	761.7	762.5	763.4	764.0	764.6
155°	783.6	784.1	784.6	785.1	785.6	786.1	786.6	787.1	787.6	788.4	789.2
157.5°	807.3	807.6	807.9	808.3	808.6	808.9	809.2	809.5	809.8	810.9	812.0
160°	821.6	821.9	822.3	822.6	822.9	823.0	823.2	823.3	823.5	824.6	825.6
162.5°	834.6	834.7	834.7	834.8	834.9	835.1	835.3	835.4	835.6	836.7	837.8
165°	851.8	851.7	851.5	851.4	851.3	851.3	851.3	851.3	851.3	852.4	853.6
167.5°	866.3	865.8	865.3	864.7	864.4	864.4	864.3	864.3	864.3	865.5	866.7
170°	874.0	873.5	873.0	872.5	872.2	872.0	871.8	871.7	871.5	872.7	873.8
172.5°	879.4	878.9	878.4	877.9	877.6	877.4	877.3	877.1	876.9	878.1	879.3
175°	886.1	885.6	885.0	884.5	884.1	883.7	883.4	883.1	882.7	883.9	885.0
177.5°	888.8	888.4	888.0	887.6	887.3	887.0	886.8	886.5	886.2	887.0	887.8
180°	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0	888.0



TEST NUMBER: P331770-840

CATALOG NUMBER: S122RDIW-S290D710U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	660.1	660.1	660.1	660.1	660.1	660.1	660.1
2.5°	683.3	685.7	686.8	686.8	688.1	687.5	687.0
5°	722.6	726.9	727.9	732.0	735.0	734.1	734.5
7.5°	761.6	768.6	775.6	778.7	779.2	781.0	781.7
10°	785.7	791.4	802.1	800.6	808.6	813.2	805.7
12.5°	808.8	816.6	824.0	826.1	830.6	832.1	829.1
15°	829.7	833.8	834.2	833.1	834.6	833.3	829.0
17.5°	810.2	803.4	789.9	783.5	778.4	770.8	767.8
20°	777.9	758.1	735.2	726.0	715.3	694.2	699.2
22.5°	708.1	685.7	662.7	635.9	623.1	603.1	601.9
25°	599.7	560.9	518.2	488.4	470.9	451.0	442.2
27.5°	466.3	417.4	382.4	364.8	348.6	332.9	332.1
30°	378.5	341.8	314.8	299.6	289.7	283.1	284.5
32.5°	319.0	293.9	275.6	263.1	255.8	250.7	250.6
35°	260.8	243.6	231.9	226.6	221.4	217.7	217.9
37.5°	223.2	212.9	206.3	200.6	197.2	195.4	194.4
40°	203.9	195.4	190.4	186.9	184.2	181.7	181.2
42.5°	188.7	181.7	176.6	173.9	171.4	169.6	169.2
45°	167.4	161.7	157.1	154.1	153.0	151.4	151.4
47.5°	149.0	143.3	139.8	137.8	135.9	134.8	134.8
50°	136.5	132.1	129.0	127.7	126.1	125.5	125.2
52.5°	125.3	122.0	119.8	119.0	118.3	117.4	117.5
55°	110.1	108.3	107.3	106.6	105.5	104.1	105.0
57.5°	97.4	95.7	93.3	91.1	90.1	89.1	89.5
60°	88.4	85.1	81.9	79.4	78.7	76.6	76.6
62.5°	77.0	72.4	68.5	67.1	66.3	65.4	65.2
65°	59.2	57.4	56.5	55.5	55.0	55.0	54.6
67.5°	49.1	48.3	47.3	47.1	46.7	46.5	46.4
70°	43.3	42.4	42.0	41.7	41.3	41.5	40.8
72.5°	37.9	37.2	37.1	36.5	36.2	36.2	35.6
75°	29.8	29.8	29.6	29.4	28.9	28.7	28.9
77.5°	22.9	23.0	22.6	22.5	22.5	22.5	22.3
80°	18.4	18.6	18.4	18.1	17.9	18.1	17.9
82.5°	14.5	14.1	14.1	14.0	14.0	13.9	13.8
85°	8.3	8.5	8.3	8.1	8.1	8.1	8.3
87.5°	8.2	8.1	8.1	8.1	8.2	8.2	8.1
90°	25.2	24.9	24.8	24.9	25.1	25.3	25.4
92.5°	24.0	24.1	24.1	24.1	24.2	24.2	24.2
95°	48.0	48.0	47.8	47.5	47.2	46.8	46.5
97.5°	80.6	80.6	80.6	80.6	80.6	80.5	80.5
100°	103.4	103.4	103.3	103.2	103.0	102.8	102.7
102.5°	128.4	128.6	128.6	128.4	128.2	128.1	127.8
105°	165.8	166.2	166.3	166.3	166.3	166.3	166.3
107.5°	205.9	206.0	205.7	204.9	204.2	203.4	202.7
110°	233.1	233.1	232.8	232.3	231.8	231.3	230.9



TEST NUMBER: P331770-840

CATALOG NUMBER: S122RDIW-S290D710U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	260.0	259.6	259.2	258.9	258.5	258.1	257.8
115°	302.3	302.1	301.7	301.2	300.7	300.2	299.7
117.5°	342.6	342.2	341.7	341.2	340.7	340.2	339.7
120°	370.2	370.2	369.9	369.4	368.9	368.4	367.9
122.5°	397.8	397.4	397.0	396.6	396.3	395.9	395.6
125°	439.1	438.6	438.3	438.2	438.0	437.8	437.7
127.5°	479.3	478.7	478.2	477.6	477.1	476.6	476.1
130°	507.1	506.8	506.2	505.5	504.9	504.2	503.6
132.5°	533.4	532.7	532.1	531.6	531.0	530.5	530.0
135°	573.5	573.4	573.0	572.5	572.0	571.5	571.0
137.5°	611.4	611.3	610.9	610.2	609.6	608.8	608.1
140°	636.9	636.9	636.6	636.0	635.3	634.6	634.0
142.5°	660.1	660.2	660.0	659.3	658.6	658.0	657.3
145°	695.2	695.3	695.1	694.4	693.8	693.1	692.5
147.5°	726.0	726.4	726.3	725.7	725.0	724.4	723.8
150°	745.6	746.1	746.1	745.6	745.1	744.7	744.2
152.5°	765.2	765.9	765.9	765.2	764.6	764.0	763.4
155°	790.1	790.9	791.1	790.6	790.1	789.6	789.1
157.5°	813.1	814.3	814.5	813.6	812.8	812.0	811.2
160°	826.6	827.6	827.7	827.1	826.4	825.8	825.1
162.5°	839.0	840.1	840.2	839.4	838.7	837.9	837.1
165°	854.7	856.0	856.2	855.3	854.4	853.6	852.8
167.5°	867.8	869.0	869.1	868.3	867.4	866.6	865.7
170°	875.0	876.2	876.3	875.3	874.2	873.2	872.2
172.5°	880.4	881.6	881.6	880.7	879.7	878.7	877.7
175°	886.3	887.5	887.5	886.5	885.6	884.5	883.5
177.5°	888.6	889.4	889.4	888.6	887.8	887.0	886.2
180°	888.0	888.0	888.0	888.0	888.0	888.0	888.0

(END OF REPORT)