

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331484-940

Luminaire Tested: **S122DIW-S290D1240U940-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331484-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIW-S290D1240U940-4F0-1E-UDD-A1  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1240 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4999.4 lumens  
Efficiency: N/A  
Efficacy: 107.3 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 46.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331484-940

CATALOG NUMBER: S122DIW-S290D1240U940-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot



— 0°-180°    - - 45°-225°    - - - 90°-270°    - - - 135°-315°



TEST NUMBER: P331484-940

CATALOG NUMBER: S122DIW-S290D1240U940-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	69	69	69	49	49	49	32	32	32	23
1	92	88	84	81	82	78	75	73	60	58	56	44	42	41	28	28	27	20
2	84	77	71	66	74	69	64	60	53	50	47	38	36	35	25	24	23	17
3	77	68	61	55	68	61	55	50	47	43	40	34	32	30	22	21	20	15
4	70	60	53	47	62	54	47	43	42	37	34	31	28	25	20	19	17	13
5	64	53	46	40	57	48	41	36	37	33	29	27	24	22	18	17	15	11
6	59	48	40	35	52	43	36	32	34	29	25	25	22	19	17	15	13	10
7	55	43	36	30	48	39	32	28	30	26	22	23	19	17	15	13	12	9
8	51	39	32	27	45	35	29	24	28	23	20	21	17	15	14	12	11	8
9	47	35	28	24	42	32	26	22	25	21	18	19	16	14	13	11	10	7
10	44	32	26	21	39	29	23	19	23	19	16	17	14	12	12	10	9	7

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	8510	8510	8510	8510
5°	9540	8566	7590	8566
10°	10932	8496	6568	8496
15°	12094	8339	5804	8339
20°	11911	8172	5290	8172
25°	10739	7949	4965	7949
30°	8874	7594	4728	7594
35°	6467	7222	4559	7222
40°	5166	6785	4466	6785
45°	4514	6277	4338	6277
50°	4245	5785	4253	5785
55°	3910	5286	4138	5286
60°	3584	4753	3965	4753
65°	3266	4279	3790	4279
70°	2965	3814	3541	3814
75°	2633	3300	3132	3300
80°	2259	2724	2520	2724
85°	2038	2038	1501	2038



TEST NUMBER: P331484-940

CATALOG NUMBER: S122DIW-S290D1240U940-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	50.2	1.0
10°-20°	145.9	2.9
20°-30°	211.8	4.2
30°-40°	223.5	4.5
40°-50°	197.9	4.0
50°-60°	157.9	3.2
60°-70°	107.3	2.1
70°-80°	55.0	1.1
80°-90°	18.7	0.4
90°-100°	86.8	1.7
100°-110°	269.6	5.4
110°-120°	460.9	9.2
120°-130°	606.1	12.1
130°-140°	680.3	13.6
140°-150°	667.1	13.3
150°-160°	559.5	11.2
160°-170°	371.1	7.4
170°-180°	129.7	2.6
0°-30°	407.9	8.2
0°-40°	631.4	12.6
0°-60°	987.2	19.7
0°-90°	1168.3	23.4
90°-120°	817.4	16.3
90°-150°	2770.9	55.4
90°-180°	3831.0	76.6
0°-180°	4999.4	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	527	527	527	527	527	
5°	589	528	468	528	589	59
15°	724	499	347	499	724	200
25°	603	446	279	446	603	272
35°	328	366	231	366	328	213
45°	198	275	190	275	198	155
55°	139	188	147	188	139	125
65°	86	112	99	112	86	85
75°	42	53	50	53	42	45
85°	11	11	8	11	11	13
90°	39	1	39	1	39	18
95°	72	60	72	60	72	80
105°	257	249	257	249	257	270
115°	462	462	462	462	462	457
125°	675	673	675	673	675	602
135°	881	871	881	871	881	678
145°	1068	1057	1068	1057	1068	667
155°	1218	1208	1218	1208	1218	560
165°	1316	1315	1316	1315	1316	371
175°	1363	1368	1363	1368	1363	130
180°	1370	1370	1370	1370	1370	



TEST NUMBER: P331484-940

CATALOG NUMBER: S122DIW-S290D1240U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1
2.5°	551.3	551.5	551.9	549.3	548.9	548.9	546.7	544.7	542.4	539.4	539.8
5°	588.6	590.8	591.7	589.2	585.6	585.2	581.8	576.1	570.8	566.6	563.6
7.5°	633.1	634.0	632.0	628.8	626.2	621.3	614.8	608.6	599.8	591.7	585.8
10°	666.8	668.1	664.6	660.0	656.1	650.4	641.1	631.6	620.1	608.9	600.0
12.5°	692.4	695.4	691.0	690.5	683.9	676.0	664.9	660.1	643.9	628.4	618.8
15°	723.5	723.4	723.8	719.9	715.1	713.8	702.1	689.3	666.5	657.3	641.5
17.5°	714.5	717.6	719.1	719.0	718.9	718.1	714.3	706.3	694.8	680.0	661.8
20°	693.2	697.2	697.9	702.5	705.2	708.6	710.0	707.8	700.7	688.3	672.5
22.5°	660.1	661.3	663.2	670.4	676.1	684.7	689.2	696.8	694.0	688.0	674.8
25°	602.8	600.8	607.9	611.5	624.7	638.5	648.5	659.3	669.1	674.9	671.1
27.5°	534.0	531.0	541.6	551.3	562.0	576.9	592.4	610.6	625.8	644.9	651.4
30°	476.0	477.9	487.9	498.3	514.5	535.6	553.0	573.0	594.8	616.0	630.8
32.5°	413.5	420.4	426.9	442.7	457.0	480.5	506.0	531.1	558.1	582.3	605.2
35°	328.1	336.3	345.2	356.7	376.7	400.0	425.0	458.8	495.7	528.7	555.8
37.5°	276.3	274.9	280.0	288.4	304.6	323.4	352.1	385.5	428.9	467.7	506.0
40°	245.1	244.3	247.9	255.7	268.0	281.8	306.9	336.3	376.6	424.0	469.6
42.5°	223.7	224.2	226.2	231.7	240.1	251.5	270.3	295.2	332.2	376.8	425.8
45°	197.7	199.1	201.3	204.0	208.8	218.2	228.7	246.6	275.7	313.0	361.1
47.5°	179.0	179.1	181.3	183.6	186.5	191.7	200.4	211.5	232.1	262.4	303.9
50°	169.0	167.6	169.2	170.9	174.0	177.6	183.3	193.9	207.6	232.1	266.8
52.5°	156.6	156.7	158.1	158.8	161.5	165.1	170.3	177.6	190.1	209.3	237.7
55°	138.9	140.0	140.8	142.0	144.5	147.0	151.1	156.0	165.7	180.0	201.2
57.5°	122.3	122.7	123.5	125.8	127.3	129.7	133.6	138.0	144.4	155.0	170.9
60°	111.0	111.0	112.6	113.6	115.7	118.1	121.1	125.4	131.1	139.7	152.6
62.5°	100.7	100.5	101.1	102.8	104.3	106.6	109.6	113.2	118.6	126.4	136.8
65°	85.5	85.1	86.3	86.7	88.3	90.5	93.0	96.8	101.1	106.7	116.1
67.5°	70.9	71.4	72.1	72.8	73.7	76.1	77.7	80.3	84.0	88.7	95.0
70°	62.8	62.8	62.8	63.4	64.6	65.8	67.4	69.6	73.1	77.1	82.8
72.5°	53.7	54.4	55.0	54.7	56.2	56.9	58.9	60.1	63.4	66.0	71.0
75°	42.2	42.2	42.2	43.2	43.8	44.3	45.6	46.8	48.4	51.6	54.3
77.5°	31.5	31.4	31.6	31.8	32.5	33.2	33.5	34.6	36.1	37.6	39.9
80°	24.3	24.7	24.9	25.3	25.3	25.7	25.9	27.4	28.4	29.3	30.8
82.5°	18.8	18.9	18.9	19.0	19.2	19.4	20.0	20.4	20.8	21.6	22.6
85°	11.0	10.7	10.7	11.1	11.0	11.0	11.3	11.8	11.8	11.9	12.6
87.5°	12.0	12.0	12.1	11.9	11.9	12.0	12.1	12.1	12.4	12.7	11.7
90°	39.3	39.1	38.8	38.5	38.3	38.4	39.0	39.4	39.9	40.5	34.8
92.5°	37.5	37.5	37.4	37.3	37.3	37.2	37.1	37.0	36.8	36.7	35.4
95°	71.7	72.2	72.7	73.2	73.7	74.0	74.0	74.0	74.0	74.0	73.5
97.5°	124.2	124.2	124.3	124.3	124.4	124.4	124.4	124.4	124.4	124.4	123.4
100°	158.4	158.6	158.9	159.2	159.4	159.5	159.5	159.5	159.5	159.5	158.8
102.5°	197.2	197.5	197.8	198.0	198.3	198.3	198.1	197.9	197.7	197.5	196.5
105°	256.7	256.7	256.7	256.7	256.7	256.5	255.9	255.4	254.9	254.4	253.9
107.5°	312.6	313.8	315.0	316.2	317.4	317.9	317.6	317.4	317.3	317.0	317.0
110°	356.1	356.9	357.7	358.5	359.2	359.6	359.6	359.6	359.6	359.6	359.6



TEST NUMBER: P331484-940

CATALOG NUMBER: S122DIW-S290D1240U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	397.7	398.3	398.9	399.4	400.0	400.6	401.2	401.8	402.4	403.1	403.2
115°	462.5	463.2	464.0	464.8	465.6	466.1	466.4	466.6	466.9	467.1	467.6
117.5°	524.2	525.0	525.8	526.6	527.4	528.0	528.6	529.2	529.9	530.5	531.9
120°	567.8	568.5	569.3	570.0	570.8	571.1	571.1	571.1	571.1	571.1	573.2
122.5°	610.3	610.8	611.4	612.0	612.5	613.1	613.8	614.4	614.9	615.5	617.0
125°	675.2	675.5	675.7	676.0	676.3	676.8	677.5	678.3	679.1	679.8	680.6
127.5°	734.4	735.3	736.1	736.9	737.7	738.6	739.5	740.5	741.4	742.3	743.2
130°	776.9	778.0	779.1	780.1	781.1	781.9	782.4	782.9	783.4	783.9	784.4
132.5°	817.7	818.5	819.3	820.2	821.0	822.0	823.0	824.2	825.4	826.4	826.3
135°	881.0	881.8	882.6	883.3	884.1	884.7	884.9	885.2	885.4	885.6	885.2
137.5°	938.4	939.4	940.5	941.5	942.5	943.2	943.3	943.5	943.8	944.0	943.3
140°	978.2	979.2	980.3	981.2	982.3	982.8	982.8	982.8	982.8	982.8	981.5
142.5°	1014.2	1015.3	1016.3	1017.4	1018.3	1018.8	1018.6	1018.3	1018.2	1018.0	1017.1
145°	1068.4	1069.4	1070.4	1071.5	1072.5	1072.8	1072.6	1072.4	1072.1	1071.8	1070.3
147.5°	1116.7	1117.7	1118.7	1119.6	1120.6	1120.8	1120.3	1119.6	1119.1	1118.6	1117.5
150°	1148.2	1148.9	1149.7	1150.5	1151.2	1151.2	1150.5	1149.7	1148.9	1148.2	1147.1
152.5°	1177.8	1178.8	1179.7	1180.6	1181.6	1181.6	1180.6	1179.7	1178.8	1177.8	1176.5
155°	1217.5	1218.3	1219.1	1219.9	1220.6	1220.3	1219.1	1217.8	1216.5	1215.2	1214.4
157.5°	1251.7	1252.9	1254.2	1255.4	1256.7	1256.4	1254.6	1252.9	1251.2	1249.5	1248.9
160°	1273.0	1274.1	1275.1	1276.1	1277.1	1276.8	1275.3	1273.8	1272.2	1270.7	1270.4
162.5°	1291.6	1292.7	1294.0	1295.2	1296.5	1296.2	1294.4	1292.7	1290.9	1289.2	1289.0
165°	1315.8	1317.1	1318.4	1319.6	1320.9	1320.7	1318.8	1317.1	1315.3	1313.5	1313.5
167.5°	1335.7	1337.0	1338.4	1339.7	1341.0	1340.8	1339.0	1337.2	1335.4	1333.6	1333.6
170°	1345.9	1347.4	1349.0	1350.5	1352.0	1351.9	1350.1	1348.3	1346.5	1344.7	1345.0
172.5°	1354.2	1355.8	1357.3	1358.8	1360.3	1360.2	1358.4	1356.6	1354.9	1353.0	1353.3
175°	1363.2	1364.8	1366.3	1367.8	1369.4	1369.2	1367.4	1365.7	1363.9	1362.0	1362.5
177.5°	1367.3	1368.6	1369.8	1371.1	1372.3	1372.3	1371.1	1369.8	1368.6	1367.3	1367.8
180°	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1



TEST NUMBER: P331484-940

CATALOG NUMBER: S122DIW-S290D1240U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1
2.5°	540.8	539.6	538.8	535.8	533.2	530.7	529.9	530.1	526.6	523.2	521.7
5°	562.0	557.9	554.0	548.6	542.1	534.9	531.4	528.5	521.4	513.7	509.3
7.5°	580.8	575.0	567.6	557.3	547.9	536.7	529.6	523.3	513.0	502.1	495.4
10°	592.3	584.4	574.9	562.3	550.8	537.2	527.7	518.2	506.0	493.0	484.9
12.5°	602.2	591.6	582.2	566.1	552.4	535.4	524.1	510.7	497.9	482.5	474.6
15°	625.7	606.1	588.3	570.0	553.2	529.5	516.9	498.9	482.1	463.1	454.0
17.5°	643.9	621.8	593.8	570.6	551.0	524.7	506.3	484.7	464.8	443.1	430.7
20°	654.2	628.9	598.8	571.2	547.8	517.7	497.7	475.6	452.4	427.8	414.5
22.5°	660.4	633.8	604.0	568.8	541.3	512.1	486.9	462.6	439.1	412.6	398.6
25°	662.4	638.1	606.5	566.8	533.2	500.2	469.8	446.2	417.7	393.0	372.6
27.5°	652.7	635.3	604.9	562.9	523.8	485.2	451.3	424.7	394.6	367.7	347.1
30°	640.9	630.8	601.2	559.1	516.3	474.8	437.6	407.3	377.4	350.3	329.1
32.5°	622.6	620.5	594.4	553.6	508.4	461.7	423.1	392.6	359.4	332.7	312.6
35°	586.7	596.4	580.0	541.3	493.5	443.0	401.3	366.4	332.0	306.5	287.7
37.5°	538.4	562.6	558.3	523.3	473.2	422.7	376.6	340.2	307.4	281.6	263.1
40°	505.2	536.0	540.5	509.4	459.1	407.0	358.1	321.9	289.9	266.4	247.7
42.5°	469.6	505.5	517.7	492.9	443.4	390.4	341.6	304.1	272.3	249.5	233.0
45°	409.8	457.4	479.5	465.3	417.5	363.2	313.0	274.9	246.1	224.6	211.9
47.5°	353.9	405.9	435.6	430.6	388.6	334.8	285.2	248.6	220.6	203.5	192.1
50°	314.4	367.8	403.7	405.4	367.8	314.6	264.7	230.3	204.6	188.6	179.2
52.5°	280.0	331.1	370.1	378.8	344.6	293.6	246.5	212.1	189.5	174.8	166.5
55°	235.1	278.3	321.6	337.5	310.1	261.5	217.9	187.8	166.5	156.4	149.1
57.5°	195.6	231.5	271.5	289.0	272.2	230.5	189.7	163.5	146.2	137.3	131.7
60°	174.6	203.0	238.6	259.5	244.9	207.9	172.2	147.2	133.0	125.2	119.9
62.5°	155.2	180.3	210.4	229.5	221.6	186.6	154.7	132.7	120.5	113.1	109.2
65°	128.0	147.8	171.2	188.8	183.5	157.0	130.8	112.0	102.3	96.4	93.4
67.5°	105.4	119.8	135.9	151.3	147.1	128.3	107.4	92.6	85.4	80.3	78.5
70°	91.1	102.1	116.5	128.9	125.4	110.0	93.4	80.8	74.5	70.3	68.5
72.5°	77.6	86.5	97.6	107.6	105.3	92.5	78.6	69.2	64.3	60.4	58.9
75°	58.6	65.5	72.1	78.8	78.2	68.3	60.2	52.9	49.0	46.0	45.4
77.5°	43.2	47.1	51.6	55.6	54.5	48.8	42.4	38.3	35.5	33.4	33.1
80°	33.0	35.2	38.5	41.3	39.9	37.5	32.4	29.3	27.4	25.3	24.5
82.5°	24.0	26.1	28.1	29.7	28.5	26.3	23.2	21.1	19.9	18.5	18.2
85°	12.6	13.7	14.6	15.0	14.6	13.2	11.8	11.0	9.9	9.3	9.1
87.5°	10.7	9.5	8.5	7.8	6.8	6.2	4.9	3.8	4.3	4.7	5.0
90°	29.2	23.5	17.8	13.5	10.4	7.3	4.3	1.2	4.3	7.3	10.4
92.5°	34.1	32.7	31.4	29.6	27.4	25.1	22.8	20.6	22.8	25.1	27.4
95°	72.9	72.5	72.0	70.4	67.9	65.3	62.7	60.1	62.7	65.3	67.9
97.5°	122.4	121.5	120.5	118.9	116.6	114.4	112.1	109.9	112.1	114.4	116.6
100°	158.0	157.2	156.5	155.1	153.0	151.0	148.9	146.9	148.9	151.0	153.0
102.5°	195.6	194.6	193.6	192.3	190.6	189.0	187.3	185.7	187.3	189.0	190.6
105°	253.3	252.8	252.4	251.6	250.9	250.1	249.3	248.6	249.3	250.1	250.9
107.5°	317.0	317.0	317.0	316.5	315.3	314.2	313.1	311.9	313.1	314.2	315.3
110°	359.6	359.6	359.6	358.8	357.3	355.7	354.2	352.7	354.2	355.7	357.3





TEST NUMBER: P331484-940

CATALOG NUMBER: S122DIW-S290D1240U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	403.5	403.7	403.9	403.2	401.7	400.1	398.6	397.1	398.6	400.1	401.7
115°	468.1	468.7	469.1	468.7	467.1	465.6	464.0	462.5	464.0	465.6	467.1
117.5°	533.3	534.8	536.3	535.9	533.9	531.8	529.8	527.7	529.8	531.8	533.9
120°	575.3	577.4	579.4	579.4	577.4	575.3	573.2	571.1	573.2	575.3	577.4
122.5°	618.5	619.9	621.3	620.8	618.3	615.9	613.4	610.9	613.4	615.9	618.3
125°	681.4	682.2	683.0	682.2	679.8	677.5	675.2	672.9	675.2	677.5	679.8
127.5°	744.1	745.1	746.0	745.0	742.1	739.1	736.2	733.3	736.2	739.1	742.1
130°	785.0	785.5	786.0	784.5	781.2	777.9	774.5	771.2	774.5	777.9	781.2
132.5°	826.3	826.2	826.1	824.7	821.9	819.2	816.5	813.8	816.5	819.2	821.9
135°	884.7	884.1	883.6	882.0	879.1	876.3	873.4	870.7	873.4	876.3	879.1
137.5°	942.6	941.9	941.3	939.8	937.5	935.1	932.8	930.5	932.8	935.1	937.5
140°	980.3	978.9	977.7	975.9	973.6	971.3	968.9	966.6	968.9	971.3	973.6
142.5°	1016.2	1015.3	1014.4	1012.9	1010.6	1008.3	1005.9	1003.6	1005.9	1008.3	1010.6
145°	1068.7	1067.2	1065.7	1064.0	1062.2	1060.4	1058.6	1056.8	1058.6	1060.4	1062.2
147.5°	1116.5	1115.4	1114.5	1112.9	1110.7	1108.5	1106.3	1104.2	1106.3	1108.5	1110.7
150°	1146.1	1145.0	1144.1	1142.7	1141.2	1139.7	1138.1	1136.6	1138.1	1139.7	1141.2
152.5°	1175.3	1174.0	1172.8	1171.4	1169.8	1168.3	1166.8	1165.3	1166.8	1168.3	1169.8
155°	1213.6	1212.9	1212.1	1211.4	1210.6	1209.8	1209.1	1208.3	1209.1	1209.8	1210.6
157.5°	1248.5	1248.0	1247.6	1247.1	1246.6	1246.1	1245.5	1245.0	1245.5	1246.1	1246.6
160°	1270.2	1269.9	1269.7	1269.3	1268.8	1268.3	1267.7	1267.2	1267.7	1268.3	1268.8
162.5°	1288.7	1288.4	1288.2	1288.0	1287.9	1287.8	1287.7	1287.5	1287.7	1287.8	1287.9
165°	1313.5	1313.5	1313.5	1313.6	1313.8	1314.1	1314.4	1314.6	1314.4	1314.1	1313.8
167.5°	1333.7	1333.7	1333.8	1334.2	1335.0	1335.8	1336.5	1337.3	1336.5	1335.8	1335.0
170°	1345.2	1345.5	1345.8	1346.2	1347.0	1347.8	1348.5	1349.3	1348.5	1347.8	1347.0
172.5°	1353.5	1353.8	1354.1	1354.6	1355.3	1356.1	1356.9	1357.6	1356.9	1356.1	1355.3
175°	1363.1	1363.6	1364.1	1364.8	1365.5	1366.3	1367.1	1367.8	1367.1	1366.3	1365.5
177.5°	1368.2	1368.6	1369.0	1369.5	1370.1	1370.7	1371.4	1372.0	1371.4	1370.7	1370.1
180°	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1



TEST NUMBER: P331484-940

CATALOG NUMBER: S122DIW-S290D1240U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1
2.5°	520.1	519.2	515.8	514.0	511.0	508.3	506.5	507.3	507.9	507.7	507.1
5°	505.2	501.3	495.4	490.4	486.8	480.1	477.2	475.8	474.6	473.2	471.8
7.5°	487.4	481.3	473.0	465.7	459.0	450.6	445.9	443.1	440.1	436.9	434.1
10°	474.8	466.3	457.4	447.3	439.2	431.7	425.0	420.5	416.4	412.6	409.8
12.5°	461.5	451.7	440.7	426.9	417.9	407.2	406.2	398.3	392.0	389.6	386.3
15°	440.4	426.6	412.6	396.2	389.1	379.4	373.4	367.2	361.8	357.9	357.0
17.5°	416.3	398.5	384.6	372.8	361.2	351.2	345.6	340.8	336.3	331.2	330.5
20°	398.1	382.6	367.5	357.1	345.2	335.0	328.1	323.3	319.4	316.4	313.8
22.5°	380.7	363.8	349.9	338.7	326.9	318.7	313.3	308.5	305.3	302.0	299.5
25°	352.8	339.7	324.5	311.7	302.0	296.8	292.3	288.3	286.2	284.0	281.2
27.5°	328.5	313.9	299.7	289.8	281.2	276.6	273.4	270.6	268.8	267.4	265.8
30°	311.4	296.6	285.4	275.7	268.6	263.9	261.9	260.3	258.1	257.3	256.5
32.5°	294.8	281.5	272.0	263.5	256.8	253.7	251.9	250.4	248.7	247.9	246.2
35°	271.4	260.3	251.0	246.3	240.9	238.2	236.8	234.8	233.2	232.4	232.1
37.5°	249.4	239.8	233.6	227.7	225.3	223.7	221.8	220.4	219.9	219.8	219.5
40°	235.1	227.3	221.8	217.0	216.0	213.5	211.9	210.7	210.7	210.9	210.7
42.5°	222.2	215.1	210.3	206.1	204.9	203.5	201.8	201.8	202.1	202.8	202.1
45°	202.6	197.5	194.0	192.1	189.8	188.4	188.2	188.8	189.0	189.2	189.8
47.5°	184.5	181.1	178.0	175.8	174.8	174.6	174.3	175.4	176.4	176.7	177.6
50°	173.8	170.0	167.3	165.9	165.1	164.7	165.1	166.3	167.1	168.1	168.7
52.5°	161.8	159.1	157.3	156.1	155.9	156.1	156.1	157.6	158.8	159.3	159.5
55°	145.3	143.2	142.9	141.0	141.8	141.6	142.6	143.4	144.6	145.9	146.1
57.5°	128.7	127.1	126.0	126.2	126.4	127.3	128.1	129.6	130.8	132.2	132.2
60°	117.7	116.9	116.3	116.3	116.6	117.9	118.9	120.3	121.1	122.0	122.5
62.5°	107.6	106.8	106.2	106.6	107.6	108.3	109.5	110.3	111.1	111.9	112.2
65°	91.8	91.4	91.9	92.4	92.6	93.5	95.0	95.6	96.4	96.8	98.3
67.5°	77.1	77.2	77.1	77.7	78.9	79.1	80.4	81.9	82.0	82.8	83.7
70°	67.2	67.7	68.0	68.5	69.5	69.9	70.9	71.5	72.3	72.9	73.6
72.5°	58.1	58.2	58.7	58.6	59.5	60.3	61.2	61.8	62.6	63.4	63.9
75°	44.8	44.8	45.2	45.4	46.4	47.4	47.2	47.6	48.4	49.2	49.7
77.5°	32.7	32.3	32.7	32.9	33.3	34.1	34.2	34.8	35.8	35.5	35.9
80°	24.9	24.3	24.9	25.1	25.1	26.1	26.1	26.6	27.1	26.6	27.1
82.5°	17.7	17.5	17.9	18.0	18.3	18.4	18.6	18.7	19.4	19.1	19.4
85°	8.9	8.7	8.9	8.7	8.9	9.1	9.1	8.9	8.9	9.3	8.7
87.5°	5.4	6.2	7.1	8.3	9.3	10.2	9.9	9.8	9.7	9.3	9.3
90°	13.5	17.8	23.5	29.2	34.8	40.5	39.9	39.4	39.0	38.4	38.3
92.5°	29.6	31.4	32.7	34.1	35.4	36.7	36.8	37.0	37.1	37.2	37.3
95°	70.4	72.0	72.5	72.9	73.5	74.0	74.0	74.0	74.0	74.0	73.7
97.5°	118.9	120.5	121.5	122.4	123.4	124.4	124.4	124.4	124.4	124.4	124.4
100°	155.1	156.5	157.2	158.0	158.8	159.5	159.5	159.5	159.5	159.5	159.4
102.5°	192.3	193.6	194.6	195.6	196.5	197.5	197.7	197.9	198.1	198.3	198.3
105°	251.6	252.4	252.8	253.3	253.9	254.4	254.9	255.4	255.9	256.5	256.7
107.5°	316.5	317.0	317.0	317.0	317.0	317.0	317.3	317.4	317.6	317.9	317.4
110°	358.8	359.6	359.6	359.6	359.6	359.6	359.6	359.6	359.6	359.6	359.2



TEST NUMBER: P331484-940

CATALOG NUMBER: S122DIW-S290D1240U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	403.2	403.9	403.7	403.5	403.2	403.1	402.4	401.8	401.2	400.6	400.0
115°	468.7	469.1	468.7	468.1	467.6	467.1	466.9	466.6	466.4	466.1	465.6
117.5°	535.9	536.3	534.8	533.3	531.9	530.5	529.9	529.2	528.6	528.0	527.4
120°	579.4	579.4	577.4	575.3	573.2	571.1	571.1	571.1	571.1	571.1	570.8
122.5°	620.8	621.3	619.9	618.5	617.0	615.5	614.9	614.4	613.8	613.1	612.5
125°	682.2	683.0	682.2	681.4	680.6	679.8	679.1	678.3	677.5	676.8	676.3
127.5°	745.0	746.0	745.1	744.1	743.2	742.3	741.4	740.5	739.5	738.6	737.7
130°	784.5	786.0	785.5	785.0	784.4	783.9	783.4	782.9	782.4	781.9	781.1
132.5°	824.7	826.1	826.2	826.3	826.3	826.4	825.4	824.2	823.0	822.0	821.0
135°	882.0	883.6	884.1	884.7	885.2	885.6	885.4	885.2	884.9	884.7	884.1
137.5°	939.8	941.3	941.9	942.6	943.3	944.0	943.8	943.5	943.3	943.2	942.5
140°	975.9	977.7	978.9	980.3	981.5	982.8	982.8	982.8	982.8	982.8	982.3
142.5°	1012.9	1014.4	1015.3	1016.2	1017.1	1018.0	1018.2	1018.3	1018.6	1018.8	1018.3
145°	1064.0	1065.7	1067.2	1068.7	1070.3	1071.8	1072.1	1072.4	1072.6	1072.8	1072.5
147.5°	1112.9	1114.5	1115.4	1116.5	1117.5	1118.6	1119.1	1119.6	1120.3	1120.8	1120.6
150°	1142.7	1144.1	1145.0	1146.1	1147.1	1148.2	1148.9	1149.7	1150.5	1151.2	1151.2
152.5°	1171.4	1172.8	1174.0	1175.3	1176.5	1177.8	1178.8	1179.7	1180.6	1181.6	1181.6
155°	1211.4	1212.1	1212.9	1213.6	1214.4	1215.2	1216.5	1217.8	1219.1	1220.3	1220.6
157.5°	1247.1	1247.6	1248.0	1248.5	1248.9	1249.5	1251.2	1252.9	1254.6	1256.4	1256.7
160°	1269.3	1269.7	1269.9	1270.2	1270.4	1270.7	1272.2	1273.8	1275.3	1276.8	1277.1
162.5°	1288.0	1288.2	1288.4	1288.7	1289.0	1289.2	1290.9	1292.7	1294.4	1296.2	1296.5
165°	1313.6	1313.5	1313.5	1313.5	1313.5	1313.5	1315.3	1317.1	1318.8	1320.7	1320.9
167.5°	1334.2	1333.8	1333.7	1333.7	1333.6	1333.6	1335.4	1337.2	1339.0	1340.8	1341.0
170°	1346.2	1345.8	1345.5	1345.2	1345.0	1344.7	1346.5	1348.3	1350.1	1351.9	1352.0
172.5°	1354.6	1354.1	1353.8	1353.5	1353.3	1353.0	1354.9	1356.6	1358.4	1360.2	1360.3
175°	1364.8	1364.1	1363.6	1363.1	1362.5	1362.0	1363.9	1365.7	1367.4	1369.2	1369.4
177.5°	1369.5	1369.0	1368.6	1368.2	1367.8	1367.3	1368.6	1369.8	1371.1	1372.3	1372.3
180°	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1



TEST NUMBER: P331484-940

CATALOG NUMBER: S122DIW-S290D1240U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1
2.5°	505.5	505.2	505.2	503.7	505.2	505.2	505.5	507.1	507.7	507.9	507.3
5°	469.0	468.3	467.3	468.3	467.3	468.3	469.0	471.8	473.2	474.6	475.8
7.5°	432.7	430.3	430.0	427.6	430.0	430.3	432.7	434.1	436.9	440.1	443.1
10°	406.4	404.7	404.5	400.6	404.5	404.7	406.4	409.8	412.6	416.4	420.5
12.5°	386.3	382.4	383.2	380.9	383.2	382.4	386.3	386.3	389.6	392.0	398.3
15°	351.4	351.4	350.6	347.2	350.6	351.4	351.4	357.0	357.9	361.8	367.2
17.5°	326.5	326.0	324.1	325.1	324.1	326.0	326.5	330.5	331.2	336.3	340.8
20°	311.6	310.3	307.9	307.9	307.9	310.3	311.6	313.8	316.4	319.4	323.3
22.5°	297.5	297.4	294.8	295.6	294.8	297.4	297.5	299.5	302.0	305.3	308.5
25°	281.0	279.4	278.1	278.7	278.1	279.4	281.0	281.2	284.0	286.2	288.3
27.5°	265.3	264.4	264.3	262.7	264.3	264.4	265.3	265.8	267.4	268.8	270.6
30°	256.3	254.2	254.6	253.6	254.6	254.2	256.3	256.5	257.3	258.1	260.3
32.5°	245.8	245.1	244.8	243.9	244.8	245.1	245.8	246.2	247.9	248.7	250.4
35°	231.8	231.9	231.0	231.3	231.0	231.9	231.8	232.1	232.4	233.2	234.8
37.5°	219.4	220.0	219.5	219.6	219.5	220.0	219.4	219.5	219.8	219.9	220.4
40°	211.2	211.2	211.2	211.9	211.2	211.2	211.2	210.7	210.9	210.7	210.7
42.5°	203.5	203.1	202.9	202.8	202.9	203.1	203.5	202.1	202.8	202.1	201.8
45°	190.2	190.8	191.0	190.0	191.0	190.8	190.2	189.8	189.2	189.0	188.8
47.5°	178.2	178.3	178.2	179.1	178.2	178.3	178.2	177.6	176.7	176.4	175.4
50°	169.8	169.3	169.8	169.3	169.8	169.3	169.8	168.7	168.1	167.1	166.3
52.5°	160.9	161.0	160.7	160.6	160.7	161.0	160.9	159.5	159.3	158.8	157.6
55°	146.9	147.2	147.0	147.0	147.0	147.2	146.9	146.1	145.9	144.6	143.4
57.5°	132.4	132.8	133.0	132.2	133.0	132.8	132.4	132.2	132.2	130.8	129.6
60°	122.3	123.3	123.1	122.8	123.1	123.3	122.3	122.5	122.0	121.1	120.3
62.5°	113.1	113.5	113.4	113.3	113.4	113.5	113.1	112.2	111.9	111.1	110.3
65°	98.9	99.2	98.6	99.2	98.6	99.2	98.9	98.3	96.8	96.4	95.6
67.5°	83.5	83.6	84.1	84.4	84.1	83.6	83.5	83.7	82.8	82.0	81.9
70°	73.9	73.7	74.4	75.0	74.4	73.7	73.9	73.6	72.9	72.3	71.5
72.5°	63.8	64.3	64.1	64.6	64.1	64.3	63.8	63.9	63.4	62.6	61.8
75°	49.2	49.8	49.7	50.2	49.7	49.8	49.2	49.7	49.2	48.4	47.6
77.5°	35.6	35.7	35.6	35.9	35.6	35.7	35.6	35.9	35.5	35.8	34.8
80°	27.1	26.8	26.3	27.1	26.3	26.8	27.1	27.1	26.6	27.1	26.6
82.5°	18.9	19.1	18.7	18.7	18.7	19.1	18.9	19.4	19.1	19.4	18.7
85°	8.7	8.5	8.1	8.1	8.1	8.5	8.7	8.7	9.3	8.9	8.9
87.5°	9.4	9.2	9.3	9.2	9.3	9.2	9.4	9.3	9.3	9.7	9.8
90°	38.5	38.8	39.1	39.3	39.1	38.8	38.5	38.3	38.4	39.0	39.4
92.5°	37.3	37.4	37.5	37.5	37.5	37.4	37.3	37.3	37.2	37.1	37.0
95°	73.2	72.7	72.2	71.7	72.2	72.7	73.2	73.7	74.0	74.0	74.0
97.5°	124.3	124.3	124.2	124.2	124.2	124.3	124.3	124.4	124.4	124.4	124.4
100°	159.2	158.9	158.6	158.4	158.6	158.9	159.2	159.4	159.5	159.5	159.5
102.5°	198.0	197.8	197.5	197.2	197.5	197.8	198.0	198.3	198.3	198.1	197.9
105°	256.7	256.7	256.7	256.7	256.7	256.7	256.7	256.7	256.5	255.9	255.4
107.5°	316.2	315.0	313.8	312.6	313.8	315.0	316.2	317.4	317.9	317.6	317.4
110°	358.5	357.7	356.9	356.1	356.9	357.7	358.5	359.2	359.6	359.6	359.6



TEST NUMBER: P331484-940

CATALOG NUMBER: S122DIW-S290D1240U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	399.4	398.9	398.3	397.7	398.3	398.9	399.4	400.0	400.6	401.2	401.8
115°	464.8	464.0	463.2	462.5	463.2	464.0	464.8	465.6	466.1	466.4	466.6
117.5°	526.6	525.8	525.0	524.2	525.0	525.8	526.6	527.4	528.0	528.6	529.2
120°	570.0	569.3	568.5	567.8	568.5	569.3	570.0	570.8	571.1	571.1	571.1
122.5°	612.0	611.4	610.8	610.3	610.8	611.4	612.0	612.5	613.1	613.8	614.4
125°	676.0	675.7	675.5	675.2	675.5	675.7	676.0	676.3	676.8	677.5	678.3
127.5°	736.9	736.1	735.3	734.4	735.3	736.1	736.9	737.7	738.6	739.5	740.5
130°	780.1	779.1	778.0	776.9	778.0	779.1	780.1	781.1	781.9	782.4	782.9
132.5°	820.2	819.3	818.5	817.7	818.5	819.3	820.2	821.0	822.0	823.0	824.2
135°	883.3	882.6	881.8	881.0	881.8	882.6	883.3	884.1	884.7	884.9	885.2
137.5°	941.5	940.5	939.4	938.4	939.4	940.5	941.5	942.5	943.2	943.3	943.5
140°	981.2	980.3	979.2	978.2	979.2	980.3	981.2	982.3	982.8	982.8	982.8
142.5°	1017.4	1016.3	1015.3	1014.2	1015.3	1016.3	1017.4	1018.3	1018.8	1018.6	1018.3
145°	1071.5	1070.4	1069.4	1068.4	1069.4	1070.4	1071.5	1072.5	1072.8	1072.6	1072.4
147.5°	1119.6	1118.7	1117.7	1116.7	1117.7	1118.7	1119.6	1120.6	1120.8	1120.3	1119.6
150°	1150.5	1149.7	1148.9	1148.2	1148.9	1149.7	1150.5	1151.2	1151.2	1150.5	1149.7
152.5°	1180.6	1179.7	1178.8	1177.8	1178.8	1179.7	1180.6	1181.6	1181.6	1180.6	1179.7
155°	1219.9	1219.1	1218.3	1217.5	1218.3	1219.1	1219.9	1220.6	1220.3	1219.1	1217.8
157.5°	1255.4	1254.2	1252.9	1251.7	1252.9	1254.2	1255.4	1256.7	1256.4	1254.6	1252.9
160°	1276.1	1275.1	1274.1	1273.0	1274.1	1275.1	1276.1	1277.1	1276.8	1275.3	1273.8
162.5°	1295.2	1294.0	1292.7	1291.6	1292.7	1294.0	1295.2	1296.5	1296.2	1294.4	1292.7
165°	1319.6	1318.4	1317.1	1315.8	1317.1	1318.4	1319.6	1320.9	1320.7	1318.8	1317.1
167.5°	1339.7	1338.4	1337.0	1335.7	1337.0	1338.4	1339.7	1341.0	1340.8	1339.0	1337.2
170°	1350.5	1349.0	1347.4	1345.9	1347.4	1349.0	1350.5	1352.0	1351.9	1350.1	1348.3
172.5°	1358.8	1357.3	1355.8	1354.2	1355.8	1357.3	1358.8	1360.3	1360.2	1358.4	1356.6
175°	1367.8	1366.3	1364.8	1363.2	1364.8	1366.3	1367.8	1369.4	1369.2	1367.4	1365.7
177.5°	1371.1	1369.8	1368.6	1367.3	1368.6	1369.8	1371.1	1372.3	1372.3	1371.1	1369.8
180°	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1



TEST NUMBER: P331484-940

CATALOG NUMBER: S122DIW-S290D1240U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1
2.5°	506.5	508.3	511.0	514.0	515.8	519.2	520.1	521.7	523.2	526.6	530.1
5°	477.2	480.1	486.8	490.4	495.4	501.3	505.2	509.3	513.7	521.4	528.5
7.5°	445.9	450.6	459.0	465.7	473.0	481.3	487.4	495.4	502.1	513.0	523.3
10°	425.0	431.7	439.2	447.3	457.4	466.3	474.8	484.9	493.0	506.0	518.2
12.5°	406.2	407.2	417.9	426.9	440.7	451.7	461.5	474.6	482.5	497.9	510.7
15°	373.4	379.4	389.1	396.2	412.6	426.6	440.4	454.0	463.1	482.1	498.9
17.5°	345.6	351.2	361.2	372.8	384.6	398.5	416.3	430.7	443.1	464.8	484.7
20°	328.1	335.0	345.2	357.1	367.5	382.6	398.1	414.5	427.8	452.4	475.6
22.5°	313.3	318.7	326.9	338.7	349.9	363.8	380.7	398.6	412.6	439.1	462.6
25°	292.3	296.8	302.0	311.7	324.5	339.7	352.8	372.6	393.0	417.7	446.2
27.5°	273.4	276.6	281.2	289.8	299.7	313.9	328.5	347.1	367.7	394.6	424.7
30°	261.9	263.9	268.6	275.7	285.4	296.6	311.4	329.1	350.3	377.4	407.3
32.5°	251.9	253.7	256.8	263.5	272.0	281.5	294.8	312.6	332.7	359.4	392.6
35°	236.8	238.2	240.9	246.3	251.0	260.3	271.4	287.7	306.5	332.0	366.4
37.5°	221.8	223.7	225.3	227.7	233.6	239.8	249.4	263.1	281.6	307.4	340.2
40°	211.9	213.5	216.0	217.0	221.8	227.3	235.1	247.7	266.4	289.9	321.9
42.5°	201.8	203.5	204.9	206.1	210.3	215.1	222.2	233.0	249.5	272.3	304.1
45°	188.2	188.4	189.8	192.1	194.0	197.5	202.6	211.9	224.6	246.1	274.9
47.5°	174.3	174.6	174.8	175.8	178.0	181.1	184.5	192.1	203.5	220.6	248.6
50°	165.1	164.7	165.1	165.9	167.3	170.0	173.8	179.2	188.6	204.6	230.3
52.5°	156.1	156.1	155.9	156.1	157.3	159.1	161.8	166.5	174.8	189.5	212.1
55°	142.6	141.6	141.8	141.0	142.9	143.2	145.3	149.1	156.4	166.5	187.8
57.5°	128.1	127.3	126.4	126.2	126.0	127.1	128.7	131.7	137.3	146.2	163.5
60°	118.9	117.9	116.6	116.3	116.3	116.9	117.7	119.9	125.2	133.0	147.2
62.5°	109.5	108.3	107.6	106.6	106.2	106.8	107.6	109.2	113.1	120.5	132.7
65°	95.0	93.5	92.6	92.4	91.9	91.4	91.8	93.4	96.4	102.3	112.0
67.5°	80.4	79.1	78.9	77.7	77.1	77.2	77.1	78.5	80.3	85.4	92.6
70°	70.9	69.9	69.5	68.5	68.0	67.7	67.2	68.5	70.3	74.5	80.8
72.5°	61.2	60.3	59.5	58.6	58.7	58.2	58.1	58.9	60.4	64.3	69.2
75°	47.2	47.4	46.4	45.4	45.2	44.8	44.8	45.4	46.0	49.0	52.9
77.5°	34.2	34.1	33.3	32.9	32.7	32.3	32.7	33.1	33.4	35.5	38.3
80°	26.1	26.1	25.1	25.1	24.9	24.3	24.9	24.5	25.3	27.4	29.3
82.5°	18.6	18.4	18.3	18.0	17.9	17.5	17.7	18.2	18.5	19.9	21.1
85°	9.1	9.1	8.9	8.7	8.9	8.7	8.9	9.1	9.3	9.9	11.0
87.5°	9.9	10.2	9.3	8.3	7.1	6.2	5.4	5.0	4.7	4.3	3.8
90°	39.9	40.5	34.8	29.2	23.5	17.8	13.5	10.4	7.3	4.3	1.2
92.5°	36.8	36.7	35.4	34.1	32.7	31.4	29.6	27.4	25.1	22.8	20.6
95°	74.0	74.0	73.5	72.9	72.5	72.0	70.4	67.9	65.3	62.7	60.1
97.5°	124.4	124.4	123.4	122.4	121.5	120.5	118.9	116.6	114.4	112.1	109.9
100°	159.5	159.5	158.8	158.0	157.2	156.5	155.1	153.0	151.0	148.9	146.9
102.5°	197.7	197.5	196.5	195.6	194.6	193.6	192.3	190.6	189.0	187.3	185.7
105°	254.9	254.4	253.9	253.3	252.8	252.4	251.6	250.9	250.1	249.3	248.6
107.5°	317.3	317.0	317.0	317.0	317.0	317.0	316.5	315.3	314.2	313.1	311.9
110°	359.6	359.6	359.6	359.6	359.6	359.6	358.8	357.3	355.7	354.2	352.7



TEST NUMBER: P331484-940

CATALOG NUMBER: S122DIW-S290D1240U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	402.4	403.1	403.2	403.5	403.7	403.9	403.2	401.7	400.1	398.6	397.1
115°	466.9	467.1	467.6	468.1	468.7	469.1	468.7	467.1	465.6	464.0	462.5
117.5°	529.9	530.5	531.9	533.3	534.8	536.3	535.9	533.9	531.8	529.8	527.7
120°	571.1	571.1	573.2	575.3	577.4	579.4	579.4	577.4	575.3	573.2	571.1
122.5°	614.9	615.5	617.0	618.5	619.9	621.3	620.8	618.3	615.9	613.4	610.9
125°	679.1	679.8	680.6	681.4	682.2	683.0	682.2	679.8	677.5	675.2	672.9
127.5°	741.4	742.3	743.2	744.1	745.1	746.0	745.0	742.1	739.1	736.2	733.3
130°	783.4	783.9	784.4	785.0	785.5	786.0	784.5	781.2	777.9	774.5	771.2
132.5°	825.4	826.4	826.3	826.3	826.2	826.1	824.7	821.9	819.2	816.5	813.8
135°	885.4	885.6	885.2	884.7	884.1	883.6	882.0	879.1	876.3	873.4	870.7
137.5°	943.8	944.0	943.3	942.6	941.9	941.3	939.8	937.5	935.1	932.8	930.5
140°	982.8	982.8	981.5	980.3	978.9	977.7	975.9	973.6	971.3	968.9	966.6
142.5°	1018.2	1018.0	1017.1	1016.2	1015.3	1014.4	1012.9	1010.6	1008.3	1005.9	1003.6
145°	1072.1	1071.8	1070.3	1068.7	1067.2	1065.7	1064.0	1062.2	1060.4	1058.6	1056.8
147.5°	1119.1	1118.6	1117.5	1116.5	1115.4	1114.5	1112.9	1110.7	1108.5	1106.3	1104.2
150°	1148.9	1148.2	1147.1	1146.1	1145.0	1144.1	1142.7	1141.2	1139.7	1138.1	1136.6
152.5°	1178.8	1177.8	1176.5	1175.3	1174.0	1172.8	1171.4	1169.8	1168.3	1166.8	1165.3
155°	1216.5	1215.2	1214.4	1213.6	1212.9	1212.1	1211.4	1210.6	1209.8	1209.1	1208.3
157.5°	1251.2	1249.5	1248.9	1248.5	1248.0	1247.6	1247.1	1246.6	1246.1	1245.5	1245.0
160°	1272.2	1270.7	1270.4	1270.2	1269.9	1269.7	1269.3	1268.8	1268.3	1267.7	1267.2
162.5°	1290.9	1289.2	1289.0	1288.7	1288.4	1288.2	1288.0	1287.9	1287.8	1287.7	1287.5
165°	1315.3	1313.5	1313.5	1313.5	1313.5	1313.5	1313.6	1313.8	1314.1	1314.4	1314.6
167.5°	1335.4	1333.6	1333.6	1333.7	1333.7	1333.8	1334.2	1335.0	1335.8	1336.5	1337.3
170°	1346.5	1344.7	1345.0	1345.2	1345.5	1345.8	1346.2	1347.0	1347.8	1348.5	1349.3
172.5°	1354.9	1353.0	1353.3	1353.5	1353.8	1354.1	1354.6	1355.3	1356.1	1356.9	1357.6
175°	1363.9	1362.0	1362.5	1363.1	1363.6	1364.1	1364.8	1365.5	1366.3	1367.1	1367.8
177.5°	1368.6	1367.3	1367.8	1368.2	1368.6	1369.0	1369.5	1370.1	1370.7	1371.4	1372.0
180°	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1



TEST NUMBER: P331484-940

CATALOG NUMBER: S122DIW-S290D1240U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1
2.5°	529.9	530.7	533.2	535.8	538.8	539.6	540.8	539.8	539.4	542.4	544.7
5°	531.4	534.9	542.1	548.6	554.0	557.9	562.0	563.6	566.6	570.8	576.1
7.5°	529.6	536.7	547.9	557.3	567.6	575.0	580.8	585.8	591.7	599.8	608.6
10°	527.7	537.2	550.8	562.3	574.9	584.4	592.3	600.0	608.9	620.1	631.6
12.5°	524.1	535.4	552.4	566.1	582.2	591.6	602.2	618.8	628.4	643.9	660.1
15°	516.9	529.5	553.2	570.0	588.3	606.1	625.7	641.5	657.3	666.5	689.3
17.5°	506.3	524.7	551.0	570.6	593.8	621.8	643.9	661.8	680.0	694.8	706.3
20°	497.7	517.7	547.8	571.2	598.8	628.9	654.2	672.5	688.3	700.7	707.8
22.5°	486.9	512.1	541.3	568.8	604.0	633.8	660.4	674.8	688.0	694.0	696.8
25°	469.8	500.2	533.2	566.8	606.5	638.1	662.4	671.1	674.9	669.1	659.3
27.5°	451.3	485.2	523.8	562.9	604.9	635.3	652.7	651.4	644.9	625.8	610.6
30°	437.6	474.8	516.3	559.1	601.2	630.8	640.9	630.8	616.0	594.8	573.0
32.5°	423.1	461.7	508.4	553.6	594.4	620.5	622.6	605.2	582.3	558.1	531.1
35°	401.3	443.0	493.5	541.3	580.0	596.4	586.7	555.8	528.7	495.7	458.8
37.5°	376.6	422.7	473.2	523.3	558.3	562.6	538.4	506.0	467.7	428.9	385.5
40°	358.1	407.0	459.1	509.4	540.5	536.0	505.2	469.6	424.0	376.6	336.3
42.5°	341.6	390.4	443.4	492.9	517.7	505.5	469.6	425.8	376.8	332.2	295.2
45°	313.0	363.2	417.5	465.3	479.5	457.4	409.8	361.1	313.0	275.7	246.6
47.5°	285.2	334.8	388.6	430.6	435.6	405.9	353.9	303.9	262.4	232.1	211.5
50°	264.7	314.6	367.8	405.4	403.7	367.8	314.4	266.8	232.1	207.6	193.9
52.5°	246.5	293.6	344.6	378.8	370.1	331.1	280.0	237.7	209.3	190.1	177.6
55°	217.9	261.5	310.1	337.5	321.6	278.3	235.1	201.2	180.0	165.7	156.0
57.5°	189.7	230.5	272.2	289.0	271.5	231.5	195.6	170.9	155.0	144.4	138.0
60°	172.2	207.9	244.9	259.5	238.6	203.0	174.6	152.6	139.7	131.1	125.4
62.5°	154.7	186.6	221.6	229.5	210.4	180.3	155.2	136.8	126.4	118.6	113.2
65°	130.8	157.0	183.5	188.8	171.2	147.8	128.0	116.1	106.7	101.1	96.8
67.5°	107.4	128.3	147.1	151.3	135.9	119.8	105.4	95.0	88.7	84.0	80.3
70°	93.4	110.0	125.4	128.9	116.5	102.1	91.1	82.8	77.1	73.1	69.6
72.5°	78.6	92.5	105.3	107.6	97.6	86.5	77.6	71.0	66.0	63.4	60.1
75°	60.2	68.3	78.2	78.8	72.1	65.5	58.6	54.3	51.6	48.4	46.8
77.5°	42.4	48.8	54.5	55.6	51.6	47.1	43.2	39.9	37.6	36.1	34.6
80°	32.4	37.5	39.9	41.3	38.5	35.2	33.0	30.8	29.3	28.4	27.4
82.5°	23.2	26.3	28.5	29.7	28.1	26.1	24.0	22.6	21.6	20.8	20.4
85°	11.8	13.2	14.6	15.0	14.6	13.7	12.6	12.6	11.9	11.8	11.8
87.5°	4.9	6.2	6.8	7.8	8.5	9.5	10.7	11.7	12.7	12.4	12.1
90°	4.3	7.3	10.4	13.5	17.8	23.5	29.2	34.8	40.5	39.9	39.4
92.5°	22.8	25.1	27.4	29.6	31.4	32.7	34.1	35.4	36.7	36.8	37.0
95°	62.7	65.3	67.9	70.4	72.0	72.5	72.9	73.5	74.0	74.0	74.0
97.5°	112.1	114.4	116.6	118.9	120.5	121.5	122.4	123.4	124.4	124.4	124.4
100°	148.9	151.0	153.0	155.1	156.5	157.2	158.0	158.8	159.5	159.5	159.5
102.5°	187.3	189.0	190.6	192.3	193.6	194.6	195.6	196.5	197.5	197.7	197.9
105°	249.3	250.1	250.9	251.6	252.4	252.8	253.3	253.9	254.4	254.9	255.4
107.5°	313.1	314.2	315.3	316.5	317.0	317.0	317.0	317.0	317.0	317.3	317.4
110°	354.2	355.7	357.3	358.8	359.6	359.6	359.6	359.6	359.6	359.6	359.6





TEST NUMBER: P331484-940

CATALOG NUMBER: S122DIW-S290D1240U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	398.6	400.1	401.7	403.2	403.9	403.7	403.5	403.2	403.1	402.4	401.8
115°	464.0	465.6	467.1	468.7	469.1	468.7	468.1	467.6	467.1	466.9	466.6
117.5°	529.8	531.8	533.9	535.9	536.3	534.8	533.3	531.9	530.5	529.9	529.2
120°	573.2	575.3	577.4	579.4	579.4	577.4	575.3	573.2	571.1	571.1	571.1
122.5°	613.4	615.9	618.3	620.8	621.3	619.9	618.5	617.0	615.5	614.9	614.4
125°	675.2	677.5	679.8	682.2	683.0	682.2	681.4	680.6	679.8	679.1	678.3
127.5°	736.2	739.1	742.1	745.0	746.0	745.1	744.1	743.2	742.3	741.4	740.5
130°	774.5	777.9	781.2	784.5	786.0	785.5	785.0	784.4	783.9	783.4	782.9
132.5°	816.5	819.2	821.9	824.7	826.1	826.2	826.3	826.3	826.4	825.4	824.2
135°	873.4	876.3	879.1	882.0	883.6	884.1	884.7	885.2	885.6	885.4	885.2
137.5°	932.8	935.1	937.5	939.8	941.3	941.9	942.6	943.3	944.0	943.8	943.5
140°	968.9	971.3	973.6	975.9	977.7	978.9	980.3	981.5	982.8	982.8	982.8
142.5°	1005.9	1008.3	1010.6	1012.9	1014.4	1015.3	1016.2	1017.1	1018.0	1018.2	1018.3
145°	1058.6	1060.4	1062.2	1064.0	1065.7	1067.2	1068.7	1070.3	1071.8	1072.1	1072.4
147.5°	1106.3	1108.5	1110.7	1112.9	1114.5	1115.4	1116.5	1117.5	1118.6	1119.1	1119.6
150°	1138.1	1139.7	1141.2	1142.7	1144.1	1145.0	1146.1	1147.1	1148.2	1148.9	1149.7
152.5°	1166.8	1168.3	1169.8	1171.4	1172.8	1174.0	1175.3	1176.5	1177.8	1178.8	1179.7
155°	1209.1	1209.8	1210.6	1211.4	1212.1	1212.9	1213.6	1214.4	1215.2	1216.5	1217.8
157.5°	1245.5	1246.1	1246.6	1247.1	1247.6	1248.0	1248.5	1248.9	1249.5	1251.2	1252.9
160°	1267.7	1268.3	1268.8	1269.3	1269.7	1269.9	1270.2	1270.4	1270.7	1272.2	1273.8
162.5°	1287.7	1287.8	1287.9	1288.0	1288.2	1288.4	1288.7	1289.0	1289.2	1290.9	1292.7
165°	1314.4	1314.1	1313.8	1313.6	1313.5	1313.5	1313.5	1313.5	1313.5	1315.3	1317.1
167.5°	1336.5	1335.8	1335.0	1334.2	1333.8	1333.7	1333.7	1333.6	1333.6	1335.4	1337.2
170°	1348.5	1347.8	1347.0	1346.2	1345.8	1345.5	1345.2	1345.0	1344.7	1346.5	1348.3
172.5°	1356.9	1356.1	1355.3	1354.6	1354.1	1353.8	1353.5	1353.3	1353.0	1354.9	1356.6
175°	1367.1	1366.3	1365.5	1364.8	1364.1	1363.6	1363.1	1362.5	1362.0	1363.9	1365.7
177.5°	1371.4	1370.7	1370.1	1369.5	1369.0	1368.6	1368.2	1367.8	1367.3	1368.6	1369.8
180°	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1



TEST NUMBER: P331484-940

CATALOG NUMBER: S122DIW-S290D1240U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	527.1	527.1	527.1	527.1	527.1	527.1	527.1
2.5°	546.7	548.9	548.9	549.3	551.9	551.5	551.3
5°	581.8	585.2	585.6	589.2	591.7	590.8	588.6
7.5°	614.8	621.3	626.2	628.8	632.0	634.0	633.1
10°	641.1	650.4	656.1	660.0	664.6	668.1	666.8
12.5°	664.9	676.0	683.9	690.5	691.0	695.4	692.4
15°	702.1	713.8	715.1	719.9	723.8	723.4	723.5
17.5°	714.3	718.1	718.9	719.0	719.1	717.6	714.5
20°	710.0	708.6	705.2	702.5	697.9	697.2	693.2
22.5°	689.2	684.7	676.1	670.4	663.2	661.3	660.1
25°	648.5	638.5	624.7	611.5	607.9	600.8	602.8
27.5°	592.4	576.9	562.0	551.3	541.6	531.0	534.0
30°	553.0	535.6	514.5	498.3	487.9	477.9	476.0
32.5°	506.0	480.5	457.0	442.7	426.9	420.4	413.5
35°	425.0	400.0	376.7	356.7	345.2	336.3	328.1
37.5°	352.1	323.4	304.6	288.4	280.0	274.9	276.3
40°	306.9	281.8	268.0	255.7	247.9	244.3	245.1
42.5°	270.3	251.5	240.1	231.7	226.2	224.2	223.7
45°	228.7	218.2	208.8	204.0	201.3	199.1	197.7
47.5°	200.4	191.7	186.5	183.6	181.3	179.1	179.0
50°	183.3	177.6	174.0	170.9	169.2	167.6	169.0
52.5°	170.3	165.1	161.5	158.8	158.1	156.7	156.6
55°	151.1	147.0	144.5	142.0	140.8	140.0	138.9
57.5°	133.6	129.7	127.3	125.8	123.5	122.7	122.3
60°	121.1	118.1	115.7	113.6	112.6	111.0	111.0
62.5°	109.6	106.6	104.3	102.8	101.1	100.5	100.7
65°	93.0	90.5	88.3	86.7	86.3	85.1	85.5
67.5°	77.7	76.1	73.7	72.8	72.1	71.4	70.9
70°	67.4	65.8	64.6	63.4	62.8	62.8	62.8
72.5°	58.9	56.9	56.2	54.7	55.0	54.4	53.7
75°	45.6	44.3	43.8	43.2	42.2	42.2	42.2
77.5°	33.5	33.2	32.5	31.8	31.6	31.4	31.5
80°	25.9	25.7	25.3	25.3	24.9	24.7	24.3
82.5°	20.0	19.4	19.2	19.0	18.9	18.9	18.8
85°	11.3	11.0	11.0	11.1	10.7	10.7	11.0
87.5°	12.1	12.0	11.9	11.9	12.1	12.0	12.0
90°	39.0	38.4	38.3	38.5	38.8	39.1	39.3
92.5°	37.1	37.2	37.3	37.3	37.4	37.5	37.5
95°	74.0	74.0	73.7	73.2	72.7	72.2	71.7
97.5°	124.4	124.4	124.4	124.3	124.3	124.2	124.2
100°	159.5	159.5	159.4	159.2	158.9	158.6	158.4
102.5°	198.1	198.3	198.3	198.0	197.8	197.5	197.2
105°	255.9	256.5	256.7	256.7	256.7	256.7	256.7
107.5°	317.6	317.9	317.4	316.2	315.0	313.8	312.6
110°	359.6	359.6	359.2	358.5	357.7	356.9	356.1



TEST NUMBER: P331484-940

CATALOG NUMBER: S122DIW-S290D1240U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	401.2	400.6	400.0	399.4	398.9	398.3	397.7
115°	466.4	466.1	465.6	464.8	464.0	463.2	462.5
117.5°	528.6	528.0	527.4	526.6	525.8	525.0	524.2
120°	571.1	571.1	570.8	570.0	569.3	568.5	567.8
122.5°	613.8	613.1	612.5	612.0	611.4	610.8	610.3
125°	677.5	676.8	676.3	676.0	675.7	675.5	675.2
127.5°	739.5	738.6	737.7	736.9	736.1	735.3	734.4
130°	782.4	781.9	781.1	780.1	779.1	778.0	776.9
132.5°	823.0	822.0	821.0	820.2	819.3	818.5	817.7
135°	884.9	884.7	884.1	883.3	882.6	881.8	881.0
137.5°	943.3	943.2	942.5	941.5	940.5	939.4	938.4
140°	982.8	982.8	982.3	981.2	980.3	979.2	978.2
142.5°	1018.6	1018.8	1018.3	1017.4	1016.3	1015.3	1014.2
145°	1072.6	1072.8	1072.5	1071.5	1070.4	1069.4	1068.4
147.5°	1120.3	1120.8	1120.6	1119.6	1118.7	1117.7	1116.7
150°	1150.5	1151.2	1151.2	1150.5	1149.7	1148.9	1148.2
152.5°	1180.6	1181.6	1181.6	1180.6	1179.7	1178.8	1177.8
155°	1219.1	1220.3	1220.6	1219.9	1219.1	1218.3	1217.5
157.5°	1254.6	1256.4	1256.7	1255.4	1254.2	1252.9	1251.7
160°	1275.3	1276.8	1277.1	1276.1	1275.1	1274.1	1273.0
162.5°	1294.4	1296.2	1296.5	1295.2	1294.0	1292.7	1291.6
165°	1318.8	1320.7	1320.9	1319.6	1318.4	1317.1	1315.8
167.5°	1339.0	1340.8	1341.0	1339.7	1338.4	1337.0	1335.7
170°	1350.1	1351.9	1352.0	1350.5	1349.0	1347.4	1345.9
172.5°	1358.4	1360.2	1360.3	1358.8	1357.3	1355.8	1354.2
175°	1367.4	1369.2	1369.4	1367.8	1366.3	1364.8	1363.2
177.5°	1371.1	1372.3	1372.3	1371.1	1369.8	1368.6	1367.3
180°	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1

(END OF REPORT)