

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331490-940

Luminaire Tested: **S122DIW-S290D1440U940-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331490-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S290D1440U940-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1440 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5623.5 lumens
Efficiency: N/A
Efficacy: 105.3 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331490-940

CATALOG NUMBER: S122DIW-S290D1440U940-4F0-1E-UDD-A1

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - - - 90°-270° - - - 135°-315°



TEST NUMBER: P331490-940

CATALOG NUMBER: S122DIW-S290D1440U940-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	100	100	100	100	89	89	89	89	67	67	67	47	47	47	29	29	29	21
1	91	87	84	80	81	77	74	72	59	57	55	42	41	40	26	26	25	18
2	83	76	71	66	74	68	63	59	52	49	46	37	35	33	23	22	21	15
3	76	67	60	55	67	60	54	49	46	42	39	33	30	28	21	19	18	13
4	70	60	52	46	61	53	47	42	41	36	33	29	27	24	19	17	16	11
5	64	53	45	40	56	47	41	36	36	32	28	26	23	21	17	15	14	10
6	59	47	40	34	52	42	36	31	33	28	25	24	21	18	15	14	12	9
7	54	43	35	30	48	38	32	27	30	25	22	22	19	16	14	12	11	8
8	50	39	31	26	44	35	28	24	27	22	19	20	17	14	13	11	10	7
9	47	35	28	23	41	31	25	21	25	20	17	18	15	13	12	10	9	7
10	43	32	25	21	38	29	23	19	22	18	15	17	14	12	11	9	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8510	8510	8510	8510
5°	9540	8566	7590	8566
10°	10932	8496	6568	8496
15°	12094	8339	5804	8339
20°	11911	8172	5290	8172
25°	10739	7949	4965	7949
30°	8874	7594	4728	7594
35°	6467	7222	4559	7222
40°	5166	6785	4466	6785
45°	4514	6277	4338	6277
50°	4245	5785	4253	5785
55°	3910	5286	4138	5286
60°	3584	4753	3965	4753
65°	3266	4279	3790	4279
70°	2965	3814	3541	3814
75°	2633	3300	3132	3300
80°	2259	2724	2520	2724
85°	2038	2038	1501	2038



TEST NUMBER: P331490-940

CATALOG NUMBER: S122DIW-S290D1440U940-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.2	0.9
10°-20°	145.9	2.6
20°-30°	211.8	3.8
30°-40°	223.5	4.0
40°-50°	197.9	3.5
50°-60°	157.9	2.8
60°-70°	107.3	1.9
70°-80°	55.0	1.0
80°-90°	19.6	0.3
90°-100°	100.9	1.8
100°-110°	313.5	5.6
110°-120°	535.9	9.5
120°-130°	704.7	12.5
130°-140°	791.0	14.1
140°-150°	775.6	13.8
150°-160°	650.5	11.6
160°-170°	431.5	7.7
170°-180°	150.8	2.7
0°-30°	407.9	7.3
0°-40°	631.4	11.2
0°-60°	987.2	17.6
0°-90°	1169.2	20.8
90°-120°	950.3	16.9
90°-150°	3221.6	57.3
90°-180°	4454.0	79.2
0°-180°	5623.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	527	527	527	527	527	
5°	589	528	468	528	589	59
15°	724	499	347	499	724	200
25°	603	446	279	446	603	272
35°	328	366	231	366	328	213
45°	198	275	190	275	198	155
55°	139	188	147	188	139	125
65°	86	112	99	112	86	85
75°	42	53	50	53	42	45
85°	11	11	8	11	11	13
90°	46	1	46	1	46	20
95°	83	70	83	70	83	93
105°	298	289	298	289	298	314
115°	538	538	538	538	538	531
125°	785	782	785	782	785	700
135°	1024	1012	1024	1012	1024	789
145°	1242	1229	1242	1229	1242	776
155°	1416	1405	1416	1405	1416	651
165°	1530	1528	1530	1528	1530	431
175°	1585	1590	1585	1590	1585	151
180°	1593	1593	1593	1593	1593	



TEST NUMBER: P331490-940

CATALOG NUMBER: S122DIW-S290D1440U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1
2.5°	551.3	551.5	551.9	549.3	548.9	548.9	546.7	544.7	542.4	539.4	539.8
5°	588.6	590.8	591.7	589.2	585.6	585.2	581.8	576.1	570.8	566.6	563.6
7.5°	633.1	634.0	632.0	628.8	626.2	621.3	614.8	608.6	599.8	591.7	585.8
10°	666.8	668.1	664.6	660.0	656.1	650.4	641.1	631.6	620.1	608.9	600.0
12.5°	692.4	695.4	691.0	690.5	683.9	676.0	664.9	660.1	643.9	628.4	618.8
15°	723.5	723.4	723.8	719.9	715.1	713.8	702.1	689.3	666.5	657.3	641.5
17.5°	714.5	717.6	719.1	719.0	718.9	718.1	714.3	706.3	694.8	680.0	661.8
20°	693.2	697.2	697.9	702.5	705.2	708.6	710.0	707.8	700.7	688.3	672.5
22.5°	660.1	661.3	663.2	670.4	676.1	684.7	689.2	696.8	694.0	688.0	674.8
25°	602.8	600.8	607.9	611.5	624.7	638.5	648.5	659.3	669.1	674.9	671.1
27.5°	534.0	531.0	541.6	551.3	562.0	576.9	592.4	610.6	625.8	644.9	651.4
30°	476.0	477.9	487.9	498.3	514.5	535.6	553.0	573.0	594.8	616.0	630.8
32.5°	413.5	420.4	426.9	442.7	457.0	480.5	506.0	531.1	558.1	582.3	605.2
35°	328.1	336.3	345.2	356.7	376.7	400.0	425.0	458.8	495.7	528.7	555.8
37.5°	276.3	274.9	280.0	288.4	304.6	323.4	352.1	385.5	428.9	467.7	506.0
40°	245.1	244.3	247.9	255.7	268.0	281.8	306.9	336.3	376.6	424.0	469.6
42.5°	223.7	224.2	226.2	231.7	240.1	251.5	270.3	295.2	332.2	376.8	425.8
45°	197.7	199.1	201.3	204.0	208.8	218.2	228.7	246.6	275.7	313.0	361.1
47.5°	179.0	179.1	181.3	183.6	186.5	191.7	200.4	211.5	232.1	262.4	303.9
50°	169.0	167.6	169.2	170.9	174.0	177.6	183.3	193.9	207.6	232.1	266.8
52.5°	156.6	156.7	158.1	158.8	161.5	165.1	170.3	177.6	190.1	209.3	237.7
55°	138.9	140.0	140.8	142.0	144.5	147.0	151.1	156.0	165.7	180.0	201.2
57.5°	122.3	122.7	123.5	125.8	127.3	129.7	133.6	138.0	144.4	155.0	170.9
60°	111.0	111.0	112.6	113.6	115.7	118.1	121.1	125.4	131.1	139.7	152.6
62.5°	100.7	100.5	101.1	102.8	104.3	106.6	109.6	113.2	118.6	126.4	136.8
65°	85.5	85.1	86.3	86.7	88.3	90.5	93.0	96.8	101.1	106.7	116.1
67.5°	70.9	71.4	72.1	72.8	73.7	76.1	77.7	80.3	84.0	88.7	95.0
70°	62.8	62.8	62.8	63.4	64.6	65.8	67.4	69.6	73.1	77.1	82.8
72.5°	53.7	54.4	55.0	54.7	56.2	56.9	58.9	60.1	63.4	66.0	71.0
75°	42.2	42.2	42.2	43.2	43.8	44.3	45.6	46.8	48.4	51.6	54.3
77.5°	31.5	31.4	31.6	31.8	32.5	33.2	33.5	34.6	36.1	37.6	39.9
80°	24.3	24.7	24.9	25.3	25.3	25.7	25.9	27.4	28.4	29.3	30.8
82.5°	18.8	18.9	18.9	19.0	19.2	19.4	20.0	20.4	20.8	21.6	22.6
85°	11.0	10.7	10.7	11.1	11.0	11.0	11.3	11.8	11.8	11.9	12.6
87.5°	13.4	13.3	13.4	13.2	13.1	13.3	13.5	13.4	13.6	13.9	12.8
90°	45.7	45.4	45.1	44.9	44.5	44.7	45.3	45.8	46.5	47.1	40.5
92.5°	43.5	43.5	43.4	43.3	43.3	43.2	43.1	43.0	42.9	42.7	41.2
95°	83.4	83.9	84.5	85.2	85.7	86.1	86.1	86.1	86.1	86.1	85.4
97.5°	144.4	144.5	144.5	144.5	144.6	144.6	144.6	144.6	144.6	144.6	143.5
100°	184.1	184.5	184.8	185.0	185.4	185.5	185.5	185.5	185.5	185.5	184.6
102.5°	229.3	229.6	230.0	230.2	230.5	230.6	230.3	230.1	229.9	229.6	228.5
105°	298.5	298.5	298.5	298.5	298.5	298.1	297.6	296.9	296.3	295.8	295.2
107.5°	363.5	364.9	366.2	367.7	369.0	369.5	369.3	369.1	368.8	368.6	368.6
110°	414.0	414.9	415.8	416.7	417.6	418.1	418.1	418.1	418.1	418.1	418.1



TEST NUMBER: P331490-940

CATALOG NUMBER: S122DIW-S290D1440U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	462.4	463.1	463.8	464.4	465.0	465.7	466.5	467.2	467.9	468.6	468.9
115°	537.7	538.6	539.5	540.4	541.3	541.9	542.2	542.5	542.8	543.1	543.7
117.5°	609.5	610.4	611.3	612.2	613.1	613.9	614.7	615.4	616.1	616.8	618.4
120°	660.0	660.9	661.8	662.7	663.6	664.1	664.1	664.1	664.1	664.1	666.5
122.5°	709.5	710.2	710.9	711.5	712.1	712.8	713.5	714.3	715.0	715.7	717.4
125°	785.1	785.4	785.7	786.0	786.3	786.8	787.7	788.6	789.5	790.4	791.4
127.5°	853.9	854.9	855.8	856.8	857.7	858.7	859.8	860.9	861.9	863.1	864.2
130°	903.4	904.6	905.8	907.0	908.1	909.0	909.6	910.3	910.9	911.4	912.0
132.5°	950.7	951.6	952.6	953.6	954.5	955.6	957.0	958.3	959.6	960.9	960.8
135°	1024.4	1025.3	1026.2	1027.1	1028.0	1028.6	1028.9	1029.1	1029.5	1029.7	1029.1
137.5°	1091.0	1092.3	1093.4	1094.7	1095.8	1096.5	1096.8	1097.0	1097.3	1097.5	1096.7
140°	1137.3	1138.4	1139.7	1140.9	1142.1	1142.6	1142.6	1142.6	1142.6	1142.6	1141.2
142.5°	1179.2	1180.4	1181.6	1182.9	1184.0	1184.5	1184.3	1184.0	1183.7	1183.6	1182.5
145°	1242.2	1243.3	1244.6	1245.7	1246.9	1247.3	1247.1	1246.8	1246.4	1246.2	1244.4
147.5°	1298.3	1299.5	1300.6	1301.7	1302.9	1303.1	1302.4	1301.8	1301.2	1300.5	1299.3
150°	1334.9	1335.8	1336.7	1337.6	1338.5	1338.5	1337.6	1336.7	1335.8	1334.9	1333.7
152.5°	1369.3	1370.5	1371.5	1372.7	1373.9	1373.9	1372.7	1371.5	1370.5	1369.3	1367.9
155°	1415.6	1416.5	1417.4	1418.3	1419.2	1418.8	1417.4	1415.9	1414.3	1412.8	1411.9
157.5°	1455.4	1456.8	1458.2	1459.6	1461.1	1460.8	1458.7	1456.7	1454.6	1452.7	1452.2
160°	1480.1	1481.3	1482.5	1483.6	1484.9	1484.5	1482.7	1481.0	1479.2	1477.4	1477.1
162.5°	1501.6	1503.1	1504.5	1505.9	1507.3	1507.0	1505.0	1503.0	1500.9	1498.9	1498.6
165°	1529.8	1531.3	1532.9	1534.3	1535.8	1535.5	1533.4	1531.3	1529.2	1527.1	1527.1
167.5°	1552.9	1554.5	1556.0	1557.6	1559.2	1558.9	1556.8	1554.7	1552.6	1550.5	1550.6
170°	1564.8	1566.6	1568.3	1570.1	1571.9	1571.8	1569.7	1567.6	1565.5	1563.4	1563.7
172.5°	1574.5	1576.3	1578.1	1579.8	1581.6	1581.4	1579.4	1577.3	1575.2	1573.1	1573.4
175°	1584.9	1586.7	1588.5	1590.3	1592.1	1592.0	1589.8	1587.8	1585.7	1583.6	1584.2
177.5°	1589.7	1591.2	1592.7	1594.1	1595.5	1595.5	1594.1	1592.7	1591.2	1589.7	1590.3
180°	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0



TEST NUMBER: P331490-940

CATALOG NUMBER: S122DIW-S290D1440U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1
2.5°	540.8	539.6	538.8	535.8	533.2	530.7	529.9	530.1	526.6	523.2	521.7
5°	562.0	557.9	554.0	548.6	542.1	534.9	531.4	528.5	521.4	513.7	509.3
7.5°	580.8	575.0	567.6	557.3	547.9	536.7	529.6	523.3	513.0	502.1	495.4
10°	592.3	584.4	574.9	562.3	550.8	537.2	527.7	518.2	506.0	493.0	484.9
12.5°	602.2	591.6	582.2	566.1	552.4	535.4	524.1	510.7	497.9	482.5	474.6
15°	625.7	606.1	588.3	570.0	553.2	529.5	516.9	498.9	482.1	463.1	454.0
17.5°	643.9	621.8	593.8	570.6	551.0	524.7	506.3	484.7	464.8	443.1	430.7
20°	654.2	628.9	598.8	571.2	547.8	517.7	497.7	475.6	452.4	427.8	414.5
22.5°	660.4	633.8	604.0	568.8	541.3	512.1	486.9	462.6	439.1	412.6	398.6
25°	662.4	638.1	606.5	566.8	533.2	500.2	469.8	446.2	417.7	393.0	372.6
27.5°	652.7	635.3	604.9	562.9	523.8	485.2	451.3	424.7	394.6	367.7	347.1
30°	640.9	630.8	601.2	559.1	516.3	474.8	437.6	407.3	377.4	350.3	329.1
32.5°	622.6	620.5	594.4	553.6	508.4	461.7	423.1	392.6	359.4	332.7	312.6
35°	586.7	596.4	580.0	541.3	493.5	443.0	401.3	366.4	332.0	306.5	287.7
37.5°	538.4	562.6	558.3	523.3	473.2	422.7	376.6	340.2	307.4	281.6	263.1
40°	505.2	536.0	540.5	509.4	459.1	407.0	358.1	321.9	289.9	266.4	247.7
42.5°	469.6	505.5	517.7	492.9	443.4	390.4	341.6	304.1	272.3	249.5	233.0
45°	409.8	457.4	479.5	465.3	417.5	363.2	313.0	274.9	246.1	224.6	211.9
47.5°	353.9	405.9	435.6	430.6	388.6	334.8	285.2	248.6	220.6	203.5	192.1
50°	314.4	367.8	403.7	405.4	367.8	314.6	264.7	230.3	204.6	188.6	179.2
52.5°	280.0	331.1	370.1	378.8	344.6	293.6	246.5	212.1	189.5	174.8	166.5
55°	235.1	278.3	321.6	337.5	310.1	261.5	217.9	187.8	166.5	156.4	149.1
57.5°	195.6	231.5	271.5	289.0	272.2	230.5	189.7	163.5	146.2	137.3	131.7
60°	174.6	203.0	238.6	259.5	244.9	207.9	172.2	147.2	133.0	125.2	119.9
62.5°	155.2	180.3	210.4	229.5	221.6	186.6	154.7	132.7	120.5	113.1	109.2
65°	128.0	147.8	171.2	188.8	183.5	157.0	130.8	112.0	102.3	96.4	93.4
67.5°	105.4	119.8	135.9	151.3	147.1	128.3	107.4	92.6	85.4	80.3	78.5
70°	91.1	102.1	116.5	128.9	125.4	110.0	93.4	80.8	74.5	70.3	68.5
72.5°	77.6	86.5	97.6	107.6	105.3	92.5	78.6	69.2	64.3	60.4	58.9
75°	58.6	65.5	72.1	78.8	78.2	68.3	60.2	52.9	49.0	46.0	45.4
77.5°	43.2	47.1	51.6	55.6	54.5	48.8	42.4	38.3	35.5	33.4	33.1
80°	33.0	35.2	38.5	41.3	39.9	37.5	32.4	29.3	27.4	25.3	24.5
82.5°	24.0	26.1	28.1	29.7	28.5	26.3	23.2	21.1	19.9	18.5	18.2
85°	12.6	13.7	14.6	15.0	14.6	13.2	11.8	11.0	9.9	9.3	9.1
87.5°	11.7	10.3	9.0	8.3	7.1	6.4	5.0	3.8	4.4	4.9	5.4
90°	33.9	27.4	20.8	15.7	12.1	8.5	4.9	1.3	4.9	8.5	12.1
92.5°	39.7	38.1	36.6	34.4	31.8	29.2	26.6	23.9	26.6	29.2	31.8
95°	84.8	84.3	83.6	81.9	78.8	75.9	72.9	69.9	72.9	75.9	78.8
97.5°	142.4	141.2	140.1	138.2	135.6	133.0	130.4	127.7	130.4	133.0	135.6
100°	183.7	182.8	181.9	180.3	177.9	175.5	173.1	170.8	173.1	175.5	177.9
102.5°	227.3	226.2	225.1	223.6	221.6	219.7	217.8	215.9	217.8	219.7	221.6
105°	294.5	294.0	293.4	292.6	291.7	290.8	289.9	289.0	289.9	290.8	291.7
107.5°	368.6	368.6	368.6	367.9	366.7	365.3	364.0	362.7	364.0	365.3	366.7
110°	418.1	418.1	418.1	417.1	415.4	413.6	411.8	410.0	411.8	413.6	415.4



TEST NUMBER: P331490-940

CATALOG NUMBER: S122DIW-S290D1440U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	469.1	469.3	469.6	468.8	467.0	465.2	463.4	461.6	463.4	465.2	467.0
115°	544.3	544.9	545.5	544.9	543.1	541.3	539.5	537.7	539.5	541.3	543.1
117.5°	620.1	621.8	623.5	623.1	620.7	618.3	615.9	613.6	615.9	618.3	620.7
120°	668.9	671.3	673.7	673.7	671.3	668.9	666.5	664.1	666.5	668.9	671.3
122.5°	719.1	720.8	722.4	721.8	718.9	716.0	713.2	710.3	713.2	716.0	718.9
125°	792.3	793.2	794.1	793.2	790.4	787.7	785.1	782.4	785.1	787.7	790.4
127.5°	865.2	866.3	867.4	866.2	862.8	859.3	856.0	852.6	856.0	859.3	862.8
130°	912.7	913.2	913.8	912.2	908.3	904.5	900.5	896.6	900.5	904.5	908.3
132.5°	960.6	960.6	960.5	958.8	955.6	952.4	949.3	946.1	949.3	952.4	955.6
135°	1028.6	1028.0	1027.3	1025.4	1022.1	1018.9	1015.6	1012.3	1015.6	1018.9	1022.1
137.5°	1095.9	1095.2	1094.4	1092.6	1089.9	1087.3	1084.6	1081.9	1084.6	1087.3	1089.9
140°	1139.7	1138.2	1136.7	1134.6	1131.9	1129.3	1126.5	1123.8	1126.5	1129.3	1131.9
142.5°	1181.5	1180.4	1179.5	1177.6	1174.9	1172.2	1169.6	1166.9	1169.6	1172.2	1174.9
145°	1242.6	1240.8	1239.0	1237.1	1234.9	1232.9	1230.8	1228.7	1230.8	1232.9	1234.9
147.5°	1298.1	1296.9	1295.7	1293.9	1291.4	1288.8	1286.3	1283.8	1286.3	1288.8	1291.4
150°	1332.5	1331.3	1330.1	1328.6	1326.9	1325.1	1323.2	1321.4	1323.2	1325.1	1326.9
152.5°	1366.5	1365.0	1363.6	1362.0	1360.1	1358.3	1356.6	1354.8	1356.6	1358.3	1360.1
155°	1411.0	1410.2	1409.3	1408.4	1407.5	1406.6	1405.7	1404.8	1405.7	1406.6	1407.5
157.5°	1451.6	1451.1	1450.5	1449.9	1449.4	1448.8	1448.1	1447.5	1448.1	1448.8	1449.4
160°	1476.8	1476.5	1476.2	1475.8	1475.2	1474.5	1474.0	1473.4	1474.0	1474.5	1475.2
162.5°	1498.3	1498.0	1497.7	1497.5	1497.4	1497.3	1497.2	1497.0	1497.2	1497.3	1497.4
165°	1527.1	1527.1	1527.1	1527.3	1527.6	1527.9	1528.2	1528.5	1528.2	1527.9	1527.6
167.5°	1550.7	1550.7	1550.8	1551.2	1552.1	1553.0	1553.9	1554.8	1553.9	1553.0	1552.1
170°	1564.1	1564.3	1564.6	1565.2	1566.1	1567.0	1567.9	1568.8	1567.9	1567.0	1566.1
172.5°	1573.7	1574.0	1574.3	1574.9	1575.8	1576.7	1577.6	1578.5	1577.6	1576.7	1575.8
175°	1584.7	1585.4	1586.0	1586.7	1587.6	1588.5	1589.4	1590.3	1589.4	1588.5	1587.6
177.5°	1590.7	1591.2	1591.7	1592.3	1593.0	1593.8	1594.5	1595.2	1594.5	1593.8	1593.0
180°	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0



TEST NUMBER: P331490-940

CATALOG NUMBER: S122DIW-S290D1440U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1
2.5°	520.1	519.2	515.8	514.0	511.0	508.3	506.5	507.3	507.9	507.7	507.1
5°	505.2	501.3	495.4	490.4	486.8	480.1	477.2	475.8	474.6	473.2	471.8
7.5°	487.4	481.3	473.0	465.7	459.0	450.6	445.9	443.1	440.1	436.9	434.1
10°	474.8	466.3	457.4	447.3	439.2	431.7	425.0	420.5	416.4	412.6	409.8
12.5°	461.5	451.7	440.7	426.9	417.9	407.2	406.2	398.3	392.0	389.6	386.3
15°	440.4	426.6	412.6	396.2	389.1	379.4	373.4	367.2	361.8	357.9	357.0
17.5°	416.3	398.5	384.6	372.8	361.2	351.2	345.6	340.8	336.3	331.2	330.5
20°	398.1	382.6	367.5	357.1	345.2	335.0	328.1	323.3	319.4	316.4	313.8
22.5°	380.7	363.8	349.9	338.7	326.9	318.7	313.3	308.5	305.3	302.0	299.5
25°	352.8	339.7	324.5	311.7	302.0	296.8	292.3	288.3	286.2	284.0	281.2
27.5°	328.5	313.9	299.7	289.8	281.2	276.6	273.4	270.6	268.8	267.4	265.8
30°	311.4	296.6	285.4	275.7	268.6	263.9	261.9	260.3	258.1	257.3	256.5
32.5°	294.8	281.5	272.0	263.5	256.8	253.7	251.9	250.4	248.7	247.9	246.2
35°	271.4	260.3	251.0	246.3	240.9	238.2	236.8	234.8	233.2	232.4	232.1
37.5°	249.4	239.8	233.6	227.7	225.3	223.7	221.8	220.4	219.9	219.8	219.5
40°	235.1	227.3	221.8	217.0	216.0	213.5	211.9	210.7	210.7	210.9	210.7
42.5°	222.2	215.1	210.3	206.1	204.9	203.5	201.8	201.8	202.1	202.8	202.1
45°	202.6	197.5	194.0	192.1	189.8	188.4	188.2	188.8	189.0	189.2	189.8
47.5°	184.5	181.1	178.0	175.8	174.8	174.6	174.3	175.4	176.4	176.7	177.6
50°	173.8	170.0	167.3	165.9	165.1	164.7	165.1	166.3	167.1	168.1	168.7
52.5°	161.8	159.1	157.3	156.1	155.9	156.1	156.1	157.6	158.8	159.3	159.5
55°	145.3	143.2	142.9	141.0	141.8	141.6	142.6	143.4	144.6	145.9	146.1
57.5°	128.7	127.1	126.0	126.2	126.4	127.3	128.1	129.6	130.8	132.2	132.2
60°	117.7	116.9	116.3	116.3	116.6	117.9	118.9	120.3	121.1	122.0	122.5
62.5°	107.6	106.8	106.2	106.6	107.6	108.3	109.5	110.3	111.1	111.9	112.2
65°	91.8	91.4	91.9	92.4	92.6	93.5	95.0	95.6	96.4	96.8	98.3
67.5°	77.1	77.2	77.1	77.7	78.9	79.1	80.4	81.9	82.0	82.8	83.7
70°	67.2	67.7	68.0	68.5	69.5	69.9	70.9	71.5	72.3	72.9	73.6
72.5°	58.1	58.2	58.7	58.6	59.5	60.3	61.2	61.8	62.6	63.4	63.9
75°	44.8	44.8	45.2	45.4	46.4	47.4	47.2	47.6	48.4	49.2	49.7
77.5°	32.7	32.3	32.7	32.9	33.3	34.1	34.2	34.8	35.8	35.5	35.9
80°	24.9	24.3	24.9	25.1	25.1	26.1	26.1	26.6	27.1	26.6	27.1
82.5°	17.7	17.5	17.9	18.0	18.3	18.4	18.6	18.7	19.4	19.1	19.4
85°	8.9	8.7	8.9	8.7	8.9	9.1	9.1	8.9	8.9	9.3	8.7
87.5°	5.9	6.8	7.9	9.2	10.3	11.5	11.2	11.1	11.0	10.5	10.5
90°	15.7	20.8	27.4	33.9	40.5	47.1	46.5	45.8	45.3	44.7	44.5
92.5°	34.4	36.6	38.1	39.7	41.2	42.7	42.9	43.0	43.1	43.2	43.3
95°	81.9	83.6	84.3	84.8	85.4	86.1	86.1	86.1	86.1	86.1	85.7
97.5°	138.2	140.1	141.2	142.4	143.5	144.6	144.6	144.6	144.6	144.6	144.6
100°	180.3	181.9	182.8	183.7	184.6	185.5	185.5	185.5	185.5	185.5	185.4
102.5°	223.6	225.1	226.2	227.3	228.5	229.6	229.9	230.1	230.3	230.6	230.5
105°	292.6	293.4	294.0	294.5	295.2	295.8	296.3	296.9	297.6	298.1	298.5
107.5°	367.9	368.6	368.6	368.6	368.6	368.6	368.8	369.1	369.3	369.5	369.0
110°	417.1	418.1	418.1	418.1	418.1	418.1	418.1	418.1	418.1	418.1	417.6



TEST NUMBER: P331490-940

CATALOG NUMBER: S122DIW-S290D1440U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	468.8	469.6	469.3	469.1	468.9	468.6	467.9	467.2	466.5	465.7	465.0
115°	544.9	545.5	544.9	544.3	543.7	543.1	542.8	542.5	542.2	541.9	541.3
117.5°	623.1	623.5	621.8	620.1	618.4	616.8	616.1	615.4	614.7	613.9	613.1
120°	673.7	673.7	671.3	668.9	666.5	664.1	664.1	664.1	664.1	664.1	663.6
122.5°	721.8	722.4	720.8	719.1	717.4	715.7	715.0	714.3	713.5	712.8	712.1
125°	793.2	794.1	793.2	792.3	791.4	790.4	789.5	788.6	787.7	786.8	786.3
127.5°	866.2	867.4	866.3	865.2	864.2	863.1	861.9	860.9	859.8	858.7	857.7
130°	912.2	913.8	913.2	912.7	912.0	911.4	910.9	910.3	909.6	909.0	908.1
132.5°	958.8	960.5	960.6	960.6	960.8	960.9	959.6	958.3	957.0	955.6	954.5
135°	1025.4	1027.3	1028.0	1028.6	1029.1	1029.7	1029.5	1029.1	1028.9	1028.6	1028.0
137.5°	1092.6	1094.4	1095.2	1095.9	1096.7	1097.5	1097.3	1097.0	1096.8	1096.5	1095.8
140°	1134.6	1136.7	1138.2	1139.7	1141.2	1142.6	1142.6	1142.6	1142.6	1142.6	1142.1
142.5°	1177.6	1179.5	1180.4	1181.5	1182.5	1183.6	1183.7	1184.0	1184.3	1184.5	1184.0
145°	1237.1	1239.0	1240.8	1242.6	1244.4	1246.2	1246.4	1246.8	1247.1	1247.3	1246.9
147.5°	1293.9	1295.7	1296.9	1298.1	1299.3	1300.5	1301.2	1301.8	1302.4	1303.1	1302.9
150°	1328.6	1330.1	1331.3	1332.5	1333.7	1334.9	1335.8	1336.7	1337.6	1338.5	1338.5
152.5°	1362.0	1363.6	1365.0	1366.5	1367.9	1369.3	1370.5	1371.5	1372.7	1373.9	1373.9
155°	1408.4	1409.3	1410.2	1411.0	1411.9	1412.8	1414.3	1415.9	1417.4	1418.8	1419.2
157.5°	1449.9	1450.5	1451.1	1451.6	1452.2	1452.7	1454.6	1456.7	1458.7	1460.8	1461.1
160°	1475.8	1476.2	1476.5	1476.8	1477.1	1477.4	1479.2	1481.0	1482.7	1484.5	1484.9
162.5°	1497.5	1497.7	1498.0	1498.3	1498.6	1498.9	1500.9	1503.0	1505.0	1507.0	1507.3
165°	1527.3	1527.1	1527.1	1527.1	1527.1	1527.1	1529.2	1531.3	1533.4	1535.5	1535.8
167.5°	1551.2	1550.8	1550.7	1550.7	1550.6	1550.5	1552.6	1554.7	1556.8	1558.9	1559.2
170°	1565.2	1564.6	1564.3	1564.1	1563.7	1563.4	1565.5	1567.6	1569.7	1571.8	1571.9
172.5°	1574.9	1574.3	1574.0	1573.7	1573.4	1573.1	1575.2	1577.3	1579.4	1581.4	1581.6
175°	1586.7	1586.0	1585.4	1584.7	1584.2	1583.6	1585.7	1587.8	1589.8	1592.0	1592.1
177.5°	1592.3	1591.7	1591.2	1590.7	1590.3	1589.7	1591.2	1592.7	1594.1	1595.5	1595.5
180°	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0



TEST NUMBER: P331490-940

CATALOG NUMBER: S122DIW-S290D1440U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1
2.5°	505.5	505.2	505.2	503.7	505.2	505.2	505.5	507.1	507.7	507.9	507.3
5°	469.0	468.3	467.3	468.3	467.3	468.3	469.0	471.8	473.2	474.6	475.8
7.5°	432.7	430.3	430.0	427.6	430.0	430.3	432.7	434.1	436.9	440.1	443.1
10°	406.4	404.7	404.5	400.6	404.5	404.7	406.4	409.8	412.6	416.4	420.5
12.5°	386.3	382.4	383.2	380.9	383.2	382.4	386.3	386.3	389.6	392.0	398.3
15°	351.4	351.4	350.6	347.2	350.6	351.4	351.4	357.0	357.9	361.8	367.2
17.5°	326.5	326.0	324.1	325.1	324.1	326.0	326.5	330.5	331.2	336.3	340.8
20°	311.6	310.3	307.9	307.9	307.9	310.3	311.6	313.8	316.4	319.4	323.3
22.5°	297.5	297.4	294.8	295.6	294.8	297.4	297.5	299.5	302.0	305.3	308.5
25°	281.0	279.4	278.1	278.7	278.1	279.4	281.0	281.2	284.0	286.2	288.3
27.5°	265.3	264.4	264.3	262.7	264.3	264.4	265.3	265.8	267.4	268.8	270.6
30°	256.3	254.2	254.6	253.6	254.6	254.2	256.3	256.5	257.3	258.1	260.3
32.5°	245.8	245.1	244.8	243.9	244.8	245.1	245.8	246.2	247.9	248.7	250.4
35°	231.8	231.9	231.0	231.3	231.0	231.9	231.8	232.1	232.4	233.2	234.8
37.5°	219.4	220.0	219.5	219.6	219.5	220.0	219.4	219.5	219.8	219.9	220.4
40°	211.2	211.2	211.2	211.9	211.2	211.2	211.2	210.7	210.9	210.7	210.7
42.5°	203.5	203.1	202.9	202.8	202.9	203.1	203.5	202.1	202.8	202.1	201.8
45°	190.2	190.8	191.0	190.0	191.0	190.8	190.2	189.8	189.2	189.0	188.8
47.5°	178.2	178.3	178.2	179.1	178.2	178.3	178.2	177.6	176.7	176.4	175.4
50°	169.8	169.3	169.8	169.3	169.8	169.3	169.8	168.7	168.1	167.1	166.3
52.5°	160.9	161.0	160.7	160.6	160.7	161.0	160.9	159.5	159.3	158.8	157.6
55°	146.9	147.2	147.0	147.0	147.0	147.2	146.9	146.1	145.9	144.6	143.4
57.5°	132.4	132.8	133.0	132.2	133.0	132.8	132.4	132.2	132.2	130.8	129.6
60°	122.3	123.3	123.1	122.8	123.1	123.3	122.3	122.5	122.0	121.1	120.3
62.5°	113.1	113.5	113.4	113.3	113.4	113.5	113.1	112.2	111.9	111.1	110.3
65°	98.9	99.2	98.6	99.2	98.6	99.2	98.9	98.3	96.8	96.4	95.6
67.5°	83.5	83.6	84.1	84.4	84.1	83.6	83.5	83.7	82.8	82.0	81.9
70°	73.9	73.7	74.4	75.0	74.4	73.7	73.9	73.6	72.9	72.3	71.5
72.5°	63.8	64.3	64.1	64.6	64.1	64.3	63.8	63.9	63.4	62.6	61.8
75°	49.2	49.8	49.7	50.2	49.7	49.8	49.2	49.7	49.2	48.4	47.6
77.5°	35.6	35.7	35.6	35.9	35.6	35.7	35.6	35.9	35.5	35.8	34.8
80°	27.1	26.8	26.3	27.1	26.3	26.8	27.1	27.1	26.6	27.1	26.6
82.5°	18.9	19.1	18.7	18.7	18.7	19.1	18.9	19.4	19.1	19.4	18.7
85°	8.7	8.5	8.1	8.1	8.1	8.5	8.7	8.7	9.3	8.9	8.9
87.5°	10.6	10.5	10.5	10.4	10.5	10.5	10.6	10.5	10.5	11.0	11.1
90°	44.9	45.1	45.4	45.7	45.4	45.1	44.9	44.5	44.7	45.3	45.8
92.5°	43.3	43.4	43.5	43.5	43.5	43.4	43.3	43.3	43.2	43.1	43.0
95°	85.2	84.5	83.9	83.4	83.9	84.5	85.2	85.7	86.1	86.1	86.1
97.5°	144.5	144.5	144.5	144.4	144.5	144.5	144.5	144.6	144.6	144.6	144.6
100°	185.0	184.8	184.5	184.1	184.5	184.8	185.0	185.4	185.5	185.5	185.5
102.5°	230.2	230.0	229.6	229.3	229.6	230.0	230.2	230.5	230.6	230.3	230.1
105°	298.5	298.5	298.5	298.5	298.5	298.5	298.5	298.5	298.1	297.6	296.9
107.5°	367.7	366.2	364.9	363.5	364.9	366.2	367.7	369.0	369.5	369.3	369.1
110°	416.7	415.8	414.9	414.0	414.9	415.8	416.7	417.6	418.1	418.1	418.1



TEST NUMBER: P331490-940

CATALOG NUMBER: S122DIW-S290D1440U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	464.4	463.8	463.1	462.4	463.1	463.8	464.4	465.0	465.7	466.5	467.2
115°	540.4	539.5	538.6	537.7	538.6	539.5	540.4	541.3	541.9	542.2	542.5
117.5°	612.2	611.3	610.4	609.5	610.4	611.3	612.2	613.1	613.9	614.7	615.4
120°	662.7	661.8	660.9	660.0	660.9	661.8	662.7	663.6	664.1	664.1	664.1
122.5°	711.5	710.9	710.2	709.5	710.2	710.9	711.5	712.1	712.8	713.5	714.3
125°	786.0	785.7	785.4	785.1	785.4	785.7	786.0	786.3	786.8	787.7	788.6
127.5°	856.8	855.8	854.9	853.9	854.9	855.8	856.8	857.7	858.7	859.8	860.9
130°	907.0	905.8	904.6	903.4	904.6	905.8	907.0	908.1	909.0	909.6	910.3
132.5°	953.6	952.6	951.6	950.7	951.6	952.6	953.6	954.5	955.6	957.0	958.3
135°	1027.1	1026.2	1025.3	1024.4	1025.3	1026.2	1027.1	1028.0	1028.6	1028.9	1029.1
137.5°	1094.7	1093.4	1092.3	1091.0	1092.3	1093.4	1094.7	1095.8	1096.5	1096.8	1097.0
140°	1140.9	1139.7	1138.4	1137.3	1138.4	1139.7	1140.9	1142.1	1142.6	1142.6	1142.6
142.5°	1182.9	1181.6	1180.4	1179.2	1180.4	1181.6	1182.9	1184.0	1184.5	1184.3	1184.0
145°	1245.7	1244.6	1243.3	1242.2	1243.3	1244.6	1245.7	1246.9	1247.3	1247.1	1246.8
147.5°	1301.7	1300.6	1299.5	1298.3	1299.5	1300.6	1301.7	1302.9	1303.1	1302.4	1301.8
150°	1337.6	1336.7	1335.8	1334.9	1335.8	1336.7	1337.6	1338.5	1338.5	1337.6	1336.7
152.5°	1372.7	1371.5	1370.5	1369.3	1370.5	1371.5	1372.7	1373.9	1373.9	1372.7	1371.5
155°	1418.3	1417.4	1416.5	1415.6	1416.5	1417.4	1418.3	1419.2	1418.8	1417.4	1415.9
157.5°	1459.6	1458.2	1456.8	1455.4	1456.8	1458.2	1459.6	1461.1	1460.8	1458.7	1456.7
160°	1483.6	1482.5	1481.3	1480.1	1481.3	1482.5	1483.6	1484.9	1484.5	1482.7	1481.0
162.5°	1505.9	1504.5	1503.1	1501.6	1503.1	1504.5	1505.9	1507.3	1507.0	1505.0	1503.0
165°	1534.3	1532.9	1531.3	1529.8	1531.3	1532.9	1534.3	1535.8	1535.5	1533.4	1531.3
167.5°	1557.6	1556.0	1554.5	1552.9	1554.5	1556.0	1557.6	1559.2	1558.9	1556.8	1554.7
170°	1570.1	1568.3	1566.6	1564.8	1566.6	1568.3	1570.1	1571.9	1571.8	1569.7	1567.6
172.5°	1579.8	1578.1	1576.3	1574.5	1576.3	1578.1	1579.8	1581.6	1581.4	1579.4	1577.3
175°	1590.3	1588.5	1586.7	1584.9	1586.7	1588.5	1590.3	1592.1	1592.0	1589.8	1587.8
177.5°	1594.1	1592.7	1591.2	1589.7	1591.2	1592.7	1594.1	1595.5	1595.5	1594.1	1592.7
180°	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0



TEST NUMBER: P331490-940

CATALOG NUMBER: S122DIW-S290D1440U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1
2.5°	506.5	508.3	511.0	514.0	515.8	519.2	520.1	521.7	523.2	526.6	530.1
5°	477.2	480.1	486.8	490.4	495.4	501.3	505.2	509.3	513.7	521.4	528.5
7.5°	445.9	450.6	459.0	465.7	473.0	481.3	487.4	495.4	502.1	513.0	523.3
10°	425.0	431.7	439.2	447.3	457.4	466.3	474.8	484.9	493.0	506.0	518.2
12.5°	406.2	407.2	417.9	426.9	440.7	451.7	461.5	474.6	482.5	497.9	510.7
15°	373.4	379.4	389.1	396.2	412.6	426.6	440.4	454.0	463.1	482.1	498.9
17.5°	345.6	351.2	361.2	372.8	384.6	398.5	416.3	430.7	443.1	464.8	484.7
20°	328.1	335.0	345.2	357.1	367.5	382.6	398.1	414.5	427.8	452.4	475.6
22.5°	313.3	318.7	326.9	338.7	349.9	363.8	380.7	398.6	412.6	439.1	462.6
25°	292.3	296.8	302.0	311.7	324.5	339.7	352.8	372.6	393.0	417.7	446.2
27.5°	273.4	276.6	281.2	289.8	299.7	313.9	328.5	347.1	367.7	394.6	424.7
30°	261.9	263.9	268.6	275.7	285.4	296.6	311.4	329.1	350.3	377.4	407.3
32.5°	251.9	253.7	256.8	263.5	272.0	281.5	294.8	312.6	332.7	359.4	392.6
35°	236.8	238.2	240.9	246.3	251.0	260.3	271.4	287.7	306.5	332.0	366.4
37.5°	221.8	223.7	225.3	227.7	233.6	239.8	249.4	263.1	281.6	307.4	340.2
40°	211.9	213.5	216.0	217.0	221.8	227.3	235.1	247.7	266.4	289.9	321.9
42.5°	201.8	203.5	204.9	206.1	210.3	215.1	222.2	233.0	249.5	272.3	304.1
45°	188.2	188.4	189.8	192.1	194.0	197.5	202.6	211.9	224.6	246.1	274.9
47.5°	174.3	174.6	174.8	175.8	178.0	181.1	184.5	192.1	203.5	220.6	248.6
50°	165.1	164.7	165.1	165.9	167.3	170.0	173.8	179.2	188.6	204.6	230.3
52.5°	156.1	156.1	155.9	156.1	157.3	159.1	161.8	166.5	174.8	189.5	212.1
55°	142.6	141.6	141.8	141.0	142.9	143.2	145.3	149.1	156.4	166.5	187.8
57.5°	128.1	127.3	126.4	126.2	126.0	127.1	128.7	131.7	137.3	146.2	163.5
60°	118.9	117.9	116.6	116.3	116.3	116.9	117.7	119.9	125.2	133.0	147.2
62.5°	109.5	108.3	107.6	106.6	106.2	106.8	107.6	109.2	113.1	120.5	132.7
65°	95.0	93.5	92.6	92.4	91.9	91.4	91.8	93.4	96.4	102.3	112.0
67.5°	80.4	79.1	78.9	77.7	77.1	77.2	77.1	78.5	80.3	85.4	92.6
70°	70.9	69.9	69.5	68.5	68.0	67.7	67.2	68.5	70.3	74.5	80.8
72.5°	61.2	60.3	59.5	58.6	58.7	58.2	58.1	58.9	60.4	64.3	69.2
75°	47.2	47.4	46.4	45.4	45.2	44.8	44.8	45.4	46.0	49.0	52.9
77.5°	34.2	34.1	33.3	32.9	32.7	32.3	32.7	33.1	33.4	35.5	38.3
80°	26.1	26.1	25.1	25.1	24.9	24.3	24.9	24.5	25.3	27.4	29.3
82.5°	18.6	18.4	18.3	18.0	17.9	17.5	17.7	18.2	18.5	19.9	21.1
85°	9.1	9.1	8.9	8.7	8.9	8.7	8.9	9.1	9.3	9.9	11.0
87.5°	11.2	11.5	10.3	9.2	7.9	6.8	5.9	5.4	4.9	4.4	3.8
90°	46.5	47.1	40.5	33.9	27.4	20.8	15.7	12.1	8.5	4.9	1.3
92.5°	42.9	42.7	41.2	39.7	38.1	36.6	34.4	31.8	29.2	26.6	23.9
95°	86.1	86.1	85.4	84.8	84.3	83.6	81.9	78.8	75.9	72.9	69.9
97.5°	144.6	144.6	143.5	142.4	141.2	140.1	138.2	135.6	133.0	130.4	127.7
100°	185.5	185.5	184.6	183.7	182.8	181.9	180.3	177.9	175.5	173.1	170.8
102.5°	229.9	229.6	228.5	227.3	226.2	225.1	223.6	221.6	219.7	217.8	215.9
105°	296.3	295.8	295.2	294.5	294.0	293.4	292.6	291.7	290.8	289.9	289.0
107.5°	368.8	368.6	368.6	368.6	368.6	368.6	367.9	366.7	365.3	364.0	362.7
110°	418.1	418.1	418.1	418.1	418.1	418.1	417.1	415.4	413.6	411.8	410.0



TEST NUMBER: P331490-940

CATALOG NUMBER: S122DIW-S290D1440U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	467.9	468.6	468.9	469.1	469.3	469.6	468.8	467.0	465.2	463.4	461.6
115°	542.8	543.1	543.7	544.3	544.9	545.5	544.9	543.1	541.3	539.5	537.7
117.5°	616.1	616.8	618.4	620.1	621.8	623.5	623.1	620.7	618.3	615.9	613.6
120°	664.1	664.1	666.5	668.9	671.3	673.7	673.7	671.3	668.9	666.5	664.1
122.5°	715.0	715.7	717.4	719.1	720.8	722.4	721.8	718.9	716.0	713.2	710.3
125°	789.5	790.4	791.4	792.3	793.2	794.1	793.2	790.4	787.7	785.1	782.4
127.5°	861.9	863.1	864.2	865.2	866.3	867.4	866.2	862.8	859.3	856.0	852.6
130°	910.9	911.4	912.0	912.7	913.2	913.8	912.2	908.3	904.5	900.5	896.6
132.5°	959.6	960.9	960.8	960.6	960.6	960.5	958.8	955.6	952.4	949.3	946.1
135°	1029.5	1029.7	1029.1	1028.6	1028.0	1027.3	1025.4	1022.1	1018.9	1015.6	1012.3
137.5°	1097.3	1097.5	1096.7	1095.9	1095.2	1094.4	1092.6	1089.9	1087.3	1084.6	1081.9
140°	1142.6	1142.6	1141.2	1139.7	1138.2	1136.7	1134.6	1131.9	1129.3	1126.5	1123.8
142.5°	1183.7	1183.6	1182.5	1181.5	1180.4	1179.5	1177.6	1174.9	1172.2	1169.6	1166.9
145°	1246.4	1246.2	1244.4	1242.6	1240.8	1239.0	1237.1	1234.9	1232.9	1230.8	1228.7
147.5°	1301.2	1300.5	1299.3	1298.1	1296.9	1295.7	1293.9	1291.4	1288.8	1286.3	1283.8
150°	1335.8	1334.9	1333.7	1332.5	1331.3	1330.1	1328.6	1326.9	1325.1	1323.2	1321.4
152.5°	1370.5	1369.3	1367.9	1366.5	1365.0	1363.6	1362.0	1360.1	1358.3	1356.6	1354.8
155°	1414.3	1412.8	1411.9	1411.0	1410.2	1409.3	1408.4	1407.5	1406.6	1405.7	1404.8
157.5°	1454.6	1452.7	1452.2	1451.6	1451.1	1450.5	1449.9	1449.4	1448.8	1448.1	1447.5
160°	1479.2	1477.4	1477.1	1476.8	1476.5	1476.2	1475.8	1475.2	1474.5	1474.0	1473.4
162.5°	1500.9	1498.9	1498.6	1498.3	1498.0	1497.7	1497.5	1497.4	1497.3	1497.2	1497.0
165°	1529.2	1527.1	1527.1	1527.1	1527.1	1527.1	1527.3	1527.6	1527.9	1528.2	1528.5
167.5°	1552.6	1550.5	1550.6	1550.7	1550.7	1550.8	1551.2	1552.1	1553.0	1553.9	1554.8
170°	1565.5	1563.4	1563.7	1564.1	1564.3	1564.6	1565.2	1566.1	1567.0	1567.9	1568.8
172.5°	1575.2	1573.1	1573.4	1573.7	1574.0	1574.3	1574.9	1575.8	1576.7	1577.6	1578.5
175°	1585.7	1583.6	1584.2	1584.7	1585.4	1586.0	1586.7	1587.6	1588.5	1589.4	1590.3
177.5°	1591.2	1589.7	1590.3	1590.7	1591.2	1591.7	1592.3	1593.0	1593.8	1594.5	1595.2
180°	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0



TEST NUMBER: P331490-940

CATALOG NUMBER: S122DIW-S290D1440U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1	527.1
2.5°	529.9	530.7	533.2	535.8	538.8	539.6	540.8	539.8	539.4	542.4	544.7
5°	531.4	534.9	542.1	548.6	554.0	557.9	562.0	563.6	566.6	570.8	576.1
7.5°	529.6	536.7	547.9	557.3	567.6	575.0	580.8	585.8	591.7	599.8	608.6
10°	527.7	537.2	550.8	562.3	574.9	584.4	592.3	600.0	608.9	620.1	631.6
12.5°	524.1	535.4	552.4	566.1	582.2	591.6	602.2	618.8	628.4	643.9	660.1
15°	516.9	529.5	553.2	570.0	588.3	606.1	625.7	641.5	657.3	666.5	689.3
17.5°	506.3	524.7	551.0	570.6	593.8	621.8	643.9	661.8	680.0	694.8	706.3
20°	497.7	517.7	547.8	571.2	598.8	628.9	654.2	672.5	688.3	700.7	707.8
22.5°	486.9	512.1	541.3	568.8	604.0	633.8	660.4	674.8	688.0	694.0	696.8
25°	469.8	500.2	533.2	566.8	606.5	638.1	662.4	671.1	674.9	669.1	659.3
27.5°	451.3	485.2	523.8	562.9	604.9	635.3	652.7	651.4	644.9	625.8	610.6
30°	437.6	474.8	516.3	559.1	601.2	630.8	640.9	630.8	616.0	594.8	573.0
32.5°	423.1	461.7	508.4	553.6	594.4	620.5	622.6	605.2	582.3	558.1	531.1
35°	401.3	443.0	493.5	541.3	580.0	596.4	586.7	555.8	528.7	495.7	458.8
37.5°	376.6	422.7	473.2	523.3	558.3	562.6	538.4	506.0	467.7	428.9	385.5
40°	358.1	407.0	459.1	509.4	540.5	536.0	505.2	469.6	424.0	376.6	336.3
42.5°	341.6	390.4	443.4	492.9	517.7	505.5	469.6	425.8	376.8	332.2	295.2
45°	313.0	363.2	417.5	465.3	479.5	457.4	409.8	361.1	313.0	275.7	246.6
47.5°	285.2	334.8	388.6	430.6	435.6	405.9	353.9	303.9	262.4	232.1	211.5
50°	264.7	314.6	367.8	405.4	403.7	367.8	314.4	266.8	232.1	207.6	193.9
52.5°	246.5	293.6	344.6	378.8	370.1	331.1	280.0	237.7	209.3	190.1	177.6
55°	217.9	261.5	310.1	337.5	321.6	278.3	235.1	201.2	180.0	165.7	156.0
57.5°	189.7	230.5	272.2	289.0	271.5	231.5	195.6	170.9	155.0	144.4	138.0
60°	172.2	207.9	244.9	259.5	238.6	203.0	174.6	152.6	139.7	131.1	125.4
62.5°	154.7	186.6	221.6	229.5	210.4	180.3	155.2	136.8	126.4	118.6	113.2
65°	130.8	157.0	183.5	188.8	171.2	147.8	128.0	116.1	106.7	101.1	96.8
67.5°	107.4	128.3	147.1	151.3	135.9	119.8	105.4	95.0	88.7	84.0	80.3
70°	93.4	110.0	125.4	128.9	116.5	102.1	91.1	82.8	77.1	73.1	69.6
72.5°	78.6	92.5	105.3	107.6	97.6	86.5	77.6	71.0	66.0	63.4	60.1
75°	60.2	68.3	78.2	78.8	72.1	65.5	58.6	54.3	51.6	48.4	46.8
77.5°	42.4	48.8	54.5	55.6	51.6	47.1	43.2	39.9	37.6	36.1	34.6
80°	32.4	37.5	39.9	41.3	38.5	35.2	33.0	30.8	29.3	28.4	27.4
82.5°	23.2	26.3	28.5	29.7	28.1	26.1	24.0	22.6	21.6	20.8	20.4
85°	11.8	13.2	14.6	15.0	14.6	13.7	12.6	12.6	11.9	11.8	11.8
87.5°	5.0	6.4	7.1	8.3	9.0	10.3	11.7	12.8	13.9	13.6	13.4
90°	4.9	8.5	12.1	15.7	20.8	27.4	33.9	40.5	47.1	46.5	45.8
92.5°	26.6	29.2	31.8	34.4	36.6	38.1	39.7	41.2	42.7	42.9	43.0
95°	72.9	75.9	78.8	81.9	83.6	84.3	84.8	85.4	86.1	86.1	86.1
97.5°	130.4	133.0	135.6	138.2	140.1	141.2	142.4	143.5	144.6	144.6	144.6
100°	173.1	175.5	177.9	180.3	181.9	182.8	183.7	184.6	185.5	185.5	185.5
102.5°	217.8	219.7	221.6	223.6	225.1	226.2	227.3	228.5	229.6	229.9	230.1
105°	289.9	290.8	291.7	292.6	293.4	294.0	294.5	295.2	295.8	296.3	296.9
107.5°	364.0	365.3	366.7	367.9	368.6	368.6	368.6	368.6	368.6	368.8	369.1
110°	411.8	413.6	415.4	417.1	418.1	418.1	418.1	418.1	418.1	418.1	418.1



TEST NUMBER: P331490-940

CATALOG NUMBER: S122DIW-S290D1440U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	463.4	465.2	467.0	468.8	469.6	469.3	469.1	468.9	468.6	467.9	467.2
115°	539.5	541.3	543.1	544.9	545.5	544.9	544.3	543.7	543.1	542.8	542.5
117.5°	615.9	618.3	620.7	623.1	623.5	621.8	620.1	618.4	616.8	616.1	615.4
120°	666.5	668.9	671.3	673.7	673.7	671.3	668.9	666.5	664.1	664.1	664.1
122.5°	713.2	716.0	718.9	721.8	722.4	720.8	719.1	717.4	715.7	715.0	714.3
125°	785.1	787.7	790.4	793.2	794.1	793.2	792.3	791.4	790.4	789.5	788.6
127.5°	856.0	859.3	862.8	866.2	867.4	866.3	865.2	864.2	863.1	861.9	860.9
130°	900.5	904.5	908.3	912.2	913.8	913.2	912.7	912.0	911.4	910.9	910.3
132.5°	949.3	952.4	955.6	958.8	960.5	960.6	960.6	960.8	960.9	959.6	958.3
135°	1015.6	1018.9	1022.1	1025.4	1027.3	1028.0	1028.6	1029.1	1029.7	1029.5	1029.1
137.5°	1084.6	1087.3	1089.9	1092.6	1094.4	1095.2	1095.9	1096.7	1097.5	1097.3	1097.0
140°	1126.5	1129.3	1131.9	1134.6	1136.7	1138.2	1139.7	1141.2	1142.6	1142.6	1142.6
142.5°	1169.6	1172.2	1174.9	1177.6	1179.5	1180.4	1181.5	1182.5	1183.6	1183.7	1184.0
145°	1230.8	1232.9	1234.9	1237.1	1239.0	1240.8	1242.6	1244.4	1246.2	1246.4	1246.8
147.5°	1286.3	1288.8	1291.4	1293.9	1295.7	1296.9	1298.1	1299.3	1300.5	1301.2	1301.8
150°	1323.2	1325.1	1326.9	1328.6	1330.1	1331.3	1332.5	1333.7	1334.9	1335.8	1336.7
152.5°	1356.6	1358.3	1360.1	1362.0	1363.6	1365.0	1366.5	1367.9	1369.3	1370.5	1371.5
155°	1405.7	1406.6	1407.5	1408.4	1409.3	1410.2	1411.0	1411.9	1412.8	1414.3	1415.9
157.5°	1448.1	1448.8	1449.4	1449.9	1450.5	1451.1	1451.6	1452.2	1452.7	1454.6	1456.7
160°	1474.0	1474.5	1475.2	1475.8	1476.2	1476.5	1476.8	1477.1	1477.4	1479.2	1481.0
162.5°	1497.2	1497.3	1497.4	1497.5	1497.7	1498.0	1498.3	1498.6	1498.9	1500.9	1503.0
165°	1528.2	1527.9	1527.6	1527.3	1527.1	1527.1	1527.1	1527.1	1527.1	1529.2	1531.3
167.5°	1553.9	1553.0	1552.1	1551.2	1550.8	1550.7	1550.7	1550.6	1550.5	1552.6	1554.7
170°	1567.9	1567.0	1566.1	1565.2	1564.6	1564.3	1564.1	1563.7	1563.4	1565.5	1567.6
172.5°	1577.6	1576.7	1575.8	1574.9	1574.3	1574.0	1573.7	1573.4	1573.1	1575.2	1577.3
175°	1589.4	1588.5	1587.6	1586.7	1586.0	1585.4	1584.7	1584.2	1583.6	1585.7	1587.8
177.5°	1594.5	1593.8	1593.0	1592.3	1591.7	1591.2	1590.7	1590.3	1589.7	1591.2	1592.7
180°	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0



TEST NUMBER: P331490-940

CATALOG NUMBER: S122DIW-S290D1440U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	527.1	527.1	527.1	527.1	527.1	527.1	527.1
2.5°	546.7	548.9	548.9	549.3	551.9	551.5	551.3
5°	581.8	585.2	585.6	589.2	591.7	590.8	588.6
7.5°	614.8	621.3	626.2	628.8	632.0	634.0	633.1
10°	641.1	650.4	656.1	660.0	664.6	668.1	666.8
12.5°	664.9	676.0	683.9	690.5	691.0	695.4	692.4
15°	702.1	713.8	715.1	719.9	723.8	723.4	723.5
17.5°	714.3	718.1	718.9	719.0	719.1	717.6	714.5
20°	710.0	708.6	705.2	702.5	697.9	697.2	693.2
22.5°	689.2	684.7	676.1	670.4	663.2	661.3	660.1
25°	648.5	638.5	624.7	611.5	607.9	600.8	602.8
27.5°	592.4	576.9	562.0	551.3	541.6	531.0	534.0
30°	553.0	535.6	514.5	498.3	487.9	477.9	476.0
32.5°	506.0	480.5	457.0	442.7	426.9	420.4	413.5
35°	425.0	400.0	376.7	356.7	345.2	336.3	328.1
37.5°	352.1	323.4	304.6	288.4	280.0	274.9	276.3
40°	306.9	281.8	268.0	255.7	247.9	244.3	245.1
42.5°	270.3	251.5	240.1	231.7	226.2	224.2	223.7
45°	228.7	218.2	208.8	204.0	201.3	199.1	197.7
47.5°	200.4	191.7	186.5	183.6	181.3	179.1	179.0
50°	183.3	177.6	174.0	170.9	169.2	167.6	169.0
52.5°	170.3	165.1	161.5	158.8	158.1	156.7	156.6
55°	151.1	147.0	144.5	142.0	140.8	140.0	138.9
57.5°	133.6	129.7	127.3	125.8	123.5	122.7	122.3
60°	121.1	118.1	115.7	113.6	112.6	111.0	111.0
62.5°	109.6	106.6	104.3	102.8	101.1	100.5	100.7
65°	93.0	90.5	88.3	86.7	86.3	85.1	85.5
67.5°	77.7	76.1	73.7	72.8	72.1	71.4	70.9
70°	67.4	65.8	64.6	63.4	62.8	62.8	62.8
72.5°	58.9	56.9	56.2	54.7	55.0	54.4	53.7
75°	45.6	44.3	43.8	43.2	42.2	42.2	42.2
77.5°	33.5	33.2	32.5	31.8	31.6	31.4	31.5
80°	25.9	25.7	25.3	25.3	24.9	24.7	24.3
82.5°	20.0	19.4	19.2	19.0	18.9	18.9	18.8
85°	11.3	11.0	11.0	11.1	10.7	10.7	11.0
87.5°	13.5	13.3	13.1	13.2	13.4	13.3	13.4
90°	45.3	44.7	44.5	44.9	45.1	45.4	45.7
92.5°	43.1	43.2	43.3	43.3	43.4	43.5	43.5
95°	86.1	86.1	85.7	85.2	84.5	83.9	83.4
97.5°	144.6	144.6	144.6	144.5	144.5	144.5	144.4
100°	185.5	185.5	185.4	185.0	184.8	184.5	184.1
102.5°	230.3	230.6	230.5	230.2	230.0	229.6	229.3
105°	297.6	298.1	298.5	298.5	298.5	298.5	298.5
107.5°	369.3	369.5	369.0	367.7	366.2	364.9	363.5
110°	418.1	418.1	417.6	416.7	415.8	414.9	414.0



TEST NUMBER: P331490-940

CATALOG NUMBER: S122DIW-S290D1440U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	466.5	465.7	465.0	464.4	463.8	463.1	462.4
115°	542.2	541.9	541.3	540.4	539.5	538.6	537.7
117.5°	614.7	613.9	613.1	612.2	611.3	610.4	609.5
120°	664.1	664.1	663.6	662.7	661.8	660.9	660.0
122.5°	713.5	712.8	712.1	711.5	710.9	710.2	709.5
125°	787.7	786.8	786.3	786.0	785.7	785.4	785.1
127.5°	859.8	858.7	857.7	856.8	855.8	854.9	853.9
130°	909.6	909.0	908.1	907.0	905.8	904.6	903.4
132.5°	957.0	955.6	954.5	953.6	952.6	951.6	950.7
135°	1028.9	1028.6	1028.0	1027.1	1026.2	1025.3	1024.4
137.5°	1096.8	1096.5	1095.8	1094.7	1093.4	1092.3	1091.0
140°	1142.6	1142.6	1142.1	1140.9	1139.7	1138.4	1137.3
142.5°	1184.3	1184.5	1184.0	1182.9	1181.6	1180.4	1179.2
145°	1247.1	1247.3	1246.9	1245.7	1244.6	1243.3	1242.2
147.5°	1302.4	1303.1	1302.9	1301.7	1300.6	1299.5	1298.3
150°	1337.6	1338.5	1338.5	1337.6	1336.7	1335.8	1334.9
152.5°	1372.7	1373.9	1373.9	1372.7	1371.5	1370.5	1369.3
155°	1417.4	1418.8	1419.2	1418.3	1417.4	1416.5	1415.6
157.5°	1458.7	1460.8	1461.1	1459.6	1458.2	1456.8	1455.4
160°	1482.7	1484.5	1484.9	1483.6	1482.5	1481.3	1480.1
162.5°	1505.0	1507.0	1507.3	1505.9	1504.5	1503.1	1501.6
165°	1533.4	1535.5	1535.8	1534.3	1532.9	1531.3	1529.8
167.5°	1556.8	1558.9	1559.2	1557.6	1556.0	1554.5	1552.9
170°	1569.7	1571.8	1571.9	1570.1	1568.3	1566.6	1564.8
172.5°	1579.4	1581.4	1581.6	1579.8	1578.1	1576.3	1574.5
175°	1589.8	1592.0	1592.1	1590.3	1588.5	1586.7	1584.9
177.5°	1594.1	1595.5	1595.5	1594.1	1592.7	1591.2	1589.7
180°	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0

(END OF REPORT)