

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331550-940

Luminaire Tested: **S122DIW-S675D1440U940-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331550-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S675D1440U940-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1440 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7073.8 lumens
Efficiency: N/A
Efficacy: 103.9 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 68.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331550-940

CATALOG NUMBER: S122DIW-S675D1440U940-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331550-940

CATALOG NUMBER: S122DIW-S675D1440U940-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	37
1	95	91	87	84	86	83	80	77	67	65	63	53	51	50	40	39	38	32
2	87	80	74	69	79	73	68	64	59	56	53	47	44	42	35	34	32	27
3	80	71	64	58	72	64	58	54	53	48	45	42	39	36	32	30	28	23
4	73	63	55	49	66	57	51	46	47	42	38	37	34	31	28	26	24	20
5	67	56	48	42	61	51	44	39	42	37	33	34	30	27	26	23	22	18
6	62	50	42	37	56	46	39	34	38	33	29	30	27	24	23	21	19	16
7	57	45	38	32	52	42	35	30	34	29	26	28	24	21	22	19	17	14
8	53	41	34	29	48	38	31	27	31	26	23	25	22	19	20	17	15	13
9	49	38	30	25	45	35	28	24	29	24	21	23	20	17	18	16	14	12
10	46	34	27	23	42	32	26	21	27	22	18	22	18	16	17	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	19125	19125	19125	19125
5°	21441	19248	17057	19248
10°	24568	19090	14762	19090
15°	27178	18740	13041	18740
20°	26764	18364	11888	18364
25°	24134	17865	11158	17865
30°	19943	17066	10625	17066
35°	14534	16232	10247	16232
40°	11609	15247	10037	15247
45°	10145	14104	9750	14104
50°	9535	12999	9560	12999
55°	8791	11879	9303	11879
60°	8054	10685	8909	10685
65°	7339	9616	8520	9616
70°	6661	8573	7950	8573
75°	5908	7411	7043	7411
80°	5086	6137	5672	6137
85°	4557	4557	3372	4557



TEST NUMBER: P331550-940

CATALOG NUMBER: S122DIW-S675D1440U940-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	112.8	1.6
10°-20°	327.9	4.6
20°-30°	475.9	6.7
30°-40°	502.2	7.1
40°-50°	444.7	6.3
50°-60°	354.9	5.0
60°-70°	241.2	3.4
70°-80°	123.7	1.7
80°-90°	36.2	0.5
90°-100°	100.9	1.4
100°-110°	313.5	4.4
110°-120°	535.9	7.6
120°-130°	704.7	10.0
130°-140°	791.0	11.2
140°-150°	775.6	11.0
150°-160°	650.5	9.2
160°-170°	431.5	6.1
170°-180°	150.8	2.1
0°-30°	916.7	13.0
0°-40°	1418.9	20.1
0°-60°	2218.4	31.4
0°-90°	2619.5	37.0
90°-120°	950.3	13.4
90°-150°	3221.6	45.5
90°-180°	4454.0	63.0
0°-180°	7073.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1184	1184	1184	1184	1184	
5°	1323	1188	1052	1188	1323	132
15°	1626	1121	780	1121	1626	449
25°	1355	1003	626	1003	1355	612
35°	737	824	520	824	737	480
45°	444	618	427	618	444	349
55°	312	422	330	422	312	280
65°	192	252	223	252	192	191
75°	95	119	113	119	95	101
85°	25	25	18	25	25	28
90°	46	1	46	1	46	21
95°	83	70	83	70	83	93
105°	298	289	298	289	298	314
115°	538	538	538	538	538	531
125°	785	782	785	782	785	700
135°	1024	1012	1024	1012	1024	789
145°	1242	1229	1242	1229	1242	776
155°	1416	1405	1416	1405	1416	651
165°	1530	1528	1530	1528	1530	431
175°	1585	1590	1585	1590	1585	151
180°	1593	1593	1593	1593	1593	



TEST NUMBER: P331550-940

CATALOG NUMBER: S122DIW-S675D1440U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5
2.5°	1239.0	1239.4	1240.2	1234.3	1233.6	1233.6	1228.5	1224.1	1219.1	1212.1	1212.8
5°	1322.9	1327.8	1329.6	1324.2	1316.0	1315.1	1307.3	1294.6	1282.7	1273.2	1266.4
7.5°	1422.8	1424.8	1420.3	1413.1	1407.0	1396.2	1381.7	1367.6	1347.8	1329.7	1316.3
10°	1498.5	1501.3	1493.5	1483.1	1474.4	1461.7	1440.7	1419.3	1393.4	1368.3	1348.3
12.5°	1556.0	1562.8	1552.9	1551.5	1536.7	1519.2	1494.2	1483.5	1446.9	1412.0	1390.5
15°	1625.9	1625.5	1626.5	1617.8	1606.9	1604.1	1577.7	1549.1	1497.6	1477.1	1441.6
17.5°	1605.8	1612.7	1615.9	1615.8	1615.5	1613.8	1605.3	1587.2	1561.5	1528.2	1487.2
20°	1557.7	1566.8	1568.2	1578.7	1584.6	1592.3	1595.4	1590.5	1574.6	1546.8	1511.3
22.5°	1483.5	1485.9	1490.2	1506.5	1519.4	1538.7	1548.9	1565.8	1559.6	1546.0	1516.4
25°	1354.7	1350.1	1366.1	1374.2	1403.8	1434.8	1457.1	1481.7	1503.5	1516.7	1508.1
27.5°	1200.1	1193.3	1217.1	1238.9	1262.9	1296.5	1331.2	1372.3	1406.4	1449.1	1463.7
30°	1069.7	1073.8	1096.6	1119.8	1156.2	1203.5	1242.7	1287.8	1336.5	1384.3	1417.5
32.5°	929.2	944.9	959.3	994.9	1026.9	1079.8	1137.1	1193.5	1254.2	1308.5	1359.9
35°	737.4	755.6	775.7	801.6	846.7	899.0	955.0	1031.0	1113.9	1188.1	1249.1
37.5°	620.7	617.8	629.3	648.0	684.6	726.7	791.2	866.4	963.9	1051.1	1137.1
40°	550.8	548.9	557.1	574.4	602.3	633.2	689.6	755.6	846.2	952.7	1055.2
42.5°	502.7	503.8	508.4	520.6	539.6	565.1	607.3	663.5	746.5	846.8	956.8
45°	444.3	447.5	452.5	458.4	469.3	490.3	513.9	554.0	619.6	703.3	811.6
47.5°	402.3	402.3	407.4	412.6	419.1	430.9	450.2	475.3	521.6	589.8	682.9
50°	379.6	376.5	380.1	384.1	391.0	399.2	412.0	435.6	466.5	521.7	599.5
52.5°	352.0	352.0	355.3	356.9	363.0	371.1	382.8	399.2	427.2	470.3	534.3
55°	312.3	314.5	316.4	319.1	324.6	330.5	339.6	350.5	372.4	404.7	452.0
57.5°	274.9	275.6	277.5	282.7	286.1	291.6	300.2	310.1	324.4	348.3	383.9
60°	249.4	249.4	253.1	255.4	259.9	265.4	272.2	281.8	294.5	314.1	342.8
62.5°	226.1	225.8	227.2	231.0	234.4	239.5	246.4	254.5	266.4	283.8	307.5
65°	192.1	191.2	193.9	194.8	198.5	203.5	208.9	217.6	227.1	239.9	260.8
67.5°	159.3	160.4	161.8	163.6	165.6	170.9	174.5	180.7	188.7	199.3	213.5
70°	141.1	141.1	141.1	142.5	145.2	147.9	151.6	156.6	164.3	173.4	186.2
72.5°	120.7	122.2	123.6	122.8	126.3	127.9	132.2	135.1	142.5	148.3	159.6
75°	94.7	94.7	94.7	96.9	98.4	99.7	102.5	105.1	108.8	116.1	122.0
77.5°	70.6	70.4	70.9	71.4	72.9	74.5	75.3	77.8	81.2	84.5	89.6
80°	54.7	55.6	56.0	56.9	56.9	57.8	58.2	61.4	63.8	66.0	69.2
82.5°	42.3	42.4	42.5	42.7	43.1	43.6	44.8	45.8	46.6	48.5	51.0
85°	24.6	24.2	24.2	25.1	24.6	24.6	25.5	26.4	26.4	26.8	28.2
87.5°	18.6	18.5	18.8	18.5	18.4	18.7	18.9	18.6	19.1	19.6	18.6
90°	45.7	45.4	45.1	44.9	44.5	44.7	45.3	45.8	46.5	47.1	40.5
92.5°	43.5	43.5	43.4	43.3	43.3	43.2	43.1	43.0	42.9	42.7	41.2
95°	83.4	83.9	84.5	85.2	85.7	86.1	86.1	86.1	86.1	86.1	85.4
97.5°	144.4	144.5	144.5	144.5	144.6	144.6	144.6	144.6	144.6	144.6	143.5
100°	184.1	184.5	184.8	185.0	185.4	185.5	185.5	185.5	185.5	185.5	184.6
102.5°	229.3	229.6	230.0	230.2	230.5	230.6	230.3	230.1	229.9	229.6	228.5
105°	298.5	298.5	298.5	298.5	298.5	298.1	297.6	296.9	296.3	295.8	295.2
107.5°	363.5	364.9	366.2	367.7	369.0	369.5	369.3	369.1	368.8	368.6	368.6
110°	414.0	414.9	415.8	416.7	417.6	418.1	418.1	418.1	418.1	418.1	418.1



TEST NUMBER: P331550-940

CATALOG NUMBER: S122DIW-S675D1440U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	462.4	463.1	463.8	464.4	465.0	465.7	466.5	467.2	467.9	468.6	468.9
115°	537.7	538.6	539.5	540.4	541.3	541.9	542.2	542.5	542.8	543.1	543.7
117.5°	609.5	610.4	611.3	612.2	613.1	613.9	614.7	615.4	616.1	616.8	618.4
120°	660.0	660.9	661.8	662.7	663.6	664.1	664.1	664.1	664.1	664.1	666.5
122.5°	709.5	710.2	710.9	711.5	712.1	712.8	713.5	714.3	715.0	715.7	717.4
125°	785.1	785.4	785.7	786.0	786.3	786.8	787.7	788.6	789.5	790.4	791.4
127.5°	853.9	854.9	855.8	856.8	857.7	858.7	859.8	860.9	861.9	863.1	864.2
130°	903.4	904.6	905.8	907.0	908.1	909.0	909.6	910.3	910.9	911.4	912.0
132.5°	950.7	951.6	952.6	953.6	954.5	955.6	957.0	958.3	959.6	960.9	960.8
135°	1024.4	1025.3	1026.2	1027.1	1028.0	1028.6	1028.9	1029.1	1029.5	1029.7	1029.1
137.5°	1091.0	1092.3	1093.4	1094.7	1095.8	1096.5	1096.8	1097.0	1097.3	1097.5	1096.7
140°	1137.3	1138.4	1139.7	1140.9	1142.1	1142.6	1142.6	1142.6	1142.6	1142.6	1141.2
142.5°	1179.2	1180.4	1181.6	1182.9	1184.0	1184.5	1184.3	1184.0	1183.7	1183.6	1182.5
145°	1242.2	1243.3	1244.6	1245.7	1246.9	1247.3	1247.1	1246.8	1246.4	1246.2	1244.4
147.5°	1298.3	1299.5	1300.6	1301.7	1302.9	1303.1	1302.4	1301.8	1301.2	1300.5	1299.3
150°	1334.9	1335.8	1336.7	1337.6	1338.5	1338.5	1337.6	1336.7	1335.8	1334.9	1333.7
152.5°	1369.3	1370.5	1371.5	1372.7	1373.9	1373.9	1372.7	1371.5	1370.5	1369.3	1367.9
155°	1415.6	1416.5	1417.4	1418.3	1419.2	1418.8	1417.4	1415.9	1414.3	1412.8	1411.9
157.5°	1455.4	1456.8	1458.2	1459.6	1461.1	1460.8	1458.7	1456.7	1454.6	1452.7	1452.2
160°	1480.1	1481.3	1482.5	1483.6	1484.9	1484.5	1482.7	1481.0	1479.2	1477.4	1477.1
162.5°	1501.6	1503.1	1504.5	1505.9	1507.3	1507.0	1505.0	1503.0	1500.9	1498.9	1498.6
165°	1529.8	1531.3	1532.9	1534.3	1535.8	1535.5	1533.4	1531.3	1529.2	1527.1	1527.1
167.5°	1552.9	1554.5	1556.0	1557.6	1559.2	1558.9	1556.8	1554.7	1552.6	1550.5	1550.6
170°	1564.8	1566.6	1568.3	1570.1	1571.9	1571.8	1569.7	1567.6	1565.5	1563.4	1563.7
172.5°	1574.5	1576.3	1578.1	1579.8	1581.6	1581.4	1579.4	1577.3	1575.2	1573.1	1573.4
175°	1584.9	1586.7	1588.5	1590.3	1592.1	1592.0	1589.8	1587.8	1585.7	1583.6	1584.2
177.5°	1589.7	1591.2	1592.7	1594.1	1595.5	1595.5	1594.1	1592.7	1591.2	1589.7	1590.3
180°	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0



TEST NUMBER: P331550-940

CATALOG NUMBER: S122DIW-S675D1440U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5
2.5°	1215.4	1212.5	1210.7	1204.1	1198.3	1192.5	1190.6	1191.3	1183.4	1175.7	1172.4
5°	1262.8	1253.7	1245.0	1232.7	1218.2	1202.2	1194.0	1187.6	1171.7	1154.4	1144.4
7.5°	1305.2	1292.2	1275.5	1252.3	1231.2	1206.1	1190.2	1176.1	1152.7	1128.4	1113.4
10°	1331.1	1313.2	1291.8	1263.6	1237.7	1207.2	1185.8	1164.4	1137.1	1108.0	1089.8
12.5°	1353.3	1329.3	1308.2	1272.0	1241.4	1203.2	1177.8	1147.6	1118.9	1084.3	1066.5
15°	1406.1	1362.0	1321.9	1280.9	1243.1	1189.9	1161.7	1121.1	1083.3	1040.6	1020.1
17.5°	1447.0	1397.4	1334.3	1282.2	1238.1	1179.2	1137.7	1089.2	1044.6	995.6	967.8
20°	1470.3	1413.4	1345.6	1283.7	1230.8	1163.5	1118.5	1068.8	1016.5	961.4	931.3
22.5°	1484.2	1424.3	1357.3	1278.2	1216.3	1150.8	1094.0	1039.6	986.6	927.2	895.6
25°	1488.5	1433.9	1362.9	1273.6	1198.1	1123.9	1055.6	1002.8	938.6	883.1	837.1
27.5°	1466.9	1427.7	1359.4	1265.1	1177.1	1090.3	1014.2	954.4	886.6	826.3	780.2
30°	1440.3	1417.5	1351.0	1256.3	1160.3	1067.0	983.2	915.4	848.0	787.0	739.7
32.5°	1399.1	1394.2	1335.8	1243.9	1142.5	1037.5	950.8	882.3	807.6	747.7	702.6
35°	1318.3	1340.2	1303.2	1216.3	1108.8	995.5	901.8	823.5	746.1	688.8	646.4
37.5°	1210.0	1264.2	1254.5	1175.8	1063.5	949.9	846.3	764.5	690.7	632.8	591.3
40°	1135.2	1204.4	1214.5	1144.9	1031.5	914.5	804.8	723.4	651.4	598.6	556.7
42.5°	1055.2	1136.0	1163.5	1107.7	996.5	877.4	767.7	683.2	612.1	560.7	523.6
45°	920.9	1027.9	1077.5	1045.6	938.2	816.2	703.3	617.7	553.0	504.8	476.2
47.5°	795.3	912.2	978.9	967.7	873.3	752.4	640.9	558.7	495.8	457.3	431.6
50°	706.5	826.6	907.2	910.9	826.6	706.9	594.9	517.5	459.8	423.8	402.9
52.5°	629.3	744.0	831.9	851.1	774.5	659.6	553.8	476.8	425.9	392.8	374.1
55°	528.5	625.4	722.8	758.4	696.9	587.6	489.8	422.0	374.2	351.4	335.0
57.5°	439.3	520.2	610.2	649.4	611.5	518.0	426.2	367.4	328.6	308.6	296.0
60°	392.4	456.1	536.2	583.1	550.4	467.1	386.9	330.9	299.1	281.3	269.5
62.5°	348.7	405.1	472.9	515.8	497.9	419.4	347.6	298.2	270.6	254.0	245.5
65°	287.7	332.3	384.7	424.3	412.4	352.8	294.1	251.7	229.9	216.7	209.8
67.5°	236.9	269.1	305.4	340.1	330.6	288.3	241.2	208.2	191.9	180.6	176.5
70°	204.8	229.4	261.7	289.5	281.8	247.2	209.8	181.6	167.6	157.9	153.8
72.5°	174.2	194.5	219.1	241.8	236.6	207.9	176.7	155.4	144.5	135.7	132.3
75°	131.5	147.0	162.0	177.1	175.7	153.4	135.2	118.8	110.1	103.3	101.9
77.5°	97.1	105.8	116.0	124.9	122.4	109.7	95.4	86.1	79.6	75.1	74.4
80°	74.2	79.2	86.5	92.8	89.7	84.2	72.9	66.0	61.4	56.9	55.1
82.5°	53.8	58.9	63.2	66.6	64.2	59.1	52.1	47.4	44.7	41.6	40.8
85°	28.2	30.9	32.8	33.7	32.8	29.6	26.4	24.6	22.3	21.0	20.5
87.5°	17.7	16.4	15.1	14.8	13.0	12.3	10.1	8.3	8.6	9.0	9.0
90°	33.9	27.4	20.8	15.7	12.1	8.5	4.9	1.3	4.9	8.5	12.1
92.5°	39.7	38.1	36.6	34.4	31.8	29.2	26.6	23.9	26.6	29.2	31.8
95°	84.8	84.3	83.6	81.9	78.8	75.9	72.9	69.9	72.9	75.9	78.8
97.5°	142.4	141.2	140.1	138.2	135.6	133.0	130.4	127.7	130.4	133.0	135.6
100°	183.7	182.8	181.9	180.3	177.9	175.5	173.1	170.8	173.1	175.5	177.9
102.5°	227.3	226.2	225.1	223.6	221.6	219.7	217.8	215.9	217.8	219.7	221.6
105°	294.5	294.0	293.4	292.6	291.7	290.8	289.9	289.0	289.9	290.8	291.7
107.5°	368.6	368.6	368.6	367.9	366.7	365.3	364.0	362.7	364.0	365.3	366.7
110°	418.1	418.1	418.1	417.1	415.4	413.6	411.8	410.0	411.8	413.6	415.4



TEST NUMBER: P331550-940

CATALOG NUMBER: S122DIW-S675D1440U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	469.1	469.3	469.6	468.8	467.0	465.2	463.4	461.6	463.4	465.2	467.0
115°	544.3	544.9	545.5	544.9	543.1	541.3	539.5	537.7	539.5	541.3	543.1
117.5°	620.1	621.8	623.5	623.1	620.7	618.3	615.9	613.6	615.9	618.3	620.7
120°	668.9	671.3	673.7	673.7	671.3	668.9	666.5	664.1	666.5	668.9	671.3
122.5°	719.1	720.8	722.4	721.8	718.9	716.0	713.2	710.3	713.2	716.0	718.9
125°	792.3	793.2	794.1	793.2	790.4	787.7	785.1	782.4	785.1	787.7	790.4
127.5°	865.2	866.3	867.4	866.2	862.8	859.3	856.0	852.6	856.0	859.3	862.8
130°	912.7	913.2	913.8	912.2	908.3	904.5	900.5	896.6	900.5	904.5	908.3
132.5°	960.6	960.6	960.5	958.8	955.6	952.4	949.3	946.1	949.3	952.4	955.6
135°	1028.6	1028.0	1027.3	1025.4	1022.1	1018.9	1015.6	1012.3	1015.6	1018.9	1022.1
137.5°	1095.9	1095.2	1094.4	1092.6	1089.9	1087.3	1084.6	1081.9	1084.6	1087.3	1089.9
140°	1139.7	1138.2	1136.7	1134.6	1131.9	1129.3	1126.5	1123.8	1126.5	1129.3	1131.9
142.5°	1181.5	1180.4	1179.5	1177.6	1174.9	1172.2	1169.6	1166.9	1169.6	1172.2	1174.9
145°	1242.6	1240.8	1239.0	1237.1	1234.9	1232.9	1230.8	1228.7	1230.8	1232.9	1234.9
147.5°	1298.1	1296.9	1295.7	1293.9	1291.4	1288.8	1286.3	1283.8	1286.3	1288.8	1291.4
150°	1332.5	1331.3	1330.1	1328.6	1326.9	1325.1	1323.2	1321.4	1323.2	1325.1	1326.9
152.5°	1366.5	1365.0	1363.6	1362.0	1360.1	1358.3	1356.6	1354.8	1356.6	1358.3	1360.1
155°	1411.0	1410.2	1409.3	1408.4	1407.5	1406.6	1405.7	1404.8	1405.7	1406.6	1407.5
157.5°	1451.6	1451.1	1450.5	1449.9	1449.4	1448.8	1448.1	1447.5	1448.1	1448.8	1449.4
160°	1476.8	1476.5	1476.2	1475.8	1475.2	1474.5	1474.0	1473.4	1474.0	1474.5	1475.2
162.5°	1498.3	1498.0	1497.7	1497.5	1497.4	1497.3	1497.2	1497.0	1497.2	1497.3	1497.4
165°	1527.1	1527.1	1527.1	1527.3	1527.6	1527.9	1528.2	1528.5	1528.2	1527.9	1527.6
167.5°	1550.7	1550.7	1550.8	1551.2	1552.1	1553.0	1553.9	1554.8	1553.9	1553.0	1552.1
170°	1564.1	1564.3	1564.6	1565.2	1566.1	1567.0	1567.9	1568.8	1567.9	1567.0	1566.1
172.5°	1573.7	1574.0	1574.3	1574.9	1575.8	1576.7	1577.6	1578.5	1577.6	1576.7	1575.8
175°	1584.7	1585.4	1586.0	1586.7	1587.6	1588.5	1589.4	1590.3	1589.4	1588.5	1587.6
177.5°	1590.7	1591.2	1591.7	1592.3	1593.0	1593.8	1594.5	1595.2	1594.5	1593.8	1593.0
180°	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0



TEST NUMBER: P331550-940

CATALOG NUMBER: S122DIW-S675D1440U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5
2.5°	1168.8	1166.6	1159.0	1154.9	1148.3	1142.2	1138.2	1140.1	1141.5	1140.8	1139.6
5°	1135.2	1126.6	1113.4	1102.1	1093.9	1078.8	1072.5	1069.3	1066.6	1063.4	1060.2
7.5°	1095.4	1081.7	1062.8	1046.6	1031.3	1012.6	1002.0	995.6	989.1	981.9	975.5
10°	1067.0	1047.8	1027.9	1005.0	986.9	970.0	955.0	945.0	935.9	927.3	920.9
12.5°	1037.1	1015.1	990.3	959.2	939.1	915.1	912.8	895.1	880.9	875.6	868.1
15°	989.6	958.7	927.3	890.4	874.4	852.6	838.9	825.3	813.0	804.3	802.1
17.5°	935.6	895.5	864.3	837.9	811.7	789.3	776.8	765.8	755.7	744.1	742.6
20°	894.5	859.9	825.7	802.5	775.7	752.9	737.4	726.5	717.8	711.1	705.1
22.5°	855.5	817.6	786.4	761.0	734.5	716.1	703.9	693.4	686.2	678.6	673.1
25°	793.0	763.4	729.2	700.5	678.7	666.9	656.8	647.7	643.2	638.2	631.9
27.5°	738.2	705.3	673.4	651.2	632.0	621.5	614.4	608.2	604.0	601.0	597.4
30°	699.6	666.4	641.4	619.6	603.6	593.2	588.6	585.0	580.0	578.1	576.3
32.5°	662.5	632.6	611.2	592.2	577.0	570.2	566.0	562.8	558.8	557.0	553.3
35°	609.9	585.0	564.0	553.5	541.3	535.3	532.2	527.5	524.0	522.1	521.7
37.5°	560.5	538.8	525.0	511.6	506.4	502.7	498.4	495.3	494.2	493.9	493.5
40°	528.5	510.8	498.5	487.5	485.3	479.7	476.2	473.4	473.4	473.9	473.4
42.5°	499.4	483.4	472.6	463.2	460.5	457.2	453.5	453.3	454.1	455.7	454.1
45°	455.2	443.8	436.0	431.5	426.5	423.3	422.8	424.3	424.7	425.2	426.5
47.5°	414.6	407.1	400.0	395.0	392.8	392.3	391.7	394.1	396.3	397.1	399.2
50°	390.6	381.9	376.0	372.8	371.0	370.1	371.0	373.7	375.5	377.8	379.2
52.5°	363.6	357.5	353.4	351.0	350.3	350.8	351.0	354.1	357.0	357.8	358.5
55°	326.4	321.8	320.9	316.8	318.6	318.2	320.5	322.3	325.0	327.7	328.2
57.5°	289.3	285.6	283.1	283.5	284.0	286.1	287.9	291.1	294.1	296.9	297.2
60°	264.5	262.6	261.3	261.3	262.2	264.9	267.2	270.4	272.2	274.0	275.4
62.5°	241.9	240.0	238.7	239.4	241.8	243.4	246.1	247.8	249.6	251.5	252.1
65°	206.2	205.3	206.7	207.6	208.0	210.3	213.5	214.8	216.7	217.6	220.8
67.5°	173.3	173.5	173.3	174.6	177.3	177.8	180.8	184.0	184.3	186.1	188.2
70°	151.1	152.0	152.9	153.8	156.1	157.0	159.3	160.7	162.5	163.9	165.2
72.5°	130.7	130.9	131.8	131.6	133.6	135.5	137.5	138.8	140.6	142.4	143.7
75°	100.6	100.6	101.5	101.9	104.2	106.6	106.0	107.0	108.8	110.6	111.6
77.5°	73.5	72.5	73.5	73.9	74.6	76.6	77.0	78.2	80.3	79.6	80.7
80°	56.0	54.7	56.0	56.4	56.4	58.8	58.8	59.7	61.0	59.7	61.0
82.5°	39.9	39.3	40.3	40.4	41.1	41.2	42.0	42.2	43.5	42.9	43.5
85°	20.1	19.6	20.1	19.6	20.1	20.5	20.5	20.1	20.1	21.0	19.6
87.5°	9.4	10.0	11.0	12.2	13.2	14.2	13.6	13.6	13.5	12.6	12.6
90°	15.7	20.8	27.4	33.9	40.5	47.1	46.5	45.8	45.3	44.7	44.5
92.5°	34.4	36.6	38.1	39.7	41.2	42.7	42.9	43.0	43.1	43.2	43.3
95°	81.9	83.6	84.3	84.8	85.4	86.1	86.1	86.1	86.1	86.1	85.7
97.5°	138.2	140.1	141.2	142.4	143.5	144.6	144.6	144.6	144.6	144.6	144.6
100°	180.3	181.9	182.8	183.7	184.6	185.5	185.5	185.5	185.5	185.5	185.4
102.5°	223.6	225.1	226.2	227.3	228.5	229.6	229.9	230.1	230.3	230.6	230.5
105°	292.6	293.4	294.0	294.5	295.2	295.8	296.3	296.9	297.6	298.1	298.5
107.5°	367.9	368.6	368.6	368.6	368.6	368.6	368.8	369.1	369.3	369.5	369.0
110°	417.1	418.1	418.1	418.1	418.1	418.1	418.1	418.1	418.1	418.1	417.6



TEST NUMBER: P331550-940

CATALOG NUMBER: S122DIW-S675D1440U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	468.8	469.6	469.3	469.1	468.9	468.6	467.9	467.2	466.5	465.7	465.0
115°	544.9	545.5	544.9	544.3	543.7	543.1	542.8	542.5	542.2	541.9	541.3
117.5°	623.1	623.5	621.8	620.1	618.4	616.8	616.1	615.4	614.7	613.9	613.1
120°	673.7	673.7	671.3	668.9	666.5	664.1	664.1	664.1	664.1	664.1	663.6
122.5°	721.8	722.4	720.8	719.1	717.4	715.7	715.0	714.3	713.5	712.8	712.1
125°	793.2	794.1	793.2	792.3	791.4	790.4	789.5	788.6	787.7	786.8	786.3
127.5°	866.2	867.4	866.3	865.2	864.2	863.1	861.9	860.9	859.8	858.7	857.7
130°	912.2	913.8	913.2	912.7	912.0	911.4	910.9	910.3	909.6	909.0	908.1
132.5°	958.8	960.5	960.6	960.6	960.8	960.9	959.6	958.3	957.0	955.6	954.5
135°	1025.4	1027.3	1028.0	1028.6	1029.1	1029.7	1029.5	1029.1	1028.9	1028.6	1028.0
137.5°	1092.6	1094.4	1095.2	1095.9	1096.7	1097.5	1097.3	1097.0	1096.8	1096.5	1095.8
140°	1134.6	1136.7	1138.2	1139.7	1141.2	1142.6	1142.6	1142.6	1142.6	1142.6	1142.1
142.5°	1177.6	1179.5	1180.4	1181.5	1182.5	1183.6	1183.7	1184.0	1184.3	1184.5	1184.0
145°	1237.1	1239.0	1240.8	1242.6	1244.4	1246.2	1246.4	1246.8	1247.1	1247.3	1246.9
147.5°	1293.9	1295.7	1296.9	1298.1	1299.3	1300.5	1301.2	1301.8	1302.4	1303.1	1302.9
150°	1328.6	1330.1	1331.3	1332.5	1333.7	1334.9	1335.8	1336.7	1337.6	1338.5	1338.5
152.5°	1362.0	1363.6	1365.0	1366.5	1367.9	1369.3	1370.5	1371.5	1372.7	1373.9	1373.9
155°	1408.4	1409.3	1410.2	1411.0	1411.9	1412.8	1414.3	1415.9	1417.4	1418.8	1419.2
157.5°	1449.9	1450.5	1451.1	1451.6	1452.2	1452.7	1454.6	1456.7	1458.7	1460.8	1461.1
160°	1475.8	1476.2	1476.5	1476.8	1477.1	1477.4	1479.2	1481.0	1482.7	1484.5	1484.9
162.5°	1497.5	1497.7	1498.0	1498.3	1498.6	1498.9	1500.9	1503.0	1505.0	1507.0	1507.3
165°	1527.3	1527.1	1527.1	1527.1	1527.1	1527.1	1529.2	1531.3	1533.4	1535.5	1535.8
167.5°	1551.2	1550.8	1550.7	1550.7	1550.6	1550.5	1552.6	1554.7	1556.8	1558.9	1559.2
170°	1565.2	1564.6	1564.3	1564.1	1563.7	1563.4	1565.5	1567.6	1569.7	1571.8	1571.9
172.5°	1574.9	1574.3	1574.0	1573.7	1573.4	1573.1	1575.2	1577.3	1579.4	1581.4	1581.6
175°	1586.7	1586.0	1585.4	1584.7	1584.2	1583.6	1585.7	1587.8	1589.8	1592.0	1592.1
177.5°	1592.3	1591.7	1591.2	1590.7	1590.3	1589.7	1591.2	1592.7	1594.1	1595.5	1595.5
180°	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0



TEST NUMBER: P331550-940

CATALOG NUMBER: S122DIW-S675D1440U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5
2.5°	1136.0	1135.2	1135.2	1132.0	1135.2	1135.2	1136.0	1139.6	1140.8	1141.5	1140.1
5°	1053.8	1052.4	1050.2	1052.4	1050.2	1052.4	1053.8	1060.2	1063.4	1066.6	1069.3
7.5°	972.5	967.1	966.3	960.8	966.3	967.1	972.5	975.5	981.9	989.1	995.6
10°	913.1	909.5	909.0	900.4	909.0	909.5	913.1	920.9	927.3	935.9	945.0
12.5°	868.0	859.3	860.9	856.0	860.9	859.3	868.0	868.1	875.6	880.9	895.1
15°	789.8	789.8	787.9	780.2	787.9	789.8	789.8	802.1	804.3	813.0	825.3
17.5°	733.6	732.7	728.3	730.5	728.3	732.7	733.6	742.6	744.1	755.7	765.8
20°	700.1	697.4	691.9	691.9	691.9	697.4	700.1	705.1	711.1	717.8	726.5
22.5°	668.4	668.2	662.5	664.2	662.5	668.2	668.4	673.1	678.6	686.2	693.4
25°	631.3	627.8	625.0	626.3	625.0	627.8	631.3	631.9	638.2	643.2	647.7
27.5°	596.2	594.2	594.1	590.3	594.1	594.2	596.2	597.4	601.0	604.0	608.2
30°	575.9	571.3	572.2	569.9	572.2	571.3	575.9	576.3	578.1	580.0	585.0
32.5°	552.5	550.9	550.0	548.0	550.0	550.9	552.5	553.3	557.0	558.8	562.8
35°	520.8	521.2	519.0	519.9	519.0	521.2	520.8	521.7	522.1	524.0	527.5
37.5°	493.0	494.5	493.4	493.7	493.4	494.5	493.0	493.5	493.9	494.2	495.3
40°	474.7	474.7	474.7	476.2	474.7	474.7	474.7	473.4	473.9	473.4	473.4
42.5°	457.3	456.6	455.8	455.8	455.8	456.6	457.3	454.1	455.7	454.1	453.3
45°	427.4	428.8	429.3	427.0	429.3	428.8	427.4	426.5	425.2	424.7	424.3
47.5°	400.4	400.6	400.4	402.4	400.4	400.6	400.4	399.2	397.1	396.3	394.1
50°	381.5	380.6	381.5	380.6	381.5	380.6	381.5	379.2	377.8	375.5	373.7
52.5°	361.4	361.6	361.1	360.9	361.1	361.6	361.4	358.5	357.8	357.0	354.1
55°	330.0	330.9	330.5	330.5	330.5	330.9	330.0	328.2	327.7	325.0	322.3
57.5°	297.6	298.4	299.0	296.9	299.0	298.4	297.6	297.2	296.9	294.1	291.1
60°	274.9	277.2	276.8	275.9	276.8	277.2	274.9	275.4	274.0	272.2	270.4
62.5°	254.2	255.0	254.9	254.8	254.9	255.0	254.2	252.1	251.5	249.6	247.8
65°	222.1	223.0	221.7	223.0	221.7	223.0	222.1	220.8	217.6	216.7	214.8
67.5°	187.6	187.9	189.0	189.6	189.0	187.9	187.6	188.2	186.1	184.3	184.0
70°	166.1	165.7	167.0	168.4	167.0	165.7	166.1	165.2	163.9	162.5	160.7
72.5°	143.6	144.5	144.1	145.1	144.1	144.5	143.6	143.7	142.4	140.6	138.8
75°	110.6	112.0	111.6	112.9	111.6	112.0	110.6	111.6	110.6	108.8	107.0
77.5°	79.9	80.1	79.9	80.7	79.9	80.1	79.9	80.7	79.6	80.3	78.2
80°	61.0	60.1	59.2	61.0	59.2	60.1	61.0	61.0	59.7	61.0	59.7
82.5°	42.4	43.0	42.1	42.1	42.1	43.0	42.4	43.5	42.9	43.5	42.2
85°	19.6	19.1	18.2	18.2	18.2	19.1	19.6	19.6	21.0	20.1	20.1
87.5°	12.6	12.3	12.4	12.0	12.4	12.3	12.6	12.6	12.6	13.5	13.6
90°	44.9	45.1	45.4	45.7	45.4	45.1	44.9	44.5	44.7	45.3	45.8
92.5°	43.3	43.4	43.5	43.5	43.5	43.4	43.3	43.3	43.2	43.1	43.0
95°	85.2	84.5	83.9	83.4	83.9	84.5	85.2	85.7	86.1	86.1	86.1
97.5°	144.5	144.5	144.5	144.4	144.5	144.5	144.5	144.6	144.6	144.6	144.6
100°	185.0	184.8	184.5	184.1	184.5	184.8	185.0	185.4	185.5	185.5	185.5
102.5°	230.2	230.0	229.6	229.3	229.6	230.0	230.2	230.5	230.6	230.3	230.1
105°	298.5	298.5	298.5	298.5	298.5	298.5	298.5	298.5	298.1	297.6	296.9
107.5°	367.7	366.2	364.9	363.5	364.9	366.2	367.7	369.0	369.5	369.3	369.1
110°	416.7	415.8	414.9	414.0	414.9	415.8	416.7	417.6	418.1	418.1	418.1



TEST NUMBER: P331550-940

CATALOG NUMBER: S122DIW-S675D1440U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	464.4	463.8	463.1	462.4	463.1	463.8	464.4	465.0	465.7	466.5	467.2
115°	540.4	539.5	538.6	537.7	538.6	539.5	540.4	541.3	541.9	542.2	542.5
117.5°	612.2	611.3	610.4	609.5	610.4	611.3	612.2	613.1	613.9	614.7	615.4
120°	662.7	661.8	660.9	660.0	660.9	661.8	662.7	663.6	664.1	664.1	664.1
122.5°	711.5	710.9	710.2	709.5	710.2	710.9	711.5	712.1	712.8	713.5	714.3
125°	786.0	785.7	785.4	785.1	785.4	785.7	786.0	786.3	786.8	787.7	788.6
127.5°	856.8	855.8	854.9	853.9	854.9	855.8	856.8	857.7	858.7	859.8	860.9
130°	907.0	905.8	904.6	903.4	904.6	905.8	907.0	908.1	909.0	909.6	910.3
132.5°	953.6	952.6	951.6	950.7	951.6	952.6	953.6	954.5	955.6	957.0	958.3
135°	1027.1	1026.2	1025.3	1024.4	1025.3	1026.2	1027.1	1028.0	1028.6	1028.9	1029.1
137.5°	1094.7	1093.4	1092.3	1091.0	1092.3	1093.4	1094.7	1095.8	1096.5	1096.8	1097.0
140°	1140.9	1139.7	1138.4	1137.3	1138.4	1139.7	1140.9	1142.1	1142.6	1142.6	1142.6
142.5°	1182.9	1181.6	1180.4	1179.2	1180.4	1181.6	1182.9	1184.0	1184.5	1184.3	1184.0
145°	1245.7	1244.6	1243.3	1242.2	1243.3	1244.6	1245.7	1246.9	1247.3	1247.1	1246.8
147.5°	1301.7	1300.6	1299.5	1298.3	1299.5	1300.6	1301.7	1302.9	1303.1	1302.4	1301.8
150°	1337.6	1336.7	1335.8	1334.9	1335.8	1336.7	1337.6	1338.5	1338.5	1337.6	1336.7
152.5°	1372.7	1371.5	1370.5	1369.3	1370.5	1371.5	1372.7	1373.9	1373.9	1372.7	1371.5
155°	1418.3	1417.4	1416.5	1415.6	1416.5	1417.4	1418.3	1419.2	1418.8	1417.4	1415.9
157.5°	1459.6	1458.2	1456.8	1455.4	1456.8	1458.2	1459.6	1461.1	1460.8	1458.7	1456.7
160°	1483.6	1482.5	1481.3	1480.1	1481.3	1482.5	1483.6	1484.9	1484.5	1482.7	1481.0
162.5°	1505.9	1504.5	1503.1	1501.6	1503.1	1504.5	1505.9	1507.3	1507.0	1505.0	1503.0
165°	1534.3	1532.9	1531.3	1529.8	1531.3	1532.9	1534.3	1535.8	1535.5	1533.4	1531.3
167.5°	1557.6	1556.0	1554.5	1552.9	1554.5	1556.0	1557.6	1559.2	1558.9	1556.8	1554.7
170°	1570.1	1568.3	1566.6	1564.8	1566.6	1568.3	1570.1	1571.9	1571.8	1569.7	1567.6
172.5°	1579.8	1578.1	1576.3	1574.5	1576.3	1578.1	1579.8	1581.6	1581.4	1579.4	1577.3
175°	1590.3	1588.5	1586.7	1584.9	1586.7	1588.5	1590.3	1592.1	1592.0	1589.8	1587.8
177.5°	1594.1	1592.7	1591.2	1589.7	1591.2	1592.7	1594.1	1595.5	1595.5	1594.1	1592.7
180°	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0



TEST NUMBER: P331550-940

CATALOG NUMBER: S122DIW-S675D1440U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5
2.5°	1138.2	1142.2	1148.3	1154.9	1159.0	1166.6	1168.8	1172.4	1175.7	1183.4	1191.3
5°	1072.5	1078.8	1093.9	1102.1	1113.4	1126.6	1135.2	1144.4	1154.4	1171.7	1187.6
7.5°	1002.0	1012.6	1031.3	1046.6	1062.8	1081.7	1095.4	1113.4	1128.4	1152.7	1176.1
10°	955.0	970.0	986.9	1005.0	1027.9	1047.8	1067.0	1089.8	1108.0	1137.1	1164.4
12.5°	912.8	915.1	939.1	959.2	990.3	1015.1	1037.1	1066.5	1084.3	1118.9	1147.6
15°	838.9	852.6	874.4	890.4	927.3	958.7	989.6	1020.1	1040.6	1083.3	1121.1
17.5°	776.8	789.3	811.7	837.9	864.3	895.5	935.6	967.8	995.6	1044.6	1089.2
20°	737.4	752.9	775.7	802.5	825.7	859.9	894.5	931.3	961.4	1016.5	1068.8
22.5°	703.9	716.1	734.5	761.0	786.4	817.6	855.5	895.6	927.2	986.6	1039.6
25°	656.8	666.9	678.7	700.5	729.2	763.4	793.0	837.1	883.1	938.6	1002.8
27.5°	614.4	621.5	632.0	651.2	673.4	705.3	738.2	780.2	826.3	886.6	954.4
30°	588.6	593.2	603.6	619.6	641.4	666.4	699.6	739.7	787.0	848.0	915.4
32.5°	566.0	570.2	577.0	592.2	611.2	632.6	662.5	702.6	747.7	807.6	882.3
35°	532.2	535.3	541.3	553.5	564.0	585.0	609.9	646.4	688.8	746.1	823.5
37.5°	498.4	502.7	506.4	511.6	525.0	538.8	560.5	591.3	632.8	690.7	764.5
40°	476.2	479.7	485.3	487.5	498.5	510.8	528.5	556.7	598.6	651.4	723.4
42.5°	453.5	457.2	460.5	463.2	472.6	483.4	499.4	523.6	560.7	612.1	683.2
45°	422.8	423.3	426.5	431.5	436.0	443.8	455.2	476.2	504.8	553.0	617.7
47.5°	391.7	392.3	392.8	395.0	400.0	407.1	414.6	431.6	457.3	495.8	558.7
50°	371.0	370.1	371.0	372.8	376.0	381.9	390.6	402.9	423.8	459.8	517.5
52.5°	351.0	350.8	350.3	351.0	353.4	357.5	363.6	374.1	392.8	425.9	476.8
55°	320.5	318.2	318.6	316.8	320.9	321.8	326.4	335.0	351.4	374.2	422.0
57.5°	287.9	286.1	284.0	283.5	283.1	285.6	289.3	296.0	308.6	328.6	367.4
60°	267.2	264.9	262.2	261.3	261.3	262.6	264.5	269.5	281.3	299.1	330.9
62.5°	246.1	243.4	241.8	239.4	238.7	240.0	241.9	245.5	254.0	270.6	298.2
65°	213.5	210.3	208.0	207.6	206.7	205.3	206.2	209.8	216.7	229.9	251.7
67.5°	180.8	177.8	177.3	174.6	173.3	173.5	173.3	176.5	180.6	191.9	208.2
70°	159.3	157.0	156.1	153.8	152.9	152.0	151.1	153.8	157.9	167.6	181.6
72.5°	137.5	135.5	133.6	131.6	131.8	130.9	130.7	132.3	135.7	144.5	155.4
75°	106.0	106.6	104.2	101.9	101.5	100.6	100.6	101.9	103.3	110.1	118.8
77.5°	77.0	76.6	74.6	73.9	73.5	72.5	73.5	74.4	75.1	79.6	86.1
80°	58.8	58.8	56.4	56.4	56.0	54.7	56.0	55.1	56.9	61.4	66.0
82.5°	42.0	41.2	41.1	40.4	40.3	39.3	39.9	40.8	41.6	44.7	47.4
85°	20.5	20.5	20.1	19.6	20.1	19.6	20.1	20.5	21.0	22.3	24.6
87.5°	13.6	14.2	13.2	12.2	11.0	10.0	9.4	9.0	9.0	8.6	8.3
90°	46.5	47.1	40.5	33.9	27.4	20.8	15.7	12.1	8.5	4.9	1.3
92.5°	42.9	42.7	41.2	39.7	38.1	36.6	34.4	31.8	29.2	26.6	23.9
95°	86.1	86.1	85.4	84.8	84.3	83.6	81.9	78.8	75.9	72.9	69.9
97.5°	144.6	144.6	143.5	142.4	141.2	140.1	138.2	135.6	133.0	130.4	127.7
100°	185.5	185.5	184.6	183.7	182.8	181.9	180.3	177.9	175.5	173.1	170.8
102.5°	229.9	229.6	228.5	227.3	226.2	225.1	223.6	221.6	219.7	217.8	215.9
105°	296.3	295.8	295.2	294.5	294.0	293.4	292.6	291.7	290.8	289.9	289.0
107.5°	368.8	368.6	368.6	368.6	368.6	368.6	367.9	366.7	365.3	364.0	362.7
110°	418.1	418.1	418.1	418.1	418.1	418.1	417.1	415.4	413.6	411.8	410.0



TEST NUMBER: P331550-940

CATALOG NUMBER: S122DIW-S675D1440U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	467.9	468.6	468.9	469.1	469.3	469.6	468.8	467.0	465.2	463.4	461.6
115°	542.8	543.1	543.7	544.3	544.9	545.5	544.9	543.1	541.3	539.5	537.7
117.5°	616.1	616.8	618.4	620.1	621.8	623.5	623.1	620.7	618.3	615.9	613.6
120°	664.1	664.1	666.5	668.9	671.3	673.7	673.7	671.3	668.9	666.5	664.1
122.5°	715.0	715.7	717.4	719.1	720.8	722.4	721.8	718.9	716.0	713.2	710.3
125°	789.5	790.4	791.4	792.3	793.2	794.1	793.2	790.4	787.7	785.1	782.4
127.5°	861.9	863.1	864.2	865.2	866.3	867.4	866.2	862.8	859.3	856.0	852.6
130°	910.9	911.4	912.0	912.7	913.2	913.8	912.2	908.3	904.5	900.5	896.6
132.5°	959.6	960.9	960.8	960.6	960.6	960.5	958.8	955.6	952.4	949.3	946.1
135°	1029.5	1029.7	1029.1	1028.6	1028.0	1027.3	1025.4	1022.1	1018.9	1015.6	1012.3
137.5°	1097.3	1097.5	1096.7	1095.9	1095.2	1094.4	1092.6	1089.9	1087.3	1084.6	1081.9
140°	1142.6	1142.6	1141.2	1139.7	1138.2	1136.7	1134.6	1131.9	1129.3	1126.5	1123.8
142.5°	1183.7	1183.6	1182.5	1181.5	1180.4	1179.5	1177.6	1174.9	1172.2	1169.6	1166.9
145°	1246.4	1246.2	1244.4	1242.6	1240.8	1239.0	1237.1	1234.9	1232.9	1230.8	1228.7
147.5°	1301.2	1300.5	1299.3	1298.1	1296.9	1295.7	1293.9	1291.4	1288.8	1286.3	1283.8
150°	1335.8	1334.9	1333.7	1332.5	1331.3	1330.1	1328.6	1326.9	1325.1	1323.2	1321.4
152.5°	1370.5	1369.3	1367.9	1366.5	1365.0	1363.6	1362.0	1360.1	1358.3	1356.6	1354.8
155°	1414.3	1412.8	1411.9	1411.0	1410.2	1409.3	1408.4	1407.5	1406.6	1405.7	1404.8
157.5°	1454.6	1452.7	1452.2	1451.6	1451.1	1450.5	1449.9	1449.4	1448.8	1448.1	1447.5
160°	1479.2	1477.4	1477.1	1476.8	1476.5	1476.2	1475.8	1475.2	1474.5	1474.0	1473.4
162.5°	1500.9	1498.9	1498.6	1498.3	1498.0	1497.7	1497.5	1497.4	1497.3	1497.2	1497.0
165°	1529.2	1527.1	1527.1	1527.1	1527.1	1527.1	1527.3	1527.6	1527.9	1528.2	1528.5
167.5°	1552.6	1550.5	1550.6	1550.7	1550.7	1550.8	1551.2	1552.1	1553.0	1553.9	1554.8
170°	1565.5	1563.4	1563.7	1564.1	1564.3	1564.6	1565.2	1566.1	1567.0	1567.9	1568.8
172.5°	1575.2	1573.1	1573.4	1573.7	1574.0	1574.3	1574.9	1575.8	1576.7	1577.6	1578.5
175°	1585.7	1583.6	1584.2	1584.7	1585.4	1586.0	1586.7	1587.6	1588.5	1589.4	1590.3
177.5°	1591.2	1589.7	1590.3	1590.7	1591.2	1591.7	1592.3	1593.0	1593.8	1594.5	1595.2
180°	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0



TEST NUMBER: P331550-940

CATALOG NUMBER: S122DIW-S675D1440U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5
2.5°	1190.6	1192.5	1198.3	1204.1	1210.7	1212.5	1215.4	1212.8	1212.1	1219.1	1224.1
5°	1194.0	1202.2	1218.2	1232.7	1245.0	1253.7	1262.8	1266.4	1273.2	1282.7	1294.6
7.5°	1190.2	1206.1	1231.2	1252.3	1275.5	1292.2	1305.2	1316.3	1329.7	1347.8	1367.6
10°	1185.8	1207.2	1237.7	1263.6	1291.8	1313.2	1331.1	1348.3	1368.3	1393.4	1419.3
12.5°	1177.8	1203.2	1241.4	1272.0	1308.2	1329.3	1353.3	1390.5	1412.0	1446.9	1483.5
15°	1161.7	1189.9	1243.1	1280.9	1321.9	1362.0	1406.1	1441.6	1477.1	1497.6	1549.1
17.5°	1137.7	1179.2	1238.1	1282.2	1334.3	1397.4	1447.0	1487.2	1528.2	1561.5	1587.2
20°	1118.5	1163.5	1230.8	1283.7	1345.6	1413.4	1470.3	1511.3	1546.8	1574.6	1590.5
22.5°	1094.0	1150.8	1216.3	1278.2	1357.3	1424.3	1484.2	1516.4	1546.0	1559.6	1565.8
25°	1055.6	1123.9	1198.1	1273.6	1362.9	1433.9	1488.5	1508.1	1516.7	1503.5	1481.7
27.5°	1014.2	1090.3	1177.1	1265.1	1359.4	1427.7	1466.9	1463.7	1449.1	1406.4	1372.3
30°	983.2	1067.0	1160.3	1256.3	1351.0	1417.5	1440.3	1417.5	1384.3	1336.5	1287.8
32.5°	950.8	1037.5	1142.5	1243.9	1335.8	1394.2	1399.1	1359.9	1308.5	1254.2	1193.5
35°	901.8	995.5	1108.8	1216.3	1303.2	1340.2	1318.3	1249.1	1188.1	1113.9	1031.0
37.5°	846.3	949.9	1063.5	1175.8	1254.5	1264.2	1210.0	1137.1	1051.1	963.9	866.4
40°	804.8	914.5	1031.5	1144.9	1214.5	1204.4	1135.2	1055.2	952.7	846.2	755.6
42.5°	767.7	877.4	996.5	1107.7	1163.5	1136.0	1055.2	956.8	846.8	746.5	663.5
45°	703.3	816.2	938.2	1045.6	1077.5	1027.9	920.9	811.6	703.3	619.6	554.0
47.5°	640.9	752.4	873.3	967.7	978.9	912.2	795.3	682.9	589.8	521.6	475.3
50°	594.9	706.9	826.6	910.9	907.2	826.6	706.5	599.5	521.7	466.5	435.6
52.5°	553.8	659.6	774.5	851.1	831.9	744.0	629.3	534.3	470.3	427.2	399.2
55°	489.8	587.6	696.9	758.4	722.8	625.4	528.5	452.0	404.7	372.4	350.5
57.5°	426.2	518.0	611.5	649.4	610.2	520.2	439.3	383.9	348.3	324.4	310.1
60°	386.9	467.1	550.4	583.1	536.2	456.1	392.4	342.8	314.1	294.5	281.8
62.5°	347.6	419.4	497.9	515.8	472.9	405.1	348.7	307.5	283.8	266.4	254.5
65°	294.1	352.8	412.4	424.3	384.7	332.3	287.7	260.8	239.9	227.1	217.6
67.5°	241.2	288.3	330.6	340.1	305.4	269.1	236.9	213.5	199.3	188.7	180.7
70°	209.8	247.2	281.8	289.5	261.7	229.4	204.8	186.2	173.4	164.3	156.6
72.5°	176.7	207.9	236.6	241.8	219.1	194.5	174.2	159.6	148.3	142.5	135.1
75°	135.2	153.4	175.7	177.1	162.0	147.0	131.5	122.0	116.1	108.8	105.1
77.5°	95.4	109.7	122.4	124.9	116.0	105.8	97.1	89.6	84.5	81.2	77.8
80°	72.9	84.2	89.7	92.8	86.5	79.2	74.2	69.2	66.0	63.8	61.4
82.5°	52.1	59.1	64.2	66.6	63.2	58.9	53.8	51.0	48.5	46.6	45.8
85°	26.4	29.6	32.8	33.7	32.8	30.9	28.2	28.2	26.8	26.4	26.4
87.5°	10.1	12.3	13.0	14.8	15.1	16.4	17.7	18.6	19.6	19.1	18.6
90°	4.9	8.5	12.1	15.7	20.8	27.4	33.9	40.5	47.1	46.5	45.8
92.5°	26.6	29.2	31.8	34.4	36.6	38.1	39.7	41.2	42.7	42.9	43.0
95°	72.9	75.9	78.8	81.9	83.6	84.3	84.8	85.4	86.1	86.1	86.1
97.5°	130.4	133.0	135.6	138.2	140.1	141.2	142.4	143.5	144.6	144.6	144.6
100°	173.1	175.5	177.9	180.3	181.9	182.8	183.7	184.6	185.5	185.5	185.5
102.5°	217.8	219.7	221.6	223.6	225.1	226.2	227.3	228.5	229.6	229.9	230.1
105°	289.9	290.8	291.7	292.6	293.4	294.0	294.5	295.2	295.8	296.3	296.9
107.5°	364.0	365.3	366.7	367.9	368.6	368.6	368.6	368.6	368.6	368.8	369.1
110°	411.8	413.6	415.4	417.1	418.1	418.1	418.1	418.1	418.1	418.1	418.1



TEST NUMBER: P331550-940

CATALOG NUMBER: S122DIW-S675D1440U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	463.4	465.2	467.0	468.8	469.6	469.3	469.1	468.9	468.6	467.9	467.2
115°	539.5	541.3	543.1	544.9	545.5	544.9	544.3	543.7	543.1	542.8	542.5
117.5°	615.9	618.3	620.7	623.1	623.5	621.8	620.1	618.4	616.8	616.1	615.4
120°	666.5	668.9	671.3	673.7	673.7	671.3	668.9	666.5	664.1	664.1	664.1
122.5°	713.2	716.0	718.9	721.8	722.4	720.8	719.1	717.4	715.7	715.0	714.3
125°	785.1	787.7	790.4	793.2	794.1	793.2	792.3	791.4	790.4	789.5	788.6
127.5°	856.0	859.3	862.8	866.2	867.4	866.3	865.2	864.2	863.1	861.9	860.9
130°	900.5	904.5	908.3	912.2	913.8	913.2	912.7	912.0	911.4	910.9	910.3
132.5°	949.3	952.4	955.6	958.8	960.5	960.6	960.6	960.8	960.9	959.6	958.3
135°	1015.6	1018.9	1022.1	1025.4	1027.3	1028.0	1028.6	1029.1	1029.7	1029.5	1029.1
137.5°	1084.6	1087.3	1089.9	1092.6	1094.4	1095.2	1095.9	1096.7	1097.5	1097.3	1097.0
140°	1126.5	1129.3	1131.9	1134.6	1136.7	1138.2	1139.7	1141.2	1142.6	1142.6	1142.6
142.5°	1169.6	1172.2	1174.9	1177.6	1179.5	1180.4	1181.5	1182.5	1183.6	1183.7	1184.0
145°	1230.8	1232.9	1234.9	1237.1	1239.0	1240.8	1242.6	1244.4	1246.2	1246.4	1246.8
147.5°	1286.3	1288.8	1291.4	1293.9	1295.7	1296.9	1298.1	1299.3	1300.5	1301.2	1301.8
150°	1323.2	1325.1	1326.9	1328.6	1330.1	1331.3	1332.5	1333.7	1334.9	1335.8	1336.7
152.5°	1356.6	1358.3	1360.1	1362.0	1363.6	1365.0	1366.5	1367.9	1369.3	1370.5	1371.5
155°	1405.7	1406.6	1407.5	1408.4	1409.3	1410.2	1411.0	1411.9	1412.8	1414.3	1415.9
157.5°	1448.1	1448.8	1449.4	1449.9	1450.5	1451.1	1451.6	1452.2	1452.7	1454.6	1456.7
160°	1474.0	1474.5	1475.2	1475.8	1476.2	1476.5	1476.8	1477.1	1477.4	1479.2	1481.0
162.5°	1497.2	1497.3	1497.4	1497.5	1497.7	1498.0	1498.3	1498.6	1498.9	1500.9	1503.0
165°	1528.2	1527.9	1527.6	1527.3	1527.1	1527.1	1527.1	1527.1	1527.1	1529.2	1531.3
167.5°	1553.9	1553.0	1552.1	1551.2	1550.8	1550.7	1550.7	1550.6	1550.5	1552.6	1554.7
170°	1567.9	1567.0	1566.1	1565.2	1564.6	1564.3	1564.1	1563.7	1563.4	1565.5	1567.6
172.5°	1577.6	1576.7	1575.8	1574.9	1574.3	1574.0	1573.7	1573.4	1573.1	1575.2	1577.3
175°	1589.4	1588.5	1587.6	1586.7	1586.0	1585.4	1584.7	1584.2	1583.6	1585.7	1587.8
177.5°	1594.5	1593.8	1593.0	1592.3	1591.7	1591.2	1590.7	1590.3	1589.7	1591.2	1592.7
180°	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0



TEST NUMBER: P331550-940

CATALOG NUMBER: S122DIW-S675D1440U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5	1184.5
2.5°	1228.5	1233.6	1233.6	1234.3	1240.2	1239.4	1239.0
5°	1307.3	1315.1	1316.0	1324.2	1329.6	1327.8	1322.9
7.5°	1381.7	1396.2	1407.0	1413.1	1420.3	1424.8	1422.8
10°	1440.7	1461.7	1474.4	1483.1	1493.5	1501.3	1498.5
12.5°	1494.2	1519.2	1536.7	1551.5	1552.9	1562.8	1556.0
15°	1577.7	1604.1	1606.9	1617.8	1626.5	1625.5	1625.9
17.5°	1605.3	1613.8	1615.5	1615.8	1615.9	1612.7	1605.8
20°	1595.4	1592.3	1584.6	1578.7	1568.2	1566.8	1557.7
22.5°	1548.9	1538.7	1519.4	1506.5	1490.2	1485.9	1483.5
25°	1457.1	1434.8	1403.8	1374.2	1366.1	1350.1	1354.7
27.5°	1331.2	1296.5	1262.9	1238.9	1217.1	1193.3	1200.1
30°	1242.7	1203.5	1156.2	1119.8	1096.6	1073.8	1069.7
32.5°	1137.1	1079.8	1026.9	994.9	959.3	944.9	929.2
35°	955.0	899.0	846.7	801.6	775.7	755.6	737.4
37.5°	791.2	726.7	684.6	648.0	629.3	617.8	620.7
40°	689.6	633.2	602.3	574.4	557.1	548.9	550.8
42.5°	607.3	565.1	539.6	520.6	508.4	503.8	502.7
45°	513.9	490.3	469.3	458.4	452.5	447.5	444.3
47.5°	450.2	430.9	419.1	412.6	407.4	402.3	402.3
50°	412.0	399.2	391.0	384.1	380.1	376.5	379.6
52.5°	382.8	371.1	363.0	356.9	355.3	352.0	352.0
55°	339.6	330.5	324.6	319.1	316.4	314.5	312.3
57.5°	300.2	291.6	286.1	282.7	277.5	275.6	274.9
60°	272.2	265.4	259.9	255.4	253.1	249.4	249.4
62.5°	246.4	239.5	234.4	231.0	227.2	225.8	226.1
65°	208.9	203.5	198.5	194.8	193.9	191.2	192.1
67.5°	174.5	170.9	165.6	163.6	161.8	160.4	159.3
70°	151.6	147.9	145.2	142.5	141.1	141.1	141.1
72.5°	132.2	127.9	126.3	122.8	123.6	122.2	120.7
75°	102.5	99.7	98.4	96.9	94.7	94.7	94.7
77.5°	75.3	74.5	72.9	71.4	70.9	70.4	70.6
80°	58.2	57.8	56.9	56.9	56.0	55.6	54.7
82.5°	44.8	43.6	43.1	42.7	42.5	42.4	42.3
85°	25.5	24.6	24.6	25.1	24.2	24.2	24.6
87.5°	18.9	18.7	18.4	18.5	18.8	18.5	18.6
90°	45.3	44.7	44.5	44.9	45.1	45.4	45.7
92.5°	43.1	43.2	43.3	43.3	43.4	43.5	43.5
95°	86.1	86.1	85.7	85.2	84.5	83.9	83.4
97.5°	144.6	144.6	144.6	144.5	144.5	144.5	144.4
100°	185.5	185.5	185.4	185.0	184.8	184.5	184.1
102.5°	230.3	230.6	230.5	230.2	230.0	229.6	229.3
105°	297.6	298.1	298.5	298.5	298.5	298.5	298.5
107.5°	369.3	369.5	369.0	367.7	366.2	364.9	363.5
110°	418.1	418.1	417.6	416.7	415.8	414.9	414.0



TEST NUMBER: P331550-940

CATALOG NUMBER: S122DIW-S675D1440U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	466.5	465.7	465.0	464.4	463.8	463.1	462.4
115°	542.2	541.9	541.3	540.4	539.5	538.6	537.7
117.5°	614.7	613.9	613.1	612.2	611.3	610.4	609.5
120°	664.1	664.1	663.6	662.7	661.8	660.9	660.0
122.5°	713.5	712.8	712.1	711.5	710.9	710.2	709.5
125°	787.7	786.8	786.3	786.0	785.7	785.4	785.1
127.5°	859.8	858.7	857.7	856.8	855.8	854.9	853.9
130°	909.6	909.0	908.1	907.0	905.8	904.6	903.4
132.5°	957.0	955.6	954.5	953.6	952.6	951.6	950.7
135°	1028.9	1028.6	1028.0	1027.1	1026.2	1025.3	1024.4
137.5°	1096.8	1096.5	1095.8	1094.7	1093.4	1092.3	1091.0
140°	1142.6	1142.6	1142.1	1140.9	1139.7	1138.4	1137.3
142.5°	1184.3	1184.5	1184.0	1182.9	1181.6	1180.4	1179.2
145°	1247.1	1247.3	1246.9	1245.7	1244.6	1243.3	1242.2
147.5°	1302.4	1303.1	1302.9	1301.7	1300.6	1299.5	1298.3
150°	1337.6	1338.5	1338.5	1337.6	1336.7	1335.8	1334.9
152.5°	1372.7	1373.9	1373.9	1372.7	1371.5	1370.5	1369.3
155°	1417.4	1418.8	1419.2	1418.3	1417.4	1416.5	1415.6
157.5°	1458.7	1460.8	1461.1	1459.6	1458.2	1456.8	1455.4
160°	1482.7	1484.5	1484.9	1483.6	1482.5	1481.3	1480.1
162.5°	1505.0	1507.0	1507.3	1505.9	1504.5	1503.1	1501.6
165°	1533.4	1535.5	1535.8	1534.3	1532.9	1531.3	1529.8
167.5°	1556.8	1558.9	1559.2	1557.6	1556.0	1554.5	1552.9
170°	1569.7	1571.8	1571.9	1570.1	1568.3	1566.6	1564.8
172.5°	1579.4	1581.4	1581.6	1579.8	1578.1	1576.3	1574.5
175°	1589.8	1592.0	1592.1	1590.3	1588.5	1586.7	1584.9
177.5°	1594.1	1595.5	1595.5	1594.1	1592.7	1591.2	1589.7
180°	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0

(END OF REPORT)