

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331769-940

Luminaire Tested: **S122RDIW-S290D710U940-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331769-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIW-S290D710U940-4F0-1E-UDD-A  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 710 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3537.8 lumens  
Efficiency: N/A  
Efficacy: 116.4 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 30.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331769-940

CATALOG NUMBER: S122RDIW-S290D710U940-4F0-1E-UDD-A

### Luminous Intensity Polar Plot



— 0°-180°    - - 45°-225°    - · - 90°-270°    - · - 135°-315°



TEST NUMBER: P331769-940

CATALOG NUMBER: S122RDIW-S290D710U940-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36	29
1	93	89	86	83	84	80	77	75	63	61	59	47	46	45	33	32	32	25
2	85	79	73	68	76	71	66	62	56	53	50	42	40	38	29	28	27	22
3	78	69	63	57	70	63	57	52	50	46	42	38	35	33	26	25	24	19
4	72	62	54	49	64	56	49	45	44	40	36	34	31	29	24	22	21	17
5	66	55	48	42	59	50	43	38	40	35	32	31	27	25	22	20	18	15
6	61	49	42	36	54	45	38	34	36	31	28	28	25	22	20	18	17	13
7	56	45	37	32	50	41	34	30	33	28	25	25	22	20	18	16	15	12
8	52	41	33	28	47	37	31	26	30	25	22	23	20	18	17	15	13	11
9	49	37	30	25	44	34	28	23	27	23	20	21	18	16	16	14	12	10
10	45	34	27	23	41	31	25	21	25	21	18	20	17	14	15	13	11	9

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	9411	9411	9411	9411
5°	10511	9470	8399	9470
10°	11663	9404	7279	9404
15°	12236	9267	5735	9267
20°	10608	9062	4962	9062
25°	6957	8783	4431	8783
30°	4683	8444	4010	8444
35°	3792	8016	3617	8016
40°	3372	7552	3347	7552
45°	3053	7005	2987	7005
50°	2778	6465	2768	6465
55°	2609	5866	2578	5866
60°	2186	5318	2160	5318
65°	1841	4829	2090	4829
70°	1699	4310	1969	4310
75°	1591	3755	1822	3755
80°	1469	3096	1618	3096
85°	1352	2445	1426	2445



TEST NUMBER: P331769-940

CATALOG NUMBER: S122RDIW-S290D710U940-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	55.3	1.6
10°-20°	154.0	4.4
20°-30°	198.4	5.6
30°-40°	188.6	5.3
40°-50°	161.5	4.6
50°-60°	123.0	3.5
60°-70°	77.8	2.2
70°-80°	38.8	1.1
80°-90°	12.2	0.3
90°-100°	28.8	0.8
100°-110°	105.5	3.0
110°-120°	282.1	8.0
120°-130°	465.6	13.2
130°-140°	495.2	14.0
140°-150°	460.3	13.0
150°-160°	370.1	10.5
160°-170°	238.5	6.7
170°-180°	82.1	2.3
0°-30°	407.7	11.5
0°-40°	596.2	16.9
0°-60°	880.8	24.9
0°-90°	1009.6	28.5
90°-120°	416.4	11.8
90°-150°	1837.6	51.9
90°-180°	2528.0	71.5
0°-180°	3537.8	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	583	583	583	583	583	
5°	648	584	518	584	648	64
15°	732	554	343	554	732	197
25°	390	493	249	493	390	185
35°	192	407	184	407	192	123
45°	134	307	131	307	134	103
55°	93	208	92	208	93	81
65°	48	126	55	126	48	49
75°	26	60	29	60	26	27
85°	7	13	8	13	7	8
90°	17	1	17	1	17	8
95°	27	41	27	41	27	25
105°	47	190	47	190	47	49
115°	51	359	51	359	51	128
125°	534	508	534	508	534	462
135°	649	628	649	628	649	500
145°	740	728	740	728	740	463
155°	803	802	803	802	803	370
165°	843	845	843	845	843	238
175°	860	865	860	865	860	82
180°	863	863	863	863	863	



TEST NUMBER: P331769-940

CATALOG NUMBER: S122RDIW-S290D710U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9
2.5°	606.6	607.1	607.6	606.5	606.5	605.5	603.3	601.7	597.2	596.6	596.6
5°	648.5	648.2	649.0	646.3	642.7	641.9	638.0	632.9	627.7	621.9	620.6
7.5°	690.3	689.6	688.0	687.6	684.8	678.7	672.5	665.9	657.2	648.6	644.4
10°	711.4	718.1	714.0	706.9	708.3	698.8	693.8	685.0	677.7	664.9	662.2
12.5°	732.1	734.8	733.4	729.4	727.6	721.0	714.2	706.6	693.1	681.7	671.7
15°	732.0	735.8	736.9	735.7	736.6	736.3	732.6	726.4	714.6	702.0	691.1
17.5°	678.0	680.6	687.3	691.8	697.5	709.4	715.4	717.6	716.0	708.7	701.1
20°	617.4	613.0	631.6	641.1	649.2	669.4	686.9	693.6	704.3	704.1	702.0
22.5°	531.5	532.5	550.2	561.5	585.1	605.5	625.3	650.4	671.2	684.9	692.9
25°	390.5	398.2	415.8	431.2	457.5	495.3	529.5	569.2	606.6	636.2	664.4
27.5°	293.3	293.9	307.8	322.1	337.7	368.5	411.7	459.1	512.5	556.6	607.3
30°	251.2	249.9	255.8	264.6	277.9	301.8	334.2	380.8	434.1	500.5	559.6
32.5°	221.3	221.4	225.9	232.3	243.3	259.5	281.7	319.6	369.9	435.2	504.5
35°	192.4	192.3	195.5	200.1	204.7	215.1	230.3	250.1	284.8	345.7	416.6
37.5°	171.7	172.5	174.2	177.1	182.2	188.0	197.1	210.4	235.1	271.2	330.7
40°	160.0	160.4	162.6	165.1	168.1	172.5	180.0	190.8	208.8	237.6	281.2
42.5°	149.4	149.7	151.3	153.6	156.0	160.4	166.7	175.9	190.6	212.9	248.9
45°	133.7	133.7	135.1	136.1	138.8	142.8	147.8	155.6	165.7	182.3	206.2
47.5°	119.0	119.0	120.0	121.7	123.4	126.5	131.5	137.9	145.2	158.0	178.4
50°	110.6	110.8	111.4	112.8	113.9	116.6	120.6	126.0	133.7	143.7	160.6
52.5°	103.8	103.7	104.4	105.0	105.8	107.7	110.7	115.5	122.3	131.0	145.1
55°	92.7	91.9	93.2	94.2	94.8	95.6	97.2	100.2	106.1	113.4	123.9
57.5°	79.0	78.6	79.5	80.4	82.4	84.5	86.0	87.8	90.9	96.1	106.6
60°	67.7	67.7	69.5	70.1	72.3	75.2	78.0	79.6	82.7	86.1	93.8
62.5°	57.6	57.8	58.6	59.2	60.5	63.9	67.9	71.5	74.4	77.7	82.8
65°	48.2	48.6	48.6	49.0	49.8	50.6	52.3	55.1	60.2	64.8	68.7
67.5°	40.9	41.0	41.2	41.6	41.7	42.6	43.3	44.6	45.7	50.1	54.9
70°	36.0	36.6	36.5	36.8	37.1	37.5	38.3	38.9	40.8	41.7	44.6
72.5°	31.5	31.9	31.9	32.2	32.7	32.8	33.4	34.1	35.2	36.0	37.6
75°	25.5	25.3	25.5	25.9	26.1	26.3	26.3	27.1	27.7	28.5	29.6
77.5°	19.7	19.9	19.9	19.9	20.0	20.3	20.2	20.6	21.2	21.7	22.1
80°	15.8	16.0	15.8	16.0	16.2	16.4	16.2	16.4	17.0	17.4	17.4
82.5°	12.2	12.3	12.4	12.4	12.5	12.5	12.8	12.8	13.3	13.2	13.4
85°	7.3	7.1	7.1	7.1	7.3	7.5	7.3	7.3	7.5	7.5	7.5
87.5°	6.0	6.1	6.0	6.0	5.9	5.8	5.7	5.7	5.4	5.4	5.0
90°	16.9	16.6	16.3	16.1	15.8	15.2	14.5	13.9	13.2	12.5	11.4
92.5°	16.9	16.7	16.5	16.3	16.2	16.0	15.6	15.2	14.8	14.4	13.9
95°	26.8	27.0	27.1	27.3	27.4	27.1	26.4	25.8	25.1	24.3	23.4
97.5°	35.8	35.7	35.5	35.3	35.1	34.8	34.2	33.7	33.2	32.5	30.3
100°	41.8	41.6	41.3	41.0	40.8	40.0	38.9	37.8	36.6	35.6	33.3
102.5°	44.9	44.4	44.1	43.7	43.2	42.4	40.9	39.5	38.0	36.6	56.3
105°	47.4	46.9	46.4	45.7	45.2	44.1	42.6	41.1	39.6	38.1	76.0
107.5°	48.8	48.2	47.7	47.2	46.6	47.1	48.7	50.2	51.7	53.3	98.7
110°	49.3	48.8	48.2	47.6	47.1	53.8	67.6	81.5	95.4	109.2	149.4



TEST NUMBER: P331769-940

CATALOG NUMBER: S122RDIW-S290D710U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	49.8	49.4	49.0	48.5	48.1	73.1	123.8	174.3	225.0	275.5	285.4
115°	51.2	61.2	71.2	81.1	91.1	128.2	192.4	256.7	320.9	385.1	381.7
117.5°	209.0	241.8	274.6	307.5	340.3	364.4	380.0	395.6	411.1	426.6	424.2
120°	380.8	399.5	418.2	436.9	455.7	464.2	462.5	460.9	459.2	457.5	455.0
122.5°	475.2	478.8	482.4	486.1	489.7	491.1	490.0	489.0	488.0	487.1	484.3
125°	533.7	533.3	532.9	532.4	532.1	531.4	530.4	529.4	528.4	527.4	524.9
127.5°	570.7	570.6	570.5	570.4	570.3	569.6	568.2	566.8	565.3	563.9	562.0
130°	593.7	593.8	594.0	594.1	594.2	593.5	592.0	590.5	589.0	587.5	585.9
132.5°	616.2	616.3	616.4	616.5	616.7	616.1	614.8	613.5	612.2	610.9	609.4
135°	648.6	648.9	649.2	649.4	649.7	649.2	647.7	646.4	645.0	643.6	642.4
137.5°	678.1	678.7	679.1	679.6	680.1	679.7	678.2	676.9	675.6	674.2	672.8
140°	696.7	697.3	698.0	698.7	699.5	699.2	697.9	696.7	695.4	694.2	692.6
142.5°	714.6	715.3	716.0	716.8	717.4	717.2	716.0	714.9	713.8	712.7	710.9
145°	739.8	740.4	741.1	741.8	742.5	742.3	741.4	740.4	739.5	738.5	736.1
147.5°	761.8	762.4	763.0	763.6	764.2	764.1	763.4	762.7	762.0	761.2	758.8
150°	775.3	776.0	776.7	777.4	778.1	778.0	777.2	776.3	775.5	774.7	772.5
152.5°	786.8	787.7	788.6	789.5	790.5	790.5	789.7	788.8	788.0	787.2	785.1
155°	802.8	803.9	805.0	806.1	807.2	807.4	806.6	805.7	804.9	804.1	802.4
157.5°	817.3	818.5	819.6	820.6	821.7	821.8	820.8	819.9	818.9	818.0	816.8
160°	825.9	826.9	827.8	828.8	829.7	829.8	829.0	828.1	827.3	826.5	825.6
162.5°	832.9	834.0	835.3	836.4	837.7	837.8	836.8	835.9	834.9	834.0	833.3
165°	843.4	844.4	845.3	846.2	847.2	847.2	846.2	845.3	844.4	843.4	842.9
167.5°	850.0	851.2	852.5	853.7	855.0	855.1	854.2	853.2	852.2	851.2	850.9
170°	854.0	855.2	856.5	857.7	859.0	859.1	858.1	857.2	856.2	855.2	855.0
172.5°	856.9	858.2	859.4	860.7	861.9	862.1	861.1	860.1	859.2	858.2	857.9
175°	859.6	860.9	862.4	863.7	865.1	865.3	864.3	863.4	862.5	861.5	861.2
177.5°	861.2	862.2	863.2	864.2	865.2	865.3	864.5	863.8	863.0	862.2	862.1
180°	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7



TEST NUMBER: P331769-940

CATALOG NUMBER: S122RDIW-S290D710U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9
2.5°	596.9	595.6	594.4	591.6	590.0	586.8	586.4	586.2	582.0	577.9	576.8
5°	617.4	614.1	609.3	603.6	597.7	591.7	587.6	584.3	576.2	568.6	564.1
7.5°	638.0	631.1	622.7	612.0	603.0	593.0	585.5	578.8	567.3	556.2	548.8
10°	653.4	642.1	631.0	616.2	604.6	593.3	582.7	573.6	560.7	546.1	535.7
12.5°	663.0	650.5	635.2	620.7	605.7	591.3	577.2	565.5	550.3	535.2	523.0
15°	675.9	662.5	643.9	623.2	604.0	585.1	569.0	554.4	534.6	516.5	501.5
17.5°	686.5	668.1	648.1	624.2	601.9	578.0	557.1	538.5	516.4	494.6	477.0
20°	689.9	671.6	648.5	624.6	598.3	570.2	547.7	527.4	503.7	480.0	459.8
22.5°	687.8	673.6	647.9	619.3	592.4	562.9	537.5	514.0	487.7	463.5	440.1
25°	673.5	668.6	644.4	613.1	582.4	548.1	518.7	493.0	463.1	437.1	411.6
27.5°	640.2	650.7	635.6	602.4	568.1	531.5	498.4	469.1	438.0	408.8	383.4
30°	608.1	632.1	625.7	594.9	556.6	520.6	483.5	452.9	419.7	389.7	364.6
32.5°	564.2	604.0	610.3	584.5	544.9	505.3	466.5	436.0	401.4	369.8	345.3
35°	494.2	553.8	581.1	564.7	525.0	482.2	442.2	406.7	371.8	340.7	316.4
37.5°	410.8	492.0	537.5	538.7	502.2	457.8	414.1	378.9	343.2	312.6	286.3
40°	356.7	444.6	504.0	517.1	486.3	438.4	394.1	358.3	323.5	293.5	263.3
42.5°	308.1	395.7	468.6	491.5	467.1	419.4	375.1	337.6	303.7	275.4	244.5
45°	249.1	325.7	406.1	447.0	433.5	389.3	342.5	306.8	275.1	250.6	221.0
47.5°	210.2	264.1	342.0	397.3	397.1	356.8	310.7	276.6	247.1	224.1	200.2
50°	188.0	235.0	300.8	363.6	368.8	335.0	291.2	257.4	229.9	205.8	186.5
52.5°	168.0	206.8	265.9	326.2	341.2	311.8	269.4	238.2	211.4	189.2	172.8
55°	142.0	172.0	217.0	273.2	296.0	275.3	237.6	208.4	186.7	168.1	153.9
57.5°	120.1	142.6	178.7	224.0	250.4	237.5	206.3	182.6	164.1	147.2	136.1
60°	106.4	124.8	155.3	193.2	222.4	213.3	186.7	164.7	148.9	134.3	123.8
62.5°	93.4	109.2	135.5	166.2	192.9	189.1	167.5	148.9	135.1	121.8	112.9
65°	75.2	86.7	107.2	131.3	152.8	154.5	138.9	126.4	114.0	103.5	95.6
67.5°	59.8	67.4	81.8	102.1	118.2	123.9	114.4	104.8	95.0	86.9	80.0
70°	50.5	56.5	67.1	83.5	98.3	104.3	98.8	91.3	82.8	76.2	70.3
72.5°	40.8	46.8	54.6	66.6	79.3	85.9	83.9	78.6	71.7	66.1	60.5
75°	30.8	32.6	37.9	46.0	55.9	61.6	63.0	60.2	54.7	50.5	47.2
77.5°	22.7	23.9	26.4	30.6	37.1	42.2	44.2	43.9	40.1	37.7	34.6
80°	18.2	18.8	20.1	21.8	26.8	31.8	33.3	33.3	30.6	29.6	26.6
82.5°	13.8	14.3	15.1	16.1	18.3	22.7	24.3	24.6	23.0	21.7	19.3
85°	7.9	7.7	8.1	8.7	9.1	10.3	12.8	13.2	12.8	11.1	10.5
87.5°	4.8	4.7	4.5	4.1	3.9	3.8	4.3	4.8	4.5	4.3	4.3
90°	10.3	9.2	8.0	6.7	5.2	3.7	2.1	0.6	2.1	3.7	5.2
92.5°	13.4	12.8	12.3	12.0	12.2	12.3	12.5	12.6	12.5	12.3	12.2
95°	22.4	21.4	20.4	22.3	26.8	31.4	36.0	40.6	36.0	31.4	26.8
97.5°	28.1	25.9	23.6	28.9	41.8	54.8	67.6	80.5	67.6	54.8	41.8
100°	30.9	28.5	26.1	34.5	53.5	72.5	91.5	110.5	91.5	72.5	53.5
102.5°	76.1	95.8	115.5	127.3	131.3	135.4	139.5	143.5	139.5	135.4	131.3
105°	113.8	151.7	189.6	206.4	202.2	198.1	193.9	189.8	193.9	198.1	202.2
107.5°	144.2	189.6	235.0	256.0	252.6	249.3	245.9	242.5	245.9	249.3	252.6
110°	189.4	229.5	269.6	288.2	285.3	282.4	279.5	276.5	279.5	282.4	285.3





TEST NUMBER: P331769-940

CATALOG NUMBER: S122RDIW-S290D710U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	295.3	305.2	315.1	318.8	316.2	313.7	311.1	308.5	311.1	313.7	316.2
115°	378.3	374.8	371.3	368.4	366.0	363.6	361.3	358.9	361.3	363.6	366.0
117.5°	421.9	419.5	417.1	414.6	411.9	409.3	406.6	404.0	406.6	409.3	411.9
120°	452.5	450.0	447.5	445.3	443.2	441.1	439.1	436.9	439.1	441.1	443.2
122.5°	481.6	478.8	476.2	473.7	471.5	469.3	467.2	464.9	467.2	469.3	471.5
125°	522.2	519.6	516.9	514.7	512.9	511.1	509.3	507.5	509.3	511.1	512.9
127.5°	560.0	558.0	556.1	554.1	552.1	550.1	548.0	546.1	548.0	550.1	552.1
130°	584.3	582.8	581.3	579.4	577.2	575.0	572.7	570.5	572.7	575.0	577.2
132.5°	607.8	606.3	604.8	603.1	601.2	599.3	597.4	595.6	597.4	599.3	601.2
135°	641.1	639.9	638.6	636.9	634.6	632.4	630.2	628.0	630.2	632.4	634.6
137.5°	671.4	669.9	668.5	667.0	665.5	664.0	662.4	660.8	662.4	664.0	665.5
140°	691.1	689.6	688.0	686.7	685.6	684.5	683.4	682.3	683.4	684.5	685.6
142.5°	709.2	707.4	705.6	704.3	703.3	702.3	701.2	700.3	701.2	702.3	703.3
145°	733.8	731.4	729.1	727.9	728.1	728.3	728.3	728.5	728.3	728.3	728.1
147.5°	756.5	754.2	751.9	751.0	751.5	752.1	752.6	753.0	752.6	752.1	751.5
150°	770.3	768.0	765.8	765.2	766.2	767.1	768.1	769.1	768.1	767.1	766.2
152.5°	782.9	780.9	778.7	778.2	779.3	780.4	781.5	782.6	781.5	780.4	779.3
155°	800.7	799.1	797.4	797.2	798.4	799.7	800.9	802.2	800.9	799.7	798.4
157.5°	815.6	814.5	813.3	813.3	814.3	815.4	816.5	817.5	816.5	815.4	814.3
160°	824.8	824.0	823.1	823.1	824.0	824.8	825.6	826.5	825.6	824.8	824.0
162.5°	832.6	831.8	831.1	831.2	832.0	832.9	833.7	834.5	833.7	832.9	832.0
165°	842.5	842.1	841.7	841.9	842.8	843.6	844.4	845.3	844.4	843.6	842.8
167.5°	850.4	850.1	849.7	849.9	850.7	851.6	852.4	853.2	852.4	851.6	850.7
170°	854.7	854.3	854.1	854.3	855.2	856.0	856.8	857.7	856.8	856.0	855.2
172.5°	857.6	857.4	857.1	857.4	858.2	859.1	859.9	860.7	859.9	859.1	858.2
175°	860.9	860.6	860.3	860.7	861.7	862.6	863.6	864.6	863.6	862.6	861.7
177.5°	862.0	861.8	861.7	862.1	862.9	863.6	864.4	865.2	864.4	863.6	862.9
180°	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7



TEST NUMBER: P331769-940

CATALOG NUMBER: S122RDIW-S290D710U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9
2.5°	574.7	573.5	571.4	568.2	566.2	562.8	560.6	561.9	562.2	561.9	561.6
5°	559.3	555.0	549.1	543.4	538.1	532.5	529.2	527.9	525.0	523.4	522.5
7.5°	540.6	533.2	525.0	515.1	506.7	497.8	493.4	491.2	485.4	482.2	479.5
10°	526.6	515.1	506.8	493.8	485.9	474.4	466.5	466.7	458.8	454.3	451.1
12.5°	511.2	498.6	484.7	473.1	462.1	452.8	443.3	439.4	431.1	426.8	418.0
15°	485.7	470.9	456.4	440.6	429.4	415.0	401.3	384.4	370.9	359.1	355.9
17.5°	457.9	439.5	424.9	406.4	387.3	363.1	347.1	337.3	329.2	323.0	318.3
20°	438.7	420.1	404.5	376.6	350.8	334.4	322.7	315.1	306.7	300.0	296.3
22.5°	418.7	399.2	377.9	346.7	326.6	313.5	303.1	294.4	288.6	283.5	280.1
25°	390.1	368.8	333.8	312.4	296.1	282.3	275.1	269.8	263.8	256.6	253.4
27.5°	360.0	326.2	301.0	285.0	269.6	260.6	254.0	246.2	240.8	237.6	234.2
30°	337.4	303.6	284.0	266.5	255.7	245.7	238.0	233.5	228.3	222.8	220.6
32.5°	312.4	285.3	266.4	252.0	240.9	232.4	226.3	219.1	215.3	212.0	207.3
35°	281.2	260.6	243.4	231.8	221.1	214.3	207.2	203.0	196.1	193.2	191.5
37.5°	254.8	237.0	224.2	211.8	203.4	195.8	191.5	184.7	181.7	177.7	173.9
40°	239.8	222.4	210.1	199.9	190.6	184.9	179.5	174.0	169.5	167.7	163.1
42.5°	224.6	210.4	198.0	187.0	180.7	174.7	167.8	163.8	159.2	156.2	153.4
45°	203.6	191.0	180.5	171.4	164.4	158.2	153.7	147.0	144.5	138.6	136.1
47.5°	185.1	173.4	163.4	154.7	148.0	143.9	137.4	132.2	128.0	124.3	121.2
50°	172.0	162.2	152.5	144.8	138.8	132.9	126.2	123.6	117.1	115.2	113.4
52.5°	160.0	150.7	141.9	134.3	128.2	122.5	116.6	113.2	108.8	107.0	105.7
55°	143.2	134.3	125.8	119.1	113.1	107.2	103.5	99.2	97.2	95.8	94.2
57.5°	126.4	118.3	111.8	105.0	98.9	94.3	90.1	87.5	85.4	83.6	81.6
60°	115.7	108.0	102.1	95.8	89.5	85.7	82.5	79.4	77.0	74.1	73.3
62.5°	104.3	97.6	92.2	86.1	80.6	77.1	74.0	71.2	68.2	64.1	63.0
65°	88.7	83.5	77.8	72.7	67.9	64.4	59.9	56.7	55.5	55.1	54.9
67.5°	74.6	69.6	64.7	59.6	55.2	52.0	49.7	49.2	48.3	48.2	47.5
70°	65.2	60.5	55.7	50.8	46.5	46.0	45.2	44.3	43.3	43.0	42.5
72.5°	56.8	52.0	47.1	43.2	41.4	40.7	39.9	39.0	38.3	37.9	37.7
75°	43.5	39.1	35.8	34.4	33.4	32.8	31.6	31.0	30.6	30.0	29.8
77.5°	31.4	28.8	27.4	26.5	25.4	24.8	24.1	23.5	23.0	22.9	22.6
80°	23.9	22.6	21.7	20.4	20.1	19.3	19.1	18.5	18.6	18.0	18.0
82.5°	18.5	17.0	16.1	15.6	15.2	14.5	14.4	14.1	14.1	13.6	13.6
85°	9.5	9.1	8.7	8.3	8.3	7.7	7.9	7.7	7.7	7.3	7.1
87.5°	4.5	4.5	4.5	4.6	4.9	4.9	5.1	5.1	5.2	5.4	5.3
90°	6.7	8.0	9.2	10.3	11.4	12.5	13.2	13.9	14.5	15.2	15.8
92.5°	12.0	12.3	12.8	13.4	13.9	14.4	14.8	15.2	15.6	16.0	16.2
95°	22.3	20.4	21.4	22.4	23.4	24.3	25.1	25.8	26.4	27.1	27.4
97.5°	28.9	23.6	25.9	28.1	30.3	32.5	33.2	33.7	34.2	34.8	35.1
100°	34.5	26.1	28.5	30.9	33.3	35.6	36.6	37.8	38.9	40.0	40.8
102.5°	127.3	115.5	95.8	76.1	56.3	36.6	38.0	39.5	40.9	42.4	43.2
105°	206.4	189.6	151.7	113.8	76.0	38.1	39.6	41.1	42.6	44.1	45.2
107.5°	256.0	235.0	189.6	144.2	98.7	53.3	51.7	50.2	48.7	47.1	46.6
110°	288.2	269.6	229.5	189.4	149.4	109.2	95.4	81.5	67.6	53.8	47.1



TEST NUMBER: P331769-940

CATALOG NUMBER: S122RDIW-S290D710U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	318.8	315.1	305.2	295.3	285.4	275.5	225.0	174.3	123.8	73.1	48.1
115°	368.4	371.3	374.8	378.3	381.7	385.1	320.9	256.7	192.4	128.2	91.1
117.5°	414.6	417.1	419.5	421.9	424.2	426.6	411.1	395.6	380.0	364.4	340.3
120°	445.3	447.5	450.0	452.5	455.0	457.5	459.2	460.9	462.5	464.2	455.7
122.5°	473.7	476.2	478.8	481.6	484.3	487.1	488.0	489.0	490.0	491.1	489.7
125°	514.7	516.9	519.6	522.2	524.9	527.4	528.4	529.4	530.4	531.4	532.1
127.5°	554.1	556.1	558.0	560.0	562.0	563.9	565.3	566.8	568.2	569.6	570.3
130°	579.4	581.3	582.8	584.3	585.9	587.5	589.0	590.5	592.0	593.5	594.2
132.5°	603.1	604.8	606.3	607.8	609.4	610.9	612.2	613.5	614.8	616.1	616.7
135°	636.9	638.6	639.9	641.1	642.4	643.6	645.0	646.4	647.7	649.2	649.7
137.5°	667.0	668.5	669.9	671.4	672.8	674.2	675.6	676.9	678.2	679.7	680.1
140°	686.7	688.0	689.6	691.1	692.6	694.2	695.4	696.7	697.9	699.2	699.5
142.5°	704.3	705.6	707.4	709.2	710.9	712.7	713.8	714.9	716.0	717.2	717.4
145°	727.9	729.1	731.4	733.8	736.1	738.5	739.5	740.4	741.4	742.3	742.5
147.5°	751.0	751.9	754.2	756.5	758.8	761.2	762.0	762.7	763.4	764.1	764.2
150°	765.2	765.8	768.0	770.3	772.5	774.7	775.5	776.3	777.2	778.0	778.1
152.5°	778.2	778.7	780.9	782.9	785.1	787.2	788.0	788.8	789.7	790.5	790.5
155°	797.2	797.4	799.1	800.7	802.4	804.1	804.9	805.7	806.6	807.4	807.2
157.5°	813.3	813.3	814.5	815.6	816.8	818.0	818.9	819.9	820.8	821.8	821.7
160°	823.1	823.1	824.0	824.8	825.6	826.5	827.3	828.1	829.0	829.8	829.7
162.5°	831.2	831.1	831.8	832.6	833.3	834.0	834.9	835.9	836.8	837.8	837.7
165°	841.9	841.7	842.1	842.5	842.9	843.4	844.4	845.3	846.2	847.2	847.2
167.5°	849.9	849.7	850.1	850.4	850.9	851.2	852.2	853.2	854.2	855.1	855.0
170°	854.3	854.1	854.3	854.7	855.0	855.2	856.2	857.2	858.1	859.1	859.0
172.5°	857.4	857.1	857.4	857.6	857.9	858.2	859.2	860.1	861.1	862.1	861.9
175°	860.7	860.3	860.6	860.9	861.2	861.5	862.5	863.4	864.3	865.3	865.1
177.5°	862.1	861.7	861.8	862.0	862.1	862.2	863.0	863.8	864.5	865.3	865.2
180°	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7



TEST NUMBER: P331769-940

CATALOG NUMBER: S122RDIW-S290D710U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9
2.5°	559.8	560.1	559.6	559.9	559.6	560.1	559.8	561.6	561.9	562.2	561.9
5°	521.6	519.2	518.7	518.2	518.7	519.2	521.6	522.5	523.4	525.0	527.9
7.5°	476.0	475.6	474.6	473.1	474.6	475.6	476.0	479.5	482.2	485.4	491.2
10°	446.7	445.6	445.4	444.0	445.4	445.6	446.7	451.1	454.3	458.8	466.7
12.5°	412.2	405.7	405.1	401.5	405.1	405.7	412.2	418.0	426.8	431.1	439.4
15°	351.1	349.8	345.7	343.1	345.7	349.8	351.1	355.9	359.1	370.9	384.4
17.5°	316.0	312.0	310.8	310.2	310.8	312.0	316.0	318.3	323.0	329.2	337.3
20°	293.5	289.9	289.3	288.8	289.3	289.9	293.5	296.3	300.0	306.7	315.1
22.5°	277.9	274.1	272.6	271.3	272.6	274.1	277.9	280.1	283.5	288.6	294.4
25°	251.4	249.9	249.1	248.7	249.1	249.9	251.4	253.4	256.6	263.8	269.8
27.5°	230.6	227.5	226.9	225.8	226.9	227.5	230.6	234.2	237.6	240.8	246.2
30°	218.7	217.8	216.3	215.1	216.3	217.8	218.7	220.6	222.8	228.3	233.5
32.5°	204.8	203.9	202.7	202.2	202.7	203.9	204.8	207.3	212.0	215.3	219.1
35°	189.4	186.5	185.3	183.5	185.3	186.5	189.4	191.5	193.2	196.1	203.0
37.5°	173.1	171.6	169.9	170.5	169.9	171.6	173.1	173.9	177.7	181.7	184.7
40°	160.4	159.4	159.0	158.8	159.0	159.4	160.4	163.1	167.7	169.5	174.0
42.5°	150.3	147.6	146.5	146.5	146.5	147.6	150.3	153.4	156.2	159.2	163.8
45°	135.1	132.5	130.6	130.8	130.6	132.5	135.1	136.1	138.6	144.5	147.0
47.5°	119.5	119.4	118.2	118.6	118.2	119.4	119.5	121.2	124.3	128.0	132.2
50°	112.0	110.8	109.9	110.2	109.9	110.8	112.0	113.4	115.2	117.1	123.6
52.5°	104.9	103.8	103.2	104.1	103.2	103.8	104.9	105.7	107.0	108.8	113.2
55°	93.2	91.9	91.8	91.6	91.8	91.9	93.2	94.2	95.8	97.2	99.2
57.5°	80.1	79.3	78.0	77.6	78.0	79.3	80.1	81.6	83.6	85.4	87.5
60°	70.7	69.1	67.1	66.9	67.1	69.1	70.7	73.3	74.1	77.0	79.4
62.5°	62.1	61.8	61.3	61.3	61.3	61.8	62.1	63.0	64.1	68.2	71.2
65°	54.5	54.3	54.5	54.7	54.5	54.3	54.5	54.9	55.1	55.5	56.7
67.5°	47.4	47.1	46.7	46.9	46.7	47.1	47.4	47.5	48.2	48.3	49.2
70°	42.1	41.9	41.7	41.7	41.7	41.9	42.1	42.5	43.0	43.3	44.3
72.5°	36.9	36.9	36.7	36.6	36.7	36.9	36.9	37.7	37.9	38.3	39.0
75°	29.6	29.2	29.2	29.2	29.2	29.2	29.6	29.8	30.0	30.6	31.0
77.5°	22.6	22.3	22.1	21.9	22.1	22.3	22.6	22.6	22.9	23.0	23.5
80°	17.8	17.7	17.4	17.4	17.4	17.7	17.8	18.0	18.0	18.6	18.5
82.5°	13.6	13.4	13.4	13.2	13.4	13.4	13.6	13.6	13.6	14.1	14.1
85°	7.3	7.5	7.3	7.7	7.3	7.5	7.3	7.1	7.3	7.7	7.7
87.5°	5.4	5.2	5.4	5.4	5.4	5.2	5.4	5.3	5.4	5.2	5.1
90°	16.1	16.3	16.6	16.9	16.6	16.3	16.1	15.8	15.2	14.5	13.9
92.5°	16.3	16.5	16.7	16.9	16.7	16.5	16.3	16.2	16.0	15.6	15.2
95°	27.3	27.1	27.0	26.8	27.0	27.1	27.3	27.4	27.1	26.4	25.8
97.5°	35.3	35.5	35.7	35.8	35.7	35.5	35.3	35.1	34.8	34.2	33.7
100°	41.0	41.3	41.6	41.8	41.6	41.3	41.0	40.8	40.0	38.9	37.8
102.5°	43.7	44.1	44.4	44.9	44.4	44.1	43.7	43.2	42.4	40.9	39.5
105°	45.7	46.4	46.9	47.4	46.9	46.4	45.7	45.2	44.1	42.6	41.1
107.5°	47.2	47.7	48.2	48.8	48.2	47.7	47.2	46.6	47.1	48.7	50.2
110°	47.6	48.2	48.8	49.3	48.8	48.2	47.6	47.1	53.8	67.6	81.5



TEST NUMBER: P331769-940

CATALOG NUMBER: S122RDIW-S290D710U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	48.5	49.0	49.4	49.8	49.4	49.0	48.5	48.1	73.1	123.8	174.3
115°	81.1	71.2	61.2	51.2	61.2	71.2	81.1	91.1	128.2	192.4	256.7
117.5°	307.5	274.6	241.8	209.0	241.8	274.6	307.5	340.3	364.4	380.0	395.6
120°	436.9	418.2	399.5	380.8	399.5	418.2	436.9	455.7	464.2	462.5	460.9
122.5°	486.1	482.4	478.8	475.2	478.8	482.4	486.1	489.7	491.1	490.0	489.0
125°	532.4	532.9	533.3	533.7	533.3	532.9	532.4	532.1	531.4	530.4	529.4
127.5°	570.4	570.5	570.6	570.7	570.6	570.5	570.4	570.3	569.6	568.2	566.8
130°	594.1	594.0	593.8	593.7	593.8	594.0	594.1	594.2	593.5	592.0	590.5
132.5°	616.5	616.4	616.3	616.2	616.3	616.4	616.5	616.7	616.1	614.8	613.5
135°	649.4	649.2	648.9	648.6	648.9	649.2	649.4	649.7	649.2	647.7	646.4
137.5°	679.6	679.1	678.7	678.1	678.7	679.1	679.6	680.1	679.7	678.2	676.9
140°	698.7	698.0	697.3	696.7	697.3	698.0	698.7	699.5	699.2	697.9	696.7
142.5°	716.8	716.0	715.3	714.6	715.3	716.0	716.8	717.4	717.2	716.0	714.9
145°	741.8	741.1	740.4	739.8	740.4	741.1	741.8	742.5	742.3	741.4	740.4
147.5°	763.6	763.0	762.4	761.8	762.4	763.0	763.6	764.2	764.1	763.4	762.7
150°	777.4	776.7	776.0	775.3	776.0	776.7	777.4	778.1	778.0	777.2	776.3
152.5°	789.5	788.6	787.7	786.8	787.7	788.6	789.5	790.5	790.5	789.7	788.8
155°	806.1	805.0	803.9	802.8	803.9	805.0	806.1	807.2	807.4	806.6	805.7
157.5°	820.6	819.6	818.5	817.3	818.5	819.6	820.6	821.7	821.8	820.8	819.9
160°	828.8	827.8	826.9	825.9	826.9	827.8	828.8	829.7	829.8	829.0	828.1
162.5°	836.4	835.3	834.0	832.9	834.0	835.3	836.4	837.7	837.8	836.8	835.9
165°	846.2	845.3	844.4	843.4	844.4	845.3	846.2	847.2	847.2	846.2	845.3
167.5°	853.7	852.5	851.2	850.0	851.2	852.5	853.7	855.0	855.1	854.2	853.2
170°	857.7	856.5	855.2	854.0	855.2	856.5	857.7	859.0	859.1	858.1	857.2
172.5°	860.7	859.4	858.2	856.9	858.2	859.4	860.7	861.9	862.1	861.1	860.1
175°	863.7	862.4	860.9	859.6	860.9	862.4	863.7	865.1	865.3	864.3	863.4
177.5°	864.2	863.2	862.2	861.2	862.2	863.2	864.2	865.2	865.3	864.5	863.8
180°	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7



TEST NUMBER: P331769-940

CATALOG NUMBER: S122RDIW-S290D710U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9
2.5°	560.6	562.8	566.2	568.2	571.4	573.5	574.7	576.8	577.9	582.0	586.2
5°	529.2	532.5	538.1	543.4	549.1	555.0	559.3	564.1	568.6	576.2	584.3
7.5°	493.4	497.8	506.7	515.1	525.0	533.2	540.6	548.8	556.2	567.3	578.8
10°	466.5	474.4	485.9	493.8	506.8	515.1	526.6	535.7	546.1	560.7	573.6
12.5°	443.3	452.8	462.1	473.1	484.7	498.6	511.2	523.0	535.2	550.3	565.5
15°	401.3	415.0	429.4	440.6	456.4	470.9	485.7	501.5	516.5	534.6	554.4
17.5°	347.1	363.1	387.3	406.4	424.9	439.5	457.9	477.0	494.6	516.4	538.5
20°	322.7	334.4	350.8	376.6	404.5	420.1	438.7	459.8	480.0	503.7	527.4
22.5°	303.1	313.5	326.6	346.7	377.9	399.2	418.7	440.1	463.5	487.7	514.0
25°	275.1	282.3	296.1	312.4	333.8	368.8	390.1	411.6	437.1	463.1	493.0
27.5°	254.0	260.6	269.6	285.0	301.0	326.2	360.0	383.4	408.8	438.0	469.1
30°	238.0	245.7	255.7	266.5	284.0	303.6	337.4	364.6	389.7	419.7	452.9
32.5°	226.3	232.4	240.9	252.0	266.4	285.3	312.4	345.3	369.8	401.4	436.0
35°	207.2	214.3	221.1	231.8	243.4	260.6	281.2	316.4	340.7	371.8	406.7
37.5°	191.5	195.8	203.4	211.8	224.2	237.0	254.8	286.3	312.6	343.2	378.9
40°	179.5	184.9	190.6	199.9	210.1	222.4	239.8	263.3	293.5	323.5	358.3
42.5°	167.8	174.7	180.7	187.0	198.0	210.4	224.6	244.5	275.4	303.7	337.6
45°	153.7	158.2	164.4	171.4	180.5	191.0	203.6	221.0	250.6	275.1	306.8
47.5°	137.4	143.9	148.0	154.7	163.4	173.4	185.1	200.2	224.1	247.1	276.6
50°	126.2	132.9	138.8	144.8	152.5	162.2	172.0	186.5	205.8	229.9	257.4
52.5°	116.6	122.5	128.2	134.3	141.9	150.7	160.0	172.8	189.2	211.4	238.2
55°	103.5	107.2	113.1	119.1	125.8	134.3	143.2	153.9	168.1	186.7	208.4
57.5°	90.1	94.3	98.9	105.0	111.8	118.3	126.4	136.1	147.2	164.1	182.6
60°	82.5	85.7	89.5	95.8	102.1	108.0	115.7	123.8	134.3	148.9	164.7
62.5°	74.0	77.1	80.6	86.1	92.2	97.6	104.3	112.9	121.8	135.1	148.9
65°	59.9	64.4	67.9	72.7	77.8	83.5	88.7	95.6	103.5	114.0	126.4
67.5°	49.7	52.0	55.2	59.6	64.7	69.6	74.6	80.0	86.9	95.0	104.8
70°	45.2	46.0	46.5	50.8	55.7	60.5	65.2	70.3	76.2	82.8	91.3
72.5°	39.9	40.7	41.4	43.2	47.1	52.0	56.8	60.5	66.1	71.7	78.6
75°	31.6	32.8	33.4	34.4	35.8	39.1	43.5	47.2	50.5	54.7	60.2
77.5°	24.1	24.8	25.4	26.5	27.4	28.8	31.4	34.6	37.7	40.1	43.9
80°	19.1	19.3	20.1	20.4	21.7	22.6	23.9	26.6	29.6	30.6	33.3
82.5°	14.4	14.5	15.2	15.6	16.1	17.0	18.5	19.3	21.7	23.0	24.6
85°	7.9	7.7	8.3	8.3	8.7	9.1	9.5	10.5	11.1	12.8	13.2
87.5°	5.1	4.9	4.9	4.6	4.5	4.5	4.5	4.3	4.3	4.5	4.8
90°	13.2	12.5	11.4	10.3	9.2	8.0	6.7	5.2	3.7	2.1	0.6
92.5°	14.8	14.4	13.9	13.4	12.8	12.3	12.0	12.2	12.3	12.5	12.6
95°	25.1	24.3	23.4	22.4	21.4	20.4	22.3	26.8	31.4	36.0	40.6
97.5°	33.2	32.5	30.3	28.1	25.9	23.6	28.9	41.8	54.8	67.6	80.5
100°	36.6	35.6	33.3	30.9	28.5	26.1	34.5	53.5	72.5	91.5	110.5
102.5°	38.0	36.6	56.3	76.1	95.8	115.5	127.3	131.3	135.4	139.5	143.5
105°	39.6	38.1	76.0	113.8	151.7	189.6	206.4	202.2	198.1	193.9	189.8
107.5°	51.7	53.3	98.7	144.2	189.6	235.0	256.0	252.6	249.3	245.9	242.5
110°	95.4	109.2	149.4	189.4	229.5	269.6	288.2	285.3	282.4	279.5	276.5



TEST NUMBER: P331769-940

CATALOG NUMBER: S122RDIW-S290D710U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	225.0	275.5	285.4	295.3	305.2	315.1	318.8	316.2	313.7	311.1	308.5
115°	320.9	385.1	381.7	378.3	374.8	371.3	368.4	366.0	363.6	361.3	358.9
117.5°	411.1	426.6	424.2	421.9	419.5	417.1	414.6	411.9	409.3	406.6	404.0
120°	459.2	457.5	455.0	452.5	450.0	447.5	445.3	443.2	441.1	439.1	436.9
122.5°	488.0	487.1	484.3	481.6	478.8	476.2	473.7	471.5	469.3	467.2	464.9
125°	528.4	527.4	524.9	522.2	519.6	516.9	514.7	512.9	511.1	509.3	507.5
127.5°	565.3	563.9	562.0	560.0	558.0	556.1	554.1	552.1	550.1	548.0	546.1
130°	589.0	587.5	585.9	584.3	582.8	581.3	579.4	577.2	575.0	572.7	570.5
132.5°	612.2	610.9	609.4	607.8	606.3	604.8	603.1	601.2	599.3	597.4	595.6
135°	645.0	643.6	642.4	641.1	639.9	638.6	636.9	634.6	632.4	630.2	628.0
137.5°	675.6	674.2	672.8	671.4	669.9	668.5	667.0	665.5	664.0	662.4	660.8
140°	695.4	694.2	692.6	691.1	689.6	688.0	686.7	685.6	684.5	683.4	682.3
142.5°	713.8	712.7	710.9	709.2	707.4	705.6	704.3	703.3	702.3	701.2	700.3
145°	739.5	738.5	736.1	733.8	731.4	729.1	727.9	728.1	728.3	728.3	728.5
147.5°	762.0	761.2	758.8	756.5	754.2	751.9	751.0	751.5	752.1	752.6	753.0
150°	775.5	774.7	772.5	770.3	768.0	765.8	765.2	766.2	767.1	768.1	769.1
152.5°	788.0	787.2	785.1	782.9	780.9	778.7	778.2	779.3	780.4	781.5	782.6
155°	804.9	804.1	802.4	800.7	799.1	797.4	797.2	798.4	799.7	800.9	802.2
157.5°	818.9	818.0	816.8	815.6	814.5	813.3	813.3	814.3	815.4	816.5	817.5
160°	827.3	826.5	825.6	824.8	824.0	823.1	823.1	824.0	824.8	825.6	826.5
162.5°	834.9	834.0	833.3	832.6	831.8	831.1	831.2	832.0	832.9	833.7	834.5
165°	844.4	843.4	842.9	842.5	842.1	841.7	841.9	842.8	843.6	844.4	845.3
167.5°	852.2	851.2	850.9	850.4	850.1	849.7	849.9	850.7	851.6	852.4	853.2
170°	856.2	855.2	855.0	854.7	854.3	854.1	854.3	855.2	856.0	856.8	857.7
172.5°	859.2	858.2	857.9	857.6	857.4	857.1	857.4	858.2	859.1	859.9	860.7
175°	862.5	861.5	861.2	860.9	860.6	860.3	860.7	861.7	862.6	863.6	864.6
177.5°	863.0	862.2	862.1	862.0	861.8	861.7	862.1	862.9	863.6	864.4	865.2
180°	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7



TEST NUMBER: P331769-940

CATALOG NUMBER: S122RDIW-S290D710U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9
2.5°	586.4	586.8	590.0	591.6	594.4	595.6	596.9	596.6	596.6	597.2	601.7
5°	587.6	591.7	597.7	603.6	609.3	614.1	617.4	620.6	621.9	627.7	632.9
7.5°	585.5	593.0	603.0	612.0	622.7	631.1	638.0	644.4	648.6	657.2	665.9
10°	582.7	593.3	604.6	616.2	631.0	642.1	653.4	662.2	664.9	677.7	685.0
12.5°	577.2	591.3	605.7	620.7	635.2	650.5	663.0	671.7	681.7	693.1	706.6
15°	569.0	585.1	604.0	623.2	643.9	662.5	675.9	691.1	702.0	714.6	726.4
17.5°	557.1	578.0	601.9	624.2	648.1	668.1	686.5	701.1	708.7	716.0	717.6
20°	547.7	570.2	598.3	624.6	648.5	671.6	689.9	702.0	704.1	704.3	693.6
22.5°	537.5	562.9	592.4	619.3	647.9	673.6	687.8	692.9	684.9	671.2	650.4
25°	518.7	548.1	582.4	613.1	644.4	668.6	673.5	664.4	636.2	606.6	569.2
27.5°	498.4	531.5	568.1	602.4	635.6	650.7	640.2	607.3	556.6	512.5	459.1
30°	483.5	520.6	556.6	594.9	625.7	632.1	608.1	559.6	500.5	434.1	380.8
32.5°	466.5	505.3	544.9	584.5	610.3	604.0	564.2	504.5	435.2	369.9	319.6
35°	442.2	482.2	525.0	564.7	581.1	553.8	494.2	416.6	345.7	284.8	250.1
37.5°	414.1	457.8	502.2	538.7	537.5	492.0	410.8	330.7	271.2	235.1	210.4
40°	394.1	438.4	486.3	517.1	504.0	444.6	356.7	281.2	237.6	208.8	190.8
42.5°	375.1	419.4	467.1	491.5	468.6	395.7	308.1	248.9	212.9	190.6	175.9
45°	342.5	389.3	433.5	447.0	406.1	325.7	249.1	206.2	182.3	165.7	155.6
47.5°	310.7	356.8	397.1	397.3	342.0	264.1	210.2	178.4	158.0	145.2	137.9
50°	291.2	335.0	368.8	363.6	300.8	235.0	188.0	160.6	143.7	133.7	126.0
52.5°	269.4	311.8	341.2	326.2	265.9	206.8	168.0	145.1	131.0	122.3	115.5
55°	237.6	275.3	296.0	273.2	217.0	172.0	142.0	123.9	113.4	106.1	100.2
57.5°	206.3	237.5	250.4	224.0	178.7	142.6	120.1	106.6	96.1	90.9	87.8
60°	186.7	213.3	222.4	193.2	155.3	124.8	106.4	93.8	86.1	82.7	79.6
62.5°	167.5	189.1	192.9	166.2	135.5	109.2	93.4	82.8	77.7	74.4	71.5
65°	138.9	154.5	152.8	131.3	107.2	86.7	75.2	68.7	64.8	60.2	55.1
67.5°	114.4	123.9	118.2	102.1	81.8	67.4	59.8	54.9	50.1	45.7	44.6
70°	98.8	104.3	98.3	83.5	67.1	56.5	50.5	44.6	41.7	40.8	38.9
72.5°	83.9	85.9	79.3	66.6	54.6	46.8	40.8	37.6	36.0	35.2	34.1
75°	63.0	61.6	55.9	46.0	37.9	32.6	30.8	29.6	28.5	27.7	27.1
77.5°	44.2	42.2	37.1	30.6	26.4	23.9	22.7	22.1	21.7	21.2	20.6
80°	33.3	31.8	26.8	21.8	20.1	18.8	18.2	17.4	17.4	17.0	16.4
82.5°	24.3	22.7	18.3	16.1	15.1	14.3	13.8	13.4	13.2	13.3	12.8
85°	12.8	10.3	9.1	8.7	8.1	7.7	7.9	7.5	7.5	7.5	7.3
87.5°	4.3	3.8	3.9	4.1	4.5	4.7	4.8	5.0	5.4	5.4	5.7
90°	2.1	3.7	5.2	6.7	8.0	9.2	10.3	11.4	12.5	13.2	13.9
92.5°	12.5	12.3	12.2	12.0	12.3	12.8	13.4	13.9	14.4	14.8	15.2
95°	36.0	31.4	26.8	22.3	20.4	21.4	22.4	23.4	24.3	25.1	25.8
97.5°	67.6	54.8	41.8	28.9	23.6	25.9	28.1	30.3	32.5	33.2	33.7
100°	91.5	72.5	53.5	34.5	26.1	28.5	30.9	33.3	35.6	36.6	37.8
102.5°	139.5	135.4	131.3	127.3	115.5	95.8	76.1	56.3	36.6	38.0	39.5
105°	193.9	198.1	202.2	206.4	189.6	151.7	113.8	76.0	38.1	39.6	41.1
107.5°	245.9	249.3	252.6	256.0	235.0	189.6	144.2	98.7	53.3	51.7	50.2
110°	279.5	282.4	285.3	288.2	269.6	229.5	189.4	149.4	109.2	95.4	81.5





TEST NUMBER: P331769-940

CATALOG NUMBER: S122RDIW-S290D710U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	311.1	313.7	316.2	318.8	315.1	305.2	295.3	285.4	275.5	225.0	174.3
115°	361.3	363.6	366.0	368.4	371.3	374.8	378.3	381.7	385.1	320.9	256.7
117.5°	406.6	409.3	411.9	414.6	417.1	419.5	421.9	424.2	426.6	411.1	395.6
120°	439.1	441.1	443.2	445.3	447.5	450.0	452.5	455.0	457.5	459.2	460.9
122.5°	467.2	469.3	471.5	473.7	476.2	478.8	481.6	484.3	487.1	488.0	489.0
125°	509.3	511.1	512.9	514.7	516.9	519.6	522.2	524.9	527.4	528.4	529.4
127.5°	548.0	550.1	552.1	554.1	556.1	558.0	560.0	562.0	563.9	565.3	566.8
130°	572.7	575.0	577.2	579.4	581.3	582.8	584.3	585.9	587.5	589.0	590.5
132.5°	597.4	599.3	601.2	603.1	604.8	606.3	607.8	609.4	610.9	612.2	613.5
135°	630.2	632.4	634.6	636.9	638.6	639.9	641.1	642.4	643.6	645.0	646.4
137.5°	662.4	664.0	665.5	667.0	668.5	669.9	671.4	672.8	674.2	675.6	676.9
140°	683.4	684.5	685.6	686.7	688.0	689.6	691.1	692.6	694.2	695.4	696.7
142.5°	701.2	702.3	703.3	704.3	705.6	707.4	709.2	710.9	712.7	713.8	714.9
145°	728.3	728.3	728.1	727.9	729.1	731.4	733.8	736.1	738.5	739.5	740.4
147.5°	752.6	752.1	751.5	751.0	751.9	754.2	756.5	758.8	761.2	762.0	762.7
150°	768.1	767.1	766.2	765.2	765.8	768.0	770.3	772.5	774.7	775.5	776.3
152.5°	781.5	780.4	779.3	778.2	778.7	780.9	782.9	785.1	787.2	788.0	788.8
155°	800.9	799.7	798.4	797.2	797.4	799.1	800.7	802.4	804.1	804.9	805.7
157.5°	816.5	815.4	814.3	813.3	813.3	814.5	815.6	816.8	818.0	818.9	819.9
160°	825.6	824.8	824.0	823.1	823.1	824.0	824.8	825.6	826.5	827.3	828.1
162.5°	833.7	832.9	832.0	831.2	831.1	831.8	832.6	833.3	834.0	834.9	835.9
165°	844.4	843.6	842.8	841.9	841.7	842.1	842.5	842.9	843.4	844.4	845.3
167.5°	852.4	851.6	850.7	849.9	849.7	850.1	850.4	850.9	851.2	852.2	853.2
170°	856.8	856.0	855.2	854.3	854.1	854.3	854.7	855.0	855.2	856.2	857.2
172.5°	859.9	859.1	858.2	857.4	857.1	857.4	857.6	857.9	858.2	859.2	860.1
175°	863.6	862.6	861.7	860.7	860.3	860.6	860.9	861.2	861.5	862.5	863.4
177.5°	864.4	863.6	862.9	862.1	861.7	861.8	862.0	862.1	862.2	863.0	863.8
180°	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7	862.7



TEST NUMBER: P331769-940

CATALOG NUMBER: S122RDIW-S290D710U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	582.9	582.9	582.9	582.9	582.9	582.9	582.9
2.5°	603.3	605.5	606.5	606.5	607.6	607.1	606.6
5°	638.0	641.9	642.7	646.3	649.0	648.2	648.5
7.5°	672.5	678.7	684.8	687.6	688.0	689.6	690.3
10°	693.8	698.8	708.3	706.9	714.0	718.1	711.4
12.5°	714.2	721.0	727.6	729.4	733.4	734.8	732.1
15°	732.6	736.3	736.6	735.7	736.9	735.8	732.0
17.5°	715.4	709.4	697.5	691.8	687.3	680.6	678.0
20°	686.9	669.4	649.2	641.1	631.6	613.0	617.4
22.5°	625.3	605.5	585.1	561.5	550.2	532.5	531.5
25°	529.5	495.3	457.5	431.2	415.8	398.2	390.5
27.5°	411.7	368.5	337.7	322.1	307.8	293.9	293.3
30°	334.2	301.8	277.9	264.6	255.8	249.9	251.2
32.5°	281.7	259.5	243.3	232.3	225.9	221.4	221.3
35°	230.3	215.1	204.7	200.1	195.5	192.3	192.4
37.5°	197.1	188.0	182.2	177.1	174.2	172.5	171.7
40°	180.0	172.5	168.1	165.1	162.6	160.4	160.0
42.5°	166.7	160.4	156.0	153.6	151.3	149.7	149.4
45°	147.8	142.8	138.8	136.1	135.1	133.7	133.7
47.5°	131.5	126.5	123.4	121.7	120.0	119.0	119.0
50°	120.6	116.6	113.9	112.8	111.4	110.8	110.6
52.5°	110.7	107.7	105.8	105.0	104.4	103.7	103.8
55°	97.2	95.6	94.8	94.2	93.2	91.9	92.7
57.5°	86.0	84.5	82.4	80.4	79.5	78.6	79.0
60°	78.0	75.2	72.3	70.1	69.5	67.7	67.7
62.5°	67.9	63.9	60.5	59.2	58.6	57.8	57.6
65°	52.3	50.6	49.8	49.0	48.6	48.6	48.2
67.5°	43.3	42.6	41.7	41.6	41.2	41.0	40.9
70°	38.3	37.5	37.1	36.8	36.5	36.6	36.0
72.5°	33.4	32.8	32.7	32.2	31.9	31.9	31.5
75°	26.3	26.3	26.1	25.9	25.5	25.3	25.5
77.5°	20.2	20.3	20.0	19.9	19.9	19.9	19.7
80°	16.2	16.4	16.2	16.0	15.8	16.0	15.8
82.5°	12.8	12.5	12.5	12.4	12.4	12.3	12.2
85°	7.3	7.5	7.3	7.1	7.1	7.1	7.3
87.5°	5.7	5.8	5.9	6.0	6.0	6.1	6.0
90°	14.5	15.2	15.8	16.1	16.3	16.6	16.9
92.5°	15.6	16.0	16.2	16.3	16.5	16.7	16.9
95°	26.4	27.1	27.4	27.3	27.1	27.0	26.8
97.5°	34.2	34.8	35.1	35.3	35.5	35.7	35.8
100°	38.9	40.0	40.8	41.0	41.3	41.6	41.8
102.5°	40.9	42.4	43.2	43.7	44.1	44.4	44.9
105°	42.6	44.1	45.2	45.7	46.4	46.9	47.4
107.5°	48.7	47.1	46.6	47.2	47.7	48.2	48.8
110°	67.6	53.8	47.1	47.6	48.2	48.8	49.3



TEST NUMBER: P331769-940

CATALOG NUMBER: S122RDIW-S290D710U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	123.8	73.1	48.1	48.5	49.0	49.4	49.8
115°	192.4	128.2	91.1	81.1	71.2	61.2	51.2
117.5°	380.0	364.4	340.3	307.5	274.6	241.8	209.0
120°	462.5	464.2	455.7	436.9	418.2	399.5	380.8
122.5°	490.0	491.1	489.7	486.1	482.4	478.8	475.2
125°	530.4	531.4	532.1	532.4	532.9	533.3	533.7
127.5°	568.2	569.6	570.3	570.4	570.5	570.6	570.7
130°	592.0	593.5	594.2	594.1	594.0	593.8	593.7
132.5°	614.8	616.1	616.7	616.5	616.4	616.3	616.2
135°	647.7	649.2	649.7	649.4	649.2	648.9	648.6
137.5°	678.2	679.7	680.1	679.6	679.1	678.7	678.1
140°	697.9	699.2	699.5	698.7	698.0	697.3	696.7
142.5°	716.0	717.2	717.4	716.8	716.0	715.3	714.6
145°	741.4	742.3	742.5	741.8	741.1	740.4	739.8
147.5°	763.4	764.1	764.2	763.6	763.0	762.4	761.8
150°	777.2	778.0	778.1	777.4	776.7	776.0	775.3
152.5°	789.7	790.5	790.5	789.5	788.6	787.7	786.8
155°	806.6	807.4	807.2	806.1	805.0	803.9	802.8
157.5°	820.8	821.8	821.7	820.6	819.6	818.5	817.3
160°	829.0	829.8	829.7	828.8	827.8	826.9	825.9
162.5°	836.8	837.8	837.7	836.4	835.3	834.0	832.9
165°	846.2	847.2	847.2	846.2	845.3	844.4	843.4
167.5°	854.2	855.1	855.0	853.7	852.5	851.2	850.0
170°	858.1	859.1	859.0	857.7	856.5	855.2	854.0
172.5°	861.1	862.1	861.9	860.7	859.4	858.2	856.9
175°	864.3	865.3	865.1	863.7	862.4	860.9	859.6
177.5°	864.5	865.3	865.2	864.2	863.2	862.2	861.2
180°	862.7	862.7	862.7	862.7	862.7	862.7	862.7

(END OF REPORT)