

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331770-940

Luminaire Tested: **S122RDIW-S290D710U940-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331770-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIW-S290D710U940-4F0-1E-UDD-A1  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 710 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3203.1 lumens  
Efficiency: N/A  
Efficacy: 105.4 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Indirect  
  
Input Watts (W): 30.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331770-940

CATALOG NUMBER: S122RDIW-S290D710U940-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P331770-940

CATALOG NUMBER: S122RDIW-S290D710U940-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39				32
1	94	90	86	83	85	81	78	75	65	63	61	49	48	47	35	35	34				27
2	86	79	74	69	77	72	67	63	57	54	51	44	42	40	32	30	29				24
3	79	70	63	58	71	63	58	53	51	47	44	39	37	34	29	27	26				21
4	72	62	55	49	65	56	50	45	46	41	37	35	32	30	26	24	23				18
5	67	56	48	42	60	51	44	39	41	36	33	32	29	26	24	22	20				16
6	61	50	42	37	55	46	39	34	37	32	29	29	26	23	22	20	18				15
7	57	45	38	33	51	41	35	30	34	29	25	27	23	21	20	18	16				13
8	53	41	34	29	48	38	31	27	31	26	23	24	21	19	18	16	15				12
9	49	38	31	26	44	34	28	24	28	24	20	23	19	17	17	15	13				11
10	46	35	28	23	41	32	26	22	26	22	18	21	18	15	16	14	12				10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	9411	9411	9411	9411
5°	10511	9470	8399	9470
10°	11663	9404	7279	9404
15°	12236	9267	5735	9267
20°	10608	9062	4962	9062
25°	6957	8783	4431	8783
30°	4683	8444	4010	8444
35°	3792	8016	3617	8016
40°	3372	7552	3347	7552
45°	3053	7005	2987	7005
50°	2778	6465	2768	6465
55°	2609	5866	2578	5866
60°	2186	5318	2160	5318
65°	1841	4829	2090	4829
70°	1699	4310	1969	4310
75°	1591	3755	1822	3755
80°	1469	3096	1618	3096
85°	1352	2445	1426	2445



TEST NUMBER: P331770-940

CATALOG NUMBER: S122RDIW-S290D710U940-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	55.3	1.7
10°-20°	154.0	4.8
20°-30°	198.4	6.2
30°-40°	188.6	5.9
40°-50°	161.5	5.0
50°-60°	123.0	3.8
60°-70°	77.8	2.4
70°-80°	38.8	1.2
80°-90°	13.2	0.4
90°-100°	49.7	1.6
100°-110°	154.3	4.8
110°-120°	263.8	8.2
120°-130°	346.9	10.8
130°-140°	389.3	12.2
140°-150°	381.7	11.9
150°-160°	320.2	10.0
160°-170°	212.4	6.6
170°-180°	74.2	2.3
0°-30°	407.7	12.7
0°-40°	596.2	18.6
0°-60°	880.8	27.5
0°-90°	1010.6	31.6
90°-120°	467.8	14.6
90°-150°	1585.7	49.5
90°-180°	2193.0	68.5
0°-180°	3203.1	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	583	583	583	583	583	
5°	648	584	518	584	648	64
15°	732	554	343	554	732	197
25°	390	493	249	493	390	185
35°	192	407	184	407	192	123
45°	134	307	131	307	134	103
55°	93	208	92	208	93	81
65°	48	126	55	126	48	49
75°	26	60	29	60	26	27
85°	7	13	8	13	7	8
90°	22	1	22	1	22	10
95°	41	34	41	34	41	46
105°	147	142	147	142	147	155
115°	265	265	265	265	265	261
125°	386	385	386	385	386	345
135°	504	498	504	498	504	388
145°	611	605	611	605	611	382
155°	697	691	697	691	697	321
165°	753	752	753	752	753	212
175°	780	783	780	783	780	74
180°	784	784	784	784	784	



TEST NUMBER: P331770-940

CATALOG NUMBER: S122RDIW-S290D710U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9
2.5°	606.6	607.1	607.6	606.5	606.5	605.5	603.3	601.7	597.2	596.6	596.6
5°	648.5	648.2	649.0	646.3	642.7	641.9	638.0	632.9	627.7	621.9	620.6
7.5°	690.3	689.6	688.0	687.6	684.8	678.7	672.5	665.9	657.2	648.6	644.4
10°	711.4	718.1	714.0	706.9	708.3	698.8	693.8	685.0	677.7	664.9	662.2
12.5°	732.1	734.8	733.4	729.4	727.6	721.0	714.2	706.6	693.1	681.7	671.7
15°	732.0	735.8	736.9	735.7	736.6	736.3	732.6	726.4	714.6	702.0	691.1
17.5°	678.0	680.6	687.3	691.8	697.5	709.4	715.4	717.6	716.0	708.7	701.1
20°	617.4	613.0	631.6	641.1	649.2	669.4	686.9	693.6	704.3	704.1	702.0
22.5°	531.5	532.5	550.2	561.5	585.1	605.5	625.3	650.4	671.2	684.9	692.9
25°	390.5	398.2	415.8	431.2	457.5	495.3	529.5	569.2	606.6	636.2	664.4
27.5°	293.3	293.9	307.8	322.1	337.7	368.5	411.7	459.1	512.5	556.6	607.3
30°	251.2	249.9	255.8	264.6	277.9	301.8	334.2	380.8	434.1	500.5	559.6
32.5°	221.3	221.4	225.9	232.3	243.3	259.5	281.7	319.6	369.9	435.2	504.5
35°	192.4	192.3	195.5	200.1	204.7	215.1	230.3	250.1	284.8	345.7	416.6
37.5°	171.7	172.5	174.2	177.1	182.2	188.0	197.1	210.4	235.1	271.2	330.7
40°	160.0	160.4	162.6	165.1	168.1	172.5	180.0	190.8	208.8	237.6	281.2
42.5°	149.4	149.7	151.3	153.6	156.0	160.4	166.7	175.9	190.6	212.9	248.9
45°	133.7	133.7	135.1	136.1	138.8	142.8	147.8	155.6	165.7	182.3	206.2
47.5°	119.0	119.0	120.0	121.7	123.4	126.5	131.5	137.9	145.2	158.0	178.4
50°	110.6	110.8	111.4	112.8	113.9	116.6	120.6	126.0	133.7	143.7	160.6
52.5°	103.8	103.7	104.4	105.0	105.8	107.7	110.7	115.5	122.3	131.0	145.1
55°	92.7	91.9	93.2	94.2	94.8	95.6	97.2	100.2	106.1	113.4	123.9
57.5°	79.0	78.6	79.5	80.4	82.4	84.5	86.0	87.8	90.9	96.1	106.6
60°	67.7	67.7	69.5	70.1	72.3	75.2	78.0	79.6	82.7	86.1	93.8
62.5°	57.6	57.8	58.6	59.2	60.5	63.9	67.9	71.5	74.4	77.7	82.8
65°	48.2	48.6	48.6	49.0	49.8	50.6	52.3	55.1	60.2	64.8	68.7
67.5°	40.9	41.0	41.2	41.6	41.7	42.6	43.3	44.6	45.7	50.1	54.9
70°	36.0	36.6	36.5	36.8	37.1	37.5	38.3	38.9	40.8	41.7	44.6
72.5°	31.5	31.9	31.9	32.2	32.7	32.8	33.4	34.1	35.2	36.0	37.6
75°	25.5	25.3	25.5	25.9	26.1	26.3	26.3	27.1	27.7	28.5	29.6
77.5°	19.7	19.9	19.9	19.9	20.0	20.3	20.2	20.6	21.2	21.7	22.1
80°	15.8	16.0	15.8	16.0	16.2	16.4	16.2	16.4	17.0	17.4	17.4
82.5°	12.2	12.3	12.4	12.4	12.5	12.5	12.8	12.8	13.3	13.2	13.4
85°	7.3	7.1	7.1	7.1	7.3	7.5	7.3	7.3	7.5	7.5	7.5
87.5°	7.1	7.2	7.2	7.1	7.1	7.1	7.2	7.4	7.3	7.6	6.8
90°	22.5	22.4	22.2	22.0	21.9	22.0	22.3	22.6	22.8	23.2	19.9
92.5°	21.4	21.4	21.4	21.3	21.3	21.3	21.2	21.1	21.1	21.0	20.2
95°	41.0	41.3	41.6	41.9	42.2	42.4	42.4	42.4	42.4	42.4	42.1
97.5°	71.1	71.1	71.2	71.2	71.2	71.2	71.2	71.2	71.2	71.2	70.6
100°	90.7	90.8	91.0	91.1	91.2	91.3	91.3	91.3	91.3	91.3	90.9
102.5°	112.9	113.1	113.2	113.3	113.5	113.5	113.3	113.2	113.2	113.0	112.4
105°	146.9	146.9	146.9	146.9	146.9	146.8	146.4	146.2	145.9	145.6	145.3
107.5°	179.0	179.6	180.3	180.9	181.6	181.9	181.8	181.6	181.6	181.5	181.5
110°	203.8	204.2	204.6	205.1	205.5	205.8	205.8	205.8	205.8	205.8	205.8



TEST NUMBER: P331770-940

CATALOG NUMBER: S122RDIW-S290D710U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	227.7	227.9	228.3	228.6	228.9	229.3	229.6	230.0	230.3	230.7	230.8
115°	264.7	265.1	265.6	266.0	266.4	266.7	266.9	267.1	267.2	267.3	267.6
117.5°	300.0	300.4	300.9	301.3	301.8	302.2	302.6	302.9	303.3	303.6	304.4
120°	324.9	325.3	325.7	326.2	326.6	326.9	326.9	326.9	326.9	326.9	328.1
122.5°	349.3	349.6	349.9	350.2	350.5	350.9	351.2	351.6	352.0	352.3	353.1
125°	386.5	386.6	386.7	386.9	387.0	387.3	387.7	388.2	388.6	389.1	389.5
127.5°	420.4	420.8	421.2	421.7	422.2	422.7	423.2	423.7	424.3	424.8	425.3
130°	444.7	445.2	445.9	446.4	447.0	447.5	447.7	448.1	448.4	448.6	448.9
132.5°	468.0	468.4	468.9	469.4	469.8	470.4	471.0	471.7	472.3	473.0	473.0
135°	504.2	504.6	505.1	505.5	506.0	506.3	506.4	506.6	506.7	506.8	506.6
137.5°	537.0	537.6	538.2	538.8	539.4	539.8	539.8	539.9	540.1	540.2	539.8
140°	559.8	560.4	561.0	561.6	562.1	562.4	562.4	562.4	562.4	562.4	561.7
142.5°	580.4	581.0	581.6	582.2	582.8	583.0	582.9	582.8	582.6	582.6	582.0
145°	611.4	612.0	612.6	613.1	613.8	613.9	613.9	613.7	613.5	613.4	612.5
147.5°	639.1	639.6	640.2	640.8	641.3	641.4	641.1	640.8	640.4	640.2	639.5
150°	657.1	657.5	657.9	658.4	658.8	658.8	658.4	657.9	657.5	657.1	656.5
152.5°	674.0	674.6	675.1	675.6	676.3	676.3	675.6	675.1	674.6	674.0	673.3
155°	696.8	697.2	697.7	698.1	698.6	698.4	697.7	696.9	696.2	695.4	695.0
157.5°	716.3	717.0	717.7	718.5	719.2	719.0	718.0	717.0	716.0	715.1	714.8
160°	728.5	729.2	729.7	730.3	730.8	730.8	729.9	729.0	728.1	727.2	727.0
162.5°	739.1	739.9	740.6	741.2	741.9	741.8	740.8	739.8	738.8	737.8	737.6
165°	753.0	753.8	754.5	755.2	756.0	755.8	754.7	753.8	752.7	751.7	751.7
167.5°	764.4	765.2	765.9	766.7	767.4	767.3	766.2	765.3	764.2	763.2	763.2
170°	770.2	771.1	772.0	772.8	773.7	773.6	772.7	771.6	770.6	769.5	769.7
172.5°	775.0	775.9	776.8	777.7	778.5	778.5	777.4	776.4	775.3	774.3	774.5
175°	780.2	781.0	781.9	782.7	783.6	783.6	782.6	781.5	780.5	779.4	779.8
177.5°	782.5	783.2	783.9	784.6	785.3	785.3	784.6	783.9	783.2	782.5	782.7
180°	784.1	784.1	784.1	784.1	784.1	784.1	784.1	784.1	784.1	784.1	784.1



TEST NUMBER: P331770-940

CATALOG NUMBER: S122RDIW-S290D710U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9
2.5°	596.9	595.6	594.4	591.6	590.0	586.8	586.4	586.2	582.0	577.9	576.8
5°	617.4	614.1	609.3	603.6	597.7	591.7	587.6	584.3	576.2	568.6	564.1
7.5°	638.0	631.1	622.7	612.0	603.0	593.0	585.5	578.8	567.3	556.2	548.8
10°	653.4	642.1	631.0	616.2	604.6	593.3	582.7	573.6	560.7	546.1	535.7
12.5°	663.0	650.5	635.2	620.7	605.7	591.3	577.2	565.5	550.3	535.2	523.0
15°	675.9	662.5	643.9	623.2	604.0	585.1	569.0	554.4	534.6	516.5	501.5
17.5°	686.5	668.1	648.1	624.2	601.9	578.0	557.1	538.5	516.4	494.6	477.0
20°	689.9	671.6	648.5	624.6	598.3	570.2	547.7	527.4	503.7	480.0	459.8
22.5°	687.8	673.6	647.9	619.3	592.4	562.9	537.5	514.0	487.7	463.5	440.1
25°	673.5	668.6	644.4	613.1	582.4	548.1	518.7	493.0	463.1	437.1	411.6
27.5°	640.2	650.7	635.6	602.4	568.1	531.5	498.4	469.1	438.0	408.8	383.4
30°	608.1	632.1	625.7	594.9	556.6	520.6	483.5	452.9	419.7	389.7	364.6
32.5°	564.2	604.0	610.3	584.5	544.9	505.3	466.5	436.0	401.4	369.8	345.3
35°	494.2	553.8	581.1	564.7	525.0	482.2	442.2	406.7	371.8	340.7	316.4
37.5°	410.8	492.0	537.5	538.7	502.2	457.8	414.1	378.9	343.2	312.6	286.3
40°	356.7	444.6	504.0	517.1	486.3	438.4	394.1	358.3	323.5	293.5	263.3
42.5°	308.1	395.7	468.6	491.5	467.1	419.4	375.1	337.6	303.7	275.4	244.5
45°	249.1	325.7	406.1	447.0	433.5	389.3	342.5	306.8	275.1	250.6	221.0
47.5°	210.2	264.1	342.0	397.3	397.1	356.8	310.7	276.6	247.1	224.1	200.2
50°	188.0	235.0	300.8	363.6	368.8	335.0	291.2	257.4	229.9	205.8	186.5
52.5°	168.0	206.8	265.9	326.2	341.2	311.8	269.4	238.2	211.4	189.2	172.8
55°	142.0	172.0	217.0	273.2	296.0	275.3	237.6	208.4	186.7	168.1	153.9
57.5°	120.1	142.6	178.7	224.0	250.4	237.5	206.3	182.6	164.1	147.2	136.1
60°	106.4	124.8	155.3	193.2	222.4	213.3	186.7	164.7	148.9	134.3	123.8
62.5°	93.4	109.2	135.5	166.2	192.9	189.1	167.5	148.9	135.1	121.8	112.9
65°	75.2	86.7	107.2	131.3	152.8	154.5	138.9	126.4	114.0	103.5	95.6
67.5°	59.8	67.4	81.8	102.1	118.2	123.9	114.4	104.8	95.0	86.9	80.0
70°	50.5	56.5	67.1	83.5	98.3	104.3	98.8	91.3	82.8	76.2	70.3
72.5°	40.8	46.8	54.6	66.6	79.3	85.9	83.9	78.6	71.7	66.1	60.5
75°	30.8	32.6	37.9	46.0	55.9	61.6	63.0	60.2	54.7	50.5	47.2
77.5°	22.7	23.9	26.4	30.6	37.1	42.2	44.2	43.9	40.1	37.7	34.6
80°	18.2	18.8	20.1	21.8	26.8	31.8	33.3	33.3	30.6	29.6	26.6
82.5°	13.8	14.3	15.1	16.1	18.3	22.7	24.3	24.6	23.0	21.7	19.3
85°	7.9	7.7	8.1	8.7	9.1	10.3	12.8	13.2	12.8	11.1	10.5
87.5°	6.1	5.6	5.0	4.3	4.1	3.9	4.4	4.8	4.5	4.4	4.5
90°	16.7	13.5	10.3	7.8	6.0	4.2	2.4	0.6	2.4	4.2	6.0
92.5°	19.5	18.7	18.0	16.9	15.7	14.4	13.1	11.8	13.1	14.4	15.7
95°	41.7	41.5	41.2	40.3	38.8	37.4	35.8	34.4	35.8	37.4	38.8
97.5°	70.1	69.6	68.9	68.0	66.7	65.5	64.1	62.9	64.1	65.5	66.7
100°	90.4	90.0	89.5	88.7	87.6	86.4	85.2	84.0	85.2	86.4	87.6
102.5°	111.9	111.4	110.8	110.0	109.1	108.2	107.2	106.3	107.2	108.2	109.1
105°	145.0	144.7	144.4	144.0	143.6	143.1	142.7	142.2	142.7	143.1	143.6
107.5°	181.5	181.5	181.5	181.1	180.5	179.9	179.1	178.5	179.1	179.9	180.5
110°	205.8	205.8	205.8	205.4	204.5	203.6	202.7	201.8	202.7	203.6	204.5





TEST NUMBER: P331770-940

CATALOG NUMBER: S122RDIW-S290D710U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	230.9	231.0	231.1	230.8	229.9	229.0	228.1	227.2	228.1	229.0	229.9
115°	267.9	268.2	268.5	268.2	267.3	266.4	265.6	264.7	265.6	266.4	267.3
117.5°	305.2	306.0	306.8	306.7	305.5	304.3	303.2	302.0	303.2	304.3	305.5
120°	329.2	330.4	331.5	331.5	330.4	329.2	328.1	326.9	328.1	329.2	330.4
122.5°	353.9	354.7	355.6	355.3	353.8	352.5	351.1	349.6	351.1	352.5	353.8
125°	389.9	390.4	390.8	390.4	389.1	387.7	386.5	385.1	386.5	387.7	389.1
127.5°	425.9	426.4	427.0	426.3	424.6	423.0	421.3	419.6	421.3	423.0	424.6
130°	449.2	449.5	449.8	449.0	447.1	445.1	443.3	441.3	443.3	445.1	447.1
132.5°	472.9	472.8	472.8	471.9	470.4	468.9	467.3	465.7	467.3	468.9	470.4
135°	506.3	506.0	505.7	504.7	503.1	501.5	499.9	498.3	499.9	501.5	503.1
137.5°	539.5	539.0	538.7	537.8	536.5	535.2	533.9	532.5	533.9	535.2	536.5
140°	561.0	560.3	559.5	558.5	557.1	555.8	554.5	553.2	554.5	555.8	557.1
142.5°	581.6	581.0	580.6	579.6	578.4	577.0	575.7	574.4	575.7	577.0	578.4
145°	611.6	610.7	609.8	608.9	607.9	606.8	605.8	604.8	605.8	606.8	607.9
147.5°	638.9	638.4	637.8	636.9	635.6	634.4	633.1	632.0	633.1	634.4	635.6
150°	655.9	655.3	654.7	654.0	653.1	652.2	651.3	650.4	651.3	652.2	653.1
152.5°	672.6	671.9	671.2	670.4	669.5	668.6	667.7	666.8	667.7	668.6	669.5
155°	694.6	694.1	693.7	693.2	692.8	692.3	691.9	691.4	691.9	692.3	692.8
157.5°	714.5	714.3	714.0	713.7	713.4	713.1	712.8	712.5	712.8	713.1	713.4
160°	726.9	726.7	726.7	726.4	726.1	725.8	725.5	725.2	725.5	725.8	726.1
162.5°	737.5	737.4	737.2	737.1	737.0	737.0	736.9	736.8	736.9	737.0	737.0
165°	751.7	751.7	751.7	751.8	751.9	752.1	752.2	752.3	752.2	752.1	751.9
167.5°	763.2	763.3	763.3	763.6	764.0	764.5	764.9	765.4	764.9	764.5	764.0
170°	769.8	770.0	770.2	770.4	770.9	771.3	771.8	772.2	771.8	771.3	770.9
172.5°	774.6	774.7	774.9	775.2	775.6	776.1	776.5	776.9	776.5	776.1	775.6
175°	780.1	780.3	780.7	781.0	781.5	781.9	782.4	782.7	782.4	781.9	781.5
177.5°	783.0	783.2	783.5	783.7	784.1	784.4	784.8	785.2	784.8	784.4	784.1
180°	784.1	784.1	784.1	784.1	784.1	784.1	784.1	784.1	784.1	784.1	784.1



TEST NUMBER: P331770-940

CATALOG NUMBER: S122RDIW-S290D710U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9
2.5°	574.7	573.5	571.4	568.2	566.2	562.8	560.6	561.9	562.2	561.9	561.6
5°	559.3	555.0	549.1	543.4	538.1	532.5	529.2	527.9	525.0	523.4	522.5
7.5°	540.6	533.2	525.0	515.1	506.7	497.8	493.4	491.2	485.4	482.2	479.5
10°	526.6	515.1	506.8	493.8	485.9	474.4	466.5	466.7	458.8	454.3	451.1
12.5°	511.2	498.6	484.7	473.1	462.1	452.8	443.3	439.4	431.1	426.8	418.0
15°	485.7	470.9	456.4	440.6	429.4	415.0	401.3	384.4	370.9	359.1	355.9
17.5°	457.9	439.5	424.9	406.4	387.3	363.1	347.1	337.3	329.2	323.0	318.3
20°	438.7	420.1	404.5	376.6	350.8	334.4	322.7	315.1	306.7	300.0	296.3
22.5°	418.7	399.2	377.9	346.7	326.6	313.5	303.1	294.4	288.6	283.5	280.1
25°	390.1	368.8	333.8	312.4	296.1	282.3	275.1	269.8	263.8	256.6	253.4
27.5°	360.0	326.2	301.0	285.0	269.6	260.6	254.0	246.2	240.8	237.6	234.2
30°	337.4	303.6	284.0	266.5	255.7	245.7	238.0	233.5	228.3	222.8	220.6
32.5°	312.4	285.3	266.4	252.0	240.9	232.4	226.3	219.1	215.3	212.0	207.3
35°	281.2	260.6	243.4	231.8	221.1	214.3	207.2	203.0	196.1	193.2	191.5
37.5°	254.8	237.0	224.2	211.8	203.4	195.8	191.5	184.7	181.7	177.7	173.9
40°	239.8	222.4	210.1	199.9	190.6	184.9	179.5	174.0	169.5	167.7	163.1
42.5°	224.6	210.4	198.0	187.0	180.7	174.7	167.8	163.8	159.2	156.2	153.4
45°	203.6	191.0	180.5	171.4	164.4	158.2	153.7	147.0	144.5	138.6	136.1
47.5°	185.1	173.4	163.4	154.7	148.0	143.9	137.4	132.2	128.0	124.3	121.2
50°	172.0	162.2	152.5	144.8	138.8	132.9	126.2	123.6	117.1	115.2	113.4
52.5°	160.0	150.7	141.9	134.3	128.2	122.5	116.6	113.2	108.8	107.0	105.7
55°	143.2	134.3	125.8	119.1	113.1	107.2	103.5	99.2	97.2	95.8	94.2
57.5°	126.4	118.3	111.8	105.0	98.9	94.3	90.1	87.5	85.4	83.6	81.6
60°	115.7	108.0	102.1	95.8	89.5	85.7	82.5	79.4	77.0	74.1	73.3
62.5°	104.3	97.6	92.2	86.1	80.6	77.1	74.0	71.2	68.2	64.1	63.0
65°	88.7	83.5	77.8	72.7	67.9	64.4	59.9	56.7	55.5	55.1	54.9
67.5°	74.6	69.6	64.7	59.6	55.2	52.0	49.7	49.2	48.3	48.2	47.5
70°	65.2	60.5	55.7	50.8	46.5	46.0	45.2	44.3	43.3	43.0	42.5
72.5°	56.8	52.0	47.1	43.2	41.4	40.7	39.9	39.0	38.3	37.9	37.7
75°	43.5	39.1	35.8	34.4	33.4	32.8	31.6	31.0	30.6	30.0	29.8
77.5°	31.4	28.8	27.4	26.5	25.4	24.8	24.1	23.5	23.0	22.9	22.6
80°	23.9	22.6	21.7	20.4	20.1	19.3	19.1	18.5	18.6	18.0	18.0
82.5°	18.5	17.0	16.1	15.6	15.2	14.5	14.4	14.1	14.1	13.6	13.6
85°	9.5	9.1	8.7	8.3	8.3	7.7	7.9	7.7	7.7	7.3	7.1
87.5°	4.6	5.0	5.3	6.0	6.6	7.0	7.0	6.8	6.7	6.7	6.5
90°	7.8	10.3	13.5	16.7	19.9	23.2	22.8	22.6	22.3	22.0	21.9
92.5°	16.9	18.0	18.7	19.5	20.2	21.0	21.1	21.1	21.2	21.3	21.3
95°	40.3	41.2	41.5	41.7	42.1	42.4	42.4	42.4	42.4	42.4	42.2
97.5°	68.0	68.9	69.6	70.1	70.6	71.2	71.2	71.2	71.2	71.2	71.2
100°	88.7	89.5	90.0	90.4	90.9	91.3	91.3	91.3	91.3	91.3	91.2
102.5°	110.0	110.8	111.4	111.9	112.4	113.0	113.2	113.2	113.3	113.5	113.5
105°	144.0	144.4	144.7	145.0	145.3	145.6	145.9	146.2	146.4	146.8	146.9
107.5°	181.1	181.5	181.5	181.5	181.5	181.5	181.6	181.6	181.8	181.9	181.6
110°	205.4	205.8	205.8	205.8	205.8	205.8	205.8	205.8	205.8	205.8	205.5



TEST NUMBER: P331770-940

CATALOG NUMBER: S122RDIW-S290D710U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	230.8	231.1	231.0	230.9	230.8	230.7	230.3	230.0	229.6	229.3	228.9
115°	268.2	268.5	268.2	267.9	267.6	267.3	267.2	267.1	266.9	266.7	266.4
117.5°	306.7	306.8	306.0	305.2	304.4	303.6	303.3	302.9	302.6	302.2	301.8
120°	331.5	331.5	330.4	329.2	328.1	326.9	326.9	326.9	326.9	326.9	326.6
122.5°	355.3	355.6	354.7	353.9	353.1	352.3	352.0	351.6	351.2	350.9	350.5
125°	390.4	390.8	390.4	389.9	389.5	389.1	388.6	388.2	387.7	387.3	387.0
127.5°	426.3	427.0	426.4	425.9	425.3	424.8	424.3	423.7	423.2	422.7	422.2
130°	449.0	449.8	449.5	449.2	448.9	448.6	448.4	448.1	447.7	447.5	447.0
132.5°	471.9	472.8	472.8	472.9	473.0	473.0	472.3	471.7	471.0	470.4	469.8
135°	504.7	505.7	506.0	506.3	506.6	506.8	506.7	506.6	506.4	506.3	506.0
137.5°	537.8	538.7	539.0	539.5	539.8	540.2	540.1	539.9	539.8	539.8	539.4
140°	558.5	559.5	560.3	561.0	561.7	562.4	562.4	562.4	562.4	562.4	562.1
142.5°	579.6	580.6	581.0	581.6	582.0	582.6	582.6	582.8	582.9	583.0	582.8
145°	608.9	609.8	610.7	611.6	612.5	613.4	613.5	613.7	613.9	613.9	613.8
147.5°	636.9	637.8	638.4	638.9	639.5	640.2	640.4	640.8	641.1	641.4	641.3
150°	654.0	654.7	655.3	655.9	656.5	657.1	657.5	657.9	658.4	658.8	658.8
152.5°	670.4	671.2	671.9	672.6	673.3	674.0	674.6	675.1	675.6	676.3	676.3
155°	693.2	693.7	694.1	694.6	695.0	695.4	696.2	696.9	697.7	698.4	698.6
157.5°	713.7	714.0	714.3	714.5	714.8	715.1	716.0	717.0	718.0	719.0	719.2
160°	726.4	726.7	726.7	726.9	727.0	727.2	728.1	729.0	729.9	730.8	730.8
162.5°	737.1	737.2	737.4	737.5	737.6	737.8	738.8	739.8	740.8	741.8	741.9
165°	751.8	751.7	751.7	751.7	751.7	751.7	752.7	753.8	754.7	755.8	756.0
167.5°	763.6	763.3	763.3	763.2	763.2	763.2	764.2	765.3	766.2	767.3	767.4
170°	770.4	770.2	770.0	769.8	769.7	769.5	770.6	771.6	772.7	773.6	773.7
172.5°	775.2	774.9	774.7	774.6	774.5	774.3	775.3	776.4	777.4	778.5	778.5
175°	781.0	780.7	780.3	780.1	779.8	779.4	780.5	781.5	782.6	783.6	783.6
177.5°	783.7	783.5	783.2	783.0	782.7	782.5	783.2	783.9	784.6	785.3	785.3
180°	784.1	784.1	784.1	784.1	784.1	784.1	784.1	784.1	784.1	784.1	784.1



TEST NUMBER: P331770-940

CATALOG NUMBER: S122RDIW-S290D710U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9
2.5°	559.8	560.1	559.6	559.9	559.6	560.1	559.8	561.6	561.9	562.2	561.9
5°	521.6	519.2	518.7	518.2	518.7	519.2	521.6	522.5	523.4	525.0	527.9
7.5°	476.0	475.6	474.6	473.1	474.6	475.6	476.0	479.5	482.2	485.4	491.2
10°	446.7	445.6	445.4	444.0	445.4	445.6	446.7	451.1	454.3	458.8	466.7
12.5°	412.2	405.7	405.1	401.5	405.1	405.7	412.2	418.0	426.8	431.1	439.4
15°	351.1	349.8	345.7	343.1	345.7	349.8	351.1	355.9	359.1	370.9	384.4
17.5°	316.0	312.0	310.8	310.2	310.8	312.0	316.0	318.3	323.0	329.2	337.3
20°	293.5	289.9	289.3	288.8	289.3	289.9	293.5	296.3	300.0	306.7	315.1
22.5°	277.9	274.1	272.6	271.3	272.6	274.1	277.9	280.1	283.5	288.6	294.4
25°	251.4	249.9	249.1	248.7	249.1	249.9	251.4	253.4	256.6	263.8	269.8
27.5°	230.6	227.5	226.9	225.8	226.9	227.5	230.6	234.2	237.6	240.8	246.2
30°	218.7	217.8	216.3	215.1	216.3	217.8	218.7	220.6	222.8	228.3	233.5
32.5°	204.8	203.9	202.7	202.2	202.7	203.9	204.8	207.3	212.0	215.3	219.1
35°	189.4	186.5	185.3	183.5	185.3	186.5	189.4	191.5	193.2	196.1	203.0
37.5°	173.1	171.6	169.9	170.5	169.9	171.6	173.1	173.9	177.7	181.7	184.7
40°	160.4	159.4	159.0	158.8	159.0	159.4	160.4	163.1	167.7	169.5	174.0
42.5°	150.3	147.6	146.5	146.5	146.5	147.6	150.3	153.4	156.2	159.2	163.8
45°	135.1	132.5	130.6	130.8	130.6	132.5	135.1	136.1	138.6	144.5	147.0
47.5°	119.5	119.4	118.2	118.6	118.2	119.4	119.5	121.2	124.3	128.0	132.2
50°	112.0	110.8	109.9	110.2	109.9	110.8	112.0	113.4	115.2	117.1	123.6
52.5°	104.9	103.8	103.2	104.1	103.2	103.8	104.9	105.7	107.0	108.8	113.2
55°	93.2	91.9	91.8	91.6	91.8	91.9	93.2	94.2	95.8	97.2	99.2
57.5°	80.1	79.3	78.0	77.6	78.0	79.3	80.1	81.6	83.6	85.4	87.5
60°	70.7	69.1	67.1	66.9	67.1	69.1	70.7	73.3	74.1	77.0	79.4
62.5°	62.1	61.8	61.3	61.3	61.3	61.8	62.1	63.0	64.1	68.2	71.2
65°	54.5	54.3	54.5	54.7	54.5	54.3	54.5	54.9	55.1	55.5	56.7
67.5°	47.4	47.1	46.7	46.9	46.7	47.1	47.4	47.5	48.2	48.3	49.2
70°	42.1	41.9	41.7	41.7	41.7	41.9	42.1	42.5	43.0	43.3	44.3
72.5°	36.9	36.9	36.7	36.6	36.7	36.9	36.9	37.7	37.9	38.3	39.0
75°	29.6	29.2	29.2	29.2	29.2	29.2	29.6	29.8	30.0	30.6	31.0
77.5°	22.6	22.3	22.1	21.9	22.1	22.3	22.6	22.6	22.9	23.0	23.5
80°	17.8	17.7	17.4	17.4	17.4	17.7	17.8	18.0	18.0	18.6	18.5
82.5°	13.6	13.4	13.4	13.2	13.4	13.4	13.6	13.6	13.6	14.1	14.1
85°	7.3	7.5	7.3	7.7	7.3	7.5	7.3	7.1	7.3	7.7	7.7
87.5°	6.5	6.4	6.6	6.4	6.6	6.4	6.5	6.5	6.7	6.7	6.8
90°	22.0	22.2	22.4	22.5	22.4	22.2	22.0	21.9	22.0	22.3	22.6
92.5°	21.3	21.4	21.4	21.4	21.4	21.4	21.3	21.3	21.3	21.2	21.1
95°	41.9	41.6	41.3	41.0	41.3	41.6	41.9	42.2	42.4	42.4	42.4
97.5°	71.2	71.2	71.1	71.1	71.1	71.2	71.2	71.2	71.2	71.2	71.2
100°	91.1	91.0	90.8	90.7	90.8	91.0	91.1	91.2	91.3	91.3	91.3
102.5°	113.3	113.2	113.1	112.9	113.1	113.2	113.3	113.5	113.5	113.3	113.2
105°	146.9	146.9	146.9	146.9	146.9	146.9	146.9	146.9	146.8	146.4	146.2
107.5°	180.9	180.3	179.6	179.0	179.6	180.3	180.9	181.6	181.9	181.8	181.6
110°	205.1	204.6	204.2	203.8	204.2	204.6	205.1	205.5	205.8	205.8	205.8



TEST NUMBER: P331770-940

CATALOG NUMBER: S122RDIW-S290D710U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	228.6	228.3	227.9	227.7	227.9	228.3	228.6	228.9	229.3	229.6	230.0
115°	266.0	265.6	265.1	264.7	265.1	265.6	266.0	266.4	266.7	266.9	267.1
117.5°	301.3	300.9	300.4	300.0	300.4	300.9	301.3	301.8	302.2	302.6	302.9
120°	326.2	325.7	325.3	324.9	325.3	325.7	326.2	326.6	326.9	326.9	326.9
122.5°	350.2	349.9	349.6	349.3	349.6	349.9	350.2	350.5	350.9	351.2	351.6
125°	386.9	386.7	386.6	386.5	386.6	386.7	386.9	387.0	387.3	387.7	388.2
127.5°	421.7	421.2	420.8	420.4	420.8	421.2	421.7	422.2	422.7	423.2	423.7
130°	446.4	445.9	445.2	444.7	445.2	445.9	446.4	447.0	447.5	447.7	448.1
132.5°	469.4	468.9	468.4	468.0	468.4	468.9	469.4	469.8	470.4	471.0	471.7
135°	505.5	505.1	504.6	504.2	504.6	505.1	505.5	506.0	506.3	506.4	506.6
137.5°	538.8	538.2	537.6	537.0	537.6	538.2	538.8	539.4	539.8	539.8	539.9
140°	561.6	561.0	560.4	559.8	560.4	561.0	561.6	562.1	562.4	562.4	562.4
142.5°	582.2	581.6	581.0	580.4	581.0	581.6	582.2	582.8	583.0	582.9	582.8
145°	613.1	612.6	612.0	611.4	612.0	612.6	613.1	613.8	613.9	613.9	613.7
147.5°	640.8	640.2	639.6	639.1	639.6	640.2	640.8	641.3	641.4	641.1	640.8
150°	658.4	657.9	657.5	657.1	657.5	657.9	658.4	658.8	658.8	658.4	657.9
152.5°	675.6	675.1	674.6	674.0	674.6	675.1	675.6	676.3	676.3	675.6	675.1
155°	698.1	697.7	697.2	696.8	697.2	697.7	698.1	698.6	698.4	697.7	696.9
157.5°	718.5	717.7	717.0	716.3	717.0	717.7	718.5	719.2	719.0	718.0	717.0
160°	730.3	729.7	729.2	728.5	729.2	729.7	730.3	730.8	730.8	729.9	729.0
162.5°	741.2	740.6	739.9	739.1	739.9	740.6	741.2	741.9	741.8	740.8	739.8
165°	755.2	754.5	753.8	753.0	753.8	754.5	755.2	756.0	755.8	754.7	753.8
167.5°	766.7	765.9	765.2	764.4	765.2	765.9	766.7	767.4	767.3	766.2	765.3
170°	772.8	772.0	771.1	770.2	771.1	772.0	772.8	773.7	773.6	772.7	771.6
172.5°	777.7	776.8	775.9	775.0	775.9	776.8	777.7	778.5	778.5	777.4	776.4
175°	782.7	781.9	781.0	780.2	781.0	781.9	782.7	783.6	783.6	782.6	781.5
177.5°	784.6	783.9	783.2	782.5	783.2	783.9	784.6	785.3	785.3	784.6	783.9
180°	784.1	784.1	784.1	784.1	784.1	784.1	784.1	784.1	784.1	784.1	784.1



TEST NUMBER: P331770-940

CATALOG NUMBER: S122RDIW-S290D710U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9
2.5°	560.6	562.8	566.2	568.2	571.4	573.5	574.7	576.8	577.9	582.0	586.2
5°	529.2	532.5	538.1	543.4	549.1	555.0	559.3	564.1	568.6	576.2	584.3
7.5°	493.4	497.8	506.7	515.1	525.0	533.2	540.6	548.8	556.2	567.3	578.8
10°	466.5	474.4	485.9	493.8	506.8	515.1	526.6	535.7	546.1	560.7	573.6
12.5°	443.3	452.8	462.1	473.1	484.7	498.6	511.2	523.0	535.2	550.3	565.5
15°	401.3	415.0	429.4	440.6	456.4	470.9	485.7	501.5	516.5	534.6	554.4
17.5°	347.1	363.1	387.3	406.4	424.9	439.5	457.9	477.0	494.6	516.4	538.5
20°	322.7	334.4	350.8	376.6	404.5	420.1	438.7	459.8	480.0	503.7	527.4
22.5°	303.1	313.5	326.6	346.7	377.9	399.2	418.7	440.1	463.5	487.7	514.0
25°	275.1	282.3	296.1	312.4	333.8	368.8	390.1	411.6	437.1	463.1	493.0
27.5°	254.0	260.6	269.6	285.0	301.0	326.2	360.0	383.4	408.8	438.0	469.1
30°	238.0	245.7	255.7	266.5	284.0	303.6	337.4	364.6	389.7	419.7	452.9
32.5°	226.3	232.4	240.9	252.0	266.4	285.3	312.4	345.3	369.8	401.4	436.0
35°	207.2	214.3	221.1	231.8	243.4	260.6	281.2	316.4	340.7	371.8	406.7
37.5°	191.5	195.8	203.4	211.8	224.2	237.0	254.8	286.3	312.6	343.2	378.9
40°	179.5	184.9	190.6	199.9	210.1	222.4	239.8	263.3	293.5	323.5	358.3
42.5°	167.8	174.7	180.7	187.0	198.0	210.4	224.6	244.5	275.4	303.7	337.6
45°	153.7	158.2	164.4	171.4	180.5	191.0	203.6	221.0	250.6	275.1	306.8
47.5°	137.4	143.9	148.0	154.7	163.4	173.4	185.1	200.2	224.1	247.1	276.6
50°	126.2	132.9	138.8	144.8	152.5	162.2	172.0	186.5	205.8	229.9	257.4
52.5°	116.6	122.5	128.2	134.3	141.9	150.7	160.0	172.8	189.2	211.4	238.2
55°	103.5	107.2	113.1	119.1	125.8	134.3	143.2	153.9	168.1	186.7	208.4
57.5°	90.1	94.3	98.9	105.0	111.8	118.3	126.4	136.1	147.2	164.1	182.6
60°	82.5	85.7	89.5	95.8	102.1	108.0	115.7	123.8	134.3	148.9	164.7
62.5°	74.0	77.1	80.6	86.1	92.2	97.6	104.3	112.9	121.8	135.1	148.9
65°	59.9	64.4	67.9	72.7	77.8	83.5	88.7	95.6	103.5	114.0	126.4
67.5°	49.7	52.0	55.2	59.6	64.7	69.6	74.6	80.0	86.9	95.0	104.8
70°	45.2	46.0	46.5	50.8	55.7	60.5	65.2	70.3	76.2	82.8	91.3
72.5°	39.9	40.7	41.4	43.2	47.1	52.0	56.8	60.5	66.1	71.7	78.6
75°	31.6	32.8	33.4	34.4	35.8	39.1	43.5	47.2	50.5	54.7	60.2
77.5°	24.1	24.8	25.4	26.5	27.4	28.8	31.4	34.6	37.7	40.1	43.9
80°	19.1	19.3	20.1	20.4	21.7	22.6	23.9	26.6	29.6	30.6	33.3
82.5°	14.4	14.5	15.2	15.6	16.1	17.0	18.5	19.3	21.7	23.0	24.6
85°	7.9	7.7	8.3	8.3	8.7	9.1	9.5	10.5	11.1	12.8	13.2
87.5°	7.0	7.0	6.6	6.0	5.3	5.0	4.6	4.5	4.4	4.5	4.8
90°	22.8	23.2	19.9	16.7	13.5	10.3	7.8	6.0	4.2	2.4	0.6
92.5°	21.1	21.0	20.2	19.5	18.7	18.0	16.9	15.7	14.4	13.1	11.8
95°	42.4	42.4	42.1	41.7	41.5	41.2	40.3	38.8	37.4	35.8	34.4
97.5°	71.2	71.2	70.6	70.1	69.6	68.9	68.0	66.7	65.5	64.1	62.9
100°	91.3	91.3	90.9	90.4	90.0	89.5	88.7	87.6	86.4	85.2	84.0
102.5°	113.2	113.0	112.4	111.9	111.4	110.8	110.0	109.1	108.2	107.2	106.3
105°	145.9	145.6	145.3	145.0	144.7	144.4	144.0	143.6	143.1	142.7	142.2
107.5°	181.6	181.5	181.5	181.5	181.5	181.5	181.1	180.5	179.9	179.1	178.5
110°	205.8	205.8	205.8	205.8	205.8	205.8	205.4	204.5	203.6	202.7	201.8



TEST NUMBER: P331770-940

CATALOG NUMBER: S122RDIW-S290D710U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	230.3	230.7	230.8	230.9	231.0	231.1	230.8	229.9	229.0	228.1	227.2
115°	267.2	267.3	267.6	267.9	268.2	268.5	268.2	267.3	266.4	265.6	264.7
117.5°	303.3	303.6	304.4	305.2	306.0	306.8	306.7	305.5	304.3	303.2	302.0
120°	326.9	326.9	328.1	329.2	330.4	331.5	331.5	330.4	329.2	328.1	326.9
122.5°	352.0	352.3	353.1	353.9	354.7	355.6	355.3	353.8	352.5	351.1	349.6
125°	388.6	389.1	389.5	389.9	390.4	390.8	390.4	389.1	387.7	386.5	385.1
127.5°	424.3	424.8	425.3	425.9	426.4	427.0	426.3	424.6	423.0	421.3	419.6
130°	448.4	448.6	448.9	449.2	449.5	449.8	449.0	447.1	445.1	443.3	441.3
132.5°	472.3	473.0	473.0	472.9	472.8	472.8	471.9	470.4	468.9	467.3	465.7
135°	506.7	506.8	506.6	506.3	506.0	505.7	504.7	503.1	501.5	499.9	498.3
137.5°	540.1	540.2	539.8	539.5	539.0	538.7	537.8	536.5	535.2	533.9	532.5
140°	562.4	562.4	561.7	561.0	560.3	559.5	558.5	557.1	555.8	554.5	553.2
142.5°	582.6	582.6	582.0	581.6	581.0	580.6	579.6	578.4	577.0	575.7	574.4
145°	613.5	613.4	612.5	611.6	610.7	609.8	608.9	607.9	606.8	605.8	604.8
147.5°	640.4	640.2	639.5	638.9	638.4	637.8	636.9	635.6	634.4	633.1	632.0
150°	657.5	657.1	656.5	655.9	655.3	654.7	654.0	653.1	652.2	651.3	650.4
152.5°	674.6	674.0	673.3	672.6	671.9	671.2	670.4	669.5	668.6	667.7	666.8
155°	696.2	695.4	695.0	694.6	694.1	693.7	693.2	692.8	692.3	691.9	691.4
157.5°	716.0	715.1	714.8	714.5	714.3	714.0	713.7	713.4	713.1	712.8	712.5
160°	728.1	727.2	727.0	726.9	726.7	726.7	726.4	726.1	725.8	725.5	725.2
162.5°	738.8	737.8	737.6	737.5	737.4	737.2	737.1	737.0	737.0	736.9	736.8
165°	752.7	751.7	751.7	751.7	751.7	751.7	751.8	751.9	752.1	752.2	752.3
167.5°	764.2	763.2	763.2	763.2	763.3	763.3	763.6	764.0	764.5	764.9	765.4
170°	770.6	769.5	769.7	769.8	770.0	770.2	770.4	770.9	771.3	771.8	772.2
172.5°	775.3	774.3	774.5	774.6	774.7	774.9	775.2	775.6	776.1	776.5	776.9
175°	780.5	779.4	779.8	780.1	780.3	780.7	781.0	781.5	781.9	782.4	782.7
177.5°	783.2	782.5	782.7	783.0	783.2	783.5	783.7	784.1	784.4	784.8	785.2
180°	784.1	784.1	784.1	784.1	784.1	784.1	784.1	784.1	784.1	784.1	784.1



TEST NUMBER: P331770-940

CATALOG NUMBER: S122RDIW-S290D710U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9
2.5°	586.4	586.8	590.0	591.6	594.4	595.6	596.9	596.6	596.6	597.2	601.7
5°	587.6	591.7	597.7	603.6	609.3	614.1	617.4	620.6	621.9	627.7	632.9
7.5°	585.5	593.0	603.0	612.0	622.7	631.1	638.0	644.4	648.6	657.2	665.9
10°	582.7	593.3	604.6	616.2	631.0	642.1	653.4	662.2	664.9	677.7	685.0
12.5°	577.2	591.3	605.7	620.7	635.2	650.5	663.0	671.7	681.7	693.1	706.6
15°	569.0	585.1	604.0	623.2	643.9	662.5	675.9	691.1	702.0	714.6	726.4
17.5°	557.1	578.0	601.9	624.2	648.1	668.1	686.5	701.1	708.7	716.0	717.6
20°	547.7	570.2	598.3	624.6	648.5	671.6	689.9	702.0	704.1	704.3	693.6
22.5°	537.5	562.9	592.4	619.3	647.9	673.6	687.8	692.9	684.9	671.2	650.4
25°	518.7	548.1	582.4	613.1	644.4	668.6	673.5	664.4	636.2	606.6	569.2
27.5°	498.4	531.5	568.1	602.4	635.6	650.7	640.2	607.3	556.6	512.5	459.1
30°	483.5	520.6	556.6	594.9	625.7	632.1	608.1	559.6	500.5	434.1	380.8
32.5°	466.5	505.3	544.9	584.5	610.3	604.0	564.2	504.5	435.2	369.9	319.6
35°	442.2	482.2	525.0	564.7	581.1	553.8	494.2	416.6	345.7	284.8	250.1
37.5°	414.1	457.8	502.2	538.7	537.5	492.0	410.8	330.7	271.2	235.1	210.4
40°	394.1	438.4	486.3	517.1	504.0	444.6	356.7	281.2	237.6	208.8	190.8
42.5°	375.1	419.4	467.1	491.5	468.6	395.7	308.1	248.9	212.9	190.6	175.9
45°	342.5	389.3	433.5	447.0	406.1	325.7	249.1	206.2	182.3	165.7	155.6
47.5°	310.7	356.8	397.1	397.3	342.0	264.1	210.2	178.4	158.0	145.2	137.9
50°	291.2	335.0	368.8	363.6	300.8	235.0	188.0	160.6	143.7	133.7	126.0
52.5°	269.4	311.8	341.2	326.2	265.9	206.8	168.0	145.1	131.0	122.3	115.5
55°	237.6	275.3	296.0	273.2	217.0	172.0	142.0	123.9	113.4	106.1	100.2
57.5°	206.3	237.5	250.4	224.0	178.7	142.6	120.1	106.6	96.1	90.9	87.8
60°	186.7	213.3	222.4	193.2	155.3	124.8	106.4	93.8	86.1	82.7	79.6
62.5°	167.5	189.1	192.9	166.2	135.5	109.2	93.4	82.8	77.7	74.4	71.5
65°	138.9	154.5	152.8	131.3	107.2	86.7	75.2	68.7	64.8	60.2	55.1
67.5°	114.4	123.9	118.2	102.1	81.8	67.4	59.8	54.9	50.1	45.7	44.6
70°	98.8	104.3	98.3	83.5	67.1	56.5	50.5	44.6	41.7	40.8	38.9
72.5°	83.9	85.9	79.3	66.6	54.6	46.8	40.8	37.6	36.0	35.2	34.1
75°	63.0	61.6	55.9	46.0	37.9	32.6	30.8	29.6	28.5	27.7	27.1
77.5°	44.2	42.2	37.1	30.6	26.4	23.9	22.7	22.1	21.7	21.2	20.6
80°	33.3	31.8	26.8	21.8	20.1	18.8	18.2	17.4	17.4	17.0	16.4
82.5°	24.3	22.7	18.3	16.1	15.1	14.3	13.8	13.4	13.2	13.3	12.8
85°	12.8	10.3	9.1	8.7	8.1	7.7	7.9	7.5	7.5	7.5	7.3
87.5°	4.4	3.9	4.1	4.3	5.0	5.6	6.1	6.8	7.6	7.3	7.4
90°	2.4	4.2	6.0	7.8	10.3	13.5	16.7	19.9	23.2	22.8	22.6
92.5°	13.1	14.4	15.7	16.9	18.0	18.7	19.5	20.2	21.0	21.1	21.1
95°	35.8	37.4	38.8	40.3	41.2	41.5	41.7	42.1	42.4	42.4	42.4
97.5°	64.1	65.5	66.7	68.0	68.9	69.6	70.1	70.6	71.2	71.2	71.2
100°	85.2	86.4	87.6	88.7	89.5	90.0	90.4	90.9	91.3	91.3	91.3
102.5°	107.2	108.2	109.1	110.0	110.8	111.4	111.9	112.4	113.0	113.2	113.2
105°	142.7	143.1	143.6	144.0	144.4	144.7	145.0	145.3	145.6	145.9	146.2
107.5°	179.1	179.9	180.5	181.1	181.5	181.5	181.5	181.5	181.5	181.6	181.6
110°	202.7	203.6	204.5	205.4	205.8	205.8	205.8	205.8	205.8	205.8	205.8





TEST NUMBER: P331770-940

CATALOG NUMBER: S122RDIW-S290D710U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	228.1	229.0	229.9	230.8	231.1	231.0	230.9	230.8	230.7	230.3	230.0
115°	265.6	266.4	267.3	268.2	268.5	268.2	267.9	267.6	267.3	267.2	267.1
117.5°	303.2	304.3	305.5	306.7	306.8	306.0	305.2	304.4	303.6	303.3	302.9
120°	328.1	329.2	330.4	331.5	331.5	330.4	329.2	328.1	326.9	326.9	326.9
122.5°	351.1	352.5	353.8	355.3	355.6	354.7	353.9	353.1	352.3	352.0	351.6
125°	386.5	387.7	389.1	390.4	390.8	390.4	389.9	389.5	389.1	388.6	388.2
127.5°	421.3	423.0	424.6	426.3	427.0	426.4	425.9	425.3	424.8	424.3	423.7
130°	443.3	445.1	447.1	449.0	449.8	449.5	449.2	448.9	448.6	448.4	448.1
132.5°	467.3	468.9	470.4	471.9	472.8	472.8	472.9	473.0	473.0	472.3	471.7
135°	499.9	501.5	503.1	504.7	505.7	506.0	506.3	506.6	506.8	506.7	506.6
137.5°	533.9	535.2	536.5	537.8	538.7	539.0	539.5	539.8	540.2	540.1	539.9
140°	554.5	555.8	557.1	558.5	559.5	560.3	561.0	561.7	562.4	562.4	562.4
142.5°	575.7	577.0	578.4	579.6	580.6	581.0	581.6	582.0	582.6	582.6	582.8
145°	605.8	606.8	607.9	608.9	609.8	610.7	611.6	612.5	613.4	613.5	613.7
147.5°	633.1	634.4	635.6	636.9	637.8	638.4	638.9	639.5	640.2	640.4	640.8
150°	651.3	652.2	653.1	654.0	654.7	655.3	655.9	656.5	657.1	657.5	657.9
152.5°	667.7	668.6	669.5	670.4	671.2	671.9	672.6	673.3	674.0	674.6	675.1
155°	691.9	692.3	692.8	693.2	693.7	694.1	694.6	695.0	695.4	696.2	696.9
157.5°	712.8	713.1	713.4	713.7	714.0	714.3	714.5	714.8	715.1	716.0	717.0
160°	725.5	725.8	726.1	726.4	726.7	726.7	726.9	727.0	727.2	728.1	729.0
162.5°	736.9	737.0	737.0	737.1	737.2	737.4	737.5	737.6	737.8	738.8	739.8
165°	752.2	752.1	751.9	751.8	751.7	751.7	751.7	751.7	751.7	752.7	753.8
167.5°	764.9	764.5	764.0	763.6	763.3	763.3	763.2	763.2	763.2	764.2	765.3
170°	771.8	771.3	770.9	770.4	770.2	770.0	769.8	769.7	769.5	770.6	771.6
172.5°	776.5	776.1	775.6	775.2	774.9	774.7	774.6	774.5	774.3	775.3	776.4
175°	782.4	781.9	781.5	781.0	780.7	780.3	780.1	779.8	779.4	780.5	781.5
177.5°	784.8	784.4	784.1	783.7	783.5	783.2	783.0	782.7	782.5	783.2	783.9
180°	784.1	784.1	784.1	784.1	784.1	784.1	784.1	784.1	784.1	784.1	784.1



TEST NUMBER: P331770-940

CATALOG NUMBER: S122RDIW-S290D710U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	582.9	582.9	582.9	582.9	582.9	582.9	582.9
2.5°	603.3	605.5	606.5	606.5	607.6	607.1	606.6
5°	638.0	641.9	642.7	646.3	649.0	648.2	648.5
7.5°	672.5	678.7	684.8	687.6	688.0	689.6	690.3
10°	693.8	698.8	708.3	706.9	714.0	718.1	711.4
12.5°	714.2	721.0	727.6	729.4	733.4	734.8	732.1
15°	732.6	736.3	736.6	735.7	736.9	735.8	732.0
17.5°	715.4	709.4	697.5	691.8	687.3	680.6	678.0
20°	686.9	669.4	649.2	641.1	631.6	613.0	617.4
22.5°	625.3	605.5	585.1	561.5	550.2	532.5	531.5
25°	529.5	495.3	457.5	431.2	415.8	398.2	390.5
27.5°	411.7	368.5	337.7	322.1	307.8	293.9	293.3
30°	334.2	301.8	277.9	264.6	255.8	249.9	251.2
32.5°	281.7	259.5	243.3	232.3	225.9	221.4	221.3
35°	230.3	215.1	204.7	200.1	195.5	192.3	192.4
37.5°	197.1	188.0	182.2	177.1	174.2	172.5	171.7
40°	180.0	172.5	168.1	165.1	162.6	160.4	160.0
42.5°	166.7	160.4	156.0	153.6	151.3	149.7	149.4
45°	147.8	142.8	138.8	136.1	135.1	133.7	133.7
47.5°	131.5	126.5	123.4	121.7	120.0	119.0	119.0
50°	120.6	116.6	113.9	112.8	111.4	110.8	110.6
52.5°	110.7	107.7	105.8	105.0	104.4	103.7	103.8
55°	97.2	95.6	94.8	94.2	93.2	91.9	92.7
57.5°	86.0	84.5	82.4	80.4	79.5	78.6	79.0
60°	78.0	75.2	72.3	70.1	69.5	67.7	67.7
62.5°	67.9	63.9	60.5	59.2	58.6	57.8	57.6
65°	52.3	50.6	49.8	49.0	48.6	48.6	48.2
67.5°	43.3	42.6	41.7	41.6	41.2	41.0	40.9
70°	38.3	37.5	37.1	36.8	36.5	36.6	36.0
72.5°	33.4	32.8	32.7	32.2	31.9	31.9	31.5
75°	26.3	26.3	26.1	25.9	25.5	25.3	25.5
77.5°	20.2	20.3	20.0	19.9	19.9	19.9	19.7
80°	16.2	16.4	16.2	16.0	15.8	16.0	15.8
82.5°	12.8	12.5	12.5	12.4	12.4	12.3	12.2
85°	7.3	7.5	7.3	7.1	7.1	7.1	7.3
87.5°	7.2	7.1	7.1	7.1	7.2	7.2	7.1
90°	22.3	22.0	21.9	22.0	22.2	22.4	22.5
92.5°	21.2	21.3	21.3	21.3	21.4	21.4	21.4
95°	42.4	42.4	42.2	41.9	41.6	41.3	41.0
97.5°	71.2	71.2	71.2	71.2	71.2	71.1	71.1
100°	91.3	91.3	91.2	91.1	91.0	90.8	90.7
102.5°	113.3	113.5	113.5	113.3	113.2	113.1	112.9
105°	146.4	146.8	146.9	146.9	146.9	146.9	146.9
107.5°	181.8	181.9	181.6	180.9	180.3	179.6	179.0
110°	205.8	205.8	205.5	205.1	204.6	204.2	203.8



TEST NUMBER: P331770-940

CATALOG NUMBER: S122RDIW-S290D710U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	229.6	229.3	228.9	228.6	228.3	227.9	227.7
115°	266.9	266.7	266.4	266.0	265.6	265.1	264.7
117.5°	302.6	302.2	301.8	301.3	300.9	300.4	300.0
120°	326.9	326.9	326.6	326.2	325.7	325.3	324.9
122.5°	351.2	350.9	350.5	350.2	349.9	349.6	349.3
125°	387.7	387.3	387.0	386.9	386.7	386.6	386.5
127.5°	423.2	422.7	422.2	421.7	421.2	420.8	420.4
130°	447.7	447.5	447.0	446.4	445.9	445.2	444.7
132.5°	471.0	470.4	469.8	469.4	468.9	468.4	468.0
135°	506.4	506.3	506.0	505.5	505.1	504.6	504.2
137.5°	539.8	539.8	539.4	538.8	538.2	537.6	537.0
140°	562.4	562.4	562.1	561.6	561.0	560.4	559.8
142.5°	582.9	583.0	582.8	582.2	581.6	581.0	580.4
145°	613.9	613.9	613.8	613.1	612.6	612.0	611.4
147.5°	641.1	641.4	641.3	640.8	640.2	639.6	639.1
150°	658.4	658.8	658.8	658.4	657.9	657.5	657.1
152.5°	675.6	676.3	676.3	675.6	675.1	674.6	674.0
155°	697.7	698.4	698.6	698.1	697.7	697.2	696.8
157.5°	718.0	719.0	719.2	718.5	717.7	717.0	716.3
160°	729.9	730.8	730.8	730.3	729.7	729.2	728.5
162.5°	740.8	741.8	741.9	741.2	740.6	739.9	739.1
165°	754.7	755.8	756.0	755.2	754.5	753.8	753.0
167.5°	766.2	767.3	767.4	766.7	765.9	765.2	764.4
170°	772.7	773.6	773.7	772.8	772.0	771.1	770.2
172.5°	777.4	778.5	778.5	777.7	776.8	775.9	775.0
175°	782.6	783.6	783.6	782.7	781.9	781.0	780.2
177.5°	784.6	785.3	785.3	784.6	783.9	783.2	782.5
180°	784.1	784.1	784.1	784.1	784.1	784.1	784.1

(END OF REPORT)