

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331774-940

Luminaire Tested: **S122RDIW-S290D970U940-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331774-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIW-S290D970U940-4F0-1E-UDD-A1  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 970 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4004.4 lumens  
Efficiency: N/A  
Efficacy: 105.4 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 38  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331774-940

CATALOG NUMBER: S122RDIW-S290D970U940-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P331774-940

CATALOG NUMBER: S122RDIW-S290D970U940-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	33	33	33	25				
1	93	89	85	82	82	79	76	73	61	59	58	45	44	43	30	29	29	22				
2	85	78	72	67	75	70	65	61	54	51	48	40	38	36	27	26	25	19				
3	77	69	62	57	69	62	56	51	48	44	41	36	33	31	24	23	22	17				
4	71	61	54	48	63	55	49	44	43	39	35	32	29	27	22	20	19	15				
5	65	54	47	41	58	49	42	38	39	34	31	29	26	24	20	18	17	13				
6	60	49	41	36	53	44	37	33	35	30	27	26	23	21	18	16	15	12				
7	56	44	37	31	49	40	33	29	32	27	24	24	21	19	17	15	14	11				
8	52	40	33	28	46	36	30	26	29	24	21	22	19	17	16	14	12	10				
9	48	36	29	25	43	33	27	23	26	22	19	20	17	15	14	13	11	9				
10	45	33	27	22	40	30	24	20	24	20	17	19	16	14	13	12	10	8				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	9411	9411	9411	9411
5°	10511	9470	8399	9470
10°	11663	9404	7279	9404
15°	12236	9267	5735	9267
20°	10608	9062	4962	9062
25°	6957	8783	4431	8783
30°	4683	8444	4010	8444
35°	3792	8016	3617	8016
40°	3372	7552	3347	7552
45°	3053	7005	2987	7005
50°	2778	6465	2768	6465
55°	2609	5866	2578	5866
60°	2186	5318	2160	5318
65°	1841	4829	2090	4829
70°	1699	4310	1969	4310
75°	1591	3755	1822	3755
80°	1469	3096	1618	3096
85°	1352	2445	1426	2445



TEST NUMBER: P331774-940

CATALOG NUMBER: S122RDIW-S290D970U940-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	55.3	1.4
10°-20°	154.0	3.8
20°-30°	198.4	5.0
30°-40°	188.6	4.7
40°-50°	161.5	4.0
50°-60°	123.0	3.1
60°-70°	77.8	1.9
70°-80°	38.8	1.0
80°-90°	14.4	0.4
90°-100°	67.8	1.7
100°-110°	210.6	5.3
110°-120°	360.0	9.0
120°-130°	473.5	11.8
130°-140°	531.4	13.3
140°-150°	521.1	13.0
150°-160°	437.0	10.9
160°-170°	289.9	7.2
170°-180°	101.3	2.5
0°-30°	407.7	10.2
0°-40°	596.2	14.9
0°-60°	880.8	22.0
0°-90°	1011.7	25.3
90°-120°	638.5	15.9
90°-150°	2164.4	54.1
90°-180°	2993.0	74.7
0°-180°	4004.4	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	583	583	583	583	583	
5°	648	584	518	584	648	64
15°	732	554	343	554	732	197
25°	390	493	249	493	390	185
35°	192	407	184	407	192	123
45°	134	307	131	307	134	103
55°	93	208	92	208	93	81
65°	48	126	55	126	48	49
75°	26	60	29	60	26	27
85°	7	13	8	13	7	9
90°	31	1	31	1	31	14
95°	56	47	56	47	56	62
105°	200	194	200	194	200	211
115°	361	361	361	361	361	357
125°	527	526	527	526	527	470
135°	688	680	688	680	688	530
145°	835	826	835	826	835	521
155°	951	944	951	944	951	438
165°	1028	1027	1028	1027	1028	290
175°	1065	1068	1065	1068	1065	101
180°	1070	1070	1070	1070	1070	



TEST NUMBER: P331774-940

CATALOG NUMBER: S122RDIW-S290D970U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9
2.5°	606.6	607.1	607.6	606.5	606.5	605.5	603.3	601.7	597.2	596.6	596.6
5°	648.5	648.2	649.0	646.3	642.7	641.9	638.0	632.9	627.7	621.9	620.6
7.5°	690.3	689.6	688.0	687.6	684.8	678.7	672.5	665.9	657.2	648.6	644.4
10°	711.4	718.1	714.0	706.9	708.3	698.8	693.8	685.0	677.7	664.9	662.2
12.5°	732.1	734.8	733.4	729.4	727.6	721.0	714.2	706.6	693.1	681.7	671.7
15°	732.0	735.8	736.9	735.7	736.6	736.3	732.6	726.4	714.6	702.0	691.1
17.5°	678.0	680.6	687.3	691.8	697.5	709.4	715.4	717.6	716.0	708.7	701.1
20°	617.4	613.0	631.6	641.1	649.2	669.4	686.9	693.6	704.3	704.1	702.0
22.5°	531.5	532.5	550.2	561.5	585.1	605.5	625.3	650.4	671.2	684.9	692.9
25°	390.5	398.2	415.8	431.2	457.5	495.3	529.5	569.2	606.6	636.2	664.4
27.5°	293.3	293.9	307.8	322.1	337.7	368.5	411.7	459.1	512.5	556.6	607.3
30°	251.2	249.9	255.8	264.6	277.9	301.8	334.2	380.8	434.1	500.5	559.6
32.5°	221.3	221.4	225.9	232.3	243.3	259.5	281.7	319.6	369.9	435.2	504.5
35°	192.4	192.3	195.5	200.1	204.7	215.1	230.3	250.1	284.8	345.7	416.6
37.5°	171.7	172.5	174.2	177.1	182.2	188.0	197.1	210.4	235.1	271.2	330.7
40°	160.0	160.4	162.6	165.1	168.1	172.5	180.0	190.8	208.8	237.6	281.2
42.5°	149.4	149.7	151.3	153.6	156.0	160.4	166.7	175.9	190.6	212.9	248.9
45°	133.7	133.7	135.1	136.1	138.8	142.8	147.8	155.6	165.7	182.3	206.2
47.5°	119.0	119.0	120.0	121.7	123.4	126.5	131.5	137.9	145.2	158.0	178.4
50°	110.6	110.8	111.4	112.8	113.9	116.6	120.6	126.0	133.7	143.7	160.6
52.5°	103.8	103.7	104.4	105.0	105.8	107.7	110.7	115.5	122.3	131.0	145.1
55°	92.7	91.9	93.2	94.2	94.8	95.6	97.2	100.2	106.1	113.4	123.9
57.5°	79.0	78.6	79.5	80.4	82.4	84.5	86.0	87.8	90.9	96.1	106.6
60°	67.7	67.7	69.5	70.1	72.3	75.2	78.0	79.6	82.7	86.1	93.8
62.5°	57.6	57.8	58.6	59.2	60.5	63.9	67.9	71.5	74.4	77.7	82.8
65°	48.2	48.6	48.6	49.0	49.8	50.6	52.3	55.1	60.2	64.8	68.7
67.5°	40.9	41.0	41.2	41.6	41.7	42.6	43.3	44.6	45.7	50.1	54.9
70°	36.0	36.6	36.5	36.8	37.1	37.5	38.3	38.9	40.8	41.7	44.6
72.5°	31.5	31.9	31.9	32.2	32.7	32.8	33.4	34.1	35.2	36.0	37.6
75°	25.5	25.3	25.5	25.9	26.1	26.3	26.3	27.1	27.7	28.5	29.6
77.5°	19.7	19.9	19.9	19.9	20.0	20.3	20.2	20.6	21.2	21.7	22.1
80°	15.8	16.0	15.8	16.0	16.2	16.4	16.2	16.4	17.0	17.4	17.4
82.5°	12.2	12.3	12.4	12.4	12.5	12.5	12.8	12.8	13.3	13.2	13.4
85°	7.3	7.1	7.1	7.1	7.3	7.5	7.3	7.3	7.5	7.5	7.5
87.5°	8.7	8.8	8.8	8.7	8.7	8.7	8.8	9.1	9.0	9.3	8.2
90°	30.7	30.5	30.3	30.1	29.9	30.0	30.4	30.8	31.2	31.6	27.2
92.5°	29.2	29.2	29.2	29.2	29.1	29.1	29.0	28.9	28.8	28.7	27.6
95°	56.0	56.4	56.8	57.2	57.6	57.8	57.8	57.8	57.8	57.8	57.4
97.5°	97.0	97.0	97.1	97.1	97.2	97.2	97.2	97.2	97.2	97.2	96.4
100°	123.8	123.9	124.1	124.3	124.6	124.7	124.7	124.7	124.7	124.7	124.0
102.5°	154.1	154.3	154.4	154.7	154.9	154.9	154.7	154.6	154.4	154.3	153.5
105°	200.5	200.5	200.5	200.5	200.5	200.3	199.9	199.5	199.1	198.7	198.3
107.5°	244.2	245.1	246.0	247.0	247.9	248.3	248.2	248.0	247.8	247.6	247.6
110°	278.2	278.7	279.4	280.0	280.6	280.9	280.9	280.9	280.9	280.9	280.9



TEST NUMBER: P331774-940

CATALOG NUMBER: S122RDIW-S290D970U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	310.7	311.1	311.6	312.0	312.5	312.9	313.4	313.9	314.3	314.9	315.0
115°	361.2	361.9	362.5	363.1	363.6	364.1	364.3	364.4	364.7	364.9	365.2
117.5°	409.5	410.1	410.7	411.3	411.9	412.4	413.0	413.4	413.9	414.4	415.5
120°	443.4	444.1	444.7	445.2	445.9	446.2	446.2	446.2	446.2	446.2	447.8
122.5°	476.7	477.2	477.6	478.0	478.5	478.9	479.4	479.9	480.4	480.8	482.0
125°	527.4	527.6	527.9	528.1	528.2	528.7	529.2	529.9	530.5	531.1	531.6
127.5°	573.7	574.4	575.0	575.6	576.2	576.9	577.7	578.4	579.1	579.9	580.6
130°	606.9	607.7	608.5	609.3	610.1	610.7	611.2	611.5	612.0	612.3	612.8
132.5°	638.7	639.4	640.0	640.7	641.3	642.0	642.9	643.8	644.7	645.6	645.5
135°	688.2	688.8	689.4	690.0	690.6	691.0	691.3	691.4	691.6	691.8	691.4
137.5°	733.0	733.8	734.6	735.4	736.2	736.7	736.9	737.0	737.2	737.4	736.8
140°	764.1	764.9	765.7	766.5	767.3	767.7	767.7	767.7	767.7	767.7	766.7
142.5°	792.3	793.1	793.9	794.7	795.5	795.8	795.7	795.5	795.3	795.1	794.5
145°	834.6	835.4	836.2	837.0	837.8	838.0	837.9	837.7	837.4	837.2	836.1
147.5°	872.3	873.1	873.8	874.6	875.3	875.5	875.0	874.6	874.1	873.7	872.9
150°	896.9	897.4	898.0	898.7	899.3	899.3	898.7	898.0	897.4	896.9	896.1
152.5°	920.0	920.7	921.5	922.3	923.0	923.0	922.3	921.5	920.7	920.0	919.0
155°	951.0	951.6	952.3	952.9	953.4	953.2	952.3	951.3	950.2	949.2	948.6
157.5°	977.8	978.7	979.7	980.7	981.6	981.4	980.1	978.7	977.3	976.0	975.6
160°	994.4	995.2	996.0	996.8	997.6	997.4	996.2	995.0	993.8	992.6	992.4
162.5°	1008.9	1009.8	1010.8	1011.7	1012.7	1012.5	1011.1	1009.8	1008.4	1007.0	1006.8
165°	1027.8	1028.9	1029.8	1030.8	1031.8	1031.6	1030.2	1028.9	1027.4	1026.0	1026.0
167.5°	1043.4	1044.4	1045.4	1046.5	1047.5	1047.3	1046.0	1044.6	1043.1	1041.7	1041.8
170°	1051.3	1052.5	1053.7	1054.9	1056.1	1056.1	1054.6	1053.2	1051.8	1050.4	1050.6
172.5°	1057.8	1059.0	1060.2	1061.4	1062.7	1062.5	1061.1	1059.7	1058.3	1056.9	1057.1
175°	1064.9	1066.0	1067.3	1068.4	1069.7	1069.5	1068.2	1066.8	1065.3	1063.9	1064.3
177.5°	1068.1	1069.1	1070.1	1070.9	1071.9	1071.9	1070.9	1070.1	1069.1	1068.1	1068.4
180°	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2



TEST NUMBER: P331774-940

CATALOG NUMBER: S122RDIW-S290D970U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9
2.5°	596.9	595.6	594.4	591.6	590.0	586.8	586.4	586.2	582.0	577.9	576.8
5°	617.4	614.1	609.3	603.6	597.7	591.7	587.6	584.3	576.2	568.6	564.1
7.5°	638.0	631.1	622.7	612.0	603.0	593.0	585.5	578.8	567.3	556.2	548.8
10°	653.4	642.1	631.0	616.2	604.6	593.3	582.7	573.6	560.7	546.1	535.7
12.5°	663.0	650.5	635.2	620.7	605.7	591.3	577.2	565.5	550.3	535.2	523.0
15°	675.9	662.5	643.9	623.2	604.0	585.1	569.0	554.4	534.6	516.5	501.5
17.5°	686.5	668.1	648.1	624.2	601.9	578.0	557.1	538.5	516.4	494.6	477.0
20°	689.9	671.6	648.5	624.6	598.3	570.2	547.7	527.4	503.7	480.0	459.8
22.5°	687.8	673.6	647.9	619.3	592.4	562.9	537.5	514.0	487.7	463.5	440.1
25°	673.5	668.6	644.4	613.1	582.4	548.1	518.7	493.0	463.1	437.1	411.6
27.5°	640.2	650.7	635.6	602.4	568.1	531.5	498.4	469.1	438.0	408.8	383.4
30°	608.1	632.1	625.7	594.9	556.6	520.6	483.5	452.9	419.7	389.7	364.6
32.5°	564.2	604.0	610.3	584.5	544.9	505.3	466.5	436.0	401.4	369.8	345.3
35°	494.2	553.8	581.1	564.7	525.0	482.2	442.2	406.7	371.8	340.7	316.4
37.5°	410.8	492.0	537.5	538.7	502.2	457.8	414.1	378.9	343.2	312.6	286.3
40°	356.7	444.6	504.0	517.1	486.3	438.4	394.1	358.3	323.5	293.5	263.3
42.5°	308.1	395.7	468.6	491.5	467.1	419.4	375.1	337.6	303.7	275.4	244.5
45°	249.1	325.7	406.1	447.0	433.5	389.3	342.5	306.8	275.1	250.6	221.0
47.5°	210.2	264.1	342.0	397.3	397.1	356.8	310.7	276.6	247.1	224.1	200.2
50°	188.0	235.0	300.8	363.6	368.8	335.0	291.2	257.4	229.9	205.8	186.5
52.5°	168.0	206.8	265.9	326.2	341.2	311.8	269.4	238.2	211.4	189.2	172.8
55°	142.0	172.0	217.0	273.2	296.0	275.3	237.6	208.4	186.7	168.1	153.9
57.5°	120.1	142.6	178.7	224.0	250.4	237.5	206.3	182.6	164.1	147.2	136.1
60°	106.4	124.8	155.3	193.2	222.4	213.3	186.7	164.7	148.9	134.3	123.8
62.5°	93.4	109.2	135.5	166.2	192.9	189.1	167.5	148.9	135.1	121.8	112.9
65°	75.2	86.7	107.2	131.3	152.8	154.5	138.9	126.4	114.0	103.5	95.6
67.5°	59.8	67.4	81.8	102.1	118.2	123.9	114.4	104.8	95.0	86.9	80.0
70°	50.5	56.5	67.1	83.5	98.3	104.3	98.8	91.3	82.8	76.2	70.3
72.5°	40.8	46.8	54.6	66.6	79.3	85.9	83.9	78.6	71.7	66.1	60.5
75°	30.8	32.6	37.9	46.0	55.9	61.6	63.0	60.2	54.7	50.5	47.2
77.5°	22.7	23.9	26.4	30.6	37.1	42.2	44.2	43.9	40.1	37.7	34.6
80°	18.2	18.8	20.1	21.8	26.8	31.8	33.3	33.3	30.6	29.6	26.6
82.5°	13.8	14.3	15.1	16.1	18.3	22.7	24.3	24.6	23.0	21.7	19.3
85°	7.9	7.7	8.1	8.7	9.1	10.3	12.8	13.2	12.8	11.1	10.5
87.5°	7.3	6.6	5.7	4.9	4.5	4.2	4.5	4.9	4.7	4.7	4.9
90°	22.7	18.4	13.9	10.5	8.1	5.7	3.3	0.9	3.3	5.7	8.1
92.5°	26.7	25.6	24.5	23.2	21.4	19.6	17.8	16.1	17.8	19.6	21.4
95°	57.0	56.6	56.2	55.0	53.0	51.0	49.0	47.0	49.0	51.0	53.0
97.5°	95.7	94.9	94.2	92.8	91.1	89.3	87.6	85.8	87.6	89.3	91.1
100°	123.4	122.8	122.3	121.1	119.5	117.9	116.3	114.7	116.3	117.9	119.5
102.5°	152.8	151.9	151.2	150.2	148.9	147.6	146.3	145.1	146.3	147.6	148.9
105°	197.9	197.5	197.1	196.6	196.0	195.4	194.7	194.2	194.7	195.4	196.0
107.5°	247.6	247.6	247.6	247.2	246.3	245.4	244.6	243.7	244.6	245.4	246.3
110°	280.9	280.9	280.9	280.3	279.1	277.9	276.7	275.4	276.7	277.9	279.1





TEST NUMBER: P331774-940

CATALOG NUMBER: S122RDIW-S290D970U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	315.1	315.3	315.5	315.0	313.8	312.5	311.4	310.1	311.4	312.5	313.8
115°	365.7	366.0	366.5	366.0	364.9	363.6	362.5	361.2	362.5	363.6	364.9
117.5°	416.6	417.8	418.8	418.7	417.1	415.4	413.8	412.2	413.8	415.4	417.1
120°	449.4	451.0	452.6	452.6	451.0	449.4	447.8	446.2	447.8	449.4	451.0
122.5°	483.1	484.2	485.4	484.9	483.0	481.1	479.2	477.2	479.2	481.1	483.0
125°	532.3	532.9	533.5	532.9	531.1	529.2	527.4	525.7	527.4	529.2	531.1
127.5°	581.3	582.0	582.7	581.9	579.7	577.4	575.1	572.8	575.1	577.4	579.7
130°	613.1	613.6	613.9	612.9	610.3	607.6	605.0	602.4	605.0	607.6	610.3
132.5°	645.4	645.3	645.2	644.2	642.0	639.9	637.8	635.6	637.8	639.9	642.0
135°	691.0	690.6	690.2	688.9	686.7	684.5	682.3	680.1	682.3	684.5	686.7
137.5°	736.3	735.8	735.3	734.1	732.3	730.5	728.7	726.8	728.7	730.5	732.3
140°	765.7	764.7	763.7	762.2	760.5	758.7	756.9	755.0	756.9	758.7	760.5
142.5°	793.8	793.1	792.5	791.2	789.3	787.6	785.8	784.0	785.8	787.6	789.3
145°	834.8	833.7	832.4	831.2	829.7	828.3	826.9	825.5	826.9	828.3	829.7
147.5°	872.1	871.3	870.5	869.2	867.5	865.9	864.2	862.6	864.2	865.9	867.5
150°	895.3	894.5	893.7	892.6	891.4	890.2	889.0	887.8	889.0	890.2	891.4
152.5°	918.0	917.1	916.1	915.1	913.8	912.7	911.4	910.3	911.4	912.7	913.8
155°	948.1	947.4	946.8	946.2	945.7	945.0	944.4	943.8	944.4	945.0	945.7
157.5°	975.3	974.9	974.6	974.1	973.7	973.3	972.9	972.5	972.9	973.3	973.7
160°	992.2	992.0	991.8	991.5	991.0	990.7	990.2	989.9	990.2	990.7	991.0
162.5°	1006.7	1006.5	1006.2	1006.1	1006.0	1005.9	1005.8	1005.8	1005.8	1005.9	1006.0
165°	1026.0	1026.0	1026.0	1026.1	1026.3	1026.5	1026.7	1026.9	1026.7	1026.5	1026.3
167.5°	1041.8	1041.9	1041.9	1042.2	1042.8	1043.4	1044.0	1044.6	1044.0	1043.4	1042.8
170°	1050.8	1051.0	1051.2	1051.6	1052.2	1052.8	1053.4	1054.0	1053.4	1052.8	1052.2
172.5°	1057.3	1057.5	1057.7	1058.1	1058.7	1059.3	1059.9	1060.5	1059.9	1059.3	1058.7
175°	1064.7	1065.1	1065.5	1066.0	1066.7	1067.3	1067.8	1068.4	1067.8	1067.3	1066.7
177.5°	1068.7	1069.1	1069.3	1069.8	1070.2	1070.8	1071.2	1071.7	1071.2	1070.8	1070.2
180°	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2



TEST NUMBER: P331774-940

CATALOG NUMBER: S122RDIW-S290D970U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9
2.5°	574.7	573.5	571.4	568.2	566.2	562.8	560.6	561.9	562.2	561.9	561.6
5°	559.3	555.0	549.1	543.4	538.1	532.5	529.2	527.9	525.0	523.4	522.5
7.5°	540.6	533.2	525.0	515.1	506.7	497.8	493.4	491.2	485.4	482.2	479.5
10°	526.6	515.1	506.8	493.8	485.9	474.4	466.5	466.7	458.8	454.3	451.1
12.5°	511.2	498.6	484.7	473.1	462.1	452.8	443.3	439.4	431.1	426.8	418.0
15°	485.7	470.9	456.4	440.6	429.4	415.0	401.3	384.4	370.9	359.1	355.9
17.5°	457.9	439.5	424.9	406.4	387.3	363.1	347.1	337.3	329.2	323.0	318.3
20°	438.7	420.1	404.5	376.6	350.8	334.4	322.7	315.1	306.7	300.0	296.3
22.5°	418.7	399.2	377.9	346.7	326.6	313.5	303.1	294.4	288.6	283.5	280.1
25°	390.1	368.8	333.8	312.4	296.1	282.3	275.1	269.8	263.8	256.6	253.4
27.5°	360.0	326.2	301.0	285.0	269.6	260.6	254.0	246.2	240.8	237.6	234.2
30°	337.4	303.6	284.0	266.5	255.7	245.7	238.0	233.5	228.3	222.8	220.6
32.5°	312.4	285.3	266.4	252.0	240.9	232.4	226.3	219.1	215.3	212.0	207.3
35°	281.2	260.6	243.4	231.8	221.1	214.3	207.2	203.0	196.1	193.2	191.5
37.5°	254.8	237.0	224.2	211.8	203.4	195.8	191.5	184.7	181.7	177.7	173.9
40°	239.8	222.4	210.1	199.9	190.6	184.9	179.5	174.0	169.5	167.7	163.1
42.5°	224.6	210.4	198.0	187.0	180.7	174.7	167.8	163.8	159.2	156.2	153.4
45°	203.6	191.0	180.5	171.4	164.4	158.2	153.7	147.0	144.5	138.6	136.1
47.5°	185.1	173.4	163.4	154.7	148.0	143.9	137.4	132.2	128.0	124.3	121.2
50°	172.0	162.2	152.5	144.8	138.8	132.9	126.2	123.6	117.1	115.2	113.4
52.5°	160.0	150.7	141.9	134.3	128.2	122.5	116.6	113.2	108.8	107.0	105.7
55°	143.2	134.3	125.8	119.1	113.1	107.2	103.5	99.2	97.2	95.8	94.2
57.5°	126.4	118.3	111.8	105.0	98.9	94.3	90.1	87.5	85.4	83.6	81.6
60°	115.7	108.0	102.1	95.8	89.5	85.7	82.5	79.4	77.0	74.1	73.3
62.5°	104.3	97.6	92.2	86.1	80.6	77.1	74.0	71.2	68.2	64.1	63.0
65°	88.7	83.5	77.8	72.7	67.9	64.4	59.9	56.7	55.5	55.1	54.9
67.5°	74.6	69.6	64.7	59.6	55.2	52.0	49.7	49.2	48.3	48.2	47.5
70°	65.2	60.5	55.7	50.8	46.5	46.0	45.2	44.3	43.3	43.0	42.5
72.5°	56.8	52.0	47.1	43.2	41.4	40.7	39.9	39.0	38.3	37.9	37.7
75°	43.5	39.1	35.8	34.4	33.4	32.8	31.6	31.0	30.6	30.0	29.8
77.5°	31.4	28.8	27.4	26.5	25.4	24.8	24.1	23.5	23.0	22.9	22.6
80°	23.9	22.6	21.7	20.4	20.1	19.3	19.1	18.5	18.6	18.0	18.0
82.5°	18.5	17.0	16.1	15.6	15.2	14.5	14.4	14.1	14.1	13.6	13.6
85°	9.5	9.1	8.7	8.3	8.3	7.7	7.9	7.7	7.7	7.3	7.1
87.5°	5.2	5.7	6.2	7.1	8.0	8.7	8.6	8.5	8.4	8.3	8.1
90°	10.5	13.9	18.4	22.7	27.2	31.6	31.2	30.8	30.4	30.0	29.9
92.5°	23.2	24.5	25.6	26.7	27.6	28.7	28.8	28.9	29.0	29.1	29.1
95°	55.0	56.2	56.6	57.0	57.4	57.8	57.8	57.8	57.8	57.8	57.6
97.5°	92.8	94.2	94.9	95.7	96.4	97.2	97.2	97.2	97.2	97.2	97.2
100°	121.1	122.3	122.8	123.4	124.0	124.7	124.7	124.7	124.7	124.7	124.6
102.5°	150.2	151.2	151.9	152.8	153.5	154.3	154.4	154.6	154.7	154.9	154.9
105°	196.6	197.1	197.5	197.9	198.3	198.7	199.1	199.5	199.9	200.3	200.5
107.5°	247.2	247.6	247.6	247.6	247.6	247.6	247.8	248.0	248.2	248.3	247.9
110°	280.3	280.9	280.9	280.9	280.9	280.9	280.9	280.9	280.9	280.9	280.6



TEST NUMBER: P331774-940

CATALOG NUMBER: S122RDIW-S290D970U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	315.0	315.5	315.3	315.1	315.0	314.9	314.3	313.9	313.4	312.9	312.5
115°	366.0	366.5	366.0	365.7	365.2	364.9	364.7	364.4	364.3	364.1	363.6
117.5°	418.7	418.8	417.8	416.6	415.5	414.4	413.9	413.4	413.0	412.4	411.9
120°	452.6	452.6	451.0	449.4	447.8	446.2	446.2	446.2	446.2	446.2	445.9
122.5°	484.9	485.4	484.2	483.1	482.0	480.8	480.4	479.9	479.4	478.9	478.5
125°	532.9	533.5	532.9	532.3	531.6	531.1	530.5	529.9	529.2	528.7	528.2
127.5°	581.9	582.7	582.0	581.3	580.6	579.9	579.1	578.4	577.7	576.9	576.2
130°	612.9	613.9	613.6	613.1	612.8	612.3	612.0	611.5	611.2	610.7	610.1
132.5°	644.2	645.2	645.3	645.4	645.5	645.6	644.7	643.8	642.9	642.0	641.3
135°	688.9	690.2	690.6	691.0	691.4	691.8	691.6	691.4	691.3	691.0	690.6
137.5°	734.1	735.3	735.8	736.3	736.8	737.4	737.2	737.0	736.9	736.7	736.2
140°	762.2	763.7	764.7	765.7	766.7	767.7	767.7	767.7	767.7	767.7	767.3
142.5°	791.2	792.5	793.1	793.8	794.5	795.1	795.3	795.5	795.7	795.8	795.5
145°	831.2	832.4	833.7	834.8	836.1	837.2	837.4	837.7	837.9	838.0	837.8
147.5°	869.2	870.5	871.3	872.1	872.9	873.7	874.1	874.6	875.0	875.5	875.3
150°	892.6	893.7	894.5	895.3	896.1	896.9	897.4	898.0	898.7	899.3	899.3
152.5°	915.1	916.1	917.1	918.0	919.0	920.0	920.7	921.5	922.3	923.0	923.0
155°	946.2	946.8	947.4	948.1	948.6	949.2	950.2	951.3	952.3	953.2	953.4
157.5°	974.1	974.6	974.9	975.3	975.6	976.0	977.3	978.7	980.1	981.4	981.6
160°	991.5	991.8	992.0	992.2	992.4	992.6	993.8	995.0	996.2	997.4	997.6
162.5°	1006.1	1006.2	1006.5	1006.7	1006.8	1007.0	1008.4	1009.8	1011.1	1012.5	1012.7
165°	1026.1	1026.0	1026.0	1026.0	1026.0	1026.0	1027.4	1028.9	1030.2	1031.6	1031.8
167.5°	1042.2	1041.9	1041.9	1041.8	1041.8	1041.7	1043.1	1044.6	1046.0	1047.3	1047.5
170°	1051.6	1051.2	1051.0	1050.8	1050.6	1050.4	1051.8	1053.2	1054.6	1056.1	1056.1
172.5°	1058.1	1057.7	1057.5	1057.3	1057.1	1056.9	1058.3	1059.7	1061.1	1062.5	1062.7
175°	1066.0	1065.5	1065.1	1064.7	1064.3	1063.9	1065.3	1066.8	1068.2	1069.5	1069.7
177.5°	1069.8	1069.3	1069.1	1068.7	1068.4	1068.1	1069.1	1070.1	1070.9	1071.9	1071.9
180°	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2



TEST NUMBER: P331774-940

CATALOG NUMBER: S122RDIW-S290D970U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9
2.5°	559.8	560.1	559.6	559.9	559.6	560.1	559.8	561.6	561.9	562.2	561.9
5°	521.6	519.2	518.7	518.2	518.7	519.2	521.6	522.5	523.4	525.0	527.9
7.5°	476.0	475.6	474.6	473.1	474.6	475.6	476.0	479.5	482.2	485.4	491.2
10°	446.7	445.6	445.4	444.0	445.4	445.6	446.7	451.1	454.3	458.8	466.7
12.5°	412.2	405.7	405.1	401.5	405.1	405.7	412.2	418.0	426.8	431.1	439.4
15°	351.1	349.8	345.7	343.1	345.7	349.8	351.1	355.9	359.1	370.9	384.4
17.5°	316.0	312.0	310.8	310.2	310.8	312.0	316.0	318.3	323.0	329.2	337.3
20°	293.5	289.9	289.3	288.8	289.3	289.9	293.5	296.3	300.0	306.7	315.1
22.5°	277.9	274.1	272.6	271.3	272.6	274.1	277.9	280.1	283.5	288.6	294.4
25°	251.4	249.9	249.1	248.7	249.1	249.9	251.4	253.4	256.6	263.8	269.8
27.5°	230.6	227.5	226.9	225.8	226.9	227.5	230.6	234.2	237.6	240.8	246.2
30°	218.7	217.8	216.3	215.1	216.3	217.8	218.7	220.6	222.8	228.3	233.5
32.5°	204.8	203.9	202.7	202.2	202.7	203.9	204.8	207.3	212.0	215.3	219.1
35°	189.4	186.5	185.3	183.5	185.3	186.5	189.4	191.5	193.2	196.1	203.0
37.5°	173.1	171.6	169.9	170.5	169.9	171.6	173.1	173.9	177.7	181.7	184.7
40°	160.4	159.4	159.0	158.8	159.0	159.4	160.4	163.1	167.7	169.5	174.0
42.5°	150.3	147.6	146.5	146.5	146.5	147.6	150.3	153.4	156.2	159.2	163.8
45°	135.1	132.5	130.6	130.8	130.6	132.5	135.1	136.1	138.6	144.5	147.0
47.5°	119.5	119.4	118.2	118.6	118.2	119.4	119.5	121.2	124.3	128.0	132.2
50°	112.0	110.8	109.9	110.2	109.9	110.8	112.0	113.4	115.2	117.1	123.6
52.5°	104.9	103.8	103.2	104.1	103.2	103.8	104.9	105.7	107.0	108.8	113.2
55°	93.2	91.9	91.8	91.6	91.8	91.9	93.2	94.2	95.8	97.2	99.2
57.5°	80.1	79.3	78.0	77.6	78.0	79.3	80.1	81.6	83.6	85.4	87.5
60°	70.7	69.1	67.1	66.9	67.1	69.1	70.7	73.3	74.1	77.0	79.4
62.5°	62.1	61.8	61.3	61.3	61.3	61.8	62.1	63.0	64.1	68.2	71.2
65°	54.5	54.3	54.5	54.7	54.5	54.3	54.5	54.9	55.1	55.5	56.7
67.5°	47.4	47.1	46.7	46.9	46.7	47.1	47.4	47.5	48.2	48.3	49.2
70°	42.1	41.9	41.7	41.7	41.7	41.9	42.1	42.5	43.0	43.3	44.3
72.5°	36.9	36.9	36.7	36.6	36.7	36.9	36.9	37.7	37.9	38.3	39.0
75°	29.6	29.2	29.2	29.2	29.2	29.2	29.6	29.8	30.0	30.6	31.0
77.5°	22.6	22.3	22.1	21.9	22.1	22.3	22.6	22.6	22.9	23.0	23.5
80°	17.8	17.7	17.4	17.4	17.4	17.7	17.8	18.0	18.0	18.6	18.5
82.5°	13.6	13.4	13.4	13.2	13.4	13.4	13.6	13.6	13.6	14.1	14.1
85°	7.3	7.5	7.3	7.7	7.3	7.5	7.3	7.1	7.3	7.7	7.7
87.5°	8.1	8.0	8.2	8.1	8.2	8.0	8.1	8.1	8.3	8.4	8.5
90°	30.1	30.3	30.5	30.7	30.5	30.3	30.1	29.9	30.0	30.4	30.8
92.5°	29.2	29.2	29.2	29.2	29.2	29.2	29.2	29.1	29.1	29.0	28.9
95°	57.2	56.8	56.4	56.0	56.4	56.8	57.2	57.6	57.8	57.8	57.8
97.5°	97.1	97.1	97.0	97.0	97.0	97.1	97.1	97.2	97.2	97.2	97.2
100°	124.3	124.1	123.9	123.8	123.9	124.1	124.3	124.6	124.7	124.7	124.7
102.5°	154.7	154.4	154.3	154.1	154.3	154.4	154.7	154.9	154.9	154.7	154.6
105°	200.5	200.5	200.5	200.5	200.5	200.5	200.5	200.5	200.3	199.9	199.5
107.5°	247.0	246.0	245.1	244.2	245.1	246.0	247.0	247.9	248.3	248.2	248.0
110°	280.0	279.4	278.7	278.2	278.7	279.4	280.0	280.6	280.9	280.9	280.9



TEST NUMBER: P331774-940

CATALOG NUMBER: S122RDIW-S290D970U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	312.0	311.6	311.1	310.7	311.1	311.6	312.0	312.5	312.9	313.4	313.9
115°	363.1	362.5	361.9	361.2	361.9	362.5	363.1	363.6	364.1	364.3	364.4
117.5°	411.3	410.7	410.1	409.5	410.1	410.7	411.3	411.9	412.4	413.0	413.4
120°	445.2	444.7	444.1	443.4	444.1	444.7	445.2	445.9	446.2	446.2	446.2
122.5°	478.0	477.6	477.2	476.7	477.2	477.6	478.0	478.5	478.9	479.4	479.9
125°	528.1	527.9	527.6	527.4	527.6	527.9	528.1	528.2	528.7	529.2	529.9
127.5°	575.6	575.0	574.4	573.7	574.4	575.0	575.6	576.2	576.9	577.7	578.4
130°	609.3	608.5	607.7	606.9	607.7	608.5	609.3	610.1	610.7	611.2	611.5
132.5°	640.7	640.0	639.4	638.7	639.4	640.0	640.7	641.3	642.0	642.9	643.8
135°	690.0	689.4	688.8	688.2	688.8	689.4	690.0	690.6	691.0	691.3	691.4
137.5°	735.4	734.6	733.8	733.0	733.8	734.6	735.4	736.2	736.7	736.9	737.0
140°	766.5	765.7	764.9	764.1	764.9	765.7	766.5	767.3	767.7	767.7	767.7
142.5°	794.7	793.9	793.1	792.3	793.1	793.9	794.7	795.5	795.8	795.7	795.5
145°	837.0	836.2	835.4	834.6	835.4	836.2	837.0	837.8	838.0	837.9	837.7
147.5°	874.6	873.8	873.1	872.3	873.1	873.8	874.6	875.3	875.5	875.0	874.6
150°	898.7	898.0	897.4	896.9	897.4	898.0	898.7	899.3	899.3	898.7	898.0
152.5°	922.3	921.5	920.7	920.0	920.7	921.5	922.3	923.0	923.0	922.3	921.5
155°	952.9	952.3	951.6	951.0	951.6	952.3	952.9	953.4	953.2	952.3	951.3
157.5°	980.7	979.7	978.7	977.8	978.7	979.7	980.7	981.6	981.4	980.1	978.7
160°	996.8	996.0	995.2	994.4	995.2	996.0	996.8	997.6	997.4	996.2	995.0
162.5°	1011.7	1010.8	1009.8	1008.9	1009.8	1010.8	1011.7	1012.7	1012.5	1011.1	1009.8
165°	1030.8	1029.8	1028.9	1027.8	1028.9	1029.8	1030.8	1031.8	1031.6	1030.2	1028.9
167.5°	1046.5	1045.4	1044.4	1043.4	1044.4	1045.4	1046.5	1047.5	1047.3	1046.0	1044.6
170°	1054.9	1053.7	1052.5	1051.3	1052.5	1053.7	1054.9	1056.1	1056.1	1054.6	1053.2
172.5°	1061.4	1060.2	1059.0	1057.8	1059.0	1060.2	1061.4	1062.7	1062.5	1061.1	1059.7
175°	1068.4	1067.3	1066.0	1064.9	1066.0	1067.3	1068.4	1069.7	1069.5	1068.2	1066.8
177.5°	1070.9	1070.1	1069.1	1068.1	1069.1	1070.1	1070.9	1071.9	1071.9	1070.9	1070.1
180°	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2



TEST NUMBER: P331774-940

CATALOG NUMBER: S122RDIW-S290D970U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9
2.5°	560.6	562.8	566.2	568.2	571.4	573.5	574.7	576.8	577.9	582.0	586.2
5°	529.2	532.5	538.1	543.4	549.1	555.0	559.3	564.1	568.6	576.2	584.3
7.5°	493.4	497.8	506.7	515.1	525.0	533.2	540.6	548.8	556.2	567.3	578.8
10°	466.5	474.4	485.9	493.8	506.8	515.1	526.6	535.7	546.1	560.7	573.6
12.5°	443.3	452.8	462.1	473.1	484.7	498.6	511.2	523.0	535.2	550.3	565.5
15°	401.3	415.0	429.4	440.6	456.4	470.9	485.7	501.5	516.5	534.6	554.4
17.5°	347.1	363.1	387.3	406.4	424.9	439.5	457.9	477.0	494.6	516.4	538.5
20°	322.7	334.4	350.8	376.6	404.5	420.1	438.7	459.8	480.0	503.7	527.4
22.5°	303.1	313.5	326.6	346.7	377.9	399.2	418.7	440.1	463.5	487.7	514.0
25°	275.1	282.3	296.1	312.4	333.8	368.8	390.1	411.6	437.1	463.1	493.0
27.5°	254.0	260.6	269.6	285.0	301.0	326.2	360.0	383.4	408.8	438.0	469.1
30°	238.0	245.7	255.7	266.5	284.0	303.6	337.4	364.6	389.7	419.7	452.9
32.5°	226.3	232.4	240.9	252.0	266.4	285.3	312.4	345.3	369.8	401.4	436.0
35°	207.2	214.3	221.1	231.8	243.4	260.6	281.2	316.4	340.7	371.8	406.7
37.5°	191.5	195.8	203.4	211.8	224.2	237.0	254.8	286.3	312.6	343.2	378.9
40°	179.5	184.9	190.6	199.9	210.1	222.4	239.8	263.3	293.5	323.5	358.3
42.5°	167.8	174.7	180.7	187.0	198.0	210.4	224.6	244.5	275.4	303.7	337.6
45°	153.7	158.2	164.4	171.4	180.5	191.0	203.6	221.0	250.6	275.1	306.8
47.5°	137.4	143.9	148.0	154.7	163.4	173.4	185.1	200.2	224.1	247.1	276.6
50°	126.2	132.9	138.8	144.8	152.5	162.2	172.0	186.5	205.8	229.9	257.4
52.5°	116.6	122.5	128.2	134.3	141.9	150.7	160.0	172.8	189.2	211.4	238.2
55°	103.5	107.2	113.1	119.1	125.8	134.3	143.2	153.9	168.1	186.7	208.4
57.5°	90.1	94.3	98.9	105.0	111.8	118.3	126.4	136.1	147.2	164.1	182.6
60°	82.5	85.7	89.5	95.8	102.1	108.0	115.7	123.8	134.3	148.9	164.7
62.5°	74.0	77.1	80.6	86.1	92.2	97.6	104.3	112.9	121.8	135.1	148.9
65°	59.9	64.4	67.9	72.7	77.8	83.5	88.7	95.6	103.5	114.0	126.4
67.5°	49.7	52.0	55.2	59.6	64.7	69.6	74.6	80.0	86.9	95.0	104.8
70°	45.2	46.0	46.5	50.8	55.7	60.5	65.2	70.3	76.2	82.8	91.3
72.5°	39.9	40.7	41.4	43.2	47.1	52.0	56.8	60.5	66.1	71.7	78.6
75°	31.6	32.8	33.4	34.4	35.8	39.1	43.5	47.2	50.5	54.7	60.2
77.5°	24.1	24.8	25.4	26.5	27.4	28.8	31.4	34.6	37.7	40.1	43.9
80°	19.1	19.3	20.1	20.4	21.7	22.6	23.9	26.6	29.6	30.6	33.3
82.5°	14.4	14.5	15.2	15.6	16.1	17.0	18.5	19.3	21.7	23.0	24.6
85°	7.9	7.7	8.3	8.3	8.7	9.1	9.5	10.5	11.1	12.8	13.2
87.5°	8.6	8.7	8.0	7.1	6.2	5.7	5.2	4.9	4.7	4.7	4.9
90°	31.2	31.6	27.2	22.7	18.4	13.9	10.5	8.1	5.7	3.3	0.9
92.5°	28.8	28.7	27.6	26.7	25.6	24.5	23.2	21.4	19.6	17.8	16.1
95°	57.8	57.8	57.4	57.0	56.6	56.2	55.0	53.0	51.0	49.0	47.0
97.5°	97.2	97.2	96.4	95.7	94.9	94.2	92.8	91.1	89.3	87.6	85.8
100°	124.7	124.7	124.0	123.4	122.8	122.3	121.1	119.5	117.9	116.3	114.7
102.5°	154.4	154.3	153.5	152.8	151.9	151.2	150.2	148.9	147.6	146.3	145.1
105°	199.1	198.7	198.3	197.9	197.5	197.1	196.6	196.0	195.4	194.7	194.2
107.5°	247.8	247.6	247.6	247.6	247.6	247.6	247.2	246.3	245.4	244.6	243.7
110°	280.9	280.9	280.9	280.9	280.9	280.9	280.3	279.1	277.9	276.7	275.4



TEST NUMBER: P331774-940

CATALOG NUMBER: S122RDIW-S290D970U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	314.3	314.9	315.0	315.1	315.3	315.5	315.0	313.8	312.5	311.4	310.1
115°	364.7	364.9	365.2	365.7	366.0	366.5	366.0	364.9	363.6	362.5	361.2
117.5°	413.9	414.4	415.5	416.6	417.8	418.8	418.7	417.1	415.4	413.8	412.2
120°	446.2	446.2	447.8	449.4	451.0	452.6	452.6	451.0	449.4	447.8	446.2
122.5°	480.4	480.8	482.0	483.1	484.2	485.4	484.9	483.0	481.1	479.2	477.2
125°	530.5	531.1	531.6	532.3	532.9	533.5	532.9	531.1	529.2	527.4	525.7
127.5°	579.1	579.9	580.6	581.3	582.0	582.7	581.9	579.7	577.4	575.1	572.8
130°	612.0	612.3	612.8	613.1	613.6	613.9	612.9	610.3	607.6	605.0	602.4
132.5°	644.7	645.6	645.5	645.4	645.3	645.2	644.2	642.0	639.9	637.8	635.6
135°	691.6	691.8	691.4	691.0	690.6	690.2	688.9	686.7	684.5	682.3	680.1
137.5°	737.2	737.4	736.8	736.3	735.8	735.3	734.1	732.3	730.5	728.7	726.8
140°	767.7	767.7	766.7	765.7	764.7	763.7	762.2	760.5	758.7	756.9	755.0
142.5°	795.3	795.1	794.5	793.8	793.1	792.5	791.2	789.3	787.6	785.8	784.0
145°	837.4	837.2	836.1	834.8	833.7	832.4	831.2	829.7	828.3	826.9	825.5
147.5°	874.1	873.7	872.9	872.1	871.3	870.5	869.2	867.5	865.9	864.2	862.6
150°	897.4	896.9	896.1	895.3	894.5	893.7	892.6	891.4	890.2	889.0	887.8
152.5°	920.7	920.0	919.0	918.0	917.1	916.1	915.1	913.8	912.7	911.4	910.3
155°	950.2	949.2	948.6	948.1	947.4	946.8	946.2	945.7	945.0	944.4	943.8
157.5°	977.3	976.0	975.6	975.3	974.9	974.6	974.1	973.7	973.3	972.9	972.5
160°	993.8	992.6	992.4	992.2	992.0	991.8	991.5	991.0	990.7	990.2	989.9
162.5°	1008.4	1007.0	1006.8	1006.7	1006.5	1006.2	1006.1	1006.0	1005.9	1005.8	1005.8
165°	1027.4	1026.0	1026.0	1026.0	1026.0	1026.0	1026.1	1026.3	1026.5	1026.7	1026.9
167.5°	1043.1	1041.7	1041.8	1041.8	1041.9	1041.9	1042.2	1042.8	1043.4	1044.0	1044.6
170°	1051.8	1050.4	1050.6	1050.8	1051.0	1051.2	1051.6	1052.2	1052.8	1053.4	1054.0
172.5°	1058.3	1056.9	1057.1	1057.3	1057.5	1057.7	1058.1	1058.7	1059.3	1059.9	1060.5
175°	1065.3	1063.9	1064.3	1064.7	1065.1	1065.5	1066.0	1066.7	1067.3	1067.8	1068.4
177.5°	1069.1	1068.1	1068.4	1068.7	1069.1	1069.3	1069.8	1070.2	1070.8	1071.2	1071.7
180°	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2



TEST NUMBER: P331774-940

CATALOG NUMBER: S122RDIW-S290D970U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9
2.5°	586.4	586.8	590.0	591.6	594.4	595.6	596.9	596.6	596.6	597.2	601.7
5°	587.6	591.7	597.7	603.6	609.3	614.1	617.4	620.6	621.9	627.7	632.9
7.5°	585.5	593.0	603.0	612.0	622.7	631.1	638.0	644.4	648.6	657.2	665.9
10°	582.7	593.3	604.6	616.2	631.0	642.1	653.4	662.2	664.9	677.7	685.0
12.5°	577.2	591.3	605.7	620.7	635.2	650.5	663.0	671.7	681.7	693.1	706.6
15°	569.0	585.1	604.0	623.2	643.9	662.5	675.9	691.1	702.0	714.6	726.4
17.5°	557.1	578.0	601.9	624.2	648.1	668.1	686.5	701.1	708.7	716.0	717.6
20°	547.7	570.2	598.3	624.6	648.5	671.6	689.9	702.0	704.1	704.3	693.6
22.5°	537.5	562.9	592.4	619.3	647.9	673.6	687.8	692.9	684.9	671.2	650.4
25°	518.7	548.1	582.4	613.1	644.4	668.6	673.5	664.4	636.2	606.6	569.2
27.5°	498.4	531.5	568.1	602.4	635.6	650.7	640.2	607.3	556.6	512.5	459.1
30°	483.5	520.6	556.6	594.9	625.7	632.1	608.1	559.6	500.5	434.1	380.8
32.5°	466.5	505.3	544.9	584.5	610.3	604.0	564.2	504.5	435.2	369.9	319.6
35°	442.2	482.2	525.0	564.7	581.1	553.8	494.2	416.6	345.7	284.8	250.1
37.5°	414.1	457.8	502.2	538.7	537.5	492.0	410.8	330.7	271.2	235.1	210.4
40°	394.1	438.4	486.3	517.1	504.0	444.6	356.7	281.2	237.6	208.8	190.8
42.5°	375.1	419.4	467.1	491.5	468.6	395.7	308.1	248.9	212.9	190.6	175.9
45°	342.5	389.3	433.5	447.0	406.1	325.7	249.1	206.2	182.3	165.7	155.6
47.5°	310.7	356.8	397.1	397.3	342.0	264.1	210.2	178.4	158.0	145.2	137.9
50°	291.2	335.0	368.8	363.6	300.8	235.0	188.0	160.6	143.7	133.7	126.0
52.5°	269.4	311.8	341.2	326.2	265.9	206.8	168.0	145.1	131.0	122.3	115.5
55°	237.6	275.3	296.0	273.2	217.0	172.0	142.0	123.9	113.4	106.1	100.2
57.5°	206.3	237.5	250.4	224.0	178.7	142.6	120.1	106.6	96.1	90.9	87.8
60°	186.7	213.3	222.4	193.2	155.3	124.8	106.4	93.8	86.1	82.7	79.6
62.5°	167.5	189.1	192.9	166.2	135.5	109.2	93.4	82.8	77.7	74.4	71.5
65°	138.9	154.5	152.8	131.3	107.2	86.7	75.2	68.7	64.8	60.2	55.1
67.5°	114.4	123.9	118.2	102.1	81.8	67.4	59.8	54.9	50.1	45.7	44.6
70°	98.8	104.3	98.3	83.5	67.1	56.5	50.5	44.6	41.7	40.8	38.9
72.5°	83.9	85.9	79.3	66.6	54.6	46.8	40.8	37.6	36.0	35.2	34.1
75°	63.0	61.6	55.9	46.0	37.9	32.6	30.8	29.6	28.5	27.7	27.1
77.5°	44.2	42.2	37.1	30.6	26.4	23.9	22.7	22.1	21.7	21.2	20.6
80°	33.3	31.8	26.8	21.8	20.1	18.8	18.2	17.4	17.4	17.0	16.4
82.5°	24.3	22.7	18.3	16.1	15.1	14.3	13.8	13.4	13.2	13.3	12.8
85°	12.8	10.3	9.1	8.7	8.1	7.7	7.9	7.5	7.5	7.5	7.3
87.5°	4.5	4.2	4.5	4.9	5.7	6.6	7.3	8.2	9.3	9.0	9.1
90°	3.3	5.7	8.1	10.5	13.9	18.4	22.7	27.2	31.6	31.2	30.8
92.5°	17.8	19.6	21.4	23.2	24.5	25.6	26.7	27.6	28.7	28.8	28.9
95°	49.0	51.0	53.0	55.0	56.2	56.6	57.0	57.4	57.8	57.8	57.8
97.5°	87.6	89.3	91.1	92.8	94.2	94.9	95.7	96.4	97.2	97.2	97.2
100°	116.3	117.9	119.5	121.1	122.3	122.8	123.4	124.0	124.7	124.7	124.7
102.5°	146.3	147.6	148.9	150.2	151.2	151.9	152.8	153.5	154.3	154.4	154.6
105°	194.7	195.4	196.0	196.6	197.1	197.5	197.9	198.3	198.7	199.1	199.5
107.5°	244.6	245.4	246.3	247.2	247.6	247.6	247.6	247.6	247.6	247.8	248.0
110°	276.7	277.9	279.1	280.3	280.9	280.9	280.9	280.9	280.9	280.9	280.9





TEST NUMBER: P331774-940

CATALOG NUMBER: S122RDIW-S290D970U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	311.4	312.5	313.8	315.0	315.5	315.3	315.1	315.0	314.9	314.3	313.9
115°	362.5	363.6	364.9	366.0	366.5	366.0	365.7	365.2	364.9	364.7	364.4
117.5°	413.8	415.4	417.1	418.7	418.8	417.8	416.6	415.5	414.4	413.9	413.4
120°	447.8	449.4	451.0	452.6	452.6	451.0	449.4	447.8	446.2	446.2	446.2
122.5°	479.2	481.1	483.0	484.9	485.4	484.2	483.1	482.0	480.8	480.4	479.9
125°	527.4	529.2	531.1	532.9	533.5	532.9	532.3	531.6	531.1	530.5	529.9
127.5°	575.1	577.4	579.7	581.9	582.7	582.0	581.3	580.6	579.9	579.1	578.4
130°	605.0	607.6	610.3	612.9	613.9	613.6	613.1	612.8	612.3	612.0	611.5
132.5°	637.8	639.9	642.0	644.2	645.2	645.3	645.4	645.5	645.6	644.7	643.8
135°	682.3	684.5	686.7	688.9	690.2	690.6	691.0	691.4	691.8	691.6	691.4
137.5°	728.7	730.5	732.3	734.1	735.3	735.8	736.3	736.8	737.4	737.2	737.0
140°	756.9	758.7	760.5	762.2	763.7	764.7	765.7	766.7	767.7	767.7	767.7
142.5°	785.8	787.6	789.3	791.2	792.5	793.1	793.8	794.5	795.1	795.3	795.5
145°	826.9	828.3	829.7	831.2	832.4	833.7	834.8	836.1	837.2	837.4	837.7
147.5°	864.2	865.9	867.5	869.2	870.5	871.3	872.1	872.9	873.7	874.1	874.6
150°	889.0	890.2	891.4	892.6	893.7	894.5	895.3	896.1	896.9	897.4	898.0
152.5°	911.4	912.7	913.8	915.1	916.1	917.1	918.0	919.0	920.0	920.7	921.5
155°	944.4	945.0	945.7	946.2	946.8	947.4	948.1	948.6	949.2	950.2	951.3
157.5°	972.9	973.3	973.7	974.1	974.6	974.9	975.3	975.6	976.0	977.3	978.7
160°	990.2	990.7	991.0	991.5	991.8	992.0	992.2	992.4	992.6	993.8	995.0
162.5°	1005.8	1005.9	1006.0	1006.1	1006.2	1006.5	1006.7	1006.8	1007.0	1008.4	1009.8
165°	1026.7	1026.5	1026.3	1026.1	1026.0	1026.0	1026.0	1026.0	1026.0	1027.4	1028.9
167.5°	1044.0	1043.4	1042.8	1042.2	1041.9	1041.9	1041.8	1041.8	1041.7	1043.1	1044.6
170°	1053.4	1052.8	1052.2	1051.6	1051.2	1051.0	1050.8	1050.6	1050.4	1051.8	1053.2
172.5°	1059.9	1059.3	1058.7	1058.1	1057.7	1057.5	1057.3	1057.1	1056.9	1058.3	1059.7
175°	1067.8	1067.3	1066.7	1066.0	1065.5	1065.1	1064.7	1064.3	1063.9	1065.3	1066.8
177.5°	1071.2	1070.8	1070.2	1069.8	1069.3	1069.1	1068.7	1068.4	1068.1	1069.1	1070.1
180°	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2



TEST NUMBER: P331774-940

CATALOG NUMBER: S122RDIW-S290D970U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	582.9	582.9	582.9	582.9	582.9	582.9	582.9
2.5°	603.3	605.5	606.5	606.5	607.6	607.1	606.6
5°	638.0	641.9	642.7	646.3	649.0	648.2	648.5
7.5°	672.5	678.7	684.8	687.6	688.0	689.6	690.3
10°	693.8	698.8	708.3	706.9	714.0	718.1	711.4
12.5°	714.2	721.0	727.6	729.4	733.4	734.8	732.1
15°	732.6	736.3	736.6	735.7	736.9	735.8	732.0
17.5°	715.4	709.4	697.5	691.8	687.3	680.6	678.0
20°	686.9	669.4	649.2	641.1	631.6	613.0	617.4
22.5°	625.3	605.5	585.1	561.5	550.2	532.5	531.5
25°	529.5	495.3	457.5	431.2	415.8	398.2	390.5
27.5°	411.7	368.5	337.7	322.1	307.8	293.9	293.3
30°	334.2	301.8	277.9	264.6	255.8	249.9	251.2
32.5°	281.7	259.5	243.3	232.3	225.9	221.4	221.3
35°	230.3	215.1	204.7	200.1	195.5	192.3	192.4
37.5°	197.1	188.0	182.2	177.1	174.2	172.5	171.7
40°	180.0	172.5	168.1	165.1	162.6	160.4	160.0
42.5°	166.7	160.4	156.0	153.6	151.3	149.7	149.4
45°	147.8	142.8	138.8	136.1	135.1	133.7	133.7
47.5°	131.5	126.5	123.4	121.7	120.0	119.0	119.0
50°	120.6	116.6	113.9	112.8	111.4	110.8	110.6
52.5°	110.7	107.7	105.8	105.0	104.4	103.7	103.8
55°	97.2	95.6	94.8	94.2	93.2	91.9	92.7
57.5°	86.0	84.5	82.4	80.4	79.5	78.6	79.0
60°	78.0	75.2	72.3	70.1	69.5	67.7	67.7
62.5°	67.9	63.9	60.5	59.2	58.6	57.8	57.6
65°	52.3	50.6	49.8	49.0	48.6	48.6	48.2
67.5°	43.3	42.6	41.7	41.6	41.2	41.0	40.9
70°	38.3	37.5	37.1	36.8	36.5	36.6	36.0
72.5°	33.4	32.8	32.7	32.2	31.9	31.9	31.5
75°	26.3	26.3	26.1	25.9	25.5	25.3	25.5
77.5°	20.2	20.3	20.0	19.9	19.9	19.9	19.7
80°	16.2	16.4	16.2	16.0	15.8	16.0	15.8
82.5°	12.8	12.5	12.5	12.4	12.4	12.3	12.2
85°	7.3	7.5	7.3	7.1	7.1	7.1	7.3
87.5°	8.8	8.7	8.7	8.7	8.8	8.8	8.7
90°	30.4	30.0	29.9	30.1	30.3	30.5	30.7
92.5°	29.0	29.1	29.1	29.2	29.2	29.2	29.2
95°	57.8	57.8	57.6	57.2	56.8	56.4	56.0
97.5°	97.2	97.2	97.2	97.1	97.1	97.0	97.0
100°	124.7	124.7	124.6	124.3	124.1	123.9	123.8
102.5°	154.7	154.9	154.9	154.7	154.4	154.3	154.1
105°	199.9	200.3	200.5	200.5	200.5	200.5	200.5
107.5°	248.2	248.3	247.9	247.0	246.0	245.1	244.2
110°	280.9	280.9	280.6	280.0	279.4	278.7	278.2



TEST NUMBER: P331774-940

CATALOG NUMBER: S122RDIW-S290D970U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	313.4	312.9	312.5	312.0	311.6	311.1	310.7
115°	364.3	364.1	363.6	363.1	362.5	361.9	361.2
117.5°	413.0	412.4	411.9	411.3	410.7	410.1	409.5
120°	446.2	446.2	445.9	445.2	444.7	444.1	443.4
122.5°	479.4	478.9	478.5	478.0	477.6	477.2	476.7
125°	529.2	528.7	528.2	528.1	527.9	527.6	527.4
127.5°	577.7	576.9	576.2	575.6	575.0	574.4	573.7
130°	611.2	610.7	610.1	609.3	608.5	607.7	606.9
132.5°	642.9	642.0	641.3	640.7	640.0	639.4	638.7
135°	691.3	691.0	690.6	690.0	689.4	688.8	688.2
137.5°	736.9	736.7	736.2	735.4	734.6	733.8	733.0
140°	767.7	767.7	767.3	766.5	765.7	764.9	764.1
142.5°	795.7	795.8	795.5	794.7	793.9	793.1	792.3
145°	837.9	838.0	837.8	837.0	836.2	835.4	834.6
147.5°	875.0	875.5	875.3	874.6	873.8	873.1	872.3
150°	898.7	899.3	899.3	898.7	898.0	897.4	896.9
152.5°	922.3	923.0	923.0	922.3	921.5	920.7	920.0
155°	952.3	953.2	953.4	952.9	952.3	951.6	951.0
157.5°	980.1	981.4	981.6	980.7	979.7	978.7	977.8
160°	996.2	997.4	997.6	996.8	996.0	995.2	994.4
162.5°	1011.1	1012.5	1012.7	1011.7	1010.8	1009.8	1008.9
165°	1030.2	1031.6	1031.8	1030.8	1029.8	1028.9	1027.8
167.5°	1046.0	1047.3	1047.5	1046.5	1045.4	1044.4	1043.4
170°	1054.6	1056.1	1056.1	1054.9	1053.7	1052.5	1051.3
172.5°	1061.1	1062.5	1062.7	1061.4	1060.2	1059.0	1057.8
175°	1068.2	1069.5	1069.7	1068.4	1067.3	1066.0	1064.9
177.5°	1070.9	1071.9	1071.9	1070.9	1070.1	1069.1	1068.1
180°	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2

(END OF REPORT)