

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332096-830

Luminaire Tested: **S123DIW-S340D755U830-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332096-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIW-S340D755U830-4F0-1E-UDD-A  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 340 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 755 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4217.4 lumens  
Efficiency: N/A  
Efficacy: 138.7 lumens/watt  
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 30.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332096-830

CATALOG NUMBER: S123DIW-S340D755U830-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P332096-830

CATALOG NUMBER: S123DIW-S340D755U830-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40	32					32			
1	94	90	86	83	85	81	78	75	65	63	61	50	48	47	36	35	34	28					28			
2	86	79	73	68	77	71	66	62	57	53	50	44	41	39	32	30	29	23					23			
3	78	69	62	57	70	63	57	52	50	46	42	39	36	33	28	26	25	20					20			
4	72	61	54	48	64	55	49	44	45	40	36	35	31	29	25	23	21	17					17			
5	66	54	47	41	59	49	43	38	40	35	31	31	28	25	23	20	19	15					15			
6	60	49	41	35	54	44	38	33	36	31	27	28	24	22	21	18	16	13					13			
7	56	44	36	31	50	40	33	29	32	27	24	25	22	19	19	16	15	12					12			
8	52	40	32	27	46	36	30	25	30	25	21	23	20	17	17	15	13	11					11			
9	48	36	29	24	43	33	27	22	27	22	19	21	18	15	16	14	12	10					10			
10	45	33	26	21	40	30	24	20	25	20	17	20	16	14	15	12	11	9					9			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	4878	4878	4878	4878
5°	5817	4900	4341	4900
10°	7282	4875	3922	4875
15°	8931	4835	3651	4835
20°	10639	4774	3477	4774
25°	11297	4700	3437	4700
30°	9684	4645	3455	4645
35°	6734	4568	3491	4568
40°	5073	4477	3481	4477
45°	4211	4341	3436	4341
50°	3773	4068	3404	4068
55°	3526	3772	3363	3772
60°	3309	3460	3328	3460
65°	3110	3156	3222	3156
70°	2917	2807	3068	2807
75°	2612	2458	2816	2458
80°	2287	2015	2424	2015
85°	1791	1470	1630	1470



TEST NUMBER: P332096-830

CATALOG NUMBER: S123DIW-S340D755U830-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	44.6	1.1
10°-20°	143.2	3.4
20°-30°	240.3	5.7
30°-40°	272.0	6.5
40°-50°	244.0	5.8
50°-60°	196.9	4.7
60°-70°	137.2	3.3
70°-80°	72.1	1.7
80°-90°	20.2	0.5
90°-100°	33.9	0.8
100°-110°	161.8	3.8
110°-120°	388.6	9.2
120°-130°	494.8	11.7
130°-140°	528.7	12.5
140°-150°	494.4	11.7
150°-160°	398.8	9.5
160°-170°	257.4	6.1
170°-180°	88.7	2.1
0°-30°	428.1	10.1
0°-40°	700.1	16.6
0°-60°	1140.9	27.1
0°-90°	1370.5	32.5
90°-120°	584.3	13.9
90°-150°	2102.1	49.8
90°-180°	2847.0	67.5
0°-180°	4217.4	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	453	453	453	453	453	
5°	538	454	402	454	538	56
15°	801	434	328	434	801	231
25°	951	396	289	396	951	417
35°	512	348	266	348	512	333
45°	277	285	226	285	277	219
55°	188	201	179	201	188	169
65°	122	124	126	124	122	122
75°	63	59	68	59	63	67
85°	14	12	13	12	14	18
90°	21	1	21	1	21	10
95°	26	42	26	42	26	22
105°	30	207	30	207	30	70
115°	408	388	408	388	408	377
125°	558	547	558	547	558	498
135°	687	680	687	680	687	530
145°	793	785	793	785	793	495
155°	864	865	864	865	864	398
165°	910	912	910	912	910	257
175°	930	934	930	934	930	89
180°	934	934	934	934	934	



TEST NUMBER: P332096-830

CATALOG NUMBER: S123DIW-S340D755U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2
2.5°	481.0	480.6	479.8	480.4	479.0	477.1	476.9	475.1	470.0	469.8	468.3
5°	538.4	536.7	536.4	536.2	533.1	529.0	521.0	520.4	509.8	504.6	498.2
7.5°	612.8	613.7	610.5	607.8	598.3	592.1	583.6	572.8	559.9	546.7	538.0
10°	666.2	673.4	664.5	658.3	652.6	641.9	629.3	613.7	598.1	579.9	566.1
12.5°	723.5	727.0	725.2	719.4	710.6	694.2	672.0	654.8	640.5	610.1	597.9
15°	801.4	814.8	806.3	786.6	786.9	771.4	742.4	710.6	693.6	667.0	630.8
17.5°	884.6	886.2	882.6	866.1	855.2	833.7	806.9	776.5	742.2	710.0	671.6
20°	928.8	927.5	919.8	911.3	892.4	875.7	846.5	812.5	768.5	736.9	694.9
22.5°	953.4	951.2	947.5	940.4	924.7	906.8	880.5	843.4	801.5	758.0	709.5
25°	951.2	954.0	954.5	952.5	947.1	936.3	915.7	886.0	844.3	788.2	737.8
27.5°	865.2	869.2	880.9	891.4	903.0	914.8	913.2	898.5	867.6	819.3	757.5
30°	779.1	770.2	792.0	819.4	838.1	871.1	889.5	890.6	873.3	831.8	771.6
32.5°	659.6	669.3	678.9	712.7	753.5	790.4	827.2	856.7	860.1	832.5	779.9
35°	512.5	524.6	542.2	559.7	603.6	641.4	706.0	762.1	806.9	812.8	780.6
37.5°	413.0	419.0	430.1	447.7	476.4	521.2	571.1	642.2	707.1	755.4	757.4
40°	361.0	362.8	375.2	388.6	411.9	448.8	493.8	556.7	634.3	701.8	729.9
42.5°	322.0	325.8	331.2	344.0	362.6	390.3	432.2	484.1	555.3	632.9	687.9
45°	276.6	281.1	284.4	292.9	306.1	324.8	353.9	401.4	455.6	535.7	609.7
47.5°	246.8	247.0	249.5	256.0	264.9	279.0	299.6	330.1	379.8	444.9	520.8
50°	225.3	228.8	229.7	234.7	241.8	252.0	269.2	295.1	335.9	393.0	462.9
52.5°	210.2	211.2	213.7	217.4	223.5	231.5	246.4	266.6	298.7	347.4	411.6
55°	187.9	187.9	190.4	193.2	196.7	204.0	213.9	228.8	253.2	291.0	344.1
57.5°	167.4	168.5	170.2	171.1	174.1	178.9	187.1	198.5	216.6	245.7	287.9
60°	153.7	155.7	155.4	157.2	159.9	163.6	170.6	179.8	196.0	219.3	255.0
62.5°	141.8	141.7	141.6	143.7	146.3	149.9	154.5	162.4	176.3	196.9	227.2
65°	122.1	121.7	123.2	124.5	125.4	128.0	131.5	138.6	147.8	163.2	186.6
67.5°	104.6	103.3	104.2	104.6	106.1	108.2	111.5	115.8	123.1	135.4	153.2
70°	92.7	91.5	91.3	91.8	93.1	94.6	97.1	101.2	108.0	117.9	130.8
72.5°	80.4	79.6	79.6	80.6	81.2	82.2	83.9	87.7	93.1	100.6	112.6
75°	62.8	62.8	62.8	63.1	63.7	64.6	65.9	67.9	72.0	77.3	85.4
77.5°	47.0	47.0	46.8	46.8	47.7	48.1	48.4	50.2	52.6	56.1	62.0
80°	36.9	35.8	36.2	36.9	37.3	37.5	38.2	38.6	40.6	42.6	46.8
82.5°	27.4	26.5	26.6	27.6	27.7	27.9	28.6	29.1	29.9	31.7	33.9
85°	14.5	14.5	14.7	14.7	14.9	14.7	15.4	15.6	15.6	16.7	18.0
87.5°	9.4	9.0	9.1	9.2	9.0	9.0	9.1	9.2	9.2	9.3	9.0
90°	20.8	20.5	20.2	19.9	19.6	19.1	18.5	17.9	17.2	16.7	14.6
92.5°	23.0	22.8	22.6	22.4	22.2	21.7	20.7	19.7	18.8	17.7	16.2
95°	26.4	26.4	26.4	26.4	26.4	25.8	24.7	23.7	22.6	21.5	19.8
97.5°	28.6	28.5	28.3	28.1	28.0	27.2	26.0	24.8	23.6	22.3	33.5
100°	29.1	28.9	28.8	28.7	28.6	27.8	26.6	25.4	24.1	22.9	46.9
102.5°	29.7	29.4	29.1	28.8	28.6	30.3	34.2	38.0	41.8	45.6	71.9
105°	30.5	30.3	29.9	29.6	29.3	42.8	70.0	97.4	124.6	151.9	165.8
107.5°	95.9	116.4	137.0	157.5	178.1	198.4	218.4	238.4	258.4	278.4	276.3
110°	190.8	212.7	234.8	256.8	278.9	292.5	297.6	302.7	307.7	312.8	311.1



TEST NUMBER: P332096-830

CATALOG NUMBER: S123DIW-S340D755U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	327.3	331.9	336.6	341.2	345.8	348.2	348.1	348.0	347.9	347.8	346.1
115°	407.8	407.2	406.6	406.0	405.4	404.3	402.7	401.2	399.6	398.1	396.7
117.5°	453.1	452.9	452.8	452.7	452.5	451.9	450.6	449.4	448.2	447.0	446.2
120°	484.1	484.1	484.1	484.1	484.1	483.5	482.3	481.1	479.8	478.5	478.2
122.5°	514.6	514.5	514.3	514.3	514.2	513.7	512.7	511.9	511.0	510.2	509.6
125°	557.6	557.3	557.0	556.8	556.4	556.1	555.8	555.4	555.2	554.9	554.2
127.5°	599.0	599.3	599.6	599.9	600.2	600.1	599.6	599.2	598.6	598.1	597.4
130°	625.6	625.9	626.2	626.5	626.9	626.7	626.0	625.5	624.8	624.2	623.6
132.5°	650.0	650.4	650.9	651.3	651.8	651.7	651.0	650.4	649.8	649.2	648.7
135°	687.3	687.8	688.2	688.7	689.2	689.2	688.7	688.2	687.8	687.3	686.7
137.5°	722.5	722.7	723.0	723.4	723.7	723.5	722.7	722.0	721.2	720.5	720.2
140°	743.5	743.9	744.1	744.4	744.8	744.6	743.9	743.4	742.7	742.2	741.7
142.5°	762.9	763.4	763.8	764.2	764.7	764.6	764.1	763.6	763.2	762.7	762.2
145°	792.8	792.8	792.8	792.8	792.8	792.6	792.3	792.0	791.6	791.4	791.1
147.5°	814.9	815.7	816.3	817.1	817.7	818.0	817.7	817.4	817.1	816.7	816.4
150°	831.6	832.1	832.5	833.0	833.5	833.5	833.2	832.9	832.6	832.3	832.0
152.5°	844.9	845.6	846.3	847.1	847.7	847.8	847.3	846.7	846.1	845.6	845.5
155°	863.5	864.4	865.3	866.3	867.2	867.3	866.5	865.7	865.0	864.2	864.0
157.5°	879.2	880.4	881.6	882.8	884.0	884.1	883.2	882.3	881.4	880.4	880.6
160°	889.2	890.2	891.4	892.4	893.5	893.5	892.7	891.7	890.8	889.9	890.0
162.5°	898.6	899.6	900.5	901.4	902.4	902.4	901.4	900.3	899.3	898.1	898.3
165°	909.9	911.1	912.1	913.2	914.3	914.2	912.9	911.7	910.5	909.3	909.5
167.5°	918.1	919.4	920.6	921.9	923.1	923.1	921.9	920.6	919.4	918.1	918.1
170°	923.1	924.4	925.6	926.9	928.1	928.1	926.9	925.6	924.4	923.1	923.1
172.5°	926.0	927.3	928.7	930.0	931.3	931.4	930.2	929.0	927.7	926.5	926.3
175°	930.1	931.3	932.6	933.8	935.0	935.1	934.1	932.9	931.9	930.8	930.7
177.5°	931.3	932.6	933.8	935.0	936.2	936.4	935.4	934.4	933.4	932.5	932.4
180°	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6



TEST NUMBER: P332096-830

CATALOG NUMBER: S123DIW-S340D755U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2
2.5°	467.2	465.9	464.5	462.0	459.9	456.9	456.0	455.0	451.8	449.0	446.9
5°	495.8	490.5	482.9	475.8	470.1	462.4	458.1	453.5	446.9	440.9	436.1
7.5°	525.7	515.3	503.3	490.5	478.4	466.8	457.5	449.1	439.9	431.2	424.3
10°	549.4	534.4	517.7	499.7	484.4	469.5	456.9	446.0	434.1	423.8	415.2
12.5°	576.5	554.3	531.3	509.4	491.3	470.5	455.3	441.4	427.9	415.6	406.0
15°	608.4	580.3	553.1	523.0	495.4	469.5	451.5	433.9	418.3	405.6	393.2
17.5°	637.6	605.8	569.9	533.3	499.9	469.2	444.0	424.1	404.6	389.1	376.8
20°	654.1	617.9	577.3	539.3	502.4	468.2	440.5	416.8	395.7	379.2	365.4
22.5°	668.4	625.9	583.9	543.3	502.2	465.3	433.9	409.5	386.7	370.6	355.9
25°	683.2	632.4	590.2	542.6	496.7	458.5	423.4	395.7	372.9	353.9	338.8
27.5°	695.8	632.0	581.9	530.7	488.0	449.7	412.2	382.5	358.3	337.7	322.3
30°	704.2	632.8	573.3	522.6	479.6	440.1	403.6	373.7	348.3	327.4	312.9
32.5°	709.5	632.3	565.4	511.3	466.2	431.2	394.3	363.4	337.1	316.7	302.7
35°	712.6	628.4	551.8	488.1	444.7	410.6	379.7	347.6	320.2	301.0	285.2
37.5°	706.3	620.3	536.0	465.7	418.1	384.7	358.5	331.3	305.0	284.0	270.3
40°	696.7	615.0	523.7	449.9	399.8	367.6	345.4	318.6	292.7	272.7	260.0
42.5°	678.3	604.4	510.2	432.3	380.9	348.6	328.2	305.8	281.3	262.5	249.8
45°	633.3	581.0	489.8	406.0	352.9	319.5	301.5	285.2	263.1	244.9	233.8
47.5°	570.8	545.9	460.5	378.2	323.6	291.5	272.8	259.8	243.6	228.8	218.3
50°	527.4	517.1	440.7	359.2	304.2	272.7	254.7	242.9	231.2	216.5	206.9
52.5°	477.4	483.7	417.5	339.6	284.3	253.4	236.5	227.1	216.5	204.3	196.0
55°	406.9	429.9	377.5	306.5	254.7	225.3	209.2	201.0	194.7	185.8	178.5
57.5°	340.9	370.2	334.1	272.5	225.6	200.3	184.9	175.9	171.9	167.2	161.5
60°	301.7	330.6	303.2	249.7	206.2	182.0	168.4	160.7	156.7	153.4	148.6
62.5°	266.7	296.1	273.1	226.5	187.0	164.7	152.8	145.2	142.2	140.5	136.4
65°	218.7	243.9	228.6	190.4	159.7	139.9	129.1	123.9	121.0	120.4	117.7
67.5°	178.0	197.2	186.1	157.9	133.7	116.7	107.5	103.0	100.9	100.6	98.6
70°	151.3	169.3	160.7	135.3	114.4	101.0	93.1	89.2	87.8	87.7	86.5
72.5°	130.5	143.1	136.3	115.1	99.0	86.8	81.0	76.8	75.4	75.7	74.9
75°	96.6	106.0	102.1	87.4	74.5	66.5	61.7	59.1	57.8	58.4	57.5
77.5°	69.6	75.5	71.9	61.7	53.7	48.1	44.5	42.9	41.7	41.7	41.3
80°	52.5	56.0	54.0	47.9	41.3	36.5	33.6	32.5	31.9	31.6	31.4
82.5°	37.4	40.3	38.0	33.8	29.3	26.4	24.8	23.4	22.9	23.0	22.8
85°	18.9	20.0	19.1	16.5	14.7	13.4	12.5	11.9	11.4	11.6	11.2
87.5°	9.0	8.8	7.9	6.8	6.1	5.3	5.0	4.3	4.3	4.6	4.7
90°	12.6	10.7	8.7	6.9	5.3	3.8	2.3	0.7	2.3	3.8	5.3
92.5°	14.7	13.2	11.7	11.2	11.6	12.1	12.4	12.9	12.4	12.1	11.6
95°	18.1	16.4	14.7	17.1	23.4	29.7	36.0	42.3	36.0	29.7	23.4
97.5°	44.5	55.6	66.7	73.7	76.5	79.4	82.2	85.0	82.2	79.4	76.5
100°	71.0	95.0	119.0	129.5	126.5	123.4	120.3	117.3	120.3	123.4	126.5
102.5°	98.1	124.4	150.7	162.7	160.5	158.3	156.1	153.8	156.1	158.3	160.5
105°	179.6	193.5	207.4	213.5	211.8	210.1	208.4	206.7	208.4	210.1	211.8
107.5°	274.0	271.8	269.7	267.9	266.6	265.1	263.8	262.4	263.8	265.1	266.6
110°	309.4	307.7	306.0	304.5	303.3	302.1	300.9	299.6	300.9	302.1	303.3





TEST NUMBER: P332096-830

CATALOG NUMBER: S123DIW-S340D755U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	344.4	342.7	341.0	339.6	338.5	337.3	336.2	335.2	336.2	337.3	338.5
115°	395.3	394.0	392.6	391.4	390.5	389.6	388.6	387.7	388.6	389.6	390.5
117.5°	445.5	444.8	444.1	443.2	442.1	440.9	439.8	438.7	439.8	440.9	442.1
120°	477.7	477.2	476.7	475.8	474.4	473.1	471.6	470.2	471.6	473.1	474.4
122.5°	509.1	508.4	507.8	507.0	505.9	504.7	503.6	502.5	503.6	504.7	505.9
125°	553.6	553.0	552.4	551.5	550.3	549.0	547.8	546.6	547.8	549.0	550.3
127.5°	596.6	596.0	595.2	594.2	593.0	591.7	590.5	589.3	590.5	591.7	593.0
130°	623.0	622.4	621.8	620.9	619.6	618.4	617.2	615.9	617.2	618.4	619.6
132.5°	648.2	647.7	647.2	646.4	645.1	643.9	642.6	641.4	642.6	643.9	645.1
135°	686.1	685.5	684.9	684.1	683.2	682.2	681.4	680.4	681.4	682.2	683.2
137.5°	719.8	719.4	719.2	718.4	717.2	716.0	714.8	713.7	714.8	716.0	717.2
140°	741.2	740.7	740.3	739.6	738.7	737.7	736.8	735.8	736.8	737.7	738.7
142.5°	761.8	761.3	760.8	760.2	759.2	758.3	757.3	756.4	757.3	758.3	759.2
145°	790.8	790.4	790.1	789.5	788.3	787.3	786.2	785.1	786.2	787.3	788.3
147.5°	816.1	815.9	815.5	815.0	814.3	813.6	812.8	812.2	812.8	813.6	814.3
150°	831.7	831.4	831.0	830.7	830.2	829.7	829.2	828.9	829.2	829.7	830.2
152.5°	845.3	845.1	844.9	844.7	844.4	844.2	844.0	843.8	844.0	844.2	844.4
155°	863.9	863.7	863.6	863.7	863.9	864.3	864.6	864.9	864.6	864.3	863.9
157.5°	880.7	880.9	881.1	881.2	881.2	881.2	881.3	881.3	881.3	881.2	881.2
160°	890.1	890.3	890.5	890.6	890.8	891.0	891.1	891.3	891.1	891.0	890.8
162.5°	898.5	898.6	898.8	899.1	899.5	899.8	900.3	900.7	900.3	899.8	899.5
165°	909.6	909.7	909.9	910.2	910.7	911.2	911.6	912.1	911.6	911.2	910.7
167.5°	918.1	918.1	918.1	918.5	919.1	919.7	920.3	921.0	920.3	919.7	919.1
170°	923.1	923.1	923.1	923.5	924.1	924.7	925.3	926.0	925.3	924.7	924.1
172.5°	926.2	926.1	926.0	926.3	927.1	927.7	928.5	929.3	928.5	927.7	927.1
175°	930.5	930.3	930.2	930.5	931.2	932.0	932.7	933.6	932.7	932.0	931.2
177.5°	932.2	932.1	932.0	932.2	932.8	933.4	934.1	934.6	934.1	933.4	932.8
180°	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6



TEST NUMBER: P332096-830

CATALOG NUMBER: S123DIW-S340D755U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2
2.5°	445.6	444.4	442.7	440.1	437.9	434.6	434.6	435.1	435.1	435.0	434.6
5°	432.2	428.9	424.9	420.3	415.5	410.6	409.7	407.9	406.7	405.8	404.7
7.5°	417.8	412.0	406.2	399.8	393.9	389.1	385.7	382.9	381.1	379.1	377.7
10°	408.2	401.0	394.2	387.4	379.8	373.9	370.2	367.6	365.6	363.8	363.0
12.5°	396.8	388.5	381.0	374.5	366.4	360.2	356.7	355.4	353.2	349.4	347.5
15°	380.1	372.4	363.4	353.5	349.6	342.1	337.9	335.9	334.6	331.8	330.9
17.5°	365.8	355.8	345.6	338.3	330.9	324.9	322.5	320.1	318.4	316.0	315.3
20°	354.4	345.4	336.2	328.3	320.6	314.0	312.0	310.3	308.5	307.5	306.5
22.5°	342.8	333.8	326.1	318.8	310.6	306.2	304.2	302.2	301.0	300.2	299.4
25°	326.5	318.6	310.0	303.5	296.9	294.0	292.7	291.6	290.7	289.6	289.4
27.5°	312.0	303.3	296.4	290.2	285.5	283.1	281.8	281.3	281.5	281.9	282.2
30°	301.0	293.1	287.5	282.2	277.8	275.6	275.3	275.3	276.3	276.4	276.9
32.5°	291.1	284.6	278.8	273.7	270.4	268.9	269.8	269.8	270.4	271.0	271.8
35°	276.4	270.7	266.4	261.9	259.1	259.8	260.2	260.6	261.7	263.1	263.9
37.5°	262.5	257.6	253.0	249.6	248.3	249.4	250.5	251.4	252.7	253.7	254.6
40°	252.5	248.7	244.4	241.3	241.8	242.4	243.3	244.4	245.5	246.2	247.0
42.5°	243.2	239.3	235.9	233.4	234.0	234.9	235.4	235.9	237.2	238.5	238.9
45°	229.0	225.9	222.9	221.3	221.8	222.3	222.6	223.3	224.4	225.3	225.6
47.5°	213.1	210.9	208.9	207.4	208.1	207.9	208.5	209.9	210.2	210.8	212.0
50°	202.9	201.0	198.5	198.0	198.0	198.0	198.3	200.0	200.0	201.0	201.8
52.5°	191.6	190.4	188.9	188.0	187.7	187.7	188.6	189.5	189.8	191.1	192.0
55°	175.0	173.7	172.4	171.7	171.3	171.7	173.4	173.9	175.0	175.7	176.3
57.5°	157.7	156.7	155.6	155.2	155.1	155.7	156.7	158.0	158.3	160.3	161.3
60°	146.3	144.7	143.8	143.8	143.4	145.3	145.0	147.1	147.6	148.9	150.4
62.5°	134.5	132.4	132.1	132.1	132.7	133.3	133.8	134.8	136.0	137.6	138.8
65°	115.5	114.4	115.9	115.7	115.3	116.6	116.6	117.7	119.0	120.6	123.0
67.5°	97.6	97.0	97.1	97.1	97.7	98.5	99.2	100.1	101.7	103.3	104.9
70°	85.4	86.1	85.0	85.9	86.5	86.7	87.2	88.5	90.2	91.3	93.1
72.5°	73.6	73.6	73.7	74.1	74.7	75.1	75.6	77.1	79.0	79.9	81.3
75°	56.6	56.5	57.1	57.1	58.2	58.6	59.1	59.8	61.5	62.8	63.9
77.5°	41.4	41.7	41.5	42.2	41.9	42.0	43.4	44.0	44.2	46.8	47.4
80°	31.2	31.6	31.9	32.0	32.2	31.9	33.4	34.0	34.0	35.5	36.7
82.5°	22.4	22.6	23.2	23.5	23.5	23.9	24.0	24.5	25.1	25.7	27.1
85°	11.2	11.9	12.1	11.9	12.1	11.6	12.3	12.5	12.7	12.7	12.7
87.5°	4.9	5.4	5.7	6.2	6.4	7.0	7.2	6.9	7.1	7.7	7.1
90°	6.9	8.7	10.7	12.6	14.6	16.7	17.2	17.9	18.5	19.1	19.6
92.5°	11.2	11.7	13.2	14.7	16.2	17.7	18.8	19.7	20.7	21.7	22.2
95°	17.1	14.7	16.4	18.1	19.8	21.5	22.6	23.7	24.7	25.8	26.4
97.5°	73.7	66.7	55.6	44.5	33.5	22.3	23.6	24.8	26.0	27.2	28.0
100°	129.5	119.0	95.0	71.0	46.9	22.9	24.1	25.4	26.6	27.8	28.6
102.5°	162.7	150.7	124.4	98.1	71.9	45.6	41.8	38.0	34.2	30.3	28.6
105°	213.5	207.4	193.5	179.6	165.8	151.9	124.6	97.4	70.0	42.8	29.3
107.5°	267.9	269.7	271.8	274.0	276.3	278.4	258.4	238.4	218.4	198.4	178.1
110°	304.5	306.0	307.7	309.4	311.1	312.8	307.7	302.7	297.6	292.5	278.9



TEST NUMBER: P332096-830

CATALOG NUMBER: S123DIW-S340D755U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	339.6	341.0	342.7	344.4	346.1	347.8	347.9	348.0	348.1	348.2	345.8
115°	391.4	392.6	394.0	395.3	396.7	398.1	399.6	401.2	402.7	404.3	405.4
117.5°	443.2	444.1	444.8	445.5	446.2	447.0	448.2	449.4	450.6	451.9	452.5
120°	475.8	476.7	477.2	477.7	478.2	478.5	479.8	481.1	482.3	483.5	484.1
122.5°	507.0	507.8	508.4	509.1	509.6	510.2	511.0	511.9	512.7	513.7	514.2
125°	551.5	552.4	553.0	553.6	554.2	554.9	555.2	555.4	555.8	556.1	556.4
127.5°	594.2	595.2	596.0	596.6	597.4	598.1	598.6	599.2	599.6	600.1	600.2
130°	620.9	621.8	622.4	623.0	623.6	624.2	624.8	625.5	626.0	626.7	626.9
132.5°	646.4	647.2	647.7	648.2	648.7	649.2	649.8	650.4	651.0	651.7	651.8
135°	684.1	684.9	685.5	686.1	686.7	687.3	687.8	688.2	688.7	689.2	689.2
137.5°	718.4	719.2	719.4	719.8	720.2	720.5	721.2	722.0	722.7	723.5	723.7
140°	739.6	740.3	740.7	741.2	741.7	742.2	742.7	743.4	743.9	744.6	744.8
142.5°	760.2	760.8	761.3	761.8	762.2	762.7	763.2	763.6	764.1	764.6	764.7
145°	789.5	790.1	790.4	790.8	791.1	791.4	791.6	792.0	792.3	792.6	792.8
147.5°	815.0	815.5	815.9	816.1	816.4	816.7	817.1	817.4	817.7	818.0	817.7
150°	830.7	831.0	831.4	831.7	832.0	832.3	832.6	832.9	833.2	833.5	833.5
152.5°	844.7	844.9	845.1	845.3	845.5	845.6	846.1	846.7	847.3	847.8	847.7
155°	863.7	863.6	863.7	863.9	864.0	864.2	865.0	865.7	866.5	867.3	867.2
157.5°	881.2	881.1	880.9	880.7	880.6	880.4	881.4	882.3	883.2	884.1	884.0
160°	890.6	890.5	890.3	890.1	890.0	889.9	890.8	891.7	892.7	893.5	893.5
162.5°	899.1	898.8	898.6	898.5	898.3	898.1	899.3	900.3	901.4	902.4	902.4
165°	910.2	909.9	909.7	909.6	909.5	909.3	910.5	911.7	912.9	914.2	914.3
167.5°	918.5	918.1	918.1	918.1	918.1	918.1	919.4	920.6	921.9	923.1	923.1
170°	923.5	923.1	923.1	923.1	923.1	923.1	924.4	925.6	926.9	928.1	928.1
172.5°	926.3	926.0	926.1	926.2	926.3	926.5	927.7	929.0	930.2	931.4	931.3
175°	930.5	930.2	930.3	930.5	930.7	930.8	931.9	932.9	934.1	935.1	935.0
177.5°	932.2	932.0	932.1	932.2	932.4	932.5	933.4	934.4	935.4	936.4	936.2
180°	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6



TEST NUMBER: P332096-830

CATALOG NUMBER: S123DIW-S340D755U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2
2.5°	433.4	433.2	434.4	433.6	434.4	433.2	433.4	434.6	435.0	435.1	435.1
5°	403.4	404.1	401.8	401.8	401.8	404.1	403.4	404.7	405.8	406.7	407.9
7.5°	376.6	375.7	375.8	374.6	375.8	375.7	376.6	377.7	379.1	381.1	382.9
10°	360.3	359.0	358.5	358.8	358.5	359.0	360.3	363.0	363.8	365.6	367.6
12.5°	346.8	346.6	343.7	343.7	343.7	346.6	346.8	347.5	349.4	353.2	355.4
15°	330.9	326.8	326.3	327.6	326.3	326.8	330.9	330.9	331.8	334.6	335.9
17.5°	315.0	312.7	312.9	312.3	312.9	312.7	315.0	315.3	316.0	318.4	320.1
20°	306.5	305.2	305.0	303.5	305.0	305.2	306.5	306.5	307.5	308.5	310.3
22.5°	298.8	298.4	298.5	296.8	298.5	298.4	298.8	299.4	300.2	301.0	302.2
25°	289.2	290.3	289.4	289.4	289.4	290.3	289.2	289.4	289.6	290.7	291.6
27.5°	282.7	282.7	282.2	282.2	282.2	282.7	282.7	282.2	281.9	281.5	281.3
30°	277.8	277.6	278.0	278.0	278.0	277.6	277.8	276.9	276.4	276.3	275.3
32.5°	272.9	273.1	273.2	273.4	273.2	273.1	272.9	271.8	271.0	270.4	269.8
35°	265.2	265.5	266.2	265.7	266.2	265.5	265.2	263.9	263.1	261.7	260.6
37.5°	255.0	256.0	255.8	256.1	255.8	256.0	255.0	254.6	253.7	252.7	251.4
40°	247.2	247.9	247.7	247.7	247.7	247.9	247.2	247.0	246.2	245.5	244.4
42.5°	239.3	239.8	239.2	238.9	239.2	239.8	239.3	238.9	238.5	237.2	235.9
45°	226.4	225.9	226.6	225.7	226.6	225.9	226.4	225.6	225.3	224.4	223.3
47.5°	211.9	212.4	212.5	213.2	212.5	212.4	211.9	212.0	210.8	210.2	209.9
50°	202.3	203.6	203.6	203.3	203.6	203.6	202.3	201.8	201.0	200.0	200.0
52.5°	192.7	193.3	194.3	194.2	194.3	193.3	192.7	192.0	191.1	189.8	189.5
55°	178.0	178.5	179.0	179.2	179.0	178.5	178.0	176.3	175.7	175.0	173.9
57.5°	162.9	162.7	163.7	164.1	163.7	162.7	162.9	161.3	160.3	158.3	158.0
60°	152.1	152.1	153.9	154.6	153.9	152.1	152.1	150.4	148.9	147.6	147.1
62.5°	140.7	141.5	143.2	142.3	143.2	141.5	140.7	138.8	137.6	136.0	134.8
65°	124.0	125.8	125.6	126.5	125.6	125.8	124.0	123.0	120.6	119.0	117.7
67.5°	106.6	107.7	109.3	109.4	109.3	107.7	106.6	104.9	103.3	101.7	100.1
70°	94.8	96.0	96.8	97.5	96.8	96.0	94.8	93.1	91.3	90.2	88.5
72.5°	83.4	84.0	86.1	85.2	86.1	84.0	83.4	81.3	79.9	79.0	77.1
75°	65.4	67.0	68.3	67.7	68.3	67.0	65.4	63.9	62.8	61.5	59.8
77.5°	48.4	50.0	50.5	50.0	50.5	50.0	48.4	47.4	46.8	44.2	44.0
80°	38.2	38.0	39.3	39.1	39.3	38.0	38.2	36.7	35.5	34.0	34.0
82.5°	28.0	27.8	28.4	28.6	28.4	27.8	28.0	27.1	25.7	25.1	24.5
85°	13.6	14.2	13.4	13.2	13.4	14.2	13.6	12.7	12.7	12.7	12.5
87.5°	7.2	7.2	7.1	7.0	7.1	7.2	7.2	7.1	7.7	7.1	6.9
90°	19.9	20.2	20.5	20.8	20.5	20.2	19.9	19.6	19.1	18.5	17.9
92.5°	22.4	22.6	22.8	23.0	22.8	22.6	22.4	22.2	21.7	20.7	19.7
95°	26.4	26.4	26.4	26.4	26.4	26.4	26.4	26.4	25.8	24.7	23.7
97.5°	28.1	28.3	28.5	28.6	28.5	28.3	28.1	28.0	27.2	26.0	24.8
100°	28.7	28.8	28.9	29.1	28.9	28.8	28.7	28.6	27.8	26.6	25.4
102.5°	28.8	29.1	29.4	29.7	29.4	29.1	28.8	28.6	30.3	34.2	38.0
105°	29.6	29.9	30.3	30.5	30.3	29.9	29.6	29.3	42.8	70.0	97.4
107.5°	157.5	137.0	116.4	95.9	116.4	137.0	157.5	178.1	198.4	218.4	238.4
110°	256.8	234.8	212.7	190.8	212.7	234.8	256.8	278.9	292.5	297.6	302.7



TEST NUMBER: P332096-830

CATALOG NUMBER: S123DIW-S340D755U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	341.2	336.6	331.9	327.3	331.9	336.6	341.2	345.8	348.2	348.1	348.0
115°	406.0	406.6	407.2	407.8	407.2	406.6	406.0	405.4	404.3	402.7	401.2
117.5°	452.7	452.8	452.9	453.1	452.9	452.8	452.7	452.5	451.9	450.6	449.4
120°	484.1	484.1	484.1	484.1	484.1	484.1	484.1	484.1	483.5	482.3	481.1
122.5°	514.3	514.3	514.5	514.6	514.5	514.3	514.3	514.2	513.7	512.7	511.9
125°	556.8	557.0	557.3	557.6	557.3	557.0	556.8	556.4	556.1	555.8	555.4
127.5°	599.9	599.6	599.3	599.0	599.3	599.6	599.9	600.2	600.1	599.6	599.2
130°	626.5	626.2	625.9	625.6	625.9	626.2	626.5	626.9	626.7	626.0	625.5
132.5°	651.3	650.9	650.4	650.0	650.4	650.9	651.3	651.8	651.7	651.0	650.4
135°	688.7	688.2	687.8	687.3	687.8	688.2	688.7	689.2	689.2	688.7	688.2
137.5°	723.4	723.0	722.7	722.5	722.7	723.0	723.4	723.7	723.5	722.7	722.0
140°	744.4	744.1	743.9	743.5	743.9	744.1	744.4	744.8	744.6	743.9	743.4
142.5°	764.2	763.8	763.4	762.9	763.4	763.8	764.2	764.7	764.6	764.1	763.6
145°	792.8	792.8	792.8	792.8	792.8	792.8	792.8	792.8	792.6	792.3	792.0
147.5°	817.1	816.3	815.7	814.9	815.7	816.3	817.1	817.7	818.0	817.7	817.4
150°	833.0	832.5	832.1	831.6	832.1	832.5	833.0	833.5	833.5	833.2	832.9
152.5°	847.1	846.3	845.6	844.9	845.6	846.3	847.1	847.7	847.8	847.3	846.7
155°	866.3	865.3	864.4	863.5	864.4	865.3	866.3	867.2	867.3	866.5	865.7
157.5°	882.8	881.6	880.4	879.2	880.4	881.6	882.8	884.0	884.1	883.2	882.3
160°	892.4	891.4	890.2	889.2	890.2	891.4	892.4	893.5	893.5	892.7	891.7
162.5°	901.4	900.5	899.6	898.6	899.6	900.5	901.4	902.4	902.4	901.4	900.3
165°	913.2	912.1	911.1	909.9	911.1	912.1	913.2	914.3	914.2	912.9	911.7
167.5°	921.9	920.6	919.4	918.1	919.4	920.6	921.9	923.1	923.1	921.9	920.6
170°	926.9	925.6	924.4	923.1	924.4	925.6	926.9	928.1	928.1	926.9	925.6
172.5°	930.0	928.7	927.3	926.0	927.3	928.7	930.0	931.3	931.4	930.2	929.0
175°	933.8	932.6	931.3	930.1	931.3	932.6	933.8	935.0	935.1	934.1	932.9
177.5°	935.0	933.8	932.6	931.3	932.6	933.8	935.0	936.2	936.4	935.4	934.4
180°	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6



TEST NUMBER: P332096-830

CATALOG NUMBER: S123DIW-S340D755U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2
2.5°	434.6	434.6	437.9	440.1	442.7	444.4	445.6	446.9	449.0	451.8	455.0
5°	409.7	410.6	415.5	420.3	424.9	428.9	432.2	436.1	440.9	446.9	453.5
7.5°	385.7	389.1	393.9	399.8	406.2	412.0	417.8	424.3	431.2	439.9	449.1
10°	370.2	373.9	379.8	387.4	394.2	401.0	408.2	415.2	423.8	434.1	446.0
12.5°	356.7	360.2	366.4	374.5	381.0	388.5	396.8	406.0	415.6	427.9	441.4
15°	337.9	342.1	349.6	353.5	363.4	372.4	380.1	393.2	405.6	418.3	433.9
17.5°	322.5	324.9	330.9	338.3	345.6	355.8	365.8	376.8	389.1	404.6	424.1
20°	312.0	314.0	320.6	328.3	336.2	345.4	354.4	365.4	379.2	395.7	416.8
22.5°	304.2	306.2	310.6	318.8	326.1	333.8	342.8	355.9	370.6	386.7	409.5
25°	292.7	294.0	296.9	303.5	310.0	318.6	326.5	338.8	353.9	372.9	395.7
27.5°	281.8	283.1	285.5	290.2	296.4	303.3	312.0	322.3	337.7	358.3	382.5
30°	275.3	275.6	277.8	282.2	287.5	293.1	301.0	312.9	327.4	348.3	373.7
32.5°	269.8	268.9	270.4	273.7	278.8	284.6	291.1	302.7	316.7	337.1	363.4
35°	260.2	259.8	259.1	261.9	266.4	270.7	276.4	285.2	301.0	320.2	347.6
37.5°	250.5	249.4	248.3	249.6	253.0	257.6	262.5	270.3	284.0	305.0	331.3
40°	243.3	242.4	241.8	241.3	244.4	248.7	252.5	260.0	272.7	292.7	318.6
42.5°	235.4	234.9	234.0	233.4	235.9	239.3	243.2	249.8	262.5	281.3	305.8
45°	222.6	222.3	221.8	221.3	222.9	225.9	229.0	233.8	244.9	263.1	285.2
47.5°	208.5	207.9	208.1	207.4	208.9	210.9	213.1	218.3	228.8	243.6	259.8
50°	198.3	198.0	198.0	198.0	198.5	201.0	202.9	206.9	216.5	231.2	242.9
52.5°	188.6	187.7	187.7	188.0	188.9	190.4	191.6	196.0	204.3	216.5	227.1
55°	173.4	171.7	171.3	171.7	172.4	173.7	175.0	178.5	185.8	194.7	201.0
57.5°	156.7	155.7	155.1	155.2	155.6	156.7	157.7	161.5	167.2	171.9	175.9
60°	145.0	145.3	143.4	143.8	143.8	144.7	146.3	148.6	153.4	156.7	160.7
62.5°	133.8	133.3	132.7	132.1	132.1	132.4	134.5	136.4	140.5	142.2	145.2
65°	116.6	116.6	115.3	115.7	115.9	114.4	115.5	117.7	120.4	121.0	123.9
67.5°	99.2	98.5	97.7	97.1	97.1	97.0	97.6	98.6	100.6	100.9	103.0
70°	87.2	86.7	86.5	85.9	85.0	86.1	85.4	86.5	87.7	87.8	89.2
72.5°	75.6	75.1	74.7	74.1	73.7	73.6	73.6	74.9	75.7	75.4	76.8
75°	59.1	58.6	58.2	57.1	57.1	56.5	56.6	57.5	58.4	57.8	59.1
77.5°	43.4	42.0	41.9	42.2	41.5	41.7	41.4	41.3	41.7	41.7	42.9
80°	33.4	31.9	32.2	32.0	31.9	31.6	31.2	31.4	31.6	31.9	32.5
82.5°	24.0	23.9	23.5	23.5	23.2	22.6	22.4	22.8	23.0	22.9	23.4
85°	12.3	11.6	12.1	11.9	12.1	11.9	11.2	11.2	11.6	11.4	11.9
87.5°	7.2	7.0	6.4	6.2	5.7	5.4	4.9	4.7	4.6	4.3	4.3
90°	17.2	16.7	14.6	12.6	10.7	8.7	6.9	5.3	3.8	2.3	0.7
92.5°	18.8	17.7	16.2	14.7	13.2	11.7	11.2	11.6	12.1	12.4	12.9
95°	22.6	21.5	19.8	18.1	16.4	14.7	17.1	23.4	29.7	36.0	42.3
97.5°	23.6	22.3	33.5	44.5	55.6	66.7	73.7	76.5	79.4	82.2	85.0
100°	24.1	22.9	46.9	71.0	95.0	119.0	129.5	126.5	123.4	120.3	117.3
102.5°	41.8	45.6	71.9	98.1	124.4	150.7	162.7	160.5	158.3	156.1	153.8
105°	124.6	151.9	165.8	179.6	193.5	207.4	213.5	211.8	210.1	208.4	206.7
107.5°	258.4	278.4	276.3	274.0	271.8	269.7	267.9	266.6	265.1	263.8	262.4
110°	307.7	312.8	311.1	309.4	307.7	306.0	304.5	303.3	302.1	300.9	299.6



TEST NUMBER: P332096-830

CATALOG NUMBER: S123DIW-S340D755U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	347.9	347.8	346.1	344.4	342.7	341.0	339.6	338.5	337.3	336.2	335.2
115°	399.6	398.1	396.7	395.3	394.0	392.6	391.4	390.5	389.6	388.6	387.7
117.5°	448.2	447.0	446.2	445.5	444.8	444.1	443.2	442.1	440.9	439.8	438.7
120°	479.8	478.5	478.2	477.7	477.2	476.7	475.8	474.4	473.1	471.6	470.2
122.5°	511.0	510.2	509.6	509.1	508.4	507.8	507.0	505.9	504.7	503.6	502.5
125°	555.2	554.9	554.2	553.6	553.0	552.4	551.5	550.3	549.0	547.8	546.6
127.5°	598.6	598.1	597.4	596.6	596.0	595.2	594.2	593.0	591.7	590.5	589.3
130°	624.8	624.2	623.6	623.0	622.4	621.8	620.9	619.6	618.4	617.2	615.9
132.5°	649.8	649.2	648.7	648.2	647.7	647.2	646.4	645.1	643.9	642.6	641.4
135°	687.8	687.3	686.7	686.1	685.5	684.9	684.1	683.2	682.2	681.4	680.4
137.5°	721.2	720.5	720.2	719.8	719.4	719.2	718.4	717.2	716.0	714.8	713.7
140°	742.7	742.2	741.7	741.2	740.7	740.3	739.6	738.7	737.7	736.8	735.8
142.5°	763.2	762.7	762.2	761.8	761.3	760.8	760.2	759.2	758.3	757.3	756.4
145°	791.6	791.4	791.1	790.8	790.4	790.1	789.5	788.3	787.3	786.2	785.1
147.5°	817.1	816.7	816.4	816.1	815.9	815.5	815.0	814.3	813.6	812.8	812.2
150°	832.6	832.3	832.0	831.7	831.4	831.0	830.7	830.2	829.7	829.2	828.9
152.5°	846.1	845.6	845.5	845.3	845.1	844.9	844.7	844.4	844.2	844.0	843.8
155°	865.0	864.2	864.0	863.9	863.7	863.6	863.7	863.9	864.3	864.6	864.9
157.5°	881.4	880.4	880.6	880.7	880.9	881.1	881.2	881.2	881.2	881.3	881.3
160°	890.8	889.9	890.0	890.1	890.3	890.5	890.6	890.8	891.0	891.1	891.3
162.5°	899.3	898.1	898.3	898.5	898.6	898.8	899.1	899.5	899.8	900.3	900.7
165°	910.5	909.3	909.5	909.6	909.7	909.9	910.2	910.7	911.2	911.6	912.1
167.5°	919.4	918.1	918.1	918.1	918.1	918.1	918.5	919.1	919.7	920.3	921.0
170°	924.4	923.1	923.1	923.1	923.1	923.1	923.5	924.1	924.7	925.3	926.0
172.5°	927.7	926.5	926.3	926.2	926.1	926.0	926.3	927.1	927.7	928.5	929.3
175°	931.9	930.8	930.7	930.5	930.3	930.2	930.5	931.2	932.0	932.7	933.6
177.5°	933.4	932.5	932.4	932.2	932.1	932.0	932.2	932.8	933.4	934.1	934.6
180°	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6



TEST NUMBER: P332096-830

CATALOG NUMBER: S123DIW-S340D755U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2
2.5°	456.0	456.9	459.9	462.0	464.5	465.9	467.2	468.3	469.8	470.0	475.1
5°	458.1	462.4	470.1	475.8	482.9	490.5	495.8	498.2	504.6	509.8	520.4
7.5°	457.5	466.8	478.4	490.5	503.3	515.3	525.7	538.0	546.7	559.9	572.8
10°	456.9	469.5	484.4	499.7	517.7	534.4	549.4	566.1	579.9	598.1	613.7
12.5°	455.3	470.5	491.3	509.4	531.3	554.3	576.5	597.9	610.1	640.5	654.8
15°	451.5	469.5	495.4	523.0	553.1	580.3	608.4	630.8	667.0	693.6	710.6
17.5°	444.0	469.2	499.9	533.3	569.9	605.8	637.6	671.6	710.0	742.2	776.5
20°	440.5	468.2	502.4	539.3	577.3	617.9	654.1	694.9	736.9	768.5	812.5
22.5°	433.9	465.3	502.2	543.3	583.9	625.9	668.4	709.5	758.0	801.5	843.4
25°	423.4	458.5	496.7	542.6	590.2	632.4	683.2	737.8	788.2	844.3	886.0
27.5°	412.2	449.7	488.0	530.7	581.9	632.0	695.8	757.5	819.3	867.6	898.5
30°	403.6	440.1	479.6	522.6	573.3	632.8	704.2	771.6	831.8	873.3	890.6
32.5°	394.3	431.2	466.2	511.3	565.4	632.3	709.5	779.9	832.5	860.1	856.7
35°	379.7	410.6	444.7	488.1	551.8	628.4	712.6	780.6	812.8	806.9	762.1
37.5°	358.5	384.7	418.1	465.7	536.0	620.3	706.3	757.4	755.4	707.1	642.2
40°	345.4	367.6	399.8	449.9	523.7	615.0	696.7	729.9	701.8	634.3	556.7
42.5°	328.2	348.6	380.9	432.3	510.2	604.4	678.3	687.9	632.9	555.3	484.1
45°	301.5	319.5	352.9	406.0	489.8	581.0	633.3	609.7	535.7	455.6	401.4
47.5°	272.8	291.5	323.6	378.2	460.5	545.9	570.8	520.8	444.9	379.8	330.1
50°	254.7	272.7	304.2	359.2	440.7	517.1	527.4	462.9	393.0	335.9	295.1
52.5°	236.5	253.4	284.3	339.6	417.5	483.7	477.4	411.6	347.4	298.7	266.6
55°	209.2	225.3	254.7	306.5	377.5	429.9	406.9	344.1	291.0	253.2	228.8
57.5°	184.9	200.3	225.6	272.5	334.1	370.2	340.9	287.9	245.7	216.6	198.5
60°	168.4	182.0	206.2	249.7	303.2	330.6	301.7	255.0	219.3	196.0	179.8
62.5°	152.8	164.7	187.0	226.5	273.1	296.1	266.7	227.2	196.9	176.3	162.4
65°	129.1	139.9	159.7	190.4	228.6	243.9	218.7	186.6	163.2	147.8	138.6
67.5°	107.5	116.7	133.7	157.9	186.1	197.2	178.0	153.2	135.4	123.1	115.8
70°	93.1	101.0	114.4	135.3	160.7	169.3	151.3	130.8	117.9	108.0	101.2
72.5°	81.0	86.8	99.0	115.1	136.3	143.1	130.5	112.6	100.6	93.1	87.7
75°	61.7	66.5	74.5	87.4	102.1	106.0	96.6	85.4	77.3	72.0	67.9
77.5°	44.5	48.1	53.7	61.7	71.9	75.5	69.6	62.0	56.1	52.6	50.2
80°	33.6	36.5	41.3	47.9	54.0	56.0	52.5	46.8	42.6	40.6	38.6
82.5°	24.8	26.4	29.3	33.8	38.0	40.3	37.4	33.9	31.7	29.9	29.1
85°	12.5	13.4	14.7	16.5	19.1	20.0	18.9	18.0	16.7	15.6	15.6
87.5°	5.0	5.3	6.1	6.8	7.9	8.8	9.0	9.0	9.3	9.2	9.2
90°	2.3	3.8	5.3	6.9	8.7	10.7	12.6	14.6	16.7	17.2	17.9
92.5°	12.4	12.1	11.6	11.2	11.7	13.2	14.7	16.2	17.7	18.8	19.7
95°	36.0	29.7	23.4	17.1	14.7	16.4	18.1	19.8	21.5	22.6	23.7
97.5°	82.2	79.4	76.5	73.7	66.7	55.6	44.5	33.5	22.3	23.6	24.8
100°	120.3	123.4	126.5	129.5	119.0	95.0	71.0	46.9	22.9	24.1	25.4
102.5°	156.1	158.3	160.5	162.7	150.7	124.4	98.1	71.9	45.6	41.8	38.0
105°	208.4	210.1	211.8	213.5	207.4	193.5	179.6	165.8	151.9	124.6	97.4
107.5°	263.8	265.1	266.6	267.9	269.7	271.8	274.0	276.3	278.4	258.4	238.4
110°	300.9	302.1	303.3	304.5	306.0	307.7	309.4	311.1	312.8	307.7	302.7





TEST NUMBER: P332096-830

CATALOG NUMBER: S123DIW-S340D755U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	336.2	337.3	338.5	339.6	341.0	342.7	344.4	346.1	347.8	347.9	348.0
115°	388.6	389.6	390.5	391.4	392.6	394.0	395.3	396.7	398.1	399.6	401.2
117.5°	439.8	440.9	442.1	443.2	444.1	444.8	445.5	446.2	447.0	448.2	449.4
120°	471.6	473.1	474.4	475.8	476.7	477.2	477.7	478.2	478.5	479.8	481.1
122.5°	503.6	504.7	505.9	507.0	507.8	508.4	509.1	509.6	510.2	511.0	511.9
125°	547.8	549.0	550.3	551.5	552.4	553.0	553.6	554.2	554.9	555.2	555.4
127.5°	590.5	591.7	593.0	594.2	595.2	596.0	596.6	597.4	598.1	598.6	599.2
130°	617.2	618.4	619.6	620.9	621.8	622.4	623.0	623.6	624.2	624.8	625.5
132.5°	642.6	643.9	645.1	646.4	647.2	647.7	648.2	648.7	649.2	649.8	650.4
135°	681.4	682.2	683.2	684.1	684.9	685.5	686.1	686.7	687.3	687.8	688.2
137.5°	714.8	716.0	717.2	718.4	719.2	719.4	719.8	720.2	720.5	721.2	722.0
140°	736.8	737.7	738.7	739.6	740.3	740.7	741.2	741.7	742.2	742.7	743.4
142.5°	757.3	758.3	759.2	760.2	760.8	761.3	761.8	762.2	762.7	763.2	763.6
145°	786.2	787.3	788.3	789.5	790.1	790.4	790.8	791.1	791.4	791.6	792.0
147.5°	812.8	813.6	814.3	815.0	815.5	815.9	816.1	816.4	816.7	817.1	817.4
150°	829.2	829.7	830.2	830.7	831.0	831.4	831.7	832.0	832.3	832.6	832.9
152.5°	844.0	844.2	844.4	844.7	844.9	845.1	845.3	845.5	845.6	846.1	846.7
155°	864.6	864.3	863.9	863.7	863.6	863.7	863.9	864.0	864.2	865.0	865.7
157.5°	881.3	881.2	881.2	881.2	881.1	880.9	880.7	880.6	880.4	881.4	882.3
160°	891.1	891.0	890.8	890.6	890.5	890.3	890.1	890.0	889.9	890.8	891.7
162.5°	900.3	899.8	899.5	899.1	898.8	898.6	898.5	898.3	898.1	899.3	900.3
165°	911.6	911.2	910.7	910.2	909.9	909.7	909.6	909.5	909.3	910.5	911.7
167.5°	920.3	919.7	919.1	918.5	918.1	918.1	918.1	918.1	918.1	919.4	920.6
170°	925.3	924.7	924.1	923.5	923.1	923.1	923.1	923.1	923.1	924.4	925.6
172.5°	928.5	927.7	927.1	926.3	926.0	926.1	926.2	926.3	926.5	927.7	929.0
175°	932.7	932.0	931.2	930.5	930.2	930.3	930.5	930.7	930.8	931.9	932.9
177.5°	934.1	933.4	932.8	932.2	932.0	932.1	932.2	932.4	932.5	933.4	934.4
180°	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6



TEST NUMBER: P332096-830

CATALOG NUMBER: S123DIW-S340D755U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	453.2	453.2	453.2	453.2	453.2	453.2	453.2
2.5°	476.9	477.1	479.0	480.4	479.8	480.6	481.0
5°	521.0	529.0	533.1	536.2	536.4	536.7	538.4
7.5°	583.6	592.1	598.3	607.8	610.5	613.7	612.8
10°	629.3	641.9	652.6	658.3	664.5	673.4	666.2
12.5°	672.0	694.2	710.6	719.4	725.2	727.0	723.5
15°	742.4	771.4	786.9	786.6	806.3	814.8	801.4
17.5°	806.9	833.7	855.2	866.1	882.6	886.2	884.6
20°	846.5	875.7	892.4	911.3	919.8	927.5	928.8
22.5°	880.5	906.8	924.7	940.4	947.5	951.2	953.4
25°	915.7	936.3	947.1	952.5	954.5	954.0	951.2
27.5°	913.2	914.8	903.0	891.4	880.9	869.2	865.2
30°	889.5	871.1	838.1	819.4	792.0	770.2	779.1
32.5°	827.2	790.4	753.5	712.7	678.9	669.3	659.6
35°	706.0	641.4	603.6	559.7	542.2	524.6	512.5
37.5°	571.1	521.2	476.4	447.7	430.1	419.0	413.0
40°	493.8	448.8	411.9	388.6	375.2	362.8	361.0
42.5°	432.2	390.3	362.6	344.0	331.2	325.8	322.0
45°	353.9	324.8	306.1	292.9	284.4	281.1	276.6
47.5°	299.6	279.0	264.9	256.0	249.5	247.0	246.8
50°	269.2	252.0	241.8	234.7	229.7	228.8	225.3
52.5°	246.4	231.5	223.5	217.4	213.7	211.2	210.2
55°	213.9	204.0	196.7	193.2	190.4	187.9	187.9
57.5°	187.1	178.9	174.1	171.1	170.2	168.5	167.4
60°	170.6	163.6	159.9	157.2	155.4	155.7	153.7
62.5°	154.5	149.9	146.3	143.7	141.6	141.7	141.8
65°	131.5	128.0	125.4	124.5	123.2	121.7	122.1
67.5°	111.5	108.2	106.1	104.6	104.2	103.3	104.6
70°	97.1	94.6	93.1	91.8	91.3	91.5	92.7
72.5°	83.9	82.2	81.2	80.6	79.6	79.6	80.4
75°	65.9	64.6	63.7	63.1	62.8	62.8	62.8
77.5°	48.4	48.1	47.7	46.8	46.8	47.0	47.0
80°	38.2	37.5	37.3	36.9	36.2	35.8	36.9
82.5°	28.6	27.9	27.7	27.6	26.6	26.5	27.4
85°	15.4	14.7	14.9	14.7	14.7	14.5	14.5
87.5°	9.1	9.0	9.0	9.2	9.1	9.0	9.4
90°	18.5	19.1	19.6	19.9	20.2	20.5	20.8
92.5°	20.7	21.7	22.2	22.4	22.6	22.8	23.0
95°	24.7	25.8	26.4	26.4	26.4	26.4	26.4
97.5°	26.0	27.2	28.0	28.1	28.3	28.5	28.6
100°	26.6	27.8	28.6	28.7	28.8	28.9	29.1
102.5°	34.2	30.3	28.6	28.8	29.1	29.4	29.7
105°	70.0	42.8	29.3	29.6	29.9	30.3	30.5
107.5°	218.4	198.4	178.1	157.5	137.0	116.4	95.9
110°	297.6	292.5	278.9	256.8	234.8	212.7	190.8



TEST NUMBER: P332096-830

CATALOG NUMBER: S123DIW-S340D755U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	348.1	348.2	345.8	341.2	336.6	331.9	327.3
115°	402.7	404.3	405.4	406.0	406.6	407.2	407.8
117.5°	450.6	451.9	452.5	452.7	452.8	452.9	453.1
120°	482.3	483.5	484.1	484.1	484.1	484.1	484.1
122.5°	512.7	513.7	514.2	514.3	514.3	514.5	514.6
125°	555.8	556.1	556.4	556.8	557.0	557.3	557.6
127.5°	599.6	600.1	600.2	599.9	599.6	599.3	599.0
130°	626.0	626.7	626.9	626.5	626.2	625.9	625.6
132.5°	651.0	651.7	651.8	651.3	650.9	650.4	650.0
135°	688.7	689.2	689.2	688.7	688.2	687.8	687.3
137.5°	722.7	723.5	723.7	723.4	723.0	722.7	722.5
140°	743.9	744.6	744.8	744.4	744.1	743.9	743.5
142.5°	764.1	764.6	764.7	764.2	763.8	763.4	762.9
145°	792.3	792.6	792.8	792.8	792.8	792.8	792.8
147.5°	817.7	818.0	817.7	817.1	816.3	815.7	814.9
150°	833.2	833.5	833.5	833.0	832.5	832.1	831.6
152.5°	847.3	847.8	847.7	847.1	846.3	845.6	844.9
155°	866.5	867.3	867.2	866.3	865.3	864.4	863.5
157.5°	883.2	884.1	884.0	882.8	881.6	880.4	879.2
160°	892.7	893.5	893.5	892.4	891.4	890.2	889.2
162.5°	901.4	902.4	902.4	901.4	900.5	899.6	898.6
165°	912.9	914.2	914.3	913.2	912.1	911.1	909.9
167.5°	921.9	923.1	923.1	921.9	920.6	919.4	918.1
170°	926.9	928.1	928.1	926.9	925.6	924.4	923.1
172.5°	930.2	931.4	931.3	930.0	928.7	927.3	926.0
175°	934.1	935.1	935.0	933.8	932.6	931.3	930.1
177.5°	935.4	936.4	936.2	935.0	933.8	932.6	931.3
180°	933.6	933.6	933.6	933.6	933.6	933.6	933.6

(END OF REPORT)