

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332126-830

Luminaire Tested: **S123DIW-S560D755U830-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332126-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S560D755U830-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 755 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5098.3 lumens
Efficiency: N/A
Efficacy: 135.6 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 37.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332126-830

CATALOG NUMBER: S123DIW-S560D755U830-4F0-1E-UDD-A

Luminous Intensity Polar Plot



56% Up

44% Dn



TEST NUMBER: P332126-830

CATALOG NUMBER: S123DIW-S560D755U830-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	44				
1	97	93	89	85	88	85	82	79	71	68	66	57	56	54	45	44	43	38				
2	88	81	75	70	81	74	69	65	62	58	55	51	48	46	40	38	37	32				
3	81	71	64	59	74	66	59	55	55	50	47	45	42	39	36	33	32	27				
4	74	63	56	50	67	58	52	46	49	44	40	40	36	33	32	29	27	24				
5	68	56	48	43	62	52	45	40	44	38	34	36	32	29	29	26	24	21				
6	62	51	43	37	57	47	40	35	39	34	30	33	29	26	26	23	21	18				
7	58	46	38	32	53	42	35	30	36	30	26	30	26	23	24	21	19	16				
8	54	41	34	29	49	38	32	27	33	27	23	27	23	20	22	19	17	14				
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	20	17	15	13				
10	46	35	27	23	43	32	26	21	27	22	19	23	19	16	19	16	14	12				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8020	8020	8020	8020
5°	9564	8055	7138	8055
10°	11970	8014	6446	8014
15°	14683	7949	6002	7949
20°	17491	7848	5715	7848
25°	18573	7726	5651	7726
30°	15919	7636	5680	7636
35°	11071	7510	5740	7510
40°	8338	7360	5722	7360
45°	6925	7138	5649	7138
50°	6203	6687	5598	6687
55°	5799	6199	5527	6199
60°	5440	5690	5470	5690
65°	5112	5186	5295	5186
70°	4793	4614	5042	4614
75°	4292	4038	4625	4038
80°	3756	3310	3986	3310
85°	2939	2408	2680	2408



TEST NUMBER: P332126-830

CATALOG NUMBER: S123DIW-S560D755U830-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.4	1.4
10°-20°	235.3	4.6
20°-30°	395.0	7.7
30°-40°	447.2	8.8
40°-50°	401.1	7.9
50°-60°	323.7	6.3
60°-70°	225.5	4.4
70°-80°	118.5	2.3
80°-90°	31.6	0.6
90°-100°	33.9	0.7
100°-110°	161.8	3.2
110°-120°	388.6	7.6
120°-130°	494.8	9.7
130°-140°	528.7	10.4
140°-150°	494.4	9.7
150°-160°	398.8	7.8
160°-170°	257.4	5.0
170°-180°	88.7	1.7
0°-30°	703.7	13.8
0°-40°	1151.0	22.6
0°-60°	1875.7	36.8
0°-90°	2251.4	44.2
90°-120°	584.3	11.5
90°-150°	2102.1	41.2
90°-180°	2847.0	55.8
0°-180°	5098.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	745	745	745	745	745	
5°	885	746	661	746	885	92
15°	1318	713	539	713	1318	380
25°	1564	650	476	650	1564	686
35°	842	572	437	572	842	547
45°	455	469	371	469	455	360
55°	309	330	294	330	309	277
65°	201	204	208	204	201	200
75°	103	97	111	97	103	110
85°	24	20	22	20	24	29
90°	21	1	21	1	21	11
95°	26	42	26	42	26	22
105°	30	207	30	207	30	70
115°	408	388	408	388	408	377
125°	558	547	558	547	558	498
135°	687	680	687	680	687	530
145°	793	785	793	785	793	495
155°	864	865	864	865	864	398
165°	910	912	910	912	910	257
175°	930	934	930	934	930	89
180°	934	934	934	934	934	



TEST NUMBER: P332126-830

CATALOG NUMBER: S123DIW-S560D755U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	745.1	745.1	745.1	745.1	745.1	745.1	745.1	745.1	745.1	745.1	745.1
2.5°	790.7	790.1	788.7	789.9	787.5	784.4	784.1	781.2	772.8	772.2	770.0
5°	885.1	882.2	881.9	881.6	876.5	869.6	856.6	855.5	838.2	829.5	819.1
7.5°	1007.5	1009.0	1003.7	999.1	983.6	973.5	959.5	941.7	920.4	898.8	884.4
10°	1095.2	1107.1	1092.3	1082.2	1072.9	1055.2	1034.6	1009.0	983.4	953.4	930.7
12.5°	1189.4	1195.2	1192.3	1182.7	1168.2	1141.2	1104.8	1076.6	1052.9	1003.1	982.9
15°	1317.6	1339.6	1325.6	1293.1	1293.8	1268.2	1220.5	1168.2	1140.4	1096.6	1037.1
17.5°	1454.2	1457.0	1451.0	1423.9	1405.8	1370.6	1326.6	1276.5	1220.1	1167.3	1104.1
20°	1527.0	1524.8	1512.2	1498.1	1467.1	1439.6	1391.6	1335.7	1263.5	1211.4	1142.6
22.5°	1567.4	1563.8	1557.8	1546.1	1520.2	1490.7	1447.7	1386.5	1317.8	1246.1	1166.5
25°	1563.8	1568.5	1569.2	1565.9	1557.0	1539.3	1505.3	1456.6	1388.0	1296.0	1213.0
27.5°	1422.3	1428.9	1448.2	1465.4	1484.5	1503.9	1501.4	1477.2	1426.4	1346.9	1245.4
30°	1280.8	1266.3	1302.1	1347.2	1377.9	1432.0	1462.4	1464.1	1435.7	1367.4	1268.5
32.5°	1084.4	1100.3	1116.1	1171.6	1238.7	1299.5	1359.8	1408.4	1414.0	1368.6	1282.0
35°	842.5	862.4	891.3	920.2	992.4	1054.4	1160.6	1253.0	1326.6	1336.3	1283.3
37.5°	678.9	688.8	707.0	735.9	783.2	856.9	939.0	1055.7	1162.4	1241.8	1245.3
40°	593.4	596.3	616.9	638.9	677.2	737.8	811.9	915.1	1042.9	1153.8	1200.0
42.5°	529.3	535.7	544.4	565.6	596.1	641.7	710.5	795.9	912.9	1040.5	1130.9
45°	454.9	462.0	467.5	481.5	503.2	533.9	581.9	659.9	749.0	880.8	1002.5
47.5°	405.6	406.1	410.2	420.8	435.5	458.6	492.6	542.6	624.5	731.3	856.3
50°	370.4	376.2	377.6	385.9	397.5	414.4	442.6	485.1	552.3	646.2	761.0
52.5°	345.5	347.2	351.3	357.3	367.4	380.6	405.0	438.4	491.1	571.1	676.7
55°	309.0	309.0	313.0	317.6	323.5	335.4	351.6	376.2	416.2	478.3	565.7
57.5°	275.2	277.0	279.8	281.3	286.2	294.1	307.6	326.3	356.2	404.0	473.4
60°	252.7	255.9	255.6	258.4	262.8	268.9	280.5	295.7	322.3	360.6	419.1
62.5°	233.1	232.8	232.8	236.2	240.5	246.4	253.9	267.0	289.7	323.7	373.4
65°	200.7	200.0	202.6	204.7	206.1	210.5	216.2	227.8	243.0	268.2	306.8
67.5°	172.0	169.8	171.3	172.0	174.5	177.9	183.2	190.4	202.5	222.7	251.8
70°	152.3	150.5	150.1	150.9	153.1	155.6	159.6	166.5	177.6	193.9	215.2
72.5°	132.1	130.9	130.8	132.4	133.5	135.1	137.9	144.2	153.1	165.2	185.1
75°	103.2	103.2	103.2	103.6	104.7	106.1	108.3	111.5	118.4	127.1	140.4
77.5°	77.4	77.3	76.9	76.8	78.4	79.1	79.6	82.6	86.4	92.3	102.0
80°	60.6	58.8	59.6	60.6	61.4	61.7	62.8	63.5	66.8	70.0	76.9
82.5°	45.1	43.5	43.6	45.3	45.5	45.8	46.9	48.0	49.2	52.1	55.8
85°	23.8	23.8	24.2	24.2	24.5	24.2	25.3	25.6	25.6	27.4	29.6
87.5°	12.8	12.2	12.4	12.6	12.3	12.4	12.6	12.8	13.0	13.1	13.0
90°	20.8	20.5	20.2	19.9	19.6	19.1	18.5	17.9	17.2	16.7	14.6
92.5°	23.0	22.8	22.6	22.4	22.2	21.7	20.7	19.7	18.8	17.7	16.2
95°	26.4	26.4	26.4	26.4	26.4	25.8	24.7	23.7	22.6	21.5	19.8
97.5°	28.6	28.5	28.3	28.1	28.0	27.2	26.0	24.8	23.6	22.3	33.5
100°	29.1	28.9	28.8	28.7	28.6	27.8	26.6	25.4	24.1	22.9	46.9
102.5°	29.7	29.4	29.1	28.8	28.6	30.3	34.2	38.0	41.8	45.6	71.9
105°	30.5	30.3	29.9	29.6	29.3	42.8	70.0	97.4	124.6	151.9	165.8
107.5°	95.9	116.4	137.0	157.5	178.1	198.4	218.4	238.4	258.4	278.4	276.3
110°	190.8	212.7	234.8	256.8	278.9	292.5	297.6	302.7	307.7	312.8	311.1



TEST NUMBER: P332126-830

CATALOG NUMBER: S123DIW-S560D755U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	327.3	331.9	336.6	341.2	345.8	348.2	348.1	348.0	347.9	347.8	346.1
115°	407.8	407.2	406.6	406.0	405.4	404.3	402.7	401.2	399.6	398.1	396.7
117.5°	453.1	452.9	452.8	452.7	452.5	451.9	450.6	449.4	448.2	447.0	446.2
120°	484.1	484.1	484.1	484.1	484.1	483.5	482.3	481.1	479.8	478.5	478.2
122.5°	514.6	514.5	514.3	514.3	514.2	513.7	512.7	511.9	511.0	510.2	509.6
125°	557.6	557.3	557.0	556.8	556.4	556.1	555.8	555.4	555.2	554.9	554.2
127.5°	599.0	599.3	599.6	599.9	600.2	600.1	599.6	599.2	598.6	598.1	597.4
130°	625.6	625.9	626.2	626.5	626.9	626.7	626.0	625.5	624.8	624.2	623.6
132.5°	650.0	650.4	650.9	651.3	651.8	651.7	651.0	650.4	649.8	649.2	648.7
135°	687.3	687.8	688.2	688.7	689.2	689.2	688.7	688.2	687.8	687.3	686.7
137.5°	722.5	722.7	723.0	723.4	723.7	723.5	722.7	722.0	721.2	720.5	720.2
140°	743.5	743.9	744.1	744.4	744.8	744.6	743.9	743.4	742.7	742.2	741.7
142.5°	762.9	763.4	763.8	764.2	764.7	764.6	764.1	763.6	763.2	762.7	762.2
145°	792.8	792.8	792.8	792.8	792.8	792.6	792.3	792.0	791.6	791.4	791.1
147.5°	814.9	815.7	816.3	817.1	817.7	818.0	817.7	817.4	817.1	816.7	816.4
150°	831.6	832.1	832.5	833.0	833.5	833.5	833.2	832.9	832.6	832.3	832.0
152.5°	844.9	845.6	846.3	847.1	847.7	847.8	847.3	846.7	846.1	845.6	845.5
155°	863.5	864.4	865.3	866.3	867.2	867.3	866.5	865.7	865.0	864.2	864.0
157.5°	879.2	880.4	881.6	882.8	884.0	884.1	883.2	882.3	881.4	880.4	880.6
160°	889.2	890.2	891.4	892.4	893.5	893.5	892.7	891.7	890.8	889.9	890.0
162.5°	898.6	899.6	900.5	901.4	902.4	902.4	901.4	900.3	899.3	898.1	898.3
165°	909.9	911.1	912.1	913.2	914.3	914.2	912.9	911.7	910.5	909.3	909.5
167.5°	918.1	919.4	920.6	921.9	923.1	923.1	921.9	920.6	919.4	918.1	918.1
170°	923.1	924.4	925.6	926.9	928.1	928.1	926.9	925.6	924.4	923.1	923.1
172.5°	926.0	927.3	928.7	930.0	931.3	931.4	930.2	929.0	927.7	926.5	926.3
175°	930.1	931.3	932.6	933.8	935.0	935.1	934.1	932.9	931.9	930.8	930.7
177.5°	931.3	932.6	933.8	935.0	936.2	936.4	935.4	934.4	933.4	932.5	932.4
180°	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6



TEST NUMBER: P332126-830

CATALOG NUMBER: S123DIW-S560D755U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	745.1	745.1	745.1	745.1	745.1	745.1	745.1	745.1	745.1	745.1	745.1
2.5°	768.2	765.9	763.6	759.5	756.0	751.1	749.7	748.0	742.8	738.1	734.7
5°	815.1	806.4	793.8	782.2	772.9	760.3	753.0	745.5	734.6	724.9	716.9
7.5°	864.2	847.2	827.6	806.3	786.6	767.4	752.1	738.4	723.2	708.8	697.7
10°	903.2	878.6	851.2	821.6	796.4	771.8	751.2	733.2	713.7	696.7	682.6
12.5°	947.6	911.3	873.5	837.4	807.6	773.5	748.7	725.7	703.6	683.2	667.3
15°	1000.3	954.1	909.4	859.9	814.4	771.8	742.2	713.3	687.7	666.8	646.5
17.5°	1048.2	995.9	936.9	876.8	821.9	771.4	729.9	697.3	665.2	639.6	619.4
20°	1075.3	1015.8	949.0	886.6	826.0	769.6	724.2	685.1	650.5	623.4	600.7
22.5°	1098.8	1029.1	960.0	893.2	825.7	765.0	713.5	673.4	635.7	609.3	585.1
25°	1123.0	1039.6	970.3	892.0	816.5	753.8	696.0	650.5	612.9	581.9	557.0
27.5°	1143.9	1039.0	956.7	872.4	802.3	739.3	677.7	628.9	589.0	555.3	530.0
30°	1157.7	1040.4	942.5	859.1	788.4	723.4	663.5	614.4	572.5	538.2	514.4
32.5°	1166.4	1039.5	929.5	840.7	766.5	709.0	648.2	597.4	554.3	520.7	497.7
35°	1171.4	1033.1	907.2	802.5	731.0	675.0	624.2	571.5	526.3	494.9	468.9
37.5°	1161.3	1019.8	881.2	765.6	687.4	632.4	589.5	544.6	501.4	466.8	444.4
40°	1145.4	1011.2	860.9	739.7	657.3	604.3	567.9	523.8	481.2	448.4	427.4
42.5°	1115.1	993.5	838.8	710.8	626.1	573.1	539.5	502.8	462.4	431.6	410.7
45°	1041.1	955.2	805.4	667.5	580.1	525.3	495.7	468.9	432.4	402.5	384.5
47.5°	938.4	897.5	757.1	621.8	532.1	479.3	448.5	427.0	400.3	376.2	358.8
50°	867.1	850.2	724.5	590.6	499.9	448.4	418.8	399.3	380.1	355.9	340.1
52.5°	784.8	795.2	686.4	558.3	467.3	416.6	388.7	373.2	355.9	336.0	322.2
55°	668.9	706.8	620.6	504.0	418.8	370.4	344.0	330.3	320.2	305.4	293.5
57.5°	560.4	608.6	549.3	448.0	371.0	329.3	304.1	289.1	282.6	274.8	265.5
60°	496.0	543.7	498.5	410.5	338.9	299.3	276.9	264.3	257.8	252.3	244.4
62.5°	438.6	486.7	448.8	372.3	307.5	270.7	251.2	238.8	233.8	230.9	224.1
65°	359.6	401.1	375.8	313.0	262.4	230.0	212.3	203.6	198.9	197.8	193.5
67.5°	292.7	324.2	305.9	259.6	219.8	191.7	176.7	169.4	165.8	165.4	162.1
70°	248.7	278.3	264.3	222.3	188.0	166.1	153.1	146.6	144.4	144.0	142.2
72.5°	214.6	235.3	224.1	189.2	162.7	142.7	133.1	126.3	123.9	124.4	123.2
75°	158.8	174.4	167.9	143.6	122.3	109.3	101.4	97.1	94.9	96.0	94.5
77.5°	114.3	124.1	118.3	101.5	88.4	79.0	73.1	70.5	68.5	68.4	67.8
80°	86.2	92.1	88.8	78.7	67.9	59.9	55.2	53.4	52.3	52.0	51.7
82.5°	61.5	66.4	62.5	55.6	48.3	43.5	40.8	38.5	37.6	37.8	37.5
85°	31.0	32.9	31.4	27.1	24.2	22.1	20.5	19.5	18.8	19.1	18.4
87.5°	13.2	13.1	11.9	10.4	9.4	8.3	7.9	7.1	6.8	7.1	7.2
90°	12.6	10.7	8.7	6.9	5.3	3.8	2.3	0.7	2.3	3.8	5.3
92.5°	14.7	13.2	11.7	11.2	11.6	12.1	12.4	12.9	12.4	12.1	11.6
95°	18.1	16.4	14.7	17.1	23.4	29.7	36.0	42.3	36.0	29.7	23.4
97.5°	44.5	55.6	66.7	73.7	76.5	79.4	82.2	85.0	82.2	79.4	76.5
100°	71.0	95.0	119.0	129.5	126.5	123.4	120.3	117.3	120.3	123.4	126.5
102.5°	98.1	124.4	150.7	162.7	160.5	158.3	156.1	153.8	156.1	158.3	160.5
105°	179.6	193.5	207.4	213.5	211.8	210.1	208.4	206.7	208.4	210.1	211.8
107.5°	274.0	271.8	269.7	267.9	266.6	265.1	263.8	262.4	263.8	265.1	266.6
110°	309.4	307.7	306.0	304.5	303.3	302.1	300.9	299.6	300.9	302.1	303.3



TEST NUMBER: P332126-830

CATALOG NUMBER: S123DIW-S560D755U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	344.4	342.7	341.0	339.6	338.5	337.3	336.2	335.2	336.2	337.3	338.5
115°	395.3	394.0	392.6	391.4	390.5	389.6	388.6	387.7	388.6	389.6	390.5
117.5°	445.5	444.8	444.1	443.2	442.1	440.9	439.8	438.7	439.8	440.9	442.1
120°	477.7	477.2	476.7	475.8	474.4	473.1	471.6	470.2	471.6	473.1	474.4
122.5°	509.1	508.4	507.8	507.0	505.9	504.7	503.6	502.5	503.6	504.7	505.9
125°	553.6	553.0	552.4	551.5	550.3	549.0	547.8	546.6	547.8	549.0	550.3
127.5°	596.6	596.0	595.2	594.2	593.0	591.7	590.5	589.3	590.5	591.7	593.0
130°	623.0	622.4	621.8	620.9	619.6	618.4	617.2	615.9	617.2	618.4	619.6
132.5°	648.2	647.7	647.2	646.4	645.1	643.9	642.6	641.4	642.6	643.9	645.1
135°	686.1	685.5	684.9	684.1	683.2	682.2	681.4	680.4	681.4	682.2	683.2
137.5°	719.8	719.4	719.2	718.4	717.2	716.0	714.8	713.7	714.8	716.0	717.2
140°	741.2	740.7	740.3	739.6	738.7	737.7	736.8	735.8	736.8	737.7	738.7
142.5°	761.8	761.3	760.8	760.2	759.2	758.3	757.3	756.4	757.3	758.3	759.2
145°	790.8	790.4	790.1	789.5	788.3	787.3	786.2	785.1	786.2	787.3	788.3
147.5°	816.1	815.9	815.5	815.0	814.3	813.6	812.8	812.2	812.8	813.6	814.3
150°	831.7	831.4	831.0	830.7	830.2	829.7	829.2	828.9	829.2	829.7	830.2
152.5°	845.3	845.1	844.9	844.7	844.4	844.2	844.0	843.8	844.0	844.2	844.4
155°	863.9	863.7	863.6	863.7	863.9	864.3	864.6	864.9	864.6	864.3	863.9
157.5°	880.7	880.9	881.1	881.2	881.2	881.2	881.3	881.3	881.3	881.2	881.2
160°	890.1	890.3	890.5	890.6	890.8	891.0	891.1	891.3	891.1	891.0	890.8
162.5°	898.5	898.6	898.8	899.1	899.5	899.8	900.3	900.7	900.3	899.8	899.5
165°	909.6	909.7	909.9	910.2	910.7	911.2	911.6	912.1	911.6	911.2	910.7
167.5°	918.1	918.1	918.1	918.5	919.1	919.7	920.3	921.0	920.3	919.7	919.1
170°	923.1	923.1	923.1	923.5	924.1	924.7	925.3	926.0	925.3	924.7	924.1
172.5°	926.2	926.1	926.0	926.3	927.1	927.7	928.5	929.3	928.5	927.7	927.1
175°	930.5	930.3	930.2	930.5	931.2	932.0	932.7	933.6	932.7	932.0	931.2
177.5°	932.2	932.1	932.0	932.2	932.8	933.4	934.1	934.6	934.1	933.4	932.8
180°	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6



TEST NUMBER: P332126-830

CATALOG NUMBER: S123DIW-S560D755U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	745.1	745.1	745.1	745.1	745.1	745.1	745.1	745.1	745.1	745.1	745.1
2.5°	732.6	730.7	727.7	723.4	719.9	714.4	714.4	715.3	715.3	715.0	714.4
5°	710.4	705.0	698.5	691.0	683.0	675.0	673.6	670.7	668.5	667.1	665.3
7.5°	686.9	677.4	667.9	657.3	647.6	639.6	634.0	629.4	626.4	623.3	620.9
10°	671.1	659.1	648.0	636.8	624.5	614.7	608.6	604.3	601.1	598.1	596.7
12.5°	652.3	638.7	626.3	615.7	602.3	592.2	586.4	584.4	580.5	574.5	571.3
15°	624.9	612.3	597.5	581.2	574.7	562.4	555.5	552.3	550.2	545.4	544.0
17.5°	601.4	584.8	568.3	556.1	544.0	534.1	530.3	526.2	523.4	519.5	518.4
20°	582.7	567.9	552.7	539.7	527.1	516.2	512.9	510.1	507.2	505.4	504.0
22.5°	563.5	548.7	536.2	524.1	510.6	503.5	499.9	496.8	494.7	493.5	492.1
25°	536.8	523.8	509.7	498.9	488.0	483.3	481.2	479.4	478.0	476.2	475.8
27.5°	512.8	498.7	487.3	477.1	469.4	465.4	463.4	462.5	462.8	463.4	463.8
30°	494.9	481.9	472.5	463.8	456.7	453.1	452.7	452.7	454.1	454.5	455.2
32.5°	478.4	467.8	458.4	450.0	444.5	442.1	443.5	443.5	444.6	445.5	446.9
35°	454.5	445.1	437.9	430.6	425.9	427.1	427.7	428.5	430.3	432.4	433.9
37.5°	431.6	423.5	415.9	410.3	408.1	410.1	411.8	413.3	415.5	417.1	418.5
40°	415.1	409.0	401.8	396.7	397.5	398.5	400.0	401.8	403.6	404.6	406.1
42.5°	399.8	393.4	388.0	383.7	384.7	386.2	387.0	388.0	390.0	392.0	392.9
45°	376.5	371.5	366.4	363.9	364.6	365.3	366.1	367.1	368.9	370.4	370.7
47.5°	350.3	346.8	343.4	340.9	342.0	341.8	342.7	345.1	345.6	346.5	348.5
50°	333.6	330.3	326.3	325.6	325.6	325.6	325.9	328.9	328.9	330.3	331.8
52.5°	315.1	313.0	310.5	309.2	308.6	308.6	310.1	311.5	312.1	314.1	315.6
55°	287.7	285.5	283.4	282.3	281.5	282.3	285.2	285.9	287.7	288.8	289.8
57.5°	259.2	257.5	255.8	255.2	255.1	256.0	257.6	259.8	260.2	263.5	265.1
60°	240.4	237.9	236.5	236.5	235.7	238.9	238.3	241.9	242.6	244.8	247.3
62.5°	221.0	217.6	217.1	217.1	218.1	219.0	220.1	221.7	223.6	226.3	228.2
65°	189.9	188.0	190.6	190.2	189.5	191.7	191.7	193.5	195.7	198.2	202.2
67.5°	160.3	159.4	159.7	159.7	160.7	161.9	163.0	164.6	167.1	169.8	172.4
70°	140.4	141.5	139.7	141.2	142.2	142.6	143.3	145.4	148.4	150.1	153.1
72.5°	121.1	121.0	121.2	121.8	122.9	123.6	124.2	126.7	129.9	131.4	133.7
75°	93.1	92.7	93.9	93.9	95.7	96.4	97.1	98.2	101.0	103.2	105.1
77.5°	68.1	68.4	68.2	69.5	69.0	69.1	71.4	72.4	72.7	77.0	77.9
80°	51.3	52.0	52.3	52.7	53.1	52.3	54.9	56.0	56.0	58.4	60.3
82.5°	36.9	37.2	38.2	38.5	38.6	39.3	39.6	40.3	41.2	42.3	44.7
85°	18.4	19.5	19.9	19.5	19.9	19.1	20.2	20.5	20.9	20.9	20.9
87.5°	7.2	7.8	7.9	8.6	8.7	9.4	9.5	9.0	9.1	10.2	9.1
90°	6.9	8.7	10.7	12.6	14.6	16.7	17.2	17.9	18.5	19.1	19.6
92.5°	11.2	11.7	13.2	14.7	16.2	17.7	18.8	19.7	20.7	21.7	22.2
95°	17.1	14.7	16.4	18.1	19.8	21.5	22.6	23.7	24.7	25.8	26.4
97.5°	73.7	66.7	55.6	44.5	33.5	22.3	23.6	24.8	26.0	27.2	28.0
100°	129.5	119.0	95.0	71.0	46.9	22.9	24.1	25.4	26.6	27.8	28.6
102.5°	162.7	150.7	124.4	98.1	71.9	45.6	41.8	38.0	34.2	30.3	28.6
105°	213.5	207.4	193.5	179.6	165.8	151.9	124.6	97.4	70.0	42.8	29.3
107.5°	267.9	269.7	271.8	274.0	276.3	278.4	258.4	238.4	218.4	198.4	178.1
110°	304.5	306.0	307.7	309.4	311.1	312.8	307.7	302.7	297.6	292.5	278.9



TEST NUMBER: P332126-830

CATALOG NUMBER: S123DIW-S560D755U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	339.6	341.0	342.7	344.4	346.1	347.8	347.9	348.0	348.1	348.2	345.8
115°	391.4	392.6	394.0	395.3	396.7	398.1	399.6	401.2	402.7	404.3	405.4
117.5°	443.2	444.1	444.8	445.5	446.2	447.0	448.2	449.4	450.6	451.9	452.5
120°	475.8	476.7	477.2	477.7	478.2	478.5	479.8	481.1	482.3	483.5	484.1
122.5°	507.0	507.8	508.4	509.1	509.6	510.2	511.0	511.9	512.7	513.7	514.2
125°	551.5	552.4	553.0	553.6	554.2	554.9	555.2	555.4	555.8	556.1	556.4
127.5°	594.2	595.2	596.0	596.6	597.4	598.1	598.6	599.2	599.6	600.1	600.2
130°	620.9	621.8	622.4	623.0	623.6	624.2	624.8	625.5	626.0	626.7	626.9
132.5°	646.4	647.2	647.7	648.2	648.7	649.2	649.8	650.4	651.0	651.7	651.8
135°	684.1	684.9	685.5	686.1	686.7	687.3	687.8	688.2	688.7	689.2	689.2
137.5°	718.4	719.2	719.4	719.8	720.2	720.5	721.2	722.0	722.7	723.5	723.7
140°	739.6	740.3	740.7	741.2	741.7	742.2	742.7	743.4	743.9	744.6	744.8
142.5°	760.2	760.8	761.3	761.8	762.2	762.7	763.2	763.6	764.1	764.6	764.7
145°	789.5	790.1	790.4	790.8	791.1	791.4	791.6	792.0	792.3	792.6	792.8
147.5°	815.0	815.5	815.9	816.1	816.4	816.7	817.1	817.4	817.7	818.0	817.7
150°	830.7	831.0	831.4	831.7	832.0	832.3	832.6	832.9	833.2	833.5	833.5
152.5°	844.7	844.9	845.1	845.3	845.5	845.6	846.1	846.7	847.3	847.8	847.7
155°	863.7	863.6	863.7	863.9	864.0	864.2	865.0	865.7	866.5	867.3	867.2
157.5°	881.2	881.1	880.9	880.7	880.6	880.4	881.4	882.3	883.2	884.1	884.0
160°	890.6	890.5	890.3	890.1	890.0	889.9	890.8	891.7	892.7	893.5	893.5
162.5°	899.1	898.8	898.6	898.5	898.3	898.1	899.3	900.3	901.4	902.4	902.4
165°	910.2	909.9	909.7	909.6	909.5	909.3	910.5	911.7	912.9	914.2	914.3
167.5°	918.5	918.1	918.1	918.1	918.1	918.1	919.4	920.6	921.9	923.1	923.1
170°	923.5	923.1	923.1	923.1	923.1	923.1	924.4	925.6	926.9	928.1	928.1
172.5°	926.3	926.0	926.1	926.2	926.3	926.5	927.7	929.0	930.2	931.4	931.3
175°	930.5	930.2	930.3	930.5	930.7	930.8	931.9	932.9	934.1	935.1	935.0
177.5°	932.2	932.0	932.1	932.2	932.4	932.5	933.4	934.4	935.4	936.4	936.2
180°	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6



TEST NUMBER: P332126-830

CATALOG NUMBER: S123DIW-S560D755U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	745.1	745.1	745.1	745.1	745.1	745.1	745.1	745.1	745.1	745.1	745.1
2.5°	712.5	712.2	714.2	712.8	714.2	712.2	712.5	714.4	715.0	715.3	715.3
5°	663.2	664.2	660.6	660.6	660.6	664.2	663.2	665.3	667.1	668.5	670.7
7.5°	619.3	617.6	617.8	615.9	617.8	617.6	619.3	620.9	623.3	626.4	629.4
10°	592.4	590.2	589.5	589.8	589.5	590.2	592.4	596.7	598.1	601.1	604.3
12.5°	570.1	569.7	565.0	565.1	565.0	569.7	570.1	571.3	574.5	580.5	584.4
15°	544.0	537.2	536.4	538.6	536.4	537.2	544.0	544.0	545.4	550.2	552.3
17.5°	517.8	514.2	514.4	513.3	514.4	514.2	517.8	518.4	519.5	523.4	526.2
20°	504.0	501.8	501.4	498.9	501.4	501.8	504.0	504.0	505.4	507.2	510.1
22.5°	491.3	490.5	490.7	488.0	490.7	490.5	491.3	492.1	493.5	494.7	496.8
25°	475.4	477.2	475.8	475.8	475.8	477.2	475.4	475.8	476.2	478.0	479.4
27.5°	464.8	464.7	463.9	463.9	463.9	464.7	464.8	463.8	463.4	462.8	462.5
30°	456.7	456.3	457.0	457.0	457.0	456.3	456.7	455.2	454.5	454.1	452.7
32.5°	448.6	449.0	449.2	449.5	449.2	449.0	448.6	446.9	445.5	444.6	443.5
35°	436.1	436.4	437.5	436.8	437.5	436.4	436.1	433.9	432.4	430.3	428.5
37.5°	419.1	420.8	420.5	421.0	420.5	420.8	419.1	418.5	417.1	415.5	413.3
40°	406.5	407.6	407.2	407.2	407.2	407.6	406.5	406.1	404.6	403.6	401.8
42.5°	393.5	394.3	393.3	392.8	393.3	394.3	393.5	392.9	392.0	390.0	388.0
45°	372.2	371.5	372.6	371.1	372.6	371.5	372.2	370.7	370.4	368.9	367.1
47.5°	348.4	349.1	349.4	350.4	349.4	349.1	348.4	348.5	346.5	345.6	345.1
50°	332.4	334.6	334.6	334.3	334.6	334.6	332.4	331.8	330.3	328.9	328.9
52.5°	316.9	317.9	319.3	319.2	319.3	317.9	316.9	315.6	314.1	312.1	311.5
55°	292.8	293.5	294.2	294.5	294.2	293.5	292.8	289.8	288.8	287.7	285.9
57.5°	267.8	267.5	269.2	269.8	269.2	267.5	267.8	265.1	263.5	260.2	259.8
60°	250.2	250.2	253.1	254.1	253.1	250.2	250.2	247.3	244.8	242.6	241.9
62.5°	231.4	232.5	235.4	233.9	235.4	232.5	231.4	228.2	226.3	223.6	221.7
65°	204.0	206.9	206.5	207.9	206.5	206.9	204.0	202.2	198.2	195.7	193.5
67.5°	175.3	177.1	179.7	179.9	179.7	177.1	175.3	172.4	169.8	167.1	164.6
70°	156.0	157.8	159.2	160.2	159.2	157.8	156.0	153.1	150.1	148.4	145.4
72.5°	137.1	138.1	141.6	140.1	141.6	138.1	137.1	133.7	131.4	129.9	126.7
75°	107.5	110.1	112.3	111.2	112.3	110.1	107.5	105.1	103.2	101.0	98.2
77.5°	79.6	82.1	83.1	82.2	83.1	82.1	79.6	77.9	77.0	72.7	72.4
80°	62.8	62.5	64.7	64.3	64.7	62.5	62.8	60.3	58.4	56.0	56.0
82.5°	46.1	45.7	46.8	46.9	46.8	45.7	46.1	44.7	42.3	41.2	40.3
85°	22.3	23.5	22.1	21.7	22.1	23.5	22.3	20.9	20.9	20.9	20.5
87.5°	9.1	9.2	9.0	8.8	9.0	9.2	9.1	9.1	10.2	9.1	9.0
90°	19.9	20.2	20.5	20.8	20.5	20.2	19.9	19.6	19.1	18.5	17.9
92.5°	22.4	22.6	22.8	23.0	22.8	22.6	22.4	22.2	21.7	20.7	19.7
95°	26.4	26.4	26.4	26.4	26.4	26.4	26.4	26.4	25.8	24.7	23.7
97.5°	28.1	28.3	28.5	28.6	28.5	28.3	28.1	28.0	27.2	26.0	24.8
100°	28.7	28.8	28.9	29.1	28.9	28.8	28.7	28.6	27.8	26.6	25.4
102.5°	28.8	29.1	29.4	29.7	29.4	29.1	28.8	28.6	30.3	34.2	38.0
105°	29.6	29.9	30.3	30.5	30.3	29.9	29.6	29.3	42.8	70.0	97.4
107.5°	157.5	137.0	116.4	95.9	116.4	137.0	157.5	178.1	198.4	218.4	238.4
110°	256.8	234.8	212.7	190.8	212.7	234.8	256.8	278.9	292.5	297.6	302.7



TEST NUMBER: P332126-830

CATALOG NUMBER: S123DIW-S560D755U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	341.2	336.6	331.9	327.3	331.9	336.6	341.2	345.8	348.2	348.1	348.0
115°	406.0	406.6	407.2	407.8	407.2	406.6	406.0	405.4	404.3	402.7	401.2
117.5°	452.7	452.8	452.9	453.1	452.9	452.8	452.7	452.5	451.9	450.6	449.4
120°	484.1	484.1	484.1	484.1	484.1	484.1	484.1	484.1	483.5	482.3	481.1
122.5°	514.3	514.3	514.5	514.6	514.5	514.3	514.3	514.2	513.7	512.7	511.9
125°	556.8	557.0	557.3	557.6	557.3	557.0	556.8	556.4	556.1	555.8	555.4
127.5°	599.9	599.6	599.3	599.0	599.3	599.6	599.9	600.2	600.1	599.6	599.2
130°	626.5	626.2	625.9	625.6	625.9	626.2	626.5	626.9	626.7	626.0	625.5
132.5°	651.3	650.9	650.4	650.0	650.4	650.9	651.3	651.8	651.7	651.0	650.4
135°	688.7	688.2	687.8	687.3	687.8	688.2	688.7	689.2	689.2	688.7	688.2
137.5°	723.4	723.0	722.7	722.5	722.7	723.0	723.4	723.7	723.5	722.7	722.0
140°	744.4	744.1	743.9	743.5	743.9	744.1	744.4	744.8	744.6	743.9	743.4
142.5°	764.2	763.8	763.4	762.9	763.4	763.8	764.2	764.7	764.6	764.1	763.6
145°	792.8	792.8	792.8	792.8	792.8	792.8	792.8	792.8	792.6	792.3	792.0
147.5°	817.1	816.3	815.7	814.9	815.7	816.3	817.1	817.7	818.0	817.7	817.4
150°	833.0	832.5	832.1	831.6	832.1	832.5	833.0	833.5	833.5	833.2	832.9
152.5°	847.1	846.3	845.6	844.9	845.6	846.3	847.1	847.7	847.8	847.3	846.7
155°	866.3	865.3	864.4	863.5	864.4	865.3	866.3	867.2	867.3	866.5	865.7
157.5°	882.8	881.6	880.4	879.2	880.4	881.6	882.8	884.0	884.1	883.2	882.3
160°	892.4	891.4	890.2	889.2	890.2	891.4	892.4	893.5	893.5	892.7	891.7
162.5°	901.4	900.5	899.6	898.6	899.6	900.5	901.4	902.4	902.4	901.4	900.3
165°	913.2	912.1	911.1	909.9	911.1	912.1	913.2	914.3	914.2	912.9	911.7
167.5°	921.9	920.6	919.4	918.1	919.4	920.6	921.9	923.1	923.1	921.9	920.6
170°	926.9	925.6	924.4	923.1	924.4	925.6	926.9	928.1	928.1	926.9	925.6
172.5°	930.0	928.7	927.3	926.0	927.3	928.7	930.0	931.3	931.4	930.2	929.0
175°	933.8	932.6	931.3	930.1	931.3	932.6	933.8	935.0	935.1	934.1	932.9
177.5°	935.0	933.8	932.6	931.3	932.6	933.8	935.0	936.2	936.4	935.4	934.4
180°	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6



TEST NUMBER: P332126-830

CATALOG NUMBER: S123DIW-S560D755U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	745.1	745.1	745.1	745.1	745.1	745.1	745.1	745.1	745.1	745.1	745.1
2.5°	714.4	714.4	719.9	723.4	727.7	730.7	732.6	734.7	738.1	742.8	748.0
5°	673.6	675.0	683.0	691.0	698.5	705.0	710.4	716.9	724.9	734.6	745.5
7.5°	634.0	639.6	647.6	657.3	667.9	677.4	686.9	697.7	708.8	723.2	738.4
10°	608.6	614.7	624.5	636.8	648.0	659.1	671.1	682.6	696.7	713.7	733.2
12.5°	586.4	592.2	602.3	615.7	626.3	638.7	652.3	667.3	683.2	703.6	725.7
15°	555.5	562.4	574.7	581.2	597.5	612.3	624.9	646.5	666.8	687.7	713.3
17.5°	530.3	534.1	544.0	556.1	568.3	584.8	601.4	619.4	639.6	665.2	697.3
20°	512.9	516.2	527.1	539.7	552.7	567.9	582.7	600.7	623.4	650.5	685.1
22.5°	499.9	503.5	510.6	524.1	536.2	548.7	563.5	585.1	609.3	635.7	673.4
25°	481.2	483.3	488.0	498.9	509.7	523.8	536.8	557.0	581.9	612.9	650.5
27.5°	463.4	465.4	469.4	477.1	487.3	498.7	512.8	530.0	555.3	589.0	628.9
30°	452.7	453.1	456.7	463.8	472.5	481.9	494.9	514.4	538.2	572.5	614.4
32.5°	443.5	442.1	444.5	450.0	458.4	467.8	478.4	497.7	520.7	554.3	597.4
35°	427.7	427.1	425.9	430.6	437.9	445.1	454.5	468.9	494.9	526.3	571.5
37.5°	411.8	410.1	408.1	410.3	415.9	423.5	431.6	444.4	466.8	501.4	544.6
40°	400.0	398.5	397.5	396.7	401.8	409.0	415.1	427.4	448.4	481.2	523.8
42.5°	387.0	386.2	384.7	383.7	388.0	393.4	399.8	410.7	431.6	462.4	502.8
45°	366.1	365.3	364.6	363.9	366.4	371.5	376.5	384.5	402.5	432.4	468.9
47.5°	342.7	341.8	342.0	340.9	343.4	346.8	350.3	358.8	376.2	400.3	427.0
50°	325.9	325.6	325.6	325.6	326.3	330.3	333.6	340.1	355.9	380.1	399.3
52.5°	310.1	308.6	308.6	309.2	310.5	313.0	315.1	322.2	336.0	355.9	373.2
55°	285.2	282.3	281.5	282.3	283.4	285.5	287.7	293.5	305.4	320.2	330.3
57.5°	257.6	256.0	255.1	255.2	255.8	257.5	259.2	265.5	274.8	282.6	289.1
60°	238.3	238.9	235.7	236.5	236.5	237.9	240.4	244.4	252.3	257.8	264.3
62.5°	220.1	219.0	218.1	217.1	217.1	217.6	221.0	224.1	230.9	233.8	238.8
65°	191.7	191.7	189.5	190.2	190.6	188.0	189.9	193.5	197.8	198.9	203.6
67.5°	163.0	161.9	160.7	159.7	159.7	159.4	160.3	162.1	165.4	165.8	169.4
70°	143.3	142.6	142.2	141.2	139.7	141.5	140.4	142.2	144.0	144.4	146.6
72.5°	124.2	123.6	122.9	121.8	121.2	121.0	121.1	123.2	124.4	123.9	126.3
75°	97.1	96.4	95.7	93.9	93.9	92.7	93.1	94.5	96.0	94.9	97.1
77.5°	71.4	69.1	69.0	69.5	68.2	68.4	68.1	67.8	68.4	68.5	70.5
80°	54.9	52.3	53.1	52.7	52.3	52.0	51.3	51.7	52.0	52.3	53.4
82.5°	39.6	39.3	38.6	38.5	38.2	37.2	36.9	37.5	37.8	37.6	38.5
85°	20.2	19.1	19.9	19.5	19.9	19.5	18.4	18.4	19.1	18.8	19.5
87.5°	9.5	9.4	8.7	8.6	7.9	7.8	7.2	7.2	7.1	6.8	7.1
90°	17.2	16.7	14.6	12.6	10.7	8.7	6.9	5.3	3.8	2.3	0.7
92.5°	18.8	17.7	16.2	14.7	13.2	11.7	11.2	11.6	12.1	12.4	12.9
95°	22.6	21.5	19.8	18.1	16.4	14.7	17.1	23.4	29.7	36.0	42.3
97.5°	23.6	22.3	33.5	44.5	55.6	66.7	73.7	76.5	79.4	82.2	85.0
100°	24.1	22.9	46.9	71.0	95.0	119.0	129.5	126.5	123.4	120.3	117.3
102.5°	41.8	45.6	71.9	98.1	124.4	150.7	162.7	160.5	158.3	156.1	153.8
105°	124.6	151.9	165.8	179.6	193.5	207.4	213.5	211.8	210.1	208.4	206.7
107.5°	258.4	278.4	276.3	274.0	271.8	269.7	267.9	266.6	265.1	263.8	262.4
110°	307.7	312.8	311.1	309.4	307.7	306.0	304.5	303.3	302.1	300.9	299.6



TEST NUMBER: P332126-830

CATALOG NUMBER: S123DIW-S560D755U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	347.9	347.8	346.1	344.4	342.7	341.0	339.6	338.5	337.3	336.2	335.2
115°	399.6	398.1	396.7	395.3	394.0	392.6	391.4	390.5	389.6	388.6	387.7
117.5°	448.2	447.0	446.2	445.5	444.8	444.1	443.2	442.1	440.9	439.8	438.7
120°	479.8	478.5	478.2	477.7	477.2	476.7	475.8	474.4	473.1	471.6	470.2
122.5°	511.0	510.2	509.6	509.1	508.4	507.8	507.0	505.9	504.7	503.6	502.5
125°	555.2	554.9	554.2	553.6	553.0	552.4	551.5	550.3	549.0	547.8	546.6
127.5°	598.6	598.1	597.4	596.6	596.0	595.2	594.2	593.0	591.7	590.5	589.3
130°	624.8	624.2	623.6	623.0	622.4	621.8	620.9	619.6	618.4	617.2	615.9
132.5°	649.8	649.2	648.7	648.2	647.7	647.2	646.4	645.1	643.9	642.6	641.4
135°	687.8	687.3	686.7	686.1	685.5	684.9	684.1	683.2	682.2	681.4	680.4
137.5°	721.2	720.5	720.2	719.8	719.4	719.2	718.4	717.2	716.0	714.8	713.7
140°	742.7	742.2	741.7	741.2	740.7	740.3	739.6	738.7	737.7	736.8	735.8
142.5°	763.2	762.7	762.2	761.8	761.3	760.8	760.2	759.2	758.3	757.3	756.4
145°	791.6	791.4	791.1	790.8	790.4	790.1	789.5	788.3	787.3	786.2	785.1
147.5°	817.1	816.7	816.4	816.1	815.9	815.5	815.0	814.3	813.6	812.8	812.2
150°	832.6	832.3	832.0	831.7	831.4	831.0	830.7	830.2	829.7	829.2	828.9
152.5°	846.1	845.6	845.5	845.3	845.1	844.9	844.7	844.4	844.2	844.0	843.8
155°	865.0	864.2	864.0	863.9	863.7	863.6	863.7	863.9	864.3	864.6	864.9
157.5°	881.4	880.4	880.6	880.7	880.9	881.1	881.2	881.2	881.2	881.3	881.3
160°	890.8	889.9	890.0	890.1	890.3	890.5	890.6	890.8	891.0	891.1	891.3
162.5°	899.3	898.1	898.3	898.5	898.6	898.8	899.1	899.5	899.8	900.3	900.7
165°	910.5	909.3	909.5	909.6	909.7	909.9	910.2	910.7	911.2	911.6	912.1
167.5°	919.4	918.1	918.1	918.1	918.1	918.1	918.5	919.1	919.7	920.3	921.0
170°	924.4	923.1	923.1	923.1	923.1	923.1	923.5	924.1	924.7	925.3	926.0
172.5°	927.7	926.5	926.3	926.2	926.1	926.0	926.3	927.1	927.7	928.5	929.3
175°	931.9	930.8	930.7	930.5	930.3	930.2	930.5	931.2	932.0	932.7	933.6
177.5°	933.4	932.5	932.4	932.2	932.1	932.0	932.2	932.8	933.4	934.1	934.6
180°	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6



TEST NUMBER: P332126-830

CATALOG NUMBER: S123DIW-S560D755U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	745.1	745.1	745.1	745.1	745.1	745.1	745.1	745.1	745.1	745.1	745.1
2.5°	749.7	751.1	756.0	759.5	763.6	765.9	768.2	770.0	772.2	772.8	781.2
5°	753.0	760.3	772.9	782.2	793.8	806.4	815.1	819.1	829.5	838.2	855.5
7.5°	752.1	767.4	786.6	806.3	827.6	847.2	864.2	884.4	898.8	920.4	941.7
10°	751.2	771.8	796.4	821.6	851.2	878.6	903.2	930.7	953.4	983.4	1009.0
12.5°	748.7	773.5	807.6	837.4	873.5	911.3	947.6	982.9	1003.1	1052.9	1076.6
15°	742.2	771.8	814.4	859.9	909.4	954.1	1000.3	1037.1	1096.6	1140.4	1168.2
17.5°	729.9	771.4	821.9	876.8	936.9	995.9	1048.2	1104.1	1167.3	1220.1	1276.5
20°	724.2	769.6	826.0	886.6	949.0	1015.8	1075.3	1142.6	1211.4	1263.5	1335.7
22.5°	713.5	765.0	825.7	893.2	960.0	1029.1	1098.8	1166.5	1246.1	1317.8	1386.5
25°	696.0	753.8	816.5	892.0	970.3	1039.6	1123.0	1213.0	1296.0	1388.0	1456.6
27.5°	677.7	739.3	802.3	872.4	956.7	1039.0	1143.9	1245.4	1346.9	1426.4	1477.2
30°	663.5	723.4	788.4	859.1	942.5	1040.4	1157.7	1268.5	1367.4	1435.7	1464.1
32.5°	648.2	709.0	766.5	840.7	929.5	1039.5	1166.4	1282.0	1368.6	1414.0	1408.4
35°	624.2	675.0	731.0	802.5	907.2	1033.1	1171.4	1283.3	1336.3	1326.6	1253.0
37.5°	589.5	632.4	687.4	765.6	881.2	1019.8	1161.3	1245.3	1241.8	1162.4	1055.7
40°	567.9	604.3	657.3	739.7	860.9	1011.2	1145.4	1200.0	1153.8	1042.9	915.1
42.5°	539.5	573.1	626.1	710.8	838.8	993.5	1115.1	1130.9	1040.5	912.9	795.9
45°	495.7	525.3	580.1	667.5	805.4	955.2	1041.1	1002.5	880.8	749.0	659.9
47.5°	448.5	479.3	532.1	621.8	757.1	897.5	938.4	856.3	731.3	624.5	542.6
50°	418.8	448.4	499.9	590.6	724.5	850.2	867.1	761.0	646.2	552.3	485.1
52.5°	388.7	416.6	467.3	558.3	686.4	795.2	784.8	676.7	571.1	491.1	438.4
55°	344.0	370.4	418.8	504.0	620.6	706.8	668.9	565.7	478.3	416.2	376.2
57.5°	304.1	329.3	371.0	448.0	549.3	608.6	560.4	473.4	404.0	356.2	326.3
60°	276.9	299.3	338.9	410.5	498.5	543.7	496.0	419.1	360.6	322.3	295.7
62.5°	251.2	270.7	307.5	372.3	448.8	486.7	438.6	373.4	323.7	289.7	267.0
65°	212.3	230.0	262.4	313.0	375.8	401.1	359.6	306.8	268.2	243.0	227.8
67.5°	176.7	191.7	219.8	259.6	305.9	324.2	292.7	251.8	222.7	202.5	190.4
70°	153.1	166.1	188.0	222.3	264.3	278.3	248.7	215.2	193.9	177.6	166.5
72.5°	133.1	142.7	162.7	189.2	224.1	235.3	214.6	185.1	165.2	153.1	144.2
75°	101.4	109.3	122.3	143.6	167.9	174.4	158.8	140.4	127.1	118.4	111.5
77.5°	73.1	79.0	88.4	101.5	118.3	124.1	114.3	102.0	92.3	86.4	82.6
80°	55.2	59.9	67.9	78.7	88.8	92.1	86.2	76.9	70.0	66.8	63.5
82.5°	40.8	43.5	48.3	55.6	62.5	66.4	61.5	55.8	52.1	49.2	48.0
85°	20.5	22.1	24.2	27.1	31.4	32.9	31.0	29.6	27.4	25.6	25.6
87.5°	7.9	8.3	9.4	10.4	11.9	13.1	13.2	13.0	13.1	13.0	12.8
90°	2.3	3.8	5.3	6.9	8.7	10.7	12.6	14.6	16.7	17.2	17.9
92.5°	12.4	12.1	11.6	11.2	11.7	13.2	14.7	16.2	17.7	18.8	19.7
95°	36.0	29.7	23.4	17.1	14.7	16.4	18.1	19.8	21.5	22.6	23.7
97.5°	82.2	79.4	76.5	73.7	66.7	55.6	44.5	33.5	22.3	23.6	24.8
100°	120.3	123.4	126.5	129.5	119.0	95.0	71.0	46.9	22.9	24.1	25.4
102.5°	156.1	158.3	160.5	162.7	150.7	124.4	98.1	71.9	45.6	41.8	38.0
105°	208.4	210.1	211.8	213.5	207.4	193.5	179.6	165.8	151.9	124.6	97.4
107.5°	263.8	265.1	266.6	267.9	269.7	271.8	274.0	276.3	278.4	258.4	238.4
110°	300.9	302.1	303.3	304.5	306.0	307.7	309.4	311.1	312.8	307.7	302.7



TEST NUMBER: P332126-830

CATALOG NUMBER: S123DIW-S560D755U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	336.2	337.3	338.5	339.6	341.0	342.7	344.4	346.1	347.8	347.9	348.0
115°	388.6	389.6	390.5	391.4	392.6	394.0	395.3	396.7	398.1	399.6	401.2
117.5°	439.8	440.9	442.1	443.2	444.1	444.8	445.5	446.2	447.0	448.2	449.4
120°	471.6	473.1	474.4	475.8	476.7	477.2	477.7	478.2	478.5	479.8	481.1
122.5°	503.6	504.7	505.9	507.0	507.8	508.4	509.1	509.6	510.2	511.0	511.9
125°	547.8	549.0	550.3	551.5	552.4	553.0	553.6	554.2	554.9	555.2	555.4
127.5°	590.5	591.7	593.0	594.2	595.2	596.0	596.6	597.4	598.1	598.6	599.2
130°	617.2	618.4	619.6	620.9	621.8	622.4	623.0	623.6	624.2	624.8	625.5
132.5°	642.6	643.9	645.1	646.4	647.2	647.7	648.2	648.7	649.2	649.8	650.4
135°	681.4	682.2	683.2	684.1	684.9	685.5	686.1	686.7	687.3	687.8	688.2
137.5°	714.8	716.0	717.2	718.4	719.2	719.4	719.8	720.2	720.5	721.2	722.0
140°	736.8	737.7	738.7	739.6	740.3	740.7	741.2	741.7	742.2	742.7	743.4
142.5°	757.3	758.3	759.2	760.2	760.8	761.3	761.8	762.2	762.7	763.2	763.6
145°	786.2	787.3	788.3	789.5	790.1	790.4	790.8	791.1	791.4	791.6	792.0
147.5°	812.8	813.6	814.3	815.0	815.5	815.9	816.1	816.4	816.7	817.1	817.4
150°	829.2	829.7	830.2	830.7	831.0	831.4	831.7	832.0	832.3	832.6	832.9
152.5°	844.0	844.2	844.4	844.7	844.9	845.1	845.3	845.5	845.6	846.1	846.7
155°	864.6	864.3	863.9	863.7	863.6	863.7	863.9	864.0	864.2	865.0	865.7
157.5°	881.3	881.2	881.2	881.2	881.1	880.9	880.7	880.6	880.4	881.4	882.3
160°	891.1	891.0	890.8	890.6	890.5	890.3	890.1	890.0	889.9	890.8	891.7
162.5°	900.3	899.8	899.5	899.1	898.8	898.6	898.5	898.3	898.1	899.3	900.3
165°	911.6	911.2	910.7	910.2	909.9	909.7	909.6	909.5	909.3	910.5	911.7
167.5°	920.3	919.7	919.1	918.5	918.1	918.1	918.1	918.1	918.1	919.4	920.6
170°	925.3	924.7	924.1	923.5	923.1	923.1	923.1	923.1	923.1	924.4	925.6
172.5°	928.5	927.7	927.1	926.3	926.0	926.1	926.2	926.3	926.5	927.7	929.0
175°	932.7	932.0	931.2	930.5	930.2	930.3	930.5	930.7	930.8	931.9	932.9
177.5°	934.1	933.4	932.8	932.2	932.0	932.1	932.2	932.4	932.5	933.4	934.4
180°	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6



TEST NUMBER: P332126-830

CATALOG NUMBER: S123DIW-S560D755U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	745.1	745.1	745.1	745.1	745.1	745.1	745.1
2.5°	784.1	784.4	787.5	789.9	788.7	790.1	790.7
5°	856.6	869.6	876.5	881.6	881.9	882.2	885.1
7.5°	959.5	973.5	983.6	999.1	1003.7	1009.0	1007.5
10°	1034.6	1055.2	1072.9	1082.2	1092.3	1107.1	1095.2
12.5°	1104.8	1141.2	1168.2	1182.7	1192.3	1195.2	1189.4
15°	1220.5	1268.2	1293.8	1293.1	1325.6	1339.6	1317.6
17.5°	1326.6	1370.6	1405.8	1423.9	1451.0	1457.0	1454.2
20°	1391.6	1439.6	1467.1	1498.1	1512.2	1524.8	1527.0
22.5°	1447.7	1490.7	1520.2	1546.1	1557.8	1563.8	1567.4
25°	1505.3	1539.3	1557.0	1565.9	1569.2	1568.5	1563.8
27.5°	1501.4	1503.9	1484.5	1465.4	1448.2	1428.9	1422.3
30°	1462.4	1432.0	1377.9	1347.2	1302.1	1266.3	1280.8
32.5°	1359.8	1299.5	1238.7	1171.6	1116.1	1100.3	1084.4
35°	1160.6	1054.4	992.4	920.2	891.3	862.4	842.5
37.5°	939.0	856.9	783.2	735.9	707.0	688.8	678.9
40°	811.9	737.8	677.2	638.9	616.9	596.3	593.4
42.5°	710.5	641.7	596.1	565.6	544.4	535.7	529.3
45°	581.9	533.9	503.2	481.5	467.5	462.0	454.9
47.5°	492.6	458.6	435.5	420.8	410.2	406.1	405.6
50°	442.6	414.4	397.5	385.9	377.6	376.2	370.4
52.5°	405.0	380.6	367.4	357.3	351.3	347.2	345.5
55°	351.6	335.4	323.5	317.6	313.0	309.0	309.0
57.5°	307.6	294.1	286.2	281.3	279.8	277.0	275.2
60°	280.5	268.9	262.8	258.4	255.6	255.9	252.7
62.5°	253.9	246.4	240.5	236.2	232.8	232.8	233.1
65°	216.2	210.5	206.1	204.7	202.6	200.0	200.7
67.5°	183.2	177.9	174.5	172.0	171.3	169.8	172.0
70°	159.6	155.6	153.1	150.9	150.1	150.5	152.3
72.5°	137.9	135.1	133.5	132.4	130.8	130.9	132.1
75°	108.3	106.1	104.7	103.6	103.2	103.2	103.2
77.5°	79.6	79.1	78.4	76.8	76.9	77.3	77.4
80°	62.8	61.7	61.4	60.6	59.6	58.8	60.6
82.5°	46.9	45.8	45.5	45.3	43.6	43.5	45.1
85°	25.3	24.2	24.5	24.2	24.2	23.8	23.8
87.5°	12.6	12.4	12.3	12.6	12.4	12.2	12.8
90°	18.5	19.1	19.6	19.9	20.2	20.5	20.8
92.5°	20.7	21.7	22.2	22.4	22.6	22.8	23.0
95°	24.7	25.8	26.4	26.4	26.4	26.4	26.4
97.5°	26.0	27.2	28.0	28.1	28.3	28.5	28.6
100°	26.6	27.8	28.6	28.7	28.8	28.9	29.1
102.5°	34.2	30.3	28.6	28.8	29.1	29.4	29.7
105°	70.0	42.8	29.3	29.6	29.9	30.3	30.5
107.5°	218.4	198.4	178.1	157.5	137.0	116.4	95.9
110°	297.6	292.5	278.9	256.8	234.8	212.7	190.8



TEST NUMBER: P332126-830

CATALOG NUMBER: S123DIW-S560D755U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	348.1	348.2	345.8	341.2	336.6	331.9	327.3
115°	402.7	404.3	405.4	406.0	406.6	407.2	407.8
117.5°	450.6	451.9	452.5	452.7	452.8	452.9	453.1
120°	482.3	483.5	484.1	484.1	484.1	484.1	484.1
122.5°	512.7	513.7	514.2	514.3	514.3	514.5	514.6
125°	555.8	556.1	556.4	556.8	557.0	557.3	557.6
127.5°	599.6	600.1	600.2	599.9	599.6	599.3	599.0
130°	626.0	626.7	626.9	626.5	626.2	625.9	625.6
132.5°	651.0	651.7	651.8	651.3	650.9	650.4	650.0
135°	688.7	689.2	689.2	688.7	688.2	687.8	687.3
137.5°	722.7	723.5	723.7	723.4	723.0	722.7	722.5
140°	743.9	744.6	744.8	744.4	744.1	743.9	743.5
142.5°	764.1	764.6	764.7	764.2	763.8	763.4	762.9
145°	792.3	792.6	792.8	792.8	792.8	792.8	792.8
147.5°	817.7	818.0	817.7	817.1	816.3	815.7	814.9
150°	833.2	833.5	833.5	833.0	832.5	832.1	831.6
152.5°	847.3	847.8	847.7	847.1	846.3	845.6	844.9
155°	866.5	867.3	867.2	866.3	865.3	864.4	863.5
157.5°	883.2	884.1	884.0	882.8	881.6	880.4	879.2
160°	892.7	893.5	893.5	892.4	891.4	890.2	889.2
162.5°	901.4	902.4	902.4	901.4	900.5	899.6	898.6
165°	912.9	914.2	914.3	913.2	912.1	911.1	909.9
167.5°	921.9	923.1	923.1	921.9	920.6	919.4	918.1
170°	926.9	928.1	928.1	926.9	925.6	924.4	923.1
172.5°	930.2	931.4	931.3	930.0	928.7	927.3	926.0
175°	934.1	935.1	935.0	933.8	932.6	931.3	930.1
177.5°	935.4	936.4	936.2	935.0	933.8	932.6	931.3
180°	933.6	933.6	933.6	933.6	933.6	933.6	933.6

(END OF REPORT)