

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: NEO-RAY

Report Number: P332414-830

Luminaire Tested: **S123RDIW-S560D755U830-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332414-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S560D755U830-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 755 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4949.3 lumens
Efficiency: N/A
Efficacy: 131.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 37.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332414-830

CATALOG NUMBER: S123RDIW-S560D755U830-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332414-830

CATALOG NUMBER: S123RDIW-S560D755U830-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR																																														
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	49	49	49	42																												
1	97	93	89	86	88	85	82	79	70	68	66	57	55	54	44	43	42	37																												
2	88	81	76	71	81	75	70	65	62	58	55	50	48	46	40	38	37	32																												
3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	35	33	32	27																												
4	74	64	56	51	68	59	52	47	49	44	40	40	37	34	32	30	28	24																												
5	68	57	49	44	62	53	46	41	44	39	35	36	33	30	29	26	24	21																												
6	63	51	44	38	57	47	41	36	40	35	31	33	29	26	26	24	22	19																												
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	24	22	19	17																												
8	54	42	35	30	49	39	32	28	33	28	24	28	24	21	22	20	17	15																												
9	50	39	31	26	46	36	29	25	30	25	22	25	22	19	21	18	16	14																												
10	47	35	28	24	43	33	27	22	28	23	20	24	20	17	19	16	14	12																												

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9077	9077	9077	9077
5°	10821	9116	8028	9116
10°	13511	9063	7252	9063
15°	15858	8971	6614	8971
20°	17699	8833	6071	8833
25°	17416	8687	5738	8687
30°	12519	8552	5393	8552
35°	8359	8377	5171	8377
40°	6159	8168	4942	8168
45°	5165	7798	4714	7798
50°	4558	7316	4401	7316
55°	3997	6762	3969	6762
60°	3559	6232	3638	6232
65°	3125	5662	3385	5662
70°	2452	5158	3091	5158
75°	2163	4504	2824	4504
80°	1878	3825	2777	3825
85°	1519	3075	2939	3075



TEST NUMBER: P332414-830

CATALOG NUMBER: S123RDIW-S560D755U830-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	82.9	1.7
10°-20°	259.1	5.2
20°-30°	407.0	8.2
30°-40°	424.7	8.6
40°-50°	363.4	7.3
50°-60°	277.0	5.6
60°-70°	177.6	3.6
70°-80°	85.4	1.7
80°-90°	25.2	0.5
90°-100°	33.9	0.7
100°-110°	161.8	3.3
110°-120°	388.6	7.9
120°-130°	494.8	10.0
130°-140°	528.7	10.7
140°-150°	494.4	10.0
150°-160°	398.8	8.1
160°-170°	257.4	5.2
170°-180°	88.7	1.8
0°-30°	749.1	15.1
0°-40°	1173.7	23.7
0°-60°	1814.2	36.7
0°-90°	2102.4	42.5
90°-120°	584.3	11.8
90°-150°	2102.1	42.5
90°-180°	2847.0	57.5
0°-180°	4949.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	843	843	843	843	843	
5°	1002	844	743	844	1002	103
15°	1423	805	594	805	1423	404
25°	1466	731	483	731	1466	630
35°	636	638	394	638	636	417
45°	339	512	310	512	339	267
55°	213	360	212	360	213	193
65°	123	222	133	222	123	121
75°	52	108	68	108	52	56
85°	12	25	24	25	12	15
90°	21	1	21	1	21	10
95°	26	42	26	42	26	22
105°	30	207	30	207	30	70
115°	408	388	408	388	408	377
125°	558	547	558	547	558	498
135°	687	680	687	680	687	530
145°	793	785	793	785	793	495
155°	864	865	864	865	864	398
165°	910	912	910	912	910	257
175°	930	934	930	934	930	89
180°	934	934	934	934	934	



TEST NUMBER: P332414-830

CATALOG NUMBER: S123RDIW-S560D755U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3
2.5°	898.1	899.4	895.6	895.0	890.7	889.6	889.6	883.4	879.7	874.8	871.9
5°	1001.5	1007.2	1004.4	997.9	987.0	984.5	977.6	966.8	954.5	939.3	932.2
7.5°	1130.4	1138.3	1135.2	1125.2	1113.9	1104.7	1085.3	1067.3	1042.2	1020.1	1001.2
10°	1236.1	1227.8	1221.3	1211.5	1201.1	1184.1	1163.9	1136.1	1104.0	1078.7	1050.6
12.5°	1315.2	1313.9	1305.6	1295.6	1280.8	1264.7	1239.8	1206.0	1168.7	1132.1	1099.9
15°	1423.1	1425.3	1419.8	1409.4	1388.5	1359.9	1322.4	1308.3	1254.9	1215.1	1175.4
17.5°	1497.8	1497.3	1496.6	1482.1	1460.8	1440.4	1405.6	1368.6	1320.2	1264.2	1210.8
20°	1545.1	1541.5	1542.3	1526.0	1510.1	1486.7	1452.7	1398.9	1359.2	1294.6	1239.3
22.5°	1544.0	1543.2	1546.0	1540.4	1528.9	1510.9	1484.2	1438.8	1388.1	1322.9	1260.7
25°	1466.4	1463.6	1480.5	1485.2	1503.6	1506.8	1498.9	1474.0	1426.0	1358.9	1282.0
27.5°	1227.3	1225.7	1257.2	1296.6	1346.6	1385.4	1423.0	1441.1	1426.0	1377.9	1300.9
30°	1007.2	1041.1	1057.1	1114.1	1177.6	1253.4	1319.8	1383.0	1398.5	1377.6	1314.5
32.5°	836.2	865.8	879.1	928.1	987.3	1076.1	1175.7	1265.2	1328.4	1344.4	1306.4
35°	636.1	636.5	666.8	688.4	743.3	834.6	931.4	1051.2	1170.4	1260.7	1270.1
37.5°	507.6	509.3	527.7	549.3	590.5	638.8	724.0	823.6	961.2	1099.8	1181.0
40°	438.3	441.5	455.2	476.5	506.1	542.6	609.1	702.9	817.7	971.9	1097.9
42.5°	393.8	399.1	406.1	422.5	440.8	475.0	528.8	601.2	705.6	851.4	996.7
45°	339.3	342.2	347.6	355.2	371.8	395.7	431.8	480.5	567.1	684.5	830.0
47.5°	299.4	297.8	303.5	309.7	320.7	337.0	361.2	401.0	462.8	556.9	680.3
50°	272.2	271.8	275.8	280.5	291.0	302.9	322.7	352.7	401.8	479.8	592.8
52.5°	246.8	248.2	251.0	256.8	264.4	274.0	291.8	313.4	355.6	422.9	517.1
55°	213.0	214.1	218.0	221.3	226.7	236.5	247.7	265.7	294.5	341.5	419.1
57.5°	184.4	183.9	187.8	188.5	194.6	202.6	211.2	225.3	246.2	281.1	333.4
60°	165.3	164.3	167.5	170.0	173.2	179.7	187.0	200.8	217.4	243.0	287.8
62.5°	148.0	147.5	149.9	152.4	155.0	161.0	167.1	177.6	190.8	212.4	247.9
65°	122.7	123.9	124.9	126.0	127.4	131.0	136.9	144.0	153.1	168.2	193.9
67.5°	96.4	97.6	97.9	100.1	103.2	105.5	109.1	115.5	121.8	134.5	149.1
70°	77.9	77.6	77.9	79.1	83.0	87.0	91.7	96.4	100.4	109.4	121.7
72.5°	67.0	66.4	67.3	67.5	69.5	70.5	73.5	77.9	83.0	89.2	98.0
75°	52.0	52.0	52.0	52.0	53.4	54.2	55.2	56.4	58.2	61.0	67.5
77.5°	38.5	38.5	39.0	39.3	39.7	40.1	40.7	41.8	42.4	44.0	46.8
80°	30.3	30.7	30.3	30.7	30.7	31.4	31.8	32.9	33.2	35.1	36.1
82.5°	22.8	22.6	22.8	23.2	23.2	23.9	23.9	24.8	24.9	25.7	26.9
85°	12.3	11.6	12.3	11.9	12.6	11.9	12.3	13.0	13.0	13.4	14.8
87.5°	7.1	7.5	6.9	7.2	7.1	7.3	7.2	7.1	7.5	7.1	7.0
90°	20.8	20.5	20.2	19.9	19.6	19.1	18.5	17.9	17.2	16.7	14.6
92.5°	23.0	22.8	22.6	22.4	22.2	21.7	20.7	19.7	18.8	17.7	16.2
95°	26.4	26.4	26.4	26.4	26.4	25.8	24.7	23.7	22.6	21.5	19.8
97.5°	28.6	28.5	28.3	28.1	28.0	27.2	26.0	24.8	23.6	22.3	33.5
100°	29.1	28.9	28.8	28.7	28.6	27.8	26.6	25.4	24.1	22.9	46.9
102.5°	29.7	29.4	29.1	28.8	28.6	30.3	34.2	38.0	41.8	45.6	71.9
105°	30.5	30.3	29.9	29.6	29.3	42.8	70.0	97.4	124.6	151.9	165.8
107.5°	95.9	116.4	137.0	157.5	178.1	198.4	218.4	238.4	258.4	278.4	276.3
110°	190.8	212.7	234.8	256.8	278.9	292.5	297.6	302.7	307.7	312.8	311.1



TEST NUMBER: P332414-830

CATALOG NUMBER: S123RDIW-S560D755U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	327.3	331.9	336.6	341.2	345.8	348.2	348.1	348.0	347.9	347.8	346.1
115°	407.8	407.2	406.6	406.0	405.4	404.3	402.7	401.2	399.6	398.1	396.7
117.5°	453.1	452.9	452.8	452.7	452.5	451.9	450.6	449.4	448.2	447.0	446.2
120°	484.1	484.1	484.1	484.1	484.1	483.5	482.3	481.1	479.8	478.5	478.2
122.5°	514.6	514.5	514.3	514.3	514.2	513.7	512.7	511.9	511.0	510.2	509.6
125°	557.6	557.3	557.0	556.8	556.4	556.1	555.8	555.4	555.2	554.9	554.2
127.5°	599.0	599.3	599.6	599.9	600.2	600.1	599.6	599.2	598.6	598.1	597.4
130°	625.6	625.9	626.2	626.5	626.9	626.7	626.0	625.5	624.8	624.2	623.6
132.5°	650.0	650.4	650.9	651.3	651.8	651.7	651.0	650.4	649.8	649.2	648.7
135°	687.3	687.8	688.2	688.7	689.2	689.2	688.7	688.2	687.8	687.3	686.7
137.5°	722.5	722.7	723.0	723.4	723.7	723.5	722.7	722.0	721.2	720.5	720.2
140°	743.5	743.9	744.1	744.4	744.8	744.6	743.9	743.4	742.7	742.2	741.7
142.5°	762.9	763.4	763.8	764.2	764.7	764.6	764.1	763.6	763.2	762.7	762.2
145°	792.8	792.8	792.8	792.8	792.8	792.6	792.3	792.0	791.6	791.4	791.1
147.5°	814.9	815.7	816.3	817.1	817.7	818.0	817.7	817.4	817.1	816.7	816.4
150°	831.6	832.1	832.5	833.0	833.5	833.5	833.2	832.9	832.6	832.3	832.0
152.5°	844.9	845.6	846.3	847.1	847.7	847.8	847.3	846.7	846.1	845.6	845.5
155°	863.5	864.4	865.3	866.3	867.2	867.3	866.5	865.7	865.0	864.2	864.0
157.5°	879.2	880.4	881.6	882.8	884.0	884.1	883.2	882.3	881.4	880.4	880.6
160°	889.2	890.2	891.4	892.4	893.5	893.5	892.7	891.7	890.8	889.9	890.0
162.5°	898.6	899.6	900.5	901.4	902.4	902.4	901.4	900.3	899.3	898.1	898.3
165°	909.9	911.1	912.1	913.2	914.3	914.2	912.9	911.7	910.5	909.3	909.5
167.5°	918.1	919.4	920.6	921.9	923.1	923.1	921.9	920.6	919.4	918.1	918.1
170°	923.1	924.4	925.6	926.9	928.1	928.1	926.9	925.6	924.4	923.1	923.1
172.5°	926.0	927.3	928.7	930.0	931.3	931.4	930.2	929.0	927.7	926.5	926.3
175°	930.1	931.3	932.6	933.8	935.0	935.1	934.1	932.9	931.9	930.8	930.7
177.5°	931.3	932.6	933.8	935.0	936.2	936.4	935.4	934.4	933.4	932.5	932.4
180°	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6



TEST NUMBER: P332414-830

CATALOG NUMBER: S123RDIW-S560D755U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3
2.5°	870.7	869.9	865.8	861.2	855.2	851.1	847.9	846.2	841.0	834.6	830.3
5°	924.5	913.7	902.2	888.1	875.1	861.8	853.5	843.7	831.8	818.4	809.0
7.5°	982.1	960.9	938.0	914.5	891.1	870.2	851.7	835.8	816.9	797.8	784.3
10°	1026.3	995.3	963.2	930.3	900.3	872.2	850.6	829.2	806.5	784.5	767.9
12.5°	1066.5	1025.7	988.6	948.2	909.9	876.3	845.1	820.0	792.7	769.2	750.3
15°	1117.3	1075.4	1030.7	969.3	918.4	875.8	837.9	805.0	771.8	743.0	724.5
17.5°	1164.8	1101.8	1041.7	990.4	924.4	871.1	824.8	785.5	749.1	718.5	695.8
20°	1184.5	1123.5	1058.1	992.8	927.8	868.3	814.5	771.1	733.2	698.5	677.6
22.5°	1196.3	1127.2	1058.4	988.2	919.2	857.2	804.1	756.4	715.3	682.4	656.6
25°	1210.1	1127.8	1052.0	982.7	912.3	845.1	781.9	731.4	687.0	652.0	624.5
27.5°	1219.2	1122.4	1032.7	955.7	884.3	817.5	759.6	706.0	660.9	623.9	594.5
30°	1221.0	1118.0	1018.0	934.6	862.0	800.7	739.3	688.1	640.5	601.1	573.6
32.5°	1223.2	1107.4	998.2	909.6	835.3	774.5	718.9	669.9	621.0	582.3	554.3
35°	1213.7	1101.5	967.9	866.1	791.7	732.8	682.7	637.5	589.6	552.0	523.5
37.5°	1172.7	1078.0	936.5	817.1	739.3	684.9	643.9	604.6	560.6	520.1	493.2
40°	1131.4	1054.9	912.3	787.4	706.2	650.2	613.3	581.3	538.7	500.7	471.8
42.5°	1069.9	1023.4	889.2	756.2	668.5	614.6	583.6	553.5	516.1	477.6	450.4
45°	957.1	963.2	841.9	706.5	616.6	562.4	533.2	512.3	479.1	447.3	419.5
47.5°	815.5	872.9	786.4	653.6	561.8	511.0	485.4	467.1	444.8	413.6	388.2
50°	723.1	805.0	741.9	618.0	527.4	476.9	451.7	436.9	417.4	392.8	368.6
52.5°	637.9	725.9	688.2	578.4	490.2	443.9	419.2	407.1	391.6	368.5	346.7
55°	520.2	609.4	600.7	518.8	434.3	392.8	374.0	360.3	349.8	332.5	315.2
57.5°	420.8	505.3	509.8	452.3	385.0	344.0	327.9	317.5	310.7	297.7	281.6
60°	358.2	435.7	450.9	407.6	349.8	313.7	297.8	289.5	284.1	273.6	261.4
62.5°	306.1	372.2	389.4	358.2	316.0	282.2	269.8	261.8	258.2	249.1	238.3
65°	234.3	289.2	305.8	288.4	266.5	239.3	229.2	222.3	219.1	214.1	206.1
67.5°	176.2	216.2	234.4	222.2	214.2	197.1	190.7	187.0	184.1	180.7	174.0
70°	141.5	171.2	189.9	186.6	180.1	171.2	166.5	163.9	161.0	158.2	152.3
72.5°	113.8	134.1	151.7	153.4	148.1	146.3	142.1	141.1	139.3	135.9	132.7
75°	75.5	89.5	101.8	106.5	108.7	110.5	108.7	108.3	107.9	105.1	103.2
77.5°	49.5	57.0	64.8	72.8	76.2	78.6	79.2	80.5	79.6	78.0	77.2
80°	37.9	39.7	45.1	52.0	57.4	59.6	61.0	61.7	61.4	61.0	59.6
82.5°	27.5	29.0	31.6	36.4	40.9	44.6	45.4	45.2	46.1	46.3	45.1
85°	14.8	15.2	15.9	16.6	19.1	23.1	24.2	24.9	25.6	25.6	23.5
87.5°	7.2	6.5	6.6	6.3	6.9	6.8	8.2	9.4	10.0	9.1	9.4
90°	12.6	10.7	8.7	6.9	5.3	3.8	2.3	0.7	2.3	3.8	5.3
92.5°	14.7	13.2	11.7	11.2	11.6	12.1	12.4	12.9	12.4	12.1	11.6
95°	18.1	16.4	14.7	17.1	23.4	29.7	36.0	42.3	36.0	29.7	23.4
97.5°	44.5	55.6	66.7	73.7	76.5	79.4	82.2	85.0	82.2	79.4	76.5
100°	71.0	95.0	119.0	129.5	126.5	123.4	120.3	117.3	120.3	123.4	126.5
102.5°	98.1	124.4	150.7	162.7	160.5	158.3	156.1	153.8	156.1	158.3	160.5
105°	179.6	193.5	207.4	213.5	211.8	210.1	208.4	206.7	208.4	210.1	211.8
107.5°	274.0	271.8	269.7	267.9	266.6	265.1	263.8	262.4	263.8	265.1	266.6
110°	309.4	307.7	306.0	304.5	303.3	302.1	300.9	299.6	300.9	302.1	303.3



TEST NUMBER: P332414-830

CATALOG NUMBER: S123RDIW-S560D755U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	344.4	342.7	341.0	339.6	338.5	337.3	336.2	335.2	336.2	337.3	338.5
115°	395.3	394.0	392.6	391.4	390.5	389.6	388.6	387.7	388.6	389.6	390.5
117.5°	445.5	444.8	444.1	443.2	442.1	440.9	439.8	438.7	439.8	440.9	442.1
120°	477.7	477.2	476.7	475.8	474.4	473.1	471.6	470.2	471.6	473.1	474.4
122.5°	509.1	508.4	507.8	507.0	505.9	504.7	503.6	502.5	503.6	504.7	505.9
125°	553.6	553.0	552.4	551.5	550.3	549.0	547.8	546.6	547.8	549.0	550.3
127.5°	596.6	596.0	595.2	594.2	593.0	591.7	590.5	589.3	590.5	591.7	593.0
130°	623.0	622.4	621.8	620.9	619.6	618.4	617.2	615.9	617.2	618.4	619.6
132.5°	648.2	647.7	647.2	646.4	645.1	643.9	642.6	641.4	642.6	643.9	645.1
135°	686.1	685.5	684.9	684.1	683.2	682.2	681.4	680.4	681.4	682.2	683.2
137.5°	719.8	719.4	719.2	718.4	717.2	716.0	714.8	713.7	714.8	716.0	717.2
140°	741.2	740.7	740.3	739.6	738.7	737.7	736.8	735.8	736.8	737.7	738.7
142.5°	761.8	761.3	760.8	760.2	759.2	758.3	757.3	756.4	757.3	758.3	759.2
145°	790.8	790.4	790.1	789.5	788.3	787.3	786.2	785.1	786.2	787.3	788.3
147.5°	816.1	815.9	815.5	815.0	814.3	813.6	812.8	812.2	812.8	813.6	814.3
150°	831.7	831.4	831.0	830.7	830.2	829.7	829.2	828.9	829.2	829.7	830.2
152.5°	845.3	845.1	844.9	844.7	844.4	844.2	844.0	843.8	844.0	844.2	844.4
155°	863.9	863.7	863.6	863.7	863.9	864.3	864.6	864.9	864.6	864.3	863.9
157.5°	880.7	880.9	881.1	881.2	881.2	881.2	881.3	881.3	881.3	881.2	881.2
160°	890.1	890.3	890.5	890.6	890.8	891.0	891.1	891.3	891.1	891.0	890.8
162.5°	898.5	898.6	898.8	899.1	899.5	899.8	900.3	900.7	900.3	899.8	899.5
165°	909.6	909.7	909.9	910.2	910.7	911.2	911.6	912.1	911.6	911.2	910.7
167.5°	918.1	918.1	918.1	918.5	919.1	919.7	920.3	921.0	920.3	919.7	919.1
170°	923.1	923.1	923.1	923.5	924.1	924.7	925.3	926.0	925.3	924.7	924.1
172.5°	926.2	926.1	926.0	926.3	927.1	927.7	928.5	929.3	928.5	927.7	927.1
175°	930.5	930.3	930.2	930.5	931.2	932.0	932.7	933.6	932.7	932.0	931.2
177.5°	932.2	932.1	932.0	932.2	932.8	933.4	934.1	934.6	934.1	933.4	932.8
180°	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6



TEST NUMBER: P332414-830

CATALOG NUMBER: S123RDIW-S560D755U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3
2.5°	828.9	825.1	822.6	816.7	813.0	809.0	804.9	807.5	807.2	806.9	806.9
5°	801.1	792.8	785.2	775.4	769.3	761.8	755.9	755.3	756.7	751.6	748.8
7.5°	773.5	762.1	751.4	740.6	729.2	720.1	714.4	711.8	708.1	705.0	701.7
10°	754.1	740.8	730.3	717.0	704.7	693.9	687.0	682.3	679.8	677.2	672.6
12.5°	734.2	721.1	707.8	692.7	681.0	668.5	663.4	658.1	653.2	650.4	643.9
15°	705.0	688.1	674.0	658.1	645.2	632.8	625.7	615.2	613.7	610.1	603.6
17.5°	675.8	657.4	638.0	626.2	611.5	598.8	587.8	584.3	573.9	570.0	564.4
20°	652.7	635.7	620.9	605.4	584.1	572.2	563.5	558.8	550.5	545.4	541.9
22.5°	632.8	615.5	598.4	580.3	562.7	549.4	543.0	535.7	531.2	524.1	520.2
25°	604.4	585.6	565.0	545.4	532.8	522.7	512.6	506.1	499.6	496.3	489.2
27.5°	571.3	551.7	532.4	517.6	502.1	492.1	483.0	477.2	469.4	463.9	460.0
30°	553.1	530.0	513.4	500.0	480.1	470.8	463.9	456.7	450.9	445.2	441.1
32.5°	532.0	510.9	495.1	478.6	463.4	453.2	444.2	437.9	433.0	427.5	423.6
35°	498.9	481.3	465.0	448.4	437.2	426.7	416.2	410.9	406.1	401.1	397.5
37.5°	469.0	452.5	437.1	421.3	407.5	398.9	390.5	386.3	380.0	376.6	373.0
40°	450.5	434.3	417.7	402.6	388.0	381.6	374.0	367.9	362.1	359.6	355.6
42.5°	430.4	414.1	400.1	383.7	371.9	363.1	356.1	349.4	345.1	341.4	339.1
45°	400.4	385.9	372.2	356.0	344.8	337.1	329.2	323.1	319.1	316.6	312.6
47.5°	371.3	356.8	342.9	328.8	317.9	309.2	301.3	297.0	291.8	288.7	286.0
50°	350.2	337.1	322.3	309.3	298.6	289.9	283.4	278.0	273.2	269.3	267.5
52.5°	330.8	317.0	304.2	292.1	280.7	270.8	264.9	259.2	255.7	251.1	249.0
55°	298.9	285.6	274.8	262.8	251.7	243.4	236.1	231.0	227.4	222.3	219.5
57.5°	268.9	256.9	244.0	233.8	222.2	215.2	209.2	202.3	197.9	194.0	191.1
60°	248.7	235.0	223.9	214.1	204.0	194.9	189.5	184.1	179.5	175.4	173.0
62.5°	227.6	215.7	205.1	194.4	185.2	177.3	171.1	166.5	162.4	159.9	157.3
65°	195.3	186.0	175.1	166.5	157.8	152.0	146.9	143.0	140.1	138.3	136.1
67.5°	165.6	156.5	147.0	138.5	132.7	128.3	125.0	121.6	120.2	117.8	116.4
70°	146.2	136.9	128.6	122.1	116.2	113.0	110.8	108.3	106.9	104.0	102.5
72.5°	125.2	118.4	112.4	107.0	102.4	99.4	96.7	93.6	91.2	88.1	86.6
75°	98.6	92.5	87.8	84.1	81.2	77.3	73.3	70.0	69.0	67.9	67.5
77.5°	73.0	69.1	65.7	62.7	59.1	56.2	55.3	54.6	54.4	53.8	53.8
80°	57.4	53.8	51.3	47.7	45.5	45.5	45.5	44.8	45.1	45.1	45.1
82.5°	42.7	39.3	38.0	36.7	36.3	36.6	36.6	36.7	36.5	37.0	36.8
85°	22.1	22.3	23.1	22.7	23.1	23.1	23.8	23.5	23.8	23.1	23.8
87.5°	9.4	10.7	11.4	12.1	12.7	12.8	13.3	13.4	13.8	13.9	14.0
90°	6.9	8.7	10.7	12.6	14.6	16.7	17.2	17.9	18.5	19.1	19.6
92.5°	11.2	11.7	13.2	14.7	16.2	17.7	18.8	19.7	20.7	21.7	22.2
95°	17.1	14.7	16.4	18.1	19.8	21.5	22.6	23.7	24.7	25.8	26.4
97.5°	73.7	66.7	55.6	44.5	33.5	22.3	23.6	24.8	26.0	27.2	28.0
100°	129.5	119.0	95.0	71.0	46.9	22.9	24.1	25.4	26.6	27.8	28.6
102.5°	162.7	150.7	124.4	98.1	71.9	45.6	41.8	38.0	34.2	30.3	28.6
105°	213.5	207.4	193.5	179.6	165.8	151.9	124.6	97.4	70.0	42.8	29.3
107.5°	267.9	269.7	271.8	274.0	276.3	278.4	258.4	238.4	218.4	198.4	178.1
110°	304.5	306.0	307.7	309.4	311.1	312.8	307.7	302.7	297.6	292.5	278.9



TEST NUMBER: P332414-830

CATALOG NUMBER: S123RDIW-S560D755U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	339.6	341.0	342.7	344.4	346.1	347.8	347.9	348.0	348.1	348.2	345.8
115°	391.4	392.6	394.0	395.3	396.7	398.1	399.6	401.2	402.7	404.3	405.4
117.5°	443.2	444.1	444.8	445.5	446.2	447.0	448.2	449.4	450.6	451.9	452.5
120°	475.8	476.7	477.2	477.7	478.2	478.5	479.8	481.1	482.3	483.5	484.1
122.5°	507.0	507.8	508.4	509.1	509.6	510.2	511.0	511.9	512.7	513.7	514.2
125°	551.5	552.4	553.0	553.6	554.2	554.9	555.2	555.4	555.8	556.1	556.4
127.5°	594.2	595.2	596.0	596.6	597.4	598.1	598.6	599.2	599.6	600.1	600.2
130°	620.9	621.8	622.4	623.0	623.6	624.2	624.8	625.5	626.0	626.7	626.9
132.5°	646.4	647.2	647.7	648.2	648.7	649.2	649.8	650.4	651.0	651.7	651.8
135°	684.1	684.9	685.5	686.1	686.7	687.3	687.8	688.2	688.7	689.2	689.2
137.5°	718.4	719.2	719.4	719.8	720.2	720.5	721.2	722.0	722.7	723.5	723.7
140°	739.6	740.3	740.7	741.2	741.7	742.2	742.7	743.4	743.9	744.6	744.8
142.5°	760.2	760.8	761.3	761.8	762.2	762.7	763.2	763.6	764.1	764.6	764.7
145°	789.5	790.1	790.4	790.8	791.1	791.4	791.6	792.0	792.3	792.6	792.8
147.5°	815.0	815.5	815.9	816.1	816.4	816.7	817.1	817.4	817.7	818.0	817.7
150°	830.7	831.0	831.4	831.7	832.0	832.3	832.6	832.9	833.2	833.5	833.5
152.5°	844.7	844.9	845.1	845.3	845.5	845.6	846.1	846.7	847.3	847.8	847.7
155°	863.7	863.6	863.7	863.9	864.0	864.2	865.0	865.7	866.5	867.3	867.2
157.5°	881.2	881.1	880.9	880.7	880.6	880.4	881.4	882.3	883.2	884.1	884.0
160°	890.6	890.5	890.3	890.1	890.0	889.9	890.8	891.7	892.7	893.5	893.5
162.5°	899.1	898.8	898.6	898.5	898.3	898.1	899.3	900.3	901.4	902.4	902.4
165°	910.2	909.9	909.7	909.6	909.5	909.3	910.5	911.7	912.9	914.2	914.3
167.5°	918.5	918.1	918.1	918.1	918.1	918.1	919.4	920.6	921.9	923.1	923.1
170°	923.5	923.1	923.1	923.1	923.1	923.1	924.4	925.6	926.9	928.1	928.1
172.5°	926.3	926.0	926.1	926.2	926.3	926.5	927.7	929.0	930.2	931.4	931.3
175°	930.5	930.2	930.3	930.5	930.7	930.8	931.9	932.9	934.1	935.1	935.0
177.5°	932.2	932.0	932.1	932.2	932.4	932.5	933.4	934.4	935.4	936.4	936.2
180°	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6



TEST NUMBER: P332414-830

CATALOG NUMBER: S123RDIW-S560D755U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3
2.5°	803.4	803.1	803.4	802.3	803.4	803.1	803.4	806.9	806.9	807.2	807.5
5°	747.6	747.2	746.2	743.0	746.2	747.2	747.6	748.8	751.6	756.7	755.3
7.5°	698.9	698.4	695.2	695.3	695.2	698.4	698.9	701.7	705.0	708.1	711.8
10°	670.1	670.4	666.1	663.5	666.1	670.4	670.1	672.6	677.2	679.8	682.3
12.5°	642.1	640.4	636.9	634.0	636.9	640.4	642.1	643.9	650.4	653.2	658.1
15°	605.0	601.4	592.8	593.5	592.8	601.4	605.0	603.6	610.1	613.7	615.2
17.5°	561.5	558.8	558.7	553.6	558.7	558.8	561.5	564.4	570.0	573.9	584.3
20°	536.1	534.3	535.0	530.0	535.0	534.3	536.1	541.9	545.4	550.5	558.8
22.5°	516.1	514.3	511.3	509.7	511.3	514.3	516.1	520.2	524.1	531.2	535.7
25°	487.0	484.1	481.3	483.1	481.3	484.1	487.0	489.2	496.3	499.6	506.1
27.5°	457.8	455.6	452.8	452.4	452.8	455.6	457.8	460.0	463.9	469.4	477.2
30°	439.3	437.2	435.7	433.9	435.7	437.2	439.3	441.1	445.2	450.9	456.7
32.5°	420.6	420.2	417.5	417.2	417.5	420.2	420.6	423.6	427.5	433.0	437.9
35°	396.1	393.9	393.1	393.5	393.1	393.9	396.1	397.5	401.1	406.1	410.9
37.5°	372.7	369.9	368.5	367.2	368.5	369.9	372.7	373.0	376.6	380.0	386.3
40°	356.0	353.1	352.3	351.7	352.3	353.1	356.0	355.6	359.6	362.1	367.9
42.5°	337.1	336.0	335.6	334.3	335.6	336.0	337.1	339.1	341.4	345.1	349.4
45°	311.5	311.2	309.1	309.7	309.1	311.2	311.5	312.6	316.6	319.1	323.1
47.5°	284.6	283.0	281.4	282.5	281.4	283.0	284.6	286.0	288.7	291.8	297.0
50°	266.1	265.3	262.1	262.8	262.1	265.3	266.1	267.5	269.3	273.2	278.0
52.5°	247.6	244.9	243.6	243.2	243.6	244.9	247.6	249.0	251.1	255.7	259.2
55°	217.0	213.7	212.3	211.5	212.3	213.7	217.0	219.5	222.3	227.4	231.0
57.5°	186.9	186.1	184.9	185.7	184.9	186.1	186.9	191.1	194.0	197.9	202.3
60°	169.3	169.3	169.3	169.0	169.3	169.3	169.3	173.0	175.4	179.5	184.1
62.5°	155.7	154.9	154.6	155.0	154.6	154.9	155.7	157.3	159.9	162.4	166.5
65°	135.0	134.7	133.2	132.9	133.2	134.7	135.0	136.1	138.3	140.1	143.0
67.5°	115.5	114.1	113.8	113.2	113.8	114.1	115.5	116.4	117.8	120.2	121.6
70°	100.8	100.0	97.8	98.2	97.8	100.0	100.8	102.5	104.0	106.9	108.3
72.5°	84.8	84.1	83.7	83.1	83.7	84.1	84.8	86.6	88.1	91.2	93.6
75°	67.1	66.8	66.4	67.9	66.4	66.8	67.1	67.5	67.9	69.0	70.0
77.5°	53.8	53.8	54.0	53.4	54.0	53.8	53.8	53.8	53.8	54.4	54.6
80°	45.1	45.1	44.8	44.8	44.8	45.1	45.1	45.1	45.1	45.1	44.8
82.5°	36.2	36.5	36.7	36.1	36.7	36.5	36.2	36.8	37.0	36.5	36.7
85°	23.8	23.5	24.2	23.8	24.2	23.5	23.8	23.8	23.1	23.8	23.5
87.5°	14.7	14.1	14.2	14.5	14.2	14.1	14.7	14.0	13.9	13.8	13.4
90°	19.9	20.2	20.5	20.8	20.5	20.2	19.9	19.6	19.1	18.5	17.9
92.5°	22.4	22.6	22.8	23.0	22.8	22.6	22.4	22.2	21.7	20.7	19.7
95°	26.4	26.4	26.4	26.4	26.4	26.4	26.4	26.4	25.8	24.7	23.7
97.5°	28.1	28.3	28.5	28.6	28.5	28.3	28.1	28.0	27.2	26.0	24.8
100°	28.7	28.8	28.9	29.1	28.9	28.8	28.7	28.6	27.8	26.6	25.4
102.5°	28.8	29.1	29.4	29.7	29.4	29.1	28.8	28.6	30.3	34.2	38.0
105°	29.6	29.9	30.3	30.5	30.3	29.9	29.6	29.3	42.8	70.0	97.4
107.5°	157.5	137.0	116.4	95.9	116.4	137.0	157.5	178.1	198.4	218.4	238.4
110°	256.8	234.8	212.7	190.8	212.7	234.8	256.8	278.9	292.5	297.6	302.7



TEST NUMBER: P332414-830

CATALOG NUMBER: S123RDIW-S560D755U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	341.2	336.6	331.9	327.3	331.9	336.6	341.2	345.8	348.2	348.1	348.0
115°	406.0	406.6	407.2	407.8	407.2	406.6	406.0	405.4	404.3	402.7	401.2
117.5°	452.7	452.8	452.9	453.1	452.9	452.8	452.7	452.5	451.9	450.6	449.4
120°	484.1	484.1	484.1	484.1	484.1	484.1	484.1	484.1	483.5	482.3	481.1
122.5°	514.3	514.3	514.5	514.6	514.5	514.3	514.3	514.2	513.7	512.7	511.9
125°	556.8	557.0	557.3	557.6	557.3	557.0	556.8	556.4	556.1	555.8	555.4
127.5°	599.9	599.6	599.3	599.0	599.3	599.6	599.9	600.2	600.1	599.6	599.2
130°	626.5	626.2	625.9	625.6	625.9	626.2	626.5	626.9	626.7	626.0	625.5
132.5°	651.3	650.9	650.4	650.0	650.4	650.9	651.3	651.8	651.7	651.0	650.4
135°	688.7	688.2	687.8	687.3	687.8	688.2	688.7	689.2	689.2	688.7	688.2
137.5°	723.4	723.0	722.7	722.5	722.7	723.0	723.4	723.7	723.5	722.7	722.0
140°	744.4	744.1	743.9	743.5	743.9	744.1	744.4	744.8	744.6	743.9	743.4
142.5°	764.2	763.8	763.4	762.9	763.4	763.8	764.2	764.7	764.6	764.1	763.6
145°	792.8	792.8	792.8	792.8	792.8	792.8	792.8	792.8	792.6	792.3	792.0
147.5°	817.1	816.3	815.7	814.9	815.7	816.3	817.1	817.7	818.0	817.7	817.4
150°	833.0	832.5	832.1	831.6	832.1	832.5	833.0	833.5	833.5	833.2	832.9
152.5°	847.1	846.3	845.6	844.9	845.6	846.3	847.1	847.7	847.8	847.3	846.7
155°	866.3	865.3	864.4	863.5	864.4	865.3	866.3	867.2	867.3	866.5	865.7
157.5°	882.8	881.6	880.4	879.2	880.4	881.6	882.8	884.0	884.1	883.2	882.3
160°	892.4	891.4	890.2	889.2	890.2	891.4	892.4	893.5	893.5	892.7	891.7
162.5°	901.4	900.5	899.6	898.6	899.6	900.5	901.4	902.4	902.4	901.4	900.3
165°	913.2	912.1	911.1	909.9	911.1	912.1	913.2	914.3	914.2	912.9	911.7
167.5°	921.9	920.6	919.4	918.1	919.4	920.6	921.9	923.1	923.1	921.9	920.6
170°	926.9	925.6	924.4	923.1	924.4	925.6	926.9	928.1	928.1	926.9	925.6
172.5°	930.0	928.7	927.3	926.0	927.3	928.7	930.0	931.3	931.4	930.2	929.0
175°	933.8	932.6	931.3	930.1	931.3	932.6	933.8	935.0	935.1	934.1	932.9
177.5°	935.0	933.8	932.6	931.3	932.6	933.8	935.0	936.2	936.4	935.4	934.4
180°	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6



TEST NUMBER: P332414-830

CATALOG NUMBER: S123RDIW-S560D755U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3
2.5°	804.9	809.0	813.0	816.7	822.6	825.1	828.9	830.3	834.6	841.0	846.2
5°	755.9	761.8	769.3	775.4	785.2	792.8	801.1	809.0	818.4	831.8	843.7
7.5°	714.4	720.1	729.2	740.6	751.4	762.1	773.5	784.3	797.8	816.9	835.8
10°	687.0	693.9	704.7	717.0	730.3	740.8	754.1	767.9	784.5	806.5	829.2
12.5°	663.4	668.5	681.0	692.7	707.8	721.1	734.2	750.3	769.2	792.7	820.0
15°	625.7	632.8	645.2	658.1	674.0	688.1	705.0	724.5	743.0	771.8	805.0
17.5°	587.8	598.8	611.5	626.2	638.0	657.4	675.8	695.8	718.5	749.1	785.5
20°	563.5	572.2	584.1	605.4	620.9	635.7	652.7	677.6	698.5	733.2	771.1
22.5°	543.0	549.4	562.7	580.3	598.4	615.5	632.8	656.6	682.4	715.3	756.4
25°	512.6	522.7	532.8	545.4	565.0	585.6	604.4	624.5	652.0	687.0	731.4
27.5°	483.0	492.1	502.1	517.6	532.4	551.7	571.3	594.5	623.9	660.9	706.0
30°	463.9	470.8	480.1	500.0	513.4	530.0	553.1	573.6	601.1	640.5	688.1
32.5°	444.2	453.2	463.4	478.6	495.1	510.9	532.0	554.3	582.3	621.0	669.9
35°	416.2	426.7	437.2	448.4	465.0	481.3	498.9	523.5	552.0	589.6	637.5
37.5°	390.5	398.9	407.5	421.3	437.1	452.5	469.0	493.2	520.1	560.6	604.6
40°	374.0	381.6	388.0	402.6	417.7	434.3	450.5	471.8	500.7	538.7	581.3
42.5°	356.1	363.1	371.9	383.7	400.1	414.1	430.4	450.4	477.6	516.1	553.5
45°	329.2	337.1	344.8	356.0	372.2	385.9	400.4	419.5	447.3	479.1	512.3
47.5°	301.3	309.2	317.9	328.8	342.9	356.8	371.3	388.2	413.6	444.8	467.1
50°	283.4	289.9	298.6	309.3	322.3	337.1	350.2	368.6	392.8	417.4	436.9
52.5°	264.9	270.8	280.7	292.1	304.2	317.0	330.8	346.7	368.5	391.6	407.1
55°	236.1	243.4	251.7	262.8	274.8	285.6	298.9	315.2	332.5	349.8	360.3
57.5°	209.2	215.2	222.2	233.8	244.0	256.9	268.9	281.6	297.7	310.7	317.5
60°	189.5	194.9	204.0	214.1	223.9	235.0	248.7	261.4	273.6	284.1	289.5
62.5°	171.1	177.3	185.2	194.4	205.1	215.7	227.6	238.3	249.1	258.2	261.8
65°	146.9	152.0	157.8	166.5	175.1	186.0	195.3	206.1	214.1	219.1	222.3
67.5°	125.0	128.3	132.7	138.5	147.0	156.5	165.6	174.0	180.7	184.1	187.0
70°	110.8	113.0	116.2	122.1	128.6	136.9	146.2	152.3	158.2	161.0	163.9
72.5°	96.7	99.4	102.4	107.0	112.4	118.4	125.2	132.7	135.9	139.3	141.1
75°	73.3	77.3	81.2	84.1	87.8	92.5	98.6	103.2	105.1	107.9	108.3
77.5°	55.3	56.2	59.1	62.7	65.7	69.1	73.0	77.2	78.0	79.6	80.5
80°	45.5	45.5	45.5	47.7	51.3	53.8	57.4	59.6	61.0	61.4	61.7
82.5°	36.6	36.6	36.3	36.7	38.0	39.3	42.7	45.1	46.3	46.1	45.2
85°	23.8	23.1	23.1	22.7	23.1	22.3	22.1	23.5	25.6	25.6	24.9
87.5°	13.3	12.8	12.7	12.1	11.4	10.7	9.4	9.4	9.1	10.0	9.4
90°	17.2	16.7	14.6	12.6	10.7	8.7	6.9	5.3	3.8	2.3	0.7
92.5°	18.8	17.7	16.2	14.7	13.2	11.7	11.2	11.6	12.1	12.4	12.9
95°	22.6	21.5	19.8	18.1	16.4	14.7	17.1	23.4	29.7	36.0	42.3
97.5°	23.6	22.3	33.5	44.5	55.6	66.7	73.7	76.5	79.4	82.2	85.0
100°	24.1	22.9	46.9	71.0	95.0	119.0	129.5	126.5	123.4	120.3	117.3
102.5°	41.8	45.6	71.9	98.1	124.4	150.7	162.7	160.5	158.3	156.1	153.8
105°	124.6	151.9	165.8	179.6	193.5	207.4	213.5	211.8	210.1	208.4	206.7
107.5°	258.4	278.4	276.3	274.0	271.8	269.7	267.9	266.6	265.1	263.8	262.4
110°	307.7	312.8	311.1	309.4	307.7	306.0	304.5	303.3	302.1	300.9	299.6



TEST NUMBER: P332414-830

CATALOG NUMBER: S123RDIW-S560D755U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	347.9	347.8	346.1	344.4	342.7	341.0	339.6	338.5	337.3	336.2	335.2
115°	399.6	398.1	396.7	395.3	394.0	392.6	391.4	390.5	389.6	388.6	387.7
117.5°	448.2	447.0	446.2	445.5	444.8	444.1	443.2	442.1	440.9	439.8	438.7
120°	479.8	478.5	478.2	477.7	477.2	476.7	475.8	474.4	473.1	471.6	470.2
122.5°	511.0	510.2	509.6	509.1	508.4	507.8	507.0	505.9	504.7	503.6	502.5
125°	555.2	554.9	554.2	553.6	553.0	552.4	551.5	550.3	549.0	547.8	546.6
127.5°	598.6	598.1	597.4	596.6	596.0	595.2	594.2	593.0	591.7	590.5	589.3
130°	624.8	624.2	623.6	623.0	622.4	621.8	620.9	619.6	618.4	617.2	615.9
132.5°	649.8	649.2	648.7	648.2	647.7	647.2	646.4	645.1	643.9	642.6	641.4
135°	687.8	687.3	686.7	686.1	685.5	684.9	684.1	683.2	682.2	681.4	680.4
137.5°	721.2	720.5	720.2	719.8	719.4	719.2	718.4	717.2	716.0	714.8	713.7
140°	742.7	742.2	741.7	741.2	740.7	740.3	739.6	738.7	737.7	736.8	735.8
142.5°	763.2	762.7	762.2	761.8	761.3	760.8	760.2	759.2	758.3	757.3	756.4
145°	791.6	791.4	791.1	790.8	790.4	790.1	789.5	788.3	787.3	786.2	785.1
147.5°	817.1	816.7	816.4	816.1	815.9	815.5	815.0	814.3	813.6	812.8	812.2
150°	832.6	832.3	832.0	831.7	831.4	831.0	830.7	830.2	829.7	829.2	828.9
152.5°	846.1	845.6	845.5	845.3	845.1	844.9	844.7	844.4	844.2	844.0	843.8
155°	865.0	864.2	864.0	863.9	863.7	863.6	863.7	863.9	864.3	864.6	864.9
157.5°	881.4	880.4	880.6	880.7	880.9	881.1	881.2	881.2	881.2	881.3	881.3
160°	890.8	889.9	890.0	890.1	890.3	890.5	890.6	890.8	891.0	891.1	891.3
162.5°	899.3	898.1	898.3	898.5	898.6	898.8	899.1	899.5	899.8	900.3	900.7
165°	910.5	909.3	909.5	909.6	909.7	909.9	910.2	910.7	911.2	911.6	912.1
167.5°	919.4	918.1	918.1	918.1	918.1	918.1	918.5	919.1	919.7	920.3	921.0
170°	924.4	923.1	923.1	923.1	923.1	923.1	923.5	924.1	924.7	925.3	926.0
172.5°	927.7	926.5	926.3	926.2	926.1	926.0	926.3	927.1	927.7	928.5	929.3
175°	931.9	930.8	930.7	930.5	930.3	930.2	930.5	931.2	932.0	932.7	933.6
177.5°	933.4	932.5	932.4	932.2	932.1	932.0	932.2	932.8	933.4	934.1	934.6
180°	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6



TEST NUMBER: P332414-830

CATALOG NUMBER: S123RDIW-S560D755U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3
2.5°	847.9	851.1	855.2	861.2	865.8	869.9	870.7	871.9	874.8	879.7	883.4
5°	853.5	861.8	875.1	888.1	902.2	913.7	924.5	932.2	939.3	954.5	966.8
7.5°	851.7	870.2	891.1	914.5	938.0	960.9	982.1	1001.2	1020.1	1042.2	1067.3
10°	850.6	872.2	900.3	930.3	963.2	995.3	1026.3	1050.6	1078.7	1104.0	1136.1
12.5°	845.1	876.3	909.9	948.2	988.6	1025.7	1066.5	1099.9	1132.1	1168.7	1206.0
15°	837.9	875.8	918.4	969.3	1030.7	1075.4	1117.3	1175.4	1215.1	1254.9	1308.3
17.5°	824.8	871.1	924.4	990.4	1041.7	1101.8	1164.8	1210.8	1264.2	1320.2	1368.6
20°	814.5	868.3	927.8	992.8	1058.1	1123.5	1184.5	1239.3	1294.6	1359.2	1398.9
22.5°	804.1	857.2	919.2	988.2	1058.4	1127.2	1196.3	1260.7	1322.9	1388.1	1438.8
25°	781.9	845.1	912.3	982.7	1052.0	1127.8	1210.1	1282.0	1358.9	1426.0	1474.0
27.5°	759.6	817.5	884.3	955.7	1032.7	1122.4	1219.2	1300.9	1377.9	1426.0	1441.1
30°	739.3	800.7	862.0	934.6	1018.0	1118.0	1221.0	1314.5	1377.6	1398.5	1383.0
32.5°	718.9	774.5	835.3	909.6	998.2	1107.4	1223.2	1306.4	1344.4	1328.4	1265.2
35°	682.7	732.8	791.7	866.1	967.9	1101.5	1213.7	1270.1	1260.7	1170.4	1051.2
37.5°	643.9	684.9	739.3	817.1	936.5	1078.0	1172.7	1181.0	1099.8	961.2	823.6
40°	613.3	650.2	706.2	787.4	912.3	1054.9	1131.4	1097.9	971.9	817.7	702.9
42.5°	583.6	614.6	668.5	756.2	889.2	1023.4	1069.9	996.7	851.4	705.6	601.2
45°	533.2	562.4	616.6	706.5	841.9	963.2	957.1	830.0	684.5	567.1	480.5
47.5°	485.4	511.0	561.8	653.6	786.4	872.9	815.5	680.3	556.9	462.8	401.0
50°	451.7	476.9	527.4	618.0	741.9	805.0	723.1	592.8	479.8	401.8	352.7
52.5°	419.2	443.9	490.2	578.4	688.2	725.9	637.9	517.1	422.9	355.6	313.4
55°	374.0	392.8	434.3	518.8	600.7	609.4	520.2	419.1	341.5	294.5	265.7
57.5°	327.9	344.0	385.0	452.3	509.8	505.3	420.8	333.4	281.1	246.2	225.3
60°	297.8	313.7	349.8	407.6	450.9	435.7	358.2	287.8	243.0	217.4	200.8
62.5°	269.8	282.2	316.0	358.2	389.4	372.2	306.1	247.9	212.4	190.8	177.6
65°	229.2	239.3	266.5	288.4	305.8	289.2	234.3	193.9	168.2	153.1	144.0
67.5°	190.7	197.1	214.2	222.2	234.4	216.2	176.2	149.1	134.5	121.8	115.5
70°	166.5	171.2	180.1	186.6	189.9	171.2	141.5	121.7	109.4	100.4	96.4
72.5°	142.1	146.3	148.1	153.4	151.7	134.1	113.8	98.0	89.2	83.0	77.9
75°	108.7	110.5	108.7	106.5	101.8	89.5	75.5	67.5	61.0	58.2	56.4
77.5°	79.2	78.6	76.2	72.8	64.8	57.0	49.5	46.8	44.0	42.4	41.8
80°	61.0	59.6	57.4	52.0	45.1	39.7	37.9	36.1	35.1	33.2	32.9
82.5°	45.4	44.6	40.9	36.4	31.6	29.0	27.5	26.9	25.7	24.9	24.8
85°	24.2	23.1	19.1	16.6	15.9	15.2	14.8	14.8	13.4	13.0	13.0
87.5°	8.2	6.8	6.9	6.3	6.6	6.5	7.2	7.0	7.1	7.5	7.1
90°	2.3	3.8	5.3	6.9	8.7	10.7	12.6	14.6	16.7	17.2	17.9
92.5°	12.4	12.1	11.6	11.2	11.7	13.2	14.7	16.2	17.7	18.8	19.7
95°	36.0	29.7	23.4	17.1	14.7	16.4	18.1	19.8	21.5	22.6	23.7
97.5°	82.2	79.4	76.5	73.7	66.7	55.6	44.5	33.5	22.3	23.6	24.8
100°	120.3	123.4	126.5	129.5	119.0	95.0	71.0	46.9	22.9	24.1	25.4
102.5°	156.1	158.3	160.5	162.7	150.7	124.4	98.1	71.9	45.6	41.8	38.0
105°	208.4	210.1	211.8	213.5	207.4	193.5	179.6	165.8	151.9	124.6	97.4
107.5°	263.8	265.1	266.6	267.9	269.7	271.8	274.0	276.3	278.4	258.4	238.4
110°	300.9	302.1	303.3	304.5	306.0	307.7	309.4	311.1	312.8	307.7	302.7



TEST NUMBER: P332414-830

CATALOG NUMBER: S123RDIW-S560D755U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	336.2	337.3	338.5	339.6	341.0	342.7	344.4	346.1	347.8	347.9	348.0
115°	388.6	389.6	390.5	391.4	392.6	394.0	395.3	396.7	398.1	399.6	401.2
117.5°	439.8	440.9	442.1	443.2	444.1	444.8	445.5	446.2	447.0	448.2	449.4
120°	471.6	473.1	474.4	475.8	476.7	477.2	477.7	478.2	478.5	479.8	481.1
122.5°	503.6	504.7	505.9	507.0	507.8	508.4	509.1	509.6	510.2	511.0	511.9
125°	547.8	549.0	550.3	551.5	552.4	553.0	553.6	554.2	554.9	555.2	555.4
127.5°	590.5	591.7	593.0	594.2	595.2	596.0	596.6	597.4	598.1	598.6	599.2
130°	617.2	618.4	619.6	620.9	621.8	622.4	623.0	623.6	624.2	624.8	625.5
132.5°	642.6	643.9	645.1	646.4	647.2	647.7	648.2	648.7	649.2	649.8	650.4
135°	681.4	682.2	683.2	684.1	684.9	685.5	686.1	686.7	687.3	687.8	688.2
137.5°	714.8	716.0	717.2	718.4	719.2	719.4	719.8	720.2	720.5	721.2	722.0
140°	736.8	737.7	738.7	739.6	740.3	740.7	741.2	741.7	742.2	742.7	743.4
142.5°	757.3	758.3	759.2	760.2	760.8	761.3	761.8	762.2	762.7	763.2	763.6
145°	786.2	787.3	788.3	789.5	790.1	790.4	790.8	791.1	791.4	791.6	792.0
147.5°	812.8	813.6	814.3	815.0	815.5	815.9	816.1	816.4	816.7	817.1	817.4
150°	829.2	829.7	830.2	830.7	831.0	831.4	831.7	832.0	832.3	832.6	832.9
152.5°	844.0	844.2	844.4	844.7	844.9	845.1	845.3	845.5	845.6	846.1	846.7
155°	864.6	864.3	863.9	863.7	863.6	863.7	863.9	864.0	864.2	865.0	865.7
157.5°	881.3	881.2	881.2	881.2	881.1	880.9	880.7	880.6	880.4	881.4	882.3
160°	891.1	891.0	890.8	890.6	890.5	890.3	890.1	890.0	889.9	890.8	891.7
162.5°	900.3	899.8	899.5	899.1	898.8	898.6	898.5	898.3	898.1	899.3	900.3
165°	911.6	911.2	910.7	910.2	909.9	909.7	909.6	909.5	909.3	910.5	911.7
167.5°	920.3	919.7	919.1	918.5	918.1	918.1	918.1	918.1	918.1	919.4	920.6
170°	925.3	924.7	924.1	923.5	923.1	923.1	923.1	923.1	923.1	924.4	925.6
172.5°	928.5	927.7	927.1	926.3	926.0	926.1	926.2	926.3	926.5	927.7	929.0
175°	932.7	932.0	931.2	930.5	930.2	930.3	930.5	930.7	930.8	931.9	932.9
177.5°	934.1	933.4	932.8	932.2	932.0	932.1	932.2	932.4	932.5	933.4	934.4
180°	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6



TEST NUMBER: P332414-830

CATALOG NUMBER: S123RDIW-S560D755U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	843.3	843.3	843.3	843.3	843.3	843.3	843.3
2.5°	889.6	889.6	890.7	895.0	895.6	899.4	898.1
5°	977.6	984.5	987.0	997.9	1004.4	1007.2	1001.5
7.5°	1085.3	1104.7	1113.9	1125.2	1135.2	1138.3	1130.4
10°	1163.9	1184.1	1201.1	1211.5	1221.3	1227.8	1236.1
12.5°	1239.8	1264.7	1280.8	1295.6	1305.6	1313.9	1315.2
15°	1322.4	1359.9	1388.5	1409.4	1419.8	1425.3	1423.1
17.5°	1405.6	1440.4	1460.8	1482.1	1496.6	1497.3	1497.8
20°	1452.7	1486.7	1510.1	1526.0	1542.3	1541.5	1545.1
22.5°	1484.2	1510.9	1528.9	1540.4	1546.0	1543.2	1544.0
25°	1498.9	1506.8	1503.6	1485.2	1480.5	1463.6	1466.4
27.5°	1423.0	1385.4	1346.6	1296.6	1257.2	1225.7	1227.3
30°	1319.8	1253.4	1177.6	1114.1	1057.1	1041.1	1007.2
32.5°	1175.7	1076.1	987.3	928.1	879.1	865.8	836.2
35°	931.4	834.6	743.3	688.4	666.8	636.5	636.1
37.5°	724.0	638.8	590.5	549.3	527.7	509.3	507.6
40°	609.1	542.6	506.1	476.5	455.2	441.5	438.3
42.5°	528.8	475.0	440.8	422.5	406.1	399.1	393.8
45°	431.8	395.7	371.8	355.2	347.6	342.2	339.3
47.5°	361.2	337.0	320.7	309.7	303.5	297.8	299.4
50°	322.7	302.9	291.0	280.5	275.8	271.8	272.2
52.5°	291.8	274.0	264.4	256.8	251.0	248.2	246.8
55°	247.7	236.5	226.7	221.3	218.0	214.1	213.0
57.5°	211.2	202.6	194.6	188.5	187.8	183.9	184.4
60°	187.0	179.7	173.2	170.0	167.5	164.3	165.3
62.5°	167.1	161.0	155.0	152.4	149.9	147.5	148.0
65°	136.9	131.0	127.4	126.0	124.9	123.9	122.7
67.5°	109.1	105.5	103.2	100.1	97.9	97.6	96.4
70°	91.7	87.0	83.0	79.1	77.9	77.6	77.9
72.5°	73.5	70.5	69.5	67.5	67.3	66.4	67.0
75°	55.2	54.2	53.4	52.0	52.0	52.0	52.0
77.5°	40.7	40.1	39.7	39.3	39.0	38.5	38.5
80°	31.8	31.4	30.7	30.7	30.3	30.7	30.3
82.5°	23.9	23.9	23.2	23.2	22.8	22.6	22.8
85°	12.3	11.9	12.6	11.9	12.3	11.6	12.3
87.5°	7.2	7.3	7.1	7.2	6.9	7.5	7.1
90°	18.5	19.1	19.6	19.9	20.2	20.5	20.8
92.5°	20.7	21.7	22.2	22.4	22.6	22.8	23.0
95°	24.7	25.8	26.4	26.4	26.4	26.4	26.4
97.5°	26.0	27.2	28.0	28.1	28.3	28.5	28.6
100°	26.6	27.8	28.6	28.7	28.8	28.9	29.1
102.5°	34.2	30.3	28.6	28.8	29.1	29.4	29.7
105°	70.0	42.8	29.3	29.6	29.9	30.3	30.5
107.5°	218.4	198.4	178.1	157.5	137.0	116.4	95.9
110°	297.6	292.5	278.9	256.8	234.8	212.7	190.8



TEST NUMBER: P332414-830

CATALOG NUMBER: S123RDIW-S560D755U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	348.1	348.2	345.8	341.2	336.6	331.9	327.3
115°	402.7	404.3	405.4	406.0	406.6	407.2	407.8
117.5°	450.6	451.9	452.5	452.7	452.8	452.9	453.1
120°	482.3	483.5	484.1	484.1	484.1	484.1	484.1
122.5°	512.7	513.7	514.2	514.3	514.3	514.5	514.6
125°	555.8	556.1	556.4	556.8	557.0	557.3	557.6
127.5°	599.6	600.1	600.2	599.9	599.6	599.3	599.0
130°	626.0	626.7	626.9	626.5	626.2	625.9	625.6
132.5°	651.0	651.7	651.8	651.3	650.9	650.4	650.0
135°	688.7	689.2	689.2	688.7	688.2	687.8	687.3
137.5°	722.7	723.5	723.7	723.4	723.0	722.7	722.5
140°	743.9	744.6	744.8	744.4	744.1	743.9	743.5
142.5°	764.1	764.6	764.7	764.2	763.8	763.4	762.9
145°	792.3	792.6	792.8	792.8	792.8	792.8	792.8
147.5°	817.7	818.0	817.7	817.1	816.3	815.7	814.9
150°	833.2	833.5	833.5	833.0	832.5	832.1	831.6
152.5°	847.3	847.8	847.7	847.1	846.3	845.6	844.9
155°	866.5	867.3	867.2	866.3	865.3	864.4	863.5
157.5°	883.2	884.1	884.0	882.8	881.6	880.4	879.2
160°	892.7	893.5	893.5	892.4	891.4	890.2	889.2
162.5°	901.4	902.4	902.4	901.4	900.5	899.6	898.6
165°	912.9	914.2	914.3	913.2	912.1	911.1	909.9
167.5°	921.9	923.1	923.1	921.9	920.6	919.4	918.1
170°	926.9	928.1	928.1	926.9	925.6	924.4	923.1
172.5°	930.2	931.4	931.3	930.0	928.7	927.3	926.0
175°	934.1	935.1	935.0	933.8	932.6	931.3	930.1
177.5°	935.4	936.4	936.2	935.0	933.8	932.6	931.3
180°	933.6	933.6	933.6	933.6	933.6	933.6	933.6

(END OF REPORT)