

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332433-830

Luminaire Tested: **S123RDIW-S775D460U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332433-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIW-S775D460U830-4F0-1E-UDD-F1  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 460 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4257.2 lumens  
Efficiency: N/A  
Efficacy: 112.9 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 37.7  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332433-830

CATALOG NUMBER: S123RDIW-S775D460U830-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332433-830

CATALOG NUMBER: S123RDIW-S775D460U830-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	91	91	91	80	80	80	70	70	70	65
1	101	97	93	90	95	92	88	85	81	78	76	71	69	68	62	61	60	55
2	93	85	79	74	87	81	75	71	71	67	64	63	60	57	55	53	51	47
3	85	75	68	62	80	71	65	60	63	58	54	56	52	49	49	46	44	40
4	78	67	59	53	73	63	56	51	57	51	46	50	46	42	44	41	38	35
5	72	60	52	46	67	57	50	44	51	45	40	45	41	37	40	36	33	31
6	66	54	46	40	62	51	44	39	46	40	36	41	36	33	37	33	30	27
7	61	49	41	35	58	47	39	34	42	36	32	38	33	29	33	29	26	24
8	57	45	37	32	54	43	35	30	38	32	28	34	30	26	31	27	24	22
9	53	41	33	28	50	39	32	27	35	29	25	32	27	23	29	25	22	20
10	50	38	30	26	47	36	29	25	33	27	23	29	25	21	27	23	20	18

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	13099	13099	13099
5°	13149	12967	13042
10°	13074	12804	12761
15°	12933	12504	12373
20°	12741	12129	11848
25°	12542	11709	11334
30°	12279	11225	10611
35°	12009	10738	9947
40°	11760	10165	9125
45°	11432	9601	8383
50°	11072	8957	7552
55°	10704	8223	6778
60°	10368	7436	5927
65°	9928	6584	5076
70°	9379	5530	4101
75°	8576	4350	3855
80°	7649	3856	3546
85°	6459	3409	3162



TEST NUMBER: P332433-830

CATALOG NUMBER: S123RDIW-S775D460U830-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	114.3	2.7
10°-20°	317.9	7.5
20°-30°	457.8	10.8
30°-40°	515.7	12.1
40°-50°	493.3	11.6
50°-60°	404.0	9.5
60°-70°	272.6	6.4
70°-80°	137.1	3.2
80°-90°	37.9	0.9
90°-100°	35.4	0.8
100°-110°	106.0	2.5
110°-120°	180.3	4.2
120°-130°	237.2	5.6
130°-140°	266.6	6.3
140°-150°	262.1	6.2
150°-160°	220.6	5.2
160°-170°	146.9	3.4
170°-180°	51.4	1.2
0°-30°	890.0	20.9
0°-40°	1405.7	33.0
0°-60°	2303.0	54.1
0°-90°	2750.6	64.6
90°-120°	321.8	7.6
90°-150°	1087.6	25.5
90°-180°	1507.0	35.4
0°-180°	4257.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1217	1217	1217	1217	1217	
5°	1217	1212	1200	1208	1207	115
15°	1161	1149	1122	1117	1110	327
25°	1056	1030	986	966	954	485
35°	914	877	817	776	757	572
45°	751	705	631	576	551	579
55°	570	520	438	383	361	511
65°	390	334	258	212	199	386
75°	206	159	105	95	93	220
85°	52	32	28	26	26	59
90°	0	5	10	12	13	4
95°	25	28	32	33	33	28
105°	96	97	101	101	102	103
115°	182	183	182	182	182	180
125°	266	267	266	264	263	237
135°	345	347	347	345	344	266
145°	418	419	420	420	418	261
155°	479	479	479	481	478	220
165°	522	520	520	522	520	147
175°	542	541	541	543	540	52
180°	544	544	544	544	544	



TEST NUMBER: P332433-830

CATALOG NUMBER: S123RDIW-S775D460U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1216.9	1216.9	1216.9	1216.9	1216.9	1216.9	1216.9	1216.9	1216.9	1216.9	1216.9
2.5°	1220.8	1220.1	1219.4	1218.7	1218.0	1216.6	1214.5	1212.4	1210.3	1208.2	1210.1
5°	1216.9	1215.8	1214.7	1213.6	1212.5	1210.6	1208.0	1205.3	1202.7	1200.1	1202.0
7.5°	1205.6	1204.5	1203.2	1202.0	1200.9	1198.5	1195.1	1191.8	1188.4	1184.9	1186.0
10°	1196.2	1194.6	1193.1	1191.6	1190.0	1187.2	1183.3	1179.4	1175.4	1171.5	1171.7
12.5°	1182.7	1181.0	1179.3	1177.6	1175.9	1172.6	1167.8	1163.0	1158.1	1153.3	1153.2
15°	1160.6	1158.2	1155.7	1153.4	1150.9	1146.7	1140.6	1134.4	1128.2	1122.1	1121.1
17.5°	1132.7	1130.0	1127.2	1124.4	1121.5	1116.3	1108.4	1100.6	1092.8	1085.1	1082.7
20°	1112.3	1108.7	1105.2	1101.7	1098.3	1092.3	1083.9	1075.6	1067.3	1058.9	1056.1
22.5°	1089.4	1085.3	1081.3	1077.2	1073.2	1066.8	1057.9	1049.0	1040.2	1031.3	1027.7
25°	1056.0	1050.6	1045.0	1039.5	1034.1	1026.2	1016.2	1006.1	996.0	985.9	981.3
27.5°	1015.5	1009.5	1003.4	997.4	991.4	982.7	971.5	960.3	949.0	937.7	931.3
30°	987.9	981.3	974.8	968.2	961.6	952.2	939.9	927.6	915.3	903.1	895.6
32.5°	960.3	952.8	945.4	937.9	930.5	920.2	907.2	894.3	881.3	868.3	860.2
35°	913.9	906.0	898.1	890.2	882.3	871.6	858.0	844.3	830.8	817.2	807.8
37.5°	867.0	858.1	849.3	840.6	831.8	820.2	805.7	791.2	776.7	762.1	751.4
40°	836.9	827.3	817.6	807.9	798.3	785.7	770.2	754.6	739.0	723.4	712.0
42.5°	803.0	793.3	783.6	774.0	764.4	751.5	735.4	719.3	703.2	687.1	674.7
45°	751.0	741.2	731.3	721.4	711.5	698.2	681.3	664.4	647.5	630.7	618.1
47.5°	699.2	688.3	677.5	666.7	655.8	642.0	625.1	608.1	591.3	574.4	560.8
50°	661.2	650.9	640.6	630.3	620.0	606.0	588.2	570.4	552.7	534.9	521.3
52.5°	627.3	616.1	604.9	593.7	582.6	568.2	550.5	533.0	515.4	497.8	483.7
55°	570.4	559.7	548.9	538.2	527.4	512.7	494.1	475.5	456.9	438.2	425.5
57.5°	517.9	506.2	494.6	482.8	471.1	455.9	437.2	418.4	399.6	381.0	368.9
60°	481.6	469.6	457.5	445.4	433.4	418.2	400.0	381.8	363.6	345.4	333.6
62.5°	445.3	433.2	421.1	409.1	397.1	381.9	363.7	345.5	327.3	309.1	297.9
65°	389.8	377.8	365.7	353.6	341.6	327.0	309.9	292.8	275.7	258.5	247.8
67.5°	334.4	322.2	310.0	297.7	285.6	271.3	254.9	238.5	222.1	205.7	197.7
70°	298.0	286.3	274.4	262.5	250.7	237.0	221.7	206.4	191.1	175.7	168.0
72.5°	261.7	250.1	238.4	226.7	215.1	202.3	188.3	174.4	160.4	146.5	140.2
75°	206.2	195.8	185.2	174.7	164.2	152.9	140.8	128.8	116.7	104.6	102.5
77.5°	155.7	146.2	136.7	127.1	117.6	109.1	101.2	93.5	85.8	77.9	76.8
80°	123.4	114.3	105.4	96.4	87.4	80.6	76.0	71.4	66.8	62.2	61.5
82.5°	92.6	84.8	77.0	69.3	61.5	56.6	54.4	52.2	50.1	48.0	47.3
85°	52.3	47.5	42.7	37.8	33.0	30.3	29.6	28.9	28.3	27.6	27.2
87.5°	19.0	17.2	15.6	13.9	12.1	11.3	11.6	11.8	12.1	12.3	12.3
90°	0.5	1.4	2.4	3.3	4.2	5.3	6.5	7.8	9.0	10.3	10.7
92.5°	10.4	11.0	11.6	12.3	12.9	13.6	14.3	15.0	15.7	16.4	16.7
95°	25.2	25.8	26.5	27.2	27.9	28.6	29.3	30.1	30.8	31.6	32.0
97.5°	44.8	45.2	45.7	46.3	46.8	47.2	47.8	48.4	48.9	49.5	49.9
100°	58.1	58.6	59.2	59.8	60.3	60.9	61.4	61.8	62.3	62.8	63.1
102.5°	73.4	73.8	74.2	74.5	74.8	75.3	76.0	76.5	77.2	77.9	78.1
105°	96.1	96.3	96.5	96.7	96.9	97.4	98.2	99.1	99.9	100.8	100.8
107.5°	122.4	122.5	122.6	122.7	122.9	123.1	123.5	123.8	124.1	124.5	124.8
110°	138.8	139.0	139.2	139.4	139.6	139.8	140.0	140.2	140.3	140.5	140.9



TEST NUMBER: P332433-830

CATALOG NUMBER: S123RDIW-S775D460U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	155.9	156.0	156.2	156.3	156.4	156.5	156.5	156.6	156.6	156.6	157.0
115°	181.5	181.8	182.1	182.4	182.7	182.8	182.6	182.4	182.2	182.0	182.1
117.5°	207.4	207.5	207.7	207.9	208.1	208.0	207.8	207.5	207.4	207.1	207.1
120°	223.4	223.9	224.5	225.1	225.6	225.7	225.3	224.8	224.3	223.9	223.8
122.5°	240.2	240.5	241.0	241.4	241.8	241.9	241.7	241.4	241.2	240.9	240.6
125°	265.7	266.0	266.3	266.6	266.8	266.8	266.6	266.5	266.3	266.1	265.7
127.5°	289.3	289.8	290.5	291.1	291.7	291.9	291.7	291.4	291.2	291.1	290.5
130°	305.0	305.8	306.5	307.3	308.0	308.2	307.9	307.6	307.4	307.1	306.7
132.5°	320.7	321.4	322.3	323.0	323.8	324.0	323.8	323.6	323.4	323.2	322.7
135°	344.7	345.3	345.8	346.4	346.9	347.2	347.1	347.0	346.9	346.9	346.5
137.5°	366.9	367.4	367.9	368.3	368.8	369.2	369.4	369.7	369.9	370.1	369.8
140°	382.3	382.8	383.2	383.7	384.2	384.5	384.6	384.7	384.7	384.8	384.7
142.5°	396.3	396.8	397.3	397.8	398.2	398.5	398.7	398.9	399.1	399.2	399.1
145°	418.2	418.4	418.6	418.8	419.0	419.1	419.4	419.7	420.0	420.3	420.2
147.5°	437.3	437.6	438.0	438.3	438.7	438.9	439.2	439.5	439.8	440.1	440.1
150°	450.6	450.8	451.0	451.2	451.4	451.6	451.8	451.9	452.1	452.3	452.3
152.5°	461.6	461.8	462.1	462.3	462.6	462.8	462.9	463.1	463.2	463.3	463.4
155°	478.8	478.8	478.8	478.8	478.8	478.9	479.0	479.1	479.2	479.3	479.7
157.5°	493.5	493.4	493.3	493.1	493.0	493.0	493.1	493.2	493.2	493.3	493.7
160°	502.8	502.6	502.4	502.2	502.0	501.9	501.9	501.9	501.9	501.9	502.4
162.5°	511.0	510.7	510.4	510.1	509.9	509.8	509.8	509.9	510.0	510.1	510.6
165°	521.5	521.2	520.9	520.7	520.4	520.3	520.3	520.3	520.3	520.3	520.8
167.5°	530.0	529.6	529.2	528.9	528.5	528.3	528.4	528.5	528.6	528.6	529.2
170°	534.8	534.4	534.0	533.7	533.3	533.1	533.1	533.1	533.1	533.1	533.8
172.5°	538.6	538.2	537.8	537.4	537.0	536.8	536.8	536.8	536.8	536.8	537.4
175°	542.4	542.1	541.7	541.3	540.9	540.7	540.7	540.7	540.7	540.7	541.3
177.5°	544.1	543.8	543.5	543.2	542.9	542.7	542.7	542.7	542.7	542.7	543.2
180°	543.8	543.8	543.8	543.8	543.8	543.8	543.8	543.8	543.8	543.8	543.8



TEST NUMBER: P332433-830

CATALOG NUMBER: S123RDIW-S775D460U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1216.9	1216.9	1216.9	1216.9	1216.9	1216.9	1216.9	1216.9
2.5°	1212.0	1214.0	1215.9	1216.7	1216.4	1216.0	1215.6	1215.3
5°	1204.0	1206.0	1208.0	1208.7	1208.3	1207.9	1207.4	1207.0
7.5°	1187.1	1188.2	1189.3	1189.5	1188.7	1188.0	1187.2	1186.5
10°	1172.0	1172.1	1172.3	1172.0	1170.8	1169.7	1168.7	1167.5
12.5°	1153.0	1152.9	1152.8	1152.1	1150.8	1149.5	1148.3	1147.0
15°	1119.9	1118.8	1117.8	1116.4	1114.9	1113.3	1111.8	1110.3
17.5°	1080.3	1078.1	1075.7	1073.5	1071.1	1068.8	1066.6	1064.3
20°	1053.3	1050.4	1047.5	1044.8	1042.2	1039.5	1036.9	1034.3
22.5°	1024.3	1020.7	1017.1	1014.1	1011.6	1009.2	1006.7	1004.3
25°	976.8	972.1	967.5	964.0	961.6	959.1	956.8	954.3
27.5°	924.9	918.6	912.2	907.1	903.4	899.8	896.1	892.4
30°	888.2	880.6	873.2	867.7	864.2	860.7	857.1	853.7
32.5°	852.0	843.9	835.7	829.7	826.0	822.4	818.7	815.0
35°	798.3	788.9	779.5	772.8	768.8	764.9	760.9	757.0
37.5°	740.6	730.0	719.3	711.5	706.6	701.7	696.9	692.0
40°	700.6	689.2	677.8	669.6	664.5	659.5	654.4	649.4
42.5°	662.1	649.7	637.3	628.8	624.2	619.7	615.2	610.7
45°	605.7	593.1	580.6	571.7	566.5	561.2	556.0	550.7
47.5°	547.1	533.6	520.0	510.9	506.1	501.4	496.8	492.1
50°	507.7	494.1	480.5	471.2	466.2	461.1	456.1	451.0
52.5°	469.6	455.4	441.3	432.0	427.4	422.9	418.4	413.9
55°	412.7	400.0	387.3	378.7	374.4	369.9	365.6	361.2
57.5°	356.9	344.9	332.9	325.0	321.3	317.5	313.8	310.1
60°	321.7	309.9	298.0	290.3	286.5	282.8	279.1	275.3
62.5°	286.8	275.7	264.6	257.0	253.1	249.2	245.3	241.4
65°	237.0	226.3	215.6	209.0	206.6	204.2	201.8	199.3
67.5°	189.6	181.6	173.5	168.2	165.7	163.1	160.5	157.9
70°	160.3	152.6	145.0	140.0	137.5	135.1	132.7	130.3
72.5°	133.9	127.6	121.4	117.7	116.7	115.7	114.7	113.7
75°	100.2	98.0	95.9	94.5	94.1	93.7	93.2	92.7
77.5°	75.6	74.4	73.2	72.4	72.0	71.5	71.1	70.7
80°	60.9	60.2	59.6	59.0	58.5	58.2	57.7	57.2
82.5°	46.7	46.0	45.3	45.0	44.9	44.8	44.7	44.6
85°	26.8	26.3	25.9	25.6	25.6	25.6	25.6	25.6
87.5°	12.2	12.0	11.9	11.8	11.7	11.5	11.4	11.2
90°	11.0	11.4	11.8	12.1	12.3	12.4	12.6	12.8
92.5°	17.0	17.3	17.6	17.7	17.6	17.4	17.3	17.2
95°	32.3	32.7	33.1	33.3	33.3	33.3	33.3	33.3
97.5°	50.3	50.8	51.2	51.4	51.4	51.4	51.3	51.3
100°	63.3	63.6	63.9	64.2	64.4	64.6	64.8	64.9
102.5°	78.4	78.7	79.0	79.1	79.1	79.0	79.0	78.9
105°	100.8	100.8	100.8	100.9	101.1	101.3	101.5	101.7
107.5°	125.1	125.4	125.6	125.7	125.6	125.5	125.5	125.4
110°	141.3	141.7	142.0	142.1	141.9	141.8	141.6	141.4





TEST NUMBER: P332433-830

CATALOG NUMBER: S123RDIW-S775D460U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	157.5	158.0	158.4	158.6	158.5	158.5	158.5	158.4
115°	182.2	182.3	182.4	182.4	182.3	182.2	182.1	182.0
117.5°	207.1	207.0	207.0	206.9	206.6	206.3	206.0	205.8
120°	223.7	223.6	223.5	223.3	223.1	222.9	222.7	222.5
122.5°	240.4	240.2	239.9	239.7	239.4	239.1	238.8	238.6
125°	265.3	264.9	264.6	264.2	263.8	263.4	263.1	262.7
127.5°	290.0	289.5	288.9	288.4	288.0	287.6	287.1	286.7
130°	306.3	305.9	305.6	305.1	304.4	303.8	303.1	302.4
132.5°	322.3	321.8	321.3	320.8	320.4	319.8	319.3	318.8
135°	346.1	345.7	345.3	345.1	344.9	344.7	344.5	344.3
137.5°	369.4	369.0	368.5	368.2	367.8	367.5	367.1	366.7
140°	384.7	384.6	384.5	384.1	383.4	382.8	382.1	381.4
142.5°	399.0	398.9	398.8	398.5	398.0	397.5	397.0	396.4
145°	420.1	420.0	419.9	419.7	419.3	419.0	418.6	418.2
147.5°	440.1	440.1	440.1	439.8	439.2	438.6	438.0	437.4
150°	452.3	452.3	452.3	452.0	451.5	450.9	450.3	449.8
152.5°	463.5	463.7	463.9	463.7	463.3	462.7	462.2	461.8
155°	480.0	480.4	480.8	480.6	479.9	479.3	478.6	478.0
157.5°	494.2	494.6	494.9	494.8	494.4	493.8	493.2	492.8
160°	502.8	503.3	503.8	503.8	503.4	503.0	502.7	502.3
162.5°	511.0	511.5	512.0	511.9	511.3	510.7	510.1	509.4
165°	521.4	522.0	522.5	522.5	521.8	521.1	520.5	519.8
167.5°	529.8	530.4	530.9	530.9	530.4	529.8	529.2	528.6
170°	534.4	535.1	535.7	535.7	535.1	534.4	533.8	533.1
172.5°	538.0	538.6	539.1	539.1	538.5	537.8	537.2	536.5
175°	541.9	542.4	543.0	543.0	542.3	541.7	541.0	540.4
177.5°	543.7	544.1	544.5	544.5	543.9	543.5	542.9	542.3
180°	543.8	543.8	543.8	543.8	543.8	543.8	543.8	543.8

(END OF REPORT)