

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332196-930

Luminaire Tested: **S123DIW-S1000D1030U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332196-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S1000D1030U930-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1030 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6722.4 lumens
Efficiency: N/A
Efficacy: 109.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 61.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332196-930

CATALOG NUMBER: S123DIW-S1000D1030U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332196-930

CATALOG NUMBER: S123DIW-S1000D1030U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50				
1	98	93	89	86	90	86	83	80	73	71	68	61	59	57	49	48	47	42				
2	89	81	75	70	82	75	70	65	64	60	56	53	50	48	44	42	40	35				
3	81	72	64	58	75	66	60	55	56	51	47	47	44	41	39	36	34	30				
4	74	63	55	49	68	59	52	46	50	45	40	42	38	35	34	32	29	25				
5	68	56	48	42	63	52	45	40	45	39	35	38	33	30	31	28	25	22				
6	63	51	42	37	58	47	40	35	40	35	30	34	30	26	28	25	22	19				
7	58	46	38	32	53	43	35	30	37	31	27	31	27	23	26	22	20	17				
8	54	41	34	28	50	39	32	27	33	28	24	28	24	21	24	20	18	15				
9	50	38	30	25	46	35	29	24	31	25	21	26	22	19	22	18	16	14				
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	15	13				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13891	13891	13891
5°	13956	13765	13861
10°	13864	13645	13729
15°	13701	13490	13515
20°	13512	13270	13283
25°	13258	13007	12981
30°	12978	12716	12619
35°	12686	12408	12248
40°	12381	12067	11880
45°	12044	11756	11469
50°	11707	11372	11055
55°	11265	10975	10640
60°	10820	10512	10176
65°	10427	10004	9694
70°	9847	9429	9010
75°	9000	8675	8305
80°	8114	7773	7705
85°	7126	6854	6570



TEST NUMBER: P332196-930

CATALOG NUMBER: S123DIW-S1000D1030U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	121.6	1.8
10°-20°	343.3	5.1
20°-30°	507.0	7.5
30°-40°	592.3	8.8
40°-50°	595.5	8.9
50°-60°	523.1	7.8
60°-70°	389.7	5.8
70°-80°	222.0	3.3
80°-90°	66.8	1.0
90°-100°	40.1	0.6
100°-110°	191.0	2.8
110°-120°	458.8	6.8
120°-130°	584.2	8.7
130°-140°	624.2	9.3
140°-150°	583.7	8.7
150°-160°	470.8	7.0
160°-170°	303.9	4.5
170°-180°	104.7	1.6
0°-30°	971.9	14.5
0°-40°	1564.1	23.3
0°-60°	2682.6	39.9
0°-90°	3361.1	50.0
90°-120°	689.8	10.3
90°-150°	2481.9	36.9
90°-180°	3361.0	50.0
0°-180°	6722.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1290	1290	1290	1290	1290	
5°	1292	1286	1274	1284	1283	122
15°	1230	1224	1211	1219	1213	346
25°	1116	1109	1095	1096	1093	514
35°	965	958	944	938	932	604
45°	791	786	772	759	753	611
55°	600	598	585	573	567	538
65°	409	404	393	384	381	404
75°	216	212	209	203	200	231
85°	58	56	56	53	53	63
90°	1	9	20	23	24	5
95°	50	19	25	31	31	62
105°	244	248	179	43	36	259
115°	458	463	470	478	482	452
125°	645	652	655	657	658	576
135°	803	808	812	814	812	618
145°	927	932	934	936	936	580
155°	1021	1020	1020	1024	1020	470
165°	1077	1074	1074	1079	1074	304
175°	1102	1098	1099	1104	1098	105
180°	1102	1102	1102	1102	1102	



TEST NUMBER: P332196-930

CATALOG NUMBER: S123DIW-S1000D1030U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5
2.5°	1294.9	1294.2	1293.4	1292.6	1291.8	1290.3	1288.2	1286.0	1283.9	1281.7	1283.6
5°	1291.6	1290.4	1289.2	1287.9	1286.7	1284.7	1282.1	1279.3	1276.6	1273.9	1276.4
7.5°	1279.0	1277.7	1276.5	1275.3	1274.1	1272.0	1269.3	1266.4	1263.6	1260.8	1263.0
10°	1268.4	1267.1	1265.8	1264.6	1263.4	1261.2	1258.0	1254.7	1251.6	1248.4	1250.6
12.5°	1254.1	1253.1	1252.1	1251.0	1250.0	1248.0	1245.0	1241.9	1238.9	1235.9	1237.5
15°	1229.5	1228.5	1227.5	1226.5	1225.6	1223.4	1220.3	1217.1	1213.8	1210.6	1212.6
17.5°	1200.9	1199.5	1198.3	1197.0	1195.7	1193.5	1190.3	1187.1	1183.9	1180.6	1182.0
20°	1179.6	1178.1	1176.6	1175.1	1173.6	1171.3	1168.1	1164.9	1161.7	1158.5	1159.4
22.5°	1155.6	1154.1	1152.7	1151.1	1149.7	1147.4	1144.1	1140.9	1137.8	1134.5	1135.3
25°	1116.3	1114.8	1113.4	1111.9	1110.4	1108.1	1104.8	1101.6	1098.5	1095.2	1095.4
27.5°	1074.4	1072.9	1071.5	1070.1	1068.6	1066.2	1062.7	1059.3	1055.8	1052.4	1052.6
30°	1044.2	1042.9	1041.7	1040.5	1039.3	1036.9	1033.5	1030.0	1026.5	1023.1	1023.1
32.5°	1014.0	1012.4	1010.7	1009.1	1007.5	1005.3	1002.7	1000.0	997.4	994.7	993.3
35°	965.4	963.9	962.5	961.0	959.4	957.2	953.9	950.7	947.5	944.3	942.8
37.5°	915.7	913.8	911.9	910.0	908.2	905.6	902.4	899.1	895.9	892.6	890.8
40°	881.1	879.5	878.1	876.6	875.1	872.7	869.2	865.8	862.3	858.8	856.9
42.5°	846.4	844.7	843.1	841.4	839.8	837.1	833.7	830.3	826.8	823.4	821.4
45°	791.2	790.2	789.2	788.2	787.3	785.1	782.0	778.7	775.5	772.3	769.4
47.5°	736.4	734.9	733.5	732.1	730.7	728.4	725.5	722.4	719.4	716.4	713.5
50°	699.1	697.8	696.6	695.4	694.1	691.9	688.7	685.5	682.3	679.1	676.4
52.5°	660.0	659.2	658.4	657.5	656.6	654.5	651.2	647.8	644.3	640.9	638.6
55°	600.3	600.1	599.8	599.6	599.3	597.6	594.4	591.2	588.0	584.8	582.0
57.5°	543.5	542.7	541.8	541.0	540.1	538.4	535.9	533.3	530.8	528.2	525.8
60°	502.6	502.4	502.1	501.9	501.7	500.1	497.1	494.2	491.2	488.3	486.0
62.5°	466.3	465.6	465.0	464.3	463.7	461.9	458.9	456.0	453.1	450.0	447.8
65°	409.4	408.2	407.0	405.8	404.6	402.7	400.2	397.8	395.3	392.8	390.9
67.5°	349.4	348.2	347.2	346.1	345.0	343.5	341.6	339.7	337.9	336.0	334.3
70°	312.9	311.4	310.0	308.5	307.0	305.5	304.0	302.6	301.1	299.6	297.9
72.5°	274.8	273.7	272.6	271.5	270.4	269.0	267.3	265.7	264.0	262.3	260.8
75°	216.4	215.4	214.4	213.4	212.5	211.6	210.8	210.1	209.4	208.6	207.4
77.5°	164.7	164.1	163.5	163.1	162.5	161.8	160.9	160.0	159.1	158.2	157.4
80°	130.9	130.2	129.5	128.7	128.0	127.3	126.9	126.4	125.9	125.4	125.1
82.5°	98.1	97.9	97.8	97.7	97.5	97.3	97.3	97.2	97.1	97.0	96.5
85°	57.7	57.2	56.7	56.3	55.8	55.5	55.5	55.5	55.5	55.5	55.0
87.5°	23.2	23.0	22.8	22.6	22.3	22.3	22.7	22.9	23.2	23.5	23.4
90°	0.8	2.6	4.5	6.3	8.1	10.2	12.6	14.9	17.3	19.6	20.4
92.5°	15.2	14.8	14.2	13.7	13.2	13.9	15.7	17.4	19.2	21.0	22.1
95°	50.0	42.5	35.1	27.6	20.1	17.4	19.4	21.4	23.4	25.4	26.7
97.5°	100.4	97.0	93.7	90.3	87.0	78.8	65.7	52.6	39.5	26.3	27.8
100°	138.4	142.0	145.7	149.3	153.0	140.6	112.2	83.8	55.4	27.0	28.5
102.5°	181.6	184.3	186.9	189.5	192.1	177.9	146.9	115.9	84.9	53.9	49.4
105°	244.0	246.1	248.0	250.1	252.0	244.8	228.4	212.1	195.8	179.4	147.2
107.5°	309.9	311.4	313.1	314.7	316.3	318.4	321.0	323.5	326.1	328.7	305.1
110°	353.8	355.2	356.7	358.2	359.5	361.3	363.3	365.3	367.3	369.3	363.3



TEST NUMBER: P332196-930

CATALOG NUMBER: S123DIW-S1000D1030U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	395.7	397.0	398.3	399.7	401.0	402.6	404.6	406.6	408.6	410.6	410.7
115°	457.8	458.9	459.9	461.1	462.1	463.5	465.1	466.8	468.4	470.0	471.9
117.5°	517.9	519.2	520.6	521.9	523.3	524.3	525.2	526.0	526.8	527.7	529.1
120°	555.2	556.8	558.5	560.1	561.7	562.9	563.4	563.9	564.5	565.0	566.5
122.5°	593.2	594.5	595.9	597.2	598.6	599.6	600.3	601.0	601.7	602.3	603.4
125°	645.3	646.8	648.2	649.6	651.1	652.2	652.9	653.6	654.4	655.1	655.5
127.5°	695.7	697.2	698.6	700.1	701.6	702.7	703.6	704.5	705.3	706.2	706.8
130°	727.2	728.6	730.1	731.6	733.0	734.1	734.8	735.6	736.3	737.0	737.8
132.5°	757.3	758.8	760.2	761.7	763.1	764.2	764.8	765.3	765.9	766.5	767.2
135°	803.3	804.5	805.5	806.6	807.7	808.6	809.3	810.1	810.8	811.5	812.0
137.5°	842.6	844.0	845.4	846.8	848.2	849.1	849.5	849.9	850.3	850.7	851.5
140°	868.9	869.9	871.1	872.1	873.2	874.0	874.6	875.1	875.6	876.2	876.9
142.5°	893.1	894.1	895.3	896.3	897.5	898.3	898.8	899.4	899.9	900.4	901.1
145°	927.0	928.2	929.5	930.8	932.1	932.9	933.3	933.6	934.0	934.3	934.7
147.5°	959.0	959.8	960.6	961.4	962.3	962.9	963.2	963.6	963.9	964.3	964.7
150°	978.6	979.1	979.7	980.2	980.7	981.2	981.5	981.9	982.3	982.7	983.0
152.5°	996.3	996.5	996.8	997.0	997.3	997.5	997.8	997.9	998.2	998.4	999.1
155°	1021.2	1020.8	1020.4	1020.1	1019.7	1019.6	1019.8	1019.9	1020.2	1020.3	1021.2
157.5°	1040.5	1040.5	1040.4	1040.4	1040.3	1040.2	1040.1	1039.8	1039.7	1039.5	1040.6
160°	1052.3	1052.1	1051.9	1051.7	1051.6	1051.3	1051.2	1051.0	1050.8	1050.7	1051.7
162.5°	1063.4	1062.9	1062.5	1062.0	1061.5	1061.2	1061.0	1060.9	1060.6	1060.5	1061.7
165°	1076.8	1076.3	1075.8	1075.2	1074.6	1074.3	1074.1	1073.9	1073.7	1073.6	1075.1
167.5°	1087.3	1086.6	1085.9	1085.2	1084.4	1084.0	1084.0	1084.0	1084.0	1084.0	1085.5
170°	1093.2	1092.5	1091.8	1091.0	1090.3	1090.0	1090.0	1090.0	1090.0	1090.0	1091.4
172.5°	1097.1	1096.3	1095.4	1094.5	1093.6	1093.3	1093.4	1093.6	1093.7	1093.9	1095.4
175°	1102.2	1101.3	1100.4	1099.5	1098.6	1098.2	1098.4	1098.6	1098.8	1098.9	1100.2
177.5°	1103.5	1102.8	1102.1	1101.4	1100.7	1100.3	1100.5	1100.7	1100.7	1100.9	1102.1
180°	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2



TEST NUMBER: P332196-930

CATALOG NUMBER: S123DIW-S1000D1030U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5
2.5°	1285.6	1287.6	1289.6	1290.5	1290.2	1290.0	1289.8	1289.6
5°	1278.8	1281.2	1283.8	1284.7	1284.3	1283.8	1283.3	1282.8
7.5°	1265.3	1267.5	1269.7	1270.6	1270.3	1270.1	1269.7	1269.4
10°	1252.8	1255.0	1257.3	1258.1	1257.6	1257.1	1256.6	1256.1
12.5°	1239.2	1240.8	1242.4	1243.1	1242.8	1242.5	1242.2	1241.9
15°	1214.6	1216.5	1218.5	1218.8	1217.3	1215.8	1214.3	1212.8
17.5°	1183.4	1184.8	1186.2	1186.6	1186.1	1185.5	1185.0	1184.5
20°	1160.4	1161.5	1162.5	1162.5	1161.8	1161.1	1160.3	1159.6
22.5°	1136.1	1136.9	1137.7	1137.6	1136.7	1135.7	1134.8	1133.8
25°	1095.7	1096.0	1096.3	1096.0	1095.2	1094.5	1093.7	1093.0
27.5°	1052.8	1053.0	1053.2	1052.8	1051.9	1050.9	1050.0	1049.0
30°	1023.1	1023.1	1023.1	1022.2	1020.5	1018.8	1017.1	1015.3
32.5°	991.9	990.6	989.2	988.0	987.1	986.1	985.2	984.2
35°	941.3	939.9	938.4	937.0	935.8	934.6	933.4	932.1
37.5°	889.1	887.3	885.5	884.2	883.5	882.6	881.8	881.1
40°	854.9	853.0	851.0	849.5	848.5	847.5	846.5	845.5
42.5°	819.4	817.4	815.5	814.0	813.0	812.0	811.1	810.1
45°	766.4	763.4	760.5	758.4	757.2	755.9	754.7	753.4
47.5°	710.5	707.7	704.7	702.8	701.6	700.6	699.5	698.4
50°	673.7	671.0	668.2	666.2	664.7	663.2	661.7	660.2
52.5°	636.3	634.0	631.7	629.7	628.3	626.8	625.3	623.9
55°	579.4	576.7	574.0	571.9	570.7	569.5	568.3	567.0
57.5°	523.3	521.0	518.5	516.6	515.2	513.7	512.3	510.9
60°	483.8	481.6	479.4	477.7	476.4	475.2	473.9	472.7
62.5°	445.6	443.4	441.2	439.7	438.8	438.0	437.2	436.3
65°	388.9	386.9	384.9	383.6	382.9	382.1	381.3	380.6
67.5°	332.6	330.8	329.1	327.8	326.7	325.6	324.6	323.6
70°	296.1	294.4	292.7	291.2	290.0	288.8	287.6	286.3
72.5°	259.3	257.7	256.2	255.1	254.5	253.8	253.2	252.6
75°	206.2	204.9	203.7	202.7	201.9	201.2	200.5	199.7
77.5°	156.5	155.7	154.9	154.5	154.5	154.5	154.5	154.5
80°	124.9	124.7	124.4	124.3	124.3	124.3	124.3	124.3
82.5°	96.1	95.6	95.2	94.9	94.7	94.5	94.3	94.1
85°	54.5	54.0	53.5	53.2	53.2	53.2	53.2	53.2
87.5°	23.3	23.3	23.2	23.2	23.3	23.4	23.5	23.6
90°	21.1	21.9	22.6	23.1	23.5	23.8	24.2	24.5
92.5°	23.3	24.5	25.6	26.3	26.5	26.7	27.0	27.1
95°	28.0	29.2	30.5	31.1	31.1	31.1	31.1	31.1
97.5°	29.3	30.7	32.2	33.0	33.2	33.3	33.6	33.8
100°	29.9	31.4	32.9	33.7	33.8	34.0	34.2	34.4
102.5°	44.8	40.4	35.8	33.8	34.1	34.4	34.7	35.1
105°	115.0	82.7	50.5	34.6	35.0	35.3	35.6	36.0
107.5°	281.4	257.9	234.2	210.3	186.0	161.8	137.5	113.2
110°	357.3	351.3	345.3	329.3	303.3	277.2	251.2	225.2



TEST NUMBER: P332196-930

CATALOG NUMBER: S123DIW-S1000D1030U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	410.8	410.9	411.0	408.3	402.8	397.4	391.8	386.4
115°	473.7	475.5	477.4	478.6	479.3	480.0	480.8	481.5
117.5°	530.6	532.1	533.5	534.3	534.4	534.6	534.8	534.9
120°	567.9	569.4	570.9	571.6	571.6	571.6	571.6	571.6
122.5°	604.4	605.4	606.4	607.1	607.2	607.3	607.5	607.6
125°	655.8	656.2	656.6	657.0	657.3	657.6	658.0	658.4
127.5°	707.4	707.9	708.6	708.7	708.3	707.9	707.6	707.2
130°	738.5	739.2	739.9	740.1	739.7	739.4	739.0	738.7
132.5°	767.9	768.7	769.4	769.5	769.0	768.5	768.0	767.4
135°	812.6	813.2	813.7	813.7	813.2	812.6	812.0	811.5
137.5°	852.4	853.3	854.2	854.4	854.0	853.7	853.3	853.0
140°	877.7	878.4	879.1	879.3	879.0	878.6	878.2	877.8
142.5°	901.6	902.2	902.8	902.8	902.3	901.8	901.3	900.7
145°	935.1	935.5	935.8	936.0	936.0	936.0	936.0	936.0
147.5°	965.1	965.4	965.8	965.6	964.7	963.8	963.0	962.2
150°	983.4	983.7	984.1	984.1	983.5	982.9	982.4	981.9
152.5°	999.7	1000.4	1001.0	1000.9	1000.0	999.2	998.4	997.6
155°	1022.1	1023.0	1024.0	1023.9	1022.8	1021.7	1020.6	1019.5
157.5°	1041.7	1042.8	1043.8	1043.7	1042.3	1040.9	1039.4	1038.0
160°	1052.8	1053.9	1055.0	1054.9	1053.6	1052.4	1051.1	1049.8
162.5°	1062.9	1064.2	1065.4	1065.4	1064.4	1063.2	1062.1	1060.9
165°	1076.4	1077.9	1079.4	1079.5	1078.2	1076.9	1075.6	1074.4
167.5°	1087.0	1088.4	1089.9	1089.9	1088.4	1087.0	1085.5	1084.0
170°	1092.8	1094.3	1095.8	1095.8	1094.3	1092.8	1091.4	1090.0
172.5°	1096.8	1098.2	1099.7	1099.6	1098.0	1096.4	1094.8	1093.2
175°	1101.5	1102.8	1104.1	1104.0	1102.5	1101.1	1099.6	1098.1
177.5°	1103.3	1104.4	1105.5	1105.5	1104.0	1102.5	1101.1	1099.6
180°	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2

(END OF REPORT)