

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332226-930

Luminaire Tested: **S123DIW-S1165D1030U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332226-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIW-S1165D1030U930-4F0-1E-UDD-F  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1030 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7242.7 lumens  
Efficiency: N/A  
Efficacy: 107.5 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 67.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332226-930

CATALOG NUMBER: S123DIW-S1165D1030U930-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332226-930

CATALOG NUMBER: S123DIW-S1165D1030U930-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	54
1	99	94	90	87	91	87	84	81	75	72	70	63	61	60	52	51	50	45
2	90	82	76	71	83	76	71	66	65	61	58	55	52	50	46	44	42	38
3	82	72	65	59	75	67	61	55	58	53	49	49	45	42	41	38	36	32
4	75	64	56	50	69	60	52	47	51	46	41	44	39	36	36	33	31	27
5	69	57	49	43	63	53	46	40	46	40	36	39	35	31	33	30	27	24
6	63	51	43	37	58	48	40	35	41	36	31	35	31	27	30	26	24	21
7	59	46	38	32	54	43	36	31	37	32	27	32	28	24	27	24	21	18
8	54	42	34	29	50	39	32	27	34	28	24	29	25	22	25	21	19	16
9	51	38	31	26	47	36	29	24	31	26	22	27	23	19	23	20	17	15
10	47	35	28	23	44	33	26	22	29	23	20	25	21	18	21	18	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	16043	16043	16043
5°	16119	15896	16008
10°	16010	15759	15856
15°	15824	15581	15610
20°	15605	15326	15340
25°	15311	15023	14992
30°	14989	14686	14574
35°	14651	14331	14146
40°	14299	13939	13722
45°	13910	13577	13247
50°	13520	13134	12769
55°	13011	12675	12288
60°	12499	12140	11752
65°	12045	11556	11196
70°	11374	10889	10408
75°	10393	10019	9590
80°	9372	8976	8901
85°	8225	7916	7608



TEST NUMBER: P332226-930

CATALOG NUMBER: S123DIW-S1165D1030U930-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	140.4	1.9
10°-20°	396.4	5.5
20°-30°	585.6	8.1
30°-40°	684.0	9.4
40°-50°	687.7	9.5
50°-60°	604.1	8.3
60°-70°	450.0	6.2
70°-80°	256.4	3.5
80°-90°	76.7	1.1
90°-100°	40.1	0.6
100°-110°	191.0	2.6
110°-120°	458.8	6.3
120°-130°	584.2	8.1
130°-140°	624.2	8.6
140°-150°	583.7	8.1
150°-160°	470.8	6.5
160°-170°	303.9	4.2
170°-180°	104.7	1.4
0°-30°	1122.4	15.5
0°-40°	1806.5	24.9
0°-60°	3098.3	42.8
0°-90°	3881.4	53.6
90°-120°	689.8	9.5
90°-150°	2481.9	34.3
90°-180°	3361.0	46.4
0°-180°	7242.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1490	1490	1490	1490	1490	
5°	1492	1485	1471	1483	1482	141
15°	1420	1414	1398	1407	1401	400
25°	1289	1281	1265	1266	1262	594
35°	1115	1107	1091	1083	1076	697
45°	914	908	892	877	870	705
55°	693	691	675	662	655	621
65°	473	466	454	444	440	466
75°	250	245	241	235	231	267
85°	67	64	64	62	62	73
90°	1	9	20	23	24	6
95°	50	19	25	31	31	62
105°	244	248	179	43	36	259
115°	458	463	470	478	482	452
125°	645	652	655	657	658	576
135°	803	808	812	814	812	618
145°	927	932	934	936	936	580
155°	1021	1020	1020	1024	1020	470
165°	1077	1074	1074	1079	1074	304
175°	1102	1098	1099	1104	1098	105
180°	1102	1102	1102	1102	1102	



TEST NUMBER: P332226-930

CATALOG NUMBER: S123DIW-S1165D1030U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4
2.5°	1495.6	1494.7	1493.8	1492.9	1491.9	1490.2	1487.8	1485.2	1482.7	1480.2	1482.5
5°	1491.8	1490.4	1488.9	1487.5	1486.0	1483.8	1480.7	1477.5	1474.4	1471.2	1474.1
7.5°	1477.2	1475.7	1474.3	1472.8	1471.5	1469.1	1465.8	1462.6	1459.4	1456.1	1458.7
10°	1464.8	1463.4	1462.0	1460.5	1459.1	1456.6	1452.9	1449.2	1445.4	1441.8	1444.3
12.5°	1448.5	1447.2	1446.0	1444.9	1443.7	1441.3	1437.9	1434.4	1430.9	1427.4	1429.3
15°	1420.0	1418.9	1417.7	1416.6	1415.4	1413.0	1409.3	1405.6	1401.9	1398.2	1400.4
17.5°	1386.9	1385.4	1384.0	1382.5	1381.0	1378.4	1374.7	1371.0	1367.3	1363.6	1365.2
20°	1362.3	1360.6	1358.9	1357.1	1355.5	1352.7	1349.1	1345.4	1341.7	1338.0	1339.1
22.5°	1334.6	1332.9	1331.2	1329.5	1327.8	1325.1	1321.4	1317.7	1314.0	1310.3	1311.2
25°	1289.2	1287.5	1285.8	1284.1	1282.5	1279.7	1276.0	1272.4	1268.6	1264.9	1265.2
27.5°	1240.8	1239.2	1237.5	1235.8	1234.2	1231.4	1227.4	1223.4	1219.4	1215.4	1215.7
30°	1206.0	1204.5	1203.1	1201.7	1200.3	1197.6	1193.6	1189.6	1185.6	1181.6	1181.6
32.5°	1171.1	1169.2	1167.3	1165.5	1163.6	1161.1	1158.1	1155.0	1151.9	1148.8	1147.2
35°	1115.0	1113.3	1111.6	1109.9	1108.2	1105.5	1101.7	1098.0	1094.3	1090.6	1088.9
37.5°	1057.5	1055.4	1053.2	1051.1	1048.9	1045.9	1042.2	1038.4	1034.7	1030.9	1028.8
40°	1017.6	1015.9	1014.2	1012.4	1010.7	1007.9	1003.9	999.9	995.9	992.0	989.7
42.5°	977.5	975.7	973.7	971.8	969.8	966.9	962.9	958.9	954.9	951.0	948.7
45°	913.8	912.6	911.5	910.4	909.2	906.8	903.1	899.4	895.7	891.9	888.6
47.5°	850.4	848.8	847.2	845.5	843.8	841.3	837.8	834.3	830.9	827.4	824.0
50°	807.4	806.0	804.5	803.2	801.7	799.2	795.4	791.7	788.0	784.3	781.2
52.5°	762.3	761.3	760.3	759.4	758.4	755.9	752.0	748.1	744.2	740.2	737.5
55°	693.3	693.1	692.8	692.5	692.2	690.2	686.5	682.8	679.1	675.4	672.3
57.5°	627.7	626.7	625.7	624.8	623.9	621.9	618.9	616.0	613.0	610.0	607.2
60°	580.6	580.2	580.0	579.7	579.4	577.6	574.1	570.7	567.3	563.9	561.3
62.5°	538.5	537.8	537.0	536.3	535.6	533.5	530.0	526.6	523.3	519.8	517.2
65°	472.9	471.5	470.0	468.6	467.2	465.0	462.2	459.3	456.5	453.7	451.4
67.5°	403.4	402.2	401.0	399.7	398.4	396.7	394.5	392.4	390.2	388.1	386.0
70°	361.4	359.7	358.0	356.3	354.6	352.9	351.1	349.4	347.7	346.0	344.1
72.5°	317.3	316.1	314.8	313.6	312.3	310.7	308.8	306.8	304.9	303.0	301.2
75°	249.9	248.7	247.6	246.5	245.3	244.3	243.5	242.6	241.8	240.9	239.5
77.5°	190.2	189.6	188.9	188.3	187.7	186.9	185.8	184.8	183.8	182.8	181.8
80°	151.2	150.3	149.5	148.6	147.8	147.1	146.5	145.9	145.4	144.8	144.6
82.5°	113.3	113.1	112.9	112.8	112.6	112.4	112.3	112.3	112.1	112.0	111.5
85°	66.6	66.0	65.5	64.9	64.3	64.1	64.1	64.1	64.1	64.1	63.5
87.5°	26.8	26.5	26.2	25.8	25.5	25.5	25.8	26.0	26.3	26.5	26.4
90°	0.8	2.6	4.5	6.3	8.1	10.2	12.6	14.9	17.3	19.6	20.4
92.5°	15.2	14.8	14.2	13.7	13.2	13.9	15.7	17.4	19.2	21.0	22.1
95°	50.0	42.5	35.1	27.6	20.1	17.4	19.4	21.4	23.4	25.4	26.7
97.5°	100.4	97.0	93.7	90.3	87.0	78.8	65.7	52.6	39.5	26.3	27.8
100°	138.4	142.0	145.7	149.3	153.0	140.6	112.2	83.8	55.4	27.0	28.5
102.5°	181.6	184.3	186.9	189.5	192.1	177.9	146.9	115.9	84.9	53.9	49.4
105°	244.0	246.1	248.0	250.1	252.0	244.8	228.4	212.1	195.8	179.4	147.2
107.5°	309.9	311.4	313.1	314.7	316.3	318.4	321.0	323.5	326.1	328.7	305.1
110°	353.8	355.2	356.7	358.2	359.5	361.3	363.3	365.3	367.3	369.3	363.3



TEST NUMBER: P332226-930

CATALOG NUMBER: S123DIW-S1165D1030U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	395.7	397.0	398.3	399.7	401.0	402.6	404.6	406.6	408.6	410.6	410.7
115°	457.8	458.9	459.9	461.1	462.1	463.5	465.1	466.8	468.4	470.0	471.9
117.5°	517.9	519.2	520.6	521.9	523.3	524.3	525.2	526.0	526.8	527.7	529.1
120°	555.2	556.8	558.5	560.1	561.7	562.9	563.4	563.9	564.5	565.0	566.5
122.5°	593.2	594.5	595.9	597.2	598.6	599.6	600.3	601.0	601.7	602.3	603.4
125°	645.3	646.8	648.2	649.6	651.1	652.2	652.9	653.6	654.4	655.1	655.5
127.5°	695.7	697.2	698.6	700.1	701.6	702.7	703.6	704.5	705.3	706.2	706.8
130°	727.2	728.6	730.1	731.6	733.0	734.1	734.8	735.6	736.3	737.0	737.8
132.5°	757.3	758.8	760.2	761.7	763.1	764.2	764.8	765.3	765.9	766.5	767.2
135°	803.3	804.5	805.5	806.6	807.7	808.6	809.3	810.1	810.8	811.5	812.0
137.5°	842.6	844.0	845.4	846.8	848.2	849.1	849.5	849.9	850.3	850.7	851.5
140°	868.9	869.9	871.1	872.1	873.2	874.0	874.6	875.1	875.6	876.2	876.9
142.5°	893.1	894.1	895.3	896.3	897.5	898.3	898.8	899.4	899.9	900.4	901.1
145°	927.0	928.2	929.5	930.8	932.1	932.9	933.3	933.6	934.0	934.3	934.7
147.5°	959.0	959.8	960.6	961.4	962.3	962.9	963.2	963.6	963.9	964.3	964.7
150°	978.6	979.1	979.7	980.2	980.7	981.2	981.5	981.9	982.3	982.7	983.0
152.5°	996.3	996.5	996.8	997.0	997.3	997.5	997.8	997.9	998.2	998.4	999.1
155°	1021.2	1020.8	1020.4	1020.1	1019.7	1019.6	1019.8	1019.9	1020.2	1020.3	1021.2
157.5°	1040.5	1040.5	1040.4	1040.4	1040.3	1040.2	1040.1	1039.8	1039.7	1039.5	1040.6
160°	1052.3	1052.1	1051.9	1051.7	1051.6	1051.3	1051.2	1051.0	1050.8	1050.7	1051.7
162.5°	1063.4	1062.9	1062.5	1062.0	1061.5	1061.2	1061.0	1060.9	1060.6	1060.5	1061.7
165°	1076.8	1076.3	1075.8	1075.2	1074.6	1074.3	1074.1	1073.9	1073.7	1073.6	1075.1
167.5°	1087.3	1086.6	1085.9	1085.2	1084.4	1084.0	1084.0	1084.0	1084.0	1084.0	1085.5
170°	1093.2	1092.5	1091.8	1091.0	1090.3	1090.0	1090.0	1090.0	1090.0	1090.0	1091.4
172.5°	1097.1	1096.3	1095.4	1094.5	1093.6	1093.3	1093.4	1093.6	1093.7	1093.9	1095.4
175°	1102.2	1101.3	1100.4	1099.5	1098.6	1098.2	1098.4	1098.6	1098.8	1098.9	1100.2
177.5°	1103.5	1102.8	1102.1	1101.4	1100.7	1100.3	1100.5	1100.7	1100.7	1100.9	1102.1
180°	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2



TEST NUMBER: P332226-930

CATALOG NUMBER: S123DIW-S1165D1030U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4
2.5°	1484.7	1487.0	1489.3	1490.4	1490.1	1489.9	1489.6	1489.5
5°	1476.9	1479.8	1482.6	1483.8	1483.2	1482.6	1482.1	1481.5
7.5°	1461.3	1463.8	1466.4	1467.5	1467.1	1466.8	1466.5	1466.2
10°	1446.9	1449.4	1452.0	1453.0	1452.5	1451.9	1451.3	1450.7
12.5°	1431.2	1433.1	1434.9	1435.7	1435.3	1435.0	1434.7	1434.4
15°	1402.7	1405.0	1407.3	1407.6	1405.9	1404.2	1402.5	1400.8
17.5°	1366.8	1368.4	1369.9	1370.4	1369.9	1369.2	1368.6	1368.0
20°	1340.3	1341.4	1342.6	1342.6	1341.8	1340.9	1340.1	1339.2
22.5°	1312.1	1313.0	1313.9	1313.9	1312.8	1311.7	1310.6	1309.5
25°	1265.5	1265.8	1266.1	1265.8	1264.9	1264.0	1263.2	1262.3
27.5°	1215.9	1216.1	1216.3	1215.9	1214.9	1213.7	1212.7	1211.6
30°	1181.6	1181.6	1181.6	1180.6	1178.6	1176.6	1174.6	1172.6
32.5°	1145.6	1144.0	1142.4	1141.1	1140.0	1138.9	1137.8	1136.8
35°	1087.2	1085.5	1083.8	1082.2	1080.8	1079.4	1077.9	1076.5
37.5°	1026.8	1024.7	1022.7	1021.2	1020.3	1019.4	1018.5	1017.6
40°	987.4	985.1	982.8	981.1	980.0	978.8	977.7	976.6
42.5°	946.4	944.1	941.8	940.1	939.0	937.8	936.7	935.6
45°	885.2	881.7	878.3	875.9	874.5	873.0	871.6	870.2
47.5°	820.7	817.3	813.9	811.6	810.4	809.1	807.9	806.7
50°	778.0	774.9	771.8	769.4	767.7	766.0	764.3	762.5
52.5°	734.9	732.2	729.5	727.3	725.6	723.9	722.2	720.5
55°	669.1	666.0	662.8	660.6	659.2	657.7	656.3	654.8
57.5°	604.5	601.7	598.8	596.6	595.0	593.4	591.7	590.0
60°	558.8	556.2	553.7	551.6	550.2	548.8	547.4	545.9
62.5°	514.7	512.1	509.6	507.8	506.8	505.8	504.9	503.9
65°	449.1	446.9	444.6	443.0	442.1	441.3	440.4	439.6
67.5°	384.1	382.0	380.1	378.5	377.3	376.1	374.9	373.7
70°	342.0	340.1	338.0	336.3	334.9	333.5	332.1	330.7
72.5°	299.5	297.7	295.9	294.6	293.9	293.2	292.4	291.7
75°	238.1	236.7	235.2	234.1	233.3	232.4	231.5	230.6
77.5°	180.8	179.9	178.9	178.4	178.4	178.4	178.4	178.4
80°	144.2	144.0	143.7	143.6	143.6	143.6	143.6	143.6
82.5°	111.0	110.5	110.0	109.6	109.3	109.2	108.9	108.7
85°	62.9	62.4	61.8	61.6	61.6	61.6	61.6	61.6
87.5°	26.3	26.3	26.2	26.2	26.3	26.3	26.3	26.4
90°	21.1	21.9	22.6	23.1	23.5	23.8	24.2	24.5
92.5°	23.3	24.5	25.6	26.3	26.5	26.7	27.0	27.1
95°	28.0	29.2	30.5	31.1	31.1	31.1	31.1	31.1
97.5°	29.3	30.7	32.2	33.0	33.2	33.3	33.6	33.8
100°	29.9	31.4	32.9	33.7	33.8	34.0	34.2	34.4
102.5°	44.8	40.4	35.8	33.8	34.1	34.4	34.7	35.1
105°	115.0	82.7	50.5	34.6	35.0	35.3	35.6	36.0
107.5°	281.4	257.9	234.2	210.3	186.0	161.8	137.5	113.2
110°	357.3	351.3	345.3	329.3	303.3	277.2	251.2	225.2





TEST NUMBER: P332226-930

CATALOG NUMBER: S123DIW-S1165D1030U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	410.8	410.9	411.0	408.3	402.8	397.4	391.8	386.4
115°	473.7	475.5	477.4	478.6	479.3	480.0	480.8	481.5
117.5°	530.6	532.1	533.5	534.3	534.4	534.6	534.8	534.9
120°	567.9	569.4	570.9	571.6	571.6	571.6	571.6	571.6
122.5°	604.4	605.4	606.4	607.1	607.2	607.3	607.5	607.6
125°	655.8	656.2	656.6	657.0	657.3	657.6	658.0	658.4
127.5°	707.4	707.9	708.6	708.7	708.3	707.9	707.6	707.2
130°	738.5	739.2	739.9	740.1	739.7	739.4	739.0	738.7
132.5°	767.9	768.7	769.4	769.5	769.0	768.5	768.0	767.4
135°	812.6	813.2	813.7	813.7	813.2	812.6	812.0	811.5
137.5°	852.4	853.3	854.2	854.4	854.0	853.7	853.3	853.0
140°	877.7	878.4	879.1	879.3	879.0	878.6	878.2	877.8
142.5°	901.6	902.2	902.8	902.8	902.3	901.8	901.3	900.7
145°	935.1	935.5	935.8	936.0	936.0	936.0	936.0	936.0
147.5°	965.1	965.4	965.8	965.6	964.7	963.8	963.0	962.2
150°	983.4	983.7	984.1	984.1	983.5	982.9	982.4	981.9
152.5°	999.7	1000.4	1001.0	1000.9	1000.0	999.2	998.4	997.6
155°	1022.1	1023.0	1024.0	1023.9	1022.8	1021.7	1020.6	1019.5
157.5°	1041.7	1042.8	1043.8	1043.7	1042.3	1040.9	1039.4	1038.0
160°	1052.8	1053.9	1055.0	1054.9	1053.6	1052.4	1051.1	1049.8
162.5°	1062.9	1064.2	1065.4	1065.4	1064.4	1063.2	1062.1	1060.9
165°	1076.4	1077.9	1079.4	1079.5	1078.2	1076.9	1075.6	1074.4
167.5°	1087.0	1088.4	1089.9	1089.9	1088.4	1087.0	1085.5	1084.0
170°	1092.8	1094.3	1095.8	1095.8	1094.3	1092.8	1091.4	1090.0
172.5°	1096.8	1098.2	1099.7	1099.6	1098.0	1096.4	1094.8	1093.2
175°	1101.5	1102.8	1104.1	1104.0	1102.5	1101.1	1099.6	1098.1
177.5°	1103.3	1104.4	1105.5	1105.5	1104.0	1102.5	1101.1	1099.6
180°	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2	1102.2

(END OF REPORT)