

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332221-930

Luminaire Tested: **S123DIW-S1165D755U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332221-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S1165D755U930-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 755 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6015.0 lumens
Efficiency: N/A
Efficacy: 100.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 59.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332221-930

CATALOG NUMBER: S123DIW-S1165D755U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332221-930

CATALOG NUMBER: S123DIW-S1165D755U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	91	91	91	80	80	80	69	69	69	65
1	101	96	92	89	95	91	87	84	80	77	75	70	68	67	61	60	59	54
2	92	84	78	73	86	79	74	69	70	66	62	62	58	56	54	51	49	45
3	84	74	66	60	78	70	63	58	62	57	52	55	50	47	48	45	42	38
4	77	66	57	51	72	62	55	49	55	49	45	49	44	40	43	39	36	33
5	71	59	50	44	66	55	48	42	49	43	38	44	39	35	38	35	31	29
6	65	53	44	38	61	50	42	37	44	38	34	40	34	31	35	31	28	25
7	60	48	39	34	56	45	38	32	40	34	30	36	31	27	32	28	25	22
8	56	43	35	30	52	41	34	29	37	31	26	33	28	24	29	25	22	20
9	52	40	32	27	49	38	31	26	34	28	24	30	25	22	27	23	20	18
10	49	36	29	24	46	35	28	23	31	25	21	28	23	20	25	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16043	16043	16043
5°	16119	15896	16008
10°	16010	15759	15856
15°	15824	15581	15610
20°	15605	15326	15340
25°	15311	15023	14992
30°	14989	14686	14574
35°	14651	14331	14146
40°	14299	13939	13722
45°	13910	13577	13247
50°	13520	13134	12769
55°	13011	12675	12288
60°	12499	12140	11752
65°	12045	11556	11196
70°	11374	10889	10408
75°	10393	10019	9590
80°	9372	8976	8901
85°	8225	7916	7608



TEST NUMBER: P332221-930

CATALOG NUMBER: S123DIW-S1165D755U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	140.4	2.3
10°-20°	396.4	6.6
20°-30°	585.6	9.7
30°-40°	684.0	11.4
40°-50°	687.7	11.4
50°-60°	604.1	10.0
60°-70°	450.0	7.5
70°-80°	256.4	4.3
80°-90°	75.9	1.3
90°-100°	50.2	0.8
100°-110°	150.2	2.5
110°-120°	255.5	4.2
120°-130°	336.1	5.6
130°-140°	377.7	6.3
140°-150°	371.3	6.2
150°-160°	312.6	5.2
160°-170°	208.1	3.5
170°-180°	72.9	1.2
0°-30°	1122.4	18.7
0°-40°	1806.5	30.0
0°-60°	3098.3	51.5
0°-90°	3880.6	64.5
90°-120°	455.9	7.6
90°-150°	1540.9	25.6
90°-180°	2134.0	35.5
0°-180°	6015.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1490	1490	1490	1490	1490	
5°	1492	1485	1471	1483	1482	141
15°	1420	1414	1398	1407	1401	400
25°	1289	1281	1265	1266	1262	594
35°	1115	1107	1091	1083	1076	697
45°	914	908	892	877	870	705
55°	693	691	675	662	655	621
65°	473	466	454	444	440	466
75°	250	245	241	235	231	267
85°	67	64	64	62	62	73
90°	1	7	14	17	18	6
95°	36	40	45	47	47	40
105°	136	138	143	143	144	146
115°	257	259	258	258	258	254
125°	376	378	377	375	372	336
135°	488	492	491	489	488	376
145°	592	594	596	595	592	370
155°	678	678	679	681	677	312
165°	739	737	737	740	736	208
175°	768	766	766	769	766	73
180°	770	770	770	770	770	



TEST NUMBER: P332221-930

CATALOG NUMBER: S123DIW-S1165D755U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4
2.5°	1495.6	1494.7	1493.8	1492.9	1491.9	1490.2	1487.8	1485.2	1482.7	1480.2	1482.5
5°	1491.8	1490.4	1488.9	1487.5	1486.0	1483.8	1480.7	1477.5	1474.4	1471.2	1474.1
7.5°	1477.2	1475.7	1474.3	1472.8	1471.5	1469.1	1465.8	1462.6	1459.4	1456.1	1458.7
10°	1464.8	1463.4	1462.0	1460.5	1459.1	1456.6	1452.9	1449.2	1445.4	1441.8	1444.3
12.5°	1448.5	1447.2	1446.0	1444.9	1443.7	1441.3	1437.9	1434.4	1430.9	1427.4	1429.3
15°	1420.0	1418.9	1417.7	1416.6	1415.4	1413.0	1409.3	1405.6	1401.9	1398.2	1400.4
17.5°	1386.9	1385.4	1384.0	1382.5	1381.0	1378.4	1374.7	1371.0	1367.3	1363.6	1365.2
20°	1362.3	1360.6	1358.9	1357.1	1355.5	1352.7	1349.1	1345.4	1341.7	1338.0	1339.1
22.5°	1334.6	1332.9	1331.2	1329.5	1327.8	1325.1	1321.4	1317.7	1314.0	1310.3	1311.2
25°	1289.2	1287.5	1285.8	1284.1	1282.5	1279.7	1276.0	1272.4	1268.6	1264.9	1265.2
27.5°	1240.8	1239.2	1237.5	1235.8	1234.2	1231.4	1227.4	1223.4	1219.4	1215.4	1215.7
30°	1206.0	1204.5	1203.1	1201.7	1200.3	1197.6	1193.6	1189.6	1185.6	1181.6	1181.6
32.5°	1171.1	1169.2	1167.3	1165.5	1163.6	1161.1	1158.1	1155.0	1151.9	1148.8	1147.2
35°	1115.0	1113.3	1111.6	1109.9	1108.2	1105.5	1101.7	1098.0	1094.3	1090.6	1088.9
37.5°	1057.5	1055.4	1053.2	1051.1	1048.9	1045.9	1042.2	1038.4	1034.7	1030.9	1028.8
40°	1017.6	1015.9	1014.2	1012.4	1010.7	1007.9	1003.9	999.9	995.9	992.0	989.7
42.5°	977.5	975.7	973.7	971.8	969.8	966.9	962.9	958.9	954.9	951.0	948.7
45°	913.8	912.6	911.5	910.4	909.2	906.8	903.1	899.4	895.7	891.9	888.6
47.5°	850.4	848.8	847.2	845.5	843.8	841.3	837.8	834.3	830.9	827.4	824.0
50°	807.4	806.0	804.5	803.2	801.7	799.2	795.4	791.7	788.0	784.3	781.2
52.5°	762.3	761.3	760.3	759.4	758.4	755.9	752.0	748.1	744.2	740.2	737.5
55°	693.3	693.1	692.8	692.5	692.2	690.2	686.5	682.8	679.1	675.4	672.3
57.5°	627.7	626.7	625.7	624.8	623.9	621.9	618.9	616.0	613.0	610.0	607.2
60°	580.6	580.2	580.0	579.7	579.4	577.6	574.1	570.7	567.3	563.9	561.3
62.5°	538.5	537.8	537.0	536.3	535.6	533.5	530.0	526.6	523.3	519.8	517.2
65°	472.9	471.5	470.0	468.6	467.2	465.0	462.2	459.3	456.5	453.7	451.4
67.5°	403.4	402.2	401.0	399.7	398.4	396.7	394.5	392.4	390.2	388.1	386.0
70°	361.4	359.7	358.0	356.3	354.6	352.9	351.1	349.4	347.7	346.0	344.1
72.5°	317.3	316.1	314.8	313.6	312.3	310.7	308.8	306.8	304.9	303.0	301.2
75°	249.9	248.7	247.6	246.5	245.3	244.3	243.5	242.6	241.8	240.9	239.5
77.5°	190.2	189.6	188.9	188.3	187.7	186.9	185.8	184.8	183.8	182.8	181.8
80°	151.2	150.3	149.5	148.6	147.8	147.1	146.5	145.9	145.4	144.8	144.6
82.5°	113.3	113.1	112.9	112.8	112.6	112.4	112.3	112.3	112.1	112.0	111.5
85°	66.6	66.0	65.5	64.9	64.3	64.1	64.1	64.1	64.1	64.1	63.5
87.5°	26.7	26.3	25.9	25.5	25.1	24.9	25.1	25.2	25.4	25.4	25.4
90°	0.6	2.0	3.3	4.6	6.0	7.5	9.3	11.0	12.8	14.5	15.1
92.5°	14.7	15.6	16.5	17.4	18.3	19.2	20.2	21.3	22.3	23.2	23.6
95°	35.7	36.6	37.6	38.6	39.5	40.4	41.6	42.6	43.7	44.8	45.3
97.5°	63.4	64.1	64.8	65.6	66.2	66.9	67.8	68.5	69.3	70.1	70.7
100°	82.3	83.1	83.9	84.7	85.5	86.3	86.9	87.6	88.3	88.9	89.4
102.5°	104.1	104.6	105.1	105.5	106.0	106.7	107.6	108.5	109.3	110.2	110.6
105°	136.2	136.4	136.7	137.0	137.2	137.9	139.2	140.4	141.6	142.8	142.8
107.5°	173.4	173.6	173.7	173.9	174.1	174.4	174.9	175.4	175.9	176.3	176.8
110°	196.7	197.0	197.2	197.5	197.7	198.0	198.3	198.5	198.9	199.1	199.7



TEST NUMBER: P332221-930

CATALOG NUMBER: S123DIW-S1165D755U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	220.9	221.0	221.2	221.4	221.5	221.6	221.7	221.8	221.8	221.8	222.5
115°	257.2	257.6	258.0	258.4	258.8	258.9	258.6	258.4	258.0	257.8	258.0
117.5°	293.8	294.0	294.2	294.6	294.8	294.8	294.4	294.1	293.8	293.3	293.3
120°	316.5	317.3	318.1	318.9	319.8	319.8	319.1	318.5	317.8	317.1	317.0
122.5°	340.2	340.8	341.4	342.0	342.6	342.7	342.3	342.0	341.7	341.3	341.0
125°	376.4	376.8	377.2	377.6	378.1	378.1	377.8	377.6	377.2	377.0	376.5
127.5°	409.8	410.7	411.6	412.4	413.3	413.5	413.3	412.9	412.6	412.4	411.6
130°	432.1	433.2	434.2	435.3	436.3	436.8	436.3	435.9	435.5	435.1	434.6
132.5°	454.4	455.4	456.5	457.5	458.7	459.0	458.8	458.4	458.1	457.9	457.2
135°	488.4	489.2	490.0	490.8	491.5	492.0	491.8	491.6	491.5	491.4	490.8
137.5°	519.8	520.5	521.1	521.9	522.5	523.0	523.3	523.7	524.1	524.4	523.8
140°	541.6	542.3	543.0	543.6	544.3	544.7	544.9	544.9	545.1	545.3	545.1
142.5°	561.5	562.1	562.8	563.5	564.1	564.6	564.8	565.1	565.3	565.6	565.4
145°	592.5	592.7	593.0	593.2	593.5	593.9	594.3	594.7	595.1	595.5	595.3
147.5°	619.5	620.0	620.5	621.0	621.5	621.9	622.3	622.6	623.1	623.5	623.5
150°	638.5	638.7	639.0	639.3	639.5	639.8	640.0	640.3	640.6	640.8	640.8
152.5°	654.0	654.3	654.7	655.1	655.4	655.7	655.8	656.0	656.2	656.3	656.6
155°	678.4	678.4	678.4	678.4	678.4	678.4	678.6	678.7	678.8	679.0	679.6
157.5°	699.2	699.0	698.9	698.7	698.5	698.5	698.6	698.7	698.9	699.0	699.5
160°	712.2	712.0	711.8	711.4	711.2	711.0	711.0	711.0	711.0	711.0	711.8
162.5°	723.9	723.5	723.1	722.8	722.4	722.3	722.4	722.4	722.6	722.7	723.3
165°	738.9	738.5	738.1	737.7	737.3	737.0	737.0	737.0	737.0	737.0	737.8
167.5°	750.9	750.3	749.8	749.3	748.7	748.5	748.6	748.7	748.9	748.9	749.7
170°	757.7	757.1	756.6	756.0	755.5	755.2	755.2	755.2	755.2	755.2	756.2
172.5°	763.0	762.5	761.9	761.3	760.8	760.5	760.5	760.5	760.5	760.5	761.4
175°	768.5	768.0	767.4	767.0	766.4	766.1	766.1	766.1	766.1	766.1	767.0
177.5°	770.9	770.4	770.0	769.6	769.2	768.9	768.9	768.9	768.9	768.9	769.6
180°	770.4	770.4	770.4	770.4	770.4	770.4	770.4	770.4	770.4	770.4	770.4



TEST NUMBER: P332221-930

CATALOG NUMBER: S123DIW-S1165D755U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4
2.5°	1484.7	1487.0	1489.3	1490.4	1490.1	1489.9	1489.6	1489.5
5°	1476.9	1479.8	1482.6	1483.8	1483.2	1482.6	1482.1	1481.5
7.5°	1461.3	1463.8	1466.4	1467.5	1467.1	1466.8	1466.5	1466.2
10°	1446.9	1449.4	1452.0	1453.0	1452.5	1451.9	1451.3	1450.7
12.5°	1431.2	1433.1	1434.9	1435.7	1435.3	1435.0	1434.7	1434.4
15°	1402.7	1405.0	1407.3	1407.6	1405.9	1404.2	1402.5	1400.8
17.5°	1366.8	1368.4	1369.9	1370.4	1369.9	1369.2	1368.6	1368.0
20°	1340.3	1341.4	1342.6	1342.6	1341.8	1340.9	1340.1	1339.2
22.5°	1312.1	1313.0	1313.9	1313.9	1312.8	1311.7	1310.6	1309.5
25°	1265.5	1265.8	1266.1	1265.8	1264.9	1264.0	1263.2	1262.3
27.5°	1215.9	1216.1	1216.3	1215.9	1214.9	1213.7	1212.7	1211.6
30°	1181.6	1181.6	1181.6	1180.6	1178.6	1176.6	1174.6	1172.6
32.5°	1145.6	1144.0	1142.4	1141.1	1140.0	1138.9	1137.8	1136.8
35°	1087.2	1085.5	1083.8	1082.2	1080.8	1079.4	1077.9	1076.5
37.5°	1026.8	1024.7	1022.7	1021.2	1020.3	1019.4	1018.5	1017.6
40°	987.4	985.1	982.8	981.1	980.0	978.8	977.7	976.6
42.5°	946.4	944.1	941.8	940.1	939.0	937.8	936.7	935.6
45°	885.2	881.7	878.3	875.9	874.5	873.0	871.6	870.2
47.5°	820.7	817.3	813.9	811.6	810.4	809.1	807.9	806.7
50°	778.0	774.9	771.8	769.4	767.7	766.0	764.3	762.5
52.5°	734.9	732.2	729.5	727.3	725.6	723.9	722.2	720.5
55°	669.1	666.0	662.8	660.6	659.2	657.7	656.3	654.8
57.5°	604.5	601.7	598.8	596.6	595.0	593.4	591.7	590.0
60°	558.8	556.2	553.7	551.6	550.2	548.8	547.4	545.9
62.5°	514.7	512.1	509.6	507.8	506.8	505.8	504.9	503.9
65°	449.1	446.9	444.6	443.0	442.1	441.3	440.4	439.6
67.5°	384.1	382.0	380.1	378.5	377.3	376.1	374.9	373.7
70°	342.0	340.1	338.0	336.3	334.9	333.5	332.1	330.7
72.5°	299.5	297.7	295.9	294.6	293.9	293.2	292.4	291.7
75°	238.1	236.7	235.2	234.1	233.3	232.4	231.5	230.6
77.5°	180.8	179.9	178.9	178.4	178.4	178.4	178.4	178.4
80°	144.2	144.0	143.7	143.6	143.6	143.6	143.6	143.6
82.5°	111.0	110.5	110.0	109.6	109.3	109.2	108.9	108.7
85°	62.9	62.4	61.8	61.6	61.6	61.6	61.6	61.6
87.5°	25.2	25.1	24.9	24.9	25.0	25.0	25.1	25.2
90°	15.6	16.1	16.7	17.0	17.4	17.6	17.9	18.2
92.5°	24.1	24.5	24.9	25.1	24.9	24.8	24.6	24.5
95°	45.8	46.4	47.0	47.2	47.2	47.2	47.2	47.2
97.5°	71.3	71.9	72.6	72.8	72.8	72.7	72.6	72.6
100°	89.8	90.2	90.6	90.9	91.2	91.5	91.7	92.0
102.5°	111.0	111.5	111.9	112.0	112.0	111.9	111.9	111.9
105°	142.8	142.8	142.8	142.9	143.2	143.5	143.7	144.1
107.5°	177.2	177.7	178.1	178.2	178.1	177.9	177.7	177.6
110°	200.2	200.7	201.2	201.4	201.1	200.8	200.6	200.3



TEST NUMBER: P332221-930

CATALOG NUMBER: S123DIW-S1165D755U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	223.1	223.8	224.5	224.7	224.7	224.6	224.5	224.5
115°	258.0	258.2	258.4	258.4	258.2	258.0	258.0	257.8
117.5°	293.3	293.3	293.3	293.1	292.7	292.3	292.0	291.6
120°	316.8	316.7	316.6	316.3	316.1	315.8	315.5	315.3
122.5°	340.6	340.2	339.9	339.6	339.2	338.8	338.4	338.0
125°	375.9	375.4	374.9	374.3	373.8	373.2	372.7	372.2
127.5°	410.8	410.1	409.4	408.6	408.1	407.4	406.8	406.2
130°	434.1	433.5	432.9	432.2	431.3	430.3	429.4	428.4
132.5°	456.6	455.9	455.3	454.6	453.9	453.1	452.4	451.7
135°	490.3	489.8	489.3	488.9	488.5	488.3	488.0	487.7
137.5°	523.3	522.7	522.2	521.6	521.1	520.6	520.1	519.6
140°	544.9	544.9	544.7	544.1	543.2	542.3	541.4	540.4
142.5°	565.3	565.2	565.0	564.6	563.9	563.1	562.4	561.7
145°	595.2	595.1	594.9	594.6	594.0	593.5	593.0	592.5
147.5°	623.5	623.5	623.5	623.1	622.2	621.4	620.6	619.8
150°	640.8	640.8	640.8	640.4	639.6	638.9	638.1	637.2
152.5°	656.8	657.0	657.2	657.0	656.2	655.6	654.8	654.2
155°	680.0	680.6	681.1	680.9	680.0	679.1	678.1	677.2
157.5°	700.1	700.7	701.2	701.1	700.3	699.6	698.9	698.1
160°	712.4	713.1	713.7	713.8	713.3	712.7	712.2	711.7
162.5°	724.0	724.7	725.4	725.3	724.4	723.6	722.7	721.8
165°	738.7	739.5	740.3	740.2	739.3	738.3	737.4	736.5
167.5°	750.6	751.5	752.3	752.3	751.5	750.6	749.7	748.9
170°	757.1	758.1	759.0	759.0	758.1	757.1	756.2	755.2
172.5°	762.2	763.0	763.9	763.9	762.9	762.0	761.0	760.1
175°	767.8	768.5	769.3	769.3	768.3	767.4	766.5	765.5
177.5°	770.2	770.9	771.5	771.4	770.7	769.9	769.2	768.4
180°	770.4	770.4	770.4	770.4	770.4	770.4	770.4	770.4

(END OF REPORT)