

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332103-930

Luminaire Tested: **S123DIW-S340D1030U930-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332103-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S340D1030U930-4F0-1E-UDD-A1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1030 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4099.6 lumens
Efficiency: N/A
Efficacy: 107.9 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 38
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332103-930

CATALOG NUMBER: S123DIW-S340D1030U930-4F0-1E-UDD-A1

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° ··· 90°-270° - · 135°-315°



TEST NUMBER: P332103-930

CATALOG NUMBER: S123DIW-S340D1030U930-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	72	72	72	53	53	53	37	37	37	29
1	93	89	85	82	83	80	77	74	63	61	59	47	46	45	33	32	31	25
2	85	78	72	67	76	70	65	61	55	52	49	42	39	37	29	28	27	21
3	78	69	62	56	69	62	56	51	49	45	41	37	34	32	26	24	23	18
4	71	61	53	47	63	55	48	43	43	39	35	33	30	27	23	21	20	15
5	65	54	46	40	58	49	42	37	39	34	30	29	26	24	21	19	17	13
6	60	48	40	35	53	44	37	32	35	30	26	27	23	21	19	17	15	12
7	55	43	36	30	49	39	33	28	31	27	23	24	21	18	17	15	13	11
8	51	39	32	27	46	36	29	25	29	24	20	22	19	16	16	14	12	9
9	47	36	29	24	43	32	26	22	26	21	18	20	17	14	15	12	11	8
10	44	33	26	21	40	30	24	19	24	19	16	19	15	13	13	11	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4219	4219	4219	4219
5°	5032	4238	3756	4238
10°	6299	4217	3393	4217
15°	7725	4182	3158	4182
20°	9203	4129	3007	4129
25°	9772	4065	2973	4065
30°	8376	4018	2988	4018
35°	5825	3951	3020	3951
40°	4388	3873	3011	3873
45°	3643	3755	2973	3755
50°	3264	3518	2946	3518
55°	3051	3262	2909	3262
60°	2863	2992	2878	2992
65°	2690	2728	2786	2728
70°	2521	2426	2653	2426
75°	2258	2125	2433	2125
80°	1977	1742	2095	1742
85°	1556	1272	1408	1272



TEST NUMBER: P332103-930

CATALOG NUMBER: S123DIW-S340D1030U930-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	38.6	0.9
10°-20°	123.8	3.0
20°-30°	207.8	5.1
30°-40°	235.3	5.7
40°-50°	211.0	5.1
50°-60°	170.3	4.2
60°-70°	118.7	2.9
70°-80°	62.4	1.5
80°-90°	18.4	0.4
90°-100°	68.5	1.7
100°-110°	205.0	5.0
110°-120°	348.7	8.5
120°-130°	458.7	11.2
130°-140°	515.5	12.6
140°-150°	506.8	12.4
150°-160°	426.6	10.4
160°-170°	284.0	6.9
170°-180°	99.4	2.4
0°-30°	370.3	9.0
0°-40°	605.6	14.8
0°-60°	986.9	24.1
0°-90°	1186.3	28.9
90°-120°	622.2	15.2
90°-150°	2103.2	51.3
90°-180°	2913.0	71.1
0°-180°	4099.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	392	392	392	392	392	
5°	466	392	348	392	466	48
15°	693	375	283	375	693	200
25°	823	342	250	342	823	361
35°	443	301	230	301	443	288
45°	239	247	195	247	239	189
55°	163	174	155	174	163	146
65°	106	107	109	107	106	105
75°	54	51	58	51	54	58
85°	13	10	11	10	13	16
90°	25	1	25	1	25	13
95°	64	49	64	49	64	66
105°	197	186	197	186	197	209
115°	352	351	352	351	352	348
125°	508	514	508	514	508	454
135°	666	667	666	667	666	512
145°	809	809	809	809	809	505
155°	924	926	924	926	924	426
165°	1005	1008	1005	1008	1005	284
175°	1045	1049	1045	1049	1045	99
180°	1052	1052	1052	1052	1052	



TEST NUMBER: P332103-930

CATALOG NUMBER: S123DIW-S340D1030U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0
2.5°	416.0	415.7	415.0	415.6	414.3	412.7	412.5	411.0	406.6	406.3	405.1
5°	465.7	464.2	464.0	463.8	461.1	457.5	450.7	450.1	441.0	436.5	431.0
7.5°	530.1	530.8	528.1	525.7	517.6	512.2	504.8	495.5	484.3	472.9	465.4
10°	576.3	582.5	574.8	569.4	564.5	555.2	544.4	530.8	517.4	501.7	489.7
12.5°	625.8	628.8	627.3	622.3	614.7	600.5	581.3	566.4	554.0	527.7	517.1
15°	693.2	704.8	697.4	680.4	680.7	667.2	642.2	614.7	600.0	577.0	545.7
17.5°	765.2	766.5	763.4	749.2	739.7	721.1	698.0	671.6	642.0	614.2	580.9
20°	803.4	802.3	795.7	788.2	771.9	757.5	732.2	702.8	664.8	637.4	601.1
22.5°	824.7	822.8	819.6	813.4	799.9	784.4	761.7	729.5	693.3	655.7	613.8
25°	822.8	825.2	825.7	823.9	819.2	809.9	792.1	766.4	730.3	681.8	638.2
27.5°	748.4	751.9	762.0	771.0	781.1	791.3	789.9	777.2	750.5	708.7	655.3
30°	673.9	666.3	685.1	708.8	725.0	753.5	769.4	770.4	755.4	719.5	667.4
32.5°	570.5	578.9	587.3	616.4	651.8	683.7	715.5	741.0	744.0	720.1	674.6
35°	443.3	453.8	469.0	484.1	522.1	554.8	610.7	659.3	698.0	703.1	675.2
37.5°	357.3	362.4	372.0	387.3	412.1	450.9	494.0	555.5	611.6	653.4	655.2
40°	312.3	313.8	324.6	336.1	356.3	388.2	427.1	481.5	548.7	607.1	631.4
42.5°	278.5	281.8	286.5	297.6	313.6	337.6	373.8	418.7	480.4	547.5	595.0
45°	239.3	243.1	246.0	253.4	264.8	281.0	306.1	347.2	394.1	463.4	527.4
47.5°	213.4	213.7	215.8	221.4	229.2	241.3	259.2	285.5	328.6	384.8	450.5
50°	194.9	197.9	198.7	203.0	209.1	218.0	232.8	255.3	290.6	340.0	400.4
52.5°	181.8	182.7	184.8	188.0	193.3	200.2	213.1	230.6	258.4	300.5	356.0
55°	162.6	162.6	164.7	167.1	170.2	176.4	185.0	197.9	219.0	251.7	297.7
57.5°	144.8	145.8	147.2	148.0	150.6	154.7	161.8	171.7	187.4	212.5	249.1
60°	133.0	134.7	134.4	136.0	138.3	141.5	147.6	155.6	169.6	189.7	220.5
62.5°	122.6	122.5	122.5	124.3	126.5	129.6	133.6	140.5	152.5	170.3	196.5
65°	105.6	105.3	106.6	107.7	108.4	110.7	113.7	119.8	127.8	141.1	161.4
67.5°	90.5	89.4	90.1	90.5	91.8	93.6	96.4	100.2	106.5	117.2	132.5
70°	80.1	79.2	79.0	79.4	80.6	81.9	84.0	87.6	93.4	102.0	113.2
72.5°	69.5	68.9	68.8	69.7	70.2	71.1	72.6	75.8	80.6	87.0	97.4
75°	54.3	54.3	54.3	54.5	55.1	55.8	57.0	58.7	62.3	66.9	73.9
77.5°	40.7	40.7	40.4	40.4	41.3	41.6	41.8	43.5	45.5	48.5	53.6
80°	31.9	31.0	31.3	31.9	32.3	32.4	33.0	33.4	35.1	36.9	40.4
82.5°	23.7	22.9	23.0	23.9	24.0	24.1	24.7	25.2	25.8	27.4	29.4
85°	12.6	12.6	12.7	12.7	12.9	12.7	13.3	13.5	13.5	14.4	15.6
87.5°	9.5	9.1	9.2	9.3	9.0	9.1	9.1	9.1	9.1	9.1	8.8
90°	24.8	24.4	24.1	23.6	23.3	22.7	22.0	21.3	20.5	19.8	17.4
92.5°	33.3	33.6	33.8	34.0	34.2	34.1	33.5	32.9	32.3	31.7	30.3
95°	64.4	64.4	64.4	64.4	64.4	64.1	63.3	62.6	61.9	61.1	59.7
97.5°	99.1	99.2	99.3	99.3	99.4	99.1	98.2	97.3	96.5	95.6	94.6
100°	125.6	125.1	124.8	124.4	124.1	123.6	123.1	122.5	122.0	121.4	120.5
102.5°	152.6	152.7	152.8	152.9	153.0	152.7	152.1	151.6	151.1	150.5	149.3
105°	196.6	196.2	195.8	195.5	195.1	194.9	194.9	194.9	194.9	194.9	193.3
107.5°	242.3	242.6	242.8	243.0	243.2	243.0	242.5	241.9	241.2	240.7	240.0
110°	273.4	273.8	274.1	274.5	274.8	274.7	273.9	273.2	272.5	271.7	271.4



TEST NUMBER: P332103-930

CATALOG NUMBER: S123DIW-S340D1030U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	306.5	306.6	306.6	306.6	306.7	306.3	305.4	304.6	303.7	302.8	302.7
115°	351.9	352.0	352.2	352.5	352.6	352.6	352.5	352.2	352.0	351.9	352.2
117.5°	397.9	398.4	399.0	399.5	400.0	400.3	400.3	400.4	400.4	400.5	400.9
120°	430.3	430.7	431.0	431.5	431.8	432.1	432.3	432.4	432.6	432.8	433.7
122.5°	461.4	461.9	462.4	462.9	463.4	464.0	464.4	464.9	465.4	465.9	466.4
125°	508.0	508.7	509.5	510.2	510.9	511.7	512.4	513.1	513.9	514.6	514.9
127.5°	554.4	555.2	556.1	556.9	557.7	558.7	559.8	560.8	561.8	562.8	563.2
130°	584.8	586.1	587.3	588.6	590.0	590.9	591.7	592.4	593.1	593.9	594.4
132.5°	616.5	617.5	618.5	619.5	620.5	621.4	622.3	623.2	624.0	624.9	625.3
135°	665.8	666.1	666.5	666.8	667.2	667.7	668.5	669.2	669.9	670.7	670.9
137.5°	709.2	709.9	710.6	711.3	712.0	712.7	713.5	714.3	715.0	715.8	715.3
140°	737.6	738.9	740.2	741.4	742.7	743.5	743.6	743.9	744.0	744.2	744.0
142.5°	766.7	767.7	768.7	769.6	770.6	771.3	771.4	771.6	771.8	772.0	771.7
145°	808.6	809.3	810.1	810.8	811.5	812.0	812.2	812.4	812.6	812.8	812.2
147.5°	846.0	847.1	848.2	849.3	850.4	850.9	850.9	850.9	850.9	850.9	850.4
150°	869.8	870.9	872.0	873.1	874.2	874.7	874.7	874.7	874.7	874.7	874.3
152.5°	892.9	893.8	894.8	895.8	896.7	897.1	896.7	896.4	896.2	895.9	895.7
155°	924.3	925.6	926.8	928.1	929.4	929.7	929.0	928.2	927.5	926.8	926.6
157.5°	952.8	953.9	955.0	955.9	957.0	957.1	956.3	955.5	954.8	954.0	953.9
160°	971.3	972.1	972.8	973.5	974.3	974.2	973.3	972.4	971.4	970.5	970.5
162.5°	985.2	986.4	987.6	988.8	989.9	990.1	989.1	988.2	987.3	986.4	986.3
165°	1005.3	1006.5	1007.8	1009.1	1010.4	1010.5	1009.3	1008.3	1007.1	1006.1	1006.1
167.5°	1022.2	1023.4	1024.5	1025.6	1026.8	1026.8	1025.6	1024.5	1023.4	1022.2	1022.1
170°	1030.9	1032.1	1033.4	1034.7	1036.0	1036.0	1034.7	1033.4	1032.1	1030.9	1030.9
172.5°	1037.5	1038.7	1040.0	1041.3	1042.6	1042.7	1041.5	1040.4	1039.3	1038.1	1038.1
175°	1044.9	1046.2	1047.4	1048.7	1050.0	1050.1	1049.0	1047.9	1046.8	1045.7	1045.7
177.5°	1048.9	1049.9	1050.9	1051.9	1053.0	1053.0	1052.1	1051.2	1050.4	1049.5	1049.5
180°	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5



TEST NUMBER: P332103-930

CATALOG NUMBER: S123DIW-S340D1030U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0
2.5°	404.1	403.0	401.8	399.7	397.8	395.3	394.4	393.5	390.8	388.4	386.5
5°	428.8	424.3	417.7	411.6	406.7	400.0	396.2	392.2	386.5	381.4	377.2
7.5°	454.7	445.7	435.4	424.3	413.8	403.8	395.7	388.5	380.5	373.0	367.0
10°	475.2	462.3	447.8	432.3	419.0	406.1	395.3	385.8	375.5	366.6	359.1
12.5°	498.6	479.5	459.6	440.7	424.9	407.0	393.9	381.8	370.1	359.5	351.1
15°	526.3	502.0	478.4	452.4	428.5	406.1	390.5	375.3	361.8	350.8	340.1
17.5°	551.5	524.0	492.9	461.3	432.4	405.9	384.1	366.9	350.0	336.6	326.0
20°	565.8	534.5	499.4	466.5	434.6	405.0	381.0	360.5	342.3	328.0	316.1
22.5°	578.1	541.4	505.1	469.9	434.4	402.5	375.4	354.2	334.5	320.6	307.9
25°	590.9	547.0	510.5	469.4	429.7	396.6	366.2	342.3	322.5	306.1	293.1
27.5°	601.9	546.7	503.4	459.0	422.1	389.0	356.5	330.8	309.9	292.1	278.8
30°	609.1	547.4	495.9	452.1	414.8	380.7	349.1	323.3	301.3	283.2	270.7
32.5°	613.7	546.9	489.1	442.3	403.2	373.0	341.0	314.3	291.6	273.9	261.9
35°	616.4	543.6	477.3	422.2	384.7	355.1	328.4	300.7	277.0	260.4	246.7
37.5°	611.0	536.5	463.7	402.8	361.7	332.7	310.1	286.6	263.8	245.6	233.8
40°	602.7	532.0	453.0	389.1	345.8	318.0	298.8	275.6	253.2	235.9	224.9
42.5°	586.7	522.8	441.3	374.0	329.5	301.6	283.9	264.5	243.3	227.1	216.1
45°	547.8	502.6	423.7	351.2	305.2	276.4	260.8	246.7	227.6	211.8	202.3
47.5°	493.7	472.2	398.4	327.2	279.9	252.2	235.9	224.7	210.7	197.9	188.8
50°	456.2	447.3	381.2	310.7	263.1	235.9	220.3	210.1	200.0	187.3	179.0
52.5°	412.9	418.4	361.2	293.8	245.9	219.2	204.6	196.4	187.3	176.8	169.5
55°	352.0	371.9	326.5	265.1	220.3	194.9	181.0	173.8	168.4	160.7	154.4
57.5°	294.9	320.2	289.0	235.7	195.2	173.3	160.0	152.1	148.7	144.6	139.7
60°	261.0	286.0	262.3	216.0	178.4	157.4	145.7	139.0	135.6	132.7	128.6
62.5°	230.7	256.1	236.2	195.9	161.8	142.4	132.2	125.6	123.0	121.6	118.0
65°	189.1	211.0	197.7	164.7	138.1	121.0	111.7	107.1	104.7	104.1	101.8
67.5°	153.9	170.6	160.9	136.6	115.7	100.9	93.0	89.1	87.2	87.0	85.3
70°	130.9	146.4	139.0	117.0	99.0	87.4	80.6	77.1	76.0	75.8	74.8
72.5°	112.9	123.8	117.9	99.5	85.6	75.1	70.0	66.4	65.2	65.5	64.8
75°	83.6	91.7	88.3	75.6	64.4	57.6	53.4	51.1	50.0	50.5	49.7
77.5°	60.2	65.3	62.2	53.4	46.5	41.6	38.5	37.1	36.0	36.0	35.7
80°	45.4	48.4	46.7	41.4	35.7	31.6	29.0	28.1	27.6	27.3	27.1
82.5°	32.4	34.9	32.9	29.3	25.4	22.8	21.4	20.2	19.8	19.9	19.7
85°	16.3	17.3	16.6	14.3	12.7	11.6	10.8	10.3	9.9	10.0	9.7
87.5°	8.6	8.3	7.3	6.4	5.7	4.8	4.5	3.8	3.9	4.2	4.5
90°	15.1	12.6	10.3	8.2	6.4	4.5	2.7	0.8	2.7	4.5	6.4
92.5°	29.0	27.6	26.3	24.9	23.7	22.5	21.2	20.0	21.2	22.5	23.7
95°	58.2	56.7	55.3	53.9	52.6	51.3	50.0	48.8	50.0	51.3	52.6
97.5°	93.5	92.5	91.4	90.4	89.4	88.5	87.5	86.6	87.5	88.5	89.4
100°	119.6	118.7	117.7	116.8	115.6	114.5	113.4	112.3	113.4	114.5	115.6
102.5°	148.1	146.8	145.6	144.7	144.1	143.4	142.8	142.1	142.8	143.4	144.1
105°	191.6	190.0	188.3	187.4	186.9	186.6	186.2	185.9	186.2	186.6	186.9
107.5°	239.4	238.7	238.1	237.6	237.4	237.2	236.9	236.8	236.9	237.2	237.4
110°	271.0	270.7	270.3	269.9	269.5	269.2	268.8	268.5	268.8	269.2	269.5



TEST NUMBER: P332103-930

CATALOG NUMBER: S123DIW-S340D1030U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	302.6	302.6	302.5	302.4	302.1	301.9	301.7	301.5	301.7	301.9	302.1
115°	352.6	352.9	353.4	353.3	352.7	352.1	351.6	351.1	351.6	352.1	352.7
117.5°	401.4	401.9	402.4	402.4	402.0	401.7	401.3	401.0	401.3	401.7	402.0
120°	434.6	435.5	436.5	436.4	435.3	434.2	433.1	432.0	433.1	434.2	435.3
122.5°	466.8	467.3	467.7	467.6	466.8	466.0	465.2	464.4	465.2	466.0	466.8
125°	515.4	515.7	516.1	516.0	515.4	514.9	514.3	513.8	514.3	514.9	515.4
127.5°	563.6	564.0	564.4	564.0	562.9	561.7	560.5	559.4	560.5	561.7	562.9
130°	595.0	595.6	596.1	595.7	594.2	592.7	591.3	589.8	591.3	592.7	594.2
132.5°	625.7	626.1	626.6	626.1	624.6	623.1	621.6	620.1	621.6	623.1	624.6
135°	671.1	671.2	671.4	671.0	669.8	668.8	667.6	666.6	667.6	668.8	669.8
137.5°	714.9	714.4	713.9	713.2	712.2	711.3	710.5	709.6	710.5	711.3	712.2
140°	743.9	743.6	743.5	742.9	742.0	741.1	740.2	739.2	740.2	741.1	742.0
142.5°	771.3	770.9	770.6	770.1	769.1	768.2	767.3	766.4	767.3	768.2	769.1
145°	811.7	811.1	810.6	810.1	809.8	809.3	809.0	808.6	809.0	809.3	809.8
147.5°	849.9	849.4	848.9	848.3	847.7	846.9	846.3	845.6	846.3	846.9	847.7
150°	874.0	873.6	873.3	872.9	872.5	872.1	871.8	871.4	871.8	872.1	872.5
152.5°	895.4	895.2	895.0	894.6	894.1	893.6	893.1	892.6	893.1	893.6	894.1
155°	926.4	926.2	926.0	925.9	925.9	925.9	925.9	925.9	925.9	925.9	925.9
157.5°	953.7	953.6	953.4	953.5	953.7	953.9	954.1	954.4	954.1	953.9	953.7
160°	970.5	970.5	970.5	970.7	971.1	971.4	971.8	972.2	971.8	971.4	971.1
162.5°	986.1	985.9	985.8	986.0	986.5	987.0	987.6	988.1	987.6	987.0	986.5
165°	1006.1	1006.1	1006.1	1006.3	1006.9	1007.5	1008.0	1008.5	1008.0	1007.5	1006.9
167.5°	1022.0	1021.8	1021.7	1022.0	1022.7	1023.4	1024.2	1024.9	1024.2	1023.4	1022.7
170°	1030.9	1030.9	1030.9	1031.2	1031.9	1032.7	1033.4	1034.1	1033.4	1032.7	1031.9
172.5°	1038.1	1038.1	1038.1	1038.4	1039.2	1039.9	1040.6	1041.4	1040.6	1039.9	1039.2
175°	1045.7	1045.7	1045.7	1046.1	1046.8	1047.6	1048.3	1049.0	1048.3	1047.6	1046.8
177.5°	1049.5	1049.5	1049.5	1049.8	1050.4	1051.0	1051.6	1052.1	1051.6	1051.0	1050.4
180°	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5



TEST NUMBER: P332103-930

CATALOG NUMBER: S123DIW-S340D1030U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0
2.5°	385.5	384.4	382.9	380.7	378.8	375.9	375.9	376.3	376.3	376.3	375.9
5°	373.8	371.0	367.5	363.5	359.4	355.1	354.4	352.9	351.8	351.0	350.1
7.5°	361.4	356.4	351.4	345.8	340.7	336.6	333.6	331.2	329.6	327.9	326.7
10°	353.1	346.8	341.0	335.1	328.6	323.4	320.2	318.0	316.3	314.7	314.0
12.5°	343.2	336.1	329.5	323.9	316.9	311.6	308.5	307.4	305.5	302.2	300.6
15°	328.8	322.1	314.4	305.8	302.4	296.0	292.3	290.6	289.4	287.0	286.3
17.5°	316.4	307.8	299.0	292.6	286.3	281.0	279.0	276.9	275.4	273.4	272.7
20°	306.6	298.8	290.8	284.0	277.3	271.6	269.9	268.4	266.8	266.0	265.1
22.5°	296.5	288.8	282.1	275.7	268.6	264.9	263.1	261.4	260.3	259.7	258.9
25°	282.4	275.6	268.2	262.5	256.8	254.3	253.2	252.3	251.4	250.5	250.3
27.5°	269.9	262.4	256.4	251.0	247.0	244.9	243.8	243.4	243.5	243.9	244.1
30°	260.4	253.6	248.7	244.1	240.3	238.4	238.1	238.1	239.0	239.1	239.5
32.5°	251.8	246.1	241.2	236.8	233.9	232.6	233.3	233.3	233.9	234.4	235.1
35°	239.1	234.2	230.4	226.6	224.1	224.7	225.1	225.4	226.4	227.6	228.3
37.5°	227.1	222.8	218.8	215.9	214.7	215.7	216.7	217.4	218.6	219.5	220.2
40°	218.4	215.2	211.4	208.7	209.1	209.7	210.4	211.4	212.4	213.0	213.7
42.5°	210.3	207.0	204.1	201.9	202.4	203.2	203.6	204.1	205.2	206.3	206.7
45°	198.1	195.4	192.8	191.4	191.8	192.2	192.6	193.1	194.1	194.9	195.1
47.5°	184.3	182.5	180.7	179.4	180.0	179.9	180.3	181.6	181.8	182.3	183.4
50°	175.5	173.8	171.7	171.3	171.3	171.3	171.5	173.0	173.0	173.8	174.6
52.5°	165.8	164.7	163.4	162.7	162.3	162.3	163.1	163.9	164.2	165.3	166.1
55°	151.4	150.3	149.1	148.5	148.1	148.5	150.0	150.4	151.4	152.0	152.5
57.5°	136.4	135.5	134.6	134.3	134.2	134.7	135.5	136.6	136.9	138.7	139.5
60°	126.5	125.1	124.4	124.4	124.0	125.7	125.4	127.3	127.7	128.8	130.1
62.5°	116.3	114.5	114.2	114.2	114.8	115.3	115.8	116.6	117.6	119.0	120.1
65°	99.9	99.0	100.3	100.1	99.7	100.9	100.9	101.8	103.0	104.3	106.4
67.5°	84.4	83.9	84.0	84.0	84.5	85.2	85.8	86.6	88.0	89.4	90.7
70°	73.9	74.4	73.5	74.3	74.8	75.0	75.4	76.6	78.0	79.0	80.6
72.5°	63.7	63.7	63.8	64.1	64.7	65.0	65.4	66.7	68.3	69.1	70.4
75°	49.0	48.8	49.4	49.4	50.3	50.7	51.1	51.7	53.2	54.3	55.3
77.5°	35.8	36.0	35.9	36.5	36.3	36.4	37.5	38.1	38.2	40.5	41.0
80°	27.0	27.3	27.6	27.7	27.9	27.6	28.9	29.4	29.4	30.7	31.7
82.5°	19.4	19.6	20.1	20.3	20.3	20.7	20.8	21.2	21.7	22.3	23.5
85°	9.7	10.3	10.4	10.3	10.4	10.0	10.6	10.8	11.0	11.0	11.0
87.5°	4.6	5.2	5.5	6.2	6.5	7.2	7.3	7.2	7.3	7.9	7.4
90°	8.2	10.3	12.6	15.1	17.4	19.8	20.5	21.3	22.0	22.7	23.3
92.5°	24.9	26.3	27.6	29.0	30.3	31.7	32.3	32.9	33.5	34.1	34.2
95°	53.9	55.3	56.7	58.2	59.7	61.1	61.9	62.6	63.3	64.1	64.4
97.5°	90.4	91.4	92.5	93.5	94.6	95.6	96.5	97.3	98.2	99.1	99.4
100°	116.8	117.7	118.7	119.6	120.5	121.4	122.0	122.5	123.1	123.6	124.1
102.5°	144.7	145.6	146.8	148.1	149.3	150.5	151.1	151.6	152.1	152.7	153.0
105°	187.4	188.3	190.0	191.6	193.3	194.9	194.9	194.9	194.9	194.9	195.1
107.5°	237.6	238.1	238.7	239.4	240.0	240.7	241.2	241.9	242.5	243.0	243.2
110°	269.9	270.3	270.7	271.0	271.4	271.7	272.5	273.2	273.9	274.7	274.8



TEST NUMBER: P332103-930

CATALOG NUMBER: S123DIW-S340D1030U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	302.4	302.5	302.6	302.6	302.7	302.8	303.7	304.6	305.4	306.3	306.7
115°	353.3	353.4	352.9	352.6	352.2	351.9	352.0	352.2	352.5	352.6	352.6
117.5°	402.4	402.4	401.9	401.4	400.9	400.5	400.4	400.4	400.3	400.3	400.0
120°	436.4	436.5	435.5	434.6	433.7	432.8	432.6	432.4	432.3	432.1	431.8
122.5°	467.6	467.7	467.3	466.8	466.4	465.9	465.4	464.9	464.4	464.0	463.4
125°	516.0	516.1	515.7	515.4	514.9	514.6	513.9	513.1	512.4	511.7	510.9
127.5°	564.0	564.4	564.0	563.6	563.2	562.8	561.8	560.8	559.8	558.7	557.7
130°	595.7	596.1	595.6	595.0	594.4	593.9	593.1	592.4	591.7	590.9	590.0
132.5°	626.1	626.6	626.1	625.7	625.3	624.9	624.0	623.2	622.3	621.4	620.5
135°	671.0	671.4	671.2	671.1	670.9	670.7	669.9	669.2	668.5	667.7	667.2
137.5°	713.2	713.9	714.4	714.9	715.3	715.8	715.0	714.3	713.5	712.7	712.0
140°	742.9	743.5	743.6	743.9	744.0	744.2	744.0	743.9	743.6	743.5	742.7
142.5°	770.1	770.6	770.9	771.3	771.7	772.0	771.8	771.6	771.4	771.3	770.6
145°	810.1	810.6	811.1	811.7	812.2	812.8	812.6	812.4	812.2	812.0	811.5
147.5°	848.3	848.9	849.4	849.9	850.4	850.9	850.9	850.9	850.9	850.9	850.4
150°	872.9	873.3	873.6	874.0	874.3	874.7	874.7	874.7	874.7	874.7	874.2
152.5°	894.6	895.0	895.2	895.4	895.7	895.9	896.2	896.4	896.7	897.1	896.7
155°	925.9	926.0	926.2	926.4	926.6	926.8	927.5	928.2	929.0	929.7	929.4
157.5°	953.5	953.4	953.6	953.7	953.9	954.0	954.8	955.5	956.3	957.1	957.0
160°	970.7	970.5	970.5	970.5	970.5	970.5	971.4	972.4	973.3	974.2	974.3
162.5°	986.0	985.8	985.9	986.1	986.3	986.4	987.3	988.2	989.1	990.1	989.9
165°	1006.3	1006.1	1006.1	1006.1	1006.1	1006.1	1007.1	1008.3	1009.3	1010.5	1010.4
167.5°	1022.0	1021.7	1021.8	1022.0	1022.1	1022.2	1023.4	1024.5	1025.6	1026.8	1026.8
170°	1031.2	1030.9	1030.9	1030.9	1030.9	1030.9	1032.1	1033.4	1034.7	1036.0	1036.0
172.5°	1038.4	1038.1	1038.1	1038.1	1038.1	1038.1	1039.3	1040.4	1041.5	1042.7	1042.6
175°	1046.1	1045.7	1045.7	1045.7	1045.7	1045.7	1046.8	1047.9	1049.0	1050.1	1050.0
177.5°	1049.8	1049.5	1049.5	1049.5	1049.5	1049.5	1050.4	1051.2	1052.1	1053.0	1053.0
180°	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5



TEST NUMBER: P332103-930

CATALOG NUMBER: S123DIW-S340D1030U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0
2.5°	374.9	374.7	375.8	375.0	375.8	374.7	374.9	375.9	376.3	376.3	376.3
5°	348.9	349.5	347.6	347.6	347.6	349.5	348.9	350.1	351.0	351.8	352.9
7.5°	325.8	325.0	325.1	324.0	325.1	325.0	325.8	326.7	327.9	329.6	331.2
10°	311.7	310.5	310.1	310.4	310.1	310.5	311.7	314.0	314.7	316.3	318.0
12.5°	299.9	299.8	297.3	297.3	297.3	299.8	299.9	300.6	302.2	305.5	307.4
15°	286.3	282.7	282.3	283.4	282.3	282.7	286.3	286.3	287.0	289.4	290.6
17.5°	272.5	270.5	270.7	270.1	270.7	270.5	272.5	272.7	273.4	275.4	276.9
20°	265.1	264.0	263.8	262.5	263.8	264.0	265.1	265.1	266.0	266.8	268.4
22.5°	258.4	258.1	258.2	256.7	258.2	258.1	258.4	258.9	259.7	260.3	261.4
25°	250.1	251.1	250.3	250.3	250.3	251.1	250.1	250.3	250.5	251.4	252.3
27.5°	244.5	244.5	244.1	244.1	244.1	244.5	244.5	244.1	243.9	243.5	243.4
30°	240.3	240.1	240.4	240.4	240.4	240.1	240.3	239.5	239.1	239.0	238.1
32.5°	236.0	236.3	236.4	236.5	236.4	236.3	236.0	235.1	234.4	233.9	233.3
35°	229.4	229.7	230.2	229.8	230.2	229.7	229.4	228.3	227.6	226.4	225.4
37.5°	220.5	221.4	221.3	221.5	221.3	221.4	220.5	220.2	219.5	218.6	217.4
40°	213.9	214.4	214.3	214.3	214.3	214.4	213.9	213.7	213.0	212.4	211.4
42.5°	207.0	207.4	206.9	206.7	206.9	207.4	207.0	206.7	206.3	205.2	204.1
45°	195.8	195.4	196.0	195.3	196.0	195.4	195.8	195.1	194.9	194.1	193.1
47.5°	183.3	183.7	183.8	184.4	183.8	183.7	183.3	183.4	182.3	181.8	181.6
50°	175.0	176.1	176.1	175.9	176.1	176.1	175.0	174.6	173.8	173.0	173.0
52.5°	166.7	167.2	168.0	168.0	168.0	167.2	166.7	166.1	165.3	164.2	163.9
55°	154.0	154.4	154.8	155.0	154.8	154.4	154.0	152.5	152.0	151.4	150.4
57.5°	140.9	140.7	141.6	141.9	141.6	140.7	140.9	139.5	138.7	136.9	136.6
60°	131.6	131.6	133.1	133.7	133.1	131.6	131.6	130.1	128.8	127.7	127.3
62.5°	121.7	122.4	123.8	123.1	123.8	122.4	121.7	120.1	119.0	117.6	116.6
65°	107.3	108.8	108.7	109.4	108.7	108.8	107.3	106.4	104.3	103.0	101.8
67.5°	92.2	93.2	94.6	94.7	94.6	93.2	92.2	90.7	89.4	88.0	86.6
70°	82.0	83.0	83.7	84.3	83.7	83.0	82.0	80.6	79.0	78.0	76.6
72.5°	72.2	72.6	74.5	73.7	74.5	72.6	72.2	70.4	69.1	68.3	66.7
75°	56.6	58.0	59.1	58.5	59.1	58.0	56.6	55.3	54.3	53.2	51.7
77.5°	41.8	43.2	43.7	43.2	43.7	43.2	41.8	41.0	40.5	38.2	38.1
80°	33.0	32.9	34.0	33.8	34.0	32.9	33.0	31.7	30.7	29.4	29.4
82.5°	24.2	24.1	24.5	24.7	24.5	24.1	24.2	23.5	22.3	21.7	21.2
85°	11.7	12.3	11.6	11.4	11.6	12.3	11.7	11.0	11.0	11.0	10.8
87.5°	7.5	7.6	7.5	7.4	7.5	7.6	7.5	7.4	7.9	7.3	7.2
90°	23.6	24.1	24.4	24.8	24.4	24.1	23.6	23.3	22.7	22.0	21.3
92.5°	34.0	33.8	33.6	33.3	33.6	33.8	34.0	34.2	34.1	33.5	32.9
95°	64.4	64.4	64.4	64.4	64.4	64.4	64.4	64.4	64.1	63.3	62.6
97.5°	99.3	99.3	99.2	99.1	99.2	99.3	99.3	99.4	99.1	98.2	97.3
100°	124.4	124.8	125.1	125.6	125.1	124.8	124.4	124.1	123.6	123.1	122.5
102.5°	152.9	152.8	152.7	152.6	152.7	152.8	152.9	153.0	152.7	152.1	151.6
105°	195.5	195.8	196.2	196.6	196.2	195.8	195.5	195.1	194.9	194.9	194.9
107.5°	243.0	242.8	242.6	242.3	242.6	242.8	243.0	243.2	243.0	242.5	241.9
110°	274.5	274.1	273.8	273.4	273.8	274.1	274.5	274.8	274.7	273.9	273.2



TEST NUMBER: P332103-930

CATALOG NUMBER: S123DIW-S340D1030U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	306.6	306.6	306.6	306.5	306.6	306.6	306.6	306.7	306.3	305.4	304.6
115°	352.5	352.2	352.0	351.9	352.0	352.2	352.5	352.6	352.6	352.5	352.2
117.5°	399.5	399.0	398.4	397.9	398.4	399.0	399.5	400.0	400.3	400.3	400.4
120°	431.5	431.0	430.7	430.3	430.7	431.0	431.5	431.8	432.1	432.3	432.4
122.5°	462.9	462.4	461.9	461.4	461.9	462.4	462.9	463.4	464.0	464.4	464.9
125°	510.2	509.5	508.7	508.0	508.7	509.5	510.2	510.9	511.7	512.4	513.1
127.5°	556.9	556.1	555.2	554.4	555.2	556.1	556.9	557.7	558.7	559.8	560.8
130°	588.6	587.3	586.1	584.8	586.1	587.3	588.6	590.0	590.9	591.7	592.4
132.5°	619.5	618.5	617.5	616.5	617.5	618.5	619.5	620.5	621.4	622.3	623.2
135°	666.8	666.5	666.1	665.8	666.1	666.5	666.8	667.2	667.7	668.5	669.2
137.5°	711.3	710.6	709.9	709.2	709.9	710.6	711.3	712.0	712.7	713.5	714.3
140°	741.4	740.2	738.9	737.6	738.9	740.2	741.4	742.7	743.5	743.6	743.9
142.5°	769.6	768.7	767.7	766.7	767.7	768.7	769.6	770.6	771.3	771.4	771.6
145°	810.8	810.1	809.3	808.6	809.3	810.1	810.8	811.5	812.0	812.2	812.4
147.5°	849.3	848.2	847.1	846.0	847.1	848.2	849.3	850.4	850.9	850.9	850.9
150°	873.1	872.0	870.9	869.8	870.9	872.0	873.1	874.2	874.7	874.7	874.7
152.5°	895.8	894.8	893.8	892.9	893.8	894.8	895.8	896.7	897.1	896.7	896.4
155°	928.1	926.8	925.6	924.3	925.6	926.8	928.1	929.4	929.7	929.0	928.2
157.5°	955.9	955.0	953.9	952.8	953.9	955.0	955.9	957.0	957.1	956.3	955.5
160°	973.5	972.8	972.1	971.3	972.1	972.8	973.5	974.3	974.2	973.3	972.4
162.5°	988.8	987.6	986.4	985.2	986.4	987.6	988.8	989.9	990.1	989.1	988.2
165°	1009.1	1007.8	1006.5	1005.3	1006.5	1007.8	1009.1	1010.4	1010.5	1009.3	1008.3
167.5°	1025.6	1024.5	1023.4	1022.2	1023.4	1024.5	1025.6	1026.8	1026.8	1025.6	1024.5
170°	1034.7	1033.4	1032.1	1030.9	1032.1	1033.4	1034.7	1036.0	1036.0	1034.7	1033.4
172.5°	1041.3	1040.0	1038.7	1037.5	1038.7	1040.0	1041.3	1042.6	1042.7	1041.5	1040.4
175°	1048.7	1047.4	1046.2	1044.9	1046.2	1047.4	1048.7	1050.0	1050.1	1049.0	1047.9
177.5°	1051.9	1050.9	1049.9	1048.9	1049.9	1050.9	1051.9	1053.0	1053.0	1052.1	1051.2
180°	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5



TEST NUMBER: P332103-930

CATALOG NUMBER: S123DIW-S340D1030U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0
2.5°	375.9	375.9	378.8	380.7	382.9	384.4	385.5	386.5	388.4	390.8	393.5
5°	354.4	355.1	359.4	363.5	367.5	371.0	373.8	377.2	381.4	386.5	392.2
7.5°	333.6	336.6	340.7	345.8	351.4	356.4	361.4	367.0	373.0	380.5	388.5
10°	320.2	323.4	328.6	335.1	341.0	346.8	353.1	359.1	366.6	375.5	385.8
12.5°	308.5	311.6	316.9	323.9	329.5	336.1	343.2	351.1	359.5	370.1	381.8
15°	292.3	296.0	302.4	305.8	314.4	322.1	328.8	340.1	350.8	361.8	375.3
17.5°	279.0	281.0	286.3	292.6	299.0	307.8	316.4	326.0	336.6	350.0	366.9
20°	269.9	271.6	277.3	284.0	290.8	298.8	306.6	316.1	328.0	342.3	360.5
22.5°	263.1	264.9	268.6	275.7	282.1	288.8	296.5	307.9	320.6	334.5	354.2
25°	253.2	254.3	256.8	262.5	268.2	275.6	282.4	293.1	306.1	322.5	342.3
27.5°	243.8	244.9	247.0	251.0	256.4	262.4	269.9	278.8	292.1	309.9	330.8
30°	238.1	238.4	240.3	244.1	248.7	253.6	260.4	270.7	283.2	301.3	323.3
32.5°	233.3	232.6	233.9	236.8	241.2	246.1	251.8	261.9	273.9	291.6	314.3
35°	225.1	224.7	224.1	226.6	230.4	234.2	239.1	246.7	260.4	277.0	300.7
37.5°	216.7	215.7	214.7	215.9	218.8	222.8	227.1	233.8	245.6	263.8	286.6
40°	210.4	209.7	209.1	208.7	211.4	215.2	218.4	224.9	235.9	253.2	275.6
42.5°	203.6	203.2	202.4	201.9	204.1	207.0	210.3	216.1	227.1	243.3	264.5
45°	192.6	192.2	191.8	191.4	192.8	195.4	198.1	202.3	211.8	227.6	246.7
47.5°	180.3	179.9	180.0	179.4	180.7	182.5	184.3	188.8	197.9	210.7	224.7
50°	171.5	171.3	171.3	171.3	171.7	173.8	175.5	179.0	187.3	200.0	210.1
52.5°	163.1	162.3	162.3	162.7	163.4	164.7	165.8	169.5	176.8	187.3	196.4
55°	150.0	148.5	148.1	148.5	149.1	150.3	151.4	154.4	160.7	168.4	173.8
57.5°	135.5	134.7	134.2	134.3	134.6	135.5	136.4	139.7	144.6	148.7	152.1
60°	125.4	125.7	124.0	124.4	124.4	125.1	126.5	128.6	132.7	135.6	139.0
62.5°	115.8	115.3	114.8	114.2	114.2	114.5	116.3	118.0	121.6	123.0	125.6
65°	100.9	100.9	99.7	100.1	100.3	99.0	99.9	101.8	104.1	104.7	107.1
67.5°	85.8	85.2	84.5	84.0	84.0	83.9	84.4	85.3	87.0	87.2	89.1
70°	75.4	75.0	74.8	74.3	73.5	74.4	73.9	74.8	75.8	76.0	77.1
72.5°	65.4	65.0	64.7	64.1	63.8	63.7	63.7	64.8	65.5	65.2	66.4
75°	51.1	50.7	50.3	49.4	49.4	48.8	49.0	49.7	50.5	50.0	51.1
77.5°	37.5	36.4	36.3	36.5	35.9	36.0	35.8	35.7	36.0	36.0	37.1
80°	28.9	27.6	27.9	27.7	27.6	27.3	27.0	27.1	27.3	27.6	28.1
82.5°	20.8	20.7	20.3	20.3	20.1	19.6	19.4	19.7	19.9	19.8	20.2
85°	10.6	10.0	10.4	10.3	10.4	10.3	9.7	9.7	10.0	9.9	10.3
87.5°	7.3	7.2	6.5	6.2	5.5	5.2	4.6	4.5	4.2	3.9	3.8
90°	20.5	19.8	17.4	15.1	12.6	10.3	8.2	6.4	4.5	2.7	0.8
92.5°	32.3	31.7	30.3	29.0	27.6	26.3	24.9	23.7	22.5	21.2	20.0
95°	61.9	61.1	59.7	58.2	56.7	55.3	53.9	52.6	51.3	50.0	48.8
97.5°	96.5	95.6	94.6	93.5	92.5	91.4	90.4	89.4	88.5	87.5	86.6
100°	122.0	121.4	120.5	119.6	118.7	117.7	116.8	115.6	114.5	113.4	112.3
102.5°	151.1	150.5	149.3	148.1	146.8	145.6	144.7	144.1	143.4	142.8	142.1
105°	194.9	194.9	193.3	191.6	190.0	188.3	187.4	186.9	186.6	186.2	185.9
107.5°	241.2	240.7	240.0	239.4	238.7	238.1	237.6	237.4	237.2	236.9	236.8
110°	272.5	271.7	271.4	271.0	270.7	270.3	269.9	269.5	269.2	268.8	268.5



TEST NUMBER: P332103-930

CATALOG NUMBER: S123DIW-S340D1030U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	303.7	302.8	302.7	302.6	302.6	302.5	302.4	302.1	301.9	301.7	301.5
115°	352.0	351.9	352.2	352.6	352.9	353.4	353.3	352.7	352.1	351.6	351.1
117.5°	400.4	400.5	400.9	401.4	401.9	402.4	402.4	402.0	401.7	401.3	401.0
120°	432.6	432.8	433.7	434.6	435.5	436.5	436.4	435.3	434.2	433.1	432.0
122.5°	465.4	465.9	466.4	466.8	467.3	467.7	467.6	466.8	466.0	465.2	464.4
125°	513.9	514.6	514.9	515.4	515.7	516.1	516.0	515.4	514.9	514.3	513.8
127.5°	561.8	562.8	563.2	563.6	564.0	564.4	564.0	562.9	561.7	560.5	559.4
130°	593.1	593.9	594.4	595.0	595.6	596.1	595.7	594.2	592.7	591.3	589.8
132.5°	624.0	624.9	625.3	625.7	626.1	626.6	626.1	624.6	623.1	621.6	620.1
135°	669.9	670.7	670.9	671.1	671.2	671.4	671.0	669.8	668.8	667.6	666.6
137.5°	715.0	715.8	715.3	714.9	714.4	713.9	713.2	712.2	711.3	710.5	709.6
140°	744.0	744.2	744.0	743.9	743.6	743.5	742.9	742.0	741.1	740.2	739.2
142.5°	771.8	772.0	771.7	771.3	770.9	770.6	770.1	769.1	768.2	767.3	766.4
145°	812.6	812.8	812.2	811.7	811.1	810.6	810.1	809.8	809.3	809.0	808.6
147.5°	850.9	850.9	850.4	849.9	849.4	848.9	848.3	847.7	846.9	846.3	845.6
150°	874.7	874.7	874.3	874.0	873.6	873.3	872.9	872.5	872.1	871.8	871.4
152.5°	896.2	895.9	895.7	895.4	895.2	895.0	894.6	894.1	893.6	893.1	892.6
155°	927.5	926.8	926.6	926.4	926.2	926.0	925.9	925.9	925.9	925.9	925.9
157.5°	954.8	954.0	953.9	953.7	953.6	953.4	953.5	953.7	953.9	954.1	954.4
160°	971.4	970.5	970.5	970.5	970.5	970.5	970.7	971.1	971.4	971.8	972.2
162.5°	987.3	986.4	986.3	986.1	985.9	985.8	986.0	986.5	987.0	987.6	988.1
165°	1007.1	1006.1	1006.1	1006.1	1006.1	1006.1	1006.3	1006.9	1007.5	1008.0	1008.5
167.5°	1023.4	1022.2	1022.1	1022.0	1021.8	1021.7	1022.0	1022.7	1023.4	1024.2	1024.9
170°	1032.1	1030.9	1030.9	1030.9	1030.9	1030.9	1031.2	1031.9	1032.7	1033.4	1034.1
172.5°	1039.3	1038.1	1038.1	1038.1	1038.1	1038.1	1038.4	1039.2	1039.9	1040.6	1041.4
175°	1046.8	1045.7	1045.7	1045.7	1045.7	1045.7	1046.1	1046.8	1047.6	1048.3	1049.0
177.5°	1050.4	1049.5	1049.5	1049.5	1049.5	1049.5	1049.8	1050.4	1051.0	1051.6	1052.1
180°	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5



TEST NUMBER: P332103-930

CATALOG NUMBER: S123DIW-S340D1030U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0
2.5°	394.4	395.3	397.8	399.7	401.8	403.0	404.1	405.1	406.3	406.6	411.0
5°	396.2	400.0	406.7	411.6	417.7	424.3	428.8	431.0	436.5	441.0	450.1
7.5°	395.7	403.8	413.8	424.3	435.4	445.7	454.7	465.4	472.9	484.3	495.5
10°	395.3	406.1	419.0	432.3	447.8	462.3	475.2	489.7	501.7	517.4	530.8
12.5°	393.9	407.0	424.9	440.7	459.6	479.5	498.6	517.1	527.7	554.0	566.4
15°	390.5	406.1	428.5	452.4	478.4	502.0	526.3	545.7	577.0	600.0	614.7
17.5°	384.1	405.9	432.4	461.3	492.9	524.0	551.5	580.9	614.2	642.0	671.6
20°	381.0	405.0	434.6	466.5	499.4	534.5	565.8	601.1	637.4	664.8	702.8
22.5°	375.4	402.5	434.4	469.9	505.1	541.4	578.1	613.8	655.7	693.3	729.5
25°	366.2	396.6	429.7	469.4	510.5	547.0	590.9	638.2	681.8	730.3	766.4
27.5°	356.5	389.0	422.1	459.0	503.4	546.7	601.9	655.3	708.7	750.5	777.2
30°	349.1	380.7	414.8	452.1	495.9	547.4	609.1	667.4	719.5	755.4	770.4
32.5°	341.0	373.0	403.2	442.3	489.1	546.9	613.7	674.6	720.1	744.0	741.0
35°	328.4	355.1	384.7	422.2	477.3	543.6	616.4	675.2	703.1	698.0	659.3
37.5°	310.1	332.7	361.7	402.8	463.7	536.5	611.0	655.2	653.4	611.6	555.5
40°	298.8	318.0	345.8	389.1	453.0	532.0	602.7	631.4	607.1	548.7	481.5
42.5°	283.9	301.6	329.5	374.0	441.3	522.8	586.7	595.0	547.5	480.4	418.7
45°	260.8	276.4	305.2	351.2	423.7	502.6	547.8	527.4	463.4	394.1	347.2
47.5°	235.9	252.2	279.9	327.2	398.4	472.2	493.7	450.5	384.8	328.6	285.5
50°	220.3	235.9	263.1	310.7	381.2	447.3	456.2	400.4	340.0	290.6	255.3
52.5°	204.6	219.2	245.9	293.8	361.2	418.4	412.9	356.0	300.5	258.4	230.6
55°	181.0	194.9	220.3	265.1	326.5	371.9	352.0	297.7	251.7	219.0	197.9
57.5°	160.0	173.3	195.2	235.7	289.0	320.2	294.9	249.1	212.5	187.4	171.7
60°	145.7	157.4	178.4	216.0	262.3	286.0	261.0	220.5	189.7	169.6	155.6
62.5°	132.2	142.4	161.8	195.9	236.2	256.1	230.7	196.5	170.3	152.5	140.5
65°	111.7	121.0	138.1	164.7	197.7	211.0	189.1	161.4	141.1	127.8	119.8
67.5°	93.0	100.9	115.7	136.6	160.9	170.6	153.9	132.5	117.2	106.5	100.2
70°	80.6	87.4	99.0	117.0	139.0	146.4	130.9	113.2	102.0	93.4	87.6
72.5°	70.0	75.1	85.6	99.5	117.9	123.8	112.9	97.4	87.0	80.6	75.8
75°	53.4	57.6	64.4	75.6	88.3	91.7	83.6	73.9	66.9	62.3	58.7
77.5°	38.5	41.6	46.5	53.4	62.2	65.3	60.2	53.6	48.5	45.5	43.5
80°	29.0	31.6	35.7	41.4	46.7	48.4	45.4	40.4	36.9	35.1	33.4
82.5°	21.4	22.8	25.4	29.3	32.9	34.9	32.4	29.4	27.4	25.8	25.2
85°	10.8	11.6	12.7	14.3	16.6	17.3	16.3	15.6	14.4	13.5	13.5
87.5°	4.5	4.8	5.7	6.4	7.3	8.3	8.6	8.8	9.1	9.1	9.1
90°	2.7	4.5	6.4	8.2	10.3	12.6	15.1	17.4	19.8	20.5	21.3
92.5°	21.2	22.5	23.7	24.9	26.3	27.6	29.0	30.3	31.7	32.3	32.9
95°	50.0	51.3	52.6	53.9	55.3	56.7	58.2	59.7	61.1	61.9	62.6
97.5°	87.5	88.5	89.4	90.4	91.4	92.5	93.5	94.6	95.6	96.5	97.3
100°	113.4	114.5	115.6	116.8	117.7	118.7	119.6	120.5	121.4	122.0	122.5
102.5°	142.8	143.4	144.1	144.7	145.6	146.8	148.1	149.3	150.5	151.1	151.6
105°	186.2	186.6	186.9	187.4	188.3	190.0	191.6	193.3	194.9	194.9	194.9
107.5°	236.9	237.2	237.4	237.6	238.1	238.7	239.4	240.0	240.7	241.2	241.9
110°	268.8	269.2	269.5	269.9	270.3	270.7	271.0	271.4	271.7	272.5	273.2



TEST NUMBER: P332103-930

CATALOG NUMBER: S123DIW-S340D1030U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	301.7	301.9	302.1	302.4	302.5	302.6	302.6	302.7	302.8	303.7	304.6
115°	351.6	352.1	352.7	353.3	353.4	352.9	352.6	352.2	351.9	352.0	352.2
117.5°	401.3	401.7	402.0	402.4	402.4	401.9	401.4	400.9	400.5	400.4	400.4
120°	433.1	434.2	435.3	436.4	436.5	435.5	434.6	433.7	432.8	432.6	432.4
122.5°	465.2	466.0	466.8	467.6	467.7	467.3	466.8	466.4	465.9	465.4	464.9
125°	514.3	514.9	515.4	516.0	516.1	515.7	515.4	514.9	514.6	513.9	513.1
127.5°	560.5	561.7	562.9	564.0	564.4	564.0	563.6	563.2	562.8	561.8	560.8
130°	591.3	592.7	594.2	595.7	596.1	595.6	595.0	594.4	593.9	593.1	592.4
132.5°	621.6	623.1	624.6	626.1	626.6	626.1	625.7	625.3	624.9	624.0	623.2
135°	667.6	668.8	669.8	671.0	671.4	671.2	671.1	670.9	670.7	669.9	669.2
137.5°	710.5	711.3	712.2	713.2	713.9	714.4	714.9	715.3	715.8	715.0	714.3
140°	740.2	741.1	742.0	742.9	743.5	743.6	743.9	744.0	744.2	744.0	743.9
142.5°	767.3	768.2	769.1	770.1	770.6	770.9	771.3	771.7	772.0	771.8	771.6
145°	809.0	809.3	809.8	810.1	810.6	811.1	811.7	812.2	812.8	812.6	812.4
147.5°	846.3	846.9	847.7	848.3	848.9	849.4	849.9	850.4	850.9	850.9	850.9
150°	871.8	872.1	872.5	872.9	873.3	873.6	874.0	874.3	874.7	874.7	874.7
152.5°	893.1	893.6	894.1	894.6	895.0	895.2	895.4	895.7	895.9	896.2	896.4
155°	925.9	925.9	925.9	925.9	926.0	926.2	926.4	926.6	926.8	927.5	928.2
157.5°	954.1	953.9	953.7	953.5	953.4	953.6	953.7	953.9	954.0	954.8	955.5
160°	971.8	971.4	971.1	970.7	970.5	970.5	970.5	970.5	970.5	971.4	972.4
162.5°	987.6	987.0	986.5	986.0	985.8	985.9	986.1	986.3	986.4	987.3	988.2
165°	1008.0	1007.5	1006.9	1006.3	1006.1	1006.1	1006.1	1006.1	1006.1	1007.1	1008.3
167.5°	1024.2	1023.4	1022.7	1022.0	1021.7	1021.8	1022.0	1022.1	1022.2	1023.4	1024.5
170°	1033.4	1032.7	1031.9	1031.2	1030.9	1030.9	1030.9	1030.9	1030.9	1032.1	1033.4
172.5°	1040.6	1039.9	1039.2	1038.4	1038.1	1038.1	1038.1	1038.1	1038.1	1039.3	1040.4
175°	1048.3	1047.6	1046.8	1046.1	1045.7	1045.7	1045.7	1045.7	1045.7	1046.8	1047.9
177.5°	1051.6	1051.0	1050.4	1049.8	1049.5	1049.5	1049.5	1049.5	1049.5	1050.4	1051.2
180°	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5



TEST NUMBER: P332103-930

CATALOG NUMBER: S123DIW-S340D1030U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	392.0	392.0	392.0	392.0	392.0	392.0	392.0
2.5°	412.5	412.7	414.3	415.6	415.0	415.7	416.0
5°	450.7	457.5	461.1	463.8	464.0	464.2	465.7
7.5°	504.8	512.2	517.6	525.7	528.1	530.8	530.1
10°	544.4	555.2	564.5	569.4	574.8	582.5	576.3
12.5°	581.3	600.5	614.7	622.3	627.3	628.8	625.8
15°	642.2	667.2	680.7	680.4	697.4	704.8	693.2
17.5°	698.0	721.1	739.7	749.2	763.4	766.5	765.2
20°	732.2	757.5	771.9	788.2	795.7	802.3	803.4
22.5°	761.7	784.4	799.9	813.4	819.6	822.8	824.7
25°	792.1	809.9	819.2	823.9	825.7	825.2	822.8
27.5°	789.9	791.3	781.1	771.0	762.0	751.9	748.4
30°	769.4	753.5	725.0	708.8	685.1	666.3	673.9
32.5°	715.5	683.7	651.8	616.4	587.3	578.9	570.5
35°	610.7	554.8	522.1	484.1	469.0	453.8	443.3
37.5°	494.0	450.9	412.1	387.3	372.0	362.4	357.3
40°	427.1	388.2	356.3	336.1	324.6	313.8	312.3
42.5°	373.8	337.6	313.6	297.6	286.5	281.8	278.5
45°	306.1	281.0	264.8	253.4	246.0	243.1	239.3
47.5°	259.2	241.3	229.2	221.4	215.8	213.7	213.4
50°	232.8	218.0	209.1	203.0	198.7	197.9	194.9
52.5°	213.1	200.2	193.3	188.0	184.8	182.7	181.8
55°	185.0	176.4	170.2	167.1	164.7	162.6	162.6
57.5°	161.8	154.7	150.6	148.0	147.2	145.8	144.8
60°	147.6	141.5	138.3	136.0	134.4	134.7	133.0
62.5°	133.6	129.6	126.5	124.3	122.5	122.5	122.6
65°	113.7	110.7	108.4	107.7	106.6	105.3	105.6
67.5°	96.4	93.6	91.8	90.5	90.1	89.4	90.5
70°	84.0	81.9	80.6	79.4	79.0	79.2	80.1
72.5°	72.6	71.1	70.2	69.7	68.8	68.9	69.5
75°	57.0	55.8	55.1	54.5	54.3	54.3	54.3
77.5°	41.8	41.6	41.3	40.4	40.4	40.7	40.7
80°	33.0	32.4	32.3	31.9	31.3	31.0	31.9
82.5°	24.7	24.1	24.0	23.9	23.0	22.9	23.7
85°	13.3	12.7	12.9	12.7	12.7	12.6	12.6
87.5°	9.1	9.1	9.0	9.3	9.2	9.1	9.5
90°	22.0	22.7	23.3	23.6	24.1	24.4	24.8
92.5°	33.5	34.1	34.2	34.0	33.8	33.6	33.3
95°	63.3	64.1	64.4	64.4	64.4	64.4	64.4
97.5°	98.2	99.1	99.4	99.3	99.3	99.2	99.1
100°	123.1	123.6	124.1	124.4	124.8	125.1	125.6
102.5°	152.1	152.7	153.0	152.9	152.8	152.7	152.6
105°	194.9	194.9	195.1	195.5	195.8	196.2	196.6
107.5°	242.5	243.0	243.2	243.0	242.8	242.6	242.3
110°	273.9	274.7	274.8	274.5	274.1	273.8	273.4



TEST NUMBER: P332103-930

CATALOG NUMBER: S123DIW-S340D1030U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	305.4	306.3	306.7	306.6	306.6	306.6	306.5
115°	352.5	352.6	352.6	352.5	352.2	352.0	351.9
117.5°	400.3	400.3	400.0	399.5	399.0	398.4	397.9
120°	432.3	432.1	431.8	431.5	431.0	430.7	430.3
122.5°	464.4	464.0	463.4	462.9	462.4	461.9	461.4
125°	512.4	511.7	510.9	510.2	509.5	508.7	508.0
127.5°	559.8	558.7	557.7	556.9	556.1	555.2	554.4
130°	591.7	590.9	590.0	588.6	587.3	586.1	584.8
132.5°	622.3	621.4	620.5	619.5	618.5	617.5	616.5
135°	668.5	667.7	667.2	666.8	666.5	666.1	665.8
137.5°	713.5	712.7	712.0	711.3	710.6	709.9	709.2
140°	743.6	743.5	742.7	741.4	740.2	738.9	737.6
142.5°	771.4	771.3	770.6	769.6	768.7	767.7	766.7
145°	812.2	812.0	811.5	810.8	810.1	809.3	808.6
147.5°	850.9	850.9	850.4	849.3	848.2	847.1	846.0
150°	874.7	874.7	874.2	873.1	872.0	870.9	869.8
152.5°	896.7	897.1	896.7	895.8	894.8	893.8	892.9
155°	929.0	929.7	929.4	928.1	926.8	925.6	924.3
157.5°	956.3	957.1	957.0	955.9	955.0	953.9	952.8
160°	973.3	974.2	974.3	973.5	972.8	972.1	971.3
162.5°	989.1	990.1	989.9	988.8	987.6	986.4	985.2
165°	1009.3	1010.5	1010.4	1009.1	1007.8	1006.5	1005.3
167.5°	1025.6	1026.8	1026.8	1025.6	1024.5	1023.4	1022.2
170°	1034.7	1036.0	1036.0	1034.7	1033.4	1032.1	1030.9
172.5°	1041.5	1042.7	1042.6	1041.3	1040.0	1038.7	1037.5
175°	1049.0	1050.1	1050.0	1048.7	1047.4	1046.2	1044.9
177.5°	1052.1	1053.0	1053.0	1051.9	1050.9	1049.9	1048.9
180°	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5

(END OF REPORT)