

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332127-930

Luminaire Tested: **S123DIW-S560D755U930-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332127-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S560D755U930-4F0-1E-UDD-A1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 755 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4081.9 lumens
Efficiency: N/A
Efficacy: 108.6 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 37.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332127-930

CATALOG NUMBER: S123DIW-S560D755U930-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P332127-930

CATALOG NUMBER: S123DIW-S560D755U930-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	48				48
1	98	93	90	86	90	86	83	80	72	70	68	60	58	57	48	47	46				41	
2	89	82	76	71	82	75	70	66	64	60	57	53	50	48	43	41	39				34	
3	81	72	65	59	75	67	60	55	56	52	48	47	43	41	38	36	34				29	
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	34	31	29				25	
5	68	57	49	43	63	53	46	40	45	40	35	38	34	30	31	28	25				22	
6	63	51	43	37	58	47	40	35	41	35	31	34	30	27	28	25	22				20	
7	58	46	38	33	54	43	36	31	37	31	27	31	27	24	26	22	20				17	
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	23	20	18				16	
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	22	18	16				14	
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15				13	

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	6937	6937	6937	6937
5°	8272	6967	6174	6967
10°	10355	6932	5576	6932
15°	12700	6876	5192	6876
20°	15131	6788	4943	6788
25°	16066	6683	4888	6683
30°	13770	6606	4913	6606
35°	9577	6495	4964	6495
40°	7213	6367	4949	6367
45°	5990	6174	4886	6174
50°	5365	5784	4843	5784
55°	5016	5362	4782	5362
60°	4706	4921	4732	4921
65°	4422	4485	4582	4485
70°	4148	3991	4362	3991
75°	3714	3493	4001	3493
80°	3248	2864	3446	2864
85°	2544	2087	2322	2087



TEST NUMBER: P332127-930

CATALOG NUMBER: S123DIW-S560D755U930-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	63.5	1.6
10°-20°	203.6	5.0
20°-30°	341.7	8.4
30°-40°	386.9	9.5
40°-50°	346.9	8.5
50°-60°	280.0	6.9
60°-70°	195.1	4.8
70°-80°	102.5	2.5
80°-90°	27.4	0.7
90°-100°	50.2	1.2
100°-110°	150.2	3.7
110°-120°	255.5	6.3
120°-130°	336.1	8.2
130°-140°	377.7	9.3
140°-150°	371.3	9.1
150°-160°	312.6	7.7
160°-170°	208.1	5.1
170°-180°	72.9	1.8
0°-30°	608.7	14.9
0°-40°	995.6	24.4
0°-60°	1622.5	39.7
0°-90°	1947.5	47.7
90°-120°	455.9	11.2
90°-150°	1540.9	37.7
90°-180°	2134.0	52.3
0°-180°	4081.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	644	644	644	644	644	
5°	766	645	571	645	766	79
15°	1140	617	466	617	1140	329
25°	1353	563	412	563	1353	593
35°	729	494	378	494	729	473
45°	394	406	321	406	394	311
55°	267	286	255	286	267	240
65°	174	176	180	176	174	173
75°	89	84	96	84	89	96
85°	21	17	19	17	21	25
90°	18	1	18	1	18	10
95°	47	36	47	36	47	48
105°	144	136	144	136	144	153
115°	258	257	258	257	258	255
125°	372	376	372	376	372	333
135°	488	488	488	488	488	375
145°	592	592	592	592	592	370
155°	677	678	677	678	677	312
165°	736	739	736	739	736	208
175°	766	768	766	768	766	73
180°	770	770	770	770	770	



TEST NUMBER: P332127-930

CATALOG NUMBER: S123DIW-S560D755U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5
2.5°	684.0	683.5	682.2	683.2	681.2	678.5	678.2	675.7	668.5	668.0	666.0
5°	765.6	763.1	762.9	762.5	758.1	752.2	740.9	740.0	725.0	717.5	708.5
7.5°	871.5	872.8	868.2	864.2	850.8	842.0	830.0	814.6	796.1	777.5	765.0
10°	947.4	957.7	944.9	936.1	928.1	912.7	895.0	872.8	850.6	824.7	805.0
12.5°	1028.8	1033.9	1031.4	1023.0	1010.5	987.2	955.6	931.2	910.8	867.6	850.2
15°	1139.7	1158.8	1146.6	1118.5	1119.2	1097.0	1055.7	1010.5	986.4	948.6	897.1
17.5°	1257.9	1260.3	1255.1	1231.7	1216.0	1185.6	1147.5	1104.2	1055.4	1009.7	955.0
20°	1320.9	1319.0	1308.1	1295.8	1269.0	1245.3	1203.7	1155.4	1092.9	1047.9	988.3
22.5°	1355.8	1352.7	1347.5	1337.3	1315.0	1289.5	1252.2	1199.3	1139.9	1077.9	1009.0
25°	1352.7	1356.7	1357.4	1354.5	1346.8	1331.5	1302.1	1260.0	1200.6	1121.0	1049.2
27.5°	1230.3	1236.0	1252.7	1267.5	1284.1	1300.9	1298.7	1277.7	1233.9	1165.1	1077.3
30°	1107.9	1095.4	1126.3	1165.3	1191.9	1238.7	1264.9	1266.5	1241.9	1182.8	1097.2
32.5°	938.0	951.8	965.4	1013.4	1071.5	1124.1	1176.2	1218.3	1223.1	1183.8	1109.0
35°	728.8	746.0	770.9	796.0	858.4	912.1	1003.9	1083.9	1147.5	1155.9	1110.0
37.5°	587.3	595.8	611.6	636.6	677.4	741.2	812.2	913.2	1005.5	1074.2	1077.2
40°	513.3	515.8	533.6	552.7	585.8	638.2	702.3	791.6	902.1	998.0	1038.0
42.5°	457.9	463.4	470.9	489.3	515.6	555.1	614.6	688.4	789.7	900.0	978.2
45°	393.5	399.7	404.4	416.5	435.3	461.8	503.4	570.8	647.9	761.9	867.2
47.5°	350.8	351.3	354.8	364.0	376.7	396.7	426.1	469.4	540.2	632.6	740.7
50°	320.4	325.4	326.6	333.8	343.8	358.5	382.9	419.6	477.8	559.0	658.3
52.5°	298.9	300.4	303.9	309.1	317.8	329.2	350.3	379.2	424.8	494.0	585.3
55°	267.3	267.3	270.8	274.8	279.8	290.1	304.1	325.4	360.0	413.8	489.3
57.5°	238.1	239.6	242.1	243.3	247.5	254.4	266.1	282.3	308.1	349.4	409.5
60°	218.6	221.4	221.1	223.6	227.3	232.6	242.6	255.8	278.8	311.9	362.6
62.5°	201.6	201.4	201.4	204.3	208.1	213.1	219.6	231.0	250.6	280.0	323.0
65°	173.6	173.0	175.2	177.1	178.3	182.1	187.0	197.1	210.2	232.0	265.4
67.5°	148.8	146.9	148.1	148.8	150.9	153.8	158.5	164.7	175.1	192.7	217.8
70°	131.8	130.2	129.9	130.5	132.4	134.6	138.0	144.0	153.6	167.7	186.1
72.5°	114.3	113.2	113.2	114.5	115.4	116.8	119.3	124.7	132.4	142.9	160.1
75°	89.3	89.3	89.3	89.6	90.6	91.8	93.7	96.4	102.4	109.9	121.5
77.5°	66.9	66.9	66.5	66.4	67.8	68.4	68.8	71.4	74.8	79.8	88.2
80°	52.4	50.9	51.5	52.4	53.1	53.4	54.3	55.0	57.8	60.6	66.5
82.5°	39.0	37.7	37.7	39.2	39.4	39.6	40.6	41.5	42.6	45.1	48.3
85°	20.6	20.6	21.0	21.0	21.2	21.0	21.9	22.2	22.2	23.7	25.6
87.5°	11.1	10.6	10.8	10.9	10.7	10.8	11.0	11.1	11.3	11.4	11.3
90°	18.2	17.9	17.6	17.4	17.0	16.7	16.1	15.6	15.1	14.5	12.8
92.5°	24.5	24.6	24.8	24.9	25.1	24.9	24.5	24.1	23.6	23.2	22.3
95°	47.2	47.2	47.2	47.2	47.2	47.0	46.4	45.8	45.3	44.8	43.7
97.5°	72.6	72.6	72.7	72.8	72.8	72.6	71.9	71.3	70.7	70.1	69.3
100°	92.0	91.7	91.5	91.2	90.9	90.6	90.2	89.8	89.4	88.9	88.3
102.5°	111.9	111.9	111.9	112.0	112.0	111.9	111.5	111.0	110.6	110.2	109.3
105°	144.1	143.7	143.5	143.2	142.9	142.8	142.8	142.8	142.8	142.8	141.6
107.5°	177.6	177.7	177.9	178.1	178.2	178.1	177.7	177.2	176.8	176.3	175.9
110°	200.3	200.6	200.8	201.1	201.4	201.2	200.7	200.2	199.7	199.1	198.9



TEST NUMBER: P332127-930

CATALOG NUMBER: S123DIW-S560D755U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	224.5	224.5	224.6	224.7	224.7	224.5	223.8	223.1	222.5	221.8	221.8
115°	257.8	258.0	258.0	258.2	258.4	258.4	258.2	258.0	258.0	257.8	258.0
117.5°	291.6	292.0	292.3	292.7	293.1	293.3	293.3	293.3	293.3	293.3	293.8
120°	315.3	315.5	315.8	316.1	316.3	316.6	316.7	316.8	317.0	317.1	317.8
122.5°	338.0	338.4	338.8	339.2	339.6	339.9	340.2	340.6	341.0	341.3	341.7
125°	372.2	372.7	373.2	373.8	374.3	374.9	375.4	375.9	376.5	377.0	377.2
127.5°	406.2	406.8	407.4	408.1	408.6	409.4	410.1	410.8	411.6	412.4	412.6
130°	428.4	429.4	430.3	431.3	432.2	432.9	433.5	434.1	434.6	435.1	435.5
132.5°	451.7	452.4	453.1	453.9	454.6	455.3	455.9	456.6	457.2	457.9	458.1
135°	487.7	488.0	488.3	488.5	488.9	489.3	489.8	490.3	490.8	491.4	491.5
137.5°	519.6	520.1	520.6	521.1	521.6	522.2	522.7	523.3	523.8	524.4	524.1
140°	540.4	541.4	542.3	543.2	544.1	544.7	544.9	544.9	545.1	545.3	545.1
142.5°	561.7	562.4	563.1	563.9	564.6	565.0	565.2	565.3	565.4	565.6	565.3
145°	592.5	593.0	593.5	594.0	594.6	594.9	595.1	595.2	595.3	595.5	595.1
147.5°	619.8	620.6	621.4	622.2	623.1	623.5	623.5	623.5	623.5	623.5	623.1
150°	637.2	638.1	638.9	639.6	640.4	640.8	640.8	640.8	640.8	640.8	640.6
152.5°	654.2	654.8	655.6	656.2	657.0	657.2	657.0	656.8	656.6	656.3	656.2
155°	677.2	678.1	679.1	680.0	680.9	681.1	680.6	680.0	679.6	679.0	678.8
157.5°	698.1	698.9	699.6	700.3	701.1	701.2	700.7	700.1	699.5	699.0	698.9
160°	711.7	712.2	712.7	713.3	713.8	713.7	713.1	712.4	711.8	711.0	711.0
162.5°	721.8	722.7	723.6	724.4	725.3	725.4	724.7	724.0	723.3	722.7	722.6
165°	736.5	737.4	738.3	739.3	740.2	740.3	739.5	738.7	737.8	737.0	737.0
167.5°	748.9	749.7	750.6	751.5	752.3	752.3	751.5	750.6	749.7	748.9	748.9
170°	755.2	756.2	757.1	758.1	759.0	759.0	758.1	757.1	756.2	755.2	755.2
172.5°	760.1	761.0	762.0	762.9	763.9	763.9	763.0	762.2	761.4	760.5	760.5
175°	765.5	766.5	767.4	768.3	769.3	769.3	768.5	767.8	767.0	766.1	766.1
177.5°	768.4	769.2	769.9	770.7	771.4	771.5	770.9	770.2	769.6	768.9	768.9
180°	770.4	770.4	770.4	770.4	770.4	770.4	770.4	770.4	770.4	770.4	770.4



TEST NUMBER: P332127-930

CATALOG NUMBER: S123DIW-S560D755U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5
2.5°	664.5	662.5	660.5	657.0	654.0	649.7	648.5	647.0	642.5	638.5	635.5
5°	705.1	697.6	686.6	676.6	668.5	657.6	651.3	644.8	635.4	627.0	620.1
7.5°	747.5	732.8	715.8	697.5	680.4	663.8	650.5	638.7	625.6	613.1	603.5
10°	781.3	760.0	736.3	710.7	688.8	667.6	649.8	634.2	617.3	602.7	590.4
12.5°	819.7	788.2	755.5	724.4	698.5	669.1	647.6	627.7	608.6	590.9	577.2
15°	865.3	825.3	786.6	743.8	704.4	667.6	642.0	617.0	594.8	576.7	559.2
17.5°	906.7	861.4	810.4	758.4	710.9	667.2	631.4	603.2	575.4	553.3	535.8
20°	930.2	878.6	820.9	766.9	714.4	665.7	626.4	592.6	562.7	539.2	519.6
22.5°	950.5	890.1	830.4	772.7	714.2	661.7	617.2	582.4	549.9	527.0	506.1
25°	971.4	899.3	839.4	771.6	706.3	652.0	602.0	562.7	530.2	503.4	481.8
27.5°	989.4	898.7	827.5	754.6	694.0	639.5	586.2	544.0	509.5	480.3	458.4
30°	1001.4	899.9	815.3	743.1	682.0	625.7	573.9	531.5	495.2	465.5	445.0
32.5°	1008.9	899.2	804.0	727.2	663.0	613.3	560.7	516.7	479.5	450.4	430.5
35°	1013.3	893.6	784.7	694.1	632.3	583.9	539.9	494.3	455.3	428.1	405.6
37.5°	1004.5	882.2	762.2	662.3	594.6	547.0	509.9	471.1	433.7	403.8	384.4
40°	990.8	874.7	744.7	639.8	568.6	522.7	491.2	453.1	416.2	387.8	369.7
42.5°	964.6	859.4	725.5	614.8	541.6	495.7	466.7	434.9	400.0	373.3	355.2
45°	900.6	826.2	696.7	577.4	501.8	454.4	428.8	405.6	374.1	348.1	332.6
47.5°	811.7	776.3	654.9	537.9	460.2	414.6	387.9	369.3	346.3	325.4	310.4
50°	750.1	735.4	626.7	510.9	432.4	387.8	362.2	345.4	328.8	307.9	294.2
52.5°	678.8	687.9	593.7	482.9	404.2	360.4	336.2	322.9	307.9	290.7	278.7
55°	578.6	611.4	536.8	435.9	362.2	320.4	297.6	285.7	277.0	264.2	253.9
57.5°	484.8	526.4	475.2	387.5	320.9	284.9	263.0	250.1	244.4	237.7	229.7
60°	429.0	470.3	431.2	355.1	293.2	258.9	239.5	228.6	223.0	218.3	211.4
62.5°	379.4	421.0	388.2	322.0	266.0	234.2	217.3	206.6	202.2	199.7	193.9
65°	311.0	346.9	325.1	270.8	227.0	198.9	183.6	176.1	172.0	171.1	167.4
67.5°	253.2	280.5	264.6	224.5	190.1	165.8	152.9	146.5	143.4	143.1	140.2
70°	215.2	240.8	228.6	192.3	162.7	143.7	132.4	126.8	124.9	124.6	123.0
72.5°	185.6	203.5	193.9	163.6	140.7	123.4	115.1	109.3	107.1	107.6	106.6
75°	137.4	150.8	145.2	124.3	105.8	94.6	87.7	84.0	82.1	83.1	81.8
77.5°	98.9	107.4	102.3	87.8	76.5	68.3	63.3	61.0	59.3	59.2	58.6
80°	74.6	79.7	76.8	68.1	58.7	51.9	47.8	46.2	45.2	45.0	44.7
82.5°	53.2	57.4	54.1	48.1	41.7	37.6	35.3	33.3	32.5	32.7	32.4
85°	26.8	28.5	27.1	23.4	21.0	19.1	17.8	16.9	16.2	16.6	15.9
87.5°	11.4	11.3	10.3	9.0	8.2	7.2	6.8	6.1	5.9	6.1	6.2
90°	11.0	9.3	7.5	6.0	4.6	3.3	2.0	0.6	2.0	3.3	4.6
92.5°	21.3	20.2	19.2	18.3	17.4	16.5	15.6	14.7	15.6	16.5	17.4
95°	42.6	41.6	40.4	39.5	38.6	37.6	36.6	35.7	36.6	37.6	38.6
97.5°	68.5	67.8	66.9	66.2	65.6	64.8	64.1	63.4	64.1	64.8	65.6
100°	87.6	86.9	86.3	85.5	84.7	83.9	83.1	82.3	83.1	83.9	84.7
102.5°	108.5	107.6	106.7	106.0	105.5	105.1	104.6	104.1	104.6	105.1	105.5
105°	140.4	139.2	137.9	137.2	137.0	136.7	136.4	136.2	136.4	136.7	137.0
107.5°	175.4	174.9	174.4	174.1	173.9	173.7	173.6	173.4	173.6	173.7	173.9
110°	198.5	198.3	198.0	197.7	197.5	197.2	197.0	196.7	197.0	197.2	197.5



TEST NUMBER: P332127-930

CATALOG NUMBER: S123DIW-S560D755U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	221.8	221.7	221.6	221.5	221.4	221.2	221.0	220.9	221.0	221.2	221.4
115°	258.4	258.6	258.9	258.8	258.4	258.0	257.6	257.2	257.6	258.0	258.4
117.5°	294.1	294.4	294.8	294.8	294.6	294.2	294.0	293.8	294.0	294.2	294.6
120°	318.5	319.1	319.8	319.8	318.9	318.1	317.3	316.5	317.3	318.1	318.9
122.5°	342.0	342.3	342.7	342.6	342.0	341.4	340.8	340.2	340.8	341.4	342.0
125°	377.6	377.8	378.1	378.1	377.6	377.2	376.8	376.4	376.8	377.2	377.6
127.5°	412.9	413.3	413.5	413.3	412.4	411.6	410.7	409.8	410.7	411.6	412.4
130°	435.9	436.3	436.8	436.3	435.3	434.2	433.2	432.1	433.2	434.2	435.3
132.5°	458.4	458.8	459.0	458.7	457.5	456.5	455.4	454.4	455.4	456.5	457.5
135°	491.6	491.8	492.0	491.5	490.8	490.0	489.2	488.4	489.2	490.0	490.8
137.5°	523.7	523.3	523.0	522.5	521.9	521.1	520.5	519.8	520.5	521.1	521.9
140°	544.9	544.9	544.7	544.3	543.6	543.0	542.3	541.6	542.3	543.0	543.6
142.5°	565.1	564.8	564.6	564.1	563.5	562.8	562.1	561.5	562.1	562.8	563.5
145°	594.7	594.3	593.9	593.5	593.2	593.0	592.7	592.5	592.7	593.0	593.2
147.5°	622.6	622.3	621.9	621.5	621.0	620.5	620.0	619.5	620.0	620.5	621.0
150°	640.3	640.0	639.8	639.5	639.3	639.0	638.7	638.5	638.7	639.0	639.3
152.5°	656.0	655.8	655.7	655.4	655.1	654.7	654.3	654.0	654.3	654.7	655.1
155°	678.7	678.6	678.4	678.4	678.4	678.4	678.4	678.4	678.4	678.4	678.4
157.5°	698.7	698.6	698.5	698.5	698.7	698.9	699.0	699.2	699.0	698.9	698.7
160°	711.0	711.0	711.0	711.2	711.4	711.8	712.0	712.2	712.0	711.8	711.4
162.5°	722.4	722.4	722.3	722.4	722.8	723.1	723.5	723.9	723.5	723.1	722.8
165°	737.0	737.0	737.0	737.3	737.7	738.1	738.5	738.9	738.5	738.1	737.7
167.5°	748.7	748.6	748.5	748.7	749.3	749.8	750.3	750.9	750.3	749.8	749.3
170°	755.2	755.2	755.2	755.5	756.0	756.6	757.1	757.7	757.1	756.6	756.0
172.5°	760.5	760.5	760.5	760.8	761.3	761.9	762.5	763.0	762.5	761.9	761.3
175°	766.1	766.1	766.1	766.4	767.0	767.4	768.0	768.5	768.0	767.4	767.0
177.5°	768.9	768.9	768.9	769.2	769.6	770.0	770.4	770.9	770.4	770.0	769.6
180°	770.4	770.4	770.4	770.4	770.4	770.4	770.4	770.4	770.4	770.4	770.4



TEST NUMBER: P332127-930

CATALOG NUMBER: S123DIW-S560D755U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5
2.5°	633.7	632.0	629.5	625.7	622.7	618.0	618.0	618.7	618.7	618.5	618.0
5°	614.5	609.8	604.2	597.7	590.8	583.9	582.7	580.2	578.3	577.1	575.5
7.5°	594.2	586.0	577.7	568.6	560.2	553.3	548.5	544.5	541.8	539.2	537.1
10°	580.5	570.1	560.5	550.8	540.2	531.7	526.4	522.7	519.9	517.4	516.2
12.5°	564.3	552.4	541.8	532.6	521.0	512.3	507.2	505.5	502.1	496.9	494.2
15°	540.5	529.6	516.8	502.7	497.1	486.5	480.5	477.8	475.9	471.8	470.6
17.5°	520.2	505.9	491.5	481.0	470.6	462.0	458.7	455.2	452.7	449.4	448.4
20°	504.0	491.2	478.1	466.8	455.9	446.5	443.7	441.2	438.7	437.2	435.9
22.5°	487.5	474.7	463.8	453.3	441.6	435.5	432.4	429.7	428.0	426.9	425.7
25°	464.3	453.1	440.9	431.5	422.2	418.1	416.2	414.7	413.4	411.9	411.6
27.5°	443.6	431.4	421.5	412.7	406.0	402.6	400.8	400.1	400.3	400.9	401.2
30°	428.1	416.9	408.7	401.2	395.0	391.9	391.6	391.6	392.8	393.1	393.8
32.5°	413.8	404.6	396.5	389.2	384.5	382.4	383.6	383.6	384.6	385.4	386.5
35°	393.1	385.0	378.8	372.5	368.4	369.4	370.0	370.6	372.2	374.1	375.4
37.5°	373.3	366.3	359.8	354.9	353.0	354.7	356.2	357.5	359.4	360.8	362.0
40°	359.1	353.8	347.6	343.2	343.8	344.7	346.0	347.6	349.1	350.0	351.3
42.5°	345.8	340.3	335.6	331.9	332.8	334.0	334.8	335.6	337.4	339.1	339.8
45°	325.7	321.3	316.9	314.8	315.4	316.0	316.7	317.6	319.1	320.4	320.7
47.5°	303.0	299.9	297.0	294.9	295.9	295.6	296.4	298.5	299.0	299.7	301.4
50°	288.5	285.7	282.3	281.7	281.7	281.7	281.9	284.5	284.5	285.7	287.0
52.5°	272.6	270.8	268.6	267.4	266.9	266.9	268.2	269.5	269.9	271.7	273.0
55°	248.8	247.0	245.2	244.2	243.5	244.2	246.7	247.3	248.8	249.8	250.7
57.5°	224.2	222.7	221.3	220.8	220.6	221.4	222.8	224.7	225.1	228.0	229.3
60°	208.0	205.8	204.6	204.6	203.9	206.7	206.1	209.2	209.9	211.7	213.9
62.5°	191.2	188.3	187.8	187.8	188.7	189.5	190.4	191.8	193.4	195.8	197.4
65°	164.3	162.7	164.9	164.5	164.0	165.8	165.8	167.4	169.3	171.5	174.9
67.5°	138.7	137.9	138.1	138.1	139.0	140.1	141.0	142.4	144.6	146.9	149.1
70°	121.5	122.4	120.8	122.1	123.0	123.4	123.9	125.8	128.3	129.9	132.4
72.5°	104.8	104.7	104.8	105.3	106.3	106.9	107.5	109.6	112.3	113.7	115.7
75°	80.6	80.2	81.2	81.2	82.8	83.4	84.0	85.0	87.4	89.3	90.9
77.5°	58.9	59.2	59.0	60.1	59.7	59.8	61.7	62.6	62.9	66.6	67.4
80°	44.4	45.0	45.2	45.6	45.9	45.2	47.5	48.4	48.4	50.5	52.2
82.5°	31.9	32.2	33.0	33.3	33.4	34.0	34.2	34.9	35.6	36.6	38.6
85°	15.9	16.9	17.2	16.9	17.2	16.6	17.4	17.8	18.1	18.1	18.1
87.5°	6.2	6.8	6.8	7.4	7.6	8.2	8.2	7.8	8.0	8.8	7.9
90°	6.0	7.5	9.3	11.0	12.8	14.5	15.1	15.6	16.1	16.7	17.0
92.5°	18.3	19.2	20.2	21.3	22.3	23.2	23.6	24.1	24.5	24.9	25.1
95°	39.5	40.4	41.6	42.6	43.7	44.8	45.3	45.8	46.4	47.0	47.2
97.5°	66.2	66.9	67.8	68.5	69.3	70.1	70.7	71.3	71.9	72.6	72.8
100°	85.5	86.3	86.9	87.6	88.3	88.9	89.4	89.8	90.2	90.6	90.9
102.5°	106.0	106.7	107.6	108.5	109.3	110.2	110.6	111.0	111.5	111.9	112.0
105°	137.2	137.9	139.2	140.4	141.6	142.8	142.8	142.8	142.8	142.8	142.9
107.5°	174.1	174.4	174.9	175.4	175.9	176.3	176.8	177.2	177.7	178.1	178.2
110°	197.7	198.0	198.3	198.5	198.9	199.1	199.7	200.2	200.7	201.2	201.4



TEST NUMBER: P332127-930

CATALOG NUMBER: S123DIW-S560D755U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	221.5	221.6	221.7	221.8	221.8	221.8	222.5	223.1	223.8	224.5	224.7
115°	258.8	258.9	258.6	258.4	258.0	257.8	258.0	258.0	258.2	258.4	258.4
117.5°	294.8	294.8	294.4	294.1	293.8	293.3	293.3	293.3	293.3	293.3	293.1
120°	319.8	319.8	319.1	318.5	317.8	317.1	317.0	316.8	316.7	316.6	316.3
122.5°	342.6	342.7	342.3	342.0	341.7	341.3	341.0	340.6	340.2	339.9	339.6
125°	378.1	378.1	377.8	377.6	377.2	377.0	376.5	375.9	375.4	374.9	374.3
127.5°	413.3	413.5	413.3	412.9	412.6	412.4	411.6	410.8	410.1	409.4	408.6
130°	436.3	436.8	436.3	435.9	435.5	435.1	434.6	434.1	433.5	432.9	432.2
132.5°	458.7	459.0	458.8	458.4	458.1	457.9	457.2	456.6	455.9	455.3	454.6
135°	491.5	492.0	491.8	491.6	491.5	491.4	490.8	490.3	489.8	489.3	488.9
137.5°	522.5	523.0	523.3	523.7	524.1	524.4	523.8	523.3	522.7	522.2	521.6
140°	544.3	544.7	544.9	544.9	545.1	545.3	545.1	544.9	544.9	544.7	544.1
142.5°	564.1	564.6	564.8	565.1	565.3	565.6	565.4	565.3	565.2	565.0	564.6
145°	593.5	593.9	594.3	594.7	595.1	595.5	595.3	595.2	595.1	594.9	594.6
147.5°	621.5	621.9	622.3	622.6	623.1	623.5	623.5	623.5	623.5	623.5	623.1
150°	639.5	639.8	640.0	640.3	640.6	640.8	640.8	640.8	640.8	640.8	640.4
152.5°	655.4	655.7	655.8	656.0	656.2	656.3	656.6	656.8	657.0	657.2	657.0
155°	678.4	678.4	678.6	678.7	678.8	679.0	679.6	680.0	680.6	681.1	680.9
157.5°	698.5	698.5	698.6	698.7	698.9	699.0	699.5	700.1	700.7	701.2	701.1
160°	711.2	711.0	711.0	711.0	711.0	711.0	711.8	712.4	713.1	713.7	713.8
162.5°	722.4	722.3	722.4	722.4	722.6	722.7	723.3	724.0	724.7	725.4	725.3
165°	737.3	737.0	737.0	737.0	737.0	737.0	737.8	738.7	739.5	740.3	740.2
167.5°	748.7	748.5	748.6	748.7	748.9	748.9	749.7	750.6	751.5	752.3	752.3
170°	755.5	755.2	755.2	755.2	755.2	755.2	756.2	757.1	758.1	759.0	759.0
172.5°	760.8	760.5	760.5	760.5	760.5	760.5	761.4	762.2	763.0	763.9	763.9
175°	766.4	766.1	766.1	766.1	766.1	766.1	767.0	767.8	768.5	769.3	769.3
177.5°	769.2	768.9	768.9	768.9	768.9	768.9	769.6	770.2	770.9	771.5	771.4
180°	770.4	770.4	770.4	770.4	770.4	770.4	770.4	770.4	770.4	770.4	770.4



TEST NUMBER: P332127-930

CATALOG NUMBER: S123DIW-S560D755U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5
2.5°	616.3	616.0	617.8	616.5	617.8	616.0	616.3	618.0	618.5	618.7	618.7
5°	573.6	574.5	571.4	571.4	571.4	574.5	573.6	575.5	577.1	578.3	580.2
7.5°	535.7	534.3	534.4	532.7	534.4	534.3	535.7	537.1	539.2	541.8	544.5
10°	512.4	510.5	509.9	510.2	509.9	510.5	512.4	516.2	517.4	519.9	522.7
12.5°	493.2	492.8	488.7	488.8	488.7	492.8	493.2	494.2	496.9	502.1	505.5
15°	470.6	464.6	464.0	465.9	464.0	464.6	470.6	470.6	471.8	475.9	477.8
17.5°	447.9	444.7	445.0	444.0	445.0	444.7	447.9	448.4	449.4	452.7	455.2
20°	435.9	434.1	433.7	431.5	433.7	434.1	435.9	435.9	437.2	438.7	441.2
22.5°	424.9	424.3	424.4	422.1	424.4	424.3	424.9	425.7	426.9	428.0	429.7
25°	411.2	412.8	411.6	411.6	411.6	412.8	411.2	411.6	411.9	413.4	414.7
27.5°	402.0	401.9	401.3	401.3	401.3	401.9	402.0	401.2	400.9	400.3	400.1
30°	395.0	394.7	395.3	395.3	395.3	394.7	395.0	393.8	393.1	392.8	391.6
32.5°	388.0	388.4	388.6	388.8	388.6	388.4	388.0	386.5	385.4	384.6	383.6
35°	377.2	377.5	378.5	377.8	378.5	377.5	377.2	375.4	374.1	372.2	370.6
37.5°	362.6	364.0	363.7	364.2	363.7	364.0	362.6	362.0	360.8	359.4	357.5
40°	351.6	352.5	352.2	352.2	352.2	352.5	351.6	351.3	350.0	349.1	347.6
42.5°	340.4	341.0	340.2	339.7	340.2	341.0	340.4	339.8	339.1	337.4	335.6
45°	322.0	321.3	322.3	321.0	322.3	321.3	322.0	320.7	320.4	319.1	317.6
47.5°	301.3	302.0	302.2	303.1	302.2	302.0	301.3	301.4	299.7	299.0	298.5
50°	287.6	289.4	289.4	289.2	289.4	289.4	287.6	287.0	285.7	284.5	284.5
52.5°	274.1	275.0	276.2	276.1	276.2	275.0	274.1	273.0	271.7	269.9	269.5
55°	253.2	253.9	254.5	254.8	254.5	253.9	253.2	250.7	249.8	248.8	247.3
57.5°	231.6	231.4	232.8	233.3	232.8	231.4	231.6	229.3	228.0	225.1	224.7
60°	216.4	216.4	218.9	219.8	218.9	216.4	216.4	213.9	211.7	209.9	209.2
62.5°	200.2	201.1	203.7	202.4	203.7	201.1	200.2	197.4	195.8	193.4	191.8
65°	176.4	179.0	178.6	179.9	178.6	179.0	176.4	174.9	171.5	169.3	167.4
67.5°	151.6	153.2	155.5	155.6	155.5	153.2	151.6	149.1	146.9	144.6	142.4
70°	134.9	136.5	137.7	138.6	137.7	136.5	134.9	132.4	129.9	128.3	125.8
72.5°	118.6	119.4	122.5	121.2	122.5	119.4	118.6	115.7	113.7	112.3	109.6
75°	93.0	95.2	97.1	96.2	97.1	95.2	93.0	90.9	89.3	87.4	85.0
77.5°	68.8	71.0	71.9	71.1	71.9	71.0	68.8	67.4	66.6	62.9	62.6
80°	54.3	54.1	55.9	55.6	55.9	54.1	54.3	52.2	50.5	48.4	48.4
82.5°	39.9	39.5	40.4	40.6	40.4	39.5	39.9	38.6	36.6	35.6	34.9
85°	19.3	20.3	19.1	18.8	19.1	20.3	19.3	18.1	18.1	18.1	17.8
87.5°	8.0	8.0	7.8	7.7	7.8	8.0	8.0	7.9	8.8	8.0	7.8
90°	17.4	17.6	17.9	18.2	17.9	17.6	17.4	17.0	16.7	16.1	15.6
92.5°	24.9	24.8	24.6	24.5	24.6	24.8	24.9	25.1	24.9	24.5	24.1
95°	47.2	47.2	47.2	47.2	47.2	47.2	47.2	47.2	47.0	46.4	45.8
97.5°	72.8	72.7	72.6	72.6	72.6	72.7	72.8	72.8	72.6	71.9	71.3
100°	91.2	91.5	91.7	92.0	91.7	91.5	91.2	90.9	90.6	90.2	89.8
102.5°	112.0	111.9	111.9	111.9	111.9	111.9	112.0	112.0	111.9	111.5	111.0
105°	143.2	143.5	143.7	144.1	143.7	143.5	143.2	142.9	142.8	142.8	142.8
107.5°	178.1	177.9	177.7	177.6	177.7	177.9	178.1	178.2	178.1	177.7	177.2
110°	201.1	200.8	200.6	200.3	200.6	200.8	201.1	201.4	201.2	200.7	200.2



TEST NUMBER: P332127-930

CATALOG NUMBER: S123DIW-S560D755U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	224.7	224.6	224.5	224.5	224.5	224.6	224.7	224.7	224.5	223.8	223.1
115°	258.2	258.0	258.0	257.8	258.0	258.0	258.2	258.4	258.4	258.2	258.0
117.5°	292.7	292.3	292.0	291.6	292.0	292.3	292.7	293.1	293.3	293.3	293.3
120°	316.1	315.8	315.5	315.3	315.5	315.8	316.1	316.3	316.6	316.7	316.8
122.5°	339.2	338.8	338.4	338.0	338.4	338.8	339.2	339.6	339.9	340.2	340.6
125°	373.8	373.2	372.7	372.2	372.7	373.2	373.8	374.3	374.9	375.4	375.9
127.5°	408.1	407.4	406.8	406.2	406.8	407.4	408.1	408.6	409.4	410.1	410.8
130°	431.3	430.3	429.4	428.4	429.4	430.3	431.3	432.2	432.9	433.5	434.1
132.5°	453.9	453.1	452.4	451.7	452.4	453.1	453.9	454.6	455.3	455.9	456.6
135°	488.5	488.3	488.0	487.7	488.0	488.3	488.5	488.9	489.3	489.8	490.3
137.5°	521.1	520.6	520.1	519.6	520.1	520.6	521.1	521.6	522.2	522.7	523.3
140°	543.2	542.3	541.4	540.4	541.4	542.3	543.2	544.1	544.7	544.9	544.9
142.5°	563.9	563.1	562.4	561.7	562.4	563.1	563.9	564.6	565.0	565.2	565.3
145°	594.0	593.5	593.0	592.5	593.0	593.5	594.0	594.6	594.9	595.1	595.2
147.5°	622.2	621.4	620.6	619.8	620.6	621.4	622.2	623.1	623.5	623.5	623.5
150°	639.6	638.9	638.1	637.2	638.1	638.9	639.6	640.4	640.8	640.8	640.8
152.5°	656.2	655.6	654.8	654.2	654.8	655.6	656.2	657.0	657.2	657.0	656.8
155°	680.0	679.1	678.1	677.2	678.1	679.1	680.0	680.9	681.1	680.6	680.0
157.5°	700.3	699.6	698.9	698.1	698.9	699.6	700.3	701.1	701.2	700.7	700.1
160°	713.3	712.7	712.2	711.7	712.2	712.7	713.3	713.8	713.7	713.1	712.4
162.5°	724.4	723.6	722.7	721.8	722.7	723.6	724.4	725.3	725.4	724.7	724.0
165°	739.3	738.3	737.4	736.5	737.4	738.3	739.3	740.2	740.3	739.5	738.7
167.5°	751.5	750.6	749.7	748.9	749.7	750.6	751.5	752.3	752.3	751.5	750.6
170°	758.1	757.1	756.2	755.2	756.2	757.1	758.1	759.0	759.0	758.1	757.1
172.5°	762.9	762.0	761.0	760.1	761.0	762.0	762.9	763.9	763.9	763.0	762.2
175°	768.3	767.4	766.5	765.5	766.5	767.4	768.3	769.3	769.3	768.5	767.8
177.5°	770.7	769.9	769.2	768.4	769.2	769.9	770.7	771.4	771.5	770.9	770.2
180°	770.4	770.4	770.4	770.4	770.4	770.4	770.4	770.4	770.4	770.4	770.4



TEST NUMBER: P332127-930

CATALOG NUMBER: S123DIW-S560D755U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5
2.5°	618.0	618.0	622.7	625.7	629.5	632.0	633.7	635.5	638.5	642.5	647.0
5°	582.7	583.9	590.8	597.7	604.2	609.8	614.5	620.1	627.0	635.4	644.8
7.5°	548.5	553.3	560.2	568.6	577.7	586.0	594.2	603.5	613.1	625.6	638.7
10°	526.4	531.7	540.2	550.8	560.5	570.1	580.5	590.4	602.7	617.3	634.2
12.5°	507.2	512.3	521.0	532.6	541.8	552.4	564.3	577.2	590.9	608.6	627.7
15°	480.5	486.5	497.1	502.7	516.8	529.6	540.5	559.2	576.7	594.8	617.0
17.5°	458.7	462.0	470.6	481.0	491.5	505.9	520.2	535.8	553.3	575.4	603.2
20°	443.7	446.5	455.9	466.8	478.1	491.2	504.0	519.6	539.2	562.7	592.6
22.5°	432.4	435.5	441.6	453.3	463.8	474.7	487.5	506.1	527.0	549.9	582.4
25°	416.2	418.1	422.2	431.5	440.9	453.1	464.3	481.8	503.4	530.2	562.7
27.5°	400.8	402.6	406.0	412.7	421.5	431.4	443.6	458.4	480.3	509.5	544.0
30°	391.6	391.9	395.0	401.2	408.7	416.9	428.1	445.0	465.5	495.2	531.5
32.5°	383.6	382.4	384.5	389.2	396.5	404.6	413.8	430.5	450.4	479.5	516.7
35°	370.0	369.4	368.4	372.5	378.8	385.0	393.1	405.6	428.1	455.3	494.3
37.5°	356.2	354.7	353.0	354.9	359.8	366.3	373.3	384.4	403.8	433.7	471.1
40°	346.0	344.7	343.8	343.2	347.6	353.8	359.1	369.7	387.8	416.2	453.1
42.5°	334.8	334.0	332.8	331.9	335.6	340.3	345.8	355.2	373.3	400.0	434.9
45°	316.7	316.0	315.4	314.8	316.9	321.3	325.7	332.6	348.1	374.1	405.6
47.5°	296.4	295.6	295.9	294.9	297.0	299.9	303.0	310.4	325.4	346.3	369.3
50°	281.9	281.7	281.7	281.7	282.3	285.7	288.5	294.2	307.9	328.8	345.4
52.5°	268.2	266.9	266.9	267.4	268.6	270.8	272.6	278.7	290.7	307.9	322.9
55°	246.7	244.2	243.5	244.2	245.2	247.0	248.8	253.9	264.2	277.0	285.7
57.5°	222.8	221.4	220.6	220.8	221.3	222.7	224.2	229.7	237.7	244.4	250.1
60°	206.1	206.7	203.9	204.6	204.6	205.8	208.0	211.4	218.3	223.0	228.6
62.5°	190.4	189.5	188.7	187.8	187.8	188.3	191.2	193.9	199.7	202.2	206.6
65°	165.8	165.8	164.0	164.5	164.9	162.7	164.3	167.4	171.1	172.0	176.1
67.5°	141.0	140.1	139.0	138.1	138.1	137.9	138.7	140.2	143.1	143.4	146.5
70°	123.9	123.4	123.0	122.1	120.8	122.4	121.5	123.0	124.6	124.9	126.8
72.5°	107.5	106.9	106.3	105.3	104.8	104.7	104.8	106.6	107.6	107.1	109.3
75°	84.0	83.4	82.8	81.2	81.2	80.2	80.6	81.8	83.1	82.1	84.0
77.5°	61.7	59.8	59.7	60.1	59.0	59.2	58.9	58.6	59.2	59.3	61.0
80°	47.5	45.2	45.9	45.6	45.2	45.0	44.4	44.7	45.0	45.2	46.2
82.5°	34.2	34.0	33.4	33.3	33.0	32.2	31.9	32.4	32.7	32.5	33.3
85°	17.4	16.6	17.2	16.9	17.2	16.9	15.9	15.9	16.6	16.2	16.9
87.5°	8.2	8.2	7.6	7.4	6.8	6.8	6.2	6.2	6.1	5.9	6.1
90°	15.1	14.5	12.8	11.0	9.3	7.5	6.0	4.6	3.3	2.0	0.6
92.5°	23.6	23.2	22.3	21.3	20.2	19.2	18.3	17.4	16.5	15.6	14.7
95°	45.3	44.8	43.7	42.6	41.6	40.4	39.5	38.6	37.6	36.6	35.7
97.5°	70.7	70.1	69.3	68.5	67.8	66.9	66.2	65.6	64.8	64.1	63.4
100°	89.4	88.9	88.3	87.6	86.9	86.3	85.5	84.7	83.9	83.1	82.3
102.5°	110.6	110.2	109.3	108.5	107.6	106.7	106.0	105.5	105.1	104.6	104.1
105°	142.8	142.8	141.6	140.4	139.2	137.9	137.2	137.0	136.7	136.4	136.2
107.5°	176.8	176.3	175.9	175.4	174.9	174.4	174.1	173.9	173.7	173.6	173.4
110°	199.7	199.1	198.9	198.5	198.3	198.0	197.7	197.5	197.2	197.0	196.7



TEST NUMBER: P332127-930

CATALOG NUMBER: S123DIW-S560D755U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	222.5	221.8	221.8	221.8	221.7	221.6	221.5	221.4	221.2	221.0	220.9
115°	258.0	257.8	258.0	258.4	258.6	258.9	258.8	258.4	258.0	257.6	257.2
117.5°	293.3	293.3	293.8	294.1	294.4	294.8	294.8	294.6	294.2	294.0	293.8
120°	317.0	317.1	317.8	318.5	319.1	319.8	319.8	318.9	318.1	317.3	316.5
122.5°	341.0	341.3	341.7	342.0	342.3	342.7	342.6	342.0	341.4	340.8	340.2
125°	376.5	377.0	377.2	377.6	377.8	378.1	378.1	377.6	377.2	376.8	376.4
127.5°	411.6	412.4	412.6	412.9	413.3	413.5	413.3	412.4	411.6	410.7	409.8
130°	434.6	435.1	435.5	435.9	436.3	436.8	436.3	435.3	434.2	433.2	432.1
132.5°	457.2	457.9	458.1	458.4	458.8	459.0	458.7	457.5	456.5	455.4	454.4
135°	490.8	491.4	491.5	491.6	491.8	492.0	491.5	490.8	490.0	489.2	488.4
137.5°	523.8	524.4	524.1	523.7	523.3	523.0	522.5	521.9	521.1	520.5	519.8
140°	545.1	545.3	545.1	544.9	544.9	544.7	544.3	543.6	543.0	542.3	541.6
142.5°	565.4	565.6	565.3	565.1	564.8	564.6	564.1	563.5	562.8	562.1	561.5
145°	595.3	595.5	595.1	594.7	594.3	593.9	593.5	593.2	593.0	592.7	592.5
147.5°	623.5	623.5	623.1	622.6	622.3	621.9	621.5	621.0	620.5	620.0	619.5
150°	640.8	640.8	640.6	640.3	640.0	639.8	639.5	639.3	639.0	638.7	638.5
152.5°	656.6	656.3	656.2	656.0	655.8	655.7	655.4	655.1	654.7	654.3	654.0
155°	679.6	679.0	678.8	678.7	678.6	678.4	678.4	678.4	678.4	678.4	678.4
157.5°	699.5	699.0	698.9	698.7	698.6	698.5	698.5	698.7	698.9	699.0	699.2
160°	711.8	711.0	711.0	711.0	711.0	711.0	711.2	711.4	711.8	712.0	712.2
162.5°	723.3	722.7	722.6	722.4	722.4	722.3	722.4	722.8	723.1	723.5	723.9
165°	737.8	737.0	737.0	737.0	737.0	737.0	737.3	737.7	738.1	738.5	738.9
167.5°	749.7	748.9	748.9	748.7	748.6	748.5	748.7	749.3	749.8	750.3	750.9
170°	756.2	755.2	755.2	755.2	755.2	755.2	755.5	756.0	756.6	757.1	757.7
172.5°	761.4	760.5	760.5	760.5	760.5	760.5	760.8	761.3	761.9	762.5	763.0
175°	767.0	766.1	766.1	766.1	766.1	766.1	766.4	767.0	767.4	768.0	768.5
177.5°	769.6	768.9	768.9	768.9	768.9	768.9	769.2	769.6	770.0	770.4	770.9
180°	770.4	770.4	770.4	770.4	770.4	770.4	770.4	770.4	770.4	770.4	770.4



TEST NUMBER: P332127-930

CATALOG NUMBER: S123DIW-S560D755U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5
2.5°	648.5	649.7	654.0	657.0	660.5	662.5	664.5	666.0	668.0	668.5	675.7
5°	651.3	657.6	668.5	676.6	686.6	697.6	705.1	708.5	717.5	725.0	740.0
7.5°	650.5	663.8	680.4	697.5	715.8	732.8	747.5	765.0	777.5	796.1	814.6
10°	649.8	667.6	688.8	710.7	736.3	760.0	781.3	805.0	824.7	850.6	872.8
12.5°	647.6	669.1	698.5	724.4	755.5	788.2	819.7	850.2	867.6	910.8	931.2
15°	642.0	667.6	704.4	743.8	786.6	825.3	865.3	897.1	948.6	986.4	1010.5
17.5°	631.4	667.2	710.9	758.4	810.4	861.4	906.7	955.0	1009.7	1055.4	1104.2
20°	626.4	665.7	714.4	766.9	820.9	878.6	930.2	988.3	1047.9	1092.9	1155.4
22.5°	617.2	661.7	714.2	772.7	830.4	890.1	950.5	1009.0	1077.9	1139.9	1199.3
25°	602.0	652.0	706.3	771.6	839.4	899.3	971.4	1049.2	1121.0	1200.6	1260.0
27.5°	586.2	639.5	694.0	754.6	827.5	898.7	989.4	1077.3	1165.1	1233.9	1277.7
30°	573.9	625.7	682.0	743.1	815.3	899.9	1001.4	1097.2	1182.8	1241.9	1266.5
32.5°	560.7	613.3	663.0	727.2	804.0	899.2	1008.9	1109.0	1183.8	1223.1	1218.3
35°	539.9	583.9	632.3	694.1	784.7	893.6	1013.3	1110.0	1155.9	1147.5	1083.9
37.5°	509.9	547.0	594.6	662.3	762.2	882.2	1004.5	1077.2	1074.2	1005.5	913.2
40°	491.2	522.7	568.6	639.8	744.7	874.7	990.8	1038.0	998.0	902.1	791.6
42.5°	466.7	495.7	541.6	614.8	725.5	859.4	964.6	978.2	900.0	789.7	688.4
45°	428.8	454.4	501.8	577.4	696.7	826.2	900.6	867.2	761.9	647.9	570.8
47.5°	387.9	414.6	460.2	537.9	654.9	776.3	811.7	740.7	632.6	540.2	469.4
50°	362.2	387.8	432.4	510.9	626.7	735.4	750.1	658.3	559.0	477.8	419.6
52.5°	336.2	360.4	404.2	482.9	593.7	687.9	678.8	585.3	494.0	424.8	379.2
55°	297.6	320.4	362.2	435.9	536.8	611.4	578.6	489.3	413.8	360.0	325.4
57.5°	263.0	284.9	320.9	387.5	475.2	526.4	484.8	409.5	349.4	308.1	282.3
60°	239.5	258.9	293.2	355.1	431.2	470.3	429.0	362.6	311.9	278.8	255.8
62.5°	217.3	234.2	266.0	322.0	388.2	421.0	379.4	323.0	280.0	250.6	231.0
65°	183.6	198.9	227.0	270.8	325.1	346.9	311.0	265.4	232.0	210.2	197.1
67.5°	152.9	165.8	190.1	224.5	264.6	280.5	253.2	217.8	192.7	175.1	164.7
70°	132.4	143.7	162.7	192.3	228.6	240.8	215.2	186.1	167.7	153.6	144.0
72.5°	115.1	123.4	140.7	163.6	193.9	203.5	185.6	160.1	142.9	132.4	124.7
75°	87.7	94.6	105.8	124.3	145.2	150.8	137.4	121.5	109.9	102.4	96.4
77.5°	63.3	68.3	76.5	87.8	102.3	107.4	98.9	88.2	79.8	74.8	71.4
80°	47.8	51.9	58.7	68.1	76.8	79.7	74.6	66.5	60.6	57.8	55.0
82.5°	35.3	37.6	41.7	48.1	54.1	57.4	53.2	48.3	45.1	42.6	41.5
85°	17.8	19.1	21.0	23.4	27.1	28.5	26.8	25.6	23.7	22.2	22.2
87.5°	6.8	7.2	8.2	9.0	10.3	11.3	11.4	11.3	11.4	11.3	11.1
90°	2.0	3.3	4.6	6.0	7.5	9.3	11.0	12.8	14.5	15.1	15.6
92.5°	15.6	16.5	17.4	18.3	19.2	20.2	21.3	22.3	23.2	23.6	24.1
95°	36.6	37.6	38.6	39.5	40.4	41.6	42.6	43.7	44.8	45.3	45.8
97.5°	64.1	64.8	65.6	66.2	66.9	67.8	68.5	69.3	70.1	70.7	71.3
100°	83.1	83.9	84.7	85.5	86.3	86.9	87.6	88.3	88.9	89.4	89.8
102.5°	104.6	105.1	105.5	106.0	106.7	107.6	108.5	109.3	110.2	110.6	111.0
105°	136.4	136.7	137.0	137.2	137.9	139.2	140.4	141.6	142.8	142.8	142.8
107.5°	173.6	173.7	173.9	174.1	174.4	174.9	175.4	175.9	176.3	176.8	177.2
110°	197.0	197.2	197.5	197.7	198.0	198.3	198.5	198.9	199.1	199.7	200.2



TEST NUMBER: P332127-930

CATALOG NUMBER: S123DIW-S560D755U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	221.0	221.2	221.4	221.5	221.6	221.7	221.8	221.8	221.8	222.5	223.1
115°	257.6	258.0	258.4	258.8	258.9	258.6	258.4	258.0	257.8	258.0	258.0
117.5°	294.0	294.2	294.6	294.8	294.8	294.4	294.1	293.8	293.3	293.3	293.3
120°	317.3	318.1	318.9	319.8	319.8	319.1	318.5	317.8	317.1	317.0	316.8
122.5°	340.8	341.4	342.0	342.6	342.7	342.3	342.0	341.7	341.3	341.0	340.6
125°	376.8	377.2	377.6	378.1	378.1	377.8	377.6	377.2	377.0	376.5	375.9
127.5°	410.7	411.6	412.4	413.3	413.5	413.3	412.9	412.6	412.4	411.6	410.8
130°	433.2	434.2	435.3	436.3	436.8	436.3	435.9	435.5	435.1	434.6	434.1
132.5°	455.4	456.5	457.5	458.7	459.0	458.8	458.4	458.1	457.9	457.2	456.6
135°	489.2	490.0	490.8	491.5	492.0	491.8	491.6	491.5	491.4	490.8	490.3
137.5°	520.5	521.1	521.9	522.5	523.0	523.3	523.7	524.1	524.4	523.8	523.3
140°	542.3	543.0	543.6	544.3	544.7	544.9	544.9	545.1	545.3	545.1	544.9
142.5°	562.1	562.8	563.5	564.1	564.6	564.8	565.1	565.3	565.6	565.4	565.3
145°	592.7	593.0	593.2	593.5	593.9	594.3	594.7	595.1	595.5	595.3	595.2
147.5°	620.0	620.5	621.0	621.5	621.9	622.3	622.6	623.1	623.5	623.5	623.5
150°	638.7	639.0	639.3	639.5	639.8	640.0	640.3	640.6	640.8	640.8	640.8
152.5°	654.3	654.7	655.1	655.4	655.7	655.8	656.0	656.2	656.3	656.6	656.8
155°	678.4	678.4	678.4	678.4	678.4	678.6	678.7	678.8	679.0	679.6	680.0
157.5°	699.0	698.9	698.7	698.5	698.5	698.6	698.7	698.9	699.0	699.5	700.1
160°	712.0	711.8	711.4	711.2	711.0	711.0	711.0	711.0	711.0	711.8	712.4
162.5°	723.5	723.1	722.8	722.4	722.3	722.4	722.4	722.6	722.7	723.3	724.0
165°	738.5	738.1	737.7	737.3	737.0	737.0	737.0	737.0	737.0	737.8	738.7
167.5°	750.3	749.8	749.3	748.7	748.5	748.6	748.7	748.9	748.9	749.7	750.6
170°	757.1	756.6	756.0	755.5	755.2	755.2	755.2	755.2	755.2	756.2	757.1
172.5°	762.5	761.9	761.3	760.8	760.5	760.5	760.5	760.5	760.5	761.4	762.2
175°	768.0	767.4	767.0	766.4	766.1	766.1	766.1	766.1	766.1	767.0	767.8
177.5°	770.4	770.0	769.6	769.2	768.9	768.9	768.9	768.9	768.9	769.6	770.2
180°	770.4	770.4	770.4	770.4	770.4	770.4	770.4	770.4	770.4	770.4	770.4



TEST NUMBER: P332127-930

CATALOG NUMBER: S123DIW-S560D755U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	644.5	644.5	644.5	644.5	644.5	644.5	644.5
2.5°	678.2	678.5	681.2	683.2	682.2	683.5	684.0
5°	740.9	752.2	758.1	762.5	762.9	763.1	765.6
7.5°	830.0	842.0	850.8	864.2	868.2	872.8	871.5
10°	895.0	912.7	928.1	936.1	944.9	957.7	947.4
12.5°	955.6	987.2	1010.5	1023.0	1031.4	1033.9	1028.8
15°	1055.7	1097.0	1119.2	1118.5	1146.6	1158.8	1139.7
17.5°	1147.5	1185.6	1216.0	1231.7	1255.1	1260.3	1257.9
20°	1203.7	1245.3	1269.0	1295.8	1308.1	1319.0	1320.9
22.5°	1252.2	1289.5	1315.0	1337.3	1347.5	1352.7	1355.8
25°	1302.1	1331.5	1346.8	1354.5	1357.4	1356.7	1352.7
27.5°	1298.7	1300.9	1284.1	1267.5	1252.7	1236.0	1230.3
30°	1264.9	1238.7	1191.9	1165.3	1126.3	1095.4	1107.9
32.5°	1176.2	1124.1	1071.5	1013.4	965.4	951.8	938.0
35°	1003.9	912.1	858.4	796.0	770.9	746.0	728.8
37.5°	812.2	741.2	677.4	636.6	611.6	595.8	587.3
40°	702.3	638.2	585.8	552.7	533.6	515.8	513.3
42.5°	614.6	555.1	515.6	489.3	470.9	463.4	457.9
45°	503.4	461.8	435.3	416.5	404.4	399.7	393.5
47.5°	426.1	396.7	376.7	364.0	354.8	351.3	350.8
50°	382.9	358.5	343.8	333.8	326.6	325.4	320.4
52.5°	350.3	329.2	317.8	309.1	303.9	300.4	298.9
55°	304.1	290.1	279.8	274.8	270.8	267.3	267.3
57.5°	266.1	254.4	247.5	243.3	242.1	239.6	238.1
60°	242.6	232.6	227.3	223.6	221.1	221.4	218.6
62.5°	219.6	213.1	208.1	204.3	201.4	201.4	201.6
65°	187.0	182.1	178.3	177.1	175.2	173.0	173.6
67.5°	158.5	153.8	150.9	148.8	148.1	146.9	148.8
70°	138.0	134.6	132.4	130.5	129.9	130.2	131.8
72.5°	119.3	116.8	115.4	114.5	113.2	113.2	114.3
75°	93.7	91.8	90.6	89.6	89.3	89.3	89.3
77.5°	68.8	68.4	67.8	66.4	66.5	66.9	66.9
80°	54.3	53.4	53.1	52.4	51.5	50.9	52.4
82.5°	40.6	39.6	39.4	39.2	37.7	37.7	39.0
85°	21.9	21.0	21.2	21.0	21.0	20.6	20.6
87.5°	11.0	10.8	10.7	10.9	10.8	10.6	11.1
90°	16.1	16.7	17.0	17.4	17.6	17.9	18.2
92.5°	24.5	24.9	25.1	24.9	24.8	24.6	24.5
95°	46.4	47.0	47.2	47.2	47.2	47.2	47.2
97.5°	71.9	72.6	72.8	72.8	72.7	72.6	72.6
100°	90.2	90.6	90.9	91.2	91.5	91.7	92.0
102.5°	111.5	111.9	112.0	112.0	111.9	111.9	111.9
105°	142.8	142.8	142.9	143.2	143.5	143.7	144.1
107.5°	177.7	178.1	178.2	178.1	177.9	177.7	177.6
110°	200.7	201.2	201.4	201.1	200.8	200.6	200.3



TEST NUMBER: P332127-930

CATALOG NUMBER: S123DIW-S560D755U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	223.8	224.5	224.7	224.7	224.6	224.5	224.5
115°	258.2	258.4	258.4	258.2	258.0	258.0	257.8
117.5°	293.3	293.3	293.1	292.7	292.3	292.0	291.6
120°	316.7	316.6	316.3	316.1	315.8	315.5	315.3
122.5°	340.2	339.9	339.6	339.2	338.8	338.4	338.0
125°	375.4	374.9	374.3	373.8	373.2	372.7	372.2
127.5°	410.1	409.4	408.6	408.1	407.4	406.8	406.2
130°	433.5	432.9	432.2	431.3	430.3	429.4	428.4
132.5°	455.9	455.3	454.6	453.9	453.1	452.4	451.7
135°	489.8	489.3	488.9	488.5	488.3	488.0	487.7
137.5°	522.7	522.2	521.6	521.1	520.6	520.1	519.6
140°	544.9	544.7	544.1	543.2	542.3	541.4	540.4
142.5°	565.2	565.0	564.6	563.9	563.1	562.4	561.7
145°	595.1	594.9	594.6	594.0	593.5	593.0	592.5
147.5°	623.5	623.5	623.1	622.2	621.4	620.6	619.8
150°	640.8	640.8	640.4	639.6	638.9	638.1	637.2
152.5°	657.0	657.2	657.0	656.2	655.6	654.8	654.2
155°	680.6	681.1	680.9	680.0	679.1	678.1	677.2
157.5°	700.7	701.2	701.1	700.3	699.6	698.9	698.1
160°	713.1	713.7	713.8	713.3	712.7	712.2	711.7
162.5°	724.7	725.4	725.3	724.4	723.6	722.7	721.8
165°	739.5	740.3	740.2	739.3	738.3	737.4	736.5
167.5°	751.5	752.3	752.3	751.5	750.6	749.7	748.9
170°	758.1	759.0	759.0	758.1	757.1	756.2	755.2
172.5°	763.0	763.9	763.9	762.9	762.0	761.0	760.1
175°	768.5	769.3	769.3	768.3	767.4	766.5	765.5
177.5°	770.9	771.5	771.4	770.7	769.9	769.2	768.4
180°	770.4	770.4	770.4	770.4	770.4	770.4	770.4

(END OF REPORT)