

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332163-930

Luminaire Tested: **S123DIW-S775D1030U930-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332163-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIW-S775D1030U930-4F0-1E-UDD-A1  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1030 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5575.3 lumens  
Efficiency: N/A  
Efficacy: 106.0 lumens/watt  
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 52.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332163-930

CATALOG NUMBER: S123DIW-S775D1030U930-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P332163-930

CATALOG NUMBER: S123DIW-S775D1030U930-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	48				48
1	98	93	90	86	90	86	83	80	72	70	68	60	58	57	48	47	46				41	
2	89	82	76	71	82	75	70	66	64	60	57	53	50	48	43	41	39				35	
3	81	72	65	59	75	67	60	55	56	52	48	47	43	41	38	36	34				29	
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	34	31	29				25	
5	68	57	49	43	63	53	46	40	45	40	35	38	34	30	31	28	25				22	
6	63	51	43	37	58	47	40	35	41	35	31	34	30	27	28	25	22				20	
7	58	46	38	33	54	43	36	31	37	31	27	31	27	24	26	22	20				17	
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	23	20	18				16	
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	22	18	16				14	
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15				13	

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	9482	9482	9482	9482
5°	11309	9524	8440	9524
10°	14154	9475	7623	9475
15°	17361	9399	7096	9399
20°	20681	9279	6757	9279
25°	21960	9136	6682	9136
30°	18821	9028	6717	9028
35°	13090	8878	6787	8878
40°	9860	8702	6764	8702
45°	8187	8441	6680	8441
50°	7333	7906	6620	7906
55°	6855	7328	6536	7328
60°	6433	6725	6469	6725
65°	6044	6133	6260	6133
70°	5668	5454	5964	5454
75°	5078	4774	5465	4774
80°	4444	3918	4711	3918
85°	3483	2853	3162	2853



TEST NUMBER: P332163-930

CATALOG NUMBER: S123DIW-S775D1030U930-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	86.8	1.6
10°-20°	278.3	5.0
20°-30°	467.0	8.4
30°-40°	528.8	9.5
40°-50°	474.2	8.5
50°-60°	382.7	6.9
60°-70°	266.7	4.8
70°-80°	140.2	2.5
80°-90°	37.4	0.7
90°-100°	68.5	1.2
100°-110°	205.0	3.7
110°-120°	348.7	6.3
120°-130°	458.7	8.2
130°-140°	515.5	9.2
140°-150°	506.8	9.1
150°-160°	426.6	7.7
160°-170°	284.0	5.1
170°-180°	99.4	1.8
0°-30°	832.1	14.9
0°-40°	1360.9	24.4
0°-60°	2217.8	39.8
0°-90°	2662.0	47.7
90°-120°	622.2	11.2
90°-150°	2103.2	37.7
90°-180°	2913.0	52.2
0°-180°	5575.3	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	881	881	881	881	881	
5°	1047	881	781	881	1047	108
15°	1558	843	637	843	1558	450
25°	1849	769	563	769	1849	811
35°	996	676	516	676	996	647
45°	538	554	439	554	538	426
55°	365	390	348	390	365	328
65°	237	241	246	241	237	236
75°	122	115	131	115	122	131
85°	28	23	26	23	28	34
90°	25	1	25	1	25	13
95°	64	49	64	49	64	66
105°	197	186	197	186	197	209
115°	352	351	352	351	352	348
125°	508	514	508	514	508	454
135°	666	667	666	667	666	512
145°	809	809	809	809	809	505
155°	924	926	924	926	924	426
165°	1005	1008	1005	1008	1005	284
175°	1045	1049	1045	1049	1045	99
180°	1052	1052	1052	1052	1052	



TEST NUMBER: P332163-930

CATALOG NUMBER: S123DIW-S775D1030U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9
2.5°	934.9	934.3	932.5	933.9	931.2	927.4	927.1	923.7	913.7	913.1	910.4
5°	1046.6	1043.2	1042.8	1042.3	1036.3	1028.3	1012.8	1011.5	991.1	980.8	968.5
7.5°	1191.2	1192.9	1186.7	1181.3	1163.0	1151.0	1134.5	1113.4	1088.3	1062.7	1045.7
10°	1295.0	1309.0	1291.6	1279.6	1268.5	1247.6	1223.3	1192.9	1162.7	1127.2	1100.3
12.5°	1406.3	1413.2	1409.7	1398.5	1381.2	1349.4	1306.3	1272.8	1245.0	1185.9	1162.1
15°	1557.9	1584.0	1567.3	1528.8	1529.7	1499.4	1443.1	1381.2	1348.3	1296.7	1226.3
17.5°	1719.4	1722.6	1715.6	1683.6	1662.2	1620.6	1568.6	1509.3	1442.7	1380.1	1305.5
20°	1805.5	1802.9	1788.0	1771.3	1734.6	1702.2	1645.4	1579.2	1493.9	1432.4	1350.9
22.5°	1853.3	1849.0	1841.9	1828.0	1797.4	1762.6	1711.6	1639.3	1558.1	1473.4	1379.2
25°	1849.0	1854.6	1855.4	1851.5	1840.9	1820.0	1779.9	1722.2	1641.1	1532.3	1434.1
27.5°	1681.7	1689.5	1712.4	1732.6	1755.2	1778.2	1775.2	1746.5	1686.5	1592.6	1472.5
30°	1514.3	1497.3	1539.5	1592.9	1629.2	1693.2	1729.1	1731.2	1697.5	1616.8	1499.8
32.5°	1282.1	1301.0	1319.6	1385.3	1464.6	1536.5	1607.9	1665.3	1671.9	1618.2	1515.9
35°	996.2	1019.7	1053.9	1087.9	1173.4	1246.8	1372.2	1481.5	1568.6	1580.1	1517.4
37.5°	802.7	814.4	836.0	870.2	926.0	1013.1	1110.2	1248.3	1374.4	1468.3	1472.3
40°	701.7	705.2	729.4	755.5	800.7	872.5	959.9	1082.0	1233.1	1364.2	1418.8
42.5°	625.9	633.4	643.8	668.7	704.7	758.7	840.1	940.9	1079.5	1230.3	1337.2
45°	537.8	546.3	552.8	569.4	595.0	631.3	688.0	780.2	885.7	1041.5	1185.3
47.5°	479.6	480.3	485.0	497.6	515.0	542.3	582.4	641.6	738.4	864.7	1012.4
50°	437.9	444.7	446.5	456.2	469.9	490.0	523.3	573.6	653.1	764.0	899.8
52.5°	408.5	410.6	415.4	422.5	434.4	450.0	478.9	518.4	580.7	675.2	800.1
55°	365.3	365.3	370.1	375.6	382.5	396.5	415.7	444.7	492.1	565.6	668.9
57.5°	325.4	327.5	330.8	332.6	338.3	347.7	363.7	385.8	421.1	477.6	559.7
60°	298.8	302.6	302.2	305.6	310.7	318.0	331.7	349.6	381.2	426.4	495.5
62.5°	275.6	275.3	275.2	279.3	284.5	291.4	300.2	315.8	342.6	382.7	441.6
65°	237.3	236.4	239.5	242.0	243.7	248.8	255.7	269.3	287.2	317.2	362.8
67.5°	203.3	200.9	202.5	203.3	206.3	210.3	216.6	225.1	239.4	263.3	297.7
70°	180.1	178.0	177.6	178.4	181.0	183.9	188.7	196.7	210.0	229.2	254.4
72.5°	156.2	154.7	154.7	156.5	157.8	159.7	163.1	170.5	181.0	195.4	218.9
75°	122.1	122.1	122.1	122.5	123.8	125.5	128.1	131.9	140.0	150.3	166.0
77.5°	91.5	91.4	90.9	90.8	92.7	93.5	94.1	97.7	102.2	109.1	120.6
80°	71.7	69.5	70.4	71.7	72.6	73.0	74.3	75.1	79.0	82.8	90.9
82.5°	53.2	51.4	51.6	53.6	53.8	54.2	55.5	56.7	58.1	61.6	66.0
85°	28.2	28.2	28.6	28.6	29.0	28.6	29.8	30.3	30.3	32.4	35.0
87.5°	15.2	14.4	14.7	15.0	14.6	14.8	15.0	15.2	15.4	15.6	15.4
90°	24.8	24.4	24.1	23.6	23.3	22.7	22.0	21.3	20.5	19.8	17.4
92.5°	33.3	33.6	33.8	34.0	34.2	34.1	33.5	32.9	32.3	31.7	30.3
95°	64.4	64.4	64.4	64.4	64.4	64.1	63.3	62.6	61.9	61.1	59.7
97.5°	99.1	99.2	99.3	99.3	99.4	99.1	98.2	97.3	96.5	95.6	94.6
100°	125.6	125.1	124.8	124.4	124.1	123.6	123.1	122.5	122.0	121.4	120.5
102.5°	152.6	152.7	152.8	152.9	153.0	152.7	152.1	151.6	151.1	150.5	149.3
105°	196.6	196.2	195.8	195.5	195.1	194.9	194.9	194.9	194.9	194.9	193.3
107.5°	242.3	242.6	242.8	243.0	243.2	243.0	242.5	241.9	241.2	240.7	240.0
110°	273.4	273.8	274.1	274.5	274.8	274.7	273.9	273.2	272.5	271.7	271.4



TEST NUMBER: P332163-930

CATALOG NUMBER: S123DIW-S775D1030U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	306.5	306.6	306.6	306.6	306.7	306.3	305.4	304.6	303.7	302.8	302.7
115°	351.9	352.0	352.2	352.5	352.6	352.6	352.5	352.2	352.0	351.9	352.2
117.5°	397.9	398.4	399.0	399.5	400.0	400.3	400.3	400.4	400.4	400.5	400.9
120°	430.3	430.7	431.0	431.5	431.8	432.1	432.3	432.4	432.6	432.8	433.7
122.5°	461.4	461.9	462.4	462.9	463.4	464.0	464.4	464.9	465.4	465.9	466.4
125°	508.0	508.7	509.5	510.2	510.9	511.7	512.4	513.1	513.9	514.6	514.9
127.5°	554.4	555.2	556.1	556.9	557.7	558.7	559.8	560.8	561.8	562.8	563.2
130°	584.8	586.1	587.3	588.6	590.0	590.9	591.7	592.4	593.1	593.9	594.4
132.5°	616.5	617.5	618.5	619.5	620.5	621.4	622.3	623.2	624.0	624.9	625.3
135°	665.8	666.1	666.5	666.8	667.2	667.7	668.5	669.2	669.9	670.7	670.9
137.5°	709.2	709.9	710.6	711.3	712.0	712.7	713.5	714.3	715.0	715.8	715.3
140°	737.6	738.9	740.2	741.4	742.7	743.5	743.6	743.9	744.0	744.2	744.0
142.5°	766.7	767.7	768.7	769.6	770.6	771.3	771.4	771.6	771.8	772.0	771.7
145°	808.6	809.3	810.1	810.8	811.5	812.0	812.2	812.4	812.6	812.8	812.2
147.5°	846.0	847.1	848.2	849.3	850.4	850.9	850.9	850.9	850.9	850.9	850.4
150°	869.8	870.9	872.0	873.1	874.2	874.7	874.7	874.7	874.7	874.7	874.3
152.5°	892.9	893.8	894.8	895.8	896.7	897.1	896.7	896.4	896.2	895.9	895.7
155°	924.3	925.6	926.8	928.1	929.4	929.7	929.0	928.2	927.5	926.8	926.6
157.5°	952.8	953.9	955.0	955.9	957.0	957.1	956.3	955.5	954.8	954.0	953.9
160°	971.3	972.1	972.8	973.5	974.3	974.2	973.3	972.4	971.4	970.5	970.5
162.5°	985.2	986.4	987.6	988.8	989.9	990.1	989.1	988.2	987.3	986.4	986.3
165°	1005.3	1006.5	1007.8	1009.1	1010.4	1010.5	1009.3	1008.3	1007.1	1006.1	1006.1
167.5°	1022.2	1023.4	1024.5	1025.6	1026.8	1026.8	1025.6	1024.5	1023.4	1022.2	1022.1
170°	1030.9	1032.1	1033.4	1034.7	1036.0	1036.0	1034.7	1033.4	1032.1	1030.9	1030.9
172.5°	1037.5	1038.7	1040.0	1041.3	1042.6	1042.7	1041.5	1040.4	1039.3	1038.1	1038.1
175°	1044.9	1046.2	1047.4	1048.7	1050.0	1050.1	1049.0	1047.9	1046.8	1045.7	1045.7
177.5°	1048.9	1049.9	1050.9	1051.9	1053.0	1053.0	1052.1	1051.2	1050.4	1049.5	1049.5
180°	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5



TEST NUMBER: P332163-930

CATALOG NUMBER: S123DIW-S775D1030U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9
2.5°	908.2	905.6	902.8	898.1	894.0	888.1	886.4	884.4	878.2	872.8	868.7
5°	963.8	953.5	938.6	925.0	913.9	898.9	890.4	881.4	868.6	857.0	847.7
7.5°	1021.8	1001.7	978.4	953.3	929.9	907.4	889.2	873.0	855.1	838.1	824.9
10°	1067.9	1038.9	1006.5	971.4	941.6	912.6	888.2	866.9	843.8	823.8	807.1
12.5°	1120.5	1077.5	1032.7	990.3	954.9	914.6	885.2	858.0	831.8	807.7	789.0
15°	1182.8	1128.1	1075.1	1016.7	963.0	912.6	877.6	843.4	813.1	788.3	764.4
17.5°	1239.4	1177.5	1107.7	1036.7	971.8	912.1	863.1	824.4	786.5	756.3	732.5
20°	1271.5	1201.1	1122.1	1048.3	976.6	910.0	856.2	810.1	769.2	737.1	710.2
22.5°	1299.2	1216.8	1135.1	1056.1	976.2	904.5	843.6	796.1	751.7	720.4	691.8
25°	1327.9	1229.2	1147.3	1054.7	965.5	891.2	822.9	769.2	724.7	688.0	658.6
27.5°	1352.4	1228.4	1131.1	1031.5	948.6	874.2	801.2	743.6	696.4	656.6	626.6
30°	1368.8	1230.1	1114.4	1015.9	932.2	855.3	784.5	726.4	676.9	636.4	608.2
32.5°	1379.1	1229.1	1099.1	994.0	906.2	838.3	766.4	706.3	655.4	615.6	588.4
35°	1385.0	1221.6	1072.6	948.8	864.3	798.2	738.0	675.6	622.3	585.1	554.5
37.5°	1373.1	1205.7	1041.9	905.3	812.8	747.6	697.0	643.9	592.9	552.0	525.5
40°	1354.3	1195.6	1018.0	874.6	777.2	714.5	671.4	619.3	568.9	530.1	505.3
42.5°	1318.4	1174.7	991.6	840.4	740.4	677.6	638.0	594.4	546.7	510.3	485.6
45°	1230.9	1129.4	952.3	789.2	685.9	621.0	586.0	554.5	511.4	475.9	454.5
47.5°	1109.5	1061.2	895.2	735.2	629.1	566.6	530.3	504.8	473.4	444.7	424.3
50°	1025.2	1005.2	856.6	698.3	591.2	530.1	495.1	472.1	449.5	420.9	402.1
52.5°	927.9	940.3	811.5	660.1	552.5	492.5	459.6	441.3	420.8	397.3	380.9
55°	790.9	835.7	733.7	595.8	495.1	437.9	406.8	390.5	378.6	361.1	347.0
57.5°	662.6	719.7	649.5	529.7	438.7	389.4	359.5	341.8	334.1	325.0	313.9
60°	586.4	642.8	589.5	485.3	400.8	353.8	327.3	312.4	304.8	298.3	288.9
62.5°	518.5	575.5	530.7	440.3	363.5	320.0	297.0	282.4	276.4	273.0	265.1
65°	425.1	474.2	444.3	370.1	310.3	271.9	250.9	240.8	235.2	233.9	228.8
67.5°	346.0	383.4	361.6	307.0	259.9	226.7	209.0	200.2	196.0	195.6	191.8
70°	294.1	329.1	312.4	262.9	222.4	196.3	181.0	173.3	170.7	170.3	168.2
72.5°	253.8	278.2	265.0	223.6	192.3	168.7	157.4	149.4	146.5	147.1	145.6
75°	187.8	206.2	198.4	169.9	144.7	129.3	119.9	114.8	112.3	113.6	111.9
77.5°	135.1	146.8	139.8	120.0	104.5	93.4	86.5	83.3	81.0	81.0	80.1
80°	102.0	108.8	105.0	93.0	80.2	70.8	65.3	63.2	61.9	61.5	61.1
82.5°	72.6	78.4	73.9	65.7	57.0	51.4	48.3	45.4	44.5	44.8	44.3
85°	36.7	38.8	37.1	32.0	28.6	26.0	24.3	23.1	22.2	22.6	21.8
87.5°	15.7	15.5	14.0	12.2	11.2	9.8	9.4	8.4	8.1	8.4	8.4
90°	15.1	12.6	10.3	8.2	6.4	4.5	2.7	0.8	2.7	4.5	6.4
92.5°	29.0	27.6	26.3	24.9	23.7	22.5	21.2	20.0	21.2	22.5	23.7
95°	58.2	56.7	55.3	53.9	52.6	51.3	50.0	48.8	50.0	51.3	52.6
97.5°	93.5	92.5	91.4	90.4	89.4	88.5	87.5	86.6	87.5	88.5	89.4
100°	119.6	118.7	117.7	116.8	115.6	114.5	113.4	112.3	113.4	114.5	115.6
102.5°	148.1	146.8	145.6	144.7	144.1	143.4	142.8	142.1	142.8	143.4	144.1
105°	191.6	190.0	188.3	187.4	186.9	186.6	186.2	185.9	186.2	186.6	186.9
107.5°	239.4	238.7	238.1	237.6	237.4	237.2	236.9	236.8	236.9	237.2	237.4
110°	271.0	270.7	270.3	269.9	269.5	269.2	268.8	268.5	268.8	269.2	269.5





TEST NUMBER: P332163-930

CATALOG NUMBER: S123DIW-S775D1030U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	302.6	302.6	302.5	302.4	302.1	301.9	301.7	301.5	301.7	301.9	302.1
115°	352.6	352.9	353.4	353.3	352.7	352.1	351.6	351.1	351.6	352.1	352.7
117.5°	401.4	401.9	402.4	402.4	402.0	401.7	401.3	401.0	401.3	401.7	402.0
120°	434.6	435.5	436.5	436.4	435.3	434.2	433.1	432.0	433.1	434.2	435.3
122.5°	466.8	467.3	467.7	467.6	466.8	466.0	465.2	464.4	465.2	466.0	466.8
125°	515.4	515.7	516.1	516.0	515.4	514.9	514.3	513.8	514.3	514.9	515.4
127.5°	563.6	564.0	564.4	564.0	562.9	561.7	560.5	559.4	560.5	561.7	562.9
130°	595.0	595.6	596.1	595.7	594.2	592.7	591.3	589.8	591.3	592.7	594.2
132.5°	625.7	626.1	626.6	626.1	624.6	623.1	621.6	620.1	621.6	623.1	624.6
135°	671.1	671.2	671.4	671.0	669.8	668.8	667.6	666.6	667.6	668.8	669.8
137.5°	714.9	714.4	713.9	713.2	712.2	711.3	710.5	709.6	710.5	711.3	712.2
140°	743.9	743.6	743.5	742.9	742.0	741.1	740.2	739.2	740.2	741.1	742.0
142.5°	771.3	770.9	770.6	770.1	769.1	768.2	767.3	766.4	767.3	768.2	769.1
145°	811.7	811.1	810.6	810.1	809.8	809.3	809.0	808.6	809.0	809.3	809.8
147.5°	849.9	849.4	848.9	848.3	847.7	846.9	846.3	845.6	846.3	846.9	847.7
150°	874.0	873.6	873.3	872.9	872.5	872.1	871.8	871.4	871.8	872.1	872.5
152.5°	895.4	895.2	895.0	894.6	894.1	893.6	893.1	892.6	893.1	893.6	894.1
155°	926.4	926.2	926.0	925.9	925.9	925.9	925.9	925.9	925.9	925.9	925.9
157.5°	953.7	953.6	953.4	953.5	953.7	953.9	954.1	954.4	954.1	953.9	953.7
160°	970.5	970.5	970.5	970.7	971.1	971.4	971.8	972.2	971.8	971.4	971.1
162.5°	986.1	985.9	985.8	986.0	986.5	987.0	987.6	988.1	987.6	987.0	986.5
165°	1006.1	1006.1	1006.1	1006.3	1006.9	1007.5	1008.0	1008.5	1008.0	1007.5	1006.9
167.5°	1022.0	1021.8	1021.7	1022.0	1022.7	1023.4	1024.2	1024.9	1024.2	1023.4	1022.7
170°	1030.9	1030.9	1030.9	1031.2	1031.9	1032.7	1033.4	1034.1	1033.4	1032.7	1031.9
172.5°	1038.1	1038.1	1038.1	1038.4	1039.2	1039.9	1040.6	1041.4	1040.6	1039.9	1039.2
175°	1045.7	1045.7	1045.7	1046.1	1046.8	1047.6	1048.3	1049.0	1048.3	1047.6	1046.8
177.5°	1049.5	1049.5	1049.5	1049.8	1050.4	1051.0	1051.6	1052.1	1051.6	1051.0	1050.4
180°	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5



TEST NUMBER: P332163-930

CATALOG NUMBER: S123DIW-S775D1030U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9
2.5°	866.3	863.9	860.5	855.3	851.3	844.7	844.7	845.8	845.8	845.5	844.7
5°	840.0	833.6	825.9	816.9	807.6	798.2	796.5	793.0	790.5	788.8	786.6
7.5°	812.3	800.9	789.7	777.1	765.7	756.3	749.7	744.2	740.7	736.9	734.3
10°	793.4	779.3	766.1	752.9	738.4	726.9	719.7	714.5	710.7	707.3	705.6
12.5°	771.3	755.1	740.5	728.0	712.1	700.3	693.3	691.0	686.4	679.2	675.5
15°	738.8	723.9	706.4	687.2	679.5	665.0	656.9	653.1	650.4	644.9	643.2
17.5°	711.1	691.5	671.9	657.5	643.3	631.5	627.0	622.2	618.8	614.2	612.9
20°	688.9	671.4	653.5	638.1	623.1	610.3	606.5	603.1	599.7	597.5	595.8
22.5°	666.3	648.9	634.0	619.6	603.7	595.3	591.2	587.4	585.0	583.6	581.9
25°	634.7	619.3	602.7	589.9	577.1	571.5	568.9	566.8	565.1	563.0	562.6
27.5°	606.3	589.6	576.1	564.2	555.0	550.3	547.9	546.8	547.2	548.0	548.5
30°	585.1	569.8	558.7	548.5	540.0	535.7	535.2	535.2	537.0	537.4	538.3
32.5°	565.7	553.1	542.0	532.1	525.6	522.7	524.3	524.3	525.7	526.8	528.3
35°	537.4	526.3	517.7	509.2	503.7	504.9	505.8	506.6	508.7	511.4	513.1
37.5°	510.3	500.7	491.8	485.1	482.6	484.9	486.9	488.7	491.2	493.2	494.9
40°	490.8	483.6	475.1	469.0	469.9	471.2	473.0	475.1	477.2	478.5	480.2
42.5°	472.7	465.1	458.7	453.7	454.9	456.6	457.5	458.7	461.1	463.4	464.5
45°	445.2	439.2	433.3	430.2	431.1	431.9	432.8	434.1	436.2	437.9	438.4
47.5°	414.2	410.0	406.0	403.1	404.5	404.1	405.2	408.0	408.6	409.7	412.1
50°	394.4	390.5	385.9	385.0	385.0	385.0	385.4	388.8	388.8	390.5	392.2
52.5°	372.5	370.1	367.0	365.5	364.8	364.8	366.6	368.4	369.0	371.5	373.2
55°	340.1	337.6	335.1	333.8	332.9	333.8	337.2	338.0	340.1	341.4	342.8
57.5°	306.5	304.5	302.5	301.7	301.6	302.7	304.6	307.1	307.7	311.6	313.6
60°	284.3	281.3	279.6	279.6	278.8	282.6	281.7	286.0	286.8	289.3	292.4
62.5°	261.4	257.4	256.7	256.7	257.9	259.0	260.2	262.0	264.3	267.5	269.9
65°	224.5	222.4	225.3	224.9	224.0	226.7	226.7	228.8	231.3	234.3	239.0
67.5°	189.6	188.5	188.7	188.7	190.0	191.5	192.7	194.5	197.6	200.8	203.8
70°	166.0	167.3	165.2	166.9	168.2	168.6	169.4	172.0	175.5	177.6	181.0
72.5°	143.2	143.1	143.3	144.0	145.3	146.0	146.9	149.9	153.6	155.4	158.1
75°	110.1	109.7	111.0	111.0	113.1	114.0	114.8	116.1	119.5	122.1	124.2
77.5°	80.4	81.0	80.6	82.1	81.5	81.7	84.3	85.6	85.9	91.0	92.1
80°	60.6	61.5	61.9	62.3	62.8	61.9	64.9	66.1	66.1	69.1	71.3
82.5°	43.5	44.0	45.2	45.6	45.7	46.6	46.8	47.7	48.8	50.1	52.8
85°	21.8	23.1	23.5	23.1	23.5	22.6	23.9	24.3	24.8	24.8	24.8
87.5°	8.5	9.2	9.4	10.2	10.4	11.2	11.3	10.8	10.9	12.1	10.8
90°	8.2	10.3	12.6	15.1	17.4	19.8	20.5	21.3	22.0	22.7	23.3
92.5°	24.9	26.3	27.6	29.0	30.3	31.7	32.3	32.9	33.5	34.1	34.2
95°	53.9	55.3	56.7	58.2	59.7	61.1	61.9	62.6	63.3	64.1	64.4
97.5°	90.4	91.4	92.5	93.5	94.6	95.6	96.5	97.3	98.2	99.1	99.4
100°	116.8	117.7	118.7	119.6	120.5	121.4	122.0	122.5	123.1	123.6	124.1
102.5°	144.7	145.6	146.8	148.1	149.3	150.5	151.1	151.6	152.1	152.7	153.0
105°	187.4	188.3	190.0	191.6	193.3	194.9	194.9	194.9	194.9	194.9	195.1
107.5°	237.6	238.1	238.7	239.4	240.0	240.7	241.2	241.9	242.5	243.0	243.2
110°	269.9	270.3	270.7	271.0	271.4	271.7	272.5	273.2	273.9	274.7	274.8



TEST NUMBER: P332163-930

CATALOG NUMBER: S123DIW-S775D1030U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	302.4	302.5	302.6	302.6	302.7	302.8	303.7	304.6	305.4	306.3	306.7
115°	353.3	353.4	352.9	352.6	352.2	351.9	352.0	352.2	352.5	352.6	352.6
117.5°	402.4	402.4	401.9	401.4	400.9	400.5	400.4	400.4	400.3	400.3	400.0
120°	436.4	436.5	435.5	434.6	433.7	432.8	432.6	432.4	432.3	432.1	431.8
122.5°	467.6	467.7	467.3	466.8	466.4	465.9	465.4	464.9	464.4	464.0	463.4
125°	516.0	516.1	515.7	515.4	514.9	514.6	513.9	513.1	512.4	511.7	510.9
127.5°	564.0	564.4	564.0	563.6	563.2	562.8	561.8	560.8	559.8	558.7	557.7
130°	595.7	596.1	595.6	595.0	594.4	593.9	593.1	592.4	591.7	590.9	590.0
132.5°	626.1	626.6	626.1	625.7	625.3	624.9	624.0	623.2	622.3	621.4	620.5
135°	671.0	671.4	671.2	671.1	670.9	670.7	669.9	669.2	668.5	667.7	667.2
137.5°	713.2	713.9	714.4	714.9	715.3	715.8	715.0	714.3	713.5	712.7	712.0
140°	742.9	743.5	743.6	743.9	744.0	744.2	744.0	743.9	743.6	743.5	742.7
142.5°	770.1	770.6	770.9	771.3	771.7	772.0	771.8	771.6	771.4	771.3	770.6
145°	810.1	810.6	811.1	811.7	812.2	812.8	812.6	812.4	812.2	812.0	811.5
147.5°	848.3	848.9	849.4	849.9	850.4	850.9	850.9	850.9	850.9	850.9	850.4
150°	872.9	873.3	873.6	874.0	874.3	874.7	874.7	874.7	874.7	874.7	874.2
152.5°	894.6	895.0	895.2	895.4	895.7	895.9	896.2	896.4	896.7	897.1	896.7
155°	925.9	926.0	926.2	926.4	926.6	926.8	927.5	928.2	929.0	929.7	929.4
157.5°	953.5	953.4	953.6	953.7	953.9	954.0	954.8	955.5	956.3	957.1	957.0
160°	970.7	970.5	970.5	970.5	970.5	970.5	971.4	972.4	973.3	974.2	974.3
162.5°	986.0	985.8	985.9	986.1	986.3	986.4	987.3	988.2	989.1	990.1	989.9
165°	1006.3	1006.1	1006.1	1006.1	1006.1	1006.1	1007.1	1008.3	1009.3	1010.5	1010.4
167.5°	1022.0	1021.7	1021.8	1022.0	1022.1	1022.2	1023.4	1024.5	1025.6	1026.8	1026.8
170°	1031.2	1030.9	1030.9	1030.9	1030.9	1030.9	1032.1	1033.4	1034.7	1036.0	1036.0
172.5°	1038.4	1038.1	1038.1	1038.1	1038.1	1038.1	1039.3	1040.4	1041.5	1042.7	1042.6
175°	1046.1	1045.7	1045.7	1045.7	1045.7	1045.7	1046.8	1047.9	1049.0	1050.1	1050.0
177.5°	1049.8	1049.5	1049.5	1049.5	1049.5	1049.5	1050.4	1051.2	1052.1	1053.0	1053.0
180°	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5



TEST NUMBER: P332163-930

CATALOG NUMBER: S123DIW-S775D1030U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9
2.5°	842.4	842.0	844.4	842.7	844.4	842.0	842.4	844.7	845.5	845.8	845.8
5°	784.1	785.4	781.1	781.1	781.1	785.4	784.1	786.6	788.8	790.5	793.0
7.5°	732.1	730.3	730.4	728.1	730.4	730.3	732.1	734.3	736.9	740.7	744.2
10°	700.4	697.9	697.0	697.4	697.0	697.9	700.4	705.6	707.3	710.7	714.5
12.5°	674.1	673.6	668.0	668.1	668.0	673.6	674.1	675.5	679.2	686.4	691.0
15°	643.2	635.1	634.2	636.8	634.2	635.1	643.2	643.2	644.9	650.4	653.1
17.5°	612.2	608.0	608.2	606.9	608.2	608.0	612.2	612.9	614.2	618.8	622.2
20°	595.8	593.3	592.9	589.9	592.9	593.3	595.8	595.8	597.5	599.7	603.1
22.5°	580.8	580.0	580.2	576.9	580.2	580.0	580.8	581.9	583.6	585.0	587.4
25°	562.1	564.3	562.6	562.6	562.6	564.3	562.1	562.6	563.0	565.1	566.8
27.5°	549.5	549.4	548.5	548.5	548.5	549.4	549.5	548.5	548.0	547.2	546.8
30°	540.0	539.5	540.4	540.4	540.4	539.5	540.0	538.3	537.4	537.0	535.2
32.5°	530.4	531.0	531.2	531.5	531.2	531.0	530.4	528.3	526.8	525.7	524.3
35°	515.6	516.0	517.3	516.5	517.3	516.0	515.6	513.1	511.4	508.7	506.6
37.5°	495.6	497.6	497.2	497.8	497.2	497.6	495.6	494.9	493.2	491.2	488.7
40°	480.6	481.9	481.4	481.4	481.4	481.9	480.6	480.2	478.5	477.2	475.1
42.5°	465.2	466.2	465.0	464.4	465.0	466.2	465.2	464.5	463.4	461.1	458.7
45°	440.0	439.2	440.5	438.8	440.5	439.2	440.0	438.4	437.9	436.2	434.1
47.5°	411.9	412.7	413.1	414.3	413.1	412.7	411.9	412.1	409.7	408.6	408.0
50°	393.1	395.7	395.7	395.3	395.7	395.7	393.1	392.2	390.5	388.8	388.8
52.5°	374.6	375.9	377.6	377.5	377.6	375.9	374.6	373.2	371.5	369.0	368.4
55°	346.2	347.0	347.9	348.3	347.9	347.0	346.2	342.8	341.4	340.1	338.0
57.5°	316.6	316.3	318.3	318.9	318.3	316.3	316.6	313.6	311.6	307.7	307.1
60°	295.8	295.8	299.2	300.5	299.2	295.8	295.8	292.4	289.3	286.8	286.0
62.5°	273.6	275.0	278.3	276.5	278.3	275.0	273.6	269.9	267.5	264.3	262.0
65°	241.2	244.6	244.2	245.8	244.2	244.6	241.2	239.0	234.3	231.3	228.8
67.5°	207.2	209.4	212.5	212.7	212.5	209.4	207.2	203.8	200.8	197.6	194.5
70°	184.4	186.5	188.3	189.5	188.3	186.5	184.4	181.0	177.6	175.5	172.0
72.5°	162.2	163.3	167.4	165.6	167.4	163.3	162.2	158.1	155.4	153.6	149.9
75°	127.2	130.2	132.7	131.4	132.7	130.2	127.2	124.2	122.1	119.5	116.1
77.5°	94.1	97.0	98.2	97.2	98.2	97.0	94.1	92.1	91.0	85.9	85.6
80°	74.3	73.9	76.4	76.0	76.4	73.9	74.3	71.3	69.1	66.1	66.1
82.5°	54.5	54.1	55.2	55.5	55.2	54.1	54.5	52.8	50.1	48.8	47.7
85°	26.5	27.7	26.0	25.6	26.0	27.7	26.5	24.8	24.8	24.8	24.3
87.5°	10.8	10.9	10.7	10.4	10.7	10.9	10.8	10.8	12.1	10.9	10.8
90°	23.6	24.1	24.4	24.8	24.4	24.1	23.6	23.3	22.7	22.0	21.3
92.5°	34.0	33.8	33.6	33.3	33.6	33.8	34.0	34.2	34.1	33.5	32.9
95°	64.4	64.4	64.4	64.4	64.4	64.4	64.4	64.4	64.1	63.3	62.6
97.5°	99.3	99.3	99.2	99.1	99.2	99.3	99.3	99.4	99.1	98.2	97.3
100°	124.4	124.8	125.1	125.6	125.1	124.8	124.4	124.1	123.6	123.1	122.5
102.5°	152.9	152.8	152.7	152.6	152.7	152.8	152.9	153.0	152.7	152.1	151.6
105°	195.5	195.8	196.2	196.6	196.2	195.8	195.5	195.1	194.9	194.9	194.9
107.5°	243.0	242.8	242.6	242.3	242.6	242.8	243.0	243.2	243.0	242.5	241.9
110°	274.5	274.1	273.8	273.4	273.8	274.1	274.5	274.8	274.7	273.9	273.2



TEST NUMBER: P332163-930

CATALOG NUMBER: S123DIW-S775D1030U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	306.6	306.6	306.6	306.5	306.6	306.6	306.6	306.7	306.3	305.4	304.6
115°	352.5	352.2	352.0	351.9	352.0	352.2	352.5	352.6	352.6	352.5	352.2
117.5°	399.5	399.0	398.4	397.9	398.4	399.0	399.5	400.0	400.3	400.3	400.4
120°	431.5	431.0	430.7	430.3	430.7	431.0	431.5	431.8	432.1	432.3	432.4
122.5°	462.9	462.4	461.9	461.4	461.9	462.4	462.9	463.4	464.0	464.4	464.9
125°	510.2	509.5	508.7	508.0	508.7	509.5	510.2	510.9	511.7	512.4	513.1
127.5°	556.9	556.1	555.2	554.4	555.2	556.1	556.9	557.7	558.7	559.8	560.8
130°	588.6	587.3	586.1	584.8	586.1	587.3	588.6	590.0	590.9	591.7	592.4
132.5°	619.5	618.5	617.5	616.5	617.5	618.5	619.5	620.5	621.4	622.3	623.2
135°	666.8	666.5	666.1	665.8	666.1	666.5	666.8	667.2	667.7	668.5	669.2
137.5°	711.3	710.6	709.9	709.2	709.9	710.6	711.3	712.0	712.7	713.5	714.3
140°	741.4	740.2	738.9	737.6	738.9	740.2	741.4	742.7	743.5	743.6	743.9
142.5°	769.6	768.7	767.7	766.7	767.7	768.7	769.6	770.6	771.3	771.4	771.6
145°	810.8	810.1	809.3	808.6	809.3	810.1	810.8	811.5	812.0	812.2	812.4
147.5°	849.3	848.2	847.1	846.0	847.1	848.2	849.3	850.4	850.9	850.9	850.9
150°	873.1	872.0	870.9	869.8	870.9	872.0	873.1	874.2	874.7	874.7	874.7
152.5°	895.8	894.8	893.8	892.9	893.8	894.8	895.8	896.7	897.1	896.7	896.4
155°	928.1	926.8	925.6	924.3	925.6	926.8	928.1	929.4	929.7	929.0	928.2
157.5°	955.9	955.0	953.9	952.8	953.9	955.0	955.9	957.0	957.1	956.3	955.5
160°	973.5	972.8	972.1	971.3	972.1	972.8	973.5	974.3	974.2	973.3	972.4
162.5°	988.8	987.6	986.4	985.2	986.4	987.6	988.8	989.9	990.1	989.1	988.2
165°	1009.1	1007.8	1006.5	1005.3	1006.5	1007.8	1009.1	1010.4	1010.5	1009.3	1008.3
167.5°	1025.6	1024.5	1023.4	1022.2	1023.4	1024.5	1025.6	1026.8	1026.8	1025.6	1024.5
170°	1034.7	1033.4	1032.1	1030.9	1032.1	1033.4	1034.7	1036.0	1036.0	1034.7	1033.4
172.5°	1041.3	1040.0	1038.7	1037.5	1038.7	1040.0	1041.3	1042.6	1042.7	1041.5	1040.4
175°	1048.7	1047.4	1046.2	1044.9	1046.2	1047.4	1048.7	1050.0	1050.1	1049.0	1047.9
177.5°	1051.9	1050.9	1049.9	1048.9	1049.9	1050.9	1051.9	1053.0	1053.0	1052.1	1051.2
180°	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5



TEST NUMBER: P332163-930

CATALOG NUMBER: S123DIW-S775D1030U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9
2.5°	844.7	844.7	851.3	855.3	860.5	863.9	866.3	868.7	872.8	878.2	884.4
5°	796.5	798.2	807.6	816.9	825.9	833.6	840.0	847.7	857.0	868.6	881.4
7.5°	749.7	756.3	765.7	777.1	789.7	800.9	812.3	824.9	838.1	855.1	873.0
10°	719.7	726.9	738.4	752.9	766.1	779.3	793.4	807.1	823.8	843.8	866.9
12.5°	693.3	700.3	712.1	728.0	740.5	755.1	771.3	789.0	807.7	831.8	858.0
15°	656.9	665.0	679.5	687.2	706.4	723.9	738.8	764.4	788.3	813.1	843.4
17.5°	627.0	631.5	643.3	657.5	671.9	691.5	711.1	732.5	756.3	786.5	824.4
20°	606.5	610.3	623.1	638.1	653.5	671.4	688.9	710.2	737.1	769.2	810.1
22.5°	591.2	595.3	603.7	619.6	634.0	648.9	666.3	691.8	720.4	751.7	796.1
25°	568.9	571.5	577.1	589.9	602.7	619.3	634.7	658.6	688.0	724.7	769.2
27.5°	547.9	550.3	555.0	564.2	576.1	589.6	606.3	626.6	656.6	696.4	743.6
30°	535.2	535.7	540.0	548.5	558.7	569.8	585.1	608.2	636.4	676.9	726.4
32.5°	524.3	522.7	525.6	532.1	542.0	553.1	565.7	588.4	615.6	655.4	706.3
35°	505.8	504.9	503.7	509.2	517.7	526.3	537.4	554.5	585.1	622.3	675.6
37.5°	486.9	484.9	482.6	485.1	491.8	500.7	510.3	525.5	552.0	592.9	643.9
40°	473.0	471.2	469.9	469.0	475.1	483.6	490.8	505.3	530.1	568.9	619.3
42.5°	457.5	456.6	454.9	453.7	458.7	465.1	472.7	485.6	510.3	546.7	594.4
45°	432.8	431.9	431.1	430.2	433.3	439.2	445.2	454.5	475.9	511.4	554.5
47.5°	405.2	404.1	404.5	403.1	406.0	410.0	414.2	424.3	444.7	473.4	504.8
50°	385.4	385.0	385.0	385.0	385.9	390.5	394.4	402.1	420.9	449.5	472.1
52.5°	366.6	364.8	364.8	365.5	367.0	370.1	372.5	380.9	397.3	420.8	441.3
55°	337.2	333.8	332.9	333.8	335.1	337.6	340.1	347.0	361.1	378.6	390.5
57.5°	304.6	302.7	301.6	301.7	302.5	304.5	306.5	313.9	325.0	334.1	341.8
60°	281.7	282.6	278.8	279.6	279.6	281.3	284.3	288.9	298.3	304.8	312.4
62.5°	260.2	259.0	257.9	256.7	256.7	257.4	261.4	265.1	273.0	276.4	282.4
65°	226.7	226.7	224.0	224.9	225.3	222.4	224.5	228.8	233.9	235.2	240.8
67.5°	192.7	191.5	190.0	188.7	188.7	188.5	189.6	191.8	195.6	196.0	200.2
70°	169.4	168.6	168.2	166.9	165.2	167.3	166.0	168.2	170.3	170.7	173.3
72.5°	146.9	146.0	145.3	144.0	143.3	143.1	143.2	145.6	147.1	146.5	149.4
75°	114.8	114.0	113.1	111.0	111.0	109.7	110.1	111.9	113.6	112.3	114.8
77.5°	84.3	81.7	81.5	82.1	80.6	81.0	80.4	80.1	81.0	81.0	83.3
80°	64.9	61.9	62.8	62.3	61.9	61.5	60.6	61.1	61.5	61.9	63.2
82.5°	46.8	46.6	45.7	45.6	45.2	44.0	43.5	44.3	44.8	44.5	45.4
85°	23.9	22.6	23.5	23.1	23.5	23.1	21.8	21.8	22.6	22.2	23.1
87.5°	11.3	11.2	10.4	10.2	9.4	9.2	8.5	8.4	8.4	8.1	8.4
90°	20.5	19.8	17.4	15.1	12.6	10.3	8.2	6.4	4.5	2.7	0.8
92.5°	32.3	31.7	30.3	29.0	27.6	26.3	24.9	23.7	22.5	21.2	20.0
95°	61.9	61.1	59.7	58.2	56.7	55.3	53.9	52.6	51.3	50.0	48.8
97.5°	96.5	95.6	94.6	93.5	92.5	91.4	90.4	89.4	88.5	87.5	86.6
100°	122.0	121.4	120.5	119.6	118.7	117.7	116.8	115.6	114.5	113.4	112.3
102.5°	151.1	150.5	149.3	148.1	146.8	145.6	144.7	144.1	143.4	142.8	142.1
105°	194.9	194.9	193.3	191.6	190.0	188.3	187.4	186.9	186.6	186.2	185.9
107.5°	241.2	240.7	240.0	239.4	238.7	238.1	237.6	237.4	237.2	236.9	236.8
110°	272.5	271.7	271.4	271.0	270.7	270.3	269.9	269.5	269.2	268.8	268.5



TEST NUMBER: P332163-930

CATALOG NUMBER: S123DIW-S775D1030U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	303.7	302.8	302.7	302.6	302.6	302.5	302.4	302.1	301.9	301.7	301.5
115°	352.0	351.9	352.2	352.6	352.9	353.4	353.3	352.7	352.1	351.6	351.1
117.5°	400.4	400.5	400.9	401.4	401.9	402.4	402.4	402.0	401.7	401.3	401.0
120°	432.6	432.8	433.7	434.6	435.5	436.5	436.4	435.3	434.2	433.1	432.0
122.5°	465.4	465.9	466.4	466.8	467.3	467.7	467.6	466.8	466.0	465.2	464.4
125°	513.9	514.6	514.9	515.4	515.7	516.1	516.0	515.4	514.9	514.3	513.8
127.5°	561.8	562.8	563.2	563.6	564.0	564.4	564.0	562.9	561.7	560.5	559.4
130°	593.1	593.9	594.4	595.0	595.6	596.1	595.7	594.2	592.7	591.3	589.8
132.5°	624.0	624.9	625.3	625.7	626.1	626.6	626.1	624.6	623.1	621.6	620.1
135°	669.9	670.7	670.9	671.1	671.2	671.4	671.0	669.8	668.8	667.6	666.6
137.5°	715.0	715.8	715.3	714.9	714.4	713.9	713.2	712.2	711.3	710.5	709.6
140°	744.0	744.2	744.0	743.9	743.6	743.5	742.9	742.0	741.1	740.2	739.2
142.5°	771.8	772.0	771.7	771.3	770.9	770.6	770.1	769.1	768.2	767.3	766.4
145°	812.6	812.8	812.2	811.7	811.1	810.6	810.1	809.8	809.3	809.0	808.6
147.5°	850.9	850.9	850.4	849.9	849.4	848.9	848.3	847.7	846.9	846.3	845.6
150°	874.7	874.7	874.3	874.0	873.6	873.3	872.9	872.5	872.1	871.8	871.4
152.5°	896.2	895.9	895.7	895.4	895.2	895.0	894.6	894.1	893.6	893.1	892.6
155°	927.5	926.8	926.6	926.4	926.2	926.0	925.9	925.9	925.9	925.9	925.9
157.5°	954.8	954.0	953.9	953.7	953.6	953.4	953.5	953.7	953.9	954.1	954.4
160°	971.4	970.5	970.5	970.5	970.5	970.5	970.7	971.1	971.4	971.8	972.2
162.5°	987.3	986.4	986.3	986.1	985.9	985.8	986.0	986.5	987.0	987.6	988.1
165°	1007.1	1006.1	1006.1	1006.1	1006.1	1006.1	1006.3	1006.9	1007.5	1008.0	1008.5
167.5°	1023.4	1022.2	1022.1	1022.0	1021.8	1021.7	1022.0	1022.7	1023.4	1024.2	1024.9
170°	1032.1	1030.9	1030.9	1030.9	1030.9	1030.9	1031.2	1031.9	1032.7	1033.4	1034.1
172.5°	1039.3	1038.1	1038.1	1038.1	1038.1	1038.1	1038.4	1039.2	1039.9	1040.6	1041.4
175°	1046.8	1045.7	1045.7	1045.7	1045.7	1045.7	1046.1	1046.8	1047.6	1048.3	1049.0
177.5°	1050.4	1049.5	1049.5	1049.5	1049.5	1049.5	1049.8	1050.4	1051.0	1051.6	1052.1
180°	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5



TEST NUMBER: P332163-930

CATALOG NUMBER: S123DIW-S775D1030U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9
2.5°	886.4	888.1	894.0	898.1	902.8	905.6	908.2	910.4	913.1	913.7	923.7
5°	890.4	898.9	913.9	925.0	938.6	953.5	963.8	968.5	980.8	991.1	1011.5
7.5°	889.2	907.4	929.9	953.3	978.4	1001.7	1021.8	1045.7	1062.7	1088.3	1113.4
10°	888.2	912.6	941.6	971.4	1006.5	1038.9	1067.9	1100.3	1127.2	1162.7	1192.9
12.5°	885.2	914.6	954.9	990.3	1032.7	1077.5	1120.5	1162.1	1185.9	1245.0	1272.8
15°	877.6	912.6	963.0	1016.7	1075.1	1128.1	1182.8	1226.3	1296.7	1348.3	1381.2
17.5°	863.1	912.1	971.8	1036.7	1107.7	1177.5	1239.4	1305.5	1380.1	1442.7	1509.3
20°	856.2	910.0	976.6	1048.3	1122.1	1201.1	1271.5	1350.9	1432.4	1493.9	1579.2
22.5°	843.6	904.5	976.2	1056.1	1135.1	1216.8	1299.2	1379.2	1473.4	1558.1	1639.3
25°	822.9	891.2	965.5	1054.7	1147.3	1229.2	1327.9	1434.1	1532.3	1641.1	1722.2
27.5°	801.2	874.2	948.6	1031.5	1131.1	1228.4	1352.4	1472.5	1592.6	1686.5	1746.5
30°	784.5	855.3	932.2	1015.9	1114.4	1230.1	1368.8	1499.8	1616.8	1697.5	1731.2
32.5°	766.4	838.3	906.2	994.0	1099.1	1229.1	1379.1	1515.9	1618.2	1671.9	1665.3
35°	738.0	798.2	864.3	948.8	1072.6	1221.6	1385.0	1517.4	1580.1	1568.6	1481.5
37.5°	697.0	747.6	812.8	905.3	1041.9	1205.7	1373.1	1472.3	1468.3	1374.4	1248.3
40°	671.4	714.5	777.2	874.6	1018.0	1195.6	1354.3	1418.8	1364.2	1233.1	1082.0
42.5°	638.0	677.6	740.4	840.4	991.6	1174.7	1318.4	1337.2	1230.3	1079.5	940.9
45°	586.0	621.0	685.9	789.2	952.3	1129.4	1230.9	1185.3	1041.5	885.7	780.2
47.5°	530.3	566.6	629.1	735.2	895.2	1061.2	1109.5	1012.4	864.7	738.4	641.6
50°	495.1	530.1	591.2	698.3	856.6	1005.2	1025.2	899.8	764.0	653.1	573.6
52.5°	459.6	492.5	552.5	660.1	811.5	940.3	927.9	800.1	675.2	580.7	518.4
55°	406.8	437.9	495.1	595.8	733.7	835.7	790.9	668.9	565.6	492.1	444.7
57.5°	359.5	389.4	438.7	529.7	649.5	719.7	662.6	559.7	477.6	421.1	385.8
60°	327.3	353.8	400.8	485.3	589.5	642.8	586.4	495.5	426.4	381.2	349.6
62.5°	297.0	320.0	363.5	440.3	530.7	575.5	518.5	441.6	382.7	342.6	315.8
65°	250.9	271.9	310.3	370.1	444.3	474.2	425.1	362.8	317.2	287.2	269.3
67.5°	209.0	226.7	259.9	307.0	361.6	383.4	346.0	297.7	263.3	239.4	225.1
70°	181.0	196.3	222.4	262.9	312.4	329.1	294.1	254.4	229.2	210.0	196.7
72.5°	157.4	168.7	192.3	223.6	265.0	278.2	253.8	218.9	195.4	181.0	170.5
75°	119.9	129.3	144.7	169.9	198.4	206.2	187.8	166.0	150.3	140.0	131.9
77.5°	86.5	93.4	104.5	120.0	139.8	146.8	135.1	120.6	109.1	102.2	97.7
80°	65.3	70.8	80.2	93.0	105.0	108.8	102.0	90.9	82.8	79.0	75.1
82.5°	48.3	51.4	57.0	65.7	73.9	78.4	72.6	66.0	61.6	58.1	56.7
85°	24.3	26.0	28.6	32.0	37.1	38.8	36.7	35.0	32.4	30.3	30.3
87.5°	9.4	9.8	11.2	12.2	14.0	15.5	15.7	15.4	15.6	15.4	15.2
90°	2.7	4.5	6.4	8.2	10.3	12.6	15.1	17.4	19.8	20.5	21.3
92.5°	21.2	22.5	23.7	24.9	26.3	27.6	29.0	30.3	31.7	32.3	32.9
95°	50.0	51.3	52.6	53.9	55.3	56.7	58.2	59.7	61.1	61.9	62.6
97.5°	87.5	88.5	89.4	90.4	91.4	92.5	93.5	94.6	95.6	96.5	97.3
100°	113.4	114.5	115.6	116.8	117.7	118.7	119.6	120.5	121.4	122.0	122.5
102.5°	142.8	143.4	144.1	144.7	145.6	146.8	148.1	149.3	150.5	151.1	151.6
105°	186.2	186.6	186.9	187.4	188.3	190.0	191.6	193.3	194.9	194.9	194.9
107.5°	236.9	237.2	237.4	237.6	238.1	238.7	239.4	240.0	240.7	241.2	241.9
110°	268.8	269.2	269.5	269.9	270.3	270.7	271.0	271.4	271.7	272.5	273.2





TEST NUMBER: P332163-930

CATALOG NUMBER: S123DIW-S775D1030U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	301.7	301.9	302.1	302.4	302.5	302.6	302.6	302.7	302.8	303.7	304.6
115°	351.6	352.1	352.7	353.3	353.4	352.9	352.6	352.2	351.9	352.0	352.2
117.5°	401.3	401.7	402.0	402.4	402.4	401.9	401.4	400.9	400.5	400.4	400.4
120°	433.1	434.2	435.3	436.4	436.5	435.5	434.6	433.7	432.8	432.6	432.4
122.5°	465.2	466.0	466.8	467.6	467.7	467.3	466.8	466.4	465.9	465.4	464.9
125°	514.3	514.9	515.4	516.0	516.1	515.7	515.4	514.9	514.6	513.9	513.1
127.5°	560.5	561.7	562.9	564.0	564.4	564.0	563.6	563.2	562.8	561.8	560.8
130°	591.3	592.7	594.2	595.7	596.1	595.6	595.0	594.4	593.9	593.1	592.4
132.5°	621.6	623.1	624.6	626.1	626.6	626.1	625.7	625.3	624.9	624.0	623.2
135°	667.6	668.8	669.8	671.0	671.4	671.2	671.1	670.9	670.7	669.9	669.2
137.5°	710.5	711.3	712.2	713.2	713.9	714.4	714.9	715.3	715.8	715.0	714.3
140°	740.2	741.1	742.0	742.9	743.5	743.6	743.9	744.0	744.2	744.0	743.9
142.5°	767.3	768.2	769.1	770.1	770.6	770.9	771.3	771.7	772.0	771.8	771.6
145°	809.0	809.3	809.8	810.1	810.6	811.1	811.7	812.2	812.8	812.6	812.4
147.5°	846.3	846.9	847.7	848.3	848.9	849.4	849.9	850.4	850.9	850.9	850.9
150°	871.8	872.1	872.5	872.9	873.3	873.6	874.0	874.3	874.7	874.7	874.7
152.5°	893.1	893.6	894.1	894.6	895.0	895.2	895.4	895.7	895.9	896.2	896.4
155°	925.9	925.9	925.9	925.9	926.0	926.2	926.4	926.6	926.8	927.5	928.2
157.5°	954.1	953.9	953.7	953.5	953.4	953.6	953.7	953.9	954.0	954.8	955.5
160°	971.8	971.4	971.1	970.7	970.5	970.5	970.5	970.5	970.5	971.4	972.4
162.5°	987.6	987.0	986.5	986.0	985.8	985.9	986.1	986.3	986.4	987.3	988.2
165°	1008.0	1007.5	1006.9	1006.3	1006.1	1006.1	1006.1	1006.1	1006.1	1007.1	1008.3
167.5°	1024.2	1023.4	1022.7	1022.0	1021.7	1021.8	1022.0	1022.1	1022.2	1023.4	1024.5
170°	1033.4	1032.7	1031.9	1031.2	1030.9	1030.9	1030.9	1030.9	1030.9	1032.1	1033.4
172.5°	1040.6	1039.9	1039.2	1038.4	1038.1	1038.1	1038.1	1038.1	1038.1	1039.3	1040.4
175°	1048.3	1047.6	1046.8	1046.1	1045.7	1045.7	1045.7	1045.7	1045.7	1046.8	1047.9
177.5°	1051.6	1051.0	1050.4	1049.8	1049.5	1049.5	1049.5	1049.5	1049.5	1050.4	1051.2
180°	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5



TEST NUMBER: P332163-930

CATALOG NUMBER: S123DIW-S775D1030U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	880.9	880.9	880.9	880.9	880.9	880.9	880.9
2.5°	927.1	927.4	931.2	933.9	932.5	934.3	934.9
5°	1012.8	1028.3	1036.3	1042.3	1042.8	1043.2	1046.6
7.5°	1134.5	1151.0	1163.0	1181.3	1186.7	1192.9	1191.2
10°	1223.3	1247.6	1268.5	1279.6	1291.6	1309.0	1295.0
12.5°	1306.3	1349.4	1381.2	1398.5	1409.7	1413.2	1406.3
15°	1443.1	1499.4	1529.7	1528.8	1567.3	1584.0	1557.9
17.5°	1568.6	1620.6	1662.2	1683.6	1715.6	1722.6	1719.4
20°	1645.4	1702.2	1734.6	1771.3	1788.0	1802.9	1805.5
22.5°	1711.6	1762.6	1797.4	1828.0	1841.9	1849.0	1853.3
25°	1779.9	1820.0	1840.9	1851.5	1855.4	1854.6	1849.0
27.5°	1775.2	1778.2	1755.2	1732.6	1712.4	1689.5	1681.7
30°	1729.1	1693.2	1629.2	1592.9	1539.5	1497.3	1514.3
32.5°	1607.9	1536.5	1464.6	1385.3	1319.6	1301.0	1282.1
35°	1372.2	1246.8	1173.4	1087.9	1053.9	1019.7	996.2
37.5°	1110.2	1013.1	926.0	870.2	836.0	814.4	802.7
40°	959.9	872.5	800.7	755.5	729.4	705.2	701.7
42.5°	840.1	758.7	704.7	668.7	643.8	633.4	625.9
45°	688.0	631.3	595.0	569.4	552.8	546.3	537.8
47.5°	582.4	542.3	515.0	497.6	485.0	480.3	479.6
50°	523.3	490.0	469.9	456.2	446.5	444.7	437.9
52.5°	478.9	450.0	434.4	422.5	415.4	410.6	408.5
55°	415.7	396.5	382.5	375.6	370.1	365.3	365.3
57.5°	363.7	347.7	338.3	332.6	330.8	327.5	325.4
60°	331.7	318.0	310.7	305.6	302.2	302.6	298.8
62.5°	300.2	291.4	284.5	279.3	275.2	275.3	275.6
65°	255.7	248.8	243.7	242.0	239.5	236.4	237.3
67.5°	216.6	210.3	206.3	203.3	202.5	200.9	203.3
70°	188.7	183.9	181.0	178.4	177.6	178.0	180.1
72.5°	163.1	159.7	157.8	156.5	154.7	154.7	156.2
75°	128.1	125.5	123.8	122.5	122.1	122.1	122.1
77.5°	94.1	93.5	92.7	90.8	90.9	91.4	91.5
80°	74.3	73.0	72.6	71.7	70.4	69.5	71.7
82.5°	55.5	54.2	53.8	53.6	51.6	51.4	53.2
85°	29.8	28.6	29.0	28.6	28.6	28.2	28.2
87.5°	15.0	14.8	14.6	15.0	14.7	14.4	15.2
90°	22.0	22.7	23.3	23.6	24.1	24.4	24.8
92.5°	33.5	34.1	34.2	34.0	33.8	33.6	33.3
95°	63.3	64.1	64.4	64.4	64.4	64.4	64.4
97.5°	98.2	99.1	99.4	99.3	99.3	99.2	99.1
100°	123.1	123.6	124.1	124.4	124.8	125.1	125.6
102.5°	152.1	152.7	153.0	152.9	152.8	152.7	152.6
105°	194.9	194.9	195.1	195.5	195.8	196.2	196.6
107.5°	242.5	243.0	243.2	243.0	242.8	242.6	242.3
110°	273.9	274.7	274.8	274.5	274.1	273.8	273.4



TEST NUMBER: P332163-930

CATALOG NUMBER: S123DIW-S775D1030U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	305.4	306.3	306.7	306.6	306.6	306.6	306.5
115°	352.5	352.6	352.6	352.5	352.2	352.0	351.9
117.5°	400.3	400.3	400.0	399.5	399.0	398.4	397.9
120°	432.3	432.1	431.8	431.5	431.0	430.7	430.3
122.5°	464.4	464.0	463.4	462.9	462.4	461.9	461.4
125°	512.4	511.7	510.9	510.2	509.5	508.7	508.0
127.5°	559.8	558.7	557.7	556.9	556.1	555.2	554.4
130°	591.7	590.9	590.0	588.6	587.3	586.1	584.8
132.5°	622.3	621.4	620.5	619.5	618.5	617.5	616.5
135°	668.5	667.7	667.2	666.8	666.5	666.1	665.8
137.5°	713.5	712.7	712.0	711.3	710.6	709.9	709.2
140°	743.6	743.5	742.7	741.4	740.2	738.9	737.6
142.5°	771.4	771.3	770.6	769.6	768.7	767.7	766.7
145°	812.2	812.0	811.5	810.8	810.1	809.3	808.6
147.5°	850.9	850.9	850.4	849.3	848.2	847.1	846.0
150°	874.7	874.7	874.2	873.1	872.0	870.9	869.8
152.5°	896.7	897.1	896.7	895.8	894.8	893.8	892.9
155°	929.0	929.7	929.4	928.1	926.8	925.6	924.3
157.5°	956.3	957.1	957.0	955.9	955.0	953.9	952.8
160°	973.3	974.2	974.3	973.5	972.8	972.1	971.3
162.5°	989.1	990.1	989.9	988.8	987.6	986.4	985.2
165°	1009.3	1010.5	1010.4	1009.1	1007.8	1006.5	1005.3
167.5°	1025.6	1026.8	1026.8	1025.6	1024.5	1023.4	1022.2
170°	1034.7	1036.0	1036.0	1034.7	1033.4	1032.1	1030.9
172.5°	1041.5	1042.7	1042.6	1041.3	1040.0	1038.7	1037.5
175°	1049.0	1050.1	1050.0	1048.7	1047.4	1046.2	1044.9
177.5°	1052.1	1053.0	1053.0	1051.9	1050.9	1049.9	1048.9
180°	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5

(END OF REPORT)