

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332169-930

Luminaire Tested: **S123DIW-S775D1320U930-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332169-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S775D1320U930-4F0-1E-UDD-A1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1320 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6392.5 lumens
Efficiency: N/A
Efficacy: 104.1 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 61.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332169-930

CATALOG NUMBER: S123DIW-S775D1320U930-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P332169-930

CATALOG NUMBER: S123DIW-S775D1320U930-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	48	48	48	42
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	43	42	41	36
2	88	81	75	70	80	74	69	64	61	57	54	49	47	44	38	37	35	30
3	80	71	64	58	73	65	59	54	54	49	46	44	40	38	34	32	30	26
4	73	63	55	49	67	58	51	46	48	43	39	39	35	32	31	28	26	22
5	67	56	48	42	61	51	45	39	43	38	34	35	31	28	28	25	23	19
6	62	50	42	37	56	46	39	34	39	33	29	32	28	25	25	22	20	17
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15
8	53	41	33	28	48	38	31	26	32	27	23	26	22	19	21	18	16	14
9	49	37	30	25	45	35	28	24	29	24	20	24	20	17	19	17	14	12
10	46	34	27	22	42	32	25	21	27	22	18	22	18	16	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9482	9482	9482	9482
5°	11309	9524	8440	9524
10°	14154	9475	7623	9475
15°	17361	9399	7096	9399
20°	20681	9279	6757	9279
25°	21960	9136	6682	9136
30°	18821	9028	6717	9028
35°	13090	8878	6787	8878
40°	9860	8702	6764	8702
45°	8187	8441	6680	8441
50°	7333	7906	6620	7906
55°	6855	7328	6536	7328
60°	6433	6725	6469	6725
65°	6044	6133	6260	6133
70°	5668	5454	5964	5454
75°	5078	4774	5465	4774
80°	4444	3918	4711	3918
85°	3483	2853	3162	2853



TEST NUMBER: P332169-930

CATALOG NUMBER: S123DIW-S775D1320U930-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.8	1.4
10°-20°	278.3	4.4
20°-30°	467.0	7.3
30°-40°	528.8	8.3
40°-50°	474.2	7.4
50°-60°	382.7	6.0
60°-70°	266.7	4.2
70°-80°	140.2	2.2
80°-90°	38.3	0.6
90°-100°	87.7	1.4
100°-110°	262.5	4.1
110°-120°	446.4	7.0
120°-130°	587.2	9.2
130°-140°	660.0	10.3
140°-150°	648.8	10.1
150°-160°	546.2	8.5
160°-170°	363.6	5.7
170°-180°	127.3	2.0
0°-30°	832.1	13.0
0°-40°	1360.9	21.3
0°-60°	2217.8	34.7
0°-90°	2662.9	41.7
90°-120°	796.6	12.5
90°-150°	2692.5	42.1
90°-180°	3730.0	58.3
0°-180°	6392.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	881	881	881	881	881	
5°	1047	881	781	881	1047	108
15°	1558	843	637	843	1558	450
25°	1849	769	563	769	1849	811
35°	996	676	516	676	996	647
45°	538	554	439	554	538	426
55°	365	390	348	390	365	328
65°	237	241	246	241	237	236
75°	122	115	131	115	122	131
85°	28	23	26	23	28	34
90°	32	1	32	1	32	17
95°	82	62	82	62	82	85
105°	252	238	252	238	252	267
115°	450	449	450	449	450	446
125°	650	658	650	658	650	581
135°	852	853	852	853	852	655
145°	1035	1035	1035	1035	1035	646
155°	1183	1185	1183	1185	1183	545
165°	1287	1291	1287	1291	1287	363
175°	1338	1343	1338	1343	1338	127
180°	1346	1346	1346	1346	1346	



TEST NUMBER: P332169-930

CATALOG NUMBER: S123DIW-S775D1320U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9
2.5°	934.9	934.3	932.5	933.9	931.2	927.4	927.1	923.7	913.7	913.1	910.4
5°	1046.6	1043.2	1042.8	1042.3	1036.3	1028.3	1012.8	1011.5	991.1	980.8	968.5
7.5°	1191.2	1192.9	1186.7	1181.3	1163.0	1151.0	1134.5	1113.4	1088.3	1062.7	1045.7
10°	1295.0	1309.0	1291.6	1279.6	1268.5	1247.6	1223.3	1192.9	1162.7	1127.2	1100.3
12.5°	1406.3	1413.2	1409.7	1398.5	1381.2	1349.4	1306.3	1272.8	1245.0	1185.9	1162.1
15°	1557.9	1584.0	1567.3	1528.8	1529.7	1499.4	1443.1	1381.2	1348.3	1296.7	1226.3
17.5°	1719.4	1722.6	1715.6	1683.6	1662.2	1620.6	1568.6	1509.3	1442.7	1380.1	1305.5
20°	1805.5	1802.9	1788.0	1771.3	1734.6	1702.2	1645.4	1579.2	1493.9	1432.4	1350.9
22.5°	1853.3	1849.0	1841.9	1828.0	1797.4	1762.6	1711.6	1639.3	1558.1	1473.4	1379.2
25°	1849.0	1854.6	1855.4	1851.5	1840.9	1820.0	1779.9	1722.2	1641.1	1532.3	1434.1
27.5°	1681.7	1689.5	1712.4	1732.6	1755.2	1778.2	1775.2	1746.5	1686.5	1592.6	1472.5
30°	1514.3	1497.3	1539.5	1592.9	1629.2	1693.2	1729.1	1731.2	1697.5	1616.8	1499.8
32.5°	1282.1	1301.0	1319.6	1385.3	1464.6	1536.5	1607.9	1665.3	1671.9	1618.2	1515.9
35°	996.2	1019.7	1053.9	1087.9	1173.4	1246.8	1372.2	1481.5	1568.6	1580.1	1517.4
37.5°	802.7	814.4	836.0	870.2	926.0	1013.1	1110.2	1248.3	1374.4	1468.3	1472.3
40°	701.7	705.2	729.4	755.5	800.7	872.5	959.9	1082.0	1233.1	1364.2	1418.8
42.5°	625.9	633.4	643.8	668.7	704.7	758.7	840.1	940.9	1079.5	1230.3	1337.2
45°	537.8	546.3	552.8	569.4	595.0	631.3	688.0	780.2	885.7	1041.5	1185.3
47.5°	479.6	480.3	485.0	497.6	515.0	542.3	582.4	641.6	738.4	864.7	1012.4
50°	437.9	444.7	446.5	456.2	469.9	490.0	523.3	573.6	653.1	764.0	899.8
52.5°	408.5	410.6	415.4	422.5	434.4	450.0	478.9	518.4	580.7	675.2	800.1
55°	365.3	365.3	370.1	375.6	382.5	396.5	415.7	444.7	492.1	565.6	668.9
57.5°	325.4	327.5	330.8	332.6	338.3	347.7	363.7	385.8	421.1	477.6	559.7
60°	298.8	302.6	302.2	305.6	310.7	318.0	331.7	349.6	381.2	426.4	495.5
62.5°	275.6	275.3	275.2	279.3	284.5	291.4	300.2	315.8	342.6	382.7	441.6
65°	237.3	236.4	239.5	242.0	243.7	248.8	255.7	269.3	287.2	317.2	362.8
67.5°	203.3	200.9	202.5	203.3	206.3	210.3	216.6	225.1	239.4	263.3	297.7
70°	180.1	178.0	177.6	178.4	181.0	183.9	188.7	196.7	210.0	229.2	254.4
72.5°	156.2	154.7	154.7	156.5	157.8	159.7	163.1	170.5	181.0	195.4	218.9
75°	122.1	122.1	122.1	122.5	123.8	125.5	128.1	131.9	140.0	150.3	166.0
77.5°	91.5	91.4	90.9	90.8	92.7	93.5	94.1	97.7	102.2	109.1	120.6
80°	71.7	69.5	70.4	71.7	72.6	73.0	74.3	75.1	79.0	82.8	90.9
82.5°	53.2	51.4	51.6	53.6	53.8	54.2	55.5	56.7	58.1	61.6	66.0
85°	28.2	28.2	28.6	28.6	29.0	28.6	29.8	30.3	30.3	32.4	35.0
87.5°	16.6	15.8	16.1	16.3	15.9	16.1	16.2	16.4	16.6	16.7	16.4
90°	31.7	31.2	30.8	30.3	29.8	29.1	28.2	27.2	26.3	25.4	22.3
92.5°	42.7	43.0	43.3	43.5	43.9	43.6	42.9	42.1	41.3	40.6	38.9
95°	82.5	82.5	82.5	82.5	82.5	82.0	81.0	80.1	79.2	78.3	76.4
97.5°	126.9	127.0	127.1	127.2	127.3	126.8	125.7	124.6	123.5	122.5	121.1
100°	160.7	160.3	159.8	159.3	158.8	158.2	157.5	156.9	156.1	155.5	154.3
102.5°	195.4	195.5	195.6	195.7	195.8	195.5	194.8	194.0	193.4	192.7	191.1
105°	251.7	251.2	250.7	250.3	249.8	249.6	249.6	249.6	249.6	249.6	247.4
107.5°	310.2	310.5	310.8	311.1	311.4	311.1	310.4	309.7	308.9	308.1	307.3
110°	350.0	350.5	351.0	351.4	351.9	351.6	350.7	349.8	348.9	347.9	347.4



TEST NUMBER: P332169-930

CATALOG NUMBER: S123DIW-S775D1320U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	392.3	392.4	392.5	392.6	392.6	392.2	391.0	389.9	388.8	387.7	387.6
115°	450.5	450.7	450.9	451.2	451.4	451.4	451.2	450.9	450.7	450.5	450.9
117.5°	509.5	510.1	510.8	511.4	512.1	512.4	512.5	512.6	512.6	512.7	513.2
120°	550.9	551.4	551.9	552.4	552.8	553.2	553.4	553.6	553.8	554.1	555.3
122.5°	590.7	591.3	592.0	592.6	593.3	593.9	594.5	595.2	595.7	596.4	597.0
125°	650.3	651.3	652.2	653.1	654.1	655.0	656.0	656.9	657.9	658.8	659.3
127.5°	709.7	710.9	711.9	713.0	714.0	715.3	716.6	717.9	719.2	720.6	721.1
130°	748.7	750.3	752.0	753.6	755.2	756.5	757.5	758.4	759.4	760.3	761.0
132.5°	789.3	790.5	791.8	793.0	794.3	795.6	796.6	797.8	798.9	800.1	800.5
135°	852.3	852.7	853.2	853.7	854.2	854.8	855.8	856.7	857.7	858.6	858.8
137.5°	907.9	908.8	909.7	910.6	911.5	912.4	913.4	914.4	915.3	916.4	915.7
140°	944.3	945.9	947.5	949.3	950.9	951.8	952.0	952.3	952.5	952.8	952.5
142.5°	981.5	982.8	984.1	985.3	986.6	987.3	987.6	987.8	988.1	988.3	987.8
145°	1035.2	1036.2	1037.1	1038.0	1039.0	1039.6	1039.8	1040.0	1040.2	1040.5	1039.8
147.5°	1083.0	1084.4	1085.8	1087.3	1088.7	1089.3	1089.3	1089.3	1089.3	1089.3	1088.7
150°	1113.5	1114.8	1116.3	1117.7	1119.1	1119.8	1119.8	1119.8	1119.8	1119.8	1119.3
152.5°	1143.0	1144.3	1145.5	1146.7	1147.9	1148.3	1148.0	1147.6	1147.3	1146.9	1146.6
155°	1183.2	1184.9	1186.6	1188.2	1189.8	1190.2	1189.3	1188.3	1187.4	1186.4	1186.2
157.5°	1219.9	1221.2	1222.5	1223.8	1225.1	1225.3	1224.3	1223.3	1222.3	1221.3	1221.2
160°	1243.5	1244.5	1245.5	1246.3	1247.3	1247.2	1246.0	1244.8	1243.7	1242.4	1242.4
162.5°	1261.3	1262.8	1264.3	1265.8	1267.3	1267.5	1266.3	1265.1	1264.0	1262.7	1262.6
165°	1286.9	1288.5	1290.2	1291.8	1293.5	1293.6	1292.2	1290.8	1289.3	1287.9	1287.9
167.5°	1308.6	1310.1	1311.6	1313.0	1314.5	1314.5	1313.0	1311.6	1310.1	1308.6	1308.5
170°	1319.6	1321.3	1323.0	1324.6	1326.2	1326.2	1324.6	1323.0	1321.3	1319.6	1319.6
172.5°	1328.1	1329.8	1331.4	1333.1	1334.7	1334.8	1333.3	1331.9	1330.4	1328.9	1328.9
175°	1337.7	1339.3	1340.9	1342.6	1344.2	1344.3	1343.0	1341.5	1340.1	1338.7	1338.7
177.5°	1342.7	1344.0	1345.3	1346.6	1348.0	1348.1	1347.0	1345.8	1344.7	1343.5	1343.5
180°	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1



TEST NUMBER: P332169-930

CATALOG NUMBER: S123DIW-S775D1320U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9
2.5°	908.2	905.6	902.8	898.1	894.0	888.1	886.4	884.4	878.2	872.8	868.7
5°	963.8	953.5	938.6	925.0	913.9	898.9	890.4	881.4	868.6	857.0	847.7
7.5°	1021.8	1001.7	978.4	953.3	929.9	907.4	889.2	873.0	855.1	838.1	824.9
10°	1067.9	1038.9	1006.5	971.4	941.6	912.6	888.2	866.9	843.8	823.8	807.1
12.5°	1120.5	1077.5	1032.7	990.3	954.9	914.6	885.2	858.0	831.8	807.7	789.0
15°	1182.8	1128.1	1075.1	1016.7	963.0	912.6	877.6	843.4	813.1	788.3	764.4
17.5°	1239.4	1177.5	1107.7	1036.7	971.8	912.1	863.1	824.4	786.5	756.3	732.5
20°	1271.5	1201.1	1122.1	1048.3	976.6	910.0	856.2	810.1	769.2	737.1	710.2
22.5°	1299.2	1216.8	1135.1	1056.1	976.2	904.5	843.6	796.1	751.7	720.4	691.8
25°	1327.9	1229.2	1147.3	1054.7	965.5	891.2	822.9	769.2	724.7	688.0	658.6
27.5°	1352.4	1228.4	1131.1	1031.5	948.6	874.2	801.2	743.6	696.4	656.6	626.6
30°	1368.8	1230.1	1114.4	1015.9	932.2	855.3	784.5	726.4	676.9	636.4	608.2
32.5°	1379.1	1229.1	1099.1	994.0	906.2	838.3	766.4	706.3	655.4	615.6	588.4
35°	1385.0	1221.6	1072.6	948.8	864.3	798.2	738.0	675.6	622.3	585.1	554.5
37.5°	1373.1	1205.7	1041.9	905.3	812.8	747.6	697.0	643.9	592.9	552.0	525.5
40°	1354.3	1195.6	1018.0	874.6	777.2	714.5	671.4	619.3	568.9	530.1	505.3
42.5°	1318.4	1174.7	991.6	840.4	740.4	677.6	638.0	594.4	546.7	510.3	485.6
45°	1230.9	1129.4	952.3	789.2	685.9	621.0	586.0	554.5	511.4	475.9	454.5
47.5°	1109.5	1061.2	895.2	735.2	629.1	566.6	530.3	504.8	473.4	444.7	424.3
50°	1025.2	1005.2	856.6	698.3	591.2	530.1	495.1	472.1	449.5	420.9	402.1
52.5°	927.9	940.3	811.5	660.1	552.5	492.5	459.6	441.3	420.8	397.3	380.9
55°	790.9	835.7	733.7	595.8	495.1	437.9	406.8	390.5	378.6	361.1	347.0
57.5°	662.6	719.7	649.5	529.7	438.7	389.4	359.5	341.8	334.1	325.0	313.9
60°	586.4	642.8	589.5	485.3	400.8	353.8	327.3	312.4	304.8	298.3	288.9
62.5°	518.5	575.5	530.7	440.3	363.5	320.0	297.0	282.4	276.4	273.0	265.1
65°	425.1	474.2	444.3	370.1	310.3	271.9	250.9	240.8	235.2	233.9	228.8
67.5°	346.0	383.4	361.6	307.0	259.9	226.7	209.0	200.2	196.0	195.6	191.8
70°	294.1	329.1	312.4	262.9	222.4	196.3	181.0	173.3	170.7	170.3	168.2
72.5°	253.8	278.2	265.0	223.6	192.3	168.7	157.4	149.4	146.5	147.1	145.6
75°	187.8	206.2	198.4	169.9	144.7	129.3	119.9	114.8	112.3	113.6	111.9
77.5°	135.1	146.8	139.8	120.0	104.5	93.4	86.5	83.3	81.0	81.0	80.1
80°	102.0	108.8	105.0	93.0	80.2	70.8	65.3	63.2	61.9	61.5	61.1
82.5°	72.6	78.4	73.9	65.7	57.0	51.4	48.3	45.4	44.5	44.8	44.3
85°	36.7	38.8	37.1	32.0	28.6	26.0	24.3	23.1	22.2	22.6	21.8
87.5°	16.5	16.2	14.6	12.6	11.5	10.0	9.5	8.4	8.2	8.6	8.8
90°	19.2	16.2	13.1	10.4	8.1	5.8	3.4	1.1	3.4	5.8	8.1
92.5°	37.1	35.4	33.7	32.0	30.4	28.8	27.1	25.6	27.1	28.8	30.4
95°	74.5	72.6	70.8	69.0	67.3	65.7	64.0	62.4	64.0	65.7	67.3
97.5°	119.7	118.4	117.0	115.7	114.5	113.2	112.0	110.8	112.0	113.2	114.5
100°	153.1	151.9	150.7	149.4	148.1	146.6	145.2	143.8	145.2	146.6	148.1
102.5°	189.6	188.0	186.5	185.2	184.4	183.6	182.7	181.9	182.7	183.6	184.4
105°	245.3	243.2	241.1	239.8	239.3	238.9	238.4	237.9	238.4	238.9	239.3
107.5°	306.5	305.6	304.8	304.2	303.9	303.6	303.4	303.0	303.4	303.6	303.9
110°	347.0	346.5	346.0	345.5	345.0	344.6	344.1	343.6	344.1	344.6	345.0



TEST NUMBER: P332169-930

CATALOG NUMBER: S123DIW-S775D1320U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	387.4	387.3	387.3	387.1	386.8	386.5	386.2	386.0	386.2	386.5	386.8
115°	451.4	451.8	452.3	452.2	451.5	450.8	450.1	449.4	450.1	450.8	451.5
117.5°	513.9	514.5	515.1	515.2	514.7	514.2	513.7	513.3	513.7	514.2	514.7
120°	556.4	557.6	558.8	558.6	557.3	555.9	554.4	553.0	554.4	555.9	557.3
122.5°	597.6	598.2	598.8	598.6	597.6	596.6	595.5	594.5	595.5	596.6	597.6
125°	659.7	660.1	660.6	660.6	659.8	659.1	658.4	657.7	658.4	659.1	659.8
127.5°	721.5	722.1	722.6	722.1	720.6	719.1	717.6	716.1	717.6	719.1	720.6
130°	761.7	762.4	763.1	762.5	760.7	758.8	756.8	755.0	756.8	758.8	760.7
132.5°	801.1	801.6	802.1	801.4	799.6	797.7	795.8	793.9	795.8	797.7	799.6
135°	859.1	859.3	859.6	859.0	857.5	856.1	854.8	853.4	854.8	856.1	857.5
137.5°	915.2	914.5	914.0	913.1	911.8	910.7	909.5	908.3	909.5	910.7	911.8
140°	952.3	952.0	951.8	951.1	949.9	948.8	947.5	946.4	947.5	948.8	949.9
142.5°	987.4	987.0	986.6	985.8	984.6	983.4	982.3	981.0	982.3	983.4	984.6
145°	1039.1	1038.4	1037.7	1037.1	1036.7	1036.2	1035.7	1035.2	1035.7	1036.2	1036.7
147.5°	1088.0	1087.4	1086.7	1086.0	1085.2	1084.3	1083.5	1082.6	1083.5	1084.3	1085.2
150°	1118.8	1118.4	1117.9	1117.4	1117.0	1116.6	1116.1	1115.6	1116.1	1116.6	1117.0
152.5°	1146.3	1146.1	1145.7	1145.3	1144.6	1143.9	1143.3	1142.6	1143.3	1143.9	1144.6
155°	1185.9	1185.7	1185.5	1185.4	1185.4	1185.4	1185.4	1185.4	1185.4	1185.4	1185.4
157.5°	1220.9	1220.7	1220.6	1220.6	1220.9	1221.2	1221.5	1221.7	1221.5	1221.2	1220.9
160°	1242.4	1242.4	1242.4	1242.7	1243.2	1243.7	1244.1	1244.6	1244.1	1243.7	1243.2
162.5°	1262.4	1262.2	1262.0	1262.2	1262.9	1263.6	1264.2	1264.9	1264.2	1263.6	1262.9
165°	1287.9	1287.9	1287.9	1288.3	1289.0	1289.7	1290.4	1291.1	1290.4	1289.7	1289.0
167.5°	1308.3	1308.1	1307.9	1308.3	1309.2	1310.2	1311.1	1312.1	1311.1	1310.2	1309.2
170°	1319.6	1319.6	1319.6	1320.1	1321.1	1322.0	1323.0	1323.9	1323.0	1322.0	1321.1
172.5°	1328.9	1328.9	1328.9	1329.4	1330.4	1331.3	1332.3	1333.2	1332.3	1331.3	1330.4
175°	1338.7	1338.7	1338.7	1339.1	1340.1	1341.1	1342.0	1343.0	1342.0	1341.1	1340.1
177.5°	1343.5	1343.5	1343.5	1343.9	1344.7	1345.4	1346.2	1347.0	1346.2	1345.4	1344.7
180°	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1



TEST NUMBER: P332169-930

CATALOG NUMBER: S123DIW-S775D1320U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9
2.5°	866.3	863.9	860.5	855.3	851.3	844.7	844.7	845.8	845.8	845.5	844.7
5°	840.0	833.6	825.9	816.9	807.6	798.2	796.5	793.0	790.5	788.8	786.6
7.5°	812.3	800.9	789.7	777.1	765.7	756.3	749.7	744.2	740.7	736.9	734.3
10°	793.4	779.3	766.1	752.9	738.4	726.9	719.7	714.5	710.7	707.3	705.6
12.5°	771.3	755.1	740.5	728.0	712.1	700.3	693.3	691.0	686.4	679.2	675.5
15°	738.8	723.9	706.4	687.2	679.5	665.0	656.9	653.1	650.4	644.9	643.2
17.5°	711.1	691.5	671.9	657.5	643.3	631.5	627.0	622.2	618.8	614.2	612.9
20°	688.9	671.4	653.5	638.1	623.1	610.3	606.5	603.1	599.7	597.5	595.8
22.5°	666.3	648.9	634.0	619.6	603.7	595.3	591.2	587.4	585.0	583.6	581.9
25°	634.7	619.3	602.7	589.9	577.1	571.5	568.9	566.8	565.1	563.0	562.6
27.5°	606.3	589.6	576.1	564.2	555.0	550.3	547.9	546.8	547.2	548.0	548.5
30°	585.1	569.8	558.7	548.5	540.0	535.7	535.2	535.2	537.0	537.4	538.3
32.5°	565.7	553.1	542.0	532.1	525.6	522.7	524.3	524.3	525.7	526.8	528.3
35°	537.4	526.3	517.7	509.2	503.7	504.9	505.8	506.6	508.7	511.4	513.1
37.5°	510.3	500.7	491.8	485.1	482.6	484.9	486.9	488.7	491.2	493.2	494.9
40°	490.8	483.6	475.1	469.0	469.9	471.2	473.0	475.1	477.2	478.5	480.2
42.5°	472.7	465.1	458.7	453.7	454.9	456.6	457.5	458.7	461.1	463.4	464.5
45°	445.2	439.2	433.3	430.2	431.1	431.9	432.8	434.1	436.2	437.9	438.4
47.5°	414.2	410.0	406.0	403.1	404.5	404.1	405.2	408.0	408.6	409.7	412.1
50°	394.4	390.5	385.9	385.0	385.0	385.0	385.4	388.8	388.8	390.5	392.2
52.5°	372.5	370.1	367.0	365.5	364.8	364.8	366.6	368.4	369.0	371.5	373.2
55°	340.1	337.6	335.1	333.8	332.9	333.8	337.2	338.0	340.1	341.4	342.8
57.5°	306.5	304.5	302.5	301.7	301.6	302.7	304.6	307.1	307.7	311.6	313.6
60°	284.3	281.3	279.6	279.6	278.8	282.6	281.7	286.0	286.8	289.3	292.4
62.5°	261.4	257.4	256.7	256.7	257.9	259.0	260.2	262.0	264.3	267.5	269.9
65°	224.5	222.4	225.3	224.9	224.0	226.7	226.7	228.8	231.3	234.3	239.0
67.5°	189.6	188.5	188.7	188.7	190.0	191.5	192.7	194.5	197.6	200.8	203.8
70°	166.0	167.3	165.2	166.9	168.2	168.6	169.4	172.0	175.5	177.6	181.0
72.5°	143.2	143.1	143.3	144.0	145.3	146.0	146.9	149.9	153.6	155.4	158.1
75°	110.1	109.7	111.0	111.0	113.1	114.0	114.8	116.1	119.5	122.1	124.2
77.5°	80.4	81.0	80.6	82.1	81.5	81.7	84.3	85.6	85.9	91.0	92.1
80°	60.6	61.5	61.9	62.3	62.8	61.9	64.9	66.1	66.1	69.1	71.3
82.5°	43.5	44.0	45.2	45.6	45.7	46.6	46.8	47.7	48.8	50.1	52.8
85°	21.8	23.1	23.5	23.1	23.5	22.6	23.9	24.3	24.8	24.8	24.8
87.5°	8.9	9.8	10.1	11.0	11.3	12.2	12.5	11.9	12.1	13.4	12.1
90°	10.4	13.1	16.2	19.2	22.3	25.4	26.3	27.2	28.2	29.1	29.8
92.5°	32.0	33.7	35.4	37.1	38.9	40.6	41.3	42.1	42.9	43.6	43.9
95°	69.0	70.8	72.6	74.5	76.4	78.3	79.2	80.1	81.0	82.0	82.5
97.5°	115.7	117.0	118.4	119.7	121.1	122.5	123.5	124.6	125.7	126.8	127.3
100°	149.4	150.7	151.9	153.1	154.3	155.5	156.1	156.9	157.5	158.2	158.8
102.5°	185.2	186.5	188.0	189.6	191.1	192.7	193.4	194.0	194.8	195.5	195.8
105°	239.8	241.1	243.2	245.3	247.4	249.6	249.6	249.6	249.6	249.6	249.8
107.5°	304.2	304.8	305.6	306.5	307.3	308.1	308.9	309.7	310.4	311.1	311.4
110°	345.5	346.0	346.5	347.0	347.4	347.9	348.9	349.8	350.7	351.6	351.9



TEST NUMBER: P332169-930

CATALOG NUMBER: S123DIW-S775D1320U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	387.1	387.3	387.3	387.4	387.6	387.7	388.8	389.9	391.0	392.2	392.6
115°	452.2	452.3	451.8	451.4	450.9	450.5	450.7	450.9	451.2	451.4	451.4
117.5°	515.2	515.1	514.5	513.9	513.2	512.7	512.6	512.6	512.5	512.4	512.1
120°	558.6	558.8	557.6	556.4	555.3	554.1	553.8	553.6	553.4	553.2	552.8
122.5°	598.6	598.8	598.2	597.6	597.0	596.4	595.7	595.2	594.5	593.9	593.3
125°	660.6	660.6	660.1	659.7	659.3	658.8	657.9	656.9	656.0	655.0	654.1
127.5°	722.1	722.6	722.1	721.5	721.1	720.6	719.2	717.9	716.6	715.3	714.0
130°	762.5	763.1	762.4	761.7	761.0	760.3	759.4	758.4	757.5	756.5	755.2
132.5°	801.4	802.1	801.6	801.1	800.5	800.1	798.9	797.8	796.6	795.6	794.3
135°	859.0	859.6	859.3	859.1	858.8	858.6	857.7	856.7	855.8	854.8	854.2
137.5°	913.1	914.0	914.5	915.2	915.7	916.4	915.3	914.4	913.4	912.4	911.5
140°	951.1	951.8	952.0	952.3	952.5	952.8	952.5	952.3	952.0	951.8	950.9
142.5°	985.8	986.6	987.0	987.4	987.8	988.3	988.1	987.8	987.6	987.3	986.6
145°	1037.1	1037.7	1038.4	1039.1	1039.8	1040.5	1040.2	1040.0	1039.8	1039.6	1039.0
147.5°	1086.0	1086.7	1087.4	1088.0	1088.7	1089.3	1089.3	1089.3	1089.3	1089.3	1088.7
150°	1117.4	1117.9	1118.4	1118.8	1119.3	1119.8	1119.8	1119.8	1119.8	1119.8	1119.1
152.5°	1145.3	1145.7	1146.1	1146.3	1146.6	1146.9	1147.3	1147.6	1148.0	1148.3	1147.9
155°	1185.4	1185.5	1185.7	1185.9	1186.2	1186.4	1187.4	1188.3	1189.3	1190.2	1189.8
157.5°	1220.6	1220.6	1220.7	1220.9	1221.2	1221.3	1222.3	1223.3	1224.3	1225.3	1225.1
160°	1242.7	1242.4	1242.4	1242.4	1242.4	1242.4	1243.7	1244.8	1246.0	1247.2	1247.3
162.5°	1262.2	1262.0	1262.2	1262.4	1262.6	1262.7	1264.0	1265.1	1266.3	1267.5	1267.3
165°	1288.3	1287.9	1287.9	1287.9	1287.9	1287.9	1289.3	1290.8	1292.2	1293.6	1293.5
167.5°	1308.3	1307.9	1308.1	1308.3	1308.5	1308.6	1310.1	1311.6	1313.0	1314.5	1314.5
170°	1320.1	1319.6	1319.6	1319.6	1319.6	1319.6	1321.3	1323.0	1324.6	1326.2	1326.2
172.5°	1329.4	1328.9	1328.9	1328.9	1328.9	1328.9	1330.4	1331.9	1333.3	1334.8	1334.7
175°	1339.1	1338.7	1338.7	1338.7	1338.7	1338.7	1340.1	1341.5	1343.0	1344.3	1344.2
177.5°	1343.9	1343.5	1343.5	1343.5	1343.5	1343.5	1344.7	1345.8	1347.0	1348.1	1348.0
180°	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1



TEST NUMBER: P332169-930

CATALOG NUMBER: S123DIW-S775D1320U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9
2.5°	842.4	842.0	844.4	842.7	844.4	842.0	842.4	844.7	845.5	845.8	845.8
5°	784.1	785.4	781.1	781.1	781.1	785.4	784.1	786.6	788.8	790.5	793.0
7.5°	732.1	730.3	730.4	728.1	730.4	730.3	732.1	734.3	736.9	740.7	744.2
10°	700.4	697.9	697.0	697.4	697.0	697.9	700.4	705.6	707.3	710.7	714.5
12.5°	674.1	673.6	668.0	668.1	668.0	673.6	674.1	675.5	679.2	686.4	691.0
15°	643.2	635.1	634.2	636.8	634.2	635.1	643.2	643.2	644.9	650.4	653.1
17.5°	612.2	608.0	608.2	606.9	608.2	608.0	612.2	612.9	614.2	618.8	622.2
20°	595.8	593.3	592.9	589.9	592.9	593.3	595.8	595.8	597.5	599.7	603.1
22.5°	580.8	580.0	580.2	576.9	580.2	580.0	580.8	581.9	583.6	585.0	587.4
25°	562.1	564.3	562.6	562.6	562.6	564.3	562.1	562.6	563.0	565.1	566.8
27.5°	549.5	549.4	548.5	548.5	548.5	549.4	549.5	548.5	548.0	547.2	546.8
30°	540.0	539.5	540.4	540.4	540.4	539.5	540.0	538.3	537.4	537.0	535.2
32.5°	530.4	531.0	531.2	531.5	531.2	531.0	530.4	528.3	526.8	525.7	524.3
35°	515.6	516.0	517.3	516.5	517.3	516.0	515.6	513.1	511.4	508.7	506.6
37.5°	495.6	497.6	497.2	497.8	497.2	497.6	495.6	494.9	493.2	491.2	488.7
40°	480.6	481.9	481.4	481.4	481.4	481.9	480.6	480.2	478.5	477.2	475.1
42.5°	465.2	466.2	465.0	464.4	465.0	466.2	465.2	464.5	463.4	461.1	458.7
45°	440.0	439.2	440.5	438.8	440.5	439.2	440.0	438.4	437.9	436.2	434.1
47.5°	411.9	412.7	413.1	414.3	413.1	412.7	411.9	412.1	409.7	408.6	408.0
50°	393.1	395.7	395.7	395.3	395.7	395.7	393.1	392.2	390.5	388.8	388.8
52.5°	374.6	375.9	377.6	377.5	377.6	375.9	374.6	373.2	371.5	369.0	368.4
55°	346.2	347.0	347.9	348.3	347.9	347.0	346.2	342.8	341.4	340.1	338.0
57.5°	316.6	316.3	318.3	318.9	318.3	316.3	316.6	313.6	311.6	307.7	307.1
60°	295.8	295.8	299.2	300.5	299.2	295.8	295.8	292.4	289.3	286.8	286.0
62.5°	273.6	275.0	278.3	276.5	278.3	275.0	273.6	269.9	267.5	264.3	262.0
65°	241.2	244.6	244.2	245.8	244.2	244.6	241.2	239.0	234.3	231.3	228.8
67.5°	207.2	209.4	212.5	212.7	212.5	209.4	207.2	203.8	200.8	197.6	194.5
70°	184.4	186.5	188.3	189.5	188.3	186.5	184.4	181.0	177.6	175.5	172.0
72.5°	162.2	163.3	167.4	165.6	167.4	163.3	162.2	158.1	155.4	153.6	149.9
75°	127.2	130.2	132.7	131.4	132.7	130.2	127.2	124.2	122.1	119.5	116.1
77.5°	94.1	97.0	98.2	97.2	98.2	97.0	94.1	92.1	91.0	85.9	85.6
80°	74.3	73.9	76.4	76.0	76.4	73.9	74.3	71.3	69.1	66.1	66.1
82.5°	54.5	54.1	55.2	55.5	55.2	54.1	54.5	52.8	50.1	48.8	47.7
85°	26.5	27.7	26.0	25.6	26.0	27.7	26.5	24.8	24.8	24.8	24.3
87.5°	12.2	12.3	12.1	11.8	12.1	12.3	12.2	12.1	13.4	12.1	11.9
90°	30.3	30.8	31.2	31.7	31.2	30.8	30.3	29.8	29.1	28.2	27.2
92.5°	43.5	43.3	43.0	42.7	43.0	43.3	43.5	43.9	43.6	42.9	42.1
95°	82.5	82.5	82.5	82.5	82.5	82.5	82.5	82.5	82.0	81.0	80.1
97.5°	127.2	127.1	127.0	126.9	127.0	127.1	127.2	127.3	126.8	125.7	124.6
100°	159.3	159.8	160.3	160.7	160.3	159.8	159.3	158.8	158.2	157.5	156.9
102.5°	195.7	195.6	195.5	195.4	195.5	195.6	195.7	195.8	195.5	194.8	194.0
105°	250.3	250.7	251.2	251.7	251.2	250.7	250.3	249.8	249.6	249.6	249.6
107.5°	311.1	310.8	310.5	310.2	310.5	310.8	311.1	311.4	311.1	310.4	309.7
110°	351.4	351.0	350.5	350.0	350.5	351.0	351.4	351.9	351.6	350.7	349.8



TEST NUMBER: P332169-930

CATALOG NUMBER: S123DIW-S775D1320U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	392.6	392.5	392.4	392.3	392.4	392.5	392.6	392.6	392.2	391.0	389.9
115°	451.2	450.9	450.7	450.5	450.7	450.9	451.2	451.4	451.4	451.2	450.9
117.5°	511.4	510.8	510.1	509.5	510.1	510.8	511.4	512.1	512.4	512.5	512.6
120°	552.4	551.9	551.4	550.9	551.4	551.9	552.4	552.8	553.2	553.4	553.6
122.5°	592.6	592.0	591.3	590.7	591.3	592.0	592.6	593.3	593.9	594.5	595.2
125°	653.1	652.2	651.3	650.3	651.3	652.2	653.1	654.1	655.0	656.0	656.9
127.5°	713.0	711.9	710.9	709.7	710.9	711.9	713.0	714.0	715.3	716.6	717.9
130°	753.6	752.0	750.3	748.7	750.3	752.0	753.6	755.2	756.5	757.5	758.4
132.5°	793.0	791.8	790.5	789.3	790.5	791.8	793.0	794.3	795.6	796.6	797.8
135°	853.7	853.2	852.7	852.3	852.7	853.2	853.7	854.2	854.8	855.8	856.7
137.5°	910.6	909.7	908.8	907.9	908.8	909.7	910.6	911.5	912.4	913.4	914.4
140°	949.3	947.5	945.9	944.3	945.9	947.5	949.3	950.9	951.8	952.0	952.3
142.5°	985.3	984.1	982.8	981.5	982.8	984.1	985.3	986.6	987.3	987.6	987.8
145°	1038.0	1037.1	1036.2	1035.2	1036.2	1037.1	1038.0	1039.0	1039.6	1039.8	1040.0
147.5°	1087.3	1085.8	1084.4	1083.0	1084.4	1085.8	1087.3	1088.7	1089.3	1089.3	1089.3
150°	1117.7	1116.3	1114.8	1113.5	1114.8	1116.3	1117.7	1119.1	1119.8	1119.8	1119.8
152.5°	1146.7	1145.5	1144.3	1143.0	1144.3	1145.5	1146.7	1147.9	1148.3	1148.0	1147.6
155°	1188.2	1186.6	1184.9	1183.2	1184.9	1186.6	1188.2	1189.8	1190.2	1189.3	1188.3
157.5°	1223.8	1222.5	1221.2	1219.9	1221.2	1222.5	1223.8	1225.1	1225.3	1224.3	1223.3
160°	1246.3	1245.5	1244.5	1243.5	1244.5	1245.5	1246.3	1247.3	1247.2	1246.0	1244.8
162.5°	1265.8	1264.3	1262.8	1261.3	1262.8	1264.3	1265.8	1267.3	1267.5	1266.3	1265.1
165°	1291.8	1290.2	1288.5	1286.9	1288.5	1290.2	1291.8	1293.5	1293.6	1292.2	1290.8
167.5°	1313.0	1311.6	1310.1	1308.6	1310.1	1311.6	1313.0	1314.5	1314.5	1313.0	1311.6
170°	1324.6	1323.0	1321.3	1319.6	1321.3	1323.0	1324.6	1326.2	1326.2	1324.6	1323.0
172.5°	1333.1	1331.4	1329.8	1328.1	1329.8	1331.4	1333.1	1334.7	1334.8	1333.3	1331.9
175°	1342.6	1340.9	1339.3	1337.7	1339.3	1340.9	1342.6	1344.2	1344.3	1343.0	1341.5
177.5°	1346.6	1345.3	1344.0	1342.7	1344.0	1345.3	1346.6	1348.0	1348.1	1347.0	1345.8
180°	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1



TEST NUMBER: P332169-930

CATALOG NUMBER: S123DIW-S775D1320U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9
2.5°	844.7	844.7	851.3	855.3	860.5	863.9	866.3	868.7	872.8	878.2	884.4
5°	796.5	798.2	807.6	816.9	825.9	833.6	840.0	847.7	857.0	868.6	881.4
7.5°	749.7	756.3	765.7	777.1	789.7	800.9	812.3	824.9	838.1	855.1	873.0
10°	719.7	726.9	738.4	752.9	766.1	779.3	793.4	807.1	823.8	843.8	866.9
12.5°	693.3	700.3	712.1	728.0	740.5	755.1	771.3	789.0	807.7	831.8	858.0
15°	656.9	665.0	679.5	687.2	706.4	723.9	738.8	764.4	788.3	813.1	843.4
17.5°	627.0	631.5	643.3	657.5	671.9	691.5	711.1	732.5	756.3	786.5	824.4
20°	606.5	610.3	623.1	638.1	653.5	671.4	688.9	710.2	737.1	769.2	810.1
22.5°	591.2	595.3	603.7	619.6	634.0	648.9	666.3	691.8	720.4	751.7	796.1
25°	568.9	571.5	577.1	589.9	602.7	619.3	634.7	658.6	688.0	724.7	769.2
27.5°	547.9	550.3	555.0	564.2	576.1	589.6	606.3	626.6	656.6	696.4	743.6
30°	535.2	535.7	540.0	548.5	558.7	569.8	585.1	608.2	636.4	676.9	726.4
32.5°	524.3	522.7	525.6	532.1	542.0	553.1	565.7	588.4	615.6	655.4	706.3
35°	505.8	504.9	503.7	509.2	517.7	526.3	537.4	554.5	585.1	622.3	675.6
37.5°	486.9	484.9	482.6	485.1	491.8	500.7	510.3	525.5	552.0	592.9	643.9
40°	473.0	471.2	469.9	469.0	475.1	483.6	490.8	505.3	530.1	568.9	619.3
42.5°	457.5	456.6	454.9	453.7	458.7	465.1	472.7	485.6	510.3	546.7	594.4
45°	432.8	431.9	431.1	430.2	433.3	439.2	445.2	454.5	475.9	511.4	554.5
47.5°	405.2	404.1	404.5	403.1	406.0	410.0	414.2	424.3	444.7	473.4	504.8
50°	385.4	385.0	385.0	385.0	385.9	390.5	394.4	402.1	420.9	449.5	472.1
52.5°	366.6	364.8	364.8	365.5	367.0	370.1	372.5	380.9	397.3	420.8	441.3
55°	337.2	333.8	332.9	333.8	335.1	337.6	340.1	347.0	361.1	378.6	390.5
57.5°	304.6	302.7	301.6	301.7	302.5	304.5	306.5	313.9	325.0	334.1	341.8
60°	281.7	282.6	278.8	279.6	279.6	281.3	284.3	288.9	298.3	304.8	312.4
62.5°	260.2	259.0	257.9	256.7	256.7	257.4	261.4	265.1	273.0	276.4	282.4
65°	226.7	226.7	224.0	224.9	225.3	222.4	224.5	228.8	233.9	235.2	240.8
67.5°	192.7	191.5	190.0	188.7	188.7	188.5	189.6	191.8	195.6	196.0	200.2
70°	169.4	168.6	168.2	166.9	165.2	167.3	166.0	168.2	170.3	170.7	173.3
72.5°	146.9	146.0	145.3	144.0	143.3	143.1	143.2	145.6	147.1	146.5	149.4
75°	114.8	114.0	113.1	111.0	111.0	109.7	110.1	111.9	113.6	112.3	114.8
77.5°	84.3	81.7	81.5	82.1	80.6	81.0	80.4	80.1	81.0	81.0	83.3
80°	64.9	61.9	62.8	62.3	61.9	61.5	60.6	61.1	61.5	61.9	63.2
82.5°	46.8	46.6	45.7	45.6	45.2	44.0	43.5	44.3	44.8	44.5	45.4
85°	23.9	22.6	23.5	23.1	23.5	23.1	21.8	21.8	22.6	22.2	23.1
87.5°	12.5	12.2	11.3	11.0	10.1	9.8	8.9	8.8	8.6	8.2	8.4
90°	26.3	25.4	22.3	19.2	16.2	13.1	10.4	8.1	5.8	3.4	1.1
92.5°	41.3	40.6	38.9	37.1	35.4	33.7	32.0	30.4	28.8	27.1	25.6
95°	79.2	78.3	76.4	74.5	72.6	70.8	69.0	67.3	65.7	64.0	62.4
97.5°	123.5	122.5	121.1	119.7	118.4	117.0	115.7	114.5	113.2	112.0	110.8
100°	156.1	155.5	154.3	153.1	151.9	150.7	149.4	148.1	146.6	145.2	143.8
102.5°	193.4	192.7	191.1	189.6	188.0	186.5	185.2	184.4	183.6	182.7	181.9
105°	249.6	249.6	247.4	245.3	243.2	241.1	239.8	239.3	238.9	238.4	237.9
107.5°	308.9	308.1	307.3	306.5	305.6	304.8	304.2	303.9	303.6	303.4	303.0
110°	348.9	347.9	347.4	347.0	346.5	346.0	345.5	345.0	344.6	344.1	343.6



TEST NUMBER: P332169-930

CATALOG NUMBER: S123DIW-S775D1320U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	388.8	387.7	387.6	387.4	387.3	387.3	387.1	386.8	386.5	386.2	386.0
115°	450.7	450.5	450.9	451.4	451.8	452.3	452.2	451.5	450.8	450.1	449.4
117.5°	512.6	512.7	513.2	513.9	514.5	515.1	515.2	514.7	514.2	513.7	513.3
120°	553.8	554.1	555.3	556.4	557.6	558.8	558.6	557.3	555.9	554.4	553.0
122.5°	595.7	596.4	597.0	597.6	598.2	598.8	598.6	597.6	596.6	595.5	594.5
125°	657.9	658.8	659.3	659.7	660.1	660.6	660.6	659.8	659.1	658.4	657.7
127.5°	719.2	720.6	721.1	721.5	722.1	722.6	722.1	720.6	719.1	717.6	716.1
130°	759.4	760.3	761.0	761.7	762.4	763.1	762.5	760.7	758.8	756.8	755.0
132.5°	798.9	800.1	800.5	801.1	801.6	802.1	801.4	799.6	797.7	795.8	793.9
135°	857.7	858.6	858.8	859.1	859.3	859.6	859.0	857.5	856.1	854.8	853.4
137.5°	915.3	916.4	915.7	915.2	914.5	914.0	913.1	911.8	910.7	909.5	908.3
140°	952.5	952.8	952.5	952.3	952.0	951.8	951.1	949.9	948.8	947.5	946.4
142.5°	988.1	988.3	987.8	987.4	987.0	986.6	985.8	984.6	983.4	982.3	981.0
145°	1040.2	1040.5	1039.8	1039.1	1038.4	1037.7	1037.1	1036.7	1036.2	1035.7	1035.2
147.5°	1089.3	1089.3	1088.7	1088.0	1087.4	1086.7	1086.0	1085.2	1084.3	1083.5	1082.6
150°	1119.8	1119.8	1119.3	1118.8	1118.4	1117.9	1117.4	1117.0	1116.6	1116.1	1115.6
152.5°	1147.3	1146.9	1146.6	1146.3	1146.1	1145.7	1145.3	1144.6	1143.9	1143.3	1142.6
155°	1187.4	1186.4	1186.2	1185.9	1185.7	1185.5	1185.4	1185.4	1185.4	1185.4	1185.4
157.5°	1222.3	1221.3	1221.2	1220.9	1220.7	1220.6	1220.6	1220.9	1221.2	1221.5	1221.7
160°	1243.7	1242.4	1242.4	1242.4	1242.4	1242.4	1242.7	1243.2	1243.7	1244.1	1244.6
162.5°	1264.0	1262.7	1262.6	1262.4	1262.2	1262.0	1262.2	1262.9	1263.6	1264.2	1264.9
165°	1289.3	1287.9	1287.9	1287.9	1287.9	1287.9	1288.3	1289.0	1289.7	1290.4	1291.1
167.5°	1310.1	1308.6	1308.5	1308.3	1308.1	1307.9	1308.3	1309.2	1310.2	1311.1	1312.1
170°	1321.3	1319.6	1319.6	1319.6	1319.6	1319.6	1320.1	1321.1	1322.0	1323.0	1323.9
172.5°	1330.4	1328.9	1328.9	1328.9	1328.9	1328.9	1329.4	1330.4	1331.3	1332.3	1333.2
175°	1340.1	1338.7	1338.7	1338.7	1338.7	1338.7	1339.1	1340.1	1341.1	1342.0	1343.0
177.5°	1344.7	1343.5	1343.5	1343.5	1343.5	1343.5	1343.9	1344.7	1345.4	1346.2	1347.0
180°	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1



TEST NUMBER: P332169-930

CATALOG NUMBER: S123DIW-S775D1320U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9
2.5°	886.4	888.1	894.0	898.1	902.8	905.6	908.2	910.4	913.1	913.7	923.7
5°	890.4	898.9	913.9	925.0	938.6	953.5	963.8	968.5	980.8	991.1	1011.5
7.5°	889.2	907.4	929.9	953.3	978.4	1001.7	1021.8	1045.7	1062.7	1088.3	1113.4
10°	888.2	912.6	941.6	971.4	1006.5	1038.9	1067.9	1100.3	1127.2	1162.7	1192.9
12.5°	885.2	914.6	954.9	990.3	1032.7	1077.5	1120.5	1162.1	1185.9	1245.0	1272.8
15°	877.6	912.6	963.0	1016.7	1075.1	1128.1	1182.8	1226.3	1296.7	1348.3	1381.2
17.5°	863.1	912.1	971.8	1036.7	1107.7	1177.5	1239.4	1305.5	1380.1	1442.7	1509.3
20°	856.2	910.0	976.6	1048.3	1122.1	1201.1	1271.5	1350.9	1432.4	1493.9	1579.2
22.5°	843.6	904.5	976.2	1056.1	1135.1	1216.8	1299.2	1379.2	1473.4	1558.1	1639.3
25°	822.9	891.2	965.5	1054.7	1147.3	1229.2	1327.9	1434.1	1532.3	1641.1	1722.2
27.5°	801.2	874.2	948.6	1031.5	1131.1	1228.4	1352.4	1472.5	1592.6	1686.5	1746.5
30°	784.5	855.3	932.2	1015.9	1114.4	1230.1	1368.8	1499.8	1616.8	1697.5	1731.2
32.5°	766.4	838.3	906.2	994.0	1099.1	1229.1	1379.1	1515.9	1618.2	1671.9	1665.3
35°	738.0	798.2	864.3	948.8	1072.6	1221.6	1385.0	1517.4	1580.1	1568.6	1481.5
37.5°	697.0	747.6	812.8	905.3	1041.9	1205.7	1373.1	1472.3	1468.3	1374.4	1248.3
40°	671.4	714.5	777.2	874.6	1018.0	1195.6	1354.3	1418.8	1364.2	1233.1	1082.0
42.5°	638.0	677.6	740.4	840.4	991.6	1174.7	1318.4	1337.2	1230.3	1079.5	940.9
45°	586.0	621.0	685.9	789.2	952.3	1129.4	1230.9	1185.3	1041.5	885.7	780.2
47.5°	530.3	566.6	629.1	735.2	895.2	1061.2	1109.5	1012.4	864.7	738.4	641.6
50°	495.1	530.1	591.2	698.3	856.6	1005.2	1025.2	899.8	764.0	653.1	573.6
52.5°	459.6	492.5	552.5	660.1	811.5	940.3	927.9	800.1	675.2	580.7	518.4
55°	406.8	437.9	495.1	595.8	733.7	835.7	790.9	668.9	565.6	492.1	444.7
57.5°	359.5	389.4	438.7	529.7	649.5	719.7	662.6	559.7	477.6	421.1	385.8
60°	327.3	353.8	400.8	485.3	589.5	642.8	586.4	495.5	426.4	381.2	349.6
62.5°	297.0	320.0	363.5	440.3	530.7	575.5	518.5	441.6	382.7	342.6	315.8
65°	250.9	271.9	310.3	370.1	444.3	474.2	425.1	362.8	317.2	287.2	269.3
67.5°	209.0	226.7	259.9	307.0	361.6	383.4	346.0	297.7	263.3	239.4	225.1
70°	181.0	196.3	222.4	262.9	312.4	329.1	294.1	254.4	229.2	210.0	196.7
72.5°	157.4	168.7	192.3	223.6	265.0	278.2	253.8	218.9	195.4	181.0	170.5
75°	119.9	129.3	144.7	169.9	198.4	206.2	187.8	166.0	150.3	140.0	131.9
77.5°	86.5	93.4	104.5	120.0	139.8	146.8	135.1	120.6	109.1	102.2	97.7
80°	65.3	70.8	80.2	93.0	105.0	108.8	102.0	90.9	82.8	79.0	75.1
82.5°	48.3	51.4	57.0	65.7	73.9	78.4	72.6	66.0	61.6	58.1	56.7
85°	24.3	26.0	28.6	32.0	37.1	38.8	36.7	35.0	32.4	30.3	30.3
87.5°	9.5	10.0	11.5	12.6	14.6	16.2	16.5	16.4	16.7	16.6	16.4
90°	3.4	5.8	8.1	10.4	13.1	16.2	19.2	22.3	25.4	26.3	27.2
92.5°	27.1	28.8	30.4	32.0	33.7	35.4	37.1	38.9	40.6	41.3	42.1
95°	64.0	65.7	67.3	69.0	70.8	72.6	74.5	76.4	78.3	79.2	80.1
97.5°	112.0	113.2	114.5	115.7	117.0	118.4	119.7	121.1	122.5	123.5	124.6
100°	145.2	146.6	148.1	149.4	150.7	151.9	153.1	154.3	155.5	156.1	156.9
102.5°	182.7	183.6	184.4	185.2	186.5	188.0	189.6	191.1	192.7	193.4	194.0
105°	238.4	238.9	239.3	239.8	241.1	243.2	245.3	247.4	249.6	249.6	249.6
107.5°	303.4	303.6	303.9	304.2	304.8	305.6	306.5	307.3	308.1	308.9	309.7
110°	344.1	344.6	345.0	345.5	346.0	346.5	347.0	347.4	347.9	348.9	349.8



TEST NUMBER: P332169-930

CATALOG NUMBER: S123DIW-S775D1320U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	386.2	386.5	386.8	387.1	387.3	387.3	387.4	387.6	387.7	388.8	389.9
115°	450.1	450.8	451.5	452.2	452.3	451.8	451.4	450.9	450.5	450.7	450.9
117.5°	513.7	514.2	514.7	515.2	515.1	514.5	513.9	513.2	512.7	512.6	512.6
120°	554.4	555.9	557.3	558.6	558.8	557.6	556.4	555.3	554.1	553.8	553.6
122.5°	595.5	596.6	597.6	598.6	598.8	598.2	597.6	597.0	596.4	595.7	595.2
125°	658.4	659.1	659.8	660.6	660.6	660.1	659.7	659.3	658.8	657.9	656.9
127.5°	717.6	719.1	720.6	722.1	722.6	722.1	721.5	721.1	720.6	719.2	717.9
130°	756.8	758.8	760.7	762.5	763.1	762.4	761.7	761.0	760.3	759.4	758.4
132.5°	795.8	797.7	799.6	801.4	802.1	801.6	801.1	800.5	800.1	798.9	797.8
135°	854.8	856.1	857.5	859.0	859.6	859.3	859.1	858.8	858.6	857.7	856.7
137.5°	909.5	910.7	911.8	913.1	914.0	914.5	915.2	915.7	916.4	915.3	914.4
140°	947.5	948.8	949.9	951.1	951.8	952.0	952.3	952.5	952.8	952.5	952.3
142.5°	982.3	983.4	984.6	985.8	986.6	987.0	987.4	987.8	988.3	988.1	987.8
145°	1035.7	1036.2	1036.7	1037.1	1037.7	1038.4	1039.1	1039.8	1040.5	1040.2	1040.0
147.5°	1083.5	1084.3	1085.2	1086.0	1086.7	1087.4	1088.0	1088.7	1089.3	1089.3	1089.3
150°	1116.1	1116.6	1117.0	1117.4	1117.9	1118.4	1118.8	1119.3	1119.8	1119.8	1119.8
152.5°	1143.3	1143.9	1144.6	1145.3	1145.7	1146.1	1146.3	1146.6	1146.9	1147.3	1147.6
155°	1185.4	1185.4	1185.4	1185.4	1185.5	1185.7	1185.9	1186.2	1186.4	1187.4	1188.3
157.5°	1221.5	1221.2	1220.9	1220.6	1220.6	1220.7	1220.9	1221.2	1221.3	1222.3	1223.3
160°	1244.1	1243.7	1243.2	1242.7	1242.4	1242.4	1242.4	1242.4	1242.4	1243.7	1244.8
162.5°	1264.2	1263.6	1262.9	1262.2	1262.0	1262.2	1262.4	1262.6	1262.7	1264.0	1265.1
165°	1290.4	1289.7	1289.0	1288.3	1287.9	1287.9	1287.9	1287.9	1287.9	1289.3	1290.8
167.5°	1311.1	1310.2	1309.2	1308.3	1307.9	1308.1	1308.3	1308.5	1308.6	1310.1	1311.6
170°	1323.0	1322.0	1321.1	1320.1	1319.6	1319.6	1319.6	1319.6	1319.6	1321.3	1323.0
172.5°	1332.3	1331.3	1330.4	1329.4	1328.9	1328.9	1328.9	1328.9	1328.9	1330.4	1331.9
175°	1342.0	1341.1	1340.1	1339.1	1338.7	1338.7	1338.7	1338.7	1338.7	1340.1	1341.5
177.5°	1346.2	1345.4	1344.7	1343.9	1343.5	1343.5	1343.5	1343.5	1343.5	1344.7	1345.8
180°	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1



TEST NUMBER: P332169-930

CATALOG NUMBER: S123DIW-S775D1320U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	880.9	880.9	880.9	880.9	880.9	880.9	880.9
2.5°	927.1	927.4	931.2	933.9	932.5	934.3	934.9
5°	1012.8	1028.3	1036.3	1042.3	1042.8	1043.2	1046.6
7.5°	1134.5	1151.0	1163.0	1181.3	1186.7	1192.9	1191.2
10°	1223.3	1247.6	1268.5	1279.6	1291.6	1309.0	1295.0
12.5°	1306.3	1349.4	1381.2	1398.5	1409.7	1413.2	1406.3
15°	1443.1	1499.4	1529.7	1528.8	1567.3	1584.0	1557.9
17.5°	1568.6	1620.6	1662.2	1683.6	1715.6	1722.6	1719.4
20°	1645.4	1702.2	1734.6	1771.3	1788.0	1802.9	1805.5
22.5°	1711.6	1762.6	1797.4	1828.0	1841.9	1849.0	1853.3
25°	1779.9	1820.0	1840.9	1851.5	1855.4	1854.6	1849.0
27.5°	1775.2	1778.2	1755.2	1732.6	1712.4	1689.5	1681.7
30°	1729.1	1693.2	1629.2	1592.9	1539.5	1497.3	1514.3
32.5°	1607.9	1536.5	1464.6	1385.3	1319.6	1301.0	1282.1
35°	1372.2	1246.8	1173.4	1087.9	1053.9	1019.7	996.2
37.5°	1110.2	1013.1	926.0	870.2	836.0	814.4	802.7
40°	959.9	872.5	800.7	755.5	729.4	705.2	701.7
42.5°	840.1	758.7	704.7	668.7	643.8	633.4	625.9
45°	688.0	631.3	595.0	569.4	552.8	546.3	537.8
47.5°	582.4	542.3	515.0	497.6	485.0	480.3	479.6
50°	523.3	490.0	469.9	456.2	446.5	444.7	437.9
52.5°	478.9	450.0	434.4	422.5	415.4	410.6	408.5
55°	415.7	396.5	382.5	375.6	370.1	365.3	365.3
57.5°	363.7	347.7	338.3	332.6	330.8	327.5	325.4
60°	331.7	318.0	310.7	305.6	302.2	302.6	298.8
62.5°	300.2	291.4	284.5	279.3	275.2	275.3	275.6
65°	255.7	248.8	243.7	242.0	239.5	236.4	237.3
67.5°	216.6	210.3	206.3	203.3	202.5	200.9	203.3
70°	188.7	183.9	181.0	178.4	177.6	178.0	180.1
72.5°	163.1	159.7	157.8	156.5	154.7	154.7	156.2
75°	128.1	125.5	123.8	122.5	122.1	122.1	122.1
77.5°	94.1	93.5	92.7	90.8	90.9	91.4	91.5
80°	74.3	73.0	72.6	71.7	70.4	69.5	71.7
82.5°	55.5	54.2	53.8	53.6	51.6	51.4	53.2
85°	29.8	28.6	29.0	28.6	28.6	28.2	28.2
87.5°	16.2	16.1	15.9	16.3	16.1	15.8	16.6
90°	28.2	29.1	29.8	30.3	30.8	31.2	31.7
92.5°	42.9	43.6	43.9	43.5	43.3	43.0	42.7
95°	81.0	82.0	82.5	82.5	82.5	82.5	82.5
97.5°	125.7	126.8	127.3	127.2	127.1	127.0	126.9
100°	157.5	158.2	158.8	159.3	159.8	160.3	160.7
102.5°	194.8	195.5	195.8	195.7	195.6	195.5	195.4
105°	249.6	249.6	249.8	250.3	250.7	251.2	251.7
107.5°	310.4	311.1	311.4	311.1	310.8	310.5	310.2
110°	350.7	351.6	351.9	351.4	351.0	350.5	350.0



TEST NUMBER: P332169-930

CATALOG NUMBER: S123DIW-S775D1320U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	391.0	392.2	392.6	392.6	392.5	392.4	392.3
115°	451.2	451.4	451.4	451.2	450.9	450.7	450.5
117.5°	512.5	512.4	512.1	511.4	510.8	510.1	509.5
120°	553.4	553.2	552.8	552.4	551.9	551.4	550.9
122.5°	594.5	593.9	593.3	592.6	592.0	591.3	590.7
125°	656.0	655.0	654.1	653.1	652.2	651.3	650.3
127.5°	716.6	715.3	714.0	713.0	711.9	710.9	709.7
130°	757.5	756.5	755.2	753.6	752.0	750.3	748.7
132.5°	796.6	795.6	794.3	793.0	791.8	790.5	789.3
135°	855.8	854.8	854.2	853.7	853.2	852.7	852.3
137.5°	913.4	912.4	911.5	910.6	909.7	908.8	907.9
140°	952.0	951.8	950.9	949.3	947.5	945.9	944.3
142.5°	987.6	987.3	986.6	985.3	984.1	982.8	981.5
145°	1039.8	1039.6	1039.0	1038.0	1037.1	1036.2	1035.2
147.5°	1089.3	1089.3	1088.7	1087.3	1085.8	1084.4	1083.0
150°	1119.8	1119.8	1119.1	1117.7	1116.3	1114.8	1113.5
152.5°	1148.0	1148.3	1147.9	1146.7	1145.5	1144.3	1143.0
155°	1189.3	1190.2	1189.8	1188.2	1186.6	1184.9	1183.2
157.5°	1224.3	1225.3	1225.1	1223.8	1222.5	1221.2	1219.9
160°	1246.0	1247.2	1247.3	1246.3	1245.5	1244.5	1243.5
162.5°	1266.3	1267.5	1267.3	1265.8	1264.3	1262.8	1261.3
165°	1292.2	1293.6	1293.5	1291.8	1290.2	1288.5	1286.9
167.5°	1313.0	1314.5	1314.5	1313.0	1311.6	1310.1	1308.6
170°	1324.6	1326.2	1326.2	1324.6	1323.0	1321.3	1319.6
172.5°	1333.3	1334.8	1334.7	1333.1	1331.4	1329.8	1328.1
175°	1343.0	1344.3	1344.2	1342.6	1340.9	1339.3	1337.7
177.5°	1347.0	1348.1	1348.0	1346.6	1345.3	1344.0	1342.7
180°	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1

(END OF REPORT)