

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332174-930

Luminaire Tested: **S123DIW-S775D1535U930-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332174-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIW-S775D1535U930-4F0-1E-UDD-A  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1535 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7666.5 lumens  
Efficiency: N/A  
Efficacy: 112.6 lumens/watt  
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 68.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332174-930

CATALOG NUMBER: S123DIW-S775D1535U930-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P332174-930

CATALOG NUMBER: S123DIW-S775D1535U930-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	42	42	42	35
1	95	90	87	83	85	82	79	76	66	64	62	51	50	48	37	37	36	30
2	86	79	73	68	78	72	67	62	58	54	51	45	43	41	33	32	30	25
3	79	70	63	57	71	63	57	52	51	47	43	40	37	35	30	28	26	21
4	72	62	54	48	65	56	49	44	45	41	37	36	32	30	26	24	23	19
5	66	55	47	41	59	50	43	38	41	36	32	32	28	26	24	22	20	16
6	61	49	41	36	55	45	38	33	37	31	28	29	25	22	22	19	17	14
7	56	44	37	31	51	40	34	29	33	28	24	26	23	20	20	17	15	13
8	52	40	33	27	47	37	30	25	30	25	22	24	20	18	18	16	14	11
9	48	37	29	24	44	33	27	23	28	23	19	22	18	16	17	14	12	10
10	45	33	26	22	41	31	24	20	25	20	17	20	17	14	15	13	11	9

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	9482	9482	9482	9482
5°	11309	9524	8440	9524
10°	14154	9475	7623	9475
15°	17361	9399	7096	9399
20°	20681	9279	6757	9279
25°	21960	9136	6682	9136
30°	18821	9028	6717	9028
35°	13090	8878	6787	8878
40°	9860	8702	6764	8702
45°	8187	8441	6680	8441
50°	7333	7906	6620	7906
55°	6855	7328	6536	7328
60°	6433	6725	6469	6725
65°	6044	6133	6260	6133
70°	5668	5454	5964	5454
75°	5078	4774	5465	4774
80°	4444	3918	4711	3918
85°	3483	2853	3162	2853



TEST NUMBER: P332174-930

CATALOG NUMBER: S123DIW-S775D1535U930-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	86.8	1.1
10°-20°	278.3	3.6
20°-30°	467.0	6.1
30°-40°	528.8	6.9
40°-50°	474.2	6.2
50°-60°	382.7	5.0
60°-70°	266.7	3.5
70°-80°	140.2	1.8
80°-90°	38.9	0.5
90°-100°	59.6	0.8
100°-110°	284.3	3.7
110°-120°	682.8	8.9
120°-130°	869.5	11.3
130°-140°	929.1	12.1
140°-150°	868.8	11.3
150°-160°	700.8	9.1
160°-170°	452.3	5.9
170°-180°	155.9	2.0
0°-30°	832.1	10.9
0°-40°	1360.9	17.8
0°-60°	2217.8	28.9
0°-90°	2663.5	34.7
90°-120°	1026.8	13.4
90°-150°	3694.1	48.2
90°-180°	5003.0	65.3
0°-180°	7666.5	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	881	881	881	881	881	
5°	1047	881	781	881	1047	108
15°	1558	843	637	843	1558	450
25°	1849	769	563	769	1849	811
35°	996	676	516	676	996	647
45°	538	554	439	554	538	426
55°	365	390	348	390	365	328
65°	237	241	246	241	237	236
75°	122	115	131	115	122	131
85°	28	23	26	23	28	34
90°	36	1	36	1	36	18
95°	46	74	46	74	46	39
105°	54	363	54	363	54	123
115°	717	681	717	681	717	662
125°	980	960	980	960	980	875
135°	1208	1196	1208	1196	1208	931
145°	1393	1380	1393	1380	1393	870
155°	1518	1520	1518	1520	1518	700
165°	1599	1603	1599	1603	1599	452
175°	1634	1640	1634	1640	1634	156
180°	1640	1640	1640	1640	1640	



TEST NUMBER: P332174-930

CATALOG NUMBER: S123DIW-S775D1535U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9
2.5°	934.9	934.3	932.5	933.9	931.2	927.4	927.1	923.7	913.7	913.1	910.4
5°	1046.6	1043.2	1042.8	1042.3	1036.3	1028.3	1012.8	1011.5	991.1	980.8	968.5
7.5°	1191.2	1192.9	1186.7	1181.3	1163.0	1151.0	1134.5	1113.4	1088.3	1062.7	1045.7
10°	1295.0	1309.0	1291.6	1279.6	1268.5	1247.6	1223.3	1192.9	1162.7	1127.2	1100.3
12.5°	1406.3	1413.2	1409.7	1398.5	1381.2	1349.4	1306.3	1272.8	1245.0	1185.9	1162.1
15°	1557.9	1584.0	1567.3	1528.8	1529.7	1499.4	1443.1	1381.2	1348.3	1296.7	1226.3
17.5°	1719.4	1722.6	1715.6	1683.6	1662.2	1620.6	1568.6	1509.3	1442.7	1380.1	1305.5
20°	1805.5	1802.9	1788.0	1771.3	1734.6	1702.2	1645.4	1579.2	1493.9	1432.4	1350.9
22.5°	1853.3	1849.0	1841.9	1828.0	1797.4	1762.6	1711.6	1639.3	1558.1	1473.4	1379.2
25°	1849.0	1854.6	1855.4	1851.5	1840.9	1820.0	1779.9	1722.2	1641.1	1532.3	1434.1
27.5°	1681.7	1689.5	1712.4	1732.6	1755.2	1778.2	1775.2	1746.5	1686.5	1592.6	1472.5
30°	1514.3	1497.3	1539.5	1592.9	1629.2	1693.2	1729.1	1731.2	1697.5	1616.8	1499.8
32.5°	1282.1	1301.0	1319.6	1385.3	1464.6	1536.5	1607.9	1665.3	1671.9	1618.2	1515.9
35°	996.2	1019.7	1053.9	1087.9	1173.4	1246.8	1372.2	1481.5	1568.6	1580.1	1517.4
37.5°	802.7	814.4	836.0	870.2	926.0	1013.1	1110.2	1248.3	1374.4	1468.3	1472.3
40°	701.7	705.2	729.4	755.5	800.7	872.5	959.9	1082.0	1233.1	1364.2	1418.8
42.5°	625.9	633.4	643.8	668.7	704.7	758.7	840.1	940.9	1079.5	1230.3	1337.2
45°	537.8	546.3	552.8	569.4	595.0	631.3	688.0	780.2	885.7	1041.5	1185.3
47.5°	479.6	480.3	485.0	497.6	515.0	542.3	582.4	641.6	738.4	864.7	1012.4
50°	437.9	444.7	446.5	456.2	469.9	490.0	523.3	573.6	653.1	764.0	899.8
52.5°	408.5	410.6	415.4	422.5	434.4	450.0	478.9	518.4	580.7	675.2	800.1
55°	365.3	365.3	370.1	375.6	382.5	396.5	415.7	444.7	492.1	565.6	668.9
57.5°	325.4	327.5	330.8	332.6	338.3	347.7	363.7	385.8	421.1	477.6	559.7
60°	298.8	302.6	302.2	305.6	310.7	318.0	331.7	349.6	381.2	426.4	495.5
62.5°	275.6	275.3	275.2	279.3	284.5	291.4	300.2	315.8	342.6	382.7	441.6
65°	237.3	236.4	239.5	242.0	243.7	248.8	255.7	269.3	287.2	317.2	362.8
67.5°	203.3	200.9	202.5	203.3	206.3	210.3	216.6	225.1	239.4	263.3	297.7
70°	180.1	178.0	177.6	178.4	181.0	183.9	188.7	196.7	210.0	229.2	254.4
72.5°	156.2	154.7	154.7	156.5	157.8	159.7	163.1	170.5	181.0	195.4	218.9
75°	122.1	122.1	122.1	122.5	123.8	125.5	128.1	131.9	140.0	150.3	166.0
77.5°	91.5	91.4	90.9	90.8	92.7	93.5	94.1	97.7	102.2	109.1	120.6
80°	71.7	69.5	70.4	71.7	72.6	73.0	74.3	75.1	79.0	82.8	90.9
82.5°	53.2	51.4	51.6	53.6	53.8	54.2	55.5	56.7	58.1	61.6	66.0
85°	28.2	28.2	28.6	28.6	29.0	28.6	29.8	30.3	30.3	32.4	35.0
87.5°	17.5	16.8	17.0	17.2	16.8	17.0	17.1	17.2	17.4	17.4	17.1
90°	36.5	36.0	35.5	35.0	34.4	33.6	32.5	31.4	30.3	29.3	25.8
92.5°	40.4	40.1	39.8	39.5	39.1	38.2	36.4	34.7	32.9	31.2	28.5
95°	46.3	46.3	46.3	46.3	46.3	45.3	43.5	41.6	39.7	37.7	34.8
97.5°	50.2	50.0	49.7	49.4	49.2	47.9	45.7	43.6	41.4	39.2	58.8
100°	51.2	51.0	50.6	50.4	50.1	48.9	46.7	44.5	42.4	40.2	82.5
102.5°	52.2	51.7	51.2	50.7	50.2	53.3	60.1	66.8	73.5	80.2	126.4
105°	53.6	53.1	52.6	52.0	51.4	75.2	123.1	171.0	219.0	266.9	291.3
107.5°	168.4	204.6	240.7	276.9	313.0	348.6	383.8	418.9	454.1	489.3	485.4
110°	335.2	373.9	412.6	451.3	490.1	514.0	522.9	531.8	540.8	549.7	546.7



TEST NUMBER: P332174-930

CATALOG NUMBER: S123DIW-S775D1535U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	575.0	583.3	591.4	599.6	607.8	611.8	611.6	611.5	611.3	611.1	608.1
115°	716.7	715.6	714.5	713.5	712.3	710.5	707.8	705.1	702.3	699.6	697.2
117.5°	796.1	796.0	795.7	795.5	795.3	794.1	791.9	789.8	787.6	785.5	784.2
120°	850.8	850.8	850.8	850.8	850.8	849.7	847.5	845.4	843.2	841.0	840.2
122.5°	904.4	904.2	903.9	903.8	903.5	902.7	901.2	899.6	898.1	896.6	895.5
125°	980.0	979.4	978.8	978.4	977.8	977.2	976.7	976.2	975.7	975.1	974.0
127.5°	1052.6	1053.1	1053.7	1054.3	1054.8	1054.6	1053.8	1052.9	1052.0	1051.2	1049.9
130°	1099.4	1099.9	1100.5	1101.1	1101.6	1101.3	1100.2	1099.1	1098.0	1097.0	1095.9
132.5°	1142.3	1143.0	1143.9	1144.6	1145.3	1145.2	1144.1	1143.0	1141.9	1140.8	1140.0
135°	1207.9	1208.7	1209.5	1210.3	1211.1	1211.1	1210.3	1209.5	1208.7	1207.9	1206.8
137.5°	1269.6	1270.1	1270.6	1271.2	1271.7	1271.4	1270.1	1268.8	1267.5	1266.2	1265.6
140°	1306.6	1307.2	1307.7	1308.2	1308.8	1308.5	1307.4	1306.4	1305.3	1304.2	1303.3
142.5°	1340.8	1341.5	1342.2	1343.0	1343.8	1343.7	1342.9	1342.0	1341.1	1340.3	1339.5
145°	1393.2	1393.2	1393.2	1393.2	1393.2	1392.9	1392.4	1391.8	1391.2	1390.7	1390.2
147.5°	1432.2	1433.4	1434.7	1435.9	1437.1	1437.5	1437.0	1436.4	1435.9	1435.3	1434.8
150°	1461.4	1462.2	1463.1	1463.9	1464.7	1464.8	1464.3	1463.7	1463.1	1462.6	1462.1
152.5°	1484.8	1486.0	1487.3	1488.6	1489.8	1490.0	1489.0	1488.0	1487.0	1486.0	1485.7
155°	1517.5	1519.1	1520.7	1522.3	1524.0	1524.1	1522.7	1521.4	1520.0	1518.7	1518.4
157.5°	1545.0	1547.1	1549.2	1551.4	1553.5	1553.7	1552.1	1550.5	1548.8	1547.2	1547.5
160°	1562.6	1564.5	1566.4	1568.2	1570.2	1570.3	1568.6	1567.1	1565.5	1563.8	1564.1
162.5°	1579.2	1580.9	1582.5	1584.2	1585.8	1585.8	1584.0	1582.1	1580.3	1578.4	1578.7
165°	1599.1	1601.0	1603.0	1604.8	1606.7	1606.6	1604.4	1602.2	1600.1	1597.9	1598.2
167.5°	1613.6	1615.7	1617.9	1620.0	1622.2	1622.2	1620.0	1617.9	1615.7	1613.6	1613.6
170°	1622.3	1624.5	1626.6	1628.8	1631.0	1631.0	1628.8	1626.6	1624.5	1622.3	1622.3
172.5°	1627.2	1629.5	1632.0	1634.3	1636.7	1636.8	1634.7	1632.5	1630.4	1628.2	1627.9
175°	1634.5	1636.6	1638.8	1641.0	1643.2	1643.3	1641.4	1639.5	1637.6	1635.7	1635.4
177.5°	1636.7	1638.8	1641.0	1643.2	1645.4	1645.6	1643.8	1642.1	1640.4	1638.7	1638.4
180°	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5



TEST NUMBER: P332174-930

CATALOG NUMBER: S123DIW-S775D1535U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9
2.5°	908.2	905.6	902.8	898.1	894.0	888.1	886.4	884.4	878.2	872.8	868.7
5°	963.8	953.5	938.6	925.0	913.9	898.9	890.4	881.4	868.6	857.0	847.7
7.5°	1021.8	1001.7	978.4	953.3	929.9	907.4	889.2	873.0	855.1	838.1	824.9
10°	1067.9	1038.9	1006.5	971.4	941.6	912.6	888.2	866.9	843.8	823.8	807.1
12.5°	1120.5	1077.5	1032.7	990.3	954.9	914.6	885.2	858.0	831.8	807.7	789.0
15°	1182.8	1128.1	1075.1	1016.7	963.0	912.6	877.6	843.4	813.1	788.3	764.4
17.5°	1239.4	1177.5	1107.7	1036.7	971.8	912.1	863.1	824.4	786.5	756.3	732.5
20°	1271.5	1201.1	1122.1	1048.3	976.6	910.0	856.2	810.1	769.2	737.1	710.2
22.5°	1299.2	1216.8	1135.1	1056.1	976.2	904.5	843.6	796.1	751.7	720.4	691.8
25°	1327.9	1229.2	1147.3	1054.7	965.5	891.2	822.9	769.2	724.7	688.0	658.6
27.5°	1352.4	1228.4	1131.1	1031.5	948.6	874.2	801.2	743.6	696.4	656.6	626.6
30°	1368.8	1230.1	1114.4	1015.9	932.2	855.3	784.5	726.4	676.9	636.4	608.2
32.5°	1379.1	1229.1	1099.1	994.0	906.2	838.3	766.4	706.3	655.4	615.6	588.4
35°	1385.0	1221.6	1072.6	948.8	864.3	798.2	738.0	675.6	622.3	585.1	554.5
37.5°	1373.1	1205.7	1041.9	905.3	812.8	747.6	697.0	643.9	592.9	552.0	525.5
40°	1354.3	1195.6	1018.0	874.6	777.2	714.5	671.4	619.3	568.9	530.1	505.3
42.5°	1318.4	1174.7	991.6	840.4	740.4	677.6	638.0	594.4	546.7	510.3	485.6
45°	1230.9	1129.4	952.3	789.2	685.9	621.0	586.0	554.5	511.4	475.9	454.5
47.5°	1109.5	1061.2	895.2	735.2	629.1	566.6	530.3	504.8	473.4	444.7	424.3
50°	1025.2	1005.2	856.6	698.3	591.2	530.1	495.1	472.1	449.5	420.9	402.1
52.5°	927.9	940.3	811.5	660.1	552.5	492.5	459.6	441.3	420.8	397.3	380.9
55°	790.9	835.7	733.7	595.8	495.1	437.9	406.8	390.5	378.6	361.1	347.0
57.5°	662.6	719.7	649.5	529.7	438.7	389.4	359.5	341.8	334.1	325.0	313.9
60°	586.4	642.8	589.5	485.3	400.8	353.8	327.3	312.4	304.8	298.3	288.9
62.5°	518.5	575.5	530.7	440.3	363.5	320.0	297.0	282.4	276.4	273.0	265.1
65°	425.1	474.2	444.3	370.1	310.3	271.9	250.9	240.8	235.2	233.9	228.8
67.5°	346.0	383.4	361.6	307.0	259.9	226.7	209.0	200.2	196.0	195.6	191.8
70°	294.1	329.1	312.4	262.9	222.4	196.3	181.0	173.3	170.7	170.3	168.2
72.5°	253.8	278.2	265.0	223.6	192.3	168.7	157.4	149.4	146.5	147.1	145.6
75°	187.8	206.2	198.4	169.9	144.7	129.3	119.9	114.8	112.3	113.6	111.9
77.5°	135.1	146.8	139.8	120.0	104.5	93.4	86.5	83.3	81.0	81.0	80.1
80°	102.0	108.8	105.0	93.0	80.2	70.8	65.3	63.2	61.9	61.5	61.1
82.5°	72.6	78.4	73.9	65.7	57.0	51.4	48.3	45.4	44.5	44.8	44.3
85°	36.7	38.8	37.1	32.0	28.6	26.0	24.3	23.1	22.2	22.6	21.8
87.5°	17.0	16.7	15.0	13.0	11.7	10.2	9.7	8.5	8.3	8.8	9.0
90°	22.2	18.7	15.2	12.1	9.4	6.6	3.9	1.2	3.9	6.6	9.4
92.5°	25.9	23.2	20.5	19.6	20.4	21.1	21.9	22.7	21.9	21.1	20.4
95°	31.8	28.9	25.8	29.9	41.0	52.2	63.3	74.4	63.3	52.2	41.0
97.5°	78.3	97.8	117.2	129.5	134.4	139.5	144.5	149.4	144.5	139.5	134.4
100°	124.7	167.0	209.2	227.6	222.3	216.8	211.4	206.0	211.4	216.8	222.3
102.5°	172.5	218.7	264.8	285.9	282.0	278.2	274.3	270.4	274.3	278.2	282.0
105°	315.7	340.1	364.4	375.1	372.2	369.2	366.2	363.2	366.2	369.2	372.2
107.5°	481.6	477.7	473.9	470.8	468.4	465.9	463.6	461.2	463.6	465.9	468.4
110°	543.7	540.8	537.8	535.2	533.0	530.8	528.7	526.5	528.7	530.8	533.0





TEST NUMBER: P332174-930

CATALOG NUMBER: S123DIW-S775D1535U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	605.2	602.2	599.2	596.7	594.8	592.9	590.9	589.0	590.9	592.9	594.8
115°	694.7	692.4	689.9	687.9	686.2	684.6	683.0	681.3	683.0	684.6	686.2
117.5°	782.9	781.7	780.5	778.9	776.8	774.8	772.8	770.8	772.8	774.8	776.8
120°	839.4	838.5	837.8	836.2	833.7	831.3	828.8	826.4	828.8	831.3	833.7
122.5°	894.5	893.5	892.5	891.0	888.9	887.0	884.9	883.0	884.9	887.0	888.9
125°	972.9	971.8	970.8	969.1	966.9	964.8	962.6	960.4	962.6	964.8	966.9
127.5°	1048.6	1047.3	1045.9	1044.2	1042.0	1039.9	1037.7	1035.5	1037.7	1039.9	1042.0
130°	1094.8	1093.7	1092.7	1091.0	1088.8	1086.7	1084.5	1082.3	1084.5	1086.7	1088.8
132.5°	1139.1	1138.2	1137.4	1135.9	1133.7	1131.6	1129.4	1127.2	1129.4	1131.6	1133.7
135°	1205.7	1204.6	1203.5	1202.2	1200.6	1199.0	1197.3	1195.7	1197.3	1199.0	1200.6
137.5°	1264.9	1264.4	1263.8	1262.4	1260.4	1258.3	1256.3	1254.2	1256.3	1258.3	1260.4
140°	1302.5	1301.7	1300.9	1299.8	1298.1	1296.5	1294.9	1293.2	1294.9	1296.5	1298.1
142.5°	1338.6	1337.8	1337.0	1335.8	1334.2	1332.5	1330.9	1329.3	1330.9	1332.5	1334.2
145°	1389.6	1389.1	1388.5	1387.3	1385.4	1383.6	1381.6	1379.7	1381.6	1383.6	1385.4
147.5°	1434.3	1433.7	1433.1	1432.2	1431.0	1429.8	1428.6	1427.3	1428.6	1429.8	1431.0
150°	1461.6	1461.0	1460.4	1459.8	1459.0	1458.2	1457.3	1456.5	1457.3	1458.2	1459.0
152.5°	1485.4	1485.1	1484.7	1484.4	1484.0	1483.6	1483.3	1482.9	1483.3	1483.6	1484.0
155°	1518.2	1517.9	1517.6	1517.8	1518.3	1518.8	1519.4	1519.9	1519.4	1518.8	1518.3
157.5°	1547.8	1548.0	1548.3	1548.5	1548.5	1548.6	1548.7	1548.7	1548.7	1548.6	1548.5
160°	1564.3	1564.6	1564.9	1565.1	1565.5	1565.7	1565.9	1566.3	1565.9	1565.7	1565.5
162.5°	1579.0	1579.2	1579.5	1580.0	1580.7	1581.4	1582.1	1582.8	1582.1	1581.4	1580.7
165°	1598.5	1598.7	1599.0	1599.5	1600.4	1601.2	1602.0	1602.8	1602.0	1601.2	1600.4
167.5°	1613.6	1613.6	1613.6	1614.0	1615.2	1616.2	1617.3	1618.4	1617.3	1616.2	1615.2
170°	1622.3	1622.3	1622.3	1622.9	1623.9	1625.0	1626.1	1627.2	1626.1	1625.0	1623.9
172.5°	1627.7	1627.5	1627.3	1627.8	1629.1	1630.4	1631.7	1633.0	1631.7	1630.4	1629.1
175°	1635.2	1634.9	1634.6	1635.2	1636.6	1637.9	1639.2	1640.5	1639.2	1637.9	1636.6
177.5°	1638.2	1638.0	1637.8	1638.2	1639.3	1640.4	1641.4	1642.5	1641.4	1640.4	1639.3
180°	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5



TEST NUMBER: P332174-930

CATALOG NUMBER: S123DIW-S775D1535U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9
2.5°	866.3	863.9	860.5	855.3	851.3	844.7	844.7	845.8	845.8	845.5	844.7
5°	840.0	833.6	825.9	816.9	807.6	798.2	796.5	793.0	790.5	788.8	786.6
7.5°	812.3	800.9	789.7	777.1	765.7	756.3	749.7	744.2	740.7	736.9	734.3
10°	793.4	779.3	766.1	752.9	738.4	726.9	719.7	714.5	710.7	707.3	705.6
12.5°	771.3	755.1	740.5	728.0	712.1	700.3	693.3	691.0	686.4	679.2	675.5
15°	738.8	723.9	706.4	687.2	679.5	665.0	656.9	653.1	650.4	644.9	643.2
17.5°	711.1	691.5	671.9	657.5	643.3	631.5	627.0	622.2	618.8	614.2	612.9
20°	688.9	671.4	653.5	638.1	623.1	610.3	606.5	603.1	599.7	597.5	595.8
22.5°	666.3	648.9	634.0	619.6	603.7	595.3	591.2	587.4	585.0	583.6	581.9
25°	634.7	619.3	602.7	589.9	577.1	571.5	568.9	566.8	565.1	563.0	562.6
27.5°	606.3	589.6	576.1	564.2	555.0	550.3	547.9	546.8	547.2	548.0	548.5
30°	585.1	569.8	558.7	548.5	540.0	535.7	535.2	535.2	537.0	537.4	538.3
32.5°	565.7	553.1	542.0	532.1	525.6	522.7	524.3	524.3	525.7	526.8	528.3
35°	537.4	526.3	517.7	509.2	503.7	504.9	505.8	506.6	508.7	511.4	513.1
37.5°	510.3	500.7	491.8	485.1	482.6	484.9	486.9	488.7	491.2	493.2	494.9
40°	490.8	483.6	475.1	469.0	469.9	471.2	473.0	475.1	477.2	478.5	480.2
42.5°	472.7	465.1	458.7	453.7	454.9	456.6	457.5	458.7	461.1	463.4	464.5
45°	445.2	439.2	433.3	430.2	431.1	431.9	432.8	434.1	436.2	437.9	438.4
47.5°	414.2	410.0	406.0	403.1	404.5	404.1	405.2	408.0	408.6	409.7	412.1
50°	394.4	390.5	385.9	385.0	385.0	385.0	385.4	388.8	388.8	390.5	392.2
52.5°	372.5	370.1	367.0	365.5	364.8	364.8	366.6	368.4	369.0	371.5	373.2
55°	340.1	337.6	335.1	333.8	332.9	333.8	337.2	338.0	340.1	341.4	342.8
57.5°	306.5	304.5	302.5	301.7	301.6	302.7	304.6	307.1	307.7	311.6	313.6
60°	284.3	281.3	279.6	279.6	278.8	282.6	281.7	286.0	286.8	289.3	292.4
62.5°	261.4	257.4	256.7	256.7	257.9	259.0	260.2	262.0	264.3	267.5	269.9
65°	224.5	222.4	225.3	224.9	224.0	226.7	226.7	228.8	231.3	234.3	239.0
67.5°	189.6	188.5	188.7	188.7	190.0	191.5	192.7	194.5	197.6	200.8	203.8
70°	166.0	167.3	165.2	166.9	168.2	168.6	169.4	172.0	175.5	177.6	181.0
72.5°	143.2	143.1	143.3	144.0	145.3	146.0	146.9	149.9	153.6	155.4	158.1
75°	110.1	109.7	111.0	111.0	113.1	114.0	114.8	116.1	119.5	122.1	124.2
77.5°	80.4	81.0	80.6	82.1	81.5	81.7	84.3	85.6	85.9	91.0	92.1
80°	60.6	61.5	61.9	62.3	62.8	61.9	64.9	66.1	66.1	69.1	71.3
82.5°	43.5	44.0	45.2	45.6	45.7	46.6	46.8	47.7	48.8	50.1	52.8
85°	21.8	23.1	23.5	23.1	23.5	22.6	23.9	24.3	24.8	24.8	24.8
87.5°	9.2	10.2	10.6	11.6	12.0	13.0	13.2	12.8	13.0	14.3	13.0
90°	12.1	15.2	18.7	22.2	25.8	29.3	30.3	31.4	32.5	33.6	34.4
92.5°	19.6	20.5	23.2	25.9	28.5	31.2	32.9	34.7	36.4	38.2	39.1
95°	29.9	25.8	28.9	31.8	34.8	37.7	39.7	41.6	43.5	45.3	46.3
97.5°	129.5	117.2	97.8	78.3	58.8	39.2	41.4	43.6	45.7	47.9	49.2
100°	227.6	209.2	167.0	124.7	82.5	40.2	42.4	44.5	46.7	48.9	50.1
102.5°	285.9	264.8	218.7	172.5	126.4	80.2	73.5	66.8	60.1	53.3	50.2
105°	375.1	364.4	340.1	315.7	291.3	266.9	219.0	171.0	123.1	75.2	51.4
107.5°	470.8	473.9	477.7	481.6	485.4	489.3	454.1	418.9	383.8	348.6	313.0
110°	535.2	537.8	540.8	543.7	546.7	549.7	540.8	531.8	522.9	514.0	490.1



TEST NUMBER: P332174-930

CATALOG NUMBER: S123DIW-S775D1535U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	596.7	599.2	602.2	605.2	608.1	611.1	611.3	611.5	611.6	611.8	607.8
115°	687.9	689.9	692.4	694.7	697.2	699.6	702.3	705.1	707.8	710.5	712.3
117.5°	778.9	780.5	781.7	782.9	784.2	785.5	787.6	789.8	791.9	794.1	795.3
120°	836.2	837.8	838.5	839.4	840.2	841.0	843.2	845.4	847.5	849.7	850.8
122.5°	891.0	892.5	893.5	894.5	895.5	896.6	898.1	899.6	901.2	902.7	903.5
125°	969.1	970.8	971.8	972.9	974.0	975.1	975.7	976.2	976.7	977.2	977.8
127.5°	1044.2	1045.9	1047.3	1048.6	1049.9	1051.2	1052.0	1052.9	1053.8	1054.6	1054.8
130°	1091.0	1092.7	1093.7	1094.8	1095.9	1097.0	1098.0	1099.1	1100.2	1101.3	1101.6
132.5°	1135.9	1137.4	1138.2	1139.1	1140.0	1140.8	1141.9	1143.0	1144.1	1145.2	1145.3
135°	1202.2	1203.5	1204.6	1205.7	1206.8	1207.9	1208.7	1209.5	1210.3	1211.1	1211.1
137.5°	1262.4	1263.8	1264.4	1264.9	1265.6	1266.2	1267.5	1268.8	1270.1	1271.4	1271.7
140°	1299.8	1300.9	1301.7	1302.5	1303.3	1304.2	1305.3	1306.4	1307.4	1308.5	1308.8
142.5°	1335.8	1337.0	1337.8	1338.6	1339.5	1340.3	1341.1	1342.0	1342.9	1343.7	1343.8
145°	1387.3	1388.5	1389.1	1389.6	1390.2	1390.7	1391.2	1391.8	1392.4	1392.9	1393.2
147.5°	1432.2	1433.1	1433.7	1434.3	1434.8	1435.3	1435.9	1436.4	1437.0	1437.5	1437.1
150°	1459.8	1460.4	1461.0	1461.6	1462.1	1462.6	1463.1	1463.7	1464.3	1464.8	1464.7
152.5°	1484.4	1484.7	1485.1	1485.4	1485.7	1486.0	1487.0	1488.0	1489.0	1490.0	1489.8
155°	1517.8	1517.6	1517.9	1518.2	1518.4	1518.7	1520.0	1521.4	1522.7	1524.1	1524.0
157.5°	1548.5	1548.3	1548.0	1547.8	1547.5	1547.2	1548.8	1550.5	1552.1	1553.7	1553.5
160°	1565.1	1564.9	1564.6	1564.3	1564.1	1563.8	1565.5	1567.1	1568.6	1570.3	1570.2
162.5°	1580.0	1579.5	1579.2	1579.0	1578.7	1578.4	1580.3	1582.1	1584.0	1585.8	1585.8
165°	1599.5	1599.0	1598.7	1598.5	1598.2	1597.9	1600.1	1602.2	1604.4	1606.6	1606.7
167.5°	1614.0	1613.6	1613.6	1613.6	1613.6	1613.6	1615.7	1617.9	1620.0	1622.2	1622.2
170°	1622.9	1622.3	1622.3	1622.3	1622.3	1622.3	1624.5	1626.6	1628.8	1631.0	1631.0
172.5°	1627.8	1627.3	1627.5	1627.7	1627.9	1628.2	1630.4	1632.5	1634.7	1636.8	1636.7
175°	1635.2	1634.6	1634.9	1635.2	1635.4	1635.7	1637.6	1639.5	1641.4	1643.3	1643.2
177.5°	1638.2	1637.8	1638.0	1638.2	1638.4	1638.7	1640.4	1642.1	1643.8	1645.6	1645.4
180°	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5



TEST NUMBER: P332174-930

CATALOG NUMBER: S123DIW-S775D1535U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9
2.5°	842.4	842.0	844.4	842.7	844.4	842.0	842.4	844.7	845.5	845.8	845.8
5°	784.1	785.4	781.1	781.1	781.1	785.4	784.1	786.6	788.8	790.5	793.0
7.5°	732.1	730.3	730.4	728.1	730.4	730.3	732.1	734.3	736.9	740.7	744.2
10°	700.4	697.9	697.0	697.4	697.0	697.9	700.4	705.6	707.3	710.7	714.5
12.5°	674.1	673.6	668.0	668.1	668.0	673.6	674.1	675.5	679.2	686.4	691.0
15°	643.2	635.1	634.2	636.8	634.2	635.1	643.2	643.2	644.9	650.4	653.1
17.5°	612.2	608.0	608.2	606.9	608.2	608.0	612.2	612.9	614.2	618.8	622.2
20°	595.8	593.3	592.9	589.9	592.9	593.3	595.8	595.8	597.5	599.7	603.1
22.5°	580.8	580.0	580.2	576.9	580.2	580.0	580.8	581.9	583.6	585.0	587.4
25°	562.1	564.3	562.6	562.6	562.6	564.3	562.1	562.6	563.0	565.1	566.8
27.5°	549.5	549.4	548.5	548.5	548.5	549.4	549.5	548.5	548.0	547.2	546.8
30°	540.0	539.5	540.4	540.4	540.4	539.5	540.0	538.3	537.4	537.0	535.2
32.5°	530.4	531.0	531.2	531.5	531.2	531.0	530.4	528.3	526.8	525.7	524.3
35°	515.6	516.0	517.3	516.5	517.3	516.0	515.6	513.1	511.4	508.7	506.6
37.5°	495.6	497.6	497.2	497.8	497.2	497.6	495.6	494.9	493.2	491.2	488.7
40°	480.6	481.9	481.4	481.4	481.4	481.9	480.6	480.2	478.5	477.2	475.1
42.5°	465.2	466.2	465.0	464.4	465.0	466.2	465.2	464.5	463.4	461.1	458.7
45°	440.0	439.2	440.5	438.8	440.5	439.2	440.0	438.4	437.9	436.2	434.1
47.5°	411.9	412.7	413.1	414.3	413.1	412.7	411.9	412.1	409.7	408.6	408.0
50°	393.1	395.7	395.7	395.3	395.7	395.7	393.1	392.2	390.5	388.8	388.8
52.5°	374.6	375.9	377.6	377.5	377.6	375.9	374.6	373.2	371.5	369.0	368.4
55°	346.2	347.0	347.9	348.3	347.9	347.0	346.2	342.8	341.4	340.1	338.0
57.5°	316.6	316.3	318.3	318.9	318.3	316.3	316.6	313.6	311.6	307.7	307.1
60°	295.8	295.8	299.2	300.5	299.2	295.8	295.8	292.4	289.3	286.8	286.0
62.5°	273.6	275.0	278.3	276.5	278.3	275.0	273.6	269.9	267.5	264.3	262.0
65°	241.2	244.6	244.2	245.8	244.2	244.6	241.2	239.0	234.3	231.3	228.8
67.5°	207.2	209.4	212.5	212.7	212.5	209.4	207.2	203.8	200.8	197.6	194.5
70°	184.4	186.5	188.3	189.5	188.3	186.5	184.4	181.0	177.6	175.5	172.0
72.5°	162.2	163.3	167.4	165.6	167.4	163.3	162.2	158.1	155.4	153.6	149.9
75°	127.2	130.2	132.7	131.4	132.7	130.2	127.2	124.2	122.1	119.5	116.1
77.5°	94.1	97.0	98.2	97.2	98.2	97.0	94.1	92.1	91.0	85.9	85.6
80°	74.3	73.9	76.4	76.0	76.4	73.9	74.3	71.3	69.1	66.1	66.1
82.5°	54.5	54.1	55.2	55.5	55.2	54.1	54.5	52.8	50.1	48.8	47.7
85°	26.5	27.7	26.0	25.6	26.0	27.7	26.5	24.8	24.8	24.8	24.3
87.5°	13.1	13.2	13.0	12.8	13.0	13.2	13.1	13.0	14.3	13.0	12.8
90°	35.0	35.5	36.0	36.5	36.0	35.5	35.0	34.4	33.6	32.5	31.4
92.5°	39.5	39.8	40.1	40.4	40.1	39.8	39.5	39.1	38.2	36.4	34.7
95°	46.3	46.3	46.3	46.3	46.3	46.3	46.3	46.3	45.3	43.5	41.6
97.5°	49.4	49.7	50.0	50.2	50.0	49.7	49.4	49.2	47.9	45.7	43.6
100°	50.4	50.6	51.0	51.2	51.0	50.6	50.4	50.1	48.9	46.7	44.5
102.5°	50.7	51.2	51.7	52.2	51.7	51.2	50.7	50.2	53.3	60.1	66.8
105°	52.0	52.6	53.1	53.6	53.1	52.6	52.0	51.4	75.2	123.1	171.0
107.5°	276.9	240.7	204.6	168.4	204.6	240.7	276.9	313.0	348.6	383.8	418.9
110°	451.3	412.6	373.9	335.2	373.9	412.6	451.3	490.1	514.0	522.9	531.8



TEST NUMBER: P332174-930

CATALOG NUMBER: S123DIW-S775D1535U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	599.6	591.4	583.3	575.0	583.3	591.4	599.6	607.8	611.8	611.6	611.5
115°	713.5	714.5	715.6	716.7	715.6	714.5	713.5	712.3	710.5	707.8	705.1
117.5°	795.5	795.7	796.0	796.1	796.0	795.7	795.5	795.3	794.1	791.9	789.8
120°	850.8	850.8	850.8	850.8	850.8	850.8	850.8	850.8	849.7	847.5	845.4
122.5°	903.8	903.9	904.2	904.4	904.2	903.9	903.8	903.5	902.7	901.2	899.6
125°	978.4	978.8	979.4	980.0	979.4	978.8	978.4	977.8	977.2	976.7	976.2
127.5°	1054.3	1053.7	1053.1	1052.6	1053.1	1053.7	1054.3	1054.8	1054.6	1053.8	1052.9
130°	1101.1	1100.5	1099.9	1099.4	1099.9	1100.5	1101.1	1101.6	1101.3	1100.2	1099.1
132.5°	1144.6	1143.9	1143.0	1142.3	1143.0	1143.9	1144.6	1145.3	1145.2	1144.1	1143.0
135°	1210.3	1209.5	1208.7	1207.9	1208.7	1209.5	1210.3	1211.1	1211.1	1210.3	1209.5
137.5°	1271.2	1270.6	1270.1	1269.6	1270.1	1270.6	1271.2	1271.7	1271.4	1270.1	1268.8
140°	1308.2	1307.7	1307.2	1306.6	1307.2	1307.7	1308.2	1308.8	1308.5	1307.4	1306.4
142.5°	1343.0	1342.2	1341.5	1340.8	1341.5	1342.2	1343.0	1343.8	1343.7	1342.9	1342.0
145°	1393.2	1393.2	1393.2	1393.2	1393.2	1393.2	1393.2	1393.2	1392.9	1392.4	1391.8
147.5°	1435.9	1434.7	1433.4	1432.2	1433.4	1434.7	1435.9	1437.1	1437.5	1437.0	1436.4
150°	1463.9	1463.1	1462.2	1461.4	1462.2	1463.1	1463.9	1464.7	1464.8	1464.3	1463.7
152.5°	1488.6	1487.3	1486.0	1484.8	1486.0	1487.3	1488.6	1489.8	1490.0	1489.0	1488.0
155°	1522.3	1520.7	1519.1	1517.5	1519.1	1520.7	1522.3	1524.0	1524.1	1522.7	1521.4
157.5°	1551.4	1549.2	1547.1	1545.0	1547.1	1549.2	1551.4	1553.5	1553.7	1552.1	1550.5
160°	1568.2	1566.4	1564.5	1562.6	1564.5	1566.4	1568.2	1570.2	1570.3	1568.6	1567.1
162.5°	1584.2	1582.5	1580.9	1579.2	1580.9	1582.5	1584.2	1585.8	1585.8	1584.0	1582.1
165°	1604.8	1603.0	1601.0	1599.1	1601.0	1603.0	1604.8	1606.7	1606.6	1604.4	1602.2
167.5°	1620.0	1617.9	1615.7	1613.6	1615.7	1617.9	1620.0	1622.2	1622.2	1620.0	1617.9
170°	1628.8	1626.6	1624.5	1622.3	1624.5	1626.6	1628.8	1631.0	1631.0	1628.8	1626.6
172.5°	1634.3	1632.0	1629.5	1627.2	1629.5	1632.0	1634.3	1636.7	1636.8	1634.7	1632.5
175°	1641.0	1638.8	1636.6	1634.5	1636.6	1638.8	1641.0	1643.2	1643.3	1641.4	1639.5
177.5°	1643.2	1641.0	1638.8	1636.7	1638.8	1641.0	1643.2	1645.4	1645.6	1643.8	1642.1
180°	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5



TEST NUMBER: P332174-930

CATALOG NUMBER: S123DIW-S775D1535U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9
2.5°	844.7	844.7	851.3	855.3	860.5	863.9	866.3	868.7	872.8	878.2	884.4
5°	796.5	798.2	807.6	816.9	825.9	833.6	840.0	847.7	857.0	868.6	881.4
7.5°	749.7	756.3	765.7	777.1	789.7	800.9	812.3	824.9	838.1	855.1	873.0
10°	719.7	726.9	738.4	752.9	766.1	779.3	793.4	807.1	823.8	843.8	866.9
12.5°	693.3	700.3	712.1	728.0	740.5	755.1	771.3	789.0	807.7	831.8	858.0
15°	656.9	665.0	679.5	687.2	706.4	723.9	738.8	764.4	788.3	813.1	843.4
17.5°	627.0	631.5	643.3	657.5	671.9	691.5	711.1	732.5	756.3	786.5	824.4
20°	606.5	610.3	623.1	638.1	653.5	671.4	688.9	710.2	737.1	769.2	810.1
22.5°	591.2	595.3	603.7	619.6	634.0	648.9	666.3	691.8	720.4	751.7	796.1
25°	568.9	571.5	577.1	589.9	602.7	619.3	634.7	658.6	688.0	724.7	769.2
27.5°	547.9	550.3	555.0	564.2	576.1	589.6	606.3	626.6	656.6	696.4	743.6
30°	535.2	535.7	540.0	548.5	558.7	569.8	585.1	608.2	636.4	676.9	726.4
32.5°	524.3	522.7	525.6	532.1	542.0	553.1	565.7	588.4	615.6	655.4	706.3
35°	505.8	504.9	503.7	509.2	517.7	526.3	537.4	554.5	585.1	622.3	675.6
37.5°	486.9	484.9	482.6	485.1	491.8	500.7	510.3	525.5	552.0	592.9	643.9
40°	473.0	471.2	469.9	469.0	475.1	483.6	490.8	505.3	530.1	568.9	619.3
42.5°	457.5	456.6	454.9	453.7	458.7	465.1	472.7	485.6	510.3	546.7	594.4
45°	432.8	431.9	431.1	430.2	433.3	439.2	445.2	454.5	475.9	511.4	554.5
47.5°	405.2	404.1	404.5	403.1	406.0	410.0	414.2	424.3	444.7	473.4	504.8
50°	385.4	385.0	385.0	385.0	385.9	390.5	394.4	402.1	420.9	449.5	472.1
52.5°	366.6	364.8	364.8	365.5	367.0	370.1	372.5	380.9	397.3	420.8	441.3
55°	337.2	333.8	332.9	333.8	335.1	337.6	340.1	347.0	361.1	378.6	390.5
57.5°	304.6	302.7	301.6	301.7	302.5	304.5	306.5	313.9	325.0	334.1	341.8
60°	281.7	282.6	278.8	279.6	279.6	281.3	284.3	288.9	298.3	304.8	312.4
62.5°	260.2	259.0	257.9	256.7	256.7	257.4	261.4	265.1	273.0	276.4	282.4
65°	226.7	226.7	224.0	224.9	225.3	222.4	224.5	228.8	233.9	235.2	240.8
67.5°	192.7	191.5	190.0	188.7	188.7	188.5	189.6	191.8	195.6	196.0	200.2
70°	169.4	168.6	168.2	166.9	165.2	167.3	166.0	168.2	170.3	170.7	173.3
72.5°	146.9	146.0	145.3	144.0	143.3	143.1	143.2	145.6	147.1	146.5	149.4
75°	114.8	114.0	113.1	111.0	111.0	109.7	110.1	111.9	113.6	112.3	114.8
77.5°	84.3	81.7	81.5	82.1	80.6	81.0	80.4	80.1	81.0	81.0	83.3
80°	64.9	61.9	62.8	62.3	61.9	61.5	60.6	61.1	61.5	61.9	63.2
82.5°	46.8	46.6	45.7	45.6	45.2	44.0	43.5	44.3	44.8	44.5	45.4
85°	23.9	22.6	23.5	23.1	23.5	23.1	21.8	21.8	22.6	22.2	23.1
87.5°	13.2	13.0	12.0	11.6	10.6	10.2	9.2	9.0	8.8	8.3	8.5
90°	30.3	29.3	25.8	22.2	18.7	15.2	12.1	9.4	6.6	3.9	1.2
92.5°	32.9	31.2	28.5	25.9	23.2	20.5	19.6	20.4	21.1	21.9	22.7
95°	39.7	37.7	34.8	31.8	28.9	25.8	29.9	41.0	52.2	63.3	74.4
97.5°	41.4	39.2	58.8	78.3	97.8	117.2	129.5	134.4	139.5	144.5	149.4
100°	42.4	40.2	82.5	124.7	167.0	209.2	227.6	222.3	216.8	211.4	206.0
102.5°	73.5	80.2	126.4	172.5	218.7	264.8	285.9	282.0	278.2	274.3	270.4
105°	219.0	266.9	291.3	315.7	340.1	364.4	375.1	372.2	369.2	366.2	363.2
107.5°	454.1	489.3	485.4	481.6	477.7	473.9	470.8	468.4	465.9	463.6	461.2
110°	540.8	549.7	546.7	543.7	540.8	537.8	535.2	533.0	530.8	528.7	526.5



TEST NUMBER: P332174-930

CATALOG NUMBER: S123DIW-S775D1535U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	611.3	611.1	608.1	605.2	602.2	599.2	596.7	594.8	592.9	590.9	589.0
115°	702.3	699.6	697.2	694.7	692.4	689.9	687.9	686.2	684.6	683.0	681.3
117.5°	787.6	785.5	784.2	782.9	781.7	780.5	778.9	776.8	774.8	772.8	770.8
120°	843.2	841.0	840.2	839.4	838.5	837.8	836.2	833.7	831.3	828.8	826.4
122.5°	898.1	896.6	895.5	894.5	893.5	892.5	891.0	888.9	887.0	884.9	883.0
125°	975.7	975.1	974.0	972.9	971.8	970.8	969.1	966.9	964.8	962.6	960.4
127.5°	1052.0	1051.2	1049.9	1048.6	1047.3	1045.9	1044.2	1042.0	1039.9	1037.7	1035.5
130°	1098.0	1097.0	1095.9	1094.8	1093.7	1092.7	1091.0	1088.8	1086.7	1084.5	1082.3
132.5°	1141.9	1140.8	1140.0	1139.1	1138.2	1137.4	1135.9	1133.7	1131.6	1129.4	1127.2
135°	1208.7	1207.9	1206.8	1205.7	1204.6	1203.5	1202.2	1200.6	1199.0	1197.3	1195.7
137.5°	1267.5	1266.2	1265.6	1264.9	1264.4	1263.8	1262.4	1260.4	1258.3	1256.3	1254.2
140°	1305.3	1304.2	1303.3	1302.5	1301.7	1300.9	1299.8	1298.1	1296.5	1294.9	1293.2
142.5°	1341.1	1340.3	1339.5	1338.6	1337.8	1337.0	1335.8	1334.2	1332.5	1330.9	1329.3
145°	1391.2	1390.7	1390.2	1389.6	1389.1	1388.5	1387.3	1385.4	1383.6	1381.6	1379.7
147.5°	1435.9	1435.3	1434.8	1434.3	1433.7	1433.1	1432.2	1431.0	1429.8	1428.6	1427.3
150°	1463.1	1462.6	1462.1	1461.6	1461.0	1460.4	1459.8	1459.0	1458.2	1457.3	1456.5
152.5°	1487.0	1486.0	1485.7	1485.4	1485.1	1484.7	1484.4	1484.0	1483.6	1483.3	1482.9
155°	1520.0	1518.7	1518.4	1518.2	1517.9	1517.6	1517.8	1518.3	1518.8	1519.4	1519.9
157.5°	1548.8	1547.2	1547.5	1547.8	1548.0	1548.3	1548.5	1548.5	1548.6	1548.7	1548.7
160°	1565.5	1563.8	1564.1	1564.3	1564.6	1564.9	1565.1	1565.5	1565.7	1565.9	1566.3
162.5°	1580.3	1578.4	1578.7	1579.0	1579.2	1579.5	1580.0	1580.7	1581.4	1582.1	1582.8
165°	1600.1	1597.9	1598.2	1598.5	1598.7	1599.0	1599.5	1600.4	1601.2	1602.0	1602.8
167.5°	1615.7	1613.6	1613.6	1613.6	1613.6	1613.6	1614.0	1615.2	1616.2	1617.3	1618.4
170°	1624.5	1622.3	1622.3	1622.3	1622.3	1622.3	1622.9	1623.9	1625.0	1626.1	1627.2
172.5°	1630.4	1628.2	1627.9	1627.7	1627.5	1627.3	1627.8	1629.1	1630.4	1631.7	1633.0
175°	1637.6	1635.7	1635.4	1635.2	1634.9	1634.6	1635.2	1636.6	1637.9	1639.2	1640.5
177.5°	1640.4	1638.7	1638.4	1638.2	1638.0	1637.8	1638.2	1639.3	1640.4	1641.4	1642.5
180°	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5



TEST NUMBER: P332174-930

CATALOG NUMBER: S123DIW-S775D1535U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9
2.5°	886.4	888.1	894.0	898.1	902.8	905.6	908.2	910.4	913.1	913.7	923.7
5°	890.4	898.9	913.9	925.0	938.6	953.5	963.8	968.5	980.8	991.1	1011.5
7.5°	889.2	907.4	929.9	953.3	978.4	1001.7	1021.8	1045.7	1062.7	1088.3	1113.4
10°	888.2	912.6	941.6	971.4	1006.5	1038.9	1067.9	1100.3	1127.2	1162.7	1192.9
12.5°	885.2	914.6	954.9	990.3	1032.7	1077.5	1120.5	1162.1	1185.9	1245.0	1272.8
15°	877.6	912.6	963.0	1016.7	1075.1	1128.1	1182.8	1226.3	1296.7	1348.3	1381.2
17.5°	863.1	912.1	971.8	1036.7	1107.7	1177.5	1239.4	1305.5	1380.1	1442.7	1509.3
20°	856.2	910.0	976.6	1048.3	1122.1	1201.1	1271.5	1350.9	1432.4	1493.9	1579.2
22.5°	843.6	904.5	976.2	1056.1	1135.1	1216.8	1299.2	1379.2	1473.4	1558.1	1639.3
25°	822.9	891.2	965.5	1054.7	1147.3	1229.2	1327.9	1434.1	1532.3	1641.1	1722.2
27.5°	801.2	874.2	948.6	1031.5	1131.1	1228.4	1352.4	1472.5	1592.6	1686.5	1746.5
30°	784.5	855.3	932.2	1015.9	1114.4	1230.1	1368.8	1499.8	1616.8	1697.5	1731.2
32.5°	766.4	838.3	906.2	994.0	1099.1	1229.1	1379.1	1515.9	1618.2	1671.9	1665.3
35°	738.0	798.2	864.3	948.8	1072.6	1221.6	1385.0	1517.4	1580.1	1568.6	1481.5
37.5°	697.0	747.6	812.8	905.3	1041.9	1205.7	1373.1	1472.3	1468.3	1374.4	1248.3
40°	671.4	714.5	777.2	874.6	1018.0	1195.6	1354.3	1418.8	1364.2	1233.1	1082.0
42.5°	638.0	677.6	740.4	840.4	991.6	1174.7	1318.4	1337.2	1230.3	1079.5	940.9
45°	586.0	621.0	685.9	789.2	952.3	1129.4	1230.9	1185.3	1041.5	885.7	780.2
47.5°	530.3	566.6	629.1	735.2	895.2	1061.2	1109.5	1012.4	864.7	738.4	641.6
50°	495.1	530.1	591.2	698.3	856.6	1005.2	1025.2	899.8	764.0	653.1	573.6
52.5°	459.6	492.5	552.5	660.1	811.5	940.3	927.9	800.1	675.2	580.7	518.4
55°	406.8	437.9	495.1	595.8	733.7	835.7	790.9	668.9	565.6	492.1	444.7
57.5°	359.5	389.4	438.7	529.7	649.5	719.7	662.6	559.7	477.6	421.1	385.8
60°	327.3	353.8	400.8	485.3	589.5	642.8	586.4	495.5	426.4	381.2	349.6
62.5°	297.0	320.0	363.5	440.3	530.7	575.5	518.5	441.6	382.7	342.6	315.8
65°	250.9	271.9	310.3	370.1	444.3	474.2	425.1	362.8	317.2	287.2	269.3
67.5°	209.0	226.7	259.9	307.0	361.6	383.4	346.0	297.7	263.3	239.4	225.1
70°	181.0	196.3	222.4	262.9	312.4	329.1	294.1	254.4	229.2	210.0	196.7
72.5°	157.4	168.7	192.3	223.6	265.0	278.2	253.8	218.9	195.4	181.0	170.5
75°	119.9	129.3	144.7	169.9	198.4	206.2	187.8	166.0	150.3	140.0	131.9
77.5°	86.5	93.4	104.5	120.0	139.8	146.8	135.1	120.6	109.1	102.2	97.7
80°	65.3	70.8	80.2	93.0	105.0	108.8	102.0	90.9	82.8	79.0	75.1
82.5°	48.3	51.4	57.0	65.7	73.9	78.4	72.6	66.0	61.6	58.1	56.7
85°	24.3	26.0	28.6	32.0	37.1	38.8	36.7	35.0	32.4	30.3	30.3
87.5°	9.7	10.2	11.7	13.0	15.0	16.7	17.0	17.1	17.4	17.4	17.2
90°	3.9	6.6	9.4	12.1	15.2	18.7	22.2	25.8	29.3	30.3	31.4
92.5°	21.9	21.1	20.4	19.6	20.5	23.2	25.9	28.5	31.2	32.9	34.7
95°	63.3	52.2	41.0	29.9	25.8	28.9	31.8	34.8	37.7	39.7	41.6
97.5°	144.5	139.5	134.4	129.5	117.2	97.8	78.3	58.8	39.2	41.4	43.6
100°	211.4	216.8	222.3	227.6	209.2	167.0	124.7	82.5	40.2	42.4	44.5
102.5°	274.3	278.2	282.0	285.9	264.8	218.7	172.5	126.4	80.2	73.5	66.8
105°	366.2	369.2	372.2	375.1	364.4	340.1	315.7	291.3	266.9	219.0	171.0
107.5°	463.6	465.9	468.4	470.8	473.9	477.7	481.6	485.4	489.3	454.1	418.9
110°	528.7	530.8	533.0	535.2	537.8	540.8	543.7	546.7	549.7	540.8	531.8





TEST NUMBER: P332174-930

CATALOG NUMBER: S123DIW-S775D1535U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	590.9	592.9	594.8	596.7	599.2	602.2	605.2	608.1	611.1	611.3	611.5
115°	683.0	684.6	686.2	687.9	689.9	692.4	694.7	697.2	699.6	702.3	705.1
117.5°	772.8	774.8	776.8	778.9	780.5	781.7	782.9	784.2	785.5	787.6	789.8
120°	828.8	831.3	833.7	836.2	837.8	838.5	839.4	840.2	841.0	843.2	845.4
122.5°	884.9	887.0	888.9	891.0	892.5	893.5	894.5	895.5	896.6	898.1	899.6
125°	962.6	964.8	966.9	969.1	970.8	971.8	972.9	974.0	975.1	975.7	976.2
127.5°	1037.7	1039.9	1042.0	1044.2	1045.9	1047.3	1048.6	1049.9	1051.2	1052.0	1052.9
130°	1084.5	1086.7	1088.8	1091.0	1092.7	1093.7	1094.8	1095.9	1097.0	1098.0	1099.1
132.5°	1129.4	1131.6	1133.7	1135.9	1137.4	1138.2	1139.1	1140.0	1140.8	1141.9	1143.0
135°	1197.3	1199.0	1200.6	1202.2	1203.5	1204.6	1205.7	1206.8	1207.9	1208.7	1209.5
137.5°	1256.3	1258.3	1260.4	1262.4	1263.8	1264.4	1264.9	1265.6	1266.2	1267.5	1268.8
140°	1294.9	1296.5	1298.1	1299.8	1300.9	1301.7	1302.5	1303.3	1304.2	1305.3	1306.4
142.5°	1330.9	1332.5	1334.2	1335.8	1337.0	1337.8	1338.6	1339.5	1340.3	1341.1	1342.0
145°	1381.6	1383.6	1385.4	1387.3	1388.5	1389.1	1389.6	1390.2	1390.7	1391.2	1391.8
147.5°	1428.6	1429.8	1431.0	1432.2	1433.1	1433.7	1434.3	1434.8	1435.3	1435.9	1436.4
150°	1457.3	1458.2	1459.0	1459.8	1460.4	1461.0	1461.6	1462.1	1462.6	1463.1	1463.7
152.5°	1483.3	1483.6	1484.0	1484.4	1484.7	1485.1	1485.4	1485.7	1486.0	1487.0	1488.0
155°	1519.4	1518.8	1518.3	1517.8	1517.6	1517.9	1518.2	1518.4	1518.7	1520.0	1521.4
157.5°	1548.7	1548.6	1548.5	1548.5	1548.3	1548.0	1547.8	1547.5	1547.2	1548.8	1550.5
160°	1565.9	1565.7	1565.5	1565.1	1564.9	1564.6	1564.3	1564.1	1563.8	1565.5	1567.1
162.5°	1582.1	1581.4	1580.7	1580.0	1579.5	1579.2	1579.0	1578.7	1578.4	1580.3	1582.1
165°	1602.0	1601.2	1600.4	1599.5	1599.0	1598.7	1598.5	1598.2	1597.9	1600.1	1602.2
167.5°	1617.3	1616.2	1615.2	1614.0	1613.6	1613.6	1613.6	1613.6	1613.6	1615.7	1617.9
170°	1626.1	1625.0	1623.9	1622.9	1622.3	1622.3	1622.3	1622.3	1622.3	1624.5	1626.6
172.5°	1631.7	1630.4	1629.1	1627.8	1627.3	1627.5	1627.7	1627.9	1628.2	1630.4	1632.5
175°	1639.2	1637.9	1636.6	1635.2	1634.6	1634.9	1635.2	1635.4	1635.7	1637.6	1639.5
177.5°	1641.4	1640.4	1639.3	1638.2	1637.8	1638.0	1638.2	1638.4	1638.7	1640.4	1642.1
180°	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5



TEST NUMBER: P332174-930

CATALOG NUMBER: S123DIW-S775D1535U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	880.9	880.9	880.9	880.9	880.9	880.9	880.9
2.5°	927.1	927.4	931.2	933.9	932.5	934.3	934.9
5°	1012.8	1028.3	1036.3	1042.3	1042.8	1043.2	1046.6
7.5°	1134.5	1151.0	1163.0	1181.3	1186.7	1192.9	1191.2
10°	1223.3	1247.6	1268.5	1279.6	1291.6	1309.0	1295.0
12.5°	1306.3	1349.4	1381.2	1398.5	1409.7	1413.2	1406.3
15°	1443.1	1499.4	1529.7	1528.8	1567.3	1584.0	1557.9
17.5°	1568.6	1620.6	1662.2	1683.6	1715.6	1722.6	1719.4
20°	1645.4	1702.2	1734.6	1771.3	1788.0	1802.9	1805.5
22.5°	1711.6	1762.6	1797.4	1828.0	1841.9	1849.0	1853.3
25°	1779.9	1820.0	1840.9	1851.5	1855.4	1854.6	1849.0
27.5°	1775.2	1778.2	1755.2	1732.6	1712.4	1689.5	1681.7
30°	1729.1	1693.2	1629.2	1592.9	1539.5	1497.3	1514.3
32.5°	1607.9	1536.5	1464.6	1385.3	1319.6	1301.0	1282.1
35°	1372.2	1246.8	1173.4	1087.9	1053.9	1019.7	996.2
37.5°	1110.2	1013.1	926.0	870.2	836.0	814.4	802.7
40°	959.9	872.5	800.7	755.5	729.4	705.2	701.7
42.5°	840.1	758.7	704.7	668.7	643.8	633.4	625.9
45°	688.0	631.3	595.0	569.4	552.8	546.3	537.8
47.5°	582.4	542.3	515.0	497.6	485.0	480.3	479.6
50°	523.3	490.0	469.9	456.2	446.5	444.7	437.9
52.5°	478.9	450.0	434.4	422.5	415.4	410.6	408.5
55°	415.7	396.5	382.5	375.6	370.1	365.3	365.3
57.5°	363.7	347.7	338.3	332.6	330.8	327.5	325.4
60°	331.7	318.0	310.7	305.6	302.2	302.6	298.8
62.5°	300.2	291.4	284.5	279.3	275.2	275.3	275.6
65°	255.7	248.8	243.7	242.0	239.5	236.4	237.3
67.5°	216.6	210.3	206.3	203.3	202.5	200.9	203.3
70°	188.7	183.9	181.0	178.4	177.6	178.0	180.1
72.5°	163.1	159.7	157.8	156.5	154.7	154.7	156.2
75°	128.1	125.5	123.8	122.5	122.1	122.1	122.1
77.5°	94.1	93.5	92.7	90.8	90.9	91.4	91.5
80°	74.3	73.0	72.6	71.7	70.4	69.5	71.7
82.5°	55.5	54.2	53.8	53.6	51.6	51.4	53.2
85°	29.8	28.6	29.0	28.6	28.6	28.2	28.2
87.5°	17.1	17.0	16.8	17.2	17.0	16.8	17.5
90°	32.5	33.6	34.4	35.0	35.5	36.0	36.5
92.5°	36.4	38.2	39.1	39.5	39.8	40.1	40.4
95°	43.5	45.3	46.3	46.3	46.3	46.3	46.3
97.5°	45.7	47.9	49.2	49.4	49.7	50.0	50.2
100°	46.7	48.9	50.1	50.4	50.6	51.0	51.2
102.5°	60.1	53.3	50.2	50.7	51.2	51.7	52.2
105°	123.1	75.2	51.4	52.0	52.6	53.1	53.6
107.5°	383.8	348.6	313.0	276.9	240.7	204.6	168.4
110°	522.9	514.0	490.1	451.3	412.6	373.9	335.2



TEST NUMBER: P332174-930

CATALOG NUMBER: S123DIW-S775D1535U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	611.6	611.8	607.8	599.6	591.4	583.3	575.0
115°	707.8	710.5	712.3	713.5	714.5	715.6	716.7
117.5°	791.9	794.1	795.3	795.5	795.7	796.0	796.1
120°	847.5	849.7	850.8	850.8	850.8	850.8	850.8
122.5°	901.2	902.7	903.5	903.8	903.9	904.2	904.4
125°	976.7	977.2	977.8	978.4	978.8	979.4	980.0
127.5°	1053.8	1054.6	1054.8	1054.3	1053.7	1053.1	1052.6
130°	1100.2	1101.3	1101.6	1101.1	1100.5	1099.9	1099.4
132.5°	1144.1	1145.2	1145.3	1144.6	1143.9	1143.0	1142.3
135°	1210.3	1211.1	1211.1	1210.3	1209.5	1208.7	1207.9
137.5°	1270.1	1271.4	1271.7	1271.2	1270.6	1270.1	1269.6
140°	1307.4	1308.5	1308.8	1308.2	1307.7	1307.2	1306.6
142.5°	1342.9	1343.7	1343.8	1343.0	1342.2	1341.5	1340.8
145°	1392.4	1392.9	1393.2	1393.2	1393.2	1393.2	1393.2
147.5°	1437.0	1437.5	1437.1	1435.9	1434.7	1433.4	1432.2
150°	1464.3	1464.8	1464.7	1463.9	1463.1	1462.2	1461.4
152.5°	1489.0	1490.0	1489.8	1488.6	1487.3	1486.0	1484.8
155°	1522.7	1524.1	1524.0	1522.3	1520.7	1519.1	1517.5
157.5°	1552.1	1553.7	1553.5	1551.4	1549.2	1547.1	1545.0
160°	1568.6	1570.3	1570.2	1568.2	1566.4	1564.5	1562.6
162.5°	1584.0	1585.8	1585.8	1584.2	1582.5	1580.9	1579.2
165°	1604.4	1606.6	1606.7	1604.8	1603.0	1601.0	1599.1
167.5°	1620.0	1622.2	1622.2	1620.0	1617.9	1615.7	1613.6
170°	1628.8	1631.0	1631.0	1628.8	1626.6	1624.5	1622.3
172.5°	1634.7	1636.8	1636.7	1634.3	1632.0	1629.5	1627.2
175°	1641.4	1643.3	1643.2	1641.0	1638.8	1636.6	1634.5
177.5°	1643.8	1645.6	1645.4	1643.2	1641.0	1638.8	1636.7
180°	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5	1640.5

(END OF REPORT)