

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332175-930

Luminaire Tested: **S123DIW-S775D1535U930-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332175-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIW-S775D1535U930-4F0-1E-UDD-A1  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1535 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6999.8 lumens  
Efficiency: N/A  
Efficacy: 102.8 lumens/watt  
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 68.1  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332175-930

CATALOG NUMBER: S123DIW-S775D1535U930-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P332175-930

CATALOG NUMBER: S123DIW-S775D1535U930-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45	38
1	95	91	87	84	86	83	80	77	67	65	63	53	52	50	40	39	38	32
2	87	80	74	69	79	73	68	63	59	56	53	47	45	42	36	34	33	27
3	79	70	63	58	72	64	58	53	52	48	44	42	39	36	32	30	28	23
4	73	62	55	49	66	57	50	45	47	42	38	37	34	31	28	26	24	20
5	67	55	48	42	60	51	44	39	42	37	33	33	30	27	26	23	21	18
6	61	50	42	36	56	45	39	34	38	32	29	30	26	24	23	21	19	16
7	57	45	37	32	51	41	34	29	34	29	25	27	24	21	21	19	17	14
8	53	41	33	28	48	37	31	26	31	26	22	25	21	19	19	17	15	12
9	49	37	30	25	44	34	28	23	28	23	20	23	19	17	18	15	13	11
10	46	34	27	22	41	31	25	21	26	21	18	21	18	15	17	14	12	10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	9482	9482	9482	9482
5°	11309	9524	8440	9524
10°	14154	9475	7623	9475
15°	17361	9399	7096	9399
20°	20681	9279	6757	9279
25°	21960	9136	6682	9136
30°	18821	9028	6717	9028
35°	13090	8878	6787	8878
40°	9860	8702	6764	8702
45°	8187	8441	6680	8441
50°	7333	7906	6620	7906
55°	6855	7328	6536	7328
60°	6433	6725	6469	6725
65°	6044	6133	6260	6133
70°	5668	5454	5964	5454
75°	5078	4774	5465	4774
80°	4444	3918	4711	3918
85°	3483	2853	3162	2853



TEST NUMBER: P332175-930

CATALOG NUMBER: S123DIW-S775D1535U930-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	86.8	1.2
10°-20°	278.3	4.0
20°-30°	467.0	6.7
30°-40°	528.8	7.6
40°-50°	474.2	6.8
50°-60°	382.7	5.5
60°-70°	266.7	3.8
70°-80°	140.2	2.0
80°-90°	38.9	0.6
90°-100°	102.0	1.5
100°-110°	305.2	4.4
110°-120°	519.0	7.4
120°-130°	682.7	9.8
130°-140°	767.4	11.0
140°-150°	754.3	10.8
150°-160°	635.0	9.1
160°-170°	422.7	6.0
170°-180°	148.0	2.1
0°-30°	832.1	11.9
0°-40°	1360.9	19.4
0°-60°	2217.8	31.7
0°-90°	2663.6	38.1
90°-120°	926.2	13.2
90°-150°	3130.5	44.7
90°-180°	4336.0	61.9
0°-180°	6999.8	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	881	881	881	881	881	
5°	1047	881	781	881	1047	108
15°	1558	843	637	843	1558	450
25°	1849	769	563	769	1849	811
35°	996	676	516	676	996	647
45°	538	554	439	554	538	426
55°	365	390	348	390	365	328
65°	237	241	246	241	237	236
75°	122	115	131	115	122	131
85°	28	23	26	23	28	34
90°	37	1	37	1	37	19
95°	96	73	96	73	96	98
105°	293	277	293	277	293	310
115°	524	522	524	522	524	519
125°	756	765	756	765	756	676
135°	991	992	991	992	991	762
145°	1204	1204	1204	1204	1204	751
155°	1376	1378	1376	1378	1376	633
165°	1496	1501	1496	1501	1496	422
175°	1555	1561	1555	1561	1555	148
180°	1565	1565	1565	1565	1565	



TEST NUMBER: P332175-930

CATALOG NUMBER: S123DIW-S775D1535U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9
2.5°	934.9	934.3	932.5	933.9	931.2	927.4	927.1	923.7	913.7	913.1	910.4
5°	1046.6	1043.2	1042.8	1042.3	1036.3	1028.3	1012.8	1011.5	991.1	980.8	968.5
7.5°	1191.2	1192.9	1186.7	1181.3	1163.0	1151.0	1134.5	1113.4	1088.3	1062.7	1045.7
10°	1295.0	1309.0	1291.6	1279.6	1268.5	1247.6	1223.3	1192.9	1162.7	1127.2	1100.3
12.5°	1406.3	1413.2	1409.7	1398.5	1381.2	1349.4	1306.3	1272.8	1245.0	1185.9	1162.1
15°	1557.9	1584.0	1567.3	1528.8	1529.7	1499.4	1443.1	1381.2	1348.3	1296.7	1226.3
17.5°	1719.4	1722.6	1715.6	1683.6	1662.2	1620.6	1568.6	1509.3	1442.7	1380.1	1305.5
20°	1805.5	1802.9	1788.0	1771.3	1734.6	1702.2	1645.4	1579.2	1493.9	1432.4	1350.9
22.5°	1853.3	1849.0	1841.9	1828.0	1797.4	1762.6	1711.6	1639.3	1558.1	1473.4	1379.2
25°	1849.0	1854.6	1855.4	1851.5	1840.9	1820.0	1779.9	1722.2	1641.1	1532.3	1434.1
27.5°	1681.7	1689.5	1712.4	1732.6	1755.2	1778.2	1775.2	1746.5	1686.5	1592.6	1472.5
30°	1514.3	1497.3	1539.5	1592.9	1629.2	1693.2	1729.1	1731.2	1697.5	1616.8	1499.8
32.5°	1282.1	1301.0	1319.6	1385.3	1464.6	1536.5	1607.9	1665.3	1671.9	1618.2	1515.9
35°	996.2	1019.7	1053.9	1087.9	1173.4	1246.8	1372.2	1481.5	1568.6	1580.1	1517.4
37.5°	802.7	814.4	836.0	870.2	926.0	1013.1	1110.2	1248.3	1374.4	1468.3	1472.3
40°	701.7	705.2	729.4	755.5	800.7	872.5	959.9	1082.0	1233.1	1364.2	1418.8
42.5°	625.9	633.4	643.8	668.7	704.7	758.7	840.1	940.9	1079.5	1230.3	1337.2
45°	537.8	546.3	552.8	569.4	595.0	631.3	688.0	780.2	885.7	1041.5	1185.3
47.5°	479.6	480.3	485.0	497.6	515.0	542.3	582.4	641.6	738.4	864.7	1012.4
50°	437.9	444.7	446.5	456.2	469.9	490.0	523.3	573.6	653.1	764.0	899.8
52.5°	408.5	410.6	415.4	422.5	434.4	450.0	478.9	518.4	580.7	675.2	800.1
55°	365.3	365.3	370.1	375.6	382.5	396.5	415.7	444.7	492.1	565.6	668.9
57.5°	325.4	327.5	330.8	332.6	338.3	347.7	363.7	385.8	421.1	477.6	559.7
60°	298.8	302.6	302.2	305.6	310.7	318.0	331.7	349.6	381.2	426.4	495.5
62.5°	275.6	275.3	275.2	279.3	284.5	291.4	300.2	315.8	342.6	382.7	441.6
65°	237.3	236.4	239.5	242.0	243.7	248.8	255.7	269.3	287.2	317.2	362.8
67.5°	203.3	200.9	202.5	203.3	206.3	210.3	216.6	225.1	239.4	263.3	297.7
70°	180.1	178.0	177.6	178.4	181.0	183.9	188.7	196.7	210.0	229.2	254.4
72.5°	156.2	154.7	154.7	156.5	157.8	159.7	163.1	170.5	181.0	195.4	218.9
75°	122.1	122.1	122.1	122.5	123.8	125.5	128.1	131.9	140.0	150.3	166.0
77.5°	91.5	91.4	90.9	90.8	92.7	93.5	94.1	97.7	102.2	109.1	120.6
80°	71.7	69.5	70.4	71.7	72.6	73.0	74.3	75.1	79.0	82.8	90.9
82.5°	53.2	51.4	51.6	53.6	53.8	54.2	55.5	56.7	58.1	61.6	66.0
85°	28.2	28.2	28.6	28.6	29.0	28.6	29.8	30.3	30.3	32.4	35.0
87.5°	17.6	16.8	17.0	17.3	16.9	17.0	17.1	17.3	17.4	17.5	17.1
90°	36.9	36.4	35.8	35.2	34.7	33.9	32.8	31.7	30.6	29.5	25.9
92.5°	49.7	50.0	50.3	50.6	51.0	50.7	49.8	48.9	48.1	47.2	45.2
95°	95.9	95.9	95.9	95.9	95.9	95.3	94.2	93.2	92.0	91.0	88.8
97.5°	147.6	147.7	147.7	147.9	148.0	147.4	146.1	144.9	143.7	142.4	140.8
100°	186.9	186.3	185.8	185.2	184.7	184.0	183.2	182.4	181.6	180.8	179.4
102.5°	227.2	227.3	227.4	227.6	227.6	227.3	226.5	225.7	224.9	224.0	222.2
105°	292.6	292.0	291.6	291.0	290.4	290.2	290.2	290.2	290.2	290.2	287.7
107.5°	360.7	361.0	361.3	361.7	362.0	361.7	360.9	360.0	359.1	358.2	357.3
110°	406.9	407.5	408.1	408.5	409.1	408.9	407.7	406.7	405.6	404.5	403.9



TEST NUMBER: P332175-930

CATALOG NUMBER: S123DIW-S775D1535U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	456.1	456.2	456.3	456.5	456.6	455.9	454.6	453.3	452.0	450.7	450.6
115°	523.7	524.0	524.3	524.6	524.8	524.8	524.6	524.3	524.0	523.7	524.3
117.5°	592.3	593.1	593.9	594.6	595.4	595.8	595.9	595.9	596.0	596.1	596.7
120°	640.5	641.1	641.6	642.2	642.7	643.1	643.4	643.7	643.9	644.2	645.6
122.5°	686.7	687.5	688.3	689.1	689.8	690.6	691.3	691.9	692.7	693.4	694.1
125°	756.1	757.2	758.3	759.4	760.4	761.6	762.6	763.8	764.8	766.0	766.5
127.5°	825.2	826.5	827.7	829.0	830.2	831.6	833.2	834.7	836.2	837.7	838.4
130°	870.4	872.4	874.2	876.2	878.1	879.6	880.7	881.7	882.9	883.9	884.8
132.5°	917.6	919.1	920.6	922.1	923.6	925.0	926.3	927.6	928.9	930.2	930.7
135°	990.9	991.5	992.0	992.5	993.1	993.9	995.0	996.1	997.2	998.3	998.6
137.5°	1055.6	1056.6	1057.7	1058.7	1059.7	1060.9	1062.0	1063.2	1064.3	1065.4	1064.7
140°	1097.9	1099.8	1101.7	1103.6	1105.5	1106.6	1106.9	1107.2	1107.4	1107.7	1107.4
142.5°	1141.2	1142.6	1144.1	1145.6	1147.0	1147.9	1148.2	1148.5	1148.8	1149.0	1148.5
145°	1203.6	1204.7	1205.8	1206.9	1207.9	1208.7	1208.9	1209.2	1209.5	1209.7	1208.9
147.5°	1259.1	1260.8	1262.5	1264.1	1265.8	1266.6	1266.6	1266.6	1266.6	1266.6	1265.8
150°	1294.6	1296.2	1297.9	1299.5	1301.1	1302.0	1302.0	1302.0	1302.0	1302.0	1301.4
152.5°	1329.0	1330.4	1331.9	1333.3	1334.7	1335.2	1334.7	1334.3	1333.9	1333.4	1333.1
155°	1375.7	1377.6	1379.6	1381.4	1383.4	1383.8	1382.7	1381.6	1380.5	1379.4	1379.2
157.5°	1418.3	1419.8	1421.3	1422.9	1424.4	1424.6	1423.4	1422.3	1421.1	1420.0	1419.8
160°	1445.8	1446.9	1448.0	1449.1	1450.2	1450.0	1448.7	1447.3	1445.9	1444.5	1444.5
162.5°	1466.5	1468.2	1470.0	1471.7	1473.5	1473.7	1472.3	1470.9	1469.6	1468.2	1467.9
165°	1496.2	1498.1	1500.1	1501.9	1503.9	1504.0	1502.4	1500.7	1499.1	1497.5	1497.5
167.5°	1521.5	1523.2	1524.9	1526.6	1528.3	1528.3	1526.6	1524.9	1523.2	1521.5	1521.3
170°	1534.3	1536.3	1538.1	1540.1	1542.0	1542.0	1540.1	1538.1	1536.3	1534.3	1534.3
172.5°	1544.2	1546.1	1548.0	1549.9	1551.8	1551.9	1550.2	1548.5	1546.9	1545.2	1545.2
175°	1555.3	1557.1	1559.0	1561.0	1562.8	1563.0	1561.4	1559.7	1558.1	1556.5	1556.5
177.5°	1561.1	1562.7	1564.2	1565.7	1567.2	1567.3	1566.0	1564.7	1563.4	1562.1	1562.1
180°	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0



TEST NUMBER: P332175-930

CATALOG NUMBER: S123DIW-S775D1535U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9
2.5°	908.2	905.6	902.8	898.1	894.0	888.1	886.4	884.4	878.2	872.8	868.7
5°	963.8	953.5	938.6	925.0	913.9	898.9	890.4	881.4	868.6	857.0	847.7
7.5°	1021.8	1001.7	978.4	953.3	929.9	907.4	889.2	873.0	855.1	838.1	824.9
10°	1067.9	1038.9	1006.5	971.4	941.6	912.6	888.2	866.9	843.8	823.8	807.1
12.5°	1120.5	1077.5	1032.7	990.3	954.9	914.6	885.2	858.0	831.8	807.7	789.0
15°	1182.8	1128.1	1075.1	1016.7	963.0	912.6	877.6	843.4	813.1	788.3	764.4
17.5°	1239.4	1177.5	1107.7	1036.7	971.8	912.1	863.1	824.4	786.5	756.3	732.5
20°	1271.5	1201.1	1122.1	1048.3	976.6	910.0	856.2	810.1	769.2	737.1	710.2
22.5°	1299.2	1216.8	1135.1	1056.1	976.2	904.5	843.6	796.1	751.7	720.4	691.8
25°	1327.9	1229.2	1147.3	1054.7	965.5	891.2	822.9	769.2	724.7	688.0	658.6
27.5°	1352.4	1228.4	1131.1	1031.5	948.6	874.2	801.2	743.6	696.4	656.6	626.6
30°	1368.8	1230.1	1114.4	1015.9	932.2	855.3	784.5	726.4	676.9	636.4	608.2
32.5°	1379.1	1229.1	1099.1	994.0	906.2	838.3	766.4	706.3	655.4	615.6	588.4
35°	1385.0	1221.6	1072.6	948.8	864.3	798.2	738.0	675.6	622.3	585.1	554.5
37.5°	1373.1	1205.7	1041.9	905.3	812.8	747.6	697.0	643.9	592.9	552.0	525.5
40°	1354.3	1195.6	1018.0	874.6	777.2	714.5	671.4	619.3	568.9	530.1	505.3
42.5°	1318.4	1174.7	991.6	840.4	740.4	677.6	638.0	594.4	546.7	510.3	485.6
45°	1230.9	1129.4	952.3	789.2	685.9	621.0	586.0	554.5	511.4	475.9	454.5
47.5°	1109.5	1061.2	895.2	735.2	629.1	566.6	530.3	504.8	473.4	444.7	424.3
50°	1025.2	1005.2	856.6	698.3	591.2	530.1	495.1	472.1	449.5	420.9	402.1
52.5°	927.9	940.3	811.5	660.1	552.5	492.5	459.6	441.3	420.8	397.3	380.9
55°	790.9	835.7	733.7	595.8	495.1	437.9	406.8	390.5	378.6	361.1	347.0
57.5°	662.6	719.7	649.5	529.7	438.7	389.4	359.5	341.8	334.1	325.0	313.9
60°	586.4	642.8	589.5	485.3	400.8	353.8	327.3	312.4	304.8	298.3	288.9
62.5°	518.5	575.5	530.7	440.3	363.5	320.0	297.0	282.4	276.4	273.0	265.1
65°	425.1	474.2	444.3	370.1	310.3	271.9	250.9	240.8	235.2	233.9	228.8
67.5°	346.0	383.4	361.6	307.0	259.9	226.7	209.0	200.2	196.0	195.6	191.8
70°	294.1	329.1	312.4	262.9	222.4	196.3	181.0	173.3	170.7	170.3	168.2
72.5°	253.8	278.2	265.0	223.6	192.3	168.7	157.4	149.4	146.5	147.1	145.6
75°	187.8	206.2	198.4	169.9	144.7	129.3	119.9	114.8	112.3	113.6	111.9
77.5°	135.1	146.8	139.8	120.0	104.5	93.4	86.5	83.3	81.0	81.0	80.1
80°	102.0	108.8	105.0	93.0	80.2	70.8	65.3	63.2	61.9	61.5	61.1
82.5°	72.6	78.4	73.9	65.7	57.0	51.4	48.3	45.4	44.5	44.8	44.3
85°	36.7	38.8	37.1	32.0	28.6	26.0	24.3	23.1	22.2	22.6	21.8
87.5°	17.1	16.7	15.0	13.0	11.8	10.2	9.7	8.5	8.3	8.9	9.0
90°	22.4	18.8	15.3	12.1	9.5	6.7	4.0	1.2	4.0	6.7	9.5
92.5°	43.1	41.2	39.1	37.2	35.3	33.4	31.6	29.8	31.6	33.4	35.3
95°	86.6	84.4	82.3	80.2	78.3	76.4	74.4	72.6	74.4	76.4	78.3
97.5°	139.2	137.6	136.0	134.5	133.1	131.7	130.3	128.8	130.3	131.7	133.1
100°	178.0	176.6	175.3	173.7	172.1	170.5	168.8	167.2	168.8	170.5	172.1
102.5°	220.4	218.6	216.8	215.4	214.4	213.4	212.5	211.5	212.5	213.4	214.4
105°	285.2	282.7	280.3	278.8	278.3	277.7	277.2	276.6	277.2	277.7	278.3
107.5°	356.3	355.3	354.3	353.7	353.4	353.0	352.7	352.4	352.7	353.0	353.4
110°	403.4	402.8	402.3	401.8	401.2	400.6	400.1	399.6	400.1	400.6	401.2





TEST NUMBER: P332175-930

CATALOG NUMBER: S123DIW-S775D1535U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	450.5	450.4	450.3	450.0	449.7	449.4	449.1	448.7	449.1	449.4	449.7
115°	524.8	525.4	525.9	525.8	525.0	524.2	523.3	522.5	523.3	524.2	525.0
117.5°	597.5	598.2	598.8	598.9	598.4	597.9	597.3	596.8	597.3	597.9	598.4
120°	646.9	648.3	649.7	649.5	647.9	646.3	644.7	643.0	644.7	646.3	647.9
122.5°	694.8	695.5	696.3	696.0	694.8	693.6	692.4	691.2	692.4	693.6	694.8
125°	767.0	767.6	768.1	768.0	767.2	766.4	765.5	764.7	765.5	766.4	767.2
127.5°	838.9	839.5	840.2	839.6	837.8	836.1	834.3	832.6	834.3	836.1	837.8
130°	885.6	886.4	887.2	886.6	884.4	882.2	880.0	877.8	880.0	882.2	884.4
132.5°	931.4	932.0	932.6	931.8	929.6	927.4	925.2	923.1	925.2	927.4	929.6
135°	998.8	999.1	999.4	998.7	997.0	995.4	993.8	992.1	993.8	995.4	997.0
137.5°	1064.0	1063.3	1062.6	1061.5	1060.2	1058.8	1057.4	1056.1	1057.4	1058.8	1060.2
140°	1107.2	1106.9	1106.6	1105.8	1104.4	1103.1	1101.7	1100.3	1101.7	1103.1	1104.4
142.5°	1148.0	1147.5	1147.0	1146.1	1144.8	1143.4	1142.0	1140.7	1142.0	1143.4	1144.8
145°	1208.1	1207.3	1206.5	1205.8	1205.3	1204.7	1204.2	1203.6	1204.2	1204.7	1205.3
147.5°	1265.0	1264.3	1263.5	1262.7	1261.7	1260.6	1259.6	1258.7	1259.6	1260.6	1261.7
150°	1300.9	1300.3	1299.8	1299.3	1298.7	1298.1	1297.6	1297.1	1297.6	1298.1	1298.7
152.5°	1332.8	1332.4	1332.1	1331.5	1330.8	1330.1	1329.3	1328.5	1329.3	1330.1	1330.8
155°	1378.8	1378.6	1378.3	1378.2	1378.2	1378.2	1378.2	1378.2	1378.2	1378.2	1378.2
157.5°	1419.5	1419.4	1419.1	1419.2	1419.5	1419.8	1420.2	1420.5	1420.2	1419.8	1419.5
160°	1444.5	1444.5	1444.5	1444.9	1445.4	1445.9	1446.5	1447.1	1446.5	1445.9	1445.4
162.5°	1467.8	1467.5	1467.3	1467.6	1468.4	1469.1	1469.9	1470.6	1469.9	1469.1	1468.4
165°	1497.5	1497.5	1497.5	1497.9	1498.7	1499.5	1500.3	1501.1	1500.3	1499.5	1498.7
167.5°	1521.1	1520.9	1520.7	1521.1	1522.2	1523.3	1524.4	1525.5	1524.4	1523.3	1522.2
170°	1534.3	1534.3	1534.3	1534.9	1535.9	1537.1	1538.1	1539.2	1538.1	1537.1	1535.9
172.5°	1545.2	1545.2	1545.2	1545.7	1546.8	1547.8	1549.0	1550.0	1549.0	1547.8	1546.8
175°	1556.5	1556.5	1556.5	1557.0	1558.1	1559.2	1560.3	1561.4	1560.3	1559.2	1558.1
177.5°	1562.1	1562.1	1562.1	1562.5	1563.4	1564.3	1565.2	1566.0	1565.2	1564.3	1563.4
180°	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0



TEST NUMBER: P332175-930

CATALOG NUMBER: S123DIW-S775D1535U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9
2.5°	866.3	863.9	860.5	855.3	851.3	844.7	844.7	845.8	845.8	845.5	844.7
5°	840.0	833.6	825.9	816.9	807.6	798.2	796.5	793.0	790.5	788.8	786.6
7.5°	812.3	800.9	789.7	777.1	765.7	756.3	749.7	744.2	740.7	736.9	734.3
10°	793.4	779.3	766.1	752.9	738.4	726.9	719.7	714.5	710.7	707.3	705.6
12.5°	771.3	755.1	740.5	728.0	712.1	700.3	693.3	691.0	686.4	679.2	675.5
15°	738.8	723.9	706.4	687.2	679.5	665.0	656.9	653.1	650.4	644.9	643.2
17.5°	711.1	691.5	671.9	657.5	643.3	631.5	627.0	622.2	618.8	614.2	612.9
20°	688.9	671.4	653.5	638.1	623.1	610.3	606.5	603.1	599.7	597.5	595.8
22.5°	666.3	648.9	634.0	619.6	603.7	595.3	591.2	587.4	585.0	583.6	581.9
25°	634.7	619.3	602.7	589.9	577.1	571.5	568.9	566.8	565.1	563.0	562.6
27.5°	606.3	589.6	576.1	564.2	555.0	550.3	547.9	546.8	547.2	548.0	548.5
30°	585.1	569.8	558.7	548.5	540.0	535.7	535.2	535.2	537.0	537.4	538.3
32.5°	565.7	553.1	542.0	532.1	525.6	522.7	524.3	524.3	525.7	526.8	528.3
35°	537.4	526.3	517.7	509.2	503.7	504.9	505.8	506.6	508.7	511.4	513.1
37.5°	510.3	500.7	491.8	485.1	482.6	484.9	486.9	488.7	491.2	493.2	494.9
40°	490.8	483.6	475.1	469.0	469.9	471.2	473.0	475.1	477.2	478.5	480.2
42.5°	472.7	465.1	458.7	453.7	454.9	456.6	457.5	458.7	461.1	463.4	464.5
45°	445.2	439.2	433.3	430.2	431.1	431.9	432.8	434.1	436.2	437.9	438.4
47.5°	414.2	410.0	406.0	403.1	404.5	404.1	405.2	408.0	408.6	409.7	412.1
50°	394.4	390.5	385.9	385.0	385.0	385.0	385.4	388.8	388.8	390.5	392.2
52.5°	372.5	370.1	367.0	365.5	364.8	364.8	366.6	368.4	369.0	371.5	373.2
55°	340.1	337.6	335.1	333.8	332.9	333.8	337.2	338.0	340.1	341.4	342.8
57.5°	306.5	304.5	302.5	301.7	301.6	302.7	304.6	307.1	307.7	311.6	313.6
60°	284.3	281.3	279.6	279.6	278.8	282.6	281.7	286.0	286.8	289.3	292.4
62.5°	261.4	257.4	256.7	256.7	257.9	259.0	260.2	262.0	264.3	267.5	269.9
65°	224.5	222.4	225.3	224.9	224.0	226.7	226.7	228.8	231.3	234.3	239.0
67.5°	189.6	188.5	188.7	188.7	190.0	191.5	192.7	194.5	197.6	200.8	203.8
70°	166.0	167.3	165.2	166.9	168.2	168.6	169.4	172.0	175.5	177.6	181.0
72.5°	143.2	143.1	143.3	144.0	145.3	146.0	146.9	149.9	153.6	155.4	158.1
75°	110.1	109.7	111.0	111.0	113.1	114.0	114.8	116.1	119.5	122.1	124.2
77.5°	80.4	81.0	80.6	82.1	81.5	81.7	84.3	85.6	85.9	91.0	92.1
80°	60.6	61.5	61.9	62.3	62.8	61.9	64.9	66.1	66.1	69.1	71.3
82.5°	43.5	44.0	45.2	45.6	45.7	46.6	46.8	47.7	48.8	50.1	52.8
85°	21.8	23.1	23.5	23.1	23.5	22.6	23.9	24.3	24.8	24.8	24.8
87.5°	9.3	10.2	10.6	11.7	12.0	13.0	13.3	12.8	13.0	14.3	13.1
90°	12.1	15.3	18.8	22.4	25.9	29.5	30.6	31.7	32.8	33.9	34.7
92.5°	37.2	39.1	41.2	43.1	45.2	47.2	48.1	48.9	49.8	50.7	51.0
95°	80.2	82.3	84.4	86.6	88.8	91.0	92.0	93.2	94.2	95.3	95.9
97.5°	134.5	136.0	137.6	139.2	140.8	142.4	143.7	144.9	146.1	147.4	148.0
100°	173.7	175.3	176.6	178.0	179.4	180.8	181.6	182.4	183.2	184.0	184.7
102.5°	215.4	216.8	218.6	220.4	222.2	224.0	224.9	225.7	226.5	227.3	227.6
105°	278.8	280.3	282.7	285.2	287.7	290.2	290.2	290.2	290.2	290.2	290.4
107.5°	353.7	354.3	355.3	356.3	357.3	358.2	359.1	360.0	360.9	361.7	362.0
110°	401.8	402.3	402.8	403.4	403.9	404.5	405.6	406.7	407.7	408.9	409.1



TEST NUMBER: P332175-930

CATALOG NUMBER: S123DIW-S775D1535U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	450.0	450.3	450.4	450.5	450.6	450.7	452.0	453.3	454.6	455.9	456.6
115°	525.8	525.9	525.4	524.8	524.3	523.7	524.0	524.3	524.6	524.8	524.8
117.5°	598.9	598.8	598.2	597.5	596.7	596.1	596.0	595.9	595.9	595.8	595.4
120°	649.5	649.7	648.3	646.9	645.6	644.2	643.9	643.7	643.4	643.1	642.7
122.5°	696.0	696.3	695.5	694.8	694.1	693.4	692.7	691.9	691.3	690.6	689.8
125°	768.0	768.1	767.6	767.0	766.5	766.0	764.8	763.8	762.6	761.6	760.4
127.5°	839.6	840.2	839.5	838.9	838.4	837.7	836.2	834.7	833.2	831.6	830.2
130°	886.6	887.2	886.4	885.6	884.8	883.9	882.9	881.7	880.7	879.6	878.1
132.5°	931.8	932.6	932.0	931.4	930.7	930.2	928.9	927.6	926.3	925.0	923.6
135°	998.7	999.4	999.1	998.8	998.6	998.3	997.2	996.1	995.0	993.9	993.1
137.5°	1061.5	1062.6	1063.3	1064.0	1064.7	1065.4	1064.3	1063.2	1062.0	1060.9	1059.7
140°	1105.8	1106.6	1106.9	1107.2	1107.4	1107.7	1107.4	1107.2	1106.9	1106.6	1105.5
142.5°	1146.1	1147.0	1147.5	1148.0	1148.5	1149.0	1148.8	1148.5	1148.2	1147.9	1147.0
145°	1205.8	1206.5	1207.3	1208.1	1208.9	1209.7	1209.5	1209.2	1208.9	1208.7	1207.9
147.5°	1262.7	1263.5	1264.3	1265.0	1265.8	1266.6	1266.6	1266.6	1266.6	1266.6	1265.8
150°	1299.3	1299.8	1300.3	1300.9	1301.4	1302.0	1302.0	1302.0	1302.0	1302.0	1301.1
152.5°	1331.5	1332.1	1332.4	1332.8	1333.1	1333.4	1333.9	1334.3	1334.7	1335.2	1334.7
155°	1378.2	1378.3	1378.6	1378.8	1379.2	1379.4	1380.5	1381.6	1382.7	1383.8	1383.4
157.5°	1419.2	1419.1	1419.4	1419.5	1419.8	1420.0	1421.1	1422.3	1423.4	1424.6	1424.4
160°	1444.9	1444.5	1444.5	1444.5	1444.5	1444.5	1445.9	1447.3	1448.7	1450.0	1450.2
162.5°	1467.6	1467.3	1467.5	1467.8	1467.9	1468.2	1469.6	1470.9	1472.3	1473.7	1473.5
165°	1497.9	1497.5	1497.5	1497.5	1497.5	1497.5	1499.1	1500.7	1502.4	1504.0	1503.9
167.5°	1521.1	1520.7	1520.9	1521.1	1521.3	1521.5	1523.2	1524.9	1526.6	1528.3	1528.3
170°	1534.9	1534.3	1534.3	1534.3	1534.3	1534.3	1536.3	1538.1	1540.1	1542.0	1542.0
172.5°	1545.7	1545.2	1545.2	1545.2	1545.2	1545.2	1546.9	1548.5	1550.2	1551.9	1551.8
175°	1557.0	1556.5	1556.5	1556.5	1556.5	1556.5	1558.1	1559.7	1561.4	1563.0	1562.8
177.5°	1562.5	1562.1	1562.1	1562.1	1562.1	1562.1	1563.4	1564.7	1566.0	1567.3	1567.2
180°	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0



TEST NUMBER: P332175-930

CATALOG NUMBER: S123DIW-S775D1535U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9
2.5°	842.4	842.0	844.4	842.7	844.4	842.0	842.4	844.7	845.5	845.8	845.8
5°	784.1	785.4	781.1	781.1	781.1	785.4	784.1	786.6	788.8	790.5	793.0
7.5°	732.1	730.3	730.4	728.1	730.4	730.3	732.1	734.3	736.9	740.7	744.2
10°	700.4	697.9	697.0	697.4	697.0	697.9	700.4	705.6	707.3	710.7	714.5
12.5°	674.1	673.6	668.0	668.1	668.0	673.6	674.1	675.5	679.2	686.4	691.0
15°	643.2	635.1	634.2	636.8	634.2	635.1	643.2	643.2	644.9	650.4	653.1
17.5°	612.2	608.0	608.2	606.9	608.2	608.0	612.2	612.9	614.2	618.8	622.2
20°	595.8	593.3	592.9	589.9	592.9	593.3	595.8	595.8	597.5	599.7	603.1
22.5°	580.8	580.0	580.2	576.9	580.2	580.0	580.8	581.9	583.6	585.0	587.4
25°	562.1	564.3	562.6	562.6	562.6	564.3	562.1	562.6	563.0	565.1	566.8
27.5°	549.5	549.4	548.5	548.5	548.5	549.4	549.5	548.5	548.0	547.2	546.8
30°	540.0	539.5	540.4	540.4	540.4	539.5	540.0	538.3	537.4	537.0	535.2
32.5°	530.4	531.0	531.2	531.5	531.2	531.0	530.4	528.3	526.8	525.7	524.3
35°	515.6	516.0	517.3	516.5	517.3	516.0	515.6	513.1	511.4	508.7	506.6
37.5°	495.6	497.6	497.2	497.8	497.2	497.6	495.6	494.9	493.2	491.2	488.7
40°	480.6	481.9	481.4	481.4	481.4	481.9	480.6	480.2	478.5	477.2	475.1
42.5°	465.2	466.2	465.0	464.4	465.0	466.2	465.2	464.5	463.4	461.1	458.7
45°	440.0	439.2	440.5	438.8	440.5	439.2	440.0	438.4	437.9	436.2	434.1
47.5°	411.9	412.7	413.1	414.3	413.1	412.7	411.9	412.1	409.7	408.6	408.0
50°	393.1	395.7	395.7	395.3	395.7	395.7	393.1	392.2	390.5	388.8	388.8
52.5°	374.6	375.9	377.6	377.5	377.6	375.9	374.6	373.2	371.5	369.0	368.4
55°	346.2	347.0	347.9	348.3	347.9	347.0	346.2	342.8	341.4	340.1	338.0
57.5°	316.6	316.3	318.3	318.9	318.3	316.3	316.6	313.6	311.6	307.7	307.1
60°	295.8	295.8	299.2	300.5	299.2	295.8	295.8	292.4	289.3	286.8	286.0
62.5°	273.6	275.0	278.3	276.5	278.3	275.0	273.6	269.9	267.5	264.3	262.0
65°	241.2	244.6	244.2	245.8	244.2	244.6	241.2	239.0	234.3	231.3	228.8
67.5°	207.2	209.4	212.5	212.7	212.5	209.4	207.2	203.8	200.8	197.6	194.5
70°	184.4	186.5	188.3	189.5	188.3	186.5	184.4	181.0	177.6	175.5	172.0
72.5°	162.2	163.3	167.4	165.6	167.4	163.3	162.2	158.1	155.4	153.6	149.9
75°	127.2	130.2	132.7	131.4	132.7	130.2	127.2	124.2	122.1	119.5	116.1
77.5°	94.1	97.0	98.2	97.2	98.2	97.0	94.1	92.1	91.0	85.9	85.6
80°	74.3	73.9	76.4	76.0	76.4	73.9	74.3	71.3	69.1	66.1	66.1
82.5°	54.5	54.1	55.2	55.5	55.2	54.1	54.5	52.8	50.1	48.8	47.7
85°	26.5	27.7	26.0	25.6	26.0	27.7	26.5	24.8	24.8	24.8	24.3
87.5°	13.2	13.3	13.0	12.8	13.0	13.3	13.2	13.1	14.3	13.0	12.8
90°	35.2	35.8	36.4	36.9	36.4	35.8	35.2	34.7	33.9	32.8	31.7
92.5°	50.6	50.3	50.0	49.7	50.0	50.3	50.6	51.0	50.7	49.8	48.9
95°	95.9	95.9	95.9	95.9	95.9	95.9	95.9	95.9	95.3	94.2	93.2
97.5°	147.9	147.7	147.7	147.6	147.7	147.7	147.9	148.0	147.4	146.1	144.9
100°	185.2	185.8	186.3	186.9	186.3	185.8	185.2	184.7	184.0	183.2	182.4
102.5°	227.6	227.4	227.3	227.2	227.3	227.4	227.6	227.6	227.3	226.5	225.7
105°	291.0	291.6	292.0	292.6	292.0	291.6	291.0	290.4	290.2	290.2	290.2
107.5°	361.7	361.3	361.0	360.7	361.0	361.3	361.7	362.0	361.7	360.9	360.0
110°	408.5	408.1	407.5	406.9	407.5	408.1	408.5	409.1	408.9	407.7	406.7



TEST NUMBER: P332175-930

CATALOG NUMBER: S123DIW-S775D1535U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	456.5	456.3	456.2	456.1	456.2	456.3	456.5	456.6	455.9	454.6	453.3
115°	524.6	524.3	524.0	523.7	524.0	524.3	524.6	524.8	524.8	524.6	524.3
117.5°	594.6	593.9	593.1	592.3	593.1	593.9	594.6	595.4	595.8	595.9	595.9
120°	642.2	641.6	641.1	640.5	641.1	641.6	642.2	642.7	643.1	643.4	643.7
122.5°	689.1	688.3	687.5	686.7	687.5	688.3	689.1	689.8	690.6	691.3	691.9
125°	759.4	758.3	757.2	756.1	757.2	758.3	759.4	760.4	761.6	762.6	763.8
127.5°	829.0	827.7	826.5	825.2	826.5	827.7	829.0	830.2	831.6	833.2	834.7
130°	876.2	874.2	872.4	870.4	872.4	874.2	876.2	878.1	879.6	880.7	881.7
132.5°	922.1	920.6	919.1	917.6	919.1	920.6	922.1	923.6	925.0	926.3	927.6
135°	992.5	992.0	991.5	990.9	991.5	992.0	992.5	993.1	993.9	995.0	996.1
137.5°	1058.7	1057.7	1056.6	1055.6	1056.6	1057.7	1058.7	1059.7	1060.9	1062.0	1063.2
140°	1103.6	1101.7	1099.8	1097.9	1099.8	1101.7	1103.6	1105.5	1106.6	1106.9	1107.2
142.5°	1145.6	1144.1	1142.6	1141.2	1142.6	1144.1	1145.6	1147.0	1147.9	1148.2	1148.5
145°	1206.9	1205.8	1204.7	1203.6	1204.7	1205.8	1206.9	1207.9	1208.7	1208.9	1209.2
147.5°	1264.1	1262.5	1260.8	1259.1	1260.8	1262.5	1264.1	1265.8	1266.6	1266.6	1266.6
150°	1299.5	1297.9	1296.2	1294.6	1296.2	1297.9	1299.5	1301.1	1302.0	1302.0	1302.0
152.5°	1333.3	1331.9	1330.4	1329.0	1330.4	1331.9	1333.3	1334.7	1335.2	1334.7	1334.3
155°	1381.4	1379.6	1377.6	1375.7	1377.6	1379.6	1381.4	1383.4	1383.8	1382.7	1381.6
157.5°	1422.9	1421.3	1419.8	1418.3	1419.8	1421.3	1422.9	1424.4	1424.6	1423.4	1422.3
160°	1449.1	1448.0	1446.9	1445.8	1446.9	1448.0	1449.1	1450.2	1450.0	1448.7	1447.3
162.5°	1471.7	1470.0	1468.2	1466.5	1468.2	1470.0	1471.7	1473.5	1473.7	1472.3	1470.9
165°	1501.9	1500.1	1498.1	1496.2	1498.1	1500.1	1501.9	1503.9	1504.0	1502.4	1500.7
167.5°	1526.6	1524.9	1523.2	1521.5	1523.2	1524.9	1526.6	1528.3	1528.3	1526.6	1524.9
170°	1540.1	1538.1	1536.3	1534.3	1536.3	1538.1	1540.1	1542.0	1542.0	1540.1	1538.1
172.5°	1549.9	1548.0	1546.1	1544.2	1546.1	1548.0	1549.9	1551.8	1551.9	1550.2	1548.5
175°	1561.0	1559.0	1557.1	1555.3	1557.1	1559.0	1561.0	1562.8	1563.0	1561.4	1559.7
177.5°	1565.7	1564.2	1562.7	1561.1	1562.7	1564.2	1565.7	1567.2	1567.3	1566.0	1564.7
180°	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0



TEST NUMBER: P332175-930

CATALOG NUMBER: S123DIW-S775D1535U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9
2.5°	844.7	844.7	851.3	855.3	860.5	863.9	866.3	868.7	872.8	878.2	884.4
5°	796.5	798.2	807.6	816.9	825.9	833.6	840.0	847.7	857.0	868.6	881.4
7.5°	749.7	756.3	765.7	777.1	789.7	800.9	812.3	824.9	838.1	855.1	873.0
10°	719.7	726.9	738.4	752.9	766.1	779.3	793.4	807.1	823.8	843.8	866.9
12.5°	693.3	700.3	712.1	728.0	740.5	755.1	771.3	789.0	807.7	831.8	858.0
15°	656.9	665.0	679.5	687.2	706.4	723.9	738.8	764.4	788.3	813.1	843.4
17.5°	627.0	631.5	643.3	657.5	671.9	691.5	711.1	732.5	756.3	786.5	824.4
20°	606.5	610.3	623.1	638.1	653.5	671.4	688.9	710.2	737.1	769.2	810.1
22.5°	591.2	595.3	603.7	619.6	634.0	648.9	666.3	691.8	720.4	751.7	796.1
25°	568.9	571.5	577.1	589.9	602.7	619.3	634.7	658.6	688.0	724.7	769.2
27.5°	547.9	550.3	555.0	564.2	576.1	589.6	606.3	626.6	656.6	696.4	743.6
30°	535.2	535.7	540.0	548.5	558.7	569.8	585.1	608.2	636.4	676.9	726.4
32.5°	524.3	522.7	525.6	532.1	542.0	553.1	565.7	588.4	615.6	655.4	706.3
35°	505.8	504.9	503.7	509.2	517.7	526.3	537.4	554.5	585.1	622.3	675.6
37.5°	486.9	484.9	482.6	485.1	491.8	500.7	510.3	525.5	552.0	592.9	643.9
40°	473.0	471.2	469.9	469.0	475.1	483.6	490.8	505.3	530.1	568.9	619.3
42.5°	457.5	456.6	454.9	453.7	458.7	465.1	472.7	485.6	510.3	546.7	594.4
45°	432.8	431.9	431.1	430.2	433.3	439.2	445.2	454.5	475.9	511.4	554.5
47.5°	405.2	404.1	404.5	403.1	406.0	410.0	414.2	424.3	444.7	473.4	504.8
50°	385.4	385.0	385.0	385.0	385.9	390.5	394.4	402.1	420.9	449.5	472.1
52.5°	366.6	364.8	364.8	365.5	367.0	370.1	372.5	380.9	397.3	420.8	441.3
55°	337.2	333.8	332.9	333.8	335.1	337.6	340.1	347.0	361.1	378.6	390.5
57.5°	304.6	302.7	301.6	301.7	302.5	304.5	306.5	313.9	325.0	334.1	341.8
60°	281.7	282.6	278.8	279.6	279.6	281.3	284.3	288.9	298.3	304.8	312.4
62.5°	260.2	259.0	257.9	256.7	256.7	257.4	261.4	265.1	273.0	276.4	282.4
65°	226.7	226.7	224.0	224.9	225.3	222.4	224.5	228.8	233.9	235.2	240.8
67.5°	192.7	191.5	190.0	188.7	188.7	188.5	189.6	191.8	195.6	196.0	200.2
70°	169.4	168.6	168.2	166.9	165.2	167.3	166.0	168.2	170.3	170.7	173.3
72.5°	146.9	146.0	145.3	144.0	143.3	143.1	143.2	145.6	147.1	146.5	149.4
75°	114.8	114.0	113.1	111.0	111.0	109.7	110.1	111.9	113.6	112.3	114.8
77.5°	84.3	81.7	81.5	82.1	80.6	81.0	80.4	80.1	81.0	81.0	83.3
80°	64.9	61.9	62.8	62.3	61.9	61.5	60.6	61.1	61.5	61.9	63.2
82.5°	46.8	46.6	45.7	45.6	45.2	44.0	43.5	44.3	44.8	44.5	45.4
85°	23.9	22.6	23.5	23.1	23.5	23.1	21.8	21.8	22.6	22.2	23.1
87.5°	13.3	13.0	12.0	11.7	10.6	10.2	9.3	9.0	8.9	8.3	8.5
90°	30.6	29.5	25.9	22.4	18.8	15.3	12.1	9.5	6.7	4.0	1.2
92.5°	48.1	47.2	45.2	43.1	41.2	39.1	37.2	35.3	33.4	31.6	29.8
95°	92.0	91.0	88.8	86.6	84.4	82.3	80.2	78.3	76.4	74.4	72.6
97.5°	143.7	142.4	140.8	139.2	137.6	136.0	134.5	133.1	131.7	130.3	128.8
100°	181.6	180.8	179.4	178.0	176.6	175.3	173.7	172.1	170.5	168.8	167.2
102.5°	224.9	224.0	222.2	220.4	218.6	216.8	215.4	214.4	213.4	212.5	211.5
105°	290.2	290.2	287.7	285.2	282.7	280.3	278.8	278.3	277.7	277.2	276.6
107.5°	359.1	358.2	357.3	356.3	355.3	354.3	353.7	353.4	353.0	352.7	352.4
110°	405.6	404.5	403.9	403.4	402.8	402.3	401.8	401.2	400.6	400.1	399.6



TEST NUMBER: P332175-930

CATALOG NUMBER: S123DIW-S775D1535U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	452.0	450.7	450.6	450.5	450.4	450.3	450.0	449.7	449.4	449.1	448.7
115°	524.0	523.7	524.3	524.8	525.4	525.9	525.8	525.0	524.2	523.3	522.5
117.5°	596.0	596.1	596.7	597.5	598.2	598.8	598.9	598.4	597.9	597.3	596.8
120°	643.9	644.2	645.6	646.9	648.3	649.7	649.5	647.9	646.3	644.7	643.0
122.5°	692.7	693.4	694.1	694.8	695.5	696.3	696.0	694.8	693.6	692.4	691.2
125°	764.8	766.0	766.5	767.0	767.6	768.1	768.0	767.2	766.4	765.5	764.7
127.5°	836.2	837.7	838.4	838.9	839.5	840.2	839.6	837.8	836.1	834.3	832.6
130°	882.9	883.9	884.8	885.6	886.4	887.2	886.6	884.4	882.2	880.0	877.8
132.5°	928.9	930.2	930.7	931.4	932.0	932.6	931.8	929.6	927.4	925.2	923.1
135°	997.2	998.3	998.6	998.8	999.1	999.4	998.7	997.0	995.4	993.8	992.1
137.5°	1064.3	1065.4	1064.7	1064.0	1063.3	1062.6	1061.5	1060.2	1058.8	1057.4	1056.1
140°	1107.4	1107.7	1107.4	1107.2	1106.9	1106.6	1105.8	1104.4	1103.1	1101.7	1100.3
142.5°	1148.8	1149.0	1148.5	1148.0	1147.5	1147.0	1146.1	1144.8	1143.4	1142.0	1140.7
145°	1209.5	1209.7	1208.9	1208.1	1207.3	1206.5	1205.8	1205.3	1204.7	1204.2	1203.6
147.5°	1266.6	1266.6	1265.8	1265.0	1264.3	1263.5	1262.7	1261.7	1260.6	1259.6	1258.7
150°	1302.0	1302.0	1301.4	1300.9	1300.3	1299.8	1299.3	1298.7	1298.1	1297.6	1297.1
152.5°	1333.9	1333.4	1333.1	1332.8	1332.4	1332.1	1331.5	1330.8	1330.1	1329.3	1328.5
155°	1380.5	1379.4	1379.2	1378.8	1378.6	1378.3	1378.2	1378.2	1378.2	1378.2	1378.2
157.5°	1421.1	1420.0	1419.8	1419.5	1419.4	1419.1	1419.2	1419.5	1419.8	1420.2	1420.5
160°	1445.9	1444.5	1444.5	1444.5	1444.5	1444.5	1444.9	1445.4	1445.9	1446.5	1447.1
162.5°	1469.6	1468.2	1467.9	1467.8	1467.5	1467.3	1467.6	1468.4	1469.1	1469.9	1470.6
165°	1499.1	1497.5	1497.5	1497.5	1497.5	1497.5	1497.9	1498.7	1499.5	1500.3	1501.1
167.5°	1523.2	1521.5	1521.3	1521.1	1520.9	1520.7	1521.1	1522.2	1523.3	1524.4	1525.5
170°	1536.3	1534.3	1534.3	1534.3	1534.3	1534.3	1534.9	1535.9	1537.1	1538.1	1539.2
172.5°	1546.9	1545.2	1545.2	1545.2	1545.2	1545.2	1545.7	1546.8	1547.8	1549.0	1550.0
175°	1558.1	1556.5	1556.5	1556.5	1556.5	1556.5	1557.0	1558.1	1559.2	1560.3	1561.4
177.5°	1563.4	1562.1	1562.1	1562.1	1562.1	1562.1	1562.5	1563.4	1564.3	1565.2	1566.0
180°	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0



TEST NUMBER: P332175-930

CATALOG NUMBER: S123DIW-S775D1535U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9
2.5°	886.4	888.1	894.0	898.1	902.8	905.6	908.2	910.4	913.1	913.7	923.7
5°	890.4	898.9	913.9	925.0	938.6	953.5	963.8	968.5	980.8	991.1	1011.5
7.5°	889.2	907.4	929.9	953.3	978.4	1001.7	1021.8	1045.7	1062.7	1088.3	1113.4
10°	888.2	912.6	941.6	971.4	1006.5	1038.9	1067.9	1100.3	1127.2	1162.7	1192.9
12.5°	885.2	914.6	954.9	990.3	1032.7	1077.5	1120.5	1162.1	1185.9	1245.0	1272.8
15°	877.6	912.6	963.0	1016.7	1075.1	1128.1	1182.8	1226.3	1296.7	1348.3	1381.2
17.5°	863.1	912.1	971.8	1036.7	1107.7	1177.5	1239.4	1305.5	1380.1	1442.7	1509.3
20°	856.2	910.0	976.6	1048.3	1122.1	1201.1	1271.5	1350.9	1432.4	1493.9	1579.2
22.5°	843.6	904.5	976.2	1056.1	1135.1	1216.8	1299.2	1379.2	1473.4	1558.1	1639.3
25°	822.9	891.2	965.5	1054.7	1147.3	1229.2	1327.9	1434.1	1532.3	1641.1	1722.2
27.5°	801.2	874.2	948.6	1031.5	1131.1	1228.4	1352.4	1472.5	1592.6	1686.5	1746.5
30°	784.5	855.3	932.2	1015.9	1114.4	1230.1	1368.8	1499.8	1616.8	1697.5	1731.2
32.5°	766.4	838.3	906.2	994.0	1099.1	1229.1	1379.1	1515.9	1618.2	1671.9	1665.3
35°	738.0	798.2	864.3	948.8	1072.6	1221.6	1385.0	1517.4	1580.1	1568.6	1481.5
37.5°	697.0	747.6	812.8	905.3	1041.9	1205.7	1373.1	1472.3	1468.3	1374.4	1248.3
40°	671.4	714.5	777.2	874.6	1018.0	1195.6	1354.3	1418.8	1364.2	1233.1	1082.0
42.5°	638.0	677.6	740.4	840.4	991.6	1174.7	1318.4	1337.2	1230.3	1079.5	940.9
45°	586.0	621.0	685.9	789.2	952.3	1129.4	1230.9	1185.3	1041.5	885.7	780.2
47.5°	530.3	566.6	629.1	735.2	895.2	1061.2	1109.5	1012.4	864.7	738.4	641.6
50°	495.1	530.1	591.2	698.3	856.6	1005.2	1025.2	899.8	764.0	653.1	573.6
52.5°	459.6	492.5	552.5	660.1	811.5	940.3	927.9	800.1	675.2	580.7	518.4
55°	406.8	437.9	495.1	595.8	733.7	835.7	790.9	668.9	565.6	492.1	444.7
57.5°	359.5	389.4	438.7	529.7	649.5	719.7	662.6	559.7	477.6	421.1	385.8
60°	327.3	353.8	400.8	485.3	589.5	642.8	586.4	495.5	426.4	381.2	349.6
62.5°	297.0	320.0	363.5	440.3	530.7	575.5	518.5	441.6	382.7	342.6	315.8
65°	250.9	271.9	310.3	370.1	444.3	474.2	425.1	362.8	317.2	287.2	269.3
67.5°	209.0	226.7	259.9	307.0	361.6	383.4	346.0	297.7	263.3	239.4	225.1
70°	181.0	196.3	222.4	262.9	312.4	329.1	294.1	254.4	229.2	210.0	196.7
72.5°	157.4	168.7	192.3	223.6	265.0	278.2	253.8	218.9	195.4	181.0	170.5
75°	119.9	129.3	144.7	169.9	198.4	206.2	187.8	166.0	150.3	140.0	131.9
77.5°	86.5	93.4	104.5	120.0	139.8	146.8	135.1	120.6	109.1	102.2	97.7
80°	65.3	70.8	80.2	93.0	105.0	108.8	102.0	90.9	82.8	79.0	75.1
82.5°	48.3	51.4	57.0	65.7	73.9	78.4	72.6	66.0	61.6	58.1	56.7
85°	24.3	26.0	28.6	32.0	37.1	38.8	36.7	35.0	32.4	30.3	30.3
87.5°	9.7	10.2	11.8	13.0	15.0	16.7	17.1	17.1	17.5	17.4	17.3
90°	4.0	6.7	9.5	12.1	15.3	18.8	22.4	25.9	29.5	30.6	31.7
92.5°	31.6	33.4	35.3	37.2	39.1	41.2	43.1	45.2	47.2	48.1	48.9
95°	74.4	76.4	78.3	80.2	82.3	84.4	86.6	88.8	91.0	92.0	93.2
97.5°	130.3	131.7	133.1	134.5	136.0	137.6	139.2	140.8	142.4	143.7	144.9
100°	168.8	170.5	172.1	173.7	175.3	176.6	178.0	179.4	180.8	181.6	182.4
102.5°	212.5	213.4	214.4	215.4	216.8	218.6	220.4	222.2	224.0	224.9	225.7
105°	277.2	277.7	278.3	278.8	280.3	282.7	285.2	287.7	290.2	290.2	290.2
107.5°	352.7	353.0	353.4	353.7	354.3	355.3	356.3	357.3	358.2	359.1	360.0
110°	400.1	400.6	401.2	401.8	402.3	402.8	403.4	403.9	404.5	405.6	406.7





TEST NUMBER: P332175-930

CATALOG NUMBER: S123DIW-S775D1535U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	449.1	449.4	449.7	450.0	450.3	450.4	450.5	450.6	450.7	452.0	453.3
115°	523.3	524.2	525.0	525.8	525.9	525.4	524.8	524.3	523.7	524.0	524.3
117.5°	597.3	597.9	598.4	598.9	598.8	598.2	597.5	596.7	596.1	596.0	595.9
120°	644.7	646.3	647.9	649.5	649.7	648.3	646.9	645.6	644.2	643.9	643.7
122.5°	692.4	693.6	694.8	696.0	696.3	695.5	694.8	694.1	693.4	692.7	691.9
125°	765.5	766.4	767.2	768.0	768.1	767.6	767.0	766.5	766.0	764.8	763.8
127.5°	834.3	836.1	837.8	839.6	840.2	839.5	838.9	838.4	837.7	836.2	834.7
130°	880.0	882.2	884.4	886.6	887.2	886.4	885.6	884.8	883.9	882.9	881.7
132.5°	925.2	927.4	929.6	931.8	932.6	932.0	931.4	930.7	930.2	928.9	927.6
135°	993.8	995.4	997.0	998.7	999.4	999.1	998.8	998.6	998.3	997.2	996.1
137.5°	1057.4	1058.8	1060.2	1061.5	1062.6	1063.3	1064.0	1064.7	1065.4	1064.3	1063.2
140°	1101.7	1103.1	1104.4	1105.8	1106.6	1106.9	1107.2	1107.4	1107.7	1107.4	1107.2
142.5°	1142.0	1143.4	1144.8	1146.1	1147.0	1147.5	1148.0	1148.5	1149.0	1148.8	1148.5
145°	1204.2	1204.7	1205.3	1205.8	1206.5	1207.3	1208.1	1208.9	1209.7	1209.5	1209.2
147.5°	1259.6	1260.6	1261.7	1262.7	1263.5	1264.3	1265.0	1265.8	1266.6	1266.6	1266.6
150°	1297.6	1298.1	1298.7	1299.3	1299.8	1300.3	1300.9	1301.4	1302.0	1302.0	1302.0
152.5°	1329.3	1330.1	1330.8	1331.5	1332.1	1332.4	1332.8	1333.1	1333.4	1333.9	1334.3
155°	1378.2	1378.2	1378.2	1378.2	1378.3	1378.6	1378.8	1379.2	1379.4	1380.5	1381.6
157.5°	1420.2	1419.8	1419.5	1419.2	1419.1	1419.4	1419.5	1419.8	1420.0	1421.1	1422.3
160°	1446.5	1445.9	1445.4	1444.9	1444.5	1444.5	1444.5	1444.5	1444.5	1445.9	1447.3
162.5°	1469.9	1469.1	1468.4	1467.6	1467.3	1467.5	1467.8	1467.9	1468.2	1469.6	1470.9
165°	1500.3	1499.5	1498.7	1497.9	1497.5	1497.5	1497.5	1497.5	1497.5	1499.1	1500.7
167.5°	1524.4	1523.3	1522.2	1521.1	1520.7	1520.9	1521.1	1521.3	1521.5	1523.2	1524.9
170°	1538.1	1537.1	1535.9	1534.9	1534.3	1534.3	1534.3	1534.3	1534.3	1536.3	1538.1
172.5°	1549.0	1547.8	1546.8	1545.7	1545.2	1545.2	1545.2	1545.2	1545.2	1546.9	1548.5
175°	1560.3	1559.2	1558.1	1557.0	1556.5	1556.5	1556.5	1556.5	1556.5	1558.1	1559.7
177.5°	1565.2	1564.3	1563.4	1562.5	1562.1	1562.1	1562.1	1562.1	1562.1	1563.4	1564.7
180°	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0



TEST NUMBER: P332175-930

CATALOG NUMBER: S123DIW-S775D1535U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	880.9	880.9	880.9	880.9	880.9	880.9	880.9
2.5°	927.1	927.4	931.2	933.9	932.5	934.3	934.9
5°	1012.8	1028.3	1036.3	1042.3	1042.8	1043.2	1046.6
7.5°	1134.5	1151.0	1163.0	1181.3	1186.7	1192.9	1191.2
10°	1223.3	1247.6	1268.5	1279.6	1291.6	1309.0	1295.0
12.5°	1306.3	1349.4	1381.2	1398.5	1409.7	1413.2	1406.3
15°	1443.1	1499.4	1529.7	1528.8	1567.3	1584.0	1557.9
17.5°	1568.6	1620.6	1662.2	1683.6	1715.6	1722.6	1719.4
20°	1645.4	1702.2	1734.6	1771.3	1788.0	1802.9	1805.5
22.5°	1711.6	1762.6	1797.4	1828.0	1841.9	1849.0	1853.3
25°	1779.9	1820.0	1840.9	1851.5	1855.4	1854.6	1849.0
27.5°	1775.2	1778.2	1755.2	1732.6	1712.4	1689.5	1681.7
30°	1729.1	1693.2	1629.2	1592.9	1539.5	1497.3	1514.3
32.5°	1607.9	1536.5	1464.6	1385.3	1319.6	1301.0	1282.1
35°	1372.2	1246.8	1173.4	1087.9	1053.9	1019.7	996.2
37.5°	1110.2	1013.1	926.0	870.2	836.0	814.4	802.7
40°	959.9	872.5	800.7	755.5	729.4	705.2	701.7
42.5°	840.1	758.7	704.7	668.7	643.8	633.4	625.9
45°	688.0	631.3	595.0	569.4	552.8	546.3	537.8
47.5°	582.4	542.3	515.0	497.6	485.0	480.3	479.6
50°	523.3	490.0	469.9	456.2	446.5	444.7	437.9
52.5°	478.9	450.0	434.4	422.5	415.4	410.6	408.5
55°	415.7	396.5	382.5	375.6	370.1	365.3	365.3
57.5°	363.7	347.7	338.3	332.6	330.8	327.5	325.4
60°	331.7	318.0	310.7	305.6	302.2	302.6	298.8
62.5°	300.2	291.4	284.5	279.3	275.2	275.3	275.6
65°	255.7	248.8	243.7	242.0	239.5	236.4	237.3
67.5°	216.6	210.3	206.3	203.3	202.5	200.9	203.3
70°	188.7	183.9	181.0	178.4	177.6	178.0	180.1
72.5°	163.1	159.7	157.8	156.5	154.7	154.7	156.2
75°	128.1	125.5	123.8	122.5	122.1	122.1	122.1
77.5°	94.1	93.5	92.7	90.8	90.9	91.4	91.5
80°	74.3	73.0	72.6	71.7	70.4	69.5	71.7
82.5°	55.5	54.2	53.8	53.6	51.6	51.4	53.2
85°	29.8	28.6	29.0	28.6	28.6	28.2	28.2
87.5°	17.1	17.0	16.9	17.3	17.0	16.8	17.6
90°	32.8	33.9	34.7	35.2	35.8	36.4	36.9
92.5°	49.8	50.7	51.0	50.6	50.3	50.0	49.7
95°	94.2	95.3	95.9	95.9	95.9	95.9	95.9
97.5°	146.1	147.4	148.0	147.9	147.7	147.7	147.6
100°	183.2	184.0	184.7	185.2	185.8	186.3	186.9
102.5°	226.5	227.3	227.6	227.6	227.4	227.3	227.2
105°	290.2	290.2	290.4	291.0	291.6	292.0	292.6
107.5°	360.9	361.7	362.0	361.7	361.3	361.0	360.7
110°	407.7	408.9	409.1	408.5	408.1	407.5	406.9



TEST NUMBER: P332175-930

CATALOG NUMBER: S123DIW-S775D1535U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	454.6	455.9	456.6	456.5	456.3	456.2	456.1
115°	524.6	524.8	524.8	524.6	524.3	524.0	523.7
117.5°	595.9	595.8	595.4	594.6	593.9	593.1	592.3
120°	643.4	643.1	642.7	642.2	641.6	641.1	640.5
122.5°	691.3	690.6	689.8	689.1	688.3	687.5	686.7
125°	762.6	761.6	760.4	759.4	758.3	757.2	756.1
127.5°	833.2	831.6	830.2	829.0	827.7	826.5	825.2
130°	880.7	879.6	878.1	876.2	874.2	872.4	870.4
132.5°	926.3	925.0	923.6	922.1	920.6	919.1	917.6
135°	995.0	993.9	993.1	992.5	992.0	991.5	990.9
137.5°	1062.0	1060.9	1059.7	1058.7	1057.7	1056.6	1055.6
140°	1106.9	1106.6	1105.5	1103.6	1101.7	1099.8	1097.9
142.5°	1148.2	1147.9	1147.0	1145.6	1144.1	1142.6	1141.2
145°	1208.9	1208.7	1207.9	1206.9	1205.8	1204.7	1203.6
147.5°	1266.6	1266.6	1265.8	1264.1	1262.5	1260.8	1259.1
150°	1302.0	1302.0	1301.1	1299.5	1297.9	1296.2	1294.6
152.5°	1334.7	1335.2	1334.7	1333.3	1331.9	1330.4	1329.0
155°	1382.7	1383.8	1383.4	1381.4	1379.6	1377.6	1375.7
157.5°	1423.4	1424.6	1424.4	1422.9	1421.3	1419.8	1418.3
160°	1448.7	1450.0	1450.2	1449.1	1448.0	1446.9	1445.8
162.5°	1472.3	1473.7	1473.5	1471.7	1470.0	1468.2	1466.5
165°	1502.4	1504.0	1503.9	1501.9	1500.1	1498.1	1496.2
167.5°	1526.6	1528.3	1528.3	1526.6	1524.9	1523.2	1521.5
170°	1540.1	1542.0	1542.0	1540.1	1538.1	1536.3	1534.3
172.5°	1550.2	1551.9	1551.8	1549.9	1548.0	1546.1	1544.2
175°	1561.4	1563.0	1562.8	1561.0	1559.0	1557.1	1555.3
177.5°	1566.0	1567.3	1567.2	1565.7	1564.2	1562.7	1561.1
180°	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0

(END OF REPORT)